

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332534-840

Luminaire Tested: **S124DIP-S350D1205U840-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332534-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIP-S350D1205U840-4F0-1E-UDD-F4
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1205 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5878.2 lumens
Efficiency: N/A
Efficacy: 139.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 42.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332534-840

CATALOG NUMBER: S124DIP-S350D1205U840-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P332534-840

CATALOG NUMBER: S124DIP-S350D1205U840-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	70	70	70	51	51	51	34	34	34	26
1	92	88	84	81	82	79	76	73	61	59	57	45	44	43	30	29	29	22
2	84	77	71	66	75	69	64	60	54	50	47	39	37	35	26	25	24	18
3	77	68	61	55	68	61	55	50	47	43	40	35	32	30	23	22	21	16
4	70	60	52	46	62	54	47	42	42	37	34	31	28	26	21	19	18	13
5	64	53	45	39	57	48	41	36	37	33	29	28	25	22	19	17	15	12
6	59	47	40	34	52	43	36	31	33	29	25	25	22	19	17	15	13	10
7	54	43	35	30	48	38	32	27	30	25	22	23	19	17	16	13	12	9
8	50	39	31	26	45	35	28	24	27	23	19	21	17	15	14	12	11	8
9	47	35	28	23	42	32	25	21	25	20	17	19	16	13	13	11	10	7
10	44	32	25	20	39	29	23	19	23	18	15	17	14	12	12	10	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4816	4816	4816
5°	4830	4772	4807
10°	4800	4733	4757
15°	4741	4667	4679
20°	4665	4582	4587
25°	4577	4488	4475
30°	4470	4376	4336
35°	4357	4258	4202
40°	4241	4126	4051
45°	4120	3995	3919
50°	3986	3878	3758
55°	3842	3727	3606
60°	3696	3559	3450
65°	3534	3396	3261
70°	3352	3182	3059
75°	3072	2923	2848
80°	2734	2627	2552
85°	2399	2297	2251



TEST NUMBER: P332534-840

CATALOG NUMBER: S124DIP-S350D1205U840-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	56.2	1.0
10°-20°	158.3	2.7
20°-30°	233.0	4.0
30°-40°	270.8	4.6
40°-50°	270.9	4.6
50°-60°	236.9	4.0
60°-70°	175.9	3.0
70°-80°	100.0	1.7
80°-90°	32.1	0.5
90°-100°	431.4	7.3
100°-110°	897.9	15.3
110°-120°	804.2	13.7
120°-130°	676.5	11.5
130°-140°	564.1	9.6
140°-150°	430.9	7.3
150°-160°	302.9	5.2
160°-170°	178.2	3.0
170°-180°	58.0	1.0
0°-30°	447.4	7.6
0°-40°	718.3	12.2
0°-60°	1226.1	20.9
0°-90°	1534.1	26.1
90°-120°	2133.5	36.3
90°-150°	3805.0	64.7
90°-180°	4344.0	73.9
0°-180°	5878.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	596	596	596	596	596	
5°	596	594	589	594	593	57
15°	567	565	558	561	560	160
25°	514	510	504	504	502	236
35°	442	439	432	429	426	276
45°	361	357	350	345	343	278
55°	273	271	265	259	256	244
65°	185	182	178	173	171	183
75°	98	96	94	92	91	105
85°	26	26	25	25	24	28
90°	1	9	21	23	25	4
95°	39	122	956	474	286	43
105°	137	199	770	1658	1651	146
115°	242	303	686	1319	1585	240
125°	337	400	683	1122	1265	300
135°	400	476	677	996	1131	309
145°	461	528	674	840	924	289
155°	524	566	655	742	773	242
165°	572	589	628	665	675	161
175°	596	597	602	610	608	57
180°	597	597	597	597	597	



TEST NUMBER: P332534-840

CATALOG NUMBER: S124DIP-S350D1205U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5
2.5°	598.0	597.8	597.5	597.3	597.0	596.4	595.5	594.6	593.7	592.7	593.6
5°	596.0	595.6	595.2	594.8	594.4	593.6	592.4	591.3	590.1	588.9	590.1
7.5°	590.6	590.1	589.7	589.3	588.9	587.9	586.6	585.4	584.1	582.8	583.7
10°	585.5	585.1	584.7	584.3	583.9	583.0	581.6	580.2	578.9	577.4	578.2
12.5°	579.1	578.7	578.2	577.7	577.3	576.4	574.9	573.5	572.0	570.6	571.5
15°	567.3	566.9	566.5	566.1	565.7	564.7	563.1	561.5	559.9	558.4	559.0
17.5°	553.3	552.8	552.3	551.8	551.2	550.2	548.7	547.1	545.6	544.1	544.5
20°	543.0	542.5	542.0	541.4	540.9	539.9	538.3	536.6	535.0	533.4	533.8
22.5°	531.9	531.2	530.5	529.8	529.1	528.0	526.3	524.8	523.2	521.6	522.2
25°	513.8	513.1	512.4	511.6	510.9	509.8	508.3	506.8	505.3	503.8	503.9
27.5°	493.2	492.4	491.7	490.9	490.2	489.1	487.7	486.4	484.9	483.5	483.3
30°	479.5	478.6	477.8	476.9	476.1	474.9	473.5	472.1	470.8	469.4	469.0
32.5°	464.9	464.1	463.3	462.6	461.8	460.7	459.3	457.8	456.4	454.8	454.3
35°	442.1	441.4	440.7	439.9	439.2	438.1	436.6	435.0	433.6	432.1	431.4
37.5°	418.2	417.5	416.8	416.2	415.5	414.3	412.7	411.1	409.5	407.9	407.1
40°	402.4	401.6	400.8	399.9	399.1	397.9	396.3	394.7	393.0	391.5	390.4
42.5°	385.7	385.2	384.7	384.2	383.6	382.4	380.7	378.9	377.2	375.5	374.2
45°	360.9	360.1	359.4	358.7	357.9	356.7	355.0	353.3	351.6	349.9	348.7
47.5°	335.0	334.5	334.0	333.5	333.0	331.9	330.3	328.7	327.2	325.6	324.3
50°	317.4	317.0	316.6	316.1	315.7	314.8	313.3	311.7	310.2	308.8	307.3
52.5°	300.2	299.6	299.1	298.6	298.1	297.1	295.5	294.0	292.4	290.8	289.5
55°	273.0	272.7	272.3	272.0	271.7	270.7	269.2	267.8	266.3	264.8	263.6
57.5°	246.9	246.6	246.2	245.9	245.5	244.6	243.1	241.7	240.1	238.7	237.5
60°	228.9	228.4	227.9	227.3	226.8	225.9	224.5	223.1	221.8	220.4	219.4
62.5°	211.4	211.0	210.5	210.1	209.5	208.6	207.1	205.7	204.2	202.8	201.9
65°	185.0	184.5	183.9	183.4	182.9	182.1	181.0	180.0	178.8	177.8	176.7
67.5°	158.4	157.9	157.4	156.9	156.4	155.7	154.7	153.7	152.7	151.6	150.6
70°	142.0	141.2	140.5	139.8	139.0	138.1	137.3	136.5	135.6	134.8	133.9
72.5°	124.4	123.6	122.9	122.2	121.4	120.7	120.0	119.4	118.7	118.0	117.2
75°	98.5	98.0	97.5	96.8	96.3	95.8	95.3	94.7	94.2	93.7	93.3
77.5°	73.7	73.5	73.2	73.0	72.8	72.4	72.0	71.5	71.0	70.6	70.4
80°	58.8	58.5	58.2	57.9	57.6	57.3	57.1	56.9	56.7	56.5	56.1
82.5°	44.2	44.1	43.9	43.8	43.6	43.5	43.5	43.5	43.4	43.4	43.3
85°	25.9	25.9	25.9	25.9	25.9	25.8	25.4	25.2	25.0	24.8	24.8
87.5°	10.2	10.6	11.2	11.3	11.5	11.4	12.7	12.6	13.0	13.4	13.1
90°	1.2	3.5	7.1	8.2	9.4	9.4	16.5	16.5	18.8	21.1	20.0
92.5°	13.3	19.5	30.5	44.8	62.0	86.3	146.0	237.0	325.8	372.2	310.0
95°	38.7	42.2	54.0	69.3	97.4	146.7	248.7	441.2	721.6	956.3	983.4
97.5°	69.5	69.5	79.6	93.6	117.9	159.2	237.7	396.7	675.4	1007.3	1235.5
100°	89.2	89.2	97.4	111.5	133.8	171.4	240.5	373.1	612.6	943.4	1243.9
102.5°	108.0	109.9	117.1	130.3	151.6	187.3	249.9	366.6	570.3	863.6	1173.5
105°	137.3	140.8	146.7	160.8	181.9	215.9	272.3	369.6	533.9	769.8	1045.5
107.5°	169.7	172.0	177.9	192.9	213.1	246.7	298.3	387.0	527.4	717.2	942.3
110°	191.3	193.6	199.4	213.6	234.7	266.4	318.0	400.1	529.3	699.4	890.7



TEST NUMBER: P332534-840

CATALOG NUMBER: S124DIP-S350D1205U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	212.0	214.3	221.1	234.2	255.4	287.0	336.8	414.2	534.8	690.9	861.5
115°	241.8	245.3	253.5	265.2	287.5	319.2	366.1	436.6	545.6	686.5	834.4
117.5°	272.7	276.0	283.3	296.2	317.1	349.9	394.6	459.3	557.1	685.3	822.1
120°	293.4	295.7	304.0	316.8	336.8	369.6	414.2	475.2	565.6	685.3	815.6
122.5°	312.1	314.5	322.8	334.7	356.5	388.4	433.0	490.3	574.1	684.4	808.1
125°	336.8	341.4	348.5	361.4	383.7	416.6	458.8	512.8	586.7	683.0	795.6
127.5°	358.6	362.3	370.8	385.6	408.8	441.9	482.7	532.3	596.8	680.3	778.9
130°	370.8	375.5	384.9	402.5	424.7	458.8	498.8	544.5	604.3	679.4	768.6
132.5°	383.0	386.8	399.0	415.7	439.8	472.0	511.9	556.7	610.9	678.5	759.2
135°	400.1	404.9	416.6	436.6	461.2	491.7	530.4	572.7	620.8	677.1	745.2
137.5°	417.3	421.7	434.6	453.6	479.3	508.4	544.5	583.9	626.6	676.8	733.0
140°	429.5	433.0	446.0	465.9	490.5	518.7	553.9	591.4	631.4	675.9	726.4
142.5°	442.6	446.2	458.1	477.2	500.8	528.1	562.3	597.0	635.1	675.9	720.7
145°	461.2	464.7	476.5	492.8	515.1	541.0	571.5	603.2	637.2	673.6	711.1
147.5°	482.0	483.2	493.5	510.5	529.0	552.2	580.9	608.5	638.3	669.3	702.5
150°	495.2	496.3	505.7	519.9	537.5	559.8	585.5	611.4	638.3	666.5	695.9
152.5°	507.4	507.7	517.1	530.2	545.9	566.3	589.4	613.3	636.5	661.9	688.3
155°	524.5	525.7	532.7	544.5	557.4	575.0	594.9	614.9	633.7	654.8	677.1
157.5°	541.2	541.2	547.8	556.9	568.2	582.1	599.0	614.9	630.7	647.5	665.6
160°	551.5	551.5	556.2	564.4	573.8	586.7	600.8	614.9	627.8	641.9	657.1
162.5°	560.9	560.0	563.7	571.0	579.5	589.6	602.7	614.9	625.0	636.2	649.6
165°	571.5	571.5	573.8	579.7	585.5	592.6	603.2	612.6	619.6	627.8	637.2
167.5°	582.1	580.9	582.1	586.5	589.8	595.2	602.9	609.8	614.0	619.4	625.9
170°	586.7	585.5	586.7	590.3	592.6	596.1	602.0	607.8	610.2	613.7	618.4
172.5°	591.4	590.3	590.5	593.1	594.5	597.0	601.1	606.0	606.4	608.0	611.9
175°	596.1	594.9	594.9	596.1	597.3	597.3	599.7	603.2	602.0	602.0	604.3
177.5°	598.2	597.3	596.3	597.3	597.3	597.3	598.2	600.1	598.2	598.2	599.2
180°	597.3	597.3	597.3	597.3	597.3	597.3	597.3	597.3	597.3	597.3	597.3



TEST NUMBER: P332534-840

CATALOG NUMBER: S124DIP-S350D1205U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5
2.5°	594.4	595.3	596.1	596.5	596.4	596.3	596.2	596.1
5°	591.3	592.4	593.6	594.0	593.8	593.6	593.4	593.2
7.5°	584.6	585.6	586.5	586.9	586.8	586.6	586.5	586.4
10°	579.2	580.0	580.9	581.2	581.0	580.7	580.5	580.3
12.5°	572.4	573.3	574.3	574.6	574.3	574.0	573.7	573.4
15°	559.6	560.2	560.9	561.0	560.7	560.4	560.1	559.8
17.5°	544.9	545.3	545.7	545.8	545.6	545.4	545.2	545.0
20°	534.1	534.4	534.7	534.8	534.5	534.3	534.1	533.9
22.5°	522.7	523.3	523.9	524.0	523.6	523.2	522.8	522.5
25°	504.0	504.1	504.2	504.1	503.6	503.2	502.8	502.4
27.5°	483.0	482.8	482.5	482.1	481.6	481.1	480.5	480.0
30°	468.6	468.2	467.7	467.3	466.7	466.2	465.6	465.1
32.5°	453.8	453.3	452.8	452.3	451.8	451.2	450.7	450.2
35°	430.6	429.9	429.1	428.5	428.0	427.5	426.9	426.4
37.5°	406.3	405.5	404.7	403.9	403.2	402.5	401.8	401.1
40°	389.4	388.3	387.3	386.5	385.9	385.4	384.9	384.4
42.5°	372.9	371.7	370.5	369.7	369.3	369.0	368.6	368.3
45°	347.6	346.4	345.3	344.5	344.2	343.9	343.6	343.3
47.5°	323.0	321.6	320.3	319.3	318.5	317.7	316.9	316.1
50°	305.8	304.4	302.9	301.7	301.1	300.5	299.8	299.2
52.5°	288.2	286.9	285.6	284.5	283.7	282.9	282.1	281.2
55°	262.3	260.9	259.7	258.7	258.1	257.5	256.8	256.2
57.5°	236.3	235.1	233.9	233.0	232.4	231.8	231.2	230.5
60°	218.4	217.5	216.5	215.8	215.3	214.7	214.2	213.7
62.5°	201.1	200.2	199.2	198.5	198.0	197.5	197.0	196.4
65°	175.7	174.6	173.6	172.8	172.3	171.7	171.2	170.7
67.5°	149.6	148.6	147.5	146.9	146.8	146.6	146.5	146.3
70°	133.1	132.3	131.4	130.8	130.5	130.2	129.9	129.6
72.5°	116.6	115.9	115.2	114.7	114.4	114.1	113.8	113.5
75°	92.8	92.4	92.0	91.7	91.6	91.5	91.4	91.3
77.5°	70.3	70.2	70.1	69.9	69.6	69.3	69.0	68.8
80°	55.9	55.7	55.5	55.4	55.2	55.1	55.0	54.9
82.5°	43.1	43.0	42.9	42.8	42.7	42.5	42.4	42.3
85°	24.8	24.8	24.8	24.8	24.7	24.6	24.4	24.3
87.5°	13.4	13.6	13.8	13.8	14.1	14.3	14.1	14.1
90°	21.1	22.3	23.4	23.4	24.6	25.9	24.6	24.6
92.5°	230.5	173.4	138.0	114.5	100.7	94.3	90.4	90.4
95°	869.5	687.6	530.4	416.6	359.1	322.8	301.5	286.3
97.5°	1284.8	1217.1	1102.4	979.9	895.5	825.0	789.7	765.4
100°	1415.2	1438.7	1381.2	1294.3	1192.2	1120.6	1085.5	1076.1
102.5°	1408.7	1525.0	1541.7	1505.5	1442.9	1391.0	1353.9	1346.5
105°	1314.2	1517.3	1633.5	1681.5	1683.9	1674.6	1658.1	1651.0
107.5°	1180.2	1396.4	1560.0	1664.7	1722.6	1749.4	1761.1	1764.2
110°	1099.5	1302.5	1472.7	1601.7	1685.1	1734.3	1755.5	1766.1



TEST NUMBER: P332534-840

CATALOG NUMBER: S124DIP-S350D1205U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	1040.4	1219.9	1380.7	1509.7	1604.4	1664.0	1693.5	1710.7
115°	981.0	1125.4	1262.6	1375.3	1468.0	1538.4	1576.0	1585.4
117.5°	951.9	1071.4	1179.3	1274.9	1353.9	1413.1	1451.1	1458.3
120°	938.8	1047.9	1141.8	1225.1	1292.0	1343.6	1374.1	1387.0
122.5°	927.5	1032.9	1118.3	1191.3	1247.9	1292.0	1317.8	1330.7
125°	908.3	1009.2	1090.1	1154.7	1201.6	1235.7	1258.0	1265.0
127.5°	884.7	981.3	1062.0	1123.3	1170.4	1200.7	1219.5	1226.5
130°	866.1	958.8	1038.5	1100.8	1148.8	1178.1	1196.9	1204.0
132.5°	846.3	933.4	1011.3	1073.5	1120.6	1153.8	1171.5	1178.6
135°	819.1	895.3	966.9	1025.6	1072.6	1105.4	1124.2	1131.3
137.5°	794.5	859.0	919.3	972.3	1016.2	1048.6	1064.1	1072.6
140°	780.3	835.5	888.3	937.6	978.7	1004.5	1020.9	1030.3
142.5°	767.2	815.8	861.1	903.8	940.2	964.1	978.7	985.2
145°	748.7	788.6	823.7	856.7	886.0	905.9	917.7	923.5
147.5°	733.5	765.1	793.2	819.1	840.7	857.8	866.8	868.8
150°	724.1	751.0	774.5	795.6	814.4	829.6	836.7	837.9
152.5°	713.7	736.9	758.5	775.9	791.8	804.3	808.5	809.7
155°	698.2	717.0	734.6	748.7	760.4	769.8	773.4	773.4
157.5°	681.6	697.3	712.1	723.4	732.3	739.3	741.4	741.4
160°	671.3	684.1	697.0	706.4	713.5	720.5	721.6	721.6
162.5°	660.9	672.0	682.1	690.4	695.6	702.7	703.9	702.9
165°	646.6	653.6	661.9	667.7	672.4	677.1	675.9	674.8
167.5°	632.8	638.1	644.7	648.2	650.6	653.6	653.4	652.5
170°	624.3	627.8	632.5	636.0	638.3	639.5	638.3	638.3
172.5°	616.7	619.4	622.2	624.7	626.1	627.3	626.1	624.3
175°	606.7	607.8	610.2	610.2	610.2	612.6	610.2	607.8
177.5°	600.1	601.1	601.1	602.0	601.1	602.0	600.1	598.2
180°	597.3	597.3	597.3	597.3	597.3	597.3	597.3	597.3

(END OF REPORT)