

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332505-830

Luminaire Tested: **S124DIP-S350D590U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332505-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIP-S350D590U830-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 590 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3654.4 lumens
Efficiency: N/A
Efficacy: 142.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 25.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332505-830

CATALOG NUMBER: S124DIP-S350D590U830-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332505-830

CATALOG NUMBER: S124DIP-S350D590U830-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	95	95	95	95	77	77	77	61	61	61	46	46	46	39
1	95	91	87	84	86	83	80	77	68	65	63	54	52	51	41	40	39	33
2	87	79	73	68	79	72	67	63	59	56	52	47	45	42	36	34	33	28
3	79	70	63	57	72	64	57	52	52	48	44	42	38	36	32	30	28	23
4	72	62	54	48	65	56	50	44	46	41	37	37	33	31	28	26	24	20
5	66	55	47	41	60	50	43	38	41	36	32	33	29	26	26	23	21	17
6	61	49	41	36	55	45	38	33	37	32	28	30	26	23	23	20	18	15
7	56	44	37	31	51	41	34	29	34	28	25	27	23	20	21	18	16	14
8	52	40	33	27	47	37	30	25	31	26	22	25	21	18	19	17	15	12
9	49	37	29	24	44	34	27	23	28	23	19	23	19	16	18	15	13	11
10	45	34	26	22	41	31	25	20	26	21	17	21	17	15	17	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4495	4495	4495
5°	4508	4454	4486
10°	4480	4418	4440
15°	4425	4355	4367
20°	4354	4277	4281
25°	4272	4188	4177
30°	4172	4084	4047
35°	4066	3975	3921
40°	3958	3851	3780
45°	3846	3729	3658
50°	3720	3620	3508
55°	3586	3478	3365
60°	3450	3321	3219
65°	3299	3171	3043
70°	3127	2969	2854
75°	2866	2729	2658
80°	2552	2450	2385
85°	2232	2149	2103



TEST NUMBER: P332505-830

CATALOG NUMBER: S124DIP-S350D590U830-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.4	1.4
10°-20°	147.7	4.0
20°-30°	217.4	6.0
30°-40°	252.8	6.9
40°-50°	252.8	6.9
50°-60°	221.1	6.1
60°-70°	164.2	4.5
70°-80°	93.3	2.6
80°-90°	29.0	0.8
90°-100°	24.6	0.7
100°-110°	156.8	4.3
110°-120°	299.9	8.2
120°-130°	380.7	10.4
130°-140°	407.3	11.1
140°-150°	380.9	10.4
150°-160°	307.1	8.4
160°-170°	198.1	5.4
170°-180°	68.3	1.9
0°-30°	417.6	11.4
0°-40°	670.4	18.3
0°-60°	1144.3	31.3
0°-90°	1430.8	39.2
90°-120°	481.2	13.2
90°-150°	1650.1	45.2
90°-180°	2224.0	60.9
0°-180°	3654.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	557	557	557	557	557	
5°	556	554	550	554	554	53
15°	530	528	521	524	522	149
25°	480	476	470	471	469	221
35°	413	409	403	400	398	258
45°	337	333	327	322	320	260
55°	255	253	247	242	239	228
65°	173	170	166	162	159	171
75°	92	90	88	86	85	98
85°	24	24	23	23	23	27
90°	2	7	12	15	16	3
95°	30	12	12	15	16	38
105°	162	165	168	171	153	169
115°	302	304	303	304	304	297
125°	425	427	426	427	428	379
135°	527	526	528	530	531	406
145°	608	609	609	610	611	380
155°	666	667	665	667	666	307
165°	703	700	700	704	700	198
175°	719	716	716	720	714	68
180°	719	719	719	719	719	



TEST NUMBER: P332505-830

CATALOG NUMBER: S124DIP-S350D590U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	556.8	556.8	556.8	556.8	556.8	556.8	556.8	556.8	556.8	556.8	556.8
2.5°	558.2	558.0	557.7	557.5	557.2	556.7	555.8	555.0	554.1	553.2	554.0
5°	556.3	555.9	555.5	555.2	554.8	554.0	552.9	551.9	550.7	549.6	550.7
7.5°	551.2	550.7	550.4	550.0	549.6	548.7	547.5	546.4	545.2	543.9	544.8
10°	546.5	546.1	545.7	545.4	545.0	544.1	542.8	541.5	540.3	538.9	539.7
12.5°	540.5	540.1	539.7	539.2	538.9	538.0	536.6	535.3	533.9	532.5	533.4
15°	529.5	529.1	528.8	528.4	528.0	527.1	525.6	524.1	522.5	521.1	521.7
17.5°	516.4	515.9	515.5	515.0	514.4	513.5	512.1	510.7	509.3	507.8	508.2
20°	506.8	506.3	505.9	505.3	504.8	503.9	502.4	500.9	499.4	497.9	498.2
22.5°	496.4	495.8	495.1	494.5	493.8	492.8	491.3	489.8	488.3	486.8	487.4
25°	479.6	478.9	478.2	477.5	476.8	475.8	474.4	473.0	471.6	470.2	470.3
27.5°	460.3	459.6	458.9	458.2	457.5	456.5	455.2	453.9	452.6	451.3	451.1
30°	447.5	446.7	445.9	445.1	444.3	443.3	442.0	440.6	439.4	438.1	437.7
32.5°	433.9	433.2	432.4	431.8	431.0	430.0	428.7	427.3	425.9	424.5	424.0
35°	412.6	412.0	411.3	410.6	409.9	408.9	407.5	406.0	404.7	403.3	402.7
37.5°	390.3	389.6	389.0	388.4	387.8	386.7	385.2	383.7	382.2	380.7	379.9
40°	375.6	374.8	374.1	373.2	372.5	371.4	369.9	368.3	366.8	365.4	364.4
42.5°	360.0	359.5	359.0	358.5	358.1	356.9	355.3	353.6	352.0	350.4	349.2
45°	336.9	336.1	335.5	334.8	334.0	332.9	331.3	329.7	328.2	326.6	325.5
47.5°	312.6	312.2	311.7	311.2	310.8	309.8	308.3	306.8	305.4	303.9	302.7
50°	296.2	295.9	295.5	295.0	294.6	293.8	292.4	291.0	289.5	288.2	286.8
52.5°	280.2	279.7	279.2	278.7	278.2	277.3	275.8	274.4	272.9	271.5	270.2
55°	254.8	254.5	254.1	253.8	253.5	252.7	251.3	250.0	248.5	247.1	246.0
57.5°	230.5	230.2	229.8	229.5	229.1	228.3	226.9	225.6	224.1	222.8	221.7
60°	213.7	213.2	212.7	212.2	211.7	210.8	209.5	208.2	207.0	205.7	204.8
62.5°	197.3	196.9	196.4	196.0	195.6	194.7	193.3	192.0	190.6	189.3	188.4
65°	172.7	172.2	171.6	171.2	170.7	169.9	168.9	168.0	166.9	166.0	164.9
67.5°	147.9	147.4	146.9	146.5	146.0	145.3	144.4	143.5	142.5	141.5	140.5
70°	132.5	131.8	131.1	130.4	129.7	128.9	128.2	127.4	126.6	125.8	125.0
72.5°	116.1	115.4	114.7	114.0	113.3	112.6	112.0	111.4	110.7	110.1	109.4
75°	91.9	91.4	91.0	90.4	89.9	89.4	89.0	88.4	87.9	87.5	87.1
77.5°	68.8	68.6	68.3	68.1	68.0	67.6	67.2	66.7	66.3	65.9	65.7
80°	54.9	54.6	54.3	54.0	53.7	53.4	53.3	53.1	52.9	52.7	52.4
82.5°	41.3	41.2	41.0	40.9	40.7	40.6	40.6	40.6	40.5	40.5	40.4
85°	24.1	24.1	24.1	24.1	24.1	24.0	23.8	23.6	23.4	23.2	23.2
87.5°	9.6	9.8	10.0	10.2	10.4	10.5	10.6	10.7	10.8	10.9	11.0
90°	1.6	2.9	4.2	5.6	6.9	8.0	9.0	9.9	10.8	11.8	12.5
92.5°	6.8	6.9	6.9	7.0	7.1	7.5	8.6	9.5	10.5	11.4	12.2
95°	29.6	25.5	21.5	17.3	13.3	11.3	11.5	11.6	11.7	11.8	12.5
97.5°	62.8	65.3	67.9	70.4	73.0	67.5	54.2	40.9	27.5	14.2	14.2
100°	88.1	90.3	92.5	94.6	96.8	89.6	73.1	56.6	40.2	23.7	21.6
102.5°	116.6	118.1	119.7	121.3	122.9	122.6	120.5	118.3	116.1	114.0	92.1
105°	161.8	162.6	163.2	164.0	164.7	165.3	166.0	166.5	167.1	167.8	168.8
107.5°	203.9	204.2	204.6	204.9	205.3	205.9	206.7	207.5	208.3	209.2	209.7
110°	232.2	232.6	233.0	233.4	233.7	234.2	235.0	235.6	236.4	237.1	237.3



TEST NUMBER: P332505-830

CATALOG NUMBER: S124DIP-S350D590U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	259.8	260.4	261.1	261.7	262.4	262.9	263.2	263.5	263.9	264.2	264.2
115°	302.2	302.6	302.8	303.2	303.6	303.7	303.6	303.5	303.3	303.2	303.5
117.5°	340.4	340.8	341.3	341.8	342.2	342.6	342.9	343.2	343.4	343.7	343.7
120°	366.2	366.6	367.1	367.6	368.1	368.3	368.2	368.0	367.9	367.8	368.0
122.5°	390.2	390.5	390.8	391.1	391.3	391.6	391.8	391.9	392.1	392.3	392.4
125°	424.7	425.2	425.7	426.2	426.7	426.8	426.5	426.3	426.0	425.8	426.2
127.5°	457.4	457.5	457.7	457.8	457.9	458.3	458.8	459.3	459.9	460.4	460.3
130°	478.5	478.6	478.7	478.9	479.0	479.2	479.6	479.9	480.3	480.7	480.8
132.5°	497.9	498.0	498.3	498.5	498.7	499.1	499.5	499.9	500.4	500.9	501.0
135°	526.9	526.8	526.7	526.5	526.4	526.6	527.1	527.5	528.0	528.5	528.8
137.5°	552.6	552.6	552.7	552.7	552.8	553.1	553.6	554.1	554.7	555.2	555.4
140°	569.4	569.6	569.9	570.0	570.3	570.5	570.8	571.1	571.3	571.6	571.8
142.5°	584.5	584.8	585.3	585.7	586.2	586.4	586.5	586.7	586.8	587.0	587.3
145°	607.6	607.9	608.2	608.6	609.0	609.2	609.2	609.2	609.2	609.2	609.3
147.5°	625.9	626.6	627.3	627.9	628.6	628.9	628.8	628.7	628.5	628.4	628.5
150°	639.2	639.7	640.3	640.7	641.2	641.4	641.2	641.1	641.0	640.8	640.8
152.5°	650.4	650.8	651.2	651.6	652.0	652.1	651.9	651.7	651.4	651.2	651.4
155°	666.2	666.3	666.4	666.5	666.7	666.5	666.2	665.8	665.4	665.1	665.5
157.5°	679.4	679.3	679.2	679.2	679.1	678.8	678.4	678.1	677.6	677.2	677.9
160°	687.1	686.7	686.4	686.1	685.7	685.4	685.3	685.2	685.0	684.9	685.7
162.5°	694.0	693.5	693.1	692.7	692.2	691.9	691.7	691.6	691.5	691.4	692.1
165°	702.7	702.1	701.5	700.9	700.3	700.0	700.0	700.0	700.0	700.0	701.0
167.5°	709.5	709.0	708.3	707.8	707.1	706.7	706.7	706.6	706.5	706.4	707.6
170°	713.5	712.8	712.0	711.3	710.6	710.3	710.4	710.5	710.7	710.8	711.7
172.5°	716.0	715.3	714.6	713.9	713.2	712.8	713.0	713.1	713.2	713.3	714.4
175°	718.9	718.1	717.4	716.7	716.0	715.7	715.8	716.0	716.0	716.1	717.2
177.5°	720.1	719.4	718.8	718.1	717.5	717.2	717.4	717.6	717.7	717.9	718.8
180°	718.9	718.9	718.9	718.9	718.9	718.9	718.9	718.9	718.9	718.9	718.9



TEST NUMBER: P332505-830

CATALOG NUMBER: S124DIP-S350D590U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	556.8	556.8	556.8	556.8	556.8	556.8	556.8	556.8
2.5°	554.8	555.6	556.4	556.8	556.7	556.6	556.5	556.4
5°	551.9	552.9	554.0	554.4	554.2	554.0	553.8	553.6
7.5°	545.6	546.6	547.4	547.8	547.7	547.5	547.4	547.3
10°	540.5	541.3	542.2	542.4	542.2	542.0	541.8	541.6
12.5°	534.2	535.1	536.0	536.3	536.0	535.7	535.5	535.2
15°	522.3	522.8	523.5	523.6	523.3	523.0	522.7	522.5
17.5°	508.6	509.0	509.3	509.4	509.3	509.1	508.9	508.7
20°	498.5	498.8	499.1	499.2	498.9	498.7	498.5	498.3
22.5°	487.9	488.4	489.0	489.1	488.7	488.3	488.0	487.7
25°	470.4	470.5	470.6	470.5	470.0	469.7	469.3	468.9
27.5°	450.8	450.6	450.3	450.0	449.5	449.0	448.5	448.0
30°	437.3	437.0	436.5	436.1	435.5	435.1	434.6	434.1
32.5°	423.6	423.1	422.6	422.2	421.7	421.1	420.7	420.2
35°	401.9	401.2	400.5	399.9	399.4	399.0	398.4	397.9
37.5°	379.2	378.4	377.7	377.0	376.4	375.7	375.0	374.4
40°	363.4	362.4	361.5	360.7	360.1	359.7	359.2	358.7
42.5°	348.1	346.9	345.8	345.1	344.7	344.4	344.0	343.7
45°	324.4	323.3	322.3	321.5	321.2	320.9	320.7	320.4
47.5°	301.4	300.2	299.0	298.0	297.3	296.5	295.8	295.0
50°	285.4	284.1	282.7	281.6	281.1	280.5	279.8	279.3
52.5°	269.0	267.8	266.6	265.5	264.8	264.0	263.3	262.5
55°	244.8	243.6	242.4	241.5	240.9	240.3	239.7	239.1
57.5°	220.6	219.4	218.3	217.4	216.9	216.3	215.7	215.1
60°	203.9	203.0	202.1	201.4	201.0	200.4	199.9	199.4
62.5°	187.7	186.8	186.0	185.3	184.8	184.4	183.9	183.3
65°	164.0	163.0	162.0	161.3	160.8	160.2	159.8	159.3
67.5°	139.6	138.6	137.7	137.1	137.0	136.9	136.8	136.6
70°	124.2	123.5	122.6	122.1	121.8	121.5	121.2	120.9
72.5°	108.9	108.2	107.5	107.1	106.8	106.5	106.2	105.9
75°	86.6	86.2	85.9	85.6	85.5	85.4	85.3	85.2
77.5°	65.6	65.5	65.4	65.2	64.9	64.7	64.4	64.2
80°	52.2	52.0	51.8	51.7	51.6	51.5	51.4	51.3
82.5°	40.2	40.2	40.1	40.0	39.9	39.7	39.6	39.5
85°	23.2	23.2	23.2	23.2	23.1	23.0	22.8	22.7
87.5°	11.2	11.4	11.5	11.6	11.7	11.7	11.8	11.8
90°	13.3	13.9	14.7	15.2	15.5	15.6	15.9	16.1
92.5°	12.8	13.6	14.2	14.6	14.7	14.7	14.8	14.8
95°	13.3	13.9	14.7	15.1	15.3	15.4	15.5	15.6
97.5°	14.3	14.4	14.5	14.6	14.7	14.8	14.9	15.1
100°	19.6	17.5	15.6	14.6	14.7	14.8	14.9	15.1
102.5°	70.1	48.3	26.3	15.4	15.5	15.5	15.5	15.5
105°	169.9	171.0	172.0	170.4	166.2	161.8	157.5	153.3
107.5°	210.2	210.8	211.2	211.7	212.2	212.6	213.1	213.6
110°	237.6	237.8	238.1	238.4	238.7	239.0	239.4	239.8



TEST NUMBER: P332505-830

CATALOG NUMBER: S124DIP-S350D590U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	264.1	264.1	264.0	264.2	264.7	265.1	265.6	266.0
115°	303.7	304.0	304.2	304.3	304.3	304.3	304.3	304.3
117.5°	343.6	343.6	343.5	343.5	343.4	343.4	343.3	343.3
120°	368.3	368.4	368.7	368.7	368.4	368.3	368.0	367.8
122.5°	392.6	392.7	392.9	392.8	392.6	392.3	392.1	391.8
125°	426.5	426.9	427.3	427.5	427.6	427.7	427.8	428.0
127.5°	460.3	460.2	460.1	460.1	460.0	459.9	459.8	459.7
130°	480.9	481.0	481.2	481.2	481.2	481.2	481.2	481.2
132.5°	501.1	501.2	501.3	501.3	501.2	501.1	501.1	501.0
135°	529.0	529.2	529.4	529.7	529.9	530.2	530.5	530.7
137.5°	555.7	556.0	556.2	556.3	556.3	556.2	556.1	556.0
140°	572.2	572.6	573.0	573.2	573.3	573.4	573.5	573.6
142.5°	587.5	587.8	588.1	588.2	588.2	588.2	588.2	588.3
145°	609.4	609.5	609.6	609.8	610.0	610.3	610.6	610.8
147.5°	628.6	628.7	628.8	628.9	629.1	629.1	629.2	629.3
150°	640.8	640.8	640.8	640.9	641.0	641.2	641.3	641.4
152.5°	651.6	651.8	652.0	652.1	652.0	651.9	651.8	651.8
155°	666.0	666.5	666.9	667.0	666.7	666.3	666.0	665.6
157.5°	678.4	679.1	679.7	679.7	679.1	678.4	677.9	677.2
160°	686.4	687.1	687.9	687.9	687.1	686.4	685.7	684.9
162.5°	692.9	693.5	694.3	694.3	693.4	692.6	691.8	691.0
165°	701.9	702.9	703.9	703.8	702.7	701.6	700.6	699.5
167.5°	708.6	709.6	710.7	710.6	709.5	708.2	707.0	705.9
170°	712.7	713.6	714.6	714.4	713.3	712.1	710.9	709.7
172.5°	715.3	716.2	717.2	717.0	715.8	714.4	713.1	711.8
175°	718.3	719.3	720.5	720.3	718.9	717.4	716.0	714.5
177.5°	719.5	720.3	721.0	720.9	719.7	718.6	717.4	716.2
180°	718.9	718.9	718.9	718.9	718.9	718.9	718.9	718.9

(END OF REPORT)