

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332555-840

Luminaire Tested: **S124DIP-S575D810U840-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332555-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124DIP-S575D810U840-4F0-1E-UDD-A4  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 575 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 810 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5542.3 lumens  
Efficiency: N/A  
Efficacy: 144.3 lumens/watt  
Spacing Criteria (0/90/45): 1.31 / 1.23 / 1.41  
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 38.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332555-840

CATALOG NUMBER: S124DIP-S575D810U840-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P332555-840

CATALOG NUMBER: S124DIP-S575D810U840-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	98	98	98	98	82	82	82	67	67	67	54	54	54	47				47
1	97	93	89	86	89	86	83	80	72	70	68	59	58	56	48	47	46				40	
2	89	82	76	71	81	75	70	66	63	60	56	52	50	47	42	40	39				34	
3	81	72	65	59	74	66	60	55	56	51	48	46	43	40	38	35	33				29	
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	34	31	29				25	
5	68	57	49	43	63	53	46	40	45	39	35	37	33	30	30	28	25				22	
6	63	51	43	37	58	47	40	35	40	35	31	34	30	26	28	25	22				19	
7	58	46	38	33	53	43	36	31	37	31	27	31	27	23	25	22	20				17	
8	54	42	34	29	50	39	32	27	33	28	24	28	24	21	23	20	18				15	
9	50	38	31	26	46	36	29	24	31	25	22	26	22	19	22	18	16				14	
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	15				13	

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	7657	7657	7657	7657
5°	9018	7678	6776	7678
10°	10797	7643	6101	7643
15°	12774	7565	5602	7565
20°	14225	7487	5158	7487
25°	14455	7371	4851	7371
30°	12299	7260	4754	7260
35°	9456	7078	4755	7078
40°	7371	6866	4845	6866
45°	6146	6545	4925	6545
50°	5408	6154	5093	6154
55°	4954	5685	5298	5685
60°	4644	5265	5546	5265
65°	4323	4797	5748	4797
70°	3949	4331	5880	4331
75°	3531	3812	5808	3812
80°	2957	3124	5625	3124
85°	2177	2251	5391	2251



TEST NUMBER: P332555-840

CATALOG NUMBER: S124DIP-S575D810U840-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	92.4	1.7
10°-20°	284.8	5.1
20°-30°	451.7	8.1
30°-40°	502.6	9.1
40°-50°	457.5	8.3
50°-60°	373.9	6.7
60°-70°	266.9	4.8
70°-80°	147.0	2.7
80°-90°	42.3	0.8
90°-100°	290.3	5.2
100°-110°	604.2	10.9
110°-120°	541.2	9.8
120°-130°	455.2	8.2
130°-140°	379.6	6.8
140°-150°	290.0	5.2
150°-160°	203.8	3.7
160°-170°	119.9	2.2
170°-180°	39.0	0.7
0°-30°	828.9	15.0
0°-40°	1331.5	24.0
0°-60°	2162.9	39.0
0°-90°	2619.2	47.3
90°-120°	1435.7	25.9
90°-150°	2560.4	46.2
90°-180°	2923.0	52.7
0°-180°	5542.3	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	948	948	948	948	948	
5°	1113	947	836	947	1113	113
15°	1528	905	670	905	1528	432
25°	1623	828	545	828	1623	715
35°	960	718	482	718	960	609
45°	538	573	431	573	538	424
55°	352	404	376	404	352	318
65°	226	251	301	251	226	224
75°	113	122	186	122	113	120
85°	24	24	58	24	24	29
90°	17	1	17	1	17	14
95°	193	26	193	26	193	299
105°	1111	92	1111	92	1111	1098
115°	1067	163	1067	163	1067	1059
125°	851	227	851	227	851	774
135°	761	269	761	269	761	588
145°	622	310	622	310	622	394
155°	520	353	520	353	520	243
165°	454	385	454	385	454	130
175°	409	401	409	401	409	40
180°	402	402	402	402	402	



TEST NUMBER: P332555-840

CATALOG NUMBER: S124DIP-S575D810U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	948.5	948.5	948.5	948.5	948.5	948.5	948.5	948.5	948.5	948.5	948.5
2.5°	1009.5	1009.2	1006.0	1005.4	1003.2	1000.4	999.8	994.7	984.6	980.0	978.7
5°	1112.8	1120.6	1110.3	1108.4	1107.2	1094.3	1087.6	1079.7	1061.7	1051.1	1042.8
7.5°	1236.0	1236.9	1232.4	1228.8	1218.8	1207.5	1190.5	1172.5	1150.9	1128.5	1111.7
10°	1317.1	1320.2	1315.1	1314.3	1294.2	1281.7	1256.6	1235.4	1210.9	1183.9	1159.1
12.5°	1402.6	1398.2	1395.5	1378.8	1375.0	1352.1	1322.9	1301.0	1263.4	1232.2	1199.3
15°	1528.4	1519.8	1514.3	1491.2	1479.8	1447.9	1416.8	1392.9	1343.8	1297.1	1261.6
17.5°	1602.4	1610.9	1598.2	1588.7	1559.2	1536.9	1505.2	1454.9	1416.4	1358.4	1313.7
20°	1655.8	1656.6	1649.5	1639.6	1616.5	1588.2	1553.6	1498.6	1452.6	1394.8	1333.5
22.5°	1670.2	1670.4	1667.4	1658.2	1640.6	1617.7	1582.9	1536.9	1481.3	1418.5	1357.2
25°	1622.8	1621.2	1624.8	1635.0	1628.3	1621.2	1601.1	1567.0	1515.1	1448.7	1382.7
27.5°	1446.4	1457.2	1477.2	1502.4	1526.6	1545.0	1550.2	1543.3	1511.1	1456.4	1387.4
30°	1319.4	1332.8	1347.7	1372.9	1421.6	1449.5	1480.2	1503.3	1490.4	1446.7	1382.3
32.5°	1179.8	1183.2	1205.3	1234.0	1278.6	1332.2	1380.8	1427.8	1443.5	1420.7	1366.9
35°	959.5	965.0	989.0	1017.2	1071.9	1137.5	1210.6	1275.8	1329.7	1351.3	1323.7
37.5°	783.0	798.8	815.7	846.1	894.2	953.3	1029.3	1113.6	1193.9	1247.6	1256.7
40°	699.4	709.2	721.4	744.6	785.5	843.6	908.8	1005.5	1090.8	1167.8	1193.0
42.5°	633.4	639.1	646.6	667.5	698.7	756.5	816.1	901.1	986.7	1078.8	1121.0
45°	538.3	544.2	556.7	569.0	592.5	632.6	688.0	757.9	843.9	932.8	1010.6
47.5°	469.6	473.4	480.9	493.9	513.9	540.4	585.4	643.8	723.6	809.8	892.7
50°	430.6	433.7	439.7	451.5	466.8	490.4	527.3	581.9	644.4	731.2	812.5
52.5°	399.8	401.1	405.5	413.4	425.7	445.5	475.7	520.9	579.1	656.4	737.4
55°	352.0	353.7	357.6	363.5	374.1	386.7	409.8	443.6	494.3	561.5	631.8
57.5°	312.8	313.9	317.2	319.4	328.2	338.4	356.2	380.3	418.8	475.7	538.6
60°	287.6	286.8	290.7	292.8	298.6	307.3	321.0	344.2	377.6	423.5	481.3
62.5°	263.1	262.0	265.3	267.9	271.2	278.6	289.9	308.0	335.2	376.8	426.7
65°	226.3	224.8	226.7	229.8	233.0	236.9	245.2	261.3	282.9	312.8	350.8
67.5°	189.3	191.1	191.4	192.9	194.7	200.1	205.7	217.1	232.4	256.3	288.5
70°	167.3	167.7	169.4	169.4	170.6	175.2	180.0	186.6	201.6	223.6	249.9
72.5°	145.4	147.0	146.4	147.6	148.6	151.7	155.1	161.5	174.2	190.6	212.8
75°	113.2	114.3	114.3	114.7	115.9	117.0	119.9	124.5	133.6	145.7	161.1
77.5°	82.5	82.7	83.2	84.6	84.6	86.5	88.6	92.3	96.8	105.1	114.5
80°	63.6	64.4	64.0	64.8	64.8	66.4	67.2	71.9	73.8	79.4	86.8
82.5°	46.7	47.5	47.4	48.5	49.1	49.4	50.5	52.4	54.3	59.3	62.3
85°	23.5	24.3	23.5	24.3	25.5	26.0	27.1	27.5	29.1	30.3	33.0
87.5°	10.2	11.2	11.3	11.5	11.9	12.3	12.4	11.9	13.0	13.5	14.4
90°	16.6	16.6	17.4	16.6	15.8	15.8	15.0	14.2	13.4	14.2	12.6
92.5°	60.8	60.8	63.5	67.8	77.1	92.9	116.7	155.1	208.6	250.4	219.2
95°	192.7	203.0	217.1	241.7	280.3	356.9	462.7	585.1	661.8	643.6	485.6
97.5°	515.0	531.4	555.1	602.7	659.3	741.7	819.0	864.4	831.3	677.8	454.5
100°	724.1	730.4	754.1	802.2	871.0	929.4	968.1	952.3	837.0	634.9	412.2
102.5°	906.1	911.1	936.0	971.0	1013.1	1037.4	1026.2	947.9	789.6	581.2	383.7
105°	1111.1	1115.8	1126.8	1133.2	1131.6	1099.1	1021.0	884.4	703.6	518.0	359.3
107.5°	1187.1	1185.1	1177.2	1159.2	1120.1	1049.8	939.7	794.3	634.1	482.6	354.9
110°	1188.4	1181.3	1167.1	1133.9	1077.8	991.0	876.5	739.9	599.4	470.6	356.1



TEST NUMBER: P332555-840

CATALOG NUMBER: S124DIP-S575D810U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1151.1	1139.6	1119.7	1079.5	1015.9	929.1	820.9	700.1	579.8	464.9	359.9
115°	1066.8	1060.5	1035.2	987.8	925.4	849.6	757.3	660.1	561.4	461.9	367.2
117.5°	981.4	976.4	950.9	911.1	857.9	793.6	720.9	640.6	553.2	461.1	375.0
120°	933.3	924.6	904.1	869.4	824.4	768.3	705.2	631.7	548.8	461.1	380.6
122.5°	895.4	886.8	869.4	839.7	801.6	752.6	695.0	624.1	543.7	460.5	386.3
125°	851.2	846.5	831.5	808.6	777.0	733.6	679.1	611.2	535.3	459.6	394.9
127.5°	825.4	820.6	808.0	787.6	755.9	714.6	660.2	595.4	524.1	457.9	401.6
130°	810.2	805.5	792.8	773.1	740.6	698.8	645.1	582.8	517.3	457.2	406.7
132.5°	793.1	788.4	776.4	754.1	722.4	680.5	628.0	569.5	510.9	456.6	411.1
135°	761.2	756.5	743.9	721.8	690.1	650.7	602.5	551.2	501.4	455.7	417.7
137.5°	721.8	716.0	705.6	683.8	654.3	618.6	578.0	534.6	493.2	455.4	421.6
140°	693.3	687.0	675.9	658.5	631.0	597.7	562.2	525.1	488.8	454.8	424.9
142.5°	663.0	658.5	648.7	632.7	608.1	579.5	549.0	516.2	485.0	454.8	427.4
145°	621.5	617.5	609.6	596.2	576.4	554.3	530.7	503.8	478.5	453.2	428.8
147.5°	584.6	583.2	577.2	565.7	551.2	533.8	514.8	493.5	472.7	450.4	429.6
150°	563.8	563.0	558.3	548.1	535.3	521.2	505.3	487.2	468.3	448.5	429.6
152.5°	544.8	544.0	541.2	532.8	522.1	510.4	495.8	480.3	463.2	445.4	428.3
155°	520.4	520.4	518.0	511.7	503.8	494.3	482.5	469.8	455.7	440.6	426.4
157.5°	498.9	498.9	497.5	492.7	486.8	479.2	469.2	458.6	447.9	435.8	424.3
160°	485.6	485.6	484.8	480.1	475.3	469.1	460.4	451.7	442.2	431.9	422.4
162.5°	473.0	473.6	472.8	468.1	464.6	459.0	452.1	444.7	437.2	428.2	420.6
165°	454.0	454.8	455.7	452.4	449.3	445.4	439.8	435.0	428.8	422.4	417.0
167.5°	439.0	439.7	439.8	437.8	436.2	433.8	429.4	425.8	421.2	416.8	413.1
170°	429.6	429.6	430.3	429.6	428.0	425.7	422.4	420.1	416.2	412.9	410.6
172.5°	420.1	421.3	422.1	421.3	420.4	418.7	416.8	415.1	411.7	409.2	408.1
175°	409.0	410.6	412.2	410.6	410.6	410.6	409.0	408.3	406.7	405.1	405.1
177.5°	402.5	403.8	405.1	404.5	405.1	404.5	404.5	403.8	403.1	402.5	402.5
180°	401.9	401.9	401.9	401.9	401.9	401.9	401.9	401.9	401.9	401.9	401.9



TEST NUMBER: P332555-840

CATALOG NUMBER: S124DIP-S575D810U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	948.5	948.5	948.5	948.5	948.5	948.5	948.5	948.5	948.5	948.5	948.5
2.5°	979.0	974.6	971.5	969.0	962.0	958.0	954.8	950.4	945.3	940.0	933.4
5°	1034.6	1021.2	1011.4	996.4	982.3	970.5	958.4	947.4	933.9	919.5	908.8
7.5°	1093.0	1073.1	1047.6	1025.5	1000.7	979.1	959.8	940.0	919.4	899.4	881.1
10°	1130.0	1104.5	1076.2	1042.8	1011.4	983.5	957.6	932.4	908.1	883.6	862.8
12.5°	1169.9	1138.1	1096.3	1057.2	1022.1	984.7	953.4	922.6	893.2	867.7	843.3
15°	1223.6	1177.6	1129.2	1077.0	1030.7	987.0	944.2	905.2	872.3	838.5	815.0
17.5°	1256.5	1199.6	1144.4	1089.7	1033.6	978.6	932.4	887.6	846.2	812.6	782.9
20°	1278.2	1221.6	1152.9	1098.2	1031.4	974.8	921.4	871.5	828.3	792.5	761.8
22.5°	1297.1	1231.6	1162.9	1091.0	1024.5	964.4	905.9	855.8	811.6	774.0	744.6
25°	1307.3	1232.2	1157.5	1086.0	1010.6	939.5	886.5	827.5	780.3	740.6	709.2
27.5°	1308.4	1228.1	1143.7	1064.2	986.3	920.1	853.1	800.4	751.5	709.5	679.3
30°	1304.8	1221.2	1130.4	1044.4	966.2	894.2	836.2	778.8	728.8	687.2	655.8
32.5°	1293.8	1206.7	1113.5	1022.4	941.4	871.0	811.0	756.5	707.8	666.8	633.8
35°	1262.0	1176.0	1076.6	981.9	899.0	827.9	773.7	718.2	669.5	630.7	598.8
37.5°	1212.3	1134.5	1033.5	935.4	854.0	782.6	728.8	678.8	634.9	595.3	562.7
40°	1168.9	1100.6	999.2	903.7	815.7	747.7	697.4	651.5	607.8	570.5	539.5
42.5°	1118.9	1059.3	965.8	864.7	779.8	711.6	662.6	621.3	580.2	545.7	514.6
45°	1029.9	990.6	902.5	809.0	720.6	656.2	609.5	573.3	538.7	504.9	479.0
47.5°	927.4	907.9	833.7	745.0	661.1	597.5	557.0	523.6	493.3	464.6	441.8
50°	858.5	849.1	785.1	699.4	619.2	559.6	518.7	490.0	464.0	438.9	417.3
52.5°	790.6	790.3	732.6	654.1	580.0	522.4	481.9	455.0	432.6	412.1	392.7
55°	686.8	697.8	652.7	582.7	516.3	464.4	427.9	403.9	388.2	371.3	356.8
57.5°	591.5	609.8	572.5	510.9	455.4	407.7	375.9	357.9	341.1	330.9	320.3
60°	529.3	546.5	517.5	465.6	413.3	372.4	342.2	326.1	311.5	304.5	297.0
62.5°	473.9	489.4	467.8	419.7	374.4	335.1	309.5	294.1	284.3	276.5	271.6
65°	394.9	407.9	389.4	354.5	315.5	284.1	263.3	251.1	241.7	238.5	233.0
67.5°	319.2	331.0	321.0	291.3	260.1	236.3	220.0	208.3	202.8	200.0	196.1
70°	274.3	286.1	275.4	249.5	225.5	205.5	190.2	183.5	177.6	176.4	171.0
72.5°	236.2	244.3	233.6	213.4	192.9	175.9	164.1	157.1	154.0	151.9	149.0
75°	177.2	184.3	177.2	161.5	146.9	135.1	124.9	122.2	118.7	117.4	115.5
77.5°	125.4	131.6	126.1	116.3	105.4	96.3	90.9	87.4	86.5	84.5	85.4
80°	95.8	99.8	94.7	88.1	79.4	73.1	69.2	67.2	64.8	64.0	65.6
82.5°	68.9	70.6	68.0	63.5	57.1	52.9	50.3	48.0	47.6	47.7	47.7
85°	35.7	35.3	34.9	31.0	29.1	26.4	24.7	24.3	23.9	24.7	25.5
87.5°	14.1	14.4	13.2	11.9	10.8	9.8	9.0	8.3	9.0	9.8	10.2
90°	11.0	11.0	6.4	6.4	5.6	4.7	2.3	0.8	2.3	4.7	5.6
92.5°	159.5	98.3	58.1	41.7	30.2	20.5	13.1	9.0	13.1	20.5	30.2
95°	296.9	167.4	98.7	65.5	46.6	36.4	28.4	26.1	28.4	36.4	46.6
97.5°	266.9	160.0	107.0	79.3	63.0	53.5	46.8	46.8	46.8	53.5	63.0
100°	251.2	161.9	115.3	90.0	75.0	65.5	60.0	60.0	60.0	65.5	75.0
102.5°	246.7	168.1	126.0	102.0	87.7	78.8	73.9	72.6	73.9	78.8	87.7
105°	248.7	183.2	145.3	122.4	108.2	98.7	94.7	92.4	94.7	98.7	108.2
107.5°	260.4	200.8	166.0	143.4	129.8	119.7	115.7	114.2	115.7	119.7	129.8
110°	269.2	214.0	179.3	157.9	143.7	134.2	130.3	128.8	130.3	134.2	143.7





TEST NUMBER: P332555-840

CATALOG NUMBER: S124DIP-S575D810U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	278.7	226.6	193.2	171.8	157.6	148.8	144.2	142.6	144.2	148.8	157.6
115°	293.8	246.4	214.8	193.5	178.4	170.6	165.0	162.7	165.0	170.6	178.4
117.5°	309.0	265.5	235.5	213.4	199.3	190.7	185.7	183.5	185.7	190.7	199.3
120°	319.8	278.7	248.7	226.6	213.2	204.5	198.9	197.4	198.9	204.5	213.2
122.5°	329.9	291.3	261.4	239.8	225.2	217.1	211.7	210.1	211.7	217.1	225.2
125°	345.1	308.7	280.3	258.2	243.2	234.5	229.7	226.6	229.7	234.5	243.2
127.5°	358.2	324.9	297.4	275.1	259.4	249.5	243.9	241.4	243.9	249.5	259.4
130°	366.4	335.6	308.7	285.9	270.8	259.0	252.7	249.5	252.7	259.0	270.8
132.5°	374.6	344.5	317.6	296.0	279.7	268.5	260.2	257.7	260.2	268.5	279.7
135°	385.4	356.9	330.8	310.3	293.8	280.3	272.5	269.2	272.5	280.3	293.8
137.5°	392.9	366.4	342.0	322.4	305.3	292.5	283.8	280.8	283.8	292.5	305.3
140°	398.0	372.7	349.0	330.0	313.5	300.0	291.3	289.0	291.3	300.0	313.5
142.5°	401.7	378.4	355.4	337.0	321.0	308.3	300.2	297.8	300.2	308.3	321.0
145°	405.9	384.6	364.1	346.7	331.6	320.6	312.7	310.3	312.7	320.6	331.6
147.5°	409.5	390.9	371.6	356.0	343.5	332.1	325.2	324.4	325.2	332.1	343.5
150°	411.4	394.0	376.7	361.6	349.8	340.3	334.1	333.3	334.1	340.3	349.8
152.5°	412.6	396.6	381.1	367.4	356.8	347.9	341.6	341.4	341.6	347.9	356.8
155°	413.7	400.3	386.9	375.1	366.4	358.5	353.8	352.9	353.8	358.5	366.4
157.5°	413.7	403.0	391.6	382.3	374.8	368.6	364.2	364.2	364.2	368.6	374.8
160°	413.7	404.2	394.9	386.2	379.8	374.3	371.1	371.1	371.1	374.3	379.8
162.5°	413.7	405.6	396.7	389.9	384.3	379.3	376.8	377.5	376.8	379.3	384.3
165°	412.2	405.9	398.8	394.0	390.1	386.2	384.6	384.6	384.6	386.2	390.1
167.5°	410.3	405.8	400.5	396.9	394.7	391.6	390.9	391.6	390.9	391.6	394.7
170°	409.0	405.1	401.1	398.8	397.2	394.9	394.0	394.9	394.0	394.9	397.2
172.5°	407.8	404.5	401.7	400.0	399.1	397.4	397.2	398.0	397.2	397.4	399.1
175°	405.9	403.5	401.9	401.9	401.1	400.3	400.3	401.1	400.3	400.3	401.1
177.5°	403.8	402.5	401.9	401.9	401.9	401.3	401.9	402.5	401.9	401.3	401.9
180°	401.9	401.9	401.9	401.9	401.9	401.9	401.9	401.9	401.9	401.9	401.9



TEST NUMBER: P332555-840

CATALOG NUMBER: S124DIP-S575D810U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	948.5	948.5	948.5	948.5	948.5	948.5	948.5	948.5	948.5	948.5	948.5
2.5°	930.3	927.5	923.3	917.7	913.0	908.0	906.7	904.8	908.6	905.4	904.5
5°	899.8	891.5	880.9	868.8	861.7	851.4	849.5	845.6	841.6	841.2	837.3
7.5°	867.5	855.4	841.5	829.1	817.6	806.5	799.1	797.6	791.7	788.4	784.5
10°	846.8	831.8	815.7	804.0	790.5	778.8	770.5	765.8	761.8	757.5	753.7
12.5°	822.2	806.4	793.0	780.3	764.5	755.5	741.9	733.8	733.0	733.1	722.9
15°	793.7	778.0	757.5	739.5	730.8	713.6	706.1	696.6	690.7	684.9	680.1
17.5°	761.1	741.5	725.6	704.8	688.3	674.6	664.7	659.0	650.3	641.9	635.8
20°	740.6	719.8	703.0	681.0	662.9	646.0	637.7	629.9	623.2	616.1	609.5
22.5°	719.9	698.1	677.5	656.1	639.2	621.5	613.5	602.8	596.4	592.5	585.8
25°	687.2	663.7	640.1	619.7	602.4	586.6	576.0	567.7	560.7	557.5	553.2
27.5°	651.7	628.2	605.5	582.3	562.7	551.3	542.8	536.5	532.5	528.4	526.3
30°	629.0	604.7	580.4	558.8	540.7	529.3	521.4	517.1	513.9	512.0	510.0
32.5°	606.1	582.1	556.4	536.7	520.6	510.4	504.4	500.1	498.6	497.9	497.2
35°	569.4	545.0	521.4	503.7	488.4	484.4	479.4	477.0	476.3	479.0	480.2
37.5°	533.7	511.1	489.4	472.3	462.2	456.5	454.7	454.8	457.7	460.1	462.9
40°	510.8	488.8	468.4	453.4	444.0	440.5	439.7	441.6	444.7	447.6	450.7
42.5°	488.5	466.8	448.3	434.2	427.7	424.4	425.0	426.9	431.3	434.6	439.4
45°	453.8	435.8	417.7	406.3	400.8	401.5	401.5	405.1	409.4	414.5	419.6
47.5°	421.2	402.9	388.1	378.5	375.7	375.0	377.2	381.8	388.1	394.4	401.5
50°	399.2	381.9	368.9	360.3	357.2	358.3	361.5	365.8	373.2	381.1	388.6
52.5°	376.9	361.1	349.1	341.1	338.9	341.0	344.2	351.0	357.6	366.1	375.1
55°	342.2	328.9	319.4	313.6	312.8	314.0	317.5	325.0	334.4	345.0	353.7
57.5°	307.7	296.6	287.9	283.9	284.3	285.4	291.1	300.0	310.1	321.4	332.5
60°	284.5	274.3	267.2	264.1	264.5	266.8	273.9	282.2	294.7	305.7	317.5
62.5°	262.5	253.5	246.7	243.9	243.4	248.5	255.3	263.9	276.5	288.7	301.4
65°	227.1	220.0	214.5	213.0	214.1	218.0	226.7	238.1	248.7	261.7	275.1
67.5°	192.5	186.7	183.0	183.7	185.1	190.9	198.1	207.9	219.9	233.4	246.6
70°	170.6	165.0	161.9	162.3	164.6	171.7	178.0	187.8	200.8	214.5	225.5
72.5°	147.9	144.3	141.5	143.1	145.4	150.4	158.1	168.0	179.5	192.2	203.9
75°	113.5	113.5	112.0	113.2	116.7	121.4	127.3	137.5	149.0	159.2	168.5
77.5°	84.2	83.4	84.4	85.8	87.9	93.4	100.2	107.6	116.0	126.3	134.1
80°	64.4	64.8	66.8	69.2	70.0	74.2	81.3	88.1	94.7	103.3	110.8
82.5°	48.4	48.8	49.8	52.8	53.6	58.3	62.8	69.5	75.5	81.3	87.6
85°	26.4	26.4	28.3	29.5	31.4	34.5	37.4	41.3	46.8	50.7	56.6
87.5°	11.3	11.3	13.5	14.1	15.5	17.3	17.8	21.4	22.8	24.5	27.4
90°	6.4	6.4	11.0	11.0	12.6	14.2	13.4	14.2	15.0	15.8	15.8
92.5°	41.7	58.1	98.3	159.5	219.2	250.4	208.6	155.1	116.7	92.9	77.1
95°	65.5	98.7	167.4	296.9	485.6	643.6	661.8	585.1	462.7	356.9	280.3
97.5°	79.3	107.0	160.0	266.9	454.5	677.8	831.3	864.4	819.0	741.7	659.3
100°	90.0	115.3	161.9	251.2	412.2	634.9	837.0	952.3	968.1	929.4	871.0
102.5°	102.0	126.0	168.1	246.7	383.7	581.2	789.6	947.9	1026.2	1037.4	1013.1
105°	122.4	145.3	183.2	248.7	359.3	518.0	703.6	884.4	1021.0	1099.1	1131.6
107.5°	143.4	166.0	200.8	260.4	354.9	482.6	634.1	794.3	939.7	1049.8	1120.1
110°	157.9	179.3	214.0	269.2	356.1	470.6	599.4	739.9	876.5	991.0	1077.8



TEST NUMBER: P332555-840

CATALOG NUMBER: S124DIP-S575D810U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	171.8	193.2	226.6	278.7	359.9	464.9	579.8	700.1	820.9	929.1	1015.9
115°	193.5	214.8	246.4	293.8	367.2	461.9	561.4	660.1	757.3	849.6	925.4
117.5°	213.4	235.5	265.5	309.0	375.0	461.1	553.2	640.6	720.9	793.6	857.9
120°	226.6	248.7	278.7	319.8	380.6	461.1	548.8	631.7	705.2	768.3	824.4
122.5°	239.8	261.4	291.3	329.9	386.3	460.5	543.7	624.1	695.0	752.6	801.6
125°	258.2	280.3	308.7	345.1	394.9	459.6	535.3	611.2	679.1	733.6	777.0
127.5°	275.1	297.4	324.9	358.2	401.6	457.9	524.1	595.4	660.2	714.6	755.9
130°	285.9	308.7	335.6	366.4	406.7	457.2	517.3	582.8	645.1	698.8	740.6
132.5°	296.0	317.6	344.5	374.6	411.1	456.6	510.9	569.5	628.0	680.5	722.4
135°	310.3	330.8	356.9	385.4	417.7	455.7	501.4	551.2	602.5	650.7	690.1
137.5°	322.4	342.0	366.4	392.9	421.6	455.4	493.2	534.6	578.0	618.6	654.3
140°	330.0	349.0	372.7	398.0	424.9	454.8	488.8	525.1	562.2	597.7	631.0
142.5°	337.0	355.4	378.4	401.7	427.4	454.8	485.0	516.2	549.0	579.5	608.1
145°	346.7	364.1	384.6	405.9	428.8	453.2	478.5	503.8	530.7	554.3	576.4
147.5°	356.0	371.6	390.9	409.5	429.6	450.4	472.7	493.5	514.8	533.8	551.2
150°	361.6	376.7	394.0	411.4	429.6	448.5	468.3	487.2	505.3	521.2	535.3
152.5°	367.4	381.1	396.6	412.6	428.3	445.4	463.2	480.3	495.8	510.4	522.1
155°	375.1	386.9	400.3	413.7	426.4	440.6	455.7	469.8	482.5	494.3	503.8
157.5°	382.3	391.6	403.0	413.7	424.3	435.8	447.9	458.6	469.2	479.2	486.8
160°	386.2	394.9	404.2	413.7	422.4	431.9	442.2	451.7	460.4	469.1	475.3
162.5°	389.9	396.7	405.6	413.7	420.6	428.2	437.2	444.7	452.1	459.0	464.6
165°	394.0	398.8	405.9	412.2	417.0	422.4	428.8	435.0	439.8	445.4	449.3
167.5°	396.9	400.5	405.8	410.3	413.1	416.8	421.2	425.8	429.4	433.8	436.2
170°	398.8	401.1	405.1	409.0	410.6	412.9	416.2	420.1	422.4	425.7	428.0
172.5°	400.0	401.7	404.5	407.8	408.1	409.2	411.7	415.1	416.8	418.7	420.4
175°	401.9	401.9	403.5	405.9	405.1	405.1	406.7	408.3	409.0	410.6	410.6
177.5°	401.9	401.9	402.5	403.8	402.5	402.5	403.1	403.8	404.5	404.5	405.1
180°	401.9	401.9	401.9	401.9	401.9	401.9	401.9	401.9	401.9	401.9	401.9



TEST NUMBER: P332555-840

CATALOG NUMBER: S124DIP-S575D810U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	948.5	948.5	948.5	948.5	948.5	948.5	948.5	948.5	948.5	948.5	948.5
2.5°	903.8	903.2	901.0	900.7	901.0	903.2	903.8	904.5	905.4	908.6	904.8
5°	835.0	833.0	831.8	836.2	831.8	833.0	835.0	837.3	841.2	841.6	845.6
7.5°	783.0	781.4	778.0	776.9	778.0	781.4	783.0	784.5	788.4	791.7	797.6
10°	749.7	748.1	745.0	744.2	745.0	748.1	749.7	753.7	757.5	761.8	765.8
12.5°	717.6	714.5	713.9	714.7	713.9	714.5	717.6	722.9	733.1	733.0	733.8
15°	675.0	673.5	669.1	670.3	669.1	673.5	675.0	680.1	684.9	690.7	696.6
17.5°	633.1	631.2	625.9	630.6	625.9	631.2	633.1	635.8	641.9	650.3	659.0
20°	606.6	603.5	600.8	600.4	600.8	603.5	606.6	609.5	616.1	623.2	629.9
22.5°	581.5	578.7	578.5	575.8	578.5	578.7	581.5	585.8	592.5	596.4	602.8
25°	550.1	547.3	546.5	544.6	546.5	547.3	550.1	553.2	557.5	560.7	567.7
27.5°	525.9	524.6	523.2	523.8	523.2	524.6	525.9	526.3	528.4	532.5	536.5
30°	511.2	510.8	510.0	510.0	510.0	510.8	511.2	510.0	512.0	513.9	517.1
32.5°	499.0	498.9	499.3	499.3	499.3	498.9	499.0	497.2	497.9	498.6	500.1
35°	481.7	482.9	483.7	482.5	483.7	482.9	481.7	480.2	479.0	476.3	477.0
37.5°	466.2	467.4	468.5	469.8	468.5	467.4	466.2	462.9	460.1	457.7	454.8
40°	454.2	457.0	457.8	459.7	457.8	457.0	454.2	450.7	447.6	444.7	441.6
42.5°	442.9	446.0	448.0	448.4	448.0	446.0	442.9	439.4	434.6	431.3	426.9
45°	425.6	428.7	431.4	431.4	431.4	428.7	425.6	419.6	414.5	409.4	405.1
47.5°	407.6	412.1	414.9	415.6	414.9	412.1	407.6	401.5	394.4	388.1	381.8
50°	395.3	400.8	403.5	405.5	403.5	400.8	395.3	388.6	381.1	373.2	365.8
52.5°	383.3	388.8	392.5	393.5	392.5	388.8	383.3	375.1	366.1	357.6	351.0
55°	362.6	370.5	374.9	376.4	374.9	370.5	362.6	353.7	345.0	334.4	325.0
57.5°	343.2	350.4	355.5	356.6	355.5	350.4	343.2	332.5	321.4	310.1	300.0
60°	328.1	336.0	342.2	343.5	342.2	336.0	328.1	317.5	305.7	294.7	282.2
62.5°	312.7	320.8	326.5	329.6	326.5	320.8	312.7	301.4	288.7	276.5	263.9
65°	286.1	294.3	299.8	300.9	299.8	294.3	286.1	275.1	261.7	248.7	238.1
67.5°	257.0	265.2	268.8	271.1	268.8	265.2	257.0	246.6	233.4	219.9	207.9
70°	236.5	243.2	247.1	249.1	247.1	243.2	236.5	225.5	214.5	200.8	187.8
72.5°	213.3	220.3	224.8	225.2	224.8	220.3	213.3	203.9	192.2	179.5	168.0
75°	177.6	183.9	186.2	186.2	186.2	183.9	177.6	168.5	159.2	149.0	137.5
77.5°	140.6	143.8	146.8	147.4	146.8	143.8	140.6	134.1	126.3	116.0	107.6
80°	116.7	118.7	121.0	121.0	121.0	118.7	116.7	110.8	103.3	94.7	88.1
82.5°	92.2	93.8	96.1	95.8	96.1	93.8	92.2	87.6	81.3	75.5	69.5
85°	55.7	59.4	59.0	58.2	59.0	59.4	55.7	56.6	50.7	46.8	41.3
87.5°	28.5	29.0	29.7	30.4	29.7	29.0	28.5	27.4	24.5	22.8	21.4
90°	16.6	17.4	16.6	16.6	16.6	17.4	16.6	15.8	15.8	15.0	14.2
92.5°	67.8	63.5	60.8	60.8	60.8	63.5	67.8	77.1	92.9	116.7	155.1
95°	241.7	217.1	203.0	192.7	203.0	217.1	241.7	280.3	356.9	462.7	585.1
97.5°	602.7	555.1	531.4	515.0	531.4	555.1	602.7	659.3	741.7	819.0	864.4
100°	802.2	754.1	730.4	724.1	730.4	754.1	802.2	871.0	929.4	968.1	952.3
102.5°	971.0	936.0	911.1	906.1	911.1	936.0	971.0	1013.1	1037.4	1026.2	947.9
105°	1133.2	1126.8	1115.8	1111.1	1115.8	1126.8	1133.2	1131.6	1099.1	1021.0	884.4
107.5°	1159.2	1177.2	1185.1	1187.1	1185.1	1177.2	1159.2	1120.1	1049.8	939.7	794.3
110°	1133.9	1167.1	1181.3	1188.4	1181.3	1167.1	1133.9	1077.8	991.0	876.5	739.9



TEST NUMBER: P332555-840

CATALOG NUMBER: S124DIP-S575D810U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1079.5	1119.7	1139.6	1151.1	1139.6	1119.7	1079.5	1015.9	929.1	820.9	700.1
115°	987.8	1035.2	1060.5	1066.8	1060.5	1035.2	987.8	925.4	849.6	757.3	660.1
117.5°	911.1	950.9	976.4	981.4	976.4	950.9	911.1	857.9	793.6	720.9	640.6
120°	869.4	904.1	924.6	933.3	924.6	904.1	869.4	824.4	768.3	705.2	631.7
122.5°	839.7	869.4	886.8	895.4	886.8	869.4	839.7	801.6	752.6	695.0	624.1
125°	808.6	831.5	846.5	851.2	846.5	831.5	808.6	777.0	733.6	679.1	611.2
127.5°	787.6	808.0	820.6	825.4	820.6	808.0	787.6	755.9	714.6	660.2	595.4
130°	773.1	792.8	805.5	810.2	805.5	792.8	773.1	740.6	698.8	645.1	582.8
132.5°	754.1	776.4	788.4	793.1	788.4	776.4	754.1	722.4	680.5	628.0	569.5
135°	721.8	743.9	756.5	761.2	756.5	743.9	721.8	690.1	650.7	602.5	551.2
137.5°	683.8	705.6	716.0	721.8	716.0	705.6	683.8	654.3	618.6	578.0	534.6
140°	658.5	675.9	687.0	693.3	687.0	675.9	658.5	631.0	597.7	562.2	525.1
142.5°	632.7	648.7	658.5	663.0	658.5	648.7	632.7	608.1	579.5	549.0	516.2
145°	596.2	609.6	617.5	621.5	617.5	609.6	596.2	576.4	554.3	530.7	503.8
147.5°	565.7	577.2	583.2	584.6	583.2	577.2	565.7	551.2	533.8	514.8	493.5
150°	548.1	558.3	563.0	563.8	563.0	558.3	548.1	535.3	521.2	505.3	487.2
152.5°	532.8	541.2	544.0	544.8	544.0	541.2	532.8	522.1	510.4	495.8	480.3
155°	511.7	518.0	520.4	520.4	520.4	518.0	511.7	503.8	494.3	482.5	469.8
157.5°	492.7	497.5	498.9	498.9	498.9	497.5	492.7	486.8	479.2	469.2	458.6
160°	480.1	484.8	485.6	485.6	485.6	484.8	480.1	475.3	469.1	460.4	451.7
162.5°	468.1	472.8	473.6	473.0	473.6	472.8	468.1	464.6	459.0	452.1	444.7
165°	452.4	455.7	454.8	454.0	454.8	455.7	452.4	449.3	445.4	439.8	435.0
167.5°	437.8	439.8	439.7	439.0	439.7	439.8	437.8	436.2	433.8	429.4	425.8
170°	429.6	430.3	429.6	429.6	429.6	430.3	429.6	428.0	425.7	422.4	420.1
172.5°	421.3	422.1	421.3	420.1	421.3	422.1	421.3	420.4	418.7	416.8	415.1
175°	410.6	412.2	410.6	409.0	410.6	412.2	410.6	410.6	410.6	409.0	408.3
177.5°	404.5	405.1	403.8	402.5	403.8	405.1	404.5	405.1	404.5	404.5	403.8
180°	401.9	401.9	401.9	401.9	401.9	401.9	401.9	401.9	401.9	401.9	401.9



TEST NUMBER: P332555-840

CATALOG NUMBER: S124DIP-S575D810U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	948.5	948.5	948.5	948.5	948.5	948.5	948.5	948.5	948.5	948.5	948.5
2.5°	906.7	908.0	913.0	917.7	923.3	927.5	930.3	933.4	940.0	945.3	950.4
5°	849.5	851.4	861.7	868.8	880.9	891.5	899.8	908.8	919.5	933.9	947.4
7.5°	799.1	806.5	817.6	829.1	841.5	855.4	867.5	881.1	899.4	919.4	940.0
10°	770.5	778.8	790.5	804.0	815.7	831.8	846.8	862.8	883.6	908.1	932.4
12.5°	741.9	755.5	764.5	780.3	793.0	806.4	822.2	843.3	867.7	893.2	922.6
15°	706.1	713.6	730.8	739.5	757.5	778.0	793.7	815.0	838.5	872.3	905.2
17.5°	664.7	674.6	688.3	704.8	725.6	741.5	761.1	782.9	812.6	846.2	887.6
20°	637.7	646.0	662.9	681.0	703.0	719.8	740.6	761.8	792.5	828.3	871.5
22.5°	613.5	621.5	639.2	656.1	677.5	698.1	719.9	744.6	774.0	811.6	855.8
25°	576.0	586.6	602.4	619.7	640.1	663.7	687.2	709.2	740.6	780.3	827.5
27.5°	542.8	551.3	562.7	582.3	605.5	628.2	651.7	679.3	709.5	751.5	800.4
30°	521.4	529.3	540.7	558.8	580.4	604.7	629.0	655.8	687.2	728.8	778.8
32.5°	504.4	510.4	520.6	536.7	556.4	582.1	606.1	633.8	666.8	707.8	756.5
35°	479.4	484.4	488.4	503.7	521.4	545.0	569.4	598.8	630.7	669.5	718.2
37.5°	454.7	456.5	462.2	472.3	489.4	511.1	533.7	562.7	595.3	634.9	678.8
40°	439.7	440.5	444.0	453.4	468.4	488.8	510.8	539.5	570.5	607.8	651.5
42.5°	425.0	424.4	427.7	434.2	448.3	466.8	488.5	514.6	545.7	580.2	621.3
45°	401.5	401.5	400.8	406.3	417.7	435.8	453.8	479.0	504.9	538.7	573.3
47.5°	377.2	375.0	375.7	378.5	388.1	402.9	421.2	441.8	464.6	493.3	523.6
50°	361.5	358.3	357.2	360.3	368.9	381.9	399.2	417.3	438.9	464.0	490.0
52.5°	344.2	341.0	338.9	341.1	349.1	361.1	376.9	392.7	412.1	432.6	455.0
55°	317.5	314.0	312.8	313.6	319.4	328.9	342.2	356.8	371.3	388.2	403.9
57.5°	291.1	285.4	284.3	283.9	287.9	296.6	307.7	320.3	330.9	341.1	357.9
60°	273.9	266.8	264.5	264.1	267.2	274.3	284.5	297.0	304.5	311.5	326.1
62.5°	255.3	248.5	243.4	243.9	246.7	253.5	262.5	271.6	276.5	284.3	294.1
65°	226.7	218.0	214.1	213.0	214.5	220.0	227.1	233.0	238.5	241.7	251.1
67.5°	198.1	190.9	185.1	183.7	183.0	186.7	192.5	196.1	200.0	202.8	208.3
70°	178.0	171.7	164.6	162.3	161.9	165.0	170.6	171.0	176.4	177.6	183.5
72.5°	158.1	150.4	145.4	143.1	141.5	144.3	147.9	149.0	151.9	154.0	157.1
75°	127.3	121.4	116.7	113.2	112.0	113.5	113.5	115.5	117.4	118.7	122.2
77.5°	100.2	93.4	87.9	85.8	84.4	83.4	84.2	85.4	84.5	86.5	87.4
80°	81.3	74.2	70.0	69.2	66.8	64.8	64.4	65.6	64.0	64.8	67.2
82.5°	62.8	58.3	53.6	52.8	49.8	48.8	48.4	47.7	47.7	47.6	48.0
85°	37.4	34.5	31.4	29.5	28.3	26.4	26.4	25.5	24.7	23.9	24.3
87.5°	17.8	17.3	15.5	14.1	13.5	11.3	11.3	10.2	9.8	9.0	8.3
90°	13.4	14.2	12.6	11.0	11.0	6.4	6.4	5.6	4.7	2.3	0.8
92.5°	208.6	250.4	219.2	159.5	98.3	58.1	41.7	30.2	20.5	13.1	9.0
95°	661.8	643.6	485.6	296.9	167.4	98.7	65.5	46.6	36.4	28.4	26.1
97.5°	831.3	677.8	454.5	266.9	160.0	107.0	79.3	63.0	53.5	46.8	46.8
100°	837.0	634.9	412.2	251.2	161.9	115.3	90.0	75.0	65.5	60.0	60.0
102.5°	789.6	581.2	383.7	246.7	168.1	126.0	102.0	87.7	78.8	73.9	72.6
105°	703.6	518.0	359.3	248.7	183.2	145.3	122.4	108.2	98.7	94.7	92.4
107.5°	634.1	482.6	354.9	260.4	200.8	166.0	143.4	129.8	119.7	115.7	114.2
110°	599.4	470.6	356.1	269.2	214.0	179.3	157.9	143.7	134.2	130.3	128.8



TEST NUMBER: P332555-840

CATALOG NUMBER: S124DIP-S575D810U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	579.8	464.9	359.9	278.7	226.6	193.2	171.8	157.6	148.8	144.2	142.6
115°	561.4	461.9	367.2	293.8	246.4	214.8	193.5	178.4	170.6	165.0	162.7
117.5°	553.2	461.1	375.0	309.0	265.5	235.5	213.4	199.3	190.7	185.7	183.5
120°	548.8	461.1	380.6	319.8	278.7	248.7	226.6	213.2	204.5	198.9	197.4
122.5°	543.7	460.5	386.3	329.9	291.3	261.4	239.8	225.2	217.1	211.7	210.1
125°	535.3	459.6	394.9	345.1	308.7	280.3	258.2	243.2	234.5	229.7	226.6
127.5°	524.1	457.9	401.6	358.2	324.9	297.4	275.1	259.4	249.5	243.9	241.4
130°	517.3	457.2	406.7	366.4	335.6	308.7	285.9	270.8	259.0	252.7	249.5
132.5°	510.9	456.6	411.1	374.6	344.5	317.6	296.0	279.7	268.5	260.2	257.7
135°	501.4	455.7	417.7	385.4	356.9	330.8	310.3	293.8	280.3	272.5	269.2
137.5°	493.2	455.4	421.6	392.9	366.4	342.0	322.4	305.3	292.5	283.8	280.8
140°	488.8	454.8	424.9	398.0	372.7	349.0	330.0	313.5	300.0	291.3	289.0
142.5°	485.0	454.8	427.4	401.7	378.4	355.4	337.0	321.0	308.3	300.2	297.8
145°	478.5	453.2	428.8	405.9	384.6	364.1	346.7	331.6	320.6	312.7	310.3
147.5°	472.7	450.4	429.6	409.5	390.9	371.6	356.0	343.5	332.1	325.2	324.4
150°	468.3	448.5	429.6	411.4	394.0	376.7	361.6	349.8	340.3	334.1	333.3
152.5°	463.2	445.4	428.3	412.6	396.6	381.1	367.4	356.8	347.9	341.6	341.4
155°	455.7	440.6	426.4	413.7	400.3	386.9	375.1	366.4	358.5	353.8	352.9
157.5°	447.9	435.8	424.3	413.7	403.0	391.6	382.3	374.8	368.6	364.2	364.2
160°	442.2	431.9	422.4	413.7	404.2	394.9	386.2	379.8	374.3	371.1	371.1
162.5°	437.2	428.2	420.6	413.7	405.6	396.7	389.9	384.3	379.3	376.8	377.5
165°	428.8	422.4	417.0	412.2	405.9	398.8	394.0	390.1	386.2	384.6	384.6
167.5°	421.2	416.8	413.1	410.3	405.8	400.5	396.9	394.7	391.6	390.9	391.6
170°	416.2	412.9	410.6	409.0	405.1	401.1	398.8	397.2	394.9	394.0	394.9
172.5°	411.7	409.2	408.1	407.8	404.5	401.7	400.0	399.1	397.4	397.2	398.0
175°	406.7	405.1	405.1	405.9	403.5	401.9	401.9	401.1	400.3	400.3	401.1
177.5°	403.1	402.5	402.5	403.8	402.5	401.9	401.9	401.9	401.3	401.9	402.5
180°	401.9	401.9	401.9	401.9	401.9	401.9	401.9	401.9	401.9	401.9	401.9



TEST NUMBER: P332555-840

CATALOG NUMBER: S124DIP-S575D810U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	948.5	948.5	948.5	948.5	948.5	948.5	948.5	948.5	948.5	948.5	948.5
2.5°	954.8	958.0	962.0	969.0	971.5	974.6	979.0	978.7	980.0	984.6	994.7
5°	958.4	970.5	982.3	996.4	1011.4	1021.2	1034.6	1042.8	1051.1	1061.7	1079.7
7.5°	959.8	979.1	1000.7	1025.5	1047.6	1073.1	1093.0	1111.7	1128.5	1150.9	1172.5
10°	957.6	983.5	1011.4	1042.8	1076.2	1104.5	1130.0	1159.1	1183.9	1210.9	1235.4
12.5°	953.4	984.7	1022.1	1057.2	1096.3	1138.1	1169.9	1199.3	1232.2	1263.4	1301.0
15°	944.2	987.0	1030.7	1077.0	1129.2	1177.6	1223.6	1261.6	1297.1	1343.8	1392.9
17.5°	932.4	978.6	1033.6	1089.7	1144.4	1199.6	1256.5	1313.7	1358.4	1416.4	1454.9
20°	921.4	974.8	1031.4	1098.2	1152.9	1221.6	1278.2	1333.5	1394.8	1452.6	1498.6
22.5°	905.9	964.4	1024.5	1091.0	1162.9	1231.6	1297.1	1357.2	1418.5	1481.3	1536.9
25°	886.5	939.5	1010.6	1086.0	1157.5	1232.2	1307.3	1382.7	1448.7	1515.1	1567.0
27.5°	853.1	920.1	986.3	1064.2	1143.7	1228.1	1308.4	1387.4	1456.4	1511.1	1543.3
30°	836.2	894.2	966.2	1044.4	1130.4	1221.2	1304.8	1382.3	1446.7	1490.4	1503.3
32.5°	811.0	871.0	941.4	1022.4	1113.5	1206.7	1293.8	1366.9	1420.7	1443.5	1427.8
35°	773.7	827.9	899.0	981.9	1076.6	1176.0	1262.0	1323.7	1351.3	1329.7	1275.8
37.5°	728.8	782.6	854.0	935.4	1033.5	1134.5	1212.3	1256.7	1247.6	1193.9	1113.6
40°	697.4	747.7	815.7	903.7	999.2	1100.6	1168.9	1193.0	1167.8	1090.8	1005.5
42.5°	662.6	711.6	779.8	864.7	965.8	1059.3	1118.9	1121.0	1078.8	986.7	901.1
45°	609.5	656.2	720.6	809.0	902.5	990.6	1029.9	1010.6	932.8	843.9	757.9
47.5°	557.0	597.5	661.1	745.0	833.7	907.9	927.4	892.7	809.8	723.6	643.8
50°	518.7	559.6	619.2	699.4	785.1	849.1	858.5	812.5	731.2	644.4	581.9
52.5°	481.9	522.4	580.0	654.1	732.6	790.3	790.6	737.4	656.4	579.1	520.9
55°	427.9	464.4	516.3	582.7	652.7	697.8	686.8	631.8	561.5	494.3	443.6
57.5°	375.9	407.7	455.4	510.9	572.5	609.8	591.5	538.6	475.7	418.8	380.3
60°	342.2	372.4	413.3	465.6	517.5	546.5	529.3	481.3	423.5	377.6	344.2
62.5°	309.5	335.1	374.4	419.7	467.8	489.4	473.9	426.7	376.8	335.2	308.0
65°	263.3	284.1	315.5	354.5	389.4	407.9	394.9	350.8	312.8	282.9	261.3
67.5°	220.0	236.3	260.1	291.3	321.0	331.0	319.2	288.5	256.3	232.4	217.1
70°	190.2	205.5	225.5	249.5	275.4	286.1	274.3	249.9	223.6	201.6	186.6
72.5°	164.1	175.9	192.9	213.4	233.6	244.3	236.2	212.8	190.6	174.2	161.5
75°	124.9	135.1	146.9	161.5	177.2	184.3	177.2	161.1	145.7	133.6	124.5
77.5°	90.9	96.3	105.4	116.3	126.1	131.6	125.4	114.5	105.1	96.8	92.3
80°	69.2	73.1	79.4	88.1	94.7	99.8	95.8	86.8	79.4	73.8	71.9
82.5°	50.3	52.9	57.1	63.5	68.0	70.6	68.9	62.3	59.3	54.3	52.4
85°	24.7	26.4	29.1	31.0	34.9	35.3	35.7	33.0	30.3	29.1	27.5
87.5°	9.0	9.8	10.8	11.9	13.2	14.4	14.1	14.4	13.5	13.0	11.9
90°	2.3	4.7	5.6	6.4	6.4	11.0	11.0	12.6	14.2	13.4	14.2
92.5°	13.1	20.5	30.2	41.7	58.1	98.3	159.5	219.2	250.4	208.6	155.1
95°	28.4	36.4	46.6	65.5	98.7	167.4	296.9	485.6	643.6	661.8	585.1
97.5°	46.8	53.5	63.0	79.3	107.0	160.0	266.9	454.5	677.8	831.3	864.4
100°	60.0	65.5	75.0	90.0	115.3	161.9	251.2	412.2	634.9	837.0	952.3
102.5°	73.9	78.8	87.7	102.0	126.0	168.1	246.7	383.7	581.2	789.6	947.9
105°	94.7	98.7	108.2	122.4	145.3	183.2	248.7	359.3	518.0	703.6	884.4
107.5°	115.7	119.7	129.8	143.4	166.0	200.8	260.4	354.9	482.6	634.1	794.3
110°	130.3	134.2	143.7	157.9	179.3	214.0	269.2	356.1	470.6	599.4	739.9





TEST NUMBER: P332555-840

CATALOG NUMBER: S124DIP-S575D810U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	144.2	148.8	157.6	171.8	193.2	226.6	278.7	359.9	464.9	579.8	700.1
115°	165.0	170.6	178.4	193.5	214.8	246.4	293.8	367.2	461.9	561.4	660.1
117.5°	185.7	190.7	199.3	213.4	235.5	265.5	309.0	375.0	461.1	553.2	640.6
120°	198.9	204.5	213.2	226.6	248.7	278.7	319.8	380.6	461.1	548.8	631.7
122.5°	211.7	217.1	225.2	239.8	261.4	291.3	329.9	386.3	460.5	543.7	624.1
125°	229.7	234.5	243.2	258.2	280.3	308.7	345.1	394.9	459.6	535.3	611.2
127.5°	243.9	249.5	259.4	275.1	297.4	324.9	358.2	401.6	457.9	524.1	595.4
130°	252.7	259.0	270.8	285.9	308.7	335.6	366.4	406.7	457.2	517.3	582.8
132.5°	260.2	268.5	279.7	296.0	317.6	344.5	374.6	411.1	456.6	510.9	569.5
135°	272.5	280.3	293.8	310.3	330.8	356.9	385.4	417.7	455.7	501.4	551.2
137.5°	283.8	292.5	305.3	322.4	342.0	366.4	392.9	421.6	455.4	493.2	534.6
140°	291.3	300.0	313.5	330.0	349.0	372.7	398.0	424.9	454.8	488.8	525.1
142.5°	300.2	308.3	321.0	337.0	355.4	378.4	401.7	427.4	454.8	485.0	516.2
145°	312.7	320.6	331.6	346.7	364.1	384.6	405.9	428.8	453.2	478.5	503.8
147.5°	325.2	332.1	343.5	356.0	371.6	390.9	409.5	429.6	450.4	472.7	493.5
150°	334.1	340.3	349.8	361.6	376.7	394.0	411.4	429.6	448.5	468.3	487.2
152.5°	341.6	347.9	356.8	367.4	381.1	396.6	412.6	428.3	445.4	463.2	480.3
155°	353.8	358.5	366.4	375.1	386.9	400.3	413.7	426.4	440.6	455.7	469.8
157.5°	364.2	368.6	374.8	382.3	391.6	403.0	413.7	424.3	435.8	447.9	458.6
160°	371.1	374.3	379.8	386.2	394.9	404.2	413.7	422.4	431.9	442.2	451.7
162.5°	376.8	379.3	384.3	389.9	396.7	405.6	413.7	420.6	428.2	437.2	444.7
165°	384.6	386.2	390.1	394.0	398.8	405.9	412.2	417.0	422.4	428.8	435.0
167.5°	390.9	391.6	394.7	396.9	400.5	405.8	410.3	413.1	416.8	421.2	425.8
170°	394.0	394.9	397.2	398.8	401.1	405.1	409.0	410.6	412.9	416.2	420.1
172.5°	397.2	397.4	399.1	400.0	401.7	404.5	407.8	408.1	409.2	411.7	415.1
175°	400.3	400.3	401.1	401.9	401.9	403.5	405.9	405.1	405.1	406.7	408.3
177.5°	401.9	401.3	401.9	401.9	401.9	402.5	403.8	402.5	402.5	403.1	403.8
180°	401.9	401.9	401.9	401.9	401.9	401.9	401.9	401.9	401.9	401.9	401.9



TEST NUMBER: P332555-840

CATALOG NUMBER: S124DIP-S575D810U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	948.5	948.5	948.5	948.5	948.5	948.5	948.5
2.5°	999.8	1000.4	1003.2	1005.4	1006.0	1009.2	1009.5
5°	1087.6	1094.3	1107.2	1108.4	1110.3	1120.6	1112.8
7.5°	1190.5	1207.5	1218.8	1228.8	1232.4	1236.9	1236.0
10°	1256.6	1281.7	1294.2	1314.3	1315.1	1320.2	1317.1
12.5°	1322.9	1352.1	1375.0	1378.8	1395.5	1398.2	1402.6
15°	1416.8	1447.9	1479.8	1491.2	1514.3	1519.8	1528.4
17.5°	1505.2	1536.9	1559.2	1588.7	1598.2	1610.9	1602.4
20°	1553.6	1588.2	1616.5	1639.6	1649.5	1656.6	1655.8
22.5°	1582.9	1617.7	1640.6	1658.2	1667.4	1670.4	1670.2
25°	1601.1	1621.2	1628.3	1635.0	1624.8	1621.2	1622.8
27.5°	1550.2	1545.0	1526.6	1502.4	1477.2	1457.2	1446.4
30°	1480.2	1449.5	1421.6	1372.9	1347.7	1332.8	1319.4
32.5°	1380.8	1332.2	1278.6	1234.0	1205.3	1183.2	1179.8
35°	1210.6	1137.5	1071.9	1017.2	989.0	965.0	959.5
37.5°	1029.3	953.3	894.2	846.1	815.7	798.8	783.0
40°	908.8	843.6	785.5	744.6	721.4	709.2	699.4
42.5°	816.1	756.5	698.7	667.5	646.6	639.1	633.4
45°	688.0	632.6	592.5	569.0	556.7	544.2	538.3
47.5°	585.4	540.4	513.9	493.9	480.9	473.4	469.6
50°	527.3	490.4	466.8	451.5	439.7	433.7	430.6
52.5°	475.7	445.5	425.7	413.4	405.5	401.1	399.8
55°	409.8	386.7	374.1	363.5	357.6	353.7	352.0
57.5°	356.2	338.4	328.2	319.4	317.2	313.9	312.8
60°	321.0	307.3	298.6	292.8	290.7	286.8	287.6
62.5°	289.9	278.6	271.2	267.9	265.3	262.0	263.1
65°	245.2	236.9	233.0	229.8	226.7	224.8	226.3
67.5°	205.7	200.1	194.7	192.9	191.4	191.1	189.3
70°	180.0	175.2	170.6	169.4	169.4	167.7	167.3
72.5°	155.1	151.7	148.6	147.6	146.4	147.0	145.4
75°	119.9	117.0	115.9	114.7	114.3	114.3	113.2
77.5°	88.6	86.5	84.6	84.6	83.2	82.7	82.5
80°	67.2	66.4	64.8	64.8	64.0	64.4	63.6
82.5°	50.5	49.4	49.1	48.5	47.4	47.5	46.7
85°	27.1	26.0	25.5	24.3	23.5	24.3	23.5
87.5°	12.4	12.3	11.9	11.5	11.3	11.2	10.2
90°	15.0	15.8	15.8	16.6	17.4	16.6	16.6
92.5°	116.7	92.9	77.1	67.8	63.5	60.8	60.8
95°	462.7	356.9	280.3	241.7	217.1	203.0	192.7
97.5°	819.0	741.7	659.3	602.7	555.1	531.4	515.0
100°	968.1	929.4	871.0	802.2	754.1	730.4	724.1
102.5°	1026.2	1037.4	1013.1	971.0	936.0	911.1	906.1
105°	1021.0	1099.1	1131.6	1133.2	1126.8	1115.8	1111.1
107.5°	939.7	1049.8	1120.1	1159.2	1177.2	1185.1	1187.1
110°	876.5	991.0	1077.8	1133.9	1167.1	1181.3	1188.4



TEST NUMBER: P332555-840

CATALOG NUMBER: S124DIP-S575D810U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	820.9	929.1	1015.9	1079.5	1119.7	1139.6	1151.1
115°	757.3	849.6	925.4	987.8	1035.2	1060.5	1066.8
117.5°	720.9	793.6	857.9	911.1	950.9	976.4	981.4
120°	705.2	768.3	824.4	869.4	904.1	924.6	933.3
122.5°	695.0	752.6	801.6	839.7	869.4	886.8	895.4
125°	679.1	733.6	777.0	808.6	831.5	846.5	851.2
127.5°	660.2	714.6	755.9	787.6	808.0	820.6	825.4
130°	645.1	698.8	740.6	773.1	792.8	805.5	810.2
132.5°	628.0	680.5	722.4	754.1	776.4	788.4	793.1
135°	602.5	650.7	690.1	721.8	743.9	756.5	761.2
137.5°	578.0	618.6	654.3	683.8	705.6	716.0	721.8
140°	562.2	597.7	631.0	658.5	675.9	687.0	693.3
142.5°	549.0	579.5	608.1	632.7	648.7	658.5	663.0
145°	530.7	554.3	576.4	596.2	609.6	617.5	621.5
147.5°	514.8	533.8	551.2	565.7	577.2	583.2	584.6
150°	505.3	521.2	535.3	548.1	558.3	563.0	563.8
152.5°	495.8	510.4	522.1	532.8	541.2	544.0	544.8
155°	482.5	494.3	503.8	511.7	518.0	520.4	520.4
157.5°	469.2	479.2	486.8	492.7	497.5	498.9	498.9
160°	460.4	469.1	475.3	480.1	484.8	485.6	485.6
162.5°	452.1	459.0	464.6	468.1	472.8	473.6	473.0
165°	439.8	445.4	449.3	452.4	455.7	454.8	454.0
167.5°	429.4	433.8	436.2	437.8	439.8	439.7	439.0
170°	422.4	425.7	428.0	429.6	430.3	429.6	429.6
172.5°	416.8	418.7	420.4	421.3	422.1	421.3	420.1
175°	409.0	410.6	410.6	410.6	412.2	410.6	409.0
177.5°	404.5	404.5	405.1	404.5	405.1	403.8	402.5
180°	401.9	401.9	401.9	401.9	401.9	401.9	401.9

(END OF REPORT)