

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332573-830

Luminaire Tested: **S124DIP-S575D1205U830-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332573-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIP-S575D1205U830-4F0-1E-UDD-A4
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 575 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1205 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6500.0 lumens
Efficiency: N/A
Efficacy: 131.6 lumens/watt
Spacing Criteria (0/90/45): 1.31 / 1.23 / 1.41
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 49.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332573-830

CATALOG NUMBER: S124DIP-S575D1205U830-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P332573-830

CATALOG NUMBER: S124DIP-S575D1205U830-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	95	95	95	95	76	76	76	60	60	60	45	45	45	38
1	95	91	87	84	86	83	80	77	67	65	63	53	51	50	40	39	38	32
2	87	80	74	69	78	72	67	63	59	55	52	47	44	42	35	34	32	27
3	79	70	63	57	72	64	58	53	52	48	44	41	38	36	31	29	28	23
4	73	62	54	49	66	57	50	45	46	42	38	37	34	31	28	26	24	20
5	67	55	47	42	60	51	44	39	42	36	33	33	30	27	25	23	21	17
6	61	50	42	36	55	45	38	33	37	32	28	30	26	23	23	20	19	15
7	57	45	37	32	51	41	34	29	34	29	25	27	24	21	21	18	16	14
8	52	41	33	28	48	37	31	26	31	26	22	25	21	18	19	17	15	12
9	49	37	30	25	44	34	27	23	28	23	20	23	19	17	18	15	13	11
10	46	34	27	22	41	31	25	21	26	21	18	21	17	15	17	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	7146	7146	7146	7146
5°	8417	7165	6324	7165
10°	10077	7133	5694	7133
15°	11922	7061	5229	7061
20°	13277	6988	4814	6988
25°	13491	6879	4528	6879
30°	11479	6776	4437	6776
35°	8825	6606	4438	6606
40°	6880	6407	4521	6407
45°	5736	6109	4598	6109
50°	5048	5743	4752	5743
55°	4625	5306	4944	5306
60°	4334	4913	5176	4913
65°	4034	4476	5366	4476
70°	3687	4043	5488	4043
75°	3297	3556	5421	3556
80°	2762	2915	5249	2915
85°	2038	2103	5030	2103



TEST NUMBER: P332573-830

CATALOG NUMBER: S124DIP-S575D1205U830-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	86.2	1.3
10°-20°	265.8	4.1
20°-30°	421.5	6.5
30°-40°	469.1	7.2
40°-50°	427.0	6.6
50°-60°	349.0	5.4
60°-70°	249.1	3.8
70°-80°	137.2	2.1
80°-90°	40.5	0.6
90°-100°	402.7	6.2
100°-110°	838.0	12.9
110°-120°	750.6	11.5
120°-130°	631.4	9.7
130°-140°	526.5	8.1
140°-150°	402.2	6.2
150°-160°	282.7	4.3
160°-170°	166.3	2.6
170°-180°	54.1	0.8
0°-30°	773.6	11.9
0°-40°	1242.8	19.1
0°-60°	2018.8	31.1
0°-90°	2445.6	37.6
90°-120°	1991.3	30.6
90°-150°	3551.4	54.6
90°-180°	4054.0	62.4
0°-180°	6500.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	885	885	885	885	885	
5°	1039	884	780	884	1039	106
15°	1426	845	626	845	1426	403
25°	1515	772	508	772	1515	668
35°	896	670	450	670	896	568
45°	502	535	403	535	502	396
55°	329	377	351	377	329	297
65°	211	234	281	234	211	209
75°	106	114	174	114	106	112
85°	22	23	54	23	22	27
90°	23	1	23	1	23	19
95°	267	36	267	36	267	415
105°	1541	128	1541	128	1541	1524
115°	1480	226	1480	226	1480	1469
125°	1181	314	1181	314	1181	1073
135°	1056	373	1056	373	1056	815
145°	862	430	862	430	862	546
155°	722	490	722	490	722	337
165°	630	533	630	533	630	180
175°	567	556	567	556	567	55
180°	558	558	558	558	558	



TEST NUMBER: P332573-830

CATALOG NUMBER: S124DIP-S575D1205U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	885.2	885.2	885.2	885.2	885.2	885.2	885.2	885.2	885.2	885.2	885.2
2.5°	942.2	941.9	939.0	938.4	936.3	933.7	933.1	928.4	919.0	914.6	913.4
5°	1038.6	1045.9	1036.3	1034.5	1033.4	1021.3	1015.1	1007.8	990.9	981.0	973.3
7.5°	1153.6	1154.4	1150.3	1146.9	1137.6	1127.0	1111.2	1094.3	1074.2	1053.3	1037.6
10°	1229.3	1232.2	1227.5	1226.7	1208.0	1196.3	1172.8	1153.0	1130.2	1104.9	1081.9
12.5°	1309.1	1305.0	1302.5	1286.9	1283.4	1262.0	1234.7	1214.3	1179.2	1150.1	1119.4
15°	1426.5	1418.5	1413.3	1391.8	1381.1	1351.4	1322.4	1300.0	1254.2	1210.6	1177.5
17.5°	1495.5	1503.5	1491.7	1482.8	1455.3	1434.5	1404.9	1357.9	1322.0	1267.8	1226.2
20°	1545.4	1546.1	1539.5	1530.3	1508.7	1482.3	1450.0	1398.7	1355.8	1301.8	1244.6
22.5°	1558.9	1559.1	1556.2	1547.7	1531.3	1509.9	1477.3	1434.5	1382.5	1323.9	1266.7
25°	1514.6	1513.2	1516.5	1526.0	1519.8	1513.2	1494.4	1462.5	1414.1	1352.1	1290.5
27.5°	1350.0	1360.1	1378.8	1402.2	1424.8	1442.0	1446.9	1440.4	1410.3	1359.3	1294.9
30°	1231.4	1244.0	1257.8	1281.4	1326.8	1352.8	1381.5	1403.1	1391.0	1350.3	1290.2
32.5°	1101.2	1104.3	1124.9	1151.7	1193.4	1243.4	1288.7	1332.7	1347.3	1326.0	1275.7
35°	895.5	900.7	923.0	949.4	1000.4	1061.7	1129.9	1190.7	1241.0	1261.2	1235.5
37.5°	730.8	745.6	761.3	789.7	834.6	889.8	960.6	1039.3	1114.3	1164.4	1172.9
40°	652.8	661.9	673.4	694.9	733.1	787.4	848.2	938.5	1018.0	1090.0	1113.4
42.5°	591.2	596.5	603.5	623.0	652.1	706.1	761.7	841.0	921.0	1006.9	1046.2
45°	502.4	507.9	519.6	531.0	553.0	590.4	642.2	707.4	787.7	870.6	943.2
47.5°	438.3	441.9	448.8	461.0	479.7	504.4	546.4	600.9	675.3	755.8	833.2
50°	401.9	404.8	410.4	421.4	435.6	457.7	492.1	543.1	601.4	682.5	758.4
52.5°	373.2	374.4	378.4	385.9	397.3	415.8	444.0	486.2	540.5	612.7	688.2
55°	328.6	330.1	333.8	339.2	349.1	360.9	382.5	414.1	461.4	524.1	589.7
57.5°	291.9	292.9	296.1	298.1	306.3	315.8	332.4	355.0	390.9	444.0	502.7
60°	268.4	267.7	271.4	273.2	278.7	286.8	299.6	321.2	352.4	395.3	449.2
62.5°	245.5	244.5	247.6	250.1	253.2	260.0	270.6	287.5	312.8	351.7	398.2
65°	211.2	209.8	211.6	214.5	217.4	221.1	228.8	243.8	264.0	291.9	327.4
67.5°	176.7	178.3	178.6	180.0	181.7	186.7	192.0	202.6	216.9	239.2	269.3
70°	156.2	156.6	158.1	158.1	159.2	163.5	168.0	174.2	188.1	208.7	233.3
72.5°	135.7	137.2	136.7	137.8	138.6	141.6	144.8	150.7	162.6	177.9	198.6
75°	105.7	106.7	106.7	107.1	108.2	109.2	111.9	116.2	124.7	136.0	150.3
77.5°	77.0	77.2	77.7	79.0	79.0	80.8	82.7	86.1	90.4	98.1	106.9
80°	59.4	60.1	59.8	60.5	60.5	62.0	62.7	67.1	68.9	74.1	81.1
82.5°	43.5	44.3	44.2	45.2	45.8	46.1	47.1	48.9	50.7	55.3	58.2
85°	22.0	22.7	22.0	22.7	23.8	24.2	25.3	25.6	27.1	28.3	30.8
87.5°	11.0	12.0	12.2	12.3	12.6	12.9	13.0	12.4	13.4	13.9	14.6
90°	23.0	23.0	24.1	23.0	21.9	21.9	20.8	19.7	18.7	19.7	17.5
92.5°	84.4	84.4	88.0	94.0	106.9	128.8	161.8	215.1	289.4	347.4	304.1
95°	267.2	281.4	301.2	335.2	388.8	495.0	641.8	811.5	917.8	892.6	673.5
97.5°	714.4	737.1	770.0	835.8	914.5	1028.9	1136.0	1199.1	1153.1	940.2	630.4
100°	1004.4	1013.1	1045.9	1112.8	1208.1	1289.1	1342.7	1320.9	1160.9	880.5	571.7
102.5°	1256.7	1263.7	1298.3	1346.7	1405.1	1438.9	1423.3	1314.8	1095.2	806.1	532.3
105°	1541.0	1547.6	1562.9	1571.7	1569.4	1524.6	1416.2	1226.6	975.8	718.5	498.3
107.5°	1646.6	1643.7	1632.8	1607.8	1553.7	1456.0	1303.3	1101.5	879.5	669.4	492.2
110°	1648.3	1638.5	1618.7	1572.7	1495.0	1374.5	1215.7	1026.2	831.3	652.8	494.0



TEST NUMBER: P332573-830

CATALOG NUMBER: S124DIP-S575D1205U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1596.7	1580.6	1553.0	1497.4	1409.1	1288.6	1138.6	971.0	804.1	644.9	499.2
115°	1479.7	1470.9	1435.9	1370.2	1283.6	1178.5	1050.4	915.6	778.7	640.7	509.3
117.5°	1361.1	1354.3	1318.9	1263.7	1189.9	1100.7	999.9	888.4	767.3	639.6	520.0
120°	1294.6	1282.5	1254.1	1205.9	1143.4	1065.6	978.1	876.2	761.2	639.6	527.9
122.5°	1242.0	1229.9	1205.9	1164.7	1111.9	1043.8	964.0	865.6	754.2	638.8	535.8
125°	1180.6	1174.1	1153.3	1121.5	1077.7	1017.5	941.9	847.7	742.5	637.4	547.6
127.5°	1144.7	1138.2	1120.7	1092.4	1048.4	991.2	915.9	825.8	727.0	635.0	557.0
130°	1123.7	1117.1	1099.6	1072.2	1027.4	969.3	894.8	808.3	717.4	634.1	564.0
132.5°	1100.0	1093.4	1076.9	1045.9	1001.9	943.9	871.2	789.9	708.6	633.3	570.1
135°	1055.8	1049.2	1031.7	1001.1	957.2	902.5	835.7	764.5	695.5	632.0	579.4
137.5°	1001.1	993.2	978.7	948.5	907.5	858.0	801.7	741.5	684.1	631.7	584.8
140°	961.6	952.8	937.5	913.4	875.1	829.1	779.8	728.3	678.0	630.8	589.3
142.5°	919.5	913.4	899.8	877.5	843.6	803.7	761.4	716.0	672.7	630.8	592.8
145°	862.0	856.5	845.6	826.9	799.6	768.8	736.0	698.8	663.7	628.7	594.7
147.5°	810.9	809.0	800.6	784.7	764.5	740.4	714.1	684.6	655.6	624.7	595.8
150°	782.0	780.9	774.3	760.1	742.5	722.8	701.0	675.8	649.5	622.1	595.8
152.5°	755.7	754.6	750.6	739.0	724.2	707.9	687.8	666.1	642.4	617.7	594.1
155°	721.8	721.8	718.5	709.7	698.8	685.6	669.2	651.7	632.0	611.1	591.4
157.5°	692.0	692.0	690.0	683.4	675.1	664.6	650.8	636.1	621.2	604.4	588.6
160°	673.5	673.5	672.5	665.9	659.3	650.5	638.5	626.5	613.3	599.1	586.0
162.5°	656.0	657.0	655.8	649.2	644.4	636.6	627.2	616.8	606.3	593.8	583.3
165°	629.8	630.8	632.0	627.5	623.2	617.7	610.0	603.5	594.7	586.0	578.2
167.5°	609.0	609.8	610.0	607.2	605.0	601.7	595.6	590.6	584.2	578.1	573.1
170°	595.8	595.8	596.9	595.8	593.6	590.3	586.0	582.7	577.2	572.8	569.5
172.5°	582.7	584.4	585.5	584.4	583.1	580.7	578.1	575.6	571.1	567.5	566.0
175°	567.3	569.5	571.7	569.5	569.5	569.5	567.3	566.3	564.0	561.8	561.8
177.5°	558.4	560.1	561.8	561.0	561.8	561.0	561.0	560.1	559.2	558.4	558.4
180°	557.5	557.5	557.5	557.5	557.5	557.5	557.5	557.5	557.5	557.5	557.5



TEST NUMBER: P332573-830

CATALOG NUMBER: S124DIP-S575D1205U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	885.2	885.2	885.2	885.2	885.2	885.2	885.2	885.2	885.2	885.2	885.2
2.5°	913.7	909.6	906.7	904.4	897.9	894.1	891.2	887.0	882.3	877.3	871.2
5°	965.6	953.1	944.0	930.0	916.8	905.8	894.5	884.2	871.7	858.2	848.2
7.5°	1020.1	1001.5	977.8	957.2	934.0	913.8	895.8	877.3	858.1	839.4	822.4
10°	1054.7	1030.9	1004.5	973.3	944.0	917.9	893.7	870.2	847.5	824.7	805.3
12.5°	1091.9	1062.2	1023.2	986.7	953.9	919.1	889.9	861.1	833.7	809.8	787.1
15°	1142.0	1099.1	1054.0	1005.2	962.0	921.2	881.3	844.9	814.2	782.6	760.6
17.5°	1172.7	1119.6	1068.1	1017.1	964.7	913.3	870.2	828.4	789.8	758.5	730.8
20°	1193.0	1140.2	1076.0	1025.0	962.6	909.8	860.0	813.4	773.1	739.7	711.1
22.5°	1210.6	1149.5	1085.3	1018.2	956.2	900.1	845.6	798.7	757.5	722.4	694.9
25°	1220.1	1150.1	1080.3	1013.6	943.2	876.8	827.4	772.3	728.3	691.3	661.9
27.5°	1221.2	1146.2	1067.4	993.3	920.6	858.8	796.3	747.1	701.4	662.2	634.0
30°	1217.9	1139.8	1055.1	974.8	901.8	834.6	780.4	726.9	680.2	641.4	612.1
32.5°	1207.6	1126.2	1039.2	954.2	878.6	812.9	757.0	706.1	660.6	622.4	591.5
35°	1177.9	1097.6	1004.8	916.4	839.1	772.7	722.1	670.3	624.9	588.6	558.9
37.5°	1131.5	1058.9	964.6	873.1	797.1	730.5	680.2	633.6	592.6	555.6	525.2
40°	1091.0	1027.2	932.6	843.5	761.3	697.9	650.9	608.0	567.3	532.4	503.5
42.5°	1044.3	988.7	901.4	807.1	727.8	664.1	618.4	579.9	541.5	509.3	480.3
45°	961.2	924.5	842.4	755.1	672.6	612.5	568.8	535.1	502.8	471.3	447.0
47.5°	865.5	847.3	778.2	695.3	617.0	557.7	519.9	488.7	460.4	433.7	412.4
50°	801.3	792.5	732.7	652.8	578.0	522.3	484.1	457.3	433.1	409.6	389.5
52.5°	737.9	737.6	683.7	610.5	541.3	487.6	449.8	424.7	403.8	384.7	366.6
55°	641.0	651.3	609.2	543.8	481.9	433.5	399.4	377.0	362.3	346.6	333.0
57.5°	552.0	569.1	534.3	476.8	425.1	380.5	350.8	334.0	318.4	308.9	299.0
60°	494.0	510.1	483.0	434.6	385.8	347.6	319.4	304.3	290.8	284.2	277.2
62.5°	442.3	456.8	436.6	391.7	349.4	312.7	288.9	274.5	265.3	258.1	253.4
65°	368.5	380.7	363.4	330.8	294.5	265.1	245.7	234.3	225.6	222.6	217.4
67.5°	297.9	309.0	299.6	271.9	242.8	220.6	205.4	194.4	189.3	186.6	183.0
70°	256.0	267.0	257.0	232.9	210.5	191.8	177.5	171.3	165.8	164.7	159.6
72.5°	220.5	228.0	218.0	199.2	180.0	164.2	153.2	146.7	143.7	141.8	139.0
75°	165.4	172.0	165.4	150.7	137.1	126.1	116.6	114.0	110.7	109.6	107.8
77.5°	117.1	122.8	117.7	108.6	98.4	89.9	84.8	81.5	80.8	78.9	79.7
80°	89.4	93.1	88.4	82.2	74.1	68.2	64.6	62.7	60.5	59.8	61.3
82.5°	64.3	65.9	63.4	59.3	53.3	49.4	46.9	44.8	44.4	44.5	44.5
85°	33.4	33.0	32.6	28.9	27.1	24.6	23.1	22.7	22.3	23.1	23.8
87.5°	14.2	14.5	12.9	11.7	10.7	9.5	8.6	7.8	8.6	9.5	10.1
90°	15.4	15.4	8.8	8.8	7.6	6.6	3.3	1.1	3.3	6.6	7.6
92.5°	221.2	136.3	80.6	57.9	41.8	28.5	18.2	12.4	18.2	28.5	41.8
95°	411.8	232.1	137.0	90.9	64.7	50.4	39.4	36.1	39.4	50.4	64.7
97.5°	370.2	221.9	148.5	110.0	87.4	74.3	64.8	64.8	64.8	74.3	87.4
100°	348.3	224.5	159.9	124.9	104.1	90.9	83.2	83.2	83.2	90.9	104.1
102.5°	342.1	233.3	174.8	141.5	121.6	109.3	102.5	100.8	102.5	109.3	121.6
105°	345.0	254.1	201.5	169.8	150.1	137.0	131.4	128.2	131.4	137.0	150.1
107.5°	361.2	278.4	230.3	198.9	180.0	166.1	160.5	158.3	160.5	166.1	180.0
110°	373.4	296.8	248.6	219.0	199.3	186.2	180.7	178.5	180.7	186.2	199.3



TEST NUMBER: P332573-830

CATALOG NUMBER: S124DIP-S575D1205U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	386.6	314.3	267.9	238.4	218.6	206.3	200.0	197.8	200.0	206.3	218.6
115°	407.5	341.7	297.9	268.3	247.5	236.6	228.9	225.6	228.9	236.6	247.5
117.5°	428.7	368.3	326.6	296.0	276.4	264.4	257.6	254.5	257.6	264.4	276.4
120°	443.6	386.6	345.0	314.3	295.7	283.7	276.0	273.8	276.0	283.7	295.7
122.5°	457.6	404.2	362.5	332.7	312.4	301.2	293.5	291.3	293.5	301.2	312.4
125°	478.6	428.2	388.8	358.2	337.3	325.3	318.7	314.3	318.7	325.3	337.3
127.5°	496.8	450.5	412.5	381.5	359.9	346.1	338.2	334.7	338.2	346.1	359.9
130°	508.2	465.5	428.2	396.4	375.7	359.2	350.4	346.1	350.4	359.2	375.7
132.5°	519.6	477.8	440.5	410.5	388.0	372.4	361.0	357.5	361.0	372.4	388.0
135°	534.5	495.0	458.9	430.5	407.5	388.8	377.9	373.4	377.9	388.8	407.5
137.5°	545.0	508.2	474.5	447.3	423.4	405.7	393.6	389.5	393.6	405.7	423.4
140°	552.0	517.0	484.1	457.8	434.8	416.2	404.2	400.9	404.2	416.2	434.8
142.5°	557.2	524.8	492.9	467.4	445.4	427.5	416.4	413.1	416.4	427.5	445.4
145°	563.0	533.4	504.9	480.8	460.0	444.7	433.8	430.5	433.8	444.7	460.0
147.5°	568.0	542.2	515.4	493.7	476.5	460.6	451.0	449.9	451.0	460.6	476.5
150°	570.6	546.5	522.5	501.6	485.2	472.0	463.3	462.2	463.3	472.0	485.2
152.5°	572.4	550.1	528.6	509.5	494.8	482.6	473.8	473.5	473.8	482.6	494.8
155°	573.9	555.3	536.7	520.3	508.2	497.2	490.7	489.6	490.7	497.2	508.2
157.5°	573.9	559.0	543.3	530.3	519.8	511.2	505.1	505.1	505.1	511.2	519.8
160°	573.9	560.7	547.6	535.6	526.8	519.2	514.7	514.7	514.7	519.2	526.8
162.5°	573.9	562.5	550.3	540.8	532.9	526.1	522.6	523.5	522.6	526.1	532.9
165°	571.7	563.0	553.1	546.5	541.0	535.6	533.4	533.4	533.4	535.6	541.0
167.5°	569.1	562.7	555.5	550.4	547.4	543.3	542.2	543.3	542.2	543.3	547.4
170°	567.3	561.8	556.4	553.1	550.9	547.6	546.5	547.6	546.5	547.6	550.9
172.5°	565.6	561.0	557.2	554.9	553.6	551.1	550.9	552.0	550.9	551.1	553.6
175°	563.0	559.7	557.5	557.5	556.4	555.3	555.3	556.4	555.3	555.3	556.4
177.5°	560.1	558.4	557.5	557.5	557.5	556.6	557.5	558.4	557.5	556.6	557.5
180°	557.5	557.5	557.5	557.5	557.5	557.5	557.5	557.5	557.5	557.5	557.5



TEST NUMBER: P332573-830

CATALOG NUMBER: S124DIP-S575D1205U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	885.2	885.2	885.2	885.2	885.2	885.2	885.2	885.2	885.2	885.2	885.2
2.5°	868.3	865.6	861.8	856.5	852.2	847.4	846.2	844.5	848.0	845.1	844.2
5°	839.8	832.1	822.2	810.9	804.3	794.7	792.9	789.2	785.5	785.1	781.5
7.5°	809.6	798.3	785.4	773.8	763.1	752.7	745.8	744.4	739.0	735.8	732.2
10°	790.3	776.4	761.3	750.4	737.8	726.9	719.2	714.7	711.1	707.0	703.4
12.5°	767.4	752.6	740.2	728.3	713.5	705.1	692.5	684.9	684.1	684.2	674.7
15°	740.7	726.1	707.0	690.2	682.1	666.0	659.0	650.2	644.7	639.2	634.8
17.5°	710.4	692.1	677.2	657.8	642.4	629.6	620.4	615.1	606.9	599.1	593.4
20°	691.3	671.8	656.1	635.6	618.7	602.9	595.2	587.9	581.6	575.0	568.8
22.5°	671.9	651.6	632.4	612.4	596.6	580.0	572.6	562.6	556.7	553.0	546.8
25°	641.4	619.4	597.4	578.3	562.2	547.5	537.6	529.9	523.3	520.4	516.3
27.5°	608.2	586.4	565.1	543.5	525.2	514.5	506.6	500.8	497.0	493.1	491.3
30°	587.1	564.4	541.7	521.5	504.6	494.0	486.6	482.6	479.7	477.9	476.0
32.5°	565.7	543.3	519.3	501.0	485.9	476.4	470.8	466.7	465.3	464.7	464.0
35°	531.4	508.7	486.6	470.1	455.8	452.1	447.4	445.2	444.5	447.0	448.2
37.5°	498.1	477.0	456.8	440.8	431.4	426.0	424.4	424.5	427.2	429.4	432.1
40°	476.7	456.2	437.2	423.2	414.4	411.1	410.4	412.2	415.1	417.7	420.7
42.5°	455.9	435.6	418.4	405.3	399.2	396.2	396.6	398.4	402.6	405.7	410.1
45°	423.6	406.7	389.8	379.2	374.1	374.8	374.8	378.1	382.1	386.9	391.6
47.5°	393.1	376.1	362.2	353.3	350.6	350.0	352.0	356.4	362.2	368.1	374.8
50°	372.6	356.5	344.3	336.3	333.4	334.4	337.4	341.4	348.4	355.7	362.7
52.5°	351.8	337.1	325.8	318.4	316.3	318.3	321.2	327.6	333.8	341.7	350.1
55°	319.4	307.0	298.1	292.7	291.9	293.0	296.3	303.3	312.1	322.0	330.1
57.5°	287.2	276.8	268.7	264.9	265.3	266.4	271.7	280.0	289.5	300.0	310.4
60°	265.5	256.0	249.4	246.5	246.9	249.0	255.6	263.3	275.0	285.3	296.3
62.5°	245.0	236.6	230.3	227.6	227.2	232.0	238.3	246.3	258.1	269.5	281.3
65°	212.0	205.4	200.2	198.8	199.8	203.5	211.6	222.3	232.1	244.2	256.7
67.5°	179.6	174.3	170.8	171.4	172.8	178.1	184.9	194.1	205.3	217.8	230.2
70°	159.2	154.0	151.1	151.5	153.6	160.2	166.2	175.3	187.4	200.2	210.5
72.5°	138.1	134.7	132.1	133.6	135.7	140.3	147.6	156.8	167.5	179.4	190.3
75°	105.9	105.9	104.5	105.7	109.0	113.3	118.9	128.4	139.0	148.5	157.3
77.5°	78.6	77.9	78.8	80.1	82.0	87.2	93.5	100.4	108.3	117.9	125.2
80°	60.1	60.5	62.3	64.6	65.3	69.3	75.9	82.2	88.4	96.4	103.4
82.5°	45.1	45.5	46.5	49.3	50.0	54.4	58.6	64.8	70.5	75.9	81.7
85°	24.6	24.6	26.4	27.5	29.3	32.2	34.9	38.5	43.6	47.3	52.8
87.5°	11.1	11.1	13.7	14.2	15.6	17.4	17.8	21.2	22.6	24.3	27.0
90°	8.8	8.8	15.4	15.4	17.5	19.7	18.7	19.7	20.8	21.9	21.9
92.5°	57.9	80.6	136.3	221.2	304.1	347.4	289.4	215.1	161.8	128.8	106.9
95°	90.9	137.0	232.1	411.8	673.5	892.6	917.8	811.5	641.8	495.0	388.8
97.5°	110.0	148.5	221.9	370.2	630.4	940.2	1153.1	1199.1	1136.0	1028.9	914.5
100°	124.9	159.9	224.5	348.3	571.7	880.5	1160.9	1320.9	1342.7	1289.1	1208.1
102.5°	141.5	174.8	233.3	342.1	532.3	806.1	1095.2	1314.8	1423.3	1438.9	1405.1
105°	169.8	201.5	254.1	345.0	498.3	718.5	975.8	1226.6	1416.2	1524.6	1569.4
107.5°	198.9	230.3	278.4	361.2	492.2	669.4	879.5	1101.5	1303.3	1456.0	1553.7
110°	219.0	248.6	296.8	373.4	494.0	652.8	831.3	1026.2	1215.7	1374.5	1495.0



TEST NUMBER: P332573-830

CATALOG NUMBER: S124DIP-S575D1205U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	238.4	267.9	314.3	386.6	499.2	644.9	804.1	971.0	1138.6	1288.6	1409.1
115°	268.3	297.9	341.7	407.5	509.3	640.7	778.7	915.6	1050.4	1178.5	1283.6
117.5°	296.0	326.6	368.3	428.7	520.0	639.6	767.3	888.4	999.9	1100.7	1189.9
120°	314.3	345.0	386.6	443.6	527.9	639.6	761.2	876.2	978.1	1065.6	1143.4
122.5°	332.7	362.5	404.2	457.6	535.8	638.8	754.2	865.6	964.0	1043.8	1111.9
125°	358.2	388.8	428.2	478.6	547.6	637.4	742.5	847.7	941.9	1017.5	1077.7
127.5°	381.5	412.5	450.5	496.8	557.0	635.0	727.0	825.8	915.9	991.2	1048.4
130°	396.4	428.2	465.5	508.2	564.0	634.1	717.4	808.3	894.8	969.3	1027.4
132.5°	410.5	440.5	477.8	519.6	570.1	633.3	708.6	789.9	871.2	943.9	1001.9
135°	430.5	458.9	495.0	534.5	579.4	632.0	695.5	764.5	835.7	902.5	957.2
137.5°	447.3	474.5	508.2	545.0	584.8	631.7	684.1	741.5	801.7	858.0	907.5
140°	457.8	484.1	517.0	552.0	589.3	630.8	678.0	728.3	779.8	829.1	875.1
142.5°	467.4	492.9	524.8	557.2	592.8	630.8	672.7	716.0	761.4	803.7	843.6
145°	480.8	504.9	533.4	563.0	594.7	628.7	663.7	698.8	736.0	768.8	799.6
147.5°	493.7	515.4	542.2	568.0	595.8	624.7	655.6	684.6	714.1	740.4	764.5
150°	501.6	522.5	546.5	570.6	595.8	622.1	649.5	675.8	701.0	722.8	742.5
152.5°	509.5	528.6	550.1	572.4	594.1	617.7	642.4	666.1	687.8	707.9	724.2
155°	520.3	536.7	555.3	573.9	591.4	611.1	632.0	651.7	669.2	685.6	698.8
157.5°	530.3	543.3	559.0	573.9	588.6	604.4	621.2	636.1	650.8	664.6	675.1
160°	535.6	547.6	560.7	573.9	586.0	599.1	613.3	626.5	638.5	650.5	659.3
162.5°	540.8	550.3	562.5	573.9	583.3	593.8	606.3	616.8	627.2	636.6	644.4
165°	546.5	553.1	563.0	571.7	578.2	586.0	594.7	603.5	610.0	617.7	623.2
167.5°	550.4	555.5	562.7	569.1	573.1	578.1	584.2	590.6	595.6	601.7	605.0
170°	553.1	556.4	561.8	567.3	569.5	572.8	577.2	582.7	586.0	590.3	593.6
172.5°	554.9	557.2	561.0	565.6	566.0	567.5	571.1	575.6	578.1	580.7	583.1
175°	557.5	557.5	559.7	563.0	561.8	561.8	564.0	566.3	567.3	569.5	569.5
177.5°	557.5	557.5	558.4	560.1	558.4	558.4	559.2	560.1	561.0	561.0	561.8
180°	557.5	557.5	557.5	557.5	557.5	557.5	557.5	557.5	557.5	557.5	557.5



TEST NUMBER: P332573-830

CATALOG NUMBER: S124DIP-S575D1205U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	885.2	885.2	885.2	885.2	885.2	885.2	885.2	885.2	885.2	885.2	885.2
2.5°	843.6	843.0	840.9	840.7	840.9	843.0	843.6	844.2	845.1	848.0	844.5
5°	779.3	777.5	776.4	780.4	776.4	777.5	779.3	781.5	785.1	785.5	789.2
7.5°	730.8	729.3	726.1	725.1	726.1	729.3	730.8	732.2	735.8	739.0	744.4
10°	699.7	698.2	695.3	694.6	695.3	698.2	699.7	703.4	707.0	711.1	714.7
12.5°	669.8	666.8	666.3	667.0	666.3	666.8	669.8	674.7	684.2	684.1	684.9
15°	630.0	628.6	624.5	625.7	624.5	628.6	630.0	634.8	639.2	644.7	650.2
17.5°	590.9	589.1	584.2	588.5	584.2	589.1	590.9	593.4	599.1	606.9	615.1
20°	566.2	563.3	560.7	560.3	560.7	563.3	566.2	568.8	575.0	581.6	587.9
22.5°	542.7	540.1	539.9	537.4	539.9	540.1	542.7	546.8	553.0	556.7	562.6
25°	513.4	510.9	510.1	508.3	510.1	510.9	513.4	516.3	520.4	523.3	529.9
27.5°	490.9	489.7	488.3	488.9	488.3	489.7	490.9	491.3	493.1	497.0	500.8
30°	477.1	476.7	476.0	476.0	476.0	476.7	477.1	476.0	477.9	479.7	482.6
32.5°	465.7	465.6	466.0	466.0	466.0	465.6	465.7	464.0	464.7	465.3	466.7
35°	449.6	450.7	451.5	450.3	451.5	450.7	449.6	448.2	447.0	444.5	445.2
37.5°	435.1	436.2	437.2	438.5	437.2	436.2	435.1	432.1	429.4	427.2	424.5
40°	424.0	426.5	427.3	429.0	427.3	426.5	424.0	420.7	417.7	415.1	412.2
42.5°	413.4	416.2	418.1	418.5	418.1	416.2	413.4	410.1	405.7	402.6	398.4
45°	397.2	400.1	402.7	402.7	402.7	400.1	397.2	391.6	386.9	382.1	378.1
47.5°	380.4	384.7	387.2	387.9	387.2	384.7	380.4	374.8	368.1	362.2	356.4
50°	368.9	374.1	376.6	378.4	376.6	374.1	368.9	362.7	355.7	348.4	341.4
52.5°	357.8	362.9	366.4	367.3	366.4	362.9	357.8	350.1	341.7	333.8	327.6
55°	338.5	345.8	349.9	351.3	349.9	345.8	338.5	330.1	322.0	312.1	303.3
57.5°	320.3	327.1	331.8	332.8	331.8	327.1	320.3	310.4	300.0	289.5	280.0
60°	306.2	313.6	319.4	320.6	319.4	313.6	306.2	296.3	285.3	275.0	263.3
62.5°	291.8	299.4	304.7	307.6	304.7	299.4	291.8	281.3	269.5	258.1	246.3
65°	267.0	274.7	279.8	280.9	279.8	274.7	267.0	256.7	244.2	232.1	222.3
67.5°	239.9	247.5	250.9	253.1	250.9	247.5	239.9	230.2	217.8	205.3	194.1
70°	220.7	227.0	230.6	232.5	230.6	227.0	220.7	210.5	200.2	187.4	175.3
72.5°	199.1	205.6	209.8	210.2	209.8	205.6	199.1	190.3	179.4	167.5	156.8
75°	165.8	171.6	173.8	173.8	173.8	171.6	165.8	157.3	148.5	139.0	128.4
77.5°	131.2	134.2	137.0	137.6	137.0	134.2	131.2	125.2	117.9	108.3	100.4
80°	109.0	110.7	112.9	112.9	112.9	110.7	109.0	103.4	96.4	88.4	82.2
82.5°	86.1	87.6	89.7	89.4	89.7	87.6	86.1	81.7	75.9	70.5	64.8
85°	52.0	55.4	55.0	54.3	55.0	55.4	52.0	52.8	47.3	43.6	38.5
87.5°	28.1	28.6	29.2	29.8	29.2	28.6	28.1	27.0	24.3	22.6	21.2
90°	23.0	24.1	23.0	23.0	23.0	24.1	23.0	21.9	21.9	20.8	19.7
92.5°	94.0	88.0	84.4	84.4	84.4	88.0	94.0	106.9	128.8	161.8	215.1
95°	335.2	301.2	281.4	267.2	281.4	301.2	335.2	388.8	495.0	641.8	811.5
97.5°	835.8	770.0	737.1	714.4	737.1	770.0	835.8	914.5	1028.9	1136.0	1199.1
100°	1112.8	1045.9	1013.1	1004.4	1013.1	1045.9	1112.8	1208.1	1289.1	1342.7	1320.9
102.5°	1346.7	1298.3	1263.7	1256.7	1263.7	1298.3	1346.7	1405.1	1438.9	1423.3	1314.8
105°	1571.7	1562.9	1547.6	1541.0	1547.6	1562.9	1571.7	1569.4	1524.6	1416.2	1226.6
107.5°	1607.8	1632.8	1643.7	1646.6	1643.7	1632.8	1607.8	1553.7	1456.0	1303.3	1101.5
110°	1572.7	1618.7	1638.5	1648.3	1638.5	1618.7	1572.7	1495.0	1374.5	1215.7	1026.2



TEST NUMBER: P332573-830

CATALOG NUMBER: S124DIP-S575D1205U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1497.4	1553.0	1580.6	1596.7	1580.6	1553.0	1497.4	1409.1	1288.6	1138.6	971.0
115°	1370.2	1435.9	1470.9	1479.7	1470.9	1435.9	1370.2	1283.6	1178.5	1050.4	915.6
117.5°	1263.7	1318.9	1354.3	1361.1	1354.3	1318.9	1263.7	1189.9	1100.7	999.9	888.4
120°	1205.9	1254.1	1282.5	1294.6	1282.5	1254.1	1205.9	1143.4	1065.6	978.1	876.2
122.5°	1164.7	1205.9	1229.9	1242.0	1229.9	1205.9	1164.7	1111.9	1043.8	964.0	865.6
125°	1121.5	1153.3	1174.1	1180.6	1174.1	1153.3	1121.5	1077.7	1017.5	941.9	847.7
127.5°	1092.4	1120.7	1138.2	1144.7	1138.2	1120.7	1092.4	1048.4	991.2	915.9	825.8
130°	1072.2	1099.6	1117.1	1123.7	1117.1	1099.6	1072.2	1027.4	969.3	894.8	808.3
132.5°	1045.9	1076.9	1093.4	1100.0	1093.4	1076.9	1045.9	1001.9	943.9	871.2	789.9
135°	1001.1	1031.7	1049.2	1055.8	1049.2	1031.7	1001.1	957.2	902.5	835.7	764.5
137.5°	948.5	978.7	993.2	1001.1	993.2	978.7	948.5	907.5	858.0	801.7	741.5
140°	913.4	937.5	952.8	961.6	952.8	937.5	913.4	875.1	829.1	779.8	728.3
142.5°	877.5	899.8	913.4	919.5	913.4	899.8	877.5	843.6	803.7	761.4	716.0
145°	826.9	845.6	856.5	862.0	856.5	845.6	826.9	799.6	768.8	736.0	698.8
147.5°	784.7	800.6	809.0	810.9	809.0	800.6	784.7	764.5	740.4	714.1	684.6
150°	760.1	774.3	780.9	782.0	780.9	774.3	760.1	742.5	722.8	701.0	675.8
152.5°	739.0	750.6	754.6	755.7	754.6	739.0	724.2	707.9	687.8	666.1	646.1
155°	709.7	718.5	721.8	721.8	721.8	718.5	709.7	698.8	685.6	669.2	651.7
157.5°	683.4	690.0	692.0	692.0	692.0	690.0	683.4	675.1	664.6	650.8	636.1
160°	665.9	672.5	673.5	673.5	673.5	672.5	665.9	659.3	650.5	638.5	626.5
162.5°	649.2	655.8	657.0	656.0	657.0	655.8	649.2	644.4	636.6	627.2	616.8
165°	627.5	632.0	630.8	629.8	630.8	632.0	627.5	623.2	617.7	610.0	603.5
167.5°	607.2	610.0	609.8	609.0	609.8	610.0	607.2	605.0	601.7	595.6	590.6
170°	595.8	596.9	595.8	595.8	595.8	596.9	595.8	593.6	590.3	586.0	582.7
172.5°	584.4	585.5	584.4	582.7	584.4	585.5	584.4	583.1	580.7	578.1	575.6
175°	569.5	571.7	569.5	567.3	569.5	571.7	569.5	569.5	569.5	567.3	566.3
177.5°	561.0	561.8	560.1	558.4	560.1	561.8	561.0	561.8	561.0	561.0	560.1
180°	557.5	557.5	557.5	557.5	557.5	557.5	557.5	557.5	557.5	557.5	557.5



TEST NUMBER: P332573-830

CATALOG NUMBER: S124DIP-S575D1205U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	885.2	885.2	885.2	885.2	885.2	885.2	885.2	885.2	885.2	885.2	885.2
2.5°	846.2	847.4	852.2	856.5	861.8	865.6	868.3	871.2	877.3	882.3	887.0
5°	792.9	794.7	804.3	810.9	822.2	832.1	839.8	848.2	858.2	871.7	884.2
7.5°	745.8	752.7	763.1	773.8	785.4	798.3	809.6	822.4	839.4	858.1	877.3
10°	719.2	726.9	737.8	750.4	761.3	776.4	790.3	805.3	824.7	847.5	870.2
12.5°	692.5	705.1	713.5	728.3	740.2	752.6	767.4	787.1	809.8	833.7	861.1
15°	659.0	666.0	682.1	690.2	707.0	726.1	740.7	760.6	782.6	814.2	844.9
17.5°	620.4	629.6	642.4	657.8	677.2	692.1	710.4	730.8	758.5	789.8	828.4
20°	595.2	602.9	618.7	635.6	656.1	671.8	691.3	711.1	739.7	773.1	813.4
22.5°	572.6	580.0	596.6	612.4	632.4	651.6	671.9	694.9	722.4	757.5	798.7
25°	537.6	547.5	562.2	578.3	597.4	619.4	641.4	661.9	691.3	728.3	772.3
27.5°	506.6	514.5	525.2	543.5	565.1	586.4	608.2	634.0	662.2	701.4	747.1
30°	486.6	494.0	504.6	521.5	541.7	564.4	587.1	612.1	641.4	680.2	726.9
32.5°	470.8	476.4	485.9	501.0	519.3	543.3	565.7	591.5	622.4	660.6	706.1
35°	447.4	452.1	455.8	470.1	486.6	508.7	531.4	558.9	588.6	624.9	670.3
37.5°	424.4	426.0	431.4	440.8	456.8	477.0	498.1	525.2	555.6	592.6	633.6
40°	410.4	411.1	414.4	423.2	437.2	456.2	476.7	503.5	532.4	567.3	608.0
42.5°	396.6	396.2	399.2	405.3	418.4	435.6	455.9	480.3	509.3	541.5	579.9
45°	374.8	374.8	374.1	379.2	389.8	406.7	423.6	447.0	471.3	502.8	535.1
47.5°	352.0	350.0	350.6	353.3	362.2	376.1	393.1	412.4	433.7	460.4	488.7
50°	337.4	334.4	333.4	336.3	344.3	356.5	372.6	389.5	409.6	433.1	457.3
52.5°	321.2	318.3	316.3	318.4	325.8	337.1	351.8	366.6	384.7	403.8	424.7
55°	296.3	293.0	291.9	292.7	298.1	307.0	319.4	333.0	346.6	362.3	377.0
57.5°	271.7	266.4	265.3	264.9	268.7	276.8	287.2	299.0	308.9	318.4	334.0
60°	255.6	249.0	246.9	246.5	249.4	256.0	265.5	277.2	284.2	290.8	304.3
62.5°	238.3	232.0	227.2	227.6	230.3	236.6	245.0	253.4	258.1	265.3	274.5
65°	211.6	203.5	199.8	198.8	200.2	205.4	212.0	217.4	222.6	225.6	234.3
67.5°	184.9	178.1	172.8	171.4	170.8	174.3	179.6	183.0	186.6	189.3	194.4
70°	166.2	160.2	153.6	151.5	151.1	154.0	159.2	159.6	164.7	165.8	171.3
72.5°	147.6	140.3	135.7	133.6	132.1	134.7	138.1	139.0	141.8	143.7	146.7
75°	118.9	113.3	109.0	105.7	104.5	105.9	105.9	107.8	109.6	110.7	114.0
77.5°	93.5	87.2	82.0	80.1	78.8	77.9	78.6	79.7	78.9	80.8	81.5
80°	75.9	69.3	65.3	64.6	62.3	60.5	60.1	61.3	59.8	60.5	62.7
82.5°	58.6	54.4	50.0	49.3	46.5	45.5	45.1	44.5	44.5	44.4	44.8
85°	34.9	32.2	29.3	27.5	26.4	24.6	24.6	23.8	23.1	22.3	22.7
87.5°	17.8	17.4	15.6	14.2	13.7	11.1	11.1	10.1	9.5	8.6	7.8
90°	18.7	19.7	17.5	15.4	15.4	8.8	8.8	7.6	6.6	3.3	1.1
92.5°	289.4	347.4	304.1	221.2	136.3	80.6	57.9	41.8	28.5	18.2	12.4
95°	917.8	892.6	673.5	411.8	232.1	137.0	90.9	64.7	50.4	39.4	36.1
97.5°	1153.1	940.2	630.4	370.2	221.9	148.5	110.0	87.4	74.3	64.8	64.8
100°	1160.9	880.5	571.7	348.3	224.5	159.9	124.9	104.1	90.9	83.2	83.2
102.5°	1095.2	806.1	532.3	342.1	233.3	174.8	141.5	121.6	109.3	102.5	100.8
105°	975.8	718.5	498.3	345.0	254.1	201.5	169.8	150.1	137.0	131.4	128.2
107.5°	879.5	669.4	492.2	361.2	278.4	230.3	198.9	180.0	166.1	160.5	158.3
110°	831.3	652.8	494.0	373.4	296.8	248.6	219.0	199.3	186.2	180.7	178.5



TEST NUMBER: P332573-830

CATALOG NUMBER: S124DIP-S575D1205U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	804.1	644.9	499.2	386.6	314.3	267.9	238.4	218.6	206.3	200.0	197.8
115°	778.7	640.7	509.3	407.5	341.7	297.9	268.3	247.5	236.6	228.9	225.6
117.5°	767.3	639.6	520.0	428.7	368.3	326.6	296.0	276.4	264.4	257.6	254.5
120°	761.2	639.6	527.9	443.6	386.6	345.0	314.3	295.7	283.7	276.0	273.8
122.5°	754.2	638.8	535.8	457.6	404.2	362.5	332.7	312.4	301.2	293.5	291.3
125°	742.5	637.4	547.6	478.6	428.2	388.8	358.2	337.3	325.3	318.7	314.3
127.5°	727.0	635.0	557.0	496.8	450.5	412.5	381.5	359.9	346.1	338.2	334.7
130°	717.4	634.1	564.0	508.2	465.5	428.2	396.4	375.7	359.2	350.4	346.1
132.5°	708.6	633.3	570.1	519.6	477.8	440.5	410.5	388.0	372.4	361.0	357.5
135°	695.5	632.0	579.4	534.5	495.0	458.9	430.5	407.5	388.8	377.9	373.4
137.5°	684.1	631.7	584.8	545.0	508.2	474.5	447.3	423.4	405.7	393.6	389.5
140°	678.0	630.8	589.3	552.0	517.0	484.1	457.8	434.8	416.2	404.2	400.9
142.5°	672.7	630.8	592.8	557.2	524.8	492.9	467.4	445.4	427.5	416.4	413.1
145°	663.7	628.7	594.7	563.0	533.4	504.9	480.8	460.0	444.7	433.8	430.5
147.5°	655.6	624.7	595.8	568.0	542.2	515.4	493.7	476.5	460.6	451.0	449.9
150°	649.5	622.1	595.8	570.6	546.5	522.5	501.6	485.2	472.0	463.3	462.2
152.5°	642.4	617.7	594.1	572.4	550.1	528.6	509.5	494.8	482.6	473.8	473.5
155°	632.0	611.1	591.4	573.9	555.3	536.7	520.3	508.2	497.2	490.7	489.6
157.5°	621.2	604.4	588.6	573.9	559.0	543.3	530.3	519.8	511.2	505.1	505.1
160°	613.3	599.1	586.0	573.9	560.7	547.6	535.6	526.8	519.2	514.7	514.7
162.5°	606.3	593.8	583.3	573.9	562.5	550.3	540.8	532.9	526.1	522.6	523.5
165°	594.7	586.0	578.2	571.7	563.0	553.1	546.5	541.0	535.6	533.4	533.4
167.5°	584.2	578.1	573.1	569.1	562.7	555.5	550.4	547.4	543.3	542.2	543.3
170°	577.2	572.8	569.5	567.3	561.8	556.4	553.1	550.9	547.6	546.5	547.6
172.5°	571.1	567.5	566.0	565.6	561.0	557.2	554.9	553.6	551.1	550.9	552.0
175°	564.0	561.8	561.8	563.0	559.7	557.5	557.5	556.4	555.3	555.3	556.4
177.5°	559.2	558.4	558.4	560.1	558.4	557.5	557.5	557.5	556.6	557.5	558.4
180°	557.5	557.5	557.5	557.5	557.5	557.5	557.5	557.5	557.5	557.5	557.5



TEST NUMBER: P332573-830

CATALOG NUMBER: S124DIP-S575D1205U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	885.2	885.2	885.2	885.2	885.2	885.2	885.2	885.2	885.2	885.2	885.2
2.5°	891.2	894.1	897.9	904.4	906.7	909.6	913.7	913.4	914.6	919.0	928.4
5°	894.5	905.8	916.8	930.0	944.0	953.1	965.6	973.3	981.0	990.9	1007.8
7.5°	895.8	913.8	934.0	957.2	977.8	1001.5	1020.1	1037.6	1053.3	1074.2	1094.3
10°	893.7	917.9	944.0	973.3	1004.5	1030.9	1054.7	1081.9	1104.9	1130.2	1153.0
12.5°	889.9	919.1	953.9	986.7	1023.2	1062.2	1091.9	1119.4	1150.1	1179.2	1214.3
15°	881.3	921.2	962.0	1005.2	1054.0	1099.1	1142.0	1177.5	1210.6	1254.2	1300.0
17.5°	870.2	913.3	964.7	1017.1	1068.1	1119.6	1172.7	1226.2	1267.8	1322.0	1357.9
20°	860.0	909.8	962.6	1025.0	1076.0	1140.2	1193.0	1244.6	1301.8	1355.8	1398.7
22.5°	845.6	900.1	956.2	1018.2	1085.3	1149.5	1210.6	1266.7	1323.9	1382.5	1434.5
25°	827.4	876.8	943.2	1013.6	1080.3	1150.1	1220.1	1290.5	1352.1	1414.1	1462.5
27.5°	796.3	858.8	920.6	993.3	1067.4	1146.2	1221.2	1294.9	1359.3	1410.3	1440.4
30°	780.4	834.6	901.8	974.8	1055.1	1139.8	1217.9	1290.2	1350.3	1391.0	1403.1
32.5°	757.0	812.9	878.6	954.2	1039.2	1126.2	1207.6	1275.7	1326.0	1347.3	1332.7
35°	722.1	772.7	839.1	916.4	1004.8	1097.6	1177.9	1235.5	1261.2	1241.0	1190.7
37.5°	680.2	730.5	797.1	873.1	964.6	1058.9	1131.5	1172.9	1164.4	1114.3	1039.3
40°	650.9	697.9	761.3	843.5	932.6	1027.2	1091.0	1113.4	1090.0	1018.0	938.5
42.5°	618.4	664.1	727.8	807.1	901.4	988.7	1044.3	1046.2	1006.9	921.0	841.0
45°	568.8	612.5	672.6	755.1	842.4	924.5	961.2	943.2	870.6	787.7	707.4
47.5°	519.9	557.7	617.0	695.3	778.2	847.3	865.5	833.2	755.8	675.3	600.9
50°	484.1	522.3	578.0	652.8	732.7	792.5	801.3	758.4	682.5	601.4	543.1
52.5°	449.8	487.6	541.3	610.5	683.7	737.6	737.9	688.2	612.7	540.5	486.2
55°	399.4	433.5	481.9	543.8	609.2	651.3	641.0	589.7	524.1	461.4	414.1
57.5°	350.8	380.5	425.1	476.8	534.3	569.1	552.0	502.7	444.0	390.9	355.0
60°	319.4	347.6	385.8	434.6	483.0	510.1	494.0	449.2	395.3	352.4	321.2
62.5°	288.9	312.7	349.4	391.7	436.6	456.8	442.3	398.2	351.7	312.8	287.5
65°	245.7	265.1	294.5	330.8	363.4	380.7	368.5	327.4	291.9	264.0	243.8
67.5°	205.4	220.6	242.8	271.9	299.6	309.0	297.9	269.3	239.2	216.9	202.6
70°	177.5	191.8	210.5	232.9	257.0	267.0	256.0	233.3	208.7	188.1	174.2
72.5°	153.2	164.2	180.0	199.2	218.0	228.0	220.5	198.6	177.9	162.6	150.7
75°	116.6	126.1	137.1	150.7	165.4	172.0	165.4	150.3	136.0	124.7	116.2
77.5°	84.8	89.9	98.4	108.6	117.7	122.8	117.1	106.9	98.1	90.4	86.1
80°	64.6	68.2	74.1	82.2	88.4	93.1	89.4	81.1	74.1	68.9	67.1
82.5°	46.9	49.4	53.3	59.3	63.4	65.9	64.3	58.2	55.3	50.7	48.9
85°	23.1	24.6	27.1	28.9	32.6	33.0	33.4	30.8	28.3	27.1	25.6
87.5°	8.6	9.5	10.7	11.7	12.9	14.5	14.2	14.6	13.9	13.4	12.4
90°	3.3	6.6	7.6	8.8	8.8	15.4	15.4	17.5	19.7	18.7	19.7
92.5°	18.2	28.5	41.8	57.9	80.6	136.3	221.2	304.1	347.4	289.4	215.1
95°	39.4	50.4	64.7	90.9	137.0	232.1	411.8	673.5	892.6	917.8	811.5
97.5°	64.8	74.3	87.4	110.0	148.5	221.9	370.2	630.4	940.2	1153.1	1199.1
100°	83.2	90.9	104.1	124.9	159.9	224.5	348.3	571.7	880.5	1160.9	1320.9
102.5°	102.5	109.3	121.6	141.5	174.8	233.3	342.1	532.3	806.1	1095.2	1314.8
105°	131.4	137.0	150.1	169.8	201.5	254.1	345.0	498.3	718.5	975.8	1226.6
107.5°	160.5	166.1	180.0	198.9	230.3	278.4	361.2	492.2	669.4	879.5	1101.5
110°	180.7	186.2	199.3	219.0	248.6	296.8	373.4	494.0	652.8	831.3	1026.2



TEST NUMBER: P332573-830

CATALOG NUMBER: S124DIP-S575D1205U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	200.0	206.3	218.6	238.4	267.9	314.3	386.6	499.2	644.9	804.1	971.0
115°	228.9	236.6	247.5	268.3	297.9	341.7	407.5	509.3	640.7	778.7	915.6
117.5°	257.6	264.4	276.4	296.0	326.6	368.3	428.7	520.0	639.6	767.3	888.4
120°	276.0	283.7	295.7	314.3	345.0	386.6	443.6	527.9	639.6	761.2	876.2
122.5°	293.5	301.2	312.4	332.7	362.5	404.2	457.6	535.8	638.8	754.2	865.6
125°	318.7	325.3	337.3	358.2	388.8	428.2	478.6	547.6	637.4	742.5	847.7
127.5°	338.2	346.1	359.9	381.5	412.5	450.5	496.8	557.0	635.0	727.0	825.8
130°	350.4	359.2	375.7	396.4	428.2	465.5	508.2	564.0	634.1	717.4	808.3
132.5°	361.0	372.4	388.0	410.5	440.5	477.8	519.6	570.1	633.3	708.6	789.9
135°	377.9	388.8	407.5	430.5	458.9	495.0	534.5	579.4	632.0	695.5	764.5
137.5°	393.6	405.7	423.4	447.3	474.5	508.2	545.0	584.8	631.7	684.1	741.5
140°	404.2	416.2	434.8	457.8	484.1	517.0	552.0	589.3	630.8	678.0	728.3
142.5°	416.4	427.5	445.4	467.4	492.9	524.8	557.2	592.8	630.8	672.7	716.0
145°	433.8	444.7	460.0	480.8	504.9	533.4	563.0	594.7	628.7	663.7	698.8
147.5°	451.0	460.6	476.5	493.7	515.4	542.2	568.0	595.8	624.7	655.6	684.6
150°	463.3	472.0	485.2	501.6	522.5	546.5	570.6	595.8	622.1	649.5	675.8
152.5°	473.8	482.6	494.8	509.5	528.6	550.1	572.4	594.1	617.7	642.4	666.1
155°	490.7	497.2	508.2	520.3	536.7	555.3	573.9	591.4	611.1	632.0	651.7
157.5°	505.1	511.2	519.8	530.3	543.3	559.0	573.9	588.6	604.4	621.2	636.1
160°	514.7	519.2	526.8	535.6	547.6	560.7	573.9	586.0	599.1	613.3	626.5
162.5°	522.6	526.1	532.9	540.8	550.3	562.5	573.9	583.3	593.8	606.3	616.8
165°	533.4	535.6	541.0	546.5	553.1	563.0	571.7	578.2	586.0	594.7	603.5
167.5°	542.2	543.3	547.4	550.4	555.5	562.7	569.1	573.1	578.1	584.2	590.6
170°	546.5	547.6	550.9	553.1	556.4	561.8	567.3	569.5	572.8	577.2	582.7
172.5°	550.9	551.1	553.6	554.9	557.2	561.0	565.6	566.0	567.5	571.1	575.6
175°	555.3	555.3	556.4	557.5	557.5	559.7	563.0	561.8	561.8	564.0	566.3
177.5°	557.5	556.6	557.5	557.5	557.5	558.4	560.1	558.4	558.4	559.2	560.1
180°	557.5	557.5	557.5	557.5	557.5	557.5	557.5	557.5	557.5	557.5	557.5



TEST NUMBER: P332573-830

CATALOG NUMBER: S124DIP-S575D1205U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	885.2	885.2	885.2	885.2	885.2	885.2	885.2
2.5°	933.1	933.7	936.3	938.4	939.0	941.9	942.2
5°	1015.1	1021.3	1033.4	1034.5	1036.3	1045.9	1038.6
7.5°	1111.2	1127.0	1137.6	1146.9	1150.3	1154.4	1153.6
10°	1172.8	1196.3	1208.0	1226.7	1227.5	1232.2	1229.3
12.5°	1234.7	1262.0	1283.4	1286.9	1302.5	1305.0	1309.1
15°	1322.4	1351.4	1381.1	1391.8	1413.3	1418.5	1426.5
17.5°	1404.9	1434.5	1455.3	1482.8	1491.7	1503.5	1495.5
20°	1450.0	1482.3	1508.7	1530.3	1539.5	1546.1	1545.4
22.5°	1477.3	1509.9	1531.3	1547.7	1556.2	1559.1	1558.9
25°	1494.4	1513.2	1519.8	1526.0	1516.5	1513.2	1514.6
27.5°	1446.9	1442.0	1424.8	1402.2	1378.8	1360.1	1350.0
30°	1381.5	1352.8	1326.8	1281.4	1257.8	1244.0	1231.4
32.5°	1288.7	1243.4	1193.4	1151.7	1124.9	1104.3	1101.2
35°	1129.9	1061.7	1000.4	949.4	923.0	900.7	895.5
37.5°	960.6	889.8	834.6	789.7	761.3	745.6	730.8
40°	848.2	787.4	733.1	694.9	673.4	661.9	652.8
42.5°	761.7	706.1	652.1	623.0	603.5	596.5	591.2
45°	642.2	590.4	553.0	531.0	519.6	507.9	502.4
47.5°	546.4	504.4	479.7	461.0	448.8	441.9	438.3
50°	492.1	457.7	435.6	421.4	410.4	404.8	401.9
52.5°	444.0	415.8	397.3	385.9	378.4	374.4	373.2
55°	382.5	360.9	349.1	339.2	333.8	330.1	328.6
57.5°	332.4	315.8	306.3	298.1	296.1	292.9	291.9
60°	299.6	286.8	278.7	273.2	271.4	267.7	268.4
62.5°	270.6	260.0	253.2	250.1	247.6	244.5	245.5
65°	228.8	221.1	217.4	214.5	211.6	209.8	211.2
67.5°	192.0	186.7	181.7	180.0	178.6	178.3	176.7
70°	168.0	163.5	159.2	158.1	158.1	156.6	156.2
72.5°	144.8	141.6	138.6	137.8	136.7	137.2	135.7
75°	111.9	109.2	108.2	107.1	106.7	106.7	105.7
77.5°	82.7	80.8	79.0	79.0	77.7	77.2	77.0
80°	62.7	62.0	60.5	60.5	59.8	60.1	59.4
82.5°	47.1	46.1	45.8	45.2	44.2	44.3	43.5
85°	25.3	24.2	23.8	22.7	22.0	22.7	22.0
87.5°	13.0	12.9	12.6	12.3	12.2	12.0	11.0
90°	20.8	21.9	21.9	23.0	24.1	23.0	23.0
92.5°	161.8	128.8	106.9	94.0	88.0	84.4	84.4
95°	641.8	495.0	388.8	335.2	301.2	281.4	267.2
97.5°	1136.0	1028.9	914.5	835.8	770.0	737.1	714.4
100°	1342.7	1289.1	1208.1	1112.8	1045.9	1013.1	1004.4
102.5°	1423.3	1438.9	1405.1	1346.7	1298.3	1263.7	1256.7
105°	1416.2	1524.6	1569.4	1571.7	1562.9	1547.6	1541.0
107.5°	1303.3	1456.0	1553.7	1607.8	1632.8	1643.7	1646.6
110°	1215.7	1374.5	1495.0	1572.7	1618.7	1638.5	1648.3



TEST NUMBER: P332573-830

CATALOG NUMBER: S124DIP-S575D1205U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	1138.6	1288.6	1409.1	1497.4	1553.0	1580.6	1596.7
115°	1050.4	1178.5	1283.6	1370.2	1435.9	1470.9	1479.7
117.5°	999.9	1100.7	1189.9	1263.7	1318.9	1354.3	1361.1
120°	978.1	1065.6	1143.4	1205.9	1254.1	1282.5	1294.6
122.5°	964.0	1043.8	1111.9	1164.7	1205.9	1229.9	1242.0
125°	941.9	1017.5	1077.7	1121.5	1153.3	1174.1	1180.6
127.5°	915.9	991.2	1048.4	1092.4	1120.7	1138.2	1144.7
130°	894.8	969.3	1027.4	1072.2	1099.6	1117.1	1123.7
132.5°	871.2	943.9	1001.9	1045.9	1076.9	1093.4	1100.0
135°	835.7	902.5	957.2	1001.1	1031.7	1049.2	1055.8
137.5°	801.7	858.0	907.5	948.5	978.7	993.2	1001.1
140°	779.8	829.1	875.1	913.4	937.5	952.8	961.6
142.5°	761.4	803.7	843.6	877.5	899.8	913.4	919.5
145°	736.0	768.8	799.6	826.9	845.6	856.5	862.0
147.5°	714.1	740.4	764.5	784.7	800.6	809.0	810.9
150°	701.0	722.8	742.5	760.1	774.3	780.9	782.0
152.5°	687.8	707.9	724.2	739.0	750.6	754.6	755.7
155°	669.2	685.6	698.8	709.7	718.5	721.8	721.8
157.5°	650.8	664.6	675.1	683.4	690.0	692.0	692.0
160°	638.5	650.5	659.3	665.9	672.5	673.5	673.5
162.5°	627.2	636.6	644.4	649.2	655.8	657.0	656.0
165°	610.0	617.7	623.2	627.5	632.0	630.8	629.8
167.5°	595.6	601.7	605.0	607.2	610.0	609.8	609.0
170°	586.0	590.3	593.6	595.8	596.9	595.8	595.8
172.5°	578.1	580.7	583.1	584.4	585.5	584.4	582.7
175°	567.3	569.5	569.5	569.5	571.7	569.5	567.3
177.5°	561.0	561.0	561.8	561.0	561.8	560.1	558.4
180°	557.5	557.5	557.5	557.5	557.5	557.5	557.5

(END OF REPORT)