

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332604-840

Luminaire Tested: **S124DIP-S795D810U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332604-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIP-S795D810U840-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 795 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 810 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6708.7 lumens
Efficiency: N/A
Efficacy: 146.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 45.9
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332604-840

CATALOG NUMBER: S124DIP-S795D810U840-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332604-840

CATALOG NUMBER: S124DIP-S795D810U840-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51	51	51	51	51	51	51		
1	98	94	90	86	90	87	83	80	74	71	69	62	60	58	51	49	48	43	43	43	43	43	43	43		
2	89	82	76	70	82	76	70	66	65	61	57	54	51	49	45	42	41	36	36	36	36	36	36	36		
3	81	72	65	59	75	67	60	55	57	52	48	48	44	41	39	37	35	31	31	31	31	31	31	31		
4	74	64	56	50	69	59	52	47	51	45	41	43	39	35	35	32	30	26	26	26	26	26	26	26		
5	68	57	49	43	63	53	45	40	45	40	35	38	34	31	32	29	26	23	23	23	23	23	23	23		
6	63	51	43	37	58	47	40	35	41	35	31	35	30	27	29	25	23	20	20	20	20	20	20	20		
7	58	46	38	32	54	43	36	31	37	31	27	31	27	24	26	23	20	18	18	18	18	18	18	18		
8	54	42	34	29	50	39	32	27	34	28	24	29	24	21	24	21	18	16	16	16	16	16	16	16		
9	50	38	31	25	46	36	29	24	31	25	22	27	22	19	22	19	16	14	14	14	14	14	14	14		
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	21	17	15	13	13	13	13	13	13	13		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10823	10823	10823
5°	10855	10724	10802
10°	10787	10637	10690
15°	10657	10486	10513
20°	10483	10299	10308
25°	10286	10085	10056
30°	10043	9833	9743
35°	9792	9570	9443
40°	9531	9271	9101
45°	9259	8977	8805
50°	8959	8715	8446
55°	8633	8376	8103
60°	8307	7995	7753
65°	7941	7633	7324
70°	7530	7152	6871
75°	6903	6569	6400
80°	6141	5890	5742
85°	5372	5169	5067



TEST NUMBER: P332604-840

CATALOG NUMBER: S124DIP-S795D810U840-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	126.2	1.9
10°-20°	355.7	5.3
20°-30°	523.5	7.8
30°-40°	608.6	9.1
40°-50°	608.7	9.1
50°-60°	532.4	7.9
60°-70°	395.4	5.9
70°-80°	224.6	3.3
80°-90°	67.9	1.0
90°-100°	36.1	0.5
100°-110°	230.2	3.4
110°-120°	440.4	6.6
120°-130°	559.1	8.3
130°-140°	598.2	8.9
140°-150°	559.3	8.3
150°-160°	451.1	6.7
160°-170°	290.9	4.3
170°-180°	100.3	1.5
0°-30°	1005.5	15.0
0°-40°	1614.1	24.1
0°-60°	2755.2	41.1
0°-90°	3443.1	51.3
90°-120°	706.7	10.5
90°-150°	2423.3	36.1
90°-180°	3266.0	48.7
0°-180°	6708.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1341	1341	1341	1341	1341	
5°	1340	1335	1323	1334	1333	127
15°	1275	1270	1255	1260	1258	359
25°	1155	1147	1132	1133	1129	531
35°	994	986	971	964	958	621
45°	811	803	786	775	771	625
55°	613	609	595	583	576	549
65°	416	410	400	389	383	411
75°	221	216	211	206	205	235
85°	58	58	56	56	55	64
90°	2	11	17	22	24	5
95°	43	18	17	22	23	56
105°	238	242	246	252	225	249
115°	444	446	445	447	447	437
125°	624	627	625	628	628	557
135°	774	773	776	778	779	596
145°	892	894	895	895	897	557
155°	978	979	977	980	978	451
165°	1032	1028	1028	1034	1027	292
175°	1056	1051	1052	1058	1049	100
180°	1056	1056	1056	1056	1056	



TEST NUMBER: P332604-840

CATALOG NUMBER: S124DIP-S795D810U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1340.6	1340.6	1340.6	1340.6	1340.6	1340.6	1340.6	1340.6	1340.6	1340.6	1340.6
2.5°	1344.0	1343.4	1342.8	1342.3	1341.7	1340.4	1338.3	1336.2	1334.0	1332.0	1333.8
5°	1339.5	1338.6	1337.6	1336.7	1335.6	1333.8	1331.2	1328.6	1326.0	1323.3	1326.0
7.5°	1327.1	1326.1	1325.1	1324.1	1323.2	1321.3	1318.4	1315.5	1312.5	1309.6	1311.7
10°	1315.9	1314.9	1313.9	1313.0	1312.0	1310.0	1306.9	1303.8	1300.7	1297.6	1299.5
12.5°	1301.2	1300.3	1299.3	1298.4	1297.5	1295.3	1292.0	1288.7	1285.5	1282.1	1284.2
15°	1275.1	1274.0	1273.1	1272.1	1271.2	1269.0	1265.4	1261.8	1258.2	1254.7	1256.1
17.5°	1243.4	1242.2	1241.0	1239.9	1238.7	1236.4	1233.0	1229.6	1226.2	1222.8	1223.8
20°	1220.2	1219.0	1217.9	1216.7	1215.5	1213.0	1209.5	1205.9	1202.3	1198.8	1199.5
22.5°	1195.4	1193.8	1192.1	1190.6	1189.0	1186.5	1182.9	1179.3	1175.7	1172.2	1173.5
25°	1154.7	1153.1	1151.3	1149.7	1148.0	1145.5	1142.2	1138.8	1135.5	1132.2	1132.4
27.5°	1108.3	1106.6	1104.9	1103.2	1101.5	1099.0	1095.9	1092.9	1089.7	1086.6	1086.0
30°	1077.4	1075.5	1073.6	1071.7	1069.8	1067.2	1064.1	1061.1	1057.9	1054.8	1053.9
32.5°	1044.7	1043.0	1041.3	1039.6	1037.8	1035.3	1032.1	1028.7	1025.5	1022.2	1021.1
35°	993.6	991.9	990.3	988.6	986.9	984.4	981.1	977.8	974.4	971.1	969.4
37.5°	939.7	938.2	936.6	935.1	933.5	931.0	927.5	923.8	920.3	916.7	914.8
40°	904.4	902.5	900.6	898.7	896.8	894.0	890.5	886.9	883.3	879.7	877.4
42.5°	866.7	865.5	864.3	863.2	862.0	859.5	855.6	851.6	847.6	843.6	840.9
45°	811.0	809.3	807.7	806.0	804.4	801.5	797.8	794.0	790.1	786.3	783.7
47.5°	752.8	751.6	750.5	749.3	748.2	745.9	742.4	738.8	735.3	731.7	728.7
50°	713.3	712.3	711.3	710.3	709.4	707.3	704.0	700.6	697.2	693.9	690.5
52.5°	674.6	673.5	672.3	671.2	669.9	667.6	664.1	660.6	657.0	653.5	650.6
55°	613.4	612.6	611.9	611.2	610.5	608.4	605.1	601.8	598.4	595.1	592.2
57.5°	554.9	554.1	553.3	552.5	551.7	549.6	546.3	543.0	539.8	536.4	533.7
60°	514.5	513.3	512.1	511.0	509.8	507.6	504.5	501.4	498.3	495.2	493.0
62.5°	475.0	474.0	473.0	472.0	471.0	468.9	465.5	462.2	459.0	455.7	453.7
65°	415.7	414.5	413.3	412.1	410.9	409.1	406.8	404.3	401.9	399.6	397.2
67.5°	356.0	354.9	353.8	352.6	351.6	349.9	347.6	345.3	343.1	340.7	338.4
70°	319.0	317.4	315.7	314.0	312.4	310.5	308.6	306.7	304.8	303.0	301.0
72.5°	279.5	277.8	276.2	274.5	272.8	271.2	269.7	268.1	266.6	265.1	263.6
75°	221.3	220.0	218.9	217.7	216.5	215.3	214.1	212.9	211.8	210.6	209.5
77.5°	165.6	165.1	164.6	164.1	163.5	162.8	161.7	160.7	159.6	158.5	158.2
80°	132.1	131.4	130.7	130.0	129.3	128.7	128.2	127.7	127.2	126.7	126.2
82.5°	99.5	99.2	98.8	98.5	98.2	98.0	97.9	97.8	97.7	97.6	97.3
85°	58.0	58.0	58.0	58.0	58.0	57.8	57.3	56.9	56.4	55.8	55.8
87.5°	22.8	23.0	23.2	23.4	23.6	23.7	23.8	23.9	24.0	24.1	24.3
90°	2.3	4.3	6.3	8.2	10.1	11.7	13.1	14.5	16.0	17.4	18.4
92.5°	10.0	10.1	10.2	10.3	10.4	11.1	12.5	13.9	15.3	16.8	17.8
95°	43.4	37.5	31.5	25.5	19.6	16.7	16.9	17.1	17.2	17.4	18.4
97.5°	92.2	95.9	99.7	103.4	107.1	99.2	79.6	60.0	40.4	20.8	20.9
100°	129.5	132.7	135.8	139.0	142.1	131.6	107.3	83.2	59.0	34.7	31.7
102.5°	171.2	173.5	175.8	178.1	180.5	180.1	176.8	173.7	170.6	167.4	135.2
105°	237.6	238.7	239.7	240.9	241.9	242.9	243.7	244.6	245.5	246.3	247.9
107.5°	299.4	299.9	300.4	301.0	301.5	302.4	303.6	304.8	306.0	307.2	307.9
110°	341.1	341.6	342.1	342.6	343.3	344.0	345.1	346.1	347.2	348.2	348.6



TEST NUMBER: P332604-840

CATALOG NUMBER: S124DIP-S795D810U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	381.5	382.4	383.4	384.4	385.4	386.1	386.6	387.0	387.5	388.0	388.0
115°	443.7	444.2	444.8	445.4	445.9	446.1	445.9	445.7	445.6	445.4	445.7
117.5°	499.8	500.5	501.2	501.9	502.6	503.2	503.5	503.9	504.3	504.7	504.6
120°	537.8	538.5	539.2	539.9	540.5	540.8	540.6	540.5	540.3	540.1	540.5
122.5°	573.1	573.5	573.9	574.3	574.8	575.1	575.3	575.6	575.8	576.1	576.3
125°	623.8	624.5	625.2	625.9	626.6	626.7	626.4	626.1	625.7	625.4	625.9
127.5°	671.8	672.0	672.2	672.4	672.5	673.0	673.8	674.6	675.4	676.2	676.1
130°	702.8	703.0	703.1	703.3	703.5	703.8	704.3	704.9	705.4	705.9	706.1
132.5°	731.1	731.4	731.8	732.2	732.5	733.0	733.6	734.3	734.9	735.6	735.8
135°	773.9	773.7	773.5	773.3	773.2	773.4	774.1	774.8	775.5	776.2	776.5
137.5°	811.5	811.6	811.7	811.7	811.8	812.2	813.0	813.9	814.6	815.4	815.8
140°	836.2	836.6	836.9	837.3	837.6	838.0	838.3	838.7	839.0	839.3	839.9
142.5°	858.3	858.9	859.6	860.2	860.8	861.2	861.4	861.7	861.9	862.1	862.5
145°	892.2	892.8	893.3	893.8	894.3	894.6	894.6	894.6	894.6	894.6	894.8
147.5°	919.3	920.3	921.2	922.2	923.2	923.6	923.4	923.2	923.0	922.9	923.0
150°	938.9	939.6	940.3	941.0	941.6	941.9	941.7	941.6	941.4	941.2	941.2
152.5°	955.2	955.8	956.3	956.9	957.6	957.7	957.4	957.0	956.6	956.3	956.6
155°	978.4	978.5	978.7	978.9	979.1	978.9	978.4	977.8	977.2	976.7	977.4
157.5°	997.7	997.6	997.5	997.4	997.3	996.9	996.3	995.8	995.2	994.6	995.5
160°	1009.2	1008.6	1008.0	1007.5	1007.0	1006.6	1006.5	1006.3	1006.1	1005.9	1007.0
162.5°	1019.3	1018.5	1017.8	1017.2	1016.5	1016.1	1015.9	1015.8	1015.6	1015.4	1016.5
165°	1032.0	1031.2	1030.3	1029.4	1028.5	1028.0	1028.0	1028.0	1028.0	1028.0	1029.5
167.5°	1042.1	1041.2	1040.3	1039.4	1038.4	1037.9	1037.8	1037.7	1037.6	1037.5	1039.1
170°	1047.8	1046.7	1045.7	1044.6	1043.6	1043.2	1043.3	1043.5	1043.7	1043.9	1045.2
172.5°	1051.6	1050.6	1049.5	1048.4	1047.4	1046.9	1047.1	1047.3	1047.4	1047.6	1049.0
175°	1055.7	1054.6	1053.6	1052.6	1051.5	1051.1	1051.3	1051.4	1051.6	1051.8	1053.3
177.5°	1057.6	1056.6	1055.6	1054.6	1053.7	1053.3	1053.6	1053.9	1054.2	1054.4	1055.5
180°	1055.7	1055.7	1055.7	1055.7	1055.7	1055.7	1055.7	1055.7	1055.7	1055.7	1055.7



TEST NUMBER: P332604-840

CATALOG NUMBER: S124DIP-S795D810U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1340.6	1340.6	1340.6	1340.6	1340.6	1340.6	1340.6	1340.6
2.5°	1335.7	1337.7	1339.6	1340.5	1340.3	1340.1	1339.9	1339.7
5°	1328.6	1331.2	1333.8	1334.9	1334.4	1334.0	1333.5	1333.0
7.5°	1313.8	1316.0	1318.0	1318.9	1318.7	1318.4	1318.1	1317.8
10°	1301.4	1303.3	1305.3	1306.0	1305.5	1304.9	1304.5	1304.0
12.5°	1286.4	1288.4	1290.5	1291.2	1290.6	1289.9	1289.2	1288.6
15°	1257.5	1258.9	1260.3	1260.7	1260.0	1259.3	1258.6	1257.9
17.5°	1224.7	1225.6	1226.5	1226.7	1226.2	1225.7	1225.3	1224.8
20°	1200.2	1200.9	1201.6	1201.7	1201.2	1200.8	1200.3	1199.8
22.5°	1174.7	1176.0	1177.3	1177.5	1176.6	1175.8	1174.9	1174.1
25°	1132.7	1132.9	1133.2	1132.8	1131.9	1130.8	1129.9	1128.9
27.5°	1085.5	1084.9	1084.3	1083.5	1082.3	1081.1	1079.8	1078.6
30°	1052.9	1052.0	1051.0	1050.0	1048.7	1047.5	1046.3	1045.2
32.5°	1019.9	1018.8	1017.6	1016.4	1015.2	1014.0	1012.8	1011.7
35°	967.8	966.0	964.3	962.9	961.7	960.6	959.4	958.2
37.5°	913.0	911.2	909.5	907.8	906.2	904.6	903.0	901.4
40°	874.9	872.6	870.2	868.4	867.2	866.1	864.8	863.6
42.5°	838.1	835.4	832.5	830.8	830.0	829.2	828.4	827.6
45°	781.0	778.4	775.8	774.2	773.4	772.6	771.9	771.2
47.5°	725.8	722.9	719.8	717.5	715.7	713.9	712.1	710.2
50°	687.2	683.9	680.5	678.1	676.7	675.3	673.9	672.5
52.5°	647.6	644.6	641.7	639.3	637.5	635.7	633.9	632.1
55°	589.4	586.5	583.6	581.5	580.1	578.7	577.1	575.7
57.5°	531.0	528.3	525.5	523.5	522.1	520.7	519.4	518.0
60°	490.9	488.8	486.6	484.9	483.7	482.5	481.3	480.2
62.5°	451.7	449.8	447.9	446.3	445.0	443.8	442.7	441.5
65°	394.9	392.4	390.0	388.3	387.1	385.9	384.7	383.4
67.5°	336.2	333.9	331.5	330.2	329.9	329.6	329.2	328.9
70°	299.1	297.2	295.3	294.0	293.3	292.6	291.9	291.1
72.5°	262.1	260.5	259.0	257.9	257.1	256.4	255.7	255.0
75°	208.6	207.6	206.7	206.1	205.9	205.6	205.4	205.2
77.5°	157.9	157.6	157.4	156.9	156.3	155.7	155.1	154.5
80°	125.8	125.3	124.8	124.5	124.2	124.0	123.8	123.5
82.5°	96.9	96.6	96.3	96.1	95.9	95.6	95.4	95.1
85°	55.8	55.8	55.8	55.7	55.5	55.2	55.0	54.7
87.5°	24.5	24.7	24.9	25.0	25.1	25.2	25.2	25.3
90°	19.5	20.5	21.6	22.3	22.6	23.0	23.3	23.7
92.5°	18.9	19.9	20.9	21.5	21.6	21.6	21.7	21.8
95°	19.5	20.5	21.6	22.2	22.4	22.5	22.7	22.9
97.5°	21.1	21.2	21.3	21.4	21.6	21.7	21.9	22.1
100°	28.8	25.8	22.8	21.4	21.6	21.7	21.9	22.1
102.5°	103.0	70.9	38.7	22.6	22.6	22.6	22.7	22.7
105°	249.5	251.1	252.7	250.3	244.0	237.6	231.4	225.0
107.5°	308.7	309.4	310.2	310.9	311.6	312.3	313.0	313.7
110°	348.9	349.3	349.6	350.0	350.6	351.1	351.6	352.1



TEST NUMBER: P332604-840

CATALOG NUMBER: S124DIP-S795D810U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	387.9	387.8	387.7	388.0	388.7	389.4	390.0	390.7
115°	446.1	446.4	446.8	447.0	447.0	447.0	447.0	447.0
117.5°	504.5	504.5	504.4	504.3	504.3	504.2	504.1	504.1
120°	540.8	541.2	541.5	541.5	541.2	540.8	540.5	540.1
122.5°	576.5	576.7	576.9	576.8	576.5	576.1	575.8	575.4
125°	626.4	626.9	627.4	627.8	628.0	628.1	628.3	628.5
127.5°	676.0	675.9	675.8	675.7	675.5	675.4	675.3	675.1
130°	706.3	706.4	706.6	706.7	706.7	706.7	706.7	706.7
132.5°	736.0	736.1	736.3	736.3	736.2	736.0	735.9	735.8
135°	776.9	777.2	777.6	777.9	778.3	778.6	779.0	779.3
137.5°	816.1	816.5	816.9	817.0	816.9	816.8	816.7	816.6
140°	840.4	840.9	841.4	841.8	842.0	842.1	842.3	842.5
142.5°	862.8	863.2	863.6	863.8	863.8	863.9	863.9	863.9
145°	894.9	895.1	895.3	895.5	896.0	896.3	896.7	897.0
147.5°	923.2	923.3	923.4	923.6	923.8	923.9	924.1	924.3
150°	941.2	941.2	941.2	941.3	941.5	941.6	941.8	942.0
152.5°	956.9	957.3	957.5	957.6	957.5	957.4	957.3	957.2
155°	978.2	978.9	979.6	979.7	979.1	978.6	978.1	977.5
157.5°	996.4	997.3	998.3	998.3	997.3	996.4	995.5	994.6
160°	1008.0	1009.2	1010.2	1010.2	1009.2	1008.0	1007.0	1005.9
162.5°	1017.5	1018.5	1019.7	1019.6	1018.3	1017.1	1016.0	1014.8
165°	1030.9	1032.3	1033.7	1033.6	1032.0	1030.5	1028.9	1027.2
167.5°	1040.7	1042.2	1043.7	1043.6	1041.9	1040.1	1038.3	1036.6
170°	1046.6	1048.0	1049.5	1049.2	1047.5	1045.8	1044.0	1042.3
172.5°	1050.5	1051.9	1053.3	1053.0	1051.2	1049.2	1047.3	1045.4
175°	1054.9	1056.5	1058.0	1057.8	1055.7	1053.6	1051.5	1049.4
177.5°	1056.7	1057.8	1058.9	1058.6	1056.9	1055.3	1053.6	1051.9
180°	1055.7	1055.7	1055.7	1055.7	1055.7	1055.7	1055.7	1055.7

(END OF REPORT)