

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332597-830

Luminaire Tested: **S124DIP-S795D590U830-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332597-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIP-S795D590U830-4F0-1E-UDD-F4
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 795 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 590 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5202.7 lumens
Efficiency: N/A
Efficacy: 129.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 40.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332597-830

CATALOG NUMBER: S124DIP-S795D590U830-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P332597-830

CATALOG NUMBER: S124DIP-S795D590U830-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67	62
1	100	96	92	88	94	90	87	83	79	76	74	69	67	65	59	58	56	52
2	91	84	77	72	85	79	73	68	69	65	61	60	57	54	52	50	48	43
3	83	74	66	60	78	69	63	57	61	56	51	53	49	46	46	43	40	37
4	76	65	57	51	71	61	54	49	54	48	44	47	43	39	41	38	35	32
5	70	58	50	44	65	55	47	42	49	43	38	43	38	34	37	33	30	27
6	65	52	44	38	60	49	42	36	44	38	33	39	34	30	34	30	27	24
7	60	47	39	33	56	45	37	32	40	34	29	35	30	27	31	27	24	21
8	56	43	35	30	52	41	33	28	36	30	26	32	27	24	28	24	21	19
9	52	39	32	27	48	37	30	25	33	27	23	30	25	21	26	22	19	17
10	48	36	29	24	45	34	28	23	31	25	21	27	23	19	24	20	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10101	10101	10101
5°	10131	10009	10083
10°	10067	9928	9977
15°	9947	9787	9812
20°	9784	9613	9620
25°	9600	9413	9386
30°	9374	9177	9093
35°	9140	8932	8814
40°	8896	8652	8495
45°	8643	8379	8218
50°	8361	8133	7882
55°	8058	7817	7562
60°	7753	7463	7237
65°	7412	7125	6837
70°	7027	6675	6413
75°	6441	6129	5973
80°	5732	5500	5360
85°	5011	4826	4733



TEST NUMBER: P332597-830

CATALOG NUMBER: S124DIP-S795D590U830-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	117.8	2.3
10°-20°	332.0	6.4
20°-30°	488.6	9.4
30°-40°	568.1	10.9
40°-50°	568.1	10.9
50°-60°	496.9	9.6
60°-70°	369.0	7.1
70°-80°	209.7	4.0
80°-90°	62.0	1.2
90°-100°	197.7	3.8
100°-110°	411.4	7.9
110°-120°	368.5	7.1
120°-130°	310.0	6.0
130°-140°	258.4	5.0
140°-150°	197.4	3.8
150°-160°	138.8	2.7
160°-170°	81.6	1.6
170°-180°	26.6	0.5
0°-30°	938.5	18.0
0°-40°	1506.5	29.0
0°-60°	2571.5	49.4
0°-90°	3212.2	61.7
90°-120°	977.6	18.8
90°-150°	1743.4	33.5
90°-180°	1990.0	38.2
0°-180°	5202.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1251	1251	1251	1251	1251	
5°	1250	1246	1235	1245	1244	119
15°	1190	1185	1171	1176	1174	335
25°	1078	1070	1057	1057	1054	496
35°	927	920	906	899	894	580
45°	757	749	734	723	720	583
55°	572	569	555	544	537	513
65°	388	383	373	363	358	384
75°	206	202	196	193	192	219
85°	54	54	52	52	51	60
90°	1	4	10	11	11	4
95°	18	56	438	217	131	20
105°	63	91	353	760	756	67
115°	111	139	314	604	726	110
125°	154	183	313	514	580	137
135°	183	218	310	456	518	142
145°	211	242	309	385	423	133
155°	240	259	300	340	354	111
165°	262	270	288	305	309	74
175°	273	274	276	280	278	26
180°	274	274	274	274	274	



TEST NUMBER: P332597-830

CATALOG NUMBER: S124DIP-S795D590U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1251.2	1251.2	1251.2	1251.2	1251.2	1251.2	1251.2	1251.2	1251.2	1251.2	1251.2
2.5°	1254.4	1253.9	1253.3	1252.8	1252.3	1251.0	1249.1	1247.1	1245.1	1243.2	1244.9
5°	1250.2	1249.3	1248.4	1247.5	1246.6	1244.9	1242.5	1240.0	1237.6	1235.1	1237.6
7.5°	1238.6	1237.7	1236.8	1235.9	1235.0	1233.2	1230.5	1227.8	1225.0	1222.3	1224.3
10°	1228.1	1227.3	1226.3	1225.5	1224.6	1222.7	1219.7	1216.9	1214.0	1211.1	1212.9
12.5°	1214.5	1213.6	1212.7	1211.8	1211.0	1208.9	1205.9	1202.8	1199.8	1196.7	1198.6
15°	1190.1	1189.1	1188.3	1187.3	1186.5	1184.4	1181.0	1177.7	1174.3	1171.0	1172.3
17.5°	1160.6	1159.4	1158.3	1157.3	1156.1	1154.0	1150.8	1147.6	1144.4	1141.3	1142.2
20°	1138.9	1137.7	1136.7	1135.6	1134.4	1132.2	1128.9	1125.5	1122.2	1118.9	1119.6
22.5°	1115.7	1114.2	1112.7	1111.3	1109.7	1107.4	1104.0	1100.7	1097.3	1094.0	1095.2
25°	1077.7	1076.2	1074.6	1073.1	1071.5	1069.1	1066.0	1062.9	1059.8	1056.7	1056.9
27.5°	1034.4	1032.8	1031.2	1029.6	1028.0	1025.8	1022.8	1020.0	1017.1	1014.2	1013.6
30°	1005.6	1003.8	1002.0	1000.2	998.4	996.1	993.2	990.3	987.4	984.5	983.6
32.5°	975.1	973.5	971.9	970.3	968.7	966.3	963.3	960.2	957.2	954.0	953.0
35°	927.4	925.8	924.3	922.7	921.1	918.8	915.7	912.6	909.5	906.3	904.7
37.5°	877.0	875.6	874.2	872.8	871.3	868.9	865.6	862.2	858.9	855.5	853.8
40°	844.1	842.4	840.6	838.8	837.0	834.4	831.1	827.7	824.4	821.0	818.9
42.5°	808.9	807.8	806.7	805.7	804.6	802.2	798.5	794.8	791.1	787.4	784.9
45°	757.0	755.4	753.8	752.2	750.7	748.1	744.6	741.0	737.4	733.9	731.4
47.5°	702.6	701.5	700.5	699.4	698.3	696.2	692.9	689.6	686.3	683.0	680.1
50°	665.7	664.8	663.9	663.0	662.1	660.2	657.0	653.9	650.7	647.6	644.5
52.5°	629.6	628.6	627.5	626.4	625.3	623.1	619.8	616.5	613.2	609.9	607.2
55°	572.5	571.7	571.1	570.4	569.8	567.9	564.8	561.7	558.6	555.4	552.7
57.5°	517.9	517.2	516.4	515.7	514.9	512.9	509.9	506.8	503.8	500.7	498.1
60°	480.2	479.1	478.0	476.9	475.8	473.7	470.9	468.0	465.1	462.2	460.1
62.5°	443.4	442.4	441.5	440.5	439.6	437.6	434.5	431.4	428.4	425.3	423.5
65°	388.0	386.9	385.8	384.7	383.5	381.8	379.7	377.4	375.1	373.0	370.7
67.5°	332.2	331.2	330.2	329.1	328.2	326.6	324.4	322.3	320.2	318.0	315.8
70°	297.7	296.2	294.6	293.0	291.5	289.8	288.0	286.3	284.5	282.8	281.0
72.5°	260.9	259.3	257.8	256.2	254.6	253.2	251.8	250.2	248.8	247.4	246.0
75°	206.5	205.4	204.3	203.2	202.1	201.0	199.8	198.7	197.7	196.5	195.6
77.5°	154.6	154.1	153.6	153.2	152.6	151.9	150.9	150.0	148.9	148.0	147.7
80°	123.3	122.6	122.0	121.3	120.6	120.1	119.6	119.2	118.8	118.3	117.8
82.5°	92.8	92.6	92.2	91.9	91.6	91.4	91.3	91.2	91.1	91.0	90.8
85°	54.1	54.1	54.1	54.1	54.1	53.9	53.4	53.1	52.6	52.1	52.1
87.5°	20.9	21.0	21.1	21.1	21.0	20.8	21.3	21.1	21.1	21.2	21.1
90°	0.6	1.6	3.2	3.8	4.3	4.3	7.5	7.5	8.6	9.7	9.1
92.5°	6.1	9.0	13.9	20.5	28.4	39.6	66.9	108.6	149.3	170.5	142.0
95°	17.7	19.3	24.7	31.8	44.6	67.2	114.0	202.2	330.6	438.2	450.5
97.5°	31.9	31.9	36.5	42.9	54.0	73.0	109.0	181.7	309.5	461.6	566.1
100°	40.9	40.9	44.6	51.1	61.3	78.5	110.2	171.0	280.7	432.3	570.0
102.5°	49.5	50.3	53.6	59.7	69.5	85.8	114.5	168.0	261.3	395.8	537.6
105°	62.9	64.6	67.2	73.7	83.3	99.0	124.7	169.4	244.7	352.7	479.1
107.5°	77.8	78.8	81.5	88.4	97.6	113.0	136.7	177.3	241.7	328.7	431.8
110°	87.7	88.7	91.4	97.8	107.5	122.1	145.7	183.3	242.5	320.5	408.1



TEST NUMBER: P332597-830

CATALOG NUMBER: S124DIP-S795D590U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	97.1	98.2	101.3	107.4	117.0	131.5	154.3	189.8	245.1	316.6	394.7
115°	110.7	112.4	116.1	121.5	131.8	146.3	167.8	200.0	250.1	314.5	382.3
117.5°	125.0	126.5	129.8	135.7	145.2	160.3	180.8	210.5	255.2	314.0	376.7
120°	134.4	135.5	139.2	145.2	154.3	169.4	189.8	217.7	259.2	314.0	373.7
122.5°	143.0	144.1	147.9	153.4	163.3	178.0	198.4	224.6	263.1	313.6	370.2
125°	154.3	156.5	159.7	165.6	175.8	190.9	210.2	235.0	268.8	312.9	364.6
127.5°	164.3	166.1	169.9	176.6	187.3	202.5	221.2	243.9	273.4	311.7	356.9
130°	169.9	172.0	176.3	184.5	194.6	210.2	228.5	249.5	276.9	311.3	352.1
132.5°	175.5	177.2	182.9	190.5	201.5	216.2	234.5	255.1	279.9	310.9	347.9
135°	183.3	185.5	190.9	200.0	211.3	225.3	243.0	262.4	284.5	310.2	341.4
137.5°	191.2	193.2	199.2	207.8	219.6	232.9	249.5	267.6	287.1	310.1	335.8
140°	196.8	198.4	204.3	213.5	224.7	237.6	253.8	271.0	289.3	309.7	332.8
142.5°	202.8	204.4	209.9	218.6	229.5	242.0	257.7	273.5	291.0	309.7	330.3
145°	211.3	212.9	218.3	225.8	236.0	247.9	261.8	276.4	292.0	308.6	325.8
147.5°	220.8	221.4	226.1	233.8	242.4	253.1	266.2	278.8	292.5	306.7	321.9
150°	226.9	227.4	231.8	238.2	246.3	256.5	268.3	280.1	292.5	305.4	318.9
152.5°	232.5	232.6	236.9	242.9	250.2	259.5	270.0	281.0	291.6	303.2	315.4
155°	240.3	240.9	244.1	249.5	255.4	263.4	272.6	281.7	290.3	300.0	310.2
157.5°	248.0	248.0	251.0	255.1	260.3	266.6	274.5	281.7	289.0	296.7	305.0
160°	252.7	252.7	254.9	258.6	262.9	268.8	275.3	281.7	287.7	294.1	301.1
162.5°	257.0	256.6	258.3	261.6	265.5	270.1	276.2	281.7	286.3	291.5	297.7
165°	261.8	261.8	262.9	265.6	268.3	271.5	276.4	280.7	283.9	287.7	292.0
167.5°	266.6	266.2	266.6	268.7	270.2	272.7	276.3	279.4	281.3	283.8	286.8
170°	268.8	268.3	268.8	270.4	271.5	273.1	275.8	278.5	279.6	281.2	283.3
172.5°	271.0	270.4	270.5	271.7	272.4	273.5	275.4	277.7	277.9	278.6	280.3
175°	273.1	272.6	272.6	273.1	273.7	273.7	274.8	276.4	275.8	275.8	276.9
177.5°	274.1	273.7	273.2	273.7	273.7	273.7	274.1	274.9	274.1	274.1	274.6
180°	273.7	273.7	273.7	273.7	273.7	273.7	273.7	273.7	273.7	273.7	273.7



TEST NUMBER: P332597-830

CATALOG NUMBER: S124DIP-S795D590U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1251.2	1251.2	1251.2	1251.2	1251.2	1251.2	1251.2	1251.2
2.5°	1246.7	1248.5	1250.3	1251.1	1250.9	1250.8	1250.6	1250.4
5°	1240.0	1242.5	1244.9	1245.9	1245.5	1245.1	1244.6	1244.2
7.5°	1226.2	1228.2	1230.1	1231.0	1230.8	1230.5	1230.2	1229.9
10°	1214.7	1216.4	1218.2	1218.9	1218.4	1218.0	1217.6	1217.1
12.5°	1200.6	1202.5	1204.5	1205.1	1204.6	1203.9	1203.2	1202.7
15°	1173.7	1175.0	1176.3	1176.7	1176.0	1175.4	1174.7	1174.0
17.5°	1143.0	1143.9	1144.7	1144.9	1144.4	1144.0	1143.6	1143.1
20°	1120.2	1120.9	1121.5	1121.6	1121.2	1120.8	1120.3	1119.8
22.5°	1096.4	1097.6	1098.8	1099.0	1098.2	1097.4	1096.6	1095.8
25°	1057.2	1057.3	1057.6	1057.2	1056.4	1055.5	1054.6	1053.7
27.5°	1013.1	1012.6	1012.0	1011.3	1010.1	1009.0	1007.9	1006.7
30°	982.7	981.8	980.9	980.0	978.8	977.7	976.6	975.5
32.5°	951.9	950.8	949.8	948.7	947.5	946.4	945.3	944.2
35°	903.2	901.6	900.0	898.7	897.6	896.5	895.4	894.3
37.5°	852.2	850.5	848.9	847.3	845.7	844.3	842.8	841.3
40°	816.6	814.5	812.2	810.5	809.4	808.3	807.2	806.1
42.5°	782.2	779.7	777.0	775.4	774.7	773.9	773.2	772.4
45°	729.0	726.5	724.1	722.6	721.8	721.1	720.5	719.8
47.5°	677.4	674.7	671.8	669.7	668.0	666.3	664.6	662.9
50°	641.4	638.3	635.2	632.9	631.6	630.3	629.0	627.6
52.5°	604.5	601.6	598.9	596.7	595.0	593.3	591.6	589.9
55°	550.1	547.4	544.7	542.7	541.4	540.1	538.7	537.3
57.5°	495.6	493.0	490.5	488.6	487.3	486.0	484.7	483.4
60°	458.2	456.2	454.1	452.6	451.5	450.3	449.2	448.2
62.5°	421.6	419.8	418.0	416.5	415.4	414.2	413.2	412.1
65°	368.5	366.3	364.0	362.4	361.3	360.1	359.0	357.9
67.5°	313.8	311.6	309.4	308.2	307.9	307.6	307.3	307.0
70°	279.2	277.4	275.6	274.4	273.7	273.1	272.4	271.7
72.5°	244.6	243.2	241.8	240.7	240.0	239.3	238.7	238.0
75°	194.7	193.8	192.9	192.4	192.2	191.9	191.7	191.5
77.5°	147.4	147.1	146.9	146.5	145.9	145.3	144.8	144.2
80°	117.4	117.0	116.5	116.2	115.9	115.7	115.6	115.3
82.5°	90.5	90.2	89.9	89.7	89.5	89.3	89.1	88.8
85°	52.1	52.1	52.1	52.0	51.8	51.6	51.4	51.1
87.5°	21.2	21.3	21.4	21.4	21.5	21.6	21.5	21.5
90°	9.7	10.2	10.7	10.7	11.3	11.8	11.3	11.3
92.5°	105.6	79.5	63.2	52.5	46.1	43.3	41.4	41.4
95°	398.4	315.1	243.0	190.9	164.6	147.9	138.2	131.2
97.5°	588.6	557.7	505.1	448.9	410.4	378.0	361.8	350.6
100°	648.5	659.2	632.8	593.0	546.3	513.5	497.4	493.0
102.5°	645.5	698.8	706.4	689.8	661.1	637.3	620.4	616.9
105°	602.2	695.2	748.5	770.5	771.6	767.2	759.7	756.5
107.5°	540.8	639.8	714.8	762.7	789.3	801.5	806.9	808.3
110°	503.8	596.8	674.8	734.0	772.1	794.7	804.4	809.2



TEST NUMBER: P332597-830

CATALOG NUMBER: S124DIP-S795D590U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	476.7	558.9	632.6	691.7	735.1	762.4	776.0	783.8
115°	449.5	515.7	578.5	630.2	672.6	704.9	722.1	726.4
117.5°	436.1	490.9	540.4	584.1	620.4	647.4	664.9	668.3
120°	430.2	480.1	523.1	561.3	592.0	615.7	629.6	635.6
122.5°	425.0	473.3	512.4	545.8	571.7	592.0	603.8	609.7
125°	416.1	462.4	499.5	529.0	550.5	566.2	576.4	579.6
127.5°	405.4	449.6	486.6	514.6	536.3	550.2	558.7	561.9
130°	396.8	439.3	475.8	504.4	526.4	539.8	548.5	551.7
132.5°	387.8	427.6	463.4	491.8	513.5	528.7	536.8	540.1
135°	375.3	410.3	443.0	470.0	491.4	506.5	515.1	518.3
137.5°	364.0	393.6	421.2	445.5	465.6	480.5	487.6	491.4
140°	357.5	382.9	407.0	429.6	448.5	460.2	467.8	472.1
142.5°	351.6	373.8	394.5	414.2	430.7	441.8	448.5	451.4
145°	343.0	361.3	377.5	392.5	406.0	415.1	420.5	423.1
147.5°	336.0	350.5	363.4	375.3	385.2	393.0	397.1	398.1
150°	331.8	344.1	354.9	364.6	373.2	380.1	383.3	383.9
152.5°	327.0	337.6	347.5	355.5	362.8	368.5	370.4	371.0
155°	319.9	328.5	336.6	343.0	348.5	352.7	354.3	354.3
157.5°	312.3	319.5	326.2	331.4	335.5	338.7	339.7	339.7
160°	307.6	313.5	319.3	323.7	326.9	330.2	330.6	330.6
162.5°	302.8	307.8	312.5	316.4	318.8	322.0	322.5	322.1
165°	296.2	299.4	303.2	305.9	308.1	310.2	309.7	309.2
167.5°	289.9	292.4	295.4	297.0	298.1	299.4	299.4	299.0
170°	286.1	287.7	289.8	291.4	292.5	293.0	292.5	292.5
172.5°	282.6	283.8	285.1	286.3	286.9	287.5	286.9	286.1
175°	278.0	278.5	279.6	279.6	279.6	280.7	279.6	278.5
177.5°	274.9	275.4	275.4	275.8	275.4	275.8	274.9	274.1
180°	273.7	273.7	273.7	273.7	273.7	273.7	273.7	273.7

(END OF REPORT)