

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332875-840

Luminaire Tested: **S124RDIP-S350D590U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332875-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124RDIP-S350D590U840-4F0-1E-UDD-F1  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 350 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 590 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3510.7 lumens  
Efficiency: N/A  
Efficacy: 137.1 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 25.6  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332875-840

CATALOG NUMBER: S124RDIP-S350D590U840-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332875-840

CATALOG NUMBER: S124RDIP-S350D590U840-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	78	78	78	63	63	63	48	48	48
1	96	92	88	85	87	84	81	78	69	67	65	55	54	52	43	42	41
2	88	80	74	69	80	74	68	64	61	57	54	49	46	44	38	36	35
3	80	71	64	58	73	65	59	54	54	49	46	43	40	38	34	32	30
4	73	63	55	49	67	58	51	46	48	43	39	39	35	32	30	28	26
5	67	56	48	42	61	51	44	39	43	38	34	35	31	28	27	25	23
6	62	50	42	37	56	46	39	34	39	33	29	31	28	25	25	22	20
7	57	45	38	32	52	42	35	30	35	30	26	29	25	22	23	20	18
8	53	41	34	28	48	38	31	27	32	27	23	26	22	19	21	18	16
9	49	38	30	25	45	35	28	24	29	24	21	24	20	18	19	17	14
10	46	34	27	23	42	32	26	21	27	22	19	22	19	16	18	15	13

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	5040	5040	5040
5°	5051	4989	5020
10°	5019	4930	4930
15°	4962	4826	4790
20°	4883	4689	4603
25°	4782	4530	4415
30°	4683	4363	4180
35°	4574	4188	3943
40°	4443	3990	3687
45°	4322	3793	3427
50°	4185	3567	3152
55°	4037	3330	2853
60°	3873	3073	2546
65°	3725	2749	2245
70°	3510	2391	1907
75°	3235	1984	1550
80°	2822	1511	1423
85°	2399	1371	1278



TEST NUMBER: P332875-840

CATALOG NUMBER: S124RDIP-S350D590U840-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	58.6	1.7
10°-20°	163.5	4.7
20°-30°	236.1	6.7
30°-40°	267.7	7.6
40°-50°	258.5	7.4
50°-60°	214.9	6.1
60°-70°	148.4	4.2
70°-80°	75.2	2.1
80°-90°	21.5	0.6
90°-100°	49.1	1.4
100°-110°	145.5	4.1
110°-120°	247.0	7.0
120°-130°	325.7	9.3
130°-140°	365.7	10.4
140°-150°	359.4	10.2
150°-160°	302.3	8.6
160°-170°	201.1	5.7
170°-180°	70.4	2.0
0°-30°	458.3	13.1
0°-40°	726.0	20.7
0°-60°	1199.4	34.2
0°-90°	1444.6	41.1
90°-120°	441.6	12.6
90°-150°	1492.4	42.5
90°-180°	2066.0	58.8
0°-180°	3510.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	624	624	624	624	624	
5°	623	621	616	620	620	59
15°	594	589	577	576	573	167
25°	537	528	509	501	496	247
35°	464	448	425	409	400	290
45°	379	360	332	310	300	292
55°	287	267	237	213	203	256
65°	195	174	144	124	118	193
75°	104	86	64	53	50	110
85°	26	17	15	14	14	29
90°	2	8	13	16	17	3
95°	34	40	44	45	46	38
105°	134	135	137	139	141	142
115°	251	251	250	249	249	248
125°	366	366	365	364	363	326
135°	472	475	475	474	472	365
145°	573	575	576	575	574	358
155°	657	657	656	658	656	302
165°	715	713	712	715	713	201
175°	744	741	740	744	740	71
180°	745	745	745	745	745	



TEST NUMBER: P332875-840

CATALOG NUMBER: S124RDIP-S350D590U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	624.3	624.3	624.3	624.3	624.3	624.3	624.3	624.3	624.3	624.3	624.3
2.5°	625.8	625.4	625.1	624.8	624.4	623.8	622.9	622.0	621.0	620.1	621.0
5°	623.3	622.9	622.5	622.1	621.6	620.8	619.5	618.2	616.9	615.7	616.7
7.5°	617.6	617.2	616.8	616.3	615.9	614.8	613.2	611.5	609.9	608.2	608.8
10°	612.3	611.8	611.3	610.8	610.2	608.9	607.0	605.1	603.2	601.4	601.8
12.5°	605.4	604.8	604.2	603.6	603.0	601.6	599.3	597.0	594.8	592.5	592.8
15°	593.7	592.7	591.8	590.8	589.9	588.0	585.4	582.7	580.1	577.4	577.2
17.5°	579.5	578.0	576.6	575.3	573.9	571.6	568.5	565.2	562.1	558.9	558.3
20°	568.4	566.9	565.6	564.2	562.8	560.4	556.7	553.1	549.5	545.8	545.0
22.5°	556.1	554.5	553.0	551.5	549.9	547.1	543.3	539.5	535.6	531.7	530.5
25°	536.8	534.9	533.0	531.1	529.2	526.0	521.7	517.4	512.9	508.6	506.8
27.5°	516.5	514.1	511.7	509.4	507.0	503.4	498.8	494.1	489.5	484.8	482.5
30°	502.4	499.7	497.1	494.4	491.8	488.0	482.9	478.0	472.9	468.0	465.3
32.5°	487.5	484.4	481.5	478.5	475.4	471.4	466.3	461.1	456.0	450.8	447.7
35°	464.1	460.7	457.4	453.9	450.5	446.2	440.9	435.6	430.3	425.0	421.3
37.5°	439.2	435.7	432.2	428.7	425.2	420.5	414.5	408.7	402.8	397.0	392.9
40°	421.6	418.1	414.5	411.1	407.6	402.8	396.8	390.7	384.7	378.6	374.2
42.5°	404.8	401.1	397.4	393.7	390.1	385.1	378.8	372.4	366.2	359.8	355.3
45°	378.6	374.7	370.7	366.8	362.8	357.7	351.3	345.0	338.6	332.2	327.0
47.5°	351.5	347.5	343.5	339.3	335.3	329.9	323.4	316.7	310.0	303.5	298.0
50°	333.2	329.0	324.9	320.7	316.6	311.1	304.4	297.5	290.7	284.0	278.6
52.5°	314.5	310.3	306.3	302.3	298.2	292.7	285.7	278.7	271.8	264.8	259.4
55°	286.8	282.6	278.3	274.1	269.8	264.2	257.3	250.4	243.5	236.6	231.1
57.5°	259.4	255.0	250.6	246.2	241.8	236.2	229.3	222.6	215.8	208.9	203.4
60°	239.9	235.7	231.5	227.2	223.0	217.4	210.7	203.8	197.0	190.3	184.7
62.5°	222.4	217.9	213.5	209.1	204.7	199.0	192.1	185.1	178.1	171.2	166.0
65°	195.0	190.5	185.9	181.4	176.7	171.1	164.3	157.4	150.7	143.9	139.4
67.5°	166.6	162.3	157.8	153.5	149.2	143.8	137.4	131.2	124.8	118.6	114.6
70°	148.7	144.2	139.8	135.3	130.8	125.5	119.5	113.4	107.3	101.3	97.9
72.5°	129.6	125.5	121.5	117.4	113.4	108.6	102.8	97.0	91.4	85.6	82.7
75°	103.7	99.8	95.8	91.9	88.0	83.5	78.6	73.5	68.6	63.6	61.1
77.5°	77.6	74.2	70.9	67.6	64.2	60.5	56.5	52.4	48.4	44.3	42.9
80°	60.7	57.7	54.5	51.5	48.4	45.2	42.1	38.9	35.6	32.5	32.2
82.5°	46.2	43.3	40.5	37.7	34.8	32.5	30.7	28.9	27.1	25.2	25.0
85°	25.9	23.7	21.6	19.4	17.3	16.1	15.8	15.5	15.1	14.8	14.6
87.5°	9.2	8.8	8.4	8.0	7.6	7.4	7.6	7.7	7.8	7.9	8.0
90°	1.7	3.1	4.5	6.0	7.4	8.6	9.6	10.6	11.6	12.6	13.4
92.5°	12.3	13.9	15.6	17.2	18.8	19.9	20.7	21.4	22.1	22.8	23.2
95°	34.5	35.7	36.9	38.0	39.2	40.2	41.1	42.0	42.9	43.7	44.1
97.5°	60.4	61.3	62.2	63.1	64.0	65.0	66.0	67.2	68.2	69.3	69.7
100°	80.6	81.2	81.7	82.2	82.7	83.5	84.6	85.8	86.9	88.2	88.4
102.5°	101.8	102.0	102.2	102.4	102.6	103.3	104.3	105.3	106.4	107.4	107.9
105°	134.2	134.3	134.4	134.6	134.7	135.0	135.5	136.0	136.5	137.0	137.4
107.5°	168.1	168.3	168.4	168.6	168.8	169.0	169.0	169.1	169.2	169.3	169.6
110°	191.3	191.5	191.8	192.0	192.3	192.3	192.2	192.1	192.0	191.8	191.6



TEST NUMBER: P332875-840

CATALOG NUMBER: S124RDIP-S350D590U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	215.2	215.2	215.3	215.3	215.4	215.3	215.1	214.8	214.6	214.4	214.3
115°	251.2	251.2	251.2	251.2	251.2	251.0	250.7	250.4	250.2	249.9	249.8
117.5°	285.0	285.1	285.2	285.3	285.4	285.4	285.2	285.0	284.8	284.7	284.2
120°	307.6	308.1	308.6	309.1	309.6	309.7	309.3	308.9	308.5	308.1	307.5
122.5°	331.0	331.2	331.4	331.6	331.8	331.9	331.7	331.5	331.3	331.2	330.7
125°	365.8	365.8	365.8	365.8	365.8	365.7	365.6	365.5	365.3	365.2	364.9
127.5°	397.2	397.6	398.0	398.4	398.7	398.8	398.6	398.4	398.2	398.0	397.8
130°	419.3	419.7	420.1	420.5	420.8	421.0	421.0	421.0	421.0	421.0	420.8
132.5°	441.9	442.2	442.4	442.7	443.0	443.1	443.0	442.9	442.8	442.7	442.4
135°	471.7	472.5	473.2	474.0	474.8	475.1	475.1	475.1	475.1	475.1	474.9
137.5°	504.2	504.5	504.9	505.2	505.6	505.9	506.1	506.3	506.5	506.8	506.4
140°	525.8	526.1	526.3	526.6	526.8	527.0	527.0	527.0	527.0	527.0	526.8
142.5°	545.6	545.9	546.2	546.4	546.7	546.7	546.6	546.5	546.4	546.3	546.3
145°	573.1	573.6	574.1	574.6	575.1	575.4	575.6	575.7	575.8	575.9	575.8
147.5°	600.3	600.9	601.5	602.1	602.8	603.0	602.9	602.8	602.7	602.6	602.5
150°	616.8	617.4	617.9	618.4	618.9	619.1	619.1	619.1	619.1	619.1	619.1
152.5°	632.6	632.9	633.2	633.5	633.8	634.0	634.1	634.2	634.3	634.4	634.7
155°	656.6	656.6	656.6	656.6	656.6	656.5	656.4	656.3	656.2	656.0	656.5
157.5°	676.9	676.6	676.4	676.2	676.0	675.8	675.8	675.8	675.8	675.7	676.1
160°	688.8	688.7	688.6	688.5	688.3	688.2	688.1	688.0	687.8	687.7	688.1
162.5°	699.9	699.6	699.2	698.9	698.6	698.3	698.2	698.1	698.0	697.8	698.5
165°	714.8	714.4	714.0	713.7	713.3	713.0	712.7	712.5	712.2	712.0	712.7
167.5°	726.2	725.7	725.1	724.6	724.1	723.8	723.8	723.9	723.9	723.9	724.7
170°	732.7	732.1	731.3	730.7	730.0	729.8	729.9	730.0	730.2	730.3	731.1
172.5°	737.2	736.7	736.2	735.7	735.1	734.9	734.9	734.9	734.9	735.0	735.8
175°	743.6	743.0	742.4	741.6	741.0	740.6	740.5	740.4	740.2	740.1	741.0
177.5°	745.7	745.2	744.7	744.2	743.6	743.4	743.4	743.4	743.4	743.4	744.1
180°	744.8	744.8	744.8	744.8	744.8	744.8	744.8	744.8	744.8	744.8	744.8



TEST NUMBER: P332875-840

CATALOG NUMBER: S124RDIP-S350D590U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	624.3	624.3	624.3	624.3	624.3	624.3	624.3	624.3
2.5°	622.0	622.9	623.8	624.2	624.1	624.1	624.0	623.9
5°	617.8	618.8	620.0	620.4	620.2	620.0	619.7	619.5
7.5°	609.6	610.3	611.0	611.1	610.8	610.5	610.1	609.8
10°	602.2	602.6	603.0	603.0	602.6	602.2	601.8	601.4
12.5°	593.0	593.3	593.6	593.4	592.8	592.2	591.6	591.0
15°	577.0	576.8	576.5	576.1	575.3	574.6	573.9	573.1
17.5°	557.6	557.1	556.5	555.6	554.5	553.4	552.3	551.2
20°	544.2	543.3	542.5	541.4	540.0	538.6	537.2	535.8
22.5°	529.2	527.9	526.6	525.4	524.3	523.2	522.1	520.9
25°	504.9	503.2	501.4	500.0	498.9	497.8	496.8	495.6
27.5°	480.3	478.1	475.8	474.0	472.4	470.9	469.4	467.9
30°	462.6	460.0	457.4	455.1	453.4	451.8	450.1	448.4
32.5°	444.6	441.5	438.5	436.1	434.4	432.8	431.2	429.6
35°	417.7	414.1	410.5	407.8	405.9	403.9	402.0	400.1
37.5°	388.9	384.9	380.8	377.8	375.9	374.0	372.0	370.1
40°	369.6	365.2	360.7	357.6	355.7	353.8	351.8	349.9
42.5°	350.7	346.2	341.6	338.4	336.4	334.4	332.3	330.4
45°	321.8	316.6	311.3	307.8	305.9	304.0	302.1	300.2
47.5°	292.7	287.2	281.9	278.1	276.0	273.9	271.8	269.7
50°	273.3	268.0	262.7	259.0	257.0	255.0	253.0	251.0
52.5°	254.0	248.6	243.3	239.4	237.4	235.3	233.2	231.1
55°	225.6	220.0	214.5	210.8	208.7	206.7	204.7	202.7
57.5°	197.7	192.2	186.5	183.0	181.5	180.0	178.3	176.8
60°	179.2	173.7	168.1	164.5	162.8	161.2	159.5	157.7
62.5°	161.0	155.8	150.8	147.5	146.1	144.8	143.4	142.1
65°	134.7	130.2	125.6	122.7	121.4	120.2	118.9	117.5
67.5°	110.7	106.7	102.8	100.2	98.8	97.4	95.9	94.5
70°	94.3	90.8	87.4	85.0	83.9	82.9	81.8	80.8
72.5°	79.7	76.6	73.7	71.7	70.7	69.8	68.8	67.8
75°	58.7	56.2	53.8	52.3	51.6	51.0	50.4	49.7
77.5°	41.5	40.1	38.7	37.9	37.7	37.5	37.3	37.1
80°	31.9	31.5	31.2	31.0	30.9	30.8	30.7	30.6
82.5°	24.7	24.5	24.3	24.1	24.0	23.9	23.8	23.7
85°	14.4	14.1	13.9	13.8	13.8	13.8	13.8	13.8
87.5°	8.0	8.1	8.2	8.3	8.4	8.6	8.7	8.8
90°	14.2	14.9	15.8	16.3	16.6	16.8	17.1	17.3
92.5°	23.7	24.2	24.6	24.9	25.1	25.2	25.4	25.5
95°	44.5	44.9	45.3	45.5	45.5	45.5	45.5	45.5
97.5°	70.2	70.6	71.1	71.3	71.3	71.3	71.3	71.3
100°	88.7	88.9	89.2	89.3	89.3	89.3	89.3	89.3
102.5°	108.2	108.6	108.9	109.2	109.3	109.4	109.5	109.6
105°	137.8	138.3	138.7	139.0	139.4	139.8	140.2	140.6
107.5°	170.0	170.3	170.7	170.9	170.8	170.8	170.8	170.8
110°	191.3	191.1	190.8	190.9	191.3	191.6	192.0	192.4





TEST NUMBER: P332875-840

CATALOG NUMBER: S124RDIP-S350D590U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	214.3	214.2	214.2	214.2	214.3	214.3	214.4	214.5
115°	249.7	249.6	249.4	249.3	249.2	249.0	248.9	248.8
117.5°	283.8	283.4	282.9	282.6	282.3	282.1	281.8	281.6
120°	306.9	306.2	305.6	305.4	305.7	305.9	306.2	306.4
122.5°	330.3	329.9	329.4	329.0	328.5	328.1	327.6	327.2
125°	364.7	364.4	364.2	363.9	363.7	363.3	363.1	362.8
127.5°	397.5	397.3	397.0	396.8	396.6	396.4	396.2	396.0
130°	420.5	420.3	420.0	419.6	419.1	418.6	418.1	417.6
132.5°	442.2	441.9	441.7	441.4	441.2	441.0	440.8	440.6
135°	474.6	474.4	474.1	473.8	473.4	473.0	472.7	472.3
137.5°	506.0	505.7	505.4	505.2	505.3	505.4	505.5	505.6
140°	526.7	526.6	526.5	526.3	526.2	526.1	526.0	525.8
142.5°	546.3	546.3	546.2	546.2	546.2	546.2	546.1	546.1
145°	575.7	575.6	575.4	575.2	574.8	574.4	574.0	573.7
147.5°	602.4	602.3	602.2	602.1	602.0	601.8	601.7	601.6
150°	619.1	619.1	619.1	619.1	618.9	618.8	618.7	618.6
152.5°	635.0	635.3	635.6	635.6	635.3	634.9	634.6	634.3
155°	657.0	657.5	658.1	658.1	657.5	657.0	656.5	656.0
157.5°	676.5	676.9	677.3	677.2	676.8	676.4	675.9	675.5
160°	688.5	688.8	689.2	689.1	688.5	687.8	687.2	686.6
162.5°	699.2	699.9	700.6	700.6	700.0	699.3	698.7	698.1
165°	713.5	714.2	715.0	715.1	714.6	714.1	713.6	713.1
167.5°	725.4	726.2	727.0	726.9	726.2	725.4	724.6	723.8
170°	731.8	732.7	733.4	733.4	732.5	731.5	730.6	729.7
172.5°	736.7	737.6	738.4	738.4	737.5	736.6	735.7	734.9
175°	741.9	742.9	743.7	743.7	742.9	741.9	741.0	740.1
177.5°	744.8	745.5	746.2	746.2	745.4	744.6	743.7	742.9
180°	744.8	744.8	744.8	744.8	744.8	744.8	744.8	744.8

(END OF REPORT)