

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332916-840

Luminaire Tested: **S124RDIP-S575D1035U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332916-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124RDIP-S575D1035U840-4F0-1E-UDD-F  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1035 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6544.4 lumens  
Efficiency: N/A  
Efficacy: 147.1 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 44.5  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332916-840

CATALOG NUMBER: S124RDIP-S575D1035U840-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P332916-840

CATALOG NUMBER: S124RDIP-S575D1035U840-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44	36
1	95	91	87	84	86	82	79	76	67	64	62	52	51	49	39	38	37	31
2	87	79	74	69	78	72	67	63	59	55	52	46	44	41	34	33	32	26
3	79	70	63	57	71	64	58	53	52	47	44	41	38	35	31	29	27	22
4	72	62	54	48	65	56	50	45	46	41	37	36	33	30	27	25	23	19
5	66	55	47	42	60	50	44	38	41	36	32	33	29	26	25	22	20	17
6	61	49	42	36	55	45	38	33	37	32	28	30	26	23	22	20	18	15
7	56	45	37	31	51	41	34	29	34	29	25	27	23	20	21	18	16	13
8	52	40	33	28	47	37	30	26	31	26	22	25	21	18	19	16	14	12
9	49	37	30	25	44	34	27	23	28	23	20	23	19	16	17	15	13	11
10	45	34	27	22	41	31	25	21	26	21	18	21	17	15	16	14	12	10

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	8285	8285	8285
5°	8304	8203	8253
10°	8252	8104	8104
15°	8157	7934	7875
20°	8027	7710	7568
25°	7861	7448	7259
30°	7699	7171	6871
35°	7521	6885	6482
40°	7304	6559	6062
45°	7106	6235	5634
50°	6880	5863	5181
55°	6636	5475	4690
60°	6370	5050	4187
65°	6124	4518	3692
70°	5769	3932	3135
75°	5321	3260	2548
80°	4640	2483	2338
85°	3927	2251	2112



TEST NUMBER: P332916-840

CATALOG NUMBER: S124RDIP-S575D1035U840-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	96.4	1.5
10°-20°	268.8	4.1
20°-30°	388.2	5.9
30°-40°	440.0	6.7
40°-50°	424.9	6.5
50°-60°	353.4	5.4
60°-70°	244.0	3.7
70°-80°	123.7	1.9
80°-90°	35.6	0.5
90°-100°	46.1	0.7
100°-110°	293.9	4.5
110°-120°	562.3	8.6
120°-130°	713.8	10.9
130°-140°	763.7	11.7
140°-150°	714.1	10.9
150°-160°	575.9	8.8
160°-170°	371.4	5.7
170°-180°	128.0	2.0
0°-30°	753.5	11.5
0°-40°	1193.5	18.2
0°-60°	1971.8	30.1
0°-90°	2375.1	36.3
90°-120°	902.3	13.8
90°-150°	3094.0	47.3
90°-180°	4169.0	63.7
0°-180°	6544.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1026	1026	1026	1026	1026	
5°	1025	1021	1012	1020	1018	97
15°	976	968	949	948	942	275
25°	882	867	836	823	815	406
35°	763	737	699	673	658	477
45°	622	592	546	509	494	480
55°	472	439	389	350	333	422
65°	321	286	236	204	193	317
75°	171	141	104	87	82	180
85°	42	28	24	23	23	48
90°	3	14	22	28	30	5
95°	55	23	22	28	29	71
105°	304	309	315	321	287	317
115°	566	569	569	570	571	557
125°	796	800	798	801	802	711
135°	988	987	991	993	995	761
145°	1139	1142	1142	1143	1145	712
155°	1249	1250	1247	1251	1248	576
165°	1318	1313	1312	1320	1312	372
175°	1348	1342	1343	1351	1340	128
180°	1348	1348	1348	1348	1348	



TEST NUMBER: P332916-840

CATALOG NUMBER: S124RDIP-S575D1035U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1026.3	1026.3	1026.3	1026.3	1026.3	1026.3	1026.3	1026.3	1026.3	1026.3	1026.3
2.5°	1028.9	1028.2	1027.7	1027.1	1026.6	1025.5	1024.0	1022.5	1020.9	1019.4	1020.9
5°	1024.7	1024.0	1023.3	1022.6	1022.0	1020.6	1018.4	1016.3	1014.2	1012.2	1013.9
7.5°	1015.4	1014.7	1014.0	1013.3	1012.5	1010.8	1008.0	1005.3	1002.6	999.9	1001.0
10°	1006.6	1005.8	1004.9	1004.0	1003.2	1001.2	998.0	994.8	991.7	988.6	989.3
12.5°	995.3	994.3	993.3	992.3	991.3	989.0	985.2	981.5	977.9	974.1	974.5
15°	976.0	974.4	972.9	971.3	969.7	966.7	962.4	958.1	953.6	949.3	949.0
17.5°	952.6	950.3	948.1	945.7	943.5	939.8	934.5	929.3	924.0	918.8	917.9
20°	934.3	932.1	929.8	927.6	925.2	921.2	915.2	909.3	903.3	897.5	896.1
22.5°	914.2	911.7	909.2	906.6	904.0	899.6	893.2	886.9	880.5	874.1	872.0
25°	882.5	879.4	876.2	873.0	869.9	864.7	857.6	850.4	843.2	836.2	833.1
27.5°	849.2	845.3	841.3	837.4	833.3	827.6	819.9	812.3	804.7	797.0	793.3
30°	825.9	821.5	817.2	812.8	808.5	802.1	794.0	785.8	777.5	769.3	765.0
32.5°	801.4	796.5	791.5	786.6	781.7	775.0	766.5	758.0	749.5	741.0	736.0
35°	763.1	757.5	751.8	746.3	740.7	733.6	724.8	716.1	707.3	698.6	692.7
37.5°	722.1	716.3	710.5	704.8	698.9	691.3	681.6	671.9	662.3	652.6	645.9
40°	693.1	687.3	681.6	675.8	670.0	662.2	652.3	642.3	632.4	622.4	615.0
42.5°	665.4	659.4	653.4	647.3	641.3	633.1	622.7	612.3	602.0	591.6	584.1
45°	622.4	615.9	609.5	603.0	596.5	588.0	577.5	567.1	556.6	546.1	537.6
47.5°	577.9	571.3	564.5	557.8	551.2	542.4	531.5	520.7	509.8	498.9	490.0
50°	547.8	540.9	534.1	527.3	520.5	511.5	500.3	489.2	478.0	466.8	458.1
52.5°	516.9	510.3	503.6	497.0	490.2	481.2	469.7	458.3	446.8	435.4	426.5
55°	471.5	464.5	457.6	450.5	443.5	434.3	423.0	411.7	400.3	389.0	379.9
57.5°	426.6	419.3	412.0	404.8	397.5	388.3	377.1	365.9	354.8	343.6	334.4
60°	394.5	387.5	380.5	373.5	366.6	357.5	346.3	335.1	324.0	312.8	303.7
62.5°	365.6	358.3	351.0	343.8	336.5	327.2	315.7	304.3	292.8	281.3	273.0
65°	320.6	313.2	305.6	298.1	290.5	281.2	270.0	258.9	247.7	236.5	229.0
67.5°	274.0	266.7	259.5	252.4	245.2	236.4	226.0	215.6	205.3	194.9	188.4
70°	244.4	237.0	229.7	222.4	215.1	206.4	196.4	186.5	176.5	166.6	160.9
72.5°	213.0	206.3	199.7	193.1	186.4	178.4	169.1	159.7	150.2	140.8	135.9
75°	170.6	164.1	157.6	151.2	144.7	137.3	129.2	120.9	112.7	104.5	100.5
77.5°	127.4	122.0	116.5	111.0	105.5	99.5	92.8	86.2	79.6	72.9	70.6
80°	99.8	94.7	89.7	84.6	79.6	74.4	69.2	63.9	58.7	53.4	52.9
82.5°	75.9	71.3	66.7	62.0	57.4	53.5	50.5	47.5	44.5	41.5	41.1
85°	42.4	39.0	35.4	31.9	28.5	26.5	26.0	25.4	24.8	24.3	24.0
87.5°	15.0	14.4	13.8	13.2	12.5	12.3	12.6	12.8	13.0	13.2	13.3
90°	3.0	5.5	8.0	10.4	12.9	15.0	16.8	18.6	20.4	22.2	23.5
92.5°	12.7	12.8	12.9	13.1	13.2	14.2	16.0	17.8	19.6	21.4	22.7
95°	55.4	47.9	40.2	32.6	24.9	21.3	21.5	21.7	21.9	22.2	23.5
97.5°	117.8	122.5	127.2	132.0	136.7	126.6	101.6	76.6	51.6	26.7	26.8
100°	165.3	169.4	173.4	177.4	181.5	168.0	137.1	106.2	75.2	44.3	40.6
102.5°	218.5	221.6	224.5	227.4	230.4	229.8	225.8	221.8	217.7	213.7	172.6
105°	303.5	304.8	306.1	307.5	308.8	310.0	311.1	312.3	313.5	314.6	316.6
107.5°	382.2	382.9	383.6	384.3	385.0	386.1	387.6	389.1	390.6	392.1	393.1
110°	435.6	436.2	436.9	437.5	438.2	439.2	440.5	441.9	443.2	444.5	445.0



TEST NUMBER: P332916-840

CATALOG NUMBER: S124RDIP-S575D1035U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	487.2	488.4	489.6	490.8	492.0	492.9	493.5	494.1	494.7	495.3	495.3
115°	566.5	567.2	567.9	568.6	569.3	569.5	569.3	569.1	568.8	568.6	569.1
117.5°	638.1	639.0	640.0	640.9	641.8	642.4	642.9	643.4	643.9	644.4	644.3
120°	686.5	687.4	688.3	689.2	690.1	690.4	690.2	690.0	689.7	689.5	690.0
122.5°	731.6	732.3	732.8	733.3	733.9	734.3	734.6	734.9	735.2	735.5	735.8
125°	796.4	797.3	798.2	799.1	800.0	800.2	799.8	799.3	798.9	798.4	799.1
127.5°	857.7	857.9	858.2	858.4	858.6	859.2	860.3	861.3	862.3	863.3	863.2
130°	897.3	897.5	897.7	897.9	898.1	898.6	899.3	899.9	900.6	901.3	901.5
132.5°	933.5	933.9	934.3	934.7	935.1	935.7	936.6	937.5	938.3	939.2	939.4
135°	988.0	987.7	987.5	987.2	987.0	987.3	988.3	989.2	990.1	991.0	991.4
137.5°	1036.1	1036.2	1036.3	1036.4	1036.5	1037.0	1038.0	1039.1	1040.0	1041.0	1041.5
140°	1067.6	1068.0	1068.5	1068.9	1069.3	1069.9	1070.3	1070.8	1071.2	1071.7	1072.3
142.5°	1095.8	1096.6	1097.4	1098.2	1099.0	1099.5	1099.8	1100.1	1100.3	1100.7	1101.2
145°	1139.1	1139.8	1140.5	1141.1	1141.9	1142.2	1142.2	1142.2	1142.2	1142.2	1142.5
147.5°	1173.7	1174.9	1176.2	1177.4	1178.7	1179.2	1178.9	1178.7	1178.5	1178.3	1178.5
150°	1198.6	1199.5	1200.4	1201.3	1202.2	1202.5	1202.3	1202.1	1201.9	1201.6	1201.6
152.5°	1219.6	1220.3	1221.0	1221.7	1222.4	1222.6	1222.2	1221.8	1221.4	1221.0	1221.4
155°	1249.1	1249.3	1249.5	1249.7	1249.9	1249.7	1249.1	1248.4	1247.7	1247.1	1247.9
157.5°	1273.8	1273.7	1273.5	1273.4	1273.3	1272.8	1272.1	1271.3	1270.6	1269.8	1271.0
160°	1288.4	1287.7	1287.1	1286.4	1285.7	1285.3	1285.1	1284.8	1284.5	1284.3	1285.7
162.5°	1301.3	1300.4	1299.6	1298.7	1297.9	1297.4	1297.1	1296.9	1296.7	1296.5	1297.8
165°	1317.6	1316.5	1315.3	1314.2	1313.1	1312.5	1312.5	1312.5	1312.5	1312.5	1314.3
167.5°	1330.5	1329.4	1328.2	1327.1	1325.9	1325.2	1325.0	1324.9	1324.8	1324.6	1326.7
170°	1337.8	1336.5	1335.0	1333.7	1332.4	1331.8	1332.0	1332.3	1332.5	1332.7	1334.5
172.5°	1342.6	1341.3	1339.9	1338.6	1337.3	1336.7	1336.9	1337.2	1337.4	1337.6	1339.4
175°	1347.9	1346.6	1345.1	1343.8	1342.5	1341.9	1342.1	1342.4	1342.6	1342.8	1344.8
177.5°	1350.3	1349.0	1347.8	1346.6	1345.2	1344.8	1345.1	1345.5	1345.8	1346.3	1347.7
180°	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9



TEST NUMBER: P332916-840

CATALOG NUMBER: S124RDIP-S575D1035U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1026.3	1026.3	1026.3	1026.3	1026.3	1026.3	1026.3	1026.3
2.5°	1022.5	1024.0	1025.5	1026.2	1026.1	1025.9	1025.8	1025.7
5°	1015.6	1017.4	1019.2	1019.9	1019.5	1019.2	1018.8	1018.4
7.5°	1002.1	1003.2	1004.4	1004.6	1004.1	1003.5	1003.0	1002.4
10°	990.0	990.7	991.4	991.4	990.7	990.0	989.3	988.6
12.5°	974.9	975.3	975.8	975.5	974.5	973.6	972.6	971.6
15°	948.6	948.3	947.9	947.2	945.8	944.6	943.4	942.2
17.5°	916.9	915.8	914.8	913.4	911.6	909.8	907.9	906.1
20°	894.6	893.2	891.8	890.0	887.8	885.4	883.2	880.9
22.5°	870.0	867.9	865.8	863.8	861.9	860.1	858.3	856.4
25°	830.2	827.2	824.3	821.9	820.1	818.4	816.7	814.9
27.5°	789.6	786.0	782.3	779.2	776.7	774.2	771.7	769.2
30°	760.6	756.2	751.8	748.3	745.5	742.7	739.9	737.1
32.5°	730.9	725.9	720.7	716.9	714.3	711.7	708.9	706.3
35°	686.7	680.8	674.9	670.3	667.2	664.0	660.9	657.7
37.5°	639.2	632.7	626.0	621.2	617.9	614.8	611.7	608.5
40°	607.7	600.4	593.0	587.8	584.6	581.5	578.3	575.2
42.5°	576.6	569.2	561.7	556.3	553.0	549.8	546.4	543.2
45°	529.1	520.5	511.9	506.0	502.9	499.8	496.7	493.5
47.5°	481.1	472.2	463.3	457.2	453.7	450.3	446.9	443.3
50°	449.3	440.6	431.8	425.9	422.5	419.2	415.9	412.5
52.5°	417.6	408.7	399.9	393.7	390.2	386.8	383.3	379.9
55°	370.8	361.7	352.6	346.5	343.2	339.8	336.5	333.2
57.5°	325.1	315.9	306.7	300.8	298.3	295.8	293.3	290.7
60°	294.6	285.5	276.4	270.5	267.7	264.9	262.2	259.3
62.5°	264.6	256.2	247.8	242.5	240.2	238.0	235.8	233.6
65°	221.6	214.0	206.5	201.7	199.7	197.5	195.4	193.3
67.5°	182.0	175.5	169.1	164.7	162.4	160.1	157.7	155.4
70°	155.1	149.4	143.5	139.8	138.0	136.3	134.5	132.8
72.5°	131.0	126.0	121.1	117.9	116.2	114.6	113.0	111.4
75°	96.4	92.5	88.5	85.9	84.8	83.8	82.8	81.7
77.5°	68.3	65.9	63.5	62.2	61.9	61.6	61.3	61.0
80°	52.4	51.9	51.3	51.0	50.8	50.6	50.5	50.3
82.5°	40.7	40.3	40.0	39.7	39.5	39.3	39.2	39.0
85°	23.6	23.3	22.9	22.8	22.8	22.8	22.8	22.8
87.5°	13.5	13.6	13.7	13.9	14.1	14.4	14.6	14.8
90°	24.8	26.3	27.6	28.5	28.9	29.4	29.8	30.2
92.5°	24.0	25.4	26.8	27.5	27.6	27.7	27.8	27.9
95°	24.8	26.3	27.6	28.4	28.6	28.8	29.0	29.2
97.5°	26.9	27.1	27.2	27.4	27.6	27.8	28.0	28.3
100°	36.8	32.9	29.1	27.4	27.6	27.8	28.0	28.3
102.5°	131.6	90.5	49.4	28.9	28.9	29.0	29.0	29.1
105°	318.6	320.5	322.6	319.6	311.5	303.5	295.4	287.3
107.5°	394.2	395.2	396.1	397.0	397.9	398.7	399.6	400.4
110°	445.5	446.0	446.4	447.0	447.6	448.3	449.0	449.6





TEST NUMBER: P332916-840

CATALOG NUMBER: S124RDIP-S575D1035U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	495.2	495.1	495.0	495.4	496.2	497.2	498.0	498.8
115°	569.5	570.0	570.4	570.6	570.6	570.6	570.6	570.6
117.5°	644.2	644.1	644.0	644.0	643.9	643.8	643.7	643.6
120°	690.4	690.8	691.4	691.4	690.8	690.4	690.0	689.5
122.5°	736.1	736.3	736.6	736.5	736.1	735.6	735.2	734.7
125°	799.8	800.4	801.1	801.5	801.8	802.0	802.2	802.4
127.5°	863.1	862.9	862.8	862.6	862.5	862.3	862.1	861.9
130°	901.7	901.9	902.1	902.3	902.3	902.3	902.3	902.3
132.5°	939.6	939.9	940.1	940.1	939.9	939.7	939.6	939.4
135°	991.9	992.3	992.8	993.2	993.7	994.1	994.5	995.0
137.5°	1042.0	1042.5	1043.0	1043.1	1043.0	1042.9	1042.7	1042.6
140°	1073.0	1073.7	1074.3	1074.8	1075.0	1075.2	1075.4	1075.7
142.5°	1101.7	1102.2	1102.7	1102.9	1103.0	1103.0	1103.1	1103.1
145°	1142.7	1142.9	1143.1	1143.5	1143.9	1144.3	1144.8	1145.2
147.5°	1178.6	1178.8	1179.0	1179.2	1179.4	1179.6	1179.9	1180.1
150°	1201.6	1201.6	1201.6	1201.7	1202.0	1202.2	1202.4	1202.6
152.5°	1221.7	1222.1	1222.4	1222.5	1222.4	1222.3	1222.1	1222.0
155°	1248.8	1249.7	1250.6	1250.7	1250.1	1249.4	1248.7	1248.1
157.5°	1272.1	1273.3	1274.4	1274.4	1273.3	1272.1	1271.0	1269.8
160°	1287.1	1288.4	1289.7	1289.7	1288.4	1287.1	1285.7	1284.3
162.5°	1299.1	1300.5	1301.8	1301.7	1300.2	1298.7	1297.2	1295.7
165°	1316.2	1318.0	1319.7	1319.6	1317.6	1315.6	1313.5	1311.5
167.5°	1328.6	1330.6	1332.5	1332.4	1330.2	1328.0	1325.6	1323.4
170°	1336.4	1338.1	1339.9	1339.7	1337.5	1335.2	1332.9	1330.7
172.5°	1341.2	1342.9	1344.7	1344.4	1342.0	1339.6	1337.2	1334.7
175°	1346.9	1348.9	1350.9	1350.5	1347.9	1345.1	1342.5	1339.8
177.5°	1349.1	1350.5	1352.0	1351.6	1349.5	1347.4	1345.1	1343.0
180°	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9

(END OF REPORT)