

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332982-830

Luminaire Tested: **S124RDIP-S1020D1205U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332982-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124RDIP-S1020D1205U830-4F0-1E-UDD-F  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1205 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 8465.8 lumens  
Efficiency: N/A  
Efficacy: 129.4 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 65.4  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332982-830

CATALOG NUMBER: S124RDIP-S1020D1205U830-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P332982-830

CATALOG NUMBER: S124RDIP-S1020D1205U830-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	106	106	106	106	98	98	98	98	81	81	81	67	67	67	53	53	53	46					46			
1	97	93	89	86	89	86	82	79	72	69	67	59	57	56	47	46	45	40					40			
2	89	82	76	71	81	75	70	66	63	59	56	52	49	47	42	40	38	34					34			
3	81	72	65	59	74	66	60	55	56	51	47	46	43	40	37	35	33	29					29			
4	74	64	56	50	68	59	52	47	50	45	41	41	38	34	33	31	29	25					25			
5	68	57	49	43	62	53	46	40	45	39	35	37	33	30	30	27	25	22					22			
6	63	51	43	37	58	47	40	35	40	35	31	34	30	26	27	24	22	19					19			
7	58	46	38	33	53	43	36	31	37	31	27	31	26	23	25	22	20	17					17			
8	54	42	34	29	50	39	32	27	33	28	24	28	24	21	23	20	18	15					15			
9	50	38	31	26	46	36	29	24	31	25	22	26	22	19	21	18	16	14					14			
10	47	35	28	23	43	33	26	22	28	23	20	24	20	17	20	17	15	13					13			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	13739	13739	13739
5°	13771	13602	13686
10°	13684	13439	13439
15°	13527	13157	13059
20°	13311	12785	12550
25°	13036	12351	12038
30°	12767	11893	11395
35°	12471	11417	10749
40°	12113	10877	10053
45°	11783	10340	9344
50°	11408	9722	8593
55°	11005	9080	7776
60°	10563	8375	6944
65°	10157	7494	6124
70°	9567	6522	5200
75°	8821	5405	4226
80°	7694	4119	3877
85°	6521	3742	3501



TEST NUMBER: P332982-830

CATALOG NUMBER: S124RDIP-S1020D1205U830-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	159.9	1.9
10°-20°	445.8	5.3
20°-30°	643.8	7.6
30°-40°	729.7	8.6
40°-50°	704.7	8.3
50°-60°	586.0	6.9
60°-70°	404.6	4.8
70°-80°	205.1	2.4
80°-90°	56.8	0.7
90°-100°	50.1	0.6
100°-110°	319.3	3.8
110°-120°	610.8	7.2
120°-130°	775.4	9.2
130°-140°	829.7	9.8
140°-150°	775.8	9.2
150°-160°	625.7	7.4
160°-170°	403.5	4.8
170°-180°	139.1	1.6
0°-30°	1249.5	14.8
0°-40°	1979.2	23.4
0°-60°	3269.8	38.6
0°-90°	3936.4	46.5
90°-120°	980.2	11.6
90°-150°	3361.2	39.7
90°-180°	4529.0	53.5
0°-180°	8465.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1702	1702	1702	1702	1702	
5°	1699	1694	1678	1691	1689	161
15°	1618	1606	1574	1571	1562	456
25°	1464	1438	1387	1365	1351	674
35°	1265	1222	1158	1115	1091	790
45°	1032	982	906	844	818	795
55°	782	728	645	580	552	699
65°	532	474	392	338	321	525
75°	283	234	173	145	136	299
85°	70	46	40	38	38	79
90°	3	15	24	30	33	6
95°	60	25	24	30	32	77
105°	330	336	342	349	312	345
115°	616	619	618	620	620	605
125°	865	869	867	871	872	772
135°	1073	1072	1077	1079	1081	827
145°	1238	1241	1241	1242	1244	773
155°	1357	1358	1355	1359	1356	625
165°	1431	1426	1426	1434	1425	404
175°	1464	1458	1459	1467	1456	139
180°	1464	1464	1464	1464	1464	



TEST NUMBER: P332982-830

CATALOG NUMBER: S124RDIP-S1020D1205U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9
2.5°	1706.1	1705.2	1704.2	1703.4	1702.4	1700.6	1698.1	1695.5	1693.0	1690.5	1693.0
5°	1699.3	1698.2	1697.0	1695.8	1694.7	1692.3	1688.9	1685.5	1682.0	1678.5	1681.4
7.5°	1683.9	1682.7	1681.5	1680.3	1679.0	1676.2	1671.7	1667.2	1662.6	1658.1	1660.0
10°	1669.3	1667.9	1666.4	1665.0	1663.6	1660.2	1655.0	1649.8	1644.5	1639.4	1640.5
12.5°	1650.6	1648.9	1647.2	1645.6	1643.9	1639.9	1633.8	1627.7	1621.6	1615.4	1616.1
15°	1618.5	1615.9	1613.4	1610.7	1608.1	1603.2	1595.9	1588.7	1581.5	1574.2	1573.7
17.5°	1579.7	1575.9	1572.2	1568.4	1564.6	1558.4	1549.7	1541.1	1532.4	1523.6	1522.0
20°	1549.4	1545.7	1541.9	1538.1	1534.4	1527.6	1517.8	1507.9	1498.1	1488.2	1485.9
22.5°	1516.1	1511.8	1507.6	1503.4	1499.2	1491.8	1481.3	1470.7	1460.2	1449.6	1446.1
25°	1463.5	1458.2	1453.0	1447.8	1442.6	1434.1	1422.2	1410.3	1398.5	1386.6	1381.7
27.5°	1408.2	1401.7	1395.2	1388.6	1382.1	1372.4	1359.7	1347.1	1334.4	1321.6	1315.6
30°	1369.6	1362.4	1355.2	1347.9	1340.7	1330.2	1316.6	1303.0	1289.4	1275.8	1268.6
32.5°	1329.0	1320.8	1312.6	1304.5	1296.3	1285.2	1271.1	1257.1	1242.9	1228.9	1220.5
35°	1265.4	1256.1	1246.8	1237.6	1228.3	1216.4	1201.9	1187.5	1173.0	1158.5	1148.7
37.5°	1197.3	1187.8	1178.3	1168.7	1159.1	1146.3	1130.3	1114.3	1098.2	1082.1	1071.1
40°	1149.4	1139.8	1130.3	1120.7	1111.2	1098.2	1081.7	1065.1	1048.6	1032.1	1019.9
42.5°	1103.5	1093.5	1083.5	1073.5	1063.5	1049.8	1032.6	1015.4	998.2	981.0	968.7
45°	1032.1	1021.4	1010.7	999.9	989.2	975.2	957.8	940.5	923.0	905.7	891.6
47.5°	958.4	947.3	936.2	925.2	914.1	899.6	881.5	863.4	845.3	827.3	812.6
50°	908.3	897.0	885.7	874.4	863.1	848.2	829.7	811.2	792.6	774.1	759.6
52.5°	857.2	846.1	835.1	824.1	812.9	798.0	778.9	760.0	740.9	722.0	707.3
55°	781.9	770.3	758.7	747.2	735.6	720.4	701.5	682.7	663.9	645.1	630.0
57.5°	707.4	695.3	683.2	671.2	659.2	643.9	625.4	606.8	588.2	569.8	554.5
60°	654.2	642.6	631.0	619.4	607.8	592.8	574.3	555.7	537.2	518.7	503.6
62.5°	606.2	594.2	582.1	570.0	558.1	542.5	523.5	504.5	485.5	466.6	452.6
65°	531.7	519.2	506.8	494.4	481.9	466.4	447.9	429.3	410.8	392.3	379.8
67.5°	454.3	442.3	430.5	418.5	406.5	392.0	374.8	357.6	340.4	323.2	312.5
70°	405.3	393.1	381.0	368.8	356.7	342.3	325.8	309.2	292.8	276.3	266.7
72.5°	353.2	342.1	331.1	320.2	309.2	295.9	280.3	264.7	249.1	233.6	225.4
75°	282.8	272.1	261.4	250.6	240.0	227.7	214.1	200.6	186.9	173.3	166.6
77.5°	211.4	202.3	193.2	184.1	175.0	164.9	153.9	143.0	132.0	120.9	117.1
80°	165.5	157.1	148.7	140.3	132.0	123.4	114.7	106.0	97.3	88.6	87.8
82.5°	125.9	118.2	110.5	102.7	95.1	88.7	83.8	78.8	73.8	68.8	68.1
85°	70.4	64.6	58.8	53.0	47.2	43.8	43.0	42.1	41.3	40.4	39.8
87.5°	24.6	23.3	22.0	20.6	19.3	18.8	18.9	19.1	19.2	19.4	19.5
90°	3.3	5.9	8.7	11.3	13.9	16.3	18.3	20.2	22.1	24.1	25.5
92.5°	13.8	13.9	14.1	14.2	14.4	15.5	17.3	19.3	21.3	23.2	24.7
95°	60.2	51.9	43.6	35.4	27.1	23.1	23.4	23.6	23.8	24.1	25.5
97.5°	127.9	133.1	138.3	143.4	148.5	137.5	110.4	83.2	56.1	28.9	29.0
100°	179.6	184.0	188.4	192.7	197.2	182.6	148.9	115.4	81.8	48.2	44.0
102.5°	237.4	240.6	243.8	247.0	250.2	249.7	245.3	240.9	236.6	232.1	187.6
105°	329.6	331.1	332.5	334.0	335.5	336.9	338.1	339.2	340.4	341.7	343.9
107.5°	415.3	416.0	416.8	417.5	418.2	419.4	421.0	422.7	424.3	426.0	427.1
110°	473.2	473.8	474.6	475.3	476.1	477.1	478.6	480.0	481.5	483.0	483.4



TEST NUMBER: P332982-830

CATALOG NUMBER: S124RDIP-S1020D1205U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	529.2	530.6	531.8	533.1	534.4	535.5	536.1	536.8	537.5	538.2	538.1
115°	615.5	616.2	617.0	617.6	618.4	618.7	618.4	618.2	617.9	617.6	618.2
117.5°	693.2	694.2	695.2	696.2	697.1	697.9	698.4	699.0	699.6	700.0	699.9
120°	745.8	746.8	747.8	748.8	749.7	750.1	749.9	749.6	749.3	749.1	749.6
122.5°	794.8	795.5	796.1	796.6	797.2	797.7	798.1	798.3	798.7	799.1	799.4
125°	865.2	866.2	867.1	868.1	869.1	869.3	868.8	868.4	867.9	867.4	868.1
127.5°	931.8	932.0	932.3	932.6	932.7	933.4	934.5	935.7	936.8	937.9	937.7
130°	974.7	975.0	975.2	975.4	975.7	976.2	976.9	977.6	978.4	979.1	979.3
132.5°	1014.2	1014.6	1015.0	1015.5	1015.9	1016.6	1017.5	1018.4	1019.4	1020.3	1020.5
135°	1073.3	1073.1	1072.8	1072.5	1072.3	1072.7	1073.7	1074.6	1075.6	1076.6	1077.0
137.5°	1125.7	1125.8	1125.9	1126.0	1126.1	1126.6	1127.7	1128.8	1129.8	1130.9	1131.4
140°	1159.8	1160.3	1160.7	1161.3	1161.8	1162.2	1162.7	1163.2	1163.7	1164.2	1164.9
142.5°	1190.4	1191.4	1192.2	1193.1	1194.0	1194.6	1194.9	1195.1	1195.4	1195.7	1196.3
145°	1237.6	1238.3	1239.1	1239.7	1240.5	1240.9	1240.9	1240.9	1240.9	1240.9	1241.1
147.5°	1275.0	1276.4	1277.7	1279.1	1280.4	1281.0	1280.8	1280.5	1280.3	1280.1	1280.3
150°	1302.2	1303.2	1304.1	1305.1	1306.1	1306.5	1306.2	1306.0	1305.7	1305.4	1305.4
152.5°	1324.9	1325.8	1326.5	1327.3	1328.0	1328.2	1327.9	1327.4	1326.9	1326.5	1326.9
155°	1357.0	1357.2	1357.4	1357.6	1357.9	1357.6	1357.0	1356.2	1355.5	1354.7	1355.8
157.5°	1383.8	1383.7	1383.6	1383.5	1383.3	1382.8	1382.0	1381.2	1380.4	1379.5	1380.7
160°	1399.7	1398.9	1398.2	1397.5	1396.8	1396.3	1396.0	1395.7	1395.5	1395.2	1396.8
162.5°	1413.6	1412.8	1411.8	1410.9	1409.9	1409.4	1409.1	1408.9	1408.6	1408.4	1409.9
165°	1431.4	1430.2	1429.0	1427.8	1426.5	1426.0	1426.0	1426.0	1426.0	1426.0	1427.9
167.5°	1445.4	1444.2	1442.9	1441.6	1440.4	1439.6	1439.5	1439.4	1439.3	1439.1	1441.2
170°	1453.3	1451.9	1450.4	1449.0	1447.5	1446.9	1447.1	1447.4	1447.6	1447.8	1449.8
172.5°	1458.6	1457.1	1455.7	1454.2	1452.7	1452.1	1452.4	1452.6	1452.8	1453.1	1455.0
175°	1464.2	1462.8	1461.3	1459.9	1458.4	1457.8	1458.0	1458.3	1458.6	1458.8	1460.9
177.5°	1466.9	1465.6	1464.1	1462.8	1461.4	1460.9	1461.3	1461.7	1462.2	1462.5	1464.1
180°	1464.2	1464.2	1464.2	1464.2	1464.2	1464.2	1464.2	1464.2	1464.2	1464.2	1464.2



TEST NUMBER: P332982-830

CATALOG NUMBER: S124RDIP-S1020D1205U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9
2.5°	1695.5	1698.1	1700.6	1701.9	1701.6	1701.4	1701.1	1700.9
5°	1684.2	1687.2	1690.1	1691.2	1690.6	1690.1	1689.5	1688.9
7.5°	1661.9	1663.7	1665.6	1666.0	1665.1	1664.2	1663.2	1662.3
10°	1641.7	1642.9	1644.0	1644.0	1642.9	1641.7	1640.5	1639.4
12.5°	1616.7	1617.5	1618.2	1617.7	1616.1	1614.5	1612.9	1611.3
15°	1573.1	1572.4	1571.9	1570.6	1568.6	1566.5	1564.5	1562.5
17.5°	1520.4	1518.8	1517.2	1514.9	1511.7	1508.7	1505.6	1502.5
20°	1483.6	1481.3	1478.9	1475.9	1472.2	1468.4	1464.6	1460.8
22.5°	1442.7	1439.2	1435.8	1432.5	1429.4	1426.3	1423.2	1420.2
25°	1376.7	1371.8	1366.9	1362.9	1360.1	1357.2	1354.2	1351.4
27.5°	1309.5	1303.4	1297.3	1292.2	1288.1	1283.8	1279.7	1275.5
30°	1261.3	1254.1	1246.8	1240.9	1236.2	1231.6	1227.0	1222.4
32.5°	1212.1	1203.7	1195.3	1188.9	1184.5	1180.1	1175.7	1171.3
35°	1138.8	1129.0	1119.1	1111.6	1106.4	1101.2	1096.0	1090.7
37.5°	1060.2	1049.1	1038.1	1030.0	1024.8	1019.5	1014.4	1009.2
40°	1007.8	995.6	983.4	974.8	969.6	964.3	959.1	953.9
42.5°	956.2	943.9	931.4	922.6	917.1	911.6	906.2	900.8
45°	877.3	863.1	848.9	839.2	834.1	828.8	823.6	818.4
47.5°	797.9	783.2	768.4	758.2	752.4	746.7	740.9	735.3
50°	745.1	730.7	716.1	706.2	700.7	695.1	689.7	684.2
52.5°	692.5	677.8	663.1	652.9	647.1	641.4	635.7	630.0
55°	614.9	599.9	584.8	574.6	569.0	563.5	558.1	552.5
57.5°	539.1	523.9	508.6	498.9	494.6	490.5	486.4	482.2
60°	488.5	473.4	458.5	448.6	443.9	439.3	434.7	430.1
62.5°	438.8	424.8	410.9	402.1	398.4	394.7	391.0	387.3
65°	367.3	354.9	342.4	334.5	331.0	327.5	324.0	320.6
67.5°	301.7	291.1	280.3	273.1	269.2	265.4	261.6	257.8
70°	257.1	247.6	238.1	231.8	228.9	226.0	223.1	220.3
72.5°	217.2	209.1	200.9	195.5	192.7	190.1	187.5	184.8
75°	160.0	153.4	146.7	142.5	140.7	139.0	137.2	135.5
77.5°	113.2	109.3	105.4	103.2	102.6	102.2	101.6	101.1
80°	86.9	86.1	85.1	84.5	84.3	84.0	83.7	83.4
82.5°	67.5	66.9	66.3	65.8	65.5	65.2	64.9	64.7
85°	39.2	38.6	38.1	37.8	37.8	37.8	37.8	37.8
87.5°	19.5	19.6	19.7	19.9	20.2	20.5	20.8	21.2
90°	27.1	28.5	30.0	30.9	31.4	31.9	32.3	32.9
92.5°	26.1	27.6	29.0	29.9	30.0	30.1	30.2	30.3
95°	27.1	28.5	30.0	30.8	31.0	31.3	31.5	31.8
97.5°	29.2	29.3	29.5	29.7	30.0	30.2	30.4	30.6
100°	39.9	35.8	31.7	29.7	30.0	30.2	30.4	30.6
102.5°	142.9	98.3	53.6	31.4	31.4	31.5	31.5	31.6
105°	346.1	348.3	350.4	347.1	338.4	329.6	320.9	312.2
107.5°	428.2	429.2	430.3	431.3	432.3	433.2	434.0	435.0
110°	484.0	484.5	484.9	485.5	486.3	487.0	487.8	488.4





TEST NUMBER: P332982-830

CATALOG NUMBER: S124RDIP-S1020D1205U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	538.0	537.9	537.8	538.2	539.1	540.1	541.0	541.9
115°	618.7	619.2	619.6	619.9	619.9	619.9	619.9	619.9
117.5°	699.8	699.7	699.6	699.6	699.5	699.4	699.3	699.2
120°	750.1	750.5	751.0	751.0	750.5	750.1	749.6	749.1
122.5°	799.7	799.9	800.2	800.1	799.7	799.2	798.6	798.1
125°	868.8	869.6	870.3	870.8	871.0	871.3	871.6	871.8
127.5°	937.6	937.5	937.4	937.2	937.0	936.8	936.6	936.4
130°	979.6	979.9	980.1	980.1	980.1	980.1	980.1	980.1
132.5°	1020.8	1021.1	1021.2	1021.2	1021.1	1020.9	1020.7	1020.5
135°	1077.5	1078.0	1078.6	1079.0	1079.5	1080.0	1080.4	1080.9
137.5°	1132.0	1132.5	1133.0	1133.2	1133.1	1132.9	1132.7	1132.7
140°	1165.6	1166.4	1167.2	1167.6	1167.8	1168.1	1168.3	1168.6
142.5°	1196.8	1197.3	1197.9	1198.2	1198.3	1198.3	1198.3	1198.3
145°	1241.3	1241.6	1241.8	1242.2	1242.6	1243.1	1243.7	1244.2
147.5°	1280.4	1280.6	1280.8	1281.0	1281.3	1281.6	1281.8	1282.0
150°	1305.4	1305.4	1305.4	1305.6	1305.8	1306.1	1306.4	1306.6
152.5°	1327.3	1327.7	1328.0	1328.1	1328.0	1327.9	1327.8	1327.6
155°	1356.7	1357.6	1358.7	1358.8	1358.0	1357.3	1356.6	1355.8
157.5°	1382.1	1383.3	1384.6	1384.6	1383.3	1382.1	1380.7	1379.5
160°	1398.2	1399.7	1401.1	1401.1	1399.7	1398.2	1396.8	1395.2
162.5°	1411.4	1412.8	1414.3	1414.2	1412.5	1410.9	1409.2	1407.5
165°	1429.8	1431.8	1433.7	1433.6	1431.4	1429.2	1427.0	1424.8
167.5°	1443.4	1445.5	1447.7	1447.5	1445.1	1442.7	1440.2	1437.8
170°	1451.7	1453.7	1455.7	1455.4	1452.9	1450.5	1448.1	1445.7
172.5°	1457.0	1459.0	1460.8	1460.6	1457.9	1455.3	1452.6	1450.0
175°	1463.2	1465.4	1467.5	1467.2	1464.2	1461.3	1458.4	1455.5
177.5°	1465.7	1467.2	1468.8	1468.4	1466.0	1463.7	1461.3	1459.1
180°	1464.2	1464.2	1464.2	1464.2	1464.2	1464.2	1464.2	1464.2

(END OF REPORT)