

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332983-830

Luminaire Tested: **S124RDIP-S1020D1205U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332983-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIP-S1020D1205U830-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1205 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7864.7 lumens
Efficiency: N/A
Efficacy: 120.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 65.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332983-830

CATALOG NUMBER: S124RDIP-S1020D1205U830-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332983-830

CATALOG NUMBER: S124RDIP-S1020D1205U830-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	50				
1	98	94	90	87	90	87	84	81	73	71	69	61	60	58	50	49	48	43				
2	90	82	76	71	82	76	71	67	65	61	58	54	51	49	44	42	41	36				
3	82	73	65	60	75	67	61	56	57	53	49	48	45	42	40	37	35	31				
4	75	64	57	51	69	60	53	48	51	46	42	43	39	36	35	33	30	27				
5	69	57	49	43	63	53	46	41	46	40	36	39	35	31	32	29	27	23				
6	64	52	44	38	58	48	41	36	41	36	32	35	31	28	29	26	24	21				
7	59	47	39	33	54	43	36	31	38	32	28	32	28	24	27	23	21	18				
8	55	42	35	29	50	40	33	28	34	29	25	29	25	22	25	21	19	17				
9	51	39	31	26	47	36	30	25	31	26	22	27	23	20	23	19	17	15				
10	48	36	28	24	44	33	27	22	29	24	20	25	21	18	21	18	16	14				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13739	13739	13739
5°	13771	13602	13686
10°	13684	13439	13439
15°	13527	13157	13059
20°	13311	12785	12550
25°	13036	12351	12038
30°	12767	11893	11395
35°	12471	11417	10749
40°	12113	10877	10053
45°	11783	10340	9344
50°	11408	9722	8593
55°	11005	9080	7776
60°	10563	8375	6944
65°	10157	7494	6124
70°	9567	6522	5200
75°	8821	5405	4226
80°	7694	4119	3877
85°	6521	3742	3501



TEST NUMBER: P332983-830

CATALOG NUMBER: S124RDIP-S1020D1205U830-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	159.9	2.0
10°-20°	445.8	5.7
20°-30°	643.8	8.2
30°-40°	729.7	9.3
40°-50°	704.7	9.0
50°-60°	586.0	7.5
60°-70°	404.6	5.1
70°-80°	205.1	2.6
80°-90°	56.8	0.7
90°-100°	93.4	1.2
100°-110°	276.7	3.5
110°-120°	469.6	6.0
120°-130°	619.1	7.9
130°-140°	695.3	8.8
140°-150°	683.3	8.7
150°-160°	574.7	7.3
160°-170°	382.4	4.9
170°-180°	133.9	1.7
0°-30°	1249.5	15.9
0°-40°	1979.2	25.2
0°-60°	3269.8	41.6
0°-90°	3936.4	50.1
90°-120°	839.6	10.7
90°-150°	2837.4	36.1
90°-180°	3928.0	49.9
0°-180°	7864.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1702	1702	1702	1702	1702	
5°	1699	1694	1678	1691	1689	161
15°	1618	1606	1574	1571	1562	456
25°	1464	1438	1387	1365	1351	674
35°	1265	1222	1158	1115	1091	790
45°	1032	982	906	844	818	795
55°	782	728	645	580	552	699
65°	532	474	392	338	321	525
75°	283	234	173	145	136	299
85°	70	46	40	38	38	79
90°	3	15	24	30	33	7
95°	66	75	83	86	86	73
105°	255	256	261	264	267	271
115°	477	477	475	474	473	471
125°	695	695	694	692	690	620
135°	897	903	903	901	898	694
145°	1090	1094	1095	1094	1091	682
155°	1248	1248	1247	1251	1247	574
165°	1359	1356	1354	1359	1356	383
175°	1414	1408	1407	1414	1407	134
180°	1416	1416	1416	1416	1416	



TEST NUMBER: P332983-830

CATALOG NUMBER: S124RDIP-S1020D1205U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9
2.5°	1706.1	1705.2	1704.2	1703.4	1702.4	1700.6	1698.1	1695.5	1693.0	1690.5	1693.0
5°	1699.3	1698.2	1697.0	1695.8	1694.7	1692.3	1688.9	1685.5	1682.0	1678.5	1681.4
7.5°	1683.9	1682.7	1681.5	1680.3	1679.0	1676.2	1671.7	1667.2	1662.6	1658.1	1660.0
10°	1669.3	1667.9	1666.4	1665.0	1663.6	1660.2	1655.0	1649.8	1644.5	1639.4	1640.5
12.5°	1650.6	1648.9	1647.2	1645.6	1643.9	1639.9	1633.8	1627.7	1621.6	1615.4	1616.1
15°	1618.5	1615.9	1613.4	1610.7	1608.1	1603.2	1595.9	1588.7	1581.5	1574.2	1573.7
17.5°	1579.7	1575.9	1572.2	1568.4	1564.6	1558.4	1549.7	1541.1	1532.4	1523.6	1522.0
20°	1549.4	1545.7	1541.9	1538.1	1534.4	1527.6	1517.8	1507.9	1498.1	1488.2	1485.9
22.5°	1516.1	1511.8	1507.6	1503.4	1499.2	1491.8	1481.3	1470.7	1460.2	1449.6	1446.1
25°	1463.5	1458.2	1453.0	1447.8	1442.6	1434.1	1422.2	1410.3	1398.5	1386.6	1381.7
27.5°	1408.2	1401.7	1395.2	1388.6	1382.1	1372.4	1359.7	1347.1	1334.4	1321.6	1315.6
30°	1369.6	1362.4	1355.2	1347.9	1340.7	1330.2	1316.6	1303.0	1289.4	1275.8	1268.6
32.5°	1329.0	1320.8	1312.6	1304.5	1296.3	1285.2	1271.1	1257.1	1242.9	1228.9	1220.5
35°	1265.4	1256.1	1246.8	1237.6	1228.3	1216.4	1201.9	1187.5	1173.0	1158.5	1148.7
37.5°	1197.3	1187.8	1178.3	1168.7	1159.1	1146.3	1130.3	1114.3	1098.2	1082.1	1071.1
40°	1149.4	1139.8	1130.3	1120.7	1111.2	1098.2	1081.7	1065.1	1048.6	1032.1	1019.9
42.5°	1103.5	1093.5	1083.5	1073.5	1063.5	1049.8	1032.6	1015.4	998.2	981.0	968.7
45°	1032.1	1021.4	1010.7	999.9	989.2	975.2	957.8	940.5	923.0	905.7	891.6
47.5°	958.4	947.3	936.2	925.2	914.1	899.6	881.5	863.4	845.3	827.3	812.6
50°	908.3	897.0	885.7	874.4	863.1	848.2	829.7	811.2	792.6	774.1	759.6
52.5°	857.2	846.1	835.1	824.1	812.9	798.0	778.9	760.0	740.9	722.0	707.3
55°	781.9	770.3	758.7	747.2	735.6	720.4	701.5	682.7	663.9	645.1	630.0
57.5°	707.4	695.3	683.2	671.2	659.2	643.9	625.4	606.8	588.2	569.8	554.5
60°	654.2	642.6	631.0	619.4	607.8	592.8	574.3	555.7	537.2	518.7	503.6
62.5°	606.2	594.2	582.1	570.0	558.1	542.5	523.5	504.5	485.5	466.6	452.6
65°	531.7	519.2	506.8	494.4	481.9	466.4	447.9	429.3	410.8	392.3	379.8
67.5°	454.3	442.3	430.5	418.5	406.5	392.0	374.8	357.6	340.4	323.2	312.5
70°	405.3	393.1	381.0	368.8	356.7	342.3	325.8	309.2	292.8	276.3	266.7
72.5°	353.2	342.1	331.1	320.2	309.2	295.9	280.3	264.7	249.1	233.6	225.4
75°	282.8	272.1	261.4	250.6	240.0	227.7	214.1	200.6	186.9	173.3	166.6
77.5°	211.4	202.3	193.2	184.1	175.0	164.9	153.9	143.0	132.0	120.9	117.1
80°	165.5	157.1	148.7	140.3	132.0	123.4	114.7	106.0	97.3	88.6	87.8
82.5°	125.9	118.2	110.5	102.7	95.1	88.7	83.8	78.8	73.8	68.8	68.1
85°	70.4	64.6	58.8	53.0	47.2	43.8	43.0	42.1	41.3	40.4	39.8
87.5°	24.6	23.3	22.0	20.6	19.3	18.8	18.9	19.1	19.2	19.4	19.5
90°	3.3	5.9	8.7	11.3	13.9	16.3	18.3	20.2	22.1	24.1	25.5
92.5°	23.5	26.5	29.6	32.6	35.7	37.9	39.3	40.6	42.0	43.4	44.2
95°	65.7	67.9	70.1	72.3	74.5	76.4	78.1	79.8	81.5	83.2	84.0
97.5°	114.8	116.5	118.3	120.0	121.8	123.7	125.6	127.6	129.6	131.6	132.5
100°	153.4	154.3	155.2	156.2	157.2	158.8	161.0	163.2	165.3	167.6	168.1
102.5°	193.6	194.0	194.4	194.7	195.2	196.3	198.3	200.4	202.4	204.3	205.0
105°	255.1	255.4	255.6	255.9	256.1	256.7	257.7	258.6	259.7	260.6	261.4
107.5°	319.7	320.1	320.4	320.7	320.9	321.1	321.3	321.4	321.6	321.7	322.4
110°	363.5	364.0	364.5	365.0	365.5	365.6	365.4	365.1	364.9	364.7	364.2



TEST NUMBER: P332983-830

CATALOG NUMBER: S124RDIP-S1020D1205U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	409.1	409.3	409.3	409.4	409.5	409.3	408.9	408.5	408.0	407.6	407.5
115°	477.4	477.4	477.4	477.4	477.4	477.2	476.7	476.3	475.7	475.2	475.0
117.5°	541.9	542.1	542.2	542.4	542.6	542.5	542.2	541.9	541.5	541.2	540.4
120°	584.8	585.7	586.7	587.7	588.6	588.8	588.1	587.3	586.5	585.9	584.7
122.5°	629.4	629.8	630.2	630.6	631.0	631.0	630.7	630.4	630.0	629.6	628.9
125°	695.3	695.3	695.3	695.3	695.3	695.2	695.0	694.7	694.5	694.3	693.8
127.5°	755.2	755.9	756.6	757.3	758.1	758.3	757.8	757.4	757.1	756.7	756.2
130°	797.2	798.0	798.6	799.4	800.1	800.5	800.5	800.5	800.5	800.5	800.0
132.5°	840.1	840.7	841.2	841.7	842.3	842.4	842.3	842.1	841.9	841.7	841.1
135°	896.8	898.3	899.8	901.3	902.7	903.4	903.4	903.4	903.4	903.4	903.0
137.5°	958.6	959.3	960.0	960.6	961.3	961.9	962.2	962.6	963.0	963.4	962.8
140°	999.8	1000.2	1000.8	1001.3	1001.7	1001.9	1001.9	1001.9	1001.9	1001.9	1001.7
142.5°	1037.5	1037.9	1038.4	1038.9	1039.4	1039.5	1039.3	1039.2	1039.0	1038.8	1038.7
145°	1089.6	1090.5	1091.6	1092.5	1093.4	1094.1	1094.3	1094.6	1094.8	1095.0	1094.8
147.5°	1141.2	1142.5	1143.6	1144.7	1145.9	1146.4	1146.2	1146.0	1145.8	1145.7	1145.5
150°	1172.8	1173.7	1174.8	1175.7	1176.7	1177.1	1177.1	1177.1	1177.1	1177.1	1177.1
152.5°	1202.6	1203.2	1203.7	1204.3	1204.9	1205.3	1205.5	1205.7	1205.9	1206.1	1206.6
155°	1248.3	1248.3	1248.3	1248.3	1248.3	1248.2	1248.0	1247.7	1247.5	1247.3	1248.2
157.5°	1286.9	1286.5	1286.0	1285.6	1285.2	1284.9	1284.9	1284.8	1284.8	1284.7	1285.4
160°	1309.7	1309.5	1309.2	1308.9	1308.7	1308.4	1308.2	1308.0	1307.7	1307.5	1308.2
162.5°	1330.7	1330.0	1329.5	1328.8	1328.1	1327.8	1327.5	1327.3	1327.0	1326.7	1328.0
165°	1359.0	1358.2	1357.4	1356.8	1356.0	1355.4	1354.9	1354.4	1354.0	1353.5	1354.9
167.5°	1380.6	1379.6	1378.6	1377.5	1376.6	1376.0	1376.1	1376.1	1376.2	1376.2	1377.7
170°	1392.9	1391.7	1390.4	1389.2	1388.0	1387.5	1387.8	1388.0	1388.3	1388.6	1390.0
172.5°	1401.7	1400.6	1399.6	1398.5	1397.6	1397.0	1397.1	1397.2	1397.2	1397.3	1398.9
175°	1413.7	1412.5	1411.3	1410.0	1408.8	1408.1	1407.9	1407.6	1407.4	1407.1	1408.8
177.5°	1417.7	1416.6	1415.7	1414.8	1413.7	1413.2	1413.2	1413.2	1413.2	1413.2	1414.7
180°	1415.9	1415.9	1415.9	1415.9	1415.9	1415.9	1415.9	1415.9	1415.9	1415.9	1415.9



TEST NUMBER: P332983-830

CATALOG NUMBER: S124RDIP-S1020D1205U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9
2.5°	1695.5	1698.1	1700.6	1701.9	1701.6	1701.4	1701.1	1700.9
5°	1684.2	1687.2	1690.1	1691.2	1690.6	1690.1	1689.5	1688.9
7.5°	1661.9	1663.7	1665.6	1666.0	1665.1	1664.2	1663.2	1662.3
10°	1641.7	1642.9	1644.0	1644.0	1642.9	1641.7	1640.5	1639.4
12.5°	1616.7	1617.5	1618.2	1617.7	1616.1	1614.5	1612.9	1611.3
15°	1573.1	1572.4	1571.9	1570.6	1568.6	1566.5	1564.5	1562.5
17.5°	1520.4	1518.8	1517.2	1514.9	1511.7	1508.7	1505.6	1502.5
20°	1483.6	1481.3	1478.9	1475.9	1472.2	1468.4	1464.6	1460.8
22.5°	1442.7	1439.2	1435.8	1432.5	1429.4	1426.3	1423.2	1420.2
25°	1376.7	1371.8	1366.9	1362.9	1360.1	1357.2	1354.2	1351.4
27.5°	1309.5	1303.4	1297.3	1292.2	1288.1	1283.8	1279.7	1275.5
30°	1261.3	1254.1	1246.8	1240.9	1236.2	1231.6	1227.0	1222.4
32.5°	1212.1	1203.7	1195.3	1188.9	1184.5	1180.1	1175.7	1171.3
35°	1138.8	1129.0	1119.1	1111.6	1106.4	1101.2	1096.0	1090.7
37.5°	1060.2	1049.1	1038.1	1030.0	1024.8	1019.5	1014.4	1009.2
40°	1007.8	995.6	983.4	974.8	969.6	964.3	959.1	953.9
42.5°	956.2	943.9	931.4	922.6	917.1	911.6	906.2	900.8
45°	877.3	863.1	848.9	839.2	834.1	828.8	823.6	818.4
47.5°	797.9	783.2	768.4	758.2	752.4	746.7	740.9	735.3
50°	745.1	730.7	716.1	706.2	700.7	695.1	689.7	684.2
52.5°	692.5	677.8	663.1	652.9	647.1	641.4	635.7	630.0
55°	614.9	599.9	584.8	574.6	569.0	563.5	558.1	552.5
57.5°	539.1	523.9	508.6	498.9	494.6	490.5	486.4	482.2
60°	488.5	473.4	458.5	448.6	443.9	439.3	434.7	430.1
62.5°	438.8	424.8	410.9	402.1	398.4	394.7	391.0	387.3
65°	367.3	354.9	342.4	334.5	331.0	327.5	324.0	320.6
67.5°	301.7	291.1	280.3	273.1	269.2	265.4	261.6	257.8
70°	257.1	247.6	238.1	231.8	228.9	226.0	223.1	220.3
72.5°	217.2	209.1	200.9	195.5	192.7	190.1	187.5	184.8
75°	160.0	153.4	146.7	142.5	140.7	139.0	137.2	135.5
77.5°	113.2	109.3	105.4	103.2	102.6	102.2	101.6	101.1
80°	86.9	86.1	85.1	84.5	84.3	84.0	83.7	83.4
82.5°	67.5	66.9	66.3	65.8	65.5	65.2	64.9	64.7
85°	39.2	38.6	38.1	37.8	37.8	37.8	37.8	37.8
87.5°	19.5	19.6	19.7	19.9	20.2	20.5	20.8	21.2
90°	27.1	28.5	30.0	30.9	31.4	31.9	32.3	32.9
92.5°	45.1	46.0	46.8	47.4	47.8	48.1	48.4	48.6
95°	84.6	85.4	86.1	86.5	86.5	86.5	86.5	86.5
97.5°	133.4	134.2	135.2	135.5	135.5	135.5	135.5	135.5
100°	168.5	169.0	169.5	169.8	169.8	169.8	169.8	169.8
102.5°	205.7	206.4	207.1	207.5	207.7	207.9	208.1	208.3
105°	262.1	262.8	263.5	264.3	265.0	265.7	266.5	267.2
107.5°	323.1	323.8	324.4	324.8	324.7	324.7	324.6	324.6
110°	363.6	363.2	362.7	362.8	363.5	364.3	365.0	365.7



TEST NUMBER: P332983-830

CATALOG NUMBER: S124RDIP-S1020D1205U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	407.4	407.3	407.2	407.2	407.4	407.5	407.6	407.8
115°	474.8	474.5	474.3	474.0	473.8	473.5	473.3	473.1
117.5°	539.5	538.7	537.8	537.2	536.7	536.2	535.7	535.3
120°	583.4	582.2	581.0	580.6	581.1	581.5	582.1	582.6
122.5°	628.0	627.2	626.3	625.5	624.6	623.8	622.8	622.0
125°	693.2	692.8	692.3	691.8	691.4	690.9	690.3	689.8
127.5°	755.7	755.3	754.7	754.3	753.9	753.5	753.1	752.7
130°	799.5	799.0	798.5	797.8	796.8	795.9	794.8	793.9
132.5°	840.7	840.2	839.7	839.2	838.9	838.5	838.1	837.7
135°	902.5	901.9	901.4	900.9	900.1	899.4	898.6	898.0
137.5°	962.1	961.5	960.9	960.6	960.8	960.9	961.1	961.2
140°	1001.5	1001.3	1001.0	1000.8	1000.5	1000.2	1000.0	999.8
142.5°	1038.7	1038.6	1038.6	1038.5	1038.5	1038.4	1038.4	1038.3
145°	1094.6	1094.3	1094.1	1093.5	1092.9	1092.1	1091.4	1090.7
147.5°	1145.3	1145.1	1144.8	1144.6	1144.4	1144.2	1143.9	1143.7
150°	1177.1	1177.1	1177.1	1177.0	1176.8	1176.6	1176.3	1176.1
152.5°	1207.2	1207.9	1208.4	1208.4	1207.8	1207.1	1206.5	1205.9
155°	1249.2	1250.2	1251.1	1251.1	1250.2	1249.2	1248.2	1247.3
157.5°	1286.2	1286.9	1287.6	1287.6	1286.8	1285.9	1285.1	1284.3
160°	1308.9	1309.7	1310.4	1310.1	1308.9	1307.7	1306.6	1305.3
162.5°	1329.4	1330.7	1332.0	1332.1	1330.9	1329.6	1328.4	1327.2
165°	1356.4	1357.8	1359.3	1359.5	1358.6	1357.6	1356.6	1355.7
167.5°	1379.1	1380.6	1382.1	1382.1	1380.5	1379.0	1377.5	1376.0
170°	1391.5	1392.9	1394.4	1394.2	1392.5	1390.8	1389.1	1387.4
172.5°	1400.6	1402.2	1403.9	1403.9	1402.1	1400.4	1398.7	1397.0
175°	1410.5	1412.2	1413.9	1413.9	1412.2	1410.5	1408.8	1407.1
177.5°	1416.0	1417.4	1418.7	1418.6	1417.0	1415.5	1413.9	1412.4
180°	1415.9	1415.9	1415.9	1415.9	1415.9	1415.9	1415.9	1415.9

(END OF REPORT)