

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333002-830

Luminaire Tested: **S124RDIP-S1195D810U830-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333002-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIP-S1195D810U830-4F0-1E-UDD-F4
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 810 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7271.7 lumens
Efficiency: N/A
Efficacy: 119.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 60.7
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333002-830

CATALOG NUMBER: S124RDIP-S1195D810U830-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P333002-830

CATALOG NUMBER: S124RDIP-S1195D810U830-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	68	68	68	62
1	101	97	93	89	94	91	87	84	80	77	75	70	68	66	60	59	58	53
2	92	85	79	74	86	80	74	70	70	66	63	62	58	56	53	51	49	45
3	84	75	68	62	79	70	64	59	62	57	53	55	51	48	48	45	42	39
4	77	66	59	53	72	63	56	50	56	50	46	49	45	41	43	39	37	33
5	71	59	51	45	66	56	49	43	50	44	40	44	39	36	39	35	32	29
6	66	54	45	40	61	51	43	38	45	39	35	40	35	32	35	31	28	26
7	61	48	40	35	57	46	39	33	41	35	31	37	32	28	32	28	25	23
8	57	44	36	31	53	42	35	30	38	32	27	34	29	25	30	26	23	21
9	53	40	33	28	50	38	31	27	35	29	25	31	26	23	27	24	21	19
10	49	37	30	25	46	35	29	24	32	26	22	29	24	21	26	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	15868	15868	15868
5°	15904	15709	15807
10°	15805	15521	15521
15°	15623	15195	15082
20°	15374	14766	14495
25°	15055	14264	13903
30°	14746	13736	13160
35°	14402	13186	12415
40°	13990	12562	11610
45°	13609	11942	10791
50°	13175	11228	9923
55°	12711	10486	8981
60°	12198	9671	8018
65°	11731	8653	7072
70°	11049	7532	6005
75°	10187	6245	4885
80°	8884	4761	4477
85°	7521	4326	4039



TEST NUMBER: P333002-830

CATALOG NUMBER: S124RDIP-S1195D810U830-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	184.6	2.5
10°-20°	514.9	7.1
20°-30°	743.5	10.2
30°-40°	842.8	11.6
40°-50°	813.8	11.2
50°-60°	676.7	9.3
60°-70°	467.3	6.4
70°-80°	236.9	3.3
80°-90°	62.8	0.9
90°-100°	270.9	3.7
100°-110°	563.9	7.8
110°-120°	505.1	6.9
120°-130°	424.9	5.8
130°-140°	354.3	4.9
140°-150°	270.6	3.7
150°-160°	190.2	2.6
160°-170°	111.9	1.5
170°-180°	36.4	0.5
0°-30°	1443.1	19.8
0°-40°	2285.8	31.4
0°-60°	3776.4	51.9
0°-90°	4543.5	62.5
90°-120°	1340.0	18.4
90°-150°	2389.7	32.9
90°-180°	2728.0	37.5
0°-180°	7271.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1966	1966	1966	1966	1966	
5°	1963	1956	1938	1953	1951	186
15°	1869	1854	1818	1815	1805	526
25°	1690	1661	1601	1576	1561	778
35°	1461	1412	1338	1288	1260	913
45°	1192	1134	1046	975	945	919
55°	903	841	745	669	638	807
65°	614	548	453	391	370	606
75°	327	270	200	167	157	345
85°	81	53	47	44	44	91
90°	1	6	13	15	16	5
95°	24	77	601	297	180	27
105°	86	125	483	1041	1037	92
115°	152	191	431	828	996	151
125°	212	251	429	705	794	188
135°	251	299	425	626	710	194
145°	290	332	423	528	580	182
155°	329	356	411	466	486	152
165°	359	370	394	418	424	101
175°	374	375	378	383	382	36
180°	375	375	375	375	375	



TEST NUMBER: P333002-830

CATALOG NUMBER: S124RDIP-S1195D810U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1965.6	1965.6	1965.6	1965.6	1965.6	1965.6	1965.6	1965.6	1965.6	1965.6	1965.6
2.5°	1970.4	1969.3	1968.3	1967.2	1966.1	1964.2	1961.2	1958.2	1955.3	1952.4	1955.3
5°	1962.6	1961.2	1959.9	1958.6	1957.3	1954.6	1950.6	1946.5	1942.6	1938.5	1941.8
7.5°	1944.8	1943.4	1942.0	1940.6	1939.2	1935.9	1930.7	1925.5	1920.2	1915.1	1917.2
10°	1928.0	1926.3	1924.7	1923.0	1921.3	1917.4	1911.5	1905.4	1899.4	1893.4	1894.7
12.5°	1906.3	1904.4	1902.4	1900.4	1898.6	1894.0	1887.0	1879.9	1872.7	1865.7	1866.5
15°	1869.3	1866.2	1863.3	1860.3	1857.3	1851.5	1843.2	1834.8	1826.5	1818.1	1817.4
17.5°	1824.5	1820.0	1815.7	1811.4	1807.0	1799.9	1789.8	1779.8	1769.7	1759.7	1757.8
20°	1789.5	1785.2	1780.8	1776.5	1772.2	1764.3	1752.9	1741.5	1730.1	1718.8	1716.1
22.5°	1751.0	1746.2	1741.3	1736.4	1731.5	1723.0	1710.7	1698.6	1686.4	1674.2	1670.2
25°	1690.2	1684.1	1678.1	1672.2	1666.1	1656.2	1642.6	1628.8	1615.1	1601.4	1595.7
27.5°	1626.4	1618.8	1611.3	1603.7	1596.1	1585.1	1570.4	1555.8	1541.1	1526.4	1519.4
30°	1581.9	1573.5	1565.1	1556.7	1548.4	1536.3	1520.6	1504.9	1489.2	1473.5	1465.1
32.5°	1534.8	1525.4	1516.0	1506.6	1497.1	1484.3	1468.0	1451.8	1435.5	1419.3	1409.6
35°	1461.4	1450.7	1440.0	1429.3	1418.6	1404.9	1388.2	1371.5	1354.7	1338.0	1326.6
37.5°	1382.9	1371.8	1360.7	1349.7	1338.7	1323.9	1305.4	1286.9	1268.4	1249.8	1237.1
40°	1327.5	1316.4	1305.4	1294.4	1283.3	1268.3	1249.2	1230.1	1211.1	1192.0	1178.0
42.5°	1274.5	1262.9	1251.3	1239.7	1228.2	1212.5	1192.6	1172.7	1152.9	1133.0	1118.7
45°	1192.0	1179.6	1167.2	1154.9	1142.6	1126.2	1106.3	1086.2	1066.1	1046.0	1029.6
47.5°	1106.8	1094.0	1081.3	1068.5	1055.7	1038.9	1018.0	997.1	976.3	955.5	938.4
50°	1049.0	1035.9	1022.9	1009.9	996.8	979.6	958.2	936.8	915.4	894.0	877.3
52.5°	990.0	977.2	964.5	951.7	939.0	921.5	899.7	877.7	855.7	833.8	816.8
55°	903.1	889.7	876.3	862.9	849.5	832.0	810.2	788.5	766.8	745.0	727.6
57.5°	816.9	803.0	789.1	775.2	761.3	743.7	722.3	700.8	679.4	658.0	640.4
60°	755.5	742.2	728.8	715.4	702.0	684.7	663.3	641.9	620.4	599.0	581.6
62.5°	700.1	686.3	672.3	658.5	644.5	626.6	604.6	582.7	560.7	538.9	522.7
65°	614.1	599.6	585.3	570.9	556.6	538.7	517.3	495.9	474.5	453.0	438.7
67.5°	524.6	510.9	497.1	483.3	469.6	452.7	432.8	413.0	393.1	373.2	360.9
70°	468.1	454.0	440.0	425.9	411.9	395.3	376.3	357.2	338.2	319.1	308.0
72.5°	407.8	395.2	382.5	369.8	357.0	341.7	323.7	305.7	287.7	269.7	260.2
75°	326.6	314.2	301.8	289.5	277.1	263.1	247.3	231.6	215.9	200.2	192.5
77.5°	244.1	233.7	223.1	212.6	202.1	190.5	177.8	165.1	152.4	139.7	135.2
80°	191.1	181.4	171.7	162.0	152.3	142.5	132.4	122.4	112.4	102.4	101.3
82.5°	145.4	136.5	127.6	118.7	109.8	102.5	96.7	91.0	85.2	79.5	78.7
85°	81.2	74.6	67.9	61.2	54.5	50.7	49.7	48.6	47.7	46.7	46.0
87.5°	27.8	26.0	24.3	22.3	20.3	19.1	19.7	19.4	19.5	19.5	19.1
90°	0.8	2.2	4.4	5.2	5.9	5.9	10.3	10.3	11.8	13.3	12.5
92.5°	8.4	12.3	19.1	28.2	38.9	54.2	91.7	148.8	204.6	233.8	194.7
95°	24.3	26.5	33.9	43.5	61.2	92.1	156.3	277.1	453.3	600.7	617.6
97.5°	43.6	43.6	50.0	58.8	74.0	99.9	149.3	249.1	424.2	632.6	775.9
100°	56.0	56.0	61.2	70.0	84.0	107.6	151.1	234.4	384.7	592.6	781.2
102.5°	67.8	69.0	73.5	81.8	95.2	117.6	156.9	230.3	358.2	542.4	737.0
105°	86.2	88.4	92.1	100.9	114.2	135.6	171.0	232.1	335.4	483.4	656.7
107.5°	106.6	108.0	111.7	121.1	133.8	155.0	187.4	243.1	331.2	450.4	591.8
110°	120.2	121.6	125.3	134.1	147.4	167.3	199.7	251.3	332.3	439.2	559.4



TEST NUMBER: P333002-830

CATALOG NUMBER: S124RDIP-S1195D810U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	133.1	134.6	138.8	147.1	160.3	180.3	211.5	260.1	335.9	433.9	541.1
115°	151.8	154.0	159.2	166.5	180.6	200.5	230.0	274.2	342.7	431.1	524.0
117.5°	171.3	173.3	178.0	186.1	199.2	219.8	247.8	288.4	350.0	430.4	516.3
120°	184.3	185.7	190.9	199.0	211.5	232.1	260.1	298.5	355.2	430.4	512.2
122.5°	196.0	197.6	202.6	210.2	223.9	243.9	271.9	307.9	360.5	429.8	507.5
125°	211.5	214.4	218.9	227.0	241.0	261.6	288.1	322.1	368.5	429.0	499.6
127.5°	225.3	227.6	232.9	242.1	256.7	277.6	303.2	334.3	374.8	427.3	489.2
130°	232.9	235.8	241.8	252.8	266.8	288.1	313.2	342.0	379.6	426.7	482.8
132.5°	240.5	242.9	250.6	261.1	276.3	296.4	321.5	349.6	383.7	426.1	476.8
135°	251.3	254.3	261.6	274.2	289.6	308.8	333.1	359.7	389.8	425.3	468.0
137.5°	262.1	264.9	273.0	284.9	301.0	319.2	342.0	366.7	393.5	425.1	460.3
140°	269.8	271.9	280.0	292.6	308.0	325.7	347.9	371.5	396.5	424.5	456.2
142.5°	278.0	280.2	287.8	299.6	314.5	331.7	353.2	374.9	398.9	424.5	452.7
145°	289.6	291.8	299.3	309.5	323.6	339.8	358.9	378.8	400.2	423.0	446.6
147.5°	302.7	303.5	310.0	320.6	332.2	346.9	364.9	382.2	401.0	420.4	441.2
150°	311.0	311.8	317.6	326.5	337.5	351.6	367.8	384.0	401.0	418.6	437.1
152.5°	318.7	318.9	324.7	333.0	342.9	355.7	370.1	385.1	399.7	415.7	432.3
155°	329.4	330.2	334.6	342.0	350.1	361.1	373.6	386.2	397.9	411.2	425.3
157.5°	339.9	339.9	344.0	349.8	356.8	365.5	376.2	386.2	396.1	406.7	418.0
160°	346.4	346.4	349.3	354.5	360.4	368.5	377.3	386.2	394.3	403.1	412.7
162.5°	352.3	351.7	354.0	358.6	363.9	370.2	378.5	386.2	392.6	399.6	408.0
165°	358.9	358.9	360.4	364.1	367.8	372.2	378.8	384.7	389.2	394.3	400.2
167.5°	365.5	364.9	365.5	368.3	370.4	373.8	378.7	383.0	385.6	389.0	393.1
170°	368.5	367.8	368.5	370.7	372.2	374.4	378.1	381.7	383.2	385.4	388.4
172.5°	371.5	370.7	370.9	372.5	373.3	374.9	377.5	380.6	380.9	381.9	384.3
175°	374.4	373.6	373.6	374.4	375.1	375.1	376.6	378.8	378.1	378.1	379.6
177.5°	375.7	375.1	374.6	375.1	375.1	375.1	375.7	376.9	375.7	375.7	376.3
180°	375.1	375.1	375.1	375.1	375.1	375.1	375.1	375.1	375.1	375.1	375.1



TEST NUMBER: P333002-830

CATALOG NUMBER: S124RDIP-S1195D810U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1965.6	1965.6	1965.6	1965.6	1965.6	1965.6	1965.6	1965.6
2.5°	1958.2	1961.2	1964.2	1965.5	1965.2	1964.9	1964.6	1964.4
5°	1945.2	1948.5	1951.9	1953.2	1952.6	1951.9	1951.3	1950.6
7.5°	1919.3	1921.5	1923.6	1924.1	1923.1	1922.0	1920.9	1919.9
10°	1896.0	1897.3	1898.8	1898.8	1897.3	1896.0	1894.7	1893.4
12.5°	1867.3	1868.1	1868.9	1868.3	1866.5	1864.6	1862.7	1860.9
15°	1816.8	1816.1	1815.4	1813.9	1811.6	1809.2	1806.9	1804.6
17.5°	1756.0	1754.1	1752.2	1749.5	1746.0	1742.4	1738.9	1735.3
20°	1713.4	1710.7	1708.1	1704.6	1700.3	1695.9	1691.5	1687.2
22.5°	1666.2	1662.2	1658.2	1654.4	1650.9	1647.3	1643.8	1640.2
25°	1590.0	1584.3	1578.7	1574.1	1570.7	1567.4	1564.1	1560.8
27.5°	1512.4	1505.3	1498.4	1492.4	1487.6	1482.8	1478.0	1473.2
30°	1456.7	1448.4	1440.0	1433.1	1427.8	1422.5	1417.1	1411.7
32.5°	1399.9	1390.2	1380.4	1373.1	1368.0	1362.9	1357.8	1352.7
35°	1315.2	1303.9	1292.5	1283.8	1277.8	1271.8	1265.7	1259.7
37.5°	1224.4	1211.6	1199.0	1189.6	1183.6	1177.5	1171.6	1165.5
40°	1163.9	1149.9	1135.9	1125.8	1119.7	1113.7	1107.8	1101.7
42.5°	1104.4	1090.1	1075.7	1065.5	1059.1	1052.9	1046.6	1040.3
45°	1013.2	996.8	980.4	969.2	963.3	957.2	951.2	945.2
47.5°	921.4	904.5	887.5	875.6	869.0	862.4	855.7	849.1
50°	860.5	843.9	827.1	815.6	809.3	802.9	796.5	790.1
52.5°	799.8	782.9	765.8	754.0	747.4	740.8	734.1	727.5
55°	710.2	692.9	675.4	663.5	657.2	650.8	644.5	638.1
57.5°	622.7	605.0	587.4	576.2	571.4	566.5	561.7	556.9
60°	564.2	546.9	529.4	518.1	512.7	507.4	502.0	496.6
62.5°	506.7	490.7	474.6	464.4	460.1	455.9	451.6	447.3
65°	424.2	409.9	395.5	386.3	382.3	378.2	374.3	370.2
67.5°	348.6	336.1	323.8	315.4	310.9	306.5	302.1	297.7
70°	297.0	286.0	274.9	267.8	264.4	261.1	257.7	254.4
72.5°	250.8	241.4	232.0	225.7	222.6	219.6	216.5	213.4
75°	184.8	177.1	169.4	164.6	162.6	160.5	158.5	156.6
77.5°	130.7	126.2	121.8	119.2	118.6	118.0	117.4	116.8
80°	100.4	99.3	98.3	97.6	97.4	97.0	96.7	96.3
82.5°	78.0	77.3	76.5	76.0	75.7	75.3	75.0	74.6
85°	45.3	44.7	44.0	43.6	43.6	43.6	43.6	43.6
87.5°	18.9	18.9	18.8	18.8	19.1	19.6	19.7	20.0
90°	13.3	14.0	14.7	14.7	15.5	16.2	15.5	15.5
92.5°	144.8	109.0	86.7	71.9	63.2	59.3	56.7	56.7
95°	546.1	431.9	333.1	261.6	225.6	202.6	189.5	179.8
97.5°	806.8	764.4	692.3	615.4	562.5	518.1	496.0	480.7
100°	888.8	903.5	867.4	812.9	748.8	703.8	681.7	675.8
102.5°	884.7	957.8	968.3	945.6	906.3	873.6	850.4	845.6
105°	825.5	952.9	1025.9	1056.1	1057.6	1051.7	1041.4	1037.0
107.5°	741.3	877.0	979.8	1045.5	1081.9	1098.7	1106.1	1108.0
110°	690.6	818.0	924.9	1006.0	1058.3	1089.3	1102.6	1109.2



TEST NUMBER: P333002-830

CATALOG NUMBER: S124RDIP-S1195D810U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	653.5	766.2	867.1	948.2	1007.6	1045.1	1063.7	1074.4
115°	616.1	706.8	793.0	863.7	922.0	966.2	989.8	995.7
117.5°	597.9	672.9	740.6	800.7	850.4	887.5	911.3	916.0
120°	589.6	658.2	717.1	769.4	811.4	843.9	863.0	871.1
122.5°	582.5	648.7	702.4	748.2	783.7	811.4	827.6	835.8
125°	570.4	633.9	684.7	725.2	754.7	776.1	790.0	794.5
127.5°	555.7	616.2	666.9	705.5	735.1	754.1	765.9	770.3
130°	543.9	602.1	652.2	691.3	721.5	740.0	751.8	756.2
132.5°	531.5	586.2	635.2	674.2	703.8	724.6	735.8	740.3
135°	514.4	562.3	607.3	644.1	673.6	694.3	706.1	710.5
137.5°	499.0	539.5	577.4	610.7	638.2	658.6	668.3	673.6
140°	490.1	524.7	557.9	588.9	614.6	630.8	641.2	647.1
142.5°	481.8	512.4	540.8	567.6	590.5	605.5	614.6	618.8
145°	470.2	495.3	517.4	538.0	556.5	568.9	576.4	580.0
147.5°	460.6	480.5	498.2	514.4	528.0	538.8	544.3	545.6
150°	454.7	471.6	486.4	499.6	511.5	521.0	525.5	526.2
152.5°	448.3	462.8	476.4	487.3	497.3	505.1	507.7	508.5
155°	438.5	450.3	461.4	470.2	477.6	483.4	485.7	485.7
157.5°	428.0	437.9	447.2	454.3	459.9	464.3	465.6	465.6
160°	421.6	429.7	437.8	443.7	448.1	452.5	453.3	453.3
162.5°	415.1	422.0	428.4	433.7	436.9	441.3	442.1	441.5
165°	406.0	410.5	415.7	419.3	422.3	425.3	424.5	423.8
167.5°	397.4	400.8	404.9	407.1	408.6	410.5	410.4	409.7
170°	392.1	394.3	397.3	399.4	401.0	401.6	401.0	401.0
172.5°	387.4	389.0	390.8	392.4	393.2	394.0	393.2	392.1
175°	381.1	381.7	383.2	383.2	383.2	384.7	383.2	381.7
177.5°	376.9	377.5	377.5	378.1	377.5	378.1	376.9	375.7
180°	375.1	375.1	375.1	375.1	375.1	375.1	375.1	375.1

(END OF REPORT)