

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332882-830

Luminaire Tested: **S124RDIP-S350D810U830-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332882-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIP-S350D810U830-4F0-1E-UDD-F4
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 810 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4076.5 lumens
Efficiency: N/A
Efficacy: 130.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 31.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332882-830

CATALOG NUMBER: S124RDIP-S350D810U830-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P332882-830

CATALOG NUMBER: S124RDIP-S350D810U830-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41
1	94	90	86	83	85	81	78	75	65	63	61	50	49	47	36	35	35
2	86	79	73	68	77	71	66	62	57	54	51	44	42	40	32	31	29
3	78	69	62	57	70	63	57	52	50	46	43	39	36	34	28	27	25
4	72	61	54	48	64	56	49	44	45	40	36	35	32	29	26	23	22
5	66	55	47	41	59	50	43	38	40	35	31	31	28	25	23	21	19
6	61	49	41	36	54	45	38	33	36	31	27	28	25	22	21	19	17
7	56	44	36	31	50	40	33	29	33	28	24	26	22	19	19	17	15
8	52	40	33	27	47	36	30	25	30	25	21	23	20	17	18	15	13
9	48	36	29	24	43	33	27	23	27	22	19	22	18	16	16	14	12
10	45	33	26	22	41	30	24	20	25	20	17	20	16	14	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4704	4704	4704
5°	4714	4657	4686
10°	4685	4601	4601
15°	4631	4504	4471
20°	4558	4376	4296
25°	4464	4228	4121
30°	4371	4072	3901
35°	4269	3909	3680
40°	4147	3724	3442
45°	4035	3540	3199
50°	3905	3328	2941
55°	3768	3108	2663
60°	3615	2868	2377
65°	3477	2565	2096
70°	3274	2231	1780
75°	3019	1853	1447
80°	2631	1409	1330
85°	2232	1288	1195



TEST NUMBER: P332882-830

CATALOG NUMBER: S124RDIP-S350D810U830-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.7	1.3
10°-20°	152.6	3.7
20°-30°	220.4	5.4
30°-40°	249.8	6.1
40°-50°	241.2	5.9
50°-60°	200.6	4.9
60°-70°	138.5	3.4
70°-80°	70.2	1.7
80°-90°	20.1	0.5
90°-100°	270.9	6.6
100°-110°	563.9	13.8
110°-120°	505.1	12.4
120°-130°	424.9	10.4
130°-140°	354.3	8.7
140°-150°	270.6	6.6
150°-160°	190.2	4.7
160°-170°	111.9	2.7
170°-180°	36.4	0.9
0°-30°	427.8	10.5
0°-40°	677.6	16.6
0°-60°	1119.4	27.5
0°-90°	1348.2	33.1
90°-120°	1340.0	32.9
90°-150°	2389.7	58.6
90°-180°	2728.0	66.9
0°-180°	4076.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	583	583	583	583	583	
5°	582	580	575	579	578	55
15°	554	550	539	538	535	156
25°	501	492	475	467	463	231
35°	433	418	397	382	373	271
45°	353	336	310	289	280	272
55°	268	249	221	198	189	239
65°	182	162	134	116	110	180
75°	97	80	59	50	46	102
85°	24	16	14	13	13	27
90°	1	6	13	15	16	3
95°	24	77	601	297	180	27
105°	86	125	483	1041	1037	92
115°	152	191	431	828	996	151
125°	212	251	429	705	794	188
135°	251	299	425	626	710	194
145°	290	332	423	528	580	182
155°	329	356	411	466	486	152
165°	359	370	394	418	424	101
175°	374	375	378	383	382	36
180°	375	375	375	375	375	



TEST NUMBER: P332882-830

CATALOG NUMBER: S124RDIP-S350D810U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	582.7	582.7	582.7	582.7	582.7	582.7	582.7	582.7	582.7	582.7	582.7
2.5°	584.1	583.7	583.4	583.2	582.8	582.2	581.4	580.5	579.6	578.7	579.6
5°	581.7	581.4	581.0	580.6	580.1	579.4	578.2	577.0	575.8	574.7	575.6
7.5°	576.5	576.1	575.7	575.2	574.9	573.8	572.3	570.7	569.2	567.7	568.3
10°	571.5	571.0	570.5	570.0	569.5	568.4	566.6	564.8	563.0	561.3	561.7
12.5°	565.1	564.5	563.9	563.4	562.8	561.5	559.3	557.2	555.2	553.0	553.3
15°	554.1	553.2	552.3	551.4	550.5	548.8	546.4	543.8	541.4	538.9	538.8
17.5°	540.8	539.5	538.2	537.0	535.6	533.5	530.6	527.5	524.6	521.6	521.0
20°	530.5	529.1	527.9	526.6	525.3	523.0	519.6	516.2	512.8	509.4	508.7
22.5°	519.1	517.6	516.1	514.7	513.2	510.7	507.1	503.5	499.9	496.2	495.1
25°	501.1	499.3	497.5	495.7	493.9	491.0	486.9	482.9	478.7	474.7	473.0
27.5°	482.1	479.8	477.6	475.4	473.2	469.9	465.5	461.2	456.9	452.5	450.3
30°	468.9	466.4	463.9	461.5	459.0	455.4	450.7	446.1	441.4	436.8	434.3
32.5°	455.0	452.1	449.4	446.6	443.7	440.0	435.2	430.4	425.6	420.8	417.8
35°	433.2	430.0	426.9	423.7	420.5	416.4	411.5	406.5	401.6	396.6	393.2
37.5°	409.9	406.6	403.4	400.1	396.8	392.5	386.9	381.4	376.0	370.5	366.7
40°	393.5	390.2	386.9	383.7	380.4	376.0	370.3	364.7	359.0	353.4	349.2
42.5°	377.8	374.4	370.9	367.5	364.1	359.4	353.5	347.6	341.8	335.8	331.6
45°	353.4	349.7	346.0	342.3	338.7	333.8	327.9	322.0	316.0	310.1	305.2
47.5°	328.1	324.3	320.6	316.7	312.9	307.9	301.8	295.6	289.4	283.2	278.1
50°	310.9	307.1	303.2	299.4	295.5	290.4	284.1	277.7	271.4	265.0	260.0
52.5°	293.5	289.6	285.9	282.1	278.3	273.1	266.6	260.1	253.6	247.1	242.1
55°	267.7	263.7	259.8	255.8	251.8	246.6	240.2	233.8	227.2	220.8	215.7
57.5°	242.1	238.0	233.9	229.8	225.6	220.5	214.1	207.7	201.4	195.0	189.8
60°	223.9	220.0	216.0	212.1	208.1	202.9	196.6	190.2	183.9	177.6	172.4
62.5°	207.5	203.4	199.3	195.2	191.1	185.8	179.3	172.8	166.3	159.8	155.0
65°	182.0	177.8	173.5	169.3	164.9	159.7	153.4	146.9	140.6	134.3	130.1
67.5°	155.5	151.5	147.3	143.3	139.2	134.2	128.3	122.4	116.5	110.7	107.0
70°	138.7	134.6	130.4	126.3	122.1	117.2	111.5	105.8	100.2	94.5	91.3
72.5°	120.9	117.2	113.4	109.6	105.8	101.3	96.0	90.6	85.3	79.9	77.2
75°	96.8	93.1	89.4	85.8	82.1	77.9	73.3	68.6	64.0	59.4	57.0
77.5°	72.4	69.3	66.2	63.1	59.9	56.5	52.7	48.9	45.1	41.4	40.1
80°	56.6	53.8	50.9	48.1	45.1	42.2	39.3	36.3	33.3	30.3	30.1
82.5°	43.1	40.4	37.8	35.2	32.5	30.3	28.7	27.0	25.3	23.6	23.4
85°	24.1	22.1	20.2	18.1	16.1	15.0	14.7	14.4	14.1	13.9	13.7
87.5°	8.4	8.0	7.8	7.4	6.9	6.5	7.3	7.3	7.4	7.6	7.4
90°	0.8	2.2	4.4	5.2	5.9	5.9	10.3	10.3	11.8	13.3	12.5
92.5°	8.4	12.3	19.1	28.2	38.9	54.2	91.7	148.8	204.6	233.8	194.7
95°	24.3	26.5	33.9	43.5	61.2	92.1	156.3	277.1	453.3	600.7	617.6
97.5°	43.6	43.6	50.0	58.8	74.0	99.9	149.3	249.1	424.2	632.6	775.9
100°	56.0	56.0	61.2	70.0	84.0	107.6	151.1	234.4	384.7	592.6	781.2
102.5°	67.8	69.0	73.5	81.8	95.2	117.6	156.9	230.3	358.2	542.4	737.0
105°	86.2	88.4	92.1	100.9	114.2	135.6	171.0	232.1	335.4	483.4	656.7
107.5°	106.6	108.0	111.7	121.1	133.8	155.0	187.4	243.1	331.2	450.4	591.8
110°	120.2	121.6	125.3	134.1	147.4	167.3	199.7	251.3	332.3	439.2	559.4



TEST NUMBER: P332882-830

CATALOG NUMBER: S124RDIP-S350D810U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	133.1	134.6	138.8	147.1	160.3	180.3	211.5	260.1	335.9	433.9	541.1
115°	151.8	154.0	159.2	166.5	180.6	200.5	230.0	274.2	342.7	431.1	524.0
117.5°	171.3	173.3	178.0	186.1	199.2	219.8	247.8	288.4	350.0	430.4	516.3
120°	184.3	185.7	190.9	199.0	211.5	232.1	260.1	298.5	355.2	430.4	512.2
122.5°	196.0	197.6	202.6	210.2	223.9	243.9	271.9	307.9	360.5	429.8	507.5
125°	211.5	214.4	218.9	227.0	241.0	261.6	288.1	322.1	368.5	429.0	499.6
127.5°	225.3	227.6	232.9	242.1	256.7	277.6	303.2	334.3	374.8	427.3	489.2
130°	232.9	235.8	241.8	252.8	266.8	288.1	313.2	342.0	379.6	426.7	482.8
132.5°	240.5	242.9	250.6	261.1	276.3	296.4	321.5	349.6	383.7	426.1	476.8
135°	251.3	254.3	261.6	274.2	289.6	308.8	333.1	359.7	389.8	425.3	468.0
137.5°	262.1	264.9	273.0	284.9	301.0	319.2	342.0	366.7	393.5	425.1	460.3
140°	269.8	271.9	280.0	292.6	308.0	325.7	347.9	371.5	396.5	424.5	456.2
142.5°	278.0	280.2	287.8	299.6	314.5	331.7	353.2	374.9	398.9	424.5	452.7
145°	289.6	291.8	299.3	309.5	323.6	339.8	358.9	378.8	400.2	423.0	446.6
147.5°	302.7	303.5	310.0	320.6	332.2	346.9	364.9	382.2	401.0	420.4	441.2
150°	311.0	311.8	317.6	326.5	337.5	351.6	367.8	384.0	401.0	418.6	437.1
152.5°	318.7	318.9	324.7	333.0	342.9	355.7	370.1	385.1	399.7	415.7	432.3
155°	329.4	330.2	334.6	342.0	350.1	361.1	373.6	386.2	397.9	411.2	425.3
157.5°	339.9	339.9	344.0	349.8	356.8	365.5	376.2	386.2	396.1	406.7	418.0
160°	346.4	346.4	349.3	354.5	360.4	368.5	377.3	386.2	394.3	403.1	412.7
162.5°	352.3	351.7	354.0	358.6	363.9	370.2	378.5	386.2	392.6	399.6	408.0
165°	358.9	358.9	360.4	364.1	367.8	372.2	378.8	384.7	389.2	394.3	400.2
167.5°	365.5	364.9	365.5	368.3	370.4	373.8	378.7	383.0	385.6	389.0	393.1
170°	368.5	367.8	368.5	370.7	372.2	374.4	378.1	381.7	383.2	385.4	388.4
172.5°	371.5	370.7	370.9	372.5	373.3	374.9	377.5	380.6	380.9	381.9	384.3
175°	374.4	373.6	373.6	374.4	375.1	375.1	376.6	378.8	378.1	378.1	379.6
177.5°	375.7	375.1	374.6	375.1	375.1	375.1	375.7	376.9	375.7	375.7	376.3
180°	375.1	375.1	375.1	375.1	375.1	375.1	375.1	375.1	375.1	375.1	375.1



TEST NUMBER: P332882-830

CATALOG NUMBER: S124RDIP-S350D810U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	582.7	582.7	582.7	582.7	582.7	582.7	582.7	582.7
2.5°	580.5	581.4	582.2	582.6	582.5	582.5	582.4	582.3
5°	576.6	577.6	578.6	579.0	578.8	578.6	578.3	578.2
7.5°	568.9	569.6	570.2	570.3	570.0	569.8	569.4	569.1
10°	562.0	562.4	562.8	562.8	562.4	562.0	561.7	561.3
12.5°	553.5	553.7	554.0	553.8	553.3	552.7	552.1	551.6
15°	538.6	538.4	538.1	537.7	537.0	536.3	535.6	534.9
17.5°	520.5	520.0	519.4	518.6	517.6	516.5	515.5	514.4
20°	507.9	507.1	506.3	505.3	504.0	502.7	501.4	500.1
22.5°	493.9	492.7	491.5	490.4	489.4	488.3	487.3	486.2
25°	471.3	469.7	468.0	466.7	465.6	464.6	463.6	462.6
27.5°	448.3	446.2	444.1	442.4	440.9	439.5	438.1	436.7
30°	431.8	429.3	426.9	424.8	423.2	421.7	420.1	418.5
32.5°	415.0	412.1	409.3	407.0	405.5	404.0	402.5	401.0
35°	389.8	386.5	383.1	380.6	378.8	377.0	375.2	373.4
37.5°	363.0	359.2	355.4	352.6	350.8	349.0	347.2	345.4
40°	345.0	340.8	336.7	333.8	332.0	330.2	328.4	326.6
42.5°	327.3	323.1	318.9	315.8	314.0	312.1	310.2	308.4
45°	300.4	295.5	290.6	287.3	285.5	283.7	281.9	280.2
47.5°	273.1	268.1	263.1	259.6	257.6	255.6	253.6	251.8
50°	255.1	250.2	245.2	241.8	239.9	238.0	236.1	234.2
52.5°	237.0	232.1	227.1	223.5	221.6	219.6	217.6	215.7
55°	210.6	205.4	200.2	196.7	194.8	192.9	191.1	189.2
57.5°	184.5	179.4	174.1	170.8	169.4	168.0	166.5	165.0
60°	167.2	162.1	156.9	153.5	151.9	150.4	148.8	147.2
62.5°	150.2	145.4	140.7	137.7	136.4	135.2	133.8	132.6
65°	125.7	121.5	117.3	114.5	113.3	112.2	110.9	109.7
67.5°	103.3	99.6	96.0	93.5	92.2	90.9	89.5	88.2
70°	88.0	84.7	81.5	79.4	78.3	77.4	76.3	75.4
72.5°	74.4	71.5	68.8	66.9	66.0	65.1	64.2	63.2
75°	54.8	52.5	50.2	48.8	48.2	47.6	47.0	46.4
77.5°	38.7	37.4	36.1	35.3	35.2	35.0	34.8	34.6
80°	29.8	29.4	29.1	28.9	28.8	28.7	28.7	28.6
82.5°	23.1	22.9	22.7	22.5	22.4	22.3	22.2	22.1
85°	13.5	13.2	13.0	12.9	12.9	12.9	12.9	12.9
87.5°	7.4	7.5	7.6	7.6	7.8	8.1	8.0	8.1
90°	13.3	14.0	14.7	14.7	15.5	16.2	15.5	15.5
92.5°	144.8	109.0	86.7	71.9	63.2	59.3	56.7	56.7
95°	546.1	431.9	333.1	261.6	225.6	202.6	189.5	179.8
97.5°	806.8	764.4	692.3	615.4	562.5	518.1	496.0	480.7
100°	888.8	903.5	867.4	812.9	748.8	703.8	681.7	675.8
102.5°	884.7	957.8	968.3	945.6	906.3	873.6	850.4	845.6
105°	825.5	952.9	1025.9	1056.1	1057.6	1051.7	1041.4	1037.0
107.5°	741.3	877.0	979.8	1045.5	1081.9	1098.7	1106.1	1108.0
110°	690.6	818.0	924.9	1006.0	1058.3	1089.3	1102.6	1109.2



TEST NUMBER: P332882-830

CATALOG NUMBER: S124RDIP-S350D810U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	653.5	766.2	867.1	948.2	1007.6	1045.1	1063.7	1074.4
115°	616.1	706.8	793.0	863.7	922.0	966.2	989.8	995.7
117.5°	597.9	672.9	740.6	800.7	850.4	887.5	911.3	916.0
120°	589.6	658.2	717.1	769.4	811.4	843.9	863.0	871.1
122.5°	582.5	648.7	702.4	748.2	783.7	811.4	827.6	835.8
125°	570.4	633.9	684.7	725.2	754.7	776.1	790.0	794.5
127.5°	555.7	616.2	666.9	705.5	735.1	754.1	765.9	770.3
130°	543.9	602.1	652.2	691.3	721.5	740.0	751.8	756.2
132.5°	531.5	586.2	635.2	674.2	703.8	724.6	735.8	740.3
135°	514.4	562.3	607.3	644.1	673.6	694.3	706.1	710.5
137.5°	499.0	539.5	577.4	610.7	638.2	658.6	668.3	673.6
140°	490.1	524.7	557.9	588.9	614.6	630.8	641.2	647.1
142.5°	481.8	512.4	540.8	567.6	590.5	605.5	614.6	618.8
145°	470.2	495.3	517.4	538.0	556.5	568.9	576.4	580.0
147.5°	460.6	480.5	498.2	514.4	528.0	538.8	544.3	545.6
150°	454.7	471.6	486.4	499.6	511.5	521.0	525.5	526.2
152.5°	448.3	462.8	476.4	487.3	497.3	505.1	507.7	508.5
155°	438.5	450.3	461.4	470.2	477.6	483.4	485.7	485.7
157.5°	428.0	437.9	447.2	454.3	459.9	464.3	465.6	465.6
160°	421.6	429.7	437.8	443.7	448.1	452.5	453.3	453.3
162.5°	415.1	422.0	428.4	433.7	436.9	441.3	442.1	441.5
165°	406.0	410.5	415.7	419.3	422.3	425.3	424.5	423.8
167.5°	397.4	400.8	404.9	407.1	408.6	410.5	410.4	409.7
170°	392.1	394.3	397.3	399.4	401.0	401.6	401.0	401.0
172.5°	387.4	389.0	390.8	392.4	393.2	394.0	393.2	392.1
175°	381.1	381.7	383.2	383.2	383.2	384.7	383.2	381.7
177.5°	376.9	377.5	377.5	378.1	377.5	378.1	376.9	375.7
180°	375.1	375.1	375.1	375.1	375.1	375.1	375.1	375.1

(END OF REPORT)