

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332899-830

Luminaire Tested: **S124RDIP-S575D365U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332899-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIP-S575D365U830-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 365 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3409.2 lumens
Efficiency: N/A
Efficacy: 124.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 27.5
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332899-830

CATALOG NUMBER: S124RDIP-S575D365U830-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332899-830

CATALOG NUMBER: S124RDIP-S575D365U830-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	104	104	104	104	92	92	92	80	80	80	70	70	70	65
1	101	97	93	90	95	92	88	85	81	78	76	71	69	68	62	61	60	55
2	93	85	79	74	87	80	75	70	71	67	64	63	60	57	55	53	51	47
3	85	75	68	62	79	71	65	59	63	58	54	56	52	49	49	46	44	40
4	78	67	59	53	73	63	56	51	56	51	46	50	46	42	44	41	38	35
5	72	60	52	46	67	57	49	44	51	45	40	45	40	37	40	36	33	30
6	66	54	46	40	62	51	44	38	46	40	35	41	36	32	36	32	29	27
7	61	49	41	35	58	46	39	34	42	36	31	37	32	29	33	29	26	24
8	57	45	37	31	54	42	35	30	38	32	28	34	29	26	31	27	24	21
9	53	41	33	28	50	39	32	27	35	29	25	32	27	23	28	24	21	19
10	50	38	30	25	47	36	29	25	32	27	23	29	25	21	26	22	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7733	7733	7733
5°	7750	7656	7703
10°	7702	7564	7564
15°	7614	7405	7350
20°	7491	7196	7064
25°	7337	6951	6774
30°	7185	6693	6413
35°	7019	6427	6050
40°	6817	6122	5658
45°	6632	5819	5259
50°	6420	5471	4835
55°	6194	5111	4376
60°	5945	4713	3907
65°	5717	4216	3446
70°	5384	3670	2924
75°	4966	3044	2380
80°	4328	2320	2180
85°	3668	2103	1973



TEST NUMBER: P332899-830

CATALOG NUMBER: S124RDIP-S575D365U830-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.0	2.6
10°-20°	250.9	7.4
20°-30°	362.3	10.6
30°-40°	410.7	12.0
40°-50°	396.6	11.6
50°-60°	329.8	9.7
60°-70°	227.7	6.7
70°-80°	115.4	3.4
80°-90°	30.9	0.9
90°-100°	28.4	0.8
100°-110°	84.2	2.5
110°-120°	142.8	4.2
120°-130°	188.3	5.5
130°-140°	211.5	6.2
140°-150°	207.8	6.1
150°-160°	174.8	5.1
160°-170°	116.3	3.4
170°-180°	40.7	1.2
0°-30°	703.2	20.6
0°-40°	1113.9	32.7
0°-60°	1840.3	54.0
0°-90°	2214.4	65.0
90°-120°	255.4	7.5
90°-150°	863.0	25.3
90°-180°	1195.0	35.1
0°-180°	3409.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	958	958	958	958	958	
5°	956	953	945	952	951	91
15°	911	904	886	884	879	257
25°	824	810	780	768	760	379
35°	712	688	652	628	614	445
45°	581	553	510	475	461	448
55°	440	410	363	326	311	394
65°	299	267	221	190	180	295
75°	159	132	98	81	76	168
85°	40	26	23	21	21	45
90°	1	5	7	9	10	3
95°	20	23	25	26	26	22
105°	78	78	79	80	81	82
115°	145	145	145	144	144	143
125°	212	211	211	210	210	188
135°	273	275	275	274	273	211
145°	331	333	333	333	332	207
155°	380	380	379	380	379	175
165°	413	412	412	413	412	116
175°	430	428	428	430	428	41
180°	431	431	431	431	431	



TEST NUMBER: P332899-830

CATALOG NUMBER: S124RDIP-S575D365U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	957.9	957.9	957.9	957.9	957.9	957.9	957.9	957.9	957.9	957.9	957.9
2.5°	960.3	959.7	959.2	958.7	958.2	957.2	955.7	954.3	952.8	951.4	952.8
5°	956.4	955.7	955.1	954.4	953.9	952.5	950.6	948.6	946.6	944.7	946.3
7.5°	947.7	947.1	946.4	945.7	945.0	943.4	940.8	938.3	935.8	933.2	934.2
10°	939.5	938.8	937.9	937.1	936.3	934.4	931.5	928.5	925.6	922.7	923.3
12.5°	929.0	928.0	927.1	926.1	925.2	923.0	919.5	916.1	912.7	909.2	909.6
15°	911.0	909.5	908.0	906.5	905.0	902.3	898.2	894.2	890.0	886.0	885.7
17.5°	889.1	886.9	884.9	882.7	880.6	877.1	872.2	867.3	862.4	857.5	856.7
20°	872.0	870.0	867.8	865.7	863.6	859.8	854.2	848.7	843.1	837.6	836.3
22.5°	853.3	850.9	848.6	846.1	843.8	839.6	833.7	827.7	821.8	815.9	813.9
25°	823.7	820.8	817.7	814.8	811.9	807.1	800.4	793.7	787.0	780.4	777.6
27.5°	792.6	788.9	785.2	781.6	777.8	772.4	765.3	758.2	751.0	743.9	740.5
30°	770.8	766.8	762.7	758.7	754.6	748.7	741.0	733.4	725.7	718.0	714.0
32.5°	748.0	743.4	738.8	734.1	729.6	723.3	715.4	707.5	699.6	691.6	686.9
35°	712.2	707.0	701.7	696.5	691.4	684.7	676.5	668.4	660.2	652.1	646.5
37.5°	673.9	668.5	663.2	657.8	652.3	645.2	636.1	627.1	618.1	609.1	602.9
40°	646.9	641.5	636.1	630.7	625.4	618.0	608.8	599.5	590.2	580.9	574.0
42.5°	621.0	615.5	609.8	604.2	598.5	590.9	581.2	571.5	561.8	552.1	545.2
45°	580.9	574.9	568.8	562.8	556.8	548.8	539.0	529.3	519.5	509.7	501.7
47.5°	539.4	533.2	526.9	520.7	514.4	506.2	496.1	486.0	475.8	465.6	457.3
50°	511.2	504.8	498.5	492.1	485.8	477.4	466.9	456.6	446.1	435.6	427.5
52.5°	482.5	476.3	470.0	463.8	457.5	449.1	438.4	427.7	417.0	406.3	398.0
55°	440.1	433.6	427.1	420.5	414.0	405.4	394.8	384.3	373.6	363.1	354.6
57.5°	398.1	391.3	384.6	377.8	371.0	362.4	351.9	341.5	331.1	320.7	312.1
60°	368.2	361.7	355.2	348.6	342.1	333.7	323.2	312.7	302.4	291.9	283.4
62.5°	341.2	334.4	327.6	320.8	314.1	305.4	294.6	284.0	273.2	262.6	254.8
65°	299.3	292.3	285.2	278.2	271.2	262.5	252.0	241.7	231.2	220.7	213.8
67.5°	255.7	248.9	242.2	235.5	228.8	220.6	210.9	201.2	191.6	181.9	175.9
70°	228.1	221.2	214.4	207.5	200.8	192.7	183.3	174.1	164.8	155.5	150.1
72.5°	198.8	192.6	186.3	180.2	174.0	166.5	157.8	149.0	140.2	131.4	126.9
75°	159.2	153.2	147.1	141.1	135.1	128.2	120.6	112.8	105.2	97.6	93.8
77.5°	118.9	113.9	108.8	103.6	98.5	92.8	86.6	80.5	74.3	68.1	65.9
80°	93.1	88.4	83.7	79.0	74.3	69.5	64.6	59.7	54.8	49.9	49.4
82.5°	70.9	66.5	62.2	57.9	53.5	50.0	47.1	44.3	41.6	38.7	38.4
85°	39.6	36.4	33.1	29.8	26.6	24.7	24.2	23.8	23.2	22.7	22.4
87.5°	13.7	12.8	12.0	11.0	10.2	9.7	9.7	9.7	9.7	9.7	9.6
90°	1.0	1.8	2.6	3.5	4.2	5.0	5.6	6.1	6.7	7.4	7.7
92.5°	7.2	8.1	9.0	9.9	10.8	11.5	12.0	12.3	12.8	13.2	13.5
95°	20.0	20.6	21.3	22.0	22.6	23.3	23.8	24.3	24.8	25.4	25.5
97.5°	34.9	35.4	36.0	36.5	37.0	37.6	38.2	38.8	39.4	40.1	40.3
100°	46.7	46.9	47.2	47.5	47.8	48.3	48.9	49.7	50.3	51.0	51.1
102.5°	58.9	59.0	59.1	59.3	59.4	59.8	60.3	61.0	61.5	62.1	62.4
105°	77.6	77.7	77.8	77.9	77.9	78.0	78.4	78.7	79.0	79.3	79.5
107.5°	97.3	97.4	97.5	97.6	97.6	97.6	97.7	97.7	97.8	97.8	98.0
110°	110.6	110.7	110.8	111.0	111.1	111.2	111.1	111.0	110.9	110.9	110.7



TEST NUMBER: P332899-830

CATALOG NUMBER: S124RDIP-S575D365U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	124.4	124.4	124.5	124.5	124.5	124.5	124.3	124.2	124.1	123.9	123.9
115°	145.2	145.2	145.2	145.2	145.2	145.2	145.0	144.9	144.7	144.6	144.5
117.5°	164.8	164.9	164.9	164.9	165.0	165.0	164.9	164.9	164.7	164.6	164.4
120°	177.9	178.1	178.4	178.7	179.1	179.1	178.9	178.6	178.4	178.2	177.9
122.5°	191.4	191.5	191.7	191.8	191.9	191.9	191.8	191.7	191.6	191.5	191.2
125°	211.5	211.5	211.5	211.5	211.5	211.4	211.4	211.3	211.2	211.1	211.0
127.5°	229.7	229.9	230.2	230.4	230.5	230.6	230.5	230.4	230.3	230.2	230.0
130°	242.5	242.7	242.9	243.2	243.4	243.5	243.5	243.5	243.5	243.5	243.4
132.5°	255.5	255.7	255.8	256.0	256.2	256.2	256.2	256.1	256.1	256.0	255.8
135°	272.8	273.2	273.6	274.1	274.6	274.8	274.8	274.8	274.8	274.8	274.7
137.5°	291.5	291.8	292.0	292.2	292.4	292.6	292.7	292.8	292.9	293.0	292.8
140°	304.1	304.3	304.3	304.5	304.7	304.7	304.7	304.7	304.7	304.7	304.7
142.5°	315.6	315.7	315.8	315.9	316.1	316.2	316.1	316.0	316.0	315.9	315.9
145°	331.4	331.7	332.0	332.2	332.6	332.8	332.8	332.9	333.0	333.1	333.0
147.5°	347.1	347.5	347.8	348.2	348.6	348.6	348.6	348.6	348.6	348.5	348.4
150°	356.8	357.0	357.3	357.6	357.9	358.1	358.1	358.1	358.1	358.1	358.1
152.5°	365.8	366.0	366.1	366.3	366.5	366.6	366.6	366.7	366.7	366.8	367.0
155°	379.7	379.7	379.7	379.7	379.7	379.7	379.6	379.5	379.5	379.4	379.7
157.5°	391.4	391.2	391.2	391.1	390.9	390.8	390.8	390.8	390.8	390.8	391.0
160°	398.3	398.2	398.2	398.1	398.0	397.9	397.9	397.8	397.8	397.7	397.9
162.5°	404.7	404.5	404.4	404.2	404.0	403.9	403.8	403.7	403.6	403.5	404.0
165°	413.3	413.1	412.9	412.6	412.5	412.3	412.1	412.0	411.8	411.7	412.1
167.5°	419.9	419.6	419.3	419.0	418.7	418.5	418.6	418.6	418.6	418.6	419.1
170°	423.7	423.3	422.9	422.5	422.2	422.1	422.1	422.2	422.3	422.4	422.7
172.5°	426.3	426.0	425.7	425.4	425.1	424.9	424.9	425.0	425.0	425.0	425.5
175°	430.0	429.6	429.2	428.9	428.5	428.3	428.2	428.1	428.1	428.0	428.5
177.5°	431.2	430.9	430.6	430.3	430.0	429.9	429.9	429.9	429.9	429.9	430.3
180°	430.6	430.6	430.6	430.6	430.6	430.6	430.6	430.6	430.6	430.6	430.6



TEST NUMBER: P332899-830

CATALOG NUMBER: S124RDIP-S575D365U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	957.9	957.9	957.9	957.9	957.9	957.9	957.9	957.9
2.5°	954.3	955.7	957.2	957.8	957.7	957.5	957.4	957.3
5°	947.9	949.6	951.2	951.9	951.5	951.2	950.8	950.6
7.5°	935.3	936.3	937.5	937.6	937.2	936.6	936.1	935.6
10°	924.0	924.6	925.3	925.3	924.6	924.0	923.3	922.7
12.5°	909.9	910.3	910.8	910.5	909.6	908.7	907.8	906.8
15°	885.3	885.0	884.7	884.0	882.8	881.7	880.5	879.4
17.5°	855.7	854.8	853.8	852.5	850.8	849.1	847.3	845.6
20°	835.0	833.7	832.4	830.7	828.6	826.4	824.3	822.2
22.5°	812.0	810.0	808.0	806.3	804.5	802.8	801.1	799.3
25°	774.9	772.0	769.3	767.1	765.4	763.8	762.2	760.5
27.5°	737.0	733.6	730.2	727.3	724.9	722.6	720.3	717.9
30°	709.9	705.8	701.7	698.4	695.8	693.1	690.6	688.0
32.5°	682.2	677.5	672.7	669.1	666.7	664.2	661.7	659.2
35°	640.9	635.4	629.9	625.7	622.7	619.7	616.8	613.9
37.5°	596.6	590.5	584.3	579.8	576.7	573.8	570.9	568.0
40°	567.2	560.3	553.5	548.7	545.6	542.7	539.8	536.9
42.5°	538.2	531.2	524.2	519.2	516.1	513.1	510.0	507.0
45°	493.8	485.8	477.8	472.3	469.4	466.5	463.5	460.6
47.5°	449.0	440.7	432.4	426.7	423.5	420.3	417.1	413.8
50°	419.3	411.2	403.0	397.5	394.4	391.2	388.1	385.0
52.5°	389.7	381.4	373.2	367.5	364.2	361.0	357.8	354.6
55°	346.1	337.6	329.1	323.4	320.3	317.2	314.1	310.9
57.5°	303.4	294.8	286.3	280.8	278.4	276.1	273.7	271.4
60°	274.9	266.5	258.0	252.5	249.9	247.2	244.7	242.0
62.5°	246.9	239.1	231.3	226.3	224.2	222.2	220.1	218.0
65°	206.8	199.7	192.7	188.2	186.3	184.4	182.4	180.4
67.5°	169.8	163.8	157.8	153.7	151.6	149.4	147.2	145.1
70°	144.8	139.4	133.9	130.4	128.8	127.2	125.5	123.9
72.5°	122.2	117.6	113.0	110.0	108.5	107.0	105.5	104.0
75°	90.0	86.3	82.6	80.2	79.2	78.2	77.3	76.3
77.5°	63.7	61.5	59.3	58.1	57.8	57.5	57.2	56.9
80°	48.9	48.4	47.9	47.6	47.4	47.2	47.1	46.9
82.5°	38.0	37.6	37.3	37.0	36.9	36.7	36.6	36.4
85°	22.1	21.8	21.4	21.3	21.3	21.3	21.3	21.3
87.5°	9.6	9.5	9.5	9.6	9.7	9.9	10.1	10.2
90°	8.2	8.7	9.1	9.4	9.5	9.7	9.8	10.0
92.5°	13.8	13.9	14.2	14.4	14.5	14.6	14.7	14.8
95°	25.7	26.0	26.2	26.3	26.3	26.3	26.3	26.3
97.5°	40.5	40.8	41.1	41.2	41.2	41.2	41.2	41.2
100°	51.3	51.4	51.6	51.7	51.7	51.7	51.7	51.7
102.5°	62.6	62.8	63.0	63.2	63.2	63.2	63.2	63.3
105°	79.7	79.9	80.1	80.4	80.6	80.9	81.1	81.2
107.5°	98.3	98.5	98.7	98.8	98.8	98.8	98.8	98.7
110°	110.7	110.5	110.3	110.4	110.6	110.8	111.0	111.2



TEST NUMBER: P332899-830

CATALOG NUMBER: S124RDIP-S575D365U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	123.9	123.9	123.9	123.9	123.9	123.9	123.9	124.0
115°	144.4	144.3	144.2	144.2	144.1	144.0	143.9	143.9
117.5°	164.1	163.8	163.6	163.4	163.2	163.1	163.0	162.8
120°	177.5	177.1	176.7	176.6	176.7	176.9	177.0	177.2
122.5°	191.1	190.8	190.5	190.2	190.0	189.7	189.5	189.2
125°	210.8	210.8	210.6	210.4	210.3	210.1	210.0	209.8
127.5°	229.9	229.7	229.5	229.4	229.3	229.2	229.0	228.9
130°	243.2	243.0	242.9	242.6	242.3	242.0	241.8	241.5
132.5°	255.7	255.5	255.4	255.2	255.1	255.1	255.0	254.8
135°	274.5	274.4	274.2	274.0	273.8	273.5	273.3	273.1
137.5°	292.7	292.5	292.3	292.2	292.2	292.3	292.3	292.4
140°	304.6	304.5	304.4	304.3	304.3	304.3	304.2	304.1
142.5°	315.9	315.9	315.8	315.8	315.8	315.8	315.8	315.8
145°	332.9	332.8	332.8	332.6	332.4	332.2	332.0	331.8
147.5°	348.4	348.3	348.2	348.2	348.1	348.0	347.9	347.9
150°	358.1	358.1	358.1	358.0	358.0	357.9	357.8	357.7
152.5°	367.2	367.4	367.6	367.5	367.3	367.1	366.9	366.7
155°	379.9	380.2	380.5	380.5	380.2	379.9	379.7	379.4
157.5°	391.2	391.4	391.6	391.6	391.3	391.2	390.9	390.6
160°	398.1	398.3	398.6	398.5	398.1	397.8	397.4	397.0
162.5°	404.4	404.7	405.1	405.1	404.8	404.4	404.1	403.7
165°	412.6	413.0	413.4	413.5	413.2	412.9	412.6	412.4
167.5°	419.5	419.9	420.4	420.4	419.9	419.4	419.0	418.5
170°	423.2	423.7	424.1	424.0	423.6	423.0	422.5	422.0
172.5°	426.0	426.5	427.0	427.0	426.5	425.9	425.5	424.9
175°	429.0	429.5	430.1	430.1	429.5	429.0	428.5	428.0
177.5°	430.6	431.1	431.5	431.5	431.0	430.6	430.1	429.6
180°	430.6	430.6	430.6	430.6	430.6	430.6	430.6	430.6

(END OF REPORT)