

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332900-830

Luminaire Tested: **S124RDIP-S575D365U830-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332900-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIP-S575D365U830-4F0-1E-UDD-F4
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3447.2 lumens
Efficiency: N/A
Efficacy: 125.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 27.5
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332900-830

CATALOG NUMBER: S124RDIP-S575D365U830-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P332900-830

CATALOG NUMBER: S124RDIP-S575D365U830-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	104	104	104	104	91	91	91	80	80	80	69	69	69	64
1	101	97	93	90	95	91	88	85	81	78	76	71	69	67	62	60	59	55
2	93	85	79	74	87	80	75	70	71	67	63	63	59	57	55	52	50	46
3	85	75	68	62	79	71	64	59	63	58	54	56	52	48	49	46	43	40
4	78	67	59	53	73	63	56	51	56	51	46	50	45	42	44	40	38	34
5	71	60	52	46	67	57	49	44	51	45	40	45	40	36	40	36	33	30
6	66	54	46	40	62	51	44	38	46	40	35	41	36	32	36	32	29	26
7	61	49	41	35	57	46	39	34	42	36	31	37	32	29	33	29	26	24
8	57	44	37	31	53	42	35	30	38	32	28	34	29	26	30	26	23	21
9	53	41	33	28	50	39	32	27	35	29	25	31	27	23	28	24	21	19
10	50	37	30	25	47	36	29	24	32	27	23	29	24	21	26	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7733	7733	7733
5°	7750	7656	7703
10°	7702	7564	7564
15°	7614	7405	7350
20°	7491	7196	7064
25°	7337	6951	6774
30°	7185	6693	6413
35°	7019	6427	6050
40°	6817	6122	5658
45°	6632	5819	5259
50°	6420	5471	4835
55°	6194	5111	4376
60°	5945	4713	3907
65°	5717	4216	3446
70°	5384	3670	2924
75°	4966	3044	2380
80°	4328	2320	2180
85°	3668	2103	1973



TEST NUMBER: P332900-830

CATALOG NUMBER: S124RDIP-S575D365U830-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.0	2.6
10°-20°	250.9	7.3
20°-30°	362.3	10.5
30°-40°	410.7	11.9
40°-50°	396.6	11.5
50°-60°	329.8	9.6
60°-70°	227.7	6.6
70°-80°	115.4	3.3
80°-90°	30.6	0.9
90°-100°	122.5	3.6
100°-110°	254.9	7.4
110°-120°	228.3	6.6
120°-130°	192.0	5.6
130°-140°	160.1	4.6
140°-150°	122.3	3.5
150°-160°	86.0	2.5
160°-170°	50.6	1.5
170°-180°	16.5	0.5
0°-30°	703.2	20.4
0°-40°	1113.9	32.3
0°-60°	1840.3	53.4
0°-90°	2214.0	64.2
90°-120°	605.7	17.6
90°-150°	1080.2	31.3
90°-180°	1233.0	35.8
0°-180°	3447.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	958	958	958	958	958	
5°	956	953	945	952	951	91
15°	911	904	886	884	879	257
25°	824	810	780	768	760	379
35°	712	688	652	628	614	445
45°	581	553	510	475	461	448
55°	440	410	363	326	311	394
65°	299	267	221	190	180	295
75°	159	132	98	81	76	168
85°	40	26	23	21	21	45
90°	0	3	6	7	7	2
95°	11	35	272	134	81	12
105°	39	56	218	471	469	42
115°	69	86	195	374	450	68
125°	96	114	194	319	359	85
135°	114	135	192	283	321	88
145°	131	150	191	238	262	82
155°	149	161	186	210	220	69
165°	162	167	178	189	192	46
175°	169	170	171	173	173	16
180°	170	170	170	170	170	



TEST NUMBER: P332900-830

CATALOG NUMBER: S124RDIP-S575D365U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	957.9	957.9	957.9	957.9	957.9	957.9	957.9	957.9	957.9	957.9	957.9
2.5°	960.3	959.7	959.2	958.7	958.2	957.2	955.7	954.3	952.8	951.4	952.8
5°	956.4	955.7	955.1	954.4	953.9	952.5	950.6	948.6	946.6	944.7	946.3
7.5°	947.7	947.1	946.4	945.7	945.0	943.4	940.8	938.3	935.8	933.2	934.2
10°	939.5	938.8	937.9	937.1	936.3	934.4	931.5	928.5	925.6	922.7	923.3
12.5°	929.0	928.0	927.1	926.1	925.2	923.0	919.5	916.1	912.7	909.2	909.6
15°	911.0	909.5	908.0	906.5	905.0	902.3	898.2	894.2	890.0	886.0	885.7
17.5°	889.1	886.9	884.9	882.7	880.6	877.1	872.2	867.3	862.4	857.5	856.7
20°	872.0	870.0	867.8	865.7	863.6	859.8	854.2	848.7	843.1	837.6	836.3
22.5°	853.3	850.9	848.6	846.1	843.8	839.6	833.7	827.7	821.8	815.9	813.9
25°	823.7	820.8	817.7	814.8	811.9	807.1	800.4	793.7	787.0	780.4	777.6
27.5°	792.6	788.9	785.2	781.6	777.8	772.4	765.3	758.2	751.0	743.9	740.5
30°	770.8	766.8	762.7	758.7	754.6	748.7	741.0	733.4	725.7	718.0	714.0
32.5°	748.0	743.4	738.8	734.1	729.6	723.3	715.4	707.5	699.6	691.6	686.9
35°	712.2	707.0	701.7	696.5	691.4	684.7	676.5	668.4	660.2	652.1	646.5
37.5°	673.9	668.5	663.2	657.8	652.3	645.2	636.1	627.1	618.1	609.1	602.9
40°	646.9	641.5	636.1	630.7	625.4	618.0	608.8	599.5	590.2	580.9	574.0
42.5°	621.0	615.5	609.8	604.2	598.5	590.9	581.2	571.5	561.8	552.1	545.2
45°	580.9	574.9	568.8	562.8	556.8	548.8	539.0	529.3	519.5	509.7	501.7
47.5°	539.4	533.2	526.9	520.7	514.4	506.2	496.1	486.0	475.8	465.6	457.3
50°	511.2	504.8	498.5	492.1	485.8	477.4	466.9	456.6	446.1	435.6	427.5
52.5°	482.5	476.3	470.0	463.8	457.5	449.1	438.4	427.7	417.0	406.3	398.0
55°	440.1	433.6	427.1	420.5	414.0	405.4	394.8	384.3	373.6	363.1	354.6
57.5°	398.1	391.3	384.6	377.8	371.0	362.4	351.9	341.5	331.1	320.7	312.1
60°	368.2	361.7	355.2	348.6	342.1	333.7	323.2	312.7	302.4	291.9	283.4
62.5°	341.2	334.4	327.6	320.8	314.1	305.4	294.6	284.0	273.2	262.6	254.8
65°	299.3	292.3	285.2	278.2	271.2	262.5	252.0	241.7	231.2	220.7	213.8
67.5°	255.7	248.9	242.2	235.5	228.8	220.6	210.9	201.2	191.6	181.9	175.9
70°	228.1	221.2	214.4	207.5	200.8	192.7	183.3	174.1	164.8	155.5	150.1
72.5°	198.8	192.6	186.3	180.2	174.0	166.5	157.8	149.0	140.2	131.4	126.9
75°	159.2	153.2	147.1	141.1	135.1	128.2	120.6	112.8	105.2	97.6	93.8
77.5°	118.9	113.9	108.8	103.6	98.5	92.8	86.6	80.5	74.3	68.1	65.9
80°	93.1	88.4	83.7	79.0	74.3	69.5	64.6	59.7	54.8	49.9	49.4
82.5°	70.9	66.5	62.2	57.9	53.5	50.0	47.1	44.3	41.6	38.7	38.4
85°	39.6	36.4	33.1	29.8	26.6	24.7	24.2	23.8	23.2	22.7	22.4
87.5°	13.6	12.6	11.8	10.8	9.9	9.2	9.5	9.4	9.4	9.4	9.2
90°	0.4	1.0	2.0	2.4	2.6	2.6	4.6	4.6	5.4	6.0	5.7
92.5°	3.8	5.6	8.7	12.7	17.6	24.5	41.5	67.3	92.5	105.7	88.0
95°	11.0	12.0	15.4	19.7	27.6	41.7	70.6	125.3	204.9	271.5	279.2
97.5°	19.7	19.7	22.6	26.6	33.5	45.1	67.5	112.6	191.7	286.0	350.7
100°	25.4	25.4	27.6	31.7	38.0	48.6	68.3	105.9	173.9	267.9	353.1
102.5°	30.6	31.2	33.3	36.9	43.1	53.2	71.0	104.1	161.9	245.2	333.1
105°	39.0	40.0	41.7	45.6	51.7	61.3	77.3	104.9	151.6	218.5	296.8
107.5°	48.2	48.8	50.5	54.8	60.5	70.0	84.6	109.9	149.7	203.6	267.5
110°	54.3	55.0	56.6	60.6	66.6	75.6	90.3	113.6	150.2	198.5	252.9



TEST NUMBER: P332900-830

CATALOG NUMBER: S124RDIP-S575D365U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	60.1	60.8	62.8	66.4	72.5	81.4	95.6	117.6	151.8	196.1	244.6
115°	68.6	69.7	71.9	75.3	81.6	90.6	104.0	123.9	154.9	194.9	236.9
117.5°	77.4	78.3	80.4	84.1	90.0	99.3	112.0	130.4	158.2	194.5	233.4
120°	83.3	84.0	86.2	89.9	95.6	104.9	117.6	134.9	160.6	194.5	231.5
122.5°	88.6	89.3	91.6	95.0	101.2	110.3	122.9	139.2	163.0	194.3	229.4
125°	95.6	96.9	99.0	102.6	109.0	118.3	130.3	145.5	166.5	193.9	225.8
127.5°	101.8	102.8	105.3	109.4	116.0	125.5	137.0	151.1	169.5	193.1	221.1
130°	105.3	106.6	109.2	114.2	120.6	130.3	141.6	154.6	171.5	192.8	218.2
132.5°	108.8	109.8	113.3	118.0	124.9	133.9	145.3	158.1	173.4	192.7	215.6
135°	113.6	114.9	118.3	123.9	130.9	139.6	150.5	162.6	176.3	192.2	211.5
137.5°	118.5	119.7	123.4	128.8	136.0	144.3	154.6	165.8	177.9	192.2	208.1
140°	122.0	122.9	126.6	132.2	139.2	147.2	157.2	167.9	179.2	191.9	206.2
142.5°	125.6	126.7	130.1	135.4	142.1	149.9	159.7	169.5	180.3	191.9	204.6
145°	130.9	132.0	135.3	139.9	146.3	153.5	162.2	171.3	180.9	191.2	201.9
147.5°	136.9	137.1	140.2	144.9	150.1	156.7	164.9	172.8	181.3	190.0	199.4
150°	140.5	140.9	143.5	147.6	152.6	158.9	166.3	173.5	181.3	189.2	197.6
152.5°	144.0	144.1	146.8	150.5	155.0	160.8	167.3	174.1	180.7	187.8	195.4
155°	148.9	149.2	151.3	154.6	158.3	163.2	168.9	174.6	179.9	185.9	192.2
157.5°	153.6	153.6	155.5	158.1	161.3	165.2	170.0	174.6	179.0	183.8	189.0
160°	156.6	156.6	157.9	160.2	162.9	166.5	170.6	174.6	178.2	182.2	186.5
162.5°	159.2	159.0	160.0	162.1	164.5	167.4	171.1	174.6	177.4	180.6	184.5
165°	162.2	162.2	162.9	164.6	166.3	168.2	171.3	173.9	175.9	178.2	180.9
167.5°	165.2	164.9	165.2	166.5	167.4	169.0	171.2	173.1	174.3	175.8	177.7
170°	166.5	166.3	166.5	167.6	168.2	169.2	170.9	172.6	173.2	174.2	175.6
172.5°	167.9	167.6	167.6	168.3	168.7	169.5	170.6	172.0	172.2	172.6	173.7
175°	169.2	168.9	168.9	169.2	169.6	169.6	170.2	171.3	170.9	170.9	171.5
177.5°	169.8	169.6	169.3	169.6	169.6	169.6	169.8	170.3	169.8	169.8	170.1
180°	169.6	169.6	169.6	169.6	169.6	169.6	169.6	169.6	169.6	169.6	169.6



TEST NUMBER: P332900-830

CATALOG NUMBER: S124RDIP-S575D365U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	957.9	957.9	957.9	957.9	957.9	957.9	957.9	957.9
2.5°	954.3	955.7	957.2	957.8	957.7	957.5	957.4	957.3
5°	947.9	949.6	951.2	951.9	951.5	951.2	950.8	950.6
7.5°	935.3	936.3	937.5	937.6	937.2	936.6	936.1	935.6
10°	924.0	924.6	925.3	925.3	924.6	924.0	923.3	922.7
12.5°	909.9	910.3	910.8	910.5	909.6	908.7	907.8	906.8
15°	885.3	885.0	884.7	884.0	882.8	881.7	880.5	879.4
17.5°	855.7	854.8	853.8	852.5	850.8	849.1	847.3	845.6
20°	835.0	833.7	832.4	830.7	828.6	826.4	824.3	822.2
22.5°	812.0	810.0	808.0	806.3	804.5	802.8	801.1	799.3
25°	774.9	772.0	769.3	767.1	765.4	763.8	762.2	760.5
27.5°	737.0	733.6	730.2	727.3	724.9	722.6	720.3	717.9
30°	709.9	705.8	701.7	698.4	695.8	693.1	690.6	688.0
32.5°	682.2	677.5	672.7	669.1	666.7	664.2	661.7	659.2
35°	640.9	635.4	629.9	625.7	622.7	619.7	616.8	613.9
37.5°	596.6	590.5	584.3	579.8	576.7	573.8	570.9	568.0
40°	567.2	560.3	553.5	548.7	545.6	542.7	539.8	536.9
42.5°	538.2	531.2	524.2	519.2	516.1	513.1	510.0	507.0
45°	493.8	485.8	477.8	472.3	469.4	466.5	463.5	460.6
47.5°	449.0	440.7	432.4	426.7	423.5	420.3	417.1	413.8
50°	419.3	411.2	403.0	397.5	394.4	391.2	388.1	385.0
52.5°	389.7	381.4	373.2	367.5	364.2	361.0	357.8	354.6
55°	346.1	337.6	329.1	323.4	320.3	317.2	314.1	310.9
57.5°	303.4	294.8	286.3	280.8	278.4	276.1	273.7	271.4
60°	274.9	266.5	258.0	252.5	249.9	247.2	244.7	242.0
62.5°	246.9	239.1	231.3	226.3	224.2	222.2	220.1	218.0
65°	206.8	199.7	192.7	188.2	186.3	184.4	182.4	180.4
67.5°	169.8	163.8	157.8	153.7	151.6	149.4	147.2	145.1
70°	144.8	139.4	133.9	130.4	128.8	127.2	125.5	123.9
72.5°	122.2	117.6	113.0	110.0	108.5	107.0	105.5	104.0
75°	90.0	86.3	82.6	80.2	79.2	78.2	77.3	76.3
77.5°	63.7	61.5	59.3	58.1	57.8	57.5	57.2	56.9
80°	48.9	48.4	47.9	47.6	47.4	47.2	47.1	46.9
82.5°	38.0	37.6	37.3	37.0	36.9	36.7	36.6	36.4
85°	22.1	21.8	21.4	21.3	21.3	21.3	21.3	21.3
87.5°	9.1	9.0	9.0	9.0	9.2	9.4	9.5	9.6
90°	6.0	6.3	6.7	6.7	7.0	7.4	7.0	7.0
92.5°	65.4	49.2	39.2	32.5	28.6	26.8	25.6	25.6
95°	246.9	195.2	150.5	118.3	101.9	91.6	85.6	81.2
97.5°	364.7	345.5	312.9	278.1	254.2	234.2	224.2	217.3
100°	401.7	408.4	392.1	367.4	338.5	318.1	308.1	305.5
102.5°	399.9	432.9	437.6	427.3	409.6	394.9	384.4	382.2
105°	373.1	430.7	463.7	477.4	478.1	475.3	470.7	468.7
107.5°	335.1	396.4	442.8	472.6	489.0	496.6	499.9	500.8
110°	312.2	369.8	418.1	454.7	478.3	492.4	498.3	501.3



TEST NUMBER: P332900-830

CATALOG NUMBER: S124RDIP-S575D365U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	295.3	346.3	391.9	428.6	455.4	472.4	480.8	485.6
115°	278.5	319.4	358.4	390.4	416.7	436.7	447.4	450.1
117.5°	270.2	304.2	334.8	361.9	384.4	401.1	411.9	414.0
120°	266.5	297.5	324.1	347.8	366.7	381.4	390.1	393.8
122.5°	263.3	293.2	317.4	338.2	354.2	366.7	374.1	377.8
125°	257.9	286.4	309.4	327.8	341.1	350.8	357.1	359.1
127.5°	251.2	278.5	301.5	318.9	332.2	340.8	346.2	348.2
130°	245.8	272.2	294.8	312.5	326.1	334.4	339.8	341.8
132.5°	240.3	264.9	287.1	304.7	318.1	327.5	332.6	334.6
135°	232.5	254.2	274.5	291.2	304.4	313.8	319.1	321.1
137.5°	225.6	243.8	261.0	276.0	288.5	297.7	302.1	304.4
140°	221.5	237.1	252.1	266.2	277.9	285.1	289.8	292.5
142.5°	217.8	231.6	244.4	256.6	266.9	273.7	277.9	279.7
145°	212.5	223.9	233.8	243.2	251.5	257.1	260.5	262.1
147.5°	208.2	217.2	225.2	232.5	238.7	243.6	246.0	246.7
150°	205.6	213.2	219.9	225.8	231.2	235.5	237.5	237.8
152.5°	202.6	209.2	215.4	220.3	224.8	228.3	229.5	229.9
155°	198.2	203.5	208.5	212.5	215.8	218.5	219.5	219.5
157.5°	193.5	197.9	202.2	205.4	207.8	209.9	210.5	210.5
160°	190.6	194.2	197.8	200.6	202.6	204.5	204.9	204.9
162.5°	187.7	190.8	193.6	196.0	197.5	199.4	199.8	199.5
165°	183.5	185.6	187.8	189.5	190.9	192.2	191.9	191.5
167.5°	179.6	181.2	183.0	184.0	184.6	185.6	185.5	185.2
170°	177.2	178.2	179.6	180.6	181.3	181.5	181.3	181.3
172.5°	175.1	175.8	176.6	177.4	177.8	178.0	177.8	177.2
175°	172.2	172.6	173.2	173.2	173.2	173.9	173.2	172.6
177.5°	170.3	170.6	170.6	170.9	170.6	170.9	170.3	169.8
180°	169.6	169.6	169.6	169.6	169.6	169.6	169.6	169.6

(END OF REPORT)