

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332928-830

Luminaire Tested: **S124RDIP-S795D365U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332928-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIP-S795D365U830-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 795 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 365 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4404.0 lumens
Efficiency: N/A
Efficacy: 125.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 35
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332928-830

CATALOG NUMBER: S124RDIP-S795D365U830-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332928-830

CATALOG NUMBER: S124RDIP-S795D365U830-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	112	112	112	112	105	105	105	105	94	94	94	83	83	83	73	73	73
1	102	98	94	91	97	93	89	86	83	80	78	74	72	70	65	64	63
2	94	86	80	75	88	82	76	71	73	69	65	65	62	59	58	56	53
3	86	76	69	63	81	72	66	60	65	60	55	58	54	50	52	49	46
4	79	68	60	53	74	64	57	51	58	52	47	52	47	44	46	43	40
5	72	60	52	46	68	58	50	45	52	46	41	47	42	38	42	38	35
6	67	54	46	40	63	52	44	39	47	41	36	43	37	34	38	34	31
7	62	49	41	36	58	47	40	34	43	37	32	39	34	30	35	31	28
8	58	45	37	32	54	43	36	31	39	33	29	36	31	27	32	28	25
9	54	41	34	29	51	40	32	28	36	30	26	33	28	24	30	26	23
10	50	38	31	26	48	36	30	25	33	28	24	30	26	22	28	24	21

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10571	10571	10571
5°	10594	10464	10529
10°	10528	10339	10339
15°	10407	10122	10046
20°	10241	9836	9655
25°	10029	9502	9260
30°	9822	9149	8766
35°	9594	8784	8270
40°	9319	8368	7734
45°	9065	7955	7188
50°	8776	7479	6610
55°	8466	6984	5983
60°	8126	6442	5341
65°	7815	5765	4713
70°	7360	5016	4001
75°	6784	4161	3250
80°	5918	3166	2985
85°	5011	2881	2686



TEST NUMBER: P332928-830

CATALOG NUMBER: S124RDIP-S795D365U830-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	123.0	2.8
10°-20°	343.0	7.8
20°-30°	495.3	11.2
30°-40°	561.4	12.7
40°-50°	542.1	12.3
50°-60°	450.8	10.2
60°-70°	311.3	7.1
70°-80°	157.8	3.6
80°-90°	41.8	0.9
90°-100°	15.2	0.3
100°-110°	97.1	2.2
110°-120°	185.8	4.2
120°-130°	235.8	5.4
130°-140°	252.3	5.7
140°-150°	236.0	5.4
150°-160°	190.3	4.3
160°-170°	122.7	2.8
170°-180°	42.3	1.0
0°-30°	961.2	21.8
0°-40°	1522.6	34.6
0°-60°	2515.6	57.1
0°-90°	3026.4	68.7
90°-120°	298.1	6.8
90°-150°	1022.3	23.2
90°-180°	1378.0	31.3
0°-180°	4404.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1309	1309	1309	1309	1309	
5°	1307	1303	1291	1301	1299	124
15°	1245	1235	1211	1209	1202	351
25°	1126	1106	1067	1050	1040	519
35°	974	940	891	858	839	608
45°	794	756	697	649	630	612
55°	602	560	496	446	425	538
65°	409	365	302	260	247	404
75°	218	180	133	111	104	230
85°	54	35	31	29	29	61
90°	1	5	7	9	10	3
95°	18	8	7	9	10	24
105°	100	102	104	106	95	105
115°	187	188	188	188	188	184
125°	263	264	264	265	265	235
135°	326	326	327	328	329	251
145°	376	377	377	378	378	235
155°	413	413	412	413	412	190
165°	435	434	434	436	433	123
175°	445	444	444	446	443	42
180°	445	445	445	445	445	



TEST NUMBER: P332928-830

CATALOG NUMBER: S124RDIP-S795D365U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1309.4	1309.4	1309.4	1309.4	1309.4	1309.4	1309.4	1309.4	1309.4	1309.4	1309.4
2.5°	1312.6	1311.8	1311.1	1310.4	1309.7	1308.3	1306.4	1304.5	1302.5	1300.5	1302.5
5°	1307.3	1306.5	1305.5	1304.7	1303.7	1302.0	1299.3	1296.7	1293.9	1291.3	1293.5
7.5°	1295.5	1294.6	1293.6	1292.7	1291.8	1289.6	1286.1	1282.6	1279.1	1275.6	1277.1
10°	1284.3	1283.2	1282.0	1280.9	1279.8	1277.2	1273.3	1269.2	1265.3	1261.2	1262.1
12.5°	1269.8	1268.6	1267.2	1265.9	1264.7	1261.7	1257.0	1252.2	1247.5	1242.7	1243.3
15°	1245.2	1243.2	1241.1	1239.2	1237.2	1233.4	1227.8	1222.2	1216.6	1211.1	1210.6
17.5°	1215.3	1212.4	1209.5	1206.6	1203.7	1198.9	1192.2	1185.5	1178.8	1172.1	1170.9
20°	1192.0	1189.1	1186.3	1183.4	1180.4	1175.3	1167.6	1160.1	1152.4	1144.9	1143.1
22.5°	1166.4	1163.1	1159.9	1156.6	1153.4	1147.6	1139.5	1131.4	1123.3	1115.2	1112.6
25°	1125.9	1121.8	1117.9	1113.8	1109.8	1103.2	1094.1	1085.0	1075.8	1066.7	1062.9
27.5°	1083.4	1078.4	1073.3	1068.3	1063.2	1055.8	1046.0	1036.3	1026.5	1016.8	1012.1
30°	1053.7	1048.1	1042.5	1037.0	1031.4	1023.4	1013.0	1002.5	991.9	981.5	975.9
32.5°	1022.4	1016.2	1009.8	1003.5	997.3	988.7	977.9	967.0	956.2	945.4	939.0
35°	973.5	966.4	959.2	952.1	945.0	935.9	924.7	913.5	902.4	891.3	883.7
37.5°	921.1	913.8	906.4	899.1	891.7	881.9	869.6	857.2	844.9	832.5	824.1
40°	884.3	876.9	869.6	862.2	854.9	844.8	832.1	819.4	806.7	794.0	784.7
42.5°	848.9	841.2	833.6	825.9	818.1	807.7	794.5	781.2	768.0	754.7	745.2
45°	794.0	785.8	777.5	769.3	761.0	750.3	736.9	723.5	710.1	696.8	685.9
47.5°	737.3	728.8	720.3	711.7	703.2	692.0	678.2	664.2	650.4	636.4	625.1
50°	698.8	690.1	681.4	672.7	664.0	652.5	638.3	624.1	609.7	595.5	584.4
52.5°	659.5	651.0	642.4	634.0	625.5	613.9	599.3	584.7	570.0	555.4	544.1
55°	601.5	592.6	583.7	574.8	565.9	554.2	539.7	525.2	510.8	496.2	484.7
57.5°	544.2	534.9	525.7	516.4	507.1	495.3	481.1	466.8	452.6	438.3	426.6
60°	503.3	494.4	485.5	476.5	467.6	456.1	441.8	427.5	413.3	399.0	387.4
62.5°	466.4	457.1	447.9	438.6	429.3	417.4	402.7	388.1	373.5	358.9	348.2
65°	409.1	399.4	389.8	380.3	370.7	358.8	344.5	330.3	316.0	301.8	292.2
67.5°	349.5	340.4	331.1	322.0	312.7	301.6	288.3	275.1	261.8	248.6	240.3
70°	311.8	302.5	293.0	283.7	274.4	263.3	250.6	237.9	225.3	212.5	205.2
72.5°	271.7	263.3	254.8	246.3	237.8	227.6	215.7	203.6	191.6	179.6	173.3
75°	217.5	209.3	201.0	192.8	184.5	175.2	164.8	154.3	143.8	133.4	128.2
77.5°	162.6	155.6	148.6	141.7	134.6	126.9	118.5	110.0	101.5	93.0	90.0
80°	127.3	120.8	114.4	107.9	101.5	94.9	88.2	81.5	74.8	68.1	67.5
82.5°	96.9	91.0	85.0	79.1	73.1	68.2	64.5	60.6	56.7	53.0	52.4
85°	54.1	49.7	45.2	40.8	36.3	33.7	33.1	32.4	31.8	31.1	30.6
87.5°	18.7	17.3	16.1	14.9	13.6	12.9	12.9	12.8	12.7	12.7	12.6
90°	1.0	1.8	2.6	3.5	4.2	5.0	5.6	6.1	6.7	7.4	7.7
92.5°	4.2	4.2	4.2	4.3	4.3	4.7	5.3	5.8	6.5	7.1	7.5
95°	18.3	15.8	13.3	10.7	8.3	7.1	7.1	7.2	7.3	7.4	7.7
97.5°	38.9	40.4	42.0	43.6	45.1	41.8	33.6	25.4	17.1	8.8	8.9
100°	54.7	56.0	57.3	58.6	59.9	55.5	45.3	35.1	24.9	14.7	13.4
102.5°	72.2	73.2	74.2	75.1	76.2	76.0	74.6	73.3	71.9	70.6	57.0
105°	100.3	100.7	101.1	101.6	102.1	102.5	102.8	103.2	103.6	104.0	104.6
107.5°	126.3	126.5	126.8	127.0	127.2	127.5	128.1	128.6	129.0	129.6	129.9
110°	143.9	144.1	144.3	144.6	144.8	145.2	145.5	146.0	146.5	146.9	147.0



TEST NUMBER: P332928-830

CATALOG NUMBER: S124RDIP-S795D365U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	161.0	161.4	161.7	162.1	162.6	162.9	163.1	163.2	163.4	163.7	163.6
115°	187.2	187.5	187.7	187.8	188.1	188.1	188.1	188.0	187.9	187.8	188.0
117.5°	210.8	211.1	211.4	211.8	212.1	212.3	212.4	212.6	212.7	212.9	212.9
120°	226.9	227.2	227.4	227.7	228.0	228.1	228.1	228.0	227.9	227.8	228.0
122.5°	241.8	242.0	242.1	242.3	242.5	242.6	242.7	242.8	242.9	243.1	243.1
125°	263.2	263.4	263.7	264.0	264.4	264.4	264.3	264.1	264.0	263.8	264.0
127.5°	283.4	283.5	283.5	283.6	283.7	283.9	284.3	284.6	284.9	285.3	285.2
130°	296.4	296.5	296.6	296.7	296.8	296.9	297.1	297.4	297.6	297.8	297.8
132.5°	308.5	308.6	308.7	308.9	309.0	309.2	309.4	309.7	310.0	310.3	310.4
135°	326.4	326.4	326.3	326.2	326.1	326.2	326.6	326.9	327.2	327.4	327.6
137.5°	342.3	342.4	342.4	342.4	342.5	342.7	343.0	343.3	343.7	343.9	344.1
140°	352.8	352.9	353.1	353.2	353.4	353.5	353.6	353.8	353.9	354.1	354.3
142.5°	362.1	362.3	362.6	362.9	363.2	363.4	363.4	363.5	363.6	363.7	363.8
145°	376.5	376.6	376.8	377.1	377.3	377.4	377.4	377.4	377.4	377.4	377.5
147.5°	387.8	388.2	388.6	389.1	389.5	389.6	389.6	389.5	389.4	389.4	389.4
150°	396.1	396.3	396.6	397.0	397.3	397.4	397.3	397.2	397.1	397.1	397.1
152.5°	403.0	403.2	403.5	403.7	404.0	404.0	403.9	403.7	403.6	403.5	403.6
155°	412.7	412.8	412.8	412.9	413.0	412.9	412.7	412.5	412.3	412.1	412.4
157.5°	420.9	420.8	420.8	420.8	420.8	420.6	420.4	420.1	419.8	419.6	420.0
160°	425.7	425.5	425.3	425.1	424.8	424.7	424.6	424.5	424.4	424.3	424.8
162.5°	430.0	429.7	429.4	429.1	428.9	428.7	428.6	428.5	428.5	428.4	428.9
165°	435.4	435.0	434.6	434.2	433.9	433.7	433.7	433.7	433.7	433.7	434.3
167.5°	439.6	439.2	438.8	438.5	438.1	437.9	437.8	437.8	437.7	437.7	438.4
170°	442.1	441.6	441.1	440.7	440.3	440.1	440.2	440.3	440.3	440.4	440.9
172.5°	443.7	443.2	442.7	442.3	441.9	441.7	441.8	441.9	441.9	442.0	442.5
175°	445.4	444.9	444.5	444.0	443.6	443.4	443.5	443.6	443.7	443.7	444.4
177.5°	446.2	445.7	445.4	444.9	444.5	444.3	444.5	444.6	444.7	444.8	445.4
180°	445.4	445.4	445.4	445.4	445.4	445.4	445.4	445.4	445.4	445.4	445.4



TEST NUMBER: P332928-830

CATALOG NUMBER: S124RDIP-S795D365U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1309.4	1309.4	1309.4	1309.4	1309.4	1309.4	1309.4	1309.4
2.5°	1304.5	1306.4	1308.3	1309.3	1309.1	1308.9	1308.7	1308.5
5°	1295.7	1298.0	1300.2	1301.1	1300.6	1300.2	1299.8	1299.3
7.5°	1278.5	1280.0	1281.4	1281.7	1281.0	1280.3	1279.6	1278.8
10°	1263.0	1263.9	1264.8	1264.8	1263.9	1263.0	1262.1	1261.2
12.5°	1243.9	1244.3	1244.9	1244.5	1243.3	1242.1	1240.8	1239.5
15°	1210.2	1209.8	1209.3	1208.3	1206.7	1205.1	1203.6	1202.0
17.5°	1169.7	1168.5	1167.2	1165.4	1163.0	1160.6	1158.3	1155.9
20°	1141.3	1139.5	1137.7	1135.5	1132.6	1129.6	1126.7	1123.9
22.5°	1109.9	1107.2	1104.6	1102.0	1099.7	1097.3	1095.0	1092.6
25°	1059.1	1055.4	1051.6	1048.6	1046.3	1044.1	1041.9	1039.6
27.5°	1007.4	1002.8	998.1	994.1	990.9	987.7	984.5	981.3
30°	970.3	964.8	959.2	954.6	951.1	947.5	944.0	940.4
32.5°	932.5	926.0	919.5	914.6	911.3	907.9	904.5	901.1
35°	876.1	868.6	861.0	855.2	851.2	847.2	843.1	839.1
37.5°	815.6	807.1	798.6	792.4	788.4	784.4	780.4	776.4
40°	775.3	765.9	756.6	749.9	745.9	741.9	737.9	733.9
42.5°	735.7	726.1	716.6	709.7	705.5	701.3	697.2	693.0
45°	675.0	664.0	653.1	645.6	641.6	637.6	633.6	629.6
47.5°	613.8	602.5	591.2	583.2	578.9	574.5	570.0	565.6
50°	573.3	562.1	550.9	543.3	539.0	534.8	530.6	526.3
52.5°	532.8	521.5	510.1	502.3	497.9	493.4	489.1	484.7
55°	473.1	461.5	450.0	442.1	437.8	433.6	429.3	425.1
57.5°	414.8	403.0	391.2	383.8	380.6	377.4	374.2	371.0
60°	375.9	364.3	352.7	345.1	341.6	338.0	334.4	330.8
62.5°	337.5	326.9	316.1	309.3	306.5	303.7	300.8	297.9
65°	282.6	273.1	263.4	257.3	254.7	251.9	249.3	246.7
67.5°	232.1	223.9	215.7	210.1	207.2	204.2	201.2	198.3
70°	197.8	190.5	183.1	178.3	176.2	173.9	171.6	169.5
72.5°	167.1	160.8	154.5	150.3	148.4	146.3	144.2	142.1
75°	123.1	118.0	112.8	109.6	108.3	107.0	105.6	104.2
77.5°	87.1	84.1	81.1	79.4	79.0	78.6	78.2	77.8
80°	66.8	66.2	65.5	65.0	64.8	64.6	64.4	64.2
82.5°	51.9	51.5	51.0	50.6	50.4	50.1	50.0	49.8
85°	30.2	29.8	29.3	29.0	29.0	29.0	29.0	29.0
87.5°	12.5	12.4	12.3	12.4	12.6	12.8	13.0	13.2
90°	8.2	8.7	9.1	9.4	9.5	9.7	9.8	10.0
92.5°	7.9	8.4	8.9	9.0	9.1	9.1	9.1	9.2
95°	8.2	8.7	9.1	9.3	9.4	9.5	9.6	9.6
97.5°	8.9	9.0	9.0	9.0	9.1	9.1	9.2	9.3
100°	12.2	10.8	9.6	9.0	9.1	9.1	9.2	9.3
102.5°	43.5	29.9	16.3	9.5	9.5	9.5	9.6	9.6
105°	105.3	105.9	106.6	105.6	102.9	100.3	97.6	94.9
107.5°	130.3	130.5	130.9	131.2	131.5	131.8	132.1	132.3
110°	147.2	147.3	147.5	147.7	147.9	148.2	148.4	148.5



TEST NUMBER: P332928-830

CATALOG NUMBER: S124RDIP-S795D365U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	163.6	163.6	163.5	163.7	164.0	164.3	164.6	164.9
115°	188.1	188.3	188.5	188.5	188.5	188.5	188.5	188.5
117.5°	212.8	212.8	212.8	212.7	212.7	212.7	212.7	212.6
120°	228.1	228.3	228.5	228.5	228.3	228.1	228.0	227.8
122.5°	243.2	243.3	243.4	243.4	243.2	243.1	242.9	242.8
125°	264.3	264.5	264.7	264.9	264.9	265.0	265.0	265.1
127.5°	285.2	285.1	285.1	285.0	285.0	284.9	284.8	284.8
130°	297.9	298.0	298.1	298.1	298.1	298.1	298.1	298.1
132.5°	310.5	310.6	310.7	310.7	310.6	310.5	310.5	310.4
135°	327.7	327.9	328.0	328.2	328.3	328.5	328.7	328.8
137.5°	344.3	344.5	344.6	344.7	344.6	344.6	344.5	344.5
140°	354.5	354.8	355.0	355.2	355.2	355.2	355.3	355.4
142.5°	364.0	364.2	364.3	364.4	364.5	364.5	364.5	364.5
145°	377.6	377.7	377.7	377.8	378.0	378.1	378.2	378.4
147.5°	389.5	389.6	389.6	389.6	389.7	389.7	389.8	389.9
150°	397.1	397.1	397.1	397.1	397.2	397.3	397.3	397.4
152.5°	403.7	403.8	404.0	404.0	403.9	403.9	403.9	403.8
155°	412.6	412.9	413.2	413.3	413.0	412.8	412.6	412.4
157.5°	420.4	420.8	421.1	421.1	420.8	420.4	420.0	419.6
160°	425.3	425.7	426.1	426.1	425.7	425.3	424.8	424.3
162.5°	429.2	429.7	430.2	430.1	429.6	429.1	428.6	428.1
165°	434.9	435.5	436.1	436.0	435.4	434.7	434.0	433.4
167.5°	439.0	439.7	440.3	440.3	439.5	438.8	438.0	437.3
170°	441.6	442.1	442.7	442.6	442.0	441.2	440.5	439.7
172.5°	443.2	443.7	444.3	444.2	443.5	442.6	441.9	441.0
175°	445.1	445.7	446.4	446.3	445.4	444.5	443.6	442.7
177.5°	445.8	446.3	446.8	446.6	445.9	445.2	444.5	443.7
180°	445.4	445.4	445.4	445.4	445.4	445.4	445.4	445.4

(END OF REPORT)