

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332654-930

Luminaire Tested: **S124DIP-S1020D1035U930-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332654-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124DIP-S1020D1035U930-4F0-1E-UDD-A4  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1020 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 1035 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6769.2 lumens  
Efficiency: N/A  
Efficacy: 111.9 lumens/watt  
Spacing Criteria (0/90/45): 1.31 / 1.23 / 1.41  
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 60.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332654-930

CATALOG NUMBER: S124DIP-S1020D1035U930-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P332654-930

CATALOG NUMBER: S124DIP-S1020D1035U930-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	55
1	99	95	91	88	92	88	85	82	76	74	71	65	63	61	54	53	52	47
2	91	83	77	72	84	78	72	68	67	63	60	57	54	52	48	46	44	40
3	83	73	66	60	77	69	62	57	59	54	50	51	47	44	43	40	38	34
4	76	65	57	51	70	61	54	49	53	47	43	45	41	38	39	35	33	29
5	70	58	50	44	65	54	47	42	47	42	37	41	37	33	35	32	29	26
6	64	52	44	38	60	49	42	37	43	37	33	37	33	29	32	28	26	23
7	60	47	39	34	55	44	37	32	39	33	29	34	29	26	29	25	23	20
8	55	43	35	30	51	40	33	29	36	30	26	31	26	23	27	23	20	18
9	52	39	32	27	48	37	30	26	33	27	23	29	24	21	25	21	18	16
10	48	36	29	24	45	34	27	23	30	25	21	26	22	19	23	19	17	15

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	10984	10984	10984	10984
5°	12935	11012	9720	11012
10°	15488	10964	8751	10964
15°	18324	10853	8037	10853
20°	20405	10740	7399	10740
25°	20735	10573	6959	10573
30°	17643	10413	6820	10413
35°	13565	10154	6821	10154
40°	10572	9848	6949	9848
45°	8816	9388	7066	9388
50°	7759	8828	7304	8828
55°	7108	8155	7600	8155
60°	6660	7553	7953	7553
65°	6202	6879	8246	6879
70°	5667	6212	8434	6212
75°	5062	5468	8334	5468
80°	4245	4482	8071	4482
85°	3131	3242	7725	3242



TEST NUMBER: P332654-930

CATALOG NUMBER: S124DIP-S1020D1035U930-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	132.5	2.0
10°-20°	408.6	6.0
20°-30°	647.9	9.6
30°-40°	721.0	10.7
40°-50°	656.3	9.7
50°-60°	536.3	7.9
60°-70°	382.9	5.7
70°-80°	210.8	3.1
80°-90°	59.8	0.9
90°-100°	299.2	4.4
100°-110°	622.8	9.2
110°-120°	557.8	8.2
120°-130°	469.2	6.9
130°-140°	391.2	5.8
140°-150°	298.9	4.4
150°-160°	210.1	3.1
160°-170°	123.6	1.8
170°-180°	40.2	0.6
0°-30°	1189.0	17.6
0°-40°	1910.0	28.2
0°-60°	3102.6	45.8
0°-90°	3756.2	55.5
90°-120°	1479.8	21.9
90°-150°	2639.2	39.0
90°-180°	3013.0	44.5
0°-180°	6769.2	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1361	1361	1361	1361	1361	
5°	1596	1359	1199	1359	1596	162
15°	2192	1299	962	1299	2192	619
25°	2328	1187	781	1187	2328	1026
35°	1376	1030	692	1030	1376	874
45°	772	822	619	822	772	608
55°	505	579	540	579	505	456
65°	325	360	432	360	325	321
75°	162	175	267	175	162	173
85°	34	35	83	35	34	42
90°	17	1	17	1	17	15
95°	199	27	199	27	199	308
105°	1145	95	1145	95	1145	1132
115°	1100	168	1100	168	1100	1092
125°	877	234	877	234	877	797
135°	785	278	785	278	785	606
145°	641	320	641	320	641	406
155°	536	364	536	364	536	250
165°	468	396	468	396	468	134
175°	422	413	422	413	422	41
180°	414	414	414	414	414	



TEST NUMBER: P332654-930

CATALOG NUMBER: S124DIP-S1020D1035U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1360.6	1360.6	1360.6	1360.6	1360.6	1360.6	1360.6	1360.6	1360.6	1360.6	1360.6
2.5°	1448.1	1447.6	1443.1	1442.2	1439.0	1435.0	1434.1	1426.9	1412.4	1405.7	1403.9
5°	1596.2	1607.4	1592.8	1590.0	1588.3	1569.7	1560.1	1548.8	1522.9	1507.7	1495.8
7.5°	1772.9	1774.3	1767.9	1762.7	1748.3	1732.1	1707.8	1681.9	1651.0	1618.9	1594.6
10°	1889.3	1893.8	1886.4	1885.3	1856.6	1838.5	1802.5	1772.1	1737.1	1698.2	1662.7
12.5°	2011.9	2005.6	2001.9	1977.8	1972.5	1939.5	1897.6	1866.3	1812.4	1767.7	1720.4
15°	2192.5	2180.1	2172.2	2138.9	2122.6	2077.0	2032.4	1998.1	1927.6	1860.5	1809.8
17.5°	2298.4	2310.9	2292.6	2278.9	2236.7	2204.7	2159.2	2087.0	2031.9	1948.6	1884.6
20°	2375.1	2376.2	2366.1	2352.0	2318.7	2278.2	2228.5	2149.6	2083.7	2000.8	1912.9
22.5°	2395.8	2396.1	2391.8	2378.6	2353.4	2320.5	2270.5	2204.7	2124.8	2034.7	1946.8
25°	2327.8	2325.5	2330.6	2345.2	2335.7	2325.5	2296.8	2247.7	2173.3	2078.0	1983.4
27.5°	2074.8	2090.3	2119.0	2155.1	2189.8	2216.3	2223.7	2213.7	2167.6	2089.2	1990.1
30°	1892.6	1911.8	1933.2	1969.3	2039.1	2079.2	2123.2	2156.4	2137.8	2075.3	1982.8
32.5°	1692.5	1697.2	1729.0	1770.0	1834.0	1911.0	1980.7	2048.2	2070.6	2037.8	1960.7
35°	1376.4	1384.2	1418.6	1459.2	1537.6	1631.7	1736.5	1830.1	1907.3	1938.3	1898.8
37.5°	1123.2	1145.8	1170.1	1213.7	1282.7	1367.4	1476.3	1597.4	1712.5	1789.6	1802.7
40°	1003.2	1017.3	1034.8	1068.0	1126.7	1210.1	1303.7	1442.3	1564.6	1675.1	1711.2
42.5°	908.6	916.8	927.5	957.6	1002.2	1085.2	1170.6	1292.6	1415.4	1547.4	1607.9
45°	772.2	780.6	798.7	816.1	849.9	907.4	986.9	1087.2	1210.6	1338.1	1449.6
47.5°	673.6	679.1	689.7	708.5	737.2	775.1	839.8	923.6	1038.0	1161.6	1280.5
50°	617.8	622.2	630.7	647.6	669.6	703.4	756.4	834.7	924.3	1048.9	1165.6
52.5°	573.6	575.4	581.6	593.0	610.5	639.0	682.4	747.2	830.5	941.6	1057.8
55°	505.0	507.3	512.9	521.4	536.5	554.6	587.8	636.3	709.1	805.4	906.3
57.5°	448.7	450.2	454.9	458.2	470.8	485.4	510.9	545.6	600.7	682.4	772.5
60°	412.5	411.5	417.1	419.9	428.4	440.8	460.5	493.7	541.6	607.6	690.4
62.5°	377.4	375.9	380.6	384.3	389.1	399.7	415.8	441.9	480.8	540.4	612.0
65°	324.7	322.4	325.2	329.7	334.2	339.9	351.7	374.8	405.8	448.7	503.3
67.5°	271.7	274.0	274.5	276.7	279.3	287.0	295.1	311.4	333.3	367.6	413.9
70°	240.1	240.7	243.0	243.0	244.6	251.4	258.1	267.7	289.1	320.7	358.5
72.5°	208.6	210.9	210.0	211.8	213.0	217.5	222.5	231.6	249.9	273.4	305.2
75°	162.3	164.0	164.0	164.6	166.2	168.0	171.9	178.6	191.6	209.1	231.1
77.5°	118.4	118.6	119.4	121.4	121.4	124.1	127.0	132.5	138.8	150.8	164.2
80°	91.3	92.5	91.9	93.0	93.0	95.2	96.4	103.1	106.0	113.8	124.6
82.5°	66.9	68.1	68.0	69.5	70.4	70.9	72.5	75.2	78.0	85.0	89.4
85°	33.8	35.0	33.8	35.0	36.6	37.2	38.9	39.5	41.7	43.4	47.4
87.5°	13.4	14.7	14.8	15.2	15.9	16.3	16.6	16.0	17.6	18.3	19.7
90°	17.1	17.1	17.9	17.1	16.3	16.3	15.5	14.7	13.9	14.7	13.0
92.5°	62.7	62.7	65.5	69.9	79.4	95.7	120.3	159.9	215.1	258.2	225.9
95°	198.6	209.2	223.8	249.1	288.9	367.9	477.0	603.1	682.1	663.3	500.6
97.5°	530.8	547.8	572.2	621.2	679.6	764.6	844.2	891.1	856.9	698.6	468.5
100°	746.4	752.8	777.3	827.0	897.7	958.0	997.8	981.6	862.7	654.4	424.9
102.5°	933.9	939.1	964.8	1000.8	1044.2	1069.3	1057.8	977.1	813.9	599.1	395.6
105°	1145.2	1150.1	1161.5	1168.0	1166.4	1132.9	1052.4	911.6	725.2	533.9	370.3
107.5°	1223.7	1221.6	1213.4	1194.8	1154.6	1082.1	968.6	818.6	653.5	497.5	365.7
110°	1225.0	1217.6	1203.0	1168.8	1111.0	1021.5	903.4	762.6	617.8	485.1	367.0



TEST NUMBER: P332654-930

CATALOG NUMBER: S124DIP-S1020D1035U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1186.5	1174.7	1154.1	1112.8	1047.2	957.7	846.1	721.6	597.6	479.2	371.0
115°	1099.6	1093.1	1067.1	1018.2	953.9	875.8	780.6	680.4	578.7	476.1	378.5
117.5°	1011.5	1006.5	980.2	939.1	884.3	818.0	743.1	660.2	570.2	475.3	386.5
120°	962.1	953.1	932.0	896.1	849.7	792.0	726.8	651.1	565.7	475.3	392.3
122.5°	923.0	914.0	896.1	865.5	826.3	775.7	716.4	643.4	560.4	474.7	398.2
125°	877.4	872.5	857.0	833.5	800.9	756.1	699.9	630.0	551.9	473.7	407.0
127.5°	850.7	845.8	832.8	811.8	779.1	736.6	680.6	613.7	540.3	471.9	413.9
130°	835.1	830.2	817.2	796.8	763.4	720.3	665.0	600.7	533.1	471.2	419.1
132.5°	817.5	812.6	800.2	777.3	744.6	701.4	647.4	587.0	526.6	470.6	423.7
135°	784.6	779.8	766.7	744.0	711.3	670.7	621.0	568.1	516.8	469.6	430.6
137.5°	744.0	738.1	727.3	704.8	674.4	637.6	595.8	551.1	508.3	469.4	434.6
140°	714.6	708.1	696.8	678.8	650.3	616.1	579.5	541.3	503.9	468.8	437.9
142.5°	683.4	678.8	668.7	652.1	626.9	597.3	565.8	532.1	499.9	468.8	440.5
145°	640.6	636.5	628.4	614.5	594.2	571.4	547.0	519.3	493.3	467.2	442.0
147.5°	602.6	601.2	595.0	583.1	568.1	550.2	530.7	508.7	487.2	464.2	442.8
150°	581.1	580.3	575.4	564.8	551.9	537.2	520.9	502.2	482.7	462.3	442.8
152.5°	561.6	560.8	557.8	549.3	538.2	526.1	511.1	495.0	477.4	459.0	441.5
155°	536.4	536.4	533.9	527.4	519.3	509.5	497.3	484.3	469.6	454.2	439.5
157.5°	514.2	514.2	512.7	507.8	501.7	493.9	483.6	472.7	461.6	449.1	437.4
160°	500.6	500.6	499.8	494.9	490.0	483.5	474.5	465.5	455.8	445.2	435.5
162.5°	487.5	488.2	487.4	482.5	478.9	473.0	466.0	458.4	450.6	441.3	433.5
165°	468.0	468.8	469.6	466.4	463.1	459.0	453.4	448.5	442.0	435.5	429.7
167.5°	452.6	453.2	453.4	451.3	449.6	447.2	442.6	438.9	434.1	429.6	425.8
170°	442.8	442.8	443.6	442.8	441.2	438.7	435.5	433.0	428.9	425.7	423.2
172.5°	433.0	434.3	435.1	434.3	433.3	431.5	429.6	427.8	424.4	421.8	420.6
175°	421.6	423.2	424.9	423.2	423.2	423.2	421.6	420.8	419.1	417.5	417.5
177.5°	414.9	416.2	417.5	416.9	417.5	416.9	416.9	416.2	415.6	414.9	414.9
180°	414.3	414.3	414.3	414.3	414.3	414.3	414.3	414.3	414.3	414.3	414.3



TEST NUMBER: P332654-930

CATALOG NUMBER: S124DIP-S1020D1035U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1360.6	1360.6	1360.6	1360.6	1360.6	1360.6	1360.6	1360.6	1360.6	1360.6	1360.6
2.5°	1404.4	1398.0	1393.5	1389.9	1380.0	1374.1	1369.6	1363.3	1356.1	1348.4	1339.0
5°	1484.0	1464.8	1450.7	1429.4	1409.1	1392.1	1374.7	1358.9	1339.7	1318.9	1303.7
7.5°	1567.7	1539.3	1502.8	1471.0	1435.4	1404.4	1376.7	1348.3	1318.7	1290.1	1263.9
10°	1621.0	1584.4	1543.8	1495.8	1450.7	1410.7	1373.5	1337.5	1302.5	1267.5	1237.7
12.5°	1678.2	1632.6	1572.6	1516.6	1466.1	1412.6	1367.7	1323.5	1281.3	1244.6	1209.7
15°	1755.1	1689.1	1619.8	1544.9	1478.4	1415.8	1354.4	1298.6	1251.2	1202.7	1169.0
17.5°	1802.4	1720.8	1641.5	1563.2	1482.6	1403.8	1337.5	1273.1	1213.8	1165.7	1123.1
20°	1833.4	1752.3	1653.7	1575.3	1479.5	1398.3	1321.7	1250.1	1188.1	1136.9	1092.8
22.5°	1860.5	1766.8	1668.1	1565.0	1469.6	1383.5	1299.6	1227.6	1164.2	1110.2	1068.0
25°	1875.2	1767.5	1660.4	1557.9	1449.6	1347.6	1271.5	1187.0	1119.3	1062.4	1017.3
27.5°	1876.7	1761.6	1640.5	1526.5	1414.8	1319.8	1223.8	1148.2	1078.0	1017.8	974.5
30°	1871.8	1751.8	1621.5	1498.1	1385.9	1282.8	1199.4	1117.1	1045.5	985.8	940.7
32.5°	1856.0	1731.0	1597.2	1466.6	1350.3	1249.4	1163.4	1085.1	1015.3	956.4	909.1
35°	1810.4	1686.9	1544.3	1408.5	1289.6	1187.6	1109.8	1030.3	960.4	904.6	859.0
37.5°	1739.0	1627.4	1482.5	1341.9	1225.1	1122.6	1045.5	973.7	910.7	854.0	807.2
40°	1676.7	1578.7	1433.3	1296.3	1170.1	1072.6	1000.5	934.5	872.0	818.4	773.9
42.5°	1605.1	1519.6	1385.5	1240.4	1118.7	1020.8	950.4	891.2	832.3	782.8	738.3
45°	1477.2	1420.9	1294.6	1160.5	1033.7	941.3	874.2	822.3	772.7	724.2	687.1
47.5°	1330.2	1302.3	1196.0	1068.6	948.3	857.1	799.0	751.1	707.6	666.5	633.7
50°	1231.5	1218.0	1126.1	1003.2	888.3	802.6	744.0	702.9	665.6	629.6	598.6
52.5°	1134.1	1133.7	1050.8	938.3	831.9	749.4	691.2	652.8	620.5	591.3	563.4
55°	985.2	1001.0	936.2	835.8	740.6	666.2	613.8	579.4	556.8	532.6	511.8
57.5°	848.5	874.7	821.2	732.8	653.4	584.8	539.2	513.3	489.3	474.7	459.5
60°	759.2	784.0	742.3	667.9	593.0	534.3	490.9	467.8	446.9	436.8	426.1
62.5°	679.9	702.0	671.1	602.1	537.0	480.6	444.0	421.8	407.7	396.6	389.6
65°	566.5	585.1	558.6	508.4	452.6	407.5	377.6	360.1	346.7	342.1	334.2
67.5°	457.9	474.8	460.5	417.8	373.1	339.0	315.6	298.8	290.8	286.9	281.3
70°	393.4	410.3	395.1	357.9	323.5	294.8	272.8	263.2	254.8	253.1	245.2
72.5°	338.8	350.3	335.2	306.1	276.6	252.4	235.4	225.3	220.9	217.9	213.6
75°	254.2	264.3	254.2	231.6	210.8	193.9	179.2	175.3	170.2	168.5	165.7
77.5°	179.9	188.7	180.9	166.8	151.2	138.2	130.3	125.2	124.1	121.2	122.5
80°	137.5	143.2	135.8	126.3	113.8	104.8	99.2	96.4	93.0	91.9	94.1
82.5°	98.7	101.3	97.5	91.1	81.9	76.0	72.2	68.9	68.2	68.4	68.4
85°	51.3	50.7	50.1	44.5	41.7	37.7	35.5	35.0	34.4	35.5	36.6
87.5°	19.4	19.9	18.4	16.6	15.1	13.6	12.6	11.9	12.6	13.6	14.2
90°	11.4	11.4	6.5	6.5	5.7	4.9	2.4	0.8	2.4	4.9	5.7
92.5°	164.4	101.3	59.9	43.0	31.1	21.2	13.5	9.3	13.5	21.2	31.1
95°	306.1	172.5	101.7	67.6	48.0	37.4	29.3	26.8	29.3	37.4	48.0
97.5°	275.1	164.9	110.4	81.7	65.0	55.2	48.2	48.2	48.2	55.2	65.0
100°	258.9	166.9	118.9	92.8	77.3	67.6	61.9	61.9	61.9	67.6	77.3
102.5°	254.3	173.3	129.9	105.2	90.3	81.2	76.1	74.8	76.1	81.2	90.3
105°	256.4	188.8	149.8	126.1	111.5	101.7	97.7	95.2	97.7	101.7	111.5
107.5°	268.4	206.9	171.0	147.8	133.8	123.4	119.4	117.7	119.4	123.4	133.8
110°	277.5	220.5	184.7	162.8	148.1	138.4	134.3	132.6	134.3	138.4	148.1





TEST NUMBER: P332654-930

CATALOG NUMBER: S124DIP-S1020D1035U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	287.3	233.6	199.1	177.1	162.5	153.4	148.6	147.0	148.6	153.4	162.5
115°	302.8	254.0	221.4	199.4	183.9	175.8	170.1	167.7	170.1	175.8	183.9
117.5°	318.5	273.6	242.7	219.9	205.5	196.5	191.4	189.1	191.4	196.5	205.5
120°	329.6	287.3	256.4	233.6	219.7	210.8	205.1	203.5	205.1	210.8	219.7
122.5°	340.1	300.4	269.4	247.3	232.1	223.8	218.1	216.5	218.1	223.8	232.1
125°	355.7	318.2	288.9	266.1	250.7	241.7	236.8	233.6	236.8	241.7	250.7
127.5°	369.2	334.8	306.6	283.6	267.4	257.2	251.4	248.7	251.4	257.2	267.4
130°	377.6	345.9	318.2	294.6	279.2	266.9	260.5	257.2	260.5	266.9	279.2
132.5°	386.1	355.1	327.3	305.1	288.3	276.7	268.2	265.6	268.2	276.7	288.3
135°	397.2	367.9	341.0	319.8	302.8	288.9	280.8	277.5	280.8	288.9	302.8
137.5°	405.0	377.6	352.6	332.4	314.6	301.5	292.5	289.4	292.5	301.5	314.6
140°	410.2	384.2	359.8	340.2	323.1	309.3	300.4	297.9	300.4	309.3	323.1
142.5°	414.1	390.0	366.2	347.4	330.9	317.7	309.5	307.0	309.5	317.7	330.9
145°	418.3	396.4	375.2	357.3	341.9	330.4	322.3	319.8	322.3	330.4	341.9
147.5°	422.1	402.9	383.0	366.9	354.1	342.3	335.2	334.4	335.2	342.3	354.1
150°	424.0	406.2	388.2	372.8	360.6	350.8	344.3	343.5	344.3	350.8	360.6
152.5°	425.3	408.8	392.8	378.6	367.7	358.7	352.1	352.0	352.1	358.7	367.7
155°	426.5	412.6	398.8	386.6	377.6	369.5	364.6	363.8	364.6	369.5	377.6
157.5°	426.5	415.4	403.7	394.1	386.3	379.9	375.4	375.4	375.4	379.9	386.3
160°	426.5	416.7	407.0	398.0	391.5	385.8	382.5	382.5	382.5	385.8	391.5
162.5°	426.5	418.0	409.0	401.9	396.1	391.0	388.4	389.1	388.4	391.0	396.1
165°	424.9	418.3	411.0	406.2	402.1	398.0	396.4	396.4	396.4	398.0	402.1
167.5°	422.9	418.2	412.8	409.1	406.8	403.7	402.9	403.7	402.9	403.7	406.8
170°	421.6	417.5	413.4	411.0	409.4	407.0	406.2	407.0	406.2	407.0	409.4
172.5°	420.3	416.9	414.1	412.3	411.3	409.5	409.4	410.2	409.4	409.5	411.3
175°	418.3	415.9	414.3	414.3	413.4	412.6	412.6	413.4	412.6	412.6	413.4
177.5°	416.2	414.9	414.3	414.3	414.3	413.6	414.3	414.9	414.3	413.6	414.3
180°	414.3	414.3	414.3	414.3	414.3	414.3	414.3	414.3	414.3	414.3	414.3



TEST NUMBER: P332654-930

CATALOG NUMBER: S124DIP-S1020D1035U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1360.6	1360.6	1360.6	1360.6	1360.6	1360.6	1360.6	1360.6	1360.6	1360.6	1360.6
2.5°	1334.4	1330.4	1324.5	1316.4	1309.6	1302.4	1300.6	1297.9	1303.3	1298.8	1297.5
5°	1290.7	1278.9	1263.6	1246.2	1236.0	1221.4	1218.5	1212.9	1207.3	1206.7	1201.1
7.5°	1244.4	1227.0	1207.1	1189.3	1172.8	1156.7	1146.3	1144.0	1135.7	1130.8	1125.2
10°	1214.6	1193.2	1170.1	1153.2	1134.0	1117.1	1105.3	1098.5	1092.8	1086.6	1081.0
12.5°	1179.4	1156.7	1137.6	1119.3	1096.6	1083.7	1064.2	1052.5	1051.4	1051.5	1036.8
15°	1138.5	1116.0	1086.6	1060.7	1048.3	1023.5	1012.8	999.3	990.8	982.4	975.7
17.5°	1091.8	1063.6	1040.8	1011.1	987.3	967.6	953.6	945.4	932.7	920.7	912.1
20°	1062.4	1032.6	1008.3	976.7	950.8	926.6	914.8	903.5	893.9	883.8	874.2
22.5°	1032.7	1001.4	971.8	941.1	917.0	891.4	880.0	864.7	855.6	849.9	840.3
25°	985.8	951.9	918.1	888.8	864.1	841.5	826.3	814.4	804.3	799.8	793.6
27.5°	934.8	901.2	868.5	835.3	807.1	790.8	778.6	769.6	763.9	757.8	755.0
30°	902.4	867.4	832.5	801.4	775.5	759.2	748.0	741.8	737.2	734.4	731.6
32.5°	869.4	834.9	798.2	769.9	746.7	732.1	723.6	717.4	715.1	714.1	713.1
35°	816.7	781.7	748.0	722.6	700.6	695.0	687.6	684.2	683.1	687.1	688.8
37.5°	765.6	733.2	702.1	677.4	663.1	654.8	652.3	652.5	656.5	660.0	664.1
40°	732.7	701.2	671.8	650.4	636.9	631.9	630.7	633.5	638.1	642.0	646.5
42.5°	700.7	669.6	642.9	622.9	613.4	608.8	609.5	612.3	618.6	623.5	630.2
45°	651.0	625.1	599.2	582.8	574.9	576.0	576.0	581.1	587.3	594.6	601.9
47.5°	604.2	578.0	556.8	543.0	538.9	537.9	541.1	547.7	556.6	565.7	575.9
50°	572.7	547.8	529.2	516.8	512.3	514.0	518.5	524.7	535.4	546.7	557.4
52.5°	540.6	518.0	500.8	489.3	486.2	489.3	493.7	503.5	512.9	525.1	538.0
55°	490.9	471.7	458.2	449.8	448.7	450.4	455.4	466.1	479.6	494.9	507.3
57.5°	441.4	425.4	413.0	407.2	407.7	409.3	417.7	430.4	444.8	461.1	477.0
60°	408.1	393.4	383.3	378.8	379.3	382.7	392.8	404.7	422.7	438.5	455.4
62.5°	376.5	363.6	353.9	349.9	349.1	356.5	366.2	378.5	396.6	414.2	432.4
65°	325.8	315.6	307.8	305.5	307.2	312.8	325.2	341.5	356.8	375.4	394.5
67.5°	276.1	267.8	262.4	263.4	265.5	273.8	284.2	298.2	315.5	334.8	353.8
70°	244.6	236.7	232.2	232.8	236.2	246.3	255.4	269.4	288.0	307.8	323.5
72.5°	212.1	206.9	202.9	205.3	208.6	215.6	226.9	241.0	257.4	275.7	292.4
75°	162.9	162.9	160.6	162.3	167.4	174.1	182.6	197.3	213.6	228.3	241.8
77.5°	120.8	119.6	121.1	123.1	126.0	134.0	143.7	154.2	166.5	181.2	192.3
80°	92.5	93.0	95.8	99.2	100.4	106.6	116.7	126.3	135.8	148.2	158.9
82.5°	69.5	70.0	71.5	75.7	76.9	83.6	90.1	99.6	108.4	116.7	125.6
85°	37.7	37.7	40.6	42.2	45.1	49.6	53.6	59.2	67.1	72.7	81.1
87.5°	15.7	15.7	18.5	19.4	21.1	23.6	24.4	29.5	31.5	33.9	38.0
90°	6.5	6.5	11.4	11.4	13.0	14.7	13.9	14.7	15.5	16.3	16.3
92.5°	43.0	59.9	101.3	164.4	225.9	258.2	215.1	159.9	120.3	95.7	79.4
95°	67.6	101.7	172.5	306.1	500.6	663.3	682.1	603.1	477.0	367.9	288.9
97.5°	81.7	110.4	164.9	275.1	468.5	698.6	856.9	891.1	844.2	764.6	679.6
100°	92.8	118.9	166.9	258.9	424.9	654.4	862.7	981.6	997.8	958.0	897.7
102.5°	105.2	129.9	173.3	254.3	395.6	599.1	813.9	977.1	1057.8	1069.3	1044.2
105°	126.1	149.8	188.8	256.4	370.3	533.9	725.2	911.6	1052.4	1132.9	1166.4
107.5°	147.8	171.0	206.9	268.4	365.7	497.5	653.5	818.6	968.6	1082.1	1154.6
110°	162.8	184.7	220.5	277.5	367.0	485.1	617.8	762.6	903.4	1021.5	1111.0



TEST NUMBER: P332654-930

CATALOG NUMBER: S124DIP-S1020D1035U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	177.1	199.1	233.6	287.3	371.0	479.2	597.6	721.6	846.1	957.7	1047.2
115°	199.4	221.4	254.0	302.8	378.5	476.1	578.7	680.4	780.6	875.8	953.9
117.5°	219.9	242.7	273.6	318.5	386.5	475.3	570.2	660.2	743.1	818.0	884.3
120°	233.6	256.4	287.3	329.6	392.3	475.3	565.7	651.1	726.8	792.0	849.7
122.5°	247.3	269.4	300.4	340.1	398.2	474.7	560.4	643.4	716.4	775.7	826.3
125°	266.1	288.9	318.2	355.7	407.0	473.7	551.9	630.0	699.9	756.1	800.9
127.5°	283.6	306.6	334.8	369.2	413.9	471.9	540.3	613.7	680.6	736.6	779.1
130°	294.6	318.2	345.9	377.6	419.1	471.2	533.1	600.7	665.0	720.3	763.4
132.5°	305.1	327.3	355.1	386.1	423.7	470.6	526.6	587.0	647.4	701.4	744.6
135°	319.8	341.0	367.9	397.2	430.6	469.6	516.8	568.1	621.0	670.7	711.3
137.5°	332.4	352.6	377.6	405.0	434.6	469.4	508.3	551.1	595.8	637.6	674.4
140°	340.2	359.8	384.2	410.2	437.9	468.8	503.9	541.3	579.5	616.1	650.3
142.5°	347.4	366.2	390.0	414.1	440.5	468.8	499.9	532.1	565.8	597.3	626.9
145°	357.3	375.2	396.4	418.3	442.0	467.2	493.3	519.3	547.0	571.4	594.2
147.5°	366.9	383.0	402.9	422.1	442.8	464.2	487.2	508.7	530.7	550.2	568.1
150°	372.8	388.2	406.2	424.0	442.8	462.3	482.7	502.2	520.9	537.2	551.9
152.5°	378.6	392.8	408.8	425.3	441.5	459.0	477.4	495.0	511.1	526.1	538.2
155°	386.6	398.8	412.6	426.5	439.5	454.2	469.6	484.3	497.3	509.5	519.3
157.5°	394.1	403.7	415.4	426.5	437.4	449.1	461.6	472.7	483.6	493.9	501.7
160°	398.0	407.0	416.7	426.5	435.5	445.2	455.8	465.5	474.5	483.5	490.0
162.5°	401.9	409.0	418.0	426.5	433.5	441.3	450.6	458.4	466.0	473.0	478.9
165°	406.2	411.0	418.3	424.9	429.7	435.5	442.0	448.5	453.4	459.0	463.1
167.5°	409.1	412.8	418.2	422.9	425.8	429.6	434.1	438.9	442.6	447.2	449.6
170°	411.0	413.4	417.5	421.6	423.2	425.7	428.9	433.0	435.5	438.7	441.2
172.5°	412.3	414.1	416.9	420.3	420.6	421.8	424.4	427.8	429.6	431.5	433.3
175°	414.3	414.3	415.9	418.3	417.5	417.5	419.1	420.8	421.6	423.2	423.2
177.5°	414.3	414.3	414.9	416.2	414.9	414.9	415.6	416.2	416.9	416.9	417.5
180°	414.3	414.3	414.3	414.3	414.3	414.3	414.3	414.3	414.3	414.3	414.3



TEST NUMBER: P332654-930

CATALOG NUMBER: S124DIP-S1020D1035U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1360.6	1360.6	1360.6	1360.6	1360.6	1360.6	1360.6	1360.6	1360.6	1360.6	1360.6
2.5°	1296.6	1295.7	1292.5	1292.1	1292.5	1295.7	1296.6	1297.5	1298.8	1303.3	1297.9
5°	1197.7	1194.9	1193.2	1199.4	1193.2	1194.9	1197.7	1201.1	1206.7	1207.3	1212.9
7.5°	1123.2	1121.0	1116.0	1114.4	1116.0	1121.0	1123.2	1125.2	1130.8	1135.7	1144.0
10°	1075.4	1073.1	1068.6	1067.5	1068.6	1073.1	1075.4	1081.0	1086.6	1092.8	1098.5
12.5°	1029.4	1024.9	1024.0	1025.1	1024.0	1024.9	1029.4	1036.8	1051.5	1051.4	1052.5
15°	968.3	966.0	959.9	961.6	959.9	966.0	968.3	975.7	982.4	990.8	999.3
17.5°	908.1	905.4	897.9	904.5	897.9	905.4	908.1	912.1	920.7	932.7	945.4
20°	870.3	865.7	861.8	861.2	861.8	865.7	870.3	874.2	883.8	893.9	903.5
22.5°	834.1	830.1	829.7	826.1	829.7	830.1	834.1	840.3	849.9	855.6	864.7
25°	789.0	785.1	784.0	781.2	784.0	785.1	789.0	793.6	799.8	804.3	814.4
27.5°	754.5	752.5	750.5	751.4	750.5	752.5	754.5	755.0	757.8	763.9	769.6
30°	733.3	732.7	731.6	731.6	731.6	732.7	733.3	731.6	734.4	737.2	741.8
32.5°	715.7	715.6	716.2	716.2	716.2	715.6	715.7	713.1	714.1	715.1	717.4
35°	691.0	692.7	693.8	692.1	693.8	692.7	691.0	688.8	687.1	683.1	684.2
37.5°	668.7	670.3	672.0	673.8	672.0	670.3	668.7	664.1	660.0	656.5	652.5
40°	651.5	655.5	656.6	659.4	656.6	655.5	651.5	646.5	642.0	638.1	633.5
42.5°	635.3	639.7	642.6	643.2	642.6	639.7	635.3	630.2	623.5	618.6	612.3
45°	610.4	614.9	618.9	618.9	618.9	614.9	610.4	601.9	594.6	587.3	581.1
47.5°	584.6	591.1	595.1	596.1	595.1	591.1	584.6	575.9	565.7	556.6	547.7
50°	567.0	574.9	578.9	581.6	578.9	574.9	567.0	557.4	546.7	535.4	524.7
52.5°	549.8	557.7	563.0	564.5	563.0	557.7	549.8	538.0	525.1	512.9	503.5
55°	520.2	531.5	537.7	540.0	537.7	531.5	520.2	507.3	494.9	479.6	466.1
57.5°	492.3	502.6	509.9	511.5	509.9	502.6	492.3	477.0	461.1	444.8	430.4
60°	470.6	481.9	490.9	492.6	490.9	481.9	470.6	455.4	438.5	422.7	404.7
62.5°	448.5	460.2	468.4	472.8	468.4	460.2	448.5	432.4	414.2	396.6	378.5
65°	410.3	422.2	430.1	431.7	430.1	422.2	410.3	394.5	375.4	356.8	341.5
67.5°	368.6	380.4	385.6	388.9	385.6	380.4	368.6	353.8	334.8	315.5	298.2
70°	339.3	348.9	354.5	357.3	354.5	348.9	339.3	323.5	307.8	288.0	269.4
72.5°	305.9	315.9	322.5	323.1	322.5	315.9	305.9	292.4	275.7	257.4	241.0
75°	254.8	263.7	267.2	267.2	267.2	263.7	254.8	241.8	228.3	213.6	197.3
77.5°	201.6	206.3	210.6	211.5	210.6	206.3	201.6	192.3	181.2	166.5	154.2
80°	167.4	170.2	173.6	173.6	173.6	170.2	167.4	158.9	148.2	135.8	126.3
82.5°	132.2	134.6	137.9	137.5	137.9	134.6	132.2	125.6	116.7	108.4	99.6
85°	80.1	85.1	84.5	83.4	84.5	85.1	80.1	81.1	72.7	67.1	59.2
87.5°	39.5	40.1	41.3	42.2	41.3	40.1	39.5	38.0	33.9	31.5	29.5
90°	17.1	17.9	17.1	17.1	17.1	17.9	17.1	16.3	16.3	15.5	14.7
92.5°	69.9	65.5	62.7	62.7	62.7	65.5	69.9	79.4	95.7	120.3	159.9
95°	249.1	223.8	209.2	198.6	209.2	223.8	249.1	288.9	367.9	477.0	603.1
97.5°	621.2	572.2	547.8	530.8	547.8	572.2	621.2	679.6	764.6	844.2	891.1
100°	827.0	777.3	752.8	746.4	752.8	777.3	827.0	897.7	958.0	997.8	981.6
102.5°	1000.8	964.8	939.1	933.9	939.1	964.8	1000.8	1044.2	1069.3	1057.8	977.1
105°	1168.0	1161.5	1150.1	1145.2	1150.1	1161.5	1168.0	1166.4	1132.9	1052.4	911.6
107.5°	1194.8	1213.4	1221.6	1223.7	1221.6	1213.4	1194.8	1154.6	1082.1	968.6	818.6
110°	1168.8	1203.0	1217.6	1225.0	1217.6	1203.0	1168.8	1111.0	1021.5	903.4	762.6



TEST NUMBER: P332654-930

CATALOG NUMBER: S124DIP-S1020D1035U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1112.8	1154.1	1174.7	1186.5	1174.7	1154.1	1112.8	1047.2	957.7	846.1	721.6
115°	1018.2	1067.1	1093.1	1099.6	1093.1	1067.1	1018.2	953.9	875.8	780.6	680.4
117.5°	939.1	980.2	1006.5	1011.5	1006.5	980.2	939.1	884.3	818.0	743.1	660.2
120°	896.1	932.0	953.1	962.1	953.1	932.0	896.1	849.7	792.0	726.8	651.1
122.5°	865.5	896.1	914.0	923.0	914.0	896.1	865.5	826.3	775.7	716.4	643.4
125°	833.5	857.0	872.5	877.4	872.5	857.0	833.5	800.9	756.1	699.9	630.0
127.5°	811.8	832.8	845.8	850.7	845.8	832.8	811.8	779.1	736.6	680.6	613.7
130°	796.8	817.2	830.2	835.1	830.2	817.2	796.8	763.4	720.3	665.0	600.7
132.5°	777.3	800.2	812.6	817.5	812.6	800.2	777.3	744.6	701.4	647.4	587.0
135°	744.0	766.7	779.8	784.6	779.8	766.7	744.0	711.3	670.7	621.0	568.1
137.5°	704.8	727.3	738.1	744.0	738.1	727.3	704.8	674.4	637.6	595.8	551.1
140°	678.8	696.8	708.1	714.6	708.1	696.8	678.8	650.3	616.1	579.5	541.3
142.5°	652.1	668.7	678.8	683.4	678.8	668.7	652.1	626.9	597.3	565.8	532.1
145°	614.5	628.4	636.5	640.6	636.5	628.4	614.5	594.2	571.4	547.0	519.3
147.5°	583.1	595.0	601.2	602.6	601.2	595.0	583.1	568.1	550.2	530.7	508.7
150°	564.8	575.4	580.3	581.1	580.3	575.4	564.8	551.9	537.2	520.9	502.2
152.5°	549.3	557.8	560.8	561.6	560.8	557.8	549.3	538.2	526.1	511.1	495.0
155°	527.4	533.9	536.4	536.4	536.4	533.9	527.4	519.3	509.5	497.3	484.3
157.5°	507.8	512.7	514.2	514.2	514.2	512.7	507.8	501.7	493.9	483.6	472.7
160°	494.9	499.8	500.6	500.6	500.6	499.8	494.9	490.0	483.5	474.5	465.5
162.5°	482.5	487.4	488.2	487.5	488.2	487.4	482.5	478.9	473.0	466.0	458.4
165°	466.4	469.6	468.8	468.0	468.8	469.6	466.4	463.1	459.0	453.4	448.5
167.5°	451.3	453.4	453.2	452.6	453.2	453.4	451.3	449.6	447.2	442.6	438.9
170°	442.8	443.6	442.8	442.8	442.8	443.6	442.8	441.2	438.7	435.5	433.0
172.5°	434.3	435.1	434.3	433.0	434.3	435.1	434.3	433.3	431.5	429.6	427.8
175°	423.2	424.9	423.2	421.6	423.2	424.9	423.2	423.2	423.2	421.6	420.8
177.5°	416.9	417.5	416.2	414.9	416.2	417.5	416.9	417.5	416.9	416.9	416.2
180°	414.3	414.3	414.3	414.3	414.3	414.3	414.3	414.3	414.3	414.3	414.3



TEST NUMBER: P332654-930

CATALOG NUMBER: S124DIP-S1020D1035U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1360.6	1360.6	1360.6	1360.6	1360.6	1360.6	1360.6	1360.6	1360.6	1360.6	1360.6
2.5°	1300.6	1302.4	1309.6	1316.4	1324.5	1330.4	1334.4	1339.0	1348.4	1356.1	1363.3
5°	1218.5	1221.4	1236.0	1246.2	1263.6	1278.9	1290.7	1303.7	1318.9	1339.7	1358.9
7.5°	1146.3	1156.7	1172.8	1189.3	1207.1	1227.0	1244.4	1263.9	1290.1	1318.7	1348.3
10°	1105.3	1117.1	1134.0	1153.2	1170.1	1193.2	1214.6	1237.7	1267.5	1302.5	1337.5
12.5°	1064.2	1083.7	1096.6	1119.3	1137.6	1156.7	1179.4	1209.7	1244.6	1281.3	1323.5
15°	1012.8	1023.5	1048.3	1060.7	1086.6	1116.0	1138.5	1169.0	1202.7	1251.2	1298.6
17.5°	953.6	967.6	987.3	1011.1	1040.8	1063.6	1091.8	1123.1	1165.7	1213.8	1273.1
20°	914.8	926.6	950.8	976.7	1008.3	1032.6	1062.4	1092.8	1136.9	1188.1	1250.1
22.5°	880.0	891.4	917.0	941.1	971.8	1001.4	1032.7	1068.0	1110.2	1164.2	1227.6
25°	826.3	841.5	864.1	888.8	918.1	951.9	985.8	1017.3	1062.4	1119.3	1187.0
27.5°	778.6	790.8	807.1	835.3	868.5	901.2	934.8	974.5	1017.8	1078.0	1148.2
30°	748.0	759.2	775.5	801.4	832.5	867.4	902.4	940.7	985.8	1045.5	1117.1
32.5°	723.6	732.1	746.7	769.9	798.2	834.9	869.4	909.1	956.4	1015.3	1085.1
35°	687.6	695.0	700.6	722.6	748.0	781.7	816.7	859.0	904.6	960.4	1030.3
37.5°	652.3	654.8	663.1	677.4	702.1	733.2	765.6	807.2	854.0	910.7	973.7
40°	630.7	631.9	636.9	650.4	671.8	701.2	732.7	773.9	818.4	872.0	934.5
42.5°	609.5	608.8	613.4	622.9	642.9	669.6	700.7	738.3	782.8	832.3	891.2
45°	576.0	576.0	574.9	582.8	599.2	625.1	651.0	687.1	724.2	772.7	822.3
47.5°	541.1	537.9	538.9	543.0	556.8	578.0	604.2	633.7	666.5	707.6	751.1
50°	518.5	514.0	512.3	516.8	529.2	547.8	572.7	598.6	629.6	665.6	702.9
52.5°	493.7	489.3	486.2	489.3	500.8	518.0	540.6	563.4	591.3	620.5	652.8
55°	455.4	450.4	448.7	449.8	458.2	471.7	490.9	511.8	532.6	556.8	579.4
57.5°	417.7	409.3	407.7	407.2	413.0	425.4	441.4	459.5	474.7	489.3	513.3
60°	392.8	382.7	379.3	378.8	383.3	393.4	408.1	426.1	436.8	446.9	467.8
62.5°	366.2	356.5	349.1	349.9	353.9	363.6	376.5	389.6	396.6	407.7	421.8
65°	325.2	312.8	307.2	305.5	307.8	315.6	325.8	334.2	342.1	346.7	360.1
67.5°	284.2	273.8	265.5	263.4	262.4	267.8	276.1	281.3	286.9	290.8	298.8
70°	255.4	246.3	236.2	232.8	232.2	236.7	244.6	245.2	253.1	254.8	263.2
72.5°	226.9	215.6	208.6	205.3	202.9	206.9	212.1	213.6	217.9	220.9	225.3
75°	182.6	174.1	167.4	162.3	160.6	162.9	162.9	165.7	168.5	170.2	175.3
77.5°	143.7	134.0	126.0	123.1	121.1	119.6	120.8	122.5	121.2	124.1	125.2
80°	116.7	106.6	100.4	99.2	95.8	93.0	92.5	94.1	91.9	93.0	96.4
82.5°	90.1	83.6	76.9	75.7	71.5	70.0	69.5	68.4	68.4	68.2	68.9
85°	53.6	49.6	45.1	42.2	40.6	37.7	37.7	36.6	35.5	34.4	35.0
87.5°	24.4	23.6	21.1	19.4	18.5	15.7	15.7	14.2	13.6	12.6	11.9
90°	13.9	14.7	13.0	11.4	11.4	6.5	6.5	5.7	4.9	2.4	0.8
92.5°	215.1	258.2	225.9	164.4	101.3	59.9	43.0	31.1	21.2	13.5	9.3
95°	682.1	663.3	500.6	306.1	172.5	101.7	67.6	48.0	37.4	29.3	26.8
97.5°	856.9	698.6	468.5	275.1	164.9	110.4	81.7	65.0	55.2	48.2	48.2
100°	862.7	654.4	424.9	258.9	166.9	118.9	92.8	77.3	67.6	61.9	61.9
102.5°	813.9	599.1	395.6	254.3	173.3	129.9	105.2	90.3	81.2	76.1	74.8
105°	725.2	533.9	370.3	256.4	188.8	149.8	126.1	111.5	101.7	97.7	95.2
107.5°	653.5	497.5	365.7	268.4	206.9	171.0	147.8	133.8	123.4	119.4	117.7
110°	617.8	485.1	367.0	277.5	220.5	184.7	162.8	148.1	138.4	134.3	132.6



TEST NUMBER: P332654-930

CATALOG NUMBER: S124DIP-S1020D1035U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	597.6	479.2	371.0	287.3	233.6	199.1	177.1	162.5	153.4	148.6	147.0
115°	578.7	476.1	378.5	302.8	254.0	221.4	199.4	183.9	175.8	170.1	167.7
117.5°	570.2	475.3	386.5	318.5	273.6	242.7	219.9	205.5	196.5	191.4	189.1
120°	565.7	475.3	392.3	329.6	287.3	256.4	233.6	219.7	210.8	205.1	203.5
122.5°	560.4	474.7	398.2	340.1	300.4	269.4	247.3	232.1	223.8	218.1	216.5
125°	551.9	473.7	407.0	355.7	318.2	288.9	266.1	250.7	241.7	236.8	233.6
127.5°	540.3	471.9	413.9	369.2	334.8	306.6	283.6	267.4	257.2	251.4	248.7
130°	533.1	471.2	419.1	377.6	345.9	318.2	294.6	279.2	266.9	260.5	257.2
132.5°	526.6	470.6	423.7	386.1	355.1	327.3	305.1	288.3	276.7	268.2	265.6
135°	516.8	469.6	430.6	397.2	367.9	341.0	319.8	302.8	288.9	280.8	277.5
137.5°	508.3	469.4	434.6	405.0	377.6	352.6	332.4	314.6	301.5	292.5	289.4
140°	503.9	468.8	437.9	410.2	384.2	359.8	340.2	323.1	309.3	300.4	297.9
142.5°	499.9	468.8	440.5	414.1	390.0	366.2	347.4	330.9	317.7	309.5	307.0
145°	493.3	467.2	442.0	418.3	396.4	375.2	357.3	341.9	330.4	322.3	319.8
147.5°	487.2	464.2	442.8	422.1	402.9	383.0	366.9	354.1	342.3	335.2	334.4
150°	482.7	462.3	442.8	424.0	406.2	388.2	372.8	360.6	350.8	344.3	343.5
152.5°	477.4	459.0	441.5	425.3	408.8	392.8	378.6	367.7	358.7	352.1	352.0
155°	469.6	454.2	439.5	426.5	412.6	398.8	386.6	377.6	369.5	364.6	363.8
157.5°	461.6	449.1	437.4	426.5	415.4	403.7	394.1	386.3	379.9	375.4	375.4
160°	455.8	445.2	435.5	426.5	416.7	407.0	398.0	391.5	385.8	382.5	382.5
162.5°	450.6	441.3	433.5	426.5	418.0	409.0	401.9	396.1	391.0	388.4	389.1
165°	442.0	435.5	429.7	424.9	418.3	411.0	406.2	402.1	398.0	396.4	396.4
167.5°	434.1	429.6	425.8	422.9	418.2	412.8	409.1	406.8	403.7	402.9	403.7
170°	428.9	425.7	423.2	421.6	417.5	413.4	411.0	409.4	407.0	406.2	407.0
172.5°	424.4	421.8	420.6	420.3	416.9	414.1	412.3	411.3	409.5	409.4	410.2
175°	419.1	417.5	417.5	418.3	415.9	414.3	414.3	413.4	412.6	412.6	413.4
177.5°	415.6	414.9	414.9	416.2	414.9	414.3	414.3	414.3	413.6	414.3	414.9
180°	414.3	414.3	414.3	414.3	414.3	414.3	414.3	414.3	414.3	414.3	414.3



TEST NUMBER: P332654-930

CATALOG NUMBER: S124DIP-S1020D1035U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1360.6	1360.6	1360.6	1360.6	1360.6	1360.6	1360.6	1360.6	1360.6	1360.6	1360.6
2.5°	1369.6	1374.1	1380.0	1389.9	1393.5	1398.0	1404.4	1403.9	1405.7	1412.4	1426.9
5°	1374.7	1392.1	1409.1	1429.4	1450.7	1464.8	1484.0	1495.8	1507.7	1522.9	1548.8
7.5°	1376.7	1404.4	1435.4	1471.0	1502.8	1539.3	1567.7	1594.6	1618.9	1651.0	1681.9
10°	1373.5	1410.7	1450.7	1495.8	1543.8	1584.4	1621.0	1662.7	1698.2	1737.1	1772.1
12.5°	1367.7	1412.6	1466.1	1516.6	1572.6	1632.6	1678.2	1720.4	1767.7	1812.4	1866.3
15°	1354.4	1415.8	1478.4	1544.9	1619.8	1689.1	1755.1	1809.8	1860.5	1927.6	1998.1
17.5°	1337.5	1403.8	1482.6	1563.2	1641.5	1720.8	1802.4	1884.6	1948.6	2031.9	2087.0
20°	1321.7	1398.3	1479.5	1575.3	1653.7	1752.3	1833.4	1912.9	2000.8	2083.7	2149.6
22.5°	1299.6	1383.5	1469.6	1565.0	1668.1	1766.8	1860.5	1946.8	2034.7	2124.8	2204.7
25°	1271.5	1347.6	1449.6	1557.9	1660.4	1767.5	1875.2	1983.4	2078.0	2173.3	2247.7
27.5°	1223.8	1319.8	1414.8	1526.5	1640.5	1761.6	1876.7	1990.1	2089.2	2167.6	2213.7
30°	1199.4	1282.8	1385.9	1498.1	1621.5	1751.8	1871.8	1982.8	2075.3	2137.8	2156.4
32.5°	1163.4	1249.4	1350.3	1466.6	1597.2	1731.0	1856.0	1960.7	2037.8	2070.6	2048.2
35°	1109.8	1187.6	1289.6	1408.5	1544.3	1686.9	1810.4	1898.8	1938.3	1907.3	1830.1
37.5°	1045.5	1122.6	1225.1	1341.9	1482.5	1627.4	1739.0	1802.7	1789.6	1712.5	1597.4
40°	1000.5	1072.6	1170.1	1296.3	1433.3	1578.7	1676.7	1711.2	1675.1	1564.6	1442.3
42.5°	950.4	1020.8	1118.7	1240.4	1385.5	1519.6	1605.1	1607.9	1547.4	1415.4	1292.6
45°	874.2	941.3	1033.7	1160.5	1294.6	1420.9	1477.2	1449.6	1338.1	1210.6	1087.2
47.5°	799.0	857.1	948.3	1068.6	1196.0	1302.3	1330.2	1280.5	1161.6	1038.0	923.6
50°	744.0	802.6	888.3	1003.2	1126.1	1218.0	1231.5	1165.6	1048.9	924.3	834.7
52.5°	691.2	749.4	831.9	938.3	1050.8	1133.7	1134.1	1057.8	941.6	830.5	747.2
55°	613.8	666.2	740.6	835.8	936.2	1001.0	985.2	906.3	805.4	709.1	636.3
57.5°	539.2	584.8	653.4	732.8	821.2	874.7	848.5	772.5	682.4	600.7	545.6
60°	490.9	534.3	593.0	667.9	742.3	784.0	759.2	690.4	607.6	541.6	493.7
62.5°	444.0	480.6	537.0	602.1	671.1	702.0	679.9	612.0	540.4	480.8	441.9
65°	377.6	407.5	452.6	508.4	558.6	585.1	566.5	503.3	448.7	405.8	374.8
67.5°	315.6	339.0	373.1	417.8	460.5	474.8	457.9	413.9	367.6	333.3	311.4
70°	272.8	294.8	323.5	357.9	395.1	410.3	393.4	358.5	320.7	289.1	267.7
72.5°	235.4	252.4	276.6	306.1	335.2	350.3	338.8	305.2	273.4	249.9	231.6
75°	179.2	193.9	210.8	231.6	254.2	264.3	254.2	231.1	209.1	191.6	178.6
77.5°	130.3	138.2	151.2	166.8	180.9	188.7	179.9	164.2	150.8	138.8	132.5
80°	99.2	104.8	113.8	126.3	135.8	143.2	137.5	124.6	113.8	106.0	103.1
82.5°	72.2	76.0	81.9	91.1	97.5	101.3	98.7	89.4	85.0	78.0	75.2
85°	35.5	37.7	41.7	44.5	50.1	50.7	51.3	47.4	43.4	41.7	39.5
87.5°	12.6	13.6	15.1	16.6	18.4	19.9	19.4	19.7	18.3	17.6	16.0
90°	2.4	4.9	5.7	6.5	6.5	11.4	11.4	13.0	14.7	13.9	14.7
92.5°	13.5	21.2	31.1	43.0	59.9	101.3	164.4	225.9	258.2	215.1	159.9
95°	29.3	37.4	48.0	67.6	101.7	172.5	306.1	500.6	663.3	682.1	603.1
97.5°	48.2	55.2	65.0	81.7	110.4	164.9	275.1	468.5	698.6	856.9	891.1
100°	61.9	67.6	77.3	92.8	118.9	166.9	258.9	424.9	654.4	862.7	981.6
102.5°	76.1	81.2	90.3	105.2	129.9	173.3	254.3	395.6	599.1	813.9	977.1
105°	97.7	101.7	111.5	126.1	149.8	188.8	256.4	370.3	533.9	725.2	911.6
107.5°	119.4	123.4	133.8	147.8	171.0	206.9	268.4	365.7	497.5	653.5	818.6
110°	134.3	138.4	148.1	162.8	184.7	220.5	277.5	367.0	485.1	617.8	762.6





TEST NUMBER: P332654-930

CATALOG NUMBER: S124DIP-S1020D1035U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	148.6	153.4	162.5	177.1	199.1	233.6	287.3	371.0	479.2	597.6	721.6
115°	170.1	175.8	183.9	199.4	221.4	254.0	302.8	378.5	476.1	578.7	680.4
117.5°	191.4	196.5	205.5	219.9	242.7	273.6	318.5	386.5	475.3	570.2	660.2
120°	205.1	210.8	219.7	233.6	256.4	287.3	329.6	392.3	475.3	565.7	651.1
122.5°	218.1	223.8	232.1	247.3	269.4	300.4	340.1	398.2	474.7	560.4	643.4
125°	236.8	241.7	250.7	266.1	288.9	318.2	355.7	407.0	473.7	551.9	630.0
127.5°	251.4	257.2	267.4	283.6	306.6	334.8	369.2	413.9	471.9	540.3	613.7
130°	260.5	266.9	279.2	294.6	318.2	345.9	377.6	419.1	471.2	533.1	600.7
132.5°	268.2	276.7	288.3	305.1	327.3	355.1	386.1	423.7	470.6	526.6	587.0
135°	280.8	288.9	302.8	319.8	341.0	367.9	397.2	430.6	469.6	516.8	568.1
137.5°	292.5	301.5	314.6	332.4	352.6	377.6	405.0	434.6	469.4	508.3	551.1
140°	300.4	309.3	323.1	340.2	359.8	384.2	410.2	437.9	468.8	503.9	541.3
142.5°	309.5	317.7	330.9	347.4	366.2	390.0	414.1	440.5	468.8	499.9	532.1
145°	322.3	330.4	341.9	357.3	375.2	396.4	418.3	442.0	467.2	493.3	519.3
147.5°	335.2	342.3	354.1	366.9	383.0	402.9	422.1	442.8	464.2	487.2	508.7
150°	344.3	350.8	360.6	372.8	388.2	406.2	424.0	442.8	462.3	482.7	502.2
152.5°	352.1	358.7	367.7	378.6	392.8	408.8	425.3	441.5	459.0	477.4	495.0
155°	364.6	369.5	377.6	386.6	398.8	412.6	426.5	439.5	454.2	469.6	484.3
157.5°	375.4	379.9	386.3	394.1	403.7	415.4	426.5	437.4	449.1	461.6	472.7
160°	382.5	385.8	391.5	398.0	407.0	416.7	426.5	435.5	445.2	455.8	465.5
162.5°	388.4	391.0	396.1	401.9	409.0	418.0	426.5	433.5	441.3	450.6	458.4
165°	396.4	398.0	402.1	406.2	411.0	418.3	424.9	429.7	435.5	442.0	448.5
167.5°	402.9	403.7	406.8	409.1	412.8	418.2	422.9	425.8	429.6	434.1	438.9
170°	406.2	407.0	409.4	411.0	413.4	417.5	421.6	423.2	425.7	428.9	433.0
172.5°	409.4	409.5	411.3	412.3	414.1	416.9	420.3	420.6	421.8	424.4	427.8
175°	412.6	412.6	413.4	414.3	414.3	415.9	418.3	417.5	417.5	419.1	420.8
177.5°	414.3	413.6	414.3	414.3	414.3	414.9	416.2	414.9	414.9	415.6	416.2
180°	414.3	414.3	414.3	414.3	414.3	414.3	414.3	414.3	414.3	414.3	414.3



TEST NUMBER: P332654-930

CATALOG NUMBER: S124DIP-S1020D1035U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1360.6	1360.6	1360.6	1360.6	1360.6	1360.6	1360.6
2.5°	1434.1	1435.0	1439.0	1442.2	1443.1	1447.6	1448.1
5°	1560.1	1569.7	1588.3	1590.0	1592.8	1607.4	1596.2
7.5°	1707.8	1732.1	1748.3	1762.7	1767.9	1774.3	1772.9
10°	1802.5	1838.5	1856.6	1885.3	1886.4	1893.8	1889.3
12.5°	1897.6	1939.5	1972.5	1977.8	2001.9	2005.6	2011.9
15°	2032.4	2077.0	2122.6	2138.9	2172.2	2180.1	2192.5
17.5°	2159.2	2204.7	2236.7	2278.9	2292.6	2310.9	2298.4
20°	2228.5	2278.2	2318.7	2352.0	2366.1	2376.2	2375.1
22.5°	2270.5	2320.5	2353.4	2378.6	2391.8	2396.1	2395.8
25°	2296.8	2325.5	2335.7	2345.2	2330.6	2325.5	2327.8
27.5°	2223.7	2216.3	2189.8	2155.1	2119.0	2090.3	2074.8
30°	2123.2	2079.2	2039.1	1969.3	1933.2	1911.8	1892.6
32.5°	1980.7	1911.0	1834.0	1770.0	1729.0	1697.2	1692.5
35°	1736.5	1631.7	1537.6	1459.2	1418.6	1384.2	1376.4
37.5°	1476.3	1367.4	1282.7	1213.7	1170.1	1145.8	1123.2
40°	1303.7	1210.1	1126.7	1068.0	1034.8	1017.3	1003.2
42.5°	1170.6	1085.2	1002.2	957.6	927.5	916.8	908.6
45°	986.9	907.4	849.9	816.1	798.7	780.6	772.2
47.5°	839.8	775.1	737.2	708.5	689.7	679.1	673.6
50°	756.4	703.4	669.6	647.6	630.7	622.2	617.8
52.5°	682.4	639.0	610.5	593.0	581.6	575.4	573.6
55°	587.8	554.6	536.5	521.4	512.9	507.3	505.0
57.5°	510.9	485.4	470.8	458.2	454.9	450.2	448.7
60°	460.5	440.8	428.4	419.9	417.1	411.5	412.5
62.5°	415.8	399.7	389.1	384.3	380.6	375.9	377.4
65°	351.7	339.9	334.2	329.7	325.2	322.4	324.7
67.5°	295.1	287.0	279.3	276.7	274.5	274.0	271.7
70°	258.1	251.4	244.6	243.0	243.0	240.7	240.1
72.5°	222.5	217.5	213.0	211.8	210.0	210.9	208.6
75°	171.9	168.0	166.2	164.6	164.0	164.0	162.3
77.5°	127.0	124.1	121.4	121.4	119.4	118.6	118.4
80°	96.4	95.2	93.0	93.0	91.9	92.5	91.3
82.5°	72.5	70.9	70.4	69.5	68.0	68.1	66.9
85°	38.9	37.2	36.6	35.0	33.8	35.0	33.8
87.5°	16.6	16.3	15.9	15.2	14.8	14.7	13.4
90°	15.5	16.3	16.3	17.1	17.9	17.1	17.1
92.5°	120.3	95.7	79.4	69.9	65.5	62.7	62.7
95°	477.0	367.9	288.9	249.1	223.8	209.2	198.6
97.5°	844.2	764.6	679.6	621.2	572.2	547.8	530.8
100°	997.8	958.0	897.7	827.0	777.3	752.8	746.4
102.5°	1057.8	1069.3	1044.2	1000.8	964.8	939.1	933.9
105°	1052.4	1132.9	1166.4	1168.0	1161.5	1150.1	1145.2
107.5°	968.6	1082.1	1154.6	1194.8	1213.4	1221.6	1223.7
110°	903.4	1021.5	1111.0	1168.8	1203.0	1217.6	1225.0



TEST NUMBER: P332654-930

CATALOG NUMBER: S124DIP-S1020D1035U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	846.1	957.7	1047.2	1112.8	1154.1	1174.7	1186.5
115°	780.6	875.8	953.9	1018.2	1067.1	1093.1	1099.6
117.5°	743.1	818.0	884.3	939.1	980.2	1006.5	1011.5
120°	726.8	792.0	849.7	896.1	932.0	953.1	962.1
122.5°	716.4	775.7	826.3	865.5	896.1	914.0	923.0
125°	699.9	756.1	800.9	833.5	857.0	872.5	877.4
127.5°	680.6	736.6	779.1	811.8	832.8	845.8	850.7
130°	665.0	720.3	763.4	796.8	817.2	830.2	835.1
132.5°	647.4	701.4	744.6	777.3	800.2	812.6	817.5
135°	621.0	670.7	711.3	744.0	766.7	779.8	784.6
137.5°	595.8	637.6	674.4	704.8	727.3	738.1	744.0
140°	579.5	616.1	650.3	678.8	696.8	708.1	714.6
142.5°	565.8	597.3	626.9	652.1	668.7	678.8	683.4
145°	547.0	571.4	594.2	614.5	628.4	636.5	640.6
147.5°	530.7	550.2	568.1	583.1	595.0	601.2	602.6
150°	520.9	537.2	551.9	564.8	575.4	580.3	581.1
152.5°	511.1	526.1	538.2	549.3	557.8	560.8	561.6
155°	497.3	509.5	519.3	527.4	533.9	536.4	536.4
157.5°	483.6	493.9	501.7	507.8	512.7	514.2	514.2
160°	474.5	483.5	490.0	494.9	499.8	500.6	500.6
162.5°	466.0	473.0	478.9	482.5	487.4	488.2	487.5
165°	453.4	459.0	463.1	466.4	469.6	468.8	468.0
167.5°	442.6	447.2	449.6	451.3	453.4	453.2	452.6
170°	435.5	438.7	441.2	442.8	443.6	442.8	442.8
172.5°	429.6	431.5	433.3	434.3	435.1	434.3	433.0
175°	421.6	423.2	423.2	423.2	424.9	423.2	421.6
177.5°	416.9	416.9	417.5	416.9	417.5	416.2	414.9
180°	414.3	414.3	414.3	414.3	414.3	414.3	414.3

(END OF REPORT)