

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332614-940

Luminaire Tested: **S124DIP-S795D1035U940-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332614-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124DIP-S795D1035U940-4F0-1E-UDD-F1  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 795 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1035 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6233.9 lumens  
Efficiency: N/A  
Efficacy: 119.9 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 52  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332614-940

CATALOG NUMBER: S124DIP-S795D1035U940-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332614-940

CATALOG NUMBER: S124DIP-S795D1035U940-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55	49
1	97	93	89	86	90	86	83	80	72	70	68	60	58	57	49	47	46	41
2	89	81	75	70	81	75	70	65	63	59	56	53	50	47	43	41	39	34
3	81	71	64	58	74	66	60	54	56	51	47	47	43	40	38	35	33	29
4	74	63	55	49	68	59	52	46	50	44	40	41	38	34	34	31	29	25
5	68	56	48	42	62	52	45	40	44	39	35	37	33	30	30	27	25	22
6	63	51	42	37	57	47	40	34	40	34	30	34	29	26	28	24	22	19
7	58	46	38	32	53	42	35	30	36	31	27	31	26	23	25	22	20	17
8	54	41	34	28	49	39	32	27	33	28	24	28	24	21	23	20	17	15
9	50	38	30	25	46	35	28	24	30	25	21	26	21	18	21	18	16	14
10	47	35	27	23	43	32	26	21	28	23	19	24	20	17	20	17	14	12

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	9556	9556	9556
5°	9585	9469	9539
10°	9525	9393	9439
15°	9410	9260	9283
20°	9257	9094	9101
25°	9082	8905	8879
30°	8869	8682	8603
35°	8647	8451	8339
40°	8416	8186	8037
45°	8176	7927	7775
50°	7910	7695	7458
55°	7623	7396	7156
60°	7335	7061	6846
65°	7011	6739	6468
70°	6649	6314	6069
75°	6095	5798	5652
80°	5421	5202	5072
85°	4742	4566	4474



TEST NUMBER: P332614-940

CATALOG NUMBER: S124DIP-S795D1035U940-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	111.5	1.8
10°-20°	314.1	5.0
20°-30°	462.3	7.4
30°-40°	537.4	8.6
40°-50°	537.5	8.6
50°-60°	470.1	7.5
60°-70°	349.1	5.6
70°-80°	198.4	3.2
80°-90°	60.7	1.0
90°-100°	75.9	1.2
100°-110°	224.9	3.6
110°-120°	381.7	6.1
120°-130°	503.2	8.1
130°-140°	565.2	9.1
140°-150°	555.4	8.9
150°-160°	467.1	7.5
160°-170°	310.8	5.0
170°-180°	108.8	1.7
0°-30°	887.8	14.2
0°-40°	1425.3	22.9
0°-60°	2432.8	39.0
0°-90°	3041.0	48.8
90°-120°	682.4	10.9
90°-150°	2306.2	37.0
90°-180°	3193.0	51.2
0°-180°	6233.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1184	1184	1184	1184	1184	
5°	1183	1179	1168	1178	1177	112
15°	1126	1122	1108	1113	1111	317
25°	1020	1013	1000	1000	997	469
35°	877	870	858	851	846	548
45°	716	709	694	684	681	552
55°	542	538	526	514	508	485
65°	367	362	353	344	339	363
75°	195	191	186	182	181	208
85°	51	51	49	49	48	56
90°	3	12	20	25	27	6
95°	53	61	68	70	70	59
105°	207	208	212	214	217	220
115°	388	388	386	385	384	383
125°	565	565	564	562	561	504
135°	729	734	734	732	730	564
145°	886	889	890	889	886	554
155°	1015	1015	1014	1017	1014	467
165°	1105	1102	1100	1105	1102	311
175°	1149	1145	1144	1149	1144	109
180°	1151	1151	1151	1151	1151	



TEST NUMBER: P332614-940

CATALOG NUMBER: S124DIP-S795D1035U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1183.7	1183.7	1183.7	1183.7	1183.7	1183.7	1183.7	1183.7	1183.7	1183.7	1183.7
2.5°	1186.8	1186.2	1185.7	1185.3	1184.7	1183.6	1181.7	1179.8	1177.9	1176.2	1177.8
5°	1182.8	1182.0	1181.1	1180.3	1179.4	1177.8	1175.5	1173.1	1170.8	1168.5	1170.8
7.5°	1171.8	1170.9	1170.1	1169.2	1168.4	1166.7	1164.1	1161.5	1159.0	1156.4	1158.2
10°	1161.9	1161.1	1160.2	1159.4	1158.5	1156.7	1154.0	1151.3	1148.5	1145.8	1147.5
12.5°	1149.0	1148.2	1147.3	1146.5	1145.7	1143.7	1140.9	1137.9	1135.1	1132.1	1134.0
15°	1125.9	1125.0	1124.2	1123.3	1122.5	1120.5	1117.3	1114.2	1111.0	1107.9	1109.1
17.5°	1098.0	1096.9	1095.8	1094.8	1093.8	1091.7	1088.8	1085.7	1082.7	1079.8	1080.6
20°	1077.5	1076.4	1075.4	1074.3	1073.3	1071.1	1068.0	1064.8	1061.7	1058.5	1059.2
22.5°	1055.5	1054.1	1052.7	1051.3	1049.9	1047.7	1044.5	1041.3	1038.1	1035.0	1036.2
25°	1019.6	1018.2	1016.6	1015.2	1013.7	1011.5	1008.5	1005.6	1002.6	999.7	999.9
27.5°	978.7	977.1	975.6	974.1	972.6	970.4	967.7	965.0	962.2	959.5	958.9
30°	951.4	949.7	948.0	946.3	944.6	942.4	939.6	936.9	934.2	931.4	930.6
32.5°	922.5	921.0	919.4	917.9	916.4	914.2	911.3	908.4	905.5	902.6	901.6
35°	877.4	875.8	874.4	872.9	871.5	869.2	866.3	863.4	860.4	857.5	856.0
37.5°	829.7	828.4	827.1	825.7	824.3	822.1	818.9	815.7	812.6	809.4	807.8
40°	798.6	796.9	795.2	793.5	791.8	789.4	786.3	783.1	780.0	776.8	774.7
42.5°	765.3	764.2	763.2	762.2	761.2	758.9	755.5	752.0	748.4	744.9	742.5
45°	716.1	714.6	713.2	711.7	710.2	707.8	704.5	701.1	697.7	694.3	692.0
47.5°	664.7	663.7	662.7	661.6	660.7	658.6	655.5	652.4	649.3	646.1	643.5
50°	629.8	628.9	628.1	627.2	626.4	624.6	621.6	618.7	615.6	612.7	609.8
52.5°	595.7	594.7	593.6	592.6	591.6	589.5	586.4	583.3	580.1	577.0	574.4
55°	541.6	540.9	540.3	539.7	539.0	537.3	534.3	531.4	528.4	525.5	522.9
57.5°	490.0	489.3	488.6	487.9	487.1	485.3	482.4	479.5	476.6	473.7	471.3
60°	454.3	453.3	452.2	451.2	450.1	448.2	445.5	442.7	440.0	437.3	435.3
62.5°	419.5	418.6	417.7	416.8	415.9	414.0	411.1	408.1	405.3	402.3	400.6
65°	367.0	366.0	365.0	363.9	362.8	361.2	359.2	357.0	354.9	352.8	350.7
67.5°	314.3	313.3	312.4	311.4	310.5	309.0	306.9	304.9	302.9	300.9	298.8
70°	281.7	280.3	278.7	277.2	275.8	274.2	272.5	270.8	269.1	267.5	265.8
72.5°	246.8	245.3	243.9	242.4	240.9	239.5	238.2	236.7	235.4	234.1	232.7
75°	195.4	194.3	193.3	192.3	191.2	190.1	189.0	188.0	187.0	185.9	185.0
77.5°	146.2	145.8	145.3	144.9	144.4	143.7	142.8	141.9	140.9	140.0	139.7
80°	116.6	116.0	115.4	114.8	114.1	113.6	113.2	112.8	112.4	111.9	111.5
82.5°	87.8	87.6	87.2	86.9	86.7	86.5	86.4	86.3	86.2	86.1	85.9
85°	51.2	51.2	51.2	51.2	51.2	51.0	50.6	50.2	49.8	49.3	49.3
87.5°	20.2	20.5	20.8	21.0	21.3	21.6	21.7	21.8	21.9	22.1	22.4
90°	2.7	4.8	7.0	9.2	11.4	13.3	14.8	16.4	18.0	19.6	20.8
92.5°	19.1	21.6	24.0	26.5	29.0	30.9	31.9	33.0	34.2	35.2	35.9
95°	53.4	55.2	57.0	58.8	60.5	62.1	63.5	64.9	66.3	67.7	68.2
97.5°	93.3	94.7	96.1	97.6	99.0	100.5	102.1	103.7	105.4	107.0	107.7
100°	124.6	125.4	126.2	127.0	127.8	129.0	130.8	132.6	134.4	136.2	136.6
102.5°	157.4	157.7	158.0	158.3	158.6	159.6	161.2	162.8	164.4	166.1	166.7
105°	207.4	207.6	207.8	207.9	208.2	208.7	209.5	210.3	211.1	211.9	212.4
107.5°	259.9	260.1	260.4	260.6	260.8	261.0	261.2	261.3	261.4	261.5	262.1
110°	295.5	295.9	296.3	296.7	297.1	297.2	296.9	296.8	296.6	296.4	296.0



TEST NUMBER: P332614-940

CATALOG NUMBER: S124DIP-S795D1035U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	332.5	332.6	332.7	332.8	332.9	332.7	332.3	332.0	331.6	331.3	331.2
115°	388.1	388.1	388.1	388.1	388.1	387.9	387.4	387.1	386.6	386.3	386.1
117.5°	440.4	440.6	440.7	440.9	441.0	441.0	440.7	440.4	440.1	439.9	439.2
120°	475.3	476.1	476.9	477.7	478.5	478.6	478.0	477.3	476.8	476.2	475.2
122.5°	511.6	511.9	512.2	512.6	512.8	512.9	512.6	512.3	512.0	511.8	511.1
125°	565.2	565.2	565.2	565.2	565.2	565.1	564.9	564.7	564.5	564.3	563.9
127.5°	613.8	614.4	614.9	615.5	616.2	616.3	616.0	615.6	615.4	615.0	614.7
130°	647.9	648.5	649.2	649.7	650.3	650.6	650.6	650.6	650.6	650.6	650.2
132.5°	682.9	683.3	683.7	684.1	684.6	684.7	684.6	684.4	684.2	684.1	683.7
135°	729.0	730.1	731.3	732.5	733.7	734.3	734.3	734.3	734.3	734.3	733.9
137.5°	779.2	779.7	780.2	780.8	781.4	781.8	782.1	782.5	782.7	783.1	782.6
140°	812.6	813.0	813.4	813.8	814.2	814.4	814.4	814.4	814.4	814.4	814.2
142.5°	843.2	843.6	844.0	844.5	844.8	844.9	844.8	844.6	844.5	844.3	844.3
145°	885.6	886.4	887.2	888.0	888.8	889.2	889.5	889.7	889.8	890.0	889.8
147.5°	927.6	928.5	929.5	930.5	931.4	931.8	931.7	931.5	931.3	931.2	931.0
150°	953.2	954.0	954.8	955.6	956.4	956.8	956.8	956.8	956.8	956.8	956.8
152.5°	977.5	977.9	978.4	978.9	979.4	979.6	979.8	980.0	980.2	980.3	980.8
155°	1014.7	1014.7	1014.7	1014.7	1014.7	1014.6	1014.3	1014.1	1014.0	1013.8	1014.6
157.5°	1046.0	1045.6	1045.3	1044.9	1044.6	1044.4	1044.3	1044.3	1044.3	1044.2	1044.8
160°	1064.5	1064.3	1064.1	1063.9	1063.7	1063.5	1063.3	1063.1	1062.9	1062.7	1063.3
162.5°	1081.6	1081.1	1080.6	1080.0	1079.5	1079.1	1079.0	1078.8	1078.6	1078.3	1079.4
165°	1104.6	1103.9	1103.4	1102.8	1102.2	1101.7	1101.3	1100.9	1100.5	1100.1	1101.3
167.5°	1122.2	1121.3	1120.5	1119.7	1118.8	1118.5	1118.5	1118.6	1118.6	1118.7	1119.8
170°	1132.1	1131.1	1130.2	1129.2	1128.2	1127.7	1128.0	1128.2	1128.4	1128.5	1129.8
172.5°	1139.2	1138.4	1137.6	1136.8	1136.0	1135.5	1135.6	1135.6	1135.7	1135.7	1137.0
175°	1149.1	1148.1	1147.1	1146.1	1145.1	1144.5	1144.3	1144.1	1143.9	1143.7	1145.1
177.5°	1152.3	1151.5	1150.7	1149.9	1149.1	1148.7	1148.7	1148.7	1148.7	1148.7	1149.8
180°	1150.8	1150.8	1150.8	1150.8	1150.8	1150.8	1150.8	1150.8	1150.8	1150.8	1150.8



TEST NUMBER: P332614-940

CATALOG NUMBER: S124DIP-S795D1035U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1183.7	1183.7	1183.7	1183.7	1183.7	1183.7	1183.7	1183.7
2.5°	1179.5	1181.2	1182.9	1183.7	1183.5	1183.3	1183.1	1182.9
5°	1173.1	1175.5	1177.8	1178.8	1178.3	1177.9	1177.5	1177.1
7.5°	1160.1	1162.0	1163.8	1164.6	1164.4	1164.1	1163.9	1163.6
10°	1149.1	1150.8	1152.5	1153.2	1152.7	1152.3	1151.9	1151.5
12.5°	1135.9	1137.6	1139.5	1140.1	1139.6	1139.0	1138.4	1137.8
15°	1110.4	1111.6	1112.9	1113.2	1112.6	1112.0	1111.3	1110.7
17.5°	1081.4	1082.2	1083.0	1083.2	1082.7	1082.3	1081.9	1081.5
20°	1059.8	1060.4	1061.0	1061.1	1060.7	1060.3	1059.9	1059.4
22.5°	1037.2	1038.4	1039.6	1039.7	1038.9	1038.2	1037.4	1036.7
25°	1000.1	1000.3	1000.6	1000.2	999.4	998.5	997.7	996.8
27.5°	958.5	958.0	957.4	956.7	955.6	954.6	953.5	952.4
30°	929.7	928.9	928.0	927.1	926.0	925.0	923.9	922.9
32.5°	900.5	899.6	898.6	897.5	896.4	895.4	894.3	893.3
35°	854.5	853.0	851.5	850.2	849.2	848.2	847.1	846.1
37.5°	806.2	804.6	803.1	801.6	800.1	798.8	797.4	795.9
40°	772.6	770.5	768.4	766.8	765.7	764.7	763.7	762.6
42.5°	740.0	737.6	735.1	733.6	732.9	732.2	731.5	730.8
45°	689.6	687.3	685.0	683.6	682.9	682.2	681.6	681.0
47.5°	640.9	638.3	635.6	633.6	632.0	630.4	628.7	627.1
50°	606.8	603.9	600.9	598.8	597.5	596.3	595.0	593.8
52.5°	571.9	569.2	566.6	564.5	562.9	561.3	559.7	558.1
55°	520.4	517.9	515.3	513.4	512.2	511.0	509.6	508.4
57.5°	468.9	466.5	464.0	462.3	461.0	459.8	458.6	457.4
60°	433.5	431.6	429.6	428.2	427.1	426.1	425.0	424.0
62.5°	398.9	397.2	395.5	394.0	393.0	391.9	390.9	389.9
65°	348.7	346.5	344.4	342.9	341.8	340.7	339.7	338.6
67.5°	296.9	294.8	292.7	291.6	291.3	291.1	290.7	290.4
70°	264.1	262.4	260.7	259.6	259.0	258.3	257.7	257.1
72.5°	231.4	230.1	228.7	227.7	227.0	226.4	225.8	225.2
75°	184.2	183.3	182.5	182.0	181.8	181.6	181.4	181.2
77.5°	139.5	139.2	139.0	138.6	138.0	137.5	137.0	136.4
80°	111.1	110.7	110.2	109.9	109.7	109.5	109.3	109.1
82.5°	85.6	85.3	85.1	84.9	84.7	84.4	84.3	84.0
85°	49.3	49.3	49.3	49.2	49.0	48.8	48.6	48.3
87.5°	22.6	22.8	23.1	23.3	23.3	23.4	23.5	23.5
90°	21.9	23.2	24.3	25.1	25.5	25.9	26.3	26.7
92.5°	36.6	37.4	38.1	38.6	38.8	39.1	39.3	39.5
95°	68.8	69.5	70.0	70.4	70.4	70.4	70.4	70.4
97.5°	108.4	109.1	109.9	110.2	110.2	110.2	110.2	110.2
100°	137.0	137.3	137.8	137.9	137.9	137.9	137.9	137.9
102.5°	167.2	167.7	168.3	168.6	168.8	169.0	169.2	169.2
105°	213.0	213.7	214.2	214.8	215.3	216.0	216.6	217.1
107.5°	262.6	263.1	263.7	263.9	263.9	263.9	263.9	263.8
110°	295.6	295.2	294.8	294.9	295.5	296.0	296.7	297.3





TEST NUMBER: P332614-940

CATALOG NUMBER: S124DIP-S795D1035U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	331.1	331.0	331.0	331.0	331.1	331.2	331.4	331.4
115°	385.8	385.7	385.5	385.3	385.1	384.9	384.7	384.5
117.5°	438.5	437.8	437.2	436.7	436.2	435.9	435.4	435.1
120°	474.2	473.2	472.3	471.9	472.3	472.7	473.1	473.5
122.5°	510.4	509.8	509.1	508.4	507.7	506.9	506.2	505.5
125°	563.5	563.1	562.7	562.3	562.0	561.5	561.2	560.7
127.5°	614.2	613.9	613.4	613.1	612.8	612.4	612.2	611.8
130°	649.9	649.4	649.1	648.5	647.6	646.8	646.0	645.2
132.5°	683.3	682.9	682.5	682.2	681.8	681.5	681.2	680.9
135°	733.5	733.1	732.7	732.2	731.6	731.0	730.4	729.9
137.5°	782.0	781.5	781.0	780.8	781.0	781.0	781.1	781.3
140°	814.0	813.8	813.6	813.4	813.2	813.0	812.8	812.6
142.5°	844.2	844.2	844.2	844.1	844.1	844.0	844.0	843.9
145°	889.7	889.5	889.2	888.9	888.2	887.7	887.1	886.4
147.5°	930.9	930.7	930.5	930.3	930.1	930.0	929.8	929.6
150°	956.8	956.8	956.8	956.7	956.5	956.3	956.1	955.9
152.5°	981.2	981.7	982.2	982.2	981.7	981.1	980.6	980.1
155°	1015.4	1016.1	1016.9	1016.9	1016.1	1015.4	1014.6	1013.8
157.5°	1045.4	1046.0	1046.6	1046.5	1045.9	1045.2	1044.6	1043.8
160°	1063.9	1064.5	1065.1	1064.9	1063.9	1062.9	1061.9	1061.0
162.5°	1080.5	1081.6	1082.6	1082.7	1081.7	1080.8	1079.8	1078.7
165°	1102.5	1103.7	1104.8	1105.0	1104.3	1103.5	1102.7	1101.9
167.5°	1121.0	1122.2	1123.4	1123.4	1122.1	1120.9	1119.6	1118.5
170°	1131.0	1132.1	1133.4	1133.2	1131.8	1130.4	1129.1	1127.7
172.5°	1138.4	1139.7	1141.1	1141.0	1139.7	1138.3	1136.9	1135.5
175°	1146.5	1147.9	1149.2	1149.2	1147.9	1146.5	1145.1	1143.7
177.5°	1150.9	1152.0	1153.2	1153.1	1151.8	1150.5	1149.2	1148.0
180°	1150.8	1150.8	1150.8	1150.8	1150.8	1150.8	1150.8	1150.8

(END OF REPORT)