

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332591-940

Luminaire Tested: **S124DIP-S795D590U940-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332591-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124DIP-S795D590U940-4F0-1E-UDD-A4  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 795 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 590 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5043.1 lumens  
Efficiency: N/A  
Efficacy: 125.1 lumens/watt  
Spacing Criteria (0/90/45): 1.31 / 1.23 / 1.41  
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 40.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332591-940

CATALOG NUMBER: S124DIP-S795D590U940-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P332591-940

CATALOG NUMBER: S124DIP-S795D590U940-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	79	79	79	68	68	68	63
1	101	97	93	89	94	91	87	84	80	77	75	70	68	66	60	59	58	53
2	92	85	79	73	86	80	74	70	70	66	62	61	58	56	53	51	49	45
3	84	75	67	62	79	70	64	59	62	57	53	55	51	47	48	45	42	39
4	77	66	58	52	72	63	55	50	55	50	45	49	44	41	43	39	37	33
5	71	59	51	45	66	56	49	43	50	44	39	44	39	36	39	35	32	29
6	66	53	45	39	61	51	43	38	45	39	35	40	35	31	35	31	28	26
7	61	48	40	35	57	46	39	33	41	35	31	36	32	28	32	28	25	23
8	56	44	36	31	53	42	35	30	37	32	27	33	29	25	30	26	23	20
9	53	40	33	28	49	38	31	27	34	29	25	31	26	23	27	23	21	19
10	49	37	30	25	46	35	29	24	32	26	22	28	24	20	25	22	19	17

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	9243	9243	9243	9243
5°	10884	9266	8178	9266
10°	13032	9225	7363	9225
15°	15419	9132	6761	9132
20°	17169	9037	6225	9037
25°	17446	8897	5855	8897
30°	14845	8763	5738	8763
35°	11413	8544	5740	8544
40°	8897	8286	5848	8286
45°	7418	7900	5946	7900
50°	6528	7428	6148	7428
55°	5980	6861	6394	6861
60°	5604	6355	6692	6355
65°	5217	5788	6940	5788
70°	4770	5228	7098	5228
75°	4261	4601	7012	4601
80°	3575	3770	6792	3770
85°	2631	2723	6502	2723



TEST NUMBER: P332591-940

CATALOG NUMBER: S124DIP-S795D590U940-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	111.5	2.2
10°-20°	343.8	6.8
20°-30°	545.1	10.8
30°-40°	606.7	12.0
40°-50°	552.2	11.0
50°-60°	451.3	8.9
60°-70°	322.2	6.4
70°-80°	177.4	3.5
80°-90°	49.9	1.0
90°-100°	187.0	3.7
100°-110°	389.2	7.7
110°-120°	348.6	6.9
120°-130°	293.2	5.8
130°-140°	244.5	4.8
140°-150°	186.8	3.7
150°-160°	131.3	2.6
160°-170°	77.2	1.5
170°-180°	25.1	0.5
0°-30°	1000.4	19.8
0°-40°	1607.1	31.9
0°-60°	2610.6	51.8
0°-90°	3160.0	62.7
90°-120°	924.8	18.3
90°-150°	1649.4	32.7
90°-180°	1883.0	37.3
0°-180°	5043.1	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1145	1145	1145	1145	1145	
5°	1343	1143	1009	1143	1343	137
15°	1845	1093	809	1093	1845	521
25°	1959	999	657	999	1959	863
35°	1158	867	582	867	1158	735
45°	650	692	521	692	650	512
55°	425	488	454	488	425	384
65°	273	303	363	303	273	270
75°	137	148	225	148	137	145
85°	28	29	70	29	28	35
90°	11	0	11	0	11	10
95°	124	17	124	17	124	193
105°	716	60	716	60	716	708
115°	687	105	687	105	687	682
125°	548	146	548	146	548	498
135°	490	173	490	173	490	379
145°	400	200	400	200	400	254
155°	335	227	335	227	335	156
165°	292	248	292	248	292	84
175°	264	258	264	258	264	26
180°	259	259	259	259	259	



TEST NUMBER: P332591-940

CATALOG NUMBER: S124DIP-S795D590U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1144.9	1144.9	1144.9	1144.9	1144.9	1144.9	1144.9	1144.9	1144.9	1144.9	1144.9
2.5°	1218.4	1218.1	1214.2	1213.5	1210.9	1207.5	1206.7	1200.6	1188.5	1182.8	1181.2
5°	1343.1	1352.5	1340.2	1337.8	1336.4	1320.8	1312.7	1303.2	1281.4	1268.6	1258.6
7.5°	1491.8	1492.9	1487.6	1483.2	1471.1	1457.4	1437.0	1415.1	1389.2	1362.1	1341.8
10°	1589.7	1593.5	1587.3	1586.4	1562.2	1547.0	1516.6	1491.0	1461.6	1428.9	1399.0
12.5°	1692.9	1687.6	1684.4	1664.1	1659.7	1632.0	1596.7	1570.3	1525.0	1487.4	1447.6
15°	1844.9	1834.4	1827.7	1799.7	1786.0	1747.6	1710.1	1681.2	1621.9	1565.5	1522.8
17.5°	1933.9	1944.4	1929.0	1917.5	1882.0	1855.0	1816.8	1756.0	1709.7	1639.6	1585.7
20°	1998.5	1999.4	1990.9	1979.1	1951.1	1916.9	1875.2	1808.7	1753.3	1683.6	1609.6
22.5°	2015.9	2016.2	2012.5	2001.4	1980.2	1952.6	1910.5	1855.0	1787.8	1712.0	1638.1
25°	1958.6	1956.8	1961.1	1973.4	1965.2	1956.8	1932.5	1891.3	1828.7	1748.6	1668.8
27.5°	1745.8	1758.9	1783.0	1813.3	1842.5	1864.8	1871.1	1862.6	1823.8	1757.9	1674.5
30°	1592.5	1608.6	1626.7	1657.0	1715.8	1749.5	1786.5	1814.5	1798.8	1746.1	1668.4
32.5°	1424.1	1428.1	1454.8	1489.3	1543.2	1608.0	1666.6	1723.4	1742.3	1714.7	1649.8
35°	1158.1	1164.8	1193.6	1227.8	1293.8	1373.0	1461.2	1539.9	1604.8	1630.9	1597.8
37.5°	945.0	964.1	984.5	1021.3	1079.3	1150.6	1242.2	1344.1	1440.9	1505.8	1516.8
40°	844.2	856.0	870.8	898.7	948.0	1018.2	1096.9	1213.6	1316.5	1409.4	1439.8
42.5°	764.5	771.4	780.4	805.7	843.3	913.1	985.0	1087.6	1191.0	1302.1	1352.9
45°	649.7	656.8	672.0	686.7	715.2	763.6	830.4	914.8	1018.7	1125.9	1219.8
47.5°	566.9	571.4	580.4	596.1	620.3	652.2	706.6	777.1	873.3	977.4	1077.5
50°	519.8	523.5	530.7	544.9	563.4	591.8	636.4	702.4	777.8	882.6	980.7
52.5°	482.6	484.1	489.4	499.0	513.7	537.6	574.2	628.7	698.8	792.3	890.1
55°	424.9	426.9	431.6	438.7	451.5	466.6	494.6	535.4	596.6	677.7	762.6
57.5°	377.5	378.8	382.8	385.6	396.1	408.4	430.0	459.1	505.4	574.2	650.0
60°	347.1	346.2	351.0	353.3	360.4	370.9	387.4	415.4	455.8	511.2	580.9
62.5°	317.5	316.2	320.2	323.3	327.4	336.4	349.9	371.8	404.6	454.7	515.0
65°	273.1	271.3	273.7	277.4	281.2	286.0	296.0	315.4	341.4	377.5	423.5
67.5°	228.5	230.6	231.0	232.8	235.1	241.5	248.3	262.1	280.4	309.3	348.3
70°	202.1	202.5	204.4	204.4	205.8	211.5	217.2	225.2	243.3	269.8	301.6
72.5°	175.5	177.5	176.7	178.3	179.2	183.1	187.3	194.9	210.3	230.0	256.8
75°	136.6	138.0	138.0	138.5	139.9	141.3	144.6	150.3	161.2	175.9	194.5
77.5°	99.6	99.8	100.4	102.2	102.2	104.4	106.9	111.5	116.8	126.9	138.2
80°	76.9	77.8	77.3	78.3	78.3	80.2	81.1	86.8	89.2	95.8	104.8
82.5°	56.4	57.2	57.2	58.5	59.3	59.7	61.0	63.2	65.6	71.5	75.2
85°	28.4	29.4	28.4	29.4	30.9	31.3	32.7	33.2	35.1	36.6	39.9
87.5°	10.5	11.6	11.7	12.0	12.7	13.0	13.3	12.8	14.3	14.7	16.1
90°	10.7	10.7	11.1	10.7	10.2	10.2	9.6	9.2	8.6	9.2	8.1
92.5°	39.1	39.1	40.9	43.6	49.7	59.8	75.2	99.9	134.4	161.3	141.2
95°	124.1	130.7	139.9	155.7	180.6	229.9	298.1	376.9	426.2	414.6	312.8
97.5°	331.7	342.3	357.6	388.3	424.7	477.9	527.6	556.9	535.6	436.7	292.8
100°	466.5	470.6	485.8	516.8	561.1	598.7	623.7	613.5	539.2	408.9	265.6
102.5°	583.6	586.9	603.0	625.4	652.6	668.3	661.1	610.6	508.6	374.4	247.2
105°	715.7	718.7	725.9	730.0	729.0	708.1	657.7	569.7	453.3	333.7	231.5
107.5°	764.7	763.4	758.3	746.7	721.6	676.3	605.3	511.7	408.5	310.9	228.6
110°	765.5	761.0	751.8	730.5	694.4	638.4	564.6	476.6	386.1	303.2	229.4



TEST NUMBER: P332591-940

CATALOG NUMBER: S124DIP-S795D590U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	741.5	734.1	721.3	695.4	654.4	598.5	528.8	451.0	373.4	299.5	231.8
115°	687.2	683.1	666.9	636.3	596.2	547.3	487.9	425.3	361.7	297.6	236.6
117.5°	632.2	629.0	612.5	586.9	552.6	511.2	464.4	412.6	356.4	297.0	241.5
120°	601.3	595.7	582.5	560.1	531.0	494.9	454.2	407.0	353.6	297.0	245.2
122.5°	576.8	571.2	560.1	540.9	516.4	484.7	447.7	402.1	350.3	296.7	248.9
125°	548.3	545.3	535.7	520.8	500.5	472.5	437.5	393.7	344.9	296.0	254.3
127.5°	531.6	528.6	520.5	507.4	486.9	460.4	425.3	383.5	337.7	294.9	258.7
130°	521.9	518.9	510.7	498.0	477.2	450.1	415.6	375.4	333.1	294.5	262.0
132.5°	511.0	507.8	500.2	485.8	465.3	438.4	404.6	366.8	329.1	294.1	264.8
135°	490.4	487.3	479.2	464.9	444.6	419.1	388.2	355.1	323.0	293.5	269.1
137.5°	464.9	461.3	454.6	440.5	421.5	398.5	372.4	344.4	317.7	293.4	271.6
140°	446.7	442.6	435.4	424.3	406.4	385.0	362.2	338.2	314.9	293.0	273.7
142.5°	427.0	424.3	417.9	407.5	391.8	373.3	353.7	332.6	312.5	293.0	275.3
145°	400.3	397.8	392.7	384.1	371.3	357.1	341.8	324.5	308.3	291.9	276.3
147.5°	376.7	375.7	371.8	364.4	355.1	343.8	331.6	317.9	304.5	290.2	276.7
150°	363.2	362.7	359.6	353.0	344.9	335.7	325.6	313.9	301.7	288.9	276.7
152.5°	351.0	350.4	348.7	343.2	336.4	328.8	319.4	309.3	298.4	286.9	275.9
155°	335.2	335.2	333.7	329.7	324.5	318.4	310.8	302.6	293.5	283.8	274.6
157.5°	321.4	321.4	320.5	317.4	313.5	308.6	302.3	295.4	288.6	280.7	273.4
160°	312.8	312.8	312.4	309.2	306.2	302.1	296.6	291.0	284.9	278.2	272.2
162.5°	304.7	305.1	304.6	301.6	299.3	295.6	291.2	286.5	281.6	275.8	270.9
165°	292.5	293.0	293.5	291.5	289.4	286.9	283.3	280.3	276.3	272.2	268.6
167.5°	282.9	283.2	283.3	282.0	281.0	279.5	276.6	274.3	271.3	268.5	266.2
170°	276.7	276.7	277.2	276.7	275.7	274.2	272.2	270.6	268.0	266.0	264.5
172.5°	270.6	271.4	272.0	271.4	270.8	269.7	268.5	267.3	265.2	263.6	262.9
175°	263.5	264.5	265.6	264.5	264.5	264.5	263.5	263.0	262.0	260.9	260.9
177.5°	259.3	260.1	260.9	260.6	260.9	260.6	260.6	260.1	259.8	259.3	259.3
180°	259.0	259.0	259.0	259.0	259.0	259.0	259.0	259.0	259.0	259.0	259.0



TEST NUMBER: P332591-940

CATALOG NUMBER: S124DIP-S795D590U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1144.9	1144.9	1144.9	1144.9	1144.9	1144.9	1144.9	1144.9	1144.9	1144.9	1144.9
2.5°	1181.6	1176.3	1172.5	1169.5	1161.2	1156.2	1152.4	1147.1	1141.0	1134.6	1126.6
5°	1248.7	1232.5	1220.8	1202.7	1185.6	1171.4	1156.7	1143.4	1127.3	1109.7	1096.9
7.5°	1319.2	1295.2	1264.4	1237.8	1207.8	1181.7	1158.4	1134.5	1109.6	1085.6	1063.5
10°	1364.0	1333.1	1299.0	1258.6	1220.8	1187.0	1155.7	1125.4	1096.0	1066.6	1041.4
12.5°	1412.1	1373.7	1323.2	1276.1	1233.6	1188.6	1150.8	1113.7	1078.2	1047.2	1017.9
15°	1476.8	1421.3	1363.0	1299.9	1243.9	1191.3	1139.6	1092.7	1052.8	1012.0	983.6
17.5°	1516.5	1447.9	1381.2	1315.3	1247.6	1181.2	1125.4	1071.2	1021.4	980.8	944.9
20°	1542.7	1474.4	1391.4	1325.5	1244.9	1176.6	1112.1	1051.9	999.7	956.5	919.5
22.5°	1565.5	1486.6	1403.6	1316.8	1236.5	1164.1	1093.5	1032.9	979.6	934.2	898.7
25°	1577.8	1487.2	1397.1	1310.8	1219.8	1133.9	1069.9	998.8	941.8	893.9	856.0
27.5°	1579.1	1482.3	1380.4	1284.4	1190.4	1110.5	1029.7	966.2	907.0	856.4	819.9
30°	1574.9	1474.0	1364.4	1260.5	1166.2	1079.4	1009.2	940.0	879.8	829.5	791.5
32.5°	1561.7	1456.5	1343.9	1233.9	1136.2	1051.3	978.8	913.0	854.3	804.8	765.0
35°	1523.3	1419.4	1299.4	1185.2	1085.0	999.3	933.8	866.9	808.2	761.2	722.7
37.5°	1463.2	1369.3	1247.3	1129.1	1030.8	944.6	879.8	819.3	766.2	718.5	679.2
40°	1410.9	1328.4	1206.0	1090.7	984.5	902.5	841.8	786.3	733.7	688.6	651.1
42.5°	1350.6	1278.6	1165.8	1043.7	941.3	858.9	799.7	749.8	700.3	658.6	621.2
45°	1243.0	1195.6	1089.3	976.5	869.8	792.0	735.6	692.0	650.2	609.4	578.1
47.5°	1119.3	1095.8	1006.4	899.2	797.9	721.2	672.3	632.0	595.4	560.9	533.2
50°	1036.3	1024.8	947.5	844.2	747.4	675.3	626.0	591.4	560.1	529.8	503.6
52.5°	954.3	953.9	884.2	789.5	700.0	630.5	581.6	549.3	522.2	497.5	474.0
55°	829.0	842.2	787.7	703.3	623.1	560.5	516.5	487.5	468.6	448.2	430.6
57.5°	713.9	735.9	691.0	616.6	549.7	492.0	453.7	431.9	411.7	399.4	386.6
60°	638.8	659.7	624.6	562.0	498.9	449.6	413.0	393.6	376.0	367.6	358.6
62.5°	572.0	590.7	564.6	506.6	451.8	404.5	373.6	354.9	343.0	333.8	327.8
65°	476.6	492.2	470.0	427.8	380.8	342.9	317.7	303.0	291.7	287.8	281.2
67.5°	385.3	399.5	387.4	351.6	314.0	285.2	265.6	251.5	244.7	241.4	236.7
70°	331.0	345.3	332.4	301.1	272.2	248.1	229.5	221.5	214.4	212.9	206.3
72.5°	285.1	294.8	282.0	257.5	232.7	212.4	198.0	189.6	185.9	183.3	179.8
75°	213.9	222.4	213.9	194.9	177.4	163.2	150.8	147.5	143.2	141.8	139.5
77.5°	151.4	158.8	152.2	140.4	127.2	116.3	109.7	105.4	104.4	101.9	103.1
80°	115.7	120.5	114.3	106.2	95.8	88.2	83.5	81.1	78.3	77.3	79.2
82.5°	83.1	85.2	82.0	76.6	68.8	63.9	60.7	58.0	57.4	57.6	57.6
85°	43.2	42.7	42.2	37.5	35.1	31.7	29.9	29.4	28.9	29.9	30.9
87.5°	15.9	16.2	15.2	13.7	12.5	11.2	10.5	10.0	10.5	11.2	11.7
90°	7.1	7.1	4.1	4.1	3.6	3.0	1.5	0.5	1.5	3.0	3.6
92.5°	102.7	63.3	37.5	26.8	19.4	13.2	8.5	5.8	8.5	13.2	19.4
95°	191.3	107.8	63.6	42.2	30.1	23.4	18.3	16.8	18.3	23.4	30.1
97.5°	171.9	103.1	69.0	51.1	40.6	34.5	30.1	30.1	30.1	34.5	40.6
100°	161.8	104.2	74.3	58.0	48.3	42.2	38.7	38.7	38.7	42.2	48.3
102.5°	158.9	108.3	81.1	65.7	56.4	50.7	47.6	46.8	47.6	50.7	56.4
105°	160.2	118.0	93.6	78.8	69.7	63.6	61.1	59.5	61.1	63.6	69.7
107.5°	167.7	129.3	106.9	92.4	83.6	77.1	74.5	73.6	74.5	77.1	83.6
110°	173.4	137.9	115.5	101.7	92.6	86.5	83.9	82.9	83.9	86.5	92.6





TEST NUMBER: P332591-940

CATALOG NUMBER: S124DIP-S795D590U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	179.6	146.0	124.4	110.7	101.6	95.9	92.9	91.8	92.9	95.9	101.6
115°	189.2	158.7	138.4	124.7	114.9	109.9	106.3	104.8	106.3	109.9	114.9
117.5°	199.1	171.0	151.7	137.4	128.4	122.8	119.7	118.2	119.7	122.8	128.4
120°	206.0	179.6	160.2	146.0	137.3	131.7	128.2	127.2	128.2	131.7	137.3
122.5°	212.5	187.7	168.4	154.5	145.1	139.9	136.3	135.3	136.3	139.9	145.1
125°	222.3	198.9	180.6	166.3	156.7	151.1	148.0	146.0	148.0	151.1	156.7
127.5°	230.8	209.3	191.5	177.2	167.1	160.8	157.1	155.4	157.1	160.8	167.1
130°	236.0	216.2	198.9	184.1	174.5	166.8	162.7	160.8	162.7	166.8	174.5
132.5°	241.3	221.9	204.6	190.6	180.2	173.0	167.6	166.0	167.6	173.0	180.2
135°	248.3	229.9	213.1	199.9	189.2	180.6	175.5	173.4	175.5	180.6	189.2
137.5°	253.2	236.0	220.3	207.8	196.6	188.4	182.8	180.9	182.8	188.4	196.6
140°	256.4	240.1	224.8	212.6	202.0	193.3	187.7	186.2	187.7	193.3	202.0
142.5°	258.8	243.8	228.9	217.1	206.8	198.6	193.4	191.9	193.4	198.6	206.8
145°	261.4	247.7	234.5	223.3	213.7	206.5	201.4	199.9	201.4	206.5	213.7
147.5°	263.8	251.8	239.4	229.3	221.2	213.9	209.5	208.9	209.5	213.9	221.2
150°	265.0	253.9	242.6	233.0	225.3	219.3	215.2	214.6	215.2	219.3	225.3
152.5°	265.8	255.5	245.5	236.7	229.8	224.1	220.1	220.0	220.1	224.1	229.8
155°	266.5	257.9	249.2	241.7	236.0	231.0	227.9	227.4	227.9	231.0	236.0
157.5°	266.5	259.7	252.3	246.3	241.4	237.5	234.6	234.6	234.6	237.5	241.4
160°	266.5	260.5	254.3	248.7	244.7	241.1	239.1	239.1	239.1	241.1	244.7
162.5°	266.5	261.3	255.6	251.2	247.5	244.3	242.7	243.2	242.7	244.3	247.5
165°	265.6	261.4	256.9	253.9	251.3	248.7	247.7	247.7	247.7	248.7	251.3
167.5°	264.3	261.4	258.0	255.7	254.2	252.3	251.8	252.3	251.8	252.3	254.2
170°	263.5	260.9	258.4	256.9	255.8	254.3	253.9	254.3	253.9	254.3	255.8
172.5°	262.7	260.6	258.8	257.7	257.1	255.9	255.8	256.4	255.8	255.9	257.1
175°	261.4	259.9	259.0	259.0	258.4	257.9	257.9	258.4	257.9	257.9	258.4
177.5°	260.1	259.3	259.0	259.0	259.0	258.5	259.0	259.3	259.0	258.5	259.0
180°	259.0	259.0	259.0	259.0	259.0	259.0	259.0	259.0	259.0	259.0	259.0



TEST NUMBER: P332591-940

CATALOG NUMBER: S124DIP-S795D590U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1144.9	1144.9	1144.9	1144.9	1144.9	1144.9	1144.9	1144.9	1144.9	1144.9	1144.9
2.5°	1122.8	1119.5	1114.5	1107.7	1102.0	1095.9	1094.4	1092.1	1096.6	1092.9	1091.7
5°	1086.0	1076.0	1063.3	1048.6	1040.0	1027.7	1025.3	1020.6	1015.8	1015.4	1010.6
7.5°	1047.0	1032.4	1015.7	1000.7	986.8	973.3	964.6	962.6	955.6	951.5	946.8
10°	1022.0	1004.0	984.5	970.3	954.2	940.0	930.0	924.3	919.5	914.4	909.6
12.5°	992.4	973.2	957.3	941.8	922.7	911.9	895.5	885.6	884.7	884.8	872.4
15°	958.0	939.0	914.4	892.5	882.1	861.2	852.2	840.8	833.7	826.6	820.9
17.5°	918.6	895.0	875.7	850.7	830.8	814.2	802.4	795.5	784.8	774.7	767.4
20°	893.9	868.8	848.5	821.9	800.0	779.6	769.7	760.2	752.2	743.6	735.6
22.5°	868.9	842.7	817.7	791.9	771.6	750.1	740.5	727.5	719.9	715.2	707.1
25°	829.5	801.0	772.6	747.9	727.0	708.0	695.3	685.3	676.7	673.0	667.7
27.5°	786.6	758.3	730.8	702.8	679.1	665.4	655.1	647.6	642.7	637.7	635.3
30°	759.3	729.9	700.4	674.4	652.6	638.8	629.3	624.1	620.3	618.0	615.5
32.5°	731.6	702.6	671.6	647.8	628.3	616.1	608.9	603.6	601.7	600.8	600.0
35°	687.2	657.8	629.3	608.0	589.5	584.8	578.5	575.8	574.8	578.1	579.5
37.5°	644.2	616.9	590.8	570.1	557.9	551.0	548.8	549.0	552.4	555.4	558.7
40°	616.5	590.0	565.3	547.2	535.9	531.6	530.7	533.1	536.8	540.2	543.9
42.5°	589.6	563.4	541.0	524.1	516.2	512.3	512.8	515.2	520.5	524.6	530.3
45°	547.8	525.9	504.1	490.4	483.8	484.6	484.6	488.9	494.2	500.3	506.5
47.5°	508.4	486.4	468.4	456.9	453.4	452.6	455.3	460.8	468.3	476.0	484.6
50°	481.8	460.9	445.3	434.9	431.1	432.5	436.3	441.5	450.5	460.0	469.0
52.5°	454.9	436.0	421.4	411.7	409.1	411.6	415.4	423.7	431.6	441.8	452.7
55°	413.0	396.9	385.6	378.4	377.5	378.9	383.2	392.2	403.6	416.4	426.9
57.5°	371.4	357.9	347.5	342.6	343.0	344.4	351.4	362.1	374.3	387.9	401.4
60°	343.4	331.0	322.5	318.7	319.1	322.0	330.6	340.5	355.7	369.0	383.2
62.5°	316.8	305.9	297.8	294.4	293.7	300.0	308.2	318.5	333.7	348.5	363.8
65°	274.1	265.6	259.0	257.1	258.5	263.2	273.7	287.4	300.2	315.8	332.0
67.5°	232.4	225.3	220.8	221.7	223.4	230.4	239.2	250.9	265.5	281.7	297.7
70°	205.8	199.2	195.4	195.8	198.7	207.2	214.8	226.7	242.4	259.0	272.2
72.5°	178.5	174.2	170.8	172.7	175.6	181.5	190.9	202.8	216.5	232.0	246.0
75°	137.1	137.1	135.2	136.6	140.9	146.5	153.6	165.9	179.8	192.1	203.5
77.5°	101.7	100.7	101.8	103.6	106.0	112.8	120.9	129.7	140.1	152.4	161.8
80°	77.8	78.3	80.6	83.5	84.4	89.6	98.2	106.2	114.3	124.8	133.8
82.5°	58.4	58.9	60.1	63.8	64.6	70.3	75.8	83.8	91.1	98.2	105.7
85°	31.7	31.7	34.2	35.6	37.9	41.7	45.0	49.8	56.4	61.2	68.3
87.5°	12.9	12.9	15.1	15.9	17.2	19.3	20.0	24.3	25.9	27.8	31.2
90°	4.1	4.1	7.1	7.1	8.1	9.2	8.6	9.2	9.6	10.2	10.2
92.5°	26.8	37.5	63.3	102.7	141.2	161.3	134.4	99.9	75.2	59.8	49.7
95°	42.2	63.6	107.8	191.3	312.8	414.6	426.2	376.9	298.1	229.9	180.6
97.5°	51.1	69.0	103.1	171.9	292.8	436.7	535.6	556.9	527.6	477.9	424.7
100°	58.0	74.3	104.2	161.8	265.6	408.9	539.2	613.5	623.7	598.7	561.1
102.5°	65.7	81.1	108.3	158.9	247.2	374.4	508.6	610.6	661.1	668.3	652.6
105°	78.8	93.6	118.0	160.2	231.5	333.7	453.3	569.7	657.7	708.1	729.0
107.5°	92.4	106.9	129.3	167.7	228.6	310.9	408.5	511.7	605.3	676.3	721.6
110°	101.7	115.5	137.9	173.4	229.4	303.2	386.1	476.6	564.6	638.4	694.4



TEST NUMBER: P332591-940

CATALOG NUMBER: S124DIP-S795D590U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	110.7	124.4	146.0	179.6	231.8	299.5	373.4	451.0	528.8	598.5	654.4
115°	124.7	138.4	158.7	189.2	236.6	297.6	361.7	425.3	487.9	547.3	596.2
117.5°	137.4	151.7	171.0	199.1	241.5	297.0	356.4	412.6	464.4	511.2	552.6
120°	146.0	160.2	179.6	206.0	245.2	297.0	353.6	407.0	454.2	494.9	531.0
122.5°	154.5	168.4	187.7	212.5	248.9	296.7	350.3	402.1	447.7	484.7	516.4
125°	166.3	180.6	198.9	222.3	254.3	296.0	344.9	393.7	437.5	472.5	500.5
127.5°	177.2	191.5	209.3	230.8	258.7	294.9	337.7	383.5	425.3	460.4	486.9
130°	184.1	198.9	216.2	236.0	262.0	294.5	333.1	375.4	415.6	450.1	477.2
132.5°	190.6	204.6	221.9	241.3	264.8	294.1	329.1	366.8	404.6	438.4	465.3
135°	199.9	213.1	229.9	248.3	269.1	293.5	323.0	355.1	388.2	419.1	444.6
137.5°	207.8	220.3	236.0	253.2	271.6	293.4	317.7	344.4	372.4	398.5	421.5
140°	212.6	224.8	240.1	256.4	273.7	293.0	314.9	338.2	362.2	385.0	406.4
142.5°	217.1	228.9	243.8	258.8	275.3	293.0	312.5	332.6	353.7	373.3	391.8
145°	223.3	234.5	247.7	261.4	276.3	291.9	308.3	324.5	341.8	357.1	371.3
147.5°	229.3	239.4	251.8	263.8	276.7	290.2	304.5	317.9	331.6	343.8	355.1
150°	233.0	242.6	253.9	265.0	276.7	288.9	301.7	313.9	325.6	335.7	344.9
152.5°	236.7	245.5	255.5	265.8	275.9	286.9	298.4	309.3	319.4	328.8	336.4
155°	241.7	249.2	257.9	266.5	274.6	283.8	293.5	302.6	310.8	318.4	324.5
157.5°	246.3	252.3	259.7	266.5	273.4	280.7	288.6	295.4	302.3	308.6	313.5
160°	248.7	254.3	260.5	266.5	272.2	278.2	284.9	291.0	296.6	302.1	306.2
162.5°	251.2	255.6	261.3	266.5	270.9	275.8	281.6	286.5	291.2	295.6	299.3
165°	253.9	256.9	261.4	265.6	268.6	272.2	276.3	280.3	283.3	286.9	289.4
167.5°	255.7	258.0	261.4	264.3	266.2	268.5	271.3	274.3	276.6	279.5	281.0
170°	256.9	258.4	260.9	263.5	264.5	266.0	268.0	270.6	272.2	274.2	275.7
172.5°	257.7	258.8	260.6	262.7	262.9	263.6	265.2	267.3	268.5	269.7	270.8
175°	259.0	259.0	259.9	261.4	260.9	260.9	262.0	263.0	263.5	264.5	264.5
177.5°	259.0	259.0	259.3	260.1	259.3	259.3	259.8	260.1	260.6	260.6	260.9
180°	259.0	259.0	259.0	259.0	259.0	259.0	259.0	259.0	259.0	259.0	259.0



TEST NUMBER: P332591-940

CATALOG NUMBER: S124DIP-S795D590U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1144.9	1144.9	1144.9	1144.9	1144.9	1144.9	1144.9	1144.9	1144.9	1144.9	1144.9
2.5°	1090.9	1090.2	1087.5	1087.2	1087.5	1090.2	1090.9	1091.7	1092.9	1096.6	1092.1
5°	1007.8	1005.4	1004.0	1009.2	1004.0	1005.4	1007.8	1010.6	1015.4	1015.8	1020.6
7.5°	945.0	943.2	939.0	937.7	939.0	943.2	945.0	946.8	951.5	955.6	962.6
10°	904.8	902.9	899.2	898.2	899.2	902.9	904.8	909.6	914.4	919.5	924.3
12.5°	866.1	862.4	861.6	862.6	861.6	862.4	866.1	872.4	884.8	884.7	885.6
15°	814.8	812.9	807.6	809.0	807.6	812.9	814.8	820.9	826.6	833.7	840.8
17.5°	764.1	761.8	755.5	761.1	755.5	761.8	764.1	767.4	774.7	784.8	795.5
20°	732.3	728.4	725.1	724.6	725.1	728.4	732.3	735.6	743.6	752.2	760.2
22.5°	701.9	698.5	698.2	695.1	698.2	698.5	701.9	707.1	715.2	719.9	727.5
25°	664.0	660.7	659.7	657.3	659.7	660.7	664.0	667.7	673.0	676.7	685.3
27.5°	634.8	633.2	631.5	632.2	631.5	633.2	634.8	635.3	637.7	642.7	647.6
30°	617.0	616.5	615.5	615.5	615.5	616.5	617.0	615.5	618.0	620.3	624.1
32.5°	602.2	602.1	602.7	602.7	602.7	602.1	602.2	600.0	600.8	601.7	603.6
35°	581.4	582.8	583.8	582.4	583.8	582.8	581.4	579.5	578.1	574.8	575.8
37.5°	562.7	564.1	565.4	567.0	565.4	564.1	562.7	558.7	555.4	552.4	549.0
40°	548.2	551.5	552.5	554.9	552.5	551.5	548.2	543.9	540.2	536.8	533.1
42.5°	534.6	538.2	540.7	541.2	540.7	538.2	534.6	530.3	524.6	520.5	515.2
45°	513.6	517.4	520.8	520.8	520.8	517.4	513.6	506.5	500.3	494.2	488.9
47.5°	491.9	497.4	500.7	501.6	500.7	497.4	491.9	484.6	476.0	468.3	460.8
50°	477.1	483.8	487.1	489.5	487.1	483.8	477.1	469.0	460.0	450.5	441.5
52.5°	462.7	469.3	473.8	475.0	473.8	469.3	462.7	452.7	441.8	431.6	423.7
55°	437.7	447.2	452.5	454.3	452.5	447.2	437.7	426.9	416.4	403.6	392.2
57.5°	414.2	422.9	429.0	430.4	429.0	422.9	414.2	401.4	387.9	374.3	362.1
60°	396.0	405.5	413.0	414.5	413.0	405.5	396.0	383.2	369.0	355.7	340.5
62.5°	377.4	387.3	394.1	397.8	394.1	387.3	377.4	363.8	348.5	333.7	318.5
65°	345.3	355.2	361.9	363.3	361.9	355.2	345.3	332.0	315.8	300.2	287.4
67.5°	310.1	320.1	324.5	327.3	324.5	320.1	310.1	297.7	281.7	265.5	250.9
70°	285.5	293.6	298.3	300.7	298.3	293.6	285.5	272.2	259.0	242.4	226.7
72.5°	257.4	265.8	271.3	271.8	271.3	265.8	257.4	246.0	232.0	216.5	202.8
75°	214.4	221.9	224.8	224.8	224.8	221.9	214.4	203.5	192.1	179.8	165.9
77.5°	169.7	173.6	177.2	177.9	177.2	173.6	169.7	161.8	152.4	140.1	129.7
80°	140.9	143.2	146.1	146.1	146.1	143.2	140.9	133.8	124.8	114.3	106.2
82.5°	111.3	113.2	116.1	115.7	116.1	113.2	111.3	105.7	98.2	91.1	83.8
85°	67.3	71.6	71.2	70.2	71.2	71.6	67.3	68.3	61.2	56.4	49.8
87.5°	32.5	33.0	34.0	34.8	34.0	33.0	32.5	31.2	27.8	25.9	24.3
90°	10.7	11.1	10.7	10.7	10.7	11.1	10.7	10.2	10.2	9.6	9.2
92.5°	43.6	40.9	39.1	39.1	39.1	40.9	43.6	49.7	59.8	75.2	99.9
95°	155.7	139.9	130.7	124.1	130.7	139.9	155.7	180.6	229.9	298.1	376.9
97.5°	388.3	357.6	342.3	331.7	342.3	357.6	388.3	424.7	477.9	527.6	556.9
100°	516.8	485.8	470.6	466.5	470.6	485.8	516.8	561.1	598.7	623.7	613.5
102.5°	625.4	603.0	586.9	583.6	586.9	603.0	625.4	652.6	668.3	661.1	610.6
105°	730.0	725.9	718.7	715.7	718.7	725.9	730.0	729.0	708.1	657.7	569.7
107.5°	746.7	758.3	763.4	764.7	763.4	758.3	746.7	721.6	676.3	605.3	511.7
110°	730.5	751.8	761.0	765.5	761.0	751.8	730.5	694.4	638.4	564.6	476.6



TEST NUMBER: P332591-940

CATALOG NUMBER: S124DIP-S795D590U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	695.4	721.3	734.1	741.5	734.1	721.3	695.4	654.4	598.5	528.8	451.0
115°	636.3	666.9	683.1	687.2	683.1	666.9	636.3	596.2	547.3	487.9	425.3
117.5°	586.9	612.5	629.0	632.2	629.0	612.5	586.9	552.6	511.2	464.4	412.6
120°	560.1	582.5	595.7	601.3	595.7	582.5	560.1	531.0	494.9	454.2	407.0
122.5°	540.9	560.1	571.2	576.8	571.2	560.1	540.9	516.4	484.7	447.7	402.1
125°	520.8	535.7	545.3	548.3	545.3	535.7	520.8	500.5	472.5	437.5	393.7
127.5°	507.4	520.5	528.6	531.6	528.6	520.5	507.4	486.9	460.4	425.3	383.5
130°	498.0	510.7	518.9	521.9	518.9	510.7	498.0	477.2	450.1	415.6	375.4
132.5°	485.8	500.2	507.8	511.0	507.8	500.2	485.8	465.3	438.4	404.6	366.8
135°	464.9	479.2	487.3	490.4	487.3	479.2	464.9	444.6	419.1	388.2	355.1
137.5°	440.5	454.6	461.3	464.9	461.3	454.6	440.5	421.5	398.5	372.4	344.4
140°	424.3	435.4	442.6	446.7	442.6	435.4	424.3	406.4	385.0	362.2	338.2
142.5°	407.5	417.9	424.3	427.0	424.3	417.9	407.5	391.8	373.3	353.7	332.6
145°	384.1	392.7	397.8	400.3	397.8	392.7	384.1	371.3	357.1	341.8	324.5
147.5°	364.4	371.8	375.7	376.7	375.7	371.8	364.4	355.1	343.8	331.6	317.9
150°	353.0	359.6	362.7	363.2	362.7	359.6	353.0	344.9	335.7	325.6	313.9
152.5°	343.2	348.7	350.4	351.0	350.4	348.7	343.2	336.4	328.8	319.4	309.3
155°	329.7	333.7	335.2	335.2	335.2	333.7	329.7	324.5	318.4	310.8	302.6
157.5°	317.4	320.5	321.4	321.4	321.4	320.5	317.4	313.5	308.6	302.3	295.4
160°	309.2	312.4	312.8	312.8	312.8	312.4	309.2	306.2	302.1	296.6	291.0
162.5°	301.6	304.6	305.1	304.7	305.1	304.6	301.6	299.3	295.6	291.2	286.5
165°	291.5	293.5	293.0	292.5	293.0	293.5	291.5	289.4	286.9	283.3	280.3
167.5°	282.0	283.3	283.2	282.9	283.2	283.3	282.0	281.0	279.5	276.6	274.3
170°	276.7	277.2	276.7	276.7	276.7	277.2	276.7	275.7	274.2	272.2	270.6
172.5°	271.4	272.0	271.4	270.6	271.4	272.0	271.4	270.8	269.7	268.5	267.3
175°	264.5	265.6	264.5	263.5	264.5	265.6	264.5	264.5	264.5	263.5	263.0
177.5°	260.6	260.9	260.1	259.3	260.1	260.9	260.6	260.9	260.6	260.6	260.1
180°	259.0	259.0	259.0	259.0	259.0	259.0	259.0	259.0	259.0	259.0	259.0



TEST NUMBER: P332591-940

CATALOG NUMBER: S124DIP-S795D590U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1144.9	1144.9	1144.9	1144.9	1144.9	1144.9	1144.9	1144.9	1144.9	1144.9	1144.9
2.5°	1094.4	1095.9	1102.0	1107.7	1114.5	1119.5	1122.8	1126.6	1134.6	1141.0	1147.1
5°	1025.3	1027.7	1040.0	1048.6	1063.3	1076.0	1086.0	1096.9	1109.7	1127.3	1143.4
7.5°	964.6	973.3	986.8	1000.7	1015.7	1032.4	1047.0	1063.5	1085.6	1109.6	1134.5
10°	930.0	940.0	954.2	970.3	984.5	1004.0	1022.0	1041.4	1066.6	1096.0	1125.4
12.5°	895.5	911.9	922.7	941.8	957.3	973.2	992.4	1017.9	1047.2	1078.2	1113.7
15°	852.2	861.2	882.1	892.5	914.4	939.0	958.0	983.6	1012.0	1052.8	1092.7
17.5°	802.4	814.2	830.8	850.7	875.7	895.0	918.6	944.9	980.8	1021.4	1071.2
20°	769.7	779.6	800.0	821.9	848.5	868.8	893.9	919.5	956.5	999.7	1051.9
22.5°	740.5	750.1	771.6	791.9	817.7	842.7	868.9	898.7	934.2	979.6	1032.9
25°	695.3	708.0	727.0	747.9	772.6	801.0	829.5	856.0	893.9	941.8	998.8
27.5°	655.1	665.4	679.1	702.8	730.8	758.3	786.6	819.9	856.4	907.0	966.2
30°	629.3	638.8	652.6	674.4	700.4	729.9	759.3	791.5	829.5	879.8	940.0
32.5°	608.9	616.1	628.3	647.8	671.6	702.6	731.6	765.0	804.8	854.3	913.0
35°	578.5	584.8	589.5	608.0	629.3	657.8	687.2	722.7	761.2	808.2	866.9
37.5°	548.8	551.0	557.9	570.1	590.8	616.9	644.2	679.2	718.5	766.2	819.3
40°	530.7	531.6	535.9	547.2	565.3	590.0	616.5	651.1	688.6	733.7	786.3
42.5°	512.8	512.3	516.2	524.1	541.0	563.4	589.6	621.2	658.6	700.3	749.8
45°	484.6	484.6	483.8	490.4	504.1	525.9	547.8	578.1	609.4	650.2	692.0
47.5°	455.3	452.6	453.4	456.9	468.4	486.4	508.4	533.2	560.9	595.4	632.0
50°	436.3	432.5	431.1	434.9	445.3	460.9	481.8	503.6	529.8	560.1	591.4
52.5°	415.4	411.6	409.1	411.7	421.4	436.0	454.9	474.0	497.5	522.2	549.3
55°	383.2	378.9	377.5	378.4	385.6	396.9	413.0	430.6	448.2	468.6	487.5
57.5°	351.4	344.4	343.0	342.6	347.5	357.9	371.4	386.6	399.4	411.7	431.9
60°	330.6	322.0	319.1	318.7	322.5	331.0	343.4	358.6	367.6	376.0	393.6
62.5°	308.2	300.0	293.7	294.4	297.8	305.9	316.8	327.8	333.8	343.0	354.9
65°	273.7	263.2	258.5	257.1	259.0	265.6	274.1	281.2	287.8	291.7	303.0
67.5°	239.2	230.4	223.4	221.7	220.8	225.3	232.4	236.7	241.4	244.7	251.5
70°	214.8	207.2	198.7	195.8	195.4	199.2	205.8	206.3	212.9	214.4	221.5
72.5°	190.9	181.5	175.6	172.7	170.8	174.2	178.5	179.8	183.3	185.9	189.6
75°	153.6	146.5	140.9	136.6	135.2	137.1	137.1	139.5	141.8	143.2	147.5
77.5°	120.9	112.8	106.0	103.6	101.8	100.7	101.7	103.1	101.9	104.4	105.4
80°	98.2	89.6	84.4	83.5	80.6	78.3	77.8	79.2	77.3	78.3	81.1
82.5°	75.8	70.3	64.6	63.8	60.1	58.9	58.4	57.6	57.6	57.4	58.0
85°	45.0	41.7	37.9	35.6	34.2	31.7	31.7	30.9	29.9	28.9	29.4
87.5°	20.0	19.3	17.2	15.9	15.1	12.9	12.9	11.7	11.2	10.5	10.0
90°	8.6	9.2	8.1	7.1	7.1	4.1	4.1	3.6	3.0	1.5	0.5
92.5°	134.4	161.3	141.2	102.7	63.3	37.5	26.8	19.4	13.2	8.5	5.8
95°	426.2	414.6	312.8	191.3	107.8	63.6	42.2	30.1	23.4	18.3	16.8
97.5°	535.6	436.7	292.8	171.9	103.1	69.0	51.1	40.6	34.5	30.1	30.1
100°	539.2	408.9	265.6	161.8	104.2	74.3	58.0	48.3	42.2	38.7	38.7
102.5°	508.6	374.4	247.2	158.9	108.3	81.1	65.7	56.4	50.7	47.6	46.8
105°	453.3	333.7	231.5	160.2	118.0	93.6	78.8	69.7	63.6	61.1	59.5
107.5°	408.5	310.9	228.6	167.7	129.3	106.9	92.4	83.6	77.1	74.5	73.6
110°	386.1	303.2	229.4	173.4	137.9	115.5	101.7	92.6	86.5	83.9	82.9



TEST NUMBER: P332591-940

CATALOG NUMBER: S124DIP-S795D590U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	373.4	299.5	231.8	179.6	146.0	124.4	110.7	101.6	95.9	92.9	91.8
115°	361.7	297.6	236.6	189.2	158.7	138.4	124.7	114.9	109.9	106.3	104.8
117.5°	356.4	297.0	241.5	199.1	171.0	151.7	137.4	128.4	122.8	119.7	118.2
120°	353.6	297.0	245.2	206.0	179.6	160.2	146.0	137.3	131.7	128.2	127.2
122.5°	350.3	296.7	248.9	212.5	187.7	168.4	154.5	145.1	139.9	136.3	135.3
125°	344.9	296.0	254.3	222.3	198.9	180.6	166.3	156.7	151.1	148.0	146.0
127.5°	337.7	294.9	258.7	230.8	209.3	191.5	177.2	167.1	160.8	157.1	155.4
130°	333.1	294.5	262.0	236.0	216.2	198.9	184.1	174.5	166.8	162.7	160.8
132.5°	329.1	294.1	264.8	241.3	221.9	204.6	190.6	180.2	173.0	167.6	166.0
135°	323.0	293.5	269.1	248.3	229.9	213.1	199.9	189.2	180.6	175.5	173.4
137.5°	317.7	293.4	271.6	253.2	236.0	220.3	207.8	196.6	188.4	182.8	180.9
140°	314.9	293.0	273.7	256.4	240.1	224.8	212.6	202.0	193.3	187.7	186.2
142.5°	312.5	293.0	275.3	258.8	243.8	228.9	217.1	206.8	198.6	193.4	191.9
145°	308.3	291.9	276.3	261.4	247.7	234.5	223.3	213.7	206.5	201.4	199.9
147.5°	304.5	290.2	276.7	263.8	251.8	239.4	229.3	221.2	213.9	209.5	208.9
150°	301.7	288.9	276.7	265.0	253.9	242.6	233.0	225.3	219.3	215.2	214.6
152.5°	298.4	286.9	275.9	265.8	255.5	245.5	236.7	229.8	224.1	220.1	220.0
155°	293.5	283.8	274.6	266.5	257.9	249.2	241.7	236.0	231.0	227.9	227.4
157.5°	288.6	280.7	273.4	266.5	259.7	252.3	246.3	241.4	237.5	234.6	234.6
160°	284.9	278.2	272.2	266.5	260.5	254.3	248.7	244.7	241.1	239.1	239.1
162.5°	281.6	275.8	270.9	266.5	261.3	255.6	251.2	247.5	244.3	242.7	243.2
165°	276.3	272.2	268.6	265.6	261.4	256.9	253.9	251.3	248.7	247.7	247.7
167.5°	271.3	268.5	266.2	264.3	261.4	258.0	255.7	254.2	252.3	251.8	252.3
170°	268.0	266.0	264.5	263.5	260.9	258.4	256.9	255.8	254.3	253.9	254.3
172.5°	265.2	263.6	262.9	262.7	260.6	258.8	257.7	257.1	255.9	255.8	256.4
175°	262.0	260.9	260.9	261.4	259.9	259.0	259.0	258.4	257.9	257.9	258.4
177.5°	259.8	259.3	259.3	260.1	259.3	259.0	259.0	259.0	258.5	259.0	259.3
180°	259.0	259.0	259.0	259.0	259.0	259.0	259.0	259.0	259.0	259.0	259.0



TEST NUMBER: P332591-940

CATALOG NUMBER: S124DIP-S795D590U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1144.9	1144.9	1144.9	1144.9	1144.9	1144.9	1144.9	1144.9	1144.9	1144.9	1144.9
2.5°	1152.4	1156.2	1161.2	1169.5	1172.5	1176.3	1181.6	1181.2	1182.8	1188.5	1200.6
5°	1156.7	1171.4	1185.6	1202.7	1220.8	1232.5	1248.7	1258.6	1268.6	1281.4	1303.2
7.5°	1158.4	1181.7	1207.8	1237.8	1264.4	1295.2	1319.2	1341.8	1362.1	1389.2	1415.1
10°	1155.7	1187.0	1220.8	1258.6	1299.0	1333.1	1364.0	1399.0	1428.9	1461.6	1491.0
12.5°	1150.8	1188.6	1233.6	1276.1	1323.2	1373.7	1412.1	1447.6	1487.4	1525.0	1570.3
15°	1139.6	1191.3	1243.9	1299.9	1363.0	1421.3	1476.8	1522.8	1565.5	1621.9	1681.2
17.5°	1125.4	1181.2	1247.6	1315.3	1381.2	1447.9	1516.5	1585.7	1639.6	1709.7	1756.0
20°	1112.1	1176.6	1244.9	1325.5	1391.4	1474.4	1542.7	1609.6	1683.6	1753.3	1808.7
22.5°	1093.5	1164.1	1236.5	1316.8	1403.6	1486.6	1565.5	1638.1	1712.0	1787.8	1855.0
25°	1069.9	1133.9	1219.8	1310.8	1397.1	1487.2	1577.8	1668.8	1748.6	1828.7	1891.3
27.5°	1029.7	1110.5	1190.4	1284.4	1380.4	1482.3	1579.1	1674.5	1757.9	1823.8	1862.6
30°	1009.2	1079.4	1166.2	1260.5	1364.4	1474.0	1574.9	1668.4	1746.1	1798.8	1814.5
32.5°	978.8	1051.3	1136.2	1233.9	1343.9	1456.5	1561.7	1649.8	1714.7	1742.3	1723.4
35°	933.8	999.3	1085.0	1185.2	1299.4	1419.4	1523.3	1597.8	1630.9	1604.8	1539.9
37.5°	879.8	944.6	1030.8	1129.1	1247.3	1369.3	1463.2	1516.8	1505.8	1440.9	1344.1
40°	841.8	902.5	984.5	1090.7	1206.0	1328.4	1410.9	1439.8	1409.4	1316.5	1213.6
42.5°	799.7	858.9	941.3	1043.7	1165.8	1278.6	1350.6	1352.9	1302.1	1191.0	1087.6
45°	735.6	792.0	869.8	976.5	1089.3	1195.6	1243.0	1219.8	1125.9	1018.7	914.8
47.5°	672.3	721.2	797.9	899.2	1006.4	1095.8	1119.3	1077.5	977.4	873.3	777.1
50°	626.0	675.3	747.4	844.2	947.5	1024.8	1036.3	980.7	882.6	777.8	702.4
52.5°	581.6	630.5	700.0	789.5	884.2	953.9	954.3	890.1	792.3	698.8	628.7
55°	516.5	560.5	623.1	703.3	787.7	842.2	829.0	762.6	677.7	596.6	535.4
57.5°	453.7	492.0	549.7	616.6	691.0	735.9	713.9	650.0	574.2	505.4	459.1
60°	413.0	449.6	498.9	562.0	624.6	659.7	638.8	580.9	511.2	455.8	415.4
62.5°	373.6	404.5	451.8	506.6	564.6	590.7	572.0	515.0	454.7	404.6	371.8
65°	317.7	342.9	380.8	427.8	470.0	492.2	476.6	423.5	377.5	341.4	315.4
67.5°	265.6	285.2	314.0	351.6	387.4	399.5	385.3	348.3	309.3	280.4	262.1
70°	229.5	248.1	272.2	301.1	332.4	345.3	331.0	301.6	269.8	243.3	225.2
72.5°	198.0	212.4	232.7	257.5	282.0	294.8	285.1	256.8	230.0	210.3	194.9
75°	150.8	163.2	177.4	194.9	213.9	222.4	213.9	194.5	175.9	161.2	150.3
77.5°	109.7	116.3	127.2	140.4	152.2	158.8	151.4	138.2	126.9	116.8	111.5
80°	83.5	88.2	95.8	106.2	114.3	120.5	115.7	104.8	95.8	89.2	86.8
82.5°	60.7	63.9	68.8	76.6	82.0	85.2	83.1	75.2	71.5	65.6	63.2
85°	29.9	31.7	35.1	37.5	42.2	42.7	43.2	39.9	36.6	35.1	33.2
87.5°	10.5	11.2	12.5	13.7	15.2	16.2	15.9	16.1	14.7	14.3	12.8
90°	1.5	3.0	3.6	4.1	4.1	7.1	7.1	8.1	9.2	8.6	9.2
92.5°	8.5	13.2	19.4	26.8	37.5	63.3	102.7	141.2	161.3	134.4	99.9
95°	18.3	23.4	30.1	42.2	63.6	107.8	191.3	312.8	414.6	426.2	376.9
97.5°	30.1	34.5	40.6	51.1	69.0	103.1	171.9	292.8	436.7	535.6	556.9
100°	38.7	42.2	48.3	58.0	74.3	104.2	161.8	265.6	408.9	539.2	613.5
102.5°	47.6	50.7	56.4	65.7	81.1	108.3	158.9	247.2	374.4	508.6	610.6
105°	61.1	63.6	69.7	78.8	93.6	118.0	160.2	231.5	333.7	453.3	569.7
107.5°	74.5	77.1	83.6	92.4	106.9	129.3	167.7	228.6	310.9	408.5	511.7
110°	83.9	86.5	92.6	101.7	115.5	137.9	173.4	229.4	303.2	386.1	476.6





TEST NUMBER: P332591-940

CATALOG NUMBER: S124DIP-S795D590U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	92.9	95.9	101.6	110.7	124.4	146.0	179.6	231.8	299.5	373.4	451.0
115°	106.3	109.9	114.9	124.7	138.4	158.7	189.2	236.6	297.6	361.7	425.3
117.5°	119.7	122.8	128.4	137.4	151.7	171.0	199.1	241.5	297.0	356.4	412.6
120°	128.2	131.7	137.3	146.0	160.2	179.6	206.0	245.2	297.0	353.6	407.0
122.5°	136.3	139.9	145.1	154.5	168.4	187.7	212.5	248.9	296.7	350.3	402.1
125°	148.0	151.1	156.7	166.3	180.6	198.9	222.3	254.3	296.0	344.9	393.7
127.5°	157.1	160.8	167.1	177.2	191.5	209.3	230.8	258.7	294.9	337.7	383.5
130°	162.7	166.8	174.5	184.1	198.9	216.2	236.0	262.0	294.5	333.1	375.4
132.5°	167.6	173.0	180.2	190.6	204.6	221.9	241.3	264.8	294.1	329.1	366.8
135°	175.5	180.6	189.2	199.9	213.1	229.9	248.3	269.1	293.5	323.0	355.1
137.5°	182.8	188.4	196.6	207.8	220.3	236.0	253.2	271.6	293.4	317.7	344.4
140°	187.7	193.3	202.0	212.6	224.8	240.1	256.4	273.7	293.0	314.9	338.2
142.5°	193.4	198.6	206.8	217.1	228.9	243.8	258.8	275.3	293.0	312.5	332.6
145°	201.4	206.5	213.7	223.3	234.5	247.7	261.4	276.3	291.9	308.3	324.5
147.5°	209.5	213.9	221.2	229.3	239.4	251.8	263.8	276.7	290.2	304.5	317.9
150°	215.2	219.3	225.3	233.0	242.6	253.9	265.0	276.7	288.9	301.7	313.9
152.5°	220.1	224.1	229.8	236.7	245.5	255.5	265.8	275.9	286.9	298.4	309.3
155°	227.9	231.0	236.0	241.7	249.2	257.9	266.5	274.6	283.8	293.5	302.6
157.5°	234.6	237.5	241.4	246.3	252.3	259.7	266.5	273.4	280.7	288.6	295.4
160°	239.1	241.1	244.7	248.7	254.3	260.5	266.5	272.2	278.2	284.9	291.0
162.5°	242.7	244.3	247.5	251.2	255.6	261.3	266.5	270.9	275.8	281.6	286.5
165°	247.7	248.7	251.3	253.9	256.9	261.4	265.6	268.6	272.2	276.3	280.3
167.5°	251.8	252.3	254.2	255.7	258.0	261.4	264.3	266.2	268.5	271.3	274.3
170°	253.9	254.3	255.8	256.9	258.4	260.9	263.5	264.5	266.0	268.0	270.6
172.5°	255.8	255.9	257.1	257.7	258.8	260.6	262.7	262.9	263.6	265.2	267.3
175°	257.9	257.9	258.4	259.0	259.0	259.9	261.4	260.9	260.9	262.0	263.0
177.5°	259.0	258.5	259.0	259.0	259.0	259.3	260.1	259.3	259.3	259.8	260.1
180°	259.0	259.0	259.0	259.0	259.0	259.0	259.0	259.0	259.0	259.0	259.0



TEST NUMBER: P332591-940

CATALOG NUMBER: S124DIP-S795D590U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1144.9	1144.9	1144.9	1144.9	1144.9	1144.9	1144.9
2.5°	1206.7	1207.5	1210.9	1213.5	1214.2	1218.1	1218.4
5°	1312.7	1320.8	1336.4	1337.8	1340.2	1352.5	1343.1
7.5°	1437.0	1457.4	1471.1	1483.2	1487.6	1492.9	1491.8
10°	1516.6	1547.0	1562.2	1586.4	1587.3	1593.5	1589.7
12.5°	1596.7	1632.0	1659.7	1664.1	1684.4	1687.6	1692.9
15°	1710.1	1747.6	1786.0	1799.7	1827.7	1834.4	1844.9
17.5°	1816.8	1855.0	1882.0	1917.5	1929.0	1944.4	1933.9
20°	1875.2	1916.9	1951.1	1979.1	1990.9	1999.4	1998.5
22.5°	1910.5	1952.6	1980.2	2001.4	2012.5	2016.2	2015.9
25°	1932.5	1956.8	1965.2	1973.4	1961.1	1956.8	1958.6
27.5°	1871.1	1864.8	1842.5	1813.3	1783.0	1758.9	1745.8
30°	1786.5	1749.5	1715.8	1657.0	1626.7	1608.6	1592.5
32.5°	1666.6	1608.0	1543.2	1489.3	1454.8	1428.1	1424.1
35°	1461.2	1373.0	1293.8	1227.8	1193.6	1164.8	1158.1
37.5°	1242.2	1150.6	1079.3	1021.3	984.5	964.1	945.0
40°	1096.9	1018.2	948.0	898.7	870.8	856.0	844.2
42.5°	985.0	913.1	843.3	805.7	780.4	771.4	764.5
45°	830.4	763.6	715.2	686.7	672.0	656.8	649.7
47.5°	706.6	652.2	620.3	596.1	580.4	571.4	566.9
50°	636.4	591.8	563.4	544.9	530.7	523.5	519.8
52.5°	574.2	537.6	513.7	499.0	489.4	484.1	482.6
55°	494.6	466.6	451.5	438.7	431.6	426.9	424.9
57.5°	430.0	408.4	396.1	385.6	382.8	378.8	377.5
60°	387.4	370.9	360.4	353.3	351.0	346.2	347.1
62.5°	349.9	336.4	327.4	323.3	320.2	316.2	317.5
65°	296.0	286.0	281.2	277.4	273.7	271.3	273.1
67.5°	248.3	241.5	235.1	232.8	231.0	230.6	228.5
70°	217.2	211.5	205.8	204.4	204.4	202.5	202.1
72.5°	187.3	183.1	179.2	178.3	176.7	177.5	175.5
75°	144.6	141.3	139.9	138.5	138.0	138.0	136.6
77.5°	106.9	104.4	102.2	102.2	100.4	99.8	99.6
80°	81.1	80.2	78.3	78.3	77.3	77.8	76.9
82.5°	61.0	59.7	59.3	58.5	57.2	57.2	56.4
85°	32.7	31.3	30.9	29.4	28.4	29.4	28.4
87.5°	13.3	13.0	12.7	12.0	11.7	11.6	10.5
90°	9.6	10.2	10.2	10.7	11.1	10.7	10.7
92.5°	75.2	59.8	49.7	43.6	40.9	39.1	39.1
95°	298.1	229.9	180.6	155.7	139.9	130.7	124.1
97.5°	527.6	477.9	424.7	388.3	357.6	342.3	331.7
100°	623.7	598.7	561.1	516.8	485.8	470.6	466.5
102.5°	661.1	668.3	652.6	625.4	603.0	586.9	583.6
105°	657.7	708.1	729.0	730.0	725.9	718.7	715.7
107.5°	605.3	676.3	721.6	746.7	758.3	763.4	764.7
110°	564.6	638.4	694.4	730.5	751.8	761.0	765.5



TEST NUMBER: P332591-940

CATALOG NUMBER: S124DIP-S795D590U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	528.8	598.5	654.4	695.4	721.3	734.1	741.5
115°	487.9	547.3	596.2	636.3	666.9	683.1	687.2
117.5°	464.4	511.2	552.6	586.9	612.5	629.0	632.2
120°	454.2	494.9	531.0	560.1	582.5	595.7	601.3
122.5°	447.7	484.7	516.4	540.9	560.1	571.2	576.8
125°	437.5	472.5	500.5	520.8	535.7	545.3	548.3
127.5°	425.3	460.4	486.9	507.4	520.5	528.6	531.6
130°	415.6	450.1	477.2	498.0	510.7	518.9	521.9
132.5°	404.6	438.4	465.3	485.8	500.2	507.8	511.0
135°	388.2	419.1	444.6	464.9	479.2	487.3	490.4
137.5°	372.4	398.5	421.5	440.5	454.6	461.3	464.9
140°	362.2	385.0	406.4	424.3	435.4	442.6	446.7
142.5°	353.7	373.3	391.8	407.5	417.9	424.3	427.0
145°	341.8	357.1	371.3	384.1	392.7	397.8	400.3
147.5°	331.6	343.8	355.1	364.4	371.8	375.7	376.7
150°	325.6	335.7	344.9	353.0	359.6	362.7	363.2
152.5°	319.4	328.8	336.4	343.2	348.7	350.4	351.0
155°	310.8	318.4	324.5	329.7	333.7	335.2	335.2
157.5°	302.3	308.6	313.5	317.4	320.5	321.4	321.4
160°	296.6	302.1	306.2	309.2	312.4	312.8	312.8
162.5°	291.2	295.6	299.3	301.6	304.6	305.1	304.7
165°	283.3	286.9	289.4	291.5	293.5	293.0	292.5
167.5°	276.6	279.5	281.0	282.0	283.3	283.2	282.9
170°	272.2	274.2	275.7	276.7	277.2	276.7	276.7
172.5°	268.5	269.7	270.8	271.4	272.0	271.4	270.6
175°	263.5	264.5	264.5	264.5	265.6	264.5	263.5
177.5°	260.6	260.6	260.9	260.6	260.9	260.1	259.3
180°	259.0	259.0	259.0	259.0	259.0	259.0	259.0

(END OF REPORT)