

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332957-940

Luminaire Tested: **S124RDIP-S1020D365U940-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332957-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124RDIP-S1020D365U940-4F0-1E-UDD-A4  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1020 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5035.1 lumens  
Efficiency: N/A  
Efficacy: 115.7 lumens/watt  
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39  
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 43.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332957-940

CATALOG NUMBER: S124RDIP-S1020D365U940-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P332957-940

CATALOG NUMBER: S124RDIP-S1020D365U940-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	114	114	114	114	108	108	108	108	98	98	98	89	89	89	81	81	81	77				77
1	105	100	97	93	100	96	92	89	87	85	82	80	78	76	73	71	70	66				66
2	96	88	82	77	91	85	79	75	77	73	69	71	67	64	65	62	60	57				57
3	88	78	71	65	84	75	69	63	69	64	59	63	59	55	58	55	52	49				49
4	81	70	62	56	77	67	60	54	62	56	51	57	52	48	52	48	45	42				42
5	74	63	55	49	71	60	53	47	56	49	45	51	46	42	47	43	40	37				37
6	69	57	48	43	66	55	47	42	50	44	39	47	41	37	43	39	35	33				33
7	64	51	43	38	61	50	42	37	46	40	35	43	37	33	40	35	32	29				29
8	60	47	39	34	57	45	38	33	42	36	31	39	34	30	36	32	28	26				26
9	56	43	36	30	53	42	35	30	39	33	28	36	31	27	34	29	26	24				24
10	52	40	32	28	50	38	32	27	36	30	26	34	28	25	31	27	24	22				22

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	12352	12352	12352	12352
5°	14327	12388	10950	12388
10°	16948	12336	9773	12336
15°	19578	12221	8398	12221
20°	21798	12064	7594	12064
25°	22502	11909	7050	11909
30°	19699	11723	6723	11723
35°	15334	11446	6525	11446
40°	11499	11129	6418	11129
45°	9079	10620	6361	10620
50°	7665	10034	6179	10034
55°	6681	9388	5847	9388
60°	6011	8719	5176	8719
65°	5299	7996	4451	7996
70°	4773	7246	4015	7246
75°	3999	6422	3425	6422
80°	3384	5472	3208	5472
85°	2862	4279	2862	4279



TEST NUMBER: P332957-940

CATALOG NUMBER: S124RDIP-S1020D365U940-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	148.2	2.9
10°-20°	447.2	8.9
20°-30°	699.4	13.9
30°-40°	777.5	15.4
40°-50°	689.9	13.7
50°-60°	537.6	10.7
60°-70°	351.9	7.0
70°-80°	173.1	3.4
80°-90°	43.6	0.9
90°-100°	115.9	2.3
100°-110°	241.1	4.8
110°-120°	216.0	4.3
120°-130°	181.7	3.6
130°-140°	151.5	3.0
140°-150°	115.7	2.3
150°-160°	81.3	1.6
160°-170°	47.8	1.0
170°-180°	15.6	0.3
0°-30°	1294.9	25.7
0°-40°	2072.4	41.2
0°-60°	3299.8	65.5
0°-90°	3868.4	76.8
90°-120°	573.0	11.4
90°-150°	1021.9	20.3
90°-180°	1167.0	23.2
0°-180°	5035.1	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1530	1530	1530	1530	1530	
5°	1768	1529	1351	1529	1768	179
15°	2342	1462	1005	1462	2342	666
25°	2526	1337	792	1337	2526	1121
35°	1556	1161	662	1161	1556	975
45°	795	930	557	930	795	630
55°	475	667	415	667	475	432
65°	277	419	233	419	277	279
75°	128	206	110	206	128	141
85°	31	46	31	46	31	35
90°	7	0	7	0	7	7
95°	77	10	77	10	77	119
105°	443	37	443	37	443	438
115°	426	65	426	65	426	423
125°	340	90	340	90	340	309
135°	304	108	304	108	304	234
145°	248	124	248	124	248	157
155°	208	141	208	141	208	97
165°	181	154	181	154	181	52
175°	163	160	163	160	163	16
180°	160	160	160	160	160	



TEST NUMBER: P332957-940

CATALOG NUMBER: S124RDIP-S1020D365U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0
2.5°	1613.8	1618.3	1613.8	1613.4	1608.5	1607.0	1605.0	1598.6	1586.7	1579.8	1581.3
5°	1768.0	1783.3	1774.8	1773.5	1760.0	1746.4	1737.8	1718.1	1697.1	1682.9	1671.2
7.5°	1946.2	1955.1	1949.7	1941.1	1919.1	1906.7	1886.7	1860.6	1823.1	1794.3	1768.1
10°	2067.5	2074.9	2072.5	2056.5	2040.4	2007.8	1989.2	1952.9	1905.4	1867.9	1832.6
12.5°	2186.9	2194.8	2173.1	2173.8	2143.5	2117.7	2088.4	2042.6	1987.8	1939.3	1895.3
15°	2342.5	2332.6	2332.6	2320.3	2286.3	2250.7	2220.4	2172.4	2103.3	2045.3	1984.3
17.5°	2464.3	2467.7	2462.7	2433.6	2407.0	2370.0	2314.6	2258.5	2194.4	2116.7	2054.2
20°	2537.3	2537.3	2531.7	2512.0	2477.5	2438.0	2378.3	2317.2	2235.9	2157.6	2087.3
22.5°	2566.9	2568.8	2562.3	2546.0	2515.0	2476.5	2425.5	2363.6	2279.7	2191.6	2104.5
25°	2526.2	2537.9	2539.1	2534.8	2525.6	2502.1	2458.4	2394.9	2319.7	2224.1	2130.4
27.5°	2319.3	2334.1	2347.1	2368.4	2396.7	2411.5	2413.5	2381.2	2315.6	2223.7	2129.3
30°	2113.2	2125.5	2165.6	2218.0	2258.6	2295.6	2327.7	2336.3	2299.4	2216.7	2117.5
32.5°	1884.4	1901.1	1941.2	1997.5	2065.3	2128.0	2199.9	2236.7	2235.7	2186.1	2094.3
35°	1555.9	1568.3	1605.3	1664.4	1745.8	1838.9	1952.9	2041.7	2102.0	2097.7	2041.7
37.5°	1254.8	1268.7	1306.1	1355.2	1434.1	1549.3	1659.7	1782.0	1893.7	1956.5	1937.7
40°	1091.1	1091.7	1128.1	1178.7	1252.6	1353.1	1473.3	1608.9	1733.4	1835.1	1854.8
42.5°	961.9	962.0	986.1	1040.5	1093.9	1188.4	1303.1	1437.8	1583.5	1701.0	1753.3
45°	795.2	800.8	820.5	853.2	895.1	975.2	1067.0	1192.2	1355.6	1494.9	1581.8
47.5°	673.4	681.5	694.1	720.8	754.1	807.5	883.5	996.0	1128.8	1282.1	1405.8
50°	610.3	611.5	627.5	642.3	671.3	713.8	780.4	874.1	996.1	1143.5	1280.9
52.5°	556.1	555.8	565.4	584.2	607.7	640.9	694.6	779.9	888.1	1020.2	1162.1
55°	474.7	477.8	485.2	499.9	517.8	541.3	583.8	647.9	733.0	845.8	974.6
57.5°	412.8	414.4	420.2	426.4	442.8	459.9	491.8	536.3	608.1	700.4	820.5
60°	372.3	372.9	374.8	384.1	397.0	413.0	434.6	472.2	532.6	617.1	712.0
62.5°	332.9	333.9	336.8	343.6	353.6	364.7	387.3	417.5	467.5	539.7	625.2
65°	277.4	278.0	282.3	284.8	292.8	302.6	319.3	339.7	374.2	434.6	499.4
67.5°	231.8	231.8	232.0	235.3	240.9	247.4	257.4	273.7	299.7	336.8	393.9
70°	202.2	202.2	203.4	205.3	208.4	213.9	219.5	231.8	250.9	281.1	324.9
72.5°	174.6	175.0	176.3	176.6	178.3	182.8	186.9	194.8	209.0	231.8	267.2
75°	128.2	130.1	133.1	135.6	138.7	138.1	142.4	147.3	151.7	165.2	185.6
77.5°	95.4	94.4	94.8	96.9	97.3	97.9	100.9	104.8	108.0	114.4	121.7
80°	72.8	72.8	74.5	75.2	74.5	75.2	78.3	80.2	81.4	83.8	90.6
82.5°	55.0	56.0	55.4	56.0	56.4	57.0	59.6	59.9	61.2	62.2	65.0
85°	30.9	31.5	32.0	30.9	30.9	30.9	32.0	32.6	33.9	33.3	34.5
87.5°	12.2	11.7	12.2	12.2	12.6	12.1	12.6	13.5	12.4	12.9	12.8
90°	6.6	6.6	7.0	6.6	6.3	6.3	6.0	5.7	5.4	5.7	5.1
92.5°	24.3	24.3	25.3	27.0	30.8	37.1	46.5	61.9	83.3	100.0	87.5
95°	76.9	81.0	86.7	96.4	111.9	142.4	184.7	233.5	264.1	256.8	193.9
97.5°	205.5	212.1	221.6	240.5	263.1	296.0	326.9	345.0	331.8	270.5	181.4
100°	289.0	291.5	301.0	320.2	347.6	371.0	386.4	380.0	334.0	253.4	164.5
102.5°	361.6	363.6	373.6	387.5	404.3	414.0	409.6	378.4	315.1	231.9	153.2
105°	443.4	445.3	449.7	452.3	451.7	438.7	407.5	352.9	280.8	206.7	143.4
107.5°	473.8	473.0	469.8	462.6	447.1	418.9	375.1	317.0	253.1	192.6	141.6
110°	474.3	471.4	465.8	452.5	430.2	395.6	349.8	295.3	239.2	187.8	142.1



TEST NUMBER: P332957-940

CATALOG NUMBER: S124RDIP-S1020D365U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	459.4	454.9	446.9	430.9	405.5	370.8	327.6	279.4	231.4	185.6	143.7
115°	425.8	423.3	413.1	394.2	369.3	339.1	302.2	263.5	224.1	184.4	146.5
117.5°	391.6	389.7	379.5	363.6	342.4	316.7	287.8	255.7	220.8	184.0	149.6
120°	372.6	369.1	360.9	347.0	329.0	306.7	281.4	252.1	219.0	184.0	151.9
122.5°	357.4	353.9	347.0	335.1	319.9	300.3	277.4	249.1	217.0	183.8	154.2
125°	339.7	337.9	331.9	322.7	310.1	292.7	271.0	244.0	213.7	183.4	157.6
127.5°	329.4	327.5	322.4	314.3	301.7	285.3	263.5	237.6	209.2	182.7	160.3
130°	323.3	321.5	316.4	308.5	295.6	278.9	257.5	232.6	206.4	182.4	162.3
132.5°	316.6	314.7	309.9	301.0	288.3	271.6	250.7	227.3	203.9	182.3	164.1
135°	303.8	301.9	296.9	288.0	275.4	259.7	240.5	220.0	200.1	181.8	166.7
137.5°	288.0	285.8	281.6	273.0	261.1	246.9	230.7	213.4	196.9	181.8	168.3
140°	276.7	274.2	269.7	262.9	251.8	238.5	224.4	209.6	195.1	181.6	169.5
142.5°	264.6	262.9	259.0	252.5	242.7	231.2	219.1	206.1	193.6	181.6	170.6
145°	248.0	246.5	243.3	237.9	230.1	221.2	211.8	201.1	191.0	180.9	171.1
147.5°	233.4	232.7	230.4	225.8	220.0	213.0	205.5	197.0	188.7	179.8	171.5
150°	225.0	224.7	222.8	218.7	213.7	208.0	201.7	194.5	186.9	179.0	171.5
152.5°	217.5	217.1	216.0	212.7	208.4	203.8	198.0	191.7	184.9	177.7	170.9
155°	207.7	207.7	206.7	204.2	201.1	197.2	192.5	187.5	181.8	175.8	170.2
157.5°	199.1	199.1	198.6	196.6	194.3	191.3	187.3	183.1	178.8	173.9	169.3
160°	193.9	193.9	193.5	191.6	189.8	187.2	183.7	180.3	176.5	172.4	168.6
162.5°	188.8	189.0	188.7	186.8	185.5	183.2	180.5	177.5	174.5	170.9	167.8
165°	181.2	181.6	181.8	180.6	179.3	177.7	175.6	173.6	171.1	168.6	166.4
167.5°	175.2	175.5	175.6	174.7	174.1	173.2	171.4	170.0	168.1	166.3	164.9
170°	171.5	171.5	171.7	171.5	170.9	169.9	168.6	167.6	166.1	164.8	163.9
172.5°	167.6	168.2	168.4	168.2	167.8	167.1	166.3	165.7	164.3	163.3	162.9
175°	163.3	163.9	164.5	163.9	163.9	163.9	163.3	162.9	162.3	161.7	161.7
177.5°	160.7	161.1	161.7	161.4	161.7	161.4	161.4	161.1	161.0	160.7	160.7
180°	160.4	160.4	160.4	160.4	160.4	160.4	160.4	160.4	160.4	160.4	160.4



TEST NUMBER: P332957-940

CATALOG NUMBER: S124RDIP-S1020D365U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0
2.5°	1576.4	1569.5	1566.0	1558.1	1548.7	1543.8	1539.4	1532.9	1524.6	1515.7	1509.3
5°	1656.4	1641.6	1623.1	1600.9	1581.2	1562.1	1545.4	1528.7	1509.7	1490.0	1470.3
7.5°	1738.5	1709.4	1677.9	1641.6	1606.2	1574.0	1544.4	1516.1	1484.0	1455.3	1429.1
10°	1795.7	1756.2	1712.4	1666.3	1620.0	1579.9	1540.5	1504.8	1465.3	1430.1	1400.5
12.5°	1842.1	1795.7	1743.0	1685.5	1629.9	1581.4	1536.1	1489.4	1444.6	1406.5	1367.0
15°	1919.0	1855.5	1784.6	1715.6	1643.4	1577.4	1516.4	1462.2	1411.0	1357.5	1319.8
17.5°	1971.8	1896.6	1810.4	1727.4	1642.2	1564.4	1494.0	1429.4	1370.4	1315.6	1270.9
20°	2003.4	1920.2	1824.7	1730.4	1634.8	1551.6	1475.8	1404.3	1343.3	1284.1	1237.8
22.5°	2021.2	1929.1	1824.7	1725.9	1626.9	1536.8	1453.6	1379.1	1312.7	1253.5	1202.3
25°	2026.9	1928.2	1821.6	1708.2	1599.6	1504.1	1417.8	1337.0	1263.1	1203.9	1149.7
27.5°	2019.0	1902.8	1793.6	1677.2	1565.3	1464.5	1373.9	1289.1	1215.0	1151.6	1095.9
30°	2007.2	1882.6	1765.5	1644.7	1531.2	1434.5	1338.9	1257.6	1180.4	1114.5	1058.5
32.5°	1981.5	1858.0	1732.0	1608.2	1493.3	1393.6	1302.9	1221.0	1145.5	1078.1	1018.5
35°	1930.7	1805.5	1668.7	1541.8	1428.9	1325.3	1240.3	1161.4	1089.2	1017.2	954.2
37.5°	1863.8	1735.9	1599.8	1460.7	1347.8	1250.0	1172.0	1097.9	1027.5	961.6	892.0
40°	1800.6	1684.1	1543.6	1405.5	1289.6	1195.2	1123.2	1056.0	985.1	919.7	850.1
42.5°	1724.2	1625.0	1482.9	1344.3	1229.9	1139.1	1071.8	1006.1	941.6	878.3	805.7
45°	1596.6	1521.3	1388.2	1255.1	1139.8	1049.8	988.2	930.2	873.5	813.1	744.7
47.5°	1450.4	1399.5	1284.5	1148.2	1041.5	960.6	901.0	853.6	805.7	745.3	685.3
50°	1348.8	1316.1	1205.1	1080.7	978.9	904.3	843.3	798.9	758.8	700.9	647.3
52.5°	1240.3	1222.9	1129.2	1010.1	911.9	838.7	786.6	746.6	706.1	658.0	607.8
55°	1075.0	1084.3	1004.8	901.9	809.4	747.8	700.3	667.0	632.5	591.8	552.9
57.5°	906.2	940.0	886.5	796.2	709.5	652.6	616.8	588.8	559.8	526.1	492.9
60°	805.0	833.4	803.3	723.7	647.9	594.9	561.6	540.0	511.0	480.2	455.0
62.5°	706.4	736.7	718.9	654.7	584.2	538.7	509.3	489.2	467.6	440.8	414.5
65°	582.6	602.3	593.6	549.3	499.4	460.5	433.4	418.6	398.9	379.2	355.7
67.5°	446.2	484.3	479.2	455.7	412.5	382.2	364.4	351.3	333.4	318.7	302.8
70°	366.8	401.9	401.3	382.2	358.7	330.4	318.1	307.0	291.0	276.8	263.9
72.5°	300.2	332.4	337.2	322.5	306.5	285.1	273.2	265.6	250.0	240.3	229.8
75°	210.2	233.6	239.8	239.8	232.4	221.3	210.8	205.9	194.8	186.2	180.0
77.5°	137.9	152.7	162.3	164.4	165.6	161.8	153.3	149.8	141.2	138.2	132.3
80°	97.4	107.3	118.3	122.1	125.1	123.9	120.2	117.7	109.8	106.6	104.2
82.5°	67.3	72.8	81.9	90.0	89.2	92.4	89.2	87.2	81.1	80.0	77.6
85°	35.1	35.8	37.0	42.5	45.7	46.8	47.4	46.2	44.4	44.4	40.0
87.5°	12.8	12.2	12.8	12.8	13.3	15.2	16.5	16.9	15.5	14.2	12.8
90°	4.4	4.4	2.5	2.5	2.2	1.9	1.0	0.4	1.0	1.9	2.2
92.5°	63.7	39.2	23.2	16.7	12.0	8.2	5.3	3.6	5.3	8.2	12.0
95°	118.5	66.8	39.4	26.1	18.6	14.5	11.3	10.4	11.3	14.5	18.6
97.5°	106.6	63.8	42.7	31.7	25.1	21.4	18.6	18.6	18.6	21.4	25.1
100°	100.2	64.6	46.0	35.9	30.0	26.1	24.0	24.0	24.0	26.1	30.0
102.5°	98.4	67.1	50.3	40.8	35.0	31.5	29.5	29.0	29.5	31.5	35.0
105°	99.2	73.1	58.0	48.9	43.2	39.4	37.8	36.9	37.8	39.4	43.2
107.5°	104.0	80.1	66.3	57.2	51.8	47.8	46.2	45.6	46.2	47.8	51.8
110°	107.5	85.4	71.5	63.0	57.3	53.6	52.0	51.4	52.0	53.6	57.3





TEST NUMBER: P332957-940

CATALOG NUMBER: S124RDIP-S1020D365U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	111.3	90.4	77.0	68.6	62.9	59.4	57.5	56.9	57.5	59.4	62.9
115°	117.3	98.4	85.7	77.2	71.2	68.0	65.9	64.9	65.9	68.0	71.2
117.5°	123.3	105.9	94.0	85.2	79.5	76.1	74.1	73.2	74.1	76.1	79.5
120°	127.6	111.3	99.2	90.4	85.1	81.6	79.5	78.8	79.5	81.6	85.1
122.5°	131.7	116.3	104.3	95.8	89.9	86.7	84.4	83.8	84.4	86.7	89.9
125°	137.7	123.2	111.9	103.1	97.1	93.6	91.7	90.4	91.7	93.6	97.1
127.5°	142.9	129.7	118.7	109.8	103.5	99.6	97.3	96.3	97.3	99.6	103.5
130°	146.2	133.9	123.2	114.0	108.1	103.3	100.9	99.6	100.9	103.3	108.1
132.5°	149.5	137.5	126.7	118.2	111.6	107.2	103.9	102.9	103.9	107.2	111.6
135°	153.8	142.4	132.1	123.9	117.3	111.9	108.7	107.5	108.7	111.9	117.3
137.5°	156.9	146.2	136.5	128.7	121.8	116.7	113.2	112.1	113.2	116.7	121.8
140°	158.8	148.7	139.3	131.7	125.1	119.8	116.3	115.4	116.3	119.8	125.1
142.5°	160.3	151.1	141.8	134.5	128.1	123.1	119.8	118.9	119.8	123.1	128.1
145°	162.0	153.5	145.3	138.4	132.3	128.0	124.8	123.9	124.8	128.0	132.3
147.5°	163.5	156.0	148.3	142.0	137.1	132.6	129.7	129.5	129.7	132.6	137.1
150°	164.2	157.3	150.3	144.4	139.6	135.8	133.3	133.0	133.3	135.8	139.6
152.5°	164.7	158.3	152.1	146.6	142.4	138.8	136.3	136.3	136.3	138.8	142.4
155°	165.1	159.8	154.4	149.7	146.2	143.1	141.2	140.9	141.2	143.1	146.2
157.5°	165.1	160.9	156.3	152.6	149.5	147.1	145.3	145.3	145.3	147.1	149.5
160°	165.1	161.4	157.6	154.1	151.6	149.4	148.1	148.1	148.1	149.4	151.6
162.5°	165.1	161.8	158.4	155.6	153.4	151.4	150.4	150.6	150.4	151.4	153.4
165°	164.5	162.0	159.2	157.3	155.7	154.1	153.5	153.5	153.5	154.1	155.7
167.5°	163.7	161.9	159.9	158.4	157.5	156.3	156.0	156.3	156.0	156.3	157.5
170°	163.3	161.7	160.1	159.2	158.5	157.6	157.3	157.6	157.3	157.6	158.5
172.5°	162.7	161.4	160.3	159.6	159.3	158.5	158.5	158.8	158.5	158.5	159.3
175°	162.0	161.0	160.4	160.4	160.1	159.8	159.8	160.1	159.8	159.8	160.1
177.5°	161.1	160.7	160.4	160.4	160.4	160.2	160.4	160.7	160.4	160.2	160.4
180°	160.4	160.4	160.4	160.4	160.4	160.4	160.4	160.4	160.4	160.4	160.4



TEST NUMBER: P332957-940

CATALOG NUMBER: S124RDIP-S1020D365U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0
2.5°	1502.4	1497.4	1491.0	1483.6	1474.8	1466.9	1463.5	1466.4	1467.8	1463.9	1463.5
5°	1456.7	1441.3	1428.9	1410.4	1395.6	1383.3	1374.7	1371.0	1372.2	1362.4	1359.9
7.5°	1405.2	1387.0	1366.8	1344.8	1324.4	1306.3	1296.7	1291.6	1281.1	1276.7	1269.2
10°	1372.2	1347.6	1327.8	1301.9	1278.5	1257.0	1246.4	1237.8	1227.4	1222.4	1211.9
12.5°	1338.2	1309.6	1287.9	1261.0	1237.1	1211.0	1201.0	1185.1	1168.7	1158.3	1144.9
15°	1290.2	1255.7	1229.2	1197.1	1168.8	1139.2	1112.7	1083.1	1072.0	1048.6	1035.0
17.5°	1234.1	1199.1	1166.3	1123.3	1079.5	1042.8	1014.5	986.1	969.2	954.2	947.4
20°	1197.1	1165.1	1119.5	1069.5	1020.8	980.2	957.3	938.9	920.3	909.9	902.5
22.5°	1162.1	1121.1	1068.2	1014.3	965.6	933.8	914.4	895.5	880.4	870.4	860.6
25°	1103.4	1049.8	993.7	932.1	898.8	871.0	850.1	834.6	825.5	812.4	807.5
27.5°	1043.1	978.2	916.3	874.9	840.2	814.8	796.6	785.0	773.3	765.0	758.6
30°	996.8	930.9	875.4	835.9	800.8	779.8	765.0	751.4	742.2	735.4	730.5
32.5°	950.9	884.9	838.4	795.9	768.2	747.8	732.0	721.8	714.6	705.8	702.8
35°	884.6	826.0	785.3	747.2	718.8	700.3	688.0	677.4	671.3	668.9	667.0
37.5°	820.8	772.9	729.2	697.9	672.5	658.0	643.5	638.3	634.1	629.6	631.6
40°	780.4	735.4	696.6	663.3	642.9	627.0	618.3	612.2	608.4	608.4	608.4
42.5°	745.4	701.4	663.5	633.7	613.3	599.8	590.2	585.0	583.8	583.3	586.2
45°	691.1	650.3	612.2	587.5	570.2	556.6	551.1	546.8	546.8	549.3	549.8
47.5°	637.1	599.1	568.4	540.7	525.0	516.5	511.7	509.4	509.7	512.1	515.0
50°	604.1	566.5	536.3	511.7	496.9	488.8	484.6	483.3	484.6	484.6	488.8
52.5°	568.1	534.5	504.7	484.0	467.3	459.8	457.4	455.7	456.4	458.4	460.2
55°	515.3	485.2	456.8	437.0	424.7	419.8	414.3	414.8	413.7	414.8	414.8
57.5°	462.4	435.3	408.9	393.3	382.5	375.3	369.3	371.0	369.2	368.9	367.9
60°	428.5	398.9	377.9	363.7	351.3	345.2	339.7	340.9	339.0	337.8	335.4
62.5°	391.5	366.8	346.8	333.1	323.2	316.1	310.6	309.3	305.1	300.9	295.4
65°	337.8	317.4	299.6	286.7	277.4	271.9	267.5	263.9	254.6	244.7	239.8
67.5°	285.7	271.0	254.3	243.3	235.9	228.5	220.3	214.0	205.4	200.0	196.9
70°	252.1	237.9	223.7	213.3	205.3	198.5	189.2	184.9	178.8	176.3	173.3
72.5°	220.1	206.9	193.7	184.2	175.7	170.4	163.1	158.8	156.0	155.1	152.0
75°	171.4	160.9	151.1	142.4	135.6	131.9	128.9	125.7	124.5	119.0	115.9
77.5°	125.0	118.2	111.9	105.8	100.9	98.5	92.6	89.0	86.9	84.4	83.7
80°	97.4	92.5	86.3	82.6	75.8	73.4	70.9	70.3	69.6	69.0	68.4
82.5°	73.2	68.3	62.2	59.9	58.1	56.6	55.1	54.5	53.9	54.2	54.1
85°	37.0	34.5	34.5	33.9	33.3	32.6	32.0	32.0	31.5	32.0	31.5
87.5°	12.8	12.3	12.8	11.8	12.4	12.5	11.9	11.9	12.6	11.6	11.6
90°	2.5	2.5	4.4	4.4	5.1	5.7	5.4	5.7	6.0	6.3	6.3
92.5°	16.7	23.2	39.2	63.7	87.5	100.0	83.3	61.9	46.5	37.1	30.8
95°	26.1	39.4	66.8	118.5	193.9	256.8	264.1	233.5	184.7	142.4	111.9
97.5°	31.7	42.7	63.8	106.6	181.4	270.5	331.8	345.0	326.9	296.0	263.1
100°	35.9	46.0	64.6	100.2	164.5	253.4	334.0	380.0	386.4	371.0	347.6
102.5°	40.8	50.3	67.1	98.4	153.2	231.9	315.1	378.4	409.6	414.0	404.3
105°	48.9	58.0	73.1	99.2	143.4	206.7	280.8	352.9	407.5	438.7	451.7
107.5°	57.2	66.3	80.1	104.0	141.6	192.6	253.1	317.0	375.1	418.9	447.1
110°	63.0	71.5	85.4	107.5	142.1	187.8	239.2	295.3	349.8	395.6	430.2



TEST NUMBER: P332957-940

CATALOG NUMBER: S124RDIP-S1020D365U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	68.6	77.0	90.4	111.3	143.7	185.6	231.4	279.4	327.6	370.8	405.5
115°	77.2	85.7	98.4	117.3	146.5	184.4	224.1	263.5	302.2	339.1	369.3
117.5°	85.2	94.0	105.9	123.3	149.6	184.0	220.8	255.7	287.8	316.7	342.4
120°	90.4	99.2	111.3	127.6	151.9	184.0	219.0	252.1	281.4	306.7	329.0
122.5°	95.8	104.3	116.3	131.7	154.2	183.8	217.0	249.1	277.4	300.3	319.9
125°	103.1	111.9	123.2	137.7	157.6	183.4	213.7	244.0	271.0	292.7	310.1
127.5°	109.8	118.7	129.7	142.9	160.3	182.7	209.2	237.6	263.5	285.3	301.7
130°	114.0	123.2	133.9	146.2	162.3	182.4	206.4	232.6	257.5	278.9	295.6
132.5°	118.2	126.7	137.5	149.5	164.1	182.3	203.9	227.3	250.7	271.6	288.3
135°	123.9	132.1	142.4	153.8	166.7	181.8	200.1	220.0	240.5	259.7	275.4
137.5°	128.7	136.5	146.2	156.9	168.3	181.8	196.9	213.4	230.7	246.9	261.1
140°	131.7	139.3	148.7	158.8	169.5	181.6	195.1	209.6	224.4	238.5	251.8
142.5°	134.5	141.8	151.1	160.3	170.6	181.6	193.6	206.1	219.1	231.2	242.7
145°	138.4	145.3	153.5	162.0	171.1	180.9	191.0	201.1	211.8	221.2	230.1
147.5°	142.0	148.3	156.0	163.5	171.5	179.8	188.7	197.0	205.5	213.0	220.0
150°	144.4	150.3	157.3	164.2	171.5	179.0	186.9	194.5	201.7	208.0	213.7
152.5°	146.6	152.1	158.3	164.7	170.9	177.7	184.9	191.7	198.0	203.8	208.4
155°	149.7	154.4	159.8	165.1	170.2	175.8	181.8	187.5	192.5	197.2	201.1
157.5°	152.6	156.3	160.9	165.1	169.3	173.9	178.8	183.1	187.3	191.3	194.3
160°	154.1	157.6	161.4	165.1	168.6	172.4	176.5	180.3	183.7	187.2	189.8
162.5°	155.6	158.4	161.8	165.1	167.8	170.9	174.5	177.5	180.5	183.2	185.5
165°	157.3	159.2	162.0	164.5	166.4	168.6	171.1	173.6	175.6	177.7	179.3
167.5°	158.4	159.9	161.9	163.7	164.9	166.3	168.1	170.0	171.4	173.2	174.1
170°	159.2	160.1	161.7	163.3	163.9	164.8	166.1	167.6	168.6	169.9	170.9
172.5°	159.6	160.3	161.4	162.7	162.9	163.3	164.3	165.7	166.3	167.1	167.8
175°	160.4	160.4	161.0	162.0	161.7	161.7	162.3	162.9	163.3	163.9	163.9
177.5°	160.4	160.4	160.7	161.1	160.7	160.7	161.0	161.1	161.4	161.4	161.7
180°	160.4	160.4	160.4	160.4	160.4	160.4	160.4	160.4	160.4	160.4	160.4



TEST NUMBER: P332957-940

CATALOG NUMBER: S124RDIP-S1020D365U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0
2.5°	1460.4	1461.4	1458.0	1457.1	1458.0	1461.4	1460.4	1463.5	1463.9	1467.8	1466.4
5°	1355.0	1353.7	1350.6	1351.2	1350.6	1353.7	1355.0	1359.9	1362.4	1372.2	1371.0
7.5°	1264.7	1259.9	1261.2	1256.3	1261.2	1259.9	1264.7	1269.2	1276.7	1281.1	1291.6
10°	1209.4	1202.7	1197.1	1192.2	1197.1	1202.7	1209.4	1211.9	1222.4	1227.4	1237.8
12.5°	1134.0	1128.2	1120.7	1122.2	1120.7	1128.2	1134.0	1144.9	1158.3	1168.7	1185.1
15°	1027.0	1017.7	1003.0	1004.8	1003.0	1017.7	1027.0	1035.0	1048.6	1072.0	1083.1
17.5°	936.4	936.5	929.7	931.3	929.7	936.5	936.4	947.4	954.2	969.2	986.1
20°	889.6	885.2	885.8	884.0	885.8	885.2	889.6	902.5	909.9	920.3	938.9
22.5°	857.0	851.7	847.4	843.6	847.4	851.7	857.0	860.6	870.4	880.4	895.5
25°	802.0	798.3	792.7	791.5	792.7	798.3	802.0	807.5	812.4	825.5	834.6
27.5°	753.7	753.0	750.7	747.9	750.7	753.0	753.7	758.6	765.0	773.3	785.0
30°	725.6	724.3	723.1	721.2	723.1	724.3	725.6	730.5	735.4	742.2	751.4
32.5°	700.4	699.6	698.4	698.6	698.4	699.6	700.4	702.8	705.8	714.6	721.8
35°	664.5	663.9	662.7	662.1	662.7	663.9	664.5	667.0	668.9	671.3	677.4
37.5°	631.0	632.6	631.9	631.7	631.9	632.6	631.0	631.6	629.6	634.1	638.3
40°	607.8	608.4	609.7	609.0	609.7	608.4	607.8	608.4	608.4	608.4	612.2
42.5°	588.6	588.7	590.4	588.4	590.4	588.7	588.6	586.2	583.3	583.8	585.0
45°	554.2	557.9	557.2	557.2	557.2	557.9	554.2	549.8	549.3	546.8	546.8
47.5°	516.6	519.8	520.7	520.5	520.7	519.8	516.6	515.0	512.1	509.7	509.4
50°	492.0	490.7	492.6	492.0	492.6	490.7	492.0	488.8	484.6	484.6	483.3
52.5°	461.8	462.1	462.0	461.4	462.0	462.1	461.8	460.2	458.4	456.4	455.7
55°	415.4	416.1	414.8	415.4	414.8	416.1	415.4	414.8	414.8	413.7	414.8
57.5°	365.2	362.2	363.5	361.9	363.5	362.2	365.2	367.9	368.9	369.2	371.0
60°	329.2	324.2	323.0	320.6	323.0	324.2	329.2	335.4	337.8	339.0	340.9
62.5°	288.7	285.3	281.1	283.0	281.1	285.3	288.7	295.4	300.9	305.1	309.3
65°	234.9	232.4	230.5	233.0	230.5	232.4	234.9	239.8	244.7	254.6	263.9
67.5°	194.4	193.1	193.1	191.8	193.1	193.1	194.4	196.9	200.0	205.4	214.0
70°	173.3	171.4	171.4	170.1	171.4	171.4	173.3	173.3	176.3	178.8	184.9
72.5°	151.5	149.6	150.2	149.5	150.2	149.6	151.5	152.0	155.1	156.0	158.8
75°	112.2	109.1	109.1	109.8	109.1	109.1	112.2	115.9	119.0	124.5	125.7
77.5°	83.7	83.1	84.0	82.8	84.0	83.1	83.7	83.7	84.4	86.9	89.0
80°	68.4	67.8	67.2	69.0	67.2	67.8	68.4	68.4	69.0	69.6	70.3
82.5°	53.1	53.1	52.9	55.2	52.9	53.1	53.1	54.1	54.2	53.9	54.5
85°	32.0	30.9	32.0	30.9	32.0	30.9	32.0	31.5	32.0	31.5	32.0
87.5°	12.7	12.2	11.7	12.2	11.7	12.2	12.7	11.6	11.6	12.6	11.9
90°	6.6	7.0	6.6	6.6	6.6	7.0	6.6	6.3	6.3	6.0	5.7
92.5°	27.0	25.3	24.3	24.3	24.3	25.3	27.0	30.8	37.1	46.5	61.9
95°	96.4	86.7	81.0	76.9	81.0	86.7	96.4	111.9	142.4	184.7	233.5
97.5°	240.5	221.6	212.1	205.5	212.1	221.6	240.5	263.1	296.0	326.9	345.0
100°	320.2	301.0	291.5	289.0	291.5	301.0	320.2	347.6	371.0	386.4	380.0
102.5°	387.5	373.6	363.6	361.6	363.6	373.6	387.5	404.3	414.0	409.6	378.4
105°	452.3	449.7	445.3	443.4	445.3	449.7	452.3	451.7	438.7	407.5	352.9
107.5°	462.6	469.8	473.0	473.8	473.0	469.8	462.6	447.1	418.9	375.1	317.0
110°	452.5	465.8	471.4	474.3	471.4	465.8	452.5	430.2	395.6	349.8	295.3



TEST NUMBER: P332957-940

CATALOG NUMBER: S124RDIP-S1020D365U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	430.9	446.9	454.9	459.4	454.9	446.9	430.9	405.5	370.8	327.6	279.4
115°	394.2	413.1	423.3	425.8	423.3	413.1	394.2	369.3	339.1	302.2	263.5
117.5°	363.6	379.5	389.7	391.6	389.7	379.5	363.6	342.4	316.7	287.8	255.7
120°	347.0	360.9	369.1	372.6	369.1	360.9	347.0	329.0	306.7	281.4	252.1
122.5°	335.1	347.0	353.9	357.4	353.9	347.0	335.1	319.9	300.3	277.4	249.1
125°	322.7	331.9	337.9	339.7	337.9	331.9	322.7	310.1	292.7	271.0	244.0
127.5°	314.3	322.4	327.5	329.4	327.5	322.4	314.3	301.7	285.3	263.5	237.6
130°	308.5	316.4	321.5	323.3	321.5	316.4	308.5	295.6	278.9	257.5	232.6
132.5°	301.0	309.9	314.7	316.6	314.7	309.9	301.0	288.3	271.6	250.7	227.3
135°	288.0	296.9	301.9	303.8	301.9	296.9	288.0	275.4	259.7	240.5	220.0
137.5°	273.0	281.6	285.8	288.0	285.8	281.6	273.0	261.1	246.9	230.7	213.4
140°	262.9	269.7	274.2	276.7	274.2	269.7	262.9	251.8	238.5	224.4	209.6
142.5°	252.5	259.0	262.9	264.6	262.9	259.0	252.5	242.7	231.2	219.1	206.1
145°	237.9	243.3	246.5	248.0	246.5	243.3	237.9	230.1	221.2	211.8	201.1
147.5°	225.8	230.4	232.7	233.4	232.7	230.4	225.8	220.0	213.0	205.5	197.0
150°	218.7	222.8	224.7	225.0	224.7	222.8	218.7	213.7	208.0	201.7	194.5
152.5°	212.7	216.0	217.1	217.5	217.1	216.0	212.7	208.4	203.8	198.0	191.7
155°	204.2	206.7	207.7	207.7	207.7	206.7	204.2	201.1	197.2	192.5	187.5
157.5°	196.6	198.6	199.1	199.1	199.1	198.6	196.6	194.3	191.3	187.3	183.1
160°	191.6	193.5	193.9	193.9	193.9	193.5	191.6	189.8	187.2	183.7	180.3
162.5°	186.8	188.7	189.0	188.8	189.0	188.7	186.8	185.5	183.2	180.5	177.5
165°	180.6	181.8	181.6	181.2	181.6	181.8	180.6	179.3	177.7	175.6	173.6
167.5°	174.7	175.6	175.5	175.2	175.5	175.6	174.7	174.1	173.2	171.4	170.0
170°	171.5	171.7	171.5	171.5	171.5	171.7	171.5	170.9	169.9	168.6	167.6
172.5°	168.2	168.4	168.2	167.6	168.2	168.4	168.2	167.8	167.1	166.3	165.7
175°	163.9	164.5	163.9	163.3	163.9	164.5	163.9	163.9	163.9	163.3	162.9
177.5°	161.4	161.7	161.1	160.7	161.1	161.7	161.4	161.7	161.4	161.4	161.1
180°	160.4	160.4	160.4	160.4	160.4	160.4	160.4	160.4	160.4	160.4	160.4



TEST NUMBER: P332957-940

CATALOG NUMBER: S124RDIP-S1020D365U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0
2.5°	1463.5	1466.9	1474.8	1483.6	1491.0	1497.4	1502.4	1509.3	1515.7	1524.6	1532.9
5°	1374.7	1383.3	1395.6	1410.4	1428.9	1441.3	1456.7	1470.3	1490.0	1509.7	1528.7
7.5°	1296.7	1306.3	1324.4	1344.8	1366.8	1387.0	1405.2	1429.1	1455.3	1484.0	1516.1
10°	1246.4	1257.0	1278.5	1301.9	1327.8	1347.6	1372.2	1400.5	1430.1	1465.3	1504.8
12.5°	1201.0	1211.0	1237.1	1261.0	1287.9	1309.6	1338.2	1367.0	1406.5	1444.6	1489.4
15°	1112.7	1139.2	1168.8	1197.1	1229.2	1255.7	1290.2	1319.8	1357.5	1411.0	1462.2
17.5°	1014.5	1042.8	1079.5	1123.3	1166.3	1199.1	1234.1	1270.9	1315.6	1370.4	1429.4
20°	957.3	980.2	1020.8	1069.5	1119.5	1165.1	1197.1	1237.8	1284.1	1343.3	1404.3
22.5°	914.4	933.8	965.6	1014.3	1068.2	1121.1	1162.1	1202.3	1253.5	1312.7	1379.1
25°	850.1	871.0	898.8	932.1	993.7	1049.8	1103.4	1149.7	1203.9	1263.1	1337.0
27.5°	796.6	814.8	840.2	874.9	916.3	978.2	1043.1	1095.9	1151.6	1215.0	1289.1
30°	765.0	779.8	800.8	835.9	875.4	930.9	996.8	1058.5	1114.5	1180.4	1257.6
32.5°	732.0	747.8	768.2	795.9	838.4	884.9	950.9	1018.5	1078.1	1145.5	1221.0
35°	688.0	700.3	718.8	747.2	785.3	826.0	884.6	954.2	1017.2	1089.2	1161.4
37.5°	643.5	658.0	672.5	697.9	729.2	772.9	820.8	892.0	961.6	1027.5	1097.9
40°	618.3	627.0	642.9	663.3	696.6	735.4	780.4	850.1	919.7	985.1	1056.0
42.5°	590.2	599.8	613.3	633.7	663.5	701.4	745.4	805.7	878.3	941.6	1006.1
45°	551.1	556.6	570.2	587.5	612.2	650.3	691.1	744.7	813.1	873.5	930.2
47.5°	511.7	516.5	525.0	540.7	568.4	599.1	637.1	685.3	745.3	805.7	853.6
50°	484.6	488.8	496.9	511.7	536.3	566.5	604.1	647.3	700.9	758.8	798.9
52.5°	457.4	459.8	467.3	484.0	504.7	534.5	568.1	607.8	658.0	706.1	746.6
55°	414.3	419.8	424.7	437.0	456.8	485.2	515.3	552.9	591.8	632.5	667.0
57.5°	369.3	375.3	382.5	393.3	408.9	435.3	462.4	492.9	526.1	559.8	588.8
60°	339.7	345.2	351.3	363.7	377.9	398.9	428.5	455.0	480.2	511.0	540.0
62.5°	310.6	316.1	323.2	333.1	346.8	366.8	391.5	414.5	440.8	467.6	489.2
65°	267.5	271.9	277.4	286.7	299.6	317.4	337.8	355.7	379.2	398.9	418.6
67.5°	220.3	228.5	235.9	243.3	254.3	271.0	285.7	302.8	318.7	333.4	351.3
70°	189.2	198.5	205.3	213.3	223.7	237.9	252.1	263.9	276.8	291.0	307.0
72.5°	163.1	170.4	175.7	184.2	193.7	206.9	220.1	229.8	240.3	250.0	265.6
75°	128.9	131.9	135.6	142.4	151.1	160.9	171.4	180.0	186.2	194.8	205.9
77.5°	92.6	98.5	100.9	105.8	111.9	118.2	125.0	132.3	138.2	141.2	149.8
80°	70.9	73.4	75.8	82.6	86.3	92.5	97.4	104.2	106.6	109.8	117.7
82.5°	55.1	56.6	58.1	59.9	62.2	68.3	73.2	77.6	80.0	81.1	87.2
85°	32.0	32.6	33.3	33.9	34.5	34.5	37.0	40.0	44.4	44.4	46.2
87.5°	11.9	12.5	12.4	11.8	12.8	12.3	12.8	12.8	14.2	15.5	16.9
90°	5.4	5.7	5.1	4.4	4.4	2.5	2.5	2.2	1.9	1.0	0.4
92.5°	83.3	100.0	87.5	63.7	39.2	23.2	16.7	12.0	8.2	5.3	3.6
95°	264.1	256.8	193.9	118.5	66.8	39.4	26.1	18.6	14.5	11.3	10.4
97.5°	331.8	270.5	181.4	106.6	63.8	42.7	31.7	25.1	21.4	18.6	18.6
100°	334.0	253.4	164.5	100.2	64.6	46.0	35.9	30.0	26.1	24.0	24.0
102.5°	315.1	231.9	153.2	98.4	67.1	50.3	40.8	35.0	31.5	29.5	29.0
105°	280.8	206.7	143.4	99.2	73.1	58.0	48.9	43.2	39.4	37.8	36.9
107.5°	253.1	192.6	141.6	104.0	80.1	66.3	57.2	51.8	47.8	46.2	45.6
110°	239.2	187.8	142.1	107.5	85.4	71.5	63.0	57.3	53.6	52.0	51.4



TEST NUMBER: P332957-940

CATALOG NUMBER: S124RDIP-S1020D365U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	231.4	185.6	143.7	111.3	90.4	77.0	68.6	62.9	59.4	57.5	56.9
115°	224.1	184.4	146.5	117.3	98.4	85.7	77.2	71.2	68.0	65.9	64.9
117.5°	220.8	184.0	149.6	123.3	105.9	94.0	85.2	79.5	76.1	74.1	73.2
120°	219.0	184.0	151.9	127.6	111.3	99.2	90.4	85.1	81.6	79.5	78.8
122.5°	217.0	183.8	154.2	131.7	116.3	104.3	95.8	89.9	86.7	84.4	83.8
125°	213.7	183.4	157.6	137.7	123.2	111.9	103.1	97.1	93.6	91.7	90.4
127.5°	209.2	182.7	160.3	142.9	129.7	118.7	109.8	103.5	99.6	97.3	96.3
130°	206.4	182.4	162.3	146.2	133.9	123.2	114.0	108.1	103.3	100.9	99.6
132.5°	203.9	182.3	164.1	149.5	137.5	126.7	118.2	111.6	107.2	103.9	102.9
135°	200.1	181.8	166.7	153.8	142.4	132.1	123.9	117.3	111.9	108.7	107.5
137.5°	196.9	181.8	168.3	156.9	146.2	136.5	128.7	121.8	116.7	113.2	112.1
140°	195.1	181.6	169.5	158.8	148.7	139.3	131.7	125.1	119.8	116.3	115.4
142.5°	193.6	181.6	170.6	160.3	151.1	141.8	134.5	128.1	123.1	119.8	118.9
145°	191.0	180.9	171.1	162.0	153.5	145.3	138.4	132.3	128.0	124.8	123.9
147.5°	188.7	179.8	171.5	163.5	156.0	148.3	142.0	137.1	132.6	129.7	129.5
150°	186.9	179.0	171.5	164.2	157.3	150.3	144.4	139.6	135.8	133.3	133.0
152.5°	184.9	177.7	170.9	164.7	158.3	152.1	146.6	142.4	138.8	136.3	136.3
155°	181.8	175.8	170.2	165.1	159.8	154.4	149.7	146.2	143.1	141.2	140.9
157.5°	178.8	173.9	169.3	165.1	160.9	156.3	152.6	149.5	147.1	145.3	145.3
160°	176.5	172.4	168.6	165.1	161.4	157.6	154.1	151.6	149.4	148.1	148.1
162.5°	174.5	170.9	167.8	165.1	161.8	158.4	155.6	153.4	151.4	150.4	150.6
165°	171.1	168.6	166.4	164.5	162.0	159.2	157.3	155.7	154.1	153.5	153.5
167.5°	168.1	166.3	164.9	163.7	161.9	159.9	158.4	157.5	156.3	156.0	156.3
170°	166.1	164.8	163.9	163.3	161.7	160.1	159.2	158.5	157.6	157.3	157.6
172.5°	164.3	163.3	162.9	162.7	161.4	160.3	159.6	159.3	158.5	158.5	158.8
175°	162.3	161.7	161.7	162.0	161.0	160.4	160.4	160.1	159.8	159.8	160.1
177.5°	161.0	160.7	160.7	161.1	160.7	160.4	160.4	160.4	160.2	160.4	160.7
180°	160.4	160.4	160.4	160.4	160.4	160.4	160.4	160.4	160.4	160.4	160.4



TEST NUMBER: P332957-940

CATALOG NUMBER: S124RDIP-S1020D365U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0
2.5°	1539.4	1543.8	1548.7	1558.1	1566.0	1569.5	1576.4	1581.3	1579.8	1586.7	1598.6
5°	1545.4	1562.1	1581.2	1600.9	1623.1	1641.6	1656.4	1671.2	1682.9	1697.1	1718.1
7.5°	1544.4	1574.0	1606.2	1641.6	1677.9	1709.4	1738.5	1768.1	1794.3	1823.1	1860.6
10°	1540.5	1579.9	1620.0	1666.3	1712.4	1756.2	1795.7	1832.6	1867.9	1905.4	1952.9
12.5°	1536.1	1581.4	1629.9	1685.5	1743.0	1795.7	1842.1	1895.3	1939.3	1987.8	2042.6
15°	1516.4	1577.4	1643.4	1715.6	1784.6	1855.5	1919.0	1984.3	2045.3	2103.3	2172.4
17.5°	1494.0	1564.4	1642.2	1727.4	1810.4	1896.6	1971.8	2054.2	2116.7	2194.4	2258.5
20°	1475.8	1551.6	1634.8	1730.4	1824.7	1920.2	2003.4	2087.3	2157.6	2235.9	2317.2
22.5°	1453.6	1536.8	1626.9	1725.9	1824.7	1929.1	2021.2	2104.5	2191.6	2279.7	2363.6
25°	1417.8	1504.1	1599.6	1708.2	1821.6	1928.2	2026.9	2130.4	2224.1	2319.7	2394.9
27.5°	1373.9	1464.5	1565.3	1677.2	1793.6	1902.8	2019.0	2129.3	2223.7	2315.6	2381.2
30°	1338.9	1434.5	1531.2	1644.7	1765.5	1882.6	2007.2	2117.5	2216.7	2299.4	2336.3
32.5°	1302.9	1393.6	1493.3	1608.2	1732.0	1858.0	1981.5	2094.3	2186.1	2235.7	2236.7
35°	1240.3	1325.3	1428.9	1541.8	1668.7	1805.5	1930.7	2041.7	2097.7	2102.0	2041.7
37.5°	1172.0	1250.0	1347.8	1460.7	1599.8	1735.9	1863.8	1937.7	1956.5	1893.7	1782.0
40°	1123.2	1195.2	1289.6	1405.5	1543.6	1684.1	1800.6	1854.8	1835.1	1733.4	1608.9
42.5°	1071.8	1139.1	1229.9	1344.3	1482.9	1625.0	1724.2	1753.3	1701.0	1583.5	1437.8
45°	988.2	1049.8	1139.8	1255.1	1388.2	1521.3	1596.6	1581.8	1494.9	1355.6	1192.2
47.5°	901.0	960.6	1041.5	1148.2	1284.5	1399.5	1450.4	1405.8	1282.1	1128.8	996.0
50°	843.3	904.3	978.9	1080.7	1205.1	1316.1	1348.8	1280.9	1143.5	996.1	874.1
52.5°	786.6	838.7	911.9	1010.1	1129.2	1222.9	1240.3	1162.1	1020.2	888.1	779.9
55°	700.3	747.8	809.4	901.9	1004.8	1084.3	1075.0	974.6	845.8	733.0	647.9
57.5°	616.8	652.6	709.5	796.2	886.5	940.0	906.2	820.5	700.4	608.1	536.3
60°	561.6	594.9	647.9	723.7	803.3	833.4	805.0	712.0	617.1	532.6	472.2
62.5°	509.3	538.7	584.2	654.7	718.9	736.7	706.4	625.2	539.7	467.5	417.5
65°	433.4	460.5	499.4	549.3	593.6	602.3	582.6	499.4	434.6	374.2	339.7
67.5°	364.4	382.2	412.5	455.7	479.2	484.3	446.2	393.9	336.8	299.7	273.7
70°	318.1	330.4	358.7	382.2	401.3	401.9	366.8	324.9	281.1	250.9	231.8
72.5°	273.2	285.1	306.5	322.5	337.2	332.4	300.2	267.2	231.8	209.0	194.8
75°	210.8	221.3	232.4	239.8	239.8	233.6	210.2	185.6	165.2	151.7	147.3
77.5°	153.3	161.8	165.6	164.4	162.3	152.7	137.9	121.7	114.4	108.0	104.8
80°	120.2	123.9	125.1	122.1	118.3	107.3	97.4	90.6	83.8	81.4	80.2
82.5°	89.2	92.4	89.2	90.0	81.9	72.8	67.3	65.0	62.2	61.2	59.9
85°	47.4	46.8	45.7	42.5	37.0	35.8	35.1	34.5	33.3	33.9	32.6
87.5°	16.5	15.2	13.3	12.8	12.8	12.2	12.8	12.8	12.9	12.4	13.5
90°	1.0	1.9	2.2	2.5	2.5	4.4	4.4	5.1	5.7	5.4	5.7
92.5°	5.3	8.2	12.0	16.7	23.2	39.2	63.7	87.5	100.0	83.3	61.9
95°	11.3	14.5	18.6	26.1	39.4	66.8	118.5	193.9	256.8	264.1	233.5
97.5°	18.6	21.4	25.1	31.7	42.7	63.8	106.6	181.4	270.5	331.8	345.0
100°	24.0	26.1	30.0	35.9	46.0	64.6	100.2	164.5	253.4	334.0	380.0
102.5°	29.5	31.5	35.0	40.8	50.3	67.1	98.4	153.2	231.9	315.1	378.4
105°	37.8	39.4	43.2	48.9	58.0	73.1	99.2	143.4	206.7	280.8	352.9
107.5°	46.2	47.8	51.8	57.2	66.3	80.1	104.0	141.6	192.6	253.1	317.0
110°	52.0	53.6	57.3	63.0	71.5	85.4	107.5	142.1	187.8	239.2	295.3





TEST NUMBER: P332957-940

CATALOG NUMBER: S124RDIP-S1020D365U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	57.5	59.4	62.9	68.6	77.0	90.4	111.3	143.7	185.6	231.4	279.4
115°	65.9	68.0	71.2	77.2	85.7	98.4	117.3	146.5	184.4	224.1	263.5
117.5°	74.1	76.1	79.5	85.2	94.0	105.9	123.3	149.6	184.0	220.8	255.7
120°	79.5	81.6	85.1	90.4	99.2	111.3	127.6	151.9	184.0	219.0	252.1
122.5°	84.4	86.7	89.9	95.8	104.3	116.3	131.7	154.2	183.8	217.0	249.1
125°	91.7	93.6	97.1	103.1	111.9	123.2	137.7	157.6	183.4	213.7	244.0
127.5°	97.3	99.6	103.5	109.8	118.7	129.7	142.9	160.3	182.7	209.2	237.6
130°	100.9	103.3	108.1	114.0	123.2	133.9	146.2	162.3	182.4	206.4	232.6
132.5°	103.9	107.2	111.6	118.2	126.7	137.5	149.5	164.1	182.3	203.9	227.3
135°	108.7	111.9	117.3	123.9	132.1	142.4	153.8	166.7	181.8	200.1	220.0
137.5°	113.2	116.7	121.8	128.7	136.5	146.2	156.9	168.3	181.8	196.9	213.4
140°	116.3	119.8	125.1	131.7	139.3	148.7	158.8	169.5	181.6	195.1	209.6
142.5°	119.8	123.1	128.1	134.5	141.8	151.1	160.3	170.6	181.6	193.6	206.1
145°	124.8	128.0	132.3	138.4	145.3	153.5	162.0	171.1	180.9	191.0	201.1
147.5°	129.7	132.6	137.1	142.0	148.3	156.0	163.5	171.5	179.8	188.7	197.0
150°	133.3	135.8	139.6	144.4	150.3	157.3	164.2	171.5	179.0	186.9	194.5
152.5°	136.3	138.8	142.4	146.6	152.1	158.3	164.7	170.9	177.7	184.9	191.7
155°	141.2	143.1	146.2	149.7	154.4	159.8	165.1	170.2	175.8	181.8	187.5
157.5°	145.3	147.1	149.5	152.6	156.3	160.9	165.1	169.3	173.9	178.8	183.1
160°	148.1	149.4	151.6	154.1	157.6	161.4	165.1	168.6	172.4	176.5	180.3
162.5°	150.4	151.4	153.4	155.6	158.4	161.8	165.1	167.8	170.9	174.5	177.5
165°	153.5	154.1	155.7	157.3	159.2	162.0	164.5	166.4	168.6	171.1	173.6
167.5°	156.0	156.3	157.5	158.4	159.9	161.9	163.7	164.9	166.3	168.1	170.0
170°	157.3	157.6	158.5	159.2	160.1	161.7	163.3	163.9	164.8	166.1	167.6
172.5°	158.5	158.5	159.3	159.6	160.3	161.4	162.7	162.9	163.3	164.3	165.7
175°	159.8	159.8	160.1	160.4	160.4	161.0	162.0	161.7	161.7	162.3	162.9
177.5°	160.4	160.2	160.4	160.4	160.4	160.7	161.1	160.7	160.7	161.0	161.1
180°	160.4	160.4	160.4	160.4	160.4	160.4	160.4	160.4	160.4	160.4	160.4



TEST NUMBER: P332957-940

CATALOG NUMBER: S124RDIP-S1020D365U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0
2.5°	1605.0	1607.0	1608.5	1613.4	1613.8	1618.3	1613.8
5°	1737.8	1746.4	1760.0	1773.5	1774.8	1783.3	1768.0
7.5°	1886.7	1906.7	1919.1	1941.1	1949.7	1955.1	1946.2
10°	1989.2	2007.8	2040.4	2056.5	2072.5	2074.9	2067.5
12.5°	2088.4	2117.7	2143.5	2173.8	2173.1	2194.8	2186.9
15°	2220.4	2250.7	2286.3	2320.3	2332.6	2332.6	2342.5
17.5°	2314.6	2370.0	2407.0	2433.6	2462.7	2467.7	2464.3
20°	2378.3	2438.0	2477.5	2512.0	2531.7	2537.3	2537.3
22.5°	2425.5	2476.5	2515.0	2546.0	2562.3	2568.8	2566.9
25°	2458.4	2502.1	2525.6	2534.8	2539.1	2537.9	2526.2
27.5°	2413.5	2411.5	2396.7	2368.4	2347.1	2334.1	2319.3
30°	2327.7	2295.6	2258.6	2218.0	2165.6	2125.5	2113.2
32.5°	2199.9	2128.0	2065.3	1997.5	1941.2	1901.1	1884.4
35°	1952.9	1838.9	1745.8	1664.4	1605.3	1568.3	1555.9
37.5°	1659.7	1549.3	1434.1	1355.2	1306.1	1268.7	1254.8
40°	1473.3	1353.1	1252.6	1178.7	1128.1	1091.7	1091.1
42.5°	1303.1	1188.4	1093.9	1040.5	986.1	962.0	961.9
45°	1067.0	975.2	895.1	853.2	820.5	800.8	795.2
47.5°	883.5	807.5	754.1	720.8	694.1	681.5	673.4
50°	780.4	713.8	671.3	642.3	627.5	611.5	610.3
52.5°	694.6	640.9	607.7	584.2	565.4	555.8	556.1
55°	583.8	541.3	517.8	499.9	485.2	477.8	474.7
57.5°	491.8	459.9	442.8	426.4	420.2	414.4	412.8
60°	434.6	413.0	397.0	384.1	374.8	372.9	372.3
62.5°	387.3	364.7	353.6	343.6	336.8	333.9	332.9
65°	319.3	302.6	292.8	284.8	282.3	278.0	277.4
67.5°	257.4	247.4	240.9	235.3	232.0	231.8	231.8
70°	219.5	213.9	208.4	205.3	203.4	202.2	202.2
72.5°	186.9	182.8	178.3	176.6	176.3	175.0	174.6
75°	142.4	138.1	138.7	135.6	133.1	130.1	128.2
77.5°	100.9	97.9	97.3	96.9	94.8	94.4	95.4
80°	78.3	75.2	74.5	75.2	74.5	72.8	72.8
82.5°	59.6	57.0	56.4	56.0	55.4	56.0	55.0
85°	32.0	30.9	30.9	30.9	32.0	31.5	30.9
87.5°	12.6	12.1	12.6	12.2	12.2	11.7	12.2
90°	6.0	6.3	6.3	6.6	7.0	6.6	6.6
92.5°	46.5	37.1	30.8	27.0	25.3	24.3	24.3
95°	184.7	142.4	111.9	96.4	86.7	81.0	76.9
97.5°	326.9	296.0	263.1	240.5	221.6	212.1	205.5
100°	386.4	371.0	347.6	320.2	301.0	291.5	289.0
102.5°	409.6	414.0	404.3	387.5	373.6	363.6	361.6
105°	407.5	438.7	451.7	452.3	449.7	445.3	443.4
107.5°	375.1	418.9	447.1	462.6	469.8	473.0	473.8
110°	349.8	395.6	430.2	452.5	465.8	471.4	474.3



TEST NUMBER: P332957-940

CATALOG NUMBER: S124RDIP-S1020D365U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	327.6	370.8	405.5	430.9	446.9	454.9	459.4
115°	302.2	339.1	369.3	394.2	413.1	423.3	425.8
117.5°	287.8	316.7	342.4	363.6	379.5	389.7	391.6
120°	281.4	306.7	329.0	347.0	360.9	369.1	372.6
122.5°	277.4	300.3	319.9	335.1	347.0	353.9	357.4
125°	271.0	292.7	310.1	322.7	331.9	337.9	339.7
127.5°	263.5	285.3	301.7	314.3	322.4	327.5	329.4
130°	257.5	278.9	295.6	308.5	316.4	321.5	323.3
132.5°	250.7	271.6	288.3	301.0	309.9	314.7	316.6
135°	240.5	259.7	275.4	288.0	296.9	301.9	303.8
137.5°	230.7	246.9	261.1	273.0	281.6	285.8	288.0
140°	224.4	238.5	251.8	262.9	269.7	274.2	276.7
142.5°	219.1	231.2	242.7	252.5	259.0	262.9	264.6
145°	211.8	221.2	230.1	237.9	243.3	246.5	248.0
147.5°	205.5	213.0	220.0	225.8	230.4	232.7	233.4
150°	201.7	208.0	213.7	218.7	222.8	224.7	225.0
152.5°	198.0	203.8	208.4	212.7	216.0	217.1	217.5
155°	192.5	197.2	201.1	204.2	206.7	207.7	207.7
157.5°	187.3	191.3	194.3	196.6	198.6	199.1	199.1
160°	183.7	187.2	189.8	191.6	193.5	193.9	193.9
162.5°	180.5	183.2	185.5	186.8	188.7	189.0	188.8
165°	175.6	177.7	179.3	180.6	181.8	181.6	181.2
167.5°	171.4	173.2	174.1	174.7	175.6	175.5	175.2
170°	168.6	169.9	170.9	171.5	171.7	171.5	171.5
172.5°	166.3	167.1	167.8	168.2	168.4	168.2	167.6
175°	163.3	163.9	163.9	163.9	164.5	163.9	163.3
177.5°	161.4	161.4	161.7	161.4	161.7	161.1	160.7
180°	160.4	160.4	160.4	160.4	160.4	160.4	160.4

(END OF REPORT)