

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332714-930

Luminaire Tested: **S124DIP-S1195D1205U930-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332714-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIP-S1195D1205U930-4F0-1E-UDD-F4
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1205 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7679.1 lumens
Efficiency: N/A
Efficacy: 107.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 71.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332714-930
CATALOG NUMBER: S124DIP-S1195D1205U930-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P332714-930

CATALOG NUMBER: S124DIP-S1195D1205U930-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	86	86	86	72	72	72	60	60	60	54
1	99	94	90	87	91	88	84	81	75	73	70	64	62	60	53	52	51	46
2	90	82	76	71	83	77	71	67	66	62	58	56	53	50	47	45	43	38
3	82	72	65	59	76	67	61	56	58	53	49	49	46	43	41	39	36	32
4	75	64	56	50	69	60	53	47	52	46	42	44	40	36	37	34	31	28
5	69	57	49	43	64	53	46	41	46	40	36	40	35	32	33	30	27	24
6	63	51	43	37	59	48	41	35	42	36	31	36	31	28	30	27	24	21
7	59	46	38	33	54	43	36	31	38	32	28	33	28	25	28	24	21	19
8	55	42	34	29	50	39	32	27	34	29	25	30	25	22	25	22	19	17
9	51	38	31	26	47	36	29	25	32	26	22	27	23	20	23	20	17	15
10	47	35	28	23	44	33	27	22	29	24	20	25	21	18	22	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13116	13116	13116
5°	13156	12998	13092
10°	13073	12892	12956
15°	12915	12709	12741
20°	12706	12482	12493
25°	12466	12222	12188
30°	12172	11918	11808
35°	11869	11599	11445
40°	11552	11236	11031
45°	11222	10880	10671
50°	10857	10562	10236
55°	10463	10151	9821
60°	10069	9689	9397
65°	9626	9251	8879
70°	9128	8665	8327
75°	8366	7960	7757
80°	7443	7141	6960
85°	6512	6271	6150



TEST NUMBER: P332714-930

CATALOG NUMBER: S124DIP-S1195D1205U930-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	153.0	2.0
10°-20°	431.1	5.6
20°-30°	634.5	8.3
30°-40°	737.7	9.6
40°-50°	737.7	9.6
50°-60°	645.3	8.4
60°-70°	479.2	6.2
70°-80°	272.3	3.5
80°-90°	81.2	1.1
90°-100°	348.3	4.5
100°-110°	724.9	9.4
110°-120°	649.3	8.5
120°-130°	546.2	7.1
130°-140°	455.4	5.9
140°-150°	347.9	4.5
150°-160°	244.5	3.2
160°-170°	143.8	1.9
170°-180°	46.8	0.6
0°-30°	1218.6	15.9
0°-40°	1956.3	25.5
0°-60°	3339.3	43.5
0°-90°	4172.0	54.3
90°-120°	1722.5	22.4
90°-150°	3071.9	40.0
90°-180°	3507.0	45.7
0°-180°	7679.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1625	1625	1625	1625	1625	
5°	1623	1618	1604	1617	1616	154
15°	1545	1539	1521	1528	1524	435
25°	1400	1390	1372	1373	1368	644
35°	1204	1195	1177	1168	1161	753
45°	983	973	953	939	935	757
55°	743	739	721	706	698	666
65°	504	497	484	472	465	499
75°	268	262	255	250	249	285
85°	70	70	68	68	66	77
90°	1	8	17	19	20	5
95°	31	99	772	382	231	35
105°	111	161	622	1338	1333	118
115°	195	245	554	1065	1280	193
125°	272	323	551	906	1021	242
135°	323	385	547	804	913	250
145°	372	426	544	678	746	234
155°	424	457	529	599	624	195
165°	461	476	507	537	545	130
175°	481	482	486	493	491	46
180°	482	482	482	482	482	



TEST NUMBER: P332714-930

CATALOG NUMBER: S124DIP-S1195D1205U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1624.7	1624.7	1624.7	1624.7	1624.7	1624.7	1624.7	1624.7	1624.7	1624.7	1624.7
2.5°	1628.9	1628.2	1627.5	1626.8	1626.1	1624.5	1622.0	1619.4	1616.9	1614.4	1616.7
5°	1623.4	1622.3	1621.1	1620.0	1618.9	1616.7	1613.5	1610.3	1607.1	1603.9	1607.1
7.5°	1608.3	1607.2	1606.1	1604.8	1603.7	1601.4	1597.8	1594.3	1590.8	1587.2	1589.8
10°	1594.8	1593.7	1592.5	1591.3	1590.2	1587.7	1584.0	1580.2	1576.5	1572.7	1575.0
12.5°	1577.1	1576.0	1574.8	1573.6	1572.5	1569.9	1565.9	1562.0	1558.0	1554.0	1556.5
15°	1545.3	1544.2	1543.0	1541.9	1540.7	1538.0	1533.6	1529.3	1524.9	1520.6	1522.3
17.5°	1507.1	1505.6	1504.1	1502.8	1501.3	1498.5	1494.4	1490.3	1486.2	1482.1	1483.2
20°	1479.0	1477.5	1476.0	1474.6	1473.2	1470.2	1465.9	1461.6	1457.3	1452.9	1453.8
22.5°	1448.7	1446.8	1445.0	1443.0	1441.1	1437.9	1433.6	1429.3	1425.0	1420.6	1422.2
25°	1399.5	1397.5	1395.5	1393.4	1391.4	1388.4	1384.3	1380.3	1376.2	1372.1	1372.5
27.5°	1343.3	1341.2	1339.1	1337.0	1335.0	1332.0	1328.3	1324.5	1320.8	1317.0	1316.3
30°	1305.8	1303.5	1301.1	1298.9	1296.6	1293.5	1289.7	1286.0	1282.2	1278.5	1277.3
32.5°	1266.2	1264.1	1262.1	1260.0	1257.8	1254.8	1250.8	1246.8	1242.8	1238.8	1237.5
35°	1204.3	1202.2	1200.2	1198.2	1196.1	1193.1	1189.0	1185.0	1181.0	1176.9	1174.8
37.5°	1138.9	1137.0	1135.2	1133.3	1131.5	1128.4	1124.1	1119.7	1115.3	1111.0	1108.8
40°	1096.2	1093.9	1091.5	1089.2	1087.0	1083.6	1079.3	1074.9	1070.6	1066.2	1063.3
42.5°	1050.4	1049.0	1047.6	1046.2	1044.8	1041.7	1036.9	1032.1	1027.3	1022.5	1019.1
45°	982.9	980.9	978.8	976.8	974.9	971.5	966.9	962.2	957.6	953.0	949.8
47.5°	912.3	910.9	909.5	908.2	906.8	904.0	899.7	895.4	891.1	886.9	883.3
50°	864.5	863.3	862.1	861.0	859.8	857.2	853.1	849.1	845.1	841.0	837.0
52.5°	817.6	816.2	814.8	813.4	812.0	809.2	804.9	800.6	796.4	792.1	788.5
55°	743.4	742.5	741.7	740.8	739.9	737.4	733.4	729.4	725.3	721.2	717.8
57.5°	672.5	671.6	670.6	669.6	668.6	666.1	662.1	658.1	654.1	650.1	646.9
60°	623.6	622.2	620.7	619.3	617.8	615.2	611.5	607.7	603.9	600.1	597.5
62.5°	575.7	574.5	573.2	572.0	570.9	568.3	564.3	560.3	556.3	552.3	549.9
65°	503.9	502.4	500.9	499.5	498.1	495.9	493.0	490.1	487.2	484.3	481.4
67.5°	431.5	430.2	428.8	427.5	426.2	424.0	421.3	418.5	415.7	412.9	410.2
70°	386.7	384.7	382.6	380.6	378.5	376.4	374.1	371.8	369.4	367.1	364.8
72.5°	338.8	336.7	334.7	332.6	330.7	328.7	326.9	325.0	323.2	321.3	319.4
75°	268.2	266.8	265.3	263.8	262.4	261.0	259.5	258.0	256.7	255.2	254.0
77.5°	200.7	200.1	199.5	198.9	198.2	197.2	196.0	194.7	193.5	192.2	191.8
80°	160.1	159.2	158.4	157.5	156.7	156.0	155.4	154.7	154.2	153.6	153.0
82.5°	120.6	120.2	119.8	119.4	119.0	118.7	118.5	118.5	118.3	118.2	117.9
85°	70.3	70.3	70.3	70.3	70.3	70.0	69.5	68.9	68.2	67.7	67.7
87.5°	27.2	27.4	27.7	27.7	27.6	27.5	28.4	28.1	28.3	28.4	28.2
90°	1.0	2.9	5.7	6.6	7.6	7.6	13.3	13.3	15.2	17.0	16.1
92.5°	10.8	15.7	24.6	36.2	50.1	69.7	117.9	191.4	263.0	300.5	250.3
95°	31.2	34.1	43.6	55.9	78.6	118.5	200.8	356.2	582.6	772.1	793.9
97.5°	56.1	56.1	64.2	75.6	95.1	128.5	191.9	320.2	545.3	813.3	997.4
100°	72.0	72.0	78.6	90.0	108.0	138.4	194.2	301.3	494.6	761.7	1004.2
102.5°	87.2	88.7	94.6	105.2	122.4	151.2	201.8	296.0	460.4	697.2	947.4
105°	110.9	113.7	118.5	129.8	146.8	174.3	219.8	298.4	431.0	621.5	844.1
107.5°	137.0	138.8	143.7	155.7	172.0	199.2	240.8	312.4	425.7	579.0	760.8
110°	154.4	156.3	161.0	172.4	189.5	215.1	256.7	323.0	427.3	564.7	719.1



TEST NUMBER: P332714-930

CATALOG NUMBER: S124DIP-S1195D1205U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	171.1	173.0	178.5	189.1	206.2	231.7	271.9	334.4	431.8	557.8	695.5
115°	195.2	198.0	204.6	214.1	232.1	257.7	295.5	352.5	440.5	554.2	673.6
117.5°	220.1	222.8	228.7	239.1	256.0	282.5	318.5	370.8	449.8	553.3	663.7
120°	236.8	238.7	245.4	255.8	271.9	298.4	334.4	383.7	456.6	553.3	658.4
122.5°	252.0	253.9	260.6	270.2	287.8	313.6	349.6	395.8	463.5	552.5	652.4
125°	271.9	275.7	281.4	291.8	309.8	336.3	370.4	414.0	473.7	551.4	642.3
127.5°	289.5	292.5	299.4	311.3	330.0	356.8	389.7	429.7	481.8	549.3	628.8
130°	299.4	303.1	310.7	325.0	342.9	370.4	402.7	439.6	487.9	548.5	620.5
132.5°	309.2	312.3	322.1	335.6	355.1	381.1	413.3	449.5	493.2	547.8	612.9
135°	323.0	326.9	336.3	352.5	372.3	397.0	428.2	462.4	501.2	546.7	601.6
137.5°	336.9	340.5	350.9	366.2	386.9	410.4	439.6	471.4	505.9	546.4	591.7
140°	346.7	349.6	360.0	376.1	396.0	418.7	447.2	477.4	509.7	545.7	586.4
142.5°	357.3	360.2	369.8	385.2	404.3	426.3	454.0	482.0	512.7	545.7	581.9
145°	372.3	375.2	384.7	397.9	415.9	436.8	461.4	487.0	514.5	543.8	574.1
147.5°	389.1	390.1	398.4	412.1	427.1	445.8	469.0	491.3	515.4	540.4	567.1
150°	399.8	400.7	408.3	419.7	433.9	451.9	472.7	493.6	515.4	538.1	561.8
152.5°	409.6	409.9	417.4	428.0	440.8	457.2	475.8	495.1	513.9	534.3	555.7
155°	423.5	424.4	430.1	439.6	450.0	464.2	480.3	496.4	511.6	528.6	546.7
157.5°	436.9	436.9	442.2	449.6	458.7	469.9	483.6	496.4	509.2	522.8	537.4
160°	445.2	445.2	449.1	455.7	463.3	473.7	485.0	496.4	506.9	518.2	530.5
162.5°	452.8	452.1	455.1	461.0	467.8	476.0	486.6	496.4	504.6	513.6	524.5
165°	461.4	461.4	463.3	468.0	472.7	478.4	487.0	494.6	500.2	506.9	514.5
167.5°	469.9	469.0	469.9	473.5	476.1	480.5	486.7	492.3	495.7	500.0	505.3
170°	473.7	472.7	473.7	476.5	478.4	481.3	486.0	490.7	492.6	495.5	499.3
172.5°	477.4	476.5	476.7	478.8	480.0	482.0	485.3	489.3	489.6	490.9	494.0
175°	481.3	480.3	480.3	481.3	482.2	482.2	484.1	487.0	486.0	486.0	487.9
177.5°	483.0	482.2	481.4	482.2	482.2	482.2	483.0	484.5	483.0	483.0	483.7
180°	482.2	482.2	482.2	482.2	482.2	482.2	482.2	482.2	482.2	482.2	482.2



TEST NUMBER: P332714-930

CATALOG NUMBER: S124DIP-S1195D1205U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1624.7	1624.7	1624.7	1624.7	1624.7	1624.7	1624.7	1624.7
2.5°	1618.9	1621.3	1623.6	1624.6	1624.4	1624.2	1623.9	1623.7
5°	1610.3	1613.5	1616.7	1618.0	1617.4	1616.8	1616.2	1615.6
7.5°	1592.4	1594.9	1597.4	1598.6	1598.2	1597.8	1597.5	1597.2
10°	1577.3	1579.6	1581.9	1582.8	1582.3	1581.7	1581.0	1580.5
12.5°	1559.0	1561.5	1564.2	1565.0	1564.2	1563.3	1562.5	1561.7
15°	1524.0	1525.8	1527.5	1528.0	1527.1	1526.2	1525.3	1524.5
17.5°	1484.3	1485.4	1486.5	1486.7	1486.1	1485.6	1485.0	1484.4
20°	1454.7	1455.5	1456.4	1456.5	1456.0	1455.4	1454.8	1454.2
22.5°	1423.8	1425.3	1426.9	1427.1	1426.1	1425.1	1424.0	1422.9
25°	1372.8	1373.0	1373.4	1372.9	1371.7	1370.6	1369.5	1368.3
27.5°	1315.6	1314.9	1314.2	1313.1	1311.7	1310.3	1308.8	1307.3
30°	1276.1	1275.0	1273.8	1272.5	1271.1	1269.7	1268.2	1266.7
32.5°	1236.1	1234.7	1233.3	1231.9	1230.4	1229.0	1227.6	1226.1
35°	1172.9	1170.9	1168.8	1167.1	1165.6	1164.2	1162.7	1161.3
37.5°	1106.6	1104.4	1102.2	1100.2	1098.3	1096.3	1094.5	1092.5
40°	1060.5	1057.5	1054.7	1052.5	1051.1	1049.6	1048.1	1046.7
42.5°	1015.8	1012.4	1009.1	1006.9	1005.9	1004.9	1004.0	1003.0
45°	946.6	943.5	940.3	938.2	937.3	936.5	935.6	934.7
47.5°	879.7	876.1	872.5	869.6	867.4	865.2	863.0	860.8
50°	832.9	828.8	824.8	821.9	820.2	818.5	816.7	815.0
52.5°	784.9	781.3	777.7	774.9	772.7	770.5	768.3	766.1
55°	714.3	710.9	707.4	704.7	703.0	701.3	699.5	697.8
57.5°	643.6	640.3	637.0	634.5	632.8	631.1	629.4	627.8
60°	594.9	592.4	589.8	587.7	586.3	584.8	583.4	582.0
62.5°	547.5	545.1	542.7	540.9	539.4	537.9	536.5	535.1
65°	478.5	475.6	472.7	470.6	469.1	467.7	466.2	464.8
67.5°	407.4	404.6	401.9	400.2	399.8	399.4	399.0	398.6
70°	362.5	360.2	357.8	356.3	355.4	354.6	353.7	352.8
72.5°	317.6	315.8	313.9	312.5	311.7	310.8	309.9	309.1
75°	252.8	251.7	250.5	249.8	249.6	249.2	248.9	248.7
77.5°	191.4	191.1	190.8	190.2	189.5	188.7	187.9	187.2
80°	152.5	151.9	151.3	150.9	150.6	150.3	150.0	149.7
82.5°	117.5	117.2	116.8	116.5	116.2	115.9	115.6	115.4
85°	67.7	67.7	67.7	67.6	67.3	66.9	66.7	66.4
87.5°	28.4	28.6	28.8	28.8	28.9	29.2	28.9	28.9
90°	17.0	18.0	18.9	18.9	19.9	20.9	19.9	19.9
92.5°	186.1	140.0	111.5	92.5	81.3	76.1	73.0	73.0
95°	702.0	555.1	428.2	336.3	289.9	260.6	243.4	231.1
97.5°	1037.2	982.6	890.0	791.1	723.0	666.0	637.6	617.9
100°	1142.6	1161.5	1115.1	1045.0	962.5	904.7	876.4	868.8
102.5°	1137.3	1231.2	1244.6	1215.4	1164.9	1123.0	1093.1	1087.0
105°	1061.0	1225.0	1318.7	1357.6	1359.5	1351.9	1338.6	1332.9
107.5°	952.8	1127.4	1259.5	1343.9	1390.7	1412.3	1421.8	1424.3
110°	887.7	1051.6	1189.0	1293.1	1360.4	1400.2	1417.3	1425.8



TEST NUMBER: P332714-930

CATALOG NUMBER: S124DIP-S1195D1205U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	839.9	984.9	1114.7	1218.9	1295.3	1343.4	1367.3	1381.1
115°	792.0	908.6	1019.4	1110.4	1185.2	1242.0	1272.4	1279.9
117.5°	768.5	865.0	952.1	1029.2	1093.1	1140.8	1171.5	1177.4
120°	757.9	846.0	921.8	989.0	1043.1	1084.8	1109.4	1119.8
122.5°	748.8	833.9	902.9	961.8	1007.5	1043.1	1063.9	1074.3
125°	733.3	814.7	880.1	932.2	970.1	997.6	1015.6	1021.2
127.5°	714.3	792.2	857.4	906.9	944.9	969.4	984.6	990.2
130°	699.2	774.0	838.5	888.7	927.5	951.1	966.3	972.0
132.5°	683.2	753.6	816.4	866.7	904.7	931.5	945.8	951.5
135°	661.3	722.8	780.6	828.0	865.9	892.4	907.6	913.3
137.5°	641.4	693.5	742.2	785.0	820.4	846.6	859.1	865.9
140°	630.0	674.5	717.1	756.9	790.1	811.0	824.2	831.8
142.5°	619.4	658.6	695.2	729.7	759.0	778.4	790.1	795.4
145°	604.5	636.7	665.0	691.6	715.3	731.4	740.9	745.6
147.5°	592.2	617.7	640.4	661.3	678.7	692.5	699.8	701.4
150°	584.6	606.3	625.3	642.3	657.5	669.8	675.5	676.5
152.5°	576.2	594.9	612.4	626.4	639.3	649.3	652.7	653.7
155°	563.7	578.9	593.0	604.5	613.9	621.5	624.4	624.4
157.5°	550.2	563.0	574.9	584.0	591.2	596.9	598.6	598.6
160°	541.9	552.3	562.7	570.3	576.0	581.7	582.6	582.6
162.5°	533.5	542.5	550.7	557.4	561.6	567.3	568.3	567.4
165°	522.0	527.7	534.3	539.1	542.8	546.7	545.7	544.8
167.5°	510.9	515.2	520.5	523.3	525.2	527.7	527.5	526.8
170°	504.0	506.9	510.6	513.5	515.4	516.3	515.4	515.4
172.5°	497.9	500.0	502.3	504.3	505.5	506.5	505.5	504.0
175°	489.8	490.7	492.6	492.6	492.6	494.6	492.6	490.7
177.5°	484.5	485.3	485.3	486.0	485.3	486.0	484.5	483.0
180°	482.2	482.2	482.2	482.2	482.2	482.2	482.2	482.2

(END OF REPORT)