

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332959-940

Luminaire Tested: **S124RDIP-S1020D365U940-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332959-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIP-S1020D365U940-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 365 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4851.7 lumens
Efficiency: N/A
Efficacy: 111.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 43.5
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332959-940

CATALOG NUMBER: S124RDIP-S1020D365U940-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332959-940

CATALOG NUMBER: S124RDIP-S1020D365U940-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	114	114	114	114	108	108	108	108	98	98	98	89	89	89	81	81	81
1	104	100	96	92	99	95	92	89	87	84	82	79	77	75	72	70	69
2	95	88	81	76	91	84	78	74	77	72	68	70	67	63	64	61	59
3	87	78	70	64	83	74	67	62	68	63	58	62	58	54	57	53	50
4	80	69	61	55	76	66	59	53	61	55	50	56	51	47	51	47	44
5	74	62	53	47	70	59	52	46	55	48	43	50	45	41	46	42	38
6	68	56	47	41	65	54	46	40	50	43	38	46	40	36	42	38	34
7	63	51	42	37	60	49	41	36	45	39	34	42	36	32	39	34	30
8	59	46	38	33	56	45	37	32	41	35	30	38	33	29	36	31	27
9	55	42	35	29	52	41	34	29	38	32	27	35	30	26	33	28	25
10	52	39	32	27	49	38	31	26	35	29	25	33	28	24	31	26	23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12999	12999	12999
5°	13028	12869	12949
10°	12946	12714	12714
15°	12797	12447	12354
20°	12594	12095	11874
25°	12333	11685	11388
30°	12078	11251	10781
35°	11798	10801	10170
40°	11460	10290	9511
45°	11147	9782	8840
50°	10792	9198	8130
55°	10412	8590	7357
60°	9993	7923	6570
65°	9608	7089	5794
70°	9050	6170	4919
75°	8344	5115	3999
80°	7280	3896	3668
85°	6169	3548	3316



TEST NUMBER: P332959-940

CATALOG NUMBER: S124RDIP-S1020D365U940-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	151.3	3.1
10°-20°	421.8	8.7
20°-30°	609.1	12.6
30°-40°	690.4	14.2
40°-50°	666.7	13.7
50°-60°	554.4	11.4
60°-70°	382.8	7.9
70°-80°	194.0	4.0
80°-90°	51.0	1.1
90°-100°	26.9	0.6
100°-110°	79.6	1.6
110°-120°	135.1	2.8
120°-130°	178.2	3.7
130°-140°	200.1	4.1
140°-150°	196.6	4.1
150°-160°	165.4	3.4
160°-170°	110.0	2.3
170°-180°	38.5	0.8
0°-30°	1182.1	24.4
0°-40°	1872.5	38.6
0°-60°	3093.5	63.8
0°-90°	3721.3	76.7
90°-120°	241.6	5.0
90°-150°	816.5	16.8
90°-180°	1130.0	23.3
0°-180°	4851.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1610	1610	1610	1610	1610	
5°	1608	1602	1588	1599	1598	152
15°	1531	1519	1489	1486	1478	431
25°	1385	1361	1312	1291	1278	638
35°	1197	1156	1096	1055	1032	748
45°	976	929	857	799	774	753
55°	740	689	610	548	523	661
65°	503	449	371	320	303	497
75°	268	221	164	137	128	282
85°	67	43	38	36	36	75
90°	1	4	7	9	10	4
95°	19	22	24	25	25	21
105°	73	74	75	76	77	78
115°	137	137	137	136	136	135
125°	200	200	200	199	198	178
135°	258	260	260	259	258	200
145°	314	315	315	315	314	196
155°	359	359	359	360	359	165
165°	391	390	390	391	390	110
175°	407	405	405	407	405	39
180°	407	407	407	407	407	



TEST NUMBER: P332959-940

CATALOG NUMBER: S124RDIP-S1020D365U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1610.2	1610.2	1610.2	1610.2	1610.2	1610.2	1610.2	1610.2	1610.2	1610.2	1610.2
2.5°	1614.1	1613.2	1612.3	1611.5	1610.6	1608.9	1606.5	1604.1	1601.7	1599.3	1601.7
5°	1607.7	1606.6	1605.5	1604.4	1603.3	1601.1	1597.9	1594.6	1591.3	1588.0	1590.7
7.5°	1593.1	1592.0	1590.8	1589.7	1588.5	1585.8	1581.5	1577.3	1573.0	1568.7	1570.5
10°	1579.3	1578.0	1576.5	1575.2	1573.9	1570.7	1565.8	1560.9	1555.9	1551.0	1552.0
12.5°	1561.6	1560.0	1558.4	1556.8	1555.2	1551.5	1545.7	1539.9	1534.1	1528.3	1528.9
15°	1531.2	1528.7	1526.3	1523.8	1521.3	1516.7	1509.8	1503.0	1496.2	1489.3	1488.8
17.5°	1494.5	1490.9	1487.4	1483.8	1480.2	1474.4	1466.2	1457.9	1449.7	1441.5	1439.9
20°	1465.9	1462.3	1458.7	1455.2	1451.6	1445.2	1435.9	1426.6	1417.3	1407.9	1405.8
22.5°	1434.3	1430.3	1426.3	1422.4	1418.4	1411.3	1401.4	1391.4	1381.4	1371.5	1368.2
25°	1384.6	1379.6	1374.7	1369.8	1364.8	1356.7	1345.5	1334.3	1323.0	1311.8	1307.2
27.5°	1332.2	1326.1	1319.9	1313.7	1307.5	1298.4	1286.4	1274.4	1262.4	1250.4	1244.6
30°	1295.7	1288.9	1282.1	1275.2	1268.4	1258.5	1245.6	1232.7	1219.9	1207.0	1200.2
32.5°	1257.3	1249.6	1241.8	1234.1	1226.4	1215.8	1202.6	1189.3	1175.9	1162.6	1154.7
35°	1197.1	1188.4	1179.6	1170.8	1162.1	1150.8	1137.1	1123.5	1109.7	1096.0	1086.7
37.5°	1132.7	1123.7	1114.7	1105.6	1096.6	1084.5	1069.3	1054.2	1038.9	1023.8	1013.3
40°	1087.4	1078.3	1069.3	1060.2	1051.2	1038.9	1023.3	1007.6	992.0	976.4	964.9
42.5°	1044.0	1034.6	1025.0	1015.6	1006.1	993.2	977.0	960.6	944.4	928.1	916.4
45°	976.4	966.3	956.2	946.0	935.9	922.6	906.2	889.7	873.3	856.8	843.5
47.5°	906.7	896.2	885.7	875.3	864.8	851.0	833.9	816.8	799.7	782.7	768.7
50°	859.3	848.6	837.9	827.2	816.5	802.5	785.0	767.4	749.8	732.4	718.6
52.5°	811.0	800.5	790.1	779.6	769.1	754.9	736.9	719.0	701.0	683.1	669.1
55°	739.8	728.8	717.8	706.9	695.9	681.5	663.7	645.9	628.1	610.3	596.0
57.5°	669.2	657.8	646.4	635.0	623.7	609.1	591.7	574.1	556.5	539.0	524.6
60°	618.9	608.0	597.0	586.0	575.1	560.8	543.3	525.8	508.2	490.7	476.4
62.5°	573.5	562.1	550.7	539.3	528.0	513.3	495.3	477.3	459.3	441.4	428.2
65°	503.0	491.2	479.5	467.7	455.9	441.2	423.7	406.2	388.6	371.1	359.4
67.5°	429.8	418.5	407.2	395.9	384.6	370.9	354.5	338.3	322.0	305.8	295.6
70°	383.4	371.9	360.4	348.9	337.4	323.9	308.3	292.6	277.0	261.4	252.4
72.5°	334.1	323.7	313.3	302.9	292.5	279.9	265.2	250.4	235.7	221.0	213.2
75°	267.5	257.4	247.3	237.1	227.0	215.4	202.6	189.8	176.8	164.0	157.7
77.5°	200.0	191.4	182.8	174.2	165.6	156.0	145.6	135.3	124.8	114.4	110.8
80°	156.6	148.6	140.7	132.8	124.8	116.7	108.5	100.3	92.0	83.8	83.0
82.5°	119.1	111.8	104.5	97.2	90.0	83.9	79.3	74.5	69.8	65.1	64.5
85°	66.6	61.1	55.6	50.1	44.7	41.5	40.7	39.9	39.1	38.3	37.6
87.5°	22.9	21.3	19.7	18.1	16.5	15.6	15.5	15.4	15.3	15.2	15.1
90°	1.0	1.7	2.5	3.3	4.0	4.7	5.3	5.8	6.3	7.0	7.3
92.5°	6.8	7.7	8.5	9.4	10.3	10.9	11.3	11.7	12.1	12.5	12.8
95°	18.9	19.5	20.2	20.8	21.4	22.0	22.5	23.0	23.5	24.0	24.2
97.5°	33.0	33.5	34.1	34.5	35.0	35.6	36.1	36.7	37.3	37.9	38.2
100°	44.1	44.4	44.7	44.9	45.2	45.7	46.3	47.0	47.6	48.2	48.3
102.5°	55.7	55.8	55.9	56.1	56.2	56.5	57.1	57.7	58.2	58.8	59.0
105°	73.4	73.5	73.6	73.7	73.7	73.8	74.2	74.5	74.7	75.0	75.2
107.5°	92.0	92.1	92.2	92.3	92.4	92.4	92.5	92.5	92.6	92.6	92.7
110°	104.6	104.8	104.9	105.0	105.1	105.2	105.1	105.0	105.0	105.0	104.8



TEST NUMBER: P332959-940

CATALOG NUMBER: S124RDIP-S1020D365U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	117.7	117.7	117.8	117.8	117.8	117.8	117.6	117.5	117.4	117.3	117.3
115°	137.4	137.4	137.4	137.4	137.4	137.3	137.1	137.1	136.9	136.8	136.7
117.5°	155.9	156.0	156.0	156.0	156.1	156.1	156.0	156.0	155.8	155.7	155.5
120°	168.3	168.5	168.8	169.1	169.4	169.4	169.2	169.0	168.8	168.6	168.3
122.5°	181.1	181.2	181.4	181.5	181.6	181.6	181.5	181.4	181.3	181.2	180.9
125°	200.1	200.1	200.1	200.1	200.1	200.0	200.0	199.9	199.8	199.7	199.7
127.5°	217.3	217.5	217.8	217.9	218.1	218.2	218.1	217.9	217.8	217.8	217.6
130°	229.4	229.6	229.8	230.1	230.2	230.3	230.3	230.3	230.3	230.3	230.2
132.5°	241.7	241.9	242.0	242.2	242.4	242.4	242.4	242.3	242.3	242.2	242.0
135°	258.1	258.5	258.9	259.3	259.8	259.9	259.9	259.9	259.9	259.9	259.8
137.5°	275.8	276.1	276.3	276.4	276.6	276.8	276.9	277.0	277.1	277.2	277.1
140°	287.7	287.8	287.9	288.1	288.3	288.3	288.3	288.3	288.3	288.3	288.3
142.5°	298.5	298.6	298.8	298.9	299.1	299.2	299.1	299.0	299.0	298.9	298.9
145°	313.5	313.8	314.1	314.3	314.7	314.9	314.9	315.0	315.0	315.1	315.0
147.5°	328.4	328.8	329.0	329.4	329.8	329.8	329.8	329.8	329.8	329.7	329.6
150°	337.5	337.8	338.0	338.3	338.6	338.8	338.8	338.8	338.8	338.8	338.8
152.5°	346.1	346.3	346.3	346.5	346.7	346.8	346.9	347.0	347.0	347.1	347.2
155°	359.2	359.2	359.2	359.2	359.2	359.2	359.1	359.0	359.0	358.9	359.2
157.5°	370.3	370.1	370.1	370.0	369.8	369.7	369.7	369.7	369.7	369.7	369.9
160°	376.8	376.7	376.7	376.7	376.6	376.5	376.5	376.4	376.3	376.2	376.5
162.5°	382.9	382.7	382.5	382.4	382.2	382.1	382.0	381.9	381.8	381.7	382.2
165°	391.0	390.8	390.7	390.4	390.2	390.0	389.9	389.8	389.6	389.5	389.9
167.5°	397.3	397.0	396.7	396.4	396.1	395.9	396.0	396.0	396.0	396.0	396.5
170°	400.8	400.5	400.1	399.8	399.4	399.3	399.3	399.4	399.5	399.6	399.9
172.5°	403.3	403.1	402.7	402.4	402.2	402.0	402.0	402.1	402.1	402.1	402.5
175°	406.8	406.4	406.1	405.7	405.4	405.2	405.1	405.0	405.0	404.9	405.4
177.5°	408.0	407.7	407.3	407.1	406.8	406.7	406.7	406.7	406.7	406.7	407.1
180°	407.4	407.4	407.4	407.4	407.4	407.4	407.4	407.4	407.4	407.4	407.4



TEST NUMBER: P332959-940

CATALOG NUMBER: S124RDIP-S1020D365U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1610.2	1610.2	1610.2	1610.2	1610.2	1610.2	1610.2	1610.2
2.5°	1604.1	1606.5	1608.9	1610.1	1609.8	1609.6	1609.4	1609.2
5°	1593.4	1596.2	1598.9	1600.0	1599.5	1598.9	1598.4	1597.9
7.5°	1572.3	1574.0	1575.7	1576.2	1575.3	1574.4	1573.5	1572.6
10°	1553.2	1554.3	1555.3	1555.3	1554.3	1553.2	1552.0	1551.0
12.5°	1529.6	1530.3	1530.9	1530.4	1528.9	1527.4	1525.9	1524.4
15°	1488.3	1487.6	1487.1	1485.9	1484.0	1482.0	1480.2	1478.2
17.5°	1438.4	1436.9	1435.4	1433.2	1430.2	1427.4	1424.4	1421.5
20°	1403.6	1401.4	1399.2	1396.3	1392.8	1389.2	1385.6	1382.1
22.5°	1364.9	1361.6	1358.3	1355.2	1352.3	1349.4	1346.5	1343.6
25°	1302.4	1297.8	1293.2	1289.4	1286.7	1284.0	1281.2	1278.5
27.5°	1238.9	1233.1	1227.4	1222.5	1218.6	1214.6	1210.7	1206.8
30°	1193.3	1186.4	1179.6	1173.9	1169.6	1165.2	1160.8	1156.5
32.5°	1146.7	1138.8	1130.9	1124.8	1120.6	1116.4	1112.3	1108.1
35°	1077.4	1068.1	1058.7	1051.7	1046.7	1041.8	1036.9	1031.9
37.5°	1003.0	992.6	982.1	974.5	969.6	964.6	959.7	954.8
40°	953.4	941.9	930.4	922.2	917.3	912.3	907.4	902.5
42.5°	904.6	893.0	881.2	872.8	867.6	862.5	857.3	852.2
45°	830.0	816.5	803.2	794.0	789.1	784.1	779.2	774.3
47.5°	754.8	740.9	726.9	717.3	711.9	706.4	701.0	695.6
50°	704.9	691.3	677.5	668.1	662.9	657.6	652.5	647.3
52.5°	655.1	641.2	627.3	617.7	612.2	606.8	601.4	596.0
55°	581.8	567.6	553.3	543.6	538.3	533.2	528.0	522.7
57.5°	510.1	495.6	481.2	472.0	468.0	464.0	460.1	456.2
60°	462.2	447.9	433.7	424.4	420.0	415.6	411.3	406.9
62.5°	415.1	401.9	388.8	380.4	376.9	373.4	369.9	366.4
65°	347.5	335.7	324.0	316.5	313.2	309.9	306.6	303.3
67.5°	285.4	275.4	265.2	258.3	254.7	251.1	247.4	243.9
70°	243.3	234.3	225.2	219.3	216.6	213.8	211.1	208.4
72.5°	205.5	197.8	190.0	184.9	182.4	179.9	177.4	174.9
75°	151.4	145.1	138.8	134.8	133.1	131.5	129.8	128.2
77.5°	107.1	103.4	99.7	97.6	97.1	96.7	96.1	95.7
80°	82.2	81.4	80.5	80.0	79.7	79.5	79.2	78.9
82.5°	63.8	63.3	62.7	62.2	62.0	61.7	61.4	61.2
85°	37.1	36.6	36.0	35.8	35.8	35.8	35.8	35.8
87.5°	14.9	14.8	14.6	14.7	15.0	15.2	15.4	15.7
90°	7.8	8.2	8.6	8.9	9.0	9.2	9.3	9.5
92.5°	13.0	13.2	13.5	13.6	13.7	13.8	13.9	14.0
95°	24.3	24.6	24.8	24.9	24.9	24.9	24.9	24.9
97.5°	38.3	38.6	38.9	39.0	39.0	39.0	39.0	39.0
100°	48.5	48.6	48.8	48.9	48.9	48.9	48.9	48.9
102.5°	59.2	59.4	59.6	59.7	59.7	59.8	59.8	59.9
105°	75.4	75.6	75.8	76.1	76.2	76.5	76.7	76.9
107.5°	93.0	93.2	93.4	93.5	93.5	93.5	93.5	93.4
110°	104.7	104.5	104.3	104.4	104.6	104.9	105.0	105.2



TEST NUMBER: P332959-940

CATALOG NUMBER: S124RDIP-S1020D365U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	117.3	117.2	117.2	117.2	117.3	117.3	117.3	117.3
115°	136.6	136.5	136.4	136.4	136.3	136.3	136.2	136.2
117.5°	155.2	155.0	154.8	154.6	154.4	154.3	154.2	154.0
120°	167.9	167.6	167.2	167.1	167.2	167.4	167.5	167.6
122.5°	180.7	180.5	180.2	179.9	179.8	179.5	179.2	179.0
125°	199.5	199.4	199.2	199.0	198.9	198.8	198.7	198.5
127.5°	217.5	217.3	217.1	217.0	217.0	216.9	216.7	216.6
130°	230.1	229.9	229.8	229.5	229.3	229.0	228.7	228.5
132.5°	241.9	241.7	241.7	241.5	241.4	241.3	241.2	241.0
135°	259.7	259.6	259.4	259.2	259.0	258.8	258.6	258.4
137.5°	276.9	276.7	276.5	276.4	276.4	276.5	276.5	276.6
140°	288.2	288.1	288.0	287.9	287.9	287.8	287.8	287.7
142.5°	298.9	298.9	298.8	298.8	298.8	298.8	298.8	298.8
145°	315.0	314.9	314.9	314.7	314.5	314.2	314.1	313.9
147.5°	329.6	329.5	329.4	329.4	329.3	329.2	329.1	329.1
150°	338.8	338.8	338.8	338.7	338.7	338.6	338.5	338.4
152.5°	347.4	347.6	347.8	347.7	347.5	347.3	347.1	347.0
155°	359.4	359.7	360.0	360.0	359.7	359.4	359.2	358.9
157.5°	370.1	370.3	370.5	370.5	370.2	370.1	369.8	369.5
160°	376.7	376.8	377.1	377.0	376.7	376.3	375.9	375.6
162.5°	382.5	382.9	383.3	383.3	383.0	382.6	382.3	381.9
165°	390.3	390.7	391.1	391.2	390.9	390.7	390.4	390.1
167.5°	396.9	397.3	397.7	397.7	397.3	396.8	396.4	395.9
170°	400.4	400.8	401.3	401.2	400.7	400.2	399.8	399.2
172.5°	403.1	403.5	403.9	403.9	403.5	403.0	402.5	402.0
175°	405.9	406.4	406.9	406.9	406.4	405.9	405.4	404.9
177.5°	407.4	407.9	408.2	408.2	407.8	407.3	406.9	406.4
180°	407.4	407.4	407.4	407.4	407.4	407.4	407.4	407.4

(END OF REPORT)