

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332965-940

Luminaire Tested: **S124RDIP-S1020D590U940-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332965-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIP-S1020D590U940-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 590 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5546.6 lumens
Efficiency: N/A
Efficacy: 113.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 48.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332965-940

CATALOG NUMBER: S124RDIP-S1020D590U940-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332965-940

CATALOG NUMBER: S124RDIP-S1020D590U940-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	72	72	72	67
1	102	98	94	90	96	92	89	86	82	80	77	73	71	69	64	63	61	57
2	93	86	80	74	88	81	76	71	72	68	64	64	61	58	57	54	52	49
3	85	76	68	62	80	72	65	60	64	59	55	57	53	50	51	48	45	41
4	78	67	59	53	73	64	57	51	57	51	47	51	47	43	45	42	39	36
5	72	60	52	46	68	57	50	44	51	45	41	46	41	37	41	37	34	31
6	66	54	46	40	63	52	44	39	47	40	36	42	37	33	37	33	30	28
7	62	49	41	35	58	47	39	34	42	36	32	38	33	29	34	30	27	25
8	57	45	37	32	54	43	36	31	39	33	28	35	30	26	32	27	24	22
9	53	41	33	28	50	39	32	27	36	30	26	32	27	24	29	25	22	20
10	50	38	30	26	47	36	29	25	33	27	23	30	25	22	27	23	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12999	12999	12999
5°	13028	12869	12949
10°	12946	12714	12714
15°	12797	12447	12354
20°	12594	12095	11874
25°	12333	11685	11388
30°	12078	11251	10781
35°	11798	10801	10170
40°	11460	10290	9511
45°	11147	9782	8840
50°	10792	9198	8130
55°	10412	8590	7357
60°	9993	7923	6570
65°	9608	7089	5794
70°	9050	6170	4919
75°	8344	5115	3999
80°	7280	3896	3668
85°	6169	3548	3316



TEST NUMBER: P332965-940

CATALOG NUMBER: S124RDIP-S1020D590U940-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	151.3	2.7
10°-20°	421.8	7.6
20°-30°	609.1	11.0
30°-40°	690.4	12.4
40°-50°	666.7	12.0
50°-60°	554.4	10.0
60°-70°	382.8	6.9
70°-80°	194.0	3.5
80°-90°	51.8	0.9
90°-100°	43.4	0.8
100°-110°	128.5	2.3
110°-120°	218.1	3.9
120°-130°	287.6	5.2
130°-140°	322.9	5.8
140°-150°	317.3	5.7
150°-160°	266.9	4.8
160°-170°	177.6	3.2
170°-180°	62.2	1.1
0°-30°	1182.1	21.3
0°-40°	1872.5	33.8
0°-60°	3093.5	55.8
0°-90°	3722.1	67.1
90°-120°	389.9	7.0
90°-150°	1317.8	23.8
90°-180°	1824.0	32.9
0°-180°	5546.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1610	1610	1610	1610	1610	
5°	1608	1602	1588	1599	1598	152
15°	1531	1519	1489	1486	1478	431
25°	1385	1361	1312	1291	1278	638
35°	1197	1156	1096	1055	1032	748
45°	976	929	857	799	774	753
55°	740	689	610	548	523	661
65°	503	449	371	320	303	497
75°	268	221	164	137	128	282
85°	67	43	38	36	36	75
90°	2	7	11	14	15	5
95°	30	35	39	40	40	34
105°	118	119	121	123	124	126
115°	222	222	221	220	220	219
125°	323	323	322	321	320	288
135°	416	419	420	419	417	322
145°	506	508	508	508	507	317
155°	580	580	579	581	579	267
165°	631	630	629	631	630	178
175°	657	654	654	657	654	62
180°	658	658	658	658	658	



TEST NUMBER: P332965-940

CATALOG NUMBER: S124RDIP-S1020D590U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1610.2	1610.2	1610.2	1610.2	1610.2	1610.2	1610.2	1610.2	1610.2	1610.2	1610.2
2.5°	1614.1	1613.2	1612.3	1611.5	1610.6	1608.9	1606.5	1604.1	1601.7	1599.3	1601.7
5°	1607.7	1606.6	1605.5	1604.4	1603.3	1601.1	1597.9	1594.6	1591.3	1588.0	1590.7
7.5°	1593.1	1592.0	1590.8	1589.7	1588.5	1585.8	1581.5	1577.3	1573.0	1568.7	1570.5
10°	1579.3	1578.0	1576.5	1575.2	1573.9	1570.7	1565.8	1560.9	1555.9	1551.0	1552.0
12.5°	1561.6	1560.0	1558.4	1556.8	1555.2	1551.5	1545.7	1539.9	1534.1	1528.3	1528.9
15°	1531.2	1528.7	1526.3	1523.8	1521.3	1516.7	1509.8	1503.0	1496.2	1489.3	1488.8
17.5°	1494.5	1490.9	1487.4	1483.8	1480.2	1474.4	1466.2	1457.9	1449.7	1441.5	1439.9
20°	1465.9	1462.3	1458.7	1455.2	1451.6	1445.2	1435.9	1426.6	1417.3	1407.9	1405.8
22.5°	1434.3	1430.3	1426.3	1422.4	1418.4	1411.3	1401.4	1391.4	1381.4	1371.5	1368.2
25°	1384.6	1379.6	1374.7	1369.8	1364.8	1356.7	1345.5	1334.3	1323.0	1311.8	1307.2
27.5°	1332.2	1326.1	1319.9	1313.7	1307.5	1298.4	1286.4	1274.4	1262.4	1250.4	1244.6
30°	1295.7	1288.9	1282.1	1275.2	1268.4	1258.5	1245.6	1232.7	1219.9	1207.0	1200.2
32.5°	1257.3	1249.6	1241.8	1234.1	1226.4	1215.8	1202.6	1189.3	1175.9	1162.6	1154.7
35°	1197.1	1188.4	1179.6	1170.8	1162.1	1150.8	1137.1	1123.5	1109.7	1096.0	1086.7
37.5°	1132.7	1123.7	1114.7	1105.6	1096.6	1084.5	1069.3	1054.2	1038.9	1023.8	1013.3
40°	1087.4	1078.3	1069.3	1060.2	1051.2	1038.9	1023.3	1007.6	992.0	976.4	964.9
42.5°	1044.0	1034.6	1025.0	1015.6	1006.1	993.2	977.0	960.6	944.4	928.1	916.4
45°	976.4	966.3	956.2	946.0	935.9	922.6	906.2	889.7	873.3	856.8	843.5
47.5°	906.7	896.2	885.7	875.3	864.8	851.0	833.9	816.8	799.7	782.7	768.7
50°	859.3	848.6	837.9	827.2	816.5	802.5	785.0	767.4	749.8	732.4	718.6
52.5°	811.0	800.5	790.1	779.6	769.1	754.9	736.9	719.0	701.0	683.1	669.1
55°	739.8	728.8	717.8	706.9	695.9	681.5	663.7	645.9	628.1	610.3	596.0
57.5°	669.2	657.8	646.4	635.0	623.7	609.1	591.7	574.1	556.5	539.0	524.6
60°	618.9	608.0	597.0	586.0	575.1	560.8	543.3	525.8	508.2	490.7	476.4
62.5°	573.5	562.1	550.7	539.3	528.0	513.3	495.3	477.3	459.3	441.4	428.2
65°	503.0	491.2	479.5	467.7	455.9	441.2	423.7	406.2	388.6	371.1	359.4
67.5°	429.8	418.5	407.2	395.9	384.6	370.9	354.5	338.3	322.0	305.8	295.6
70°	383.4	371.9	360.4	348.9	337.4	323.9	308.3	292.6	277.0	261.4	252.4
72.5°	334.1	323.7	313.3	302.9	292.5	279.9	265.2	250.4	235.7	221.0	213.2
75°	267.5	257.4	247.3	237.1	227.0	215.4	202.6	189.8	176.8	164.0	157.7
77.5°	200.0	191.4	182.8	174.2	165.6	156.0	145.6	135.3	124.8	114.4	110.8
80°	156.6	148.6	140.7	132.8	124.8	116.7	108.5	100.3	92.0	83.8	83.0
82.5°	119.1	111.8	104.5	97.2	90.0	83.9	79.3	74.5	69.8	65.1	64.5
85°	66.6	61.1	55.6	50.1	44.7	41.5	40.7	39.9	39.1	38.3	37.6
87.5°	23.0	21.5	20.0	18.5	16.9	16.2	16.1	16.1	16.1	16.1	16.0
90°	1.5	2.8	4.0	5.3	6.5	7.6	8.5	9.4	10.3	11.1	11.9
92.5°	10.9	12.3	13.7	15.2	16.6	17.6	18.3	18.9	19.5	20.2	20.5
95°	30.5	31.6	32.5	33.5	34.6	35.5	36.3	37.1	37.9	38.6	39.0
97.5°	53.3	54.1	54.9	55.7	56.5	57.4	58.3	59.3	60.2	61.2	61.5
100°	71.2	71.7	72.1	72.6	73.0	73.7	74.7	75.8	76.8	77.8	78.0
102.5°	89.9	90.1	90.2	90.4	90.6	91.2	92.1	93.0	94.0	94.9	95.2
105°	118.5	118.6	118.7	118.9	119.0	119.2	119.7	120.1	120.6	121.0	121.4
107.5°	148.5	148.6	148.7	148.9	149.1	149.2	149.2	149.3	149.4	149.5	149.7
110°	168.9	169.1	169.3	169.5	169.8	169.8	169.7	169.6	169.5	169.3	169.2



TEST NUMBER: P332965-940

CATALOG NUMBER: S124RDIP-S1020D590U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	190.0	190.0	190.1	190.1	190.2	190.1	189.9	189.7	189.5	189.3	189.2
115°	221.8	221.8	221.8	221.8	221.8	221.6	221.4	221.1	221.0	220.7	220.6
117.5°	251.6	251.7	251.8	251.9	252.0	252.0	251.8	251.6	251.5	251.4	250.9
120°	271.6	272.1	272.5	273.0	273.4	273.5	273.1	272.8	272.4	272.1	271.5
122.5°	292.3	292.5	292.7	292.8	293.0	293.1	292.9	292.7	292.6	292.5	292.0
125°	323.0	323.0	323.0	323.0	323.0	322.9	322.8	322.7	322.5	322.4	322.2
127.5°	350.7	351.1	351.4	351.8	352.0	352.1	352.0	351.8	351.6	351.4	351.2
130°	370.2	370.6	371.0	371.3	371.6	371.8	371.8	371.8	371.8	371.8	371.6
132.5°	390.2	390.5	390.7	390.9	391.2	391.3	391.2	391.1	391.0	390.9	390.7
135°	416.5	417.2	417.9	418.6	419.3	419.5	419.5	419.5	419.5	419.5	419.4
137.5°	445.2	445.5	445.9	446.1	446.5	446.7	446.9	447.1	447.3	447.5	447.2
140°	464.3	464.6	464.8	465.0	465.2	465.4	465.4	465.4	465.4	465.4	465.2
142.5°	481.8	482.1	482.3	482.5	482.8	482.8	482.7	482.6	482.5	482.4	482.4
145°	506.0	506.5	506.9	507.4	507.8	508.1	508.3	508.4	508.5	508.5	508.5
147.5°	530.0	530.6	531.1	531.6	532.3	532.4	532.4	532.3	532.2	532.1	532.0
150°	544.7	545.2	545.6	546.1	546.5	546.7	546.7	546.7	546.7	546.7	546.7
152.5°	558.6	558.8	559.1	559.4	559.6	559.8	559.9	560.0	560.1	560.2	560.4
155°	579.8	579.8	579.8	579.8	579.8	579.7	579.6	579.5	579.4	579.3	579.7
157.5°	597.7	597.4	597.3	597.1	596.9	596.7	596.7	596.7	596.7	596.6	597.0
160°	608.2	608.1	608.1	608.0	607.8	607.7	607.6	607.5	607.3	607.3	607.6
162.5°	618.0	617.8	617.4	617.2	616.9	616.6	616.5	616.4	616.4	616.2	616.8
165°	631.2	630.8	630.4	630.2	629.8	629.5	629.3	629.1	628.8	628.7	629.3
167.5°	641.2	640.8	640.2	639.8	639.4	639.1	639.1	639.2	639.2	639.2	639.9
170°	646.9	646.4	645.8	645.2	644.6	644.4	644.5	644.6	644.8	644.9	645.6
172.5°	650.9	650.5	650.1	649.6	649.1	648.9	648.9	648.9	648.9	649.0	649.7
175°	656.6	656.0	655.5	654.9	654.3	654.0	653.9	653.8	653.6	653.5	654.3
177.5°	658.4	658.0	657.5	657.1	656.6	656.4	656.4	656.4	656.4	656.4	657.0
180°	657.6	657.6	657.6	657.6	657.6	657.6	657.6	657.6	657.6	657.6	657.6



TEST NUMBER: P332965-940

CATALOG NUMBER: S124RDIP-S1020D590U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1610.2	1610.2	1610.2	1610.2	1610.2	1610.2	1610.2	1610.2
2.5°	1604.1	1606.5	1608.9	1610.1	1609.8	1609.6	1609.4	1609.2
5°	1593.4	1596.2	1598.9	1600.0	1599.5	1598.9	1598.4	1597.9
7.5°	1572.3	1574.0	1575.7	1576.2	1575.3	1574.4	1573.5	1572.6
10°	1553.2	1554.3	1555.3	1555.3	1554.3	1553.2	1552.0	1551.0
12.5°	1529.6	1530.3	1530.9	1530.4	1528.9	1527.4	1525.9	1524.4
15°	1488.3	1487.6	1487.1	1485.9	1484.0	1482.0	1480.2	1478.2
17.5°	1438.4	1436.9	1435.4	1433.2	1430.2	1427.4	1424.4	1421.5
20°	1403.6	1401.4	1399.2	1396.3	1392.8	1389.2	1385.6	1382.1
22.5°	1364.9	1361.6	1358.3	1355.2	1352.3	1349.4	1346.5	1343.6
25°	1302.4	1297.8	1293.2	1289.4	1286.7	1284.0	1281.2	1278.5
27.5°	1238.9	1233.1	1227.4	1222.5	1218.6	1214.6	1210.7	1206.8
30°	1193.3	1186.4	1179.6	1173.9	1169.6	1165.2	1160.8	1156.5
32.5°	1146.7	1138.8	1130.9	1124.8	1120.6	1116.4	1112.3	1108.1
35°	1077.4	1068.1	1058.7	1051.7	1046.7	1041.8	1036.9	1031.9
37.5°	1003.0	992.6	982.1	974.5	969.6	964.6	959.7	954.8
40°	953.4	941.9	930.4	922.2	917.3	912.3	907.4	902.5
42.5°	904.6	893.0	881.2	872.8	867.6	862.5	857.3	852.2
45°	830.0	816.5	803.2	794.0	789.1	784.1	779.2	774.3
47.5°	754.8	740.9	726.9	717.3	711.9	706.4	701.0	695.6
50°	704.9	691.3	677.5	668.1	662.9	657.6	652.5	647.3
52.5°	655.1	641.2	627.3	617.7	612.2	606.8	601.4	596.0
55°	581.8	567.6	553.3	543.6	538.3	533.2	528.0	522.7
57.5°	510.1	495.6	481.2	472.0	468.0	464.0	460.1	456.2
60°	462.2	447.9	433.7	424.4	420.0	415.6	411.3	406.9
62.5°	415.1	401.9	388.8	380.4	376.9	373.4	369.9	366.4
65°	347.5	335.7	324.0	316.5	313.2	309.9	306.6	303.3
67.5°	285.4	275.4	265.2	258.3	254.7	251.1	247.4	243.9
70°	243.3	234.3	225.2	219.3	216.6	213.8	211.1	208.4
72.5°	205.5	197.8	190.0	184.9	182.4	179.9	177.4	174.9
75°	151.4	145.1	138.8	134.8	133.1	131.5	129.8	128.2
77.5°	107.1	103.4	99.7	97.6	97.1	96.7	96.1	95.7
80°	82.2	81.4	80.5	80.0	79.7	79.5	79.2	78.9
82.5°	63.8	63.3	62.7	62.2	62.0	61.7	61.4	61.2
85°	37.1	36.6	36.0	35.8	35.8	35.8	35.8	35.8
87.5°	15.9	15.8	15.7	15.8	16.1	16.3	16.6	16.9
90°	12.6	13.2	13.9	14.4	14.6	14.8	15.1	15.2
92.5°	21.0	21.4	21.8	22.0	22.2	22.3	22.5	22.6
95°	39.3	39.7	40.0	40.2	40.2	40.2	40.2	40.2
97.5°	62.0	62.3	62.8	63.0	63.0	63.0	63.0	63.0
100°	78.3	78.5	78.7	78.8	78.8	78.8	78.8	78.8
102.5°	95.5	95.9	96.1	96.4	96.5	96.6	96.7	96.8
105°	121.7	122.1	122.4	122.7	123.1	123.4	123.8	124.1
107.5°	150.1	150.3	150.7	150.9	150.8	150.8	150.8	150.8
110°	168.9	168.7	168.4	168.5	168.9	169.2	169.5	169.9



TEST NUMBER: P332965-940

CATALOG NUMBER: S124RDIP-S1020D590U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	189.2	189.1	189.1	189.1	189.2	189.2	189.3	189.4
115°	220.5	220.4	220.3	220.2	220.1	219.9	219.8	219.7
117.5°	250.6	250.2	249.8	249.5	249.2	249.1	248.8	248.6
120°	271.0	270.4	269.8	269.7	269.9	270.1	270.4	270.5
122.5°	291.7	291.3	290.9	290.5	290.1	289.7	289.3	288.9
125°	322.0	321.7	321.6	321.3	321.1	320.8	320.7	320.4
127.5°	351.0	350.8	350.5	350.4	350.2	350.0	349.8	349.6
130°	371.3	371.1	370.9	370.5	370.1	369.6	369.2	368.7
132.5°	390.5	390.2	390.0	389.8	389.6	389.4	389.2	389.1
135°	419.1	418.9	418.7	418.4	418.0	417.7	417.4	417.1
137.5°	446.8	446.6	446.3	446.1	446.2	446.3	446.4	446.5
140°	465.1	465.0	464.9	464.8	464.7	464.6	464.5	464.3
142.5°	482.4	482.4	482.3	482.3	482.3	482.3	482.2	482.2
145°	508.4	508.3	508.1	507.9	507.6	507.2	506.8	506.6
147.5°	531.9	531.8	531.7	531.6	531.5	531.4	531.3	531.2
150°	546.7	546.7	546.7	546.7	546.5	546.4	546.4	546.3
152.5°	560.7	561.0	561.2	561.2	561.0	560.6	560.4	560.1
155°	580.1	580.6	581.1	581.1	580.6	580.1	579.7	579.3
157.5°	597.4	597.7	598.1	598.0	597.6	597.3	596.8	596.5
160°	608.0	608.2	608.6	608.5	608.0	607.3	606.8	606.3
162.5°	617.4	618.0	618.7	618.7	618.1	617.5	617.0	616.4
165°	630.0	630.6	631.3	631.4	631.0	630.5	630.1	629.6
167.5°	640.5	641.2	641.9	641.9	641.2	640.5	639.8	639.1
170°	646.2	646.9	647.6	647.6	646.8	646.0	645.2	644.4
172.5°	650.5	651.3	652.0	652.0	651.2	650.4	649.6	648.9
175°	655.1	655.9	656.7	656.7	655.9	655.1	654.3	653.5
177.5°	657.6	658.3	658.9	658.9	658.2	657.5	656.7	655.9
180°	657.6	657.6	657.6	657.6	657.6	657.6	657.6	657.6

(END OF REPORT)