

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333006-940

Luminaire Tested: **S124RDIP-S1195D1035U940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333006-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124RDIP-S1195D1035U940-4F0-1E-UDD-F  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1035 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7981.4 lumens  
Efficiency: N/A  
Efficacy: 119.5 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 66.8  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333006-940

CATALOG NUMBER: S124RDIP-S1195D1035U940-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P333006-940

CATALOG NUMBER: S124RDIP-S1195D1035U940-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	60	60	60
1	99	95	91	87	92	88	85	82	75	73	71	64	62	61	53	52	51
2	90	83	77	72	84	77	72	68	66	62	59	56	54	51	47	45	43
3	83	73	66	60	76	68	62	57	59	54	50	50	47	43	42	39	37
4	76	65	57	51	70	61	54	48	52	47	43	45	41	37	38	35	32
5	70	58	50	44	64	54	47	42	47	41	37	40	36	33	34	31	28
6	64	52	44	38	59	49	42	36	42	37	33	37	32	29	31	28	25
7	59	47	39	34	55	44	37	32	39	33	29	33	29	26	28	25	22
8	55	43	35	30	51	40	33	29	35	30	26	31	26	23	26	23	20
9	51	39	32	27	48	37	30	26	32	27	23	28	24	21	24	21	18
10	48	36	29	24	45	34	27	23	30	25	21	26	22	19	22	19	17

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	15012	15012	15012
5°	15046	14862	14955
10°	14952	14684	14684
15°	14780	14375	14269
20°	14545	13970	13713
25°	14243	13495	13153
30°	13951	12995	12450
35°	13626	12476	11745
40°	13235	11884	10984
45°	12875	11298	10209
50°	12465	10623	9388
55°	12024	9920	8497
60°	11541	9150	7585
65°	11096	8187	6692
70°	10452	7124	5681
75°	9638	5908	4619
80°	8405	4500	4235
85°	7123	4085	3825



TEST NUMBER: P333006-940

CATALOG NUMBER: S124RDIP-S1195D1035U940-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	174.7	2.2
10°-20°	487.1	6.1
20°-30°	703.4	8.8
30°-40°	797.3	10.0
40°-50°	770.0	9.6
50°-60°	640.3	8.0
60°-70°	442.1	5.5
70°-80°	224.1	2.8
80°-90°	60.9	0.8
90°-100°	40.7	0.5
100°-110°	259.5	3.3
110°-120°	496.5	6.2
120°-130°	630.3	7.9
130°-140°	674.3	8.4
140°-150°	630.6	7.9
150°-160°	508.5	6.4
160°-170°	328.0	4.1
170°-180°	113.0	1.4
0°-30°	1365.2	17.1
0°-40°	2162.6	27.1
0°-60°	3572.8	44.8
0°-90°	4299.9	53.9
90°-120°	796.7	10.0
90°-150°	2731.9	34.2
90°-180°	3681.0	46.1
0°-180°	7981.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1860	1860	1860	1860	1860	
5°	1857	1850	1834	1847	1845	176
15°	1768	1754	1720	1717	1707	498
25°	1599	1572	1515	1491	1477	736
35°	1383	1336	1266	1219	1192	864
45°	1128	1073	990	922	894	869
55°	854	795	705	633	604	764
65°	581	518	429	370	350	573
75°	309	256	189	158	148	326
85°	77	50	44	41	41	87
90°	3	12	20	25	27	6
95°	49	20	20	25	26	63
105°	268	273	278	284	254	280
115°	500	503	502	504	504	492
125°	703	706	705	708	709	628
135°	872	872	875	877	879	672
145°	1006	1008	1008	1010	1011	628
155°	1103	1104	1101	1104	1102	508
165°	1163	1159	1159	1165	1158	329
175°	1190	1185	1186	1193	1183	113
180°	1190	1190	1190	1190	1190	



TEST NUMBER: P333006-940

CATALOG NUMBER: S124RDIP-S1195D1035U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1859.6	1859.6	1859.6	1859.6	1859.6	1859.6	1859.6	1859.6	1859.6	1859.6	1859.6
2.5°	1864.1	1863.1	1862.2	1861.1	1860.1	1858.2	1855.5	1852.6	1849.9	1847.1	1849.9
5°	1856.7	1855.5	1854.2	1853.0	1851.7	1849.1	1845.4	1841.6	1837.8	1834.0	1837.1
7.5°	1840.0	1838.6	1837.3	1835.9	1834.6	1831.5	1826.6	1821.7	1816.7	1811.8	1813.8
10°	1824.0	1822.4	1820.9	1819.3	1817.7	1814.0	1808.4	1802.7	1797.0	1791.3	1792.5
12.5°	1803.5	1801.7	1799.8	1798.0	1796.2	1791.9	1785.2	1778.5	1771.7	1765.1	1765.9
15°	1768.4	1765.6	1762.8	1760.0	1757.1	1751.7	1743.8	1735.9	1728.0	1720.0	1719.4
17.5°	1726.1	1721.9	1717.8	1713.7	1709.6	1702.8	1693.3	1683.8	1674.3	1664.8	1663.0
20°	1693.0	1688.9	1684.8	1680.7	1676.6	1669.1	1658.4	1647.6	1636.8	1626.1	1623.5
22.5°	1656.5	1652.0	1647.3	1642.7	1638.1	1630.0	1618.5	1607.0	1595.4	1583.9	1580.1
25°	1599.0	1593.3	1587.6	1582.0	1576.3	1566.9	1554.0	1541.0	1528.0	1515.0	1509.7
27.5°	1538.6	1531.5	1524.4	1517.2	1510.0	1499.6	1485.7	1471.9	1457.9	1444.1	1437.4
30°	1496.6	1488.6	1480.7	1472.7	1464.9	1453.5	1438.6	1423.7	1408.9	1394.0	1386.1
32.5°	1452.1	1443.1	1434.2	1425.3	1416.4	1404.3	1388.8	1373.5	1358.1	1342.7	1333.6
35°	1382.6	1372.4	1362.4	1352.2	1342.1	1329.1	1313.3	1297.5	1281.7	1265.9	1255.1
37.5°	1308.3	1297.8	1287.4	1276.9	1266.5	1252.5	1235.0	1217.5	1200.0	1182.4	1170.4
40°	1255.9	1245.5	1235.0	1224.6	1214.1	1199.9	1181.9	1163.8	1145.8	1127.7	1114.5
42.5°	1205.8	1194.8	1183.8	1172.9	1162.0	1147.1	1128.3	1109.5	1090.7	1071.9	1058.4
45°	1127.7	1116.0	1104.3	1092.6	1080.9	1065.5	1046.6	1027.6	1008.6	989.6	974.1
47.5°	1047.1	1035.0	1023.0	1010.8	998.8	982.8	963.1	943.3	923.6	903.9	887.8
50°	992.5	980.1	967.8	955.5	943.1	926.8	906.5	886.3	866.0	845.8	830.0
52.5°	936.7	924.5	912.5	900.4	888.3	871.8	851.1	830.4	809.6	788.8	772.8
55°	854.3	841.7	829.0	816.4	803.7	787.1	766.5	746.0	725.4	704.8	688.4
57.5°	772.8	759.7	746.5	733.4	720.2	703.6	683.3	663.0	642.7	622.5	605.8
60°	714.8	702.1	689.5	676.8	664.1	647.7	627.5	607.3	586.9	566.7	550.3
62.5°	662.4	649.3	636.1	622.9	609.8	592.8	572.0	551.3	530.5	509.8	494.5
65°	580.9	567.3	553.8	540.1	526.6	509.6	489.4	469.1	448.9	428.6	415.0
67.5°	496.3	483.3	470.3	457.3	444.3	428.3	409.5	390.7	371.9	353.1	341.4
70°	442.8	429.5	416.3	403.0	389.7	374.0	356.0	338.0	319.9	301.8	291.4
72.5°	385.8	373.9	361.9	349.8	337.8	323.2	306.2	289.2	272.2	255.1	246.2
75°	309.0	297.3	285.5	273.8	262.2	248.9	234.0	219.1	204.3	189.4	182.1
77.5°	231.0	221.1	211.1	201.2	191.2	180.2	168.2	156.2	144.2	132.2	127.9
80°	180.8	171.7	162.5	153.3	144.1	134.8	125.3	115.8	106.3	96.8	95.9
82.5°	137.6	129.1	120.7	112.3	103.9	96.9	91.5	86.1	80.6	75.2	74.5
85°	76.9	70.5	64.2	57.9	51.5	48.0	47.0	46.0	45.1	44.1	43.5
87.5°	26.8	25.1	23.5	21.9	20.3	19.6	19.7	19.7	19.8	19.9	19.9
90°	2.7	4.8	7.0	9.2	11.4	13.3	14.8	16.4	18.0	19.6	20.8
92.5°	11.2	11.3	11.4	11.6	11.7	12.6	14.1	15.7	17.3	18.9	20.1
95°	49.0	42.3	35.5	28.8	22.0	18.8	19.0	19.2	19.4	19.6	20.8
97.5°	104.0	108.2	112.4	116.5	120.7	111.8	89.7	67.7	45.6	23.5	23.6
100°	146.0	149.5	153.1	156.7	160.2	148.4	121.1	93.8	66.4	39.1	35.8
102.5°	193.0	195.6	198.2	200.8	203.4	203.0	199.4	195.8	192.3	188.7	152.4
105°	268.0	269.1	270.3	271.5	272.7	273.8	274.7	275.7	276.8	277.8	279.6
107.5°	337.5	338.1	338.8	339.3	339.9	340.9	342.2	343.6	344.9	346.3	347.1
110°	384.6	385.1	385.8	386.3	386.9	387.8	389.0	390.2	391.4	392.5	393.0



TEST NUMBER: P333006-940

CATALOG NUMBER: S124RDIP-S1195D1035U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	430.2	431.2	432.3	433.4	434.4	435.2	435.8	436.3	436.8	437.4	437.4
115°	500.2	500.9	501.5	502.0	502.7	502.8	502.7	502.5	502.2	502.0	502.5
117.5°	563.5	564.3	565.1	565.9	566.7	567.2	567.7	568.1	568.6	569.0	568.9
120°	606.2	607.0	607.8	608.6	609.4	609.7	609.5	609.3	609.0	608.9	609.3
122.5°	646.0	646.6	647.0	647.5	648.0	648.4	648.6	648.9	649.2	649.4	649.7
125°	703.2	704.0	704.8	705.6	706.4	706.6	706.2	705.8	705.4	705.0	705.6
127.5°	757.3	757.5	757.8	758.0	758.1	758.7	759.6	760.5	761.4	762.3	762.2
130°	792.3	792.5	792.6	792.8	793.0	793.4	794.1	794.6	795.2	795.9	796.0
132.5°	824.3	824.7	825.0	825.4	825.7	826.3	827.1	827.8	828.5	829.3	829.5
135°	872.4	872.2	872.0	871.7	871.6	871.8	872.6	873.4	874.2	875.0	875.4
137.5°	914.9	915.0	915.1	915.2	915.3	915.7	916.6	917.5	918.3	919.2	919.6
140°	942.7	943.1	943.5	943.9	944.2	944.7	945.0	945.5	945.8	946.3	946.8
142.5°	967.6	968.3	969.0	969.7	970.4	970.9	971.2	971.4	971.6	971.9	972.3
145°	1005.8	1006.5	1007.1	1007.6	1008.3	1008.5	1008.5	1008.5	1008.5	1008.5	1008.8
147.5°	1036.3	1037.4	1038.6	1039.6	1040.8	1041.3	1041.0	1040.8	1040.6	1040.4	1040.6
150°	1058.4	1059.2	1060.0	1060.8	1061.6	1061.8	1061.7	1061.5	1061.3	1061.0	1061.0
152.5°	1076.9	1077.5	1078.2	1078.8	1079.4	1079.6	1079.2	1078.9	1078.5	1078.2	1078.5
155°	1103.0	1103.1	1103.3	1103.5	1103.7	1103.5	1103.0	1102.3	1101.7	1101.2	1101.9
157.5°	1124.8	1124.7	1124.5	1124.4	1124.4	1123.9	1123.3	1122.6	1122.0	1121.2	1122.3
160°	1137.6	1137.0	1136.5	1135.9	1135.2	1134.9	1134.7	1134.4	1134.3	1134.1	1135.2
162.5°	1149.1	1148.3	1147.5	1146.7	1146.0	1145.6	1145.3	1145.1	1145.0	1144.8	1145.9
165°	1163.4	1162.4	1161.5	1160.5	1159.5	1159.0	1159.0	1159.0	1159.0	1159.0	1160.6
167.5°	1174.8	1173.8	1172.8	1171.8	1170.7	1170.2	1170.0	1169.9	1169.8	1169.7	1171.4
170°	1181.2	1180.1	1178.8	1177.7	1176.5	1176.0	1176.2	1176.4	1176.6	1176.8	1178.4
172.5°	1185.5	1184.4	1183.1	1182.0	1180.8	1180.3	1180.4	1180.7	1180.9	1181.1	1182.7
175°	1190.2	1189.0	1187.8	1186.6	1185.4	1184.9	1185.1	1185.4	1185.5	1185.7	1187.5
177.5°	1192.3	1191.1	1190.1	1189.0	1187.8	1187.5	1187.8	1188.1	1188.4	1188.7	1190.0
180°	1190.2	1190.2	1190.2	1190.2	1190.2	1190.2	1190.2	1190.2	1190.2	1190.2	1190.2



TEST NUMBER: P333006-940

CATALOG NUMBER: S124RDIP-S1195D1035U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1859.6	1859.6	1859.6	1859.6	1859.6	1859.6	1859.6	1859.6
2.5°	1852.6	1855.5	1858.2	1859.5	1859.2	1858.9	1858.7	1858.5
5°	1840.3	1843.4	1846.6	1847.9	1847.3	1846.6	1846.0	1845.4
7.5°	1815.8	1817.8	1819.9	1820.3	1819.4	1818.4	1817.3	1816.3
10°	1793.8	1795.0	1796.4	1796.4	1795.0	1793.8	1792.5	1791.3
12.5°	1766.6	1767.4	1768.1	1767.5	1765.9	1764.1	1762.3	1760.5
15°	1718.8	1718.1	1717.5	1716.1	1713.9	1711.6	1709.5	1707.3
17.5°	1661.3	1659.5	1657.7	1655.2	1651.8	1648.4	1645.1	1641.7
20°	1621.0	1618.5	1616.0	1612.7	1608.6	1604.5	1600.3	1596.2
22.5°	1576.4	1572.5	1568.8	1565.2	1561.8	1558.4	1555.1	1551.8
25°	1504.2	1498.9	1493.5	1489.2	1486.0	1482.9	1479.7	1476.6
27.5°	1430.8	1424.2	1417.6	1411.9	1407.4	1402.8	1398.3	1393.7
30°	1378.1	1370.3	1362.4	1355.8	1350.8	1345.8	1340.7	1335.6
32.5°	1324.4	1315.2	1306.0	1299.0	1294.2	1289.4	1284.6	1279.8
35°	1244.3	1233.6	1222.8	1214.6	1208.9	1203.2	1197.5	1191.8
37.5°	1158.3	1146.3	1134.3	1125.4	1119.7	1114.0	1108.4	1102.7
40°	1101.2	1087.9	1074.6	1065.1	1059.4	1053.6	1048.0	1042.3
42.5°	1044.8	1031.3	1017.7	1008.0	1002.0	996.1	990.2	984.2
45°	958.6	943.1	927.6	916.9	911.3	905.6	899.9	894.2
47.5°	871.7	855.7	839.6	828.4	822.2	815.9	809.6	803.3
50°	814.1	798.3	782.5	771.6	765.6	759.6	753.6	747.5
52.5°	756.7	740.7	724.5	713.4	707.1	700.9	694.6	688.3
55°	671.9	655.5	639.0	627.8	621.8	615.7	609.8	603.7
57.5°	589.2	572.4	555.7	545.1	540.6	535.9	531.4	526.8
60°	533.8	517.4	500.9	490.2	485.1	480.0	474.9	469.8
62.5°	479.4	464.2	449.0	439.3	435.3	431.3	427.2	423.2
65°	401.4	387.8	374.2	365.4	361.7	357.8	354.1	350.3
67.5°	329.8	318.0	306.3	298.4	294.2	290.0	285.8	281.6
70°	281.0	270.5	260.1	253.3	250.1	247.0	243.8	240.7
72.5°	237.3	228.4	219.5	213.6	210.6	207.8	204.8	201.9
75°	174.9	167.6	160.2	155.7	153.8	151.9	150.0	148.1
77.5°	123.7	119.4	115.2	112.8	112.2	111.6	111.1	110.5
80°	95.0	94.0	93.0	92.4	92.1	91.8	91.5	91.1
82.5°	73.8	73.1	72.4	71.9	71.6	71.2	71.0	70.6
85°	42.9	42.3	41.6	41.3	41.3	41.3	41.3	41.3
87.5°	19.8	19.8	19.8	20.0	20.3	20.6	21.0	21.3
90°	21.9	23.2	24.3	25.1	25.5	25.9	26.3	26.7
92.5°	21.2	22.5	23.6	24.3	24.3	24.4	24.5	24.6
95°	21.9	23.2	24.3	25.1	25.2	25.4	25.6	25.8
97.5°	23.7	23.9	24.0	24.2	24.3	24.5	24.7	25.0
100°	32.5	29.1	25.7	24.2	24.3	24.5	24.7	25.0
102.5°	116.2	79.9	43.6	25.5	25.5	25.6	25.6	25.7
105°	281.3	283.0	284.8	282.2	275.1	268.0	260.8	253.7
107.5°	348.0	348.9	349.7	350.5	351.3	352.0	352.8	353.6
110°	393.3	393.8	394.1	394.7	395.2	395.8	396.5	397.0





TEST NUMBER: P333006-940

CATALOG NUMBER: S124RDIP-S1195D1035U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	437.3	437.2	437.1	437.5	438.2	439.0	439.7	440.4
115°	502.8	503.3	503.6	503.8	503.8	503.8	503.8	503.8
117.5°	568.8	568.7	568.6	568.6	568.6	568.5	568.4	568.3
120°	609.7	610.0	610.5	610.5	610.0	609.7	609.3	608.9
122.5°	650.0	650.1	650.4	650.3	650.0	649.5	649.2	648.7
125°	706.2	706.8	707.4	707.8	708.0	708.2	708.4	708.6
127.5°	762.1	762.0	761.9	761.7	761.6	761.4	761.3	761.1
130°	796.2	796.4	796.6	796.7	796.7	796.7	796.7	796.7
132.5°	829.6	829.9	830.1	830.1	829.9	829.7	829.6	829.5
135°	875.8	876.2	876.6	877.0	877.4	877.8	878.2	878.6
137.5°	920.1	920.5	921.0	921.0	921.0	920.9	920.7	920.6
140°	947.4	948.1	948.6	949.0	949.2	949.4	949.6	949.9
142.5°	972.8	973.2	973.7	973.8	973.9	973.9	974.0	974.0
145°	1009.0	1009.1	1009.3	1009.7	1010.0	1010.4	1010.8	1011.2
147.5°	1040.7	1040.9	1041.1	1041.3	1041.4	1041.6	1041.9	1042.1
150°	1061.0	1061.0	1061.0	1061.1	1061.4	1061.6	1061.8	1061.9
152.5°	1078.8	1079.1	1079.4	1079.5	1079.4	1079.3	1079.1	1079.1
155°	1102.7	1103.5	1104.3	1104.4	1103.8	1103.2	1102.6	1102.1
157.5°	1123.3	1124.4	1125.3	1125.3	1124.4	1123.3	1122.3	1121.2
160°	1136.5	1137.6	1138.8	1138.8	1137.6	1136.5	1135.2	1134.1
162.5°	1147.1	1148.3	1149.5	1149.4	1148.1	1146.7	1145.4	1144.1
165°	1162.2	1163.8	1165.3	1165.2	1163.4	1161.6	1159.8	1158.1
167.5°	1173.1	1174.9	1176.6	1176.5	1174.6	1172.6	1170.5	1168.6
170°	1180.0	1181.5	1183.1	1182.9	1181.0	1179.0	1177.0	1175.0
172.5°	1184.3	1185.8	1187.4	1187.1	1185.0	1182.9	1180.7	1178.6
175°	1189.3	1191.1	1192.8	1192.5	1190.2	1187.8	1185.4	1183.0
177.5°	1191.2	1192.5	1193.8	1193.5	1191.6	1189.7	1187.8	1185.9
180°	1190.2	1190.2	1190.2	1190.2	1190.2	1190.2	1190.2	1190.2

(END OF REPORT)