

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333009-940

Luminaire Tested: **S124RDIP-S1195D1205U940-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333009-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIP-S1195D1205U940-4F0-1E-UDD-A
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1195 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1205 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8755.9 lumens
Efficiency: N/A
Efficacy: 122.1 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 71.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333009-940

CATALOG NUMBER: S124RDIP-S1195D1205U940-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P333009-940

CATALOG NUMBER: S124RDIP-S1195D1205U940-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20			20			20			20
RC	80				70				50			30			10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51
1	99	94	91	87	91	87	84	81	74	72	70	62	61	59	51	50	49	44
2	90	83	77	72	83	77	72	67	66	62	59	55	53	50	46	44	42	38
3	82	73	66	61	76	68	62	57	58	54	50	49	46	43	41	38	36	32
4	76	65	57	52	70	61	54	49	52	47	43	44	40	37	37	34	32	28
5	70	58	50	44	64	54	47	42	47	41	37	40	36	32	33	30	28	25
6	64	52	44	39	59	49	42	37	42	37	33	36	32	29	30	27	25	22
7	59	47	40	34	55	44	37	32	38	33	29	33	29	25	28	25	22	19
8	55	43	35	30	51	40	33	29	35	30	26	30	26	23	26	22	20	18
9	51	39	32	27	48	37	30	26	32	27	23	28	24	21	24	20	18	16
10	48	36	29	24	45	34	27	23	30	24	21	26	22	19	22	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	14266	14266	14266	14266
5°	16546	14309	12647	14309
10°	19575	14246	11287	14246
15°	22612	14114	9699	14114
20°	25175	13933	8771	13933
25°	25989	13755	8143	13755
30°	22750	13539	7764	13539
35°	17710	13219	7535	13219
40°	13281	12853	7413	12853
45°	10485	12265	7348	12265
50°	8852	11588	7135	11588
55°	7716	10842	6753	10842
60°	6943	10070	5977	10070
65°	6120	9234	5140	9234
70°	5511	8368	4638	8368
75°	4619	7417	3952	7417
80°	3905	6323	3705	6323
85°	3298	4946	3298	4946



TEST NUMBER: P333009-940

CATALOG NUMBER: S124RDIP-S1195D1205U940-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	171.2	2.0
10°-20°	516.5	5.9
20°-30°	807.8	9.2
30°-40°	898.0	10.3
40°-50°	796.7	9.1
50°-60°	620.8	7.1
60°-70°	406.5	4.6
70°-80°	199.9	2.3
80°-90°	53.3	0.6
90°-100°	47.4	0.5
100°-110°	302.1	3.5
110°-120°	577.9	6.6
120°-130°	733.6	8.4
130°-140°	784.9	9.0
140°-150°	734.0	8.4
150°-160°	591.9	6.8
160°-170°	381.8	4.4
170°-180°	131.6	1.5
0°-30°	1495.5	17.1
0°-40°	2393.5	27.3
0°-60°	3811.0	43.5
0°-90°	4470.7	51.1
90°-120°	927.4	10.6
90°-150°	3179.9	36.3
90°-180°	4285.0	48.9
0°-180°	8755.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1767	1767	1767	1767	1767	
5°	2042	1766	1561	1766	2042	207
15°	2706	1689	1160	1689	2706	769
25°	2918	1544	914	1544	2918	1294
35°	1797	1341	765	1341	1797	1126
45°	918	1074	644	1074	918	727
55°	548	770	480	770	548	499
65°	320	483	269	483	320	322
75°	148	238	127	238	148	163
85°	36	53	36	53	36	41
90°	31	3	31	3	31	15
95°	30	57	30	57	30	24
105°	295	312	295	312	295	258
115°	586	582	586	582	586	580
125°	825	818	825	818	825	734
135°	1023	1015	1023	1015	1023	787
145°	1177	1171	1177	1171	1177	736
155°	1283	1284	1283	1284	1283	591
165°	1348	1354	1348	1354	1348	381
175°	1377	1385	1377	1385	1377	131
180°	1385	1385	1385	1385	1385	



TEST NUMBER: P333009-940

CATALOG NUMBER: S124RDIP-S1195D1205U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1
2.5°	1863.9	1869.0	1863.9	1863.3	1857.6	1855.9	1853.6	1846.2	1832.6	1824.6	1826.3
5°	2041.8	2059.7	2049.7	2048.3	2032.7	2017.0	2007.0	1984.2	1960.0	1943.7	1930.1
7.5°	2247.7	2258.0	2251.7	2241.8	2216.4	2202.1	2179.0	2148.9	2105.5	2072.3	2042.0
10°	2387.9	2396.4	2393.6	2375.1	2356.5	2318.8	2297.5	2255.5	2200.7	2157.2	2116.7
12.5°	2525.7	2534.9	2509.8	2510.6	2475.6	2445.9	2412.0	2359.1	2295.8	2239.8	2189.0
15°	2705.5	2694.0	2694.0	2679.8	2640.6	2599.3	2564.5	2508.9	2429.2	2362.2	2291.8
17.5°	2846.1	2850.1	2844.2	2810.7	2779.9	2737.2	2673.3	2608.4	2534.4	2444.5	2372.5
20°	2930.4	2930.4	2924.0	2901.2	2861.3	2815.8	2746.7	2676.2	2582.2	2491.8	2410.7
22.5°	2964.6	2966.8	2959.3	2940.5	2904.7	2860.2	2801.4	2729.8	2633.0	2531.1	2430.6
25°	2917.6	2931.1	2932.5	2927.6	2916.9	2889.8	2839.3	2765.9	2679.1	2568.8	2460.5
27.5°	2678.6	2695.7	2710.7	2735.3	2768.0	2785.2	2787.4	2750.1	2674.3	2568.1	2459.2
30°	2440.5	2454.8	2501.1	2561.6	2608.6	2651.3	2688.3	2698.3	2655.6	2560.2	2445.5
32.5°	2176.3	2195.7	2241.9	2307.0	2385.3	2457.6	2540.8	2583.2	2582.1	2524.9	2418.8
35°	1797.0	1811.2	1854.0	1922.3	2016.2	2123.8	2255.5	2358.0	2427.8	2422.8	2358.0
37.5°	1449.2	1465.3	1508.5	1565.1	1656.3	1789.4	1916.8	2058.1	2187.1	2259.6	2237.9
40°	1260.2	1260.9	1302.9	1361.3	1446.7	1562.7	1701.6	1858.1	2002.0	2119.5	2142.2
42.5°	1110.9	1111.1	1138.8	1201.8	1263.3	1372.5	1505.0	1660.5	1828.9	1964.5	2024.9
45°	918.4	924.8	947.6	985.3	1033.8	1126.3	1232.3	1376.9	1565.6	1726.4	1826.8
47.5°	777.8	787.1	801.6	832.4	871.0	932.6	1020.4	1150.2	1303.7	1480.7	1623.5
50°	704.8	706.2	724.8	741.8	775.3	824.5	901.3	1009.5	1150.5	1320.6	1479.4
52.5°	642.2	641.9	653.0	674.7	701.9	740.1	802.2	900.7	1025.7	1178.3	1342.2
55°	548.2	551.8	560.3	577.4	598.1	625.1	674.2	748.2	846.5	976.8	1125.6
57.5°	476.7	478.6	485.3	492.5	511.5	531.1	568.0	619.4	702.3	809.0	947.6
60°	430.0	430.7	432.8	443.5	458.5	477.0	501.9	545.4	615.1	712.7	822.3
62.5°	384.4	385.8	389.1	396.8	408.4	421.2	447.3	482.1	539.9	623.2	722.0
65°	320.4	321.1	326.1	329.0	338.1	349.6	368.8	392.3	432.1	501.9	576.7
67.5°	267.7	267.7	268.0	271.8	278.2	285.8	297.3	316.1	346.2	389.1	455.0
70°	233.5	233.5	235.0	237.1	240.7	247.0	253.4	267.7	289.8	324.7	375.2
72.5°	201.6	202.2	203.6	204.0	205.9	211.2	215.9	225.0	241.4	267.7	308.5
75°	148.1	150.3	153.8	156.7	160.2	159.4	164.4	170.1	175.1	190.8	214.3
77.5°	110.2	109.1	109.5	111.9	112.4	113.1	116.6	121.0	124.8	132.2	140.5
80°	84.0	84.0	86.1	86.9	86.1	86.9	90.4	92.6	94.0	96.8	104.7
82.5°	63.5	64.6	63.9	64.6	65.1	65.8	68.8	69.2	70.6	71.8	75.1
85°	35.6	36.3	37.0	35.6	35.6	35.6	37.0	37.7	39.1	38.4	39.9
87.5°	18.7	18.1	18.5	18.5	18.9	18.2	18.5	19.4	17.9	18.2	17.8
90°	31.1	30.6	30.1	29.7	29.2	28.4	26.9	25.6	24.2	22.8	21.0
92.5°	28.6	28.5	28.4	28.4	28.3	27.5	26.1	24.7	23.4	21.9	20.2
95°	30.1	29.8	29.6	29.3	29.2	28.4	26.9	25.6	24.2	22.8	22.6
97.5°	29.0	28.8	28.5	28.4	28.1	27.9	27.7	27.6	27.5	27.4	53.1
100°	29.0	28.8	28.5	28.4	28.1	30.0	33.9	37.7	41.6	45.6	77.4
102.5°	29.9	29.8	29.8	29.7	29.7	50.7	93.0	135.2	177.5	219.6	223.8
105°	295.3	303.6	311.8	320.1	328.4	331.5	329.5	327.4	325.4	323.2	322.1
107.5°	411.5	410.6	409.8	408.9	408.0	407.1	406.1	405.1	404.0	403.1	401.4
110°	462.1	461.5	460.7	460.0	459.3	458.8	458.3	457.9	457.4	456.9	455.6



TEST NUMBER: P333009-940

CATALOG NUMBER: S124RDIP-S1195D1205U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	512.6	511.8	511.0	510.1	509.2	508.8	508.9	509.0	509.1	509.2	508.5
115°	586.5	586.5	586.5	586.5	586.5	586.2	585.8	585.3	584.9	584.3	584.6
117.5°	661.5	661.6	661.6	661.7	661.8	661.9	662.0	662.1	662.2	662.3	661.8
120°	708.7	709.2	709.6	710.1	710.5	710.5	710.1	709.6	709.2	708.7	708.9
122.5°	755.1	755.5	756.1	756.5	757.0	757.1	756.8	756.5	756.3	756.0	755.6
125°	824.7	824.6	824.3	824.0	823.9	823.4	822.7	822.0	821.3	820.6	821.1
127.5°	885.9	886.1	886.3	886.4	886.6	886.8	886.9	887.1	887.2	887.3	886.3
130°	927.3	927.3	927.3	927.3	927.3	927.2	927.0	926.8	926.5	926.3	925.6
132.5°	965.5	965.6	965.8	966.0	966.2	966.2	966.0	965.7	965.5	965.3	964.4
135°	1022.6	1022.2	1021.7	1021.3	1020.8	1020.4	1019.8	1019.4	1019.0	1018.5	1017.6
137.5°	1071.6	1071.7	1071.8	1072.0	1072.1	1071.9	1071.4	1070.9	1070.4	1069.9	1068.9
140°	1105.5	1105.3	1105.1	1104.8	1104.7	1104.2	1103.5	1102.8	1102.1	1101.4	1100.9
142.5°	1133.7	1133.7	1133.6	1133.6	1133.5	1133.3	1132.7	1132.3	1131.8	1131.2	1131.0
145°	1177.1	1176.6	1176.1	1175.6	1175.2	1174.8	1174.7	1174.4	1174.2	1173.9	1173.9
147.5°	1212.9	1212.6	1212.5	1212.2	1211.9	1211.7	1211.6	1211.4	1211.2	1211.0	1211.2
150°	1236.1	1235.9	1235.6	1235.4	1235.2	1235.0	1235.0	1235.0	1235.0	1235.0	1235.3
152.5°	1256.0	1256.2	1256.2	1256.4	1256.5	1256.4	1256.1	1255.7	1255.4	1255.0	1255.4
155°	1282.7	1283.4	1284.1	1284.8	1285.5	1285.4	1284.4	1283.5	1282.6	1281.7	1282.4
157.5°	1305.1	1306.3	1307.5	1308.7	1309.9	1309.9	1308.7	1307.5	1306.3	1305.1	1305.9
160°	1320.0	1321.4	1322.8	1324.2	1325.5	1325.5	1324.2	1322.8	1321.4	1320.0	1320.3
162.5°	1331.6	1333.2	1334.8	1336.3	1337.9	1338.0	1336.6	1335.2	1333.8	1332.5	1332.7
165°	1348.0	1350.1	1352.1	1354.2	1356.3	1356.4	1354.6	1352.7	1350.9	1349.1	1349.1
167.5°	1360.2	1362.5	1364.9	1367.2	1369.4	1369.6	1367.5	1365.6	1363.5	1361.5	1361.6
170°	1367.7	1370.0	1372.3	1374.6	1376.9	1377.2	1375.3	1373.4	1371.6	1369.8	1369.5
172.5°	1371.8	1374.3	1376.8	1379.3	1381.8	1382.1	1380.3	1378.4	1376.5	1374.8	1374.5
175°	1377.0	1379.7	1382.5	1385.3	1388.0	1388.4	1386.3	1384.3	1382.2	1380.1	1379.9
177.5°	1380.4	1382.5	1384.7	1387.0	1389.2	1389.6	1388.0	1386.6	1385.1	1383.7	1383.3
180°	1385.3	1385.3	1385.3	1385.3	1385.3	1385.3	1385.3	1385.3	1385.3	1385.3	1385.3



TEST NUMBER: P333009-940

CATALOG NUMBER: S124RDIP-S1195D1205U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1
2.5°	1820.6	1812.7	1808.7	1799.6	1788.7	1783.0	1777.9	1770.5	1760.8	1750.5	1743.1
5°	1913.0	1896.0	1874.6	1849.0	1826.1	1804.1	1784.8	1765.7	1743.6	1720.8	1698.0
7.5°	2007.9	1974.2	1938.0	1896.0	1855.0	1817.9	1783.7	1751.0	1714.0	1680.8	1650.6
10°	2073.9	2028.4	1977.8	1924.4	1871.0	1824.7	1779.1	1737.9	1692.3	1651.7	1617.6
12.5°	2127.4	2073.9	2013.1	1946.6	1882.4	1826.4	1774.1	1720.2	1668.4	1624.4	1578.9
15°	2216.3	2143.0	2061.1	1981.4	1898.1	1821.9	1751.4	1688.7	1629.7	1567.7	1524.3
17.5°	2277.4	2190.4	2090.9	1995.0	1896.7	1806.8	1725.5	1650.9	1582.7	1519.5	1467.8
20°	2313.8	2217.7	2107.4	1998.4	1888.1	1792.0	1704.4	1621.8	1551.3	1483.0	1429.6
22.5°	2334.3	2227.9	2107.4	1993.3	1879.0	1774.9	1678.7	1592.8	1516.0	1447.7	1388.6
25°	2340.9	2227.0	2103.8	1972.8	1847.5	1737.1	1637.4	1544.2	1458.7	1390.4	1327.8
27.5°	2331.8	2197.6	2071.5	1937.1	1807.8	1691.5	1586.8	1488.8	1403.3	1329.9	1265.7
30°	2318.1	2174.3	2039.0	1899.5	1768.4	1656.7	1546.3	1452.4	1363.4	1287.2	1222.4
32.5°	2288.5	2145.8	2000.3	1857.3	1724.7	1609.4	1504.8	1410.2	1322.9	1245.1	1176.3
35°	2229.8	2085.3	1927.3	1780.6	1650.3	1530.7	1432.4	1341.3	1258.0	1174.7	1102.1
37.5°	2152.5	2004.8	1847.6	1687.0	1556.6	1443.7	1353.5	1268.0	1186.7	1110.6	1030.2
40°	2079.6	1945.1	1782.7	1623.3	1489.4	1380.5	1297.2	1219.6	1137.7	1062.2	981.8
42.5°	1991.4	1876.7	1712.7	1552.6	1420.5	1315.5	1238.0	1162.1	1087.6	1014.4	930.5
45°	1844.0	1757.1	1603.3	1449.6	1316.4	1212.5	1141.3	1074.3	1008.8	939.1	860.1
47.5°	1675.1	1616.2	1483.5	1326.1	1202.9	1109.4	1040.6	985.9	930.5	860.8	791.4
50°	1557.7	1520.0	1391.9	1248.0	1130.6	1044.5	973.9	922.7	876.4	809.5	747.5
52.5°	1432.4	1412.4	1304.1	1166.6	1053.1	968.7	908.5	862.3	815.5	759.9	702.0
55°	1241.6	1252.3	1160.5	1041.6	934.8	863.6	808.8	770.3	730.5	683.5	638.6
57.5°	1046.6	1085.6	1024.0	919.5	819.5	753.7	712.4	680.0	646.6	607.6	569.3
60°	929.8	962.5	927.6	835.8	748.2	687.1	648.6	623.7	590.2	554.6	525.4
62.5°	815.9	851.0	830.3	756.1	674.8	622.1	588.2	565.0	540.1	509.1	478.8
65°	672.8	695.5	685.6	634.4	576.7	531.8	500.5	483.4	460.7	437.8	410.8
67.5°	515.3	559.3	553.5	526.3	476.4	441.4	420.9	405.8	385.0	368.1	349.7
70°	423.7	464.2	463.5	441.4	414.4	381.6	367.4	354.5	336.0	319.7	304.7
72.5°	346.7	383.9	389.4	372.5	354.0	329.2	315.6	306.7	288.7	277.5	265.4
75°	242.8	269.8	277.0	277.0	268.4	255.6	243.5	237.8	225.0	215.0	207.9
77.5°	159.2	176.3	187.3	189.9	191.3	187.0	177.0	173.0	163.2	159.6	152.8
80°	112.4	123.9	136.7	141.0	144.5	143.1	138.8	136.0	126.7	123.1	120.3
82.5°	77.8	84.0	94.5	104.0	102.9	106.6	102.9	100.7	93.7	92.4	89.5
85°	40.6	41.3	42.7	49.1	52.7	54.1	54.8	53.4	51.3	51.3	46.3
87.5°	17.5	16.6	17.3	16.9	16.9	18.7	19.9	20.0	18.8	17.6	16.4
90°	19.1	17.3	15.4	13.2	10.7	8.2	5.6	3.1	5.6	8.2	10.7
92.5°	18.3	16.4	14.6	13.6	13.5	13.4	13.2	13.0	13.2	13.4	13.5
95°	22.3	22.1	21.8	25.7	33.5	41.3	49.1	57.0	49.1	41.3	33.5
97.5°	78.7	104.4	130.1	140.5	135.6	130.8	125.9	121.0	125.9	130.8	135.6
100°	109.1	140.9	172.7	186.5	182.4	178.3	174.1	170.0	174.1	178.3	182.4
102.5°	227.9	232.1	236.2	236.7	233.7	230.7	227.7	224.6	227.7	230.7	233.7
105°	320.9	319.9	318.7	317.4	316.0	314.6	313.3	311.8	313.3	314.6	316.0
107.5°	399.9	398.3	396.8	395.7	394.9	394.3	393.6	392.9	393.6	394.3	394.9
110°	454.1	452.8	451.4	450.4	449.7	449.0	448.3	447.6	448.3	449.0	449.7



TEST NUMBER: P333009-940

CATALOG NUMBER: S124RDIP-S1195D1205U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	507.8	507.2	506.6	505.6	504.4	503.1	501.9	500.7	501.9	503.1	504.4
115°	584.9	585.1	585.3	585.1	584.3	583.7	583.0	582.3	583.0	583.7	584.3
117.5°	661.3	660.8	660.2	659.5	658.6	657.7	656.7	655.9	656.7	657.7	658.6
120°	709.2	709.4	709.6	709.3	708.4	707.5	706.5	705.6	706.5	707.5	708.4
122.5°	755.3	755.0	754.7	754.2	753.7	753.1	752.6	752.0	752.6	753.1	753.7
125°	821.5	822.0	822.4	822.2	821.3	820.4	819.5	818.5	819.5	820.4	821.3
127.5°	885.2	884.1	883.1	882.4	882.3	882.0	881.7	881.5	881.7	882.0	882.3
130°	924.9	924.3	923.5	923.1	922.8	922.7	922.4	922.1	922.4	922.7	922.8
132.5°	963.5	962.6	961.8	961.1	960.7	960.3	959.8	959.5	959.8	960.3	960.7
135°	1016.6	1015.7	1014.9	1014.5	1014.7	1014.9	1015.2	1015.4	1015.2	1014.9	1014.7
137.5°	1067.9	1066.8	1065.9	1065.3	1065.2	1065.1	1065.1	1065.0	1065.1	1065.1	1065.2
140°	1100.5	1100.0	1099.6	1099.1	1098.7	1098.1	1097.7	1097.3	1097.7	1098.1	1098.7
142.5°	1130.7	1130.4	1130.2	1129.6	1128.7	1127.9	1127.1	1126.2	1127.1	1127.9	1128.7
145°	1173.9	1173.9	1173.9	1173.6	1172.9	1172.2	1171.5	1170.8	1171.5	1172.2	1172.9
147.5°	1211.5	1211.7	1211.9	1211.4	1210.1	1208.8	1207.6	1206.2	1207.6	1208.8	1210.1
150°	1235.6	1235.7	1236.0	1235.6	1234.8	1233.8	1232.9	1232.0	1232.9	1233.8	1234.8
152.5°	1255.8	1256.2	1256.6	1256.4	1255.7	1255.0	1254.3	1253.5	1254.3	1255.0	1255.7
155°	1283.1	1283.8	1284.4	1284.7	1284.4	1284.2	1284.0	1283.8	1284.0	1284.2	1284.4
157.5°	1306.7	1307.4	1308.2	1308.7	1308.9	1308.9	1309.1	1309.2	1309.1	1308.9	1308.9
160°	1320.4	1320.7	1321.0	1321.4	1322.1	1322.8	1323.5	1324.2	1323.5	1322.8	1322.1
162.5°	1332.9	1333.1	1333.4	1333.9	1334.8	1335.7	1336.6	1337.4	1336.6	1335.7	1334.8
165°	1349.1	1349.1	1349.1	1349.6	1350.8	1351.9	1353.1	1354.2	1353.1	1351.9	1350.8
167.5°	1361.7	1361.9	1362.0	1362.7	1363.9	1365.1	1366.3	1367.4	1366.3	1365.1	1363.9
170°	1369.3	1369.0	1368.9	1369.4	1370.8	1372.2	1373.6	1374.9	1373.6	1372.2	1370.8
172.5°	1374.3	1374.0	1373.8	1374.4	1375.7	1377.2	1378.5	1379.9	1378.5	1377.2	1375.7
175°	1379.7	1379.4	1379.2	1379.7	1381.2	1382.5	1383.9	1385.3	1383.9	1382.5	1381.2
177.5°	1382.9	1382.5	1382.2	1382.6	1383.9	1385.2	1386.5	1387.8	1386.5	1385.2	1383.9
180°	1385.3	1385.3	1385.3	1385.3	1385.3	1385.3	1385.3	1385.3	1385.3	1385.3	1385.3



TEST NUMBER: P333009-940

CATALOG NUMBER: S124RDIP-S1195D1205U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1
2.5°	1735.2	1729.5	1722.1	1713.5	1703.3	1694.2	1690.1	1693.6	1695.3	1690.8	1690.1
5°	1682.3	1664.6	1650.3	1629.0	1611.9	1597.6	1587.7	1583.4	1584.8	1573.4	1570.6
7.5°	1623.0	1601.9	1578.5	1553.2	1529.6	1508.6	1497.6	1491.7	1479.6	1474.4	1465.8
10°	1584.8	1556.3	1533.6	1503.6	1476.6	1451.7	1439.6	1429.6	1417.5	1411.8	1399.7
12.5°	1545.5	1512.4	1487.4	1456.3	1428.7	1398.7	1387.1	1368.7	1349.7	1337.7	1322.2
15°	1490.1	1450.3	1419.6	1382.6	1349.9	1315.7	1285.0	1250.9	1238.1	1211.0	1195.3
17.5°	1425.3	1384.9	1347.0	1297.4	1246.8	1204.3	1171.7	1139.0	1119.4	1102.1	1094.1
20°	1382.6	1345.6	1292.9	1235.2	1179.0	1132.0	1105.6	1084.3	1062.9	1050.9	1042.3
22.5°	1342.2	1294.9	1233.7	1171.4	1115.2	1078.4	1056.1	1034.2	1016.8	1005.3	993.9
25°	1274.4	1212.5	1147.6	1076.5	1038.0	1006.0	981.8	963.9	953.3	938.3	932.6
27.5°	1204.8	1129.7	1058.3	1010.4	970.4	941.0	920.0	906.6	893.0	883.5	876.1
30°	1151.2	1075.0	1010.9	965.4	924.8	900.6	883.5	867.9	857.2	849.4	843.6
32.5°	1098.2	1022.1	968.2	919.3	887.3	863.6	845.3	833.7	825.3	815.2	811.7
35°	1021.6	954.0	907.0	862.9	830.1	808.8	794.5	782.5	775.3	772.5	770.3
37.5°	948.1	892.6	842.1	805.9	776.8	759.9	743.2	737.2	732.3	727.2	729.5
40°	901.3	849.4	804.5	766.1	742.5	724.1	714.1	706.9	702.7	702.7	702.7
42.5°	860.9	810.0	766.3	731.9	708.4	692.8	681.6	675.6	674.2	673.7	677.1
45°	798.1	751.1	706.9	678.5	658.5	642.9	636.5	631.5	631.5	634.4	635.1
47.5°	735.8	691.9	656.4	624.6	606.3	596.5	590.9	588.4	588.6	591.5	594.8
50°	697.7	654.2	619.4	590.9	573.8	564.5	559.5	558.2	559.5	559.5	564.5
52.5°	656.1	617.2	582.9	559.0	539.7	531.0	528.2	526.3	527.1	529.4	531.5
55°	595.2	560.3	527.5	504.8	490.5	484.8	478.4	479.1	477.7	479.1	479.1
57.5°	534.1	502.7	472.3	454.2	441.7	433.5	426.4	428.5	426.3	426.1	424.9
60°	494.8	460.7	436.4	420.1	405.8	398.7	392.3	393.7	391.6	390.1	387.3
62.5°	452.1	423.7	400.6	384.8	373.4	365.1	358.6	357.2	352.3	347.4	341.2
65°	390.1	366.7	346.0	331.1	320.4	314.0	309.0	304.7	294.0	282.7	277.0
67.5°	329.9	313.0	293.7	281.1	272.4	264.0	254.5	247.2	237.2	231.0	227.4
70°	291.1	274.8	258.4	246.3	237.1	229.3	218.6	213.6	206.4	203.6	200.1
72.5°	254.1	238.9	223.7	212.8	202.9	196.8	188.4	183.4	180.3	179.1	175.6
75°	198.0	185.8	174.4	164.4	156.7	152.4	148.8	145.3	143.8	137.4	133.8
77.5°	144.4	136.4	129.3	122.2	116.6	113.8	106.9	102.8	100.4	97.4	96.7
80°	112.4	106.8	99.7	95.4	87.6	84.7	81.9	81.1	80.4	79.7	79.0
82.5°	84.6	78.9	71.8	69.2	67.1	65.4	63.7	63.0	62.2	62.7	62.5
85°	42.7	39.9	39.9	39.1	38.4	37.7	37.0	37.0	36.3	37.0	36.3
87.5°	16.9	16.8	17.1	16.3	17.3	17.7	17.4	17.7	18.5	17.7	17.8
90°	13.2	15.4	17.3	19.1	21.0	22.8	24.2	25.6	26.9	28.4	29.2
92.5°	13.6	14.6	16.4	18.3	20.2	21.9	23.4	24.7	26.1	27.5	28.3
95°	25.7	21.8	22.1	22.3	22.6	22.8	24.2	25.6	26.9	28.4	29.2
97.5°	140.5	130.1	104.4	78.7	53.1	27.4	27.5	27.6	27.7	27.9	28.1
100°	186.5	172.7	140.9	109.1	77.4	45.6	41.6	37.7	33.9	30.0	28.1
102.5°	236.7	236.2	232.1	227.9	223.8	219.6	177.5	135.2	93.0	50.7	29.7
105°	317.4	318.7	319.9	320.9	322.1	323.2	325.4	327.4	329.5	331.5	328.4
107.5°	395.7	396.8	398.3	399.9	401.4	403.1	404.0	405.1	406.1	407.1	408.0
110°	450.4	451.4	452.8	454.1	455.6	456.9	457.4	457.9	458.3	458.8	459.3



TEST NUMBER: P333009-940

CATALOG NUMBER: S124RDIP-S1195D1205U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	505.6	506.6	507.2	507.8	508.5	509.2	509.1	509.0	508.9	508.8	509.2
115°	585.1	585.3	585.1	584.9	584.6	584.3	584.9	585.3	585.8	586.2	586.5
117.5°	659.5	660.2	660.8	661.3	661.8	662.3	662.2	662.1	662.0	661.9	661.8
120°	709.3	709.6	709.4	709.2	708.9	708.7	709.2	709.6	710.1	710.5	710.5
122.5°	754.2	754.7	755.0	755.3	755.6	756.0	756.3	756.5	756.8	757.1	757.0
125°	822.2	822.4	822.0	821.5	821.1	820.6	821.3	822.0	822.7	823.4	823.9
127.5°	882.4	883.1	884.1	885.2	886.3	887.3	887.2	887.1	886.9	886.8	886.6
130°	923.1	923.5	924.3	924.9	925.6	926.3	926.5	926.8	927.0	927.2	927.3
132.5°	961.1	961.8	962.6	963.5	964.4	965.3	965.5	965.7	966.0	966.2	966.2
135°	1014.5	1014.9	1015.7	1016.6	1017.6	1018.5	1019.0	1019.4	1019.8	1020.4	1020.8
137.5°	1065.3	1065.9	1066.8	1067.9	1068.9	1069.9	1070.4	1070.9	1071.4	1071.9	1072.1
140°	1099.1	1099.6	1100.0	1100.5	1100.9	1101.4	1102.1	1102.8	1103.5	1104.2	1104.7
142.5°	1129.6	1130.2	1130.4	1130.7	1131.0	1131.2	1131.8	1132.3	1132.7	1133.3	1133.5
145°	1173.6	1173.9	1173.9	1173.9	1173.9	1173.9	1174.2	1174.4	1174.7	1174.8	1175.2
147.5°	1211.4	1211.9	1211.7	1211.5	1211.2	1211.0	1211.2	1211.4	1211.6	1211.7	1211.9
150°	1235.6	1236.0	1235.7	1235.6	1235.3	1235.0	1235.0	1235.0	1235.0	1235.0	1235.2
152.5°	1256.4	1256.6	1256.2	1255.8	1255.4	1255.0	1255.4	1255.7	1256.1	1256.4	1256.5
155°	1284.7	1284.4	1283.8	1283.1	1282.4	1281.7	1282.6	1283.5	1284.4	1285.4	1285.5
157.5°	1308.7	1308.2	1307.4	1306.7	1305.9	1305.1	1306.3	1307.5	1308.7	1309.9	1309.9
160°	1321.4	1321.0	1320.7	1320.4	1320.3	1320.0	1321.4	1322.8	1324.2	1325.5	1325.5
162.5°	1333.9	1333.4	1333.1	1332.9	1332.7	1332.5	1333.8	1335.2	1336.6	1338.0	1337.9
165°	1349.6	1349.1	1349.1	1349.1	1349.1	1349.1	1350.9	1352.7	1354.6	1356.4	1356.3
167.5°	1362.7	1362.0	1361.9	1361.7	1361.6	1361.5	1363.5	1365.6	1367.5	1369.6	1369.4
170°	1369.4	1368.9	1369.0	1369.3	1369.5	1369.8	1371.6	1373.4	1375.3	1377.2	1376.9
172.5°	1374.4	1373.8	1374.0	1374.3	1374.5	1374.8	1376.5	1378.4	1380.3	1382.1	1381.8
175°	1379.7	1379.2	1379.4	1379.7	1379.9	1380.1	1382.2	1384.3	1386.3	1388.4	1388.0
177.5°	1382.6	1382.2	1382.5	1382.9	1383.3	1383.7	1385.1	1386.6	1388.0	1389.6	1389.2
180°	1385.3	1385.3	1385.3	1385.3	1385.3	1385.3	1385.3	1385.3	1385.3	1385.3	1385.3



TEST NUMBER: P333009-940

CATALOG NUMBER: S124RDIP-S1195D1205U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1
2.5°	1686.8	1687.9	1683.9	1682.7	1683.9	1687.9	1686.8	1690.1	1690.8	1695.3	1693.6
5°	1564.9	1563.4	1559.9	1560.6	1559.9	1563.4	1564.9	1570.6	1573.4	1584.8	1583.4
7.5°	1460.6	1455.1	1456.6	1451.0	1456.6	1455.1	1460.6	1465.8	1474.4	1479.6	1491.7
10°	1396.9	1389.0	1382.6	1376.9	1382.6	1389.0	1396.9	1399.7	1411.8	1417.5	1429.6
12.5°	1309.7	1303.0	1294.3	1296.0	1294.3	1303.0	1309.7	1322.2	1337.7	1349.7	1368.7
15°	1186.1	1175.5	1158.3	1160.5	1158.3	1175.5	1186.1	1195.3	1211.0	1238.1	1250.9
17.5°	1081.5	1081.6	1073.8	1075.6	1073.8	1081.6	1081.5	1094.1	1102.1	1119.4	1139.0
20°	1027.3	1022.3	1023.1	1020.9	1023.1	1022.3	1027.3	1042.3	1050.9	1062.9	1084.3
22.5°	989.7	983.6	978.7	974.2	978.7	983.6	989.7	993.9	1005.3	1016.8	1034.2
25°	926.2	921.9	915.6	914.2	915.6	921.9	926.2	932.6	938.3	953.3	963.9
27.5°	870.4	869.6	867.0	863.7	867.0	869.6	870.4	876.1	883.5	893.0	906.6
30°	837.9	836.5	835.1	832.9	835.1	836.5	837.9	843.6	849.4	857.2	867.9
32.5°	809.0	808.1	806.6	806.8	806.6	808.1	809.0	811.7	815.2	825.3	833.7
35°	767.5	766.8	765.4	764.6	765.4	766.8	767.5	770.3	772.5	775.3	782.5
37.5°	728.8	730.6	729.8	729.6	729.8	730.6	728.8	729.5	727.2	732.3	737.2
40°	702.0	702.7	704.1	703.4	704.1	702.7	702.0	702.7	702.7	702.7	706.9
42.5°	679.8	679.9	681.9	679.5	681.9	679.9	679.8	677.1	673.7	674.2	675.6
45°	640.1	644.4	643.6	643.6	643.6	644.4	640.1	635.1	634.4	631.5	631.5
47.5°	596.6	600.3	601.3	601.2	601.3	600.3	596.6	594.8	591.5	588.6	588.4
50°	568.1	566.7	568.8	568.1	568.8	566.7	568.1	564.5	559.5	559.5	558.2
52.5°	533.4	533.7	533.5	532.8	533.5	533.7	533.4	531.5	529.4	527.1	526.3
55°	479.8	480.5	479.1	479.8	479.1	480.5	479.8	479.1	479.1	477.7	479.1
57.5°	421.8	418.3	419.7	418.0	419.7	418.3	421.8	424.9	426.1	426.3	428.5
60°	380.2	374.5	373.1	370.2	373.1	374.5	380.2	387.3	390.1	391.6	393.7
62.5°	333.5	329.5	324.7	326.9	324.7	329.5	333.5	341.2	347.4	352.3	357.2
65°	271.3	268.4	266.3	269.1	266.3	268.4	271.3	277.0	282.7	294.0	304.7
67.5°	224.5	223.0	223.0	221.6	223.0	223.0	224.5	227.4	231.0	237.2	247.2
70°	200.1	198.0	198.0	196.5	198.0	198.0	200.1	200.1	203.6	206.4	213.6
72.5°	175.0	172.9	173.4	172.5	173.4	172.9	175.0	175.6	179.1	180.3	183.4
75°	129.6	126.0	126.0	126.7	126.0	126.0	129.6	133.8	137.4	143.8	145.3
77.5°	96.7	95.9	96.9	95.7	96.9	95.9	96.7	96.7	97.4	100.4	102.8
80°	79.0	78.3	77.6	79.7	77.6	78.3	79.0	79.0	79.7	80.4	81.1
82.5°	61.3	61.3	61.1	63.8	61.1	61.3	61.3	62.5	62.7	62.2	63.0
85°	37.0	35.6	37.0	35.6	37.0	35.6	37.0	36.3	37.0	36.3	37.0
87.5°	19.1	18.5	18.1	18.7	18.1	18.5	19.1	17.8	17.7	18.5	17.7
90°	29.7	30.1	30.6	31.1	30.6	30.1	29.7	29.2	28.4	26.9	25.6
92.5°	28.4	28.4	28.5	28.6	28.5	28.4	28.4	28.3	27.5	26.1	24.7
95°	29.3	29.6	29.8	30.1	29.8	29.6	29.3	29.2	28.4	26.9	25.6
97.5°	28.4	28.5	28.8	29.0	28.8	28.5	28.4	28.1	27.9	27.7	27.6
100°	28.4	28.5	28.8	29.0	28.8	28.5	28.4	28.1	30.0	33.9	37.7
102.5°	29.7	29.8	29.8	29.9	29.8	29.8	29.7	29.7	50.7	93.0	135.2
105°	320.1	311.8	303.6	295.3	303.6	311.8	320.1	328.4	331.5	329.5	327.4
107.5°	408.9	409.8	410.6	411.5	410.6	409.8	408.9	408.0	407.1	406.1	405.1
110°	460.0	460.7	461.5	462.1	461.5	460.7	460.0	459.3	458.8	458.3	457.9



TEST NUMBER: P333009-940

CATALOG NUMBER: S124RDIP-S1195D1205U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	510.1	511.0	511.8	512.6	511.8	511.0	510.1	509.2	508.8	508.9	509.0
115°	586.5	586.5	586.5	586.5	586.5	586.5	586.5	586.5	586.2	585.8	585.3
117.5°	661.7	661.6	661.6	661.5	661.6	661.6	661.7	661.8	661.9	662.0	662.1
120°	710.1	709.6	709.2	708.7	709.2	709.6	710.1	710.5	710.5	710.1	709.6
122.5°	756.5	756.1	755.5	755.1	755.5	756.1	756.5	757.0	757.1	756.8	756.5
125°	824.0	824.3	824.6	824.7	824.6	824.3	824.0	823.9	823.4	822.7	822.0
127.5°	886.4	886.3	886.1	885.9	886.1	886.3	886.4	886.6	886.8	886.9	887.1
130°	927.3	927.3	927.3	927.3	927.3	927.3	927.3	927.3	927.2	927.0	926.8
132.5°	966.0	965.8	965.6	965.5	965.6	965.8	966.0	966.2	966.2	966.0	965.7
135°	1021.3	1021.7	1022.2	1022.6	1022.2	1021.7	1021.3	1020.8	1020.4	1019.8	1019.4
137.5°	1072.0	1071.8	1071.7	1071.6	1071.7	1071.8	1072.0	1072.1	1071.9	1071.4	1070.9
140°	1104.8	1105.1	1105.3	1105.5	1105.3	1105.1	1104.8	1104.7	1104.2	1103.5	1102.8
142.5°	1133.6	1133.6	1133.7	1133.7	1133.7	1133.6	1133.6	1133.5	1133.3	1132.7	1132.3
145°	1175.6	1176.1	1176.6	1177.1	1176.6	1176.1	1175.6	1175.2	1174.8	1174.7	1174.4
147.5°	1212.2	1212.5	1212.6	1212.9	1212.6	1212.5	1212.2	1211.9	1211.7	1211.6	1211.4
150°	1235.4	1235.6	1235.9	1236.1	1235.9	1235.6	1235.4	1235.2	1235.0	1235.0	1235.0
152.5°	1256.4	1256.2	1256.2	1256.0	1256.2	1256.2	1256.4	1256.5	1256.4	1256.1	1255.7
155°	1284.8	1284.1	1283.4	1282.7	1283.4	1284.1	1284.8	1285.5	1285.4	1284.4	1283.5
157.5°	1308.7	1307.5	1306.3	1305.1	1306.3	1307.5	1308.7	1309.9	1309.9	1308.7	1307.5
160°	1324.2	1322.8	1321.4	1320.0	1321.4	1322.8	1324.2	1325.5	1325.5	1324.2	1322.8
162.5°	1336.3	1334.8	1333.2	1331.6	1333.2	1334.8	1336.3	1337.9	1338.0	1336.6	1335.2
165°	1354.2	1352.1	1350.1	1348.0	1350.1	1352.1	1354.2	1356.3	1356.4	1354.6	1352.7
167.5°	1367.2	1364.9	1362.5	1360.2	1362.5	1364.9	1367.2	1369.4	1369.6	1367.5	1365.6
170°	1374.6	1372.3	1370.0	1367.7	1370.0	1372.3	1374.6	1376.9	1377.2	1375.3	1373.4
172.5°	1379.3	1376.8	1374.3	1371.8	1374.3	1376.8	1379.3	1381.8	1382.1	1380.3	1378.4
175°	1385.3	1382.5	1379.7	1377.0	1379.7	1382.5	1385.3	1388.0	1388.4	1386.3	1384.3
177.5°	1387.0	1384.7	1382.5	1380.4	1382.5	1384.7	1387.0	1389.2	1389.6	1388.0	1386.6
180°	1385.3	1385.3	1385.3	1385.3	1385.3	1385.3	1385.3	1385.3	1385.3	1385.3	1385.3



TEST NUMBER: P333009-940

CATALOG NUMBER: S124RDIP-S1195D1205U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1
2.5°	1690.1	1694.2	1703.3	1713.5	1722.1	1729.5	1735.2	1743.1	1750.5	1760.8	1770.5
5°	1587.7	1597.6	1611.9	1629.0	1650.3	1664.6	1682.3	1698.0	1720.8	1743.6	1765.7
7.5°	1497.6	1508.6	1529.6	1553.2	1578.5	1601.9	1623.0	1650.6	1680.8	1714.0	1751.0
10°	1439.6	1451.7	1476.6	1503.6	1533.6	1556.3	1584.8	1617.6	1651.7	1692.3	1737.9
12.5°	1387.1	1398.7	1428.7	1456.3	1487.4	1512.4	1545.5	1578.9	1624.4	1668.4	1720.2
15°	1285.0	1315.7	1349.9	1382.6	1419.6	1450.3	1490.1	1524.3	1567.7	1629.7	1688.7
17.5°	1171.7	1204.3	1246.8	1297.4	1347.0	1384.9	1425.3	1467.8	1519.5	1582.7	1650.9
20°	1105.6	1132.0	1179.0	1235.2	1292.9	1345.6	1382.6	1429.6	1483.0	1551.3	1621.8
22.5°	1056.1	1078.4	1115.2	1171.4	1233.7	1294.9	1342.2	1388.6	1447.7	1516.0	1592.8
25°	981.8	1006.0	1038.0	1076.5	1147.6	1212.5	1274.4	1327.8	1390.4	1458.7	1544.2
27.5°	920.0	941.0	970.4	1010.4	1058.3	1129.7	1204.8	1265.7	1329.9	1403.3	1488.8
30°	883.5	900.6	924.8	965.4	1010.9	1075.0	1151.2	1222.4	1287.2	1363.4	1452.4
32.5°	845.3	863.6	887.3	919.3	968.2	1022.1	1098.2	1176.3	1245.1	1322.9	1410.2
35°	794.5	808.8	830.1	862.9	907.0	954.0	1021.6	1102.1	1174.7	1258.0	1341.3
37.5°	743.2	759.9	776.8	805.9	842.1	892.6	948.1	1030.2	1110.6	1186.7	1268.0
40°	714.1	724.1	742.5	766.1	804.5	849.4	901.3	981.8	1062.2	1137.7	1219.6
42.5°	681.6	692.8	708.4	731.9	766.3	810.0	860.9	930.5	1014.4	1087.6	1162.1
45°	636.5	642.9	658.5	678.5	706.9	751.1	798.1	860.1	939.1	1008.8	1074.3
47.5°	590.9	596.5	606.3	624.6	656.4	691.9	735.8	791.4	860.8	930.5	985.9
50°	559.5	564.5	573.8	590.9	619.4	654.2	697.7	747.5	809.5	876.4	922.7
52.5°	528.2	531.0	539.7	559.0	582.9	617.2	656.1	702.0	759.9	815.5	862.3
55°	478.4	484.8	490.5	504.8	527.5	560.3	595.2	638.6	683.5	730.5	770.3
57.5°	426.4	433.5	441.7	454.2	472.3	502.7	534.1	569.3	607.6	646.6	680.0
60°	392.3	398.7	405.8	420.1	436.4	460.7	494.8	525.4	554.6	590.2	623.7
62.5°	358.6	365.1	373.4	384.8	400.6	423.7	452.1	478.8	509.1	540.1	565.0
65°	309.0	314.0	320.4	331.1	346.0	366.7	390.1	410.8	437.8	460.7	483.4
67.5°	254.5	264.0	272.4	281.1	293.7	313.0	329.9	349.7	368.1	385.0	405.8
70°	218.6	229.3	237.1	246.3	258.4	274.8	291.1	304.7	319.7	336.0	354.5
72.5°	188.4	196.8	202.9	212.8	223.7	238.9	254.1	265.4	277.5	288.7	306.7
75°	148.8	152.4	156.7	164.4	174.4	185.8	198.0	207.9	215.0	225.0	237.8
77.5°	106.9	113.8	116.6	122.2	129.3	136.4	144.4	152.8	159.6	163.2	173.0
80°	81.9	84.7	87.6	95.4	99.7	106.8	112.4	120.3	123.1	126.7	136.0
82.5°	63.7	65.4	67.1	69.2	71.8	78.9	84.6	89.5	92.4	93.7	100.7
85°	37.0	37.7	38.4	39.1	39.9	39.9	42.7	46.3	51.3	51.3	53.4
87.5°	17.4	17.7	17.3	16.3	17.1	16.8	16.9	16.4	17.6	18.8	20.0
90°	24.2	22.8	21.0	19.1	17.3	15.4	13.2	10.7	8.2	5.6	3.1
92.5°	23.4	21.9	20.2	18.3	16.4	14.6	13.6	13.5	13.4	13.2	13.0
95°	24.2	22.8	22.6	22.3	22.1	21.8	25.7	33.5	41.3	49.1	57.0
97.5°	27.5	27.4	53.1	78.7	104.4	130.1	140.5	135.6	130.8	125.9	121.0
100°	41.6	45.6	77.4	109.1	140.9	172.7	186.5	182.4	178.3	174.1	170.0
102.5°	177.5	219.6	223.8	227.9	232.1	236.2	236.7	233.7	230.7	227.7	224.6
105°	325.4	323.2	322.1	320.9	319.9	318.7	317.4	316.0	314.6	313.3	311.8
107.5°	404.0	403.1	401.4	399.9	398.3	396.8	395.7	394.9	394.3	393.6	392.9
110°	457.4	456.9	455.6	454.1	452.8	451.4	450.4	449.7	449.0	448.3	447.6



TEST NUMBER: P333009-940

CATALOG NUMBER: S124RDIP-S1195D1205U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	509.1	509.2	508.5	507.8	507.2	506.6	505.6	504.4	503.1	501.9	500.7
115°	584.9	584.3	584.6	584.9	585.1	585.3	585.1	584.3	583.7	583.0	582.3
117.5°	662.2	662.3	661.8	661.3	660.8	660.2	659.5	658.6	657.7	656.7	655.9
120°	709.2	708.7	708.9	709.2	709.4	709.6	709.3	708.4	707.5	706.5	705.6
122.5°	756.3	756.0	755.6	755.3	755.0	754.7	754.2	753.7	753.1	752.6	752.0
125°	821.3	820.6	821.1	821.5	822.0	822.4	822.2	821.3	820.4	819.5	818.5
127.5°	887.2	887.3	886.3	885.2	884.1	883.1	882.4	882.3	882.0	881.7	881.5
130°	926.5	926.3	925.6	924.9	924.3	923.5	923.1	922.8	922.7	922.4	922.1
132.5°	965.5	965.3	964.4	963.5	962.6	961.8	961.1	960.7	960.3	959.8	959.5
135°	1019.0	1018.5	1017.6	1016.6	1015.7	1014.9	1014.5	1014.7	1014.9	1015.2	1015.4
137.5°	1070.4	1069.9	1068.9	1067.9	1066.8	1065.9	1065.3	1065.2	1065.1	1065.1	1065.0
140°	1102.1	1101.4	1100.9	1100.5	1100.0	1099.6	1099.1	1098.7	1098.1	1097.7	1097.3
142.5°	1131.8	1131.2	1131.0	1130.7	1130.4	1130.2	1129.6	1128.7	1127.9	1127.1	1126.2
145°	1174.2	1173.9	1173.9	1173.9	1173.9	1173.9	1173.6	1172.9	1172.2	1171.5	1170.8
147.5°	1211.2	1211.0	1211.2	1211.5	1211.7	1211.9	1211.4	1210.1	1208.8	1207.6	1206.2
150°	1235.0	1235.0	1235.3	1235.6	1235.7	1236.0	1235.6	1234.8	1233.8	1232.9	1232.0
152.5°	1255.4	1255.0	1255.4	1255.8	1256.2	1256.6	1256.4	1255.7	1255.0	1254.3	1253.5
155°	1282.6	1281.7	1282.4	1283.1	1283.8	1284.4	1284.7	1284.4	1284.2	1284.0	1283.8
157.5°	1306.3	1305.1	1305.9	1306.7	1307.4	1308.2	1308.7	1308.9	1308.9	1309.1	1309.2
160°	1321.4	1320.0	1320.3	1320.4	1320.7	1321.0	1321.4	1322.1	1322.8	1323.5	1324.2
162.5°	1333.8	1332.5	1332.7	1332.9	1333.1	1333.4	1333.9	1334.8	1335.7	1336.6	1337.4
165°	1350.9	1349.1	1349.1	1349.1	1349.1	1349.1	1349.6	1350.8	1351.9	1353.1	1354.2
167.5°	1363.5	1361.5	1361.6	1361.7	1361.9	1362.0	1362.7	1363.9	1365.1	1366.3	1367.4
170°	1371.6	1369.8	1369.5	1369.3	1369.0	1368.9	1369.4	1370.8	1372.2	1373.6	1374.9
172.5°	1376.5	1374.8	1374.5	1374.3	1374.0	1373.8	1374.4	1375.7	1377.2	1378.5	1379.9
175°	1382.2	1380.1	1379.9	1379.7	1379.4	1379.2	1379.7	1381.2	1382.5	1383.9	1385.3
177.5°	1385.1	1383.7	1383.3	1382.9	1382.5	1382.2	1382.6	1383.9	1385.2	1386.5	1387.8
180°	1385.3	1385.3	1385.3	1385.3	1385.3	1385.3	1385.3	1385.3	1385.3	1385.3	1385.3



TEST NUMBER: P333009-940

CATALOG NUMBER: S124RDIP-S1195D1205U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1
2.5°	1777.9	1783.0	1788.7	1799.6	1808.7	1812.7	1820.6	1826.3	1824.6	1832.6	1846.2
5°	1784.8	1804.1	1826.1	1849.0	1874.6	1896.0	1913.0	1930.1	1943.7	1960.0	1984.2
7.5°	1783.7	1817.9	1855.0	1896.0	1938.0	1974.2	2007.9	2042.0	2072.3	2105.5	2148.9
10°	1779.1	1824.7	1871.0	1924.4	1977.8	2028.4	2073.9	2116.7	2157.2	2200.7	2255.5
12.5°	1774.1	1826.4	1882.4	1946.6	2013.1	2073.9	2127.4	2189.0	2239.8	2295.8	2359.1
15°	1751.4	1821.9	1898.1	1981.4	2061.1	2143.0	2216.3	2291.8	2362.2	2429.2	2508.9
17.5°	1725.5	1806.8	1896.7	1995.0	2090.9	2190.4	2277.4	2372.5	2444.5	2534.4	2608.4
20°	1704.4	1792.0	1888.1	1998.4	2107.4	2217.7	2313.8	2410.7	2491.8	2582.2	2676.2
22.5°	1678.7	1774.9	1879.0	1993.3	2107.4	2227.9	2334.3	2430.6	2531.1	2633.0	2729.8
25°	1637.4	1737.1	1847.5	1972.8	2103.8	2227.0	2340.9	2460.5	2568.8	2679.1	2765.9
27.5°	1586.8	1691.5	1807.8	1937.1	2071.5	2197.6	2331.8	2459.2	2568.1	2674.3	2750.1
30°	1546.3	1656.7	1768.4	1899.5	2039.0	2174.3	2318.1	2445.5	2560.2	2655.6	2698.3
32.5°	1504.8	1609.4	1724.7	1857.3	2000.3	2145.8	2288.5	2418.8	2524.9	2582.1	2583.2
35°	1432.4	1530.7	1650.3	1780.6	1927.3	2085.3	2229.8	2358.0	2422.8	2427.8	2358.0
37.5°	1353.5	1443.7	1556.6	1687.0	1847.6	2004.8	2152.5	2237.9	2259.6	2187.1	2058.1
40°	1297.2	1380.5	1489.4	1623.3	1782.7	1945.1	2079.6	2142.2	2119.5	2002.0	1858.1
42.5°	1238.0	1315.5	1420.5	1552.6	1712.7	1876.7	1991.4	2024.9	1964.5	1828.9	1660.5
45°	1141.3	1212.5	1316.4	1449.6	1603.3	1757.1	1844.0	1826.8	1726.4	1565.6	1376.9
47.5°	1040.6	1109.4	1202.9	1326.1	1483.5	1616.2	1675.1	1623.5	1480.7	1303.7	1150.2
50°	973.9	1044.5	1130.6	1248.0	1391.9	1520.0	1557.7	1479.4	1320.6	1150.5	1009.5
52.5°	908.5	968.7	1053.1	1166.6	1304.1	1412.4	1432.4	1342.2	1178.3	1025.7	900.7
55°	808.8	863.6	934.8	1041.6	1160.5	1252.3	1241.6	1125.6	976.8	846.5	748.2
57.5°	712.4	753.7	819.5	919.5	1024.0	1085.6	1046.6	947.6	809.0	702.3	619.4
60°	648.6	687.1	748.2	835.8	927.6	962.5	929.8	822.3	712.7	615.1	545.4
62.5°	588.2	622.1	674.8	756.1	830.3	851.0	815.9	722.0	623.2	539.9	482.1
65°	500.5	531.8	576.7	634.4	685.6	695.5	672.8	576.7	501.9	432.1	392.3
67.5°	420.9	441.4	476.4	526.3	553.5	559.3	515.3	455.0	389.1	346.2	316.1
70°	367.4	381.6	414.4	441.4	463.5	464.2	423.7	375.2	324.7	289.8	267.7
72.5°	315.6	329.2	354.0	372.5	389.4	383.9	346.7	308.5	267.7	241.4	225.0
75°	243.5	255.6	268.4	277.0	277.0	269.8	242.8	214.3	190.8	175.1	170.1
77.5°	177.0	187.0	191.3	189.9	187.3	176.3	159.2	140.5	132.2	124.8	121.0
80°	138.8	143.1	144.5	141.0	136.7	123.9	112.4	104.7	96.8	94.0	92.6
82.5°	102.9	106.6	102.9	104.0	94.5	84.0	77.8	75.1	71.8	70.6	69.2
85°	54.8	54.1	52.7	49.1	42.7	41.3	40.6	39.9	38.4	39.1	37.7
87.5°	19.9	18.7	16.9	16.9	17.3	16.6	17.5	17.8	18.2	17.9	19.4
90°	5.6	8.2	10.7	13.2	15.4	17.3	19.1	21.0	22.8	24.2	25.6
92.5°	13.2	13.4	13.5	13.6	14.6	16.4	18.3	20.2	21.9	23.4	24.7
95°	49.1	41.3	33.5	25.7	21.8	22.1	22.3	22.6	22.8	24.2	25.6
97.5°	125.9	130.8	135.6	140.5	130.1	104.4	78.7	53.1	27.4	27.5	27.6
100°	174.1	178.3	182.4	186.5	172.7	140.9	109.1	77.4	45.6	41.6	37.7
102.5°	227.7	230.7	233.7	236.7	236.2	232.1	227.9	223.8	219.6	177.5	135.2
105°	313.3	314.6	316.0	317.4	318.7	319.9	320.9	322.1	323.2	325.4	327.4
107.5°	393.6	394.3	394.9	395.7	396.8	398.3	399.9	401.4	403.1	404.0	405.1
110°	448.3	449.0	449.7	450.4	451.4	452.8	454.1	455.6	456.9	457.4	457.9



TEST NUMBER: P333009-940

CATALOG NUMBER: S124RDIP-S1195D1205U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	501.9	503.1	504.4	505.6	506.6	507.2	507.8	508.5	509.2	509.1	509.0
115°	583.0	583.7	584.3	585.1	585.3	585.1	584.9	584.6	584.3	584.9	585.3
117.5°	656.7	657.7	658.6	659.5	660.2	660.8	661.3	661.8	662.3	662.2	662.1
120°	706.5	707.5	708.4	709.3	709.6	709.4	709.2	708.9	708.7	709.2	709.6
122.5°	752.6	753.1	753.7	754.2	754.7	755.0	755.3	755.6	756.0	756.3	756.5
125°	819.5	820.4	821.3	822.2	822.4	822.0	821.5	821.1	820.6	821.3	822.0
127.5°	881.7	882.0	882.3	882.4	883.1	884.1	885.2	886.3	887.3	887.2	887.1
130°	922.4	922.7	922.8	923.1	923.5	924.3	924.9	925.6	926.3	926.5	926.8
132.5°	959.8	960.3	960.7	961.1	961.8	962.6	963.5	964.4	965.3	965.5	965.7
135°	1015.2	1014.9	1014.7	1014.5	1014.9	1015.7	1016.6	1017.6	1018.5	1019.0	1019.4
137.5°	1065.1	1065.1	1065.2	1065.3	1065.9	1066.8	1067.9	1068.9	1069.9	1070.4	1070.9
140°	1097.7	1098.1	1098.7	1099.1	1099.6	1100.0	1100.5	1100.9	1101.4	1102.1	1102.8
142.5°	1127.1	1127.9	1128.7	1129.6	1130.2	1130.4	1130.7	1131.0	1131.2	1131.8	1132.3
145°	1171.5	1172.2	1172.9	1173.6	1173.9	1173.9	1173.9	1173.9	1173.9	1174.2	1174.4
147.5°	1207.6	1208.8	1210.1	1211.4	1211.9	1211.7	1211.5	1211.2	1211.0	1211.2	1211.4
150°	1232.9	1233.8	1234.8	1235.6	1236.0	1235.7	1235.6	1235.3	1235.0	1235.0	1235.0
152.5°	1254.3	1255.0	1255.7	1256.4	1256.6	1256.2	1255.8	1255.4	1255.0	1255.4	1255.7
155°	1284.0	1284.2	1284.4	1284.7	1284.4	1283.8	1283.1	1282.4	1281.7	1282.6	1283.5
157.5°	1309.1	1308.9	1308.9	1308.7	1308.2	1307.4	1306.7	1305.9	1305.1	1306.3	1307.5
160°	1323.5	1322.8	1322.1	1321.4	1321.0	1320.7	1320.4	1320.3	1320.0	1321.4	1322.8
162.5°	1336.6	1335.7	1334.8	1333.9	1333.4	1333.1	1332.9	1332.7	1332.5	1333.8	1335.2
165°	1353.1	1351.9	1350.8	1349.6	1349.1	1349.1	1349.1	1349.1	1349.1	1350.9	1352.7
167.5°	1366.3	1365.1	1363.9	1362.7	1362.0	1361.9	1361.7	1361.6	1361.5	1363.5	1365.6
170°	1373.6	1372.2	1370.8	1369.4	1368.9	1369.0	1369.3	1369.5	1369.8	1371.6	1373.4
172.5°	1378.5	1377.2	1375.7	1374.4	1373.8	1374.0	1374.3	1374.5	1374.8	1376.5	1378.4
175°	1383.9	1382.5	1381.2	1379.7	1379.2	1379.4	1379.7	1379.9	1380.1	1382.2	1384.3
177.5°	1386.5	1385.2	1383.9	1382.6	1382.2	1382.5	1382.9	1383.3	1383.7	1385.1	1386.6
180°	1385.3	1385.3	1385.3	1385.3	1385.3	1385.3	1385.3	1385.3	1385.3	1385.3	1385.3



TEST NUMBER: P333009-940

CATALOG NUMBER: S124RDIP-S1195D1205U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1
2.5°	1853.6	1855.9	1857.6	1863.3	1863.9	1869.0	1863.9
5°	2007.0	2017.0	2032.7	2048.3	2049.7	2059.7	2041.8
7.5°	2179.0	2202.1	2216.4	2241.8	2251.7	2258.0	2247.7
10°	2297.5	2318.8	2356.5	2375.1	2393.6	2396.4	2387.9
12.5°	2412.0	2445.9	2475.6	2510.6	2509.8	2534.9	2525.7
15°	2564.5	2599.3	2640.6	2679.8	2694.0	2694.0	2705.5
17.5°	2673.3	2737.2	2779.9	2810.7	2844.2	2850.1	2846.1
20°	2746.7	2815.8	2861.3	2901.2	2924.0	2930.4	2930.4
22.5°	2801.4	2860.2	2904.7	2940.5	2959.3	2966.8	2964.6
25°	2839.3	2889.8	2916.9	2927.6	2932.5	2931.1	2917.6
27.5°	2787.4	2785.2	2768.0	2735.3	2710.7	2695.7	2678.6
30°	2688.3	2651.3	2608.6	2561.6	2501.1	2454.8	2440.5
32.5°	2540.8	2457.6	2385.3	2307.0	2241.9	2195.7	2176.3
35°	2255.5	2123.8	2016.2	1922.3	1854.0	1811.2	1797.0
37.5°	1916.8	1789.4	1656.3	1565.1	1508.5	1465.3	1449.2
40°	1701.6	1562.7	1446.7	1361.3	1302.9	1260.9	1260.2
42.5°	1505.0	1372.5	1263.3	1201.8	1138.8	1111.1	1110.9
45°	1232.3	1126.3	1033.8	985.3	947.6	924.8	918.4
47.5°	1020.4	932.6	871.0	832.4	801.6	787.1	777.8
50°	901.3	824.5	775.3	741.8	724.8	706.2	704.8
52.5°	802.2	740.1	701.9	674.7	653.0	641.9	642.2
55°	674.2	625.1	598.1	577.4	560.3	551.8	548.2
57.5°	568.0	531.1	511.5	492.5	485.3	478.6	476.7
60°	501.9	477.0	458.5	443.5	432.8	430.7	430.0
62.5°	447.3	421.2	408.4	396.8	389.1	385.8	384.4
65°	368.8	349.6	338.1	329.0	326.1	321.1	320.4
67.5°	297.3	285.8	278.2	271.8	268.0	267.7	267.7
70°	253.4	247.0	240.7	237.1	235.0	233.5	233.5
72.5°	215.9	211.2	205.9	204.0	203.6	202.2	201.6
75°	164.4	159.4	160.2	156.7	153.8	150.3	148.1
77.5°	116.6	113.1	112.4	111.9	109.5	109.1	110.2
80°	90.4	86.9	86.1	86.9	86.1	84.0	84.0
82.5°	68.8	65.8	65.1	64.6	63.9	64.6	63.5
85°	37.0	35.6	35.6	35.6	37.0	36.3	35.6
87.5°	18.5	18.2	18.9	18.5	18.5	18.1	18.7
90°	26.9	28.4	29.2	29.7	30.1	30.6	31.1
92.5°	26.1	27.5	28.3	28.4	28.4	28.5	28.6
95°	26.9	28.4	29.2	29.3	29.6	29.8	30.1
97.5°	27.7	27.9	28.1	28.4	28.5	28.8	29.0
100°	33.9	30.0	28.1	28.4	28.5	28.8	29.0
102.5°	93.0	50.7	29.7	29.7	29.8	29.8	29.9
105°	329.5	331.5	328.4	320.1	311.8	303.6	295.3
107.5°	406.1	407.1	408.0	408.9	409.8	410.6	411.5
110°	458.3	458.8	459.3	460.0	460.7	461.5	462.1



TEST NUMBER: P333009-940

CATALOG NUMBER: S124RDIP-S1195D1205U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	508.9	508.8	509.2	510.1	511.0	511.8	512.6
115°	585.8	586.2	586.5	586.5	586.5	586.5	586.5
117.5°	662.0	661.9	661.8	661.7	661.6	661.6	661.5
120°	710.1	710.5	710.5	710.1	709.6	709.2	708.7
122.5°	756.8	757.1	757.0	756.5	756.1	755.5	755.1
125°	822.7	823.4	823.9	824.0	824.3	824.6	824.7
127.5°	886.9	886.8	886.6	886.4	886.3	886.1	885.9
130°	927.0	927.2	927.3	927.3	927.3	927.3	927.3
132.5°	966.0	966.2	966.2	966.0	965.8	965.6	965.5
135°	1019.8	1020.4	1020.8	1021.3	1021.7	1022.2	1022.6
137.5°	1071.4	1071.9	1072.1	1072.0	1071.8	1071.7	1071.6
140°	1103.5	1104.2	1104.7	1104.8	1105.1	1105.3	1105.5
142.5°	1132.7	1133.3	1133.5	1133.6	1133.6	1133.7	1133.7
145°	1174.7	1174.8	1175.2	1175.6	1176.1	1176.6	1177.1
147.5°	1211.6	1211.7	1211.9	1212.2	1212.5	1212.6	1212.9
150°	1235.0	1235.0	1235.2	1235.4	1235.6	1235.9	1236.1
152.5°	1256.1	1256.4	1256.5	1256.4	1256.2	1256.2	1256.0
155°	1284.4	1285.4	1285.5	1284.8	1284.1	1283.4	1282.7
157.5°	1308.7	1309.9	1309.9	1308.7	1307.5	1306.3	1305.1
160°	1324.2	1325.5	1325.5	1324.2	1322.8	1321.4	1320.0
162.5°	1336.6	1338.0	1337.9	1336.3	1334.8	1333.2	1331.6
165°	1354.6	1356.4	1356.3	1354.2	1352.1	1350.1	1348.0
167.5°	1367.5	1369.6	1369.4	1367.2	1364.9	1362.5	1360.2
170°	1375.3	1377.2	1376.9	1374.6	1372.3	1370.0	1367.7
172.5°	1380.3	1382.1	1381.8	1379.3	1376.8	1374.3	1371.8
175°	1386.3	1388.4	1388.0	1385.3	1382.5	1379.7	1377.0
177.5°	1388.0	1389.6	1389.2	1387.0	1384.7	1382.5	1380.4
180°	1385.3	1385.3	1385.3	1385.3	1385.3	1385.3	1385.3

(END OF REPORT)