

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332985-940

Luminaire Tested: **S124RDIP-S1195D365U940-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332985-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIP-S1195D365U940-4F0-1E-UDD-A
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1195 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 365 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5771.3 lumens
Efficiency: N/A
Efficacy: 115.9 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 49.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332985-940

CATALOG NUMBER: S124RDIP-S1195D365U940-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P332985-940

CATALOG NUMBER: S124RDIP-S1195D365U940-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	114	114	114	114	108	108	108	108	99	99	99	90	90	90	81	81	81	77
1	105	100	97	93	100	96	93	90	88	85	83	80	78	76	73	72	70	67
2	96	89	83	77	91	85	79	75	78	73	70	71	68	65	65	63	60	57
3	88	79	71	65	84	75	69	63	69	64	59	64	59	56	58	55	52	49
4	81	70	62	56	77	67	60	54	62	56	51	57	52	48	53	49	45	43
5	75	63	55	49	71	60	53	47	56	50	45	52	46	42	48	43	40	37
6	69	57	49	43	66	55	47	42	51	44	40	47	42	37	43	39	35	33
7	64	52	44	38	61	50	42	37	46	40	35	43	37	33	40	35	32	30
8	60	47	39	34	57	45	38	33	42	36	32	39	34	30	37	32	29	27
9	56	43	36	30	53	42	35	30	39	33	29	36	31	27	34	29	26	24
10	52	40	33	28	50	39	32	27	36	30	26	34	29	25	32	27	24	22

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	14266	14266	14266	14266
5°	16546	14309	12647	14309
10°	19575	14246	11287	14246
15°	22612	14114	9699	14114
20°	25175	13933	8771	13933
25°	25989	13755	8143	13755
30°	22750	13539	7764	13539
35°	17710	13219	7535	13219
40°	13281	12853	7413	12853
45°	10485	12265	7348	12265
50°	8852	11588	7135	11588
55°	7716	10842	6753	10842
60°	6943	10070	5977	10070
65°	6120	9234	5140	9234
70°	5511	8368	4638	8368
75°	4619	7417	3952	7417
80°	3905	6323	3705	6323
85°	3298	4946	3298	4946



TEST NUMBER: P332985-940

CATALOG NUMBER: S124RDIP-S1195D365U940-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	171.2	3.0
10°-20°	516.5	8.9
20°-30°	807.8	14.0
30°-40°	898.0	15.6
40°-50°	796.7	13.8
50°-60°	620.8	10.8
60°-70°	406.5	7.0
70°-80°	199.9	3.5
80°-90°	50.5	0.9
90°-100°	14.4	0.2
100°-110°	91.9	1.6
110°-120°	175.8	3.0
120°-130°	223.1	3.9
130°-140°	238.7	4.1
140°-150°	223.2	3.9
150°-160°	180.0	3.1
160°-170°	116.1	2.0
170°-180°	40.0	0.7
0°-30°	1495.5	25.9
0°-40°	2393.5	41.5
0°-60°	3811.0	66.0
0°-90°	4467.9	77.4
90°-120°	282.1	4.9
90°-150°	967.2	16.8
90°-180°	1303.0	22.6
0°-180°	5771.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1767	1767	1767	1767	1767	
5°	2042	1766	1561	1766	2042	207
15°	2706	1689	1160	1689	2706	769
25°	2918	1544	914	1544	2918	1294
35°	1797	1341	765	1341	1797	1126
45°	918	1074	644	1074	918	727
55°	548	770	480	770	548	499
65°	320	483	269	483	320	322
75°	148	238	127	238	148	163
85°	36	53	36	53	36	40
90°	10	1	10	1	10	6
95°	9	17	9	17	9	7
105°	90	95	90	95	90	78
115°	178	177	178	177	178	177
125°	251	249	251	249	251	223
135°	311	309	311	309	311	239
145°	358	356	358	356	358	224
155°	390	390	390	390	390	180
165°	410	412	410	412	410	116
175°	419	421	419	421	419	40
180°	421	421	421	421	421	



TEST NUMBER: P332985-940

CATALOG NUMBER: S124RDIP-S1195D365U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1
2.5°	1863.9	1869.0	1863.9	1863.3	1857.6	1855.9	1853.6	1846.2	1832.6	1824.6	1826.3
5°	2041.8	2059.7	2049.7	2048.3	2032.7	2017.0	2007.0	1984.2	1960.0	1943.7	1930.1
7.5°	2247.7	2258.0	2251.7	2241.8	2216.4	2202.1	2179.0	2148.9	2105.5	2072.3	2042.0
10°	2387.9	2396.4	2393.6	2375.1	2356.5	2318.8	2297.5	2255.5	2200.7	2157.2	2116.7
12.5°	2525.7	2534.9	2509.8	2510.6	2475.6	2445.9	2412.0	2359.1	2295.8	2239.8	2189.0
15°	2705.5	2694.0	2694.0	2679.8	2640.6	2599.3	2564.5	2508.9	2429.2	2362.2	2291.8
17.5°	2846.1	2850.1	2844.2	2810.7	2779.9	2737.2	2673.3	2608.4	2534.4	2444.5	2372.5
20°	2930.4	2930.4	2924.0	2901.2	2861.3	2815.8	2746.7	2676.2	2582.2	2491.8	2410.7
22.5°	2964.6	2966.8	2959.3	2940.5	2904.7	2860.2	2801.4	2729.8	2633.0	2531.1	2430.6
25°	2917.6	2931.1	2932.5	2927.6	2916.9	2889.8	2839.3	2765.9	2679.1	2568.8	2460.5
27.5°	2678.6	2695.7	2710.7	2735.3	2768.0	2785.2	2787.4	2750.1	2674.3	2568.1	2459.2
30°	2440.5	2454.8	2501.1	2561.6	2608.6	2651.3	2688.3	2698.3	2655.6	2560.2	2445.5
32.5°	2176.3	2195.7	2241.9	2307.0	2385.3	2457.6	2540.8	2583.2	2582.1	2524.9	2418.8
35°	1797.0	1811.2	1854.0	1922.3	2016.2	2123.8	2255.5	2358.0	2427.8	2422.8	2358.0
37.5°	1449.2	1465.3	1508.5	1565.1	1656.3	1789.4	1916.8	2058.1	2187.1	2259.6	2237.9
40°	1260.2	1260.9	1302.9	1361.3	1446.7	1562.7	1701.6	1858.1	2002.0	2119.5	2142.2
42.5°	1110.9	1111.1	1138.8	1201.8	1263.3	1372.5	1505.0	1660.5	1828.9	1964.5	2024.9
45°	918.4	924.8	947.6	985.3	1033.8	1126.3	1232.3	1376.9	1565.6	1726.4	1826.8
47.5°	777.8	787.1	801.6	832.4	871.0	932.6	1020.4	1150.2	1303.7	1480.7	1623.5
50°	704.8	706.2	724.8	741.8	775.3	824.5	901.3	1009.5	1150.5	1320.6	1479.4
52.5°	642.2	641.9	653.0	674.7	701.9	740.1	802.2	900.7	1025.7	1178.3	1342.2
55°	548.2	551.8	560.3	577.4	598.1	625.1	674.2	748.2	846.5	976.8	1125.6
57.5°	476.7	478.6	485.3	492.5	511.5	531.1	568.0	619.4	702.3	809.0	947.6
60°	430.0	430.7	432.8	443.5	458.5	477.0	501.9	545.4	615.1	712.7	822.3
62.5°	384.4	385.8	389.1	396.8	408.4	421.2	447.3	482.1	539.9	623.2	722.0
65°	320.4	321.1	326.1	329.0	338.1	349.6	368.8	392.3	432.1	501.9	576.7
67.5°	267.7	267.7	268.0	271.8	278.2	285.8	297.3	316.1	346.2	389.1	455.0
70°	233.5	233.5	235.0	237.1	240.7	247.0	253.4	267.7	289.8	324.7	375.2
72.5°	201.6	202.2	203.6	204.0	205.9	211.2	215.9	225.0	241.4	267.7	308.5
75°	148.1	150.3	153.8	156.7	160.2	159.4	164.4	170.1	175.1	190.8	214.3
77.5°	110.2	109.1	109.5	111.9	112.4	113.1	116.6	121.0	124.8	132.2	140.5
80°	84.0	84.0	86.1	86.9	86.1	86.9	90.4	92.6	94.0	96.8	104.7
82.5°	63.5	64.6	63.9	64.6	65.1	65.8	68.8	69.2	70.6	71.8	75.1
85°	35.6	36.3	37.0	35.6	35.6	35.6	37.0	37.7	39.1	38.4	39.9
87.5°	14.4	13.8	14.4	14.4	14.9	14.3	14.7	15.8	14.5	15.1	15.0
90°	9.5	9.3	9.2	9.0	8.9	8.6	8.2	7.8	7.3	7.0	6.3
92.5°	8.7	8.6	8.6	8.6	8.6	8.4	7.9	7.5	7.1	6.7	6.2
95°	9.1	9.1	9.0	8.9	8.8	8.6	8.2	7.8	7.3	7.0	6.9
97.5°	8.8	8.7	8.6	8.6	8.6	8.5	8.5	8.4	8.4	8.3	16.1
100°	8.8	8.7	8.6	8.6	8.6	9.1	10.3	11.5	12.7	13.9	23.5
102.5°	9.1	9.1	9.0	9.0	9.0	15.4	28.3	41.1	53.9	66.8	68.0
105°	89.8	92.3	94.9	97.4	99.9	100.9	100.2	99.6	99.0	98.4	98.0
107.5°	125.2	124.9	124.7	124.4	124.1	123.9	123.5	123.2	122.9	122.6	122.1
110°	140.5	140.4	140.2	139.9	139.7	139.6	139.4	139.3	139.1	139.0	138.6



TEST NUMBER: P332985-940

CATALOG NUMBER: S124RDIP-S1195D365U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	156.0	155.7	155.4	155.2	154.9	154.7	154.8	154.8	154.8	154.9	154.6
115°	178.3	178.3	178.3	178.3	178.3	178.3	178.2	178.0	177.9	177.7	177.8
117.5°	201.2	201.3	201.3	201.3	201.3	201.3	201.3	201.3	201.4	201.4	201.3
120°	215.5	215.7	215.8	216.0	216.2	216.2	216.0	215.8	215.7	215.5	215.6
122.5°	229.7	229.8	230.0	230.1	230.2	230.2	230.2	230.1	230.0	230.0	229.8
125°	250.8	250.7	250.7	250.7	250.6	250.4	250.2	250.0	249.8	249.6	249.8
127.5°	269.5	269.5	269.6	269.7	269.7	269.7	269.7	269.8	269.8	269.9	269.6
130°	282.0	282.0	282.0	282.0	282.0	282.0	282.0	281.9	281.8	281.8	281.5
132.5°	293.6	293.7	293.7	293.8	293.9	293.9	293.8	293.7	293.6	293.6	293.3
135°	311.0	310.9	310.8	310.6	310.5	310.3	310.2	310.0	310.0	309.8	309.5
137.5°	325.9	325.9	326.0	326.0	326.1	326.0	325.9	325.7	325.6	325.4	325.1
140°	336.3	336.2	336.1	336.1	336.0	335.8	335.6	335.4	335.2	335.0	334.8
142.5°	344.8	344.8	344.8	344.8	344.7	344.6	344.6	344.4	344.2	344.1	344.0
145°	358.0	357.8	357.8	357.6	357.4	357.3	357.3	357.2	357.1	357.0	357.0
147.5°	368.9	368.8	368.7	368.7	368.6	368.5	368.5	368.5	368.4	368.4	368.4
150°	375.9	375.9	375.9	375.8	375.7	375.7	375.7	375.7	375.7	375.7	375.7
152.5°	382.0	382.1	382.1	382.1	382.2	382.2	382.0	381.9	381.8	381.7	381.8
155°	390.1	390.4	390.6	390.7	391.0	390.9	390.7	390.4	390.1	389.9	390.0
157.5°	397.0	397.3	397.7	398.1	398.4	398.4	398.1	397.7	397.3	397.0	397.2
160°	401.4	401.9	402.3	402.8	403.1	403.1	402.8	402.3	401.9	401.4	401.5
162.5°	405.0	405.5	406.0	406.4	406.9	407.0	406.5	406.1	405.7	405.3	405.4
165°	410.0	410.6	411.3	411.9	412.5	412.6	412.0	411.4	410.9	410.3	410.3
167.5°	413.8	414.4	415.1	415.8	416.5	416.5	416.0	415.4	414.7	414.1	414.1
170°	416.0	416.7	417.4	418.1	418.7	418.8	418.3	417.8	417.1	416.6	416.5
172.5°	417.2	418.0	418.7	419.5	420.3	420.4	419.8	419.3	418.7	418.1	418.0
175°	418.8	419.6	420.5	421.3	422.2	422.3	421.7	421.1	420.4	419.7	419.7
177.5°	419.8	420.5	421.2	421.9	422.5	422.7	422.2	421.8	421.3	420.8	420.7
180°	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3



TEST NUMBER: P332985-940

CATALOG NUMBER: S124RDIP-S1195D365U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1
2.5°	1820.6	1812.7	1808.7	1799.6	1788.7	1783.0	1777.9	1770.5	1760.8	1750.5	1743.1
5°	1913.0	1896.0	1874.6	1849.0	1826.1	1804.1	1784.8	1765.7	1743.6	1720.8	1698.0
7.5°	2007.9	1974.2	1938.0	1896.0	1855.0	1817.9	1783.7	1751.0	1714.0	1680.8	1650.6
10°	2073.9	2028.4	1977.8	1924.4	1871.0	1824.7	1779.1	1737.9	1692.3	1651.7	1617.6
12.5°	2127.4	2073.9	2013.1	1946.6	1882.4	1826.4	1774.1	1720.2	1668.4	1624.4	1578.9
15°	2216.3	2143.0	2061.1	1981.4	1898.1	1821.9	1751.4	1688.7	1629.7	1567.7	1524.3
17.5°	2277.4	2190.4	2090.9	1995.0	1896.7	1806.8	1725.5	1650.9	1582.7	1519.5	1467.8
20°	2313.8	2217.7	2107.4	1998.4	1888.1	1792.0	1704.4	1621.8	1551.3	1483.0	1429.6
22.5°	2334.3	2227.9	2107.4	1993.3	1879.0	1774.9	1678.7	1592.8	1516.0	1447.7	1388.6
25°	2340.9	2227.0	2103.8	1972.8	1847.5	1737.1	1637.4	1544.2	1458.7	1390.4	1327.8
27.5°	2331.8	2197.6	2071.5	1937.1	1807.8	1691.5	1586.8	1488.8	1403.3	1329.9	1265.7
30°	2318.1	2174.3	2039.0	1899.5	1768.4	1656.7	1546.3	1452.4	1363.4	1287.2	1222.4
32.5°	2288.5	2145.8	2000.3	1857.3	1724.7	1609.4	1504.8	1410.2	1322.9	1245.1	1176.3
35°	2229.8	2085.3	1927.3	1780.6	1650.3	1530.7	1432.4	1341.3	1258.0	1174.7	1102.1
37.5°	2152.5	2004.8	1847.6	1687.0	1556.6	1443.7	1353.5	1268.0	1186.7	1110.6	1030.2
40°	2079.6	1945.1	1782.7	1623.3	1489.4	1380.5	1297.2	1219.6	1137.7	1062.2	981.8
42.5°	1991.4	1876.7	1712.7	1552.6	1420.5	1315.5	1238.0	1162.1	1087.6	1014.4	930.5
45°	1844.0	1757.1	1603.3	1449.6	1316.4	1212.5	1141.3	1074.3	1008.8	939.1	860.1
47.5°	1675.1	1616.2	1483.5	1326.1	1202.9	1109.4	1040.6	985.9	930.5	860.8	791.4
50°	1557.7	1520.0	1391.9	1248.0	1130.6	1044.5	973.9	922.7	876.4	809.5	747.5
52.5°	1432.4	1412.4	1304.1	1166.6	1053.1	968.7	908.5	862.3	815.5	759.9	702.0
55°	1241.6	1252.3	1160.5	1041.6	934.8	863.6	808.8	770.3	730.5	683.5	638.6
57.5°	1046.6	1085.6	1024.0	919.5	819.5	753.7	712.4	680.0	646.6	607.6	569.3
60°	929.8	962.5	927.6	835.8	748.2	687.1	648.6	623.7	590.2	554.6	525.4
62.5°	815.9	851.0	830.3	756.1	674.8	622.1	588.2	565.0	540.1	509.1	478.8
65°	672.8	695.5	685.6	634.4	576.7	531.8	500.5	483.4	460.7	437.8	410.8
67.5°	515.3	559.3	553.5	526.3	476.4	441.4	420.9	405.8	385.0	368.1	349.7
70°	423.7	464.2	463.5	441.4	414.4	381.6	367.4	354.5	336.0	319.7	304.7
72.5°	346.7	383.9	389.4	372.5	354.0	329.2	315.6	306.7	288.7	277.5	265.4
75°	242.8	269.8	277.0	277.0	268.4	255.6	243.5	237.8	225.0	215.0	207.9
77.5°	159.2	176.3	187.3	189.9	191.3	187.0	177.0	173.0	163.2	159.6	152.8
80°	112.4	123.9	136.7	141.0	144.5	143.1	138.8	136.0	126.7	123.1	120.3
82.5°	77.8	84.0	94.5	104.0	102.9	106.6	102.9	100.7	93.7	92.4	89.5
85°	40.6	41.3	42.7	49.1	52.7	54.1	54.8	53.4	51.3	51.3	46.3
87.5°	14.8	14.2	15.2	15.1	15.4	17.6	19.2	19.5	18.0	16.4	14.9
90°	5.8	5.3	4.7	4.0	3.3	2.5	1.7	1.0	1.7	2.5	3.3
92.5°	5.5	5.0	4.5	4.1	4.1	4.0	4.0	4.0	4.0	4.0	4.1
95°	6.8	6.7	6.7	7.8	10.2	12.6	15.0	17.3	15.0	12.6	10.2
97.5°	24.0	31.7	39.6	42.7	41.3	39.8	38.3	36.8	38.3	39.8	41.3
100°	33.2	42.9	52.5	56.7	55.5	54.2	53.0	51.7	53.0	54.2	55.5
102.5°	69.4	70.6	71.9	72.1	71.1	70.2	69.3	68.3	69.3	70.2	71.1
105°	97.6	97.3	96.9	96.6	96.1	95.7	95.2	94.9	95.2	95.7	96.1
107.5°	121.6	121.2	120.6	120.4	120.1	119.9	119.7	119.5	119.7	119.9	120.1
110°	138.1	137.7	137.3	137.0	136.8	136.5	136.3	136.2	136.3	136.5	136.8



TEST NUMBER: P332985-940

CATALOG NUMBER: S124RDIP-S1195D365U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	154.4	154.3	154.1	153.8	153.4	153.0	152.7	152.3	152.7	153.0	153.4
115°	177.9	178.0	178.0	178.0	177.7	177.5	177.4	177.1	177.4	177.5	177.7
117.5°	201.2	201.0	200.8	200.6	200.4	200.0	199.7	199.5	199.7	200.0	200.4
120°	215.7	215.8	215.8	215.7	215.4	215.2	214.9	214.6	214.9	215.2	215.4
122.5°	229.7	229.6	229.5	229.4	229.3	229.1	228.9	228.7	228.9	229.1	229.3
125°	249.9	250.0	250.1	250.1	249.8	249.5	249.2	249.0	249.2	249.5	249.8
127.5°	269.2	268.9	268.6	268.4	268.3	268.2	268.2	268.1	268.2	268.2	268.3
130°	281.3	281.1	280.9	280.8	280.7	280.6	280.5	280.4	280.5	280.6	280.7
132.5°	293.0	292.7	292.5	292.3	292.2	292.0	291.9	291.9	291.9	292.0	292.2
135°	309.2	309.0	308.6	308.5	308.6	308.7	308.8	308.8	308.8	308.7	308.6
137.5°	324.8	324.5	324.2	324.0	324.0	324.0	324.0	323.9	324.0	324.0	324.0
140°	334.7	334.6	334.4	334.3	334.1	334.0	333.9	333.8	333.9	334.0	334.1
142.5°	343.9	343.8	343.8	343.6	343.3	343.0	342.8	342.6	342.8	343.0	343.3
145°	357.0	357.0	357.0	357.0	356.8	356.5	356.3	356.1	356.3	356.5	356.8
147.5°	368.5	368.5	368.6	368.5	368.1	367.7	367.3	366.8	367.3	367.7	368.1
150°	375.8	375.9	375.9	375.9	375.6	375.2	375.0	374.7	375.0	375.2	375.6
152.5°	381.9	382.1	382.2	382.2	381.9	381.7	381.5	381.3	381.5	381.7	381.9
155°	390.2	390.5	390.7	390.7	390.7	390.6	390.6	390.5	390.6	390.6	390.7
157.5°	397.4	397.7	397.9	398.1	398.1	398.1	398.1	398.2	398.1	398.1	398.1
160°	401.6	401.7	401.8	401.9	402.2	402.3	402.5	402.8	402.5	402.3	402.2
162.5°	405.4	405.5	405.6	405.7	406.0	406.3	406.5	406.8	406.5	406.3	406.0
165°	410.3	410.3	410.3	410.5	410.8	411.2	411.5	411.9	411.5	411.2	410.8
167.5°	414.2	414.2	414.3	414.5	414.8	415.2	415.5	415.9	415.5	415.2	414.8
170°	416.5	416.4	416.3	416.5	417.0	417.3	417.8	418.2	417.8	417.3	417.0
172.5°	418.0	417.9	417.9	418.0	418.5	418.8	419.3	419.7	419.3	418.8	418.5
175°	419.6	419.5	419.5	419.6	420.1	420.5	420.9	421.3	420.9	420.5	420.1
177.5°	420.6	420.5	420.4	420.5	420.9	421.3	421.7	422.1	421.7	421.3	420.9
180°	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3



TEST NUMBER: P332985-940

CATALOG NUMBER: S124RDIP-S1195D365U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1
2.5°	1735.2	1729.5	1722.1	1713.5	1703.3	1694.2	1690.1	1693.6	1695.3	1690.8	1690.1
5°	1682.3	1664.6	1650.3	1629.0	1611.9	1597.6	1587.7	1583.4	1584.8	1573.4	1570.6
7.5°	1623.0	1601.9	1578.5	1553.2	1529.6	1508.6	1497.6	1491.7	1479.6	1474.4	1465.8
10°	1584.8	1556.3	1533.6	1503.6	1476.6	1451.7	1439.6	1429.6	1417.5	1411.8	1399.7
12.5°	1545.5	1512.4	1487.4	1456.3	1428.7	1398.7	1387.1	1368.7	1349.7	1337.7	1322.2
15°	1490.1	1450.3	1419.6	1382.6	1349.9	1315.7	1285.0	1250.9	1238.1	1211.0	1195.3
17.5°	1425.3	1384.9	1347.0	1297.4	1246.8	1204.3	1171.7	1139.0	1119.4	1102.1	1094.1
20°	1382.6	1345.6	1292.9	1235.2	1179.0	1132.0	1105.6	1084.3	1062.9	1050.9	1042.3
22.5°	1342.2	1294.9	1233.7	1171.4	1115.2	1078.4	1056.1	1034.2	1016.8	1005.3	993.9
25°	1274.4	1212.5	1147.6	1076.5	1038.0	1006.0	981.8	963.9	953.3	938.3	932.6
27.5°	1204.8	1129.7	1058.3	1010.4	970.4	941.0	920.0	906.6	893.0	883.5	876.1
30°	1151.2	1075.0	1010.9	965.4	924.8	900.6	883.5	867.9	857.2	849.4	843.6
32.5°	1098.2	1022.1	968.2	919.3	887.3	863.6	845.3	833.7	825.3	815.2	811.7
35°	1021.6	954.0	907.0	862.9	830.1	808.8	794.5	782.5	775.3	772.5	770.3
37.5°	948.1	892.6	842.1	805.9	776.8	759.9	743.2	737.2	732.3	727.2	729.5
40°	901.3	849.4	804.5	766.1	742.5	724.1	714.1	706.9	702.7	702.7	702.7
42.5°	860.9	810.0	766.3	731.9	708.4	692.8	681.6	675.6	674.2	673.7	677.1
45°	798.1	751.1	706.9	678.5	658.5	642.9	636.5	631.5	631.5	634.4	635.1
47.5°	735.8	691.9	656.4	624.6	606.3	596.5	590.9	588.4	588.6	591.5	594.8
50°	697.7	654.2	619.4	590.9	573.8	564.5	559.5	558.2	559.5	559.5	564.5
52.5°	656.1	617.2	582.9	559.0	539.7	531.0	528.2	526.3	527.1	529.4	531.5
55°	595.2	560.3	527.5	504.8	490.5	484.8	478.4	479.1	477.7	479.1	479.1
57.5°	534.1	502.7	472.3	454.2	441.7	433.5	426.4	428.5	426.3	426.1	424.9
60°	494.8	460.7	436.4	420.1	405.8	398.7	392.3	393.7	391.6	390.1	387.3
62.5°	452.1	423.7	400.6	384.8	373.4	365.1	358.6	357.2	352.3	347.4	341.2
65°	390.1	366.7	346.0	331.1	320.4	314.0	309.0	304.7	294.0	282.7	277.0
67.5°	329.9	313.0	293.7	281.1	272.4	264.0	254.5	247.2	237.2	231.0	227.4
70°	291.1	274.8	258.4	246.3	237.1	229.3	218.6	213.6	206.4	203.6	200.1
72.5°	254.1	238.9	223.7	212.8	202.9	196.8	188.4	183.4	180.3	179.1	175.6
75°	198.0	185.8	174.4	164.4	156.7	152.4	148.8	145.3	143.8	137.4	133.8
77.5°	144.4	136.4	129.3	122.2	116.6	113.8	106.9	102.8	100.4	97.4	96.7
80°	112.4	106.8	99.7	95.4	87.6	84.7	81.9	81.1	80.4	79.7	79.0
82.5°	84.6	78.9	71.8	69.2	67.1	65.4	63.7	63.0	62.2	62.7	62.5
85°	42.7	39.9	39.9	39.1	38.4	37.7	37.0	37.0	36.3	37.0	36.3
87.5°	15.1	14.6	14.7	13.7	14.4	14.4	14.0	14.1	14.7	13.6	13.7
90°	4.0	4.7	5.3	5.8	6.3	7.0	7.3	7.8	8.2	8.6	8.9
92.5°	4.1	4.5	5.0	5.5	6.2	6.7	7.1	7.5	7.9	8.4	8.6
95°	7.8	6.7	6.7	6.8	6.9	7.0	7.3	7.8	8.2	8.6	8.8
97.5°	42.7	39.6	31.7	24.0	16.1	8.3	8.4	8.4	8.5	8.5	8.6
100°	56.7	52.5	42.9	33.2	23.5	13.9	12.7	11.5	10.3	9.1	8.6
102.5°	72.1	71.9	70.6	69.4	68.0	66.8	53.9	41.1	28.3	15.4	9.0
105°	96.6	96.9	97.3	97.6	98.0	98.4	99.0	99.6	100.2	100.9	99.9
107.5°	120.4	120.6	121.2	121.6	122.1	122.6	122.9	123.2	123.5	123.9	124.1
110°	137.0	137.3	137.7	138.1	138.6	139.0	139.1	139.3	139.4	139.6	139.7



TEST NUMBER: P332985-940

CATALOG NUMBER: S124RDIP-S1195D365U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	153.8	154.1	154.3	154.4	154.6	154.9	154.8	154.8	154.8	154.7	154.9
115°	178.0	178.0	178.0	177.9	177.8	177.7	177.9	178.0	178.2	178.3	178.3
117.5°	200.6	200.8	201.0	201.2	201.3	201.4	201.4	201.3	201.3	201.3	201.3
120°	215.7	215.8	215.8	215.7	215.6	215.5	215.7	215.8	216.0	216.2	216.2
122.5°	229.4	229.5	229.6	229.7	229.8	230.0	230.0	230.1	230.2	230.2	230.2
125°	250.1	250.1	250.0	249.9	249.8	249.6	249.8	250.0	250.2	250.4	250.6
127.5°	268.4	268.6	268.9	269.2	269.6	269.9	269.8	269.8	269.7	269.7	269.7
130°	280.8	280.9	281.1	281.3	281.5	281.8	281.8	281.9	282.0	282.0	282.0
132.5°	292.3	292.5	292.7	293.0	293.3	293.6	293.6	293.7	293.8	293.9	293.9
135°	308.5	308.6	309.0	309.2	309.5	309.8	310.0	310.0	310.2	310.3	310.5
137.5°	324.0	324.2	324.5	324.8	325.1	325.4	325.6	325.7	325.9	326.0	326.1
140°	334.3	334.4	334.6	334.7	334.8	335.0	335.2	335.4	335.6	335.8	336.0
142.5°	343.6	343.8	343.8	343.9	344.0	344.1	344.2	344.4	344.6	344.6	344.7
145°	357.0	357.0	357.0	357.0	357.0	357.0	357.1	357.2	357.3	357.3	357.4
147.5°	368.5	368.6	368.5	368.5	368.4	368.4	368.4	368.5	368.5	368.5	368.6
150°	375.9	375.9	375.9	375.8	375.7	375.7	375.7	375.7	375.7	375.7	375.7
152.5°	382.2	382.2	382.1	381.9	381.8	381.7	381.8	381.9	382.0	382.2	382.2
155°	390.7	390.7	390.5	390.2	390.0	389.9	390.1	390.4	390.7	390.9	391.0
157.5°	398.1	397.9	397.7	397.4	397.2	397.0	397.3	397.7	398.1	398.4	398.4
160°	401.9	401.8	401.7	401.6	401.5	401.4	401.9	402.3	402.8	403.1	403.1
162.5°	405.7	405.6	405.5	405.4	405.4	405.3	405.7	406.1	406.5	407.0	406.9
165°	410.5	410.3	410.3	410.3	410.3	410.3	410.9	411.4	412.0	412.6	412.5
167.5°	414.5	414.3	414.2	414.2	414.1	414.1	414.7	415.4	416.0	416.5	416.5
170°	416.5	416.3	416.4	416.5	416.5	416.6	417.1	417.8	418.3	418.8	418.7
172.5°	418.0	417.9	417.9	418.0	418.0	418.1	418.7	419.3	419.8	420.4	420.3
175°	419.6	419.5	419.5	419.6	419.7	419.7	420.4	421.1	421.7	422.3	422.2
177.5°	420.5	420.4	420.5	420.6	420.7	420.8	421.3	421.8	422.2	422.7	422.5
180°	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3



TEST NUMBER: P332985-940

CATALOG NUMBER: S124RDIP-S1195D365U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1
2.5°	1686.8	1687.9	1683.9	1682.7	1683.9	1687.9	1686.8	1690.1	1690.8	1695.3	1693.6
5°	1564.9	1563.4	1559.9	1560.6	1559.9	1563.4	1564.9	1570.6	1573.4	1584.8	1583.4
7.5°	1460.6	1455.1	1456.6	1451.0	1456.6	1455.1	1460.6	1465.8	1474.4	1479.6	1491.7
10°	1396.9	1389.0	1382.6	1376.9	1382.6	1389.0	1396.9	1399.7	1411.8	1417.5	1429.6
12.5°	1309.7	1303.0	1294.3	1296.0	1294.3	1303.0	1309.7	1322.2	1337.7	1349.7	1368.7
15°	1186.1	1175.5	1158.3	1160.5	1158.3	1175.5	1186.1	1195.3	1211.0	1238.1	1250.9
17.5°	1081.5	1081.6	1073.8	1075.6	1073.8	1081.6	1081.5	1094.1	1102.1	1119.4	1139.0
20°	1027.3	1022.3	1023.1	1020.9	1023.1	1022.3	1027.3	1042.3	1050.9	1062.9	1084.3
22.5°	989.7	983.6	978.7	974.2	978.7	983.6	989.7	993.9	1005.3	1016.8	1034.2
25°	926.2	921.9	915.6	914.2	915.6	921.9	926.2	932.6	938.3	953.3	963.9
27.5°	870.4	869.6	867.0	863.7	867.0	869.6	870.4	876.1	883.5	893.0	906.6
30°	837.9	836.5	835.1	832.9	835.1	836.5	837.9	843.6	849.4	857.2	867.9
32.5°	809.0	808.1	806.6	806.8	806.6	808.1	809.0	811.7	815.2	825.3	833.7
35°	767.5	766.8	765.4	764.6	765.4	766.8	767.5	770.3	772.5	775.3	782.5
37.5°	728.8	730.6	729.8	729.6	729.8	730.6	728.8	729.5	727.2	732.3	737.2
40°	702.0	702.7	704.1	703.4	704.1	702.7	702.0	702.7	702.7	702.7	706.9
42.5°	679.8	679.9	681.9	679.5	681.9	679.9	679.8	677.1	673.7	674.2	675.6
45°	640.1	644.4	643.6	643.6	643.6	644.4	640.1	635.1	634.4	631.5	631.5
47.5°	596.6	600.3	601.3	601.2	601.3	600.3	596.6	594.8	591.5	588.6	588.4
50°	568.1	566.7	568.8	568.1	568.8	566.7	568.1	564.5	559.5	559.5	558.2
52.5°	533.4	533.7	533.5	532.8	533.5	533.7	533.4	531.5	529.4	527.1	526.3
55°	479.8	480.5	479.1	479.8	479.1	480.5	479.8	479.1	479.1	477.7	479.1
57.5°	421.8	418.3	419.7	418.0	419.7	418.3	421.8	424.9	426.1	426.3	428.5
60°	380.2	374.5	373.1	370.2	373.1	374.5	380.2	387.3	390.1	391.6	393.7
62.5°	333.5	329.5	324.7	326.9	324.7	329.5	333.5	341.2	347.4	352.3	357.2
65°	271.3	268.4	266.3	269.1	266.3	268.4	271.3	277.0	282.7	294.0	304.7
67.5°	224.5	223.0	223.0	221.6	223.0	223.0	224.5	227.4	231.0	237.2	247.2
70°	200.1	198.0	198.0	196.5	198.0	198.0	200.1	200.1	203.6	206.4	213.6
72.5°	175.0	172.9	173.4	172.5	173.4	172.9	175.0	175.6	179.1	180.3	183.4
75°	129.6	126.0	126.0	126.7	126.0	126.0	129.6	133.8	137.4	143.8	145.3
77.5°	96.7	95.9	96.9	95.7	96.9	95.9	96.7	96.7	97.4	100.4	102.8
80°	79.0	78.3	77.6	79.7	77.6	78.3	79.0	79.0	79.7	80.4	81.1
82.5°	61.3	61.3	61.1	63.8	61.1	61.3	61.3	62.5	62.7	62.2	63.0
85°	37.0	35.6	37.0	35.6	37.0	35.6	37.0	36.3	37.0	36.3	37.0
87.5°	14.9	14.4	13.8	14.4	13.8	14.4	14.9	13.7	13.6	14.7	14.1
90°	9.0	9.2	9.3	9.5	9.3	9.2	9.0	8.9	8.6	8.2	7.8
92.5°	8.6	8.6	8.6	8.7	8.6	8.6	8.6	8.6	8.4	7.9	7.5
95°	8.9	9.0	9.1	9.1	9.1	9.0	8.9	8.8	8.6	8.2	7.8
97.5°	8.6	8.6	8.7	8.8	8.7	8.6	8.6	8.6	8.5	8.5	8.4
100°	8.6	8.6	8.7	8.8	8.7	8.6	8.6	8.6	9.1	10.3	11.5
102.5°	9.0	9.0	9.1	9.1	9.1	9.0	9.0	9.0	15.4	28.3	41.1
105°	97.4	94.9	92.3	89.8	92.3	94.9	97.4	99.9	100.9	100.2	99.6
107.5°	124.4	124.7	124.9	125.2	124.9	124.7	124.4	124.1	123.9	123.5	123.2
110°	139.9	140.2	140.4	140.5	140.4	140.2	139.9	139.7	139.6	139.4	139.3



TEST NUMBER: P332985-940

CATALOG NUMBER: S124RDIP-S1195D365U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	155.2	155.4	155.7	156.0	155.7	155.4	155.2	154.9	154.7	154.8	154.8
115°	178.3	178.3	178.3	178.3	178.3	178.3	178.3	178.3	178.3	178.2	178.0
117.5°	201.3	201.3	201.3	201.2	201.3	201.3	201.3	201.3	201.3	201.3	201.3
120°	216.0	215.8	215.7	215.5	215.7	215.8	216.0	216.2	216.2	216.0	215.8
122.5°	230.1	230.0	229.8	229.7	229.8	230.0	230.1	230.2	230.2	230.2	230.1
125°	250.7	250.7	250.7	250.8	250.7	250.7	250.7	250.6	250.4	250.2	250.0
127.5°	269.7	269.6	269.5	269.5	269.5	269.6	269.7	269.7	269.7	269.7	269.8
130°	282.0	282.0	282.0	282.0	282.0	282.0	282.0	282.0	282.0	282.0	281.9
132.5°	293.8	293.7	293.7	293.6	293.7	293.7	293.8	293.9	293.9	293.8	293.7
135°	310.6	310.8	310.9	311.0	310.9	310.8	310.6	310.5	310.3	310.2	310.0
137.5°	326.0	326.0	325.9	325.9	325.9	326.0	326.0	326.1	326.0	325.9	325.7
140°	336.1	336.1	336.2	336.3	336.2	336.1	336.1	336.0	335.8	335.6	335.4
142.5°	344.8	344.8	344.8	344.8	344.8	344.8	344.8	344.7	344.6	344.6	344.4
145°	357.6	357.8	357.8	358.0	357.8	357.8	357.6	357.4	357.3	357.3	357.2
147.5°	368.7	368.7	368.8	368.9	368.8	368.7	368.7	368.6	368.5	368.5	368.5
150°	375.8	375.9	375.9	375.9	375.9	375.9	375.8	375.7	375.7	375.7	375.7
152.5°	382.1	382.1	382.1	382.0	382.1	382.1	382.1	382.2	382.2	382.0	381.9
155°	390.7	390.6	390.4	390.1	390.4	390.6	390.7	391.0	390.9	390.7	390.4
157.5°	398.1	397.7	397.3	397.0	397.3	397.7	398.1	398.4	398.4	398.1	397.7
160°	402.8	402.3	401.9	401.4	401.9	402.3	402.8	403.1	403.1	402.8	402.3
162.5°	406.4	406.0	405.5	405.0	405.5	406.0	406.4	406.9	407.0	406.5	406.1
165°	411.9	411.3	410.6	410.0	410.6	411.3	411.9	412.5	412.6	412.0	411.4
167.5°	415.8	415.1	414.4	413.8	414.4	415.1	415.8	416.5	416.5	416.0	415.4
170°	418.1	417.4	416.7	416.0	416.7	417.4	418.1	418.7	418.8	418.3	417.8
172.5°	419.5	418.7	418.0	417.2	418.0	418.7	419.5	420.3	420.4	419.8	419.3
175°	421.3	420.5	419.6	418.8	419.6	420.5	421.3	422.2	422.3	421.7	421.1
177.5°	421.9	421.2	420.5	419.8	420.5	421.2	421.9	422.5	422.7	422.2	421.8
180°	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3



TEST NUMBER: P332985-940

CATALOG NUMBER: S124RDIP-S1195D365U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1
2.5°	1690.1	1694.2	1703.3	1713.5	1722.1	1729.5	1735.2	1743.1	1750.5	1760.8	1770.5
5°	1587.7	1597.6	1611.9	1629.0	1650.3	1664.6	1682.3	1698.0	1720.8	1743.6	1765.7
7.5°	1497.6	1508.6	1529.6	1553.2	1578.5	1601.9	1623.0	1650.6	1680.8	1714.0	1751.0
10°	1439.6	1451.7	1476.6	1503.6	1533.6	1556.3	1584.8	1617.6	1651.7	1692.3	1737.9
12.5°	1387.1	1398.7	1428.7	1456.3	1487.4	1512.4	1545.5	1578.9	1624.4	1668.4	1720.2
15°	1285.0	1315.7	1349.9	1382.6	1419.6	1450.3	1490.1	1524.3	1567.7	1629.7	1688.7
17.5°	1171.7	1204.3	1246.8	1297.4	1347.0	1384.9	1425.3	1467.8	1519.5	1582.7	1650.9
20°	1105.6	1132.0	1179.0	1235.2	1292.9	1345.6	1382.6	1429.6	1483.0	1551.3	1621.8
22.5°	1056.1	1078.4	1115.2	1171.4	1233.7	1294.9	1342.2	1388.6	1447.7	1516.0	1592.8
25°	981.8	1006.0	1038.0	1076.5	1147.6	1212.5	1274.4	1327.8	1390.4	1458.7	1544.2
27.5°	920.0	941.0	970.4	1010.4	1058.3	1129.7	1204.8	1265.7	1329.9	1403.3	1488.8
30°	883.5	900.6	924.8	965.4	1010.9	1075.0	1151.2	1222.4	1287.2	1363.4	1452.4
32.5°	845.3	863.6	887.3	919.3	968.2	1022.1	1098.2	1176.3	1245.1	1322.9	1410.2
35°	794.5	808.8	830.1	862.9	907.0	954.0	1021.6	1102.1	1174.7	1258.0	1341.3
37.5°	743.2	759.9	776.8	805.9	842.1	892.6	948.1	1030.2	1110.6	1186.7	1268.0
40°	714.1	724.1	742.5	766.1	804.5	849.4	901.3	981.8	1062.2	1137.7	1219.6
42.5°	681.6	692.8	708.4	731.9	766.3	810.0	860.9	930.5	1014.4	1087.6	1162.1
45°	636.5	642.9	658.5	678.5	706.9	751.1	798.1	860.1	939.1	1008.8	1074.3
47.5°	590.9	596.5	606.3	624.6	656.4	691.9	735.8	791.4	860.8	930.5	985.9
50°	559.5	564.5	573.8	590.9	619.4	654.2	697.7	747.5	809.5	876.4	922.7
52.5°	528.2	531.0	539.7	559.0	582.9	617.2	656.1	702.0	759.9	815.5	862.3
55°	478.4	484.8	490.5	504.8	527.5	560.3	595.2	638.6	683.5	730.5	770.3
57.5°	426.4	433.5	441.7	454.2	472.3	502.7	534.1	569.3	607.6	646.6	680.0
60°	392.3	398.7	405.8	420.1	436.4	460.7	494.8	525.4	554.6	590.2	623.7
62.5°	358.6	365.1	373.4	384.8	400.6	423.7	452.1	478.8	509.1	540.1	565.0
65°	309.0	314.0	320.4	331.1	346.0	366.7	390.1	410.8	437.8	460.7	483.4
67.5°	254.5	264.0	272.4	281.1	293.7	313.0	329.9	349.7	368.1	385.0	405.8
70°	218.6	229.3	237.1	246.3	258.4	274.8	291.1	304.7	319.7	336.0	354.5
72.5°	188.4	196.8	202.9	212.8	223.7	238.9	254.1	265.4	277.5	288.7	306.7
75°	148.8	152.4	156.7	164.4	174.4	185.8	198.0	207.9	215.0	225.0	237.8
77.5°	106.9	113.8	116.6	122.2	129.3	136.4	144.4	152.8	159.6	163.2	173.0
80°	81.9	84.7	87.6	95.4	99.7	106.8	112.4	120.3	123.1	126.7	136.0
82.5°	63.7	65.4	67.1	69.2	71.8	78.9	84.6	89.5	92.4	93.7	100.7
85°	37.0	37.7	38.4	39.1	39.9	39.9	42.7	46.3	51.3	51.3	53.4
87.5°	14.0	14.4	14.4	13.7	14.7	14.6	15.1	14.9	16.4	18.0	19.5
90°	7.3	7.0	6.3	5.8	5.3	4.7	4.0	3.3	2.5	1.7	1.0
92.5°	7.1	6.7	6.2	5.5	5.0	4.5	4.1	4.1	4.0	4.0	4.0
95°	7.3	7.0	6.9	6.8	6.7	6.7	7.8	10.2	12.6	15.0	17.3
97.5°	8.4	8.3	16.1	24.0	31.7	39.6	42.7	41.3	39.8	38.3	36.8
100°	12.7	13.9	23.5	33.2	42.9	52.5	56.7	55.5	54.2	53.0	51.7
102.5°	53.9	66.8	68.0	69.4	70.6	71.9	72.1	71.1	70.2	69.3	68.3
105°	99.0	98.4	98.0	97.6	97.3	96.9	96.6	96.1	95.7	95.2	94.9
107.5°	122.9	122.6	122.1	121.6	121.2	120.6	120.4	120.1	119.9	119.7	119.5
110°	139.1	139.0	138.6	138.1	137.7	137.3	137.0	136.8	136.5	136.3	136.2



TEST NUMBER: P332985-940

CATALOG NUMBER: S124RDIP-S1195D365U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	154.8	154.9	154.6	154.4	154.3	154.1	153.8	153.4	153.0	152.7	152.3
115°	177.9	177.7	177.8	177.9	178.0	178.0	178.0	177.7	177.5	177.4	177.1
117.5°	201.4	201.4	201.3	201.2	201.0	200.8	200.6	200.4	200.0	199.7	199.5
120°	215.7	215.5	215.6	215.7	215.8	215.8	215.7	215.4	215.2	214.9	214.6
122.5°	230.0	230.0	229.8	229.7	229.6	229.5	229.4	229.3	229.1	228.9	228.7
125°	249.8	249.6	249.8	249.9	250.0	250.1	250.1	249.8	249.5	249.2	249.0
127.5°	269.8	269.9	269.6	269.2	268.9	268.6	268.4	268.3	268.2	268.2	268.1
130°	281.8	281.8	281.5	281.3	281.1	280.9	280.8	280.7	280.6	280.5	280.4
132.5°	293.6	293.6	293.3	293.0	292.7	292.5	292.3	292.2	292.0	291.9	291.9
135°	310.0	309.8	309.5	309.2	309.0	308.6	308.5	308.6	308.7	308.8	308.8
137.5°	325.6	325.4	325.1	324.8	324.5	324.2	324.0	324.0	324.0	324.0	323.9
140°	335.2	335.0	334.8	334.7	334.6	334.4	334.3	334.1	334.0	333.9	333.8
142.5°	344.2	344.1	344.0	343.9	343.8	343.8	343.6	343.3	343.0	342.8	342.6
145°	357.1	357.0	357.0	357.0	357.0	357.0	357.0	356.8	356.5	356.3	356.1
147.5°	368.4	368.4	368.4	368.5	368.5	368.6	368.5	368.1	367.7	367.3	366.8
150°	375.7	375.7	375.7	375.8	375.9	375.9	375.9	375.6	375.2	375.0	374.7
152.5°	381.8	381.7	381.8	381.9	382.1	382.2	382.2	381.9	381.7	381.5	381.3
155°	390.1	389.9	390.0	390.2	390.5	390.7	390.7	390.7	390.6	390.6	390.5
157.5°	397.3	397.0	397.2	397.4	397.7	397.9	398.1	398.1	398.1	398.1	398.2
160°	401.9	401.4	401.5	401.6	401.7	401.8	401.9	402.2	402.3	402.5	402.8
162.5°	405.7	405.3	405.4	405.4	405.5	405.6	405.7	406.0	406.3	406.5	406.8
165°	410.9	410.3	410.3	410.3	410.3	410.3	410.5	410.8	411.2	411.5	411.9
167.5°	414.7	414.1	414.1	414.2	414.2	414.3	414.5	414.8	415.2	415.5	415.9
170°	417.1	416.6	416.5	416.5	416.4	416.3	416.5	417.0	417.3	417.8	418.2
172.5°	418.7	418.1	418.0	418.0	417.9	417.9	418.0	418.5	418.8	419.3	419.7
175°	420.4	419.7	419.7	419.6	419.5	419.5	419.6	420.1	420.5	420.9	421.3
177.5°	421.3	420.8	420.7	420.6	420.5	420.4	420.5	420.9	421.3	421.7	422.1
180°	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3



TEST NUMBER: P332985-940

CATALOG NUMBER: S124RDIP-S1195D365U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1
2.5°	1777.9	1783.0	1788.7	1799.6	1808.7	1812.7	1820.6	1826.3	1824.6	1832.6	1846.2
5°	1784.8	1804.1	1826.1	1849.0	1874.6	1896.0	1913.0	1930.1	1943.7	1960.0	1984.2
7.5°	1783.7	1817.9	1855.0	1896.0	1938.0	1974.2	2007.9	2042.0	2072.3	2105.5	2148.9
10°	1779.1	1824.7	1871.0	1924.4	1977.8	2028.4	2073.9	2116.7	2157.2	2200.7	2255.5
12.5°	1774.1	1826.4	1882.4	1946.6	2013.1	2073.9	2127.4	2189.0	2239.8	2295.8	2359.1
15°	1751.4	1821.9	1898.1	1981.4	2061.1	2143.0	2216.3	2291.8	2362.2	2429.2	2508.9
17.5°	1725.5	1806.8	1896.7	1995.0	2090.9	2190.4	2277.4	2372.5	2444.5	2534.4	2608.4
20°	1704.4	1792.0	1888.1	1998.4	2107.4	2217.7	2313.8	2410.7	2491.8	2582.2	2676.2
22.5°	1678.7	1774.9	1879.0	1993.3	2107.4	2227.9	2334.3	2430.6	2531.1	2633.0	2729.8
25°	1637.4	1737.1	1847.5	1972.8	2103.8	2227.0	2340.9	2460.5	2568.8	2679.1	2765.9
27.5°	1586.8	1691.5	1807.8	1937.1	2071.5	2197.6	2331.8	2459.2	2568.1	2674.3	2750.1
30°	1546.3	1656.7	1768.4	1899.5	2039.0	2174.3	2318.1	2445.5	2560.2	2655.6	2698.3
32.5°	1504.8	1609.4	1724.7	1857.3	2000.3	2145.8	2288.5	2418.8	2524.9	2582.1	2583.2
35°	1432.4	1530.7	1650.3	1780.6	1927.3	2085.3	2229.8	2358.0	2422.8	2427.8	2358.0
37.5°	1353.5	1443.7	1556.6	1687.0	1847.6	2004.8	2152.5	2237.9	2259.6	2187.1	2058.1
40°	1297.2	1380.5	1489.4	1623.3	1782.7	1945.1	2079.6	2142.2	2119.5	2002.0	1858.1
42.5°	1238.0	1315.5	1420.5	1552.6	1712.7	1876.7	1991.4	2024.9	1964.5	1828.9	1660.5
45°	1141.3	1212.5	1316.4	1449.6	1603.3	1757.1	1844.0	1826.8	1726.4	1565.6	1376.9
47.5°	1040.6	1109.4	1202.9	1326.1	1483.5	1616.2	1675.1	1623.5	1480.7	1303.7	1150.2
50°	973.9	1044.5	1130.6	1248.0	1391.9	1520.0	1557.7	1479.4	1320.6	1150.5	1009.5
52.5°	908.5	968.7	1053.1	1166.6	1304.1	1412.4	1432.4	1342.2	1178.3	1025.7	900.7
55°	808.8	863.6	934.8	1041.6	1160.5	1252.3	1241.6	1125.6	976.8	846.5	748.2
57.5°	712.4	753.7	819.5	919.5	1024.0	1085.6	1046.6	947.6	809.0	702.3	619.4
60°	648.6	687.1	748.2	835.8	927.6	962.5	929.8	822.3	712.7	615.1	545.4
62.5°	588.2	622.1	674.8	756.1	830.3	851.0	815.9	722.0	623.2	539.9	482.1
65°	500.5	531.8	576.7	634.4	685.6	695.5	672.8	576.7	501.9	432.1	392.3
67.5°	420.9	441.4	476.4	526.3	553.5	559.3	515.3	455.0	389.1	346.2	316.1
70°	367.4	381.6	414.4	441.4	463.5	464.2	423.7	375.2	324.7	289.8	267.7
72.5°	315.6	329.2	354.0	372.5	389.4	383.9	346.7	308.5	267.7	241.4	225.0
75°	243.5	255.6	268.4	277.0	277.0	269.8	242.8	214.3	190.8	175.1	170.1
77.5°	177.0	187.0	191.3	189.9	187.3	176.3	159.2	140.5	132.2	124.8	121.0
80°	138.8	143.1	144.5	141.0	136.7	123.9	112.4	104.7	96.8	94.0	92.6
82.5°	102.9	106.6	102.9	104.0	94.5	84.0	77.8	75.1	71.8	70.6	69.2
85°	54.8	54.1	52.7	49.1	42.7	41.3	40.6	39.9	38.4	39.1	37.7
87.5°	19.2	17.6	15.4	15.1	15.2	14.2	14.8	15.0	15.1	14.5	15.8
90°	1.7	2.5	3.3	4.0	4.7	5.3	5.8	6.3	7.0	7.3	7.8
92.5°	4.0	4.0	4.1	4.1	4.5	5.0	5.5	6.2	6.7	7.1	7.5
95°	15.0	12.6	10.2	7.8	6.7	6.7	6.8	6.9	7.0	7.3	7.8
97.5°	38.3	39.8	41.3	42.7	39.6	31.7	24.0	16.1	8.3	8.4	8.4
100°	53.0	54.2	55.5	56.7	52.5	42.9	33.2	23.5	13.9	12.7	11.5
102.5°	69.3	70.2	71.1	72.1	71.9	70.6	69.4	68.0	66.8	53.9	41.1
105°	95.2	95.7	96.1	96.6	96.9	97.3	97.6	98.0	98.4	99.0	99.6
107.5°	119.7	119.9	120.1	120.4	120.6	121.2	121.6	122.1	122.6	122.9	123.2
110°	136.3	136.5	136.8	137.0	137.3	137.7	138.1	138.6	139.0	139.1	139.3



TEST NUMBER: P332985-940

CATALOG NUMBER: S124RDIP-S1195D365U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	152.7	153.0	153.4	153.8	154.1	154.3	154.4	154.6	154.9	154.8	154.8
115°	177.4	177.5	177.7	178.0	178.0	178.0	177.9	177.8	177.7	177.9	178.0
117.5°	199.7	200.0	200.4	200.6	200.8	201.0	201.2	201.3	201.4	201.4	201.3
120°	214.9	215.2	215.4	215.7	215.8	215.8	215.7	215.6	215.5	215.7	215.8
122.5°	228.9	229.1	229.3	229.4	229.5	229.6	229.7	229.8	230.0	230.0	230.1
125°	249.2	249.5	249.8	250.1	250.1	250.0	249.9	249.8	249.6	249.8	250.0
127.5°	268.2	268.2	268.3	268.4	268.6	268.9	269.2	269.6	269.9	269.8	269.8
130°	280.5	280.6	280.7	280.8	280.9	281.1	281.3	281.5	281.8	281.8	281.9
132.5°	291.9	292.0	292.2	292.3	292.5	292.7	293.0	293.3	293.6	293.6	293.7
135°	308.8	308.7	308.6	308.5	308.6	309.0	309.2	309.5	309.8	310.0	310.0
137.5°	324.0	324.0	324.0	324.0	324.2	324.5	324.8	325.1	325.4	325.6	325.7
140°	333.9	334.0	334.1	334.3	334.4	334.6	334.7	334.8	335.0	335.2	335.4
142.5°	342.8	343.0	343.3	343.6	343.8	343.8	343.9	344.0	344.1	344.2	344.4
145°	356.3	356.5	356.8	357.0	357.0	357.0	357.0	357.0	357.0	357.1	357.2
147.5°	367.3	367.7	368.1	368.5	368.6	368.5	368.5	368.4	368.4	368.4	368.5
150°	375.0	375.2	375.6	375.9	375.9	375.9	375.8	375.7	375.7	375.7	375.7
152.5°	381.5	381.7	381.9	382.2	382.2	382.1	381.9	381.8	381.7	381.8	381.9
155°	390.6	390.6	390.7	390.7	390.7	390.5	390.2	390.0	389.9	390.1	390.4
157.5°	398.1	398.1	398.1	398.1	397.9	397.7	397.4	397.2	397.0	397.3	397.7
160°	402.5	402.3	402.2	401.9	401.8	401.7	401.6	401.5	401.4	401.9	402.3
162.5°	406.5	406.3	406.0	405.7	405.6	405.5	405.4	405.4	405.3	405.7	406.1
165°	411.5	411.2	410.8	410.5	410.3	410.3	410.3	410.3	410.3	410.9	411.4
167.5°	415.5	415.2	414.8	414.5	414.3	414.2	414.2	414.1	414.1	414.7	415.4
170°	417.8	417.3	417.0	416.5	416.3	416.4	416.5	416.5	416.6	417.1	417.8
172.5°	419.3	418.8	418.5	418.0	417.9	417.9	418.0	418.0	418.1	418.7	419.3
175°	420.9	420.5	420.1	419.6	419.5	419.5	419.6	419.7	419.7	420.4	421.1
177.5°	421.7	421.3	420.9	420.5	420.4	420.5	420.6	420.7	420.8	421.3	421.8
180°	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3



TEST NUMBER: P332985-940

CATALOG NUMBER: S124RDIP-S1195D365U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1
2.5°	1853.6	1855.9	1857.6	1863.3	1863.9	1869.0	1863.9
5°	2007.0	2017.0	2032.7	2048.3	2049.7	2059.7	2041.8
7.5°	2179.0	2202.1	2216.4	2241.8	2251.7	2258.0	2247.7
10°	2297.5	2318.8	2356.5	2375.1	2393.6	2396.4	2387.9
12.5°	2412.0	2445.9	2475.6	2510.6	2509.8	2534.9	2525.7
15°	2564.5	2599.3	2640.6	2679.8	2694.0	2694.0	2705.5
17.5°	2673.3	2737.2	2779.9	2810.7	2844.2	2850.1	2846.1
20°	2746.7	2815.8	2861.3	2901.2	2924.0	2930.4	2930.4
22.5°	2801.4	2860.2	2904.7	2940.5	2959.3	2966.8	2964.6
25°	2839.3	2889.8	2916.9	2927.6	2932.5	2931.1	2917.6
27.5°	2787.4	2785.2	2768.0	2735.3	2710.7	2695.7	2678.6
30°	2688.3	2651.3	2608.6	2561.6	2501.1	2454.8	2440.5
32.5°	2540.8	2457.6	2385.3	2307.0	2241.9	2195.7	2176.3
35°	2255.5	2123.8	2016.2	1922.3	1854.0	1811.2	1797.0
37.5°	1916.8	1789.4	1656.3	1565.1	1508.5	1465.3	1449.2
40°	1701.6	1562.7	1446.7	1361.3	1302.9	1260.9	1260.2
42.5°	1505.0	1372.5	1263.3	1201.8	1138.8	1111.1	1110.9
45°	1232.3	1126.3	1033.8	985.3	947.6	924.8	918.4
47.5°	1020.4	932.6	871.0	832.4	801.6	787.1	777.8
50°	901.3	824.5	775.3	741.8	724.8	706.2	704.8
52.5°	802.2	740.1	701.9	674.7	653.0	641.9	642.2
55°	674.2	625.1	598.1	577.4	560.3	551.8	548.2
57.5°	568.0	531.1	511.5	492.5	485.3	478.6	476.7
60°	501.9	477.0	458.5	443.5	432.8	430.7	430.0
62.5°	447.3	421.2	408.4	396.8	389.1	385.8	384.4
65°	368.8	349.6	338.1	329.0	326.1	321.1	320.4
67.5°	297.3	285.8	278.2	271.8	268.0	267.7	267.7
70°	253.4	247.0	240.7	237.1	235.0	233.5	233.5
72.5°	215.9	211.2	205.9	204.0	203.6	202.2	201.6
75°	164.4	159.4	160.2	156.7	153.8	150.3	148.1
77.5°	116.6	113.1	112.4	111.9	109.5	109.1	110.2
80°	90.4	86.9	86.1	86.9	86.1	84.0	84.0
82.5°	68.8	65.8	65.1	64.6	63.9	64.6	63.5
85°	37.0	35.6	35.6	35.6	37.0	36.3	35.6
87.5°	14.7	14.3	14.9	14.4	14.4	13.8	14.4
90°	8.2	8.6	8.9	9.0	9.2	9.3	9.5
92.5°	7.9	8.4	8.6	8.6	8.6	8.6	8.7
95°	8.2	8.6	8.8	8.9	9.0	9.1	9.1
97.5°	8.5	8.5	8.6	8.6	8.6	8.7	8.8
100°	10.3	9.1	8.6	8.6	8.6	8.7	8.8
102.5°	28.3	15.4	9.0	9.0	9.0	9.1	9.1
105°	100.2	100.9	99.9	97.4	94.9	92.3	89.8
107.5°	123.5	123.9	124.1	124.4	124.7	124.9	125.2
110°	139.4	139.6	139.7	139.9	140.2	140.4	140.5



TEST NUMBER: P332985-940

CATALOG NUMBER: S124RDIP-S1195D365U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	154.8	154.7	154.9	155.2	155.4	155.7	156.0
115°	178.2	178.3	178.3	178.3	178.3	178.3	178.3
117.5°	201.3	201.3	201.3	201.3	201.3	201.3	201.2
120°	216.0	216.2	216.2	216.0	215.8	215.7	215.5
122.5°	230.2	230.2	230.2	230.1	230.0	229.8	229.7
125°	250.2	250.4	250.6	250.7	250.7	250.7	250.8
127.5°	269.7	269.7	269.7	269.7	269.6	269.5	269.5
130°	282.0	282.0	282.0	282.0	282.0	282.0	282.0
132.5°	293.8	293.9	293.9	293.8	293.7	293.7	293.6
135°	310.2	310.3	310.5	310.6	310.8	310.9	311.0
137.5°	325.9	326.0	326.1	326.0	326.0	325.9	325.9
140°	335.6	335.8	336.0	336.1	336.1	336.2	336.3
142.5°	344.6	344.6	344.7	344.8	344.8	344.8	344.8
145°	357.3	357.3	357.4	357.6	357.8	357.8	358.0
147.5°	368.5	368.5	368.6	368.7	368.7	368.8	368.9
150°	375.7	375.7	375.7	375.8	375.9	375.9	375.9
152.5°	382.0	382.2	382.2	382.1	382.1	382.1	382.0
155°	390.7	390.9	391.0	390.7	390.6	390.4	390.1
157.5°	398.1	398.4	398.4	398.1	397.7	397.3	397.0
160°	402.8	403.1	403.1	402.8	402.3	401.9	401.4
162.5°	406.5	407.0	406.9	406.4	406.0	405.5	405.0
165°	412.0	412.6	412.5	411.9	411.3	410.6	410.0
167.5°	416.0	416.5	416.5	415.8	415.1	414.4	413.8
170°	418.3	418.8	418.7	418.1	417.4	416.7	416.0
172.5°	419.8	420.4	420.3	419.5	418.7	418.0	417.2
175°	421.7	422.3	422.2	421.3	420.5	419.6	418.8
177.5°	422.2	422.7	422.5	421.9	421.2	420.5	419.8
180°	421.3	421.3	421.3	421.3	421.3	421.3	421.3

(END OF REPORT)