

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332894-940

Luminaire Tested: **S124RDIP-S350D1205U940-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332894-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIP-S350D1205U940-4F0-1E-UDD-F4
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1205 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5112.3 lumens
Efficiency: N/A
Efficacy: 121.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 42.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332894-940

CATALOG NUMBER: S124RDIP-S350D1205U940-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P332894-940

CATALOG NUMBER: S124RDIP-S350D1205U940-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	69	69	69	51	51	51	33	33	33	25
1	92	88	85	81	82	79	76	73	61	59	57	45	43	42	29	29	28	21
2	84	77	71	66	75	69	64	60	53	50	47	39	37	35	26	25	24	18
3	77	68	61	55	68	61	55	50	47	43	40	35	32	30	23	22	20	15
4	70	60	52	47	62	54	47	42	42	37	34	31	28	26	21	19	18	13
5	64	53	46	40	57	48	41	36	37	33	29	28	25	22	19	17	15	12
6	59	48	40	34	53	43	36	31	34	29	25	25	22	19	17	15	14	10
7	55	43	35	30	48	39	32	27	30	26	22	23	20	17	15	14	12	9
8	51	39	31	26	45	35	29	24	28	23	20	21	18	15	14	12	11	8
9	47	35	28	23	42	32	26	21	25	21	17	19	16	14	13	11	10	7
10	44	32	25	21	39	29	23	19	23	19	16	17	14	12	12	10	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4451	4451	4451
5°	4460	4406	4433
10°	4432	4353	4353
15°	4381	4262	4229
20°	4312	4141	4064
25°	4222	4000	3899
30°	4135	3852	3691
35°	4039	3698	3482
40°	3923	3523	3256
45°	3817	3350	3027
50°	3695	3149	2783
55°	3564	2940	2519
60°	3421	2713	2249
65°	3289	2428	1983
70°	3099	2110	1683
75°	2857	1753	1369
80°	2492	1334	1255
85°	2112	1213	1130



TEST NUMBER: P332894-940

CATALOG NUMBER: S124RDIP-S350D1205U940-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	51.8	1.0
10°-20°	144.4	2.8
20°-30°	208.5	4.1
30°-40°	236.4	4.6
40°-50°	228.2	4.5
50°-60°	189.8	3.7
60°-70°	131.1	2.6
70°-80°	66.4	1.3
80°-90°	19.9	0.4
90°-100°	380.9	7.5
100°-110°	792.8	15.5
110°-120°	710.1	13.9
120°-130°	597.3	11.7
130°-140°	498.1	9.7
140°-150°	380.5	7.4
150°-160°	267.5	5.2
160°-170°	157.3	3.1
170°-180°	51.2	1.0
0°-30°	404.7	7.9
0°-40°	641.0	12.5
0°-60°	1059.1	20.7
0°-90°	1276.5	25.0
90°-120°	1883.9	36.9
90°-150°	3359.8	65.7
90°-180°	3836.0	75.0
0°-180°	5112.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	551	551	551	551	551	
5°	550	548	544	548	547	52
15°	524	520	510	509	506	148
25°	474	466	449	442	438	218
35°	410	396	375	361	353	256
45°	334	318	293	273	265	258
55°	253	236	209	188	179	226
65°	172	154	127	110	104	170
75°	92	76	56	47	44	97
85°	23	15	13	12	12	26
90°	1	8	19	21	22	3
95°	34	108	844	418	253	38
105°	121	176	680	1464	1458	129
115°	214	268	606	1165	1400	212
125°	297	353	603	991	1117	265
135°	353	421	598	880	999	273
145°	407	466	595	742	816	256
155°	463	500	578	655	683	213
165°	505	520	554	587	596	142
175°	526	527	532	539	537	50
180°	527	527	527	527	527	



TEST NUMBER: P332894-940

CATALOG NUMBER: S124RDIP-S350D1205U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	551.3	551.3	551.3	551.3	551.3	551.3	551.3	551.3	551.3	551.3	551.3
2.5°	552.6	552.2	552.0	551.7	551.3	550.8	550.0	549.2	548.3	547.5	548.3
5°	550.4	550.0	549.7	549.3	548.8	548.1	547.0	545.9	544.7	543.7	544.6
7.5°	545.4	545.0	544.7	544.2	543.9	542.9	541.4	539.9	538.5	537.1	537.6
10°	540.6	540.2	539.8	539.3	538.8	537.7	536.0	534.3	532.6	531.0	531.4
12.5°	534.6	534.0	533.5	533.0	532.4	531.2	529.1	527.2	525.2	523.2	523.4
15°	524.2	523.3	522.5	521.7	520.8	519.2	516.9	514.5	512.2	509.9	509.7
17.5°	511.7	510.4	509.2	508.0	506.8	504.7	501.9	499.1	496.3	493.5	492.9
20°	501.9	500.6	499.4	498.2	497.0	494.8	491.6	488.4	485.2	482.0	481.3
22.5°	491.1	489.6	488.3	487.0	485.5	483.1	479.7	476.4	473.0	469.5	468.4
25°	474.0	472.3	470.6	469.0	467.3	464.5	460.7	456.8	452.9	449.1	447.5
27.5°	456.1	454.0	451.8	449.8	447.6	444.5	440.4	436.3	432.2	428.1	426.1
30°	443.6	441.2	438.9	436.6	434.3	430.9	426.4	422.0	417.6	413.2	410.9
32.5°	430.4	427.8	425.2	422.5	419.8	416.3	411.7	407.2	402.6	398.1	395.3
35°	409.8	406.8	403.9	400.8	397.8	394.0	389.3	384.6	380.0	375.2	372.0
37.5°	387.8	384.7	381.7	378.5	375.4	371.3	366.0	360.9	355.7	350.5	347.0
40°	372.3	369.2	366.0	363.0	359.9	355.7	350.4	345.0	339.7	334.3	330.4
42.5°	357.4	354.2	350.9	347.7	344.5	340.0	334.5	328.9	323.3	317.7	313.7
45°	334.3	330.8	327.3	323.9	320.4	315.8	310.2	304.6	299.0	293.4	288.7
47.5°	310.4	306.8	303.3	299.6	296.0	291.3	285.5	279.6	273.8	268.0	263.1
50°	294.2	290.5	286.9	283.2	279.6	274.7	268.8	262.7	256.7	250.7	246.0
52.5°	277.7	274.0	270.5	266.9	263.3	258.4	252.3	246.1	240.0	233.8	229.1
55°	253.2	249.5	245.8	242.0	238.3	233.3	227.2	221.1	215.0	208.9	204.0
57.5°	229.1	225.2	221.3	217.4	213.5	208.6	202.5	196.5	190.6	184.5	179.6
60°	211.9	208.1	204.4	200.6	196.9	192.0	186.0	179.9	174.0	168.0	163.1
62.5°	196.4	192.4	188.5	184.7	180.7	175.8	169.6	163.5	157.3	151.1	146.6
65°	172.2	168.2	164.2	160.2	156.0	151.1	145.1	139.0	133.0	127.1	123.1
67.5°	147.1	143.3	139.4	135.5	131.7	127.0	121.4	115.8	110.2	104.7	101.2
70°	131.3	127.3	123.4	119.5	115.5	110.8	105.5	100.1	94.8	89.4	86.4
72.5°	114.4	110.8	107.3	103.7	100.1	95.9	90.8	85.7	80.7	75.6	73.0
75°	91.6	88.1	84.6	81.1	77.7	73.7	69.4	64.9	60.5	56.2	53.9
77.5°	68.5	65.5	62.6	59.7	56.7	53.4	49.8	46.3	42.7	39.1	37.9
80°	53.6	50.9	48.2	45.5	42.7	39.9	37.2	34.3	31.5	28.7	28.4
82.5°	40.8	38.3	35.8	33.3	30.8	28.7	27.1	25.5	23.9	22.3	22.1
85°	22.8	21.0	19.1	17.1	15.2	14.2	13.9	13.6	13.4	13.1	12.9
87.5°	7.9	7.8	7.8	7.4	7.0	6.7	7.8	7.8	8.1	8.5	8.2
90°	1.1	3.1	6.2	7.2	8.3	8.3	14.5	14.5	16.6	18.6	17.7
92.5°	11.8	17.2	26.9	39.6	54.8	76.2	128.9	209.3	287.7	328.7	273.8
95°	34.2	37.3	47.7	61.2	86.0	129.6	219.6	389.6	637.2	844.5	868.3
97.5°	61.3	61.3	70.3	82.7	104.1	140.5	209.9	350.3	596.4	889.5	1090.9
100°	78.7	78.7	86.0	98.4	118.2	151.3	212.4	329.5	540.9	833.0	1098.3
102.5°	95.3	97.0	103.4	115.0	133.8	165.4	220.7	323.7	503.5	762.6	1036.2
105°	121.3	124.3	129.6	142.0	160.6	190.6	240.4	326.4	471.4	679.8	923.2
107.5°	149.8	151.9	157.1	170.3	188.2	217.8	263.4	341.7	465.7	633.3	832.1
110°	168.9	170.9	176.1	188.6	207.2	235.2	280.8	353.3	467.3	617.6	786.5



TEST NUMBER: P332894-940

CATALOG NUMBER: S124RDIP-S350D1205U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	187.2	189.2	195.2	206.8	225.5	253.4	297.4	365.8	472.3	610.1	760.7
115°	213.5	216.6	223.8	234.2	253.9	281.9	323.2	385.5	481.8	606.2	736.7
117.5°	240.8	243.7	250.1	261.5	280.0	309.0	348.4	405.6	492.0	605.1	725.9
120°	259.0	261.1	268.4	279.7	297.4	326.4	365.8	419.6	499.4	605.1	720.1
122.5°	275.6	277.7	285.0	295.5	314.8	343.0	382.4	432.9	506.9	604.3	713.5
125°	297.4	301.5	307.7	319.1	338.9	367.8	405.1	452.8	518.1	603.1	702.5
127.5°	316.6	319.9	327.4	340.5	361.0	390.2	426.2	470.0	527.0	600.7	687.8
130°	327.4	331.5	339.8	355.4	375.1	405.1	440.4	480.8	533.6	599.9	678.7
132.5°	338.2	341.5	352.3	367.0	388.3	416.8	452.0	491.6	539.4	599.1	670.4
135°	353.3	357.5	367.8	385.5	407.2	434.2	468.3	505.7	548.1	597.9	658.0
137.5°	368.5	372.4	383.8	400.6	423.2	448.9	480.8	515.6	553.3	597.6	647.2
140°	379.2	382.4	393.8	411.3	433.1	458.0	489.1	522.2	557.5	596.8	641.4
142.5°	390.8	394.0	404.5	421.3	442.2	466.3	496.5	527.2	560.8	596.8	636.4
145°	407.2	410.4	420.7	435.2	454.9	477.7	504.6	532.6	562.7	594.8	627.9
147.5°	425.6	426.7	435.8	450.8	467.1	487.6	512.9	537.3	563.7	591.0	620.3
150°	437.3	438.3	446.6	459.1	474.6	494.3	517.0	539.8	563.7	588.5	614.5
152.5°	448.0	448.3	456.6	468.1	482.1	500.1	520.4	541.5	562.0	584.4	607.8
155°	463.2	464.2	470.4	480.8	492.2	507.7	525.3	543.0	559.5	578.2	597.9
157.5°	477.9	477.9	483.7	491.8	501.7	514.0	528.9	543.0	556.9	571.8	587.7
160°	487.0	487.0	491.2	498.4	506.7	518.1	530.5	543.0	554.4	566.8	580.2
162.5°	495.3	494.5	497.8	504.2	511.7	520.6	532.2	543.0	551.9	561.8	573.6
165°	504.6	504.6	506.7	511.8	517.0	523.3	532.6	540.9	547.1	554.4	562.7
167.5°	514.0	512.9	514.0	517.9	520.8	525.6	532.4	538.4	542.2	546.9	552.7
170°	518.1	517.0	518.1	521.2	523.3	526.4	531.5	536.7	538.8	541.9	546.1
172.5°	522.2	521.2	521.4	523.7	525.0	527.2	530.7	535.1	535.5	536.9	540.3
175°	526.4	525.3	525.3	526.4	527.4	527.4	529.5	532.6	531.5	531.5	533.6
177.5°	528.2	527.4	526.6	527.4	527.4	527.4	528.2	529.9	528.2	528.2	529.1
180°	527.4	527.4	527.4	527.4	527.4	527.4	527.4	527.4	527.4	527.4	527.4



TEST NUMBER: P332894-940

CATALOG NUMBER: S124RDIP-S350D1205U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	551.3	551.3	551.3	551.3	551.3	551.3	551.3	551.3
2.5°	549.2	550.0	550.8	551.2	551.1	551.1	551.0	550.9
5°	545.5	546.4	547.4	547.8	547.6	547.4	547.2	547.0
7.5°	538.2	538.9	539.5	539.6	539.3	539.0	538.7	538.4
10°	531.7	532.1	532.4	532.4	532.1	531.7	531.4	531.0
12.5°	523.6	523.9	524.1	524.0	523.4	522.9	522.4	521.8
15°	509.5	509.3	509.1	508.7	508.0	507.4	506.8	506.0
17.5°	492.4	492.0	491.4	490.6	489.6	488.7	487.7	486.7
20°	480.5	479.7	479.0	478.0	476.8	475.5	474.4	473.1
22.5°	467.3	466.1	465.0	464.0	463.0	462.0	461.0	459.9
25°	445.9	444.3	442.7	441.5	440.5	439.5	438.6	437.7
27.5°	424.1	422.1	420.2	418.6	417.1	415.8	414.5	413.1
30°	408.5	406.2	403.9	401.9	400.4	399.0	397.4	395.9
32.5°	392.6	389.9	387.2	385.0	383.6	382.2	380.8	379.3
35°	368.8	365.7	362.5	360.1	358.4	356.7	355.0	353.3
37.5°	343.4	339.8	336.3	333.6	331.9	330.2	328.5	326.8
40°	326.4	322.4	318.5	315.8	314.1	312.4	310.7	309.0
42.5°	309.7	305.7	301.7	298.8	297.0	295.2	293.5	291.8
45°	284.2	279.6	274.9	271.8	270.1	268.4	266.7	265.1
47.5°	258.4	253.6	248.9	245.6	243.7	241.8	240.0	238.2
50°	241.3	236.7	231.9	228.7	226.9	225.2	223.4	221.6
52.5°	224.3	219.5	214.8	211.4	209.6	207.8	205.9	204.0
55°	199.2	194.3	189.4	186.1	184.3	182.5	180.7	179.0
57.5°	174.6	169.7	164.7	161.6	160.2	158.9	157.5	156.1
60°	158.2	153.4	148.5	145.3	143.7	142.3	140.8	139.3
62.5°	142.1	137.6	133.1	130.3	129.0	127.9	126.6	125.5
65°	119.0	114.9	110.9	108.3	107.2	106.1	105.0	103.8
67.5°	97.7	94.3	90.8	88.5	87.2	86.0	84.7	83.5
70°	83.3	80.2	77.1	75.1	74.1	73.2	72.2	71.3
72.5°	70.4	67.7	65.1	63.3	62.4	61.6	60.7	59.8
75°	51.8	49.7	47.5	46.2	45.6	45.0	44.5	43.9
77.5°	36.6	35.4	34.2	33.4	33.3	33.1	32.9	32.7
80°	28.2	27.8	27.6	27.4	27.3	27.2	27.1	27.0
82.5°	21.8	21.7	21.5	21.3	21.2	21.1	21.0	21.0
85°	12.8	12.5	12.3	12.2	12.2	12.2	12.2	12.2
87.5°	8.3	8.5	8.6	8.6	8.8	9.1	9.0	9.1
90°	18.6	19.7	20.7	20.7	21.8	22.8	21.8	21.8
92.5°	203.5	153.1	121.9	101.1	88.9	83.3	79.8	79.8
95°	767.8	607.2	468.3	367.8	317.1	285.0	266.3	252.8
97.5°	1134.4	1074.7	973.4	865.2	790.8	728.4	697.3	675.8
100°	1249.6	1270.3	1219.6	1142.9	1052.8	989.5	958.5	950.2
102.5°	1243.8	1346.6	1361.3	1329.4	1274.1	1228.2	1195.5	1188.9
105°	1160.5	1339.8	1442.3	1484.8	1486.9	1478.6	1464.1	1457.9
107.5°	1042.1	1233.1	1377.5	1469.9	1521.1	1544.7	1555.1	1557.8
110°	970.9	1150.1	1300.4	1414.3	1487.9	1531.4	1550.2	1559.4



TEST NUMBER: P332894-940

CATALOG NUMBER: S124RDIP-S350D1205U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	918.6	1077.2	1219.1	1333.1	1416.7	1469.3	1495.4	1510.6
115°	866.2	993.7	1114.9	1214.4	1296.3	1358.4	1391.6	1399.9
117.5°	840.5	946.0	1041.3	1125.7	1195.5	1247.8	1281.3	1287.7
120°	828.9	925.3	1008.2	1081.7	1140.9	1186.4	1213.4	1224.8
122.5°	818.9	912.0	987.5	1052.0	1101.9	1140.9	1163.6	1175.0
125°	802.0	891.1	962.6	1019.6	1061.0	1091.1	1110.8	1117.0
127.5°	781.2	866.5	937.7	991.8	1033.5	1060.2	1076.8	1083.0
130°	764.7	846.6	917.0	972.0	1014.4	1040.3	1056.9	1063.1
132.5°	747.3	824.2	893.0	947.9	989.5	1018.8	1034.5	1040.7
135°	723.3	790.6	853.8	905.6	947.1	976.1	992.7	998.9
137.5°	701.5	758.5	811.7	858.5	897.3	926.0	939.6	947.1
140°	689.0	737.7	784.3	827.9	864.2	887.0	901.4	909.7
142.5°	677.4	720.3	760.4	798.1	830.2	851.3	864.2	870.0
145°	661.1	696.3	727.4	756.4	782.3	800.0	810.3	815.5
147.5°	647.6	675.6	700.4	723.3	742.3	757.4	765.4	767.1
150°	639.4	663.2	683.9	702.5	719.1	732.5	738.8	739.9
152.5°	630.2	650.7	669.8	685.1	699.2	710.2	713.9	715.0
155°	616.5	633.1	648.6	661.1	671.5	679.8	682.9	682.9
157.5°	601.8	615.7	628.7	638.7	646.6	652.8	654.7	654.7
160°	592.7	604.0	615.5	623.8	630.0	636.2	637.2	637.2
162.5°	583.5	593.3	602.3	609.7	614.2	620.5	621.5	620.6
165°	571.0	577.1	584.4	589.6	593.7	597.9	596.8	595.8
167.5°	558.7	563.5	569.3	572.4	574.4	577.1	576.9	576.1
170°	551.3	554.4	558.5	561.6	563.7	564.7	563.7	563.7
172.5°	544.6	546.9	549.4	551.6	552.9	553.9	552.9	551.3
175°	535.7	536.7	538.8	538.8	538.8	540.9	538.8	536.7
177.5°	529.9	530.7	530.7	531.5	530.7	531.5	529.9	528.2
180°	527.4	527.4	527.4	527.4	527.4	527.4	527.4	527.4

(END OF REPORT)