

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332880-940

Luminaire Tested: **S124RDIP-S350D810U940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332880-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIP-S350D810U940-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 810 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4159.8 lumens
Efficiency: N/A
Efficacy: 133.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 31.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332880-940

CATALOG NUMBER: S124RDIP-S350D810U940-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332880-940

CATALOG NUMBER: S124RDIP-S350D810U940-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	38	38	38	31
1	94	89	86	82	84	81	77	75	64	62	60	48	47	46	34	33	33	26
2	85	78	72	68	76	71	66	61	56	53	50	43	40	38	30	29	28	22
3	78	69	62	56	70	62	56	51	49	45	42	38	35	33	27	25	24	19
4	71	61	53	48	64	55	49	44	44	39	36	34	31	28	24	22	21	16
5	65	54	46	41	58	49	42	37	39	34	31	30	27	24	22	20	18	14
6	60	49	41	35	54	44	37	32	35	30	27	27	24	21	20	18	16	13
7	56	44	36	31	50	40	33	28	32	27	24	25	21	19	18	16	14	11
8	51	40	32	27	46	36	30	25	29	24	21	23	19	17	17	14	13	10
9	48	36	29	24	43	33	27	22	27	22	19	21	17	15	15	13	11	9
10	45	33	26	21	40	30	24	20	24	20	17	19	16	13	14	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4451	4451	4451
5°	4460	4406	4433
10°	4432	4353	4353
15°	4381	4262	4229
20°	4312	4141	4064
25°	4222	4000	3899
30°	4135	3852	3691
35°	4039	3698	3482
40°	3923	3523	3256
45°	3817	3350	3027
50°	3695	3149	2783
55°	3564	2940	2519
60°	3421	2713	2249
65°	3289	2428	1983
70°	3099	2110	1683
75°	2857	1753	1369
80°	2492	1334	1255
85°	2112	1213	1130



TEST NUMBER: P332880-940

CATALOG NUMBER: S124RDIP-S350D810U940-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	51.8	1.2
10°-20°	144.4	3.5
20°-30°	208.5	5.0
30°-40°	236.4	5.7
40°-50°	228.2	5.5
50°-60°	189.8	4.6
60°-70°	131.1	3.2
70°-80°	66.4	1.6
80°-90°	19.7	0.5
90°-100°	31.9	0.8
100°-110°	203.3	4.9
110°-120°	388.9	9.3
120°-130°	493.7	11.9
130°-140°	528.2	12.7
140°-150°	493.9	11.9
150°-160°	398.3	9.6
160°-170°	256.9	6.2
170°-180°	88.5	2.1
0°-30°	404.7	9.7
0°-40°	641.0	15.4
0°-60°	1059.1	25.5
0°-90°	1276.3	30.7
90°-120°	624.1	15.0
90°-150°	2139.8	51.4
90°-180°	2884.0	69.3
0°-180°	4159.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	551	551	551	551	551	
5°	550	548	544	548	547	52
15°	524	520	510	509	506	148
25°	474	466	449	442	438	218
35°	410	396	375	361	353	256
45°	334	318	293	273	265	258
55°	253	236	209	188	179	226
65°	172	154	127	110	104	170
75°	92	76	56	47	44	97
85°	23	15	13	12	12	26
90°	2	10	15	19	21	3
95°	38	16	15	19	20	49
105°	210	214	218	222	199	220
115°	392	394	393	395	395	385
125°	551	553	552	554	555	492
135°	683	683	685	687	688	526
145°	788	790	790	791	792	492
155°	864	864	862	865	863	398
165°	911	908	908	913	907	257
175°	932	928	929	934	927	89
180°	932	932	932	932	932	



TEST NUMBER: P332880-940

CATALOG NUMBER: S124RDIP-S350D810U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	551.3	551.3	551.3	551.3	551.3	551.3	551.3	551.3	551.3	551.3	551.3
2.5°	552.6	552.2	552.0	551.7	551.3	550.8	550.0	549.2	548.3	547.5	548.3
5°	550.4	550.0	549.7	549.3	548.8	548.1	547.0	545.9	544.7	543.7	544.6
7.5°	545.4	545.0	544.7	544.2	543.9	542.9	541.4	539.9	538.5	537.1	537.6
10°	540.6	540.2	539.8	539.3	538.8	537.7	536.0	534.3	532.6	531.0	531.4
12.5°	534.6	534.0	533.5	533.0	532.4	531.2	529.1	527.2	525.2	523.2	523.4
15°	524.2	523.3	522.5	521.7	520.8	519.2	516.9	514.5	512.2	509.9	509.7
17.5°	511.7	510.4	509.2	508.0	506.8	504.7	501.9	499.1	496.3	493.5	492.9
20°	501.9	500.6	499.4	498.2	497.0	494.8	491.6	488.4	485.2	482.0	481.3
22.5°	491.1	489.6	488.3	487.0	485.5	483.1	479.7	476.4	473.0	469.5	468.4
25°	474.0	472.3	470.6	469.0	467.3	464.5	460.7	456.8	452.9	449.1	447.5
27.5°	456.1	454.0	451.8	449.8	447.6	444.5	440.4	436.3	432.2	428.1	426.1
30°	443.6	441.2	438.9	436.6	434.3	430.9	426.4	422.0	417.6	413.2	410.9
32.5°	430.4	427.8	425.2	422.5	419.8	416.3	411.7	407.2	402.6	398.1	395.3
35°	409.8	406.8	403.9	400.8	397.8	394.0	389.3	384.6	380.0	375.2	372.0
37.5°	387.8	384.7	381.7	378.5	375.4	371.3	366.0	360.9	355.7	350.5	347.0
40°	372.3	369.2	366.0	363.0	359.9	355.7	350.4	345.0	339.7	334.3	330.4
42.5°	357.4	354.2	350.9	347.7	344.5	340.0	334.5	328.9	323.3	317.7	313.7
45°	334.3	330.8	327.3	323.9	320.4	315.8	310.2	304.6	299.0	293.4	288.7
47.5°	310.4	306.8	303.3	299.6	296.0	291.3	285.5	279.6	273.8	268.0	263.1
50°	294.2	290.5	286.9	283.2	279.6	274.7	268.8	262.7	256.7	250.7	246.0
52.5°	277.7	274.0	270.5	266.9	263.3	258.4	252.3	246.1	240.0	233.8	229.1
55°	253.2	249.5	245.8	242.0	238.3	233.3	227.2	221.1	215.0	208.9	204.0
57.5°	229.1	225.2	221.3	217.4	213.5	208.6	202.5	196.5	190.6	184.5	179.6
60°	211.9	208.1	204.4	200.6	196.9	192.0	186.0	179.9	174.0	168.0	163.1
62.5°	196.4	192.4	188.5	184.7	180.7	175.8	169.6	163.5	157.3	151.1	146.6
65°	172.2	168.2	164.2	160.2	156.0	151.1	145.1	139.0	133.0	127.1	123.1
67.5°	147.1	143.3	139.4	135.5	131.7	127.0	121.4	115.8	110.2	104.7	101.2
70°	131.3	127.3	123.4	119.5	115.5	110.8	105.5	100.1	94.8	89.4	86.4
72.5°	114.4	110.8	107.3	103.7	100.1	95.9	90.8	85.7	80.7	75.6	73.0
75°	91.6	88.1	84.6	81.1	77.7	73.7	69.4	64.9	60.5	56.2	53.9
77.5°	68.5	65.5	62.6	59.7	56.7	53.4	49.8	46.3	42.7	39.1	37.9
80°	53.6	50.9	48.2	45.5	42.7	39.9	37.2	34.3	31.5	28.7	28.4
82.5°	40.8	38.3	35.8	33.3	30.8	28.7	27.1	25.5	23.9	22.3	22.1
85°	22.8	21.0	19.1	17.1	15.2	14.2	13.9	13.6	13.4	13.1	12.9
87.5°	8.2	7.9	7.7	7.4	7.1	7.1	7.3	7.5	7.6	7.8	7.9
90°	2.1	3.8	5.5	7.2	8.9	10.3	11.6	12.8	14.1	15.3	16.2
92.5°	8.8	8.9	9.0	9.1	9.2	9.8	11.1	12.3	13.6	14.8	15.7
95°	38.3	33.1	27.8	22.6	17.3	14.7	14.9	15.1	15.2	15.3	16.2
97.5°	81.4	84.7	88.0	91.3	94.6	87.6	70.3	53.0	35.7	18.4	18.5
100°	114.3	117.2	119.9	122.7	125.5	116.2	94.8	73.5	52.1	30.7	28.0
102.5°	151.1	153.2	155.2	157.3	159.3	159.0	156.1	153.4	150.6	147.8	119.4
105°	209.8	210.8	211.7	212.7	213.6	214.5	215.2	216.0	216.8	217.5	218.9
107.5°	264.4	264.8	265.3	265.8	266.3	267.0	268.0	269.1	270.2	271.3	271.9
110°	301.2	301.7	302.1	302.6	303.1	303.7	304.7	305.6	306.6	307.5	307.8



TEST NUMBER: P332880-940

CATALOG NUMBER: S124RDIP-S350D810U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	336.9	337.7	338.6	339.4	340.3	340.9	341.3	341.7	342.1	342.6	342.6
115°	391.8	392.3	392.8	393.2	393.7	393.9	393.7	393.5	393.4	393.2	393.5
117.5°	441.3	441.9	442.6	443.2	443.8	444.3	444.6	445.0	445.3	445.7	445.6
120°	474.8	475.5	476.1	476.7	477.2	477.5	477.3	477.2	477.1	476.9	477.2
122.5°	506.0	506.4	506.8	507.1	507.6	507.8	508.0	508.3	508.5	508.7	508.9
125°	550.8	551.4	552.1	552.7	553.3	553.4	553.1	552.9	552.5	552.2	552.7
127.5°	593.2	593.3	593.5	593.7	593.8	594.2	594.9	595.7	596.4	597.1	597.0
130°	620.5	620.7	620.8	621.0	621.2	621.4	621.9	622.4	622.9	623.3	623.5
132.5°	645.6	645.9	646.2	646.5	646.8	647.2	647.7	648.4	648.9	649.5	649.7
135°	683.3	683.1	683.0	682.8	682.7	682.9	683.5	684.1	684.7	685.4	685.6
137.5°	716.6	716.7	716.8	716.8	716.8	717.2	717.9	718.6	719.3	720.0	720.3
140°	738.3	738.7	739.0	739.3	739.6	739.9	740.2	740.6	740.8	741.1	741.6
142.5°	757.9	758.4	759.0	759.6	760.1	760.5	760.6	760.9	761.1	761.3	761.6
145°	787.8	788.4	788.8	789.3	789.7	790.0	790.0	790.0	790.0	790.0	790.1
147.5°	811.7	812.6	813.4	814.3	815.2	815.6	815.4	815.2	815.0	814.9	815.0
150°	829.0	829.6	830.3	830.9	831.4	831.7	831.5	831.4	831.3	831.1	831.1
152.5°	843.5	844.0	844.5	845.0	845.5	845.6	845.3	845.1	844.7	844.5	844.7
155°	863.9	864.0	864.2	864.3	864.5	864.3	863.9	863.4	862.9	862.5	863.1
157.5°	881.0	880.9	880.8	880.7	880.7	880.3	879.8	879.3	878.8	878.2	879.0
160°	891.1	890.6	890.1	889.7	889.2	888.9	888.8	888.6	888.4	888.2	889.2
162.5°	900.0	899.4	898.8	898.2	897.6	897.2	897.1	897.0	896.8	896.6	897.6
165°	911.2	910.5	909.7	908.9	908.2	907.8	907.8	907.8	907.8	907.8	909.0
167.5°	920.2	919.4	918.6	917.7	916.9	916.5	916.4	916.3	916.2	916.1	917.5
170°	925.2	924.3	923.4	922.4	921.5	921.1	921.2	921.4	921.6	921.8	922.9
172.5°	928.5	927.6	926.7	925.8	924.9	924.4	924.6	924.8	924.9	925.1	926.3
175°	932.2	931.2	930.3	929.4	928.4	928.1	928.3	928.4	928.5	928.7	930.1
177.5°	933.9	933.0	932.1	931.2	930.4	930.1	930.3	930.6	930.9	931.0	932.0
180°	932.2	932.2	932.2	932.2	932.2	932.2	932.2	932.2	932.2	932.2	932.2



TEST NUMBER: P332880-940

CATALOG NUMBER: S124RDIP-S350D810U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	551.3	551.3	551.3	551.3	551.3	551.3	551.3	551.3
2.5°	549.2	550.0	550.8	551.2	551.1	551.1	551.0	550.9
5°	545.5	546.4	547.4	547.8	547.6	547.4	547.2	547.0
7.5°	538.2	538.9	539.5	539.6	539.3	539.0	538.7	538.4
10°	531.7	532.1	532.4	532.4	532.1	531.7	531.4	531.0
12.5°	523.6	523.9	524.1	524.0	523.4	522.9	522.4	521.8
15°	509.5	509.3	509.1	508.7	508.0	507.4	506.8	506.0
17.5°	492.4	492.0	491.4	490.6	489.6	488.7	487.7	486.7
20°	480.5	479.7	479.0	478.0	476.8	475.5	474.4	473.1
22.5°	467.3	466.1	465.0	464.0	463.0	462.0	461.0	459.9
25°	445.9	444.3	442.7	441.5	440.5	439.5	438.6	437.7
27.5°	424.1	422.1	420.2	418.6	417.1	415.8	414.5	413.1
30°	408.5	406.2	403.9	401.9	400.4	399.0	397.4	395.9
32.5°	392.6	389.9	387.2	385.0	383.6	382.2	380.8	379.3
35°	368.8	365.7	362.5	360.1	358.4	356.7	355.0	353.3
37.5°	343.4	339.8	336.3	333.6	331.9	330.2	328.5	326.8
40°	326.4	322.4	318.5	315.8	314.1	312.4	310.7	309.0
42.5°	309.7	305.7	301.7	298.8	297.0	295.2	293.5	291.8
45°	284.2	279.6	274.9	271.8	270.1	268.4	266.7	265.1
47.5°	258.4	253.6	248.9	245.6	243.7	241.8	240.0	238.2
50°	241.3	236.7	231.9	228.7	226.9	225.2	223.4	221.6
52.5°	224.3	219.5	214.8	211.4	209.6	207.8	205.9	204.0
55°	199.2	194.3	189.4	186.1	184.3	182.5	180.7	179.0
57.5°	174.6	169.7	164.7	161.6	160.2	158.9	157.5	156.1
60°	158.2	153.4	148.5	145.3	143.7	142.3	140.8	139.3
62.5°	142.1	137.6	133.1	130.3	129.0	127.9	126.6	125.5
65°	119.0	114.9	110.9	108.3	107.2	106.1	105.0	103.8
67.5°	97.7	94.3	90.8	88.5	87.2	86.0	84.7	83.5
70°	83.3	80.2	77.1	75.1	74.1	73.2	72.2	71.3
72.5°	70.4	67.7	65.1	63.3	62.4	61.6	60.7	59.8
75°	51.8	49.7	47.5	46.2	45.6	45.0	44.5	43.9
77.5°	36.6	35.4	34.2	33.4	33.3	33.1	32.9	32.7
80°	28.2	27.8	27.6	27.4	27.3	27.2	27.1	27.0
82.5°	21.8	21.7	21.5	21.3	21.2	21.1	21.0	21.0
85°	12.8	12.5	12.3	12.2	12.2	12.2	12.2	12.2
87.5°	8.0	8.1	8.2	8.4	8.5	8.6	8.7	8.9
90°	17.2	18.1	19.1	19.7	20.0	20.3	20.6	21.0
92.5°	16.7	17.6	18.5	19.0	19.1	19.1	19.2	19.3
95°	17.2	18.1	19.1	19.6	19.8	19.9	20.1	20.2
97.5°	18.6	18.7	18.8	18.9	19.1	19.2	19.4	19.5
100°	25.4	22.7	20.2	18.9	19.1	19.2	19.4	19.5
102.5°	91.0	62.6	34.2	20.0	20.0	20.0	20.1	20.1
105°	220.3	221.7	223.1	221.1	215.4	209.8	204.3	198.7
107.5°	272.6	273.2	273.9	274.6	275.2	275.7	276.3	277.0
110°	308.1	308.4	308.7	309.1	309.6	310.0	310.5	310.9



TEST NUMBER: P332880-940

CATALOG NUMBER: S124RDIP-S350D810U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	342.5	342.4	342.3	342.6	343.2	343.8	344.4	345.0
115°	393.9	394.1	394.5	394.7	394.7	394.7	394.7	394.7
117.5°	445.5	445.5	445.4	445.3	445.3	445.2	445.1	445.1
120°	477.5	477.9	478.1	478.1	477.9	477.5	477.2	476.9
122.5°	509.1	509.3	509.4	509.3	509.1	508.7	508.5	508.1
125°	553.1	553.6	554.0	554.4	554.6	554.6	554.8	555.0
127.5°	596.9	596.8	596.7	596.6	596.5	596.4	596.3	596.1
130°	623.7	623.8	623.9	624.0	624.0	624.0	624.0	624.0
132.5°	649.9	650.0	650.1	650.1	650.1	649.9	649.8	649.7
135°	686.0	686.3	686.6	686.9	687.2	687.5	687.9	688.1
137.5°	720.6	720.9	721.3	721.4	721.3	721.2	721.1	721.0
140°	742.1	742.5	743.0	743.3	743.5	743.6	743.8	744.0
142.5°	761.9	762.2	762.6	762.8	762.8	762.9	762.9	762.9
145°	790.2	790.4	790.6	790.8	791.1	791.4	791.8	792.0
147.5°	815.2	815.3	815.4	815.6	815.7	815.8	816.0	816.2
150°	831.1	831.1	831.1	831.2	831.3	831.4	831.6	831.8
152.5°	845.0	845.3	845.4	845.5	845.4	845.3	845.3	845.2
155°	863.7	864.3	865.0	865.0	864.5	864.1	863.6	863.2
157.5°	879.9	880.7	881.5	881.5	880.7	879.9	879.0	878.2
160°	890.1	891.1	892.0	892.0	891.1	890.1	889.2	888.2
162.5°	898.5	899.4	900.4	900.3	899.2	898.1	897.2	896.1
165°	910.3	911.5	912.8	912.7	911.2	909.9	908.5	907.0
167.5°	918.9	920.2	921.6	921.5	920.0	918.4	916.9	915.3
170°	924.2	925.4	926.7	926.5	925.0	923.5	921.9	920.3
172.5°	927.6	928.8	930.1	929.8	928.2	926.5	924.8	923.1
175°	931.5	932.9	934.2	934.1	932.2	930.3	928.4	926.6
177.5°	933.1	934.1	935.0	934.8	933.3	931.8	930.3	928.8
180°	932.2	932.2	932.2	932.2	932.2	932.2	932.2	932.2

(END OF REPORT)