

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332936-940

Luminaire Tested: **S124RDIP-S795D590U940-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332936-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124RDIP-S795D590U940-4F0-1E-UDD-F4  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 795 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 590 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4746.4 lumens  
Efficiency: N/A  
Efficacy: 117.8 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 40.3  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332936-940

CATALOG NUMBER: S124RDIP-S795D590U940-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P332936-940

CATALOG NUMBER: S124RDIP-S795D590U940-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	102	102	102	102	89	89	89	77	77	77	66	66	66	60
1	100	96	92	89	94	90	87	84	79	76	74	68	66	65	59	57	56	51
2	92	84	78	73	86	79	74	69	69	65	62	60	57	55	52	50	48	44
3	84	74	67	61	78	70	63	58	61	56	52	54	50	47	46	43	41	37
4	77	66	58	52	72	62	55	50	55	49	45	48	44	40	42	38	36	32
5	71	59	51	45	66	56	48	43	49	43	39	43	39	35	38	34	31	28
6	65	53	45	39	61	50	43	38	44	39	34	39	34	31	34	30	28	25
7	60	48	40	35	56	46	38	33	40	35	30	36	31	27	31	28	25	22
8	56	44	36	31	53	41	34	29	37	31	27	33	28	25	29	25	22	20
9	52	40	33	28	49	38	31	26	34	28	24	30	26	22	27	23	20	18
10	49	37	30	25	46	35	28	24	31	26	22	28	23	20	25	21	18	16

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	10001	10001	10001
5°	10023	9900	9961
10°	9960	9781	9781
15°	9845	9576	9504
20°	9688	9306	9135
25°	9487	8989	8761
30°	9292	8655	8294
35°	9077	8310	7824
40°	8816	7917	7317
45°	8576	7526	6801
50°	8303	7076	6253
55°	8010	6608	5661
60°	7689	6095	5054
65°	7393	5454	4458
70°	6963	4747	3784
75°	6419	3936	3075
80°	5602	2999	2822
85°	4742	2723	2547



TEST NUMBER: P332936-940

CATALOG NUMBER: S124RDIP-S795D590U940-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	116.4	2.5
10°-20°	324.5	6.8
20°-30°	468.6	9.9
30°-40°	531.1	11.2
40°-50°	512.9	10.8
50°-60°	426.5	9.0
60°-70°	294.5	6.2
70°-80°	149.3	3.1
80°-90°	39.7	0.8
90°-100°	187.0	3.9
100°-110°	389.2	8.2
110°-120°	348.6	7.3
120°-130°	293.2	6.2
130°-140°	244.5	5.2
140°-150°	186.8	3.9
150°-160°	131.3	2.8
160°-170°	77.2	1.6
170°-180°	25.1	0.5
0°-30°	909.4	19.2
0°-40°	1440.5	30.3
0°-60°	2379.9	50.1
0°-90°	2863.4	60.3
90°-120°	924.8	19.5
90°-150°	1649.4	34.8
90°-180°	1883.0	39.7
0°-180°	4746.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1239	1239	1239	1239	1239	
5°	1237	1233	1222	1230	1229	117
15°	1178	1169	1146	1144	1137	332
25°	1065	1047	1009	993	984	491
35°	921	890	843	812	794	575
45°	751	715	659	614	596	579
55°	569	530	470	422	402	509
65°	387	345	286	246	233	382
75°	206	170	126	105	99	217
85°	51	33	29	28	28	58
90°	0	4	9	10	11	3
95°	17	53	415	205	124	19
105°	60	86	334	719	716	63
115°	105	132	298	572	687	104
125°	146	173	296	486	548	130
135°	173	206	294	432	490	134
145°	200	229	292	364	400	125
155°	227	245	284	321	335	105
165°	248	255	272	288	292	70
175°	258	259	261	264	264	25
180°	259	259	259	259	259	



TEST NUMBER: P332936-940

CATALOG NUMBER: S124RDIP-S795D590U940-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8
2.5°	1241.8	1241.1	1240.4	1239.7	1239.0	1237.8	1235.9	1234.1	1232.3	1230.4	1232.3
5°	1236.8	1236.0	1235.1	1234.3	1233.4	1231.8	1229.2	1226.7	1224.1	1221.6	1223.8
7.5°	1225.7	1224.8	1223.9	1223.0	1222.1	1220.0	1216.7	1213.4	1210.1	1206.8	1208.2
10°	1215.0	1214.0	1212.9	1211.8	1210.8	1208.4	1204.6	1200.8	1197.0	1193.2	1194.0
12.5°	1201.3	1200.2	1198.9	1197.7	1196.5	1193.6	1189.2	1184.6	1180.2	1175.7	1176.3
15°	1178.0	1176.2	1174.2	1172.3	1170.5	1166.9	1161.5	1156.3	1151.0	1145.8	1145.3
17.5°	1149.8	1147.0	1144.2	1141.6	1138.8	1134.3	1127.9	1121.6	1115.3	1108.9	1107.8
20°	1127.7	1125.0	1122.3	1119.5	1116.8	1111.9	1104.7	1097.5	1090.3	1083.2	1081.5
22.5°	1103.5	1100.4	1097.3	1094.2	1091.2	1085.7	1078.1	1070.4	1062.7	1055.1	1052.6
25°	1065.1	1061.3	1057.6	1053.7	1050.0	1043.7	1035.1	1026.4	1017.8	1009.1	1005.6
27.5°	1024.9	1020.2	1015.4	1010.7	1005.8	998.9	989.6	980.4	971.2	962.0	957.5
30°	996.8	991.6	986.3	981.1	975.8	968.2	958.3	948.4	938.4	928.5	923.3
32.5°	967.2	961.4	955.4	949.4	943.5	935.4	925.1	914.9	904.6	894.4	888.3
35°	921.0	914.3	907.5	900.7	894.0	885.4	874.9	864.2	853.7	843.2	836.1
37.5°	871.5	864.5	857.6	850.6	843.6	834.4	822.7	811.0	799.3	787.6	779.6
40°	836.6	829.6	822.7	815.7	808.8	799.2	787.2	775.3	763.2	751.2	742.3
42.5°	803.2	795.9	788.6	781.3	774.0	764.1	751.6	739.0	726.6	714.0	705.0
45°	751.2	743.4	735.6	727.8	720.0	709.8	697.1	684.5	671.8	659.2	648.9
47.5°	697.5	689.5	681.4	673.3	665.3	654.7	641.6	628.4	615.3	602.1	591.4
50°	661.1	652.9	644.6	636.4	628.2	617.3	603.9	590.4	576.8	563.4	552.9
52.5°	623.9	615.9	607.8	599.8	591.7	580.8	566.9	553.1	539.3	525.5	514.8
55°	569.1	560.6	552.2	543.8	535.4	524.3	510.6	496.9	483.2	469.5	458.5
57.5°	514.9	506.0	497.3	488.6	479.7	468.6	455.1	441.7	428.2	414.6	403.6
60°	476.2	467.7	459.3	450.8	442.4	431.5	417.9	404.5	391.0	377.5	366.5
62.5°	441.2	432.5	423.7	414.9	406.2	394.8	381.0	367.2	353.4	339.6	329.4
65°	387.0	377.9	368.8	359.8	350.7	339.5	325.9	312.5	299.0	285.5	276.4
67.5°	330.6	322.0	313.3	304.6	295.9	285.3	272.8	260.3	247.7	235.2	227.4
70°	295.0	286.1	277.2	268.4	259.6	249.1	237.1	225.1	213.1	201.1	194.1
72.5°	257.1	249.1	241.0	233.0	225.0	215.3	204.0	192.6	181.3	170.0	164.0
75°	205.8	198.0	190.2	182.4	174.6	165.8	155.9	146.0	136.1	126.2	121.3
77.5°	153.8	147.2	140.6	134.0	127.3	120.0	112.1	104.1	96.0	88.0	85.2
80°	120.5	114.3	108.3	102.1	96.0	89.8	83.5	77.1	70.8	64.5	63.8
82.5°	91.7	86.1	80.4	74.8	69.2	64.6	61.0	57.3	53.7	50.1	49.6
85°	51.2	47.0	42.8	38.6	34.3	31.9	31.3	30.7	30.1	29.4	29.0
87.5°	17.6	16.4	15.3	14.1	12.8	12.1	12.6	12.4	12.4	12.5	12.2
90°	0.5	1.5	3.0	3.6	4.1	4.1	7.1	7.1	8.1	9.2	8.6
92.5°	5.8	8.5	13.2	19.4	26.8	37.5	63.3	102.7	141.2	161.3	134.4
95°	16.8	18.3	23.4	30.1	42.2	63.6	107.8	191.3	312.8	414.6	426.2
97.5°	30.1	30.1	34.5	40.6	51.1	69.0	103.1	171.9	292.8	436.7	535.6
100°	38.7	38.7	42.2	48.3	58.0	74.3	104.2	161.8	265.6	408.9	539.2
102.5°	46.8	47.6	50.7	56.4	65.7	81.1	108.3	158.9	247.2	374.4	508.6
105°	59.5	61.1	63.6	69.7	78.8	93.6	118.0	160.2	231.5	333.7	453.3
107.5°	73.6	74.5	77.1	83.6	92.4	106.9	129.3	167.7	228.6	310.9	408.5
110°	82.9	83.9	86.5	92.6	101.7	115.5	137.9	173.4	229.4	303.2	386.1



TEST NUMBER: P332936-940

CATALOG NUMBER: S124RDIP-S795D590U940-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	91.8	92.9	95.9	101.6	110.7	124.4	146.0	179.6	231.8	299.5	373.4
115°	104.8	106.3	109.9	114.9	124.7	138.4	158.7	189.2	236.6	297.6	361.7
117.5°	118.2	119.7	122.8	128.4	137.4	151.7	171.0	199.1	241.5	297.0	356.4
120°	127.2	128.2	131.7	137.3	146.0	160.2	179.6	206.0	245.2	297.0	353.6
122.5°	135.3	136.3	139.9	145.1	154.5	168.4	187.7	212.5	248.9	296.7	350.3
125°	146.0	148.0	151.1	156.7	166.3	180.6	198.9	222.3	254.3	296.0	344.9
127.5°	155.4	157.1	160.8	167.1	177.2	191.5	209.3	230.8	258.7	294.9	337.7
130°	160.8	162.7	166.8	174.5	184.1	198.9	216.2	236.0	262.0	294.5	333.1
132.5°	166.0	167.6	173.0	180.2	190.6	204.6	221.9	241.3	264.8	294.1	329.1
135°	173.4	175.5	180.6	189.2	199.9	213.1	229.9	248.3	269.1	293.5	323.0
137.5°	180.9	182.8	188.4	196.6	207.8	220.3	236.0	253.2	271.6	293.4	317.7
140°	186.2	187.7	193.3	202.0	212.6	224.8	240.1	256.4	273.7	293.0	314.9
142.5°	191.9	193.4	198.6	206.8	217.1	228.9	243.8	258.8	275.3	293.0	312.5
145°	199.9	201.4	206.5	213.7	223.3	234.5	247.7	261.4	276.3	291.9	308.3
147.5°	208.9	209.5	213.9	221.2	229.3	239.4	251.8	263.8	276.7	290.2	304.5
150°	214.6	215.2	219.3	225.3	233.0	242.6	253.9	265.0	276.7	288.9	301.7
152.5°	220.0	220.1	224.1	229.8	236.7	245.5	255.5	265.8	275.9	286.9	298.4
155°	227.4	227.9	231.0	236.0	241.7	249.2	257.9	266.5	274.6	283.8	293.5
157.5°	234.6	234.6	237.5	241.4	246.3	252.3	259.7	266.5	273.4	280.7	288.6
160°	239.1	239.1	241.1	244.7	248.7	254.3	260.5	266.5	272.2	278.2	284.9
162.5°	243.2	242.7	244.3	247.5	251.2	255.6	261.3	266.5	270.9	275.8	281.6
165°	247.7	247.7	248.7	251.3	253.9	256.9	261.4	265.6	268.6	272.2	276.3
167.5°	252.3	251.8	252.3	254.2	255.7	258.0	261.4	264.3	266.2	268.5	271.3
170°	254.3	253.9	254.3	255.8	256.9	258.4	260.9	263.5	264.5	266.0	268.0
172.5°	256.4	255.8	255.9	257.1	257.7	258.8	260.6	262.7	262.9	263.6	265.2
175°	258.4	257.9	257.9	258.4	259.0	259.0	259.9	261.4	260.9	260.9	262.0
177.5°	259.3	259.0	258.5	259.0	259.0	259.0	259.3	260.1	259.3	259.3	259.8
180°	259.0	259.0	259.0	259.0	259.0	259.0	259.0	259.0	259.0	259.0	259.0



TEST NUMBER: P332936-940

CATALOG NUMBER: S124RDIP-S795D590U940-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8
2.5°	1234.1	1235.9	1237.8	1238.7	1238.5	1238.3	1238.1	1238.0
5°	1225.8	1228.0	1230.1	1230.9	1230.5	1230.1	1229.7	1229.2
7.5°	1209.5	1210.9	1212.3	1212.5	1211.9	1211.2	1210.6	1209.9
10°	1194.9	1195.7	1196.6	1196.6	1195.7	1194.9	1194.0	1193.2
12.5°	1176.8	1177.2	1177.8	1177.4	1176.3	1175.1	1173.8	1172.7
15°	1145.0	1144.5	1144.1	1143.2	1141.7	1140.1	1138.7	1137.2
17.5°	1106.6	1105.5	1104.2	1102.5	1100.3	1098.1	1095.8	1093.6
20°	1079.8	1078.1	1076.4	1074.2	1071.5	1068.7	1066.0	1063.3
22.5°	1050.1	1047.5	1045.0	1042.6	1040.4	1038.1	1035.9	1033.7
25°	1002.0	998.4	994.9	992.0	989.9	987.8	985.7	983.6
27.5°	953.1	948.7	944.2	940.5	937.5	934.4	931.4	928.4
30°	918.0	912.8	907.5	903.1	899.8	896.4	893.0	889.7
32.5°	882.2	876.1	870.0	865.3	862.1	858.9	855.7	852.5
35°	828.8	821.7	814.6	809.0	805.3	801.5	797.6	793.9
37.5°	771.6	763.6	755.5	749.7	745.9	742.1	738.3	734.5
40°	733.5	724.6	715.8	709.4	705.7	701.9	698.1	694.3
42.5°	696.0	687.0	678.0	671.5	667.4	663.5	659.6	655.6
45°	638.6	628.2	617.9	610.8	607.0	603.2	599.4	595.7
47.5°	580.7	570.0	559.3	551.8	547.7	543.5	539.3	535.1
50°	542.3	531.8	521.2	514.0	510.0	506.0	501.9	497.9
52.5°	504.1	493.4	482.6	475.2	471.0	466.8	462.7	458.5
55°	447.5	436.6	425.7	418.2	414.2	410.2	406.2	402.2
57.5°	392.4	381.3	370.1	363.1	360.1	357.0	354.0	351.0
60°	355.6	344.6	333.7	326.5	323.2	319.8	316.4	313.0
62.5°	319.3	309.2	299.1	292.7	290.0	287.3	284.5	281.9
65°	267.3	258.3	249.2	243.4	240.9	238.4	235.9	233.4
67.5°	219.6	211.9	204.0	198.8	196.0	193.1	190.4	187.6
70°	187.2	180.2	173.3	168.7	166.7	164.5	162.4	160.3
72.5°	158.1	152.1	146.2	142.2	140.4	138.4	136.4	134.5
75°	116.5	111.6	106.7	103.7	102.5	101.2	99.9	98.6
77.5°	82.4	79.5	76.7	75.1	74.7	74.4	74.0	73.6
80°	63.2	62.6	62.0	61.5	61.3	61.1	60.9	60.7
82.5°	49.1	48.7	48.2	47.9	47.7	47.4	47.3	47.1
85°	28.5	28.2	27.7	27.5	27.5	27.5	27.5	27.5
87.5°	12.1	12.0	11.9	11.9	12.2	12.5	12.6	12.8
90°	9.2	9.6	10.2	10.2	10.7	11.1	10.7	10.7
92.5°	99.9	75.2	59.8	49.7	43.6	40.9	39.1	39.1
95°	376.9	298.1	229.9	180.6	155.7	139.9	130.7	124.1
97.5°	556.9	527.6	477.9	424.7	388.3	357.6	342.3	331.7
100°	613.5	623.7	598.7	561.1	516.8	485.8	470.6	466.5
102.5°	610.6	661.1	668.3	652.6	625.4	603.0	586.9	583.6
105°	569.7	657.7	708.1	729.0	730.0	725.9	718.7	715.7
107.5°	511.7	605.3	676.3	721.6	746.7	758.3	763.4	764.7
110°	476.6	564.6	638.4	694.4	730.5	751.8	761.0	765.5





TEST NUMBER: P332936-940

CATALOG NUMBER: S124RDIP-S795D590U940-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	451.0	528.8	598.5	654.4	695.4	721.3	734.1	741.5
115°	425.3	487.9	547.3	596.2	636.3	666.9	683.1	687.2
117.5°	412.6	464.4	511.2	552.6	586.9	612.5	629.0	632.2
120°	407.0	454.2	494.9	531.0	560.1	582.5	595.7	601.3
122.5°	402.1	447.7	484.7	516.4	540.9	560.1	571.2	576.8
125°	393.7	437.5	472.5	500.5	520.8	535.7	545.3	548.3
127.5°	383.5	425.3	460.4	486.9	507.4	520.5	528.6	531.6
130°	375.4	415.6	450.1	477.2	498.0	510.7	518.9	521.9
132.5°	366.8	404.6	438.4	465.3	485.8	500.2	507.8	511.0
135°	355.1	388.2	419.1	444.6	464.9	479.2	487.3	490.4
137.5°	344.4	372.4	398.5	421.5	440.5	454.6	461.3	464.9
140°	338.2	362.2	385.0	406.4	424.3	435.4	442.6	446.7
142.5°	332.6	353.7	373.3	391.8	407.5	417.9	424.3	427.0
145°	324.5	341.8	357.1	371.3	384.1	392.7	397.8	400.3
147.5°	317.9	331.6	343.8	355.1	364.4	371.8	375.7	376.7
150°	313.9	325.6	335.7	344.9	353.0	359.6	362.7	363.2
152.5°	309.3	319.4	328.8	336.4	343.2	348.7	350.4	351.0
155°	302.6	310.8	318.4	324.5	329.7	333.7	335.2	335.2
157.5°	295.4	302.3	308.6	313.5	317.4	320.5	321.4	321.4
160°	291.0	296.6	302.1	306.2	309.2	312.4	312.8	312.8
162.5°	286.5	291.2	295.6	299.3	301.6	304.6	305.1	304.7
165°	280.3	283.3	286.9	289.4	291.5	293.5	293.0	292.5
167.5°	274.3	276.6	279.5	281.0	282.0	283.3	283.2	282.9
170°	270.6	272.2	274.2	275.7	276.7	277.2	276.7	276.7
172.5°	267.3	268.5	269.7	270.8	271.4	272.0	271.4	270.6
175°	263.0	263.5	264.5	264.5	264.5	265.6	264.5	263.5
177.5°	260.1	260.6	260.6	260.9	260.6	260.9	260.1	259.3
180°	259.0	259.0	259.0	259.0	259.0	259.0	259.0	259.0

(END OF REPORT)