

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333003-930

Luminaire Tested: **S124RDIP-S1195D1035U930-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333003-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124RDIP-S1195D1035U930-4F0-1E-UDD-A  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1195 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1035 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 7453.1 lumens  
Efficiency: N/A  
Efficacy: 111.6 lumens/watt  
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39  
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 66.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333003-930

CATALOG NUMBER: S124RDIP-S1195D1035U930-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P333003-930

CATALOG NUMBER: S124RDIP-S1195D1035U930-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	55
1	99	95	91	88	92	89	85	82	76	74	72	65	63	62	54	53	52	47
2	91	84	78	73	84	78	73	69	67	64	60	58	55	52	48	46	45	40
3	83	74	67	61	77	69	63	58	60	55	51	51	48	45	43	41	39	35
4	76	66	58	52	71	62	55	49	53	48	44	46	42	39	39	36	34	30
5	70	59	51	45	65	55	48	43	48	43	38	41	37	34	35	32	30	26
6	65	53	45	39	60	50	43	37	43	38	34	38	33	30	32	29	26	23
7	60	48	40	35	56	45	38	33	40	34	30	34	30	27	29	26	23	21
8	56	44	36	31	52	41	34	29	36	31	27	31	27	24	27	24	21	19
9	52	40	33	28	48	38	31	26	33	28	24	29	25	21	25	22	19	17
10	49	37	30	25	45	35	28	24	31	25	22	27	23	19	23	20	17	15

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	13043	13043	13043	13043
5°	15129	13083	11563	13083
10°	17898	13025	10320	13025
15°	20674	12904	8868	12904
20°	23018	12740	8019	12740
25°	23762	12577	7445	12577
30°	20801	12379	7100	12379
35°	16192	12086	6890	12086
40°	12142	11751	6777	11751
45°	9587	11215	6719	11215
50°	8093	10595	6523	10595
55°	7054	9913	6175	9913
60°	6347	9206	5465	9206
65°	5595	8443	4701	8443
70°	5039	7652	4242	7652
75°	4223	6781	3615	6781
80°	3570	5779	3389	5779
85°	3010	4520	3010	4520



TEST NUMBER: P333003-930

CATALOG NUMBER: S124RDIP-S1195D1035U930-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	156.5	2.1
10°-20°	472.2	6.3
20°-30°	738.6	9.9
30°-40°	821.0	11.0
40°-50°	728.5	9.8
50°-60°	567.6	7.6
60°-70°	371.6	5.0
70°-80°	182.8	2.5
80°-90°	48.2	0.6
90°-100°	37.2	0.5
100°-110°	237.3	3.2
110°-120°	453.9	6.1
120°-130°	576.3	7.7
130°-140°	616.6	8.3
140°-150°	576.6	7.7
150°-160°	464.9	6.2
160°-170°	299.9	4.0
170°-180°	103.4	1.4
0°-30°	1367.3	18.3
0°-40°	2188.4	29.4
0°-60°	3484.5	46.8
0°-90°	4087.1	54.8
90°-120°	728.5	9.8
90°-150°	2497.9	33.5
90°-180°	3366.0	45.2
0°-180°	7453.1	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1616	1616	1616	1616	1616	
5°	1867	1614	1427	1614	1867	189
15°	2474	1544	1061	1544	2474	703
25°	2668	1412	836	1412	2668	1183
35°	1643	1226	699	1226	1643	1030
45°	840	982	588	982	840	665
55°	501	704	439	704	501	456
65°	293	442	246	442	293	295
75°	135	217	116	217	135	149
85°	32	49	32	49	32	37
90°	24	2	24	2	24	12
95°	24	45	24	45	24	19
105°	232	245	232	245	232	202
115°	461	457	461	457	461	456
125°	648	643	648	643	648	577
135°	803	798	803	798	803	618
145°	924	920	924	920	924	578
155°	1008	1008	1008	1008	1008	465
165°	1059	1064	1059	1064	1059	299
175°	1082	1088	1082	1088	1082	103
180°	1088	1088	1088	1088	1088	



TEST NUMBER: P333003-930

CATALOG NUMBER: S124RDIP-S1195D1035U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7
2.5°	1704.1	1708.9	1704.1	1703.6	1698.4	1696.9	1694.8	1688.0	1675.5	1668.3	1669.8
5°	1866.9	1883.2	1874.0	1872.7	1858.5	1844.1	1835.0	1814.2	1792.0	1777.1	1764.7
7.5°	2055.1	2064.5	2058.8	2049.7	2026.5	2013.4	1992.3	1964.8	1925.1	1894.8	1867.0
10°	2183.3	2191.0	2188.5	2171.5	2154.6	2120.1	2100.6	2062.2	2012.1	1972.4	1935.3
12.5°	2309.3	2317.7	2294.7	2295.5	2263.4	2236.3	2205.3	2157.0	2099.1	2047.9	2001.4
15°	2473.6	2463.2	2463.2	2450.1	2414.3	2376.6	2344.7	2293.9	2221.0	2159.8	2095.4
17.5°	2602.2	2605.9	2600.5	2569.8	2541.7	2502.6	2444.2	2384.9	2317.2	2235.1	2169.2
20°	2679.3	2679.3	2673.4	2652.6	2616.1	2574.5	2511.4	2446.9	2360.9	2278.3	2204.1
22.5°	2710.5	2712.6	2705.7	2688.5	2655.8	2615.1	2561.3	2495.9	2407.3	2314.2	2222.3
25°	2667.6	2680.0	2681.2	2676.7	2666.9	2642.1	2596.0	2528.9	2449.5	2348.6	2249.7
27.5°	2449.1	2464.7	2478.4	2500.9	2530.9	2546.5	2548.5	2514.5	2445.2	2348.1	2248.5
30°	2231.4	2244.4	2286.8	2342.1	2385.1	2424.1	2458.0	2467.1	2428.0	2340.8	2236.0
32.5°	1989.8	2007.5	2049.8	2109.3	2180.9	2247.0	2323.1	2361.8	2360.9	2308.5	2211.5
35°	1643.0	1656.0	1695.1	1757.5	1843.5	1941.8	2062.2	2155.9	2219.7	2215.2	2155.9
37.5°	1325.0	1339.8	1379.2	1431.0	1514.3	1636.1	1752.6	1881.7	1999.7	2066.0	2046.2
40°	1152.2	1152.8	1191.2	1244.6	1322.7	1428.8	1555.8	1698.9	1830.4	1937.9	1958.7
42.5°	1015.7	1015.9	1041.2	1098.8	1155.0	1254.9	1376.1	1518.3	1672.2	1796.2	1851.4
45°	839.7	845.5	866.4	900.9	945.2	1029.8	1126.7	1258.9	1431.4	1578.5	1670.3
47.5°	711.1	719.7	733.0	761.1	796.4	852.7	932.9	1051.7	1192.0	1353.8	1484.4
50°	644.4	645.7	662.7	678.2	708.9	753.8	824.1	923.0	1051.9	1207.5	1352.7
52.5°	587.2	586.9	597.0	616.9	641.7	676.7	733.4	823.5	937.8	1077.3	1227.2
55°	501.2	504.5	512.3	527.9	546.8	571.5	616.4	684.1	774.0	893.1	1029.2
57.5°	435.9	437.6	443.7	450.3	467.7	485.6	519.3	566.3	642.1	739.6	866.4
60°	393.1	393.8	395.7	405.5	419.2	436.1	458.9	498.6	562.4	651.6	751.9
62.5°	351.5	352.7	355.7	362.8	373.4	385.1	409.0	440.8	493.7	569.8	660.1
65°	292.9	293.6	298.2	300.8	309.2	319.6	337.2	358.7	395.1	458.9	527.3
67.5°	244.8	244.8	245.0	248.5	254.4	261.3	271.8	289.0	316.5	355.7	416.0
70°	213.5	213.5	214.8	216.8	220.0	225.8	231.7	244.8	265.0	296.9	343.1
72.5°	184.3	184.8	186.1	186.5	188.3	193.1	197.4	205.7	220.7	244.8	282.1
75°	135.4	137.4	140.6	143.2	146.4	145.8	150.3	155.6	160.1	174.5	195.9
77.5°	100.8	99.7	100.1	102.3	102.7	103.4	106.6	110.6	114.1	120.8	128.5
80°	76.8	76.8	78.8	79.4	78.8	79.4	82.7	84.6	85.9	88.5	95.7
82.5°	58.0	59.1	58.5	59.1	59.5	60.2	62.9	63.3	64.6	65.6	68.6
85°	32.5	33.2	33.8	32.5	32.5	32.5	33.8	34.5	35.8	35.1	36.4
87.5°	16.3	15.7	16.2	16.1	16.6	15.9	16.2	17.0	15.7	16.1	15.8
90°	24.4	24.1	23.7	23.3	23.0	22.3	21.2	20.1	19.0	17.9	16.5
92.5°	22.5	22.4	22.3	22.3	22.2	21.6	20.5	19.4	18.3	17.3	15.8
95°	23.6	23.4	23.2	23.1	22.9	22.3	21.2	20.1	19.0	17.9	17.7
97.5°	22.8	22.6	22.4	22.3	22.1	21.9	21.9	21.7	21.6	21.5	41.7
100°	22.8	22.6	22.4	22.3	22.1	23.5	26.6	29.7	32.8	35.8	60.7
102.5°	23.5	23.4	23.4	23.3	23.3	39.9	73.1	106.2	139.3	172.5	175.8
105°	232.0	238.5	245.0	251.5	258.0	260.4	258.8	257.2	255.6	254.0	253.1
107.5°	323.3	322.6	321.9	321.2	320.5	319.8	319.0	318.2	317.4	316.6	315.4
110°	363.0	362.5	361.9	361.3	360.9	360.4	360.0	359.6	359.3	358.9	357.8



TEST NUMBER: P333003-930

CATALOG NUMBER: S124RDIP-S1195D1035U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	402.7	402.0	401.4	400.6	400.0	399.7	399.7	399.8	399.9	399.9	399.4
115°	460.6	460.6	460.6	460.6	460.6	460.5	460.2	459.7	459.4	459.0	459.2
117.5°	519.6	519.7	519.8	519.8	519.9	519.9	520.0	520.1	520.2	520.2	519.8
120°	556.7	557.1	557.4	557.7	558.2	558.2	557.7	557.4	557.1	556.7	556.8
122.5°	593.1	593.5	593.9	594.3	594.6	594.7	594.4	594.3	594.0	593.8	593.5
125°	647.8	647.7	647.5	647.3	647.1	646.8	646.2	645.7	645.1	644.6	645.0
127.5°	695.9	696.0	696.2	696.3	696.4	696.6	696.7	696.8	696.9	697.0	696.2
130°	728.5	728.5	728.5	728.5	728.5	728.3	728.1	728.0	727.8	727.7	727.1
132.5°	758.4	758.6	758.6	758.8	759.0	759.0	758.8	758.6	758.4	758.2	757.5
135°	803.3	802.9	802.6	802.3	801.8	801.5	801.1	800.8	800.4	800.1	799.3
137.5°	841.7	841.8	842.0	842.0	842.1	842.0	841.6	841.2	840.8	840.4	839.6
140°	868.5	868.2	868.0	867.9	867.7	867.3	866.8	866.3	865.7	865.2	864.8
142.5°	890.6	890.6	890.5	890.5	890.4	890.2	889.8	889.4	889.0	888.6	888.4
145°	924.5	924.2	923.8	923.5	923.2	922.8	922.7	922.5	922.3	922.1	922.1
147.5°	952.8	952.6	952.4	952.2	952.0	951.9	951.7	951.5	951.5	951.3	951.5
150°	970.9	970.8	970.6	970.5	970.2	970.1	970.1	970.1	970.1	970.1	970.4
152.5°	986.6	986.7	986.8	986.9	987.0	986.9	986.7	986.3	986.1	985.8	986.1
155°	1007.6	1008.1	1008.7	1009.3	1009.7	1009.7	1008.9	1008.2	1007.5	1006.8	1007.3
157.5°	1025.2	1026.1	1027.0	1028.0	1028.9	1028.9	1028.0	1027.0	1026.1	1025.2	1025.8
160°	1036.9	1038.0	1039.1	1040.2	1041.2	1041.2	1040.2	1039.1	1038.0	1036.9	1037.1
162.5°	1046.0	1047.3	1048.5	1049.7	1050.9	1051.0	1049.9	1048.8	1047.7	1046.7	1046.8
165°	1058.8	1060.5	1062.1	1063.7	1065.4	1065.4	1064.0	1062.6	1061.1	1059.6	1059.6
167.5°	1068.4	1070.2	1072.1	1073.9	1075.7	1075.8	1074.2	1072.6	1071.1	1069.4	1069.6
170°	1074.3	1076.1	1078.0	1079.8	1081.6	1081.7	1080.3	1078.9	1077.4	1076.0	1075.8
172.5°	1077.6	1079.5	1081.5	1083.5	1085.4	1085.7	1084.2	1082.8	1081.3	1079.9	1079.7
175°	1081.7	1083.9	1086.0	1088.2	1090.3	1090.6	1089.0	1087.4	1085.7	1084.1	1083.9
177.5°	1084.3	1086.0	1087.8	1089.5	1091.2	1091.5	1090.3	1089.2	1088.0	1086.9	1086.5
180°	1088.2	1088.2	1088.2	1088.2	1088.2	1088.2	1088.2	1088.2	1088.2	1088.2	1088.2



TEST NUMBER: P333003-930

CATALOG NUMBER: S124RDIP-S1195D1035U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7
2.5°	1664.6	1657.3	1653.7	1645.4	1635.4	1630.2	1625.5	1618.8	1609.9	1600.5	1593.7
5°	1749.1	1733.5	1713.9	1690.5	1669.7	1649.5	1631.9	1614.4	1594.2	1573.4	1552.5
7.5°	1835.8	1805.1	1771.9	1733.5	1696.1	1662.2	1630.8	1600.9	1567.1	1536.8	1509.1
10°	1896.2	1854.6	1808.3	1759.5	1710.7	1668.3	1626.7	1588.9	1547.3	1510.2	1479.0
12.5°	1945.1	1896.2	1840.6	1779.8	1721.1	1669.9	1622.0	1572.8	1525.4	1485.2	1443.6
15°	2026.3	1959.3	1884.5	1811.6	1735.4	1665.7	1601.3	1544.0	1490.0	1433.4	1393.7
17.5°	2082.3	2002.7	1911.7	1824.1	1734.1	1652.0	1577.6	1509.4	1447.1	1389.3	1342.0
20°	2115.5	2027.6	1926.8	1827.2	1726.3	1638.4	1558.4	1482.9	1418.4	1355.9	1307.1
22.5°	2134.3	2037.0	1926.8	1822.5	1718.0	1622.8	1534.9	1456.3	1386.1	1323.6	1269.6
25°	2140.3	2036.1	1923.5	1803.8	1689.2	1588.3	1497.1	1411.9	1333.7	1271.3	1214.0
27.5°	2132.0	2009.3	1894.0	1771.1	1652.9	1546.5	1450.8	1361.2	1283.0	1215.9	1157.2
30°	2119.5	1987.9	1864.3	1736.8	1616.9	1514.7	1413.8	1328.0	1246.6	1176.9	1117.7
32.5°	2092.4	1961.9	1828.9	1698.2	1576.9	1471.5	1375.8	1289.4	1209.6	1138.4	1075.5
35°	2038.7	1906.6	1762.1	1628.0	1508.9	1399.5	1309.7	1226.4	1150.2	1074.1	1007.6
37.5°	1968.1	1833.0	1689.3	1542.5	1423.2	1320.0	1237.5	1159.4	1085.0	1015.5	941.9
40°	1901.4	1778.4	1629.9	1484.2	1361.8	1262.2	1186.0	1115.1	1040.2	971.2	897.6
42.5°	1820.7	1715.9	1565.9	1419.6	1298.8	1202.8	1131.9	1062.5	994.4	927.5	850.8
45°	1686.0	1606.5	1465.9	1325.4	1203.6	1108.6	1043.5	982.3	922.3	858.6	786.4
47.5°	1531.5	1477.7	1356.4	1212.4	1099.8	1014.3	951.5	901.4	850.8	787.0	723.6
50°	1424.2	1389.8	1272.6	1141.1	1033.7	955.0	890.5	843.6	801.3	740.1	683.5
52.5°	1309.7	1291.4	1192.4	1066.7	962.9	885.7	830.6	788.4	745.6	694.8	641.8
55°	1135.2	1145.0	1061.0	952.4	854.7	789.6	739.5	704.3	667.9	624.9	583.9
57.5°	956.9	992.5	936.2	840.7	749.3	689.1	651.3	621.7	591.2	555.5	520.5
60°	850.1	880.0	848.2	764.2	684.1	628.2	593.0	570.2	539.6	507.1	480.4
62.5°	746.0	778.0	759.1	691.3	616.9	568.8	537.8	516.6	493.8	465.5	437.7
65°	615.1	635.9	626.9	580.0	527.3	486.2	457.6	442.0	421.2	400.3	375.6
67.5°	471.2	511.4	506.1	481.2	435.6	403.6	384.8	371.0	352.0	336.6	319.8
70°	387.3	424.4	423.8	403.6	378.9	348.9	335.9	324.2	307.2	292.3	278.6
72.5°	317.0	351.0	356.0	340.6	323.7	301.0	288.5	280.5	264.0	253.7	242.6
75°	222.0	246.7	253.2	253.2	245.4	233.7	222.7	217.4	205.7	196.6	190.0
77.5°	145.5	161.2	171.3	173.7	174.9	171.0	161.8	158.2	149.2	145.9	139.7
80°	102.8	113.2	125.0	128.9	132.2	130.9	126.9	124.3	115.9	112.6	110.0
82.5°	71.1	76.8	86.4	95.1	94.1	97.5	94.1	92.0	85.7	84.5	81.9
85°	37.1	37.7	39.1	44.9	48.2	49.5	50.1	48.8	46.9	46.9	42.3
87.5°	15.5	14.7	15.4	15.1	15.2	16.9	18.1	18.2	17.0	15.9	14.7
90°	15.0	13.5	12.1	10.4	8.4	6.4	4.4	2.4	4.4	6.4	8.4
92.5°	14.3	12.9	11.5	10.7	10.6	10.4	10.4	10.3	10.4	10.4	10.6
95°	17.5	17.4	17.2	20.1	26.3	32.4	38.6	44.8	38.6	32.4	26.3
97.5°	61.9	82.0	102.2	110.4	106.6	102.7	98.9	95.1	98.9	102.7	106.6
100°	85.8	110.7	135.7	146.5	143.2	140.0	136.7	133.5	136.7	140.0	143.2
102.5°	179.0	182.3	185.6	186.0	183.6	181.2	178.9	176.4	178.9	181.2	183.6
105°	252.1	251.2	250.3	249.3	248.3	247.1	246.1	245.0	246.1	247.1	248.3
107.5°	314.1	312.9	311.7	310.8	310.2	309.7	309.2	308.6	309.2	309.7	310.2
110°	356.8	355.6	354.6	353.8	353.2	352.7	352.1	351.6	352.1	352.7	353.2





TEST NUMBER: P333003-930

CATALOG NUMBER: S124RDIP-S1195D1035U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	398.9	398.4	397.9	397.2	396.2	395.3	394.3	393.3	394.3	395.3	396.2
115°	459.4	459.6	459.7	459.6	459.0	458.5	458.0	457.4	458.0	458.5	459.0
117.5°	519.4	519.0	518.6	518.1	517.4	516.7	515.9	515.2	515.9	516.7	517.4
120°	557.1	557.3	557.4	557.2	556.4	555.7	555.0	554.2	555.0	555.7	556.4
122.5°	593.3	593.0	592.8	592.5	592.0	591.6	591.2	590.7	591.2	591.6	592.0
125°	645.3	645.7	646.0	645.9	645.1	644.4	643.7	642.9	643.7	644.4	645.1
127.5°	695.4	694.6	693.7	693.2	693.0	692.8	692.6	692.4	692.6	692.8	693.0
130°	726.5	726.0	725.5	725.0	724.9	724.7	724.6	724.4	724.6	724.7	724.9
132.5°	756.8	756.2	755.5	755.0	754.6	754.3	754.0	753.7	754.0	754.3	754.6
135°	798.6	797.9	797.1	796.9	797.0	797.3	797.4	797.6	797.4	797.3	797.0
137.5°	838.9	838.0	837.2	836.8	836.7	836.7	836.6	836.5	836.6	836.7	836.7
140°	864.5	864.1	863.7	863.3	863.0	862.7	862.3	861.9	862.3	862.7	863.0
142.5°	888.2	887.9	887.7	887.3	886.6	886.0	885.3	884.7	885.3	886.0	886.6
145°	922.1	922.1	922.1	921.9	921.3	920.8	920.2	919.7	920.2	920.8	921.3
147.5°	951.6	951.8	952.0	951.6	950.6	949.6	948.5	947.5	948.5	949.6	950.6
150°	970.5	970.7	970.9	970.6	969.9	969.1	968.4	967.7	968.4	969.1	969.9
152.5°	986.4	986.8	987.1	986.9	986.3	985.8	985.2	984.6	985.2	985.8	986.3
155°	1007.9	1008.4	1008.9	1009.1	1008.9	1008.8	1008.6	1008.4	1008.6	1008.8	1008.9
157.5°	1026.4	1027.0	1027.6	1028.0	1028.1	1028.2	1028.3	1028.4	1028.3	1028.2	1028.1
160°	1037.2	1037.5	1037.6	1038.0	1038.5	1039.1	1039.6	1040.2	1039.6	1039.1	1038.5
162.5°	1047.0	1047.2	1047.4	1047.8	1048.5	1049.2	1049.9	1050.6	1049.9	1049.2	1048.5
165°	1059.6	1059.6	1059.6	1060.1	1061.0	1061.9	1062.8	1063.7	1062.8	1061.9	1061.0
167.5°	1069.7	1069.8	1069.9	1070.4	1071.4	1072.3	1073.3	1074.2	1073.3	1072.3	1071.4
170°	1075.6	1075.4	1075.2	1075.7	1076.8	1077.8	1079.0	1080.0	1079.0	1077.8	1076.8
172.5°	1079.5	1079.3	1079.1	1079.6	1080.7	1081.7	1082.9	1083.9	1082.9	1081.7	1080.7
175°	1083.8	1083.5	1083.4	1083.9	1084.9	1086.0	1087.1	1088.2	1087.1	1086.0	1084.9
177.5°	1086.3	1086.0	1085.7	1086.1	1087.1	1088.1	1089.1	1090.1	1089.1	1088.1	1087.1
180°	1088.2	1088.2	1088.2	1088.2	1088.2	1088.2	1088.2	1088.2	1088.2	1088.2	1088.2



TEST NUMBER: P333003-930

CATALOG NUMBER: S124RDIP-S1195D1035U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7
2.5°	1586.5	1581.3	1574.5	1566.7	1557.3	1549.0	1545.3	1548.5	1550.0	1545.9	1545.3
5°	1538.1	1521.9	1508.9	1489.4	1473.7	1460.7	1451.6	1447.7	1449.0	1438.6	1436.0
7.5°	1483.9	1464.6	1443.2	1420.1	1398.5	1379.3	1369.3	1363.8	1352.8	1348.1	1340.2
10°	1449.0	1422.9	1402.2	1374.8	1350.1	1327.3	1316.2	1307.1	1296.0	1290.8	1279.8
12.5°	1413.1	1382.8	1359.9	1331.5	1306.3	1278.9	1268.3	1251.4	1234.0	1223.1	1208.9
15°	1362.4	1326.0	1298.0	1264.1	1234.2	1203.0	1174.9	1143.7	1132.0	1107.3	1092.9
17.5°	1303.2	1266.2	1231.6	1186.2	1140.0	1101.1	1071.3	1041.4	1023.4	1007.6	1000.4
20°	1264.1	1230.3	1182.1	1129.4	1078.0	1035.0	1010.9	991.4	971.8	960.8	953.0
22.5°	1227.2	1183.9	1128.0	1071.1	1019.6	986.0	965.6	945.6	929.7	919.2	908.7
25°	1165.2	1108.6	1049.3	984.2	949.1	919.8	897.6	881.3	871.6	857.9	852.7
27.5°	1101.6	1032.9	967.6	923.8	887.2	860.4	841.1	828.9	816.5	807.8	801.0
30°	1052.6	982.9	924.3	882.6	845.5	823.5	807.8	793.5	783.7	776.6	771.4
32.5°	1004.1	934.5	885.3	840.5	811.2	789.6	772.9	762.2	754.6	745.3	742.2
35°	934.1	872.3	829.3	789.0	759.0	739.5	726.4	715.4	708.9	706.3	704.3
37.5°	866.8	816.1	770.0	736.9	710.2	694.8	679.5	674.0	669.5	664.9	667.0
40°	824.1	776.6	735.6	700.4	678.9	662.0	652.9	646.4	642.5	642.5	642.5
42.5°	787.1	740.6	700.7	669.2	647.7	633.4	623.2	617.8	616.4	616.0	619.1
45°	729.7	686.7	646.4	620.4	602.1	587.8	582.0	577.4	577.4	580.0	580.7
47.5°	672.8	632.6	600.1	571.0	554.3	545.4	540.3	537.9	538.2	540.8	543.8
50°	637.9	598.2	566.3	540.3	524.6	516.2	511.6	510.4	511.6	511.6	516.2
52.5°	599.9	564.4	533.0	511.1	493.4	485.5	483.0	481.2	481.9	484.0	486.0
55°	544.2	512.3	482.3	461.5	448.5	443.3	437.4	438.1	436.8	438.1	438.1
57.5°	488.4	459.7	431.9	415.3	403.8	396.3	389.9	391.8	389.8	389.6	388.5
60°	452.4	421.2	399.0	384.1	371.0	364.5	358.7	360.0	358.0	356.7	354.1
62.5°	413.4	387.3	366.2	351.8	341.4	333.8	327.9	326.6	322.1	317.6	311.9
65°	356.7	335.3	316.3	302.7	292.9	287.1	282.5	278.6	268.8	258.4	253.2
67.5°	301.7	286.2	268.6	257.0	249.1	241.4	232.7	226.0	216.9	211.2	207.9
70°	266.2	251.3	236.3	225.2	216.8	209.6	199.8	195.3	188.7	186.1	183.0
72.5°	232.4	218.4	204.6	194.5	185.5	179.9	172.3	167.7	164.9	163.8	160.5
75°	181.0	169.9	159.5	150.3	143.2	139.3	136.1	132.8	131.5	125.6	122.4
77.5°	132.0	124.7	118.2	111.7	106.6	104.0	97.8	94.0	91.8	89.0	88.4
80°	102.8	97.7	91.2	87.2	80.1	77.5	74.8	74.2	73.5	72.9	72.2
82.5°	77.4	72.2	65.6	63.3	61.3	59.8	58.2	57.6	56.9	57.3	57.2
85°	39.1	36.4	36.4	35.8	35.1	34.5	33.8	33.8	33.2	33.8	33.2
87.5°	15.1	14.9	15.2	14.4	15.2	15.6	15.2	15.5	16.2	15.4	15.5
90°	10.4	12.1	13.5	15.0	16.5	17.9	19.0	20.1	21.2	22.3	23.0
92.5°	10.7	11.5	12.9	14.3	15.8	17.3	18.3	19.4	20.5	21.6	22.2
95°	20.1	17.2	17.4	17.5	17.7	17.9	19.0	20.1	21.2	22.3	22.9
97.5°	110.4	102.2	82.0	61.9	41.7	21.5	21.6	21.7	21.9	21.9	22.1
100°	146.5	135.7	110.7	85.8	60.7	35.8	32.8	29.7	26.6	23.5	22.1
102.5°	186.0	185.6	182.3	179.0	175.8	172.5	139.3	106.2	73.1	39.9	23.3
105°	249.3	250.3	251.2	252.1	253.1	254.0	255.6	257.2	258.8	260.4	258.0
107.5°	310.8	311.7	312.9	314.1	315.4	316.6	317.4	318.2	319.0	319.8	320.5
110°	353.8	354.6	355.6	356.8	357.8	358.9	359.3	359.6	360.0	360.4	360.9



TEST NUMBER: P333003-930

CATALOG NUMBER: S124RDIP-S1195D1035U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	397.2	397.9	398.4	398.9	399.4	399.9	399.9	399.8	399.7	399.7	400.0
115°	459.6	459.7	459.6	459.4	459.2	459.0	459.4	459.7	460.2	460.5	460.6
117.5°	518.1	518.6	519.0	519.4	519.8	520.2	520.2	520.1	520.0	519.9	519.9
120°	557.2	557.4	557.3	557.1	556.8	556.7	557.1	557.4	557.7	558.2	558.2
122.5°	592.5	592.8	593.0	593.3	593.5	593.8	594.0	594.3	594.4	594.7	594.6
125°	645.9	646.0	645.7	645.3	645.0	644.6	645.1	645.7	646.2	646.8	647.1
127.5°	693.2	693.7	694.6	695.4	696.2	697.0	696.9	696.8	696.7	696.6	696.4
130°	725.0	725.5	726.0	726.5	727.1	727.7	727.8	728.0	728.1	728.3	728.5
132.5°	755.0	755.5	756.2	756.8	757.5	758.2	758.4	758.6	758.8	759.0	759.0
135°	796.9	797.1	797.9	798.6	799.3	800.1	800.4	800.8	801.1	801.5	801.8
137.5°	836.8	837.2	838.0	838.9	839.6	840.4	840.8	841.2	841.6	842.0	842.1
140°	863.3	863.7	864.1	864.5	864.8	865.2	865.7	866.3	866.8	867.3	867.7
142.5°	887.3	887.7	887.9	888.2	888.4	888.6	889.0	889.4	889.8	890.2	890.4
145°	921.9	922.1	922.1	922.1	922.1	922.1	922.3	922.5	922.7	922.8	923.2
147.5°	951.6	952.0	951.8	951.6	951.5	951.3	951.5	951.5	951.7	951.9	952.0
150°	970.6	970.9	970.7	970.5	970.4	970.1	970.1	970.1	970.1	970.1	970.2
152.5°	986.9	987.1	986.8	986.4	986.1	985.8	986.1	986.3	986.7	986.9	987.0
155°	1009.1	1008.9	1008.4	1007.9	1007.3	1006.8	1007.5	1008.2	1008.9	1009.7	1009.7
157.5°	1028.0	1027.6	1027.0	1026.4	1025.8	1025.2	1026.1	1027.0	1028.0	1028.9	1028.9
160°	1038.0	1037.6	1037.5	1037.2	1037.1	1036.9	1038.0	1039.1	1040.2	1041.2	1041.2
162.5°	1047.8	1047.4	1047.2	1047.0	1046.8	1046.7	1047.7	1048.8	1049.9	1051.0	1050.9
165°	1060.1	1059.6	1059.6	1059.6	1059.6	1059.6	1061.1	1062.6	1064.0	1065.4	1065.4
167.5°	1070.4	1069.9	1069.8	1069.7	1069.6	1069.4	1071.1	1072.6	1074.2	1075.8	1075.7
170°	1075.7	1075.2	1075.4	1075.6	1075.8	1076.0	1077.4	1078.9	1080.3	1081.7	1081.6
172.5°	1079.6	1079.1	1079.3	1079.5	1079.7	1079.9	1081.3	1082.8	1084.2	1085.7	1085.4
175°	1083.9	1083.4	1083.5	1083.8	1083.9	1084.1	1085.7	1087.4	1089.0	1090.6	1090.3
177.5°	1086.1	1085.7	1086.0	1086.3	1086.5	1086.9	1088.0	1089.2	1090.3	1091.5	1091.2
180°	1088.2	1088.2	1088.2	1088.2	1088.2	1088.2	1088.2	1088.2	1088.2	1088.2	1088.2



TEST NUMBER: P333003-930

CATALOG NUMBER: S124RDIP-S1195D1035U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7
2.5°	1542.2	1543.3	1539.6	1538.6	1539.6	1543.3	1542.2	1545.3	1545.9	1550.0	1548.5
5°	1430.8	1429.5	1426.2	1426.9	1426.2	1429.5	1430.8	1436.0	1438.6	1449.0	1447.7
7.5°	1335.5	1330.4	1331.8	1326.7	1331.8	1330.4	1335.5	1340.2	1348.1	1352.8	1363.8
10°	1277.2	1270.0	1264.1	1258.9	1264.1	1270.0	1277.2	1279.8	1290.8	1296.0	1307.1
12.5°	1197.5	1191.3	1183.4	1185.0	1183.4	1191.3	1197.5	1208.9	1223.1	1234.0	1251.4
15°	1084.4	1074.7	1059.1	1061.0	1059.1	1074.7	1084.4	1092.9	1107.3	1132.0	1143.7
17.5°	988.8	988.9	981.8	983.4	981.8	988.9	988.8	1000.4	1007.6	1023.4	1041.4
20°	939.3	934.7	935.4	933.4	935.4	934.7	939.3	953.0	960.8	971.8	991.4
22.5°	904.9	899.4	894.8	890.7	894.8	899.4	904.9	908.7	919.2	929.7	945.6
25°	846.9	842.9	837.1	835.8	837.1	842.9	846.9	852.7	857.9	871.6	881.3
27.5°	795.8	795.1	792.7	789.7	792.7	795.1	795.8	801.0	807.8	816.5	828.9
30°	766.1	764.8	763.5	761.6	763.5	764.8	766.1	771.4	776.6	783.7	793.5
32.5°	739.6	738.8	737.5	737.7	737.5	738.8	739.6	742.2	745.3	754.6	762.2
35°	701.7	701.1	699.8	699.1	699.8	701.1	701.7	704.3	706.3	708.9	715.4
37.5°	666.3	668.0	667.2	667.1	667.2	668.0	666.3	667.0	664.9	669.5	674.0
40°	641.8	642.5	643.8	643.1	643.8	642.5	641.8	642.5	642.5	642.5	646.4
42.5°	621.5	621.7	623.5	621.3	623.5	621.7	621.5	619.1	616.0	616.4	617.8
45°	585.2	589.1	588.5	588.5	588.5	589.1	585.2	580.7	580.0	577.4	577.4
47.5°	545.5	548.9	549.8	549.7	549.8	548.9	545.5	543.8	540.8	538.2	537.9
50°	519.4	518.1	520.1	519.4	520.1	518.1	519.4	516.2	511.6	511.6	510.4
52.5°	487.7	488.0	487.8	487.1	487.8	488.0	487.7	486.0	484.0	481.9	481.2
55°	438.7	439.4	438.1	438.7	438.1	439.4	438.7	438.1	438.1	436.8	438.1
57.5°	385.6	382.5	383.8	382.2	383.8	382.5	385.6	388.5	389.6	389.8	391.8
60°	347.6	342.4	341.1	338.5	341.1	342.4	347.6	354.1	356.7	358.0	360.0
62.5°	304.9	301.3	296.9	298.9	296.9	301.3	304.9	311.9	317.6	322.1	326.6
65°	248.0	245.4	243.4	246.1	243.4	245.4	248.0	253.2	258.4	268.8	278.6
67.5°	205.3	203.9	203.9	202.6	203.9	203.9	205.3	207.9	211.2	216.9	226.0
70°	183.0	181.0	181.0	179.7	181.0	181.0	183.0	183.0	186.1	188.7	195.3
72.5°	160.0	158.1	158.6	157.8	158.6	158.1	160.0	160.5	163.8	164.9	167.7
75°	118.5	115.2	115.2	115.9	115.2	115.2	118.5	122.4	125.6	131.5	132.8
77.5°	88.4	87.7	88.6	87.5	88.6	87.7	88.4	88.4	89.0	91.8	94.0
80°	72.2	71.6	70.9	72.9	70.9	71.6	72.2	72.2	72.9	73.5	74.2
82.5°	56.1	56.0	55.8	58.3	55.8	56.0	56.1	57.2	57.3	56.9	57.6
85°	33.8	32.5	33.8	32.5	33.8	32.5	33.8	33.2	33.8	33.2	33.8
87.5°	16.6	16.2	15.7	16.3	15.7	16.2	16.6	15.5	15.4	16.2	15.5
90°	23.3	23.7	24.1	24.4	24.1	23.7	23.3	23.0	22.3	21.2	20.1
92.5°	22.3	22.3	22.4	22.5	22.4	22.3	22.3	22.2	21.6	20.5	19.4
95°	23.1	23.2	23.4	23.6	23.4	23.2	23.1	22.9	22.3	21.2	20.1
97.5°	22.3	22.4	22.6	22.8	22.6	22.4	22.3	22.1	21.9	21.9	21.7
100°	22.3	22.4	22.6	22.8	22.6	22.4	22.3	22.1	23.5	26.6	29.7
102.5°	23.3	23.4	23.4	23.5	23.4	23.4	23.3	23.3	39.9	73.1	106.2
105°	251.5	245.0	238.5	232.0	238.5	245.0	251.5	258.0	260.4	258.8	257.2
107.5°	321.2	321.9	322.6	323.3	322.6	321.9	321.2	320.5	319.8	319.0	318.2
110°	361.3	361.9	362.5	363.0	362.5	361.9	361.3	360.9	360.4	360.0	359.6



TEST NUMBER: P333003-930

CATALOG NUMBER: S124RDIP-S1195D1035U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	400.6	401.4	402.0	402.7	402.0	401.4	400.6	400.0	399.7	399.7	399.8
115°	460.6	460.6	460.6	460.6	460.6	460.6	460.6	460.6	460.5	460.2	459.7
117.5°	519.8	519.8	519.7	519.6	519.7	519.8	519.8	519.9	519.9	520.0	520.1
120°	557.7	557.4	557.1	556.7	557.1	557.4	557.7	558.2	558.2	557.7	557.4
122.5°	594.3	593.9	593.5	593.1	593.5	593.9	594.3	594.6	594.7	594.4	594.3
125°	647.3	647.5	647.7	647.8	647.7	647.5	647.3	647.1	646.8	646.2	645.7
127.5°	696.3	696.2	696.0	695.9	696.0	696.2	696.3	696.4	696.6	696.7	696.8
130°	728.5	728.5	728.5	728.5	728.5	728.5	728.5	728.5	728.3	728.1	728.0
132.5°	758.8	758.6	758.6	758.4	758.6	758.6	758.8	759.0	759.0	758.8	758.6
135°	802.3	802.6	802.9	803.3	802.9	802.6	802.3	801.8	801.5	801.1	800.8
137.5°	842.0	842.0	841.8	841.7	841.8	842.0	842.0	842.1	842.0	841.6	841.2
140°	867.9	868.0	868.2	868.5	868.2	868.0	867.9	867.7	867.3	866.8	866.3
142.5°	890.5	890.5	890.6	890.6	890.6	890.5	890.5	890.4	890.2	889.8	889.4
145°	923.5	923.8	924.2	924.5	924.2	923.8	923.5	923.2	922.8	922.7	922.5
147.5°	952.2	952.4	952.6	952.8	952.6	952.4	952.2	952.0	951.9	951.7	951.5
150°	970.5	970.6	970.8	970.9	970.8	970.6	970.5	970.2	970.1	970.1	970.1
152.5°	986.9	986.8	986.7	986.6	986.7	986.8	986.9	987.0	986.9	986.7	986.3
155°	1009.3	1008.7	1008.1	1007.6	1008.1	1008.7	1009.3	1009.7	1009.7	1008.9	1008.2
157.5°	1028.0	1027.0	1026.1	1025.2	1026.1	1027.0	1028.0	1028.9	1028.9	1028.0	1027.0
160°	1040.2	1039.1	1038.0	1036.9	1038.0	1039.1	1040.2	1041.2	1041.2	1040.2	1039.1
162.5°	1049.7	1048.5	1047.3	1046.0	1047.3	1048.5	1049.7	1050.9	1051.0	1049.9	1048.8
165°	1063.7	1062.1	1060.5	1058.8	1060.5	1062.1	1063.7	1065.4	1065.4	1064.0	1062.6
167.5°	1073.9	1072.1	1070.2	1068.4	1070.2	1072.1	1073.9	1075.7	1075.8	1074.2	1072.6
170°	1079.8	1078.0	1076.1	1074.3	1076.1	1078.0	1079.8	1081.6	1081.7	1080.3	1078.9
172.5°	1083.5	1081.5	1079.5	1077.6	1079.5	1081.5	1083.5	1085.4	1085.7	1084.2	1082.8
175°	1088.2	1086.0	1083.9	1081.7	1083.9	1086.0	1088.2	1090.3	1090.6	1089.0	1087.4
177.5°	1089.5	1087.8	1086.0	1084.3	1086.0	1087.8	1089.5	1091.2	1091.5	1090.3	1089.2
180°	1088.2	1088.2	1088.2	1088.2	1088.2	1088.2	1088.2	1088.2	1088.2	1088.2	1088.2



TEST NUMBER: P333003-930

CATALOG NUMBER: S124RDIP-S1195D1035U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7
2.5°	1545.3	1549.0	1557.3	1566.7	1574.5	1581.3	1586.5	1593.7	1600.5	1609.9	1618.8
5°	1451.6	1460.7	1473.7	1489.4	1508.9	1521.9	1538.1	1552.5	1573.4	1594.2	1614.4
7.5°	1369.3	1379.3	1398.5	1420.1	1443.2	1464.6	1483.9	1509.1	1536.8	1567.1	1600.9
10°	1316.2	1327.3	1350.1	1374.8	1402.2	1422.9	1449.0	1479.0	1510.2	1547.3	1588.9
12.5°	1268.3	1278.9	1306.3	1331.5	1359.9	1382.8	1413.1	1443.6	1485.2	1525.4	1572.8
15°	1174.9	1203.0	1234.2	1264.1	1298.0	1326.0	1362.4	1393.7	1433.4	1490.0	1544.0
17.5°	1071.3	1101.1	1140.0	1186.2	1231.6	1266.2	1303.2	1342.0	1389.3	1447.1	1509.4
20°	1010.9	1035.0	1078.0	1129.4	1182.1	1230.3	1264.1	1307.1	1355.9	1418.4	1482.9
22.5°	965.6	986.0	1019.6	1071.1	1128.0	1183.9	1227.2	1269.6	1323.6	1386.1	1456.3
25°	897.6	919.8	949.1	984.2	1049.3	1108.6	1165.2	1214.0	1271.3	1333.7	1411.9
27.5°	841.1	860.4	887.2	923.8	967.6	1032.9	1101.6	1157.2	1215.9	1283.0	1361.2
30°	807.8	823.5	845.5	882.6	924.3	982.9	1052.6	1117.7	1176.9	1246.6	1328.0
32.5°	772.9	789.6	811.2	840.5	885.3	934.5	1004.1	1075.5	1138.4	1209.6	1289.4
35°	726.4	739.5	759.0	789.0	829.3	872.3	934.1	1007.6	1074.1	1150.2	1226.4
37.5°	679.5	694.8	710.2	736.9	770.0	816.1	866.8	941.9	1015.5	1085.0	1159.4
40°	652.9	662.0	678.9	700.4	735.6	776.6	824.1	897.6	971.2	1040.2	1115.1
42.5°	623.2	633.4	647.7	669.2	700.7	740.6	787.1	850.8	927.5	994.4	1062.5
45°	582.0	587.8	602.1	620.4	646.4	686.7	729.7	786.4	858.6	922.3	982.3
47.5°	540.3	545.4	554.3	571.0	600.1	632.6	672.8	723.6	787.0	850.8	901.4
50°	511.6	516.2	524.6	540.3	566.3	598.2	637.9	683.5	740.1	801.3	843.6
52.5°	483.0	485.5	493.4	511.1	533.0	564.4	599.9	641.8	694.8	745.6	788.4
55°	437.4	443.3	448.5	461.5	482.3	512.3	544.2	583.9	624.9	667.9	704.3
57.5°	389.9	396.3	403.8	415.3	431.9	459.7	488.4	520.5	555.5	591.2	621.7
60°	358.7	364.5	371.0	384.1	399.0	421.2	452.4	480.4	507.1	539.6	570.2
62.5°	327.9	333.8	341.4	351.8	366.2	387.3	413.4	437.7	465.5	493.8	516.6
65°	282.5	287.1	292.9	302.7	316.3	335.3	356.7	375.6	400.3	421.2	442.0
67.5°	232.7	241.4	249.1	257.0	268.6	286.2	301.7	319.8	336.6	352.0	371.0
70°	199.8	209.6	216.8	225.2	236.3	251.3	266.2	278.6	292.3	307.2	324.2
72.5°	172.3	179.9	185.5	194.5	204.6	218.4	232.4	242.6	253.7	264.0	280.5
75°	136.1	139.3	143.2	150.3	159.5	169.9	181.0	190.0	196.6	205.7	217.4
77.5°	97.8	104.0	106.6	111.7	118.2	124.7	132.0	139.7	145.9	149.2	158.2
80°	74.8	77.5	80.1	87.2	91.2	97.7	102.8	110.0	112.6	115.9	124.3
82.5°	58.2	59.8	61.3	63.3	65.6	72.2	77.4	81.9	84.5	85.7	92.0
85°	33.8	34.5	35.1	35.8	36.4	36.4	39.1	42.3	46.9	46.9	48.8
87.5°	15.2	15.6	15.2	14.4	15.2	14.9	15.1	14.7	15.9	17.0	18.2
90°	19.0	17.9	16.5	15.0	13.5	12.1	10.4	8.4	6.4	4.4	2.4
92.5°	18.3	17.3	15.8	14.3	12.9	11.5	10.7	10.6	10.4	10.4	10.3
95°	19.0	17.9	17.7	17.5	17.4	17.2	20.1	26.3	32.4	38.6	44.8
97.5°	21.6	21.5	41.7	61.9	82.0	102.2	110.4	106.6	102.7	98.9	95.1
100°	32.8	35.8	60.7	85.8	110.7	135.7	146.5	143.2	140.0	136.7	133.5
102.5°	139.3	172.5	175.8	179.0	182.3	185.6	186.0	183.6	181.2	178.9	176.4
105°	255.6	254.0	253.1	252.1	251.2	250.3	249.3	248.3	247.1	246.1	245.0
107.5°	317.4	316.6	315.4	314.1	312.9	311.7	310.8	310.2	309.7	309.2	308.6
110°	359.3	358.9	357.8	356.8	355.6	354.6	353.8	353.2	352.7	352.1	351.6



TEST NUMBER: P333003-930

CATALOG NUMBER: S124RDIP-S1195D1035U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	399.9	399.9	399.4	398.9	398.4	397.9	397.2	396.2	395.3	394.3	393.3
115°	459.4	459.0	459.2	459.4	459.6	459.7	459.6	459.0	458.5	458.0	457.4
117.5°	520.2	520.2	519.8	519.4	519.0	518.6	518.1	517.4	516.7	515.9	515.2
120°	557.1	556.7	556.8	557.1	557.3	557.4	557.2	556.4	555.7	555.0	554.2
122.5°	594.0	593.8	593.5	593.3	593.0	592.8	592.5	592.0	591.6	591.2	590.7
125°	645.1	644.6	645.0	645.3	645.7	646.0	645.9	645.1	644.4	643.7	642.9
127.5°	696.9	697.0	696.2	695.4	694.6	693.7	693.2	693.0	692.8	692.6	692.4
130°	727.8	727.7	727.1	726.5	726.0	725.5	725.0	724.9	724.7	724.6	724.4
132.5°	758.4	758.2	757.5	756.8	756.2	755.5	755.0	754.6	754.3	754.0	753.7
135°	800.4	800.1	799.3	798.6	797.9	797.1	796.9	797.0	797.3	797.4	797.6
137.5°	840.8	840.4	839.6	838.9	838.0	837.2	836.8	836.7	836.7	836.6	836.5
140°	865.7	865.2	864.8	864.5	864.1	863.7	863.3	863.0	862.7	862.3	861.9
142.5°	889.0	888.6	888.4	888.2	887.9	887.7	887.3	886.6	886.0	885.3	884.7
145°	922.3	922.1	922.1	922.1	922.1	922.1	921.9	921.3	920.8	920.2	919.7
147.5°	951.5	951.3	951.5	951.6	951.8	952.0	951.6	950.6	949.6	948.5	947.5
150°	970.1	970.1	970.4	970.5	970.7	970.9	970.6	969.9	969.1	968.4	967.7
152.5°	986.1	985.8	986.1	986.4	986.8	987.1	986.9	986.3	985.8	985.2	984.6
155°	1007.5	1006.8	1007.3	1007.9	1008.4	1008.9	1009.1	1008.9	1008.8	1008.6	1008.4
157.5°	1026.1	1025.2	1025.8	1026.4	1027.0	1027.6	1028.0	1028.1	1028.2	1028.3	1028.4
160°	1038.0	1036.9	1037.1	1037.2	1037.5	1037.6	1038.0	1038.5	1039.1	1039.6	1040.2
162.5°	1047.7	1046.7	1046.8	1047.0	1047.2	1047.4	1047.8	1048.5	1049.2	1049.9	1050.6
165°	1061.1	1059.6	1059.6	1059.6	1059.6	1059.6	1060.1	1061.0	1061.9	1062.8	1063.7
167.5°	1071.1	1069.4	1069.6	1069.7	1069.8	1069.9	1070.4	1071.4	1072.3	1073.3	1074.2
170°	1077.4	1076.0	1075.8	1075.6	1075.4	1075.2	1075.7	1076.8	1077.8	1079.0	1080.0
172.5°	1081.3	1079.9	1079.7	1079.5	1079.3	1079.1	1079.6	1080.7	1081.7	1082.9	1083.9
175°	1085.7	1084.1	1083.9	1083.8	1083.5	1083.4	1083.9	1084.9	1086.0	1087.1	1088.2
177.5°	1088.0	1086.9	1086.5	1086.3	1086.0	1085.7	1086.1	1087.1	1088.1	1089.1	1090.1
180°	1088.2	1088.2	1088.2	1088.2	1088.2	1088.2	1088.2	1088.2	1088.2	1088.2	1088.2



TEST NUMBER: P333003-930

CATALOG NUMBER: S124RDIP-S1195D1035U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7
2.5°	1625.5	1630.2	1635.4	1645.4	1653.7	1657.3	1664.6	1669.8	1668.3	1675.5	1688.0
5°	1631.9	1649.5	1669.7	1690.5	1713.9	1733.5	1749.1	1764.7	1777.1	1792.0	1814.2
7.5°	1630.8	1662.2	1696.1	1733.5	1771.9	1805.1	1835.8	1867.0	1894.8	1925.1	1964.8
10°	1626.7	1668.3	1710.7	1759.5	1808.3	1854.6	1896.2	1935.3	1972.4	2012.1	2062.2
12.5°	1622.0	1669.9	1721.1	1779.8	1840.6	1896.2	1945.1	2001.4	2047.9	2099.1	2157.0
15°	1601.3	1665.7	1735.4	1811.6	1884.5	1959.3	2026.3	2095.4	2159.8	2221.0	2293.9
17.5°	1577.6	1652.0	1734.1	1824.1	1911.7	2002.7	2082.3	2169.2	2235.1	2317.2	2384.9
20°	1558.4	1638.4	1726.3	1827.2	1926.8	2027.6	2115.5	2204.1	2278.3	2360.9	2446.9
22.5°	1534.9	1622.8	1718.0	1822.5	1926.8	2037.0	2134.3	2222.3	2314.2	2407.3	2495.9
25°	1497.1	1588.3	1689.2	1803.8	1923.5	2036.1	2140.3	2249.7	2348.6	2449.5	2528.9
27.5°	1450.8	1546.5	1652.9	1771.1	1894.0	2009.3	2132.0	2248.5	2348.1	2445.2	2514.5
30°	1413.8	1514.7	1616.9	1736.8	1864.3	1987.9	2119.5	2236.0	2340.8	2428.0	2467.1
32.5°	1375.8	1471.5	1576.9	1698.2	1828.9	1961.9	2092.4	2211.5	2308.5	2360.9	2361.8
35°	1309.7	1399.5	1508.9	1628.0	1762.1	1906.6	2038.7	2155.9	2215.2	2219.7	2155.9
37.5°	1237.5	1320.0	1423.2	1542.5	1689.3	1833.0	1968.1	2046.2	2066.0	1999.7	1881.7
40°	1186.0	1262.2	1361.8	1484.2	1629.9	1778.4	1901.4	1958.7	1937.9	1830.4	1698.9
42.5°	1131.9	1202.8	1298.8	1419.6	1565.9	1715.9	1820.7	1851.4	1796.2	1672.2	1518.3
45°	1043.5	1108.6	1203.6	1325.4	1465.9	1606.5	1686.0	1670.3	1578.5	1431.4	1258.9
47.5°	951.5	1014.3	1099.8	1212.4	1356.4	1477.7	1531.5	1484.4	1353.8	1192.0	1051.7
50°	890.5	955.0	1033.7	1141.1	1272.6	1389.8	1424.2	1352.7	1207.5	1051.9	923.0
52.5°	830.6	885.7	962.9	1066.7	1192.4	1291.4	1309.7	1227.2	1077.3	937.8	823.5
55°	739.5	789.6	854.7	952.4	1061.0	1145.0	1135.2	1029.2	893.1	774.0	684.1
57.5°	651.3	689.1	749.3	840.7	936.2	992.5	956.9	866.4	739.6	642.1	566.3
60°	593.0	628.2	684.1	764.2	848.2	880.0	850.1	751.9	651.6	562.4	498.6
62.5°	537.8	568.8	616.9	691.3	759.1	778.0	746.0	660.1	569.8	493.7	440.8
65°	457.6	486.2	527.3	580.0	626.9	635.9	615.1	527.3	458.9	395.1	358.7
67.5°	384.8	403.6	435.6	481.2	506.1	511.4	471.2	416.0	355.7	316.5	289.0
70°	335.9	348.9	378.9	403.6	423.8	424.4	387.3	343.1	296.9	265.0	244.8
72.5°	288.5	301.0	323.7	340.6	356.0	351.0	317.0	282.1	244.8	220.7	205.7
75°	222.7	233.7	245.4	253.2	253.2	246.7	222.0	195.9	174.5	160.1	155.6
77.5°	161.8	171.0	174.9	173.7	171.3	161.2	145.5	128.5	120.8	114.1	110.6
80°	126.9	130.9	132.2	128.9	125.0	113.2	102.8	95.7	88.5	85.9	84.6
82.5°	94.1	97.5	94.1	95.1	86.4	76.8	71.1	68.6	65.6	64.6	63.3
85°	50.1	49.5	48.2	44.9	39.1	37.7	37.1	36.4	35.1	35.8	34.5
87.5°	18.1	16.9	15.2	15.1	15.4	14.7	15.5	15.8	16.1	15.7	17.0
90°	4.4	6.4	8.4	10.4	12.1	13.5	15.0	16.5	17.9	19.0	20.1
92.5°	10.4	10.4	10.6	10.7	11.5	12.9	14.3	15.8	17.3	18.3	19.4
95°	38.6	32.4	26.3	20.1	17.2	17.4	17.5	17.7	17.9	19.0	20.1
97.5°	98.9	102.7	106.6	110.4	102.2	82.0	61.9	41.7	21.5	21.6	21.7
100°	136.7	140.0	143.2	146.5	135.7	110.7	85.8	60.7	35.8	32.8	29.7
102.5°	178.9	181.2	183.6	186.0	185.6	182.3	179.0	175.8	172.5	139.3	106.2
105°	246.1	247.1	248.3	249.3	250.3	251.2	252.1	253.1	254.0	255.6	257.2
107.5°	309.2	309.7	310.2	310.8	311.7	312.9	314.1	315.4	316.6	317.4	318.2
110°	352.1	352.7	353.2	353.8	354.6	355.6	356.8	357.8	358.9	359.3	359.6





TEST NUMBER: P333003-930

CATALOG NUMBER: S124RDIP-S1195D1035U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	394.3	395.3	396.2	397.2	397.9	398.4	398.9	399.4	399.9	399.9	399.8
115°	458.0	458.5	459.0	459.6	459.7	459.6	459.4	459.2	459.0	459.4	459.7
117.5°	515.9	516.7	517.4	518.1	518.6	519.0	519.4	519.8	520.2	520.2	520.1
120°	555.0	555.7	556.4	557.2	557.4	557.3	557.1	556.8	556.7	557.1	557.4
122.5°	591.2	591.6	592.0	592.5	592.8	593.0	593.3	593.5	593.8	594.0	594.3
125°	643.7	644.4	645.1	645.9	646.0	645.7	645.3	645.0	644.6	645.1	645.7
127.5°	692.6	692.8	693.0	693.2	693.7	694.6	695.4	696.2	697.0	696.9	696.8
130°	724.6	724.7	724.9	725.0	725.5	726.0	726.5	727.1	727.7	727.8	728.0
132.5°	754.0	754.3	754.6	755.0	755.5	756.2	756.8	757.5	758.2	758.4	758.6
135°	797.4	797.3	797.0	796.9	797.1	797.9	798.6	799.3	800.1	800.4	800.8
137.5°	836.6	836.7	836.7	836.8	837.2	838.0	838.9	839.6	840.4	840.8	841.2
140°	862.3	862.7	863.0	863.3	863.7	864.1	864.5	864.8	865.2	865.7	866.3
142.5°	885.3	886.0	886.6	887.3	887.7	887.9	888.2	888.4	888.6	889.0	889.4
145°	920.2	920.8	921.3	921.9	922.1	922.1	922.1	922.1	922.1	922.3	922.5
147.5°	948.5	949.6	950.6	951.6	952.0	951.8	951.6	951.5	951.3	951.5	951.5
150°	968.4	969.1	969.9	970.6	970.9	970.7	970.5	970.4	970.1	970.1	970.1
152.5°	985.2	985.8	986.3	986.9	987.1	986.8	986.4	986.1	985.8	986.1	986.3
155°	1008.6	1008.8	1008.9	1009.1	1008.9	1008.4	1007.9	1007.3	1006.8	1007.5	1008.2
157.5°	1028.3	1028.2	1028.1	1028.0	1027.6	1027.0	1026.4	1025.8	1025.2	1026.1	1027.0
160°	1039.6	1039.1	1038.5	1038.0	1037.6	1037.5	1037.2	1037.1	1036.9	1038.0	1039.1
162.5°	1049.9	1049.2	1048.5	1047.8	1047.4	1047.2	1047.0	1046.8	1046.7	1047.7	1048.8
165°	1062.8	1061.9	1061.0	1060.1	1059.6	1059.6	1059.6	1059.6	1059.6	1061.1	1062.6
167.5°	1073.3	1072.3	1071.4	1070.4	1069.9	1069.8	1069.7	1069.6	1069.4	1071.1	1072.6
170°	1079.0	1077.8	1076.8	1075.7	1075.2	1075.4	1075.6	1075.8	1076.0	1077.4	1078.9
172.5°	1082.9	1081.7	1080.7	1079.6	1079.1	1079.3	1079.5	1079.7	1079.9	1081.3	1082.8
175°	1087.1	1086.0	1084.9	1083.9	1083.4	1083.5	1083.8	1083.9	1084.1	1085.7	1087.4
177.5°	1089.1	1088.1	1087.1	1086.1	1085.7	1086.0	1086.3	1086.5	1086.9	1088.0	1089.2
180°	1088.2	1088.2	1088.2	1088.2	1088.2	1088.2	1088.2	1088.2	1088.2	1088.2	1088.2



TEST NUMBER: P333003-930

CATALOG NUMBER: S124RDIP-S1195D1035U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7
2.5°	1694.8	1696.9	1698.4	1703.6	1704.1	1708.9	1704.1
5°	1835.0	1844.1	1858.5	1872.7	1874.0	1883.2	1866.9
7.5°	1992.3	2013.4	2026.5	2049.7	2058.8	2064.5	2055.1
10°	2100.6	2120.1	2154.6	2171.5	2188.5	2191.0	2183.3
12.5°	2205.3	2236.3	2263.4	2295.5	2294.7	2317.7	2309.3
15°	2344.7	2376.6	2414.3	2450.1	2463.2	2463.2	2473.6
17.5°	2444.2	2502.6	2541.7	2569.8	2600.5	2605.9	2602.2
20°	2511.4	2574.5	2616.1	2652.6	2673.4	2679.3	2679.3
22.5°	2561.3	2615.1	2655.8	2688.5	2705.7	2712.6	2710.5
25°	2596.0	2642.1	2666.9	2676.7	2681.2	2680.0	2667.6
27.5°	2548.5	2546.5	2530.9	2500.9	2478.4	2464.7	2449.1
30°	2458.0	2424.1	2385.1	2342.1	2286.8	2244.4	2231.4
32.5°	2323.1	2247.0	2180.9	2109.3	2049.8	2007.5	1989.8
35°	2062.2	1941.8	1843.5	1757.5	1695.1	1656.0	1643.0
37.5°	1752.6	1636.1	1514.3	1431.0	1379.2	1339.8	1325.0
40°	1555.8	1428.8	1322.7	1244.6	1191.2	1152.8	1152.2
42.5°	1376.1	1254.9	1155.0	1098.8	1041.2	1015.9	1015.7
45°	1126.7	1029.8	945.2	900.9	866.4	845.5	839.7
47.5°	932.9	852.7	796.4	761.1	733.0	719.7	711.1
50°	824.1	753.8	708.9	678.2	662.7	645.7	644.4
52.5°	733.4	676.7	641.7	616.9	597.0	586.9	587.2
55°	616.4	571.5	546.8	527.9	512.3	504.5	501.2
57.5°	519.3	485.6	467.7	450.3	443.7	437.6	435.9
60°	458.9	436.1	419.2	405.5	395.7	393.8	393.1
62.5°	409.0	385.1	373.4	362.8	355.7	352.7	351.5
65°	337.2	319.6	309.2	300.8	298.2	293.6	292.9
67.5°	271.8	261.3	254.4	248.5	245.0	244.8	244.8
70°	231.7	225.8	220.0	216.8	214.8	213.5	213.5
72.5°	197.4	193.1	188.3	186.5	186.1	184.8	184.3
75°	150.3	145.8	146.4	143.2	140.6	137.4	135.4
77.5°	106.6	103.4	102.7	102.3	100.1	99.7	100.8
80°	82.7	79.4	78.8	79.4	78.8	76.8	76.8
82.5°	62.9	60.2	59.5	59.1	58.5	59.1	58.0
85°	33.8	32.5	32.5	32.5	33.8	33.2	32.5
87.5°	16.2	15.9	16.6	16.1	16.2	15.7	16.3
90°	21.2	22.3	23.0	23.3	23.7	24.1	24.4
92.5°	20.5	21.6	22.2	22.3	22.3	22.4	22.5
95°	21.2	22.3	22.9	23.1	23.2	23.4	23.6
97.5°	21.9	21.9	22.1	22.3	22.4	22.6	22.8
100°	26.6	23.5	22.1	22.3	22.4	22.6	22.8
102.5°	73.1	39.9	23.3	23.3	23.4	23.4	23.5
105°	258.8	260.4	258.0	251.5	245.0	238.5	232.0
107.5°	319.0	319.8	320.5	321.2	321.9	322.6	323.3
110°	360.0	360.4	360.9	361.3	361.9	362.5	363.0



TEST NUMBER: P333003-930

CATALOG NUMBER: S124RDIP-S1195D1035U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	399.7	399.7	400.0	400.6	401.4	402.0	402.7
115°	460.2	460.5	460.6	460.6	460.6	460.6	460.6
117.5°	520.0	519.9	519.9	519.8	519.8	519.7	519.6
120°	557.7	558.2	558.2	557.7	557.4	557.1	556.7
122.5°	594.4	594.7	594.6	594.3	593.9	593.5	593.1
125°	646.2	646.8	647.1	647.3	647.5	647.7	647.8
127.5°	696.7	696.6	696.4	696.3	696.2	696.0	695.9
130°	728.1	728.3	728.5	728.5	728.5	728.5	728.5
132.5°	758.8	759.0	759.0	758.8	758.6	758.6	758.4
135°	801.1	801.5	801.8	802.3	802.6	802.9	803.3
137.5°	841.6	842.0	842.1	842.0	842.0	841.8	841.7
140°	866.8	867.3	867.7	867.9	868.0	868.2	868.5
142.5°	889.8	890.2	890.4	890.5	890.5	890.6	890.6
145°	922.7	922.8	923.2	923.5	923.8	924.2	924.5
147.5°	951.7	951.9	952.0	952.2	952.4	952.6	952.8
150°	970.1	970.1	970.2	970.5	970.6	970.8	970.9
152.5°	986.7	986.9	987.0	986.9	986.8	986.7	986.6
155°	1008.9	1009.7	1009.7	1009.3	1008.7	1008.1	1007.6
157.5°	1028.0	1028.9	1028.9	1028.0	1027.0	1026.1	1025.2
160°	1040.2	1041.2	1041.2	1040.2	1039.1	1038.0	1036.9
162.5°	1049.9	1051.0	1050.9	1049.7	1048.5	1047.3	1046.0
165°	1064.0	1065.4	1065.4	1063.7	1062.1	1060.5	1058.8
167.5°	1074.2	1075.8	1075.7	1073.9	1072.1	1070.2	1068.4
170°	1080.3	1081.7	1081.6	1079.8	1078.0	1076.1	1074.3
172.5°	1084.2	1085.7	1085.4	1083.5	1081.5	1079.5	1077.6
175°	1089.0	1090.6	1090.3	1088.2	1086.0	1083.9	1081.7
177.5°	1090.3	1091.5	1091.2	1089.5	1087.8	1086.0	1084.3
180°	1088.2	1088.2	1088.2	1088.2	1088.2	1088.2	1088.2

(END OF REPORT)