

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332916-930

Luminaire Tested: **S124RDIP-S575D1035U930-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332916-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIP-S575D1035U930-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1035 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5283.5 lumens
Efficiency: N/A
Efficacy: 118.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 44.5
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332916-930

CATALOG NUMBER: S124RDIP-S575D1035U930-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332916-930

CATALOG NUMBER: S124RDIP-S575D1035U930-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44	36
1	95	91	87	84	86	82	79	76	67	64	62	52	51	49	39	38	37	31
2	87	79	74	69	78	72	67	63	59	55	52	46	44	41	34	33	32	26
3	79	70	63	57	71	64	58	53	52	47	44	41	38	35	31	29	27	22
4	72	62	54	48	65	56	50	45	46	41	37	36	33	30	27	25	23	19
5	66	55	47	42	60	50	44	38	41	36	32	33	29	26	25	22	20	17
6	61	49	42	36	55	45	38	33	37	32	28	30	26	23	22	20	18	15
7	56	45	37	31	51	41	34	29	34	29	25	27	23	20	21	18	16	13
8	52	40	33	28	47	37	30	26	31	26	22	25	21	18	19	16	14	12
9	49	37	30	25	44	34	27	23	28	23	20	23	19	16	17	15	13	11
10	45	34	27	22	41	31	25	21	26	21	18	21	17	15	16	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6689	6689	6689
5°	6704	6622	6663
10°	6662	6542	6542
15°	6586	6405	6358
20°	6480	6225	6110
25°	6347	6013	5860
30°	6216	5790	5547
35°	6071	5558	5233
40°	5896	5296	4894
45°	5737	5034	4548
50°	5554	4732	4182
55°	5358	4421	3786
60°	5142	4077	3381
65°	4946	3647	2980
70°	4657	3175	2530
75°	4295	2633	2059
80°	3747	2004	1888
85°	3168	1815	1704



TEST NUMBER: P332916-930

CATALOG NUMBER: S124RDIP-S575D1035U930-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	77.8	1.5
10°-20°	217.0	4.1
20°-30°	313.4	5.9
30°-40°	355.3	6.7
40°-50°	343.1	6.5
50°-60°	285.3	5.4
60°-70°	197.0	3.7
70°-80°	99.8	1.9
80°-90°	28.8	0.5
90°-100°	37.2	0.7
100°-110°	237.3	4.5
110°-120°	453.9	8.6
120°-130°	576.3	10.9
130°-140°	616.6	11.7
140°-150°	576.6	10.9
150°-160°	464.9	8.8
160°-170°	299.9	5.7
170°-180°	103.4	2.0
0°-30°	608.3	11.5
0°-40°	963.6	18.2
0°-60°	1591.9	30.1
0°-90°	1917.5	36.3
90°-120°	728.5	13.8
90°-150°	2497.9	47.3
90°-180°	3366.0	63.7
0°-180°	5283.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	829	829	829	829	829	
5°	827	824	817	823	822	78
15°	788	782	766	765	761	222
25°	712	700	675	664	658	328
35°	616	595	564	543	531	385
45°	502	478	441	411	398	387
55°	381	354	314	282	269	340
65°	259	231	191	165	156	256
75°	138	114	84	70	66	145
85°	34	22	20	18	18	39
90°	2	11	18	23	24	4
95°	45	19	18	23	24	58
105°	245	250	254	259	232	256
115°	457	460	459	461	461	450
125°	643	646	645	647	648	574
135°	798	797	800	802	803	614
145°	920	922	922	923	924	574
155°	1008	1009	1007	1010	1008	465
165°	1064	1060	1060	1065	1059	300
175°	1088	1084	1084	1090	1082	104
180°	1088	1088	1088	1088	1088	



TEST NUMBER: P332916-930

CATALOG NUMBER: S124RDIP-S575D1035U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	828.6	828.6	828.6	828.6	828.6	828.6	828.6	828.6	828.6	828.6	828.6
2.5°	830.6	830.1	829.7	829.2	828.8	827.9	826.7	825.5	824.2	823.0	824.2
5°	827.3	826.7	826.1	825.6	825.1	823.9	822.2	820.5	818.8	817.2	818.6
7.5°	819.8	819.2	818.6	818.1	817.4	816.0	813.8	811.6	809.4	807.2	808.1
10°	812.7	812.0	811.3	810.6	809.9	808.3	805.8	803.2	800.6	798.1	798.7
12.5°	803.6	802.7	801.9	801.1	800.3	798.4	795.4	792.4	789.5	786.4	786.8
15°	788.0	786.7	785.5	784.2	782.9	780.5	777.0	773.5	769.9	766.4	766.1
17.5°	769.1	767.2	765.4	763.5	761.7	758.7	754.5	750.2	746.0	741.8	741.0
20°	754.3	752.5	750.6	748.9	747.0	743.7	738.9	734.1	729.3	724.6	723.4
22.5°	738.1	736.1	734.0	731.9	729.9	726.3	721.1	716.0	710.9	705.7	704.0
25°	712.5	710.0	707.4	704.8	702.3	698.1	692.4	686.6	680.8	675.1	672.6
27.5°	685.6	682.4	679.2	676.0	672.8	668.1	661.9	655.8	649.6	643.4	640.5
30°	666.8	663.2	659.7	656.2	652.7	647.6	641.0	634.4	627.7	621.1	617.6
32.5°	647.0	643.0	639.0	635.0	631.1	625.7	618.8	612.0	605.1	598.3	594.2
35°	616.0	611.6	607.0	602.5	598.0	592.2	585.1	578.1	571.0	564.0	559.2
37.5°	582.9	578.3	573.6	569.0	564.3	558.1	550.2	542.4	534.7	526.8	521.5
40°	559.5	554.9	550.2	545.6	541.0	534.6	526.6	518.5	510.5	502.5	496.5
42.5°	537.2	532.4	527.5	522.6	517.7	511.1	502.7	494.3	486.0	477.6	471.6
45°	502.5	497.3	492.0	486.8	481.6	474.7	466.3	457.9	449.4	440.9	434.0
47.5°	466.6	461.2	455.8	450.4	445.0	437.9	429.1	420.4	411.6	402.8	395.6
50°	442.2	436.7	431.2	425.7	420.2	412.9	403.9	394.9	385.9	376.8	369.8
52.5°	417.4	412.0	406.6	401.2	395.7	388.5	379.2	370.0	360.7	351.5	344.3
55°	380.7	375.0	369.4	363.7	358.1	350.7	341.5	332.4	323.2	314.1	306.7
57.5°	344.4	338.5	332.6	326.8	320.9	313.5	304.4	295.4	286.4	277.4	269.9
60°	318.5	312.8	307.2	301.6	296.0	288.6	279.6	270.5	261.5	252.5	245.2
62.5°	295.1	289.3	283.4	277.5	271.7	264.2	254.9	245.6	236.4	227.1	220.4
65°	258.9	252.8	246.7	240.7	234.6	227.1	218.0	209.0	200.0	190.9	184.9
67.5°	221.2	215.3	209.5	203.7	198.0	190.9	182.5	174.1	165.8	157.4	152.1
70°	197.3	191.4	185.5	179.5	173.7	166.6	158.6	150.6	142.5	134.5	129.9
72.5°	171.9	166.6	161.2	155.9	150.5	144.1	136.5	128.9	121.2	113.7	109.7
75°	137.7	132.5	127.3	122.1	116.8	110.9	104.3	97.6	91.0	84.4	81.1
77.5°	102.9	98.5	94.1	89.6	85.2	80.3	74.9	69.6	64.2	58.9	57.0
80°	80.6	76.5	72.4	68.3	64.2	60.1	55.8	51.6	47.4	43.1	42.7
82.5°	61.3	57.6	53.8	50.1	46.3	43.2	40.8	38.3	36.0	33.5	33.2
85°	34.2	31.5	28.6	25.8	23.0	21.4	21.0	20.5	20.1	19.6	19.4
87.5°	12.1	11.7	11.2	10.7	10.1	9.9	10.2	10.4	10.5	10.7	10.8
90°	2.4	4.4	6.4	8.4	10.4	12.1	13.5	15.0	16.5	17.9	19.0
92.5°	10.3	10.4	10.4	10.6	10.7	11.5	12.9	14.3	15.8	17.3	18.3
95°	44.8	38.6	32.4	26.3	20.1	17.2	17.4	17.5	17.7	17.9	19.0
97.5°	95.1	98.9	102.7	106.6	110.4	102.2	82.0	61.9	41.7	21.5	21.6
100°	133.5	136.7	140.0	143.2	146.5	135.7	110.7	85.8	60.7	35.8	32.8
102.5°	176.4	178.9	181.2	183.6	186.0	185.6	182.3	179.0	175.8	172.5	139.3
105°	245.0	246.1	247.1	248.3	249.3	250.3	251.2	252.1	253.1	254.0	255.6
107.5°	308.6	309.2	309.7	310.2	310.8	311.7	312.9	314.1	315.4	316.6	317.4
110°	351.6	352.1	352.7	353.2	353.8	354.6	355.6	356.8	357.8	358.9	359.3



TEST NUMBER: P332916-930

CATALOG NUMBER: S124RDIP-S575D1035U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	393.3	394.3	395.3	396.2	397.2	397.9	398.4	398.9	399.4	399.9	399.9
115°	457.4	458.0	458.5	459.0	459.6	459.7	459.6	459.4	459.2	459.0	459.4
117.5°	515.2	515.9	516.7	517.4	518.1	518.6	519.0	519.4	519.8	520.2	520.2
120°	554.2	555.0	555.7	556.4	557.2	557.4	557.3	557.1	556.8	556.7	557.1
122.5°	590.7	591.2	591.6	592.0	592.5	592.8	593.0	593.3	593.5	593.8	594.0
125°	642.9	643.7	644.4	645.1	645.9	646.0	645.7	645.3	645.0	644.6	645.1
127.5°	692.4	692.6	692.8	693.0	693.2	693.7	694.6	695.4	696.2	697.0	696.9
130°	724.4	724.6	724.7	724.9	725.0	725.5	726.0	726.5	727.1	727.7	727.8
132.5°	753.7	754.0	754.3	754.6	755.0	755.5	756.2	756.8	757.5	758.2	758.4
135°	797.6	797.4	797.3	797.0	796.9	797.1	797.9	798.6	799.3	800.1	800.4
137.5°	836.5	836.6	836.7	836.7	836.8	837.2	838.0	838.9	839.6	840.4	840.8
140°	861.9	862.3	862.7	863.0	863.3	863.7	864.1	864.5	864.8	865.2	865.7
142.5°	884.7	885.3	886.0	886.6	887.3	887.7	887.9	888.2	888.4	888.6	889.0
145°	919.7	920.2	920.8	921.3	921.9	922.1	922.1	922.1	922.1	922.1	922.3
147.5°	947.5	948.5	949.6	950.6	951.6	952.0	951.8	951.6	951.5	951.3	951.5
150°	967.7	968.4	969.1	969.9	970.6	970.9	970.7	970.5	970.4	970.1	970.1
152.5°	984.6	985.2	985.8	986.3	986.9	987.1	986.8	986.4	986.1	985.8	986.1
155°	1008.4	1008.6	1008.8	1008.9	1009.1	1008.9	1008.4	1007.9	1007.3	1006.8	1007.5
157.5°	1028.4	1028.3	1028.2	1028.1	1028.0	1027.6	1027.0	1026.4	1025.8	1025.2	1026.1
160°	1040.2	1039.6	1039.1	1038.5	1038.0	1037.6	1037.5	1037.2	1037.1	1036.9	1038.0
162.5°	1050.6	1049.9	1049.2	1048.5	1047.8	1047.4	1047.2	1047.0	1046.8	1046.7	1047.7
165°	1063.7	1062.8	1061.9	1061.0	1060.1	1059.6	1059.6	1059.6	1059.6	1059.6	1061.1
167.5°	1074.2	1073.3	1072.3	1071.4	1070.4	1069.9	1069.8	1069.7	1069.6	1069.4	1071.1
170°	1080.0	1079.0	1077.8	1076.8	1075.7	1075.2	1075.4	1075.6	1075.8	1076.0	1077.4
172.5°	1083.9	1082.9	1081.7	1080.7	1079.6	1079.1	1079.3	1079.5	1079.7	1079.9	1081.3
175°	1088.2	1087.1	1086.0	1084.9	1083.9	1083.4	1083.5	1083.8	1083.9	1084.1	1085.7
177.5°	1090.1	1089.1	1088.1	1087.1	1086.1	1085.7	1086.0	1086.3	1086.5	1086.9	1088.0
180°	1088.2	1088.2	1088.2	1088.2	1088.2	1088.2	1088.2	1088.2	1088.2	1088.2	1088.2



TEST NUMBER: P332916-930

CATALOG NUMBER: S124RDIP-S575D1035U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	828.6	828.6	828.6	828.6	828.6	828.6	828.6	828.6
2.5°	825.5	826.7	827.9	828.5	828.4	828.3	828.2	828.1
5°	819.9	821.4	822.8	823.4	823.0	822.8	822.5	822.2
7.5°	809.0	809.9	810.9	811.1	810.7	810.2	809.8	809.3
10°	799.2	799.8	800.4	800.4	799.8	799.2	798.7	798.1
12.5°	787.1	787.4	787.8	787.6	786.8	786.0	785.2	784.4
15°	765.8	765.6	765.2	764.7	763.6	762.6	761.7	760.7
17.5°	740.2	739.4	738.6	737.4	736.0	734.5	733.0	731.5
20°	722.3	721.1	720.0	718.5	716.7	714.9	713.1	711.2
22.5°	702.4	700.7	699.0	697.4	695.9	694.4	692.9	691.4
25°	670.3	667.8	665.4	663.6	662.1	660.7	659.3	657.9
27.5°	637.5	634.5	631.6	629.1	627.0	625.0	623.1	621.0
30°	614.1	610.5	607.0	604.1	601.9	599.6	597.4	595.1
32.5°	590.1	586.0	581.9	578.8	576.7	574.5	572.3	570.2
35°	554.4	549.6	544.9	541.2	538.7	536.1	533.5	531.0
37.5°	516.1	510.8	505.4	501.5	498.9	496.4	493.8	491.3
40°	490.6	484.7	478.7	474.6	472.0	469.4	466.9	464.4
42.5°	465.5	459.5	453.5	449.1	446.5	443.8	441.2	438.5
45°	427.1	420.2	413.3	408.5	406.0	403.5	401.0	398.4
47.5°	388.4	381.2	374.1	369.1	366.3	363.5	360.8	357.9
50°	362.7	355.7	348.6	343.8	341.1	338.4	335.7	333.0
52.5°	337.1	330.0	322.9	317.9	315.0	312.3	309.5	306.7
55°	299.4	292.0	284.7	279.7	277.0	274.3	271.7	269.0
57.5°	262.4	255.0	247.6	242.9	240.8	238.8	236.8	234.7
60°	237.8	230.5	223.1	218.4	216.1	213.9	211.7	209.4
62.5°	213.6	206.8	200.1	195.8	194.0	192.2	190.4	188.6
65°	178.9	172.8	166.7	162.8	161.2	159.5	157.8	156.0
67.5°	146.9	141.7	136.5	133.0	131.1	129.2	127.3	125.5
70°	125.2	120.6	115.9	112.8	111.5	110.1	108.6	107.2
72.5°	105.7	101.7	97.8	95.1	93.8	92.5	91.2	89.9
75°	77.9	74.7	71.4	69.4	68.5	67.7	66.9	66.0
77.5°	55.1	53.2	51.3	50.2	50.0	49.7	49.5	49.2
80°	42.3	41.9	41.4	41.2	41.0	40.8	40.8	40.6
82.5°	32.9	32.5	32.3	32.0	31.9	31.7	31.6	31.5
85°	19.1	18.8	18.5	18.4	18.4	18.4	18.4	18.4
87.5°	10.9	11.0	11.1	11.3	11.4	11.7	11.8	12.0
90°	20.1	21.2	22.3	23.0	23.3	23.7	24.1	24.4
92.5°	19.4	20.5	21.6	22.2	22.3	22.3	22.4	22.5
95°	20.1	21.2	22.3	22.9	23.1	23.2	23.4	23.6
97.5°	21.7	21.9	21.9	22.1	22.3	22.4	22.6	22.8
100°	29.7	26.6	23.5	22.1	22.3	22.4	22.6	22.8
102.5°	106.2	73.1	39.9	23.3	23.3	23.4	23.4	23.5
105°	257.2	258.8	260.4	258.0	251.5	245.0	238.5	232.0
107.5°	318.2	319.0	319.8	320.5	321.2	321.9	322.6	323.3
110°	359.6	360.0	360.4	360.9	361.3	361.9	362.5	363.0



TEST NUMBER: P332916-930

CATALOG NUMBER: S124RDIP-S575D1035U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	399.8	399.7	399.7	400.0	400.6	401.4	402.0	402.7
115°	459.7	460.2	460.5	460.6	460.6	460.6	460.6	460.6
117.5°	520.1	520.0	519.9	519.9	519.8	519.8	519.7	519.6
120°	557.4	557.7	558.2	558.2	557.7	557.4	557.1	556.7
122.5°	594.3	594.4	594.7	594.6	594.3	593.9	593.5	593.1
125°	645.7	646.2	646.8	647.1	647.3	647.5	647.7	647.8
127.5°	696.8	696.7	696.6	696.4	696.3	696.2	696.0	695.9
130°	728.0	728.1	728.3	728.5	728.5	728.5	728.5	728.5
132.5°	758.6	758.8	759.0	759.0	758.8	758.6	758.6	758.4
135°	800.8	801.1	801.5	801.8	802.3	802.6	802.9	803.3
137.5°	841.2	841.6	842.0	842.1	842.0	842.0	841.8	841.7
140°	866.3	866.8	867.3	867.7	867.9	868.0	868.2	868.5
142.5°	889.4	889.8	890.2	890.4	890.5	890.5	890.6	890.6
145°	922.5	922.7	922.8	923.2	923.5	923.8	924.2	924.5
147.5°	951.5	951.7	951.9	952.0	952.2	952.4	952.6	952.8
150°	970.1	970.1	970.1	970.2	970.5	970.6	970.8	970.9
152.5°	986.3	986.7	986.9	987.0	986.9	986.8	986.7	986.6
155°	1008.2	1008.9	1009.7	1009.7	1009.3	1008.7	1008.1	1007.6
157.5°	1027.0	1028.0	1028.9	1028.9	1028.0	1027.0	1026.1	1025.2
160°	1039.1	1040.2	1041.2	1041.2	1040.2	1039.1	1038.0	1036.9
162.5°	1048.8	1049.9	1051.0	1050.9	1049.7	1048.5	1047.3	1046.0
165°	1062.6	1064.0	1065.4	1065.4	1063.7	1062.1	1060.5	1058.8
167.5°	1072.6	1074.2	1075.8	1075.7	1073.9	1072.1	1070.2	1068.4
170°	1078.9	1080.3	1081.7	1081.6	1079.8	1078.0	1076.1	1074.3
172.5°	1082.8	1084.2	1085.7	1085.4	1083.5	1081.5	1079.5	1077.6
175°	1087.4	1089.0	1090.6	1090.3	1088.2	1086.0	1083.9	1081.7
177.5°	1089.2	1090.3	1091.5	1091.2	1089.5	1087.8	1086.0	1084.3
180°	1088.2	1088.2	1088.2	1088.2	1088.2	1088.2	1088.2	1088.2

(END OF REPORT)