

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P334263

Luminaire Tested: **S124RDP-S1020D940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P334263  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1802-639-26)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124RDP-S1020D940-4F0-1E-UDD-F  
Description: DEFINE 4 REGRESSED DIRECT LED LUMINAIRE, FLUSH SATIN WHITE DIFFUSER  
PENDANT/SURFACE/WALL MOUNT, 1020 LUMENS PER FOOT  
Light Source: 4000K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3431.5 lumens  
Efficiency: N/A  
Efficacy: 98.6 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: Direct


Input Watts (W): 34.8  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P334263

CATALOG NUMBER: S124RDP-S1020D940-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P334263

CATALOG NUMBER: S124RDP-S1020D940-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	110	105	101	98	107	103	99	96	99	96	93	95	92	90	91	89	87	85					85			
2	100	93	86	81	98	91	85	80	87	82	78	84	80	76	81	78	74	72					72			
3	92	82	74	68	89	80	73	67	77	71	66	75	69	65	72	68	64	62					62			
4	84	73	65	58	82	72	64	58	69	62	57	67	61	56	65	60	56	54					54			
5	78	66	57	51	76	65	56	50	62	55	50	61	54	49	59	53	49	47					47			
6	72	59	51	45	70	58	50	44	57	49	44	55	49	44	53	48	43	41					41			
7	67	54	46	40	65	53	45	40	52	45	39	50	44	39	49	43	39	37					37			
8	63	50	41	36	61	49	41	36	48	40	35	46	40	35	45	39	35	33					33			
9	59	46	38	32	57	45	37	32	44	37	32	43	36	32	42	36	32	30					30			
10	55	42	35	29	54	42	34	29	41	34	29	40	33	29	39	33	29	27					27			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	11989	11989	11989
5°	12016	11869	11943
10°	11941	11726	11726
15°	11804	11481	11395
20°	11616	11156	10951
25°	11375	10777	10504
30°	11141	10378	9943
35°	10882	9963	9380
40°	10570	9491	8772
45°	10282	9023	8153
50°	9954	8484	7498
55°	9603	7923	6787
60°	9216	7308	6060
65°	8863	6539	5343
70°	8349	5691	4537
75°	7698	4716	3690
80°	6713	3594	3384
85°	5687	3270	3057



TEST NUMBER: P334263

CATALOG NUMBER: S124RDP-S1020D940-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	139.7	4.1
10°-20°	389.4	11.3
20°-30°	562.2	16.4
30°-40°	637.1	18.6
40°-50°	615.1	17.9
50°-60°	511.4	14.9
60°-70°	353.0	10.3
70°-80°	178.4	5.2
80°-90°	45.3	1.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1091.2	31.8
0°-40°	1728.3	50.4
0°-60°	2854.9	83.2
0°-90°	3431.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3431.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1485	1485	1485	1485	1485	
5°	1483	1478	1465	1476	1474	141
15°	1412	1402	1374	1371	1363	398
25°	1277	1257	1210	1191	1179	588
35°	1104	1068	1011	972	952	690
45°	901	858	790	735	714	694
55°	682	637	563	504	482	610
65°	464	415	342	293	280	458
75°	247	205	151	125	118	260
85°	61	39	35	33	33	71
90°	0	0	0	0	0	



TEST NUMBER: P334263

CATALOG NUMBER: S124RDP-S1020D940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1485.1	1485.1	1485.1	1485.1	1485.1
2.5°	1489.7	1485.1	1472.6	1485.1	1484.0
5°	1482.8	1478.3	1464.6	1476.0	1473.7
7.5°	1472.6	1468.1	1451.0	1459.0	1455.6
10°	1456.7	1451.0	1430.5	1435.1	1430.5
12.5°	1436.2	1429.4	1404.4	1406.7	1399.8
15°	1412.3	1402.1	1373.7	1371.4	1363.4
17.5°	1385.0	1370.3	1337.3	1331.6	1320.2
20°	1352.1	1337.3	1298.6	1289.5	1274.7
22.5°	1315.7	1298.6	1256.6	1241.8	1230.4
25°	1277.0	1256.6	1209.9	1190.6	1179.2
27.5°	1237.2	1212.2	1163.3	1140.6	1124.6
30°	1195.1	1166.7	1113.3	1084.8	1066.6
32.5°	1150.8	1117.8	1062.1	1028.0	1010.9
35°	1104.2	1067.8	1010.9	972.3	951.8
37.5°	1055.3	1017.7	955.2	913.1	892.7
40°	1003.0	965.4	900.6	852.9	832.4
42.5°	952.9	913.1	844.9	796.0	774.4
45°	900.6	858.5	790.3	734.6	714.1
47.5°	847.2	804.0	733.5	675.5	652.7
50°	792.6	748.2	675.5	618.6	597.0
52.5°	736.9	693.7	618.6	560.6	537.9
55°	682.3	636.8	562.9	503.8	482.2
57.5°	628.8	581.1	508.3	448.0	432.1
60°	570.8	525.4	452.6	393.5	375.3
62.5°	518.5	470.8	395.7	342.3	328.6
65°	464.0	415.1	342.3	293.4	279.7
67.5°	407.1	360.5	292.2	249.0	233.1
70°	353.7	305.9	241.1	203.5	192.2
72.5°	296.8	254.7	194.5	163.7	153.5
75°	246.8	204.7	151.2	125.1	118.3
77.5°	194.5	158.1	112.6	94.4	92.1
80°	144.4	111.4	77.3	73.9	72.8
82.5°	101.2	71.6	55.7	53.4	52.3
85°	61.4	38.7	35.3	33.0	33.0
87.5°	26.2	17.1	15.9	14.8	15.9
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)