

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332923-930

Luminaire Tested: **S124RDIP-S575D1205U930-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332923-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIP-S575D1205U930-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1205 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5316.0 lumens
Efficiency: N/A
Efficacy: 107.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 49.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332923-930

CATALOG NUMBER: S124RDIP-S575D1205U930-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332923-930

CATALOG NUMBER: S124RDIP-S575D1205U930-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	43	43	43	36
1	95	91	87	84	86	82	79	76	66	64	62	52	51	49	39	38	37	31
2	86	79	73	69	78	72	67	63	58	55	52	46	43	41	34	33	31	26
3	79	70	63	57	71	64	58	53	52	47	44	41	38	35	30	29	27	22
4	72	62	54	48	65	56	50	45	46	41	37	36	33	30	27	25	23	19
5	66	55	47	41	60	50	43	38	41	36	32	33	29	26	25	22	20	17
6	61	49	42	36	55	45	38	33	37	32	28	29	26	23	22	20	18	15
7	56	45	37	31	51	41	34	29	34	28	25	27	23	20	20	18	16	13
8	52	40	33	28	47	37	30	26	31	26	22	24	21	18	19	16	14	12
9	49	37	30	25	44	34	27	23	28	23	20	23	19	16	17	15	13	11
10	45	34	27	22	41	31	25	21	26	21	18	21	17	15	16	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6689	6689	6689
5°	6704	6622	6663
10°	6662	6542	6542
15°	6586	6405	6358
20°	6480	6225	6110
25°	6347	6013	5860
30°	6216	5790	5547
35°	6071	5558	5233
40°	5896	5296	4894
45°	5737	5034	4548
50°	5554	4732	4182
55°	5358	4421	3786
60°	5142	4077	3381
65°	4946	3647	2980
70°	4657	3175	2530
75°	4295	2633	2059
80°	3747	2004	1888
85°	3168	1815	1704



TEST NUMBER: P332923-930

CATALOG NUMBER: S124RDIP-S575D1205U930-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	77.8	1.5
10°-20°	217.0	4.1
20°-30°	313.4	5.9
30°-40°	355.3	6.7
40°-50°	343.1	6.5
50°-60°	285.3	5.4
60°-70°	197.0	3.7
70°-80°	99.8	1.9
80°-90°	29.3	0.6
90°-100°	80.8	1.5
100°-110°	239.3	4.5
110°-120°	406.2	7.6
120°-130°	535.6	10.1
130°-140°	601.5	11.3
140°-150°	591.0	11.1
150°-160°	497.1	9.4
160°-170°	330.7	6.2
170°-180°	115.8	2.2
0°-30°	608.3	11.4
0°-40°	963.6	18.1
0°-60°	1591.9	29.9
0°-90°	1918.0	36.1
90°-120°	726.2	13.7
90°-150°	2454.3	46.2
90°-180°	3398.0	63.9
0°-180°	5316.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	829	829	829	829	829	
5°	827	824	817	823	822	78
15°	788	782	766	765	761	222
25°	712	700	675	664	658	328
35°	616	595	564	543	531	385
45°	502	478	441	411	398	387
55°	381	354	314	282	269	340
65°	259	231	191	165	156	256
75°	138	114	84	70	66	145
85°	34	22	20	18	18	39
90°	3	13	21	26	28	5
95°	57	65	72	75	75	63
105°	221	222	225	228	231	234
115°	413	413	411	410	409	407
125°	601	601	600	599	597	536
135°	776	781	782	780	777	600
145°	942	946	947	946	944	590
155°	1080	1080	1079	1082	1079	497
165°	1176	1173	1171	1176	1173	331
175°	1223	1218	1217	1223	1217	116
180°	1225	1225	1225	1225	1225	



TEST NUMBER: P332923-930

CATALOG NUMBER: S124RDIP-S575D1205U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	828.6	828.6	828.6	828.6	828.6	828.6	828.6	828.6	828.6	828.6	828.6
2.5°	830.6	830.1	829.7	829.2	828.8	827.9	826.7	825.5	824.2	823.0	824.2
5°	827.3	826.7	826.1	825.6	825.1	823.9	822.2	820.5	818.8	817.2	818.6
7.5°	819.8	819.2	818.6	818.1	817.4	816.0	813.8	811.6	809.4	807.2	808.1
10°	812.7	812.0	811.3	810.6	809.9	808.3	805.8	803.2	800.6	798.1	798.7
12.5°	803.6	802.7	801.9	801.1	800.3	798.4	795.4	792.4	789.5	786.4	786.8
15°	788.0	786.7	785.5	784.2	782.9	780.5	777.0	773.5	769.9	766.4	766.1
17.5°	769.1	767.2	765.4	763.5	761.7	758.7	754.5	750.2	746.0	741.8	741.0
20°	754.3	752.5	750.6	748.9	747.0	743.7	738.9	734.1	729.3	724.6	723.4
22.5°	738.1	736.1	734.0	731.9	729.9	726.3	721.1	716.0	710.9	705.7	704.0
25°	712.5	710.0	707.4	704.8	702.3	698.1	692.4	686.6	680.8	675.1	672.6
27.5°	685.6	682.4	679.2	676.0	672.8	668.1	661.9	655.8	649.6	643.4	640.5
30°	666.8	663.2	659.7	656.2	652.7	647.6	641.0	634.4	627.7	621.1	617.6
32.5°	647.0	643.0	639.0	635.0	631.1	625.7	618.8	612.0	605.1	598.3	594.2
35°	616.0	611.6	607.0	602.5	598.0	592.2	585.1	578.1	571.0	564.0	559.2
37.5°	582.9	578.3	573.6	569.0	564.3	558.1	550.2	542.4	534.7	526.8	521.5
40°	559.5	554.9	550.2	545.6	541.0	534.6	526.6	518.5	510.5	502.5	496.5
42.5°	537.2	532.4	527.5	522.6	517.7	511.1	502.7	494.3	486.0	477.6	471.6
45°	502.5	497.3	492.0	486.8	481.6	474.7	466.3	457.9	449.4	440.9	434.0
47.5°	466.6	461.2	455.8	450.4	445.0	437.9	429.1	420.4	411.6	402.8	395.6
50°	442.2	436.7	431.2	425.7	420.2	412.9	403.9	394.9	385.9	376.8	369.8
52.5°	417.4	412.0	406.6	401.2	395.7	388.5	379.2	370.0	360.7	351.5	344.3
55°	380.7	375.0	369.4	363.7	358.1	350.7	341.5	332.4	323.2	314.1	306.7
57.5°	344.4	338.5	332.6	326.8	320.9	313.5	304.4	295.4	286.4	277.4	269.9
60°	318.5	312.8	307.2	301.6	296.0	288.6	279.6	270.5	261.5	252.5	245.2
62.5°	295.1	289.3	283.4	277.5	271.7	264.2	254.9	245.6	236.4	227.1	220.4
65°	258.9	252.8	246.7	240.7	234.6	227.1	218.0	209.0	200.0	190.9	184.9
67.5°	221.2	215.3	209.5	203.7	198.0	190.9	182.5	174.1	165.8	157.4	152.1
70°	197.3	191.4	185.5	179.5	173.7	166.6	158.6	150.6	142.5	134.5	129.9
72.5°	171.9	166.6	161.2	155.9	150.5	144.1	136.5	128.9	121.2	113.7	109.7
75°	137.7	132.5	127.3	122.1	116.8	110.9	104.3	97.6	91.0	84.4	81.1
77.5°	102.9	98.5	94.1	89.6	85.2	80.3	74.9	69.6	64.2	58.9	57.0
80°	80.6	76.5	72.4	68.3	64.2	60.1	55.8	51.6	47.4	43.1	42.7
82.5°	61.3	57.6	53.8	50.1	46.3	43.2	40.8	38.3	36.0	33.5	33.2
85°	34.2	31.5	28.6	25.8	23.0	21.4	21.0	20.5	20.1	19.6	19.4
87.5°	12.2	11.8	11.3	10.9	10.5	10.4	10.6	10.8	11.1	11.3	11.4
90°	2.9	5.1	7.5	9.8	12.1	14.1	15.8	17.4	19.2	20.9	22.1
92.5°	20.3	22.9	25.6	28.2	30.9	32.8	34.0	35.1	36.4	37.5	38.2
95°	56.8	58.7	60.7	62.5	64.4	66.1	67.6	69.1	70.5	72.0	72.6
97.5°	99.3	100.8	102.3	103.8	105.3	107.0	108.7	110.4	112.1	113.8	114.6
100°	132.6	133.5	134.3	135.1	136.0	137.4	139.3	141.1	143.0	145.0	145.4
102.5°	167.5	167.8	168.1	168.4	168.8	169.8	171.5	173.3	175.0	176.8	177.3
105°	220.7	220.9	221.1	221.4	221.5	222.1	222.9	223.7	224.6	225.4	226.1
107.5°	276.5	276.9	277.1	277.4	277.6	277.8	277.9	278.0	278.2	278.3	278.9
110°	314.5	314.9	315.3	315.8	316.2	316.3	316.1	315.8	315.6	315.4	315.0



TEST NUMBER: P332923-930

CATALOG NUMBER: S124RDIP-S575D1205U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	353.8	354.0	354.1	354.2	354.2	354.1	353.7	353.4	352.9	352.5	352.5
115°	412.9	412.9	412.9	412.9	412.9	412.8	412.4	412.0	411.5	411.1	410.9
117.5°	468.7	468.9	469.0	469.2	469.4	469.3	469.0	468.7	468.4	468.1	467.4
120°	505.8	506.6	507.5	508.3	509.2	509.3	508.7	508.0	507.4	506.8	505.7
122.5°	544.5	544.8	545.1	545.4	545.8	545.8	545.5	545.3	544.9	544.6	544.0
125°	601.4	601.4	601.4	601.4	601.4	601.4	601.2	601.0	600.7	600.5	600.1
127.5°	653.2	653.9	654.4	655.1	655.7	655.9	655.5	655.2	654.8	654.5	654.1
130°	689.6	690.2	690.8	691.5	692.1	692.4	692.4	692.4	692.4	692.4	692.0
132.5°	726.7	727.2	727.7	728.1	728.6	728.7	728.6	728.4	728.2	728.1	727.6
135°	775.8	777.1	778.3	779.6	780.8	781.5	781.5	781.5	781.5	781.5	781.1
137.5°	829.2	829.8	830.4	831.0	831.5	832.0	832.3	832.7	833.0	833.3	832.8
140°	864.8	865.2	865.7	866.1	866.5	866.7	866.7	866.7	866.7	866.7	866.5
142.5°	897.4	897.8	898.2	898.6	899.1	899.2	899.0	898.9	898.7	898.5	898.5
145°	942.5	943.3	944.2	945.0	945.8	946.4	946.6	946.8	947.0	947.2	947.0
147.5°	987.2	988.2	989.2	990.2	991.2	991.6	991.5	991.3	991.2	991.0	990.8
150°	1014.5	1015.3	1016.2	1017.0	1017.8	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2
152.5°	1040.2	1040.7	1041.2	1041.7	1042.3	1042.6	1042.8	1042.9	1043.1	1043.3	1043.7
155°	1079.8	1079.8	1079.8	1079.8	1079.8	1079.7	1079.5	1079.3	1079.0	1078.9	1079.7
157.5°	1113.1	1112.8	1112.4	1112.1	1111.7	1111.4	1111.4	1111.3	1111.3	1111.3	1111.9
160°	1132.9	1132.7	1132.5	1132.2	1132.0	1131.8	1131.6	1131.4	1131.1	1131.0	1131.6
162.5°	1151.0	1150.5	1150.0	1149.4	1148.8	1148.5	1148.3	1148.1	1147.9	1147.6	1148.8
165°	1175.5	1174.8	1174.2	1173.6	1173.0	1172.4	1172.0	1171.6	1171.2	1170.8	1172.0
167.5°	1194.3	1193.4	1192.5	1191.6	1190.7	1190.3	1190.3	1190.3	1190.4	1190.4	1191.7
170°	1204.8	1203.8	1202.7	1201.7	1200.6	1200.2	1200.4	1200.6	1200.9	1201.1	1202.3
172.5°	1212.4	1211.5	1210.6	1209.7	1208.9	1208.4	1208.5	1208.6	1208.6	1208.7	1210.1
175°	1222.9	1221.8	1220.7	1219.7	1218.6	1218.0	1217.8	1217.6	1217.4	1217.2	1218.6
177.5°	1226.3	1225.4	1224.6	1223.8	1222.9	1222.5	1222.5	1222.5	1222.5	1222.5	1223.7
180°	1224.7	1224.7	1224.7	1224.7	1224.7	1224.7	1224.7	1224.7	1224.7	1224.7	1224.7



TEST NUMBER: P332923-930

CATALOG NUMBER: S124RDIP-S575D1205U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	828.6	828.6	828.6	828.6	828.6	828.6	828.6	828.6
2.5°	825.5	826.7	827.9	828.5	828.4	828.3	828.2	828.1
5°	819.9	821.4	822.8	823.4	823.0	822.8	822.5	822.2
7.5°	809.0	809.9	810.9	811.1	810.7	810.2	809.8	809.3
10°	799.2	799.8	800.4	800.4	799.8	799.2	798.7	798.1
12.5°	787.1	787.4	787.8	787.6	786.8	786.0	785.2	784.4
15°	765.8	765.6	765.2	764.7	763.6	762.6	761.7	760.7
17.5°	740.2	739.4	738.6	737.4	736.0	734.5	733.0	731.5
20°	722.3	721.1	720.0	718.5	716.7	714.9	713.1	711.2
22.5°	702.4	700.7	699.0	697.4	695.9	694.4	692.9	691.4
25°	670.3	667.8	665.4	663.6	662.1	660.7	659.3	657.9
27.5°	637.5	634.5	631.6	629.1	627.0	625.0	623.1	621.0
30°	614.1	610.5	607.0	604.1	601.9	599.6	597.4	595.1
32.5°	590.1	586.0	581.9	578.8	576.7	574.5	572.3	570.2
35°	554.4	549.6	544.9	541.2	538.7	536.1	533.5	531.0
37.5°	516.1	510.8	505.4	501.5	498.9	496.4	493.8	491.3
40°	490.6	484.7	478.7	474.6	472.0	469.4	466.9	464.4
42.5°	465.5	459.5	453.5	449.1	446.5	443.8	441.2	438.5
45°	427.1	420.2	413.3	408.5	406.0	403.5	401.0	398.4
47.5°	388.4	381.2	374.1	369.1	366.3	363.5	360.8	357.9
50°	362.7	355.7	348.6	343.8	341.1	338.4	335.7	333.0
52.5°	337.1	330.0	322.9	317.9	315.0	312.3	309.5	306.7
55°	299.4	292.0	284.7	279.7	277.0	274.3	271.7	269.0
57.5°	262.4	255.0	247.6	242.9	240.8	238.8	236.8	234.7
60°	237.8	230.5	223.1	218.4	216.1	213.9	211.7	209.4
62.5°	213.6	206.8	200.1	195.8	194.0	192.2	190.4	188.6
65°	178.9	172.8	166.7	162.8	161.2	159.5	157.8	156.0
67.5°	146.9	141.7	136.5	133.0	131.1	129.2	127.3	125.5
70°	125.2	120.6	115.9	112.8	111.5	110.1	108.6	107.2
72.5°	105.7	101.7	97.8	95.1	93.8	92.5	91.2	89.9
75°	77.9	74.7	71.4	69.4	68.5	67.7	66.9	66.0
77.5°	55.1	53.2	51.3	50.2	50.0	49.7	49.5	49.2
80°	42.3	41.9	41.4	41.2	41.0	40.8	40.8	40.6
82.5°	32.9	32.5	32.3	32.0	31.9	31.7	31.6	31.5
85°	19.1	18.8	18.5	18.4	18.4	18.4	18.4	18.4
87.5°	11.6	11.7	11.8	12.0	12.2	12.4	12.6	12.8
90°	23.4	24.6	25.9	26.7	27.1	27.6	28.0	28.5
92.5°	39.1	39.8	40.5	41.0	41.3	41.6	41.8	42.1
95°	73.2	73.9	74.5	74.8	74.8	74.8	74.8	74.8
97.5°	115.4	116.1	116.9	117.2	117.2	117.2	117.2	117.2
100°	145.8	146.2	146.6	146.8	146.8	146.8	146.8	146.8
102.5°	177.9	178.6	179.1	179.4	179.7	179.9	180.0	180.2
105°	226.7	227.3	228.0	228.6	229.3	229.8	230.5	231.1
107.5°	279.5	280.1	280.6	281.0	280.9	280.9	280.8	280.8
110°	314.5	314.1	313.7	313.8	314.5	315.1	315.8	316.3



TEST NUMBER: P332923-930

CATALOG NUMBER: S124RDIP-S575D1205U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	352.4	352.3	352.2	352.2	352.4	352.5	352.6	352.8
115°	410.7	410.4	410.3	410.0	409.9	409.6	409.4	409.2
117.5°	466.7	465.9	465.2	464.7	464.2	463.8	463.4	463.0
120°	504.7	503.6	502.6	502.2	502.6	503.0	503.5	503.9
122.5°	543.2	542.5	541.8	541.0	540.3	539.6	538.7	538.0
125°	599.7	599.2	598.8	598.4	598.0	597.6	597.1	596.7
127.5°	653.7	653.3	652.8	652.5	652.2	651.8	651.4	651.1
130°	691.5	691.1	690.7	690.1	689.3	688.4	687.5	686.7
132.5°	727.2	726.8	726.4	725.9	725.6	725.3	725.0	724.6
135°	780.6	780.2	779.8	779.3	778.6	778.0	777.3	776.7
137.5°	832.3	831.7	831.2	831.0	831.1	831.2	831.4	831.4
140°	866.3	866.1	865.8	865.7	865.4	865.2	865.0	864.8
142.5°	898.5	898.4	898.4	898.3	898.3	898.2	898.2	898.1
145°	946.8	946.6	946.4	945.9	945.3	944.7	944.0	943.5
147.5°	990.7	990.5	990.3	990.1	989.9	989.7	989.4	989.3
150°	1018.2	1018.2	1018.2	1018.1	1017.9	1017.7	1017.5	1017.3
152.5°	1044.2	1044.8	1045.3	1045.3	1044.7	1044.2	1043.6	1043.1
155°	1080.6	1081.4	1082.2	1082.2	1081.4	1080.6	1079.7	1078.9
157.5°	1112.6	1113.1	1113.8	1113.8	1113.0	1112.3	1111.6	1110.9
160°	1132.2	1132.9	1133.5	1133.3	1132.2	1131.1	1130.2	1129.1
162.5°	1149.9	1151.0	1152.2	1152.3	1151.2	1150.1	1149.1	1148.0
165°	1173.3	1174.5	1175.8	1176.0	1175.2	1174.4	1173.5	1172.6
167.5°	1192.9	1194.3	1195.5	1195.5	1194.2	1192.9	1191.6	1190.3
170°	1203.6	1204.8	1206.2	1206.0	1204.5	1203.1	1201.6	1200.1
172.5°	1211.5	1212.9	1214.4	1214.4	1212.8	1211.4	1209.9	1208.4
175°	1220.1	1221.6	1223.0	1223.0	1221.6	1220.1	1218.6	1217.2
177.5°	1224.8	1226.0	1227.2	1227.1	1225.7	1224.4	1223.0	1221.7
180°	1224.7	1224.7	1224.7	1224.7	1224.7	1224.7	1224.7	1224.7

(END OF REPORT)