

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333277-927

Luminaire Tested: **S125DIP-S1090D1035U927-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333277-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S1090D1035U927-4F0-1E-UDD-A
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1090 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1035 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6833.5 lumens
Efficiency: N/A
Efficacy: 113.0 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 60.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333277-927

CATALOG NUMBER: S125DIP-S1090D1035U927-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P333277-927

CATALOG NUMBER: S125DIP-S1090D1035U927-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	84	84	84	71	71	71	58	58	58	52
1	98	94	90	87	91	87	84	81	74	72	70	63	61	59	52	51	49	44
2	90	83	76	71	83	77	71	67	65	62	58	55	52	50	46	44	42	37
3	82	73	65	60	76	68	61	56	58	53	49	49	45	42	41	38	36	32
4	75	64	57	51	69	60	53	48	52	46	42	44	40	36	36	34	31	28
5	69	57	49	43	64	54	46	41	46	41	36	39	35	32	33	30	27	24
6	64	52	44	38	59	48	41	36	42	36	32	36	31	28	30	27	24	21
7	59	47	39	33	54	44	36	31	38	32	28	32	28	25	27	24	21	19
8	55	42	35	29	50	40	33	28	34	29	25	30	25	22	25	22	19	17
9	51	39	31	26	47	36	29	25	32	26	22	27	23	20	23	20	17	15
10	47	35	28	23	44	33	27	22	29	24	20	25	21	18	21	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	8136	8136	8136	8136
5°	9422	8163	7148	8163
10°	10961	8121	6263	8121
15°	12133	8062	5777	8062
20°	13582	7967	5388	7967
25°	15911	7860	5197	7860
30°	17186	7756	5032	7756
35°	14130	7559	4924	7559
40°	10044	7284	4806	7284
45°	7716	6915	4737	6915
50°	6586	6457	4728	6457
55°	5864	6008	4769	6008
60°	5291	5518	4890	5518
65°	4886	5025	5017	5025
70°	4443	4513	5089	4513
75°	3923	3975	5043	3975
80°	3299	3239	4616	3239
85°	2616	2334	3720	2334



TEST NUMBER: P333277-927

CATALOG NUMBER: S125DIP-S1090D1035U927-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	121.3	1.8
10°-20°	361.1	5.3
20°-30°	586.3	8.6
30°-40°	715.2	10.5
40°-50°	650.6	9.5
50°-60°	518.2	7.6
60°-70°	361.0	5.3
70°-80°	192.5	2.8
80°-90°	50.8	0.7
90°-100°	38.8	0.6
100°-110°	239.0	3.5
110°-120°	433.4	6.3
120°-130°	556.2	8.1
130°-140°	598.3	8.8
140°-150°	561.6	8.2
150°-160°	454.3	6.6
160°-170°	293.8	4.3
170°-180°	101.3	1.5
0°-30°	1068.7	15.6
0°-40°	1783.8	26.1
0°-60°	2952.7	43.2
0°-90°	3556.9	52.1
90°-120°	711.2	10.4
90°-150°	2427.2	35.5
90°-180°	3277.0	48.0
0°-180°	6833.5	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1260	1260	1260	1260	1260	
5°	1453	1259	1102	1259	1453	146
15°	1815	1206	864	1206	1815	519
25°	2233	1103	729	1103	2233	1020
35°	1792	959	624	959	1792	1097
45°	845	757	519	757	845	676
55°	521	534	424	534	521	469
65°	320	329	328	329	320	317
75°	157	159	202	159	157	169
85°	35	32	50	32	35	41
90°	19	1	19	1	19	10
95°	17	45	17	45	17	14
105°	235	232	235	232	235	212
115°	434	437	434	437	434	430
125°	621	621	621	621	621	552
135°	771	774	771	774	771	595
145°	895	898	895	898	895	559
155°	982	989	982	989	982	452
165°	1038	1043	1038	1043	1038	293
175°	1062	1067	1062	1067	1062	101
180°	1067	1067	1067	1067	1067	



TEST NUMBER: P333277-927

CATALOG NUMBER: S125DIP-S1090D1035U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7
2.5°	1332.5	1330.7	1329.0	1325.6	1328.2	1320.9	1317.5	1311.5	1304.2	1301.6	1298.6
5°	1453.3	1456.0	1458.6	1447.4	1448.4	1441.0	1423.9	1409.9	1398.8	1384.3	1374.1
7.5°	1598.7	1592.4	1591.9	1584.6	1572.1	1562.0	1544.0	1521.1	1499.0	1473.8	1452.9
10°	1671.4	1672.0	1667.1	1658.6	1645.2	1635.6	1612.1	1589.6	1562.3	1530.3	1507.3
12.5°	1726.2	1728.4	1722.4	1710.8	1704.2	1682.7	1664.3	1637.5	1605.1	1579.5	1544.5
15°	1814.7	1808.9	1804.6	1790.1	1778.9	1756.4	1727.0	1699.2	1663.9	1631.3	1598.7
17.5°	1900.0	1904.7	1896.7	1883.6	1848.7	1822.5	1783.0	1745.0	1701.1	1657.3	1618.3
20°	1976.2	1980.5	1968.2	1945.2	1903.5	1877.3	1825.4	1776.2	1725.5	1669.3	1626.5
22.5°	2071.2	2067.8	2051.1	2016.2	1980.1	1931.6	1875.5	1815.6	1751.9	1688.5	1631.7
25°	2232.8	2210.3	2200.2	2157.0	2109.3	2038.2	1961.2	1873.5	1794.4	1710.5	1637.8
27.5°	2322.4	2315.4	2304.1	2273.9	2223.9	2147.8	2057.1	1950.2	1838.6	1732.6	1637.4
30°	2304.5	2305.6	2306.6	2297.0	2264.9	2207.7	2117.3	2002.4	1869.8	1750.6	1640.4
32.5°	2145.4	2164.8	2183.4	2205.4	2214.5	2203.5	2146.9	2043.0	1906.5	1771.1	1638.7
35°	1792.2	1798.2	1858.5	1918.4	1999.7	2062.8	2105.1	2059.0	1944.1	1788.5	1636.6
37.5°	1397.5	1426.3	1468.2	1535.8	1653.1	1758.2	1893.2	1955.3	1918.3	1794.2	1632.9
40°	1191.3	1218.0	1245.3	1314.2	1413.2	1540.4	1693.8	1824.9	1855.4	1776.2	1620.1
42.5°	1032.1	1053.4	1083.6	1135.4	1218.1	1330.9	1477.4	1648.6	1754.0	1724.0	1593.2
45°	844.8	858.2	881.7	922.9	982.8	1071.0	1200.4	1387.5	1550.6	1604.6	1529.2
47.5°	723.1	723.0	741.3	769.8	812.9	887.9	983.6	1130.2	1304.4	1433.3	1427.3
50°	655.5	652.8	667.3	691.9	726.1	775.9	867.3	984.4	1151.7	1297.7	1338.3
52.5°	597.4	597.7	606.6	624.7	653.4	695.9	764.1	869.7	1012.7	1162.5	1239.1
55°	520.8	518.6	528.8	541.1	562.0	589.8	639.0	719.7	835.7	983.3	1082.8
57.5°	450.6	456.5	460.6	469.1	486.5	505.1	546.5	605.8	697.8	824.5	929.6
60°	409.6	415.4	418.7	427.2	441.1	457.2	489.3	537.3	614.9	724.0	828.2
62.5°	372.8	377.4	378.4	386.1	397.5	413.1	438.3	478.8	540.0	635.4	737.5
65°	319.7	319.7	321.9	329.9	335.3	349.1	368.4	397.8	447.0	521.3	608.5
67.5°	268.6	271.2	270.7	274.2	279.1	289.9	303.7	328.0	364.4	418.7	488.4
70°	235.3	237.4	236.9	239.6	244.9	251.8	263.1	286.1	312.3	358.8	418.7
72.5°	205.3	206.2	204.8	208.3	211.5	217.6	230.1	242.4	266.9	306.2	355.4
75°	157.2	158.3	159.3	161.4	164.7	167.9	174.3	186.6	202.6	232.0	263.6
77.5°	117.9	115.8	118.4	118.0	119.9	122.3	128.0	134.5	147.7	166.3	190.7
80°	88.7	89.3	89.3	89.8	92.5	94.1	98.9	103.7	113.9	127.8	144.9
82.5°	64.8	66.2	65.4	66.3	68.5	69.7	72.4	76.4	82.2	93.2	105.5
85°	35.3	32.6	33.7	34.8	34.8	35.3	37.4	39.1	42.2	46.5	51.3
87.5°	14.1	14.8	15.1	15.1	15.4	15.2	16.7	16.6	17.7	18.8	20.3
90°	19.0	18.5	17.9	17.4	16.9	16.2	15.3	14.4	13.5	12.7	11.4
92.5°	17.7	17.5	17.2	17.0	16.7	16.2	15.3	14.4	13.5	12.7	11.6
95°	16.6	16.6	16.6	16.6	16.6	16.2	15.3	14.4	13.5	12.7	19.3
97.5°	16.6	16.6	16.6	16.6	16.6	19.1	24.1	29.0	34.0	38.9	52.1
100°	16.6	17.3	18.0	18.7	19.4	32.9	59.1	85.2	111.5	137.6	136.9
102.5°	99.5	111.5	123.4	135.4	147.3	155.7	160.7	165.6	170.6	175.6	175.2
105°	234.9	235.1	235.3	235.4	235.6	235.7	235.7	235.7	235.7	235.7	235.7
107.5°	296.1	296.7	297.2	297.7	298.3	298.5	298.5	298.4	298.4	298.3	298.0
110°	338.5	338.3	338.2	338.0	337.9	338.0	338.5	339.1	339.6	340.1	339.8



TEST NUMBER: P333277-927

CATALOG NUMBER: S125DIP-S1090D1035U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	376.5	376.8	377.0	377.2	377.5	378.0	378.6	379.3	379.9	380.6	380.4
115°	433.5	434.5	435.5	436.7	437.7	438.6	439.3	440.0	440.7	441.3	441.2
117.5°	494.2	494.6	495.1	495.6	496.0	496.7	497.6	498.5	499.5	500.3	499.7
120°	531.6	532.4	533.3	534.2	535.0	535.7	536.0	536.4	536.7	537.1	536.5
122.5°	567.0	568.0	569.0	570.1	571.0	571.7	572.1	572.4	572.7	573.1	572.9
125°	620.9	621.5	621.9	622.5	623.1	623.6	624.3	625.0	625.7	626.5	626.5
127.5°	666.3	667.7	668.9	670.2	671.5	672.3	672.7	673.1	673.5	673.9	674.0
130°	699.2	700.1	701.0	701.9	702.7	703.5	703.9	704.5	705.0	705.5	705.4
132.5°	729.6	730.5	731.3	732.2	733.1	733.6	733.7	733.8	733.9	734.0	734.4
135°	771.2	772.2	773.3	774.4	775.4	776.1	776.5	776.8	777.1	777.5	777.8
137.5°	812.9	813.9	814.8	815.7	816.6	817.1	817.0	816.9	816.8	816.7	817.1
140°	837.7	838.7	839.7	840.8	841.9	842.2	841.9	841.5	841.1	840.8	841.0
142.5°	861.0	862.1	863.2	864.2	865.3	865.8	865.7	865.6	865.5	865.5	865.2
145°	895.4	896.4	897.5	898.6	899.6	900.0	899.8	899.7	899.5	899.4	899.4
147.5°	923.7	925.0	926.2	927.5	928.8	929.3	929.1	928.8	928.7	928.4	928.2
150°	942.1	943.4	944.8	946.3	947.7	948.2	947.8	947.5	947.1	946.8	946.4
152.5°	959.1	960.4	961.6	962.9	964.2	964.6	964.3	963.9	963.6	963.2	962.9
155°	981.6	983.0	984.4	985.8	987.2	987.7	987.1	986.6	986.1	985.6	985.2
157.5°	1000.4	1001.8	1003.2	1004.6	1006.1	1006.5	1005.9	1005.4	1004.8	1004.2	1004.2
160°	1012.4	1013.8	1015.3	1016.7	1018.0	1018.4	1017.7	1017.0	1016.3	1015.6	1015.4
162.5°	1023.2	1024.8	1026.3	1027.9	1029.4	1029.7	1028.6	1027.7	1026.7	1025.7	1025.6
165°	1037.8	1039.2	1040.5	1042.0	1043.4	1043.5	1042.5	1041.4	1040.4	1039.3	1039.2
167.5°	1047.9	1049.5	1051.1	1052.7	1054.2	1054.4	1053.1	1051.9	1050.6	1049.3	1049.1
170°	1053.6	1055.2	1056.8	1058.3	1059.9	1060.0	1058.6	1057.2	1055.7	1054.4	1054.2
172.5°	1057.4	1058.9	1060.5	1062.1	1063.7	1063.8	1062.6	1061.3	1060.0	1058.8	1058.4
175°	1062.2	1063.8	1065.4	1067.0	1068.6	1068.7	1067.3	1065.9	1064.5	1063.0	1062.9
177.5°	1065.1	1066.3	1067.4	1068.5	1069.6	1069.7	1068.7	1067.7	1066.8	1065.7	1065.6
180°	1067.0	1067.0	1067.0	1067.0	1067.0	1067.0	1067.0	1067.0	1067.0	1067.0	1067.0



TEST NUMBER: P333277-927

CATALOG NUMBER: S125DIP-S1090D1035U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7
2.5°	1296.1	1293.1	1289.7	1283.7	1276.4	1272.6	1266.5	1262.7	1255.0	1248.6	1241.7
5°	1361.8	1348.0	1335.1	1318.5	1300.4	1288.6	1274.7	1259.2	1243.2	1226.5	1208.4
7.5°	1430.0	1405.3	1378.6	1349.9	1321.8	1295.9	1271.1	1246.9	1224.2	1196.8	1173.6
10°	1475.8	1444.7	1411.6	1372.5	1334.6	1301.4	1267.7	1238.3	1208.4	1176.3	1148.0
12.5°	1521.5	1480.2	1433.4	1390.5	1344.8	1304.8	1265.2	1227.6	1190.0	1154.5	1121.4
15°	1553.8	1517.4	1474.1	1413.2	1361.8	1306.8	1254.3	1205.7	1160.2	1120.7	1079.0
17.5°	1575.1	1528.2	1481.7	1423.2	1356.0	1294.3	1235.0	1179.3	1128.1	1077.9	1037.7
20°	1578.9	1530.8	1482.2	1424.9	1356.0	1285.4	1226.1	1159.2	1104.1	1052.3	1003.1
22.5°	1577.6	1523.1	1470.1	1411.3	1344.0	1279.0	1207.2	1139.1	1079.3	1028.3	977.0
25°	1565.6	1507.3	1441.0	1381.6	1315.3	1246.3	1173.6	1103.0	1042.1	983.8	933.0
27.5°	1555.5	1479.9	1404.9	1335.6	1271.6	1208.4	1138.8	1066.5	998.9	939.8	892.0
30°	1543.1	1460.2	1375.7	1303.5	1237.8	1176.3	1110.6	1040.0	969.4	911.6	860.3
32.5°	1532.0	1435.4	1346.2	1267.7	1198.0	1138.2	1077.6	1010.4	941.1	882.6	831.2
35°	1510.5	1398.8	1296.6	1207.8	1133.5	1072.1	1021.3	958.7	895.1	838.4	789.2
37.5°	1483.2	1350.6	1241.0	1148.0	1066.5	1001.7	954.4	906.4	845.3	790.7	746.2
40°	1461.8	1316.4	1200.4	1105.2	1020.7	953.3	909.5	864.0	813.3	762.5	715.4
42.5°	1434.9	1285.6	1159.3	1056.9	973.2	907.6	861.6	823.0	778.2	730.8	687.1
45°	1385.4	1229.8	1092.9	982.8	898.3	833.5	786.0	757.1	723.4	678.5	641.6
47.5°	1312.6	1162.7	1021.1	907.4	820.3	760.3	715.7	688.0	664.3	630.9	597.5
50°	1247.9	1112.7	969.4	856.6	769.4	709.0	667.8	642.7	622.3	596.7	568.4
52.5°	1175.7	1049.8	918.5	806.9	720.6	661.1	620.8	598.7	581.7	563.3	535.4
55°	1060.8	953.9	831.9	726.1	646.4	588.1	552.9	533.6	519.8	505.8	488.7
57.5°	934.3	850.6	742.7	645.9	572.5	519.5	486.6	467.9	457.0	449.9	439.8
60°	845.3	773.7	680.6	592.4	520.8	473.7	441.6	427.2	418.1	412.3	404.7
62.5°	762.8	703.9	617.7	537.3	474.6	430.1	401.5	387.5	378.7	375.9	369.7
65°	641.1	595.6	524.5	457.7	404.3	366.2	342.2	328.8	323.4	320.3	320.8
67.5°	521.2	493.5	436.4	379.4	336.8	304.9	285.7	275.4	272.7	268.4	268.3
70°	448.1	427.2	379.1	329.4	291.4	266.8	249.7	239.0	236.3	234.2	233.7
72.5°	383.5	365.2	323.4	283.6	249.5	227.9	213.7	207.3	203.0	201.7	201.6
75°	288.2	278.1	244.9	213.3	189.8	174.8	165.2	159.3	156.1	155.6	156.1
77.5°	204.9	196.0	174.9	152.6	137.8	126.4	118.3	116.2	112.6	112.7	112.2
80°	154.0	148.1	134.8	117.1	104.8	95.1	90.9	87.1	86.1	84.4	86.1
82.5°	111.6	105.4	96.3	85.0	74.9	69.1	64.8	63.6	63.0	62.3	62.6
85°	55.1	55.6	50.2	41.7	37.4	34.2	31.5	31.5	31.0	30.5	31.0
87.5°	20.8	19.7	17.8	16.2	13.9	12.3	11.6	11.7	10.7	10.5	11.2
90°	10.2	9.0	7.8	6.4	5.0	3.6	2.2	0.8	2.2	3.6	5.0
92.5°	10.5	9.3	8.3	8.2	9.2	10.2	11.2	12.2	11.2	10.2	9.2
95°	26.0	32.7	39.4	43.0	43.5	44.0	44.5	45.1	44.5	44.0	43.5
97.5°	65.4	78.6	91.8	97.9	97.0	96.0	95.1	94.1	95.1	96.0	97.0
100°	136.3	135.5	134.8	134.2	133.6	133.2	132.6	132.1	132.6	133.2	133.6
102.5°	174.8	174.4	173.9	173.3	172.7	172.1	171.3	170.7	171.3	172.1	172.7
105°	235.7	235.7	235.7	235.4	234.6	233.9	233.2	232.5	233.2	233.9	234.6
107.5°	297.6	297.3	296.9	296.8	296.8	296.8	296.8	296.8	296.8	296.8	296.8
110°	339.5	339.1	338.7	338.5	338.5	338.5	338.5	338.5	338.5	338.5	338.5



TEST NUMBER: P333277-927

CATALOG NUMBER: S125DIP-S1090D1035U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	380.2	380.0	379.8	379.5	379.1	378.6	378.2	377.8	378.2	378.6	379.1
115°	441.0	440.8	440.7	440.1	439.3	438.4	437.5	436.7	437.5	438.4	439.3
117.5°	499.0	498.4	497.7	497.4	497.4	497.4	497.5	497.5	497.5	497.4	497.4
120°	536.0	535.5	535.0	534.8	535.0	535.1	535.3	535.5	535.3	535.1	535.0
122.5°	572.7	572.4	572.1	571.7	571.0	570.4	569.7	569.0	569.7	570.4	571.0
125°	626.5	626.5	626.5	625.8	624.6	623.4	622.1	620.9	622.1	623.4	624.6
127.5°	674.1	674.2	674.3	673.9	673.0	672.2	671.3	670.4	671.3	672.2	673.0
130°	705.2	705.0	704.8	704.3	703.5	702.6	701.7	700.8	701.7	702.6	703.5
132.5°	734.8	735.1	735.5	735.2	734.2	733.2	732.2	731.2	732.2	733.2	734.2
135°	778.2	778.6	779.0	778.6	777.5	776.5	775.4	774.4	775.4	776.5	777.5
137.5°	817.4	817.7	818.0	817.7	816.8	815.9	815.0	814.0	815.0	815.9	816.8
140°	841.1	841.3	841.5	841.4	841.1	840.7	840.3	840.0	840.3	840.7	841.1
142.5°	865.0	864.7	864.5	864.3	864.0	863.9	863.6	863.4	863.6	863.9	864.0
145°	899.4	899.4	899.4	899.1	898.8	898.4	898.1	897.8	898.1	898.4	898.8
147.5°	928.0	927.8	927.6	927.5	927.6	927.6	927.7	927.8	927.7	927.6	927.6
150°	946.1	945.7	945.4	945.4	945.7	946.1	946.4	946.8	946.4	946.1	945.7
152.5°	962.5	962.2	961.9	962.0	962.8	963.6	964.4	965.1	964.4	963.6	962.8
155°	984.8	984.5	984.1	984.5	985.6	986.6	987.7	988.7	987.7	986.6	985.6
157.5°	1004.2	1004.1	1004.1	1004.4	1005.0	1005.7	1006.2	1006.9	1006.2	1005.7	1005.0
160°	1015.3	1015.1	1014.9	1015.3	1016.4	1017.5	1018.5	1019.5	1018.5	1017.5	1016.4
162.5°	1025.4	1025.2	1025.0	1025.5	1026.5	1027.5	1028.6	1029.7	1028.6	1027.5	1026.5
165°	1038.9	1038.8	1038.6	1039.1	1040.1	1041.2	1042.2	1043.3	1042.2	1041.2	1040.1
167.5°	1048.9	1048.8	1048.6	1049.1	1050.1	1051.2	1052.3	1053.4	1052.3	1051.2	1050.1
170°	1054.0	1053.8	1053.7	1054.2	1055.4	1056.6	1057.9	1059.1	1057.9	1056.6	1055.4
172.5°	1058.1	1057.8	1057.6	1058.0	1059.2	1060.4	1061.7	1062.9	1061.7	1060.4	1059.2
175°	1062.7	1062.6	1062.4	1062.8	1063.8	1064.9	1066.0	1067.0	1066.0	1064.9	1063.8
177.5°	1065.5	1065.3	1065.2	1065.6	1066.4	1067.2	1068.1	1068.9	1068.1	1067.2	1066.4
180°	1067.0	1067.0	1067.0	1067.0	1067.0	1067.0	1067.0	1067.0	1067.0	1067.0	1067.0



TEST NUMBER: P333277-927

CATALOG NUMBER: S125DIP-S1090D1035U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7
2.5°	1237.9	1233.2	1229.3	1220.8	1216.1	1209.7	1204.5	1210.1	1204.1	1206.7	1202.8
5°	1199.3	1184.3	1173.6	1158.1	1144.8	1132.4	1123.4	1121.7	1117.5	1115.3	1108.9
7.5°	1152.9	1134.2	1115.8	1095.4	1078.3	1060.9	1049.8	1040.6	1034.5	1026.5	1021.0
10°	1125.5	1100.3	1079.0	1054.4	1033.0	1014.3	999.3	991.8	984.9	974.7	971.0
12.5°	1091.7	1065.7	1039.7	1013.4	992.8	971.9	959.1	947.8	942.9	931.5	930.3
15°	1051.2	1012.2	986.5	959.7	931.4	914.3	903.6	891.3	886.0	878.0	872.0
17.5°	1002.8	968.0	935.9	908.2	883.9	869.5	856.3	847.8	838.6	833.4	823.7
20°	967.8	934.6	902.5	873.1	854.4	837.8	827.1	819.1	809.5	806.8	797.3
22.5°	938.3	901.7	870.9	846.2	825.8	807.1	795.5	790.0	783.4	775.2	773.2
25°	890.3	852.3	826.1	801.5	783.3	766.2	758.2	751.2	744.8	738.9	736.8
27.5°	848.7	814.8	783.7	761.5	745.7	730.1	723.0	714.5	709.9	705.1	699.3
30°	819.7	784.9	757.6	736.3	719.1	705.3	697.8	691.9	687.6	683.3	680.1
32.5°	789.7	757.6	731.1	710.2	693.1	682.5	676.0	671.8	667.1	661.9	657.9
35°	750.2	714.9	689.2	671.1	657.7	649.7	642.1	638.4	633.0	633.0	628.8
37.5°	705.6	675.1	652.4	635.9	623.8	616.7	608.6	606.0	602.6	600.3	598.8
40°	679.1	650.7	629.3	612.8	599.9	594.1	587.6	583.4	581.2	578.5	577.4
42.5°	651.6	624.6	604.1	588.8	577.7	572.7	566.6	563.6	559.4	555.9	555.2
45°	610.1	583.8	565.1	552.9	543.2	537.3	533.6	527.2	525.1	520.8	520.2
47.5°	570.6	545.5	527.1	517.1	508.6	503.7	497.9	491.5	489.0	486.9	486.6
50°	541.1	518.1	501.0	491.4	483.4	476.4	470.6	466.3	464.6	464.6	465.7
52.5°	511.2	491.5	477.1	465.2	457.7	450.3	444.9	442.3	439.8	442.4	444.3
55°	467.3	447.5	436.8	425.6	418.1	409.6	406.9	405.8	404.3	408.5	410.7
57.5°	420.9	407.0	394.5	383.3	376.6	371.7	368.0	367.4	370.4	372.5	379.4
60°	391.4	375.3	364.1	355.5	347.5	344.4	343.3	342.2	344.4	350.2	359.3
62.5°	358.9	345.9	333.7	327.3	321.5	316.1	315.9	316.6	320.8	327.6	336.6
65°	311.2	299.9	291.9	284.5	279.6	276.4	277.5	279.6	284.5	293.5	303.7
67.5°	262.8	255.1	247.9	241.8	237.2	237.2	238.3	241.5	247.2	257.6	266.9
70°	231.6	223.0	217.1	214.4	210.6	208.5	211.8	217.1	221.9	231.6	239.6
72.5°	200.3	193.1	188.5	186.6	185.0	183.3	184.3	190.1	196.6	206.3	215.6
75°	154.0	151.3	148.1	146.0	144.3	145.4	146.5	151.9	157.2	167.4	178.1
77.5°	112.4	109.6	107.7	107.2	106.3	106.9	109.8	113.8	119.0	126.4	134.5
80°	85.0	84.0	82.9	82.3	82.3	82.9	87.1	89.8	94.7	101.6	108.0
82.5°	61.9	61.2	61.1	60.9	61.4	61.5	64.1	67.6	71.5	76.8	82.3
85°	32.6	31.5	33.1	33.7	32.6	34.2	35.3	37.4	39.1	41.7	44.4
87.5°	12.0	13.1	12.9	13.6	13.9	15.0	14.7	16.6	17.6	18.6	18.4
90°	6.4	7.8	9.0	10.2	11.4	12.7	13.5	14.4	15.3	16.2	16.9
92.5°	8.2	8.3	9.3	10.5	11.6	12.7	13.5	14.4	15.3	16.2	16.7
95°	43.0	39.4	32.7	26.0	19.3	12.7	13.5	14.4	15.3	16.2	16.6
97.5°	97.9	91.8	78.6	65.4	52.1	38.9	34.0	29.0	24.1	19.1	16.6
100°	134.2	134.8	135.5	136.3	136.9	137.6	111.5	85.2	59.1	32.9	19.4
102.5°	173.3	173.9	174.4	174.8	175.2	175.6	170.6	165.6	160.7	155.7	147.3
105°	235.4	235.7	235.7	235.7	235.7	235.7	235.7	235.7	235.7	235.7	235.6
107.5°	296.8	296.9	297.3	297.6	298.0	298.3	298.4	298.4	298.5	298.5	298.3
110°	338.5	338.7	339.1	339.5	339.8	340.1	339.6	339.1	338.5	338.0	337.9



TEST NUMBER: P333277-927

CATALOG NUMBER: S125DIP-S1090D1035U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	379.5	379.8	380.0	380.2	380.4	380.6	379.9	379.3	378.6	378.0	377.5
115°	440.1	440.7	440.8	441.0	441.2	441.3	440.7	440.0	439.3	438.6	437.7
117.5°	497.4	497.7	498.4	499.0	499.7	500.3	499.5	498.5	497.6	496.7	496.0
120°	534.8	535.0	535.5	536.0	536.5	537.1	536.7	536.4	536.0	535.7	535.0
122.5°	571.7	572.1	572.4	572.7	572.9	573.1	572.7	572.4	572.1	571.7	571.0
125°	625.8	626.5	626.5	626.5	626.5	626.5	625.7	625.0	624.3	623.6	623.1
127.5°	673.9	674.3	674.2	674.1	674.0	673.9	673.5	673.1	672.7	672.3	671.5
130°	704.3	704.8	705.0	705.2	705.4	705.5	705.0	704.5	703.9	703.5	702.7
132.5°	735.2	735.5	735.1	734.8	734.4	734.0	733.9	733.8	733.7	733.6	733.1
135°	778.6	779.0	778.6	778.2	777.8	777.5	777.1	776.8	776.5	776.1	775.4
137.5°	817.7	818.0	817.7	817.4	817.1	816.7	816.8	816.9	817.0	817.1	816.6
140°	841.4	841.5	841.3	841.1	841.0	840.8	841.1	841.5	841.9	842.2	841.9
142.5°	864.3	864.5	864.7	865.0	865.2	865.5	865.5	865.6	865.7	865.8	865.3
145°	899.1	899.4	899.4	899.4	899.4	899.4	899.5	899.7	899.8	900.0	899.6
147.5°	927.5	927.6	927.8	928.0	928.2	928.4	928.7	928.8	929.1	929.3	928.8
150°	945.4	945.4	945.7	946.1	946.4	946.8	947.1	947.5	947.8	948.2	947.7
152.5°	962.0	961.9	962.2	962.5	962.9	963.2	963.6	963.9	964.3	964.6	964.2
155°	984.5	984.1	984.5	984.8	985.2	985.6	986.1	986.6	987.1	987.7	987.2
157.5°	1004.4	1004.1	1004.1	1004.2	1004.2	1004.2	1004.8	1005.4	1005.9	1006.5	1006.1
160°	1015.3	1014.9	1015.1	1015.3	1015.4	1015.6	1016.3	1017.0	1017.7	1018.4	1018.0
162.5°	1025.5	1025.0	1025.2	1025.4	1025.6	1025.7	1026.7	1027.7	1028.6	1029.7	1029.4
165°	1039.1	1038.6	1038.8	1038.9	1039.2	1039.3	1040.4	1041.4	1042.5	1043.5	1043.4
167.5°	1049.1	1048.6	1048.8	1048.9	1049.1	1049.3	1050.6	1051.9	1053.1	1054.4	1054.2
170°	1054.2	1053.7	1053.8	1054.0	1054.2	1054.4	1055.7	1057.2	1058.6	1060.0	1059.9
172.5°	1058.0	1057.6	1057.8	1058.1	1058.4	1058.8	1060.0	1061.3	1062.6	1063.8	1063.7
175°	1062.8	1062.4	1062.6	1062.7	1062.9	1063.0	1064.5	1065.9	1067.3	1068.7	1068.6
177.5°	1065.6	1065.2	1065.3	1065.5	1065.6	1065.7	1066.8	1067.7	1068.7	1069.7	1069.6
180°	1067.0	1067.0	1067.0	1067.0	1067.0	1067.0	1067.0	1067.0	1067.0	1067.0	1067.0



TEST NUMBER: P333277-927

CATALOG NUMBER: S125DIP-S1090D1035U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7
2.5°	1200.2	1203.2	1200.7	1204.1	1200.7	1203.2	1200.2	1202.8	1206.7	1204.1	1210.1
5°	1106.3	1101.5	1104.6	1102.5	1104.6	1101.5	1106.3	1108.9	1115.3	1117.5	1121.7
7.5°	1019.5	1014.9	1009.6	1007.1	1009.6	1014.9	1019.5	1021.0	1026.5	1034.5	1040.6
10°	965.1	959.3	958.7	955.0	958.7	959.3	965.1	971.0	974.7	984.9	991.8
12.5°	925.3	919.9	913.8	912.2	913.8	919.9	925.3	930.3	931.5	942.9	947.8
15°	868.9	864.6	860.9	864.0	860.9	864.6	868.9	872.0	878.0	886.0	891.3
17.5°	821.9	818.4	817.8	813.8	817.8	818.4	821.9	823.7	833.4	838.6	847.8
20°	792.4	789.7	790.8	783.9	790.8	789.7	792.4	797.3	806.8	809.5	819.1
22.5°	768.9	763.7	763.0	761.6	763.0	763.7	768.9	773.2	775.2	783.4	790.0
25°	732.0	729.3	726.7	729.3	726.7	729.3	732.0	736.8	738.9	744.8	751.2
27.5°	699.8	696.6	695.9	696.2	695.9	696.6	699.8	699.3	705.1	709.9	714.5
30°	680.1	674.8	675.3	674.8	675.3	674.8	680.1	680.1	683.3	687.6	691.9
32.5°	658.7	655.1	654.3	653.4	654.3	655.1	658.7	657.9	661.9	667.1	671.8
35°	627.2	627.2	624.5	624.5	624.5	627.2	627.2	628.8	633.0	633.0	638.4
37.5°	597.5	597.0	595.4	595.6	595.4	597.0	597.5	598.8	600.3	602.6	606.0
40°	575.3	574.8	573.1	570.0	573.1	574.8	575.3	577.4	578.5	581.2	583.4
42.5°	553.9	552.2	551.4	550.3	551.4	552.2	553.9	555.2	555.9	559.4	563.6
45°	520.2	520.2	519.2	518.6	519.2	520.2	520.2	520.2	520.8	525.1	527.2
47.5°	487.5	488.5	490.5	490.2	490.5	488.5	487.5	486.6	486.9	489.0	491.5
50°	467.9	468.4	470.0	470.6	470.0	468.4	467.9	465.7	464.6	464.6	466.3
52.5°	446.0	449.2	451.1	450.8	451.1	449.2	446.0	444.3	442.4	439.8	442.3
55°	415.4	419.2	422.9	423.5	422.9	419.2	415.4	410.7	408.5	404.3	405.8
57.5°	385.2	390.4	394.3	395.7	394.3	390.4	385.2	379.4	372.5	370.4	367.4
60°	364.6	371.6	376.4	378.6	376.4	371.6	364.6	359.3	350.2	344.4	342.2
62.5°	345.0	352.8	357.6	358.0	357.6	352.8	345.0	336.6	327.6	320.8	316.6
65°	312.8	320.8	325.1	328.3	325.1	320.8	312.8	303.7	293.5	284.5	279.6
67.5°	278.1	286.1	290.9	293.4	290.9	286.1	278.1	266.9	257.6	247.2	241.5
70°	252.9	260.9	267.4	269.5	267.4	260.9	252.9	239.6	231.6	221.9	217.1
72.5°	228.1	235.3	240.4	243.0	240.4	235.3	228.1	215.6	206.3	196.6	190.1
75°	185.0	194.6	199.5	202.1	199.5	194.6	185.0	178.1	167.4	157.2	151.9
77.5°	142.7	151.4	154.3	155.7	154.3	151.4	142.7	134.5	126.4	119.0	113.8
80°	114.4	119.8	123.5	124.1	123.5	119.8	114.4	108.0	101.6	94.7	89.8
82.5°	87.9	92.4	93.6	95.0	93.6	92.4	87.9	82.3	76.8	71.5	67.6
85°	48.1	50.2	50.8	50.2	50.8	50.2	48.1	44.4	41.7	39.1	37.4
87.5°	19.3	19.0	19.1	20.0	19.1	19.0	19.3	18.4	18.6	17.6	16.6
90°	17.4	17.9	18.5	19.0	18.5	17.9	17.4	16.9	16.2	15.3	14.4
92.5°	17.0	17.2	17.5	17.7	17.5	17.2	17.0	16.7	16.2	15.3	14.4
95°	16.6	16.6	16.6	16.6	16.6	16.6	16.6	16.6	16.2	15.3	14.4
97.5°	16.6	16.6	16.6	16.6	16.6	16.6	16.6	16.6	19.1	24.1	29.0
100°	18.7	18.0	17.3	16.6	17.3	18.0	18.7	19.4	32.9	59.1	85.2
102.5°	135.4	123.4	111.5	99.5	111.5	123.4	135.4	147.3	155.7	160.7	165.6
105°	235.4	235.3	235.1	234.9	235.1	235.3	235.4	235.6	235.7	235.7	235.7
107.5°	297.7	297.2	296.7	296.1	296.7	297.2	297.7	298.3	298.5	298.5	298.4
110°	338.0	338.2	338.3	338.5	338.3	338.2	338.0	337.9	338.0	338.5	339.1



TEST NUMBER: P333277-927

CATALOG NUMBER: S125DIP-S1090D1035U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	377.2	377.0	376.8	376.5	376.8	377.0	377.2	377.5	378.0	378.6	379.3
115°	436.7	435.5	434.5	433.5	434.5	435.5	436.7	437.7	438.6	439.3	440.0
117.5°	495.6	495.1	494.6	494.2	494.6	495.1	495.6	496.0	496.7	497.6	498.5
120°	534.2	533.3	532.4	531.6	532.4	533.3	534.2	535.0	535.7	536.0	536.4
122.5°	570.1	569.0	568.0	567.0	568.0	569.0	570.1	571.0	571.7	572.1	572.4
125°	622.5	621.9	621.5	620.9	621.5	621.9	622.5	623.1	623.6	624.3	625.0
127.5°	670.2	668.9	667.7	666.3	667.7	668.9	670.2	671.5	672.3	672.7	673.1
130°	701.9	701.0	700.1	699.2	700.1	701.0	701.9	702.7	703.5	703.9	704.5
132.5°	732.2	731.3	730.5	729.6	730.5	731.3	732.2	733.1	733.6	733.7	733.8
135°	774.4	773.3	772.2	771.2	772.2	773.3	774.4	775.4	776.1	776.5	776.8
137.5°	815.7	814.8	813.9	812.9	813.9	814.8	815.7	816.6	817.1	817.0	816.9
140°	840.8	839.7	838.7	837.7	838.7	839.7	840.8	841.9	842.2	841.9	841.5
142.5°	864.2	863.2	862.1	861.0	862.1	863.2	864.2	865.3	865.8	865.7	865.6
145°	898.6	897.5	896.4	895.4	896.4	897.5	898.6	899.6	900.0	899.8	899.7
147.5°	927.5	926.2	925.0	923.7	925.0	926.2	927.5	928.8	929.3	929.1	928.8
150°	946.3	944.8	943.4	942.1	943.4	944.8	946.3	947.7	948.2	947.8	947.5
152.5°	962.9	961.6	960.4	959.1	960.4	961.6	962.9	964.2	964.6	964.3	963.9
155°	985.8	984.4	983.0	981.6	983.0	984.4	985.8	987.2	987.7	987.1	986.6
157.5°	1004.6	1003.2	1001.8	1000.4	1001.8	1003.2	1004.6	1006.1	1006.5	1005.9	1005.4
160°	1016.7	1015.3	1013.8	1012.4	1013.8	1015.3	1016.7	1018.0	1018.4	1017.7	1017.0
162.5°	1027.9	1026.3	1024.8	1023.2	1024.8	1026.3	1027.9	1029.4	1029.7	1028.6	1027.7
165°	1042.0	1040.5	1039.2	1037.8	1039.2	1040.5	1042.0	1043.4	1043.5	1042.5	1041.4
167.5°	1052.7	1051.1	1049.5	1047.9	1049.5	1051.1	1052.7	1054.2	1054.4	1053.1	1051.9
170°	1058.3	1056.8	1055.2	1053.6	1055.2	1056.8	1058.3	1059.9	1060.0	1058.6	1057.2
172.5°	1062.1	1060.5	1058.9	1057.4	1058.9	1060.5	1062.1	1063.7	1063.8	1062.6	1061.3
175°	1067.0	1065.4	1063.8	1062.2	1063.8	1065.4	1067.0	1068.6	1068.7	1067.3	1065.9
177.5°	1068.5	1067.4	1066.3	1065.1	1066.3	1067.4	1068.5	1069.6	1069.7	1068.7	1067.7
180°	1067.0	1067.0	1067.0	1067.0	1067.0	1067.0	1067.0	1067.0	1067.0	1067.0	1067.0



TEST NUMBER: P333277-927

CATALOG NUMBER: S125DIP-S1090D1035U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7
2.5°	1204.5	1209.7	1216.1	1220.8	1229.3	1233.2	1237.9	1241.7	1248.6	1255.0	1262.7
5°	1123.4	1132.4	1144.8	1158.1	1173.6	1184.3	1199.3	1208.4	1226.5	1243.2	1259.2
7.5°	1049.8	1060.9	1078.3	1095.4	1115.8	1134.2	1152.9	1173.6	1196.8	1224.2	1246.9
10°	999.3	1014.3	1033.0	1054.4	1079.0	1100.3	1125.5	1148.0	1176.3	1208.4	1238.3
12.5°	959.1	971.9	992.8	1013.4	1039.7	1065.7	1091.7	1121.4	1154.5	1190.0	1227.6
15°	903.6	914.3	931.4	959.7	986.5	1012.2	1051.2	1079.0	1120.7	1160.2	1205.7
17.5°	856.3	869.5	883.9	908.2	935.9	968.0	1002.8	1037.7	1077.9	1128.1	1179.3
20°	827.1	837.8	854.4	873.1	902.5	934.6	967.8	1003.1	1052.3	1104.1	1159.2
22.5°	795.5	807.1	825.8	846.2	870.9	901.7	938.3	977.0	1028.3	1079.3	1139.1
25°	758.2	766.2	783.3	801.5	826.1	852.3	890.3	933.0	983.8	1042.1	1103.0
27.5°	723.0	730.1	745.7	761.5	783.7	814.8	848.7	892.0	939.8	998.9	1066.5
30°	697.8	705.3	719.1	736.3	757.6	784.9	819.7	860.3	911.6	969.4	1040.0
32.5°	676.0	682.5	693.1	710.2	731.1	757.6	789.7	831.2	882.6	941.1	1010.4
35°	642.1	649.7	657.7	671.1	689.2	714.9	750.2	789.2	838.4	895.1	958.7
37.5°	608.6	616.7	623.8	635.9	652.4	675.1	705.6	746.2	790.7	845.3	906.4
40°	587.6	594.1	599.9	612.8	629.3	650.7	679.1	715.4	762.5	813.3	864.0
42.5°	566.6	572.7	577.7	588.8	604.1	624.6	651.6	687.1	730.8	778.2	823.0
45°	533.6	537.3	543.2	552.9	565.1	583.8	610.1	641.6	678.5	723.4	757.1
47.5°	497.9	503.7	508.6	517.1	527.1	545.5	570.6	597.5	630.9	664.3	688.0
50°	470.6	476.4	483.4	491.4	501.0	518.1	541.1	568.4	596.7	622.3	642.7
52.5°	444.9	450.3	457.7	465.2	477.1	491.5	511.2	535.4	563.3	581.7	598.7
55°	406.9	409.6	418.1	425.6	436.8	447.5	467.3	488.7	505.8	519.8	533.6
57.5°	368.0	371.7	376.6	383.3	394.5	407.0	420.9	439.8	449.9	457.0	467.9
60°	343.3	344.4	347.5	355.5	364.1	375.3	391.4	404.7	412.3	418.1	427.2
62.5°	315.9	316.1	321.5	327.3	333.7	345.9	358.9	369.7	375.9	378.7	387.5
65°	277.5	276.4	279.6	284.5	291.9	299.9	311.2	320.8	320.3	323.4	328.8
67.5°	238.3	237.2	237.2	241.8	247.9	255.1	262.8	268.3	268.4	272.7	275.4
70°	211.8	208.5	210.6	214.4	217.1	223.0	231.6	233.7	234.2	236.3	239.0
72.5°	184.3	183.3	185.0	186.6	188.5	193.1	200.3	201.6	201.7	203.0	207.3
75°	146.5	145.4	144.3	146.0	148.1	151.3	154.0	156.1	155.6	156.1	159.3
77.5°	109.8	106.9	106.3	107.2	107.7	109.6	112.4	112.2	112.7	112.6	116.2
80°	87.1	82.9	82.3	82.3	82.9	84.0	85.0	86.1	84.4	86.1	87.1
82.5°	64.1	61.5	61.4	60.9	61.1	61.2	61.9	62.6	62.3	63.0	63.6
85°	35.3	34.2	32.6	33.7	33.1	31.5	32.6	31.0	30.5	31.0	31.5
87.5°	14.7	15.0	13.9	13.6	12.9	13.1	12.0	11.2	10.5	10.7	11.7
90°	13.5	12.7	11.4	10.2	9.0	7.8	6.4	5.0	3.6	2.2	0.8
92.5°	13.5	12.7	11.6	10.5	9.3	8.3	8.2	9.2	10.2	11.2	12.2
95°	13.5	12.7	19.3	26.0	32.7	39.4	43.0	43.5	44.0	44.5	45.1
97.5°	34.0	38.9	52.1	65.4	78.6	91.8	97.9	97.0	96.0	95.1	94.1
100°	111.5	137.6	136.9	136.3	135.5	134.8	134.2	133.6	133.2	132.6	132.1
102.5°	170.6	175.6	175.2	174.8	174.4	173.9	173.3	172.7	172.1	171.3	170.7
105°	235.7	235.7	235.7	235.7	235.7	235.7	235.4	234.6	233.9	233.2	232.5
107.5°	298.4	298.3	298.0	297.6	297.3	296.9	296.8	296.8	296.8	296.8	296.8
110°	339.6	340.1	339.8	339.5	339.1	338.7	338.5	338.5	338.5	338.5	338.5



TEST NUMBER: P333277-927

CATALOG NUMBER: S125DIP-S1090D1035U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	379.9	380.6	380.4	380.2	380.0	379.8	379.5	379.1	378.6	378.2	377.8
115°	440.7	441.3	441.2	441.0	440.8	440.7	440.1	439.3	438.4	437.5	436.7
117.5°	499.5	500.3	499.7	499.0	498.4	497.7	497.4	497.4	497.4	497.5	497.5
120°	536.7	537.1	536.5	536.0	535.5	535.0	534.8	535.0	535.1	535.3	535.5
122.5°	572.7	573.1	572.9	572.7	572.4	572.1	571.7	571.0	570.4	569.7	569.0
125°	625.7	626.5	626.5	626.5	626.5	626.5	625.8	624.6	623.4	622.1	620.9
127.5°	673.5	673.9	674.0	674.1	674.2	674.3	673.9	673.0	672.2	671.3	670.4
130°	705.0	705.5	705.4	705.2	705.0	704.8	704.3	703.5	702.6	701.7	700.8
132.5°	733.9	734.0	734.4	734.8	735.1	735.5	735.2	734.2	733.2	732.2	731.2
135°	777.1	777.5	777.8	778.2	778.6	779.0	778.6	777.5	776.5	775.4	774.4
137.5°	816.8	816.7	817.1	817.4	817.7	818.0	817.7	816.8	815.9	815.0	814.0
140°	841.1	840.8	841.0	841.1	841.3	841.5	841.4	841.1	840.7	840.3	840.0
142.5°	865.5	865.5	865.2	865.0	864.7	864.5	864.3	864.0	863.9	863.6	863.4
145°	899.5	899.4	899.4	899.4	899.4	899.4	899.1	898.8	898.4	898.1	897.8
147.5°	928.7	928.4	928.2	928.0	927.8	927.6	927.5	927.6	927.6	927.7	927.8
150°	947.1	946.8	946.4	946.1	945.7	945.4	945.4	945.7	946.1	946.4	946.8
152.5°	963.6	963.2	962.9	962.5	962.2	961.9	962.0	962.8	963.6	964.4	965.1
155°	986.1	985.6	985.2	984.8	984.5	984.1	984.5	985.6	986.6	987.7	988.7
157.5°	1004.8	1004.2	1004.2	1004.2	1004.1	1004.1	1004.4	1005.0	1005.7	1006.2	1006.9
160°	1016.3	1015.6	1015.4	1015.3	1015.1	1014.9	1015.3	1016.4	1017.5	1018.5	1019.5
162.5°	1026.7	1025.7	1025.6	1025.4	1025.2	1025.0	1025.5	1026.5	1027.5	1028.6	1029.7
165°	1040.4	1039.3	1039.2	1038.9	1038.8	1038.6	1039.1	1040.1	1041.2	1042.2	1043.3
167.5°	1050.6	1049.3	1049.1	1048.9	1048.8	1048.6	1049.1	1050.1	1051.2	1052.3	1053.4
170°	1055.7	1054.4	1054.2	1054.0	1053.8	1053.7	1054.2	1055.4	1056.6	1057.9	1059.1
172.5°	1060.0	1058.8	1058.4	1058.1	1057.8	1057.6	1058.0	1059.2	1060.4	1061.7	1062.9
175°	1064.5	1063.0	1062.9	1062.7	1062.6	1062.4	1062.8	1063.8	1064.9	1066.0	1067.0
177.5°	1066.8	1065.7	1065.6	1065.5	1065.3	1065.2	1065.6	1066.4	1067.2	1068.1	1068.9
180°	1067.0	1067.0	1067.0	1067.0	1067.0	1067.0	1067.0	1067.0	1067.0	1067.0	1067.0



TEST NUMBER: P333277-927

CATALOG NUMBER: S125DIP-S1090D1035U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7
2.5°	1266.5	1272.6	1276.4	1283.7	1289.7	1293.1	1296.1	1298.6	1301.6	1304.2	1311.5
5°	1274.7	1288.6	1300.4	1318.5	1335.1	1348.0	1361.8	1374.1	1384.3	1398.8	1409.9
7.5°	1271.1	1295.9	1321.8	1349.9	1378.6	1405.3	1430.0	1452.9	1473.8	1499.0	1521.1
10°	1267.7	1301.4	1334.6	1372.5	1411.6	1444.7	1475.8	1507.3	1530.3	1562.3	1589.6
12.5°	1265.2	1304.8	1344.8	1390.5	1433.4	1480.2	1521.5	1544.5	1579.5	1605.1	1637.5
15°	1254.3	1306.8	1361.8	1413.2	1474.1	1517.4	1553.8	1598.7	1631.3	1663.9	1699.2
17.5°	1235.0	1294.3	1356.0	1423.2	1481.7	1528.2	1575.1	1618.3	1657.3	1701.1	1745.0
20°	1226.1	1285.4	1356.0	1424.9	1482.2	1530.8	1578.9	1626.5	1669.3	1725.5	1776.2
22.5°	1207.2	1279.0	1344.0	1411.3	1470.1	1523.1	1577.6	1631.7	1688.5	1751.9	1815.6
25°	1173.6	1246.3	1315.3	1381.6	1441.0	1507.3	1565.6	1637.8	1710.5	1794.4	1873.5
27.5°	1138.8	1208.4	1271.6	1335.6	1404.9	1479.9	1555.5	1637.4	1732.6	1838.6	1950.2
30°	1110.6	1176.3	1237.8	1303.5	1375.7	1460.2	1543.1	1640.4	1750.6	1869.8	2002.4
32.5°	1077.6	1138.2	1198.0	1267.7	1346.2	1435.4	1532.0	1638.7	1771.1	1906.5	2043.0
35°	1021.3	1072.1	1133.5	1207.8	1296.6	1398.8	1510.5	1636.6	1788.5	1944.1	2059.0
37.5°	954.4	1001.7	1066.5	1148.0	1241.0	1350.6	1483.2	1632.9	1794.2	1918.3	1955.3
40°	909.5	953.3	1020.7	1105.2	1200.4	1316.4	1461.8	1620.1	1776.2	1855.4	1824.9
42.5°	861.6	907.6	973.2	1056.9	1159.3	1285.6	1434.9	1593.2	1724.0	1754.0	1648.6
45°	786.0	833.5	898.3	982.8	1092.9	1229.8	1385.4	1529.2	1604.6	1550.6	1387.5
47.5°	715.7	760.3	820.3	907.4	1021.1	1162.7	1312.6	1427.3	1433.3	1304.4	1130.2
50°	667.8	709.0	769.4	856.6	969.4	1112.7	1247.9	1338.3	1297.7	1151.7	984.4
52.5°	620.8	661.1	720.6	806.9	918.5	1049.8	1175.7	1239.1	1162.5	1012.7	869.7
55°	552.9	588.1	646.4	726.1	831.9	953.9	1060.8	1082.8	983.3	835.7	719.7
57.5°	486.6	519.5	572.5	645.9	742.7	850.6	934.3	929.6	824.5	697.8	605.8
60°	441.6	473.7	520.8	592.4	680.6	773.7	845.3	828.2	724.0	614.9	537.3
62.5°	401.5	430.1	474.6	537.3	617.7	703.9	762.8	737.5	635.4	540.0	478.8
65°	342.2	366.2	404.3	457.7	524.5	595.6	641.1	608.5	521.3	447.0	397.8
67.5°	285.7	304.9	336.8	379.4	436.4	493.5	521.2	488.4	418.7	364.4	328.0
70°	249.7	266.8	291.4	329.4	379.1	427.2	448.1	418.7	358.8	312.3	286.1
72.5°	213.7	227.9	249.5	283.6	323.4	365.2	383.5	355.4	306.2	266.9	242.4
75°	165.2	174.8	189.8	213.3	244.9	278.1	288.2	263.6	232.0	202.6	186.6
77.5°	118.3	126.4	137.8	152.6	174.9	196.0	204.9	190.7	166.3	147.7	134.5
80°	90.9	95.1	104.8	117.1	134.8	148.1	154.0	144.9	127.8	113.9	103.7
82.5°	64.8	69.1	74.9	85.0	96.3	105.4	111.6	105.5	93.2	82.2	76.4
85°	31.5	34.2	37.4	41.7	50.2	55.6	55.1	51.3	46.5	42.2	39.1
87.5°	11.6	12.3	13.9	16.2	17.8	19.7	20.8	20.3	18.8	17.7	16.6
90°	2.2	3.6	5.0	6.4	7.8	9.0	10.2	11.4	12.7	13.5	14.4
92.5°	11.2	10.2	9.2	8.2	8.3	9.3	10.5	11.6	12.7	13.5	14.4
95°	44.5	44.0	43.5	43.0	39.4	32.7	26.0	19.3	12.7	13.5	14.4
97.5°	95.1	96.0	97.0	97.9	91.8	78.6	65.4	52.1	38.9	34.0	29.0
100°	132.6	133.2	133.6	134.2	134.8	135.5	136.3	136.9	137.6	111.5	85.2
102.5°	171.3	172.1	172.7	173.3	173.9	174.4	174.8	175.2	175.6	170.6	165.6
105°	233.2	233.9	234.6	235.4	235.7	235.7	235.7	235.7	235.7	235.7	235.7
107.5°	296.8	296.8	296.8	296.8	296.9	297.3	297.6	298.0	298.3	298.4	298.4
110°	338.5	338.5	338.5	338.5	338.7	339.1	339.5	339.8	340.1	339.6	339.1



TEST NUMBER: P333277-927

CATALOG NUMBER: S125DIP-S1090D1035U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	378.2	378.6	379.1	379.5	379.8	380.0	380.2	380.4	380.6	379.9	379.3
115°	437.5	438.4	439.3	440.1	440.7	440.8	441.0	441.2	441.3	440.7	440.0
117.5°	497.5	497.4	497.4	497.4	497.7	498.4	499.0	499.7	500.3	499.5	498.5
120°	535.3	535.1	535.0	534.8	535.0	535.5	536.0	536.5	537.1	536.7	536.4
122.5°	569.7	570.4	571.0	571.7	572.1	572.4	572.7	572.9	573.1	572.7	572.4
125°	622.1	623.4	624.6	625.8	626.5	626.5	626.5	626.5	626.5	625.7	625.0
127.5°	671.3	672.2	673.0	673.9	674.3	674.2	674.1	674.0	673.9	673.5	673.1
130°	701.7	702.6	703.5	704.3	704.8	705.0	705.2	705.4	705.5	705.0	704.5
132.5°	732.2	733.2	734.2	735.2	735.5	735.1	734.8	734.4	734.0	733.9	733.8
135°	775.4	776.5	777.5	778.6	779.0	778.6	778.2	777.8	777.5	777.1	776.8
137.5°	815.0	815.9	816.8	817.7	818.0	817.7	817.4	817.1	816.7	816.8	816.9
140°	840.3	840.7	841.1	841.4	841.5	841.3	841.1	841.0	840.8	841.1	841.5
142.5°	863.6	863.9	864.0	864.3	864.5	864.7	865.0	865.2	865.5	865.5	865.6
145°	898.1	898.4	898.8	899.1	899.4	899.4	899.4	899.4	899.4	899.5	899.7
147.5°	927.7	927.6	927.6	927.5	927.6	927.8	928.0	928.2	928.4	928.7	928.8
150°	946.4	946.1	945.7	945.4	945.4	945.7	946.1	946.4	946.8	947.1	947.5
152.5°	964.4	963.6	962.8	962.0	961.9	962.2	962.5	962.9	963.2	963.6	963.9
155°	987.7	986.6	985.6	984.5	984.1	984.5	984.8	985.2	985.6	986.1	986.6
157.5°	1006.2	1005.7	1005.0	1004.4	1004.1	1004.1	1004.2	1004.2	1004.2	1004.8	1005.4
160°	1018.5	1017.5	1016.4	1015.3	1014.9	1015.1	1015.3	1015.4	1015.6	1016.3	1017.0
162.5°	1028.6	1027.5	1026.5	1025.5	1025.0	1025.2	1025.4	1025.6	1025.7	1026.7	1027.7
165°	1042.2	1041.2	1040.1	1039.1	1038.6	1038.8	1038.9	1039.2	1039.3	1040.4	1041.4
167.5°	1052.3	1051.2	1050.1	1049.1	1048.6	1048.8	1048.9	1049.1	1049.3	1050.6	1051.9
170°	1057.9	1056.6	1055.4	1054.2	1053.7	1053.8	1054.0	1054.2	1054.4	1055.7	1057.2
172.5°	1061.7	1060.4	1059.2	1058.0	1057.6	1057.8	1058.1	1058.4	1058.8	1060.0	1061.3
175°	1066.0	1064.9	1063.8	1062.8	1062.4	1062.6	1062.7	1062.9	1063.0	1064.5	1065.9
177.5°	1068.1	1067.2	1066.4	1065.6	1065.2	1065.3	1065.5	1065.6	1065.7	1066.8	1067.7
180°	1067.0	1067.0	1067.0	1067.0	1067.0	1067.0	1067.0	1067.0	1067.0	1067.0	1067.0



TEST NUMBER: P333277-927

CATALOG NUMBER: S125DIP-S1090D1035U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7
2.5°	1317.5	1320.9	1328.2	1325.6	1329.0	1330.7	1332.5
5°	1423.9	1441.0	1448.4	1447.4	1458.6	1456.0	1453.3
7.5°	1544.0	1562.0	1572.1	1584.6	1591.9	1592.4	1598.7
10°	1612.1	1635.6	1645.2	1658.6	1667.1	1672.0	1671.4
12.5°	1664.3	1682.7	1704.2	1710.8	1722.4	1728.4	1726.2
15°	1727.0	1756.4	1778.9	1790.1	1804.6	1808.9	1814.7
17.5°	1783.0	1822.5	1848.7	1883.6	1896.7	1904.7	1900.0
20°	1825.4	1877.3	1903.5	1945.2	1968.2	1980.5	1976.2
22.5°	1875.5	1931.6	1980.1	2016.2	2051.1	2067.8	2071.2
25°	1961.2	2038.2	2109.3	2157.0	2200.2	2210.3	2232.8
27.5°	2057.1	2147.8	2223.9	2273.9	2304.1	2315.4	2322.4
30°	2117.3	2207.7	2264.9	2297.0	2306.6	2305.6	2304.5
32.5°	2146.9	2203.5	2214.5	2205.4	2183.4	2164.8	2145.4
35°	2105.1	2062.8	1999.7	1918.4	1858.5	1798.2	1792.2
37.5°	1893.2	1758.2	1653.1	1535.8	1468.2	1426.3	1397.5
40°	1693.8	1540.4	1413.2	1314.2	1245.3	1218.0	1191.3
42.5°	1477.4	1330.9	1218.1	1135.4	1083.6	1053.4	1032.1
45°	1200.4	1071.0	982.8	922.9	881.7	858.2	844.8
47.5°	983.6	887.9	812.9	769.8	741.3	723.0	723.1
50°	867.3	775.9	726.1	691.9	667.3	652.8	655.5
52.5°	764.1	695.9	653.4	624.7	606.6	597.7	597.4
55°	639.0	589.8	562.0	541.1	528.8	518.6	520.8
57.5°	546.5	505.1	486.5	469.1	460.6	456.5	450.6
60°	489.3	457.2	441.1	427.2	418.7	415.4	409.6
62.5°	438.3	413.1	397.5	386.1	378.4	377.4	372.8
65°	368.4	349.1	335.3	329.9	321.9	319.7	319.7
67.5°	303.7	289.9	279.1	274.2	270.7	271.2	268.6
70°	263.1	251.8	244.9	239.6	236.9	237.4	235.3
72.5°	230.1	217.6	211.5	208.3	204.8	206.2	205.3
75°	174.3	167.9	164.7	161.4	159.3	158.3	157.2
77.5°	128.0	122.3	119.9	118.0	118.4	115.8	117.9
80°	98.9	94.1	92.5	89.8	89.3	89.3	88.7
82.5°	72.4	69.7	68.5	66.3	65.4	66.2	64.8
85°	37.4	35.3	34.8	34.8	33.7	32.6	35.3
87.5°	16.7	15.2	15.4	15.1	15.1	14.8	14.1
90°	15.3	16.2	16.9	17.4	17.9	18.5	19.0
92.5°	15.3	16.2	16.7	17.0	17.2	17.5	17.7
95°	15.3	16.2	16.6	16.6	16.6	16.6	16.6
97.5°	24.1	19.1	16.6	16.6	16.6	16.6	16.6
100°	59.1	32.9	19.4	18.7	18.0	17.3	16.6
102.5°	160.7	155.7	147.3	135.4	123.4	111.5	99.5
105°	235.7	235.7	235.6	235.4	235.3	235.1	234.9
107.5°	298.5	298.5	298.3	297.7	297.2	296.7	296.1
110°	338.5	338.0	337.9	338.0	338.2	338.3	338.5



TEST NUMBER: P333277-927

CATALOG NUMBER: S125DIP-S1090D1035U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	378.6	378.0	377.5	377.2	377.0	376.8	376.5
115°	439.3	438.6	437.7	436.7	435.5	434.5	433.5
117.5°	497.6	496.7	496.0	495.6	495.1	494.6	494.2
120°	536.0	535.7	535.0	534.2	533.3	532.4	531.6
122.5°	572.1	571.7	571.0	570.1	569.0	568.0	567.0
125°	624.3	623.6	623.1	622.5	621.9	621.5	620.9
127.5°	672.7	672.3	671.5	670.2	668.9	667.7	666.3
130°	703.9	703.5	702.7	701.9	701.0	700.1	699.2
132.5°	733.7	733.6	733.1	732.2	731.3	730.5	729.6
135°	776.5	776.1	775.4	774.4	773.3	772.2	771.2
137.5°	817.0	817.1	816.6	815.7	814.8	813.9	812.9
140°	841.9	842.2	841.9	840.8	839.7	838.7	837.7
142.5°	865.7	865.8	865.3	864.2	863.2	862.1	861.0
145°	899.8	900.0	899.6	898.6	897.5	896.4	895.4
147.5°	929.1	929.3	928.8	927.5	926.2	925.0	923.7
150°	947.8	948.2	947.7	946.3	944.8	943.4	942.1
152.5°	964.3	964.6	964.2	962.9	961.6	960.4	959.1
155°	987.1	987.7	987.2	985.8	984.4	983.0	981.6
157.5°	1005.9	1006.5	1006.1	1004.6	1003.2	1001.8	1000.4
160°	1017.7	1018.4	1018.0	1016.7	1015.3	1013.8	1012.4
162.5°	1028.6	1029.7	1029.4	1027.9	1026.3	1024.8	1023.2
165°	1042.5	1043.5	1043.4	1042.0	1040.5	1039.2	1037.8
167.5°	1053.1	1054.4	1054.2	1052.7	1051.1	1049.5	1047.9
170°	1058.6	1060.0	1059.9	1058.3	1056.8	1055.2	1053.6
172.5°	1062.6	1063.8	1063.7	1062.1	1060.5	1058.9	1057.4
175°	1067.3	1068.7	1068.6	1067.0	1065.4	1063.8	1062.2
177.5°	1068.7	1069.7	1069.6	1068.5	1067.4	1066.3	1065.1
180°	1067.0	1067.0	1067.0	1067.0	1067.0	1067.0	1067.0

(END OF REPORT)