

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332940-930

Luminaire Tested: **S124RDIP-S795D810U930-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332940-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIP-S795D810U930-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 795 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 810 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5255.6 lumens
Efficiency: N/A
Efficacy: 114.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 45.9
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332940-930

CATALOG NUMBER: S124RDIP-S795D810U930-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332940-930

CATALOG NUMBER: S124RDIP-S795D810U930-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	50
1	98	94	90	87	90	87	83	81	73	71	69	61	60	58	50	49	48	43
2	89	82	76	71	82	76	71	66	65	61	57	54	51	49	44	42	41	36
3	82	72	65	60	75	67	61	56	57	52	49	48	45	42	39	37	35	31
4	75	64	57	51	69	60	53	48	51	46	42	43	39	36	35	33	30	27
5	69	57	49	43	63	53	46	41	46	40	36	39	34	31	32	29	26	23
6	63	52	44	38	58	48	41	36	41	36	32	35	31	27	29	26	23	21
7	59	47	39	33	54	43	36	31	37	32	28	32	28	24	27	23	21	18
8	55	42	35	29	50	40	33	28	34	29	25	29	25	22	24	21	19	16
9	51	39	31	26	47	36	30	25	31	26	22	27	23	20	23	19	17	15
10	47	36	28	24	44	33	27	22	29	24	20	25	21	18	21	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9143	9143	9143
5°	9164	9052	9108
10°	9107	8943	8943
15°	9002	8756	8690
20°	8858	8508	8352
25°	8675	8219	8011
30°	8496	7914	7582
35°	8298	7597	7154
40°	8061	7238	6690
45°	7841	6882	6218
50°	7592	6469	5718
55°	7323	6042	5175
60°	7030	5572	4621
65°	6758	4988	4076
70°	6366	4338	3460
75°	5870	3599	2813
80°	5119	2738	2580
85°	4335	2492	2325



TEST NUMBER: P332940-930

CATALOG NUMBER: S124RDIP-S795D810U930-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	106.4	2.0
10°-20°	296.7	5.6
20°-30°	428.4	8.2
30°-40°	485.6	9.2
40°-50°	468.9	8.9
50°-60°	389.9	7.4
60°-70°	269.3	5.1
70°-80°	136.5	2.6
80°-90°	37.5	0.7
90°-100°	29.1	0.6
100°-110°	185.9	3.5
110°-120°	355.6	6.8
120°-130°	451.4	8.6
130°-140°	482.9	9.2
140°-150°	451.6	8.6
150°-160°	364.2	6.9
160°-170°	234.9	4.5
170°-180°	81.0	1.5
0°-30°	831.5	15.8
0°-40°	1317.1	25.1
0°-60°	2176.0	41.4
0°-90°	2619.2	49.8
90°-120°	570.6	10.9
90°-150°	1956.4	37.2
90°-180°	2636.0	50.2
0°-180°	5255.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1133	1133	1133	1133	1133	
5°	1131	1127	1117	1125	1124	107
15°	1077	1069	1048	1046	1040	303
25°	974	957	923	908	899	449
35°	842	813	771	742	726	526
45°	687	654	603	562	545	529
55°	520	484	429	386	368	465
65°	354	316	261	225	213	349
75°	188	156	115	96	90	199
85°	47	30	27	25	25	53
90°	2	9	14	18	19	4
95°	35	15	14	18	18	45
105°	192	196	199	203	182	201
115°	358	360	360	361	361	352
125°	504	506	505	507	507	449
135°	625	624	627	628	629	481
145°	720	722	722	723	724	450
155°	790	790	789	791	789	364
165°	833	830	830	834	829	235
175°	852	849	849	854	847	81
180°	852	852	852	852	852	



TEST NUMBER: P332940-930

CATALOG NUMBER: S124RDIP-S795D810U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1132.6	1132.6	1132.6	1132.6	1132.6	1132.6	1132.6	1132.6	1132.6	1132.6	1132.6
2.5°	1135.4	1134.7	1134.1	1133.5	1132.9	1131.7	1130.0	1128.4	1126.7	1124.9	1126.7
5°	1130.8	1130.1	1129.3	1128.5	1127.7	1126.3	1123.9	1121.6	1119.2	1117.0	1118.9
7.5°	1120.6	1119.8	1119.0	1118.2	1117.4	1115.5	1112.5	1109.5	1106.4	1103.4	1104.6
10°	1110.9	1109.9	1109.0	1108.0	1107.0	1104.8	1101.4	1097.9	1094.5	1091.0	1091.7
12.5°	1098.4	1097.3	1096.2	1095.0	1094.0	1091.4	1087.3	1083.1	1079.0	1075.0	1075.5
15°	1077.1	1075.4	1073.6	1071.9	1070.2	1066.9	1062.0	1057.2	1052.4	1047.6	1047.2
17.5°	1051.2	1048.7	1046.2	1043.7	1041.2	1037.1	1031.3	1025.5	1019.7	1013.9	1012.8
20°	1031.1	1028.6	1026.1	1023.6	1021.1	1016.6	1010.0	1003.5	996.9	990.3	988.8
22.5°	1008.9	1006.1	1003.3	1000.5	997.7	992.7	985.7	978.7	971.7	964.7	962.4
25°	973.9	970.4	966.9	963.4	960.0	954.3	946.4	938.5	930.6	922.7	919.4
27.5°	937.1	932.8	928.4	924.1	919.7	913.3	904.8	896.4	887.9	879.5	875.5
30°	911.4	906.6	901.8	897.0	892.2	885.3	876.2	867.2	858.0	849.0	844.2
32.5°	884.4	879.0	873.5	868.0	862.7	855.2	845.9	836.5	827.1	817.7	812.2
35°	842.0	835.9	829.7	823.5	817.4	809.5	799.9	790.2	780.6	770.9	764.4
37.5°	796.8	790.4	784.1	777.7	771.4	762.9	752.2	741.5	730.8	720.2	712.8
40°	764.9	758.6	752.2	745.8	739.5	730.8	719.7	708.8	697.8	686.8	678.7
42.5°	734.3	727.7	721.1	714.4	707.7	698.6	687.2	675.7	664.3	652.8	644.6
45°	686.8	679.7	672.5	665.4	658.3	649.0	637.4	625.8	614.2	602.8	593.3
47.5°	637.7	630.4	623.1	615.6	608.3	598.6	586.6	574.5	562.6	550.5	540.7
50°	604.5	597.0	589.4	581.9	574.4	564.4	552.1	539.8	527.4	515.1	505.5
52.5°	570.5	563.1	555.7	548.4	541.0	531.0	518.4	505.7	493.1	480.5	470.7
55°	520.3	512.6	504.9	497.2	489.5	479.4	466.8	454.3	441.8	429.3	419.2
57.5°	470.8	462.7	454.7	446.7	438.6	428.4	416.1	403.8	391.5	379.1	369.0
60°	435.4	427.6	420.0	412.2	404.5	394.5	382.1	369.8	357.5	345.1	335.1
62.5°	403.4	395.4	387.4	379.4	371.4	361.0	348.4	335.7	323.1	310.5	301.2
65°	353.8	345.5	337.2	329.0	320.7	310.4	298.0	285.7	273.4	261.1	252.7
67.5°	302.3	294.4	286.4	278.5	270.5	260.9	249.4	238.0	226.5	215.1	207.9
70°	269.7	261.6	253.5	245.4	237.3	227.8	216.8	205.8	194.9	183.8	177.5
72.5°	235.1	227.7	220.4	213.0	205.7	196.9	186.5	176.1	165.8	155.4	149.9
75°	188.2	181.1	173.9	166.8	159.6	151.6	142.5	133.5	124.4	115.4	110.9
77.5°	140.6	134.6	128.6	122.5	116.4	109.7	102.5	95.1	87.8	80.5	77.9
80°	110.1	104.5	99.0	93.4	87.8	82.1	76.3	70.5	64.7	58.9	58.4
82.5°	83.8	78.7	73.5	68.4	63.3	59.0	55.8	52.4	49.1	45.8	45.3
85°	46.8	43.0	39.1	35.3	31.4	29.2	28.6	28.0	27.5	26.9	26.5
87.5°	16.3	15.4	14.5	13.5	12.6	12.2	12.3	12.4	12.5	12.6	12.6
90°	1.9	3.5	5.1	6.6	8.2	9.5	10.6	11.7	12.9	14.0	14.8
92.5°	8.1	8.2	8.2	8.3	8.4	9.0	10.1	11.3	12.4	13.5	14.3
95°	35.1	30.2	25.4	20.6	15.8	13.5	13.6	13.8	13.9	14.0	14.8
97.5°	74.4	77.5	80.5	83.5	86.5	80.1	64.2	48.4	32.6	16.8	16.9
100°	104.5	107.1	109.7	112.2	114.7	106.2	86.7	67.2	47.6	28.0	25.6
102.5°	138.2	140.1	141.9	143.8	145.7	145.4	142.8	140.2	137.7	135.2	109.2
105°	191.8	192.7	193.6	194.4	195.3	196.1	196.7	197.5	198.2	198.9	200.2
107.5°	241.7	242.1	242.6	243.0	243.4	244.1	245.1	246.1	247.0	248.0	248.6
110°	275.4	275.8	276.2	276.6	277.1	277.7	278.6	279.4	280.3	281.1	281.4



TEST NUMBER: P332940-930

CATALOG NUMBER: S124RDIP-S795D810U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	308.0	308.8	309.6	310.3	311.1	311.7	312.1	312.4	312.8	313.2	313.2
115°	358.2	358.7	359.1	359.5	360.0	360.1	360.0	359.8	359.7	359.5	359.8
117.5°	403.5	404.1	404.6	405.2	405.8	406.3	406.5	406.8	407.2	407.5	407.4
120°	434.1	434.7	435.3	435.9	436.3	436.6	436.4	436.3	436.2	436.0	436.3
122.5°	462.7	463.0	463.3	463.7	464.1	464.3	464.5	464.7	464.9	465.1	465.3
125°	503.6	504.2	504.8	505.3	505.9	506.0	505.7	505.5	505.2	504.9	505.3
127.5°	542.3	542.5	542.7	542.8	542.9	543.3	544.0	544.6	545.3	545.9	545.8
130°	567.4	567.5	567.6	567.8	567.9	568.2	568.6	569.1	569.5	569.9	570.1
132.5°	590.3	590.5	590.8	591.1	591.3	591.7	592.2	592.8	593.3	593.9	594.0
135°	624.8	624.6	624.4	624.3	624.2	624.4	624.9	625.5	626.1	626.6	626.9
137.5°	655.2	655.3	655.3	655.3	655.4	655.7	656.4	657.0	657.6	658.3	658.6
140°	675.1	675.4	675.6	676.0	676.2	676.5	676.8	677.1	677.4	677.6	678.1
142.5°	692.9	693.4	694.0	694.5	695.0	695.3	695.5	695.7	695.9	696.0	696.3
145°	720.3	720.8	721.2	721.6	722.0	722.3	722.3	722.3	722.3	722.3	722.4
147.5°	742.2	743.0	743.7	744.5	745.3	745.7	745.5	745.3	745.2	745.1	745.2
150°	758.0	758.6	759.1	759.7	760.2	760.4	760.3	760.2	760.0	759.9	759.9
152.5°	771.2	771.7	772.1	772.6	773.1	773.1	772.9	772.7	772.3	772.1	772.3
155°	789.9	789.9	790.1	790.3	790.4	790.3	789.9	789.4	789.0	788.6	789.1
157.5°	805.5	805.4	805.4	805.3	805.2	804.9	804.4	804.0	803.5	803.0	803.7
160°	814.7	814.2	813.8	813.4	813.0	812.7	812.6	812.4	812.3	812.1	813.0
162.5°	822.9	822.3	821.7	821.3	820.7	820.4	820.2	820.1	819.9	819.8	820.7
165°	833.2	832.5	831.8	831.0	830.4	830.0	830.0	830.0	830.0	830.0	831.1
167.5°	841.3	840.6	839.8	839.1	838.4	838.0	837.9	837.8	837.7	837.6	838.9
170°	846.0	845.1	844.2	843.3	842.5	842.2	842.3	842.4	842.6	842.8	843.8
172.5°	849.0	848.2	847.3	846.4	845.6	845.2	845.4	845.5	845.6	845.8	846.9
175°	852.3	851.4	850.6	849.8	848.9	848.6	848.7	848.8	849.0	849.1	850.4
177.5°	853.9	853.0	852.2	851.4	850.7	850.4	850.6	850.8	851.1	851.3	852.2
180°	852.3	852.3	852.3	852.3	852.3	852.3	852.3	852.3	852.3	852.3	852.3



TEST NUMBER: P332940-930

CATALOG NUMBER: S124RDIP-S795D810U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1132.6	1132.6	1132.6	1132.6	1132.6	1132.6	1132.6	1132.6
2.5°	1128.4	1130.0	1131.7	1132.5	1132.4	1132.2	1132.0	1131.9
5°	1120.8	1122.7	1124.7	1125.4	1125.0	1124.7	1124.3	1123.9
7.5°	1105.9	1107.2	1108.4	1108.6	1108.1	1107.4	1106.9	1106.2
10°	1092.5	1093.2	1094.1	1094.1	1093.2	1092.5	1091.7	1091.0
12.5°	1076.0	1076.4	1076.8	1076.5	1075.5	1074.4	1073.3	1072.2
15°	1046.8	1046.4	1046.0	1045.2	1043.8	1042.4	1041.1	1039.8
17.5°	1011.8	1010.7	1009.6	1008.0	1006.0	1004.0	1001.9	999.9
20°	987.2	985.7	984.1	982.2	979.7	977.1	974.6	972.2
22.5°	960.1	957.7	955.4	953.2	951.2	949.2	947.1	945.1
25°	916.2	912.9	909.6	907.0	905.1	903.2	901.2	899.3
27.5°	871.4	867.4	863.3	859.9	857.1	854.4	851.6	848.8
30°	839.4	834.5	829.7	825.7	822.7	819.6	816.5	813.4
32.5°	806.6	801.0	795.4	791.2	788.2	785.3	782.4	779.4
35°	757.8	751.3	744.8	739.7	736.3	732.8	729.3	725.9
37.5°	705.5	698.1	690.8	685.4	682.0	678.5	675.1	671.6
40°	670.7	662.5	654.4	648.7	645.2	641.7	638.3	634.8
42.5°	636.3	628.1	619.9	613.9	610.3	606.7	603.1	599.4
45°	583.8	574.4	564.9	558.5	555.0	551.5	548.0	544.6
47.5°	530.9	521.1	511.4	504.5	500.8	496.9	493.1	489.3
50°	495.9	486.2	476.5	469.9	466.3	462.6	458.9	455.3
52.5°	460.9	451.1	441.2	434.5	430.6	426.8	423.1	419.2
55°	409.2	399.2	389.2	382.4	378.7	375.0	371.4	367.7
57.5°	358.8	348.6	338.4	332.0	329.2	326.4	323.7	320.9
60°	325.1	315.1	305.1	298.5	295.5	292.4	289.3	286.2
62.5°	292.0	282.7	273.5	267.6	265.1	262.7	260.2	257.7
65°	244.4	236.2	227.9	222.6	220.3	217.9	215.6	213.4
67.5°	200.8	193.7	186.5	181.7	179.2	176.6	174.1	171.5
70°	171.1	164.8	158.4	154.3	152.4	150.4	148.5	146.6
72.5°	144.6	139.1	133.6	130.0	128.3	126.5	124.7	122.9
75°	106.5	102.1	97.6	94.8	93.7	92.5	91.3	90.2
77.5°	75.3	72.7	70.1	68.6	68.3	68.0	67.7	67.3
80°	57.8	57.2	56.7	56.3	56.1	55.8	55.7	55.5
82.5°	44.9	44.5	44.1	43.8	43.6	43.4	43.2	43.0
85°	26.1	25.8	25.4	25.1	25.1	25.1	25.1	25.1
87.5°	12.6	12.6	12.6	12.7	12.9	13.1	13.3	13.5
90°	15.7	16.6	17.4	18.0	18.3	18.6	18.8	19.2
92.5°	15.2	16.1	16.9	17.4	17.4	17.4	17.5	17.6
95°	15.7	16.6	17.4	17.9	18.1	18.2	18.3	18.5
97.5°	17.0	17.1	17.2	17.3	17.4	17.5	17.7	17.9
100°	23.2	20.8	18.4	17.3	17.4	17.5	17.7	17.9
102.5°	83.2	57.2	31.2	18.3	18.3	18.3	18.3	18.3
105°	201.5	202.7	204.0	202.1	197.0	191.8	186.8	181.6
107.5°	249.2	249.8	250.5	251.0	251.6	252.1	252.7	253.2
110°	281.7	282.0	282.3	282.6	283.1	283.5	283.9	284.3



TEST NUMBER: P332940-930

CATALOG NUMBER: S124RDIP-S795D810U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	313.2	313.1	313.0	313.2	313.8	314.4	314.9	315.4
115°	360.1	360.4	360.7	360.9	360.9	360.9	360.9	360.9
117.5°	407.3	407.3	407.2	407.2	407.2	407.1	407.0	407.0
120°	436.6	436.9	437.2	437.2	436.9	436.6	436.3	436.0
122.5°	465.5	465.6	465.8	465.7	465.5	465.1	464.9	464.6
125°	505.7	506.1	506.5	506.9	507.0	507.1	507.3	507.4
127.5°	545.8	545.7	545.6	545.5	545.4	545.3	545.2	545.0
130°	570.2	570.3	570.5	570.5	570.5	570.5	570.5	570.5
132.5°	594.2	594.3	594.4	594.4	594.4	594.2	594.1	594.0
135°	627.2	627.5	627.8	628.0	628.4	628.6	628.9	629.2
137.5°	658.8	659.2	659.5	659.6	659.5	659.4	659.3	659.3
140°	678.5	678.9	679.3	679.6	679.8	679.9	680.0	680.2
142.5°	696.6	696.9	697.2	697.4	697.4	697.5	697.5	697.5
145°	722.5	722.7	722.8	723.0	723.3	723.6	723.9	724.1
147.5°	745.3	745.4	745.5	745.7	745.8	745.9	746.1	746.2
150°	759.9	759.9	759.9	759.9	760.1	760.2	760.3	760.5
152.5°	772.6	772.8	773.0	773.1	773.0	772.9	772.8	772.7
155°	789.7	790.3	790.8	790.9	790.4	790.0	789.6	789.2
157.5°	804.5	805.2	805.9	805.9	805.2	804.5	803.7	803.0
160°	813.8	814.7	815.5	815.5	814.7	813.8	813.0	812.1
162.5°	821.5	822.3	823.2	823.1	822.1	821.2	820.3	819.3
165°	832.3	833.4	834.5	834.5	833.2	831.9	830.6	829.3
167.5°	840.2	841.4	842.6	842.5	841.1	839.7	838.3	836.9
170°	845.0	846.1	847.3	847.1	845.7	844.3	842.9	841.5
172.5°	848.1	849.2	850.4	850.1	848.6	847.1	845.5	844.0
175°	851.7	853.0	854.2	854.0	852.3	850.6	848.9	847.2
177.5°	853.1	854.0	854.9	854.7	853.3	852.0	850.6	849.2
180°	852.3	852.3	852.3	852.3	852.3	852.3	852.3	852.3

(END OF REPORT)