

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333279-927

Luminaire Tested: **S125DIP-S1090D1035U927-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333279-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S1090D1035U927-4F0-1E-UDD-A4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1090 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1035 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6498.4 lumens
Efficiency: N/A
Efficacy: 107.4 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 60.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333279-927

CATALOG NUMBER: S125DIP-S1090D1035U927-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P333279-927

CATALOG NUMBER: S125DIP-S1090D1035U927-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	86	86	86	73	73	73	60	60	60	55
1	99	95	91	88	92	88	85	82	76	73	71	64	63	61	54	53	52	47
2	90	83	77	72	84	77	72	68	67	63	59	57	54	51	48	46	44	39
3	83	73	66	60	76	68	62	57	59	54	50	50	47	44	42	40	37	34
4	76	65	57	51	70	61	54	48	53	47	43	45	41	38	38	35	32	29
5	70	58	50	44	64	54	47	42	47	41	37	40	36	33	34	31	28	25
6	64	52	44	38	59	49	41	36	42	37	32	37	32	29	31	28	25	22
7	59	47	39	33	55	44	37	32	39	33	29	33	29	25	28	25	22	20
8	55	43	35	30	51	40	33	28	35	29	25	30	26	23	26	23	20	18
9	51	39	31	26	48	37	30	25	32	27	23	28	24	20	24	21	18	16
10	48	36	29	24	44	34	27	23	30	24	20	26	21	18	22	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	8136	8136	8136	8136
5°	9422	8163	7148	8163
10°	10961	8121	6263	8121
15°	12133	8062	5777	8062
20°	13582	7967	5388	7967
25°	15911	7860	5197	7860
30°	17186	7756	5032	7756
35°	14130	7559	4924	7559
40°	10044	7284	4806	7284
45°	7716	6915	4737	6915
50°	6586	6457	4728	6457
55°	5864	6008	4769	6008
60°	5291	5518	4890	5518
65°	4886	5025	5017	5025
70°	4443	4513	5089	4513
75°	3923	3975	5043	3975
80°	3299	3239	4616	3239
85°	2616	2334	3720	2334



TEST NUMBER: P333279-927

CATALOG NUMBER: S125DIP-S1090D1035U927-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	121.3	1.9
10°-20°	361.1	5.6
20°-30°	586.3	9.0
30°-40°	715.2	11.0
40°-50°	650.6	10.0
50°-60°	518.2	8.0
60°-70°	361.0	5.6
70°-80°	192.5	3.0
80°-90°	50.8	0.8
90°-100°	284.3	4.4
100°-110°	611.2	9.4
110°-120°	573.6	8.8
120°-130°	464.9	7.2
130°-140°	373.0	5.7
140°-150°	281.5	4.3
150°-160°	198.2	3.0
160°-170°	116.8	1.8
170°-180°	38.0	0.6
0°-30°	1068.7	16.4
0°-40°	1783.8	27.5
0°-60°	2952.7	45.4
0°-90°	3556.9	54.7
90°-120°	1469.1	22.6
90°-150°	2588.5	39.8
90°-180°	2941.0	45.3
0°-180°	6498.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1260	1260	1260	1260	1260	
5°	1453	1259	1102	1259	1453	146
15°	1815	1206	864	1206	1815	519
25°	2233	1103	729	1103	2233	1020
35°	1792	959	624	959	1792	1097
45°	845	757	519	757	845	676
55°	521	534	424	534	521	469
65°	320	329	328	329	320	317
75°	157	159	202	159	157	169
85°	35	32	50	32	35	41
90°	18	1	18	1	18	14
95°	186	26	186	26	186	263
105°	1048	89	1048	89	1048	1042
115°	1167	160	1167	160	1167	1140
125°	920	221	920	221	920	832
135°	764	259	764	259	764	592
145°	603	302	603	302	603	383
155°	505	345	505	345	505	236
165°	443	376	443	376	443	127
175°	398	391	398	391	398	39
180°	392	392	392	392	392	



TEST NUMBER: P333279-927

CATALOG NUMBER: S125DIP-S1090D1035U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7
2.5°	1332.5	1330.7	1329.0	1325.6	1328.2	1320.9	1317.5	1311.5	1304.2	1301.6	1298.6
5°	1453.3	1456.0	1458.6	1447.4	1448.4	1441.0	1423.9	1409.9	1398.8	1384.3	1374.1
7.5°	1598.7	1592.4	1591.9	1584.6	1572.1	1562.0	1544.0	1521.1	1499.0	1473.8	1452.9
10°	1671.4	1672.0	1667.1	1658.6	1645.2	1635.6	1612.1	1589.6	1562.3	1530.3	1507.3
12.5°	1726.2	1728.4	1722.4	1710.8	1704.2	1682.7	1664.3	1637.5	1605.1	1579.5	1544.5
15°	1814.7	1808.9	1804.6	1790.1	1778.9	1756.4	1727.0	1699.2	1663.9	1631.3	1598.7
17.5°	1900.0	1904.7	1896.7	1883.6	1848.7	1822.5	1783.0	1745.0	1701.1	1657.3	1618.3
20°	1976.2	1980.5	1968.2	1945.2	1903.5	1877.3	1825.4	1776.2	1725.5	1669.3	1626.5
22.5°	2071.2	2067.8	2051.1	2016.2	1980.1	1931.6	1875.5	1815.6	1751.9	1688.5	1631.7
25°	2232.8	2210.3	2200.2	2157.0	2109.3	2038.2	1961.2	1873.5	1794.4	1710.5	1637.8
27.5°	2322.4	2315.4	2304.1	2273.9	2223.9	2147.8	2057.1	1950.2	1838.6	1732.6	1637.4
30°	2304.5	2305.6	2306.6	2297.0	2264.9	2207.7	2117.3	2002.4	1869.8	1750.6	1640.4
32.5°	2145.4	2164.8	2183.4	2205.4	2214.5	2203.5	2146.9	2043.0	1906.5	1771.1	1638.7
35°	1792.2	1798.2	1858.5	1918.4	1999.7	2062.8	2105.1	2059.0	1944.1	1788.5	1636.6
37.5°	1397.5	1426.3	1468.2	1535.8	1653.1	1758.2	1893.2	1955.3	1918.3	1794.2	1632.9
40°	1191.3	1218.0	1245.3	1314.2	1413.2	1540.4	1693.8	1824.9	1855.4	1776.2	1620.1
42.5°	1032.1	1053.4	1083.6	1135.4	1218.1	1330.9	1477.4	1648.6	1754.0	1724.0	1593.2
45°	844.8	858.2	881.7	922.9	982.8	1071.0	1200.4	1387.5	1550.6	1604.6	1529.2
47.5°	723.1	723.0	741.3	769.8	812.9	887.9	983.6	1130.2	1304.4	1433.3	1427.3
50°	655.5	652.8	667.3	691.9	726.1	775.9	867.3	984.4	1151.7	1297.7	1338.3
52.5°	597.4	597.7	606.6	624.7	653.4	695.9	764.1	869.7	1012.7	1162.5	1239.1
55°	520.8	518.6	528.8	541.1	562.0	589.8	639.0	719.7	835.7	983.3	1082.8
57.5°	450.6	456.5	460.6	469.1	486.5	505.1	546.5	605.8	697.8	824.5	929.6
60°	409.6	415.4	418.7	427.2	441.1	457.2	489.3	537.3	614.9	724.0	828.2
62.5°	372.8	377.4	378.4	386.1	397.5	413.1	438.3	478.8	540.0	635.4	737.5
65°	319.7	319.7	321.9	329.9	335.3	349.1	368.4	397.8	447.0	521.3	608.5
67.5°	268.6	271.2	270.7	274.2	279.1	289.9	303.7	328.0	364.4	418.7	488.4
70°	235.3	237.4	236.9	239.6	244.9	251.8	263.1	286.1	312.3	358.8	418.7
72.5°	205.3	206.2	204.8	208.3	211.5	217.6	230.1	242.4	266.9	306.2	355.4
75°	157.2	158.3	159.3	161.4	164.7	167.9	174.3	186.6	202.6	232.0	263.6
77.5°	117.9	115.8	118.4	118.0	119.9	122.3	128.0	134.5	147.7	166.3	190.7
80°	88.7	89.3	89.3	89.8	92.5	94.1	98.9	103.7	113.9	127.8	144.9
82.5°	64.8	66.2	65.4	66.3	68.5	69.7	72.4	76.4	82.2	93.2	105.5
85°	35.3	32.6	33.7	34.8	34.8	35.3	37.4	39.1	42.2	46.5	51.3
87.5°	13.9	14.7	15.1	15.1	15.4	15.1	16.7	16.6	17.7	18.8	20.2
90°	18.2	18.2	17.4	17.4	17.4	15.8	15.1	14.3	13.5	12.7	11.1
92.5°	50.5	51.7	52.8	54.7	64.9	76.5	101.7	140.1	206.4	254.9	259.0
95°	185.8	198.5	204.9	228.5	284.7	351.1	448.4	568.6	685.6	700.7	571.8
97.5°	449.2	459.3	482.2	526.6	575.4	667.7	762.5	846.8	867.5	748.3	510.6
100°	616.9	629.5	658.8	715.7	770.2	852.5	934.0	972.7	911.8	714.1	455.5
102.5°	804.1	813.6	845.4	885.9	944.2	999.9	1038.9	1015.1	885.3	654.0	413.8
105°	1047.8	1057.3	1073.2	1099.2	1124.5	1133.2	1098.4	990.1	800.3	573.3	373.3
107.5°	1177.2	1183.5	1188.7	1188.9	1176.1	1134.8	1045.4	900.9	713.6	517.8	356.2
110°	1220.2	1220.2	1214.7	1199.7	1164.1	1096.9	985.3	835.1	664.2	491.9	351.1



TEST NUMBER: P333279-927

CATALOG NUMBER: S125DIP-S1090D1035U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1215.1	1209.5	1195.7	1169.9	1117.9	1038.6	925.9	783.2	627.6	476.7	351.1
115°	1167.3	1157.0	1134.8	1096.9	1035.1	949.0	840.7	718.0	587.6	460.3	353.5
117.5°	1083.2	1076.9	1054.9	1015.7	954.0	875.0	781.6	676.0	563.7	452.2	358.7
120°	1028.9	1022.5	1001.2	963.2	904.7	835.1	748.1	653.2	550.4	448.4	363.8
122.5°	980.8	975.1	953.7	918.9	866.7	801.5	724.1	636.1	539.0	445.2	368.2
125°	919.7	911.8	894.4	862.0	817.7	760.7	692.0	611.3	523.6	441.2	375.7
127.5°	867.5	864.0	847.6	819.0	778.8	725.5	661.3	586.0	509.3	439.3	384.0
130°	839.1	834.3	818.5	792.4	752.9	701.5	639.8	570.2	499.8	438.1	389.1
132.5°	810.6	805.2	790.7	764.5	725.0	675.5	619.5	554.4	492.2	438.1	394.7
135°	763.9	759.1	745.0	718.8	684.0	639.0	588.4	533.8	483.2	438.1	402.5
137.5°	714.1	708.9	695.8	672.0	640.9	602.6	560.5	516.4	475.2	439.0	409.6
140°	679.3	675.3	663.5	642.9	613.7	580.4	544.1	506.9	471.3	439.7	412.8
142.5°	647.1	643.7	632.5	615.1	590.3	561.5	530.1	498.7	468.2	440.3	414.7
145°	602.6	599.4	590.7	577.3	558.3	536.9	512.5	487.9	463.4	439.7	416.8
147.5°	565.0	563.6	558.5	547.7	532.7	516.6	497.7	477.8	458.5	437.6	417.6
150°	544.1	543.3	540.1	530.6	518.8	504.5	489.5	472.1	454.7	435.7	417.6
152.5°	527.6	526.8	523.7	516.1	506.1	495.0	481.3	465.8	450.3	433.2	416.9
155°	505.3	504.5	502.2	496.6	488.7	480.1	469.0	456.3	442.8	428.6	415.2
157.5°	485.4	485.5	483.3	478.8	472.6	465.8	457.2	446.8	435.9	423.9	413.1
160°	472.1	472.9	471.3	467.4	461.8	456.3	448.4	440.5	430.2	420.7	411.2
162.5°	460.1	460.3	459.9	456.6	452.3	447.4	440.8	433.6	425.2	416.9	409.3
165°	442.8	442.8	442.8	441.2	438.1	434.2	429.4	423.9	417.6	411.2	406.5
167.5°	427.1	427.2	427.9	426.4	424.8	422.0	418.4	414.7	410.1	405.7	402.0
170°	417.6	418.4	418.4	417.6	416.0	414.4	412.0	409.6	405.7	402.5	400.1
172.5°	408.7	409.5	410.7	409.3	409.0	408.1	406.3	403.9	401.2	398.7	397.6
175°	397.8	398.5	400.1	399.3	399.3	399.3	397.8	397.8	395.4	394.6	394.6
177.5°	392.2	392.2	394.1	393.5	394.1	394.1	394.1	393.5	392.8	392.2	392.2
180°	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2



TEST NUMBER: P333279-927

CATALOG NUMBER: S125DIP-S1090D1035U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7
2.5°	1296.1	1293.1	1289.7	1283.7	1276.4	1272.6	1266.5	1262.7	1255.0	1248.6	1241.7
5°	1361.8	1348.0	1335.1	1318.5	1300.4	1288.6	1274.7	1259.2	1243.2	1226.5	1208.4
7.5°	1430.0	1405.3	1378.6	1349.9	1321.8	1295.9	1271.1	1246.9	1224.2	1196.8	1173.6
10°	1475.8	1444.7	1411.6	1372.5	1334.6	1301.4	1267.7	1238.3	1208.4	1176.3	1148.0
12.5°	1521.5	1480.2	1433.4	1390.5	1344.8	1304.8	1265.2	1227.6	1190.0	1154.5	1121.4
15°	1553.8	1517.4	1474.1	1413.2	1361.8	1306.8	1254.3	1205.7	1160.2	1120.7	1079.0
17.5°	1575.1	1528.2	1481.7	1423.2	1356.0	1294.3	1235.0	1179.3	1128.1	1077.9	1037.7
20°	1578.9	1530.8	1482.2	1424.9	1356.0	1285.4	1226.1	1159.2	1104.1	1052.3	1003.1
22.5°	1577.6	1523.1	1470.1	1411.3	1344.0	1279.0	1207.2	1139.1	1079.3	1028.3	977.0
25°	1565.6	1507.3	1441.0	1381.6	1315.3	1246.3	1173.6	1103.0	1042.1	983.8	933.0
27.5°	1555.5	1479.9	1404.9	1335.6	1271.6	1208.4	1138.8	1066.5	998.9	939.8	892.0
30°	1543.1	1460.2	1375.7	1303.5	1237.8	1176.3	1110.6	1040.0	969.4	911.6	860.3
32.5°	1532.0	1435.4	1346.2	1267.7	1198.0	1138.2	1077.6	1010.4	941.1	882.6	831.2
35°	1510.5	1398.8	1296.6	1207.8	1133.5	1072.1	1021.3	958.7	895.1	838.4	789.2
37.5°	1483.2	1350.6	1241.0	1148.0	1066.5	1001.7	954.4	906.4	845.3	790.7	746.2
40°	1461.8	1316.4	1200.4	1105.2	1020.7	953.3	909.5	864.0	813.3	762.5	715.4
42.5°	1434.9	1285.6	1159.3	1056.9	973.2	907.6	861.6	823.0	778.2	730.8	687.1
45°	1385.4	1229.8	1092.9	982.8	898.3	833.5	786.0	757.1	723.4	678.5	641.6
47.5°	1312.6	1162.7	1021.1	907.4	820.3	760.3	715.7	688.0	664.3	630.9	597.5
50°	1247.9	1112.7	969.4	856.6	769.4	709.0	667.8	642.7	622.3	596.7	568.4
52.5°	1175.7	1049.8	918.5	806.9	720.6	661.1	620.8	598.7	581.7	563.3	535.4
55°	1060.8	953.9	831.9	726.1	646.4	588.1	552.9	533.6	519.8	505.8	488.7
57.5°	934.3	850.6	742.7	645.9	572.5	519.5	486.6	467.9	457.0	449.9	439.8
60°	845.3	773.7	680.6	592.4	520.8	473.7	441.6	427.2	418.1	412.3	404.7
62.5°	762.8	703.9	617.7	537.3	474.6	430.1	401.5	387.5	378.7	375.9	369.7
65°	641.1	595.6	524.5	457.7	404.3	366.2	342.2	328.8	323.4	320.3	320.8
67.5°	521.2	493.5	436.4	379.4	336.8	304.9	285.7	275.4	272.7	268.4	268.3
70°	448.1	427.2	379.1	329.4	291.4	266.8	249.7	239.0	236.3	234.2	233.7
72.5°	383.5	365.2	323.4	283.6	249.5	227.9	213.7	207.3	203.0	201.7	201.6
75°	288.2	278.1	244.9	213.3	189.8	174.8	165.2	159.3	156.1	155.6	156.1
77.5°	204.9	196.0	174.9	152.6	137.8	126.4	118.3	116.2	112.6	112.7	112.2
80°	154.0	148.1	134.8	117.1	104.8	95.1	90.9	87.1	86.1	84.4	86.1
82.5°	111.6	105.4	96.3	85.0	74.9	69.1	64.8	63.6	63.0	62.3	62.6
85°	55.1	55.6	50.2	41.7	37.4	34.2	31.5	31.5	31.0	30.5	31.0
87.5°	20.9	19.7	17.8	16.2	13.8	12.2	11.4	11.7	10.6	10.5	11.2
90°	10.3	8.7	7.9	6.3	4.8	3.2	1.6	0.8	1.6	3.2	4.8
92.5°	180.5	108.1	64.9	41.7	28.1	18.4	11.7	9.7	11.7	18.4	28.1
95°	353.5	179.5	94.9	59.3	41.9	33.2	26.9	26.1	26.9	33.2	41.9
97.5°	282.2	154.7	98.7	73.0	57.4	48.7	44.3	43.3	44.3	48.7	57.4
100°	256.2	153.4	107.6	83.8	68.8	60.1	57.0	55.4	57.0	60.1	68.8
102.5°	245.5	159.1	118.3	95.2	81.4	72.1	69.6	68.7	69.6	72.1	81.4
105°	241.2	170.8	136.0	113.9	101.2	93.3	89.4	89.4	89.4	93.3	101.2
107.5°	248.5	188.2	154.6	134.6	121.4	114.9	111.2	109.6	111.2	114.9	121.4
110°	255.4	200.9	168.4	147.9	136.0	128.9	125.7	124.1	125.7	128.9	136.0



TEST NUMBER: P333279-927

CATALOG NUMBER: S125DIP-S1090D1035U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	264.3	212.9	181.7	161.8	150.0	142.8	140.3	138.7	140.3	142.8	150.0
115°	277.6	231.7	202.5	182.7	170.8	163.7	161.3	159.8	161.3	163.7	170.8
117.5°	292.8	251.0	223.3	204.2	190.8	183.6	181.1	178.7	181.1	183.6	190.8
120°	302.9	264.9	237.3	217.5	204.1	196.9	193.8	191.4	193.8	196.9	204.1
122.5°	314.3	278.2	250.6	230.8	216.0	208.9	206.4	204.7	206.4	208.9	216.0
125°	329.8	295.8	269.7	249.1	234.1	227.0	223.0	221.4	223.0	227.0	234.1
127.5°	344.0	312.7	287.6	267.0	251.0	242.0	236.9	234.6	236.9	242.0	251.0
130°	353.5	323.4	298.9	278.4	261.7	251.5	245.2	242.8	245.2	251.5	261.7
132.5°	361.7	333.6	309.0	288.5	271.2	259.7	252.1	249.1	252.1	259.7	271.2
135°	373.3	347.1	322.7	301.3	284.7	272.0	262.5	259.4	262.5	272.0	284.7
137.5°	381.8	356.8	334.5	312.5	296.3	283.6	274.7	272.4	274.7	283.6	296.3
140°	387.5	363.8	340.9	319.5	304.4	291.8	282.3	280.0	282.3	291.8	304.4
142.5°	390.6	368.2	346.5	326.5	312.0	299.4	290.6	288.8	290.6	299.4	312.0
145°	395.4	375.7	355.1	336.9	322.7	311.6	303.6	302.1	303.6	311.6	322.7
147.5°	398.2	380.4	362.3	346.3	334.1	323.8	317.0	316.0	317.0	323.8	334.1
150°	400.1	383.6	366.1	352.7	341.7	331.4	325.8	324.2	325.8	331.4	341.7
152.5°	401.4	386.7	370.6	358.4	347.9	339.0	334.1	333.1	334.1	339.0	347.9
155°	402.5	389.8	376.4	365.4	357.4	349.5	344.8	344.8	344.8	349.5	357.4
157.5°	403.3	392.5	381.0	372.6	365.7	358.9	355.1	355.2	355.1	358.9	365.7
160°	403.3	393.8	383.6	376.4	370.1	364.6	361.4	362.2	361.4	364.6	370.1
162.5°	402.7	395.1	386.1	380.2	375.2	370.3	367.1	367.9	367.1	370.3	375.2
165°	401.7	395.4	389.1	384.4	381.2	377.2	374.9	376.4	374.9	377.2	381.2
167.5°	399.8	395.4	390.1	387.2	385.0	382.8	381.4	382.1	381.4	382.8	385.0
170°	398.5	395.4	391.4	389.1	387.5	386.0	385.2	386.0	385.2	386.0	387.5
172.5°	397.3	394.7	391.4	390.3	389.4	387.9	387.1	388.5	387.1	387.9	389.4
175°	395.4	393.8	391.4	391.4	391.4	390.6	389.8	391.4	389.8	390.6	391.4
177.5°	393.5	392.8	391.6	391.6	392.2	391.6	391.6	392.8	391.6	391.6	392.2
180°	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2



TEST NUMBER: P333279-927

CATALOG NUMBER: S125DIP-S1090D1035U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7
2.5°	1237.9	1233.2	1229.3	1220.8	1216.1	1209.7	1204.5	1210.1	1204.1	1206.7	1202.8
5°	1199.3	1184.3	1173.6	1158.1	1144.8	1132.4	1123.4	1121.7	1117.5	1115.3	1108.9
7.5°	1152.9	1134.2	1115.8	1095.4	1078.3	1060.9	1049.8	1040.6	1034.5	1026.5	1021.0
10°	1125.5	1100.3	1079.0	1054.4	1033.0	1014.3	999.3	991.8	984.9	974.7	971.0
12.5°	1091.7	1065.7	1039.7	1013.4	992.8	971.9	959.1	947.8	942.9	931.5	930.3
15°	1051.2	1012.2	986.5	959.7	931.4	914.3	903.6	891.3	886.0	878.0	872.0
17.5°	1002.8	968.0	935.9	908.2	883.9	869.5	856.3	847.8	838.6	833.4	823.7
20°	967.8	934.6	902.5	873.1	854.4	837.8	827.1	819.1	809.5	806.8	797.3
22.5°	938.3	901.7	870.9	846.2	825.8	807.1	795.5	790.0	783.4	775.2	773.2
25°	890.3	852.3	826.1	801.5	783.3	766.2	758.2	751.2	744.8	738.9	736.8
27.5°	848.7	814.8	783.7	761.5	745.7	730.1	723.0	714.5	709.9	705.1	699.3
30°	819.7	784.9	757.6	736.3	719.1	705.3	697.8	691.9	687.6	683.3	680.1
32.5°	789.7	757.6	731.1	710.2	693.1	682.5	676.0	671.8	667.1	661.9	657.9
35°	750.2	714.9	689.2	671.1	657.7	649.7	642.1	638.4	633.0	633.0	628.8
37.5°	705.6	675.1	652.4	635.9	623.8	616.7	608.6	606.0	602.6	600.3	598.8
40°	679.1	650.7	629.3	612.8	599.9	594.1	587.6	583.4	581.2	578.5	577.4
42.5°	651.6	624.6	604.1	588.8	577.7	572.7	566.6	563.6	559.4	555.9	555.2
45°	610.1	583.8	565.1	552.9	543.2	537.3	533.6	527.2	525.1	520.8	520.2
47.5°	570.6	545.5	527.1	517.1	508.6	503.7	497.9	491.5	489.0	486.9	486.6
50°	541.1	518.1	501.0	491.4	483.4	476.4	470.6	466.3	464.6	464.6	465.7
52.5°	511.2	491.5	477.1	465.2	457.7	450.3	444.9	442.3	439.8	442.4	444.3
55°	467.3	447.5	436.8	425.6	418.1	409.6	406.9	405.8	404.3	408.5	410.7
57.5°	420.9	407.0	394.5	383.3	376.6	371.7	368.0	367.4	370.4	372.5	379.4
60°	391.4	375.3	364.1	355.5	347.5	344.4	343.3	342.2	344.4	350.2	359.3
62.5°	358.9	345.9	333.7	327.3	321.5	316.1	315.9	316.6	320.8	327.6	336.6
65°	311.2	299.9	291.9	284.5	279.6	276.4	277.5	279.6	284.5	293.5	303.7
67.5°	262.8	255.1	247.9	241.8	237.2	237.2	238.3	241.5	247.2	257.6	266.9
70°	231.6	223.0	217.1	214.4	210.6	208.5	211.8	217.1	221.9	231.6	239.6
72.5°	200.3	193.1	188.5	186.6	185.0	183.3	184.3	190.1	196.6	206.3	215.6
75°	154.0	151.3	148.1	146.0	144.3	145.4	146.5	151.9	157.2	167.4	178.1
77.5°	112.4	109.6	107.7	107.2	106.3	106.9	109.8	113.8	119.0	126.4	134.5
80°	85.0	84.0	82.9	82.3	82.3	82.9	87.1	89.8	94.7	101.6	108.0
82.5°	61.9	61.2	61.1	60.9	61.4	61.5	64.1	67.6	71.5	76.8	82.3
85°	32.6	31.5	33.1	33.7	32.6	34.2	35.3	37.4	39.1	41.7	44.4
87.5°	12.0	13.2	12.8	13.6	13.8	15.0	14.7	16.6	17.6	18.5	18.5
90°	6.3	7.9	8.7	10.3	11.1	12.7	13.5	14.3	15.1	15.8	17.4
92.5°	41.7	64.9	108.1	180.5	259.0	254.9	206.4	140.1	101.7	76.5	64.9
95°	59.3	94.9	179.5	353.5	571.8	700.7	685.6	568.6	448.4	351.1	284.7
97.5°	73.0	98.7	154.7	282.2	510.6	748.3	867.5	846.8	762.5	667.7	575.4
100°	83.8	107.6	153.4	256.2	455.5	714.1	911.8	972.7	934.0	852.5	770.2
102.5°	95.2	118.3	159.1	245.5	413.8	654.0	885.3	1015.1	1038.9	999.9	944.2
105°	113.9	136.0	170.8	241.2	373.3	573.3	800.3	990.1	1098.4	1133.2	1124.5
107.5°	134.6	154.6	188.2	248.5	356.2	517.8	713.6	900.9	1045.4	1134.8	1176.1
110°	147.9	168.4	200.9	255.4	351.1	491.9	664.2	835.1	985.3	1096.9	1164.1



TEST NUMBER: P333279-927

CATALOG NUMBER: S125DIP-S1090D1035U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	161.8	181.7	212.9	264.3	351.1	476.7	627.6	783.2	925.9	1038.6	1117.9
115°	182.7	202.5	231.7	277.6	353.5	460.3	587.6	718.0	840.7	949.0	1035.1
117.5°	204.2	223.3	251.0	292.8	358.7	452.2	563.7	676.0	781.6	875.0	954.0
120°	217.5	237.3	264.9	302.9	363.8	448.4	550.4	653.2	748.1	835.1	904.7
122.5°	230.8	250.6	278.2	314.3	368.2	445.2	539.0	636.1	724.1	801.5	866.7
125°	249.1	269.7	295.8	329.8	375.7	441.2	523.6	611.3	692.0	760.7	817.7
127.5°	267.0	287.6	312.7	344.0	384.0	439.3	509.3	586.0	661.3	725.5	778.8
130°	278.4	298.9	323.4	353.5	389.1	438.1	499.8	570.2	639.8	701.5	752.9
132.5°	288.5	309.0	333.6	361.7	394.7	438.1	492.2	554.4	619.5	675.5	725.0
135°	301.3	322.7	347.1	373.3	402.5	438.1	483.2	533.8	588.4	639.0	684.0
137.5°	312.5	334.5	356.8	381.8	409.6	439.0	475.2	516.4	560.5	602.6	640.9
140°	319.5	340.9	363.8	387.5	412.8	439.7	471.3	506.9	544.1	580.4	613.7
142.5°	326.5	346.5	368.2	390.6	414.7	440.3	468.2	498.7	530.1	561.5	590.3
145°	336.9	355.1	375.7	395.4	416.8	439.7	463.4	487.9	512.5	536.9	558.3
147.5°	346.3	362.3	380.4	398.2	417.6	437.6	458.5	477.8	497.7	516.6	532.7
150°	352.7	366.1	383.6	400.1	417.6	435.7	454.7	472.1	489.5	504.5	518.8
152.5°	358.4	370.6	386.7	401.4	416.9	433.2	450.3	465.8	481.3	495.0	506.1
155°	365.4	376.4	389.8	402.5	415.2	428.6	442.8	456.3	469.0	480.1	488.7
157.5°	372.6	381.0	392.5	403.3	413.1	423.9	435.9	446.8	457.2	465.8	472.6
160°	376.4	383.6	393.8	403.3	411.2	420.7	430.2	440.5	448.4	456.3	461.8
162.5°	380.2	386.1	395.1	402.7	409.3	416.9	425.2	433.6	440.8	447.4	452.3
165°	384.4	389.1	395.4	401.7	406.5	411.2	417.6	423.9	429.4	434.2	438.1
167.5°	387.2	390.1	395.4	399.8	402.0	405.7	410.1	414.7	418.4	422.0	424.8
170°	389.1	391.4	395.4	398.5	400.1	402.5	405.7	409.6	412.0	414.4	416.0
172.5°	390.3	391.4	394.7	397.3	397.6	398.7	401.2	403.9	406.3	408.1	409.0
175°	391.4	391.4	393.8	395.4	394.6	394.6	395.4	397.8	397.8	399.3	399.3
177.5°	391.6	391.6	392.8	393.5	392.2	392.2	392.8	393.5	394.1	394.1	394.1
180°	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2



TEST NUMBER: P333279-927

CATALOG NUMBER: S125DIP-S1090D1035U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7
2.5°	1200.2	1203.2	1200.7	1204.1	1200.7	1203.2	1200.2	1202.8	1206.7	1204.1	1210.1
5°	1106.3	1101.5	1104.6	1102.5	1104.6	1101.5	1106.3	1108.9	1115.3	1117.5	1121.7
7.5°	1019.5	1014.9	1009.6	1007.1	1009.6	1014.9	1019.5	1021.0	1026.5	1034.5	1040.6
10°	965.1	959.3	958.7	955.0	958.7	959.3	965.1	971.0	974.7	984.9	991.8
12.5°	925.3	919.9	913.8	912.2	913.8	919.9	925.3	930.3	931.5	942.9	947.8
15°	868.9	864.6	860.9	864.0	860.9	864.6	868.9	872.0	878.0	886.0	891.3
17.5°	821.9	818.4	817.8	813.8	817.8	818.4	821.9	823.7	833.4	838.6	847.8
20°	792.4	789.7	790.8	783.9	790.8	789.7	792.4	797.3	806.8	809.5	819.1
22.5°	768.9	763.7	763.0	761.6	763.0	763.7	768.9	773.2	775.2	783.4	790.0
25°	732.0	729.3	726.7	729.3	726.7	729.3	732.0	736.8	738.9	744.8	751.2
27.5°	699.8	696.6	695.9	696.2	695.9	696.6	699.8	699.3	705.1	709.9	714.5
30°	680.1	674.8	675.3	674.8	675.3	674.8	680.1	680.1	683.3	687.6	691.9
32.5°	658.7	655.1	654.3	653.4	654.3	655.1	658.7	657.9	661.9	667.1	671.8
35°	627.2	627.2	624.5	624.5	624.5	627.2	627.2	628.8	633.0	633.0	638.4
37.5°	597.5	597.0	595.4	595.6	595.4	597.0	597.5	598.8	600.3	602.6	606.0
40°	575.3	574.8	573.1	570.0	573.1	574.8	575.3	577.4	578.5	581.2	583.4
42.5°	553.9	552.2	551.4	550.3	551.4	552.2	553.9	555.2	555.9	559.4	563.6
45°	520.2	520.2	519.2	518.6	519.2	520.2	520.2	520.2	520.8	525.1	527.2
47.5°	487.5	488.5	490.5	490.2	490.5	488.5	487.5	486.6	486.9	489.0	491.5
50°	467.9	468.4	470.0	470.6	470.0	468.4	467.9	465.7	464.6	464.6	466.3
52.5°	446.0	449.2	451.1	450.8	451.1	449.2	446.0	444.3	442.4	439.8	442.3
55°	415.4	419.2	422.9	423.5	422.9	419.2	415.4	410.7	408.5	404.3	405.8
57.5°	385.2	390.4	394.3	395.7	394.3	390.4	385.2	379.4	372.5	370.4	367.4
60°	364.6	371.6	376.4	378.6	376.4	371.6	364.6	359.3	350.2	344.4	342.2
62.5°	345.0	352.8	357.6	358.0	357.6	352.8	345.0	336.6	327.6	320.8	316.6
65°	312.8	320.8	325.1	328.3	325.1	320.8	312.8	303.7	293.5	284.5	279.6
67.5°	278.1	286.1	290.9	293.4	290.9	286.1	278.1	266.9	257.6	247.2	241.5
70°	252.9	260.9	267.4	269.5	267.4	260.9	252.9	239.6	231.6	221.9	217.1
72.5°	228.1	235.3	240.4	243.0	240.4	235.3	228.1	215.6	206.3	196.6	190.1
75°	185.0	194.6	199.5	202.1	199.5	194.6	185.0	178.1	167.4	157.2	151.9
77.5°	142.7	151.4	154.3	155.7	154.3	151.4	142.7	134.5	126.4	119.0	113.8
80°	114.4	119.8	123.5	124.1	123.5	119.8	114.4	108.0	101.6	94.7	89.8
82.5°	87.9	92.4	93.6	95.0	93.6	92.4	87.9	82.3	76.8	71.5	67.6
85°	48.1	50.2	50.8	50.2	50.8	50.2	48.1	44.4	41.7	39.1	37.4
87.5°	19.3	18.9	19.0	19.9	19.0	18.9	19.3	18.5	18.5	17.6	16.6
90°	17.4	17.4	18.2	18.2	18.2	17.4	17.4	17.4	15.8	15.1	14.3
92.5°	54.7	52.8	51.7	50.5	51.7	52.8	54.7	64.9	76.5	101.7	140.1
95°	228.5	204.9	198.5	185.8	198.5	204.9	228.5	284.7	351.1	448.4	568.6
97.5°	526.6	482.2	459.3	449.2	459.3	482.2	526.6	575.4	667.7	762.5	846.8
100°	715.7	658.8	629.5	616.9	629.5	658.8	715.7	770.2	852.5	934.0	972.7
102.5°	885.9	845.4	813.6	804.1	813.6	845.4	885.9	944.2	999.9	1038.9	1015.1
105°	1099.2	1073.2	1057.3	1047.8	1057.3	1073.2	1099.2	1124.5	1133.2	1098.4	990.1
107.5°	1188.9	1188.7	1183.5	1177.2	1183.5	1188.7	1188.9	1176.1	1134.8	1045.4	900.9
110°	1199.7	1214.7	1220.2	1220.2	1220.2	1214.7	1199.7	1164.1	1096.9	985.3	835.1



TEST NUMBER: P333279-927

CATALOG NUMBER: S125DIP-S1090D1035U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1169.9	1195.7	1209.5	1215.1	1209.5	1195.7	1169.9	1117.9	1038.6	925.9	783.2
115°	1096.9	1134.8	1157.0	1167.3	1157.0	1134.8	1096.9	1035.1	949.0	840.7	718.0
117.5°	1015.7	1054.9	1076.9	1083.2	1076.9	1054.9	1015.7	954.0	875.0	781.6	676.0
120°	963.2	1001.2	1022.5	1028.9	1022.5	1001.2	963.2	904.7	835.1	748.1	653.2
122.5°	918.9	953.7	975.1	980.8	975.1	953.7	918.9	866.7	801.5	724.1	636.1
125°	862.0	894.4	911.8	919.7	911.8	894.4	862.0	817.7	760.7	692.0	611.3
127.5°	819.0	847.6	864.0	867.5	864.0	847.6	819.0	778.8	725.5	661.3	586.0
130°	792.4	818.5	834.3	839.1	834.3	818.5	792.4	752.9	701.5	639.8	570.2
132.5°	764.5	790.7	805.2	810.6	805.2	790.7	764.5	725.0	675.5	619.5	554.4
135°	718.8	745.0	759.1	763.9	759.1	745.0	718.8	684.0	639.0	588.4	533.8
137.5°	672.0	695.8	708.9	714.1	708.9	695.8	672.0	640.9	602.6	560.5	516.4
140°	642.9	663.5	675.3	679.3	675.3	663.5	642.9	613.7	580.4	544.1	506.9
142.5°	615.1	632.5	643.7	647.1	643.7	632.5	615.1	590.3	561.5	530.1	498.7
145°	577.3	590.7	599.4	602.6	599.4	590.7	577.3	558.3	536.9	512.5	487.9
147.5°	547.7	558.5	563.6	565.0	563.6	558.5	547.7	532.7	516.6	497.7	477.8
150°	530.6	540.1	543.3	544.1	543.3	540.1	530.6	518.8	504.5	489.5	472.1
152.5°	516.1	523.7	526.8	527.6	526.8	523.7	516.1	506.1	495.0	481.3	465.8
155°	496.6	502.2	504.5	505.3	504.5	502.2	496.6	488.7	480.1	469.0	456.3
157.5°	478.8	483.3	485.5	485.4	485.5	483.3	478.8	472.6	465.8	457.2	446.8
160°	467.4	471.3	472.9	472.1	472.9	471.3	467.4	461.8	456.3	448.4	440.5
162.5°	456.6	459.9	460.3	460.1	460.3	459.9	456.6	452.3	447.4	440.8	433.6
165°	441.2	442.8	442.8	442.8	442.8	442.8	441.2	438.1	434.2	429.4	423.9
167.5°	426.4	427.9	427.2	427.1	427.2	427.9	426.4	424.8	422.0	418.4	414.7
170°	417.6	418.4	418.4	417.6	418.4	418.4	417.6	416.0	414.4	412.0	409.6
172.5°	409.3	410.7	409.5	408.7	409.5	410.7	409.3	409.0	408.1	406.3	403.9
175°	399.3	400.1	398.5	397.8	398.5	400.1	399.3	399.3	399.3	397.8	397.8
177.5°	393.5	394.1	392.2	392.2	392.2	394.1	393.5	394.1	394.1	394.1	393.5
180°	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2



TEST NUMBER: P333279-927

CATALOG NUMBER: S125DIP-S1090D1035U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7
2.5°	1204.5	1209.7	1216.1	1220.8	1229.3	1233.2	1237.9	1241.7	1248.6	1255.0	1262.7
5°	1123.4	1132.4	1144.8	1158.1	1173.6	1184.3	1199.3	1208.4	1226.5	1243.2	1259.2
7.5°	1049.8	1060.9	1078.3	1095.4	1115.8	1134.2	1152.9	1173.6	1196.8	1224.2	1246.9
10°	999.3	1014.3	1033.0	1054.4	1079.0	1100.3	1125.5	1148.0	1176.3	1208.4	1238.3
12.5°	959.1	971.9	992.8	1013.4	1039.7	1065.7	1091.7	1121.4	1154.5	1190.0	1227.6
15°	903.6	914.3	931.4	959.7	986.5	1012.2	1051.2	1079.0	1120.7	1160.2	1205.7
17.5°	856.3	869.5	883.9	908.2	935.9	968.0	1002.8	1037.7	1077.9	1128.1	1179.3
20°	827.1	837.8	854.4	873.1	902.5	934.6	967.8	1003.1	1052.3	1104.1	1159.2
22.5°	795.5	807.1	825.8	846.2	870.9	901.7	938.3	977.0	1028.3	1079.3	1139.1
25°	758.2	766.2	783.3	801.5	826.1	852.3	890.3	933.0	983.8	1042.1	1103.0
27.5°	723.0	730.1	745.7	761.5	783.7	814.8	848.7	892.0	939.8	998.9	1066.5
30°	697.8	705.3	719.1	736.3	757.6	784.9	819.7	860.3	911.6	969.4	1040.0
32.5°	676.0	682.5	693.1	710.2	731.1	757.6	789.7	831.2	882.6	941.1	1010.4
35°	642.1	649.7	657.7	671.1	689.2	714.9	750.2	789.2	838.4	895.1	958.7
37.5°	608.6	616.7	623.8	635.9	652.4	675.1	705.6	746.2	790.7	845.3	906.4
40°	587.6	594.1	599.9	612.8	629.3	650.7	679.1	715.4	762.5	813.3	864.0
42.5°	566.6	572.7	577.7	588.8	604.1	624.6	651.6	687.1	730.8	778.2	823.0
45°	533.6	537.3	543.2	552.9	565.1	583.8	610.1	641.6	678.5	723.4	757.1
47.5°	497.9	503.7	508.6	517.1	527.1	545.5	570.6	597.5	630.9	664.3	688.0
50°	470.6	476.4	483.4	491.4	501.0	518.1	541.1	568.4	596.7	622.3	642.7
52.5°	444.9	450.3	457.7	465.2	477.1	491.5	511.2	535.4	563.3	581.7	598.7
55°	406.9	409.6	418.1	425.6	436.8	447.5	467.3	488.7	505.8	519.8	533.6
57.5°	368.0	371.7	376.6	383.3	394.5	407.0	420.9	439.8	449.9	457.0	467.9
60°	343.3	344.4	347.5	355.5	364.1	375.3	391.4	404.7	412.3	418.1	427.2
62.5°	315.9	316.1	321.5	327.3	333.7	345.9	358.9	369.7	375.9	378.7	387.5
65°	277.5	276.4	279.6	284.5	291.9	299.9	311.2	320.8	320.3	323.4	328.8
67.5°	238.3	237.2	237.2	241.8	247.9	255.1	262.8	268.3	268.4	272.7	275.4
70°	211.8	208.5	210.6	214.4	217.1	223.0	231.6	233.7	234.2	236.3	239.0
72.5°	184.3	183.3	185.0	186.6	188.5	193.1	200.3	201.6	201.7	203.0	207.3
75°	146.5	145.4	144.3	146.0	148.1	151.3	154.0	156.1	155.6	156.1	159.3
77.5°	109.8	106.9	106.3	107.2	107.7	109.6	112.4	112.2	112.7	112.6	116.2
80°	87.1	82.9	82.3	82.3	82.9	84.0	85.0	86.1	84.4	86.1	87.1
82.5°	64.1	61.5	61.4	60.9	61.1	61.2	61.9	62.6	62.3	63.0	63.6
85°	35.3	34.2	32.6	33.7	33.1	31.5	32.6	31.0	30.5	31.0	31.5
87.5°	14.7	15.0	13.8	13.6	12.8	13.2	12.0	11.2	10.5	10.6	11.7
90°	13.5	12.7	11.1	10.3	8.7	7.9	6.3	4.8	3.2	1.6	0.8
92.5°	206.4	254.9	259.0	180.5	108.1	64.9	41.7	28.1	18.4	11.7	9.7
95°	685.6	700.7	571.8	353.5	179.5	94.9	59.3	41.9	33.2	26.9	26.1
97.5°	867.5	748.3	510.6	282.2	154.7	98.7	73.0	57.4	48.7	44.3	43.3
100°	911.8	714.1	455.5	256.2	153.4	107.6	83.8	68.8	60.1	57.0	55.4
102.5°	885.3	654.0	413.8	245.5	159.1	118.3	95.2	81.4	72.1	69.6	68.7
105°	800.3	573.3	373.3	241.2	170.8	136.0	113.9	101.2	93.3	89.4	89.4
107.5°	713.6	517.8	356.2	248.5	188.2	154.6	134.6	121.4	114.9	111.2	109.6
110°	664.2	491.9	351.1	255.4	200.9	168.4	147.9	136.0	128.9	125.7	124.1



TEST NUMBER: P333279-927

CATALOG NUMBER: S125DIP-S1090D1035U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	627.6	476.7	351.1	264.3	212.9	181.7	161.8	150.0	142.8	140.3	138.7
115°	587.6	460.3	353.5	277.6	231.7	202.5	182.7	170.8	163.7	161.3	159.8
117.5°	563.7	452.2	358.7	292.8	251.0	223.3	204.2	190.8	183.6	181.1	178.7
120°	550.4	448.4	363.8	302.9	264.9	237.3	217.5	204.1	196.9	193.8	191.4
122.5°	539.0	445.2	368.2	314.3	278.2	250.6	230.8	216.0	208.9	206.4	204.7
125°	523.6	441.2	375.7	329.8	295.8	269.7	249.1	234.1	227.0	223.0	221.4
127.5°	509.3	439.3	384.0	344.0	312.7	287.6	267.0	251.0	242.0	236.9	234.6
130°	499.8	438.1	389.1	353.5	323.4	298.9	278.4	261.7	251.5	245.2	242.8
132.5°	492.2	438.1	394.7	361.7	333.6	309.0	288.5	271.2	259.7	252.1	249.1
135°	483.2	438.1	402.5	373.3	347.1	322.7	301.3	284.7	272.0	262.5	259.4
137.5°	475.2	439.0	409.6	381.8	356.8	334.5	312.5	296.3	283.6	274.7	272.4
140°	471.3	439.7	412.8	387.5	363.8	340.9	319.5	304.4	291.8	282.3	280.0
142.5°	468.2	440.3	414.7	390.6	368.2	346.5	326.5	312.0	299.4	290.6	288.8
145°	463.4	439.7	416.8	395.4	375.7	355.1	336.9	322.7	311.6	303.6	302.1
147.5°	458.5	437.6	417.6	398.2	380.4	362.3	346.3	334.1	323.8	317.0	316.0
150°	454.7	435.7	417.6	400.1	383.6	366.1	352.7	341.7	331.4	325.8	324.2
152.5°	450.3	433.2	416.9	401.4	386.7	370.6	358.4	347.9	339.0	334.1	333.1
155°	442.8	428.6	415.2	402.5	389.8	376.4	365.4	357.4	349.5	344.8	344.8
157.5°	435.9	423.9	413.1	403.3	392.5	381.0	372.6	365.7	358.9	355.1	355.2
160°	430.2	420.7	411.2	403.3	393.8	383.6	376.4	370.1	364.6	361.4	362.2
162.5°	425.2	416.9	409.3	402.7	395.1	386.1	380.2	375.2	370.3	367.1	367.9
165°	417.6	411.2	406.5	401.7	395.4	389.1	384.4	381.2	377.2	374.9	376.4
167.5°	410.1	405.7	402.0	399.8	395.4	390.1	387.2	385.0	382.8	381.4	382.1
170°	405.7	402.5	400.1	398.5	395.4	391.4	389.1	387.5	386.0	385.2	386.0
172.5°	401.2	398.7	397.6	397.3	394.7	391.4	390.3	389.4	387.9	387.1	388.5
175°	395.4	394.6	394.6	395.4	393.8	391.4	391.4	391.4	390.6	389.8	391.4
177.5°	392.8	392.2	392.2	393.5	392.8	391.6	391.6	392.2	391.6	391.6	392.8
180°	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2



TEST NUMBER: P333279-927

CATALOG NUMBER: S125DIP-S1090D1035U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7
2.5°	1266.5	1272.6	1276.4	1283.7	1289.7	1293.1	1296.1	1298.6	1301.6	1304.2	1311.5
5°	1274.7	1288.6	1300.4	1318.5	1335.1	1348.0	1361.8	1374.1	1384.3	1398.8	1409.9
7.5°	1271.1	1295.9	1321.8	1349.9	1378.6	1405.3	1430.0	1452.9	1473.8	1499.0	1521.1
10°	1267.7	1301.4	1334.6	1372.5	1411.6	1444.7	1475.8	1507.3	1530.3	1562.3	1589.6
12.5°	1265.2	1304.8	1344.8	1390.5	1433.4	1480.2	1521.5	1544.5	1579.5	1605.1	1637.5
15°	1254.3	1306.8	1361.8	1413.2	1474.1	1517.4	1553.8	1598.7	1631.3	1663.9	1699.2
17.5°	1235.0	1294.3	1356.0	1423.2	1481.7	1528.2	1575.1	1618.3	1657.3	1701.1	1745.0
20°	1226.1	1285.4	1356.0	1424.9	1482.2	1530.8	1578.9	1626.5	1669.3	1725.5	1776.2
22.5°	1207.2	1279.0	1344.0	1411.3	1470.1	1523.1	1577.6	1631.7	1688.5	1751.9	1815.6
25°	1173.6	1246.3	1315.3	1381.6	1441.0	1507.3	1565.6	1637.8	1710.5	1794.4	1873.5
27.5°	1138.8	1208.4	1271.6	1335.6	1404.9	1479.9	1555.5	1637.4	1732.6	1838.6	1950.2
30°	1110.6	1176.3	1237.8	1303.5	1375.7	1460.2	1543.1	1640.4	1750.6	1869.8	2002.4
32.5°	1077.6	1138.2	1198.0	1267.7	1346.2	1435.4	1532.0	1638.7	1771.1	1906.5	2043.0
35°	1021.3	1072.1	1133.5	1207.8	1296.6	1398.8	1510.5	1636.6	1788.5	1944.1	2059.0
37.5°	954.4	1001.7	1066.5	1148.0	1241.0	1350.6	1483.2	1632.9	1794.2	1918.3	1955.3
40°	909.5	953.3	1020.7	1105.2	1200.4	1316.4	1461.8	1620.1	1776.2	1855.4	1824.9
42.5°	861.6	907.6	973.2	1056.9	1159.3	1285.6	1434.9	1593.2	1724.0	1754.0	1648.6
45°	786.0	833.5	898.3	982.8	1092.9	1229.8	1385.4	1529.2	1604.6	1550.6	1387.5
47.5°	715.7	760.3	820.3	907.4	1021.1	1162.7	1312.6	1427.3	1433.3	1304.4	1130.2
50°	667.8	709.0	769.4	856.6	969.4	1112.7	1247.9	1338.3	1297.7	1151.7	984.4
52.5°	620.8	661.1	720.6	806.9	918.5	1049.8	1175.7	1239.1	1162.5	1012.7	869.7
55°	552.9	588.1	646.4	726.1	831.9	953.9	1060.8	1082.8	983.3	835.7	719.7
57.5°	486.6	519.5	572.5	645.9	742.7	850.6	934.3	929.6	824.5	697.8	605.8
60°	441.6	473.7	520.8	592.4	680.6	773.7	845.3	828.2	724.0	614.9	537.3
62.5°	401.5	430.1	474.6	537.3	617.7	703.9	762.8	737.5	635.4	540.0	478.8
65°	342.2	366.2	404.3	457.7	524.5	595.6	641.1	608.5	521.3	447.0	397.8
67.5°	285.7	304.9	336.8	379.4	436.4	493.5	521.2	488.4	418.7	364.4	328.0
70°	249.7	266.8	291.4	329.4	379.1	427.2	448.1	418.7	358.8	312.3	286.1
72.5°	213.7	227.9	249.5	283.6	323.4	365.2	383.5	355.4	306.2	266.9	242.4
75°	165.2	174.8	189.8	213.3	244.9	278.1	288.2	263.6	232.0	202.6	186.6
77.5°	118.3	126.4	137.8	152.6	174.9	196.0	204.9	190.7	166.3	147.7	134.5
80°	90.9	95.1	104.8	117.1	134.8	148.1	154.0	144.9	127.8	113.9	103.7
82.5°	64.8	69.1	74.9	85.0	96.3	105.4	111.6	105.5	93.2	82.2	76.4
85°	31.5	34.2	37.4	41.7	50.2	55.6	55.1	51.3	46.5	42.2	39.1
87.5°	11.4	12.2	13.8	16.2	17.8	19.7	20.9	20.2	18.8	17.7	16.6
90°	1.6	3.2	4.8	6.3	7.9	8.7	10.3	11.1	12.7	13.5	14.3
92.5°	11.7	18.4	28.1	41.7	64.9	108.1	180.5	259.0	254.9	206.4	140.1
95°	26.9	33.2	41.9	59.3	94.9	179.5	353.5	571.8	700.7	685.6	568.6
97.5°	44.3	48.7	57.4	73.0	98.7	154.7	282.2	510.6	748.3	867.5	846.8
100°	57.0	60.1	68.8	83.8	107.6	153.4	256.2	455.5	714.1	911.8	972.7
102.5°	69.6	72.1	81.4	95.2	118.3	159.1	245.5	413.8	654.0	885.3	1015.1
105°	89.4	93.3	101.2	113.9	136.0	170.8	241.2	373.3	573.3	800.3	990.1
107.5°	111.2	114.9	121.4	134.6	154.6	188.2	248.5	356.2	517.8	713.6	900.9
110°	125.7	128.9	136.0	147.9	168.4	200.9	255.4	351.1	491.9	664.2	835.1



TEST NUMBER: P333279-927

CATALOG NUMBER: S125DIP-S1090D1035U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	140.3	142.8	150.0	161.8	181.7	212.9	264.3	351.1	476.7	627.6	783.2
115°	161.3	163.7	170.8	182.7	202.5	231.7	277.6	353.5	460.3	587.6	718.0
117.5°	181.1	183.6	190.8	204.2	223.3	251.0	292.8	358.7	452.2	563.7	676.0
120°	193.8	196.9	204.1	217.5	237.3	264.9	302.9	363.8	448.4	550.4	653.2
122.5°	206.4	208.9	216.0	230.8	250.6	278.2	314.3	368.2	445.2	539.0	636.1
125°	223.0	227.0	234.1	249.1	269.7	295.8	329.8	375.7	441.2	523.6	611.3
127.5°	236.9	242.0	251.0	267.0	287.6	312.7	344.0	384.0	439.3	509.3	586.0
130°	245.2	251.5	261.7	278.4	298.9	323.4	353.5	389.1	438.1	499.8	570.2
132.5°	252.1	259.7	271.2	288.5	309.0	333.6	361.7	394.7	438.1	492.2	554.4
135°	262.5	272.0	284.7	301.3	322.7	347.1	373.3	402.5	438.1	483.2	533.8
137.5°	274.7	283.6	296.3	312.5	334.5	356.8	381.8	409.6	439.0	475.2	516.4
140°	282.3	291.8	304.4	319.5	340.9	363.8	387.5	412.8	439.7	471.3	506.9
142.5°	290.6	299.4	312.0	326.5	346.5	368.2	390.6	414.7	440.3	468.2	498.7
145°	303.6	311.6	322.7	336.9	355.1	375.7	395.4	416.8	439.7	463.4	487.9
147.5°	317.0	323.8	334.1	346.3	362.3	380.4	398.2	417.6	437.6	458.5	477.8
150°	325.8	331.4	341.7	352.7	366.1	383.6	400.1	417.6	435.7	454.7	472.1
152.5°	334.1	339.0	347.9	358.4	370.6	386.7	401.4	416.9	433.2	450.3	465.8
155°	344.8	349.5	357.4	365.4	376.4	389.8	402.5	415.2	428.6	442.8	456.3
157.5°	355.1	358.9	365.7	372.6	381.0	392.5	403.3	413.1	423.9	435.9	446.8
160°	361.4	364.6	370.1	376.4	383.6	393.8	403.3	411.2	420.7	430.2	440.5
162.5°	367.1	370.3	375.2	380.2	386.1	395.1	402.7	409.3	416.9	425.2	433.6
165°	374.9	377.2	381.2	384.4	389.1	395.4	401.7	406.5	411.2	417.6	423.9
167.5°	381.4	382.8	385.0	387.2	390.1	395.4	399.8	402.0	405.7	410.1	414.7
170°	385.2	386.0	387.5	389.1	391.4	395.4	398.5	400.1	402.5	405.7	409.6
172.5°	387.1	387.9	389.4	390.3	391.4	394.7	397.3	397.6	398.7	401.2	403.9
175°	389.8	390.6	391.4	391.4	391.4	393.8	395.4	394.6	394.6	395.4	397.8
177.5°	391.6	391.6	392.2	391.6	391.6	392.8	393.5	392.2	392.2	392.8	393.5
180°	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2



TEST NUMBER: P333279-927

CATALOG NUMBER: S125DIP-S1090D1035U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7
2.5°	1317.5	1320.9	1328.2	1325.6	1329.0	1330.7	1332.5
5°	1423.9	1441.0	1448.4	1447.4	1458.6	1456.0	1453.3
7.5°	1544.0	1562.0	1572.1	1584.6	1591.9	1592.4	1598.7
10°	1612.1	1635.6	1645.2	1658.6	1667.1	1672.0	1671.4
12.5°	1664.3	1682.7	1704.2	1710.8	1722.4	1728.4	1726.2
15°	1727.0	1756.4	1778.9	1790.1	1804.6	1808.9	1814.7
17.5°	1783.0	1822.5	1848.7	1883.6	1896.7	1904.7	1900.0
20°	1825.4	1877.3	1903.5	1945.2	1968.2	1980.5	1976.2
22.5°	1875.5	1931.6	1980.1	2016.2	2051.1	2067.8	2071.2
25°	1961.2	2038.2	2109.3	2157.0	2200.2	2210.3	2232.8
27.5°	2057.1	2147.8	2223.9	2273.9	2304.1	2315.4	2322.4
30°	2117.3	2207.7	2264.9	2297.0	2306.6	2305.6	2304.5
32.5°	2146.9	2203.5	2214.5	2205.4	2183.4	2164.8	2145.4
35°	2105.1	2062.8	1999.7	1918.4	1858.5	1798.2	1792.2
37.5°	1893.2	1758.2	1653.1	1535.8	1468.2	1426.3	1397.5
40°	1693.8	1540.4	1413.2	1314.2	1245.3	1218.0	1191.3
42.5°	1477.4	1330.9	1218.1	1135.4	1083.6	1053.4	1032.1
45°	1200.4	1071.0	982.8	922.9	881.7	858.2	844.8
47.5°	983.6	887.9	812.9	769.8	741.3	723.0	723.1
50°	867.3	775.9	726.1	691.9	667.3	652.8	655.5
52.5°	764.1	695.9	653.4	624.7	606.6	597.7	597.4
55°	639.0	589.8	562.0	541.1	528.8	518.6	520.8
57.5°	546.5	505.1	486.5	469.1	460.6	456.5	450.6
60°	489.3	457.2	441.1	427.2	418.7	415.4	409.6
62.5°	438.3	413.1	397.5	386.1	378.4	377.4	372.8
65°	368.4	349.1	335.3	329.9	321.9	319.7	319.7
67.5°	303.7	289.9	279.1	274.2	270.7	271.2	268.6
70°	263.1	251.8	244.9	239.6	236.9	237.4	235.3
72.5°	230.1	217.6	211.5	208.3	204.8	206.2	205.3
75°	174.3	167.9	164.7	161.4	159.3	158.3	157.2
77.5°	128.0	122.3	119.9	118.0	118.4	115.8	117.9
80°	98.9	94.1	92.5	89.8	89.3	89.3	88.7
82.5°	72.4	69.7	68.5	66.3	65.4	66.2	64.8
85°	37.4	35.3	34.8	34.8	33.7	32.6	35.3
87.5°	16.7	15.1	15.4	15.1	15.1	14.7	13.9
90°	15.1	15.8	17.4	17.4	17.4	18.2	18.2
92.5°	101.7	76.5	64.9	54.7	52.8	51.7	50.5
95°	448.4	351.1	284.7	228.5	204.9	198.5	185.8
97.5°	762.5	667.7	575.4	526.6	482.2	459.3	449.2
100°	934.0	852.5	770.2	715.7	658.8	629.5	616.9
102.5°	1038.9	999.9	944.2	885.9	845.4	813.6	804.1
105°	1098.4	1133.2	1124.5	1099.2	1073.2	1057.3	1047.8
107.5°	1045.4	1134.8	1176.1	1188.9	1188.7	1183.5	1177.2
110°	985.3	1096.9	1164.1	1199.7	1214.7	1220.2	1220.2



TEST NUMBER: P333279-927

CATALOG NUMBER: S125DIP-S1090D1035U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	925.9	1038.6	1117.9	1169.9	1195.7	1209.5	1215.1
115°	840.7	949.0	1035.1	1096.9	1134.8	1157.0	1167.3
117.5°	781.6	875.0	954.0	1015.7	1054.9	1076.9	1083.2
120°	748.1	835.1	904.7	963.2	1001.2	1022.5	1028.9
122.5°	724.1	801.5	866.7	918.9	953.7	975.1	980.8
125°	692.0	760.7	817.7	862.0	894.4	911.8	919.7
127.5°	661.3	725.5	778.8	819.0	847.6	864.0	867.5
130°	639.8	701.5	752.9	792.4	818.5	834.3	839.1
132.5°	619.5	675.5	725.0	764.5	790.7	805.2	810.6
135°	588.4	639.0	684.0	718.8	745.0	759.1	763.9
137.5°	560.5	602.6	640.9	672.0	695.8	708.9	714.1
140°	544.1	580.4	613.7	642.9	663.5	675.3	679.3
142.5°	530.1	561.5	590.3	615.1	632.5	643.7	647.1
145°	512.5	536.9	558.3	577.3	590.7	599.4	602.6
147.5°	497.7	516.6	532.7	547.7	558.5	563.6	565.0
150°	489.5	504.5	518.8	530.6	540.1	543.3	544.1
152.5°	481.3	495.0	506.1	516.1	523.7	526.8	527.6
155°	469.0	480.1	488.7	496.6	502.2	504.5	505.3
157.5°	457.2	465.8	472.6	478.8	483.3	485.5	485.4
160°	448.4	456.3	461.8	467.4	471.3	472.9	472.1
162.5°	440.8	447.4	452.3	456.6	459.9	460.3	460.1
165°	429.4	434.2	438.1	441.2	442.8	442.8	442.8
167.5°	418.4	422.0	424.8	426.4	427.9	427.2	427.1
170°	412.0	414.4	416.0	417.6	418.4	418.4	417.6
172.5°	406.3	408.1	409.0	409.3	410.7	409.5	408.7
175°	397.8	399.3	399.3	399.3	400.1	398.5	397.8
177.5°	394.1	394.1	394.1	393.5	394.1	392.2	392.2
180°	392.2	392.2	392.2	392.2	392.2	392.2	392.2

(END OF REPORT)