

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333292-927

Luminaire Tested: **S125DIP-S1090D1205U927-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333292-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S1090D1205U927-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1090 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1205 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7334.0 lumens
Efficiency: N/A
Efficacy: 112.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 65.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333292-927

CATALOG NUMBER: S125DIP-S1090D1205U927-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333292-927

CATALOG NUMBER: S125DIP-S1090D1205U927-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	54	54	54	48
1	97	93	89	86	89	86	82	79	72	70	67	59	58	56	48	47	46	40
2	89	81	75	70	81	75	69	65	63	59	56	52	49	47	42	40	38	34
3	81	71	64	58	74	66	59	54	56	51	47	46	43	40	37	35	33	29
4	74	63	55	49	68	58	51	46	49	44	40	41	37	34	33	30	28	24
5	68	56	48	42	62	52	45	39	44	39	34	37	33	29	30	27	25	21
6	62	50	42	36	57	47	39	34	40	34	30	33	29	26	27	24	22	19
7	58	45	37	32	53	42	35	30	36	30	26	30	26	23	25	22	19	17
8	54	41	33	28	49	38	31	27	33	27	23	28	23	20	23	20	17	15
9	50	38	30	25	46	35	28	24	30	25	21	25	21	18	21	18	15	13
10	47	34	27	22	43	32	26	21	28	22	19	23	19	16	20	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8730	8730	8730
5°	8749	8666	8722
10°	8697	8605	8655
15°	8602	8501	8538
20°	8467	8357	8372
25°	8322	8185	8177
30°	8143	7999	7959
35°	7950	7799	7689
40°	7754	7583	7474
45°	7541	7384	7237
50°	7306	7145	6931
55°	7080	6875	6683
60°	6810	6603	6368
65°	6487	6276	6062
70°	6180	5897	5695
75°	5629	5445	5255
80°	5013	4932	4813
85°	4357	4439	4194



TEST NUMBER: P333292-927

CATALOG NUMBER: S125DIP-S1090D1205U927-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	127.5	1.7
10°-20°	360.0	4.9
20°-30°	531.6	7.2
30°-40°	620.3	8.5
40°-50°	623.0	8.5
50°-60°	546.9	7.5
60°-70°	407.5	5.6
70°-80°	233.0	3.2
80°-90°	70.4	1.0
90°-100°	45.1	0.6
100°-110°	278.2	3.8
110°-120°	504.5	6.9
120°-130°	647.4	8.8
130°-140°	696.4	9.5
140°-150°	653.6	8.9
150°-160°	528.7	7.2
160°-170°	342.0	4.7
170°-180°	117.9	1.6
0°-30°	1019.1	13.9
0°-40°	1639.4	22.4
0°-60°	2809.2	38.3
0°-90°	3520.1	48.0
90°-120°	827.8	11.3
90°-150°	2825.2	38.5
90°-180°	3814.0	52.0
0°-180°	7334.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1352	1352	1352	1352	1352	
5°	1350	1347	1337	1346	1345	128
15°	1286	1283	1272	1277	1277	362
25°	1168	1162	1149	1150	1148	537
35°	1008	1004	989	984	975	631
45°	826	821	808	796	792	636
55°	629	625	611	601	594	561
65°	424	422	411	401	397	421
75°	226	223	218	215	211	241
85°	59	60	60	59	57	66
90°	1	8	15	19	22	5
95°	52	48	15	19	19	67
105°	271	274	274	274	274	287
115°	508	513	514	510	504	504
125°	723	729	729	726	723	645
135°	901	906	905	903	898	694
145°	1045	1047	1047	1047	1042	653
155°	1151	1146	1147	1149	1143	530
165°	1214	1209	1210	1215	1208	343
175°	1242	1237	1237	1244	1236	118
180°	1242	1242	1242	1242	1242	



TEST NUMBER: P333292-927

CATALOG NUMBER: S125DIP-S1090D1205U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1351.8	1351.8	1351.8	1351.8	1351.8	1351.8	1351.8	1351.8	1351.8	1351.8	1351.8
2.5°	1355.2	1354.6	1354.0	1353.4	1352.9	1351.6	1349.7	1347.8	1345.9	1344.0	1345.9
5°	1349.6	1349.2	1348.7	1348.2	1347.7	1346.3	1343.9	1341.6	1339.2	1336.8	1338.9
7.5°	1337.2	1336.7	1336.3	1335.8	1335.3	1333.7	1331.1	1328.5	1325.9	1323.3	1325.4
10°	1326.1	1325.6	1325.2	1324.7	1324.2	1322.6	1320.0	1317.4	1314.8	1312.2	1314.1
12.5°	1312.4	1311.5	1310.7	1309.8	1309.0	1307.3	1304.9	1302.5	1300.1	1297.6	1299.2
15°	1286.5	1285.8	1285.1	1284.4	1283.7	1282.0	1279.4	1276.8	1274.1	1271.5	1272.7
17.5°	1256.8	1255.8	1254.7	1253.6	1252.6	1250.7	1248.0	1245.3	1242.6	1239.8	1241.3
20°	1232.0	1231.5	1231.1	1230.6	1230.1	1228.3	1225.2	1222.1	1219.0	1215.9	1217.6
22.5°	1207.1	1206.3	1205.5	1204.6	1203.7	1201.8	1199.0	1196.0	1193.2	1190.3	1191.4
25°	1167.8	1166.6	1165.5	1164.3	1163.1	1160.9	1157.9	1154.8	1151.7	1148.6	1149.1
27.5°	1121.8	1121.1	1120.4	1119.7	1119.0	1117.1	1113.8	1110.6	1107.5	1104.3	1104.4
30°	1091.9	1091.2	1090.4	1089.7	1089.0	1086.9	1083.3	1079.7	1076.2	1072.6	1072.1
32.5°	1059.4	1058.3	1057.2	1056.1	1055.0	1052.9	1049.6	1046.5	1043.3	1040.1	1039.3
35°	1008.4	1007.5	1006.5	1005.6	1004.6	1002.5	999.2	995.9	992.5	989.2	988.0
37.5°	955.6	954.4	953.2	952.0	950.9	948.7	945.5	942.5	939.3	936.2	934.4
40°	919.7	918.5	917.3	916.2	915.0	912.7	909.3	906.0	902.7	899.4	897.2
42.5°	881.2	880.2	879.2	878.2	877.2	875.0	871.7	868.4	865.1	861.7	859.8
45°	825.6	824.7	823.7	822.8	821.8	819.9	817.1	814.2	811.4	808.5	805.6
47.5°	765.7	765.7	765.8	765.9	765.9	764.2	760.8	757.3	753.9	750.5	747.6
50°	727.2	726.5	725.8	725.1	724.4	722.5	719.7	716.8	714.0	711.1	708.1
52.5°	687.9	687.3	686.8	686.3	685.8	684.0	681.0	677.9	674.9	671.8	669.1
55°	628.8	628.1	627.4	626.7	626.0	623.9	620.6	617.3	613.9	610.6	608.5
57.5°	566.6	566.2	565.9	565.5	565.1	563.5	560.6	557.9	555.1	552.2	549.5
60°	527.2	526.2	525.3	524.3	523.4	521.7	519.0	516.4	513.8	511.2	508.8
62.5°	486.2	485.4	484.7	483.9	483.2	481.6	479.3	477.1	474.9	472.7	470.1
65°	424.5	424.1	423.6	423.1	422.6	421.1	418.5	415.9	413.3	410.7	408.5
67.5°	364.9	363.8	362.9	361.9	360.9	359.4	357.4	355.5	353.6	351.6	349.8
70°	327.3	326.1	324.9	323.7	322.5	320.8	318.7	316.6	314.4	312.3	310.9
72.5°	286.2	285.3	284.6	283.8	283.0	281.9	280.5	279.1	277.7	276.3	274.7
75°	225.6	225.1	224.7	224.2	223.7	222.9	221.7	220.5	219.4	218.2	217.5
77.5°	169.8	169.6	169.4	169.3	169.1	168.7	167.9	167.3	166.7	166.0	165.6
80°	134.8	134.8	134.8	134.8	134.8	134.5	134.0	133.6	133.1	132.6	132.4
82.5°	103.9	103.5	103.2	102.8	102.4	102.2	102.1	102.0	101.9	101.8	101.4
85°	58.8	59.0	59.3	59.5	59.7	59.9	59.9	59.9	59.9	59.9	59.7
87.5°	23.3	23.6	23.9	24.2	24.6	24.8	24.9	25.0	25.1	25.2	25.4
90°	1.0	2.5	4.2	5.9	7.4	9.0	10.5	11.9	13.3	14.7	15.8
92.5°	14.2	13.1	11.9	10.8	9.6	9.7	10.9	12.2	13.5	14.7	15.8
95°	52.4	51.9	51.3	50.6	50.0	45.9	38.0	30.3	22.5	14.7	15.8
97.5°	109.6	110.7	111.8	112.9	114.0	106.9	91.4	76.0	60.7	45.3	39.5
100°	153.8	154.4	155.0	155.6	156.2	156.9	157.7	158.6	159.4	160.2	129.7
102.5°	198.7	199.5	200.3	201.0	201.8	202.4	202.9	203.4	203.9	204.4	198.6
105°	270.7	271.5	272.3	273.1	273.9	274.3	274.3	274.3	274.3	274.3	274.3
107.5°	345.5	345.5	345.5	345.5	345.5	345.6	346.0	346.4	346.9	347.3	347.3
110°	394.0	394.0	394.0	394.0	394.0	394.3	394.7	395.1	395.5	395.9	395.3



TEST NUMBER: P333292-927

CATALOG NUMBER: S125DIP-S1090D1205U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	439.7	440.2	440.7	441.2	441.6	442.0	442.3	442.5	442.8	443.0	442.3
115°	508.2	509.2	510.2	511.3	512.3	512.9	513.1	513.3	513.5	513.7	512.9
117.5°	579.1	579.1	579.0	579.0	578.9	579.3	580.1	580.8	581.6	582.4	581.4
120°	623.3	623.1	622.9	622.7	622.5	622.7	623.3	623.9	624.5	625.1	624.7
122.5°	662.3	663.1	663.8	664.6	665.4	666.0	666.2	666.5	666.9	667.1	666.7
125°	722.7	724.1	725.6	727.0	728.4	729.1	729.1	729.1	729.1	729.1	728.3
127.5°	780.4	781.4	782.4	783.4	784.4	784.9	784.7	784.7	784.5	784.4	783.9
130°	815.7	816.7	817.8	818.8	819.8	820.4	820.6	820.9	821.0	821.3	820.6
132.5°	851.0	852.2	853.4	854.6	855.8	856.2	855.7	855.2	854.8	854.4	854.3
135°	901.3	902.5	903.8	905.0	906.3	906.7	906.3	905.9	905.4	905.0	904.6
137.5°	947.5	948.6	949.7	950.7	951.8	952.1	951.8	951.4	951.0	950.7	950.8
140°	977.7	978.2	978.6	979.0	979.4	979.5	979.3	979.1	978.9	978.7	979.1
142.5°	1005.0	1005.2	1005.5	1005.8	1006.0	1006.2	1006.5	1006.8	1007.1	1007.4	1007.5
145°	1045.0	1045.4	1045.8	1046.2	1046.6	1046.8	1046.8	1046.8	1046.8	1046.8	1047.0
147.5°	1079.9	1079.8	1079.7	1079.7	1079.6	1079.7	1079.9	1080.1	1080.5	1080.7	1080.9
150°	1102.0	1101.6	1101.2	1100.8	1100.4	1100.4	1100.8	1101.2	1101.6	1102.0	1102.4
152.5°	1123.4	1122.5	1121.6	1120.7	1119.7	1119.5	1120.0	1120.4	1120.8	1121.2	1121.6
155°	1150.8	1149.6	1148.3	1147.2	1145.9	1145.5	1145.9	1146.3	1146.8	1147.2	1147.8
157.5°	1172.0	1171.2	1170.5	1169.8	1169.0	1168.7	1168.8	1168.8	1168.9	1168.9	1169.5
160°	1186.8	1185.5	1184.3	1183.0	1181.9	1181.3	1181.5	1181.7	1181.9	1182.1	1183.0
162.5°	1198.5	1197.3	1196.0	1194.8	1193.6	1193.1	1193.3	1193.5	1193.7	1193.9	1195.1
165°	1214.3	1213.1	1211.9	1210.7	1209.4	1208.9	1209.1	1209.3	1209.5	1209.7	1211.0
167.5°	1226.1	1224.9	1223.6	1222.3	1221.1	1220.5	1220.8	1220.9	1221.1	1221.4	1222.8
170°	1232.8	1231.4	1229.9	1228.4	1227.0	1226.5	1226.6	1226.9	1227.0	1227.2	1228.9
172.5°	1237.2	1235.7	1234.3	1232.9	1231.4	1230.9	1231.3	1231.7	1232.0	1232.4	1233.9
175°	1242.0	1240.7	1239.5	1238.3	1237.1	1236.5	1236.8	1237.0	1237.2	1237.4	1239.0
177.5°	1244.2	1243.2	1242.2	1241.3	1240.2	1239.8	1240.0	1240.2	1240.3	1240.5	1241.7
180°	1242.0	1242.0	1242.0	1242.0	1242.0	1242.0	1242.0	1242.0	1242.0	1242.0	1242.0



TEST NUMBER: P333292-927

CATALOG NUMBER: S125DIP-S1090D1205U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1351.8	1351.8	1351.8	1351.8	1351.8	1351.8	1351.8	1351.8
2.5°	1347.8	1349.7	1351.6	1352.5	1352.3	1352.1	1351.9	1351.8
5°	1341.1	1343.2	1345.4	1346.3	1346.1	1345.8	1345.6	1345.4
7.5°	1327.5	1329.6	1331.7	1332.6	1332.4	1332.1	1331.9	1331.7
10°	1316.0	1317.9	1319.8	1320.6	1320.4	1320.2	1319.9	1319.7
12.5°	1300.7	1302.2	1303.7	1304.5	1304.4	1304.3	1304.3	1304.2
15°	1273.9	1275.1	1276.3	1276.9	1276.9	1276.9	1276.9	1276.9
17.5°	1242.9	1244.3	1245.8	1245.9	1244.8	1243.6	1242.4	1241.2
20°	1219.2	1220.9	1222.6	1222.8	1221.6	1220.4	1219.2	1218.1
22.5°	1192.5	1193.6	1194.6	1194.8	1194.0	1193.2	1192.4	1191.5
25°	1149.5	1150.0	1150.5	1150.3	1149.6	1148.9	1148.2	1147.5
27.5°	1104.5	1104.5	1104.7	1104.4	1103.7	1103.0	1102.2	1101.5
30°	1071.7	1071.2	1070.7	1070.2	1069.4	1068.7	1068.0	1067.3
32.5°	1038.4	1037.5	1036.7	1035.6	1034.4	1033.1	1031.7	1030.5
35°	986.8	985.6	984.4	982.9	981.0	979.1	977.2	975.3
37.5°	932.6	930.9	929.2	927.7	926.6	925.5	924.4	923.4
40°	895.1	892.9	890.8	889.4	888.7	888.0	887.2	886.5
42.5°	857.9	855.9	854.0	852.4	851.4	850.2	849.1	848.0
45°	802.8	799.9	797.1	795.3	794.6	793.8	793.1	792.4
47.5°	744.7	741.8	738.9	736.7	735.0	733.3	731.7	730.0
50°	705.0	701.9	698.8	696.4	694.7	693.1	691.4	689.8
52.5°	666.4	663.7	661.0	658.7	656.8	655.0	653.2	651.3
55°	606.3	604.2	602.1	600.2	598.5	596.8	595.2	593.5
57.5°	546.8	544.0	541.2	539.4	538.5	537.6	536.7	535.8
60°	506.4	504.1	501.7	499.6	498.0	496.3	494.6	493.0
62.5°	467.5	465.0	462.4	460.5	459.2	458.0	456.6	455.3
65°	406.4	404.3	402.1	400.5	399.6	398.6	397.7	396.7
67.5°	348.0	346.2	344.4	343.2	342.6	342.1	341.5	341.0
70°	309.4	308.0	306.6	305.4	304.4	303.5	302.5	301.6
72.5°	273.1	271.5	269.9	268.6	267.7	266.7	265.8	264.8
75°	216.7	216.0	215.3	214.4	213.5	212.5	211.6	210.6
77.5°	165.1	164.7	164.3	163.7	163.0	162.4	161.7	161.1
80°	132.1	131.9	131.7	131.3	130.8	130.3	129.8	129.4
82.5°	100.9	100.5	100.1	99.8	99.7	99.7	99.6	99.4
85°	59.4	59.2	58.9	58.5	58.1	57.6	57.1	56.6
87.5°	25.6	25.8	26.0	26.0	25.7	25.4	25.2	25.0
90°	16.8	17.8	18.9	19.6	20.3	20.8	21.5	22.1
92.5°	16.8	17.8	18.9	19.5	19.7	20.0	20.4	20.6
95°	16.8	17.8	18.9	19.3	19.3	19.3	19.3	19.3
97.5°	33.7	28.0	22.2	19.3	19.3	19.3	19.3	19.3
100°	99.3	68.8	38.3	22.6	21.8	21.0	20.1	19.3
102.5°	192.8	187.1	181.3	171.5	157.6	143.6	129.8	115.8
105°	274.3	274.3	274.3	274.3	274.0	273.9	273.6	273.5
107.5°	347.4	347.4	347.5	347.1	346.5	345.9	345.3	344.7
110°	394.7	394.0	393.4	393.2	393.4	393.6	393.9	394.0



TEST NUMBER: P333292-927

CATALOG NUMBER: S125DIP-S1090D1205U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	441.5	440.7	439.9	439.3	439.1	438.8	438.6	438.2
115°	512.1	511.3	510.5	509.5	508.2	507.0	505.7	504.5
117.5°	580.3	579.2	578.1	577.3	576.8	576.3	575.8	575.2
120°	624.3	623.9	623.5	622.8	621.8	620.8	619.7	618.7
122.5°	666.3	665.9	665.5	664.6	663.5	662.3	661.2	660.0
125°	727.5	726.7	725.9	725.2	724.5	724.0	723.3	722.7
127.5°	783.5	783.1	782.6	781.6	780.1	778.6	777.1	775.5
130°	820.0	819.4	818.8	817.9	816.9	815.9	814.9	813.9
132.5°	854.1	854.0	853.9	853.3	852.3	851.3	850.2	849.2
135°	904.2	903.8	903.4	902.5	901.3	900.1	898.9	897.6
137.5°	950.9	950.9	951.0	950.5	949.4	948.4	947.3	946.3
140°	979.5	979.9	980.3	979.9	978.7	977.5	976.2	975.0
142.5°	1007.6	1007.7	1007.7	1007.2	1005.9	1004.7	1003.5	1002.3
145°	1047.2	1047.4	1047.6	1047.1	1045.8	1044.7	1043.4	1042.2
147.5°	1081.2	1081.4	1081.6	1081.0	1079.6	1078.1	1076.7	1075.1
150°	1102.9	1103.3	1103.7	1103.0	1101.5	1099.8	1098.1	1096.5
152.5°	1122.0	1122.4	1122.8	1122.3	1120.8	1119.4	1117.8	1116.4
155°	1148.3	1149.0	1149.6	1149.1	1147.5	1145.8	1144.1	1142.6
157.5°	1170.2	1170.8	1171.5	1171.0	1169.3	1167.8	1166.1	1164.4
160°	1183.8	1184.6	1185.4	1185.0	1183.4	1181.7	1180.1	1178.5
162.5°	1196.2	1197.4	1198.5	1198.2	1196.4	1194.5	1192.8	1191.0
165°	1212.2	1213.5	1214.7	1214.4	1212.8	1211.2	1209.5	1207.9
167.5°	1224.3	1225.7	1227.2	1227.1	1225.2	1223.4	1221.5	1219.7
170°	1230.5	1232.2	1233.8	1233.7	1231.8	1230.0	1228.2	1226.3
172.5°	1235.3	1236.8	1238.3	1238.1	1236.3	1234.5	1232.6	1230.7
175°	1240.6	1242.3	1243.9	1243.8	1242.0	1240.2	1238.3	1236.4
177.5°	1242.8	1244.0	1245.1	1245.0	1243.7	1242.4	1241.0	1239.8
180°	1242.0	1242.0	1242.0	1242.0	1242.0	1242.0	1242.0	1242.0

(END OF REPORT)