

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332650

Luminaire Tested: **S124DIP-S1020D810U835-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332650
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIP-S1020D810U835-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 810 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7235.4 lumens
Efficiency: N/A
Efficacy: 133.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 54.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332650

CATALOG NUMBER: S124DIP-S1020D810U835-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332650

CATALOG NUMBER: S124DIP-S1020D810U835-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	66	66	66	66	66	66	66	66	66	61		
1	100	96	92	88	94	90	86	83	79	76	74	68	66	65	59	57	56	56	56	56	56	56	56	51		
2	91	84	77	72	85	79	73	68	69	65	61	60	57	54	52	49	47	47	47	47	47	47	47	43		
3	83	74	66	60	78	69	62	57	61	56	51	53	49	46	46	43	40	40	40	40	40	40	40	36		
4	76	65	57	51	71	61	54	48	54	48	44	47	43	39	41	37	35	35	35	35	35	35	35	31		
5	70	58	50	44	65	55	47	42	48	42	38	42	38	34	37	33	30	30	30	30	30	30	30	27		
6	65	52	44	38	60	49	42	36	44	38	33	38	34	30	33	30	27	27	27	27	27	27	27	24		
7	60	47	39	33	56	45	37	32	40	34	29	35	30	26	31	27	24	24	24	24	24	24	24	21		
8	56	43	35	30	52	41	33	28	36	30	26	32	27	24	28	24	21	21	21	21	21	21	21	19		
9	52	39	32	26	48	37	30	25	33	27	23	29	25	21	26	22	19	19	19	19	19	19	19	17		
10	48	36	29	24	45	34	27	23	31	25	21	27	23	19	24	20	17	17	17	17	17	17	17	16		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13930	13930	13930
5°	13972	13804	13904
10°	13884	13691	13759
15°	13717	13497	13531
20°	13493	13256	13268
25°	13239	12981	12944
30°	12928	12656	12541
35°	12604	12318	12154
40°	12269	11934	11715
45°	11918	11555	11334
50°	11531	11218	10870
55°	11112	10781	10431
60°	10693	10291	9978
65°	10222	9824	9429
70°	9692	9203	8844
75°	8883	8453	8238
80°	7908	7583	7392
85°	6919	6660	6530



TEST NUMBER: P332650

CATALOG NUMBER: S124DIP-S1020D810U835-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	162.5	2.2
10°-20°	457.8	6.3
20°-30°	673.9	9.3
30°-40°	783.4	10.8
40°-50°	783.4	10.8
50°-60°	685.3	9.5
60°-70°	508.9	7.0
70°-80°	289.1	4.0
80°-90°	86.5	1.2
90°-100°	66.7	0.9
100°-110°	197.5	2.7
110°-120°	335.2	4.6
120°-130°	442.0	6.1
130°-140°	496.4	6.9
140°-150°	487.8	6.7
150°-160°	410.3	5.7
160°-170°	273.0	3.8
170°-180°	95.6	1.3
0°-30°	1294.2	17.9
0°-40°	2077.6	28.7
0°-60°	3546.4	49.0
0°-90°	4430.9	61.2
90°-120°	599.4	8.3
90°-150°	2025.7	28.0
90°-180°	2805.0	38.8
0°-180°	7235.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1726	1726	1726	1726	1726	
5°	1724	1718	1703	1718	1716	163
15°	1641	1635	1615	1622	1619	462
25°	1486	1476	1457	1458	1453	684
35°	1279	1269	1250	1240	1233	799
45°	1044	1034	1012	997	993	804
55°	790	784	766	750	741	707
65°	535	528	514	501	494	530
75°	285	278	271	266	264	303
85°	75	75	72	72	70	82
90°	2	11	17	22	24	7
95°	47	54	59	62	62	52
105°	182	183	186	188	191	193
115°	341	341	339	338	338	336
125°	496	496	496	494	492	442
135°	640	645	645	643	641	495
145°	778	781	782	781	779	487
155°	891	891	890	893	890	410
165°	970	968	966	971	968	273
175°	1009	1006	1005	1010	1005	96
180°	1011	1011	1011	1011	1011	



TEST NUMBER: P332650

CATALOG NUMBER: S124DIP-S1020D810U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1725.5	1725.5	1725.5	1725.5	1725.5	1725.5	1725.5	1725.5	1725.5	1725.5	1725.5
2.5°	1729.9	1729.2	1728.4	1727.7	1727.0	1725.2	1722.5	1719.8	1717.1	1714.4	1716.9
5°	1724.1	1722.9	1721.7	1720.4	1719.2	1716.9	1713.5	1710.1	1706.8	1703.4	1706.8
7.5°	1708.1	1706.8	1705.6	1704.4	1703.2	1700.7	1696.9	1693.2	1689.4	1685.7	1688.4
10°	1693.7	1692.5	1691.2	1690.0	1688.8	1686.2	1682.2	1678.2	1674.2	1670.2	1672.6
12.5°	1674.9	1673.7	1672.4	1671.2	1670.0	1667.2	1663.0	1658.8	1654.5	1650.3	1653.0
15°	1641.2	1639.9	1638.7	1637.5	1636.2	1633.3	1628.7	1624.1	1619.5	1614.9	1616.7
17.5°	1600.5	1599.0	1597.4	1595.9	1594.4	1591.4	1587.0	1582.7	1578.3	1574.0	1575.1
20°	1570.6	1569.1	1567.6	1566.0	1564.5	1561.4	1556.8	1552.2	1547.6	1543.0	1543.9
22.5°	1538.6	1536.5	1534.5	1532.5	1530.5	1527.1	1522.5	1517.9	1513.3	1508.7	1510.4
25°	1486.3	1484.2	1482.0	1479.8	1477.7	1474.5	1470.2	1465.9	1461.6	1457.3	1457.6
27.5°	1426.6	1424.4	1422.1	1419.9	1417.7	1414.6	1410.6	1406.6	1402.6	1398.6	1397.9
30°	1386.8	1384.3	1381.8	1379.4	1376.9	1373.7	1369.7	1365.7	1361.7	1357.7	1356.5
32.5°	1344.7	1342.5	1340.3	1338.1	1335.9	1332.6	1328.4	1324.2	1319.9	1315.7	1314.2
35°	1278.9	1276.8	1274.6	1272.5	1270.3	1267.1	1262.8	1258.5	1254.2	1249.9	1247.7
37.5°	1209.5	1207.5	1205.6	1203.6	1201.6	1198.4	1193.7	1189.1	1184.5	1179.9	1177.6
40°	1164.2	1161.7	1159.2	1156.8	1154.3	1150.8	1146.2	1141.6	1137.0	1132.4	1129.3
42.5°	1115.5	1114.0	1112.5	1111.1	1109.6	1106.3	1101.2	1096.1	1091.0	1085.9	1082.3
45°	1043.9	1041.7	1039.6	1037.4	1035.3	1031.7	1026.8	1021.9	1017.0	1012.1	1008.7
47.5°	968.9	967.5	966.0	964.5	963.0	960.0	955.5	950.9	946.4	941.8	938.0
50°	918.1	916.8	915.6	914.4	913.1	910.4	906.1	901.8	897.5	893.2	888.9
52.5°	868.3	866.8	865.3	863.9	862.4	859.4	854.8	850.3	845.7	841.2	837.4
55°	789.5	788.5	787.6	786.7	785.8	783.2	778.9	774.6	770.3	766.0	762.3
57.5°	714.3	713.2	712.2	711.1	710.1	707.4	703.2	699.0	694.7	690.5	687.0
60°	662.3	660.7	659.2	657.7	656.1	653.4	649.4	645.4	641.4	637.4	634.6
62.5°	611.4	610.1	608.8	607.5	606.2	603.5	599.2	595.0	590.7	586.5	584.0
65°	535.1	533.5	532.0	530.5	528.9	526.6	523.5	520.5	517.4	514.3	511.3
67.5°	458.2	456.8	455.4	454.0	452.5	450.4	447.4	444.5	441.5	438.6	435.6
70°	410.6	408.5	406.3	404.2	402.0	399.7	397.3	394.8	392.4	389.9	387.4
72.5°	359.8	357.6	355.5	353.3	351.2	349.1	347.1	345.2	343.2	341.2	339.3
75°	284.8	283.3	281.7	280.2	278.7	277.1	275.6	274.1	272.5	271.0	269.8
77.5°	213.2	212.5	211.8	211.2	210.5	209.5	208.1	206.8	205.4	204.1	203.7
80°	170.1	169.1	168.2	167.3	166.4	165.6	165.0	164.4	163.8	163.1	162.5
82.5°	128.0	127.6	127.2	126.7	126.3	126.0	125.9	125.8	125.7	125.5	125.2
85°	74.7	74.7	74.7	74.7	74.7	74.4	73.7	73.1	72.5	71.9	71.9
87.5°	29.2	29.4	29.5	29.6	29.8	29.9	29.9	29.9	30.0	30.0	30.2
90°	2.3	4.3	6.2	8.1	10.0	11.6	13.0	14.4	15.8	17.2	18.2
92.5°	16.7	18.9	21.1	23.3	25.5	27.1	28.0	29.0	30.0	31.0	31.6
95°	46.9	48.5	50.0	51.6	53.2	54.6	55.8	57.0	58.2	59.4	59.9
97.5°	81.9	83.2	84.4	85.7	86.9	88.3	89.7	91.1	92.5	94.0	94.6
100°	109.5	110.1	110.8	111.5	112.2	113.4	114.9	116.5	118.0	119.6	120.0
102.5°	138.2	138.5	138.8	139.1	139.3	140.2	141.6	143.0	144.5	145.9	146.4
105°	182.2	182.3	182.5	182.7	182.9	183.3	184.0	184.7	185.4	186.1	186.6
107.5°	228.3	228.5	228.7	228.9	229.1	229.3	229.4	229.5	229.6	229.7	230.2
110°	259.6	259.9	260.2	260.6	260.9	261.0	260.9	260.7	260.5	260.3	260.0



TEST NUMBER: P332650

CATALOG NUMBER: S124DIP-S1020D810U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	292.1	292.1	292.2	292.3	292.4	292.2	291.9	291.6	291.3	291.0	290.9
115°	340.9	340.9	340.9	340.9	340.9	340.7	340.3	340.0	339.6	339.3	339.1
117.5°	386.8	387.0	387.1	387.2	387.4	387.3	387.1	386.8	386.6	386.4	385.8
120°	417.5	418.2	418.9	419.6	420.3	420.3	419.8	419.3	418.8	418.3	417.4
122.5°	449.4	449.6	449.9	450.2	450.5	450.5	450.3	450.0	449.8	449.5	448.9
125°	496.4	496.4	496.4	496.4	496.4	496.3	496.2	496.0	495.8	495.7	495.3
127.5°	539.1	539.6	540.2	540.7	541.2	541.3	541.0	540.8	540.5	540.2	539.9
130°	569.1	569.7	570.2	570.7	571.2	571.5	571.5	571.5	571.5	571.5	571.1
132.5°	599.8	600.2	600.6	600.9	601.3	601.4	601.3	601.2	601.0	600.9	600.5
135°	640.3	641.3	642.4	643.4	644.5	645.0	645.0	645.0	645.0	645.0	644.6
137.5°	684.4	684.9	685.3	685.8	686.3	686.7	687.0	687.3	687.5	687.8	687.4
140°	713.8	714.1	714.5	714.8	715.2	715.3	715.3	715.3	715.3	715.3	715.2
142.5°	740.7	741.0	741.4	741.7	742.1	742.2	742.0	741.9	741.7	741.6	741.6
145°	777.9	778.6	779.3	780.0	780.7	781.1	781.3	781.4	781.6	781.8	781.6
147.5°	814.8	815.6	816.4	817.3	818.1	818.5	818.3	818.2	818.0	817.9	817.8
150°	837.3	838.0	838.7	839.4	840.1	840.4	840.4	840.4	840.4	840.4	840.4
152.5°	858.6	859.0	859.4	859.8	860.2	860.5	860.6	860.8	860.9	861.1	861.5
155°	891.2	891.2	891.2	891.2	891.2	891.1	891.0	890.8	890.6	890.5	891.1
157.5°	918.8	918.4	918.1	917.8	917.5	917.3	917.3	917.3	917.2	917.2	917.7
160°	935.0	934.8	934.7	934.5	934.3	934.1	934.0	933.8	933.6	933.5	934.0
162.5°	950.0	949.6	949.1	948.7	948.2	947.9	947.7	947.6	947.4	947.2	948.2
165°	970.2	969.7	969.2	968.6	968.1	967.7	967.3	967.0	966.6	966.3	967.3
167.5°	985.7	984.9	984.2	983.5	982.8	982.4	982.4	982.5	982.5	982.5	983.6
170°	994.4	993.6	992.7	991.8	991.0	990.6	990.8	991.0	991.1	991.3	992.3
172.5°	1000.7	1000.0	999.2	998.5	997.8	997.4	997.5	997.5	997.5	997.6	998.7
175°	1009.3	1008.4	1007.5	1006.7	1005.8	1005.3	1005.1	1004.9	1004.8	1004.6	1005.8
177.5°	1012.1	1011.4	1010.7	1010.0	1009.3	1009.0	1009.0	1009.0	1009.0	1009.0	1009.9
180°	1010.8	1010.8	1010.8	1010.8	1010.8	1010.8	1010.8	1010.8	1010.8	1010.8	1010.8



TEST NUMBER: P332650

CATALOG NUMBER: S124DIP-S1020D810U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1725.5	1725.5	1725.5	1725.5	1725.5	1725.5	1725.5	1725.5
2.5°	1719.3	1721.8	1724.3	1725.4	1725.1	1724.9	1724.6	1724.4
5°	1710.1	1713.5	1716.9	1718.3	1717.7	1717.0	1716.4	1715.8
7.5°	1691.1	1693.8	1696.5	1697.7	1697.3	1696.9	1696.5	1696.2
10°	1675.1	1677.6	1680.0	1680.9	1680.3	1679.7	1679.1	1678.5
12.5°	1655.7	1658.4	1661.1	1662.0	1661.2	1660.3	1659.4	1658.6
15°	1618.6	1620.4	1622.3	1622.7	1621.8	1620.9	1620.0	1619.0
17.5°	1576.3	1577.5	1578.6	1578.9	1578.3	1577.7	1577.1	1576.4
20°	1544.8	1545.8	1546.7	1546.8	1546.2	1545.6	1545.0	1544.4
22.5°	1512.0	1513.7	1515.3	1515.6	1514.5	1513.4	1512.3	1511.2
25°	1457.9	1458.2	1458.5	1458.0	1456.8	1455.6	1454.3	1453.1
27.5°	1397.2	1396.4	1395.7	1394.6	1393.0	1391.5	1389.9	1388.4
30°	1355.3	1354.0	1352.8	1351.4	1349.9	1348.3	1346.8	1345.3
32.5°	1312.7	1311.3	1309.8	1308.3	1306.7	1305.2	1303.7	1302.1
35°	1245.6	1243.4	1241.3	1239.4	1237.9	1236.4	1234.8	1233.3
37.5°	1175.2	1172.9	1170.6	1168.4	1166.4	1164.3	1162.3	1160.3
40°	1126.2	1123.1	1120.1	1117.8	1116.2	1114.7	1113.2	1111.6
42.5°	1078.8	1075.2	1071.6	1069.3	1068.3	1067.2	1066.2	1065.2
45°	1005.3	1001.9	998.5	996.4	995.5	994.6	993.6	992.7
47.5°	934.2	930.4	926.6	923.5	921.2	918.8	916.5	914.2
50°	884.6	880.3	876.0	872.9	871.0	869.2	867.4	865.5
52.5°	833.6	829.7	825.9	822.9	820.5	818.2	815.9	813.5
55°	758.6	754.9	751.2	748.5	746.6	744.8	742.9	741.1
57.5°	683.5	680.0	676.5	673.8	672.0	670.3	668.5	666.7
60°	631.9	629.1	626.3	624.2	622.6	621.1	619.6	618.0
62.5°	581.5	578.9	576.4	574.4	572.9	571.3	569.8	568.3
65°	508.2	505.1	502.0	499.7	498.2	496.7	495.1	493.6
67.5°	432.7	429.7	426.8	425.1	424.6	424.2	423.8	423.4
70°	385.0	382.5	380.1	378.4	377.5	376.5	375.6	374.7
72.5°	337.3	335.3	333.4	331.9	331.0	330.1	329.2	328.2
75°	268.5	267.3	266.1	265.3	265.0	264.7	264.4	264.1
77.5°	203.3	203.0	202.6	202.0	201.2	200.4	199.6	198.8
80°	161.9	161.3	160.7	160.2	159.9	159.6	159.3	159.0
82.5°	124.8	124.4	124.1	123.7	123.4	123.1	122.8	122.5
85°	71.9	71.9	71.9	71.7	71.4	71.1	70.8	70.5
87.5°	30.4	30.6	30.8	31.0	31.0	31.1	31.2	31.2
90°	19.3	20.3	21.4	22.1	22.4	22.8	23.1	23.5
92.5°	32.2	32.8	33.5	33.9	34.1	34.3	34.5	34.7
95°	60.5	61.0	61.5	61.8	61.8	61.8	61.8	61.8
97.5°	95.2	95.8	96.5	96.8	96.8	96.8	96.8	96.8
100°	120.3	120.7	121.0	121.2	121.2	121.2	121.2	121.2
102.5°	146.9	147.3	147.8	148.1	148.3	148.4	148.6	148.7
105°	187.1	187.6	188.1	188.7	189.2	189.7	190.2	190.8
107.5°	230.7	231.1	231.6	231.9	231.8	231.8	231.8	231.7
110°	259.6	259.3	258.9	259.0	259.6	260.1	260.6	261.1



TEST NUMBER: P332650

CATALOG NUMBER: S124DIP-S1020D810U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	290.8	290.8	290.7	290.7	290.8	290.9	291.0	291.1
115°	338.9	338.8	338.6	338.4	338.3	338.1	337.9	337.7
117.5°	385.2	384.6	384.0	383.5	383.2	382.8	382.5	382.1
120°	416.5	415.6	414.8	414.5	414.9	415.2	415.6	415.9
122.5°	448.3	447.8	447.2	446.6	445.9	445.3	444.7	444.1
125°	495.0	494.6	494.3	493.9	493.6	493.2	492.9	492.5
127.5°	539.5	539.2	538.8	538.5	538.2	538.0	537.7	537.4
130°	570.8	570.4	570.1	569.6	568.9	568.2	567.5	566.8
132.5°	600.2	599.8	599.5	599.2	598.9	598.6	598.3	598.1
135°	644.3	643.9	643.6	643.1	642.6	642.1	641.6	641.1
137.5°	686.9	686.5	686.0	685.8	685.9	686.0	686.1	686.3
140°	715.0	714.8	714.6	714.5	714.3	714.1	713.9	713.8
142.5°	741.5	741.5	741.5	741.4	741.4	741.4	741.3	741.3
145°	781.4	781.3	781.1	780.7	780.2	779.7	779.2	778.7
147.5°	817.6	817.5	817.3	817.2	817.0	816.8	816.7	816.5
150°	840.4	840.4	840.4	840.3	840.2	840.0	839.8	839.6
152.5°	861.9	862.3	862.7	862.7	862.3	861.8	861.4	860.9
155°	891.8	892.5	893.2	893.2	892.5	891.8	891.1	890.5
157.5°	918.2	918.8	919.3	919.2	918.7	918.1	917.5	916.9
160°	934.5	935.0	935.5	935.4	934.5	933.6	932.8	931.9
162.5°	949.1	950.0	951.0	951.0	950.1	949.3	948.4	947.5
165°	968.4	969.4	970.5	970.6	969.9	969.2	968.5	967.9
167.5°	984.6	985.7	986.7	986.7	985.6	984.5	983.5	982.4
170°	993.4	994.4	995.5	995.4	994.2	993.0	991.7	990.5
172.5°	999.9	1001.1	1002.3	1002.3	1001.1	999.8	998.6	997.4
175°	1007.0	1008.2	1009.5	1009.5	1008.2	1007.0	1005.8	1004.6
177.5°	1010.9	1011.9	1012.9	1012.8	1011.7	1010.6	1009.5	1008.3
180°	1010.8	1010.8	1010.8	1010.8	1010.8	1010.8	1010.8	1010.8

(END OF REPORT)