

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333260-927

Luminaire Tested: **S125DIP-S1090D590U927-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333260-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIP-S1090D590U927-4F0-1E-UDD-A1  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1090 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 590 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5176.4 lumens  
Efficiency: N/A  
Efficacy: 106.1 lumens/watt  
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: Semi-Direct  
  
Input Watts (W): 48.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333260-927

CATALOG NUMBER: S125DIP-S1090D590U927-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P333260-927

CATALOG NUMBER: S125DIP-S1090D590U927-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	105	105	105	105	94	94	94	83	83	83	73	73	73	69
1	102	98	94	91	96	93	89	86	83	80	78	74	72	70	65	64	63	59
2	93	86	80	75	88	81	76	71	73	69	65	65	62	59	58	55	53	49
3	85	76	68	62	80	72	65	60	65	59	55	58	54	50	51	48	46	42
4	78	67	59	53	74	64	57	51	58	52	47	52	47	43	46	42	39	36
5	72	60	52	46	68	57	50	44	52	46	41	46	42	38	42	38	34	32
6	66	54	46	40	63	52	44	38	47	40	36	42	37	33	38	34	30	28
7	62	49	41	35	58	47	39	34	42	36	32	38	33	29	35	30	27	25
8	57	45	37	31	54	43	35	30	39	33	28	35	30	26	32	27	24	22
9	53	41	33	28	50	39	32	27	36	30	25	32	27	24	29	25	22	20
10	50	37	30	25	47	36	29	24	33	27	23	30	25	21	27	23	20	18

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	8136	8136	8136	8136
5°	9422	8163	7148	8163
10°	10961	8121	6263	8121
15°	12133	8062	5777	8062
20°	13582	7967	5388	7967
25°	15911	7860	5197	7860
30°	17186	7756	5032	7756
35°	14130	7559	4924	7559
40°	10044	7284	4806	7284
45°	7716	6915	4737	6915
50°	6586	6457	4728	6457
55°	5864	6008	4769	6008
60°	5291	5518	4890	5518
65°	4886	5025	5017	5025
70°	4443	4513	5089	4513
75°	3923	3975	5043	3975
80°	3299	3239	4616	3239
85°	2616	2334	3720	2334



TEST NUMBER: P333260-927

CATALOG NUMBER: S125DIP-S1090D590U927-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	121.3	2.3
10°-20°	361.1	7.0
20°-30°	586.3	11.3
30°-40°	715.2	13.8
40°-50°	650.6	12.6
50°-60°	518.2	10.0
60°-70°	361.0	7.0
70°-80°	192.5	3.7
80°-90°	49.9	1.0
90°-100°	38.9	0.8
100°-110°	114.9	2.2
110°-120°	194.5	3.8
120°-130°	256.0	4.9
130°-140°	286.9	5.5
140°-150°	281.2	5.4
150°-160°	236.2	4.6
160°-170°	157.0	3.0
170°-180°	54.9	1.1
0°-30°	1068.7	20.6
0°-40°	1783.8	34.5
0°-60°	2952.7	57.0
0°-90°	3556.0	68.7
90°-120°	348.3	6.7
90°-150°	1172.4	22.6
90°-180°	1620.0	31.3
0°-180°	5176.4	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1260	1260	1260	1260	1260	
5°	1453	1259	1102	1259	1453	146
15°	1815	1206	864	1206	1815	519
25°	2233	1103	729	1103	2233	1020
35°	1792	959	624	959	1792	1097
45°	845	757	519	757	845	676
55°	521	534	424	534	521	469
65°	320	329	328	329	320	317
75°	157	159	202	159	157	169
85°	35	32	50	32	35	41
90°	11	0	11	0	11	8
95°	39	29	39	29	39	40
105°	112	103	112	103	112	119
115°	197	195	197	195	197	194
125°	286	284	286	284	286	255
135°	371	370	371	370	371	286
145°	450	448	450	448	450	281
155°	512	512	512	512	512	236
165°	556	557	556	557	556	157
175°	577	579	577	579	577	55
180°	581	581	581	581	581	



TEST NUMBER: P333260-927

CATALOG NUMBER: S125DIP-S1090D590U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7
2.5°	1332.5	1330.7	1329.0	1325.6	1328.2	1320.9	1317.5	1311.5	1304.2	1301.6	1298.6
5°	1453.3	1456.0	1458.6	1447.4	1448.4	1441.0	1423.9	1409.9	1398.8	1384.3	1374.1
7.5°	1598.7	1592.4	1591.9	1584.6	1572.1	1562.0	1544.0	1521.1	1499.0	1473.8	1452.9
10°	1671.4	1672.0	1667.1	1658.6	1645.2	1635.6	1612.1	1589.6	1562.3	1530.3	1507.3
12.5°	1726.2	1728.4	1722.4	1710.8	1704.2	1682.7	1664.3	1637.5	1605.1	1579.5	1544.5
15°	1814.7	1808.9	1804.6	1790.1	1778.9	1756.4	1727.0	1699.2	1663.9	1631.3	1598.7
17.5°	1900.0	1904.7	1896.7	1883.6	1848.7	1822.5	1783.0	1745.0	1701.1	1657.3	1618.3
20°	1976.2	1980.5	1968.2	1945.2	1903.5	1877.3	1825.4	1776.2	1725.5	1669.3	1626.5
22.5°	2071.2	2067.8	2051.1	2016.2	1980.1	1931.6	1875.5	1815.6	1751.9	1688.5	1631.7
25°	2232.8	2210.3	2200.2	2157.0	2109.3	2038.2	1961.2	1873.5	1794.4	1710.5	1637.8
27.5°	2322.4	2315.4	2304.1	2273.9	2223.9	2147.8	2057.1	1950.2	1838.6	1732.6	1637.4
30°	2304.5	2305.6	2306.6	2297.0	2264.9	2207.7	2117.3	2002.4	1869.8	1750.6	1640.4
32.5°	2145.4	2164.8	2183.4	2205.4	2214.5	2203.5	2146.9	2043.0	1906.5	1771.1	1638.7
35°	1792.2	1798.2	1858.5	1918.4	1999.7	2062.8	2105.1	2059.0	1944.1	1788.5	1636.6
37.5°	1397.5	1426.3	1468.2	1535.8	1653.1	1758.2	1893.2	1955.3	1918.3	1794.2	1632.9
40°	1191.3	1218.0	1245.3	1314.2	1413.2	1540.4	1693.8	1824.9	1855.4	1776.2	1620.1
42.5°	1032.1	1053.4	1083.6	1135.4	1218.1	1330.9	1477.4	1648.6	1754.0	1724.0	1593.2
45°	844.8	858.2	881.7	922.9	982.8	1071.0	1200.4	1387.5	1550.6	1604.6	1529.2
47.5°	723.1	723.0	741.3	769.8	812.9	887.9	983.6	1130.2	1304.4	1433.3	1427.3
50°	655.5	652.8	667.3	691.9	726.1	775.9	867.3	984.4	1151.7	1297.7	1338.3
52.5°	597.4	597.7	606.6	624.7	653.4	695.9	764.1	869.7	1012.7	1162.5	1239.1
55°	520.8	518.6	528.8	541.1	562.0	589.8	639.0	719.7	835.7	983.3	1082.8
57.5°	450.6	456.5	460.6	469.1	486.5	505.1	546.5	605.8	697.8	824.5	929.6
60°	409.6	415.4	418.7	427.2	441.1	457.2	489.3	537.3	614.9	724.0	828.2
62.5°	372.8	377.4	378.4	386.1	397.5	413.1	438.3	478.8	540.0	635.4	737.5
65°	319.7	319.7	321.9	329.9	335.3	349.1	368.4	397.8	447.0	521.3	608.5
67.5°	268.6	271.2	270.7	274.2	279.1	289.9	303.7	328.0	364.4	418.7	488.4
70°	235.3	237.4	236.9	239.6	244.9	251.8	263.1	286.1	312.3	358.8	418.7
72.5°	205.3	206.2	204.8	208.3	211.5	217.6	230.1	242.4	266.9	306.2	355.4
75°	157.2	158.3	159.3	161.4	164.7	167.9	174.3	186.6	202.6	232.0	263.6
77.5°	117.9	115.8	118.4	118.0	119.9	122.3	128.0	134.5	147.7	166.3	190.7
80°	88.7	89.3	89.3	89.8	92.5	94.1	98.9	103.7	113.9	127.8	144.9
82.5°	64.8	66.2	65.4	66.3	68.5	69.7	72.4	76.4	82.2	93.2	105.5
85°	35.3	32.6	33.7	34.8	34.8	35.3	37.4	39.1	42.2	46.5	51.3
87.5°	12.4	13.2	13.6	13.5	13.9	13.9	15.4	15.4	16.6	17.7	19.3
90°	10.9	10.5	10.2	10.0	9.7	9.3	8.7	8.2	7.8	7.2	6.5
92.5°	21.3	21.1	20.9	20.7	20.4	20.0	19.3	18.7	18.0	17.3	16.5
95°	38.9	38.7	38.5	38.3	38.0	37.6	36.9	36.2	35.5	34.8	33.8
97.5°	58.9	58.8	58.7	58.5	58.5	58.1	57.4	56.7	56.1	55.4	54.0
100°	74.1	73.9	73.8	73.5	73.3	72.7	71.9	71.0	70.0	69.2	67.8
102.5°	89.3	89.0	88.7	88.5	88.2	87.5	86.6	85.6	84.6	83.6	82.9
105°	112.1	111.8	111.5	111.1	110.9	110.4	109.8	109.2	108.6	108.0	107.4
107.5°	135.4	135.4	135.5	135.5	135.5	135.3	135.1	134.8	134.4	134.1	133.6
110°	152.7	152.8	153.0	153.0	153.1	153.0	152.7	152.4	152.2	151.9	151.5



TEST NUMBER: P333260-927

CATALOG NUMBER: S125DIP-S1090D590U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	169.8	169.9	170.1	170.3	170.5	170.5	170.3	170.2	170.1	169.9	169.5
115°	196.6	196.7	196.8	196.9	197.0	197.1	197.2	197.3	197.4	197.5	197.3
117.5°	222.8	223.2	223.6	224.0	224.4	224.6	224.5	224.4	224.3	224.3	224.0
120°	240.9	241.3	241.7	242.1	242.5	242.6	242.6	242.6	242.6	242.6	242.6
122.5°	259.0	259.3	259.6	259.9	260.2	260.5	260.5	260.6	260.7	260.8	260.5
125°	286.1	286.1	286.3	286.4	286.5	286.6	286.8	287.0	287.2	287.4	287.3
127.5°	312.1	312.3	312.5	312.7	312.9	313.1	313.1	313.2	313.4	313.5	313.3
130°	329.5	329.6	329.9	330.0	330.3	330.4	330.5	330.6	330.7	330.8	330.6
132.5°	345.7	346.0	346.3	346.6	346.8	347.1	347.1	347.2	347.4	347.5	347.5
135°	371.1	371.5	371.9	372.2	372.6	372.8	372.8	372.8	372.8	372.8	372.7
137.5°	395.8	396.3	396.8	397.3	397.8	398.0	397.8	397.8	397.6	397.5	397.3
140°	411.7	412.2	412.7	413.2	413.7	413.8	413.7	413.4	413.3	413.0	412.7
142.5°	426.9	427.4	427.9	428.4	428.9	429.0	429.0	428.8	428.7	428.6	428.3
145°	449.6	450.0	450.3	450.6	450.8	451.0	451.0	451.0	451.0	451.0	450.8
147.5°	469.1	469.8	470.5	471.1	471.8	472.1	471.8	471.6	471.3	471.1	470.9
150°	483.5	483.8	483.9	484.2	484.3	484.4	484.4	484.4	484.4	484.4	484.0
152.5°	495.5	495.8	496.2	496.5	496.9	497.0	496.8	496.5	496.3	496.1	495.8
155°	512.5	512.9	513.5	514.0	514.5	514.5	514.1	513.7	513.3	512.9	512.9
157.5°	526.6	527.4	528.0	528.6	529.3	529.4	529.0	528.6	528.2	527.8	527.8
160°	536.5	536.9	537.4	538.0	538.4	538.4	538.1	537.7	537.3	536.9	536.8
162.5°	544.7	545.3	545.9	546.5	547.1	547.2	546.6	546.1	545.7	545.2	545.2
165°	555.9	556.4	557.1	557.7	558.3	558.4	557.9	557.5	557.1	556.7	556.7
167.5°	564.7	565.3	565.9	566.6	567.2	567.2	566.6	566.0	565.4	564.8	564.8
170°	569.4	570.1	570.8	571.6	572.2	572.3	571.6	571.1	570.5	569.9	569.9
172.5°	573.4	574.0	574.6	575.3	575.9	575.9	575.3	574.7	574.1	573.5	573.5
175°	577.1	577.8	578.5	579.2	579.9	580.0	579.3	578.8	578.1	577.6	577.6
177.5°	579.2	579.8	580.4	581.0	581.5	581.5	581.1	580.6	580.1	579.6	579.7
180°	580.7	580.7	580.7	580.7	580.7	580.7	580.7	580.7	580.7	580.7	580.7



TEST NUMBER: P333260-927

CATALOG NUMBER: S125DIP-S1090D590U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7
2.5°	1296.1	1293.1	1289.7	1283.7	1276.4	1272.6	1266.5	1262.7	1255.0	1248.6	1241.7
5°	1361.8	1348.0	1335.1	1318.5	1300.4	1288.6	1274.7	1259.2	1243.2	1226.5	1208.4
7.5°	1430.0	1405.3	1378.6	1349.9	1321.8	1295.9	1271.1	1246.9	1224.2	1196.8	1173.6
10°	1475.8	1444.7	1411.6	1372.5	1334.6	1301.4	1267.7	1238.3	1208.4	1176.3	1148.0
12.5°	1521.5	1480.2	1433.4	1390.5	1344.8	1304.8	1265.2	1227.6	1190.0	1154.5	1121.4
15°	1553.8	1517.4	1474.1	1413.2	1361.8	1306.8	1254.3	1205.7	1160.2	1120.7	1079.0
17.5°	1575.1	1528.2	1481.7	1423.2	1356.0	1294.3	1235.0	1179.3	1128.1	1077.9	1037.7
20°	1578.9	1530.8	1482.2	1424.9	1356.0	1285.4	1226.1	1159.2	1104.1	1052.3	1003.1
22.5°	1577.6	1523.1	1470.1	1411.3	1344.0	1279.0	1207.2	1139.1	1079.3	1028.3	977.0
25°	1565.6	1507.3	1441.0	1381.6	1315.3	1246.3	1173.6	1103.0	1042.1	983.8	933.0
27.5°	1555.5	1479.9	1404.9	1335.6	1271.6	1208.4	1138.8	1066.5	998.9	939.8	892.0
30°	1543.1	1460.2	1375.7	1303.5	1237.8	1176.3	1110.6	1040.0	969.4	911.6	860.3
32.5°	1532.0	1435.4	1346.2	1267.7	1198.0	1138.2	1077.6	1010.4	941.1	882.6	831.2
35°	1510.5	1398.8	1296.6	1207.8	1133.5	1072.1	1021.3	958.7	895.1	838.4	789.2
37.5°	1483.2	1350.6	1241.0	1148.0	1066.5	1001.7	954.4	906.4	845.3	790.7	746.2
40°	1461.8	1316.4	1200.4	1105.2	1020.7	953.3	909.5	864.0	813.3	762.5	715.4
42.5°	1434.9	1285.6	1159.3	1056.9	973.2	907.6	861.6	823.0	778.2	730.8	687.1
45°	1385.4	1229.8	1092.9	982.8	898.3	833.5	786.0	757.1	723.4	678.5	641.6
47.5°	1312.6	1162.7	1021.1	907.4	820.3	760.3	715.7	688.0	664.3	630.9	597.5
50°	1247.9	1112.7	969.4	856.6	769.4	709.0	667.8	642.7	622.3	596.7	568.4
52.5°	1175.7	1049.8	918.5	806.9	720.6	661.1	620.8	598.7	581.7	563.3	535.4
55°	1060.8	953.9	831.9	726.1	646.4	588.1	552.9	533.6	519.8	505.8	488.7
57.5°	934.3	850.6	742.7	645.9	572.5	519.5	486.6	467.9	457.0	449.9	439.8
60°	845.3	773.7	680.6	592.4	520.8	473.7	441.6	427.2	418.1	412.3	404.7
62.5°	762.8	703.9	617.7	537.3	474.6	430.1	401.5	387.5	378.7	375.9	369.7
65°	641.1	595.6	524.5	457.7	404.3	366.2	342.2	328.8	323.4	320.3	320.8
67.5°	521.2	493.5	436.4	379.4	336.8	304.9	285.7	275.4	272.7	268.4	268.3
70°	448.1	427.2	379.1	329.4	291.4	266.8	249.7	239.0	236.3	234.2	233.7
72.5°	383.5	365.2	323.4	283.6	249.5	227.9	213.7	207.3	203.0	201.7	201.6
75°	288.2	278.1	244.9	213.3	189.8	174.8	165.2	159.3	156.1	155.6	156.1
77.5°	204.9	196.0	174.9	152.6	137.8	126.4	118.3	116.2	112.6	112.7	112.2
80°	154.0	148.1	134.8	117.1	104.8	95.1	90.9	87.1	86.1	84.4	86.1
82.5°	111.6	105.4	96.3	85.0	74.9	69.1	64.8	63.6	63.0	62.3	62.6
85°	55.1	55.6	50.2	41.7	37.4	34.2	31.5	31.5	31.0	30.5	31.0
87.5°	20.0	19.0	17.1	15.7	13.4	12.0	11.4	11.6	10.5	10.2	10.9
90°	5.9	5.1	4.4	3.6	2.9	2.1	1.3	0.5	1.3	2.1	2.9
92.5°	15.6	14.7	13.9	13.2	12.6	12.0	11.5	10.9	11.5	12.0	12.6
95°	32.8	31.8	30.8	30.2	29.9	29.8	29.5	29.4	29.5	29.8	29.9
97.5°	52.6	51.3	49.8	49.1	49.0	49.0	48.9	48.8	48.9	49.0	49.0
100°	66.5	65.2	63.9	63.3	63.3	63.3	63.3	63.3	63.3	63.3	63.3
102.5°	82.3	81.6	81.0	80.4	80.0	79.6	79.2	78.8	79.2	79.6	80.0
105°	106.8	106.2	105.6	105.0	104.6	104.0	103.5	103.1	103.5	104.0	104.6
107.5°	133.2	132.8	132.3	131.8	131.3	130.8	130.3	129.8	130.3	130.8	131.3
110°	151.2	150.9	150.7	150.3	149.7	149.2	148.7	148.2	148.7	149.2	149.7





TEST NUMBER: P333260-927

CATALOG NUMBER: S125DIP-S1090D590U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	169.1	168.8	168.4	168.1	167.8	167.5	167.3	167.0	167.3	167.5	167.8
115°	197.1	196.9	196.7	196.4	196.0	195.6	195.2	194.8	195.2	195.6	196.0
117.5°	223.9	223.7	223.6	223.3	223.2	223.0	222.8	222.6	222.8	223.0	223.2
120°	242.5	242.4	242.2	242.0	241.5	241.0	240.5	240.0	240.5	241.0	241.5
122.5°	260.2	260.0	259.7	259.5	259.3	259.1	259.0	258.8	259.0	259.1	259.3
125°	287.2	287.1	287.0	286.7	286.1	285.4	284.9	284.2	284.9	285.4	286.1
127.5°	313.2	313.1	313.0	312.8	312.4	312.0	311.7	311.4	311.7	312.0	312.4
130°	330.4	330.2	330.0	329.6	329.2	328.7	328.1	327.6	328.1	328.7	329.2
132.5°	347.5	347.5	347.6	347.2	346.3	345.5	344.8	343.9	344.8	345.5	346.3
135°	372.6	372.6	372.4	372.1	371.5	370.9	370.3	369.6	370.3	370.9	371.5
137.5°	397.0	396.9	396.6	396.2	395.6	395.1	394.5	393.9	394.5	395.1	395.6
140°	412.5	412.2	411.9	411.5	410.9	410.4	410.0	409.4	410.0	410.4	410.9
142.5°	427.9	427.5	427.1	426.7	426.3	425.8	425.4	425.0	425.4	425.8	426.3
145°	450.4	450.1	449.8	449.5	449.1	448.7	448.2	447.8	448.2	448.7	449.1
147.5°	470.6	470.3	470.1	469.9	469.7	469.4	469.2	469.0	469.2	469.4	469.7
150°	483.6	483.2	482.8	482.7	482.8	482.9	483.0	483.1	483.0	482.9	482.8
152.5°	495.7	495.5	495.4	495.2	495.1	495.0	494.8	494.6	494.8	495.0	495.1
155°	512.7	512.6	512.5	512.5	512.5	512.5	512.5	512.5	512.5	512.5	512.5
157.5°	527.7	527.5	527.4	527.5	527.8	527.9	528.1	528.4	528.1	527.9	527.8
160°	536.7	536.5	536.5	536.5	536.9	537.2	537.5	537.8	537.5	537.2	536.9
162.5°	545.2	545.1	545.1	545.2	545.4	545.7	545.9	546.1	545.9	545.7	545.4
165°	556.6	556.4	556.3	556.4	556.6	556.8	557.0	557.2	557.0	556.8	556.6
167.5°	564.8	564.8	564.8	565.0	565.4	565.8	566.3	566.6	566.3	565.8	565.4
170°	569.9	569.9	569.9	570.1	570.5	570.8	571.2	571.6	571.2	570.8	570.5
172.5°	573.5	573.5	573.5	573.7	574.1	574.5	574.9	575.3	574.9	574.5	574.1
175°	577.6	577.6	577.6	577.7	578.1	578.5	578.9	579.3	578.9	578.5	578.1
177.5°	579.8	579.9	580.0	580.1	580.5	580.8	581.1	581.5	581.1	580.8	580.5
180°	580.7	580.7	580.7	580.7	580.7	580.7	580.7	580.7	580.7	580.7	580.7



TEST NUMBER: P333260-927

CATALOG NUMBER: S125DIP-S1090D590U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7
2.5°	1237.9	1233.2	1229.3	1220.8	1216.1	1209.7	1204.5	1210.1	1204.1	1206.7	1202.8
5°	1199.3	1184.3	1173.6	1158.1	1144.8	1132.4	1123.4	1121.7	1117.5	1115.3	1108.9
7.5°	1152.9	1134.2	1115.8	1095.4	1078.3	1060.9	1049.8	1040.6	1034.5	1026.5	1021.0
10°	1125.5	1100.3	1079.0	1054.4	1033.0	1014.3	999.3	991.8	984.9	974.7	971.0
12.5°	1091.7	1065.7	1039.7	1013.4	992.8	971.9	959.1	947.8	942.9	931.5	930.3
15°	1051.2	1012.2	986.5	959.7	931.4	914.3	903.6	891.3	886.0	878.0	872.0
17.5°	1002.8	968.0	935.9	908.2	883.9	869.5	856.3	847.8	838.6	833.4	823.7
20°	967.8	934.6	902.5	873.1	854.4	837.8	827.1	819.1	809.5	806.8	797.3
22.5°	938.3	901.7	870.9	846.2	825.8	807.1	795.5	790.0	783.4	775.2	773.2
25°	890.3	852.3	826.1	801.5	783.3	766.2	758.2	751.2	744.8	738.9	736.8
27.5°	848.7	814.8	783.7	761.5	745.7	730.1	723.0	714.5	709.9	705.1	699.3
30°	819.7	784.9	757.6	736.3	719.1	705.3	697.8	691.9	687.6	683.3	680.1
32.5°	789.7	757.6	731.1	710.2	693.1	682.5	676.0	671.8	667.1	661.9	657.9
35°	750.2	714.9	689.2	671.1	657.7	649.7	642.1	638.4	633.0	633.0	628.8
37.5°	705.6	675.1	652.4	635.9	623.8	616.7	608.6	606.0	602.6	600.3	598.8
40°	679.1	650.7	629.3	612.8	599.9	594.1	587.6	583.4	581.2	578.5	577.4
42.5°	651.6	624.6	604.1	588.8	577.7	572.7	566.6	563.6	559.4	555.9	555.2
45°	610.1	583.8	565.1	552.9	543.2	537.3	533.6	527.2	525.1	520.8	520.2
47.5°	570.6	545.5	527.1	517.1	508.6	503.7	497.9	491.5	489.0	486.9	486.6
50°	541.1	518.1	501.0	491.4	483.4	476.4	470.6	466.3	464.6	464.6	465.7
52.5°	511.2	491.5	477.1	465.2	457.7	450.3	444.9	442.3	439.8	442.4	444.3
55°	467.3	447.5	436.8	425.6	418.1	409.6	406.9	405.8	404.3	408.5	410.7
57.5°	420.9	407.0	394.5	383.3	376.6	371.7	368.0	367.4	370.4	372.5	379.4
60°	391.4	375.3	364.1	355.5	347.5	344.4	343.3	342.2	344.4	350.2	359.3
62.5°	358.9	345.9	333.7	327.3	321.5	316.1	315.9	316.6	320.8	327.6	336.6
65°	311.2	299.9	291.9	284.5	279.6	276.4	277.5	279.6	284.5	293.5	303.7
67.5°	262.8	255.1	247.9	241.8	237.2	237.2	238.3	241.5	247.2	257.6	266.9
70°	231.6	223.0	217.1	214.4	210.6	208.5	211.8	217.1	221.9	231.6	239.6
72.5°	200.3	193.1	188.5	186.6	185.0	183.3	184.3	190.1	196.6	206.3	215.6
75°	154.0	151.3	148.1	146.0	144.3	145.4	146.5	151.9	157.2	167.4	178.1
77.5°	112.4	109.6	107.7	107.2	106.3	106.9	109.8	113.8	119.0	126.4	134.5
80°	85.0	84.0	82.9	82.3	82.3	82.9	87.1	89.8	94.7	101.6	108.0
82.5°	61.9	61.2	61.1	60.9	61.4	61.5	64.1	67.6	71.5	76.8	82.3
85°	32.6	31.5	33.1	33.7	32.6	34.2	35.3	37.4	39.1	41.7	44.4
87.5°	11.4	12.4	12.1	12.7	12.8	13.9	13.5	15.4	16.3	17.3	16.9
90°	3.6	4.4	5.1	5.9	6.5	7.2	7.8	8.2	8.7	9.3	9.7
92.5°	13.2	13.9	14.7	15.6	16.5	17.3	18.0	18.7	19.3	20.0	20.4
95°	30.2	30.8	31.8	32.8	33.8	34.8	35.5	36.2	36.9	37.6	38.0
97.5°	49.1	49.8	51.3	52.6	54.0	55.4	56.1	56.7	57.4	58.1	58.5
100°	63.3	63.9	65.2	66.5	67.8	69.2	70.0	71.0	71.9	72.7	73.3
102.5°	80.4	81.0	81.6	82.3	82.9	83.6	84.6	85.6	86.6	87.5	88.2
105°	105.0	105.6	106.2	106.8	107.4	108.0	108.6	109.2	109.8	110.4	110.9
107.5°	131.8	132.3	132.8	133.2	133.6	134.1	134.4	134.8	135.1	135.3	135.5
110°	150.3	150.7	150.9	151.2	151.5	151.9	152.2	152.4	152.7	153.0	153.1



TEST NUMBER: P333260-927

CATALOG NUMBER: S125DIP-S1090D590U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	168.1	168.4	168.8	169.1	169.5	169.9	170.1	170.2	170.3	170.5	170.5
115°	196.4	196.7	196.9	197.1	197.3	197.5	197.4	197.3	197.2	197.1	197.0
117.5°	223.3	223.6	223.7	223.9	224.0	224.3	224.3	224.4	224.5	224.6	224.4
120°	242.0	242.2	242.4	242.5	242.6	242.6	242.6	242.6	242.6	242.6	242.5
122.5°	259.5	259.7	260.0	260.2	260.5	260.8	260.7	260.6	260.5	260.5	260.2
125°	286.7	287.0	287.1	287.2	287.3	287.4	287.2	287.0	286.8	286.6	286.5
127.5°	312.8	313.0	313.1	313.2	313.3	313.5	313.4	313.2	313.1	313.1	312.9
130°	329.6	330.0	330.2	330.4	330.6	330.8	330.7	330.6	330.5	330.4	330.3
132.5°	347.2	347.6	347.5	347.5	347.5	347.5	347.4	347.2	347.1	347.1	346.8
135°	372.1	372.4	372.6	372.6	372.7	372.8	372.8	372.8	372.8	372.8	372.6
137.5°	396.2	396.6	396.9	397.0	397.3	397.5	397.6	397.8	397.8	398.0	397.8
140°	411.5	411.9	412.2	412.5	412.7	413.0	413.3	413.4	413.7	413.8	413.7
142.5°	426.7	427.1	427.5	427.9	428.3	428.6	428.7	428.8	429.0	429.0	428.9
145°	449.5	449.8	450.1	450.4	450.8	451.0	451.0	451.0	451.0	451.0	450.8
147.5°	469.9	470.1	470.3	470.6	470.9	471.1	471.3	471.6	471.8	472.1	471.8
150°	482.7	482.8	483.2	483.6	484.0	484.4	484.4	484.4	484.4	484.4	484.3
152.5°	495.2	495.4	495.5	495.7	495.8	496.1	496.3	496.5	496.8	497.0	496.9
155°	512.5	512.5	512.6	512.7	512.9	512.9	513.3	513.7	514.1	514.5	514.5
157.5°	527.5	527.4	527.5	527.7	527.8	527.8	528.2	528.6	529.0	529.4	529.3
160°	536.5	536.5	536.5	536.7	536.8	536.9	537.3	537.7	538.1	538.4	538.4
162.5°	545.2	545.1	545.1	545.2	545.2	545.2	545.7	546.1	546.6	547.2	547.1
165°	556.4	556.3	556.4	556.6	556.7	556.7	557.1	557.5	557.9	558.4	558.3
167.5°	565.0	564.8	564.8	564.8	564.8	564.8	565.4	566.0	566.6	567.2	567.2
170°	570.1	569.9	569.9	569.9	569.9	569.9	570.5	571.1	571.6	572.3	572.2
172.5°	573.7	573.5	573.5	573.5	573.5	573.5	574.1	574.7	575.3	575.9	575.9
175°	577.7	577.6	577.6	577.6	577.6	577.6	578.1	578.8	579.3	580.0	579.9
177.5°	580.1	580.0	579.9	579.8	579.7	579.6	580.1	580.6	581.1	581.5	581.5
180°	580.7	580.7	580.7	580.7	580.7	580.7	580.7	580.7	580.7	580.7	580.7



TEST NUMBER: P333260-927

CATALOG NUMBER: S125DIP-S1090D590U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7
2.5°	1200.2	1203.2	1200.7	1204.1	1200.7	1203.2	1200.2	1202.8	1206.7	1204.1	1210.1
5°	1106.3	1101.5	1104.6	1102.5	1104.6	1101.5	1106.3	1108.9	1115.3	1117.5	1121.7
7.5°	1019.5	1014.9	1009.6	1007.1	1009.6	1014.9	1019.5	1021.0	1026.5	1034.5	1040.6
10°	965.1	959.3	958.7	955.0	958.7	959.3	965.1	971.0	974.7	984.9	991.8
12.5°	925.3	919.9	913.8	912.2	913.8	919.9	925.3	930.3	931.5	942.9	947.8
15°	868.9	864.6	860.9	864.0	860.9	864.6	868.9	872.0	878.0	886.0	891.3
17.5°	821.9	818.4	817.8	813.8	817.8	818.4	821.9	823.7	833.4	838.6	847.8
20°	792.4	789.7	790.8	783.9	790.8	789.7	792.4	797.3	806.8	809.5	819.1
22.5°	768.9	763.7	763.0	761.6	763.0	763.7	768.9	773.2	775.2	783.4	790.0
25°	732.0	729.3	726.7	729.3	726.7	729.3	732.0	736.8	738.9	744.8	751.2
27.5°	699.8	696.6	695.9	696.2	695.9	696.6	699.8	699.3	705.1	709.9	714.5
30°	680.1	674.8	675.3	674.8	675.3	674.8	680.1	680.1	683.3	687.6	691.9
32.5°	658.7	655.1	654.3	653.4	654.3	655.1	658.7	657.9	661.9	667.1	671.8
35°	627.2	627.2	624.5	624.5	624.5	627.2	627.2	628.8	633.0	633.0	638.4
37.5°	597.5	597.0	595.4	595.6	595.4	597.0	597.5	598.8	600.3	602.6	606.0
40°	575.3	574.8	573.1	570.0	573.1	574.8	575.3	577.4	578.5	581.2	583.4
42.5°	553.9	552.2	551.4	550.3	551.4	552.2	553.9	555.2	555.9	559.4	563.6
45°	520.2	520.2	519.2	518.6	519.2	520.2	520.2	520.2	520.8	525.1	527.2
47.5°	487.5	488.5	490.5	490.2	490.5	488.5	487.5	486.6	486.9	489.0	491.5
50°	467.9	468.4	470.0	470.6	470.0	468.4	467.9	465.7	464.6	464.6	466.3
52.5°	446.0	449.2	451.1	450.8	451.1	449.2	446.0	444.3	442.4	439.8	442.3
55°	415.4	419.2	422.9	423.5	422.9	419.2	415.4	410.7	408.5	404.3	405.8
57.5°	385.2	390.4	394.3	395.7	394.3	390.4	385.2	379.4	372.5	370.4	367.4
60°	364.6	371.6	376.4	378.6	376.4	371.6	364.6	359.3	350.2	344.4	342.2
62.5°	345.0	352.8	357.6	358.0	357.6	352.8	345.0	336.6	327.6	320.8	316.6
65°	312.8	320.8	325.1	328.3	325.1	320.8	312.8	303.7	293.5	284.5	279.6
67.5°	278.1	286.1	290.9	293.4	290.9	286.1	278.1	266.9	257.6	247.2	241.5
70°	252.9	260.9	267.4	269.5	267.4	260.9	252.9	239.6	231.6	221.9	217.1
72.5°	228.1	235.3	240.4	243.0	240.4	235.3	228.1	215.6	206.3	196.6	190.1
75°	185.0	194.6	199.5	202.1	199.5	194.6	185.0	178.1	167.4	157.2	151.9
77.5°	142.7	151.4	154.3	155.7	154.3	151.4	142.7	134.5	126.4	119.0	113.8
80°	114.4	119.8	123.5	124.1	123.5	119.8	114.4	108.0	101.6	94.7	89.8
82.5°	87.9	92.4	93.6	95.0	93.6	92.4	87.9	82.3	76.8	71.5	67.6
85°	48.1	50.2	50.8	50.2	50.8	50.2	48.1	44.4	41.7	39.1	37.4
87.5°	17.8	17.4	17.5	18.5	17.5	17.4	17.8	16.9	17.3	16.3	15.4
90°	10.0	10.2	10.5	10.9	10.5	10.2	10.0	9.7	9.3	8.7	8.2
92.5°	20.7	20.9	21.1	21.3	21.1	20.9	20.7	20.4	20.0	19.3	18.7
95°	38.3	38.5	38.7	38.9	38.7	38.5	38.3	38.0	37.6	36.9	36.2
97.5°	58.5	58.7	58.8	58.9	58.8	58.7	58.5	58.5	58.1	57.4	56.7
100°	73.5	73.8	73.9	74.1	73.9	73.8	73.5	73.3	72.7	71.9	71.0
102.5°	88.5	88.7	89.0	89.3	89.0	88.7	88.5	88.2	87.5	86.6	85.6
105°	111.1	111.5	111.8	112.1	111.8	111.5	111.1	110.9	110.4	109.8	109.2
107.5°	135.5	135.5	135.4	135.4	135.4	135.5	135.5	135.5	135.3	135.1	134.8
110°	153.0	153.0	152.8	152.7	152.8	153.0	153.0	153.1	153.0	152.7	152.4



TEST NUMBER: P333260-927

CATALOG NUMBER: S125DIP-S1090D590U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	170.3	170.1	169.9	169.8	169.9	170.1	170.3	170.5	170.5	170.3	170.2
115°	196.9	196.8	196.7	196.6	196.7	196.8	196.9	197.0	197.1	197.2	197.3
117.5°	224.0	223.6	223.2	222.8	223.2	223.6	224.0	224.4	224.6	224.5	224.4
120°	242.1	241.7	241.3	240.9	241.3	241.7	242.1	242.5	242.6	242.6	242.6
122.5°	259.9	259.6	259.3	259.0	259.3	259.6	259.9	260.2	260.5	260.5	260.6
125°	286.4	286.3	286.1	286.1	286.1	286.3	286.4	286.5	286.6	286.8	287.0
127.5°	312.7	312.5	312.3	312.1	312.3	312.5	312.7	312.9	313.1	313.1	313.2
130°	330.0	329.9	329.6	329.5	329.6	329.9	330.0	330.3	330.4	330.5	330.6
132.5°	346.6	346.3	346.0	345.7	346.0	346.3	346.6	346.8	347.1	347.1	347.2
135°	372.2	371.9	371.5	371.1	371.5	371.9	372.2	372.6	372.8	372.8	372.8
137.5°	397.3	396.8	396.3	395.8	396.3	396.8	397.3	397.8	398.0	397.8	397.8
140°	413.2	412.7	412.2	411.7	412.2	412.7	413.2	413.7	413.8	413.7	413.4
142.5°	428.4	427.9	427.4	426.9	427.4	427.9	428.4	428.9	429.0	429.0	428.8
145°	450.6	450.3	450.0	449.6	450.0	450.3	450.6	450.8	451.0	451.0	451.0
147.5°	471.1	470.5	469.8	469.1	469.8	470.5	471.1	471.8	472.1	471.8	471.6
150°	484.2	483.9	483.8	483.5	483.8	483.9	484.2	484.3	484.4	484.4	484.4
152.5°	496.5	496.2	495.8	495.5	495.8	496.2	496.5	496.9	497.0	496.8	496.5
155°	514.0	513.5	512.9	512.5	512.9	513.5	514.0	514.5	514.5	514.1	513.7
157.5°	528.6	528.0	527.4	526.6	527.4	528.0	528.6	529.3	529.4	529.0	528.6
160°	538.0	537.4	536.9	536.5	536.9	537.4	538.0	538.4	538.4	538.1	537.7
162.5°	546.5	545.9	545.3	544.7	545.3	545.9	546.5	547.1	547.2	546.6	546.1
165°	557.7	557.1	556.4	555.9	556.4	557.1	557.7	558.3	558.4	557.9	557.5
167.5°	566.6	565.9	565.3	564.7	565.3	565.9	566.6	567.2	567.2	566.6	566.0
170°	571.6	570.8	570.1	569.4	570.1	570.8	571.6	572.2	572.3	571.6	571.1
172.5°	575.3	574.6	574.0	573.4	574.0	574.6	575.3	575.9	575.9	575.3	574.7
175°	579.2	578.5	577.8	577.1	577.8	578.5	579.2	579.9	580.0	579.3	578.8
177.5°	581.0	580.4	579.8	579.2	579.8	580.4	581.0	581.5	581.5	581.1	580.6
180°	580.7	580.7	580.7	580.7	580.7	580.7	580.7	580.7	580.7	580.7	580.7



TEST NUMBER: P333260-927

CATALOG NUMBER: S125DIP-S1090D590U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7
2.5°	1204.5	1209.7	1216.1	1220.8	1229.3	1233.2	1237.9	1241.7	1248.6	1255.0	1262.7
5°	1123.4	1132.4	1144.8	1158.1	1173.6	1184.3	1199.3	1208.4	1226.5	1243.2	1259.2
7.5°	1049.8	1060.9	1078.3	1095.4	1115.8	1134.2	1152.9	1173.6	1196.8	1224.2	1246.9
10°	999.3	1014.3	1033.0	1054.4	1079.0	1100.3	1125.5	1148.0	1176.3	1208.4	1238.3
12.5°	959.1	971.9	992.8	1013.4	1039.7	1065.7	1091.7	1121.4	1154.5	1190.0	1227.6
15°	903.6	914.3	931.4	959.7	986.5	1012.2	1051.2	1079.0	1120.7	1160.2	1205.7
17.5°	856.3	869.5	883.9	908.2	935.9	968.0	1002.8	1037.7	1077.9	1128.1	1179.3
20°	827.1	837.8	854.4	873.1	902.5	934.6	967.8	1003.1	1052.3	1104.1	1159.2
22.5°	795.5	807.1	825.8	846.2	870.9	901.7	938.3	977.0	1028.3	1079.3	1139.1
25°	758.2	766.2	783.3	801.5	826.1	852.3	890.3	933.0	983.8	1042.1	1103.0
27.5°	723.0	730.1	745.7	761.5	783.7	814.8	848.7	892.0	939.8	998.9	1066.5
30°	697.8	705.3	719.1	736.3	757.6	784.9	819.7	860.3	911.6	969.4	1040.0
32.5°	676.0	682.5	693.1	710.2	731.1	757.6	789.7	831.2	882.6	941.1	1010.4
35°	642.1	649.7	657.7	671.1	689.2	714.9	750.2	789.2	838.4	895.1	958.7
37.5°	608.6	616.7	623.8	635.9	652.4	675.1	705.6	746.2	790.7	845.3	906.4
40°	587.6	594.1	599.9	612.8	629.3	650.7	679.1	715.4	762.5	813.3	864.0
42.5°	566.6	572.7	577.7	588.8	604.1	624.6	651.6	687.1	730.8	778.2	823.0
45°	533.6	537.3	543.2	552.9	565.1	583.8	610.1	641.6	678.5	723.4	757.1
47.5°	497.9	503.7	508.6	517.1	527.1	545.5	570.6	597.5	630.9	664.3	688.0
50°	470.6	476.4	483.4	491.4	501.0	518.1	541.1	568.4	596.7	622.3	642.7
52.5°	444.9	450.3	457.7	465.2	477.1	491.5	511.2	535.4	563.3	581.7	598.7
55°	406.9	409.6	418.1	425.6	436.8	447.5	467.3	488.7	505.8	519.8	533.6
57.5°	368.0	371.7	376.6	383.3	394.5	407.0	420.9	439.8	449.9	457.0	467.9
60°	343.3	344.4	347.5	355.5	364.1	375.3	391.4	404.7	412.3	418.1	427.2
62.5°	315.9	316.1	321.5	327.3	333.7	345.9	358.9	369.7	375.9	378.7	387.5
65°	277.5	276.4	279.6	284.5	291.9	299.9	311.2	320.8	320.3	323.4	328.8
67.5°	238.3	237.2	237.2	241.8	247.9	255.1	262.8	268.3	268.4	272.7	275.4
70°	211.8	208.5	210.6	214.4	217.1	223.0	231.6	233.7	234.2	236.3	239.0
72.5°	184.3	183.3	185.0	186.6	188.5	193.1	200.3	201.6	201.7	203.0	207.3
75°	146.5	145.4	144.3	146.0	148.1	151.3	154.0	156.1	155.6	156.1	159.3
77.5°	109.8	106.9	106.3	107.2	107.7	109.6	112.4	112.2	112.7	112.6	116.2
80°	87.1	82.9	82.3	82.3	82.9	84.0	85.0	86.1	84.4	86.1	87.1
82.5°	64.1	61.5	61.4	60.9	61.1	61.2	61.9	62.6	62.3	63.0	63.6
85°	35.3	34.2	32.6	33.7	33.1	31.5	32.6	31.0	30.5	31.0	31.5
87.5°	13.5	13.9	12.8	12.7	12.1	12.4	11.4	10.9	10.2	10.5	11.6
90°	7.8	7.2	6.5	5.9	5.1	4.4	3.6	2.9	2.1	1.3	0.5
92.5°	18.0	17.3	16.5	15.6	14.7	13.9	13.2	12.6	12.0	11.5	10.9
95°	35.5	34.8	33.8	32.8	31.8	30.8	30.2	29.9	29.8	29.5	29.4
97.5°	56.1	55.4	54.0	52.6	51.3	49.8	49.1	49.0	49.0	48.9	48.8
100°	70.0	69.2	67.8	66.5	65.2	63.9	63.3	63.3	63.3	63.3	63.3
102.5°	84.6	83.6	82.9	82.3	81.6	81.0	80.4	80.0	79.6	79.2	78.8
105°	108.6	108.0	107.4	106.8	106.2	105.6	105.0	104.6	104.0	103.5	103.1
107.5°	134.4	134.1	133.6	133.2	132.8	132.3	131.8	131.3	130.8	130.3	129.8
110°	152.2	151.9	151.5	151.2	150.9	150.7	150.3	149.7	149.2	148.7	148.2



TEST NUMBER: P333260-927

CATALOG NUMBER: S125DIP-S1090D590U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	170.1	169.9	169.5	169.1	168.8	168.4	168.1	167.8	167.5	167.3	167.0
115°	197.4	197.5	197.3	197.1	196.9	196.7	196.4	196.0	195.6	195.2	194.8
117.5°	224.3	224.3	224.0	223.9	223.7	223.6	223.3	223.2	223.0	222.8	222.6
120°	242.6	242.6	242.6	242.5	242.4	242.2	242.0	241.5	241.0	240.5	240.0
122.5°	260.7	260.8	260.5	260.2	260.0	259.7	259.5	259.3	259.1	259.0	258.8
125°	287.2	287.4	287.3	287.2	287.1	287.0	286.7	286.1	285.4	284.9	284.2
127.5°	313.4	313.5	313.3	313.2	313.1	313.0	312.8	312.4	312.0	311.7	311.4
130°	330.7	330.8	330.6	330.4	330.2	330.0	329.6	329.2	328.7	328.1	327.6
132.5°	347.4	347.5	347.5	347.5	347.5	347.6	347.2	346.3	345.5	344.8	343.9
135°	372.8	372.8	372.7	372.6	372.6	372.4	372.1	371.5	370.9	370.3	369.6
137.5°	397.6	397.5	397.3	397.0	396.9	396.6	396.2	395.6	395.1	394.5	393.9
140°	413.3	413.0	412.7	412.5	412.2	411.9	411.5	410.9	410.4	410.0	409.4
142.5°	428.7	428.6	428.3	427.9	427.5	427.1	426.7	426.3	425.8	425.4	425.0
145°	451.0	451.0	450.8	450.4	450.1	449.8	449.5	449.1	448.7	448.2	447.8
147.5°	471.3	471.1	470.9	470.6	470.3	470.1	469.9	469.7	469.4	469.2	469.0
150°	484.4	484.4	484.0	483.6	483.2	482.8	482.7	482.8	482.9	483.0	483.1
152.5°	496.3	496.1	495.8	495.7	495.5	495.4	495.2	495.1	495.0	494.8	494.6
155°	513.3	512.9	512.9	512.7	512.6	512.5	512.5	512.5	512.5	512.5	512.5
157.5°	528.2	527.8	527.8	527.7	527.5	527.4	527.5	527.8	527.9	528.1	528.4
160°	537.3	536.9	536.8	536.7	536.5	536.5	536.5	536.9	537.2	537.5	537.8
162.5°	545.7	545.2	545.2	545.2	545.1	545.1	545.2	545.4	545.7	545.9	546.1
165°	557.1	556.7	556.7	556.6	556.4	556.3	556.4	556.6	556.8	557.0	557.2
167.5°	565.4	564.8	564.8	564.8	564.8	564.8	565.0	565.4	565.8	566.3	566.6
170°	570.5	569.9	569.9	569.9	569.9	569.9	570.1	570.5	570.8	571.2	571.6
172.5°	574.1	573.5	573.5	573.5	573.5	573.5	573.7	574.1	574.5	574.9	575.3
175°	578.1	577.6	577.6	577.6	577.6	577.6	577.7	578.1	578.5	578.9	579.3
177.5°	580.1	579.6	579.7	579.8	579.9	580.0	580.1	580.5	580.8	581.1	581.5
180°	580.7	580.7	580.7	580.7	580.7	580.7	580.7	580.7	580.7	580.7	580.7



TEST NUMBER: P333260-927

CATALOG NUMBER: S125DIP-S1090D590U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7
2.5°	1266.5	1272.6	1276.4	1283.7	1289.7	1293.1	1296.1	1298.6	1301.6	1304.2	1311.5
5°	1274.7	1288.6	1300.4	1318.5	1335.1	1348.0	1361.8	1374.1	1384.3	1398.8	1409.9
7.5°	1271.1	1295.9	1321.8	1349.9	1378.6	1405.3	1430.0	1452.9	1473.8	1499.0	1521.1
10°	1267.7	1301.4	1334.6	1372.5	1411.6	1444.7	1475.8	1507.3	1530.3	1562.3	1589.6
12.5°	1265.2	1304.8	1344.8	1390.5	1433.4	1480.2	1521.5	1544.5	1579.5	1605.1	1637.5
15°	1254.3	1306.8	1361.8	1413.2	1474.1	1517.4	1553.8	1598.7	1631.3	1663.9	1699.2
17.5°	1235.0	1294.3	1356.0	1423.2	1481.7	1528.2	1575.1	1618.3	1657.3	1701.1	1745.0
20°	1226.1	1285.4	1356.0	1424.9	1482.2	1530.8	1578.9	1626.5	1669.3	1725.5	1776.2
22.5°	1207.2	1279.0	1344.0	1411.3	1470.1	1523.1	1577.6	1631.7	1688.5	1751.9	1815.6
25°	1173.6	1246.3	1315.3	1381.6	1441.0	1507.3	1565.6	1637.8	1710.5	1794.4	1873.5
27.5°	1138.8	1208.4	1271.6	1335.6	1404.9	1479.9	1555.5	1637.4	1732.6	1838.6	1950.2
30°	1110.6	1176.3	1237.8	1303.5	1375.7	1460.2	1543.1	1640.4	1750.6	1869.8	2002.4
32.5°	1077.6	1138.2	1198.0	1267.7	1346.2	1435.4	1532.0	1638.7	1771.1	1906.5	2043.0
35°	1021.3	1072.1	1133.5	1207.8	1296.6	1398.8	1510.5	1636.6	1788.5	1944.1	2059.0
37.5°	954.4	1001.7	1066.5	1148.0	1241.0	1350.6	1483.2	1632.9	1794.2	1918.3	1955.3
40°	909.5	953.3	1020.7	1105.2	1200.4	1316.4	1461.8	1620.1	1776.2	1855.4	1824.9
42.5°	861.6	907.6	973.2	1056.9	1159.3	1285.6	1434.9	1593.2	1724.0	1754.0	1648.6
45°	786.0	833.5	898.3	982.8	1092.9	1229.8	1385.4	1529.2	1604.6	1550.6	1387.5
47.5°	715.7	760.3	820.3	907.4	1021.1	1162.7	1312.6	1427.3	1433.3	1304.4	1130.2
50°	667.8	709.0	769.4	856.6	969.4	1112.7	1247.9	1338.3	1297.7	1151.7	984.4
52.5°	620.8	661.1	720.6	806.9	918.5	1049.8	1175.7	1239.1	1162.5	1012.7	869.7
55°	552.9	588.1	646.4	726.1	831.9	953.9	1060.8	1082.8	983.3	835.7	719.7
57.5°	486.6	519.5	572.5	645.9	742.7	850.6	934.3	929.6	824.5	697.8	605.8
60°	441.6	473.7	520.8	592.4	680.6	773.7	845.3	828.2	724.0	614.9	537.3
62.5°	401.5	430.1	474.6	537.3	617.7	703.9	762.8	737.5	635.4	540.0	478.8
65°	342.2	366.2	404.3	457.7	524.5	595.6	641.1	608.5	521.3	447.0	397.8
67.5°	285.7	304.9	336.8	379.4	436.4	493.5	521.2	488.4	418.7	364.4	328.0
70°	249.7	266.8	291.4	329.4	379.1	427.2	448.1	418.7	358.8	312.3	286.1
72.5°	213.7	227.9	249.5	283.6	323.4	365.2	383.5	355.4	306.2	266.9	242.4
75°	165.2	174.8	189.8	213.3	244.9	278.1	288.2	263.6	232.0	202.6	186.6
77.5°	118.3	126.4	137.8	152.6	174.9	196.0	204.9	190.7	166.3	147.7	134.5
80°	90.9	95.1	104.8	117.1	134.8	148.1	154.0	144.9	127.8	113.9	103.7
82.5°	64.8	69.1	74.9	85.0	96.3	105.4	111.6	105.5	93.2	82.2	76.4
85°	31.5	34.2	37.4	41.7	50.2	55.6	55.1	51.3	46.5	42.2	39.1
87.5°	11.4	12.0	13.4	15.7	17.1	19.0	20.0	19.3	17.7	16.6	15.4
90°	1.3	2.1	2.9	3.6	4.4	5.1	5.9	6.5	7.2	7.8	8.2
92.5°	11.5	12.0	12.6	13.2	13.9	14.7	15.6	16.5	17.3	18.0	18.7
95°	29.5	29.8	29.9	30.2	30.8	31.8	32.8	33.8	34.8	35.5	36.2
97.5°	48.9	49.0	49.0	49.1	49.8	51.3	52.6	54.0	55.4	56.1	56.7
100°	63.3	63.3	63.3	63.3	63.9	65.2	66.5	67.8	69.2	70.0	71.0
102.5°	79.2	79.6	80.0	80.4	81.0	81.6	82.3	82.9	83.6	84.6	85.6
105°	103.5	104.0	104.6	105.0	105.6	106.2	106.8	107.4	108.0	108.6	109.2
107.5°	130.3	130.8	131.3	131.8	132.3	132.8	133.2	133.6	134.1	134.4	134.8
110°	148.7	149.2	149.7	150.3	150.7	150.9	151.2	151.5	151.9	152.2	152.4





TEST NUMBER: P333260-927

CATALOG NUMBER: S125DIP-S1090D590U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	167.3	167.5	167.8	168.1	168.4	168.8	169.1	169.5	169.9	170.1	170.2
115°	195.2	195.6	196.0	196.4	196.7	196.9	197.1	197.3	197.5	197.4	197.3
117.5°	222.8	223.0	223.2	223.3	223.6	223.7	223.9	224.0	224.3	224.3	224.4
120°	240.5	241.0	241.5	242.0	242.2	242.4	242.5	242.6	242.6	242.6	242.6
122.5°	259.0	259.1	259.3	259.5	259.7	260.0	260.2	260.5	260.8	260.7	260.6
125°	284.9	285.4	286.1	286.7	287.0	287.1	287.2	287.3	287.4	287.2	287.0
127.5°	311.7	312.0	312.4	312.8	313.0	313.1	313.2	313.3	313.5	313.4	313.2
130°	328.1	328.7	329.2	329.6	330.0	330.2	330.4	330.6	330.8	330.7	330.6
132.5°	344.8	345.5	346.3	347.2	347.6	347.5	347.5	347.5	347.5	347.4	347.2
135°	370.3	370.9	371.5	372.1	372.4	372.6	372.6	372.7	372.8	372.8	372.8
137.5°	394.5	395.1	395.6	396.2	396.6	396.9	397.0	397.3	397.5	397.6	397.8
140°	410.0	410.4	410.9	411.5	411.9	412.2	412.5	412.7	413.0	413.3	413.4
142.5°	425.4	425.8	426.3	426.7	427.1	427.5	427.9	428.3	428.6	428.7	428.8
145°	448.2	448.7	449.1	449.5	449.8	450.1	450.4	450.8	451.0	451.0	451.0
147.5°	469.2	469.4	469.7	469.9	470.1	470.3	470.6	470.9	471.1	471.3	471.6
150°	483.0	482.9	482.8	482.7	482.8	483.2	483.6	484.0	484.4	484.4	484.4
152.5°	494.8	495.0	495.1	495.2	495.4	495.5	495.7	495.8	496.1	496.3	496.5
155°	512.5	512.5	512.5	512.5	512.5	512.6	512.7	512.9	512.9	513.3	513.7
157.5°	528.1	527.9	527.8	527.5	527.4	527.5	527.7	527.8	527.8	528.2	528.6
160°	537.5	537.2	536.9	536.5	536.5	536.5	536.7	536.8	536.9	537.3	537.7
162.5°	545.9	545.7	545.4	545.2	545.1	545.1	545.2	545.2	545.2	545.7	546.1
165°	557.0	556.8	556.6	556.4	556.3	556.4	556.6	556.7	556.7	557.1	557.5
167.5°	566.3	565.8	565.4	565.0	564.8	564.8	564.8	564.8	564.8	565.4	566.0
170°	571.2	570.8	570.5	570.1	569.9	569.9	569.9	569.9	569.9	570.5	571.1
172.5°	574.9	574.5	574.1	573.7	573.5	573.5	573.5	573.5	573.5	574.1	574.7
175°	578.9	578.5	578.1	577.7	577.6	577.6	577.6	577.6	577.6	578.1	578.8
177.5°	581.1	580.8	580.5	580.1	580.0	579.9	579.8	579.7	579.6	580.1	580.6
180°	580.7	580.7	580.7	580.7	580.7	580.7	580.7	580.7	580.7	580.7	580.7



TEST NUMBER: P333260-927

CATALOG NUMBER: S125DIP-S1090D590U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7
2.5°	1317.5	1320.9	1328.2	1325.6	1329.0	1330.7	1332.5
5°	1423.9	1441.0	1448.4	1447.4	1458.6	1456.0	1453.3
7.5°	1544.0	1562.0	1572.1	1584.6	1591.9	1592.4	1598.7
10°	1612.1	1635.6	1645.2	1658.6	1667.1	1672.0	1671.4
12.5°	1664.3	1682.7	1704.2	1710.8	1722.4	1728.4	1726.2
15°	1727.0	1756.4	1778.9	1790.1	1804.6	1808.9	1814.7
17.5°	1783.0	1822.5	1848.7	1883.6	1896.7	1904.7	1900.0
20°	1825.4	1877.3	1903.5	1945.2	1968.2	1980.5	1976.2
22.5°	1875.5	1931.6	1980.1	2016.2	2051.1	2067.8	2071.2
25°	1961.2	2038.2	2109.3	2157.0	2200.2	2210.3	2232.8
27.5°	2057.1	2147.8	2223.9	2273.9	2304.1	2315.4	2322.4
30°	2117.3	2207.7	2264.9	2297.0	2306.6	2305.6	2304.5
32.5°	2146.9	2203.5	2214.5	2205.4	2183.4	2164.8	2145.4
35°	2105.1	2062.8	1999.7	1918.4	1858.5	1798.2	1792.2
37.5°	1893.2	1758.2	1653.1	1535.8	1468.2	1426.3	1397.5
40°	1693.8	1540.4	1413.2	1314.2	1245.3	1218.0	1191.3
42.5°	1477.4	1330.9	1218.1	1135.4	1083.6	1053.4	1032.1
45°	1200.4	1071.0	982.8	922.9	881.7	858.2	844.8
47.5°	983.6	887.9	812.9	769.8	741.3	723.0	723.1
50°	867.3	775.9	726.1	691.9	667.3	652.8	655.5
52.5°	764.1	695.9	653.4	624.7	606.6	597.7	597.4
55°	639.0	589.8	562.0	541.1	528.8	518.6	520.8
57.5°	546.5	505.1	486.5	469.1	460.6	456.5	450.6
60°	489.3	457.2	441.1	427.2	418.7	415.4	409.6
62.5°	438.3	413.1	397.5	386.1	378.4	377.4	372.8
65°	368.4	349.1	335.3	329.9	321.9	319.7	319.7
67.5°	303.7	289.9	279.1	274.2	270.7	271.2	268.6
70°	263.1	251.8	244.9	239.6	236.9	237.4	235.3
72.5°	230.1	217.6	211.5	208.3	204.8	206.2	205.3
75°	174.3	167.9	164.7	161.4	159.3	158.3	157.2
77.5°	128.0	122.3	119.9	118.0	118.4	115.8	117.9
80°	98.9	94.1	92.5	89.8	89.3	89.3	88.7
82.5°	72.4	69.7	68.5	66.3	65.4	66.2	64.8
85°	37.4	35.3	34.8	34.8	33.7	32.6	35.3
87.5°	15.4	13.9	13.9	13.5	13.6	13.2	12.4
90°	8.7	9.3	9.7	10.0	10.2	10.5	10.9
92.5°	19.3	20.0	20.4	20.7	20.9	21.1	21.3
95°	36.9	37.6	38.0	38.3	38.5	38.7	38.9
97.5°	57.4	58.1	58.5	58.5	58.7	58.8	58.9
100°	71.9	72.7	73.3	73.5	73.8	73.9	74.1
102.5°	86.6	87.5	88.2	88.5	88.7	89.0	89.3
105°	109.8	110.4	110.9	111.1	111.5	111.8	112.1
107.5°	135.1	135.3	135.5	135.5	135.5	135.4	135.4
110°	152.7	153.0	153.1	153.0	153.0	152.8	152.7



TEST NUMBER: P333260-927

CATALOG NUMBER: S125DIP-S1090D590U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	170.3	170.5	170.5	170.3	170.1	169.9	169.8
115°	197.2	197.1	197.0	196.9	196.8	196.7	196.6
117.5°	224.5	224.6	224.4	224.0	223.6	223.2	222.8
120°	242.6	242.6	242.5	242.1	241.7	241.3	240.9
122.5°	260.5	260.5	260.2	259.9	259.6	259.3	259.0
125°	286.8	286.6	286.5	286.4	286.3	286.1	286.1
127.5°	313.1	313.1	312.9	312.7	312.5	312.3	312.1
130°	330.5	330.4	330.3	330.0	329.9	329.6	329.5
132.5°	347.1	347.1	346.8	346.6	346.3	346.0	345.7
135°	372.8	372.8	372.6	372.2	371.9	371.5	371.1
137.5°	397.8	398.0	397.8	397.3	396.8	396.3	395.8
140°	413.7	413.8	413.7	413.2	412.7	412.2	411.7
142.5°	429.0	429.0	428.9	428.4	427.9	427.4	426.9
145°	451.0	451.0	450.8	450.6	450.3	450.0	449.6
147.5°	471.8	472.1	471.8	471.1	470.5	469.8	469.1
150°	484.4	484.4	484.3	484.2	483.9	483.8	483.5
152.5°	496.8	497.0	496.9	496.5	496.2	495.8	495.5
155°	514.1	514.5	514.5	514.0	513.5	512.9	512.5
157.5°	529.0	529.4	529.3	528.6	528.0	527.4	526.6
160°	538.1	538.4	538.4	538.0	537.4	536.9	536.5
162.5°	546.6	547.2	547.1	546.5	545.9	545.3	544.7
165°	557.9	558.4	558.3	557.7	557.1	556.4	555.9
167.5°	566.6	567.2	567.2	566.6	565.9	565.3	564.7
170°	571.6	572.3	572.2	571.6	570.8	570.1	569.4
172.5°	575.3	575.9	575.9	575.3	574.6	574.0	573.4
175°	579.3	580.0	579.9	579.2	578.5	577.8	577.1
177.5°	581.1	581.5	581.5	581.0	580.4	579.8	579.2
180°	580.7	580.7	580.7	580.7	580.7	580.7	580.7

(END OF REPORT)