

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332651

Luminaire Tested: **S124DIP-S1020D810U835-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332651
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIP-S1020D810U835-4F0-1E-UDD-F4
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 810 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7324.7 lumens
Efficiency: N/A
Efficacy: 134.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 54.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332651

CATALOG NUMBER: S124DIP-S1020D810U835-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P332651

CATALOG NUMBER: S124DIP-S1020D810U835-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	110	110	110	110	102	102	102	102	89	89	89	77	77	77	66	66	66	60																				
1	100	96	92	88	93	90	86	83	78	76	73	68	66	64	58	57	55	51																				
2	91	84	77	72	85	78	73	68	69	64	61	59	56	53	51	49	47	43																				
3	83	73	66	60	77	69	62	57	60	55	51	53	49	45	45	42	40	36																				
4	76	65	57	51	71	61	54	48	54	48	44	47	42	39	40	37	34	31																				
5	70	58	50	44	65	55	47	42	48	42	38	42	37	34	36	33	30	27																				
6	64	52	44	38	60	49	42	36	43	37	33	38	33	30	33	29	26	24																				
7	60	47	39	33	56	44	37	32	39	33	29	35	30	26	30	26	23	21																				
8	55	43	35	30	52	40	33	28	36	30	26	32	27	23	28	24	21	19																				
9	52	39	32	26	48	37	30	25	33	27	23	29	24	21	26	22	19	17																				
10	48	36	29	24	45	34	27	23	30	25	21	27	22	19	24	20	17	15																				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13930	13930	13930
5°	13972	13804	13904
10°	13884	13691	13759
15°	13717	13497	13531
20°	13493	13256	13268
25°	13239	12981	12944
30°	12928	12656	12541
35°	12604	12318	12154
40°	12269	11934	11715
45°	11918	11555	11334
50°	11531	11218	10870
55°	11112	10781	10431
60°	10693	10291	9978
65°	10222	9824	9429
70°	9692	9203	8844
75°	8883	8453	8238
80°	7908	7583	7392
85°	6919	6660	6530



TEST NUMBER: P332651

CATALOG NUMBER: S124DIP-S1020D810U835-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	162.5	2.2
10°-20°	457.8	6.3
20°-30°	673.9	9.2
30°-40°	783.4	10.7
40°-50°	783.4	10.7
50°-60°	685.3	9.4
60°-70°	508.9	6.9
70°-80°	289.1	3.9
80°-90°	85.6	1.2
90°-100°	287.5	3.9
100°-110°	598.3	8.2
110°-120°	535.9	7.3
120°-130°	450.8	6.2
130°-140°	375.9	5.1
140°-150°	287.1	3.9
150°-160°	201.8	2.8
160°-170°	118.7	1.6
170°-180°	38.6	0.5
0°-30°	1294.2	17.7
0°-40°	2077.6	28.4
0°-60°	3546.4	48.4
0°-90°	4430.1	60.5
90°-120°	1421.6	19.4
90°-150°	2535.4	34.6
90°-180°	2895.0	39.5
0°-180°	7324.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1726	1726	1726	1726	1726	
5°	1724	1718	1703	1718	1716	163
15°	1641	1635	1615	1622	1619	462
25°	1486	1476	1457	1458	1453	684
35°	1279	1269	1250	1240	1233	799
45°	1044	1034	1012	997	993	804
55°	790	784	766	750	741	707
65°	535	528	514	501	494	530
75°	285	278	271	266	264	303
85°	75	75	72	72	70	82
90°	1	6	14	16	16	5
95°	26	81	637	316	191	29
105°	92	133	513	1104	1100	98
115°	161	202	457	879	1056	160
125°	224	267	455	748	843	200
135°	267	317	451	664	754	206
145°	307	352	449	560	615	193
155°	350	377	436	494	515	161
165°	381	393	418	443	450	107
175°	397	398	401	407	405	38
180°	398	398	398	398	398	



TEST NUMBER: P332651

CATALOG NUMBER: S124DIP-S1020D810U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1725.5	1725.5	1725.5	1725.5	1725.5	1725.5	1725.5	1725.5	1725.5	1725.5	1725.5
2.5°	1729.9	1729.2	1728.4	1727.7	1727.0	1725.2	1722.5	1719.8	1717.1	1714.4	1716.9
5°	1724.1	1722.9	1721.7	1720.4	1719.2	1716.9	1713.5	1710.1	1706.8	1703.4	1706.8
7.5°	1708.1	1706.8	1705.6	1704.4	1703.2	1700.7	1696.9	1693.2	1689.4	1685.7	1688.4
10°	1693.7	1692.5	1691.2	1690.0	1688.8	1686.2	1682.2	1678.2	1674.2	1670.2	1672.6
12.5°	1674.9	1673.7	1672.4	1671.2	1670.0	1667.2	1663.0	1658.8	1654.5	1650.3	1653.0
15°	1641.2	1639.9	1638.7	1637.5	1636.2	1633.3	1628.7	1624.1	1619.5	1614.9	1616.7
17.5°	1600.5	1599.0	1597.4	1595.9	1594.4	1591.4	1587.0	1582.7	1578.3	1574.0	1575.1
20°	1570.6	1569.1	1567.6	1566.0	1564.5	1561.4	1556.8	1552.2	1547.6	1543.0	1543.9
22.5°	1538.6	1536.5	1534.5	1532.5	1530.5	1527.1	1522.5	1517.9	1513.3	1508.7	1510.4
25°	1486.3	1484.2	1482.0	1479.8	1477.7	1474.5	1470.2	1465.9	1461.6	1457.3	1457.6
27.5°	1426.6	1424.4	1422.1	1419.9	1417.7	1414.6	1410.6	1406.6	1402.6	1398.6	1397.9
30°	1386.8	1384.3	1381.8	1379.4	1376.9	1373.7	1369.7	1365.7	1361.7	1357.7	1356.5
32.5°	1344.7	1342.5	1340.3	1338.1	1335.9	1332.6	1328.4	1324.2	1319.9	1315.7	1314.2
35°	1278.9	1276.8	1274.6	1272.5	1270.3	1267.1	1262.8	1258.5	1254.2	1249.9	1247.7
37.5°	1209.5	1207.5	1205.6	1203.6	1201.6	1198.4	1193.7	1189.1	1184.5	1179.9	1177.6
40°	1164.2	1161.7	1159.2	1156.8	1154.3	1150.8	1146.2	1141.6	1137.0	1132.4	1129.3
42.5°	1115.5	1114.0	1112.5	1111.1	1109.6	1106.3	1101.2	1096.1	1091.0	1085.9	1082.3
45°	1043.9	1041.7	1039.6	1037.4	1035.3	1031.7	1026.8	1021.9	1017.0	1012.1	1008.7
47.5°	968.9	967.5	966.0	964.5	963.0	960.0	955.5	950.9	946.4	941.8	938.0
50°	918.1	916.8	915.6	914.4	913.1	910.4	906.1	901.8	897.5	893.2	888.9
52.5°	868.3	866.8	865.3	863.9	862.4	859.4	854.8	850.3	845.7	841.2	837.4
55°	789.5	788.5	787.6	786.7	785.8	783.2	778.9	774.6	770.3	766.0	762.3
57.5°	714.3	713.2	712.2	711.1	710.1	707.4	703.2	699.0	694.7	690.5	687.0
60°	662.3	660.7	659.2	657.7	656.1	653.4	649.4	645.4	641.4	637.4	634.6
62.5°	611.4	610.1	608.8	607.5	606.2	603.5	599.2	595.0	590.7	586.5	584.0
65°	535.1	533.5	532.0	530.5	528.9	526.6	523.5	520.5	517.4	514.3	511.3
67.5°	458.2	456.8	455.4	454.0	452.5	450.4	447.4	444.5	441.5	438.6	435.6
70°	410.6	408.5	406.3	404.2	402.0	399.7	397.3	394.8	392.4	389.9	387.4
72.5°	359.8	357.6	355.5	353.3	351.2	349.1	347.1	345.2	343.2	341.2	339.3
75°	284.8	283.3	281.7	280.2	278.7	277.1	275.6	274.1	272.5	271.0	269.8
77.5°	213.2	212.5	211.8	211.2	210.5	209.5	208.1	206.8	205.4	204.1	203.7
80°	170.1	169.1	168.2	167.3	166.4	165.6	165.0	164.4	163.8	163.1	162.5
82.5°	128.0	127.6	127.2	126.7	126.3	126.0	125.9	125.8	125.7	125.5	125.2
85°	74.7	74.7	74.7	74.7	74.7	74.4	73.7	73.1	72.5	71.9	71.9
87.5°	28.9	29.0	29.2	29.1	29.0	28.8	29.5	29.2	29.3	29.4	29.2
90°	0.8	2.3	4.7	5.5	6.3	6.3	10.9	10.9	12.5	14.1	13.3
92.5°	8.9	13.0	20.3	29.9	41.3	57.5	97.3	157.9	217.1	248.0	206.6
95°	25.8	28.1	36.0	46.1	64.9	97.7	165.8	294.0	480.9	637.3	655.3
97.5°	46.3	46.3	53.0	62.4	78.5	106.0	158.4	264.3	450.1	671.2	823.2
100°	59.4	59.4	64.9	74.3	89.1	114.2	160.3	248.7	408.2	628.7	828.8
102.5°	71.9	73.2	78.0	86.8	101.0	124.8	166.5	244.3	380.0	575.5	781.9
105°	91.5	93.8	97.7	107.1	121.2	143.9	181.4	246.3	355.8	512.9	696.7
107.5°	113.1	114.6	118.5	128.5	142.0	164.4	198.8	257.9	351.4	477.9	627.9
110°	127.5	129.0	132.9	142.3	156.4	177.5	211.9	266.6	352.6	466.0	593.5



TEST NUMBER: P332651

CATALOG NUMBER: S124DIP-S1020D810U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	141.2	142.8	147.3	156.1	170.1	191.3	224.4	276.0	356.4	460.4	574.1
115°	161.1	163.4	168.9	176.7	191.6	212.7	244.0	290.9	363.6	457.4	555.9
117.5°	181.7	183.9	188.8	197.4	211.3	233.2	262.9	306.0	371.3	456.6	547.8
120°	195.5	197.0	202.5	211.1	224.4	246.3	276.0	316.7	376.9	456.6	543.4
122.5°	208.0	209.6	215.0	223.0	237.5	258.8	288.5	326.7	382.5	456.0	538.4
125°	224.4	227.5	232.2	240.8	255.7	277.6	305.7	341.7	391.0	455.1	530.1
127.5°	239.0	241.5	247.1	256.9	272.4	294.5	321.7	354.7	397.7	453.4	519.0
130°	247.1	250.2	256.5	268.2	283.1	305.7	332.3	362.8	402.7	452.7	512.2
132.5°	255.2	257.7	265.9	277.0	293.1	314.5	341.1	370.9	407.1	452.1	505.9
135°	266.6	269.8	277.6	290.9	307.3	327.6	353.4	381.6	413.6	451.2	496.5
137.5°	278.1	281.0	289.6	302.3	319.3	338.7	362.8	389.1	417.5	451.0	488.4
140°	286.2	288.5	297.1	310.4	326.8	345.6	369.1	394.1	420.7	450.4	484.0
142.5°	294.9	297.3	305.3	317.9	333.7	351.9	374.7	397.8	423.2	450.4	480.3
145°	307.3	309.6	317.5	328.4	343.3	360.5	380.8	401.9	424.6	448.8	473.8
147.5°	321.2	322.0	328.9	340.1	352.5	368.0	387.1	405.5	425.4	446.0	468.1
150°	330.0	330.8	337.0	346.4	358.1	373.0	390.2	407.4	425.4	444.1	463.7
152.5°	338.1	338.3	344.5	353.3	363.8	377.4	392.7	408.6	424.1	441.0	458.7
155°	349.5	350.3	355.0	362.8	371.4	383.1	396.4	409.7	422.2	436.3	451.2
157.5°	360.6	360.6	365.0	371.1	378.6	387.8	399.1	409.7	420.2	431.5	443.5
160°	367.5	367.5	370.6	376.1	382.4	391.0	400.3	409.7	418.3	427.7	437.9
162.5°	373.8	373.1	375.6	380.5	386.1	392.8	401.6	409.7	416.5	424.0	432.9
165°	380.8	380.8	382.4	386.3	390.2	394.9	401.9	408.2	412.9	418.3	424.6
167.5°	387.8	387.1	387.8	390.8	393.0	396.6	401.8	406.3	409.1	412.7	417.1
170°	391.0	390.2	391.0	393.3	394.9	397.2	401.1	405.0	406.6	408.9	412.1
172.5°	394.1	393.3	393.5	395.2	396.1	397.8	400.5	403.8	404.1	405.2	407.7
175°	397.2	396.4	396.4	397.2	398.0	398.0	399.6	401.9	401.1	401.1	402.7
177.5°	398.6	398.0	397.4	398.0	398.0	398.0	398.6	399.9	398.6	398.6	399.2
180°	398.0	398.0	398.0	398.0	398.0	398.0	398.0	398.0	398.0	398.0	398.0



TEST NUMBER: P332651

CATALOG NUMBER: S124DIP-S1020D810U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1725.5	1725.5	1725.5	1725.5	1725.5	1725.5	1725.5	1725.5
2.5°	1719.3	1721.8	1724.3	1725.4	1725.1	1724.9	1724.6	1724.4
5°	1710.1	1713.5	1716.9	1718.3	1717.7	1717.0	1716.4	1715.8
7.5°	1691.1	1693.8	1696.5	1697.7	1697.3	1696.9	1696.5	1696.2
10°	1675.1	1677.6	1680.0	1680.9	1680.3	1679.7	1679.1	1678.5
12.5°	1655.7	1658.4	1661.1	1662.0	1661.2	1660.3	1659.4	1658.6
15°	1618.6	1620.4	1622.3	1622.7	1621.8	1620.9	1620.0	1619.0
17.5°	1576.3	1577.5	1578.6	1578.9	1578.3	1577.7	1577.1	1576.4
20°	1544.8	1545.8	1546.7	1546.8	1546.2	1545.6	1545.0	1544.4
22.5°	1512.0	1513.7	1515.3	1515.6	1514.5	1513.4	1512.3	1511.2
25°	1457.9	1458.2	1458.5	1458.0	1456.8	1455.6	1454.3	1453.1
27.5°	1397.2	1396.4	1395.7	1394.6	1393.0	1391.5	1389.9	1388.4
30°	1355.3	1354.0	1352.8	1351.4	1349.9	1348.3	1346.8	1345.3
32.5°	1312.7	1311.3	1309.8	1308.3	1306.7	1305.2	1303.7	1302.1
35°	1245.6	1243.4	1241.3	1239.4	1237.9	1236.4	1234.8	1233.3
37.5°	1175.2	1172.9	1170.6	1168.4	1166.4	1164.3	1162.3	1160.3
40°	1126.2	1123.1	1120.1	1117.8	1116.2	1114.7	1113.2	1111.6
42.5°	1078.8	1075.2	1071.6	1069.3	1068.3	1067.2	1066.2	1065.2
45°	1005.3	1001.9	998.5	996.4	995.5	994.6	993.6	992.7
47.5°	934.2	930.4	926.6	923.5	921.2	918.8	916.5	914.2
50°	884.6	880.3	876.0	872.9	871.0	869.2	867.4	865.5
52.5°	833.6	829.7	825.9	822.9	820.5	818.2	815.9	813.5
55°	758.6	754.9	751.2	748.5	746.6	744.8	742.9	741.1
57.5°	683.5	680.0	676.5	673.8	672.0	670.3	668.5	666.7
60°	631.9	629.1	626.3	624.2	622.6	621.1	619.6	618.0
62.5°	581.5	578.9	576.4	574.4	572.9	571.3	569.8	568.3
65°	508.2	505.1	502.0	499.7	498.2	496.7	495.1	493.6
67.5°	432.7	429.7	426.8	425.1	424.6	424.2	423.8	423.4
70°	385.0	382.5	380.1	378.4	377.5	376.5	375.6	374.7
72.5°	337.3	335.3	333.4	331.9	331.0	330.1	329.2	328.2
75°	268.5	267.3	266.1	265.3	265.0	264.7	264.4	264.1
77.5°	203.3	203.0	202.6	202.0	201.2	200.4	199.6	198.8
80°	161.9	161.3	160.7	160.2	159.9	159.6	159.3	159.0
82.5°	124.8	124.4	124.1	123.7	123.4	123.1	122.8	122.5
85°	71.9	71.9	71.9	71.7	71.4	71.1	70.8	70.5
87.5°	29.4	29.5	29.7	29.7	29.8	30.0	29.8	29.8
90°	14.1	14.9	15.6	15.6	16.4	17.2	16.4	16.4
92.5°	153.6	115.6	92.0	76.3	67.1	62.9	60.2	60.2
95°	579.4	458.2	353.4	277.6	239.3	215.0	201.0	190.8
97.5°	856.0	811.0	734.5	652.9	596.8	549.7	526.2	510.0
100°	943.0	958.6	920.3	862.5	794.4	746.7	723.3	717.0
102.5°	938.6	1016.2	1027.3	1003.2	961.5	926.9	902.2	897.2
105°	875.8	1011.0	1088.4	1120.5	1122.1	1115.8	1104.9	1100.2
107.5°	786.5	930.5	1039.5	1109.2	1147.9	1165.7	1173.5	1175.5
110°	732.7	867.9	981.3	1067.3	1122.8	1155.7	1169.8	1176.8



TEST NUMBER: P332651

CATALOG NUMBER: S124DIP-S1020D810U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	693.3	812.9	920.0	1006.0	1069.0	1108.8	1128.5	1139.9
115°	653.7	749.9	841.3	916.4	978.2	1025.1	1050.1	1056.4
117.5°	634.3	713.9	785.8	849.5	902.2	941.6	966.9	971.8
120°	625.5	698.3	760.8	816.3	860.9	895.3	915.6	924.2
122.5°	618.0	688.2	745.2	793.8	831.5	860.9	878.1	886.7
125°	605.2	672.5	726.4	769.4	800.7	823.4	838.2	842.9
127.5°	589.6	653.8	707.6	748.5	779.9	800.1	812.6	817.3
130°	577.1	638.8	692.0	733.4	765.5	785.1	797.6	802.3
132.5°	563.9	621.9	673.9	715.3	746.7	768.8	780.7	785.4
135°	545.8	596.6	644.3	683.4	714.7	736.6	749.1	753.8
137.5°	529.4	572.4	612.6	647.9	677.1	698.7	709.0	714.7
140°	520.0	556.7	591.9	624.8	652.1	669.3	680.3	686.5
142.5°	511.2	543.6	573.8	602.2	626.5	642.4	652.1	656.5
145°	498.9	525.5	548.9	570.8	590.4	603.6	611.5	615.4
147.5°	488.7	509.8	528.6	545.8	560.2	571.6	577.5	578.9
150°	482.4	500.4	516.1	530.1	542.7	552.8	557.5	558.3
152.5°	475.6	491.0	505.4	517.0	527.6	535.9	538.7	539.5
155°	465.2	477.8	489.5	498.9	506.7	512.9	515.3	515.3
157.5°	454.1	464.6	474.5	482.0	487.9	492.6	494.0	494.0
160°	447.3	455.9	464.5	470.7	475.4	480.1	480.9	480.9
162.5°	440.4	447.7	454.5	460.1	463.5	468.2	469.0	468.4
165°	430.8	435.5	441.0	444.9	448.0	451.2	450.4	449.6
167.5°	421.6	425.2	429.6	431.9	433.5	435.5	435.4	434.7
170°	416.0	418.3	421.5	423.8	425.4	426.1	425.4	425.4
172.5°	411.0	412.7	414.6	416.3	417.2	418.0	417.2	416.0
175°	404.3	405.0	406.6	406.6	406.6	408.2	406.6	405.0
177.5°	399.9	400.5	400.5	401.1	400.5	401.1	399.9	398.6
180°	398.0	398.0	398.0	398.0	398.0	398.0	398.0	398.0

(END OF REPORT)