

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332697

Luminaire Tested: **S124DIP-S1195D1035U835-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332697
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIP-S1195D1035U835-4F0-1E-UDD-A
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1195 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1035 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9450.1 lumens
Efficiency: N/A
Efficacy: 141.5 lumens/watt
Spacing Criteria (0/90/45): 1.31 / 1.23 / 1.41
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 66.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332697

CATALOG NUMBER: S124DIP-S1195D1035U835-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P332697

CATALOG NUMBER: S124DIP-S1195D1035U835-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62	56																				
1	99	95	91	88	92	89	85	82	77	74	72	65	64	62	55	54	53	48																				
2	91	83	77	72	84	78	73	68	67	63	60	58	55	52	49	47	45	41																				
3	83	74	66	60	77	69	62	57	60	55	51	51	48	44	43	41	38	35																				
4	76	65	57	51	70	61	54	49	53	48	43	46	42	38	39	36	33	30																				
5	70	58	50	44	65	55	47	42	48	42	38	41	37	33	35	32	29	26																				
6	64	52	44	39	60	49	42	37	43	37	33	37	33	29	32	29	26	23																				
7	60	47	39	34	55	45	37	32	39	33	29	34	30	26	29	26	23	21																				
8	55	43	35	30	52	41	34	29	36	30	26	31	27	23	27	23	21	18																				
9	52	39	32	27	48	37	30	26	33	27	23	29	24	21	25	21	19	17																				
10	48	36	29	24	45	34	28	23	30	25	21	27	22	19	23	20	17	15																				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	15560	15560	15560	15560
5°	18323	15600	13768	15600
10°	21939	15531	12396	15531
15°	25957	15374	11384	15374
20°	28905	15214	10481	15214
25°	29372	14978	9857	14978
30°	24993	14752	9660	14752
35°	19215	14384	9662	14384
40°	14977	13951	9844	13951
45°	12488	13300	10009	13300
50°	10991	12504	10349	12504
55°	10069	11553	10766	11553
60°	9436	10700	11267	10700
65°	8785	9746	11683	9746
70°	8028	8802	11948	8802
75°	7171	7745	11803	7745
80°	6011	6346	11432	6346
85°	4437	4585	10948	4585



TEST NUMBER: P332697

CATALOG NUMBER: S124DIP-S1195D1035U835-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	187.8	2.0
10°-20°	578.8	6.1
20°-30°	917.8	9.7
30°-40°	1021.3	10.8
40°-50°	929.7	9.8
50°-60°	759.7	8.0
60°-70°	542.4	5.7
70°-80°	298.7	3.2
80°-90°	85.4	0.9
90°-100°	45.7	0.5
100°-110°	291.1	3.1
110°-120°	556.8	5.9
120°-130°	706.8	7.5
130°-140°	756.2	8.0
140°-150°	707.2	7.5
150°-160°	570.3	6.0
160°-170°	367.8	3.9
170°-180°	126.8	1.3
0°-30°	1684.3	17.8
0°-40°	2705.6	28.6
0°-60°	4395.1	46.5
0°-90°	5321.5	56.3
90°-120°	893.5	9.5
90°-150°	3063.7	32.4
90°-180°	4129.0	43.7
0°-180°	9450.1	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1927	1927	1927	1927	1927	
5°	2261	1925	1699	1925	2261	230
15°	3106	1840	1362	1840	3106	878
25°	3297	1682	1107	1682	3297	1454
35°	1950	1460	980	1460	1950	1238
45°	1094	1165	877	1165	1094	862
55°	715	821	765	821	715	646
65°	460	510	612	510	460	455
75°	230	248	378	248	230	244
85°	48	50	118	50	48	59
90°	30	3	30	3	30	15
95°	29	55	29	55	29	23
105°	284	300	284	300	284	248
115°	565	561	565	561	565	559
125°	795	789	795	789	795	708
135°	985	978	985	978	985	758
145°	1134	1128	1134	1128	1134	709
155°	1236	1237	1236	1237	1236	570
165°	1299	1305	1299	1305	1299	367
175°	1327	1335	1327	1335	1327	126
180°	1335	1335	1335	1335	1335	



TEST NUMBER: P332697

CATALOG NUMBER: S124DIP-S1195D1035U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4
2.5°	2051.3	2050.6	2044.3	2043.0	2038.5	2032.8	2031.5	2021.3	2000.8	1991.2	1988.7
5°	2261.1	2277.1	2256.3	2252.3	2249.9	2223.6	2210.0	2194.0	2157.3	2135.8	2119.0
7.5°	2511.5	2513.4	2504.3	2497.0	2476.7	2453.7	2419.2	2382.5	2338.7	2293.2	2258.9
10°	2676.3	2682.7	2672.3	2670.7	2630.0	2604.4	2553.3	2510.2	2460.7	2405.6	2355.3
12.5°	2850.0	2841.1	2835.8	2801.6	2794.1	2747.5	2688.1	2643.7	2567.4	2504.0	2437.1
15°	3105.8	3088.3	3077.1	3030.0	3006.8	2942.1	2879.1	2830.4	2730.6	2635.6	2563.7
17.5°	3255.9	3273.5	3247.6	3228.3	3168.4	3123.1	3058.6	2956.4	2878.3	2760.3	2669.6
20°	3364.5	3366.1	3351.7	3331.8	3284.7	3227.2	3156.9	3045.1	2951.7	2834.4	2709.8
22.5°	3393.9	3394.2	3388.1	3369.5	3333.8	3287.2	3216.3	3123.1	3009.9	2882.3	2757.7
25°	3297.4	3294.2	3301.4	3322.2	3308.6	3294.2	3253.5	3184.1	3078.7	2943.7	2809.6
27.5°	2939.1	2961.1	3001.7	3052.8	3102.0	3139.5	3150.1	3135.8	3070.5	2959.6	2819.0
30°	2681.1	2708.2	2738.6	2789.6	2888.7	2945.3	3007.6	3054.7	3028.4	2939.8	2808.8
32.5°	2397.5	2404.2	2449.2	2507.3	2598.0	2707.1	2805.8	2901.4	2933.2	2886.7	2777.5
35°	1949.7	1960.9	2009.6	2067.1	2178.1	2311.4	2459.9	2592.4	2701.8	2745.7	2689.8
37.5°	1591.1	1623.2	1657.5	1719.3	1817.0	1937.1	2091.4	2262.9	2425.9	2535.1	2553.6
40°	1421.2	1441.1	1465.9	1513.0	1596.0	1714.2	1846.7	2043.1	2216.4	2372.9	2424.0
42.5°	1287.0	1298.7	1313.9	1356.5	1419.7	1537.3	1658.3	1831.1	2005.0	2192.1	2277.7
45°	1093.8	1105.8	1131.3	1156.1	1204.0	1285.4	1398.0	1540.1	1715.0	1895.4	2053.5
47.5°	954.3	961.9	977.1	1003.6	1044.3	1098.0	1189.6	1308.3	1470.4	1645.5	1814.0
50°	875.1	881.4	893.4	917.4	948.5	996.4	1071.5	1182.4	1309.4	1485.8	1651.1
52.5°	812.5	815.0	823.8	840.1	864.8	905.1	966.7	1058.5	1176.5	1333.8	1498.5
55°	715.4	718.6	726.6	738.5	760.1	785.6	832.7	901.4	1004.4	1140.9	1283.8
57.5°	635.5	637.8	644.5	649.1	666.8	687.6	723.8	772.9	850.9	966.7	1094.3
60°	584.4	582.8	590.8	594.8	606.8	624.4	652.3	699.4	767.3	860.7	978.1
62.5°	534.6	532.4	539.1	544.4	551.2	566.2	589.1	626.0	681.0	765.5	866.9
65°	459.9	456.7	460.7	467.1	473.5	481.4	498.2	530.9	574.9	635.5	713.0
67.5°	384.8	388.2	388.8	392.0	395.7	406.6	418.0	441.2	472.2	520.7	586.4
70°	340.1	340.9	344.1	344.1	346.5	356.1	365.7	379.2	409.6	454.3	507.8
72.5°	295.4	298.8	297.5	300.0	301.8	308.2	315.2	328.1	354.0	387.2	432.4
75°	229.9	232.3	232.3	233.1	235.5	237.9	243.5	253.1	271.5	296.2	327.3
77.5°	167.7	168.0	169.1	172.0	172.0	175.8	180.0	187.6	196.7	213.7	232.7
80°	129.3	130.9	130.1	131.7	131.7	134.9	136.5	146.1	150.1	161.3	176.4
82.5°	94.9	96.4	96.3	98.5	99.8	100.4	102.7	106.5	110.5	120.4	126.6
85°	47.9	49.5	47.9	49.5	51.9	52.7	55.1	55.9	59.1	61.5	67.1
87.5°	20.0	21.9	21.8	22.3	23.5	24.0	24.4	23.4	25.7	26.1	28.3
90°	29.9	29.5	29.1	28.6	28.2	27.3	26.0	24.6	23.3	22.0	20.2
92.5°	27.6	27.5	27.4	27.3	27.2	26.5	25.2	23.8	22.5	21.2	19.4
95°	28.9	28.7	28.5	28.3	28.1	27.3	26.0	24.6	23.3	22.0	21.7
97.5°	28.0	27.7	27.5	27.3	27.1	26.9	26.8	26.6	26.5	26.4	51.1
100°	28.0	27.7	27.5	27.3	27.1	28.8	32.6	36.4	40.2	43.9	74.5
102.5°	28.8	28.7	28.7	28.6	28.6	48.9	89.6	130.3	170.9	211.6	215.6
105°	284.5	292.5	300.5	308.5	316.5	319.4	317.4	315.5	313.5	311.5	310.4
107.5°	396.5	395.7	394.8	394.0	393.1	392.2	391.3	390.3	389.3	388.3	386.8
110°	445.2	444.6	443.9	443.2	442.6	442.0	441.6	441.1	440.7	440.2	438.9



TEST NUMBER: P332697

CATALOG NUMBER: S124DIP-S1195D1035U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	493.9	<i>493.1</i>	492.3	491.4	490.6	490.2	490.3	490.4	490.5	490.5	489.9
115°	565.0	<i>565.0</i>	565.0	565.0	565.0	564.8	564.4	563.9	563.5	563.0	563.2
117.5°	637.3	<i>637.4</i>	637.5	637.6	637.7	637.7	637.8	637.9	638.0	638.1	637.6
120°	682.8	<i>683.3</i>	683.7	684.1	684.6	684.6	684.1	683.7	683.3	682.8	683.0
122.5°	727.5	<i>728.0</i>	728.4	728.9	729.3	729.4	729.1	728.9	728.6	728.3	728.0
125°	794.6	<i>794.4</i>	794.2	794.0	793.7	793.3	792.6	792.0	791.3	790.6	791.1
127.5°	853.5	<i>853.7</i>	853.9	854.1	854.2	854.4	854.5	854.7	854.8	854.9	853.9
130°	893.5	<i>893.5</i>	893.5	893.5	893.5	893.3	893.1	892.9	892.7	892.5	891.8
132.5°	930.2	<i>930.4</i>	930.5	930.7	930.9	930.9	930.7	930.4	930.2	930.0	929.1
135°	985.3	<i>984.8</i>	984.4	984.0	983.5	983.1	982.6	982.2	981.7	981.3	980.4
137.5°	1032.4	<i>1032.5</i>	1032.7	1032.8	1032.9	1032.8	1032.3	1031.8	1031.3	1030.8	1029.8
140°	1065.2	<i>1064.9</i>	1064.7	1064.5	1064.3	1063.8	1063.2	1062.5	1061.8	1061.2	1060.7
142.5°	1092.3	<i>1092.3</i>	1092.2	1092.2	1092.1	1091.9	1091.4	1090.9	1090.4	1089.9	1089.6
145°	1134.0	<i>1133.6</i>	1133.1	1132.7	1132.3	1131.9	1131.7	1131.5	1131.3	1131.0	1131.0
147.5°	1168.6	<i>1168.4</i>	1168.1	1167.9	1167.7	1167.5	1167.3	1167.1	1167.0	1166.8	1167.0
150°	1190.9	<i>1190.7</i>	1190.5	1190.3	1190.0	1189.9	1189.9	1189.9	1189.9	1189.9	1190.2
152.5°	1210.1	<i>1210.2</i>	1210.4	1210.5	1210.6	1210.5	1210.2	1209.8	1209.5	1209.1	1209.5
155°	1235.9	<i>1236.5</i>	1237.2	1237.9	1238.5	1238.4	1237.5	1236.6	1235.7	1234.9	1235.5
157.5°	1257.4	<i>1258.6</i>	1259.7	1260.9	1262.0	1262.0	1260.9	1259.7	1258.6	1257.4	1258.2
160°	1271.8	<i>1273.1</i>	1274.5	1275.8	1277.1	1277.1	1275.8	1274.5	1273.1	1271.8	1272.0
162.5°	1283.0	<i>1284.5</i>	1286.0	1287.5	1289.0	1289.1	1287.8	1286.4	1285.1	1283.8	1284.0
165°	1298.7	<i>1300.7</i>	1302.7	1304.7	1306.7	1306.8	1305.1	1303.3	1301.5	1299.7	1299.7
167.5°	1310.5	<i>1312.7</i>	1315.0	1317.2	1319.4	1319.5	1317.6	1315.6	1313.7	1311.7	1311.9
170°	1317.7	<i>1319.9</i>	1322.2	1324.4	1326.6	1326.8	1325.0	1323.3	1321.5	1319.7	1319.5
172.5°	1321.7	<i>1324.1</i>	1326.5	1328.9	1331.3	1331.6	1329.8	1328.1	1326.3	1324.5	1324.3
175°	1326.7	<i>1329.4</i>	1332.0	1334.7	1337.3	1337.7	1335.7	1333.7	1331.7	1329.7	1329.5
177.5°	1329.9	<i>1332.0</i>	1334.2	1336.3	1338.4	1338.8	1337.3	1335.9	1334.5	1333.1	1332.7
180°	1334.7	<i>1334.7</i>	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7



TEST NUMBER: P332697

CATALOG NUMBER: S124DIP-S1195D1035U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4
2.5°	1989.3	1980.4	1974.0	1968.9	1954.8	1946.5	1940.1	1931.2	1921.0	1910.1	1896.7
5°	2102.2	2075.1	2055.1	2024.8	1996.0	1972.1	1947.3	1925.0	1897.8	1868.3	1846.7
7.5°	2220.9	2180.5	2128.7	2083.9	2033.4	1989.5	1950.2	1910.0	1868.1	1827.6	1790.4
10°	2296.2	2244.3	2186.8	2119.0	2055.1	1998.4	1945.7	1894.6	1845.1	1795.6	1753.3
12.5°	2377.4	2312.7	2227.7	2148.4	2076.8	2001.0	1937.4	1874.8	1815.1	1763.1	1713.7
15°	2486.3	2392.8	2294.6	2188.4	2094.2	2005.6	1918.6	1839.5	1772.5	1703.8	1655.9
17.5°	2553.2	2437.6	2325.3	2214.3	2100.3	1988.5	1894.6	1803.5	1719.5	1651.3	1590.9
20°	2597.2	2482.3	2342.5	2231.6	2095.8	1980.9	1872.3	1770.9	1683.1	1610.4	1548.1
22.5°	2635.6	2502.7	2363.0	2216.9	2081.8	1959.8	1841.0	1738.9	1649.2	1572.7	1513.0
25°	2656.3	2503.8	2352.1	2206.8	2053.5	1909.0	1801.2	1681.5	1585.6	1505.0	1441.1
27.5°	2658.6	2495.5	2323.9	2162.4	2004.2	1869.6	1733.5	1626.5	1527.0	1441.8	1380.5
30°	2651.5	2481.5	2297.0	2122.2	1963.3	1817.2	1699.0	1582.5	1481.1	1396.4	1332.5
32.5°	2629.2	2452.1	2262.5	2077.5	1912.8	1769.9	1647.9	1537.1	1438.3	1354.9	1287.8
35°	2564.5	2389.6	2187.6	1995.2	1826.8	1682.3	1572.1	1459.5	1360.5	1281.5	1216.8
37.5°	2463.4	2305.3	2100.0	1900.9	1735.4	1590.3	1481.1	1379.3	1290.1	1209.8	1143.5
40°	2375.3	2236.4	2030.4	1836.3	1657.5	1519.4	1417.2	1323.8	1235.1	1159.3	1096.2
42.5°	2273.7	2152.7	1962.7	1757.1	1584.7	1445.9	1346.3	1262.4	1178.9	1108.8	1045.8
45°	2092.6	2012.8	1834.0	1643.9	1464.3	1333.3	1238.3	1164.9	1094.6	1026.0	973.3
47.5°	1884.4	1844.8	1694.2	1513.8	1343.2	1214.2	1131.8	1064.0	1002.3	944.2	897.7
50°	1744.5	1725.4	1595.2	1421.2	1258.3	1136.9	1053.9	995.6	942.9	891.8	847.9
52.5°	1606.6	1605.9	1488.6	1329.2	1178.5	1061.6	979.2	924.7	879.1	837.5	798.1
55°	1395.6	1418.0	1326.2	1184.0	1049.1	943.7	869.5	820.8	788.8	754.5	725.0
57.5°	1201.9	1239.0	1163.3	1038.1	925.5	828.4	763.8	727.2	693.2	672.4	650.9
60°	1075.5	1110.6	1051.5	946.1	839.9	756.9	695.4	662.7	633.1	618.8	603.6
62.5°	963.0	994.3	950.6	852.9	760.7	680.9	629.0	597.5	577.6	561.9	551.9
65°	802.4	828.8	791.2	720.2	641.1	577.3	534.9	510.2	491.0	484.6	473.5
67.5°	648.6	672.6	652.3	591.9	528.5	480.2	447.1	423.3	412.0	406.4	398.4
70°	557.3	581.2	559.7	507.0	458.3	417.6	386.4	372.9	360.9	358.5	347.3
72.5°	480.0	496.3	474.7	433.5	391.9	357.5	333.4	319.2	313.0	308.7	302.6
75°	360.1	374.5	360.1	328.1	298.6	274.7	253.9	248.3	241.1	238.7	234.7
77.5°	254.9	267.3	256.3	236.3	214.3	195.8	184.6	177.4	175.8	171.7	173.6
80°	194.8	202.8	192.4	178.8	161.3	148.5	140.5	136.5	131.7	130.1	133.3
82.5°	139.9	143.4	138.1	129.0	115.9	107.6	102.2	97.6	96.6	96.9	96.9
85°	72.7	71.9	71.1	63.1	59.1	53.5	50.3	49.5	48.7	50.3	51.9
87.5°	28.0	28.2	27.2	24.3	21.9	19.5	18.3	17.2	18.3	19.5	20.6
90°	18.4	16.6	14.9	12.8	10.3	7.9	5.4	3.0	5.4	7.9	10.3
92.5°	17.6	15.8	14.1	13.1	13.0	12.8	12.7	12.6	12.7	12.8	13.0
95°	21.5	21.3	21.1	24.7	32.3	39.8	47.4	54.9	47.4	39.8	32.3
97.5°	75.9	100.6	125.4	135.4	130.7	126.0	121.3	116.6	121.3	126.0	130.7
100°	105.2	135.8	166.4	179.7	175.7	171.7	167.7	163.7	167.7	171.7	175.7
102.5°	219.6	223.6	227.6	228.1	225.2	222.3	219.4	216.4	219.4	222.3	225.2
105°	309.2	308.1	307.0	305.8	304.5	303.1	301.8	300.5	301.8	303.1	304.5
107.5°	385.3	383.8	382.3	381.2	380.5	379.9	379.2	378.5	379.2	379.9	380.5
110°	437.6	436.2	434.9	433.9	433.2	432.6	431.9	431.3	431.9	432.6	433.2



TEST NUMBER: P332697

CATALOG NUMBER: S124DIP-S1195D1035U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	489.3	488.7	488.1	487.2	486.0	484.8	483.6	482.4	483.6	484.8	486.0
115°	563.5	563.7	563.9	563.7	563.0	562.4	561.7	561.0	561.7	562.4	563.0
117.5°	637.1	636.6	636.1	635.5	634.6	633.7	632.8	631.9	632.8	633.7	634.6
120°	683.3	683.5	683.7	683.4	682.5	681.6	680.7	679.8	680.7	681.6	682.5
122.5°	727.7	727.4	727.1	726.7	726.1	725.6	725.1	724.5	725.1	725.6	726.1
125°	791.5	792.0	792.4	792.2	791.3	790.4	789.5	788.6	789.5	790.4	791.3
127.5°	852.9	851.9	850.8	850.2	850.0	849.8	849.5	849.3	849.5	849.8	850.0
130°	891.1	890.5	889.8	889.3	889.1	888.9	888.7	888.5	888.7	888.9	889.1
132.5°	928.3	927.5	926.6	926.0	925.6	925.2	924.8	924.4	924.8	925.2	925.6
135°	979.5	978.6	977.7	977.4	977.6	977.9	978.1	978.3	978.1	977.9	977.6
137.5°	1028.9	1027.9	1026.9	1026.4	1026.3	1026.2	1026.1	1026.0	1026.1	1026.2	1026.3
140°	1060.3	1059.8	1059.4	1058.9	1058.5	1058.1	1057.6	1057.2	1057.6	1058.1	1058.5
142.5°	1089.4	1089.1	1088.8	1088.3	1087.5	1086.7	1085.9	1085.1	1085.9	1086.7	1087.5
145°	1131.0	1131.0	1131.0	1130.7	1130.0	1129.4	1128.7	1128.0	1128.7	1129.4	1130.0
147.5°	1167.2	1167.4	1167.7	1167.2	1165.9	1164.7	1163.4	1162.2	1163.4	1164.7	1165.9
150°	1190.4	1190.6	1190.8	1190.5	1189.6	1188.7	1187.8	1186.9	1187.8	1188.7	1189.6
152.5°	1209.9	1210.3	1210.7	1210.5	1209.8	1209.1	1208.4	1207.7	1208.4	1209.1	1209.8
155°	1236.2	1236.9	1237.5	1237.7	1237.5	1237.3	1237.1	1236.9	1237.1	1237.3	1237.5
157.5°	1258.9	1259.7	1260.4	1260.9	1261.0	1261.1	1261.3	1261.4	1261.3	1261.1	1261.0
160°	1272.2	1272.5	1272.7	1273.1	1273.8	1274.5	1275.1	1275.8	1275.1	1274.5	1273.8
162.5°	1284.2	1284.4	1284.7	1285.2	1286.0	1286.9	1287.7	1288.6	1287.7	1286.9	1286.0
165°	1299.7	1299.7	1299.7	1300.3	1301.4	1302.5	1303.6	1304.7	1303.6	1302.5	1301.4
167.5°	1312.0	1312.1	1312.3	1312.9	1314.1	1315.2	1316.4	1317.5	1316.4	1315.2	1314.1
170°	1319.3	1319.0	1318.8	1319.4	1320.7	1322.0	1323.4	1324.7	1323.4	1322.0	1320.7
172.5°	1324.1	1323.8	1323.6	1324.2	1325.5	1326.8	1328.2	1329.5	1328.2	1326.8	1325.5
175°	1329.3	1329.0	1328.8	1329.4	1330.7	1332.0	1333.4	1334.7	1333.4	1332.0	1330.7
177.5°	1332.4	1332.0	1331.7	1332.1	1333.4	1334.6	1335.8	1337.1	1335.8	1334.6	1333.4
180°	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7



TEST NUMBER: P332697

CATALOG NUMBER: S124DIP-S1195D1035U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4
2.5°	1890.3	1884.6	1876.3	1864.8	1855.2	1845.0	1842.4	1838.6	1846.2	1839.9	1837.9
5°	1828.4	1811.6	1790.0	1765.3	1750.9	1730.2	1726.2	1718.2	1710.2	1709.4	1701.4
7.5°	1762.7	1738.1	1709.9	1684.6	1661.3	1638.7	1623.8	1620.6	1608.8	1601.9	1593.9
10°	1720.6	1690.2	1657.5	1633.6	1606.4	1582.5	1565.7	1556.1	1548.1	1539.3	1531.4
12.5°	1670.8	1638.5	1611.5	1585.6	1553.4	1535.2	1507.6	1491.0	1489.4	1489.5	1468.8
15°	1612.8	1580.9	1539.3	1502.6	1485.0	1449.9	1434.7	1415.6	1403.6	1391.6	1382.1
17.5°	1546.5	1506.8	1474.3	1432.2	1398.7	1370.7	1350.8	1339.3	1321.2	1304.3	1292.0
20°	1505.0	1462.7	1428.4	1383.6	1346.9	1312.6	1295.8	1279.9	1266.3	1251.9	1238.3
22.5°	1462.8	1418.6	1376.6	1333.2	1299.0	1262.8	1246.6	1224.9	1212.0	1204.0	1190.4
25°	1396.4	1348.5	1300.6	1259.1	1224.0	1192.0	1170.5	1153.7	1139.3	1132.9	1124.2
27.5°	1324.2	1276.7	1230.4	1183.2	1143.3	1120.2	1102.9	1090.3	1082.0	1073.5	1069.6
30°	1278.3	1228.8	1179.3	1135.3	1098.6	1075.5	1059.5	1050.7	1044.3	1040.3	1036.3
32.5°	1231.6	1182.8	1130.7	1090.6	1057.7	1037.1	1025.0	1016.2	1013.0	1011.6	1010.2
35°	1156.9	1107.4	1059.5	1023.6	992.4	984.4	974.1	969.3	967.7	973.3	975.7
37.5°	1084.6	1038.6	994.5	959.7	939.3	927.6	924.1	924.2	930.0	934.9	940.7
40°	1037.9	993.2	951.7	921.4	902.2	895.0	893.4	897.4	903.8	909.4	915.8
42.5°	992.6	948.5	910.8	882.4	869.0	862.4	863.4	867.4	876.3	883.2	892.8
45°	922.2	885.4	848.7	825.6	814.4	816.0	816.0	823.2	831.9	842.3	852.7
47.5°	855.9	818.9	788.7	769.2	763.4	762.0	766.5	775.9	788.5	801.3	815.8
50°	811.2	776.1	749.7	732.1	725.8	728.2	734.5	743.3	758.5	774.5	789.6
52.5°	765.8	733.9	709.5	693.2	688.7	693.0	699.4	713.3	726.6	743.8	762.2
55°	695.4	668.3	649.1	637.1	635.5	637.9	645.1	660.3	679.4	701.0	718.6
57.5°	625.3	602.6	585.1	576.8	577.6	579.8	591.6	609.7	630.1	653.1	675.8
60°	578.0	557.3	542.9	536.5	537.3	542.1	556.5	573.3	598.8	621.2	645.1
62.5°	533.3	515.1	501.4	495.7	494.5	505.1	518.8	536.2	561.8	586.7	612.5
65°	461.5	447.1	435.9	432.7	435.1	443.1	460.7	483.8	505.4	531.7	558.9
67.5°	391.2	379.4	371.7	373.2	376.1	387.9	402.6	422.5	447.0	474.3	501.1
70°	346.5	335.3	328.9	329.7	334.5	348.9	361.7	381.6	408.0	435.9	458.3
72.5°	300.5	293.2	287.4	290.8	295.6	305.5	321.4	341.4	364.6	390.6	414.2
75°	230.7	230.7	227.5	229.9	237.1	246.7	258.7	279.4	302.6	323.4	342.5
77.5°	171.2	169.4	171.5	174.4	178.5	189.9	203.6	218.4	235.9	256.6	272.4
80°	130.9	131.7	135.7	140.5	142.1	150.9	165.3	178.8	192.4	210.0	225.2
82.5°	98.4	99.2	101.2	107.3	108.9	118.3	127.6	141.2	153.5	165.3	177.9
85°	53.5	53.5	57.5	59.9	63.9	70.3	75.8	83.8	95.0	103.0	115.0
87.5°	23.0	23.4	26.3	28.0	30.2	33.8	35.3	42.6	45.4	48.9	54.8
90°	12.8	14.9	16.6	18.4	20.2	22.0	23.3	24.6	26.0	27.3	28.2
92.5°	13.1	14.1	15.8	17.6	19.4	21.2	22.5	23.8	25.2	26.5	27.2
95°	24.7	21.1	21.3	21.5	21.7	22.0	23.3	24.6	26.0	27.3	28.1
97.5°	135.4	125.4	100.6	75.9	51.1	26.4	26.5	26.6	26.8	26.9	27.1
100°	179.7	166.4	135.8	105.2	74.5	43.9	40.2	36.4	32.6	28.8	27.1
102.5°	228.1	227.6	223.6	219.6	215.6	211.6	170.9	130.3	89.6	48.9	28.6
105°	305.8	307.0	308.1	309.2	310.4	311.5	313.5	315.5	317.4	319.4	316.5
107.5°	381.2	382.3	383.8	385.3	386.8	388.3	389.3	390.3	391.3	392.2	393.1
110°	433.9	434.9	436.2	437.6	438.9	440.2	440.7	441.1	441.6	442.0	442.6



TEST NUMBER: P332697

CATALOG NUMBER: S124DIP-S1195D1035U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	487.2	488.1	488.7	489.3	489.9	490.5	490.5	490.4	490.3	490.2	490.6
115°	563.7	563.9	563.7	563.5	563.2	563.0	563.5	563.9	564.4	564.8	565.0
117.5°	635.5	636.1	636.6	637.1	637.6	638.1	638.0	637.9	637.8	637.7	637.7
120°	683.4	683.7	683.5	683.3	683.0	682.8	683.3	683.7	684.1	684.6	684.6
122.5°	726.7	727.1	727.4	727.7	728.0	728.3	728.6	728.9	729.1	729.4	729.3
125°	792.2	792.4	792.0	791.5	791.1	790.6	791.3	792.0	792.6	793.3	793.7
127.5°	850.2	850.8	851.9	852.9	853.9	854.9	854.8	854.7	854.5	854.4	854.2
130°	889.3	889.8	890.5	891.1	891.8	892.5	892.7	892.9	893.1	893.3	893.5
132.5°	926.0	926.6	927.5	928.3	929.1	930.0	930.2	930.4	930.7	930.9	930.9
135°	977.4	977.7	978.6	979.5	980.4	981.3	981.7	982.2	982.6	983.1	983.5
137.5°	1026.4	1026.9	1027.9	1028.9	1029.8	1030.8	1031.3	1031.8	1032.3	1032.8	1032.9
140°	1058.9	1059.4	1059.8	1060.3	1060.7	1061.2	1061.8	1062.5	1063.2	1063.8	1064.3
142.5°	1088.3	1088.8	1089.1	1089.4	1089.6	1089.9	1090.4	1090.9	1091.4	1091.9	1092.1
145°	1130.7	1131.0	1131.0	1131.0	1131.0	1131.0	1131.3	1131.5	1131.7	1131.9	1132.3
147.5°	1167.2	1167.7	1167.4	1167.2	1167.0	1166.8	1167.0	1167.1	1167.3	1167.5	1167.7
150°	1190.5	1190.8	1190.6	1190.4	1190.2	1189.9	1189.9	1189.9	1189.9	1189.9	1190.0
152.5°	1210.5	1210.7	1210.3	1209.9	1209.5	1209.1	1209.5	1209.8	1210.2	1210.5	1210.6
155°	1237.7	1237.5	1236.9	1236.2	1235.5	1234.9	1235.7	1236.6	1237.5	1238.4	1238.5
157.5°	1260.9	1260.4	1259.7	1258.9	1258.2	1257.4	1258.6	1259.7	1260.9	1262.0	1262.0
160°	1273.1	1272.7	1272.5	1272.2	1272.0	1271.8	1273.1	1274.5	1275.8	1277.1	1277.1
162.5°	1285.2	1284.7	1284.4	1284.2	1284.0	1283.8	1285.1	1286.4	1287.8	1289.1	1289.0
165°	1300.3	1299.7	1299.7	1299.7	1299.7	1299.7	1301.5	1303.3	1305.1	1306.8	1306.7
167.5°	1312.9	1312.3	1312.1	1312.0	1311.9	1311.7	1313.7	1315.6	1317.6	1319.5	1319.4
170°	1319.4	1318.8	1319.0	1319.3	1319.5	1319.7	1321.5	1323.3	1325.0	1326.8	1326.6
172.5°	1324.2	1323.6	1323.8	1324.1	1324.3	1324.5	1326.3	1328.1	1329.8	1331.6	1331.3
175°	1329.4	1328.8	1329.0	1329.3	1329.5	1329.7	1331.7	1333.7	1335.7	1337.7	1337.3
177.5°	1332.1	1331.7	1332.0	1332.4	1332.7	1333.1	1334.5	1335.9	1337.3	1338.8	1338.4
180°	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7



TEST NUMBER: P332697

CATALOG NUMBER: S124DIP-S1195D1035U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4
2.5°	1836.7	1835.4	1830.9	1830.3	1830.9	1835.4	1836.7	1837.9	1839.9	1846.2	1838.6
5°	1696.6	1692.6	1690.2	1699.0	1690.2	1692.6	1696.6	1701.4	1709.4	1710.2	1718.2
7.5°	1591.1	1587.9	1580.9	1578.6	1580.9	1587.9	1591.1	1593.9	1601.9	1608.8	1620.6
10°	1523.4	1520.2	1513.8	1512.2	1513.8	1520.2	1523.4	1531.4	1539.3	1548.1	1556.1
12.5°	1458.2	1451.8	1450.6	1452.2	1450.6	1451.8	1458.2	1468.8	1489.5	1489.4	1491.0
15°	1371.7	1368.5	1359.7	1362.1	1359.7	1368.5	1371.7	1382.1	1391.6	1403.6	1415.6
17.5°	1286.4	1282.6	1271.9	1281.3	1271.9	1282.6	1286.4	1292.0	1304.3	1321.2	1339.3
20°	1232.7	1226.4	1220.8	1220.0	1220.8	1226.4	1232.7	1238.3	1251.9	1266.3	1279.9
22.5°	1181.6	1175.9	1175.4	1170.2	1175.4	1175.9	1181.6	1190.4	1204.0	1212.0	1224.9
25°	1117.8	1112.2	1110.6	1106.6	1110.6	1112.2	1117.8	1124.2	1132.9	1139.3	1153.7
27.5°	1068.8	1066.0	1063.2	1064.4	1063.2	1066.0	1068.8	1069.6	1073.5	1082.0	1090.3
30°	1038.7	1037.9	1036.3	1036.3	1036.3	1037.9	1038.7	1036.3	1040.3	1044.3	1050.7
32.5°	1013.8	1013.7	1014.6	1014.6	1014.6	1013.7	1013.8	1010.2	1011.6	1013.0	1016.2
35°	978.9	981.2	982.8	980.4	982.8	981.2	978.9	975.7	973.3	967.7	969.3
37.5°	947.2	949.6	951.9	954.6	951.9	949.6	947.2	940.7	934.9	930.0	924.2
40°	923.0	928.6	930.1	934.1	930.1	928.6	923.0	915.8	909.4	903.8	897.4
42.5°	900.0	906.2	910.3	911.1	910.3	906.2	900.0	892.8	883.2	876.3	867.4
45°	864.7	871.1	876.7	876.7	876.7	871.1	864.7	852.7	842.3	831.9	823.2
47.5°	828.1	837.4	843.0	844.4	843.0	837.4	828.1	815.8	801.3	788.5	775.9
50°	803.2	814.4	820.0	824.0	820.0	814.4	803.2	789.6	774.5	758.5	743.3
52.5°	778.9	790.1	797.6	799.7	797.6	790.1	778.9	762.2	743.8	726.6	713.3
55°	736.9	752.9	761.7	764.9	761.7	752.9	736.9	718.6	701.0	679.4	660.3
57.5°	697.3	712.0	722.2	724.6	722.2	712.0	697.3	675.8	653.1	630.1	609.7
60°	666.7	682.6	695.4	697.8	695.4	682.6	666.7	645.1	621.2	598.8	573.3
62.5°	635.4	652.0	663.5	669.7	663.5	652.0	635.4	612.5	586.7	561.8	536.2
65°	581.2	598.0	609.2	611.6	609.2	598.0	581.2	558.9	531.7	505.4	483.8
67.5°	522.2	538.9	546.3	550.9	546.3	538.9	522.2	501.1	474.3	447.0	422.5
70°	480.6	494.2	502.2	506.2	502.2	494.2	480.6	458.3	435.9	408.0	381.6
72.5°	433.4	447.6	456.9	457.6	456.9	447.6	433.4	414.2	390.6	364.6	341.4
75°	360.9	373.7	378.4	378.4	378.4	373.7	360.9	342.5	323.4	302.6	279.4
77.5°	285.7	292.2	298.3	299.6	298.3	292.2	285.7	272.4	256.6	235.9	218.4
80°	237.1	241.1	245.9	245.9	245.9	241.1	237.1	225.2	210.0	192.4	178.8
82.5°	187.3	190.7	195.5	194.8	195.5	190.7	187.3	177.9	165.3	153.5	141.2
85°	113.4	120.6	119.8	118.2	119.8	120.6	113.4	115.0	103.0	95.0	83.8
87.5°	56.8	57.5	59.6	60.9	59.6	57.5	56.8	54.8	48.9	45.4	42.6
90°	28.6	29.1	29.5	29.9	29.5	29.1	28.6	28.2	27.3	26.0	24.6
92.5°	27.3	27.4	27.5	27.6	27.5	27.4	27.3	27.2	26.5	25.2	23.8
95°	28.3	28.5	28.7	28.9	28.7	28.5	28.3	28.1	27.3	26.0	24.6
97.5°	27.3	27.5	27.7	28.0	27.7	27.5	27.3	27.1	26.9	26.8	26.6
100°	27.3	27.5	27.7	28.0	27.7	27.5	27.3	27.1	28.8	32.6	36.4
102.5°	28.6	28.7	28.7	28.8	28.7	28.7	28.6	28.6	48.9	89.6	130.3
105°	308.5	300.5	292.5	284.5	292.5	300.5	308.5	316.5	319.4	317.4	315.5
107.5°	394.0	394.8	395.7	396.5	395.7	394.8	394.0	393.1	392.2	391.3	390.3
110°	443.2	443.9	444.6	445.2	444.6	443.9	443.2	442.6	442.0	441.6	441.1



TEST NUMBER: P332697

CATALOG NUMBER: S124DIP-S1195D1035U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	491.4	492.3	493.1	493.9	493.1	492.3	491.4	490.6	490.2	490.3	490.4
115°	565.0	565.0	565.0	565.0	565.0	565.0	565.0	565.0	564.8	564.4	563.9
117.5°	637.6	637.5	637.4	637.3	637.4	637.5	637.6	637.7	637.7	637.8	637.9
120°	684.1	683.7	683.3	682.8	683.3	683.7	684.1	684.6	684.6	684.1	683.7
122.5°	728.9	728.4	728.0	727.5	728.0	728.4	728.9	729.3	729.4	729.1	728.9
125°	794.0	794.2	794.4	794.6	794.4	794.2	794.0	793.7	793.3	792.6	792.0
127.5°	854.1	853.9	853.7	853.5	853.7	853.9	854.1	854.2	854.4	854.5	854.7
130°	893.5	893.5	893.5	893.5	893.5	893.5	893.5	893.5	893.3	893.1	892.9
132.5°	930.7	930.5	930.4	930.2	930.4	930.5	930.7	930.9	930.9	930.7	930.4
135°	984.0	984.4	984.8	985.3	984.8	984.4	984.0	983.5	983.1	982.6	982.2
137.5°	1032.8	1032.7	1032.5	1032.4	1032.5	1032.7	1032.8	1032.9	1032.8	1032.3	1031.8
140°	1064.5	1064.7	1064.9	1065.2	1064.9	1064.7	1064.5	1064.3	1063.8	1063.2	1062.5
142.5°	1092.2	1092.2	1092.3	1092.3	1092.3	1092.2	1092.2	1092.1	1091.9	1091.4	1090.9
145°	1132.7	1133.1	1133.6	1134.0	1133.6	1133.1	1132.7	1132.3	1131.9	1131.7	1131.5
147.5°	1167.9	1168.1	1168.4	1168.6	1168.4	1168.1	1167.9	1167.7	1167.5	1167.3	1167.1
150°	1190.3	1190.5	1190.7	1190.9	1190.7	1190.5	1190.3	1190.0	1189.9	1189.9	1189.9
152.5°	1210.5	1210.4	1210.2	1210.1	1210.2	1210.4	1210.5	1210.6	1210.5	1210.2	1209.8
155°	1237.9	1237.2	1236.5	1235.9	1236.5	1237.2	1237.9	1238.5	1238.4	1237.5	1236.6
157.5°	1260.9	1259.7	1258.6	1257.4	1258.6	1259.7	1260.9	1262.0	1262.0	1260.9	1259.7
160°	1275.8	1274.5	1273.1	1271.8	1273.1	1274.5	1275.8	1277.1	1277.1	1275.8	1274.5
162.5°	1287.5	1286.0	1284.5	1283.0	1284.5	1286.0	1287.5	1289.0	1289.1	1287.8	1286.4
165°	1304.7	1302.7	1300.7	1298.7	1300.7	1302.7	1304.7	1306.7	1306.8	1305.1	1303.3
167.5°	1317.2	1315.0	1312.7	1310.5	1312.7	1315.0	1317.2	1319.4	1319.5	1317.6	1315.6
170°	1324.4	1322.2	1319.9	1317.7	1319.9	1322.2	1324.4	1326.6	1326.8	1325.0	1323.3
172.5°	1328.9	1326.5	1324.1	1321.7	1324.1	1326.5	1328.9	1331.3	1331.6	1329.8	1328.1
175°	1334.7	1332.0	1329.4	1326.7	1329.4	1332.0	1334.7	1337.3	1337.7	1335.7	1333.7
177.5°	1336.3	1334.2	1332.0	1329.9	1332.0	1334.2	1336.3	1338.4	1338.8	1337.3	1335.9
180°	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7



TEST NUMBER: P332697

CATALOG NUMBER: S124DIP-S1195D1035U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4
2.5°	1842.4	1845.0	1855.2	1864.8	1876.3	1884.6	1890.3	1896.7	1910.1	1921.0	1931.2
5°	1726.2	1730.2	1750.9	1765.3	1790.0	1811.6	1828.4	1846.7	1868.3	1897.8	1925.0
7.5°	1623.8	1638.7	1661.3	1684.6	1709.9	1738.1	1762.7	1790.4	1827.6	1868.1	1910.0
10°	1565.7	1582.5	1606.4	1633.6	1657.5	1690.2	1720.6	1753.3	1795.6	1845.1	1894.6
12.5°	1507.6	1535.2	1553.4	1585.6	1611.5	1638.5	1670.8	1713.7	1763.1	1815.1	1874.8
15°	1434.7	1449.9	1485.0	1502.6	1539.3	1580.9	1612.8	1655.9	1703.8	1772.5	1839.5
17.5°	1350.8	1370.7	1398.7	1432.2	1474.3	1506.8	1546.5	1590.9	1651.3	1719.5	1803.5
20°	1295.8	1312.6	1346.9	1383.6	1428.4	1462.7	1505.0	1548.1	1610.4	1683.1	1770.9
22.5°	1246.6	1262.8	1299.0	1333.2	1376.6	1418.6	1462.8	1513.0	1572.7	1649.2	1738.9
25°	1170.5	1192.0	1224.0	1259.1	1300.6	1348.5	1396.4	1441.1	1505.0	1585.6	1681.5
27.5°	1102.9	1120.2	1143.3	1183.2	1230.4	1276.7	1324.2	1380.5	1441.8	1527.0	1626.5
30°	1059.5	1075.5	1098.6	1135.3	1179.3	1228.8	1278.3	1332.5	1396.4	1481.1	1582.5
32.5°	1025.0	1037.1	1057.7	1090.6	1130.7	1182.8	1231.6	1287.8	1354.9	1438.3	1537.1
35°	974.1	984.4	992.4	1023.6	1059.5	1107.4	1156.9	1216.8	1281.5	1360.5	1459.5
37.5°	924.1	927.6	939.3	959.7	994.5	1038.6	1084.6	1143.5	1209.8	1290.1	1379.3
40°	893.4	895.0	902.2	921.4	951.7	993.2	1037.9	1096.2	1159.3	1235.1	1323.8
42.5°	863.4	862.4	869.0	882.4	910.8	948.5	992.6	1045.8	1108.8	1178.9	1262.4
45°	816.0	816.0	814.4	825.6	848.7	885.4	922.2	973.3	1026.0	1094.6	1164.9
47.5°	766.5	762.0	763.4	769.2	788.7	818.9	855.9	897.7	944.2	1002.3	1064.0
50°	734.5	728.2	725.8	732.1	749.7	776.1	811.2	847.9	891.8	942.9	995.6
52.5°	699.4	693.0	688.7	693.2	709.5	733.9	765.8	798.1	837.5	879.1	924.7
55°	645.1	637.9	635.5	637.1	649.1	668.3	695.4	725.0	754.5	788.8	820.8
57.5°	591.6	579.8	577.6	576.8	585.1	602.6	625.3	650.9	672.4	693.2	727.2
60°	556.5	542.1	537.3	536.5	542.9	557.3	578.0	603.6	618.8	633.1	662.7
62.5°	518.8	505.1	494.5	495.7	501.4	515.1	533.3	551.9	561.9	577.6	597.5
65°	460.7	443.1	435.1	432.7	435.9	447.1	461.5	473.5	484.6	491.0	510.2
67.5°	402.6	387.9	376.1	373.2	371.7	379.4	391.2	398.4	406.4	412.0	423.3
70°	361.7	348.9	334.5	329.7	328.9	335.3	346.5	347.3	358.5	360.9	372.9
72.5°	321.4	305.5	295.6	290.8	287.4	293.2	300.5	302.6	308.7	313.0	319.2
75°	258.7	246.7	237.1	229.9	227.5	230.7	230.7	234.7	238.7	241.1	248.3
77.5°	203.6	189.9	178.5	174.4	171.5	169.4	171.2	173.6	171.7	175.8	177.4
80°	165.3	150.9	142.1	140.5	135.7	131.7	130.9	133.3	130.1	131.7	136.5
82.5°	127.6	118.3	108.9	107.3	101.2	99.2	98.4	96.9	96.9	96.6	97.6
85°	75.8	70.3	63.9	59.9	57.5	53.5	53.5	51.9	50.3	48.7	49.5
87.5°	35.3	33.8	30.2	28.0	26.3	23.4	23.0	20.6	19.5	18.3	17.2
90°	23.3	22.0	20.2	18.4	16.6	14.9	12.8	10.3	7.9	5.4	3.0
92.5°	22.5	21.2	19.4	17.6	15.8	14.1	13.1	13.0	12.8	12.7	12.6
95°	23.3	22.0	21.7	21.5	21.3	21.1	24.7	32.3	39.8	47.4	54.9
97.5°	26.5	26.4	51.1	75.9	100.6	125.4	135.4	130.7	126.0	121.3	116.6
100°	40.2	43.9	74.5	105.2	135.8	166.4	179.7	175.7	171.7	167.7	163.7
102.5°	170.9	211.6	215.6	219.6	223.6	227.6	228.1	225.2	222.3	219.4	216.4
105°	313.5	311.5	310.4	309.2	308.1	307.0	305.8	304.5	303.1	301.8	300.5
107.5°	389.3	388.3	386.8	385.3	383.8	382.3	381.2	380.5	379.9	379.2	378.5
110°	440.7	440.2	438.9	437.6	436.2	434.9	433.9	433.2	432.6	431.9	431.3



TEST NUMBER: P332697

CATALOG NUMBER: S124DIP-S1195D1035U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	490.5	490.5	489.9	489.3	488.7	488.1	487.2	486.0	484.8	483.6	482.4
115°	563.5	563.0	563.2	563.5	563.7	563.9	563.7	563.0	562.4	561.7	561.0
117.5°	638.0	638.1	637.6	637.1	636.6	636.1	635.5	634.6	633.7	632.8	631.9
120°	683.3	682.8	683.0	683.3	683.5	683.7	683.4	682.5	681.6	680.7	679.8
122.5°	728.6	728.3	728.0	727.7	727.4	727.1	726.7	726.1	725.6	725.1	724.5
125°	791.3	790.6	791.1	791.5	792.0	792.4	792.2	791.3	790.4	789.5	788.6
127.5°	854.8	854.9	853.9	852.9	851.9	850.8	850.2	850.0	849.8	849.5	849.3
130°	892.7	892.5	891.8	891.1	890.5	889.8	889.3	889.1	888.9	888.7	888.5
132.5°	930.2	930.0	929.1	928.3	927.5	926.6	926.0	925.6	925.2	924.8	924.4
135°	981.7	981.3	980.4	979.5	978.6	977.7	977.4	977.6	977.9	978.1	978.3
137.5°	1031.3	1030.8	1029.8	1028.9	1027.9	1026.9	1026.4	1026.3	1026.2	1026.1	1026.0
140°	1061.8	1061.2	1060.7	1060.3	1059.8	1059.4	1058.9	1058.5	1058.1	1057.6	1057.2
142.5°	1090.4	1089.9	1089.6	1089.4	1089.1	1088.8	1088.3	1087.5	1086.7	1085.9	1085.1
145°	1131.3	1131.0	1131.0	1131.0	1131.0	1131.0	1130.7	1130.0	1129.4	1128.7	1128.0
147.5°	1167.0	1166.8	1167.0	1167.2	1167.4	1167.7	1167.2	1165.9	1164.7	1163.4	1162.2
150°	1189.9	1189.9	1190.2	1190.4	1190.6	1190.8	1190.5	1189.6	1188.7	1187.8	1186.9
152.5°	1209.5	1209.1	1209.5	1209.9	1210.3	1210.7	1210.5	1209.8	1209.1	1208.4	1207.7
155°	1235.7	1234.9	1235.5	1236.2	1236.9	1237.5	1237.7	1237.5	1237.3	1237.1	1236.9
157.5°	1258.6	1257.4	1258.2	1258.9	1259.7	1260.4	1260.9	1261.0	1261.1	1261.3	1261.4
160°	1273.1	1271.8	1272.0	1272.2	1272.5	1272.7	1273.1	1273.8	1274.5	1275.1	1275.8
162.5°	1285.1	1283.8	1284.0	1284.2	1284.4	1284.7	1285.2	1286.0	1286.9	1287.7	1288.6
165°	1301.5	1299.7	1299.7	1299.7	1299.7	1299.7	1300.3	1301.4	1302.5	1303.6	1304.7
167.5°	1313.7	1311.7	1311.9	1312.0	1312.1	1312.3	1312.9	1314.1	1315.2	1316.4	1317.5
170°	1321.5	1319.7	1319.5	1319.3	1319.0	1318.8	1319.4	1320.7	1322.0	1323.4	1324.7
172.5°	1326.3	1324.5	1324.3	1324.1	1323.8	1323.6	1324.2	1325.5	1326.8	1328.2	1329.5
175°	1331.7	1329.7	1329.5	1329.3	1329.0	1328.8	1329.4	1330.7	1332.0	1333.4	1334.7
177.5°	1334.5	1333.1	1332.7	1332.4	1332.0	1331.7	1332.1	1333.4	1334.6	1335.8	1337.1
180°	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7



TEST NUMBER: P332697

CATALOG NUMBER: S124DIP-S1195D1035U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4
2.5°	1940.1	1946.5	1954.8	1968.9	1974.0	1980.4	1989.3	1988.7	1991.2	2000.8	2021.3
5°	1947.3	1972.1	1996.0	2024.8	2055.1	2075.1	2102.2	2119.0	2135.8	2157.3	2194.0
7.5°	1950.2	1989.5	2033.4	2083.9	2128.7	2180.5	2220.9	2258.9	2293.2	2338.7	2382.5
10°	1945.7	1998.4	2055.1	2119.0	2186.8	2244.3	2296.2	2355.3	2405.6	2460.7	2510.2
12.5°	1937.4	2001.0	2076.8	2148.4	2227.7	2312.7	2377.4	2437.1	2504.0	2567.4	2643.7
15°	1918.6	2005.6	2094.2	2188.4	2294.6	2392.8	2486.3	2563.7	2635.6	2730.6	2830.4
17.5°	1894.6	1988.5	2100.3	2214.3	2325.3	2437.6	2553.2	2669.6	2760.3	2878.3	2956.4
20°	1872.3	1980.9	2095.8	2231.6	2342.5	2482.3	2597.2	2709.8	2834.4	2951.7	3045.1
22.5°	1841.0	1959.8	2081.8	2216.9	2363.0	2502.7	2635.6	2757.7	2882.3	3009.9	3123.1
25°	1801.2	1909.0	2053.5	2206.8	2352.1	2503.8	2656.3	2809.6	2943.7	3078.7	3184.1
27.5°	1733.5	1869.6	2004.2	2162.4	2323.9	2495.5	2658.6	2819.0	2959.6	3070.5	3135.8
30°	1699.0	1817.2	1963.3	2122.2	2297.0	2481.5	2651.5	2808.8	2939.8	3028.4	3054.7
32.5°	1647.9	1769.9	1912.8	2077.5	2262.5	2452.1	2629.2	2777.5	2886.7	2933.2	2901.4
35°	1572.1	1682.3	1826.8	1995.2	2187.6	2389.6	2564.5	2689.8	2745.7	2701.8	2592.4
37.5°	1481.1	1590.3	1735.4	1900.9	2100.0	2305.3	2463.4	2553.6	2535.1	2425.9	2262.9
40°	1417.2	1519.4	1657.5	1836.3	2030.4	2236.4	2375.3	2424.0	2372.9	2216.4	2043.1
42.5°	1346.3	1445.9	1584.7	1757.1	1962.7	2152.7	2273.7	2277.7	2192.1	2005.0	1831.1
45°	1238.3	1333.3	1464.3	1643.9	1834.0	2012.8	2092.6	2053.5	1895.4	1715.0	1540.1
47.5°	1131.8	1214.2	1343.2	1513.8	1694.2	1844.8	1884.4	1814.0	1645.5	1470.4	1308.3
50°	1053.9	1136.9	1258.3	1421.2	1595.2	1725.4	1744.5	1651.1	1485.8	1309.4	1182.4
52.5°	979.2	1061.6	1178.5	1329.2	1488.6	1605.9	1606.6	1498.5	1333.8	1176.5	1058.5
55°	869.5	943.7	1049.1	1184.0	1326.2	1418.0	1395.6	1283.8	1140.9	1004.4	901.4
57.5°	763.8	828.4	925.5	1038.1	1163.3	1239.0	1201.9	1094.3	966.7	850.9	772.9
60°	695.4	756.9	839.9	946.1	1051.5	1110.6	1075.5	978.1	860.7	767.3	699.4
62.5°	629.0	680.9	760.7	852.9	950.6	994.3	963.0	866.9	765.5	681.0	626.0
65°	534.9	577.3	641.1	720.2	791.2	828.8	802.4	713.0	635.5	574.9	530.9
67.5°	447.1	480.2	528.5	591.9	652.3	672.6	648.6	586.4	520.7	472.2	441.2
70°	386.4	417.6	458.3	507.0	559.7	581.2	557.3	507.8	454.3	409.6	379.2
72.5°	333.4	357.5	391.9	433.5	474.7	496.3	480.0	432.4	387.2	354.0	328.1
75°	253.9	274.7	298.6	328.1	360.1	374.5	360.1	327.3	296.2	271.5	253.1
77.5°	184.6	195.8	214.3	236.3	256.3	267.3	254.9	232.7	213.7	196.7	187.6
80°	140.5	148.5	161.3	178.8	192.4	202.8	194.8	176.4	161.3	150.1	146.1
82.5°	102.2	107.6	115.9	129.0	138.1	143.4	139.9	126.6	120.4	110.5	106.5
85°	50.3	53.5	59.1	63.1	71.1	71.9	72.7	67.1	61.5	59.1	55.9
87.5°	18.3	19.5	21.9	24.3	27.2	28.2	28.0	28.3	26.1	25.7	23.4
90°	5.4	7.9	10.3	12.8	14.9	16.6	18.4	20.2	22.0	23.3	24.6
92.5°	12.7	12.8	13.0	13.1	14.1	15.8	17.6	19.4	21.2	22.5	23.8
95°	47.4	39.8	32.3	24.7	21.1	21.3	21.5	21.7	22.0	23.3	24.6
97.5°	121.3	126.0	130.7	135.4	125.4	100.6	75.9	51.1	26.4	26.5	26.6
100°	167.7	171.7	175.7	179.7	166.4	135.8	105.2	74.5	43.9	40.2	36.4
102.5°	219.4	222.3	225.2	228.1	227.6	223.6	219.6	215.6	211.6	170.9	130.3
105°	301.8	303.1	304.5	305.8	307.0	308.1	309.2	310.4	311.5	313.5	315.5
107.5°	379.2	379.9	380.5	381.2	382.3	383.8	385.3	386.8	388.3	389.3	390.3
110°	431.9	432.6	433.2	433.9	434.9	436.2	437.6	438.9	440.2	440.7	441.1



TEST NUMBER: P332697

CATALOG NUMBER: S124DIP-S1195D1035U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	483.6	484.8	486.0	487.2	488.1	488.7	489.3	489.9	490.5	490.5	490.4
115°	561.7	562.4	563.0	563.7	563.9	563.7	563.5	563.2	563.0	563.5	563.9
117.5°	632.8	633.7	634.6	635.5	636.1	636.6	637.1	637.6	638.1	638.0	637.9
120°	680.7	681.6	682.5	683.4	683.7	683.5	683.3	683.0	682.8	683.3	683.7
122.5°	725.1	725.6	726.1	726.7	727.1	727.4	727.7	728.0	728.3	728.6	728.9
125°	789.5	790.4	791.3	792.2	792.4	792.0	791.5	791.1	790.6	791.3	792.0
127.5°	849.5	849.8	850.0	850.2	850.8	851.9	852.9	853.9	854.9	854.8	854.7
130°	888.7	888.9	889.1	889.3	889.8	890.5	891.1	891.8	892.5	892.7	892.9
132.5°	924.8	925.2	925.6	926.0	926.6	927.5	928.3	929.1	930.0	930.2	930.4
135°	978.1	977.9	977.6	977.4	977.7	978.6	979.5	980.4	981.3	981.7	982.2
137.5°	1026.1	1026.2	1026.3	1026.4	1026.9	1027.9	1028.9	1029.8	1030.8	1031.3	1031.8
140°	1057.6	1058.1	1058.5	1058.9	1059.4	1059.8	1060.3	1060.7	1061.2	1061.8	1062.5
142.5°	1085.9	1086.7	1087.5	1088.3	1088.8	1089.1	1089.4	1089.6	1089.9	1090.4	1090.9
145°	1128.7	1129.4	1130.0	1130.7	1131.0	1131.0	1131.0	1131.0	1131.0	1131.3	1131.5
147.5°	1163.4	1164.7	1165.9	1167.2	1167.7	1167.4	1167.2	1167.0	1166.8	1167.0	1167.1
150°	1187.8	1188.7	1189.6	1190.5	1190.8	1190.6	1190.4	1190.2	1189.9	1189.9	1189.9
152.5°	1208.4	1209.1	1209.8	1210.5	1210.7	1210.3	1209.9	1209.5	1209.1	1209.5	1209.8
155°	1237.1	1237.3	1237.5	1237.7	1237.5	1236.9	1236.2	1235.5	1234.9	1235.7	1236.6
157.5°	1261.3	1261.1	1261.0	1260.9	1260.4	1259.7	1258.9	1258.2	1257.4	1258.6	1259.7
160°	1275.1	1274.5	1273.8	1273.1	1272.7	1272.5	1272.2	1272.0	1271.8	1273.1	1274.5
162.5°	1287.7	1286.9	1286.0	1285.2	1284.7	1284.4	1284.2	1284.0	1283.8	1285.1	1286.4
165°	1303.6	1302.5	1301.4	1300.3	1299.7	1299.7	1299.7	1299.7	1299.7	1301.5	1303.3
167.5°	1316.4	1315.2	1314.1	1312.9	1312.3	1312.1	1312.0	1311.9	1311.7	1313.7	1315.6
170°	1323.4	1322.0	1320.7	1319.4	1318.8	1319.0	1319.3	1319.5	1319.7	1321.5	1323.3
172.5°	1328.2	1326.8	1325.5	1324.2	1323.6	1323.8	1324.1	1324.3	1324.5	1326.3	1328.1
175°	1333.4	1332.0	1330.7	1329.4	1328.8	1329.0	1329.3	1329.5	1329.7	1331.7	1333.7
177.5°	1335.8	1334.6	1333.4	1332.1	1331.7	1332.0	1332.4	1332.7	1333.1	1334.5	1335.9
180°	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7



TEST NUMBER: P332697

CATALOG NUMBER: S124DIP-S1195D1035U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4
2.5°	2031.5	2032.8	2038.5	2043.0	2044.3	2050.6	2051.3
5°	2210.0	2223.6	2249.9	2252.3	2256.3	2277.1	2261.1
7.5°	2419.2	2453.7	2476.7	2497.0	2504.3	2513.4	2511.5
10°	2553.3	2604.4	2630.0	2670.7	2672.3	2682.7	2676.3
12.5°	2688.1	2747.5	2794.1	2801.6	2835.8	2841.1	2850.0
15°	2879.1	2942.1	3006.8	3030.0	3077.1	3088.3	3105.8
17.5°	3058.6	3123.1	3168.4	3228.3	3247.6	3273.5	3255.9
20°	3156.9	3227.2	3284.7	3331.8	3351.7	3366.1	3364.5
22.5°	3216.3	3287.2	3333.8	3369.5	3388.1	3394.2	3393.9
25°	3253.5	3294.2	3308.6	3322.2	3301.4	3294.2	3297.4
27.5°	3150.1	3139.5	3102.0	3052.8	3001.7	2961.1	2939.1
30°	3007.6	2945.3	2888.7	2789.6	2738.6	2708.2	2681.1
32.5°	2805.8	2707.1	2598.0	2507.3	2449.2	2404.2	2397.5
35°	2459.9	2311.4	2178.1	2067.1	2009.6	1960.9	1949.7
37.5°	2091.4	1937.1	1817.0	1719.3	1657.5	1623.2	1591.1
40°	1846.7	1714.2	1596.0	1513.0	1465.9	1441.1	1421.2
42.5°	1658.3	1537.3	1419.7	1356.5	1313.9	1298.7	1287.0
45°	1398.0	1285.4	1204.0	1156.1	1131.3	1105.8	1093.8
47.5°	1189.6	1098.0	1044.3	1003.6	977.1	961.9	954.3
50°	1071.5	996.4	948.5	917.4	893.4	881.4	875.1
52.5°	966.7	905.1	864.8	840.1	823.8	815.0	812.5
55°	832.7	785.6	760.1	738.5	726.6	718.6	715.4
57.5°	723.8	687.6	666.8	649.1	644.5	637.8	635.5
60°	652.3	624.4	606.8	594.8	590.8	582.8	584.4
62.5°	589.1	566.2	551.2	544.4	539.1	532.4	534.6
65°	498.2	481.4	473.5	467.1	460.7	456.7	459.9
67.5°	418.0	406.6	395.7	392.0	388.8	388.2	384.8
70°	365.7	356.1	346.5	344.1	344.1	340.9	340.1
72.5°	315.2	308.2	301.8	300.0	297.5	298.8	295.4
75°	243.5	237.9	235.5	233.1	232.3	232.3	229.9
77.5°	180.0	175.8	172.0	172.0	169.1	168.0	167.7
80°	136.5	134.9	131.7	131.7	130.1	130.9	129.3
82.5°	102.7	100.4	99.8	98.5	96.3	96.4	94.9
85°	55.1	52.7	51.9	49.5	47.9	49.5	47.9
87.5°	24.4	24.0	23.5	22.3	21.8	21.9	20.0
90°	26.0	27.3	28.2	28.6	29.1	29.5	29.9
92.5°	25.2	26.5	27.2	27.3	27.4	27.5	27.6
95°	26.0	27.3	28.1	28.3	28.5	28.7	28.9
97.5°	26.8	26.9	27.1	27.3	27.5	27.7	28.0
100°	32.6	28.8	27.1	27.3	27.5	27.7	28.0
102.5°	89.6	48.9	28.6	28.6	28.7	28.7	28.8
105°	317.4	319.4	316.5	308.5	300.5	292.5	284.5
107.5°	391.3	392.2	393.1	394.0	394.8	395.7	396.5
110°	441.6	442.0	442.6	443.2	443.9	444.6	445.2



TEST NUMBER: P332697

CATALOG NUMBER: S124DIP-S1195D1035U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	490.3	490.2	490.6	491.4	492.3	493.1	493.9
115°	564.4	564.8	565.0	565.0	565.0	565.0	565.0
117.5°	637.8	637.7	637.7	637.6	637.5	637.4	637.3
120°	684.1	684.6	684.6	684.1	683.7	683.3	682.8
122.5°	729.1	729.4	729.3	728.9	728.4	728.0	727.5
125°	792.6	793.3	793.7	794.0	794.2	794.4	794.6
127.5°	854.5	854.4	854.2	854.1	853.9	853.7	853.5
130°	893.1	893.3	893.5	893.5	893.5	893.5	893.5
132.5°	930.7	930.9	930.9	930.7	930.5	930.4	930.2
135°	982.6	983.1	983.5	984.0	984.4	984.8	985.3
137.5°	1032.3	1032.8	1032.9	1032.8	1032.7	1032.5	1032.4
140°	1063.2	1063.8	1064.3	1064.5	1064.7	1064.9	1065.2
142.5°	1091.4	1091.9	1092.1	1092.2	1092.2	1092.3	1092.3
145°	1131.7	1131.9	1132.3	1132.7	1133.1	1133.6	1134.0
147.5°	1167.3	1167.5	1167.7	1167.9	1168.1	1168.4	1168.6
150°	1189.9	1189.9	1190.0	1190.3	1190.5	1190.7	1190.9
152.5°	1210.2	1210.5	1210.6	1210.5	1210.4	1210.2	1210.1
155°	1237.5	1238.4	1238.5	1237.9	1237.2	1236.5	1235.9
157.5°	1260.9	1262.0	1262.0	1260.9	1259.7	1258.6	1257.4
160°	1275.8	1277.1	1277.1	1275.8	1274.5	1273.1	1271.8
162.5°	1287.8	1289.1	1289.0	1287.5	1286.0	1284.5	1283.0
165°	1305.1	1306.8	1306.7	1304.7	1302.7	1300.7	1298.7
167.5°	1317.6	1319.5	1319.4	1317.2	1315.0	1312.7	1310.5
170°	1325.0	1326.8	1326.6	1324.4	1322.2	1319.9	1317.7
172.5°	1329.8	1331.6	1331.3	1328.9	1326.5	1324.1	1321.7
175°	1335.7	1337.7	1337.3	1334.7	1332.0	1329.4	1326.7
177.5°	1337.3	1338.8	1338.4	1336.3	1334.2	1332.0	1329.9
180°	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7

(END OF REPORT)