

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332699

Luminaire Tested: **S124DIP-S1195D1035U835-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332699
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIP-S1195D1035U835-4F0-1E-UDD-A4
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1195 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1035 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9016.1 lumens
Efficiency: N/A
Efficacy: 135.0 lumens/watt
Spacing Criteria (0/90/45): 1.31 / 1.23 / 1.41
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 66.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332699

CATALOG NUMBER: S124DIP-S1195D1035U835-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P332699

CATALOG NUMBER: S124DIP-S1195D1035U835-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64	59
1	100	96	92	88	93	90	86	83	78	75	73	67	65	64	57	56	55	50
2	91	84	78	73	85	79	73	69	69	65	61	59	56	54	51	49	47	42
3	84	74	67	61	78	69	63	58	61	56	52	53	49	46	45	42	40	36
4	77	66	58	52	71	62	55	49	54	49	44	47	43	39	41	37	35	31
5	70	59	51	45	66	55	48	43	49	43	38	42	38	34	37	33	30	27
6	65	53	45	39	60	50	42	37	44	38	34	38	34	30	33	30	27	24
7	60	48	40	34	56	45	38	33	40	34	30	35	30	27	31	27	24	22
8	56	44	36	30	52	41	34	29	36	31	27	32	27	24	28	24	22	19
9	52	40	32	27	49	38	31	26	34	28	24	30	25	22	26	22	20	17
10	49	37	29	24	46	35	28	24	31	25	22	27	23	20	24	20	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	15560	15560	15560	15560
5°	18323	15600	13768	15600
10°	21939	15531	12396	15531
15°	25957	15374	11384	15374
20°	28905	15214	10481	15214
25°	29372	14978	9857	14978
30°	24993	14752	9660	14752
35°	19215	14384	9662	14384
40°	14977	13951	9844	13951
45°	12488	13300	10009	13300
50°	10991	12504	10349	12504
55°	10069	11553	10766	11553
60°	9436	10700	11267	10700
65°	8785	9746	11683	9746
70°	8028	8802	11948	8802
75°	7171	7745	11803	7745
80°	6011	6346	11432	6346
85°	4437	4585	10948	4585



TEST NUMBER: P332699

CATALOG NUMBER: S124DIP-S1195D1035U835-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	187.8	2.1
10°-20°	578.8	6.4
20°-30°	917.8	10.2
30°-40°	1021.3	11.3
40°-50°	929.7	10.3
50°-60°	759.7	8.4
60°-70°	542.4	6.0
70°-80°	298.7	3.3
80°-90°	84.3	0.9
90°-100°	367.0	4.1
100°-110°	763.9	8.5
110°-120°	684.2	7.6
120°-130°	575.5	6.4
130°-140°	479.9	5.3
140°-150°	366.6	4.1
150°-160°	257.7	2.9
160°-170°	151.6	1.7
170°-180°	49.3	0.5
0°-30°	1684.3	18.7
0°-40°	2705.6	30.0
0°-60°	4395.1	48.7
0°-90°	5320.5	59.0
90°-120°	1815.1	20.1
90°-150°	3237.1	35.9
90°-180°	3696.0	41.0
0°-180°	9016.1	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1927	1927	1927	1927	1927	
5°	2261	1925	1699	1925	2261	230
15°	3106	1840	1362	1840	3106	878
25°	3297	1682	1107	1682	3297	1454
35°	1950	1460	980	1460	1950	1238
45°	1094	1165	877	1165	1094	862
55°	715	821	765	821	715	646
65°	460	510	612	510	460	455
75°	230	248	378	248	230	244
85°	48	50	118	50	48	59
90°	21	1	21	1	21	19
95°	244	33	244	33	244	378
105°	1405	117	1405	117	1405	1389
115°	1349	206	1349	206	1349	1339
125°	1076	286	1076	286	1076	978
135°	962	340	962	340	962	743
145°	786	392	786	392	786	498
155°	658	446	658	446	658	307
165°	574	486	574	486	574	165
175°	517	507	517	507	517	50
180°	508	508	508	508	508	



TEST NUMBER: P332699

CATALOG NUMBER: S124DIP-S1195D1035U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4
2.5°	2051.3	2050.6	2044.3	2043.0	2038.5	2032.8	2031.5	2021.3	2000.8	1991.2	1988.7
5°	2261.1	2277.1	2256.3	2252.3	2249.9	2223.6	2210.0	2194.0	2157.3	2135.8	2119.0
7.5°	2511.5	2513.4	2504.3	2497.0	2476.7	2453.7	2419.2	2382.5	2338.7	2293.2	2258.9
10°	2676.3	2682.7	2672.3	2670.7	2630.0	2604.4	2553.3	2510.2	2460.7	2405.6	2355.3
12.5°	2850.0	2841.1	2835.8	2801.6	2794.1	2747.5	2688.1	2643.7	2567.4	2504.0	2437.1
15°	3105.8	3088.3	3077.1	3030.0	3006.8	2942.1	2879.1	2830.4	2730.6	2635.6	2563.7
17.5°	3255.9	3273.5	3247.6	3228.3	3168.4	3123.1	3058.6	2956.4	2878.3	2760.3	2669.6
20°	3364.5	3366.1	3351.7	3331.8	3284.7	3227.2	3156.9	3045.1	2951.7	2834.4	2709.8
22.5°	3393.9	3394.2	3388.1	3369.5	3333.8	3287.2	3216.3	3123.1	3009.9	2882.3	2757.7
25°	3297.4	3294.2	3301.4	3322.2	3308.6	3294.2	3253.5	3184.1	3078.7	2943.7	2809.6
27.5°	2939.1	2961.1	3001.7	3052.8	3102.0	3139.5	3150.1	3135.8	3070.5	2959.6	2819.0
30°	2681.1	2708.2	2738.6	2789.6	2888.7	2945.3	3007.6	3054.7	3028.4	2939.8	2808.8
32.5°	2397.5	2404.2	2449.2	2507.3	2598.0	2707.1	2805.8	2901.4	2933.2	2886.7	2777.5
35°	1949.7	1960.9	2009.6	2067.1	2178.1	2311.4	2459.9	2592.4	2701.8	2745.7	2689.8
37.5°	1591.1	1623.2	1657.5	1719.3	1817.0	1937.1	2091.4	2262.9	2425.9	2535.1	2553.6
40°	1421.2	1441.1	1465.9	1513.0	1596.0	1714.2	1846.7	2043.1	2216.4	2372.9	2424.0
42.5°	1287.0	1298.7	1313.9	1356.5	1419.7	1537.3	1658.3	1831.1	2005.0	2192.1	2277.7
45°	1093.8	1105.8	1131.3	1156.1	1204.0	1285.4	1398.0	1540.1	1715.0	1895.4	2053.5
47.5°	954.3	961.9	977.1	1003.6	1044.3	1098.0	1189.6	1308.3	1470.4	1645.5	1814.0
50°	875.1	881.4	893.4	917.4	948.5	996.4	1071.5	1182.4	1309.4	1485.8	1651.1
52.5°	812.5	815.0	823.8	840.1	864.8	905.1	966.7	1058.5	1176.5	1333.8	1498.5
55°	715.4	718.6	726.6	738.5	760.1	785.6	832.7	901.4	1004.4	1140.9	1283.8
57.5°	635.5	637.8	644.5	649.1	666.8	687.6	723.8	772.9	850.9	966.7	1094.3
60°	584.4	582.8	590.8	594.8	606.8	624.4	652.3	699.4	767.3	860.7	978.1
62.5°	534.6	532.4	539.1	544.4	551.2	566.2	589.1	626.0	681.0	765.5	866.9
65°	459.9	456.7	460.7	467.1	473.5	481.4	498.2	530.9	574.9	635.5	713.0
67.5°	384.8	388.2	388.8	392.0	395.7	406.6	418.0	441.2	472.2	520.7	586.4
70°	340.1	340.9	344.1	344.1	346.5	356.1	365.7	379.2	409.6	454.3	507.8
72.5°	295.4	298.8	297.5	300.0	301.8	308.2	315.2	328.1	354.0	387.2	432.4
75°	229.9	232.3	232.3	233.1	235.5	237.9	243.5	253.1	271.5	296.2	327.3
77.5°	167.7	168.0	169.1	172.0	172.0	175.8	180.0	187.6	196.7	213.7	232.7
80°	129.3	130.9	130.1	131.7	131.7	134.9	136.5	146.1	150.1	161.3	176.4
82.5°	94.9	96.4	96.3	98.5	99.8	100.4	102.7	106.5	110.5	120.4	126.6
85°	47.9	49.5	47.9	49.5	51.9	52.7	55.1	55.9	59.1	61.5	67.1
87.5°	18.2	20.2	20.4	20.8	21.9	22.5	23.0	22.1	24.5	25.3	27.5
90°	21.0	21.0	22.0	21.0	20.0	20.0	19.0	18.0	17.0	18.0	16.0
92.5°	76.9	76.9	80.3	85.7	97.4	117.4	147.6	196.1	263.8	316.7	277.1
95°	243.6	256.6	274.5	305.5	354.4	451.2	585.0	739.7	836.6	813.6	614.0
97.5°	651.1	671.9	701.8	761.9	833.6	937.8	1035.4	1093.0	1051.0	856.9	574.6
100°	915.5	923.4	953.4	1014.3	1101.1	1175.0	1223.9	1204.0	1058.2	802.6	521.1
102.5°	1145.5	1151.9	1183.4	1227.5	1280.8	1311.6	1297.4	1198.4	998.3	734.8	485.2
105°	1404.6	1410.6	1424.6	1432.6	1430.6	1389.6	1290.8	1118.1	889.5	654.9	454.2
107.5°	1500.9	1498.3	1488.3	1465.5	1416.2	1327.2	1188.0	1004.1	801.6	610.2	448.6
110°	1502.5	1493.5	1475.5	1433.6	1362.7	1252.9	1108.1	935.4	757.7	595.0	450.2



TEST NUMBER: P332699

CATALOG NUMBER: S124DIP-S1195D1035U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1455.3	1440.8	1415.6	1364.9	1284.4	1174.6	1037.8	885.1	733.0	587.8	455.0
115°	1348.7	1340.7	1308.8	1248.9	1170.0	1074.2	957.4	834.6	709.8	584.0	464.2
117.5°	1240.7	1234.5	1202.2	1151.9	1084.6	1003.3	911.5	809.8	699.4	583.0	474.0
120°	1180.0	1169.0	1143.1	1099.1	1042.2	971.4	891.5	798.6	693.8	583.0	481.2
122.5°	1132.1	1121.1	1099.1	1061.6	1013.5	951.4	878.7	789.1	687.4	582.2	488.4
125°	1076.2	1070.2	1051.2	1022.3	982.3	927.4	858.5	772.7	676.9	581.0	499.2
127.5°	1043.4	1037.4	1021.5	995.7	955.6	903.5	834.8	752.7	662.7	578.8	507.7
130°	1024.3	1018.3	1002.3	977.3	936.4	883.5	815.6	736.8	653.9	578.0	514.1
132.5°	1002.7	996.7	981.5	953.4	913.3	860.3	794.1	720.0	645.9	577.2	519.7
135°	962.4	956.4	940.4	912.5	872.5	822.6	761.7	696.8	633.9	576.0	528.1
137.5°	912.5	905.3	892.1	864.5	827.2	782.1	730.8	675.9	623.5	575.8	533.1
140°	876.5	868.5	854.6	832.6	797.6	755.7	710.8	663.9	618.0	575.0	537.1
142.5°	838.2	832.6	820.2	799.8	768.9	732.6	694.0	652.7	613.2	575.0	540.3
145°	785.7	780.7	770.7	753.7	728.8	700.8	670.9	636.9	605.0	573.0	542.1
147.5°	739.1	737.4	729.8	715.2	696.8	674.9	650.9	623.9	597.6	569.4	543.1
150°	712.8	711.8	705.8	692.8	676.9	658.9	638.9	616.0	592.0	567.0	543.1
152.5°	688.8	687.8	684.2	673.7	660.1	645.3	626.9	607.2	585.6	563.0	541.5
155°	657.9	657.9	654.9	646.9	636.9	624.9	610.0	594.0	576.0	557.1	539.1
157.5°	630.7	630.7	628.9	622.9	615.4	605.8	593.2	579.8	566.2	550.9	536.5
160°	614.0	614.0	613.0	607.0	601.0	593.0	582.0	571.0	559.1	546.1	534.1
162.5°	598.0	598.8	597.8	591.8	587.4	580.2	571.6	562.2	552.7	541.3	531.7
165°	574.0	575.0	576.0	572.0	568.0	563.0	556.1	550.1	542.1	534.1	527.1
167.5°	555.1	555.9	556.1	553.5	551.5	548.5	542.9	538.3	532.5	526.9	522.3
170°	543.1	543.1	544.1	543.1	541.1	538.1	534.1	531.1	526.1	522.1	519.1
172.5°	531.1	532.7	533.7	532.7	531.5	529.3	526.9	524.7	520.5	517.3	515.9
175°	517.1	519.1	521.1	519.1	519.1	519.1	517.1	516.1	514.1	512.1	512.1
177.5°	508.9	510.5	512.1	511.3	512.1	511.3	511.3	510.5	509.7	508.9	508.9
180°	508.1	508.1	508.1	508.1	508.1	508.1	508.1	508.1	508.1	508.1	508.1



TEST NUMBER: P332699

CATALOG NUMBER: S124DIP-S1195D1035U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4
2.5°	1989.3	1980.4	1974.0	1968.9	1954.8	1946.5	1940.1	1931.2	1921.0	1910.1	1896.7
5°	2102.2	2075.1	2055.1	2024.8	1996.0	1972.1	1947.3	1925.0	1897.8	1868.3	1846.7
7.5°	2220.9	2180.5	2128.7	2083.9	2033.4	1989.5	1950.2	1910.0	1868.1	1827.6	1790.4
10°	2296.2	2244.3	2186.8	2119.0	2055.1	1998.4	1945.7	1894.6	1845.1	1795.6	1753.3
12.5°	2377.4	2312.7	2227.7	2148.4	2076.8	2001.0	1937.4	1874.8	1815.1	1763.1	1713.7
15°	2486.3	2392.8	2294.6	2188.4	2094.2	2005.6	1918.6	1839.5	1772.5	1703.8	1655.9
17.5°	2553.2	2437.6	2325.3	2214.3	2100.3	1988.5	1894.6	1803.5	1719.5	1651.3	1590.9
20°	2597.2	2482.3	2342.5	2231.6	2095.8	1980.9	1872.3	1770.9	1683.1	1610.4	1548.1
22.5°	2635.6	2502.7	2363.0	2216.9	2081.8	1959.8	1841.0	1738.9	1649.2	1572.7	1513.0
25°	2656.3	2503.8	2352.1	2206.8	2053.5	1909.0	1801.2	1681.5	1585.6	1505.0	1441.1
27.5°	2658.6	2495.5	2323.9	2162.4	2004.2	1869.6	1733.5	1626.5	1527.0	1441.8	1380.5
30°	2651.5	2481.5	2297.0	2122.2	1963.3	1817.2	1699.0	1582.5	1481.1	1396.4	1332.5
32.5°	2629.2	2452.1	2262.5	2077.5	1912.8	1769.9	1647.9	1537.1	1438.3	1354.9	1287.8
35°	2564.5	2389.6	2187.6	1995.2	1826.8	1682.3	1572.1	1459.5	1360.5	1281.5	1216.8
37.5°	2463.4	2305.3	2100.0	1900.9	1735.4	1590.3	1481.1	1379.3	1290.1	1209.8	1143.5
40°	2375.3	2236.4	2030.4	1836.3	1657.5	1519.4	1417.2	1323.8	1235.1	1159.3	1096.2
42.5°	2273.7	2152.7	1962.7	1757.1	1584.7	1445.9	1346.3	1262.4	1178.9	1108.8	1045.8
45°	2092.6	2012.8	1834.0	1643.9	1464.3	1333.3	1238.3	1164.9	1094.6	1026.0	973.3
47.5°	1884.4	1844.8	1694.2	1513.8	1343.2	1214.2	1131.8	1064.0	1002.3	944.2	897.7
50°	1744.5	1725.4	1595.2	1421.2	1258.3	1136.9	1053.9	995.6	942.9	891.8	847.9
52.5°	1606.6	1605.9	1488.6	1329.2	1178.5	1061.6	979.2	924.7	879.1	837.5	798.1
55°	1395.6	1418.0	1326.2	1184.0	1049.1	943.7	869.5	820.8	788.8	754.5	725.0
57.5°	1201.9	1239.0	1163.3	1038.1	925.5	828.4	763.8	727.2	693.2	672.4	650.9
60°	1075.5	1110.6	1051.5	946.1	839.9	756.9	695.4	662.7	633.1	618.8	603.6
62.5°	963.0	994.3	950.6	852.9	760.7	680.9	629.0	597.5	577.6	561.9	551.9
65°	802.4	828.8	791.2	720.2	641.1	577.3	534.9	510.2	491.0	484.6	473.5
67.5°	648.6	672.6	652.3	591.9	528.5	480.2	447.1	423.3	412.0	406.4	398.4
70°	557.3	581.2	559.7	507.0	458.3	417.6	386.4	372.9	360.9	358.5	347.3
72.5°	480.0	496.3	474.7	433.5	391.9	357.5	333.4	319.2	313.0	308.7	302.6
75°	360.1	374.5	360.1	328.1	298.6	274.7	253.9	248.3	241.1	238.7	234.7
77.5°	254.9	267.3	256.3	236.3	214.3	195.8	184.6	177.4	175.8	171.7	173.6
80°	194.8	202.8	192.4	178.8	161.3	148.5	140.5	136.5	131.7	130.1	133.3
82.5°	139.9	143.4	138.1	129.0	115.9	107.6	102.2	97.6	96.6	96.9	96.9
85°	72.7	71.9	71.1	63.1	59.1	53.5	50.3	49.5	48.7	50.3	51.9
87.5°	27.1	27.7	25.9	23.3	21.2	19.1	17.8	16.8	17.8	19.1	19.9
90°	14.0	14.0	8.0	8.0	7.0	6.0	3.0	1.0	3.0	6.0	7.0
92.5°	201.7	124.2	73.5	52.7	38.1	26.0	16.6	11.4	16.6	26.0	38.1
95°	375.4	211.6	124.8	82.9	58.9	45.9	35.9	32.9	35.9	45.9	58.9
97.5°	337.4	202.3	135.4	100.2	79.7	67.7	59.1	59.1	59.1	67.7	79.7
100°	317.5	204.7	145.8	113.8	94.8	82.9	75.9	75.9	75.9	82.9	94.8
102.5°	311.9	212.6	159.3	129.0	110.8	99.6	93.4	91.8	93.4	99.6	110.8
105°	314.5	231.6	183.7	154.7	136.8	124.8	119.8	116.8	119.8	124.8	136.8
107.5°	329.2	253.8	209.8	181.3	164.1	151.3	146.4	144.4	146.4	151.3	164.1
110°	340.4	270.5	226.6	199.7	181.7	169.7	164.7	162.7	164.7	169.7	181.7



TEST NUMBER: P332699

CATALOG NUMBER: S124DIP-S1195D1035U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	352.4	286.5	244.2	217.2	199.3	188.1	182.3	180.3	182.3	188.1	199.3
115°	371.4	311.5	271.5	244.6	225.6	215.6	208.6	205.7	208.6	215.6	225.6
117.5°	390.7	335.6	297.7	269.7	252.0	241.0	234.8	232.0	234.8	241.0	252.0
120°	404.3	352.4	314.5	286.5	269.5	258.6	251.6	249.6	251.6	258.6	269.5
122.5°	417.1	368.4	330.4	303.3	284.7	274.5	267.5	265.6	267.5	274.5	284.7
125°	436.3	390.3	354.4	326.4	307.5	296.5	290.5	286.5	290.5	296.5	307.5
127.5°	452.8	410.7	376.0	347.8	328.0	315.5	308.3	305.1	308.3	315.5	328.0
130°	463.2	424.3	390.3	361.4	342.4	327.4	319.5	315.5	319.5	327.4	342.4
132.5°	473.6	435.5	401.5	374.2	353.6	339.4	329.0	325.8	329.0	339.4	353.6
135°	487.2	451.2	418.3	392.3	371.4	354.4	344.4	340.4	344.4	354.4	371.4
137.5°	496.8	463.2	432.5	407.7	385.9	369.8	358.8	355.0	358.8	369.8	385.9
140°	503.1	471.2	441.3	417.3	396.3	379.4	368.4	365.4	368.4	379.4	396.3
142.5°	507.9	478.4	449.2	426.1	405.9	389.7	379.6	376.6	379.6	389.7	405.9
145°	513.1	486.2	460.2	438.3	419.3	405.3	395.3	392.3	395.3	405.3	419.3
147.5°	517.7	494.2	469.8	450.0	434.3	419.9	411.1	410.1	411.1	419.9	434.3
150°	520.1	498.2	476.2	457.2	442.3	430.3	422.3	421.3	422.3	430.3	442.3
152.5°	521.7	501.4	481.8	464.4	451.0	439.9	431.9	431.7	431.9	439.9	451.0
155°	523.1	506.1	489.2	474.2	463.2	453.2	447.2	446.2	447.2	453.2	463.2
157.5°	523.1	509.5	495.2	483.4	473.8	466.0	460.4	460.4	460.4	466.0	473.8
160°	523.1	511.1	499.2	488.2	480.2	473.2	469.2	469.2	469.2	473.2	480.2
162.5°	523.1	512.7	501.6	493.0	485.8	479.6	476.4	477.2	476.4	479.6	485.8
165°	521.1	513.1	504.1	498.2	493.2	488.2	486.2	486.2	486.2	488.2	493.2
167.5°	518.7	512.9	506.3	501.8	499.0	495.2	494.2	495.2	494.2	495.2	499.0
170°	517.1	512.1	507.1	504.1	502.2	499.2	498.2	499.2	498.2	499.2	502.2
172.5°	515.5	511.3	507.9	505.7	504.5	502.3	502.2	503.1	502.2	502.3	504.5
175°	513.1	510.1	508.1	508.1	507.1	506.1	506.1	507.1	506.1	506.1	507.1
177.5°	510.5	508.9	508.1	508.1	508.1	507.3	508.1	508.9	508.1	507.3	508.1
180°	508.1	508.1	508.1	508.1	508.1	508.1	508.1	508.1	508.1	508.1	508.1



TEST NUMBER: P332699

CATALOG NUMBER: S124DIP-S1195D1035U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4
2.5°	1890.3	1884.6	1876.3	1864.8	1855.2	1845.0	1842.4	1838.6	1846.2	1839.9	1837.9
5°	1828.4	1811.6	1790.0	1765.3	1750.9	1730.2	1726.2	1718.2	1710.2	1709.4	1701.4
7.5°	1762.7	1738.1	1709.9	1684.6	1661.3	1638.7	1623.8	1620.6	1608.8	1601.9	1593.9
10°	1720.6	1690.2	1657.5	1633.6	1606.4	1582.5	1565.7	1556.1	1548.1	1539.3	1531.4
12.5°	1670.8	1638.5	1611.5	1585.6	1553.4	1535.2	1507.6	1491.0	1489.4	1489.5	1468.8
15°	1612.8	1580.9	1539.3	1502.6	1485.0	1449.9	1434.7	1415.6	1403.6	1391.6	1382.1
17.5°	1546.5	1506.8	1474.3	1432.2	1398.7	1370.7	1350.8	1339.3	1321.2	1304.3	1292.0
20°	1505.0	1462.7	1428.4	1383.6	1346.9	1312.6	1295.8	1279.9	1266.3	1251.9	1238.3
22.5°	1462.8	1418.6	1376.6	1333.2	1299.0	1262.8	1246.6	1224.9	1212.0	1204.0	1190.4
25°	1396.4	1348.5	1300.6	1259.1	1224.0	1192.0	1170.5	1153.7	1139.3	1132.9	1124.2
27.5°	1324.2	1276.7	1230.4	1183.2	1143.3	1120.2	1102.9	1090.3	1082.0	1073.5	1069.6
30°	1278.3	1228.8	1179.3	1135.3	1098.6	1075.5	1059.5	1050.7	1044.3	1040.3	1036.3
32.5°	1231.6	1182.8	1130.7	1090.6	1057.7	1037.1	1025.0	1016.2	1013.0	1011.6	1010.2
35°	1156.9	1107.4	1059.5	1023.6	992.4	984.4	974.1	969.3	967.7	973.3	975.7
37.5°	1084.6	1038.6	994.5	959.7	939.3	927.6	924.1	924.2	930.0	934.9	940.7
40°	1037.9	993.2	951.7	921.4	902.2	895.0	893.4	897.4	903.8	909.4	915.8
42.5°	992.6	948.5	910.8	882.4	869.0	862.4	863.4	867.4	876.3	883.2	892.8
45°	922.2	885.4	848.7	825.6	814.4	816.0	816.0	823.2	831.9	842.3	852.7
47.5°	855.9	818.9	788.7	769.2	763.4	762.0	766.5	775.9	788.5	801.3	815.8
50°	811.2	776.1	749.7	732.1	725.8	728.2	734.5	743.3	758.5	774.5	789.6
52.5°	765.8	733.9	709.5	693.2	688.7	693.0	699.4	713.3	726.6	743.8	762.2
55°	695.4	668.3	649.1	637.1	635.5	637.9	645.1	660.3	679.4	701.0	718.6
57.5°	625.3	602.6	585.1	576.8	577.6	579.8	591.6	609.7	630.1	653.1	675.8
60°	578.0	557.3	542.9	536.5	537.3	542.1	556.5	573.3	598.8	621.2	645.1
62.5°	533.3	515.1	501.4	495.7	494.5	505.1	518.8	536.2	561.8	586.7	612.5
65°	461.5	447.1	435.9	432.7	435.1	443.1	460.7	483.8	505.4	531.7	558.9
67.5°	391.2	379.4	371.7	373.2	376.1	387.9	402.6	422.5	447.0	474.3	501.1
70°	346.5	335.3	328.9	329.7	334.5	348.9	361.7	381.6	408.0	435.9	458.3
72.5°	300.5	293.2	287.4	290.8	295.6	305.5	321.4	341.4	364.6	390.6	414.2
75°	230.7	230.7	227.5	229.9	237.1	246.7	258.7	279.4	302.6	323.4	342.5
77.5°	171.2	169.4	171.5	174.4	178.5	189.9	203.6	218.4	235.9	256.6	272.4
80°	130.9	131.7	135.7	140.5	142.1	150.9	165.3	178.8	192.4	210.0	225.2
82.5°	98.4	99.2	101.2	107.3	108.9	118.3	127.6	141.2	153.5	165.3	177.9
85°	53.5	53.5	57.5	59.9	63.9	70.3	75.8	83.8	95.0	103.0	115.0
87.5°	22.0	22.0	25.8	27.1	29.4	33.0	34.1	41.3	44.0	47.4	53.2
90°	8.0	8.0	14.0	14.0	16.0	18.0	17.0	18.0	19.0	20.0	20.0
92.5°	52.7	73.5	124.2	201.7	277.1	316.7	263.8	196.1	147.6	117.4	97.4
95°	82.9	124.8	211.6	375.4	614.0	813.6	836.6	739.7	585.0	451.2	354.4
97.5°	100.2	135.4	202.3	337.4	574.6	856.9	1051.0	1093.0	1035.4	937.8	833.6
100°	113.8	145.8	204.7	317.5	521.1	802.6	1058.2	1204.0	1223.9	1175.0	1101.1
102.5°	129.0	159.3	212.6	311.9	485.2	734.8	998.3	1198.4	1297.4	1311.6	1280.8
105°	154.7	183.7	231.6	314.5	454.2	654.9	889.5	1118.1	1290.8	1389.6	1430.6
107.5°	181.3	209.8	253.8	329.2	448.6	610.2	801.6	1004.1	1188.0	1327.2	1416.2
110°	199.7	226.6	270.5	340.4	450.2	595.0	757.7	935.4	1108.1	1252.9	1362.7



TEST NUMBER: P332699

CATALOG NUMBER: S124DIP-S1195D1035U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	217.2	244.2	286.5	352.4	455.0	587.8	733.0	885.1	1037.8	1174.6	1284.4
115°	244.6	271.5	311.5	371.4	464.2	584.0	709.8	834.6	957.4	1074.2	1170.0
117.5°	269.7	297.7	335.6	390.7	474.0	583.0	699.4	809.8	911.5	1003.3	1084.6
120°	286.5	314.5	352.4	404.3	481.2	583.0	693.8	798.6	891.5	971.4	1042.2
122.5°	303.3	330.4	368.4	417.1	488.4	582.2	687.4	789.1	878.7	951.4	1013.5
125°	326.4	354.4	390.3	436.3	499.2	581.0	676.9	772.7	858.5	927.4	982.3
127.5°	347.8	376.0	410.7	452.8	507.7	578.8	662.7	752.7	834.8	903.5	955.6
130°	361.4	390.3	424.3	463.2	514.1	578.0	653.9	736.8	815.6	883.5	936.4
132.5°	374.2	401.5	435.5	473.6	519.7	577.2	645.9	720.0	794.1	860.3	913.3
135°	392.3	418.3	451.2	487.2	528.1	576.0	633.9	696.8	761.7	822.6	872.5
137.5°	407.7	432.5	463.2	496.8	533.1	575.8	623.5	675.9	730.8	782.1	827.2
140°	417.3	441.3	471.2	503.1	537.1	575.0	618.0	663.9	710.8	755.7	797.6
142.5°	426.1	449.2	478.4	507.9	540.3	575.0	613.2	652.7	694.0	732.6	768.9
145°	438.3	460.2	486.2	513.1	542.1	573.0	605.0	636.9	670.9	700.8	728.8
147.5°	450.0	469.8	494.2	517.7	543.1	569.4	597.6	623.9	650.9	674.9	696.8
150°	457.2	476.2	498.2	520.1	543.1	567.0	592.0	616.0	638.9	658.9	676.9
152.5°	464.4	481.8	501.4	521.7	541.5	563.0	585.6	607.2	626.9	645.3	660.1
155°	474.2	489.2	506.1	523.1	539.1	557.1	576.0	594.0	610.0	624.9	636.9
157.5°	483.4	495.2	509.5	523.1	536.5	550.9	566.2	579.8	593.2	605.8	615.4
160°	488.2	499.2	511.1	523.1	534.1	546.1	559.1	571.0	582.0	593.0	601.0
162.5°	493.0	501.6	512.7	523.1	531.7	541.3	552.7	562.2	571.6	580.2	587.4
165°	498.2	504.1	513.1	521.1	527.1	534.1	542.1	550.1	556.1	563.0	568.0
167.5°	501.8	506.3	512.9	518.7	522.3	526.9	532.5	538.3	542.9	548.5	551.5
170°	504.1	507.1	512.1	517.1	519.1	522.1	526.1	531.1	534.1	538.1	541.1
172.5°	505.7	507.9	511.3	515.5	515.9	517.3	520.5	524.7	526.9	529.3	531.5
175°	508.1	508.1	510.1	513.1	512.1	512.1	514.1	516.1	517.1	519.1	519.1
177.5°	508.1	508.1	508.9	510.5	508.9	508.9	509.7	510.5	511.3	511.3	512.1
180°	508.1	508.1	508.1	508.1	508.1	508.1	508.1	508.1	508.1	508.1	508.1



TEST NUMBER: P332699

CATALOG NUMBER: S124DIP-S1195D1035U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4
2.5°	1836.7	1835.4	1830.9	1830.3	1830.9	1835.4	1836.7	1837.9	1839.9	1846.2	1838.6
5°	1696.6	1692.6	1690.2	1699.0	1690.2	1692.6	1696.6	1701.4	1709.4	1710.2	1718.2
7.5°	1591.1	1587.9	1580.9	1578.6	1580.9	1587.9	1591.1	1593.9	1601.9	1608.8	1620.6
10°	1523.4	1520.2	1513.8	1512.2	1513.8	1520.2	1523.4	1531.4	1539.3	1548.1	1556.1
12.5°	1458.2	1451.8	1450.6	1452.2	1450.6	1451.8	1458.2	1468.8	1489.5	1489.4	1491.0
15°	1371.7	1368.5	1359.7	1362.1	1359.7	1368.5	1371.7	1382.1	1391.6	1403.6	1415.6
17.5°	1286.4	1282.6	1271.9	1281.3	1271.9	1282.6	1286.4	1292.0	1304.3	1321.2	1339.3
20°	1232.7	1226.4	1220.8	1220.0	1220.8	1226.4	1232.7	1238.3	1251.9	1266.3	1279.9
22.5°	1181.6	1175.9	1175.4	1170.2	1175.4	1175.9	1181.6	1190.4	1204.0	1212.0	1224.9
25°	1117.8	1112.2	1110.6	1106.6	1110.6	1112.2	1117.8	1124.2	1132.9	1139.3	1153.7
27.5°	1068.8	1066.0	1063.2	1064.4	1063.2	1066.0	1068.8	1069.6	1073.5	1082.0	1090.3
30°	1038.7	1037.9	1036.3	1036.3	1036.3	1037.9	1038.7	1036.3	1040.3	1044.3	1050.7
32.5°	1013.8	1013.7	1014.6	1014.6	1014.6	1013.7	1013.8	1010.2	1011.6	1013.0	1016.2
35°	978.9	981.2	982.8	980.4	982.8	981.2	978.9	975.7	973.3	967.7	969.3
37.5°	947.2	949.6	951.9	954.6	951.9	949.6	947.2	940.7	934.9	930.0	924.2
40°	923.0	928.6	930.1	934.1	930.1	928.6	923.0	915.8	909.4	903.8	897.4
42.5°	900.0	906.2	910.3	911.1	910.3	906.2	900.0	892.8	883.2	876.3	867.4
45°	864.7	871.1	876.7	876.7	876.7	871.1	864.7	852.7	842.3	831.9	823.2
47.5°	828.1	837.4	843.0	844.4	843.0	837.4	828.1	815.8	801.3	788.5	775.9
50°	803.2	814.4	820.0	824.0	820.0	814.4	803.2	789.6	774.5	758.5	743.3
52.5°	778.9	790.1	797.6	799.7	797.6	790.1	778.9	762.2	743.8	726.6	713.3
55°	736.9	752.9	761.7	764.9	761.7	752.9	736.9	718.6	701.0	679.4	660.3
57.5°	697.3	712.0	722.2	724.6	722.2	712.0	697.3	675.8	653.1	630.1	609.7
60°	666.7	682.6	695.4	697.8	695.4	682.6	666.7	645.1	621.2	598.8	573.3
62.5°	635.4	652.0	663.5	669.7	663.5	652.0	635.4	612.5	586.7	561.8	536.2
65°	581.2	598.0	609.2	611.6	609.2	598.0	581.2	558.9	531.7	505.4	483.8
67.5°	522.2	538.9	546.3	550.9	546.3	538.9	522.2	501.1	474.3	447.0	422.5
70°	480.6	494.2	502.2	506.2	502.2	494.2	480.6	458.3	435.9	408.0	381.6
72.5°	433.4	447.6	456.9	457.6	456.9	447.6	433.4	414.2	390.6	364.6	341.4
75°	360.9	373.7	378.4	378.4	378.4	373.7	360.9	342.5	323.4	302.6	279.4
77.5°	285.7	292.2	298.3	299.6	298.3	292.2	285.7	272.4	256.6	235.9	218.4
80°	237.1	241.1	245.9	245.9	245.9	241.1	237.1	225.2	210.0	192.4	178.8
82.5°	187.3	190.7	195.5	194.8	195.5	190.7	187.3	177.9	165.3	153.5	141.2
85°	113.4	120.6	119.8	118.2	119.8	120.6	113.4	115.0	103.0	95.0	83.8
87.5°	55.3	56.1	57.8	59.1	57.8	56.1	55.3	53.2	47.4	44.0	41.3
90°	21.0	22.0	21.0	21.0	21.0	22.0	21.0	20.0	20.0	19.0	18.0
92.5°	85.7	80.3	76.9	76.9	76.9	80.3	85.7	97.4	117.4	147.6	196.1
95°	305.5	274.5	256.6	243.6	256.6	274.5	305.5	354.4	451.2	585.0	739.7
97.5°	761.9	701.8	671.9	651.1	671.9	701.8	761.9	833.6	937.8	1035.4	1093.0
100°	1014.3	953.4	923.4	915.5	923.4	953.4	1014.3	1101.1	1175.0	1223.9	1204.0
102.5°	1227.5	1183.4	1151.9	1145.5	1151.9	1183.4	1227.5	1280.8	1311.6	1297.4	1198.4
105°	1432.6	1424.6	1410.6	1404.6	1410.6	1424.6	1432.6	1430.6	1389.6	1290.8	1118.1
107.5°	1465.5	1488.3	1498.3	1500.9	1498.3	1488.3	1465.5	1416.2	1327.2	1188.0	1004.1
110°	1433.6	1475.5	1493.5	1502.5	1493.5	1475.5	1433.6	1362.7	1252.9	1108.1	935.4



TEST NUMBER: P332699

CATALOG NUMBER: S124DIP-S1195D1035U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1364.9	1415.6	1440.8	1455.3	1440.8	1415.6	1364.9	1284.4	1174.6	1037.8	885.1
115°	1248.9	1308.8	1340.7	1348.7	1340.7	1308.8	1248.9	1170.0	1074.2	957.4	834.6
117.5°	1151.9	1202.2	1234.5	1240.7	1234.5	1202.2	1151.9	1084.6	1003.3	911.5	809.8
120°	1099.1	1143.1	1169.0	1180.0	1169.0	1143.1	1099.1	1042.2	971.4	891.5	798.6
122.5°	1061.6	1099.1	1121.1	1132.1	1121.1	1099.1	1061.6	1013.5	951.4	878.7	789.1
125°	1022.3	1051.2	1070.2	1076.2	1070.2	1051.2	1022.3	982.3	927.4	858.5	772.7
127.5°	995.7	1021.5	1037.4	1043.4	1037.4	1021.5	995.7	955.6	903.5	834.8	752.7
130°	977.3	1002.3	1018.3	1024.3	1018.3	1002.3	977.3	936.4	883.5	815.6	736.8
132.5°	953.4	981.5	996.7	1002.7	996.7	981.5	953.4	913.3	860.3	794.1	720.0
135°	912.5	940.4	956.4	962.4	956.4	940.4	912.5	872.5	822.6	761.7	696.8
137.5°	864.5	892.1	905.3	912.5	905.3	892.1	864.5	827.2	782.1	730.8	675.9
140°	832.6	854.6	868.5	876.5	868.5	854.6	832.6	797.6	755.7	710.8	663.9
142.5°	799.8	820.2	832.6	838.2	832.6	820.2	799.8	768.9	732.6	694.0	652.7
145°	753.7	770.7	780.7	785.7	780.7	770.7	753.7	728.8	700.8	670.9	636.9
147.5°	715.2	729.8	737.4	739.1	737.4	729.8	715.2	696.8	674.9	650.9	623.9
150°	692.8	705.8	711.8	712.8	711.8	705.8	692.8	676.9	658.9	638.9	616.0
152.5°	673.7	684.2	687.8	688.8	687.8	684.2	673.7	660.1	645.3	626.9	607.2
155°	646.9	654.9	657.9	657.9	657.9	654.9	646.9	636.9	624.9	610.0	594.0
157.5°	622.9	628.9	630.7	630.7	630.7	628.9	622.9	615.4	605.8	593.2	579.8
160°	607.0	613.0	614.0	614.0	614.0	613.0	607.0	601.0	593.0	582.0	571.0
162.5°	591.8	597.8	598.8	598.0	598.8	597.8	591.8	587.4	580.2	571.6	562.2
165°	572.0	576.0	575.0	574.0	575.0	576.0	572.0	568.0	563.0	556.1	550.1
167.5°	553.5	556.1	555.9	555.1	555.9	556.1	553.5	551.5	548.5	542.9	538.3
170°	543.1	544.1	543.1	543.1	543.1	544.1	543.1	541.1	538.1	534.1	531.1
172.5°	532.7	533.7	532.7	531.1	532.7	533.7	532.7	531.5	529.3	526.9	524.7
175°	519.1	521.1	519.1	517.1	519.1	521.1	519.1	519.1	519.1	517.1	516.1
177.5°	511.3	512.1	510.5	508.9	510.5	512.1	511.3	512.1	511.3	511.3	510.5
180°	508.1	508.1	508.1	508.1	508.1	508.1	508.1	508.1	508.1	508.1	508.1



TEST NUMBER: P332699

CATALOG NUMBER: S124DIP-S1195D1035U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4
2.5°	1842.4	1845.0	1855.2	1864.8	1876.3	1884.6	1890.3	1896.7	1910.1	1921.0	1931.2
5°	1726.2	1730.2	1750.9	1765.3	1790.0	1811.6	1828.4	1846.7	1868.3	1897.8	1925.0
7.5°	1623.8	1638.7	1661.3	1684.6	1709.9	1738.1	1762.7	1790.4	1827.6	1868.1	1910.0
10°	1565.7	1582.5	1606.4	1633.6	1657.5	1690.2	1720.6	1753.3	1795.6	1845.1	1894.6
12.5°	1507.6	1535.2	1553.4	1585.6	1611.5	1638.5	1670.8	1713.7	1763.1	1815.1	1874.8
15°	1434.7	1449.9	1485.0	1502.6	1539.3	1580.9	1612.8	1655.9	1703.8	1772.5	1839.5
17.5°	1350.8	1370.7	1398.7	1432.2	1474.3	1506.8	1546.5	1590.9	1651.3	1719.5	1803.5
20°	1295.8	1312.6	1346.9	1383.6	1428.4	1462.7	1505.0	1548.1	1610.4	1683.1	1770.9
22.5°	1246.6	1262.8	1299.0	1333.2	1376.6	1418.6	1462.8	1513.0	1572.7	1649.2	1738.9
25°	1170.5	1192.0	1224.0	1259.1	1300.6	1348.5	1396.4	1441.1	1505.0	1585.6	1681.5
27.5°	1102.9	1120.2	1143.3	1183.2	1230.4	1276.7	1324.2	1380.5	1441.8	1527.0	1626.5
30°	1059.5	1075.5	1098.6	1135.3	1179.3	1228.8	1278.3	1332.5	1396.4	1481.1	1582.5
32.5°	1025.0	1037.1	1057.7	1090.6	1130.7	1182.8	1231.6	1287.8	1354.9	1438.3	1537.1
35°	974.1	984.4	992.4	1023.6	1059.5	1107.4	1156.9	1216.8	1281.5	1360.5	1459.5
37.5°	924.1	927.6	939.3	959.7	994.5	1038.6	1084.6	1143.5	1209.8	1290.1	1379.3
40°	893.4	895.0	902.2	921.4	951.7	993.2	1037.9	1096.2	1159.3	1235.1	1323.8
42.5°	863.4	862.4	869.0	882.4	910.8	948.5	992.6	1045.8	1108.8	1178.9	1262.4
45°	816.0	816.0	814.4	825.6	848.7	885.4	922.2	973.3	1026.0	1094.6	1164.9
47.5°	766.5	762.0	763.4	769.2	788.7	818.9	855.9	897.7	944.2	1002.3	1064.0
50°	734.5	728.2	725.8	732.1	749.7	776.1	811.2	847.9	891.8	942.9	995.6
52.5°	699.4	693.0	688.7	693.2	709.5	733.9	765.8	798.1	837.5	879.1	924.7
55°	645.1	637.9	635.5	637.1	649.1	668.3	695.4	725.0	754.5	788.8	820.8
57.5°	591.6	579.8	577.6	576.8	585.1	602.6	625.3	650.9	672.4	693.2	727.2
60°	556.5	542.1	537.3	536.5	542.9	557.3	578.0	603.6	618.8	633.1	662.7
62.5°	518.8	505.1	494.5	495.7	501.4	515.1	533.3	551.9	561.9	577.6	597.5
65°	460.7	443.1	435.1	432.7	435.9	447.1	461.5	473.5	484.6	491.0	510.2
67.5°	402.6	387.9	376.1	373.2	371.7	379.4	391.2	398.4	406.4	412.0	423.3
70°	361.7	348.9	334.5	329.7	328.9	335.3	346.5	347.3	358.5	360.9	372.9
72.5°	321.4	305.5	295.6	290.8	287.4	293.2	300.5	302.6	308.7	313.0	319.2
75°	258.7	246.7	237.1	229.9	227.5	230.7	230.7	234.7	238.7	241.1	248.3
77.5°	203.6	189.9	178.5	174.4	171.5	169.4	171.2	173.6	171.7	175.8	177.4
80°	165.3	150.9	142.1	140.5	135.7	131.7	130.9	133.3	130.1	131.7	136.5
82.5°	127.6	118.3	108.9	107.3	101.2	99.2	98.4	96.9	96.9	96.6	97.6
85°	75.8	70.3	63.9	59.9	57.5	53.5	53.5	51.9	50.3	48.7	49.5
87.5°	34.1	33.0	29.4	27.1	25.8	22.0	22.0	19.9	19.1	17.8	16.8
90°	17.0	18.0	16.0	14.0	14.0	8.0	8.0	7.0	6.0	3.0	1.0
92.5°	263.8	316.7	277.1	201.7	124.2	73.5	52.7	38.1	26.0	16.6	11.4
95°	836.6	813.6	614.0	375.4	211.6	124.8	82.9	58.9	45.9	35.9	32.9
97.5°	1051.0	856.9	574.6	337.4	202.3	135.4	100.2	79.7	67.7	59.1	59.1
100°	1058.2	802.6	521.1	317.5	204.7	145.8	113.8	94.8	82.9	75.9	75.9
102.5°	998.3	734.8	485.2	311.9	212.6	159.3	129.0	110.8	99.6	93.4	91.8
105°	889.5	654.9	454.2	314.5	231.6	183.7	154.7	136.8	124.8	119.8	116.8
107.5°	801.6	610.2	448.6	329.2	253.8	209.8	181.3	164.1	151.3	146.4	144.4
110°	757.7	595.0	450.2	340.4	270.5	226.6	199.7	181.7	169.7	164.7	162.7



TEST NUMBER: P332699

CATALOG NUMBER: S124DIP-S1195D1035U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	733.0	587.8	455.0	352.4	286.5	244.2	217.2	199.3	188.1	182.3	180.3
115°	709.8	584.0	464.2	371.4	311.5	271.5	244.6	225.6	215.6	208.6	205.7
117.5°	699.4	583.0	474.0	390.7	335.6	297.7	269.7	252.0	241.0	234.8	232.0
120°	693.8	583.0	481.2	404.3	352.4	314.5	286.5	269.5	258.6	251.6	249.6
122.5°	687.4	582.2	488.4	417.1	368.4	330.4	303.3	284.7	274.5	267.5	265.6
125°	676.9	581.0	499.2	436.3	390.3	354.4	326.4	307.5	296.5	290.5	286.5
127.5°	662.7	578.8	507.7	452.8	410.7	376.0	347.8	328.0	315.5	308.3	305.1
130°	653.9	578.0	514.1	463.2	424.3	390.3	361.4	342.4	327.4	319.5	315.5
132.5°	645.9	577.2	519.7	473.6	435.5	401.5	374.2	353.6	339.4	329.0	325.8
135°	633.9	576.0	528.1	487.2	451.2	418.3	392.3	371.4	354.4	344.4	340.4
137.5°	623.5	575.8	533.1	496.8	463.2	432.5	407.7	385.9	369.8	358.8	355.0
140°	618.0	575.0	537.1	503.1	471.2	441.3	417.3	396.3	379.4	368.4	365.4
142.5°	613.2	575.0	540.3	507.9	478.4	449.2	426.1	405.9	389.7	379.6	376.6
145°	605.0	573.0	542.1	513.1	486.2	460.2	438.3	419.3	405.3	395.3	392.3
147.5°	597.6	569.4	543.1	517.7	494.2	469.8	450.0	434.3	419.9	411.1	410.1
150°	592.0	567.0	543.1	520.1	498.2	476.2	457.2	442.3	430.3	422.3	421.3
152.5°	585.6	563.0	541.5	521.7	501.4	481.8	464.4	451.0	439.9	431.9	431.7
155°	576.0	557.1	539.1	523.1	506.1	489.2	474.2	463.2	453.2	447.2	446.2
157.5°	566.2	550.9	536.5	523.1	509.5	495.2	483.4	473.8	466.0	460.4	460.4
160°	559.1	546.1	534.1	523.1	511.1	499.2	488.2	480.2	473.2	469.2	469.2
162.5°	552.7	541.3	531.7	523.1	512.7	501.6	493.0	485.8	479.6	476.4	477.2
165°	542.1	534.1	527.1	521.1	513.1	504.1	498.2	493.2	488.2	486.2	486.2
167.5°	532.5	526.9	522.3	518.7	512.9	506.3	501.8	499.0	495.2	494.2	495.2
170°	526.1	522.1	519.1	517.1	512.1	507.1	504.1	502.2	499.2	498.2	499.2
172.5°	520.5	517.3	515.9	515.5	511.3	507.9	505.7	504.5	502.3	502.2	503.1
175°	514.1	512.1	512.1	513.1	510.1	508.1	508.1	507.1	506.1	506.1	507.1
177.5°	509.7	508.9	508.9	510.5	508.9	508.1	508.1	508.1	507.3	508.1	508.9
180°	508.1	508.1	508.1	508.1	508.1	508.1	508.1	508.1	508.1	508.1	508.1



TEST NUMBER: P332699

CATALOG NUMBER: S124DIP-S1195D1035U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4
2.5°	1940.1	1946.5	1954.8	1968.9	1974.0	1980.4	1989.3	1988.7	1991.2	2000.8	2021.3
5°	1947.3	1972.1	1996.0	2024.8	2055.1	2075.1	2102.2	2119.0	2135.8	2157.3	2194.0
7.5°	1950.2	1989.5	2033.4	2083.9	2128.7	2180.5	2220.9	2258.9	2293.2	2338.7	2382.5
10°	1945.7	1998.4	2055.1	2119.0	2186.8	2244.3	2296.2	2355.3	2405.6	2460.7	2510.2
12.5°	1937.4	2001.0	2076.8	2148.4	2227.7	2312.7	2377.4	2437.1	2504.0	2567.4	2643.7
15°	1918.6	2005.6	2094.2	2188.4	2294.6	2392.8	2486.3	2563.7	2635.6	2730.6	2830.4
17.5°	1894.6	1988.5	2100.3	2214.3	2325.3	2437.6	2553.2	2669.6	2760.3	2878.3	2956.4
20°	1872.3	1980.9	2095.8	2231.6	2342.5	2482.3	2597.2	2709.8	2834.4	2951.7	3045.1
22.5°	1841.0	1959.8	2081.8	2216.9	2363.0	2502.7	2635.6	2757.7	2882.3	3009.9	3123.1
25°	1801.2	1909.0	2053.5	2206.8	2352.1	2503.8	2656.3	2809.6	2943.7	3078.7	3184.1
27.5°	1733.5	1869.6	2004.2	2162.4	2323.9	2495.5	2658.6	2819.0	2959.6	3070.5	3135.8
30°	1699.0	1817.2	1963.3	2122.2	2297.0	2481.5	2651.5	2808.8	2939.8	3028.4	3054.7
32.5°	1647.9	1769.9	1912.8	2077.5	2262.5	2452.1	2629.2	2777.5	2886.7	2933.2	2901.4
35°	1572.1	1682.3	1826.8	1995.2	2187.6	2389.6	2564.5	2689.8	2745.7	2701.8	2592.4
37.5°	1481.1	1590.3	1735.4	1900.9	2100.0	2305.3	2463.4	2553.6	2535.1	2425.9	2262.9
40°	1417.2	1519.4	1657.5	1836.3	2030.4	2236.4	2375.3	2424.0	2372.9	2216.4	2043.1
42.5°	1346.3	1445.9	1584.7	1757.1	1962.7	2152.7	2273.7	2277.7	2192.1	2005.0	1831.1
45°	1238.3	1333.3	1464.3	1643.9	1834.0	2012.8	2092.6	2053.5	1895.4	1715.0	1540.1
47.5°	1131.8	1214.2	1343.2	1513.8	1694.2	1844.8	1884.4	1814.0	1645.5	1470.4	1308.3
50°	1053.9	1136.9	1258.3	1421.2	1595.2	1725.4	1744.5	1651.1	1485.8	1309.4	1182.4
52.5°	979.2	1061.6	1178.5	1329.2	1488.6	1605.9	1606.6	1498.5	1333.8	1176.5	1058.5
55°	869.5	943.7	1049.1	1184.0	1326.2	1418.0	1395.6	1283.8	1140.9	1004.4	901.4
57.5°	763.8	828.4	925.5	1038.1	1163.3	1239.0	1201.9	1094.3	966.7	850.9	772.9
60°	695.4	756.9	839.9	946.1	1051.5	1110.6	1075.5	978.1	860.7	767.3	699.4
62.5°	629.0	680.9	760.7	852.9	950.6	994.3	963.0	866.9	765.5	681.0	626.0
65°	534.9	577.3	641.1	720.2	791.2	828.8	802.4	713.0	635.5	574.9	530.9
67.5°	447.1	480.2	528.5	591.9	652.3	672.6	648.6	586.4	520.7	472.2	441.2
70°	386.4	417.6	458.3	507.0	559.7	581.2	557.3	507.8	454.3	409.6	379.2
72.5°	333.4	357.5	391.9	433.5	474.7	496.3	480.0	432.4	387.2	354.0	328.1
75°	253.9	274.7	298.6	328.1	360.1	374.5	360.1	327.3	296.2	271.5	253.1
77.5°	184.6	195.8	214.3	236.3	256.3	267.3	254.9	232.7	213.7	196.7	187.6
80°	140.5	148.5	161.3	178.8	192.4	202.8	194.8	176.4	161.3	150.1	146.1
82.5°	102.2	107.6	115.9	129.0	138.1	143.4	139.9	126.6	120.4	110.5	106.5
85°	50.3	53.5	59.1	63.1	71.1	71.9	72.7	67.1	61.5	59.1	55.9
87.5°	17.8	19.1	21.2	23.3	25.9	27.7	27.1	27.5	25.3	24.5	22.1
90°	3.0	6.0	7.0	8.0	8.0	14.0	14.0	16.0	18.0	17.0	18.0
92.5°	16.6	26.0	38.1	52.7	73.5	124.2	201.7	277.1	316.7	263.8	196.1
95°	35.9	45.9	58.9	82.9	124.8	211.6	375.4	614.0	813.6	836.6	739.7
97.5°	59.1	67.7	79.7	100.2	135.4	202.3	337.4	574.6	856.9	1051.0	1093.0
100°	75.9	82.9	94.8	113.8	145.8	204.7	317.5	521.1	802.6	1058.2	1204.0
102.5°	93.4	99.6	110.8	129.0	159.3	212.6	311.9	485.2	734.8	998.3	1198.4
105°	119.8	124.8	136.8	154.7	183.7	231.6	314.5	454.2	654.9	889.5	1118.1
107.5°	146.4	151.3	164.1	181.3	209.8	253.8	329.2	448.6	610.2	801.6	1004.1
110°	164.7	169.7	181.7	199.7	226.6	270.5	340.4	450.2	595.0	757.7	935.4



TEST NUMBER: P332699

CATALOG NUMBER: S124DIP-S1195D1035U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	182.3	188.1	199.3	217.2	244.2	286.5	352.4	455.0	587.8	733.0	885.1
115°	208.6	215.6	225.6	244.6	271.5	311.5	371.4	464.2	584.0	709.8	834.6
117.5°	234.8	241.0	252.0	269.7	297.7	335.6	390.7	474.0	583.0	699.4	809.8
120°	251.6	258.6	269.5	286.5	314.5	352.4	404.3	481.2	583.0	693.8	798.6
122.5°	267.5	274.5	284.7	303.3	330.4	368.4	417.1	488.4	582.2	687.4	789.1
125°	290.5	296.5	307.5	326.4	354.4	390.3	436.3	499.2	581.0	676.9	772.7
127.5°	308.3	315.5	328.0	347.8	376.0	410.7	452.8	507.7	578.8	662.7	752.7
130°	319.5	327.4	342.4	361.4	390.3	424.3	463.2	514.1	578.0	653.9	736.8
132.5°	329.0	339.4	353.6	374.2	401.5	435.5	473.6	519.7	577.2	645.9	720.0
135°	344.4	354.4	371.4	392.3	418.3	451.2	487.2	528.1	576.0	633.9	696.8
137.5°	358.8	369.8	385.9	407.7	432.5	463.2	496.8	533.1	575.8	623.5	675.9
140°	368.4	379.4	396.3	417.3	441.3	471.2	503.1	537.1	575.0	618.0	663.9
142.5°	379.6	389.7	405.9	426.1	449.2	478.4	507.9	540.3	575.0	613.2	652.7
145°	395.3	405.3	419.3	438.3	460.2	486.2	513.1	542.1	573.0	605.0	636.9
147.5°	411.1	419.9	434.3	450.0	469.8	494.2	517.7	543.1	569.4	597.6	623.9
150°	422.3	430.3	442.3	457.2	476.2	498.2	520.1	543.1	567.0	592.0	616.0
152.5°	431.9	439.9	451.0	464.4	481.8	501.4	521.7	541.5	563.0	585.6	607.2
155°	447.2	453.2	463.2	474.2	489.2	506.1	523.1	539.1	557.1	576.0	594.0
157.5°	460.4	466.0	473.8	483.4	495.2	509.5	523.1	536.5	550.9	566.2	579.8
160°	469.2	473.2	480.2	488.2	499.2	511.1	523.1	534.1	546.1	559.1	571.0
162.5°	476.4	479.6	485.8	493.0	501.6	512.7	523.1	531.7	541.3	552.7	562.2
165°	486.2	488.2	493.2	498.2	504.1	513.1	521.1	527.1	534.1	542.1	550.1
167.5°	494.2	495.2	499.0	501.8	506.3	512.9	518.7	522.3	526.9	532.5	538.3
170°	498.2	499.2	502.2	504.1	507.1	512.1	517.1	519.1	522.1	526.1	531.1
172.5°	502.2	502.3	504.5	505.7	507.9	511.3	515.5	515.9	517.3	520.5	524.7
175°	506.1	506.1	507.1	508.1	508.1	510.1	513.1	512.1	512.1	514.1	516.1
177.5°	508.1	507.3	508.1	508.1	508.1	508.9	510.5	508.9	508.9	509.7	510.5
180°	508.1	508.1	508.1	508.1	508.1	508.1	508.1	508.1	508.1	508.1	508.1



TEST NUMBER: P332699

CATALOG NUMBER: S124DIP-S1195D1035U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4
2.5°	2031.5	2032.8	2038.5	2043.0	2044.3	2050.6	2051.3
5°	2210.0	2223.6	2249.9	2252.3	2256.3	2277.1	2261.1
7.5°	2419.2	2453.7	2476.7	2497.0	2504.3	2513.4	2511.5
10°	2553.3	2604.4	2630.0	2670.7	2672.3	2682.7	2676.3
12.5°	2688.1	2747.5	2794.1	2801.6	2835.8	2841.1	2850.0
15°	2879.1	2942.1	3006.8	3030.0	3077.1	3088.3	3105.8
17.5°	3058.6	3123.1	3168.4	3228.3	3247.6	3273.5	3255.9
20°	3156.9	3227.2	3284.7	3331.8	3351.7	3366.1	3364.5
22.5°	3216.3	3287.2	3333.8	3369.5	3388.1	3394.2	3393.9
25°	3253.5	3294.2	3308.6	3322.2	3301.4	3294.2	3297.4
27.5°	3150.1	3139.5	3102.0	3052.8	3001.7	2961.1	2939.1
30°	3007.6	2945.3	2888.7	2789.6	2738.6	2708.2	2681.1
32.5°	2805.8	2707.1	2598.0	2507.3	2449.2	2404.2	2397.5
35°	2459.9	2311.4	2178.1	2067.1	2009.6	1960.9	1949.7
37.5°	2091.4	1937.1	1817.0	1719.3	1657.5	1623.2	1591.1
40°	1846.7	1714.2	1596.0	1513.0	1465.9	1441.1	1421.2
42.5°	1658.3	1537.3	1419.7	1356.5	1313.9	1298.7	1287.0
45°	1398.0	1285.4	1204.0	1156.1	1131.3	1105.8	1093.8
47.5°	1189.6	1098.0	1044.3	1003.6	977.1	961.9	954.3
50°	1071.5	996.4	948.5	917.4	893.4	881.4	875.1
52.5°	966.7	905.1	864.8	840.1	823.8	815.0	812.5
55°	832.7	785.6	760.1	738.5	726.6	718.6	715.4
57.5°	723.8	687.6	666.8	649.1	644.5	637.8	635.5
60°	652.3	624.4	606.8	594.8	590.8	582.8	584.4
62.5°	589.1	566.2	551.2	544.4	539.1	532.4	534.6
65°	498.2	481.4	473.5	467.1	460.7	456.7	459.9
67.5°	418.0	406.6	395.7	392.0	388.8	388.2	384.8
70°	365.7	356.1	346.5	344.1	344.1	340.9	340.1
72.5°	315.2	308.2	301.8	300.0	297.5	298.8	295.4
75°	243.5	237.9	235.5	233.1	232.3	232.3	229.9
77.5°	180.0	175.8	172.0	172.0	169.1	168.0	167.7
80°	136.5	134.9	131.7	131.7	130.1	130.9	129.3
82.5°	102.7	100.4	99.8	98.5	96.3	96.4	94.9
85°	55.1	52.7	51.9	49.5	47.9	49.5	47.9
87.5°	23.0	22.5	21.9	20.8	20.4	20.2	18.2
90°	19.0	20.0	20.0	21.0	22.0	21.0	21.0
92.5°	147.6	117.4	97.4	85.7	80.3	76.9	76.9
95°	585.0	451.2	354.4	305.5	274.5	256.6	243.6
97.5°	1035.4	937.8	833.6	761.9	701.8	671.9	651.1
100°	1223.9	1175.0	1101.1	1014.3	953.4	923.4	915.5
102.5°	1297.4	1311.6	1280.8	1227.5	1183.4	1151.9	1145.5
105°	1290.8	1389.6	1430.6	1432.6	1424.6	1410.6	1404.6
107.5°	1188.0	1327.2	1416.2	1465.5	1488.3	1498.3	1500.9
110°	1108.1	1252.9	1362.7	1433.6	1475.5	1493.5	1502.5



TEST NUMBER: P332699

CATALOG NUMBER: S124DIP-S1195D1035U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	1037.8	1174.6	1284.4	1364.9	1415.6	1440.8	1455.3
115°	957.4	1074.2	1170.0	1248.9	1308.8	1340.7	1348.7
117.5°	911.5	1003.3	1084.6	1151.9	1202.2	1234.5	1240.7
120°	891.5	971.4	1042.2	1099.1	1143.1	1169.0	1180.0
122.5°	878.7	951.4	1013.5	1061.6	1099.1	1121.1	1132.1
125°	858.5	927.4	982.3	1022.3	1051.2	1070.2	1076.2
127.5°	834.8	903.5	955.6	995.7	1021.5	1037.4	1043.4
130°	815.6	883.5	936.4	977.3	1002.3	1018.3	1024.3
132.5°	794.1	860.3	913.3	953.4	981.5	996.7	1002.7
135°	761.7	822.6	872.5	912.5	940.4	956.4	962.4
137.5°	730.8	782.1	827.2	864.5	892.1	905.3	912.5
140°	710.8	755.7	797.6	832.6	854.6	868.5	876.5
142.5°	694.0	732.6	768.9	799.8	820.2	832.6	838.2
145°	670.9	700.8	728.8	753.7	770.7	780.7	785.7
147.5°	650.9	674.9	696.8	715.2	729.8	737.4	739.1
150°	638.9	658.9	676.9	692.8	705.8	711.8	712.8
152.5°	626.9	645.3	660.1	673.7	684.2	687.8	688.8
155°	610.0	624.9	636.9	646.9	654.9	657.9	657.9
157.5°	593.2	605.8	615.4	622.9	628.9	630.7	630.7
160°	582.0	593.0	601.0	607.0	613.0	614.0	614.0
162.5°	571.6	580.2	587.4	591.8	597.8	598.8	598.0
165°	556.1	563.0	568.0	572.0	576.0	575.0	574.0
167.5°	542.9	548.5	551.5	553.5	556.1	555.9	555.1
170°	534.1	538.1	541.1	543.1	544.1	543.1	543.1
172.5°	526.9	529.3	531.5	532.7	533.7	532.7	531.1
175°	517.1	519.1	519.1	519.1	521.1	519.1	517.1
177.5°	511.3	511.3	512.1	511.3	512.1	510.5	508.9
180°	508.1	508.1	508.1	508.1	508.1	508.1	508.1

(END OF REPORT)