

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333314-927

Luminaire Tested: **S125DIP-S1270D810U927-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333314-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S1270D810U927-4F0-1E-UDD-A1
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1270 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 810 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6328.3 lumens
Efficiency: N/A
Efficacy: 104.3 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 60.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333314-927

CATALOG NUMBER: S125DIP-S1270D810U927-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P333314-927

CATALOG NUMBER: S125DIP-S1270D810U927-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	104	104	104	104	92	92	92	80	80	80	70	70	70	65
1	101	97	93	90	95	91	88	85	81	78	76	71	69	68	62	61	60	55
2	93	85	79	74	87	80	75	70	71	67	63	63	60	57	55	53	51	47
3	85	75	68	62	79	71	64	59	63	58	54	56	52	48	49	46	43	40
4	78	67	59	53	73	63	56	50	56	50	46	50	45	42	44	40	38	34
5	71	60	51	45	67	56	49	43	50	44	40	45	40	36	40	36	33	30
6	66	54	45	39	62	51	43	38	46	39	35	41	36	32	36	32	29	26
7	61	48	40	35	57	46	39	33	41	35	31	37	32	28	33	29	26	23
8	57	44	36	31	53	42	35	30	38	32	27	34	29	25	30	26	23	21
9	53	40	33	28	50	38	31	27	35	29	25	31	26	23	28	24	21	19
10	49	37	30	25	46	35	28	24	32	26	22	29	24	21	26	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9396	9396	9396	9396
5°	10881	9428	8255	9428
10°	12660	9379	7233	9379
15°	14014	9310	6672	9310
20°	15687	9201	6222	9201
25°	18377	9079	6002	9079
30°	19848	8957	5812	8957
35°	16320	8729	5687	8729
40°	11600	8413	5550	8413
45°	8912	7986	5471	7986
50°	7607	7458	5460	7458
55°	6773	6939	5507	6939
60°	6110	6373	5647	6373
65°	5644	5804	5793	5804
70°	5130	5212	5876	5212
75°	4531	4591	5827	4591
80°	3812	3745	5326	3745
85°	3016	2697	4305	2697



TEST NUMBER: P333314-927

CATALOG NUMBER: S125DIP-S1270D810U927-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	140.1	2.2
10°-20°	417.0	6.6
20°-30°	677.1	10.7
30°-40°	826.0	13.1
40°-50°	751.4	11.9
50°-60°	598.5	9.5
60°-70°	416.9	6.6
70°-80°	222.3	3.5
80°-90°	57.9	0.9
90°-100°	53.3	0.8
100°-110°	157.4	2.5
110°-120°	266.7	4.2
120°-130°	350.9	5.5
130°-140°	393.2	6.2
140°-150°	385.4	6.1
150°-160°	323.7	5.1
160°-170°	215.2	3.4
170°-180°	75.3	1.2
0°-30°	1234.2	19.5
0°-40°	2060.2	32.6
0°-60°	3410.1	53.9
0°-90°	4107.2	64.9
90°-120°	477.4	7.5
90°-150°	1607.0	25.4
90°-180°	2221.0	35.1
0°-180°	6328.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1455	1455	1455	1455	1455	
5°	1678	1454	1273	1454	1678	169
15°	2096	1392	998	1392	2096	600
25°	2579	1274	842	1274	2579	1178
35°	2070	1107	721	1107	2070	1267
45°	976	874	599	874	976	781
55°	602	616	489	616	602	542
65°	369	380	379	380	369	367
75°	182	184	234	184	182	196
85°	41	36	58	36	41	47
90°	15	1	15	1	15	10
95°	53	40	53	40	53	54
105°	154	141	154	141	154	163
115°	270	267	270	267	270	267
125°	392	390	392	390	392	350
135°	509	507	509	507	509	392
145°	616	614	616	614	616	385
155°	702	702	702	702	702	323
165°	762	764	762	764	762	215
175°	791	794	791	794	791	75
180°	796	796	796	796	796	



TEST NUMBER: P333314-927

CATALOG NUMBER: S125DIP-S1270D810U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1454.9	1454.9	1454.9	1454.9	1454.9	1454.9	1454.9	1454.9	1454.9	1454.9	1454.9
2.5°	1538.9	1536.9	1534.9	1531.0	1533.9	1525.5	1521.5	1514.7	1506.3	1503.3	1499.8
5°	1678.4	1681.5	1684.6	1671.7	1672.9	1664.2	1644.5	1628.4	1615.4	1598.8	1587.1
7.5°	1846.4	1839.1	1838.5	1830.1	1815.7	1804.0	1783.3	1756.8	1731.3	1702.2	1678.1
10°	1930.4	1931.0	1925.5	1915.6	1900.1	1889.0	1861.9	1835.9	1804.4	1767.4	1740.8
12.5°	1993.6	1996.2	1989.2	1975.9	1968.3	1943.4	1922.1	1891.3	1853.8	1824.2	1783.8
15°	2095.9	2089.1	2084.2	2067.4	2054.5	2028.5	1994.6	1962.5	1921.8	1884.0	1846.4
17.5°	2194.4	2199.9	2190.6	2175.4	2135.2	2104.9	2059.4	2015.3	1964.6	1914.1	1869.2
20°	2282.4	2287.3	2273.1	2246.5	2198.4	2168.1	2108.2	2051.4	1992.7	1927.9	1878.5
22.5°	2392.1	2388.1	2368.9	2328.5	2286.8	2230.9	2166.1	2096.8	2023.4	1950.1	1884.4
25°	2578.8	2552.8	2541.1	2491.1	2436.1	2354.0	2265.1	2163.8	2072.4	1975.5	1891.5
27.5°	2682.3	2674.1	2661.0	2626.2	2568.4	2480.6	2375.8	2252.3	2123.4	2001.1	1891.1
30°	2661.5	2662.8	2664.0	2652.9	2615.9	2549.7	2445.4	2312.6	2159.5	2021.8	1894.6
32.5°	2477.8	2500.2	2521.8	2547.2	2557.6	2544.8	2479.5	2359.6	2201.9	2045.5	1892.6
35°	2070.0	2076.7	2146.5	2215.7	2309.5	2382.4	2431.2	2378.1	2245.3	2065.6	1890.2
37.5°	1614.0	1647.3	1695.6	1773.8	1909.2	2030.5	2186.5	2258.3	2215.4	2072.2	1885.9
40°	1375.9	1406.8	1438.2	1517.9	1632.1	1779.1	1956.3	2107.6	2142.8	2051.4	1871.1
42.5°	1192.1	1216.6	1251.5	1311.4	1406.8	1537.0	1706.4	1904.1	2025.7	1991.2	1840.0
45°	975.7	991.1	1018.3	1065.9	1135.0	1236.9	1386.3	1602.5	1790.8	1853.2	1766.1
47.5°	835.1	835.0	856.1	889.0	938.9	1025.5	1136.0	1305.4	1506.5	1655.3	1648.5
50°	757.1	754.0	770.6	799.1	838.6	896.0	1001.6	1136.9	1330.2	1498.7	1545.6
52.5°	689.9	690.2	700.5	721.5	754.6	803.7	882.6	1004.5	1169.6	1342.6	1431.1
55°	601.5	599.0	610.7	625.0	649.0	681.1	737.9	831.2	965.2	1135.6	1250.5
57.5°	520.5	527.3	532.0	541.9	561.8	583.3	631.2	699.7	806.0	952.2	1073.6
60°	473.0	479.8	483.5	493.4	509.5	528.0	565.1	620.6	710.2	836.1	956.6
62.5°	430.6	435.9	437.0	446.0	459.1	477.1	506.3	552.9	623.7	733.9	851.8
65°	369.3	369.3	371.8	381.0	387.2	403.2	425.5	459.5	516.3	602.1	702.7
67.5°	310.2	313.2	312.6	316.6	322.3	334.9	350.8	378.8	420.9	483.5	564.0
70°	271.7	274.2	273.5	276.6	282.8	290.9	303.8	330.3	360.6	414.4	483.5
72.5°	237.1	238.1	236.5	240.6	244.3	251.4	265.8	280.0	308.2	353.6	410.4
75°	181.6	182.8	184.0	186.5	190.2	193.9	201.3	215.6	234.0	268.0	304.4
77.5°	136.1	133.7	136.7	136.3	138.5	141.3	147.8	155.3	170.6	192.0	220.2
80°	102.5	103.1	103.1	103.8	106.9	108.7	114.2	119.8	131.5	147.6	167.4
82.5°	74.9	76.4	75.5	76.6	79.1	80.5	83.6	88.2	95.0	107.6	121.9
85°	40.7	37.7	38.9	40.2	40.2	40.7	43.3	45.1	48.8	53.7	59.3
87.5°	14.8	15.8	16.2	16.1	16.5	16.4	18.2	18.1	19.4	20.8	22.6
90°	14.9	14.4	14.0	13.6	13.2	12.7	12.0	11.2	10.6	9.9	9.0
92.5°	29.2	28.9	28.6	28.4	28.0	27.4	26.5	25.6	24.7	23.8	22.6
95°	53.2	53.0	52.8	52.4	52.2	51.6	50.6	49.6	48.6	47.7	46.3
97.5°	80.8	80.6	80.4	80.2	80.1	79.6	78.7	77.8	76.8	76.0	74.1
100°	101.6	101.3	101.0	100.8	100.5	99.7	98.5	97.3	96.0	94.7	93.0
102.5°	122.4	122.0	121.6	121.3	120.9	120.0	118.7	117.3	116.0	114.6	113.7
105°	153.6	153.2	152.8	152.4	151.9	151.4	150.5	149.7	148.9	148.1	147.2
107.5°	185.6	185.6	185.6	185.7	185.7	185.5	185.1	184.7	184.3	183.9	183.2
110°	209.4	209.5	209.6	209.8	209.9	209.8	209.4	209.0	208.6	208.1	207.7



TEST NUMBER: P333314-927

CATALOG NUMBER: S125DIP-S1270D810U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	232.7	232.9	233.1	233.4	233.7	233.7	233.5	233.3	233.1	232.9	232.4
115°	269.5	269.6	269.7	269.9	270.0	270.1	270.3	270.5	270.5	270.7	270.5
117.5°	305.4	305.9	306.5	307.0	307.6	307.8	307.7	307.6	307.4	307.4	307.1
120°	330.2	330.7	331.3	331.8	332.4	332.6	332.6	332.6	332.6	332.6	332.5
122.5°	355.0	355.4	355.8	356.2	356.7	357.0	357.1	357.2	357.3	357.4	357.0
125°	392.1	392.3	392.4	392.5	392.7	392.8	393.2	393.4	393.7	394.0	393.8
127.5°	427.8	428.1	428.3	428.6	428.9	429.1	429.2	429.4	429.5	429.7	429.5
130°	451.5	451.9	452.1	452.4	452.7	452.9	453.0	453.1	453.3	453.4	453.1
132.5°	473.9	474.3	474.7	475.1	475.4	475.7	475.8	475.9	476.1	476.3	476.3
135°	508.6	509.1	509.7	510.2	510.8	511.0	511.0	511.0	511.0	511.0	510.9
137.5°	542.5	543.2	543.9	544.5	545.3	545.5	545.3	545.2	545.0	544.9	544.5
140°	564.4	565.0	565.7	566.4	567.0	567.3	567.0	566.7	566.5	566.2	565.8
142.5°	585.1	585.8	586.5	587.2	587.9	588.1	588.0	587.8	587.6	587.5	586.9
145°	616.3	616.8	617.2	617.6	618.0	618.2	618.2	618.2	618.2	618.2	617.8
147.5°	643.0	644.0	644.8	645.8	646.7	647.1	646.7	646.3	646.0	645.7	645.4
150°	662.8	663.1	663.4	663.6	663.9	664.1	664.1	664.1	664.1	664.1	663.5
152.5°	679.1	679.7	680.2	680.6	681.1	681.2	680.9	680.6	680.2	679.9	679.7
155°	702.4	703.1	703.9	704.5	705.2	705.3	704.7	704.2	703.6	703.1	702.9
157.5°	721.9	722.8	723.7	724.6	725.6	725.7	725.2	724.6	724.1	723.5	723.3
160°	735.3	735.9	736.7	737.4	738.1	738.1	737.5	737.0	736.5	735.9	735.8
162.5°	746.7	747.5	748.3	749.1	749.9	750.0	749.3	748.6	748.0	747.3	747.3
165°	761.9	762.7	763.6	764.4	765.2	765.3	764.9	764.3	763.7	763.2	763.0
167.5°	774.0	774.9	775.8	776.7	777.4	777.5	776.7	775.9	775.0	774.2	774.2
170°	780.5	781.5	782.4	783.4	784.3	784.4	783.6	782.8	782.0	781.1	781.1
172.5°	785.9	786.8	787.7	788.5	789.4	789.4	788.5	787.7	786.9	786.1	786.1
175°	791.1	792.0	793.0	793.9	794.9	795.0	794.2	793.3	792.5	791.6	791.6
177.5°	794.0	794.8	795.6	796.3	797.1	797.2	796.5	795.8	795.2	794.5	794.6
180°	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0



TEST NUMBER: P333314-927

CATALOG NUMBER: S125DIP-S1270D810U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1454.9	1454.9	1454.9	1454.9	1454.9	1454.9	1454.9	1454.9	1454.9	1454.9	1454.9
2.5°	1496.9	1493.4	1489.5	1482.6	1474.2	1469.7	1462.8	1458.3	1449.5	1442.0	1434.2
5°	1572.8	1556.8	1542.0	1522.8	1501.8	1488.2	1472.2	1454.3	1435.8	1416.6	1395.6
7.5°	1651.5	1623.1	1592.2	1559.0	1526.5	1496.6	1468.1	1440.0	1413.9	1382.3	1355.5
10°	1704.4	1668.6	1630.2	1585.2	1541.3	1503.1	1464.1	1430.2	1395.6	1358.5	1325.8
12.5°	1757.2	1709.5	1655.4	1605.9	1553.2	1507.0	1461.2	1417.8	1374.4	1333.3	1295.2
15°	1794.5	1752.5	1702.5	1632.1	1572.8	1509.3	1448.7	1392.5	1340.1	1294.3	1246.2
17.5°	1819.1	1765.0	1711.3	1643.7	1566.1	1494.9	1426.3	1362.0	1302.8	1244.9	1198.5
20°	1823.5	1768.0	1711.7	1645.7	1566.1	1484.5	1415.9	1338.8	1275.2	1215.3	1158.5
22.5°	1822.1	1759.0	1698.0	1629.9	1552.2	1477.1	1394.2	1315.6	1246.5	1187.6	1128.3
25°	1808.1	1740.8	1664.2	1595.7	1519.1	1439.5	1355.5	1274.0	1203.6	1136.2	1077.6
27.5°	1796.5	1709.2	1622.5	1542.5	1468.6	1395.6	1315.2	1231.7	1153.7	1085.4	1030.2
30°	1782.2	1686.5	1588.9	1505.5	1429.6	1358.5	1282.6	1201.1	1119.6	1052.9	993.6
32.5°	1769.3	1657.8	1554.8	1464.0	1383.6	1314.5	1244.5	1167.0	1087.0	1019.3	960.0
35°	1744.5	1615.4	1497.5	1395.0	1309.2	1238.1	1179.5	1107.2	1033.7	968.3	911.5
37.5°	1713.0	1559.9	1433.3	1325.8	1231.7	1156.9	1102.2	1046.8	976.3	913.2	861.8
40°	1688.3	1520.4	1386.3	1276.4	1178.8	1101.1	1050.4	997.9	939.3	880.6	826.2
42.5°	1657.2	1484.8	1338.9	1220.6	1124.0	1048.2	995.1	950.5	898.7	844.1	793.6
45°	1600.0	1420.3	1262.2	1135.0	1037.4	962.7	907.8	874.4	835.5	783.6	741.0
47.5°	1515.9	1342.8	1179.3	1048.1	947.4	878.1	826.6	794.6	767.2	728.6	690.0
50°	1441.3	1285.1	1119.6	989.3	888.6	818.8	771.3	742.3	718.8	689.1	656.4
52.5°	1357.8	1212.4	1060.8	932.0	832.3	763.5	716.9	691.4	671.8	650.6	618.4
55°	1225.2	1101.7	960.8	838.6	746.6	679.3	638.5	616.3	600.2	584.2	564.4
57.5°	1079.0	982.5	857.8	746.0	661.2	600.0	562.0	540.3	527.8	519.6	507.9
60°	976.3	893.6	786.1	684.2	601.5	547.2	510.1	493.4	482.9	476.1	467.5
62.5°	881.0	813.0	713.5	620.5	548.1	496.7	463.7	447.4	437.4	434.1	427.0
65°	740.4	687.9	605.8	528.6	466.8	423.0	395.2	379.8	373.6	369.9	370.5
67.5°	602.0	570.0	504.0	438.2	388.9	352.1	329.9	318.1	315.0	310.0	309.9
70°	517.5	493.4	437.8	380.4	336.5	308.2	288.4	276.0	272.9	270.5	269.9
72.5°	442.9	421.8	373.6	327.6	288.1	263.2	246.9	239.5	234.4	232.9	232.8
75°	332.9	321.2	282.8	246.4	219.2	201.9	190.8	184.0	180.3	179.7	180.3
77.5°	236.6	226.4	202.1	176.3	159.1	146.0	136.6	134.3	130.1	130.2	129.5
80°	177.8	171.0	155.6	135.2	121.0	110.0	105.0	100.7	99.4	97.6	99.4
82.5°	129.0	121.7	111.1	98.2	86.4	79.8	74.9	73.5	72.7	71.9	72.2
85°	63.6	64.2	58.1	48.2	43.3	39.5	36.4	36.4	35.8	35.2	35.8
87.5°	23.4	22.2	20.0	18.3	15.6	13.9	13.2	13.5	12.2	12.0	12.7
90°	8.0	7.1	6.0	5.0	4.0	2.9	1.7	0.6	1.7	2.9	4.0
92.5°	21.4	20.2	19.0	18.1	17.3	16.6	15.8	15.0	15.8	16.6	17.3
95°	44.9	43.6	42.2	41.4	41.1	40.8	40.6	40.2	40.6	40.8	41.1
97.5°	72.2	70.3	68.4	67.3	67.3	67.1	67.0	66.9	67.0	67.1	67.3
100°	91.2	89.4	87.6	86.7	86.7	86.7	86.7	86.7	86.7	86.7	86.7
102.5°	112.8	111.9	111.0	110.3	109.7	109.2	108.6	108.1	108.6	109.2	109.7
105°	146.4	145.6	144.7	144.0	143.3	142.6	142.0	141.2	142.0	142.6	143.3
107.5°	182.6	182.0	181.3	180.7	180.0	179.3	178.6	177.9	178.6	179.3	180.0
110°	207.3	206.9	206.5	206.0	205.3	204.5	203.9	203.2	203.9	204.5	205.3



TEST NUMBER: P333314-927

CATALOG NUMBER: S125DIP-S1270D810U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	231.9	231.3	230.8	230.4	230.0	229.7	229.3	228.9	229.3	229.7	230.0
115°	270.1	269.9	269.6	269.2	268.6	268.1	267.5	267.0	267.5	268.1	268.6
117.5°	306.9	306.7	306.4	306.1	305.9	305.6	305.4	305.1	305.4	305.6	305.9
120°	332.4	332.2	332.1	331.7	331.0	330.3	329.6	328.9	329.6	330.3	331.0
122.5°	356.7	356.3	356.0	355.7	355.5	355.2	355.0	354.7	355.0	355.2	355.5
125°	393.7	393.6	393.4	392.9	392.1	391.3	390.5	389.6	390.5	391.3	392.1
127.5°	429.3	429.1	429.0	428.6	428.2	427.7	427.3	426.8	427.3	427.7	428.2
130°	452.9	452.6	452.3	451.9	451.1	450.5	449.8	449.1	449.8	450.5	451.1
132.5°	476.3	476.4	476.4	475.9	474.8	473.6	472.5	471.4	472.5	473.6	474.8
135°	510.8	510.6	510.5	510.0	509.2	508.3	507.6	506.7	507.6	508.3	509.2
137.5°	544.2	544.0	543.7	543.1	542.3	541.5	540.7	540.0	540.7	541.5	542.3
140°	565.4	564.9	564.5	564.0	563.3	562.6	561.9	561.3	561.9	562.6	563.3
142.5°	586.5	585.9	585.4	584.9	584.2	583.7	583.1	582.6	583.1	583.7	584.2
145°	617.3	617.0	616.6	616.1	615.5	615.0	614.4	613.9	614.4	615.0	615.5
147.5°	645.1	644.8	644.4	644.0	643.8	643.5	643.2	642.9	643.2	643.5	643.8
150°	663.0	662.4	661.9	661.6	661.8	661.9	662.0	662.2	662.0	661.9	661.8
152.5°	679.5	679.2	679.1	678.8	678.7	678.4	678.3	678.0	678.3	678.4	678.7
155°	702.8	702.7	702.5	702.4	702.4	702.4	702.4	702.4	702.4	702.4	702.4
157.5°	723.3	723.1	722.9	723.0	723.3	723.7	724.0	724.3	724.0	723.7	723.3
160°	735.6	735.5	735.4	735.5	735.9	736.3	736.7	737.1	736.7	736.3	735.9
162.5°	747.3	747.2	747.2	747.3	747.7	747.9	748.2	748.5	748.2	747.9	747.7
165°	762.9	762.7	762.6	762.7	763.0	763.3	763.5	763.8	763.5	763.3	763.0
167.5°	774.2	774.2	774.2	774.4	775.0	775.5	776.1	776.7	776.1	775.5	775.0
170°	781.1	781.1	781.1	781.4	782.0	782.5	783.1	783.6	783.1	782.5	782.0
172.5°	786.1	786.1	786.1	786.3	786.9	787.4	788.0	788.5	788.0	787.4	786.9
175°	791.6	791.6	791.6	791.9	792.5	793.1	793.6	794.2	793.6	793.1	792.5
177.5°	794.7	794.9	795.0	795.2	795.7	796.1	796.5	797.0	796.5	796.1	795.7
180°	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0



TEST NUMBER: P333314-927

CATALOG NUMBER: S125DIP-S1270D810U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1454.9	1454.9	1454.9	1454.9	1454.9	1454.9	1454.9	1454.9	1454.9	1454.9	1454.9
2.5°	1429.7	1424.3	1419.8	1409.9	1404.5	1397.1	1391.2	1397.6	1390.7	1393.6	1389.2
5°	1385.1	1367.8	1355.5	1337.5	1322.2	1307.9	1297.4	1295.5	1290.6	1288.2	1280.7
7.5°	1331.5	1309.9	1288.6	1265.2	1245.4	1225.3	1212.4	1201.8	1194.8	1185.5	1179.2
10°	1299.9	1270.9	1246.2	1217.7	1193.0	1171.5	1154.1	1145.5	1137.5	1125.8	1121.4
12.5°	1260.8	1230.8	1200.7	1170.4	1146.6	1122.5	1107.7	1094.6	1089.1	1075.9	1074.5
15°	1214.0	1168.9	1139.3	1108.4	1075.7	1056.0	1043.6	1029.4	1023.3	1014.0	1007.2
17.5°	1158.2	1117.9	1080.9	1048.9	1020.9	1004.2	988.9	979.1	968.5	962.5	951.3
20°	1117.7	1079.4	1042.4	1008.4	986.8	967.7	955.3	946.0	934.9	931.8	920.8
22.5°	1083.6	1041.4	1005.8	977.3	953.7	932.1	918.8	912.4	904.8	895.3	893.0
25°	1028.2	984.4	954.1	925.7	904.7	884.9	875.7	867.6	860.2	853.4	851.0
27.5°	980.2	941.1	905.1	879.5	861.2	843.2	835.0	825.3	819.8	814.4	807.7
30°	946.7	906.5	875.0	850.3	830.6	814.5	805.9	799.1	794.2	789.2	785.5
32.5°	912.1	874.9	844.4	820.2	800.4	788.3	780.7	775.9	770.4	764.5	759.8
35°	866.4	825.6	796.0	775.0	759.5	750.3	741.6	737.3	731.2	731.2	726.2
37.5°	814.9	779.7	753.5	734.4	720.5	712.3	702.9	699.9	695.9	693.3	691.7
40°	784.3	751.5	726.8	707.7	692.8	686.0	678.7	673.8	671.2	668.1	666.9
42.5°	752.7	721.4	697.7	680.0	667.2	661.4	654.4	651.0	646.0	642.0	641.3
45°	704.6	674.3	652.8	638.5	627.4	620.6	616.3	608.9	606.4	601.5	600.9
47.5°	659.0	630.0	608.8	597.1	587.4	581.9	575.0	567.6	564.8	562.3	562.1
50°	625.0	598.4	578.6	567.5	558.3	550.2	543.4	538.4	536.6	536.6	537.9
52.5°	590.3	567.8	551.0	537.3	528.6	520.1	513.8	510.8	507.9	511.0	513.2
55°	539.7	516.9	504.5	491.5	482.9	473.0	469.9	468.7	466.8	471.8	474.3
57.5°	486.1	470.1	455.6	442.8	435.0	429.3	425.1	424.4	427.9	430.2	438.2
60°	452.0	433.5	420.6	410.7	401.4	397.7	396.5	395.2	397.7	404.5	414.9
62.5°	414.5	399.4	385.5	378.0	371.2	365.1	364.8	365.6	370.5	378.3	388.8
65°	359.4	346.4	337.2	328.5	323.0	319.2	320.5	323.0	328.5	339.1	350.8
67.5°	303.5	294.5	286.3	279.2	273.9	273.9	275.2	278.8	285.4	297.5	308.2
70°	267.4	257.5	250.7	247.6	243.3	240.8	244.5	250.7	256.3	267.4	276.6
72.5°	231.3	222.9	217.6	215.6	213.7	211.7	212.9	219.6	227.1	238.2	249.0
75°	177.8	174.8	171.0	168.6	166.8	167.9	169.2	175.4	181.6	193.3	205.7
77.5°	129.8	126.6	124.4	123.7	122.8	123.3	126.8	131.4	137.4	146.0	155.3
80°	98.2	97.0	95.7	95.1	95.1	95.7	100.7	103.8	109.3	117.3	124.8
82.5°	71.5	70.7	70.5	70.4	70.9	71.0	74.0	78.0	82.6	88.6	95.1
85°	37.7	36.4	38.3	38.9	37.7	39.5	40.7	43.3	45.1	48.2	51.3
87.5°	13.4	14.6	14.3	15.0	15.1	16.3	15.9	18.1	19.2	20.3	20.0
90°	5.0	6.0	7.1	8.0	9.0	9.9	10.6	11.2	12.0	12.7	13.2
92.5°	18.1	19.0	20.2	21.4	22.6	23.8	24.7	25.6	26.5	27.4	28.0
95°	41.4	42.2	43.6	44.9	46.3	47.7	48.6	49.6	50.6	51.6	52.2
97.5°	67.3	68.4	70.3	72.2	74.1	76.0	76.8	77.8	78.7	79.6	80.1
100°	86.7	87.6	89.4	91.2	93.0	94.7	96.0	97.3	98.5	99.7	100.5
102.5°	110.3	111.0	111.9	112.8	113.7	114.6	116.0	117.3	118.7	120.0	120.9
105°	144.0	144.7	145.6	146.4	147.2	148.1	148.9	149.7	150.5	151.4	151.9
107.5°	180.7	181.3	182.0	182.6	183.2	183.9	184.3	184.7	185.1	185.5	185.7
110°	206.0	206.5	206.9	207.3	207.7	208.1	208.6	209.0	209.4	209.8	209.9



TEST NUMBER: P333314-927

CATALOG NUMBER: S125DIP-S1270D810U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	230.4	230.8	231.3	231.9	232.4	232.9	233.1	233.3	233.5	233.7	233.7
115°	269.2	269.6	269.9	270.1	270.5	270.7	270.5	270.5	270.3	270.1	270.0
117.5°	306.1	306.4	306.7	306.9	307.1	307.4	307.4	307.6	307.7	307.8	307.6
120°	331.7	332.1	332.2	332.4	332.5	332.6	332.6	332.6	332.6	332.6	332.4
122.5°	355.7	356.0	356.3	356.7	357.0	357.4	357.3	357.2	357.1	357.0	356.7
125°	392.9	393.4	393.6	393.7	393.8	394.0	393.7	393.4	393.2	392.8	392.7
127.5°	428.6	429.0	429.1	429.3	429.5	429.7	429.5	429.4	429.2	429.1	428.9
130°	451.9	452.3	452.6	452.9	453.1	453.4	453.3	453.1	453.0	452.9	452.7
132.5°	475.9	476.4	476.4	476.3	476.3	476.3	476.1	475.9	475.8	475.7	475.4
135°	510.0	510.5	510.6	510.8	510.9	511.0	511.0	511.0	511.0	511.0	510.8
137.5°	543.1	543.7	544.0	544.2	544.5	544.9	545.0	545.2	545.3	545.5	545.3
140°	564.0	564.5	564.9	565.4	565.8	566.2	566.5	566.7	567.0	567.3	567.0
142.5°	584.9	585.4	585.9	586.5	586.9	587.5	587.6	587.8	588.0	588.1	587.9
145°	616.1	616.6	617.0	617.3	617.8	618.2	618.2	618.2	618.2	618.2	618.0
147.5°	644.0	644.4	644.8	645.1	645.4	645.7	646.0	646.3	646.7	647.1	646.7
150°	661.6	661.9	662.4	663.0	663.5	664.1	664.1	664.1	664.1	664.1	663.9
152.5°	678.8	679.1	679.2	679.5	679.7	679.9	680.2	680.6	680.9	681.2	681.1
155°	702.4	702.5	702.7	702.8	702.9	703.1	703.6	704.2	704.7	705.3	705.2
157.5°	723.0	722.9	723.1	723.3	723.3	723.5	724.1	724.6	725.2	725.7	725.6
160°	735.5	735.4	735.5	735.6	735.8	735.9	736.5	737.0	737.5	738.1	738.1
162.5°	747.3	747.2	747.2	747.3	747.3	747.3	748.0	748.6	749.3	750.0	749.9
165°	762.7	762.6	762.7	762.9	763.0	763.2	763.7	764.3	764.9	765.3	765.2
167.5°	774.4	774.2	774.2	774.2	774.2	774.2	775.0	775.9	776.7	777.5	777.4
170°	781.4	781.1	781.1	781.1	781.1	781.1	782.0	782.8	783.6	784.4	784.3
172.5°	786.3	786.1	786.1	786.1	786.1	786.1	786.9	787.7	788.5	789.4	789.4
175°	791.9	791.6	791.6	791.6	791.6	791.6	792.5	793.3	794.2	795.0	794.9
177.5°	795.2	795.0	794.9	794.7	794.6	794.5	795.2	795.8	796.5	797.2	797.1
180°	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0



TEST NUMBER: P333314-927

CATALOG NUMBER: S125DIP-S1270D810U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1454.9	1454.9	1454.9	1454.9	1454.9	1454.9	1454.9	1454.9	1454.9	1454.9	1454.9
2.5°	1386.2	1389.6	1386.7	1390.7	1386.7	1389.6	1386.2	1389.2	1393.6	1390.7	1397.6
5°	1277.6	1272.1	1275.8	1273.4	1275.8	1272.1	1277.6	1280.7	1288.2	1290.6	1295.5
7.5°	1177.3	1172.0	1166.0	1163.2	1166.0	1172.0	1177.3	1179.2	1185.5	1194.8	1201.8
10°	1114.6	1107.9	1107.2	1102.9	1107.2	1107.9	1114.6	1121.4	1125.8	1137.5	1145.5
12.5°	1068.7	1062.4	1055.3	1053.5	1055.3	1062.4	1068.7	1074.5	1075.9	1089.1	1094.6
15°	1003.5	998.5	994.2	997.9	994.2	998.5	1003.5	1007.2	1014.0	1023.3	1029.4
17.5°	949.3	945.2	944.4	939.8	944.4	945.2	949.3	951.3	962.5	968.5	979.1
20°	915.2	912.1	913.3	905.3	913.3	912.1	915.2	920.8	931.8	934.9	946.0
22.5°	888.0	881.9	881.2	879.6	881.2	881.9	888.0	893.0	895.3	904.8	912.4
25°	845.4	842.3	839.2	842.3	839.2	842.3	845.4	851.0	853.4	860.2	867.6
27.5°	808.2	804.5	803.7	804.0	803.7	804.5	808.2	807.7	814.4	819.8	825.3
30°	785.5	779.3	779.9	779.3	779.9	779.3	785.5	785.5	789.2	794.2	799.1
32.5°	760.8	756.6	755.7	754.6	755.7	756.6	760.8	759.8	764.5	770.4	775.9
35°	724.4	724.4	721.3	721.3	721.3	724.4	724.4	726.2	731.2	731.2	737.3
37.5°	690.1	689.5	687.7	687.9	687.7	689.5	690.1	691.7	693.3	695.9	699.9
40°	664.5	663.8	661.9	658.3	661.9	663.8	664.5	666.9	668.1	671.2	673.8
42.5°	639.8	637.6	636.8	635.6	636.8	637.6	639.8	641.3	642.0	646.0	651.0
45°	600.9	600.9	599.6	599.0	599.6	600.9	600.9	600.9	601.5	606.4	608.9
47.5°	563.1	564.2	566.5	566.2	566.5	564.2	563.1	562.1	562.3	564.8	567.6
50°	540.3	541.0	542.8	543.4	542.8	541.0	540.3	537.9	536.6	536.6	538.4
52.5°	515.2	518.7	521.1	520.7	521.1	518.7	515.2	513.2	511.0	507.9	510.8
55°	479.8	484.1	488.5	489.1	488.5	484.1	479.8	474.3	471.8	466.8	468.7
57.5°	444.9	450.9	455.5	456.9	455.5	450.9	444.9	438.2	430.2	427.9	424.4
60°	421.1	429.2	434.7	437.2	434.7	429.2	421.1	414.9	404.5	397.7	395.2
62.5°	398.4	407.4	413.0	413.5	413.0	407.4	398.4	388.8	378.3	370.5	365.6
65°	361.2	370.5	375.4	379.1	375.4	370.5	361.2	350.8	339.1	328.5	323.0
67.5°	321.2	330.5	336.0	338.9	336.0	330.5	321.2	308.2	297.5	285.4	278.8
70°	292.1	301.3	308.8	311.2	308.8	301.3	292.1	276.6	267.4	256.3	250.7
72.5°	263.4	271.7	277.7	280.6	277.7	271.7	263.4	249.0	238.2	227.1	219.6
75°	213.7	224.7	230.4	233.5	230.4	224.7	213.7	205.7	193.3	181.6	175.4
77.5°	164.8	174.9	178.2	179.8	178.2	174.9	164.8	155.3	146.0	137.4	131.4
80°	132.1	138.3	142.7	143.2	142.7	138.3	132.1	124.8	117.3	109.3	103.8
82.5°	101.6	106.7	108.1	109.6	108.1	106.7	101.6	95.1	88.6	82.6	78.0
85°	55.6	58.1	58.7	58.1	58.7	58.1	55.6	51.3	48.2	45.1	43.3
87.5°	21.0	20.6	20.7	21.8	20.7	20.6	21.0	20.0	20.3	19.2	18.1
90°	13.6	14.0	14.4	14.9	14.4	14.0	13.6	13.2	12.7	12.0	11.2
92.5°	28.4	28.6	28.9	29.2	28.9	28.6	28.4	28.0	27.4	26.5	25.6
95°	52.4	52.8	53.0	53.2	53.0	52.8	52.4	52.2	51.6	50.6	49.6
97.5°	80.2	80.4	80.6	80.8	80.6	80.4	80.2	80.1	79.6	78.7	77.8
100°	100.8	101.0	101.3	101.6	101.3	101.0	100.8	100.5	99.7	98.5	97.3
102.5°	121.3	121.6	122.0	122.4	122.0	121.6	121.3	120.9	120.0	118.7	117.3
105°	152.4	152.8	153.2	153.6	153.2	152.8	152.4	151.9	151.4	150.5	149.7
107.5°	185.7	185.6	185.6	185.6	185.6	185.6	185.7	185.7	185.5	185.1	184.7
110°	209.8	209.6	209.5	209.4	209.5	209.6	209.8	209.9	209.8	209.4	209.0



TEST NUMBER: P333314-927

CATALOG NUMBER: S125DIP-S1270D810U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	233.4	233.1	232.9	232.7	232.9	233.1	233.4	233.7	233.7	233.5	233.3
115°	269.9	269.7	269.6	269.5	269.6	269.7	269.9	270.0	270.1	270.3	270.5
117.5°	307.0	306.5	305.9	305.4	305.9	306.5	307.0	307.6	307.8	307.7	307.6
120°	331.8	331.3	330.7	330.2	330.7	331.3	331.8	332.4	332.6	332.6	332.6
122.5°	356.2	355.8	355.4	355.0	355.4	355.8	356.2	356.7	357.0	357.1	357.2
125°	392.5	392.4	392.3	392.1	392.3	392.4	392.5	392.7	392.8	393.2	393.4
127.5°	428.6	428.3	428.1	427.8	428.1	428.3	428.6	428.9	429.1	429.2	429.4
130°	452.4	452.1	451.9	451.5	451.9	452.1	452.4	452.7	452.9	453.0	453.1
132.5°	475.1	474.7	474.3	473.9	474.3	474.7	475.1	475.4	475.7	475.8	475.9
135°	510.2	509.7	509.1	508.6	509.1	509.7	510.2	510.8	511.0	511.0	511.0
137.5°	544.5	543.9	543.2	542.5	543.2	543.9	544.5	545.3	545.5	545.3	545.2
140°	566.4	565.7	565.0	564.4	565.0	565.7	566.4	567.0	567.3	567.0	566.7
142.5°	587.2	586.5	585.8	585.1	585.8	586.5	587.2	587.9	588.1	588.0	587.8
145°	617.6	617.2	616.8	616.3	616.8	617.2	617.6	618.0	618.2	618.2	618.2
147.5°	645.8	644.8	644.0	643.0	644.0	644.8	645.8	646.7	647.1	646.7	646.3
150°	663.6	663.4	663.1	662.8	663.1	663.4	663.6	663.9	664.1	664.1	664.1
152.5°	680.6	680.2	679.7	679.1	679.7	680.2	680.6	681.1	681.2	680.9	680.6
155°	704.5	703.9	703.1	702.4	703.1	703.9	704.5	705.2	705.3	704.7	704.2
157.5°	724.6	723.7	722.8	721.9	722.8	723.7	724.6	725.6	725.7	725.2	724.6
160°	737.4	736.7	735.9	735.3	735.9	736.7	737.4	738.1	738.1	737.5	737.0
162.5°	749.1	748.3	747.5	746.7	747.5	748.3	749.1	749.9	750.0	749.3	748.6
165°	764.4	763.6	762.7	761.9	762.7	763.6	764.4	765.2	765.3	764.9	764.3
167.5°	776.7	775.8	774.9	774.0	774.9	775.8	776.7	777.4	777.5	776.7	775.9
170°	783.4	782.4	781.5	780.5	781.5	782.4	783.4	784.3	784.4	783.6	782.8
172.5°	788.5	787.7	786.8	785.9	786.8	787.7	788.5	789.4	789.4	788.5	787.7
175°	793.9	793.0	792.0	791.1	792.0	793.0	793.9	794.9	795.0	794.2	793.3
177.5°	796.3	795.6	794.8	794.0	794.8	795.6	796.3	797.1	797.2	796.5	795.8
180°	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0



TEST NUMBER: P333314-927

CATALOG NUMBER: S125DIP-S1270D810U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1454.9	1454.9	1454.9	1454.9	1454.9	1454.9	1454.9	1454.9	1454.9	1454.9	1454.9
2.5°	1391.2	1397.1	1404.5	1409.9	1419.8	1424.3	1429.7	1434.2	1442.0	1449.5	1458.3
5°	1297.4	1307.9	1322.2	1337.5	1355.5	1367.8	1385.1	1395.6	1416.6	1435.8	1454.3
7.5°	1212.4	1225.3	1245.4	1265.2	1288.6	1309.9	1331.5	1355.5	1382.3	1413.9	1440.0
10°	1154.1	1171.5	1193.0	1217.7	1246.2	1270.9	1299.9	1325.8	1358.5	1395.6	1430.2
12.5°	1107.7	1122.5	1146.6	1170.4	1200.7	1230.8	1260.8	1295.2	1333.3	1374.4	1417.8
15°	1043.6	1056.0	1075.7	1108.4	1139.3	1168.9	1214.0	1246.2	1294.3	1340.1	1392.5
17.5°	988.9	1004.2	1020.9	1048.9	1080.9	1117.9	1158.2	1198.5	1244.9	1302.8	1362.0
20°	955.3	967.7	986.8	1008.4	1042.4	1079.4	1117.7	1158.5	1215.3	1275.2	1338.8
22.5°	918.8	932.1	953.7	977.3	1005.8	1041.4	1083.6	1128.3	1187.6	1246.5	1315.6
25°	875.7	884.9	904.7	925.7	954.1	984.4	1028.2	1077.6	1136.2	1203.6	1274.0
27.5°	835.0	843.2	861.2	879.5	905.1	941.1	980.2	1030.2	1085.4	1153.7	1231.7
30°	805.9	814.5	830.6	850.3	875.0	906.5	946.7	993.6	1052.9	1119.6	1201.1
32.5°	780.7	788.3	800.4	820.2	844.4	874.9	912.1	960.0	1019.3	1087.0	1167.0
35°	741.6	750.3	759.5	775.0	796.0	825.6	866.4	911.5	968.3	1033.7	1107.2
37.5°	702.9	712.3	720.5	734.4	753.5	779.7	814.9	861.8	913.2	976.3	1046.8
40°	678.7	686.0	692.8	707.7	726.8	751.5	784.3	826.2	880.6	939.3	997.9
42.5°	654.4	661.4	667.2	680.0	697.7	721.4	752.7	793.6	844.1	898.7	950.5
45°	616.3	620.6	627.4	638.5	652.8	674.3	704.6	741.0	783.6	835.5	874.4
47.5°	575.0	581.9	587.4	597.1	608.8	630.0	659.0	690.0	728.6	767.2	794.6
50°	543.4	550.2	558.3	567.5	578.6	598.4	625.0	656.4	689.1	718.8	742.3
52.5°	513.8	520.1	528.6	537.3	551.0	567.8	590.3	618.4	650.6	671.8	691.4
55°	469.9	473.0	482.9	491.5	504.5	516.9	539.7	564.4	584.2	600.2	616.3
57.5°	425.1	429.3	435.0	442.8	455.6	470.1	486.1	507.9	519.6	527.8	540.3
60°	396.5	397.7	401.4	410.7	420.6	433.5	452.0	467.5	476.1	482.9	493.4
62.5°	364.8	365.1	371.2	378.0	385.5	399.4	414.5	427.0	434.1	437.4	447.4
65°	320.5	319.2	323.0	328.5	337.2	346.4	359.4	370.5	369.9	373.6	379.8
67.5°	275.2	273.9	273.9	279.2	286.3	294.5	303.5	309.9	310.0	315.0	318.1
70°	244.5	240.8	243.3	247.6	250.7	257.5	267.4	269.9	270.5	272.9	276.0
72.5°	212.9	211.7	213.7	215.6	217.6	222.9	231.3	232.8	232.9	234.4	239.5
75°	169.2	167.9	166.8	168.6	171.0	174.8	177.8	180.3	179.7	180.3	184.0
77.5°	126.8	123.3	122.8	123.7	124.4	126.6	129.8	129.5	130.2	130.1	134.3
80°	100.7	95.7	95.1	95.1	95.7	97.0	98.2	99.4	97.6	99.4	100.7
82.5°	74.0	71.0	70.9	70.4	70.5	70.7	71.5	72.2	71.9	72.7	73.5
85°	40.7	39.5	37.7	38.9	38.3	36.4	37.7	35.8	35.2	35.8	36.4
87.5°	15.9	16.3	15.1	15.0	14.3	14.6	13.4	12.7	12.0	12.2	13.5
90°	10.6	9.9	9.0	8.0	7.1	6.0	5.0	4.0	2.9	1.7	0.6
92.5°	24.7	23.8	22.6	21.4	20.2	19.0	18.1	17.3	16.6	15.8	15.0
95°	48.6	47.7	46.3	44.9	43.6	42.2	41.4	41.1	40.8	40.6	40.2
97.5°	76.8	76.0	74.1	72.2	70.3	68.4	67.3	67.3	67.1	67.0	66.9
100°	96.0	94.7	93.0	91.2	89.4	87.6	86.7	86.7	86.7	86.7	86.7
102.5°	116.0	114.6	113.7	112.8	111.9	111.0	110.3	109.7	109.2	108.6	108.1
105°	148.9	148.1	147.2	146.4	145.6	144.7	144.0	143.3	142.6	142.0	141.2
107.5°	184.3	183.9	183.2	182.6	182.0	181.3	180.7	180.0	179.3	178.6	177.9
110°	208.6	208.1	207.7	207.3	206.9	206.5	206.0	205.3	204.5	203.9	203.2



TEST NUMBER: P333314-927

CATALOG NUMBER: S125DIP-S1270D810U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	233.1	232.9	232.4	231.9	231.3	230.8	230.4	230.0	229.7	229.3	228.9
115°	270.5	270.7	270.5	270.1	269.9	269.6	269.2	268.6	268.1	267.5	267.0
117.5°	307.4	307.4	307.1	306.9	306.7	306.4	306.1	305.9	305.6	305.4	305.1
120°	332.6	332.6	332.5	332.4	332.2	332.1	331.7	331.0	330.3	329.6	328.9
122.5°	357.3	357.4	357.0	356.7	356.3	356.0	355.7	355.5	355.2	355.0	354.7
125°	393.7	394.0	393.8	393.7	393.6	393.4	392.9	392.1	391.3	390.5	389.6
127.5°	429.5	429.7	429.5	429.3	429.1	429.0	428.6	428.2	427.7	427.3	426.8
130°	453.3	453.4	453.1	452.9	452.6	452.3	451.9	451.1	450.5	449.8	449.1
132.5°	476.1	476.3	476.3	476.3	476.4	476.4	475.9	474.8	473.6	472.5	471.4
135°	511.0	511.0	510.9	510.8	510.6	510.5	510.0	509.2	508.3	507.6	506.7
137.5°	545.0	544.9	544.5	544.2	544.0	543.7	543.1	542.3	541.5	540.7	540.0
140°	566.5	566.2	565.8	565.4	564.9	564.5	564.0	563.3	562.6	561.9	561.3
142.5°	587.6	587.5	586.9	586.5	585.9	585.4	584.9	584.2	583.7	583.1	582.6
145°	618.2	618.2	617.8	617.3	617.0	616.6	616.1	615.5	615.0	614.4	613.9
147.5°	646.0	645.7	645.4	645.1	644.8	644.4	644.0	643.8	643.5	643.2	642.9
150°	664.1	664.1	663.5	663.0	662.4	661.9	661.6	661.8	661.9	662.0	662.2
152.5°	680.2	679.9	679.7	679.5	679.2	679.1	678.8	678.7	678.4	678.3	678.0
155°	703.6	703.1	702.9	702.8	702.7	702.5	702.4	702.4	702.4	702.4	702.4
157.5°	724.1	723.5	723.3	723.3	723.1	722.9	723.0	723.3	723.7	724.0	724.3
160°	736.5	735.9	735.8	735.6	735.5	735.4	735.5	735.9	736.3	736.7	737.1
162.5°	748.0	747.3	747.3	747.3	747.2	747.2	747.3	747.7	747.9	748.2	748.5
165°	763.7	763.2	763.0	762.9	762.7	762.6	762.7	763.0	763.3	763.5	763.8
167.5°	775.0	774.2	774.2	774.2	774.2	774.2	774.4	775.0	775.5	776.1	776.7
170°	782.0	781.1	781.1	781.1	781.1	781.1	781.4	782.0	782.5	783.1	783.6
172.5°	786.9	786.1	786.1	786.1	786.1	786.1	786.3	786.9	787.4	788.0	788.5
175°	792.5	791.6	791.6	791.6	791.6	791.6	791.9	792.5	793.1	793.6	794.2
177.5°	795.2	794.5	794.6	794.7	794.9	795.0	795.2	795.7	796.1	796.5	797.0
180°	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0



TEST NUMBER: P333314-927

CATALOG NUMBER: S125DIP-S1270D810U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1454.9	1454.9	1454.9	1454.9	1454.9	1454.9	1454.9	1454.9	1454.9	1454.9	1454.9
2.5°	1462.8	1469.7	1474.2	1482.6	1489.5	1493.4	1496.9	1499.8	1503.3	1506.3	1514.7
5°	1472.2	1488.2	1501.8	1522.8	1542.0	1556.8	1572.8	1587.1	1598.8	1615.4	1628.4
7.5°	1468.1	1496.6	1526.5	1559.0	1592.2	1623.1	1651.5	1678.1	1702.2	1731.3	1756.8
10°	1464.1	1503.1	1541.3	1585.2	1630.2	1668.6	1704.4	1740.8	1767.4	1804.4	1835.9
12.5°	1461.2	1507.0	1553.2	1605.9	1655.4	1709.5	1757.2	1783.8	1824.2	1853.8	1891.3
15°	1448.7	1509.3	1572.8	1632.1	1702.5	1752.5	1794.5	1846.4	1884.0	1921.8	1962.5
17.5°	1426.3	1494.9	1566.1	1643.7	1711.3	1765.0	1819.1	1869.2	1914.1	1964.6	2015.3
20°	1415.9	1484.5	1566.1	1645.7	1711.7	1768.0	1823.5	1878.5	1927.9	1992.7	2051.4
22.5°	1394.2	1477.1	1552.2	1629.9	1698.0	1759.0	1822.1	1884.4	1950.1	2023.4	2096.8
25°	1355.5	1439.5	1519.1	1595.7	1664.2	1740.8	1808.1	1891.5	1975.5	2072.4	2163.8
27.5°	1315.2	1395.6	1468.6	1542.5	1622.5	1709.2	1796.5	1891.1	2001.1	2123.4	2252.3
30°	1282.6	1358.5	1429.6	1505.5	1588.9	1686.5	1782.2	1894.6	2021.8	2159.5	2312.6
32.5°	1244.5	1314.5	1383.6	1464.0	1554.8	1657.8	1769.3	1892.6	2045.5	2201.9	2359.6
35°	1179.5	1238.1	1309.2	1395.0	1497.5	1615.4	1744.5	1890.2	2065.6	2245.3	2378.1
37.5°	1102.2	1156.9	1231.7	1325.8	1433.3	1559.9	1713.0	1885.9	2072.2	2215.4	2258.3
40°	1050.4	1101.1	1178.8	1276.4	1386.3	1520.4	1688.3	1871.1	2051.4	2142.8	2107.6
42.5°	995.1	1048.2	1124.0	1220.6	1338.9	1484.8	1657.2	1840.0	1991.2	2025.7	1904.1
45°	907.8	962.7	1037.4	1135.0	1262.2	1420.3	1600.0	1766.1	1853.2	1790.8	1602.5
47.5°	826.6	878.1	947.4	1048.1	1179.3	1342.8	1515.9	1648.5	1655.3	1506.5	1305.4
50°	771.3	818.8	888.6	989.3	1119.6	1285.1	1441.3	1545.6	1498.7	1330.2	1136.9
52.5°	716.9	763.5	832.3	932.0	1060.8	1212.4	1357.8	1431.1	1342.6	1169.6	1004.5
55°	638.5	679.3	746.6	838.6	960.8	1101.7	1225.2	1250.5	1135.6	965.2	831.2
57.5°	562.0	600.0	661.2	746.0	857.8	982.5	1079.0	1073.6	952.2	806.0	699.7
60°	510.1	547.2	601.5	684.2	786.1	893.6	976.3	956.6	836.1	710.2	620.6
62.5°	463.7	496.7	548.1	620.5	713.5	813.0	881.0	851.8	733.9	623.7	552.9
65°	395.2	423.0	466.8	528.6	605.8	687.9	740.4	702.7	602.1	516.3	459.5
67.5°	329.9	352.1	388.9	438.2	504.0	570.0	602.0	564.0	483.5	420.9	378.8
70°	288.4	308.2	336.5	380.4	437.8	493.4	517.5	483.5	414.4	360.6	330.3
72.5°	246.9	263.2	288.1	327.6	373.6	421.8	442.9	410.4	353.6	308.2	280.0
75°	190.8	201.9	219.2	246.4	282.8	321.2	332.9	304.4	268.0	234.0	215.6
77.5°	136.6	146.0	159.1	176.3	202.1	226.4	236.6	220.2	192.0	170.6	155.3
80°	105.0	110.0	121.0	135.2	155.6	171.0	177.8	167.4	147.6	131.5	119.8
82.5°	74.9	79.8	86.4	98.2	111.1	121.7	129.0	121.9	107.6	95.0	88.2
85°	36.4	39.5	43.3	48.2	58.1	64.2	63.6	59.3	53.7	48.8	45.1
87.5°	13.2	13.9	15.6	18.3	20.0	22.2	23.4	22.6	20.8	19.4	18.1
90°	1.7	2.9	4.0	5.0	6.0	7.1	8.0	9.0	9.9	10.6	11.2
92.5°	15.8	16.6	17.3	18.1	19.0	20.2	21.4	22.6	23.8	24.7	25.6
95°	40.6	40.8	41.1	41.4	42.2	43.6	44.9	46.3	47.7	48.6	49.6
97.5°	67.0	67.1	67.3	67.3	68.4	70.3	72.2	74.1	76.0	76.8	77.8
100°	86.7	86.7	86.7	86.7	87.6	89.4	91.2	93.0	94.7	96.0	97.3
102.5°	108.6	109.2	109.7	110.3	111.0	111.9	112.8	113.7	114.6	116.0	117.3
105°	142.0	142.6	143.3	144.0	144.7	145.6	146.4	147.2	148.1	148.9	149.7
107.5°	178.6	179.3	180.0	180.7	181.3	182.0	182.6	183.2	183.9	184.3	184.7
110°	203.9	204.5	205.3	206.0	206.5	206.9	207.3	207.7	208.1	208.6	209.0



TEST NUMBER: P333314-927

CATALOG NUMBER: S125DIP-S1270D810U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	229.3	229.7	230.0	230.4	230.8	231.3	231.9	232.4	232.9	233.1	233.3
115°	267.5	268.1	268.6	269.2	269.6	269.9	270.1	270.5	270.7	270.5	270.5
117.5°	305.4	305.6	305.9	306.1	306.4	306.7	306.9	307.1	307.4	307.4	307.6
120°	329.6	330.3	331.0	331.7	332.1	332.2	332.4	332.5	332.6	332.6	332.6
122.5°	355.0	355.2	355.5	355.7	356.0	356.3	356.7	357.0	357.4	357.3	357.2
125°	390.5	391.3	392.1	392.9	393.4	393.6	393.7	393.8	394.0	393.7	393.4
127.5°	427.3	427.7	428.2	428.6	429.0	429.1	429.3	429.5	429.7	429.5	429.4
130°	449.8	450.5	451.1	451.9	452.3	452.6	452.9	453.1	453.4	453.3	453.1
132.5°	472.5	473.6	474.8	475.9	476.4	476.4	476.3	476.3	476.3	476.1	475.9
135°	507.6	508.3	509.2	510.0	510.5	510.6	510.8	510.9	511.0	511.0	511.0
137.5°	540.7	541.5	542.3	543.1	543.7	544.0	544.2	544.5	544.9	545.0	545.2
140°	561.9	562.6	563.3	564.0	564.5	564.9	565.4	565.8	566.2	566.5	566.7
142.5°	583.1	583.7	584.2	584.9	585.4	585.9	586.5	586.9	587.5	587.6	587.8
145°	614.4	615.0	615.5	616.1	616.6	617.0	617.3	617.8	618.2	618.2	618.2
147.5°	643.2	643.5	643.8	644.0	644.4	644.8	645.1	645.4	645.7	646.0	646.3
150°	662.0	661.9	661.8	661.6	661.9	662.4	663.0	663.5	664.1	664.1	664.1
152.5°	678.3	678.4	678.7	678.8	679.1	679.2	679.5	679.7	679.9	680.2	680.6
155°	702.4	702.4	702.4	702.4	702.5	702.7	702.8	702.9	703.1	703.6	704.2
157.5°	724.0	723.7	723.3	723.0	722.9	723.1	723.3	723.3	723.5	724.1	724.6
160°	736.7	736.3	735.9	735.5	735.4	735.5	735.6	735.8	735.9	736.5	737.0
162.5°	748.2	747.9	747.7	747.3	747.2	747.2	747.3	747.3	747.3	748.0	748.6
165°	763.5	763.3	763.0	762.7	762.6	762.7	762.9	763.0	763.2	763.7	764.3
167.5°	776.1	775.5	775.0	774.4	774.2	774.2	774.2	774.2	774.2	775.0	775.9
170°	783.1	782.5	782.0	781.4	781.1	781.1	781.1	781.1	781.1	782.0	782.8
172.5°	788.0	787.4	786.9	786.3	786.1	786.1	786.1	786.1	786.1	786.9	787.7
175°	793.6	793.1	792.5	791.9	791.6	791.6	791.6	791.6	791.6	792.5	793.3
177.5°	796.5	796.1	795.7	795.2	795.0	794.9	794.7	794.6	794.5	795.2	795.8
180°	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0



TEST NUMBER: P333314-927

CATALOG NUMBER: S125DIP-S1270D810U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1454.9	1454.9	1454.9	1454.9	1454.9	1454.9	1454.9
2.5°	1521.5	1525.5	1533.9	1531.0	1534.9	1536.9	1538.9
5°	1644.5	1664.2	1672.9	1671.7	1684.6	1681.5	1678.4
7.5°	1783.3	1804.0	1815.7	1830.1	1838.5	1839.1	1846.4
10°	1861.9	1889.0	1900.1	1915.6	1925.5	1931.0	1930.4
12.5°	1922.1	1943.4	1968.3	1975.9	1989.2	1996.2	1993.6
15°	1994.6	2028.5	2054.5	2067.4	2084.2	2089.1	2095.9
17.5°	2059.4	2104.9	2135.2	2175.4	2190.6	2199.9	2194.4
20°	2108.2	2168.1	2198.4	2246.5	2273.1	2287.3	2282.4
22.5°	2166.1	2230.9	2286.8	2328.5	2368.9	2388.1	2392.1
25°	2265.1	2354.0	2436.1	2491.1	2541.1	2552.8	2578.8
27.5°	2375.8	2480.6	2568.4	2626.2	2661.0	2674.1	2682.3
30°	2445.4	2549.7	2615.9	2652.9	2664.0	2662.8	2661.5
32.5°	2479.5	2544.8	2557.6	2547.2	2521.8	2500.2	2477.8
35°	2431.2	2382.4	2309.5	2215.7	2146.5	2076.7	2070.0
37.5°	2186.5	2030.5	1909.2	1773.8	1695.6	1647.3	1614.0
40°	1956.3	1779.1	1632.1	1517.9	1438.2	1406.8	1375.9
42.5°	1706.4	1537.0	1406.8	1311.4	1251.5	1216.6	1192.1
45°	1386.3	1236.9	1135.0	1065.9	1018.3	991.1	975.7
47.5°	1136.0	1025.5	938.9	889.0	856.1	835.0	835.1
50°	1001.6	896.0	838.6	799.1	770.6	754.0	757.1
52.5°	882.6	803.7	754.6	721.5	700.5	690.2	689.9
55°	737.9	681.1	649.0	625.0	610.7	599.0	601.5
57.5°	631.2	583.3	561.8	541.9	532.0	527.3	520.5
60°	565.1	528.0	509.5	493.4	483.5	479.8	473.0
62.5°	506.3	477.1	459.1	446.0	437.0	435.9	430.6
65°	425.5	403.2	387.2	381.0	371.8	369.3	369.3
67.5°	350.8	334.9	322.3	316.6	312.6	313.2	310.2
70°	303.8	290.9	282.8	276.6	273.5	274.2	271.7
72.5°	265.8	251.4	244.3	240.6	236.5	238.1	237.1
75°	201.3	193.9	190.2	186.5	184.0	182.8	181.6
77.5°	147.8	141.3	138.5	136.3	136.7	133.7	136.1
80°	114.2	108.7	106.9	103.8	103.1	103.1	102.5
82.5°	83.6	80.5	79.1	76.6	75.5	76.4	74.9
85°	43.3	40.7	40.2	40.2	38.9	37.7	40.7
87.5°	18.2	16.4	16.5	16.1	16.2	15.8	14.8
90°	12.0	12.7	13.2	13.6	14.0	14.4	14.9
92.5°	26.5	27.4	28.0	28.4	28.6	28.9	29.2
95°	50.6	51.6	52.2	52.4	52.8	53.0	53.2
97.5°	78.7	79.6	80.1	80.2	80.4	80.6	80.8
100°	98.5	99.7	100.5	100.8	101.0	101.3	101.6
102.5°	118.7	120.0	120.9	121.3	121.6	122.0	122.4
105°	150.5	151.4	151.9	152.4	152.8	153.2	153.6
107.5°	185.1	185.5	185.7	185.7	185.6	185.6	185.6
110°	209.4	209.8	209.9	209.8	209.6	209.5	209.4



TEST NUMBER: P333314-927

CATALOG NUMBER: S125DIP-S1270D810U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	233.5	233.7	233.7	233.4	233.1	232.9	232.7
115°	270.3	270.1	270.0	269.9	269.7	269.6	269.5
117.5°	307.7	307.8	307.6	307.0	306.5	305.9	305.4
120°	332.6	332.6	332.4	331.8	331.3	330.7	330.2
122.5°	357.1	357.0	356.7	356.2	355.8	355.4	355.0
125°	393.2	392.8	392.7	392.5	392.4	392.3	392.1
127.5°	429.2	429.1	428.9	428.6	428.3	428.1	427.8
130°	453.0	452.9	452.7	452.4	452.1	451.9	451.5
132.5°	475.8	475.7	475.4	475.1	474.7	474.3	473.9
135°	511.0	511.0	510.8	510.2	509.7	509.1	508.6
137.5°	545.3	545.5	545.3	544.5	543.9	543.2	542.5
140°	567.0	567.3	567.0	566.4	565.7	565.0	564.4
142.5°	588.0	588.1	587.9	587.2	586.5	585.8	585.1
145°	618.2	618.2	618.0	617.6	617.2	616.8	616.3
147.5°	646.7	647.1	646.7	645.8	644.8	644.0	643.0
150°	664.1	664.1	663.9	663.6	663.4	663.1	662.8
152.5°	680.9	681.2	681.1	680.6	680.2	679.7	679.1
155°	704.7	705.3	705.2	704.5	703.9	703.1	702.4
157.5°	725.2	725.7	725.6	724.6	723.7	722.8	721.9
160°	737.5	738.1	738.1	737.4	736.7	735.9	735.3
162.5°	749.3	750.0	749.9	749.1	748.3	747.5	746.7
165°	764.9	765.3	765.2	764.4	763.6	762.7	761.9
167.5°	776.7	777.5	777.4	776.7	775.8	774.9	774.0
170°	783.6	784.4	784.3	783.4	782.4	781.5	780.5
172.5°	788.5	789.4	789.4	788.5	787.7	786.8	785.9
175°	794.2	795.0	794.9	793.9	793.0	792.0	791.1
177.5°	796.5	797.2	797.1	796.3	795.6	794.8	794.0
180°	796.0	796.0	796.0	796.0	796.0	796.0	796.0

(END OF REPORT)