

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332713

Luminaire Tested: **S124DIP-S1195D1205U835-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332713  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124DIP-S1195D1205U835-4F0-1E-UDD-F1  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1205 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 9286.1 lumens  
Efficiency: N/A  
Efficacy: 129.5 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 71.7  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332713

CATALOG NUMBER: S124DIP-S1195D1205U835-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332713

CATALOG NUMBER: S124DIP-S1195D1205U835-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	55
1	99	94	91	87	92	88	84	81	76	73	71	64	62	61	54	52	51	46
2	90	83	76	71	83	77	71	67	66	62	59	56	53	51	47	45	43	39
3	82	73	65	59	76	68	61	56	58	53	49	50	46	43	42	39	37	33
4	75	64	56	50	69	60	53	47	52	46	42	44	40	37	37	34	32	28
5	69	57	49	43	64	54	46	41	46	41	36	40	35	32	34	30	28	24
6	64	51	43	37	59	48	41	35	42	36	32	36	31	28	31	27	24	21
7	59	46	38	33	54	44	36	31	38	32	28	33	28	25	28	24	22	19
8	55	42	34	29	51	40	33	28	35	29	25	30	25	22	26	22	19	17
9	51	39	31	26	47	36	29	25	32	26	22	28	23	20	24	20	18	15
10	48	35	28	23	44	33	27	22	29	24	20	26	21	18	22	18	16	14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	16088	16088	16088
5°	16136	15943	16058
10°	16035	15813	15891
15°	15841	15588	15628
20°	15584	15309	15323
25°	15291	14991	14949
30°	14930	14618	14483
35°	14557	14226	14038
40°	14169	13782	13529
45°	13764	13345	13089
50°	13317	12955	12554
55°	12833	12451	12047
60°	12350	11885	11525
65°	11805	11347	10890
70°	11195	10629	10213
75°	10259	9763	9513
80°	9131	8759	8536
85°	7984	7688	7540



TEST NUMBER: P332713

CATALOG NUMBER: S124DIP-S1195D1205U835-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	187.7	2.0
10°-20°	528.8	5.7
20°-30°	778.3	8.4
30°-40°	904.8	9.7
40°-50°	904.8	9.7
50°-60°	791.5	8.5
60°-70°	587.8	6.3
70°-80°	333.9	3.6
80°-90°	100.9	1.1
90°-100°	99.1	1.1
100°-110°	293.5	3.2
110°-120°	498.2	5.4
120°-130°	656.9	7.1
130°-140°	737.7	7.9
140°-150°	724.9	7.8
150°-160°	609.7	6.6
160°-170°	405.7	4.4
170°-180°	142.1	1.5
0°-30°	1494.7	16.1
0°-40°	2399.5	25.8
0°-60°	4095.8	44.1
0°-90°	5118.4	55.1
90°-120°	890.8	9.6
90°-150°	3010.3	32.4
90°-180°	4168.0	44.9
0°-180°	9286.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1993	1993	1993	1993	1993	
5°	1991	1984	1967	1984	1982	189
15°	1895	1888	1865	1874	1870	534
25°	1717	1705	1683	1684	1678	789
35°	1477	1465	1444	1433	1424	923
45°	1206	1194	1169	1152	1146	929
55°	912	906	885	866	856	816
65°	618	610	594	578	570	612
75°	329	321	313	307	305	350
85°	86	86	83	83	81	95
90°	4	16	26	32	35	9
95°	70	80	88	92	92	78
105°	271	272	276	280	284	287
115°	506	506	504	503	502	499
125°	738	738	737	734	732	657
135°	952	958	958	956	953	736
145°	1156	1160	1162	1160	1157	723
155°	1324	1324	1323	1327	1323	609
165°	1442	1438	1436	1442	1438	406
175°	1500	1494	1493	1500	1493	142
180°	1502	1502	1502	1502	1502	



TEST NUMBER: P332713

CATALOG NUMBER: S124DIP-S1195D1205U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8
2.5°	1997.9	1997.1	1996.2	1995.4	1994.5	1992.5	1989.4	1986.3	1983.2	1980.1	1982.9
5°	1991.2	1989.8	1988.4	1987.0	1985.6	1982.9	1979.0	1975.1	1971.2	1967.3	1971.2
7.5°	1972.7	1971.3	1969.9	1968.4	1967.0	1964.2	1959.8	1955.5	1951.2	1946.8	1950.0
10°	1956.1	1954.7	1953.3	1951.8	1950.4	1947.4	1942.8	1938.2	1933.6	1929.0	1931.8
12.5°	1934.4	1933.0	1931.5	1930.1	1928.7	1925.5	1920.7	1915.8	1910.9	1906.0	1909.1
15°	1895.4	1894.0	1892.6	1891.2	1889.7	1886.4	1881.0	1875.7	1870.4	1865.1	1867.2
17.5°	1848.5	1846.7	1844.9	1843.2	1841.4	1838.0	1832.9	1827.9	1822.9	1817.8	1819.2
20°	1814.0	1812.2	1810.4	1808.7	1806.9	1803.3	1798.0	1792.7	1787.4	1782.0	1783.1
22.5°	1776.9	1774.6	1772.3	1769.9	1767.6	1763.7	1758.4	1753.1	1747.8	1742.4	1744.4
25°	1716.6	1714.1	1711.6	1709.1	1706.6	1702.9	1697.9	1693.0	1688.0	1683.0	1683.4
27.5°	1647.6	1645.0	1642.5	1639.9	1637.4	1633.8	1629.2	1624.6	1620.0	1615.3	1614.5
30°	1601.6	1598.8	1595.9	1593.1	1590.3	1586.5	1581.9	1577.3	1572.7	1568.1	1566.7
32.5°	1553.1	1550.5	1548.0	1545.4	1542.8	1539.1	1534.2	1529.3	1524.4	1519.5	1517.8
35°	1477.1	1474.6	1472.1	1469.6	1467.1	1463.4	1458.4	1453.5	1448.5	1443.5	1441.0
37.5°	1396.9	1394.6	1392.4	1390.1	1387.8	1384.0	1378.7	1373.4	1368.0	1362.7	1360.0
40°	1344.5	1341.7	1338.8	1336.0	1333.2	1329.1	1323.8	1318.4	1313.1	1307.8	1304.2
42.5°	1288.3	1286.6	1284.9	1283.2	1281.5	1277.7	1271.8	1265.9	1260.0	1254.1	1250.0
45°	1205.6	1203.1	1200.6	1198.1	1195.7	1191.6	1185.9	1180.2	1174.5	1168.9	1165.0
47.5°	1119.0	1117.3	1115.6	1113.9	1112.2	1108.8	1103.5	1098.3	1093.0	1087.8	1083.4
50°	1060.3	1058.9	1057.4	1056.0	1054.6	1051.4	1046.4	1041.5	1036.5	1031.5	1026.6
52.5°	1002.8	1001.1	999.4	997.7	996.0	992.5	987.3	982.0	976.8	971.5	967.1
55°	911.8	910.7	909.7	908.6	907.5	904.5	899.5	894.6	889.6	884.6	880.4
57.5°	824.9	823.7	822.5	821.3	820.1	817.0	812.1	807.2	802.3	797.4	793.4
60°	764.9	763.1	761.3	759.6	757.8	754.6	750.0	745.4	740.7	736.1	732.9
62.5°	706.1	704.6	703.1	701.6	700.2	697.0	692.1	687.2	682.3	677.4	674.5
65°	618.0	616.2	614.4	612.6	610.9	608.2	604.7	601.1	597.6	594.0	590.5
67.5°	529.2	527.6	525.9	524.3	522.7	520.1	516.7	513.3	509.9	506.5	503.1
70°	474.3	471.8	469.3	466.8	464.3	461.7	458.8	456.0	453.1	450.3	447.5
72.5°	415.5	413.0	410.5	408.0	405.6	403.2	400.9	398.6	396.4	394.1	391.8
75°	328.9	327.2	325.4	323.6	321.8	320.1	318.3	316.5	314.8	313.0	311.6
77.5°	246.2	245.4	244.7	243.9	243.1	241.9	240.4	238.8	237.3	235.7	235.3
80°	196.4	195.3	194.3	193.2	192.2	191.3	190.6	189.8	189.1	188.4	187.7
82.5°	147.9	147.4	146.9	146.4	145.9	145.6	145.4	145.3	145.1	145.0	144.6
85°	86.2	86.2	86.2	86.2	86.2	85.9	85.2	84.5	83.7	83.0	83.0
87.5°	33.9	34.2	34.5	34.8	35.0	35.3	35.4	35.5	35.6	35.8	36.1
90°	3.5	6.3	9.2	12.0	14.8	17.3	19.4	21.4	23.5	25.6	27.1
92.5°	24.9	28.1	31.4	34.6	37.9	40.2	41.7	43.1	44.6	46.0	46.9
95°	69.7	72.0	74.4	76.7	79.0	81.1	82.9	84.7	86.5	88.3	89.1
97.5°	121.8	123.6	125.5	127.3	129.2	131.2	133.3	135.4	137.5	139.6	140.6
100°	162.7	163.7	164.7	165.7	166.8	168.5	170.8	173.1	175.4	177.8	178.3
102.5°	205.4	205.8	206.2	206.6	207.1	208.3	210.4	212.6	214.7	216.8	217.5
105°	270.7	271.0	271.2	271.5	271.7	272.4	273.4	274.4	275.5	276.5	277.3
107.5°	339.2	339.6	339.9	340.2	340.5	340.7	340.9	341.0	341.2	341.3	342.1
110°	385.7	386.2	386.7	387.3	387.8	387.9	387.7	387.4	387.1	386.9	386.4



TEST NUMBER: P332713

CATALOG NUMBER: S124DIP-S1195D1205U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	434.0	434.2	434.3	434.4	434.5	434.3	433.8	433.4	432.9	432.4	432.3
115°	506.5	506.5	506.5	506.5	506.5	506.3	505.8	505.3	504.7	504.2	504.0
117.5°	574.9	575.1	575.3	575.5	575.7	575.6	575.2	574.9	574.5	574.2	573.3
120°	620.4	621.4	622.5	623.5	624.5	624.7	623.9	623.1	622.3	621.6	620.3
122.5°	667.8	668.2	668.6	669.0	669.5	669.5	669.1	668.8	668.4	668.0	667.2
125°	737.7	737.7	737.7	737.7	737.7	737.6	737.4	737.1	736.8	736.6	736.1
127.5°	801.2	802.0	802.7	803.5	804.3	804.5	804.0	803.6	803.2	802.8	802.3
130°	845.8	846.6	847.3	848.1	848.9	849.3	849.3	849.3	849.3	849.3	848.8
132.5°	891.3	891.9	892.5	893.0	893.6	893.8	893.6	893.4	893.2	893.0	892.4
135°	951.5	953.1	954.6	956.2	957.7	958.5	958.5	958.5	958.5	958.5	958.0
137.5°	1017.0	1017.8	1018.5	1019.2	1019.9	1020.5	1020.9	1021.3	1021.7	1022.1	1021.5
140°	1060.7	1061.2	1061.8	1062.3	1062.8	1063.0	1063.0	1063.0	1063.0	1063.0	1062.8
142.5°	1100.7	1101.2	1101.7	1102.2	1102.8	1102.9	1102.7	1102.5	1102.3	1102.1	1102.0
145°	1156.0	1157.0	1158.1	1159.1	1160.1	1160.8	1161.0	1161.3	1161.5	1161.8	1161.5
147.5°	1210.8	1212.1	1213.3	1214.5	1215.8	1216.3	1216.1	1215.9	1215.7	1215.5	1215.3
150°	1244.3	1245.3	1246.4	1247.4	1248.4	1248.9	1248.9	1248.9	1248.9	1248.9	1248.9
152.5°	1275.9	1276.5	1277.1	1277.7	1278.4	1278.8	1279.0	1279.2	1279.4	1279.6	1280.2
155°	1324.4	1324.4	1324.4	1324.4	1324.4	1324.3	1324.1	1323.8	1323.5	1323.3	1324.3
157.5°	1365.3	1364.9	1364.4	1364.0	1363.5	1363.2	1363.2	1363.1	1363.1	1363.0	1363.8
160°	1389.5	1389.3	1389.0	1388.7	1388.5	1388.2	1388.0	1387.7	1387.4	1387.2	1388.0
162.5°	1411.8	1411.1	1410.5	1409.8	1409.1	1408.7	1408.4	1408.2	1407.9	1407.6	1409.0
165°	1441.8	1441.0	1440.2	1439.5	1438.7	1438.0	1437.5	1437.0	1436.5	1436.0	1437.5
167.5°	1464.8	1463.7	1462.6	1461.5	1460.5	1459.9	1460.0	1460.0	1460.1	1460.1	1461.7
170°	1477.8	1476.5	1475.2	1473.9	1472.6	1472.1	1472.4	1472.6	1472.9	1473.2	1474.7
172.5°	1487.1	1486.0	1484.9	1483.8	1482.8	1482.2	1482.3	1482.4	1482.4	1482.5	1484.2
175°	1499.9	1498.6	1497.3	1496.0	1494.7	1493.9	1493.7	1493.4	1493.2	1492.9	1494.7
177.5°	1504.1	1503.0	1502.0	1501.0	1499.9	1499.4	1499.4	1499.4	1499.4	1499.4	1500.9
180°	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2



TEST NUMBER: P332713

CATALOG NUMBER: S124DIP-S1195D1205U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8
2.5°	1985.7	1988.6	1991.4	1992.7	1992.4	1992.1	1991.8	1991.5
5°	1975.1	1979.0	1982.9	1984.5	1983.8	1983.1	1982.4	1981.6
7.5°	1953.1	1956.2	1959.3	1960.7	1960.3	1959.8	1959.4	1959.0
10°	1934.6	1937.5	1940.3	1941.4	1940.7	1940.0	1939.2	1938.5
12.5°	1912.2	1915.3	1918.5	1919.5	1918.5	1917.5	1916.5	1915.5
15°	1869.3	1871.5	1873.6	1874.1	1873.1	1872.0	1870.9	1869.9
17.5°	1820.5	1821.9	1823.2	1823.5	1822.8	1822.1	1821.4	1820.7
20°	1784.2	1785.2	1786.3	1786.5	1785.8	1785.1	1784.4	1783.6
22.5°	1746.3	1748.2	1750.1	1750.4	1749.2	1747.9	1746.6	1745.3
25°	1683.8	1684.1	1684.5	1683.9	1682.5	1681.1	1679.7	1678.3
27.5°	1613.6	1612.8	1611.9	1610.6	1608.8	1607.1	1605.3	1603.5
30°	1565.2	1563.8	1562.4	1560.8	1559.0	1557.3	1555.5	1553.7
32.5°	1516.1	1514.4	1512.7	1511.0	1509.2	1507.4	1505.7	1503.9
35°	1438.6	1436.1	1433.6	1431.5	1429.7	1427.9	1426.1	1424.4
37.5°	1357.3	1354.6	1351.9	1349.4	1347.1	1344.7	1342.4	1340.0
40°	1300.7	1297.1	1293.6	1290.9	1289.2	1287.4	1285.6	1283.8
42.5°	1245.9	1241.8	1237.7	1235.0	1233.8	1232.6	1231.4	1230.2
45°	1161.1	1157.2	1153.3	1150.8	1149.7	1148.6	1147.6	1146.5
47.5°	1079.0	1074.6	1070.2	1066.6	1063.9	1061.2	1058.5	1055.8
50°	1021.6	1016.6	1011.7	1008.1	1006.0	1003.9	1001.7	999.6
52.5°	962.7	958.3	953.9	950.4	947.7	945.0	942.3	939.6
55°	876.1	871.9	867.6	864.4	862.3	860.2	858.0	855.9
57.5°	789.4	785.3	781.3	778.2	776.2	774.1	772.0	770.0
60°	729.7	726.6	723.4	720.9	719.1	717.3	715.6	713.8
62.5°	671.5	668.6	665.7	663.4	661.6	659.8	658.1	656.3
65°	586.9	583.4	579.8	577.2	575.4	573.6	571.8	570.1
67.5°	499.7	496.3	492.9	490.9	490.4	489.9	489.4	488.9
70°	444.6	441.8	438.9	437.0	435.9	434.9	433.8	432.7
72.5°	389.6	387.3	385.0	383.3	382.3	381.2	380.1	379.1
75°	310.1	308.7	307.3	306.4	306.1	305.7	305.3	305.0
77.5°	234.8	234.4	234.0	233.3	232.4	231.5	230.5	229.6
80°	187.0	186.3	185.6	185.1	184.7	184.3	184.0	183.6
82.5°	144.1	143.7	143.3	142.9	142.5	142.2	141.8	141.5
85°	83.0	83.0	83.0	82.9	82.5	82.1	81.8	81.4
87.5°	36.4	36.7	37.0	37.2	37.3	37.4	37.5	37.6
90°	28.7	30.2	31.8	32.8	33.3	33.8	34.3	34.9
92.5°	47.9	48.8	49.7	50.3	50.7	51.0	51.3	51.6
95°	89.8	90.6	91.4	91.8	91.8	91.8	91.8	91.8
97.5°	141.5	142.4	143.4	143.8	143.8	143.8	143.8	143.8
100°	178.8	179.3	179.8	180.1	180.1	180.1	180.1	180.1
102.5°	218.2	219.0	219.7	220.1	220.4	220.6	220.8	221.0
105°	278.1	278.8	279.6	280.4	281.2	281.9	282.7	283.5
107.5°	342.8	343.5	344.2	344.6	344.5	344.5	344.4	344.4
110°	385.8	385.3	384.8	384.9	385.7	386.5	387.3	388.0





TEST NUMBER: P332713

CATALOG NUMBER: S124DIP-S1195D1205U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	432.2	432.1	432.0	432.0	432.2	432.3	432.5	432.7
115°	503.7	503.4	503.2	502.9	502.7	502.4	502.2	501.9
117.5°	572.4	571.5	570.6	570.0	569.4	568.9	568.4	567.9
120°	619.0	617.7	616.4	616.0	616.5	617.0	617.6	618.1
122.5°	666.3	665.4	664.5	663.6	662.7	661.8	660.8	659.9
125°	735.5	735.0	734.5	734.0	733.5	733.0	732.4	731.9
127.5°	801.8	801.3	800.7	800.3	799.9	799.4	799.0	798.6
130°	848.2	847.7	847.2	846.4	845.4	844.4	843.3	842.3
132.5°	891.9	891.4	890.9	890.4	890.0	889.6	889.2	888.8
135°	957.5	956.9	956.4	955.8	955.0	954.2	953.4	952.7
137.5°	1020.8	1020.1	1019.5	1019.2	1019.4	1019.5	1019.7	1019.8
140°	1062.5	1062.3	1062.0	1061.8	1061.5	1061.2	1061.0	1060.7
142.5°	1102.0	1101.9	1101.9	1101.8	1101.8	1101.7	1101.7	1101.6
145°	1161.3	1161.0	1160.8	1160.2	1159.5	1158.7	1157.9	1157.2
147.5°	1215.1	1214.9	1214.6	1214.4	1214.2	1213.9	1213.6	1213.4
150°	1248.9	1248.9	1248.9	1248.8	1248.5	1248.3	1248.0	1247.8
152.5°	1280.8	1281.5	1282.1	1282.1	1281.4	1280.7	1280.0	1279.4
155°	1325.4	1326.4	1327.4	1327.4	1326.4	1325.4	1324.3	1323.3
157.5°	1364.6	1365.3	1366.1	1366.1	1365.2	1364.3	1363.4	1362.6
160°	1388.7	1389.5	1390.3	1390.0	1388.7	1387.4	1386.2	1384.9
162.5°	1410.4	1411.8	1413.2	1413.3	1412.0	1410.7	1409.4	1408.1
165°	1439.1	1440.6	1442.2	1442.4	1441.4	1440.4	1439.3	1438.3
167.5°	1463.2	1464.8	1466.3	1466.3	1464.7	1463.1	1461.5	1459.9
170°	1476.3	1477.8	1479.4	1479.2	1477.4	1475.6	1473.8	1472.0
172.5°	1486.0	1487.7	1489.5	1489.5	1487.6	1485.8	1484.0	1482.2
175°	1496.5	1498.3	1500.1	1500.1	1498.3	1496.5	1494.7	1492.9
177.5°	1502.3	1503.8	1505.2	1505.1	1503.4	1501.8	1500.1	1498.5
180°	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2

(END OF REPORT)