

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333159-927

Luminaire Tested: **S125DIP-S375D1205U927-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333159-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIP-S375D1205U927-4F0-1E-UDD-F4  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 375 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1205 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4630.5 lumens  
Efficiency: N/A  
Efficacy: 109.7 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 42.2  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333159-927

CATALOG NUMBER: S125DIP-S375D1205U927-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P333159-927

CATALOG NUMBER: S125DIP-S375D1205U927-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	70	70	70	51	51	51	34	34	34	26
1	92	88	84	81	82	79	76	73	61	59	57	45	44	42	30	29	29	22
2	84	77	71	66	75	69	64	60	54	50	47	39	37	35	26	25	24	18
3	77	68	61	55	68	60	55	50	47	43	40	35	32	30	23	22	20	15
4	70	60	52	46	62	53	47	42	42	37	34	31	28	26	21	19	18	13
5	64	53	45	39	57	48	41	36	37	32	29	28	24	22	19	17	15	12
6	59	47	40	34	52	43	36	31	33	29	25	25	22	19	17	15	13	10
7	54	43	35	30	48	38	32	27	30	25	22	23	19	17	15	13	12	9
8	50	38	31	26	45	35	28	24	27	23	19	21	17	15	14	12	11	8
9	47	35	28	23	42	32	25	21	25	20	17	19	16	13	13	11	10	7
10	44	32	25	20	39	29	23	19	23	18	15	17	14	12	12	10	9	7

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	2989	2989	2989
5°	2995	2967	2986
10°	2977	2946	2963
15°	2945	2910	2923
20°	2899	2861	2866
25°	2849	2802	2799
30°	2788	2738	2725
35°	2722	2670	2633
40°	2655	2596	2559
45°	2582	2528	2478
50°	2502	2446	2372
55°	2423	2354	2288
60°	2331	2260	2180
65°	2222	2149	2077
70°	2115	2019	1949
75°	1926	1864	1799
80°	1715	1689	1648
85°	1489	1519	1438



TEST NUMBER: P333159-927

CATALOG NUMBER: S125DIP-S375D1205U927-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	43.6	0.9
10°-20°	123.3	2.7
20°-30°	182.0	3.9
30°-40°	212.4	4.6
40°-50°	213.3	4.6
50°-60°	187.2	4.0
60°-70°	139.5	3.0
70°-80°	79.8	1.7
80°-90°	25.7	0.6
90°-100°	330.9	7.1
100°-110°	711.4	15.4
110°-120°	667.6	14.4
120°-130°	541.1	11.7
130°-140°	434.2	9.4
140°-150°	327.7	7.1
150°-160°	230.6	5.0
160°-170°	136.0	2.9
170°-180°	44.2	1.0
0°-30°	348.9	7.5
0°-40°	561.2	12.1
0°-60°	961.7	20.8
0°-90°	1206.7	26.1
90°-120°	1710.0	36.9
90°-150°	3013.0	65.1
90°-180°	3424.0	73.9
0°-180°	4630.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	463	463	463	463	463	
5°	462	461	458	461	461	44
15°	440	439	435	437	437	124
25°	400	398	393	394	393	184
35°	345	344	339	337	334	216
45°	283	281	277	273	271	218
55°	215	214	209	206	203	192
65°	145	144	141	137	136	144
75°	77	76	75	74	72	82
85°	20	20	20	20	19	23
90°	1	8	15	19	21	3
95°	30	90	816	370	216	32
105°	104	145	667	1314	1220	110
115°	186	224	536	1155	1359	183
125°	258	302	514	919	1071	229
135°	302	363	510	770	889	234
145°	352	403	512	637	701	220
155°	401	432	499	564	588	185
165°	438	450	479	508	516	123
175°	456	456	459	465	463	43
180°	456	456	456	456	456	



TEST NUMBER: P333159-927

CATALOG NUMBER: S125DIP-S375D1205U927-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8
2.5°	463.9	463.7	463.6	463.3	463.2	462.7	462.1	461.4	460.8	460.1	460.8
5°	462.0	461.8	461.7	461.5	461.4	460.9	460.1	459.3	458.4	457.6	458.4
7.5°	457.8	457.6	457.5	457.3	457.2	456.6	455.7	454.8	453.9	453.0	453.8
10°	454.0	453.8	453.7	453.5	453.4	452.8	451.9	451.0	450.1	449.2	449.9
12.5°	449.3	449.0	448.7	448.5	448.1	447.6	446.7	445.9	445.0	444.3	444.7
15°	440.5	440.2	440.0	439.7	439.4	438.9	438.0	437.1	436.2	435.3	435.7
17.5°	430.2	429.9	429.5	429.2	428.8	428.2	427.2	426.4	425.4	424.5	425.0
20°	421.8	421.6	421.4	421.3	421.1	420.5	419.5	418.4	417.3	416.3	416.8
22.5°	413.3	413.0	412.6	412.4	412.1	411.5	410.4	409.5	408.4	407.5	407.9
25°	399.8	399.4	398.9	398.5	398.2	397.4	396.4	395.3	394.3	393.2	393.4
27.5°	384.0	383.8	383.6	383.3	383.1	382.4	381.4	380.2	379.1	378.0	378.1
30°	373.8	373.6	373.3	373.0	372.8	372.1	370.9	369.6	368.4	367.2	367.0
32.5°	362.7	362.3	361.9	361.6	361.2	360.4	359.3	358.2	357.2	356.1	355.8
35°	345.2	344.9	344.6	344.3	344.0	343.2	342.1	341.0	339.8	338.7	338.3
37.5°	327.2	326.8	326.4	325.9	325.5	324.8	323.7	322.7	321.5	320.5	319.9
40°	314.9	314.4	314.0	313.6	313.2	312.4	311.3	310.2	309.0	307.9	307.2
42.5°	301.7	301.3	301.0	300.6	300.3	299.6	298.4	297.3	296.1	295.0	294.4
45°	282.7	282.3	282.0	281.7	281.3	280.7	279.7	278.8	277.7	276.8	275.8
47.5°	262.1	262.1	262.1	262.2	262.2	261.7	260.5	259.3	258.1	256.9	256.0
50°	249.0	248.7	248.5	248.2	248.0	247.4	246.4	245.4	244.5	243.4	242.4
52.5°	235.5	235.3	235.1	235.0	234.8	234.2	233.1	232.1	231.0	230.0	229.1
55°	215.2	215.0	214.8	214.5	214.3	213.6	212.5	211.4	210.2	209.1	208.3
57.5°	194.0	193.8	193.7	193.6	193.5	192.9	191.9	191.0	190.0	189.1	188.1
60°	180.5	180.1	179.8	179.5	179.2	178.6	177.7	176.8	175.9	175.0	174.2
62.5°	166.4	166.2	165.9	165.6	165.4	164.9	164.1	163.3	162.6	161.8	161.0
65°	145.4	145.2	145.0	144.9	144.7	144.2	143.3	142.4	141.5	140.6	139.8
67.5°	124.9	124.6	124.2	123.9	123.6	123.0	122.4	121.7	121.0	120.4	119.8
70°	112.0	111.6	111.2	110.8	110.4	109.8	109.1	108.4	107.7	106.9	106.4
72.5°	98.0	97.7	97.4	97.1	96.9	96.5	96.0	95.5	95.1	94.6	94.0
75°	77.2	77.1	76.9	76.8	76.6	76.3	75.9	75.5	75.1	74.7	74.5
77.5°	58.1	58.1	58.0	57.9	57.9	57.8	57.5	57.3	57.0	56.8	56.6
80°	46.1	46.1	46.1	46.1	46.1	46.0	45.9	45.7	45.6	45.4	45.3
82.5°	35.6	35.5	35.3	35.2	35.1	35.0	34.9	34.9	34.9	34.9	34.7
85°	20.1	20.2	20.3	20.4	20.4	20.5	20.5	20.5	20.5	20.5	20.4
87.5°	8.1	8.2	8.6	9.0	9.3	9.7	9.8	10.1	10.2	10.5	10.8
90°	1.0	1.8	3.6	5.5	7.4	9.2	10.1	12.0	12.9	14.7	15.7
92.5°	11.2	13.6	21.4	32.8	48.6	75.5	125.7	210.1	301.6	296.8	240.3
95°	30.3	31.3	38.7	48.8	69.0	110.4	209.0	411.5	665.5	815.6	798.0
97.5°	50.5	51.6	56.7	66.9	85.1	114.9	180.1	328.4	594.3	870.9	1009.8
100°	64.4	66.3	69.9	80.1	97.6	125.2	178.6	298.3	530.2	831.2	1061.3
102.5°	79.9	81.0	84.0	94.8	110.8	137.7	185.2	285.7	481.6	761.2	1030.4
105°	104.0	104.0	108.6	117.8	132.5	158.4	198.8	280.7	434.4	667.3	931.5
107.5°	127.5	129.4	133.8	141.4	156.7	179.8	219.0	289.2	414.5	602.7	830.7
110°	144.5	146.4	150.0	158.4	172.1	196.1	233.8	297.3	408.7	572.5	773.2



TEST NUMBER: P333159-927

CATALOG NUMBER: S125DIP-S375D1205U927-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	161.4	163.3	166.2	174.5	188.3	211.5	247.8	307.6	408.7	554.8	730.5
115°	185.9	187.7	190.5	198.8	212.6	235.7	269.7	323.1	411.5	535.8	683.9
117.5°	208.0	210.8	213.7	222.0	237.7	259.9	292.2	340.8	417.6	526.3	656.1
120°	222.8	225.5	229.2	237.5	253.1	276.2	308.4	352.5	423.4	521.9	640.6
122.5°	238.2	240.3	243.2	251.4	268.6	291.6	323.8	365.8	428.6	518.2	627.4
125°	257.7	259.6	264.2	272.4	289.9	313.9	344.3	383.8	437.2	513.7	609.3
127.5°	273.0	275.8	281.7	292.2	310.8	334.7	363.9	400.4	446.9	511.4	592.8
130°	282.6	285.3	292.7	304.7	324.0	347.9	376.4	411.5	452.9	509.9	581.8
132.5°	289.9	293.4	302.3	315.8	335.8	359.7	388.2	421.0	459.5	509.9	572.9
135°	301.9	305.6	316.6	331.4	350.7	375.6	404.1	434.4	468.5	509.9	562.4
137.5°	317.0	319.8	330.1	344.8	363.8	389.4	415.3	444.4	476.8	511.0	553.0
140°	325.8	328.6	339.7	354.4	371.9	396.7	423.4	451.1	480.5	511.7	548.6
142.5°	336.1	338.2	348.5	363.2	380.0	403.4	428.6	454.7	482.7	512.5	544.9
145°	351.6	353.5	362.7	375.6	392.1	413.3	437.2	460.3	485.1	511.7	539.4
147.5°	367.8	368.9	376.8	388.8	403.1	421.8	442.8	463.6	486.0	509.4	533.7
150°	377.4	379.2	385.7	397.7	410.5	426.2	446.4	465.8	486.0	507.2	529.3
152.5°	387.7	388.8	394.5	405.0	417.2	431.3	450.1	467.2	485.3	504.2	524.1
155°	401.3	401.3	406.9	416.1	425.2	438.2	453.8	468.5	483.2	498.9	515.5
157.5°	413.5	413.3	417.7	425.6	433.7	443.5	456.9	469.4	480.9	493.4	507.4
160°	421.6	420.6	424.4	430.8	438.2	446.4	458.4	469.4	478.6	489.7	500.7
162.5°	428.2	427.3	430.9	436.7	442.6	449.4	459.9	468.7	476.4	485.3	494.9
165°	438.2	436.3	439.1	443.7	447.3	452.9	460.3	467.6	473.1	478.6	486.0
167.5°	444.8	443.9	445.5	448.1	450.7	454.2	460.3	465.4	467.9	472.2	477.4
170°	449.2	448.3	449.2	451.1	452.9	455.7	460.3	463.9	465.8	468.5	472.2
172.5°	452.2	450.5	451.4	453.2	454.3	455.7	459.5	462.5	462.8	464.1	467.1
175°	455.7	453.8	454.7	455.7	455.7	455.7	458.4	460.3	459.3	459.3	460.3
177.5°	457.3	455.8	455.8	456.5	455.8	455.8	457.3	458.0	456.5	456.5	457.3
180°	456.5	456.5	456.5	456.5	456.5	456.5	456.5	456.5	456.5	456.5	456.5



TEST NUMBER: P333159-927

CATALOG NUMBER: S125DIP-S375D1205U927-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8
2.5°	461.4	462.1	462.7	463.0	463.0	462.9	462.9	462.8
5°	459.1	459.9	460.6	460.9	460.8	460.7	460.7	460.6
7.5°	454.5	455.2	455.9	456.2	456.1	456.1	456.0	455.9
10°	450.5	451.1	451.9	452.1	452.0	451.9	451.9	451.8
12.5°	445.3	445.8	446.3	446.6	446.6	446.6	446.6	446.5
15°	436.1	436.5	437.0	437.1	437.1	437.1	437.1	437.1
17.5°	425.5	426.0	426.5	426.5	426.1	425.7	425.3	424.9
20°	417.4	418.0	418.5	418.7	418.2	417.8	417.4	417.0
22.5°	408.2	408.6	409.0	409.0	408.8	408.4	408.2	407.9
25°	393.6	393.7	393.9	393.8	393.6	393.3	393.1	392.8
27.5°	378.1	378.1	378.2	378.1	377.8	377.6	377.3	377.1
30°	366.9	366.7	366.5	366.4	366.1	365.9	365.6	365.4
32.5°	355.5	355.2	354.9	354.6	354.1	353.6	353.2	352.8
35°	337.9	337.5	337.0	336.5	335.9	335.2	334.5	333.9
37.5°	319.3	318.7	318.1	317.6	317.2	316.9	316.5	316.1
40°	306.4	305.7	305.0	304.5	304.3	304.0	303.7	303.5
42.5°	293.7	293.0	292.3	291.8	291.4	291.0	290.7	290.3
45°	274.8	273.9	272.9	272.3	272.0	271.8	271.6	271.3
47.5°	254.9	254.0	252.9	252.2	251.6	251.0	250.5	249.9
50°	241.4	240.3	239.2	238.4	237.8	237.3	236.7	236.1
52.5°	228.1	227.2	226.2	225.5	224.9	224.3	223.6	223.0
55°	207.6	206.8	206.1	205.5	204.9	204.3	203.7	203.2
57.5°	187.2	186.2	185.3	184.7	184.3	184.0	183.7	183.4
60°	173.4	172.5	171.7	171.0	170.5	169.9	169.4	168.8
62.5°	160.1	159.1	158.3	157.6	157.2	156.8	156.3	155.9
65°	139.1	138.4	137.7	137.1	136.8	136.5	136.2	135.9
67.5°	119.1	118.5	117.9	117.5	117.3	117.1	116.9	116.7
70°	105.9	105.4	105.0	104.6	104.3	103.9	103.5	103.2
72.5°	93.5	92.9	92.4	92.0	91.7	91.3	90.9	90.6
75°	74.2	74.0	73.7	73.4	73.1	72.8	72.5	72.1
77.5°	56.6	56.4	56.2	56.1	55.8	55.6	55.4	55.1
80°	45.2	45.2	45.1	44.9	44.8	44.6	44.4	44.3
82.5°	34.5	34.4	34.3	34.1	34.1	34.1	34.1	34.1
85°	20.4	20.3	20.2	20.0	19.9	19.7	19.6	19.4
87.5°	10.9	11.1	11.3	11.6	11.5	11.3	11.4	11.2
90°	16.6	17.5	18.4	20.3	20.3	20.3	21.2	21.2
92.5°	163.1	118.4	89.1	75.5	63.7	61.5	60.2	58.7
95°	661.8	521.9	408.7	331.4	266.0	238.4	231.1	216.3
97.5°	985.6	887.6	777.3	669.7	612.8	561.3	534.6	522.8
100°	1132.2	1087.1	992.3	896.5	833.1	766.8	732.7	718.0
102.5°	1181.5	1209.3	1163.9	1099.1	1031.1	984.0	947.0	936.0
105°	1152.5	1278.6	1319.1	1308.9	1279.5	1249.1	1230.7	1219.6
107.5°	1048.6	1216.9	1320.9	1369.0	1383.9	1383.7	1377.6	1370.2
110°	972.0	1146.9	1276.7	1354.9	1396.4	1413.9	1420.3	1420.3





TEST NUMBER: P333159-927

CATALOG NUMBER: S125DIP-S375D1205U927-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	911.6	1077.7	1208.9	1301.2	1361.8	1391.8	1407.8	1414.4
115°	835.8	978.5	1104.5	1204.9	1276.7	1320.9	1346.6	1358.6
117.5°	786.8	909.8	1018.4	1110.5	1182.3	1228.0	1253.5	1260.8
120°	760.3	870.8	972.0	1053.0	1121.2	1165.3	1190.2	1197.5
122.5°	740.5	842.8	933.0	1008.8	1069.6	1110.1	1135.0	1141.6
125°	711.5	805.4	885.5	951.8	1003.3	1041.1	1061.3	1070.6
127.5°	682.1	769.7	844.5	906.5	953.2	986.6	1005.8	1009.8
130°	663.7	744.7	816.5	876.3	922.3	952.7	971.1	976.6
132.5°	645.2	721.1	786.2	843.9	889.9	920.3	937.2	943.5
135°	621.3	684.8	743.8	796.2	836.7	867.1	883.7	889.2
137.5°	601.1	652.4	701.4	746.0	782.2	809.8	825.1	831.2
140°	590.0	633.3	675.7	714.3	748.4	772.3	786.1	790.7
142.5°	580.4	617.1	653.6	687.1	716.0	736.2	749.2	753.1
145°	567.9	596.4	625.0	649.8	671.9	687.6	697.8	701.4
147.5°	556.2	579.3	601.3	620.0	637.5	650.1	655.9	657.6
150°	549.5	569.8	587.2	603.8	617.7	628.7	632.4	633.3
152.5°	542.2	560.2	576.2	589.1	600.7	609.5	613.2	614.2
155°	531.1	545.8	558.7	568.9	578.1	584.5	587.2	588.2
157.5°	520.1	532.2	542.2	550.1	557.2	562.6	565.1	565.0
160°	512.7	521.9	531.1	537.6	544.0	548.6	550.5	549.5
162.5°	504.6	513.1	520.8	526.5	531.5	535.4	535.8	535.5
165°	493.4	499.8	505.3	509.9	513.7	515.5	515.5	515.5
167.5°	482.7	487.0	491.2	494.5	496.3	498.0	497.3	497.1
170°	476.8	479.6	482.4	484.2	486.0	487.0	487.0	486.0
172.5°	470.2	472.9	475.0	476.1	476.4	478.1	476.7	475.7
175°	463.0	463.0	464.9	464.9	464.9	465.8	463.9	463.0
177.5°	458.0	458.8	458.8	458.8	458.0	458.8	456.5	456.5
180°	456.5	456.5	456.5	456.5	456.5	456.5	456.5	456.5

(END OF REPORT)