

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333130-927

Luminaire Tested: **S125DIP-S375D590U927-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333130-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S375D590U927-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 375 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 590 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3077.8 lumens
Efficiency: N/A
Efficacy: 120.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 25.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333130-927

CATALOG NUMBER: S125DIP-S375D590U927-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333130-927

CATALOG NUMBER: S125DIP-S375D590U927-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	95	95	95	95	77	77	77	61	61	61	46	46	46	39
1	95	91	87	84	86	83	80	77	68	65	63	54	52	51	41	40	39	33
2	87	79	73	68	79	72	67	63	59	56	52	47	44	42	36	34	33	27
3	79	70	63	57	72	64	57	52	52	48	44	42	38	36	32	30	28	23
4	72	62	54	48	65	56	50	44	46	41	37	37	33	31	28	26	24	20
5	66	55	47	41	60	50	43	38	41	36	32	33	29	26	25	23	21	17
6	61	49	41	35	55	45	38	33	37	32	28	30	26	23	23	20	18	15
7	56	44	36	31	51	41	34	29	34	28	25	27	23	20	21	18	16	13
8	52	40	33	27	47	37	30	25	31	25	22	25	21	18	19	17	15	12
9	49	37	29	24	44	34	27	23	28	23	19	23	19	16	18	15	13	11
10	45	33	26	22	41	31	24	20	26	21	17	21	17	15	17	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2989	2989	2989
5°	2995	2967	2986
10°	2977	2946	2963
15°	2945	2910	2923
20°	2899	2861	2866
25°	2849	2802	2799
30°	2788	2738	2725
35°	2722	2670	2633
40°	2655	2596	2559
45°	2582	2528	2478
50°	2502	2446	2372
55°	2423	2354	2288
60°	2331	2260	2180
65°	2222	2149	2077
70°	2115	2019	1949
75°	1926	1864	1799
80°	1715	1689	1648
85°	1489	1519	1438



TEST NUMBER: P333130-927

CATALOG NUMBER: S125DIP-S375D590U927-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	43.6	1.4
10°-20°	123.3	4.0
20°-30°	182.0	5.9
30°-40°	212.4	6.9
40°-50°	213.3	6.9
50°-60°	187.2	6.1
60°-70°	139.5	4.5
70°-80°	79.8	2.6
80°-90°	24.5	0.8
90°-100°	22.2	0.7
100°-110°	136.6	4.4
110°-120°	247.7	8.0
120°-130°	317.8	10.3
130°-140°	341.9	11.1
140°-150°	320.9	10.4
150°-160°	259.6	8.4
160°-170°	167.9	5.5
170°-180°	57.9	1.9
0°-30°	348.9	11.3
0°-40°	561.2	18.2
0°-60°	961.7	31.2
0°-90°	1205.5	39.2
90°-120°	406.4	13.2
90°-150°	1387.0	45.1
90°-180°	1872.0	60.8
0°-180°	3077.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	463	463	463	463	463	
5°	462	461	458	461	461	44
15°	440	439	435	437	437	124
25°	400	398	393	394	393	184
35°	345	344	339	337	334	216
45°	283	281	277	273	271	218
55°	215	214	209	206	203	192
65°	145	144	141	137	136	144
75°	77	76	75	74	72	82
85°	20	20	20	20	19	23
90°	0	4	7	10	11	2
95°	26	24	7	9	10	33
105°	133	135	135	135	134	141
115°	250	252	252	250	248	247
125°	355	358	358	356	355	317
135°	442	445	444	443	441	341
145°	513	514	514	514	512	321
155°	565	562	563	564	561	260
165°	596	594	594	596	593	168
175°	610	607	607	611	607	58
180°	610	610	610	610	610	



TEST NUMBER: P333130-927

CATALOG NUMBER: S125DIP-S375D590U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8
2.5°	463.9	463.7	463.6	463.3	463.2	462.7	462.1	461.4	460.8	460.1	460.8
5°	462.0	461.8	461.7	461.5	461.4	460.9	460.1	459.3	458.4	457.6	458.4
7.5°	457.8	457.6	457.5	457.3	457.2	456.6	455.7	454.8	453.9	453.0	453.8
10°	454.0	453.8	453.7	453.5	453.4	452.8	451.9	451.0	450.1	449.2	449.9
12.5°	449.3	449.0	448.7	448.5	448.1	447.6	446.7	445.9	445.0	444.3	444.7
15°	440.5	440.2	440.0	439.7	439.4	438.9	438.0	437.1	436.2	435.3	435.7
17.5°	430.2	429.9	429.5	429.2	428.8	428.2	427.2	426.4	425.4	424.5	425.0
20°	421.8	421.6	421.4	421.3	421.1	420.5	419.5	418.4	417.3	416.3	416.8
22.5°	413.3	413.0	412.6	412.4	412.1	411.5	410.4	409.5	408.4	407.5	407.9
25°	399.8	399.4	398.9	398.5	398.2	397.4	396.4	395.3	394.3	393.2	393.4
27.5°	384.0	383.8	383.6	383.3	383.1	382.4	381.4	380.2	379.1	378.0	378.1
30°	373.8	373.6	373.3	373.0	372.8	372.1	370.9	369.6	368.4	367.2	367.0
32.5°	362.7	362.3	361.9	361.6	361.2	360.4	359.3	358.2	357.2	356.1	355.8
35°	345.2	344.9	344.6	344.3	344.0	343.2	342.1	341.0	339.8	338.7	338.3
37.5°	327.2	326.8	326.4	325.9	325.5	324.8	323.7	322.7	321.5	320.5	319.9
40°	314.9	314.4	314.0	313.6	313.2	312.4	311.3	310.2	309.0	307.9	307.2
42.5°	301.7	301.3	301.0	300.6	300.3	299.6	298.4	297.3	296.1	295.0	294.4
45°	282.7	282.3	282.0	281.7	281.3	280.7	279.7	278.8	277.7	276.8	275.8
47.5°	262.1	262.1	262.1	262.2	262.2	261.7	260.5	259.3	258.1	256.9	256.0
50°	249.0	248.7	248.5	248.2	248.0	247.4	246.4	245.4	244.5	243.4	242.4
52.5°	235.5	235.3	235.1	235.0	234.8	234.2	233.1	232.1	231.0	230.0	229.1
55°	215.2	215.0	214.8	214.5	214.3	213.6	212.5	211.4	210.2	209.1	208.3
57.5°	194.0	193.8	193.7	193.6	193.5	192.9	191.9	191.0	190.0	189.1	188.1
60°	180.5	180.1	179.8	179.5	179.2	178.6	177.7	176.8	175.9	175.0	174.2
62.5°	166.4	166.2	165.9	165.6	165.4	164.9	164.1	163.3	162.6	161.8	161.0
65°	145.4	145.2	145.0	144.9	144.7	144.2	143.3	142.4	141.5	140.6	139.8
67.5°	124.9	124.6	124.2	123.9	123.6	123.0	122.4	121.7	121.0	120.4	119.8
70°	112.0	111.6	111.2	110.8	110.4	109.8	109.1	108.4	107.7	106.9	106.4
72.5°	98.0	97.7	97.4	97.1	96.9	96.5	96.0	95.5	95.1	94.6	94.0
75°	77.2	77.1	76.9	76.8	76.6	76.3	75.9	75.5	75.1	74.7	74.5
77.5°	58.1	58.1	58.0	57.9	57.9	57.8	57.5	57.3	57.0	56.8	56.6
80°	46.1	46.1	46.1	46.1	46.1	46.0	45.9	45.7	45.6	45.4	45.3
82.5°	35.6	35.5	35.3	35.2	35.1	35.0	34.9	34.9	34.9	34.9	34.7
85°	20.1	20.2	20.3	20.4	20.4	20.5	20.5	20.5	20.5	20.5	20.4
87.5°	8.0	8.2	8.3	8.5	8.6	8.8	8.9	8.9	9.0	9.0	9.2
90°	0.5	1.3	2.1	2.9	3.6	4.4	5.1	5.9	6.5	7.2	7.8
92.5°	7.0	6.4	5.9	5.3	4.7	4.8	5.4	6.0	6.6	7.2	7.8
95°	25.7	25.4	25.2	24.9	24.6	22.5	18.7	14.9	11.0	7.2	7.8
97.5°	53.8	54.3	54.9	55.4	55.9	52.4	44.9	37.3	29.8	22.3	19.4
100°	75.5	75.8	76.0	76.4	76.7	77.0	77.5	77.9	78.3	78.7	63.7
102.5°	97.5	97.9	98.3	98.7	99.0	99.3	99.6	99.9	100.1	100.4	97.5
105°	132.8	133.2	133.7	134.1	134.5	134.7	134.7	134.7	134.7	134.7	134.7
107.5°	169.6	169.6	169.6	169.6	169.6	169.7	169.8	170.1	170.3	170.5	170.5
110°	193.5	193.5	193.5	193.5	193.5	193.5	193.8	193.9	194.2	194.3	194.1



TEST NUMBER: P333130-927

CATALOG NUMBER: S125DIP-S375D590U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	215.9	216.1	216.3	216.6	216.8	217.0	217.1	217.2	217.4	217.5	217.1
115°	249.5	250.0	250.5	251.0	251.5	251.8	251.9	252.0	252.1	252.2	251.8
117.5°	284.3	284.2	284.2	284.2	284.2	284.4	284.8	285.2	285.5	285.9	285.4
120°	306.0	305.9	305.8	305.7	305.5	305.7	306.0	306.3	306.6	306.9	306.7
122.5°	325.1	325.5	325.9	326.3	326.7	326.9	327.1	327.3	327.3	327.5	327.3
125°	354.8	355.5	356.2	356.9	357.6	358.0	358.0	358.0	358.0	358.0	357.6
127.5°	383.1	383.6	384.1	384.6	385.1	385.3	385.2	385.2	385.2	385.1	384.8
130°	400.4	400.9	401.5	402.0	402.4	402.7	402.8	403.0	403.1	403.1	402.8
132.5°	417.8	418.4	419.0	419.5	420.1	420.3	420.1	419.9	419.6	419.5	419.4
135°	442.5	443.1	443.7	444.3	444.9	445.1	444.9	444.7	444.5	444.3	444.1
137.5°	465.2	465.7	466.2	466.8	467.2	467.5	467.2	467.1	466.9	466.7	466.8
140°	480.0	480.2	480.4	480.6	480.8	480.9	480.8	480.6	480.5	480.5	480.6
142.5°	493.4	493.5	493.6	493.8	493.8	494.0	494.2	494.2	494.4	494.6	494.6
145°	513.0	513.2	513.4	513.6	513.8	513.9	513.9	513.9	513.9	513.9	514.0
147.5°	530.1	530.1	530.0	530.0	530.0	530.0	530.1	530.3	530.4	530.5	530.7
150°	541.0	540.8	540.6	540.4	540.2	540.2	540.4	540.6	540.8	541.0	541.2
152.5°	551.5	551.0	550.6	550.2	549.7	549.6	549.8	550.0	550.2	550.4	550.6
155°	565.0	564.4	563.8	563.2	562.5	562.4	562.5	562.8	562.9	563.2	563.5
157.5°	575.4	575.0	574.6	574.3	573.9	573.8	573.8	573.8	573.8	573.9	574.2
160°	582.6	582.0	581.4	580.7	580.2	580.0	580.0	580.1	580.2	580.4	580.7
162.5°	588.4	587.8	587.2	586.5	586.0	585.7	585.8	585.9	586.0	586.1	586.7
165°	596.1	595.6	594.9	594.4	593.7	593.5	593.6	593.7	593.8	593.9	594.5
167.5°	601.9	601.3	600.7	600.1	599.4	599.2	599.3	599.4	599.4	599.6	600.3
170°	605.2	604.5	603.8	603.1	602.4	602.1	602.1	602.3	602.4	602.5	603.2
172.5°	607.4	606.7	605.9	605.2	604.5	604.3	604.4	604.7	604.8	605.0	605.7
175°	609.7	609.1	608.5	607.9	607.3	607.0	607.1	607.3	607.4	607.4	608.2
177.5°	610.8	610.3	609.8	609.3	608.9	608.6	608.7	608.8	608.9	609.0	609.6
180°	609.7	609.7	609.7	609.7	609.7	609.7	609.7	609.7	609.7	609.7	609.7



TEST NUMBER: P333130-927

CATALOG NUMBER: S125DIP-S375D590U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8
2.5°	461.4	462.1	462.7	463.0	463.0	462.9	462.9	462.8
5°	459.1	459.9	460.6	460.9	460.8	460.7	460.7	460.6
7.5°	454.5	455.2	455.9	456.2	456.1	456.1	456.0	455.9
10°	450.5	451.1	451.9	452.1	452.0	451.9	451.9	451.8
12.5°	445.3	445.8	446.3	446.6	446.6	446.6	446.6	446.5
15°	436.1	436.5	437.0	437.1	437.1	437.1	437.1	437.1
17.5°	425.5	426.0	426.5	426.5	426.1	425.7	425.3	424.9
20°	417.4	418.0	418.5	418.7	418.2	417.8	417.4	417.0
22.5°	408.2	408.6	409.0	409.0	408.8	408.4	408.2	407.9
25°	393.6	393.7	393.9	393.8	393.6	393.3	393.1	392.8
27.5°	378.1	378.1	378.2	378.1	377.8	377.6	377.3	377.1
30°	366.9	366.7	366.5	366.4	366.1	365.9	365.6	365.4
32.5°	355.5	355.2	354.9	354.6	354.1	353.6	353.2	352.8
35°	337.9	337.5	337.0	336.5	335.9	335.2	334.5	333.9
37.5°	319.3	318.7	318.1	317.6	317.2	316.9	316.5	316.1
40°	306.4	305.7	305.0	304.5	304.3	304.0	303.7	303.5
42.5°	293.7	293.0	292.3	291.8	291.4	291.0	290.7	290.3
45°	274.8	273.9	272.9	272.3	272.0	271.8	271.6	271.3
47.5°	254.9	254.0	252.9	252.2	251.6	251.0	250.5	249.9
50°	241.4	240.3	239.2	238.4	237.8	237.3	236.7	236.1
52.5°	228.1	227.2	226.2	225.5	224.9	224.3	223.6	223.0
55°	207.6	206.8	206.1	205.5	204.9	204.3	203.7	203.2
57.5°	187.2	186.2	185.3	184.7	184.3	184.0	183.7	183.4
60°	173.4	172.5	171.7	171.0	170.5	169.9	169.4	168.8
62.5°	160.1	159.1	158.3	157.6	157.2	156.8	156.3	155.9
65°	139.1	138.4	137.7	137.1	136.8	136.5	136.2	135.9
67.5°	119.1	118.5	117.9	117.5	117.3	117.1	116.9	116.7
70°	105.9	105.4	105.0	104.6	104.3	103.9	103.5	103.2
72.5°	93.5	92.9	92.4	92.0	91.7	91.3	90.9	90.6
75°	74.2	74.0	73.7	73.4	73.1	72.8	72.5	72.1
77.5°	56.6	56.4	56.2	56.1	55.8	55.6	55.4	55.1
80°	45.2	45.2	45.1	44.9	44.8	44.6	44.4	44.3
82.5°	34.5	34.4	34.3	34.1	34.1	34.1	34.1	34.1
85°	20.4	20.3	20.2	20.0	19.9	19.7	19.6	19.4
87.5°	9.3	9.3	9.4	9.5	9.4	9.3	9.3	9.2
90°	8.2	8.7	9.3	9.7	10.0	10.2	10.5	10.9
92.5°	8.2	8.7	9.3	9.6	9.7	9.8	10.0	10.1
95°	8.2	8.7	9.3	9.5	9.5	9.5	9.5	9.5
97.5°	16.6	13.7	10.9	9.5	9.5	9.5	9.5	9.5
100°	48.7	33.7	18.8	11.1	10.7	10.3	9.9	9.5
102.5°	94.7	91.8	89.0	84.2	77.3	70.5	63.7	56.9
105°	134.7	134.7	134.7	134.7	134.5	134.4	134.4	134.2
107.5°	170.6	170.6	170.6	170.4	170.2	169.8	169.5	169.2
110°	193.8	193.5	193.1	193.1	193.1	193.2	193.4	193.5



TEST NUMBER: P333130-927

CATALOG NUMBER: S125DIP-S375D590U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	216.7	216.3	215.9	215.7	215.6	215.4	215.3	215.2
115°	251.4	251.0	250.6	250.1	249.5	248.9	248.3	247.7
117.5°	284.9	284.3	283.8	283.4	283.2	282.9	282.7	282.4
120°	306.5	306.3	306.1	305.7	305.2	304.8	304.2	303.7
122.5°	327.1	326.9	326.7	326.3	325.7	325.1	324.6	324.0
125°	357.2	356.7	356.3	356.0	355.7	355.4	355.1	354.8
127.5°	384.6	384.4	384.2	383.7	382.9	382.2	381.5	380.7
130°	402.6	402.3	402.0	401.6	401.1	400.5	400.1	399.6
132.5°	419.3	419.2	419.2	418.9	418.4	417.9	417.4	416.9
135°	443.9	443.7	443.5	443.1	442.5	441.9	441.2	440.7
137.5°	466.8	466.8	466.8	466.6	466.1	465.6	465.1	464.5
140°	480.9	481.0	481.3	481.0	480.5	479.8	479.3	478.6
142.5°	494.6	494.6	494.7	494.4	493.8	493.2	492.6	492.0
145°	514.1	514.2	514.3	514.0	513.4	512.9	512.2	511.6
147.5°	530.8	530.9	531.0	530.7	530.0	529.3	528.5	527.8
150°	541.4	541.6	541.8	541.5	540.7	539.9	539.1	538.3
152.5°	550.8	551.0	551.2	551.0	550.2	549.5	548.7	548.0
155°	563.8	564.0	564.4	564.1	563.3	562.5	561.7	560.9
157.5°	574.5	574.8	575.1	574.9	574.1	573.2	572.4	571.6
160°	581.1	581.5	581.9	581.7	580.9	580.1	579.3	578.5
162.5°	587.2	587.8	588.4	588.2	587.3	586.5	585.6	584.6
165°	595.1	595.7	596.3	596.2	595.4	594.6	593.8	592.9
167.5°	601.0	601.7	602.5	602.4	601.5	600.6	599.7	598.7
170°	604.1	604.9	605.7	605.6	604.8	603.8	602.9	602.1
172.5°	606.4	607.2	607.9	607.8	606.9	606.0	605.1	604.2
175°	609.0	609.8	610.7	610.6	609.7	608.8	607.9	607.0
177.5°	610.1	610.7	611.2	611.2	610.5	609.9	609.3	608.6
180°	609.7	609.7	609.7	609.7	609.7	609.7	609.7	609.7

(END OF REPORT)