

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333134-927

Luminaire Tested: **S125DIP-S375D810U927-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333134-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIP-S375D810U927-4F0-1E-UDD-A1  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 375 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 810 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3439.8 lumens  
Efficiency: N/A  
Efficacy: 110.3 lumens/watt  
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 31.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333134-927

CATALOG NUMBER: S125DIP-S375D810U927-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P333134-927

CATALOG NUMBER: S125DIP-S375D810U927-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	43	43	43	35
1	95	91	87	83	85	82	79	76	66	64	62	51	50	49	38	37	36	30
2	86	79	73	68	78	72	67	63	58	55	51	45	43	41	34	32	31	25
3	79	70	63	57	71	63	57	52	51	47	43	40	37	35	30	28	26	22
4	72	62	54	48	65	56	49	44	46	41	37	36	32	30	27	25	23	19
5	66	55	47	41	60	50	43	38	41	36	32	32	29	26	24	22	20	16
6	61	49	41	36	55	45	38	33	37	32	28	29	25	23	22	19	17	14
7	56	44	37	31	51	40	34	29	33	28	24	26	23	20	20	17	16	13
8	52	40	33	27	47	37	30	25	30	25	22	24	20	18	18	16	14	11
9	48	36	29	24	44	33	27	23	28	23	19	22	18	16	17	14	13	10
10	45	33	26	22	41	31	24	20	25	20	17	20	17	14	16	13	11	9

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	2785	2785	2785	2785
5°	3225	2795	2447	2795
10°	3752	2781	2144	2781
15°	4153	2760	1978	2760
20°	4649	2728	1844	2728
25°	5447	2691	1779	2691
30°	5883	2655	1723	2655
35°	4837	2588	1686	2588
40°	3438	2494	1645	2494
45°	2641	2367	1621	2367
50°	2255	2210	1619	2210
55°	2008	2057	1633	2057
60°	1811	1888	1674	1888
65°	1673	1721	1718	1721
70°	1522	1545	1743	1545
75°	1342	1362	1727	1362
80°	1131	1112	1581	1112
85°	897	800	1275	800



TEST NUMBER: P333134-927

CATALOG NUMBER: S125DIP-S375D810U927-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	41.5	1.2
10°-20°	123.6	3.6
20°-30°	200.7	5.8
30°-40°	244.8	7.1
40°-50°	222.7	6.5
50°-60°	177.4	5.2
60°-70°	123.6	3.6
70°-80°	65.9	1.9
80°-90°	18.4	0.5
90°-100°	53.3	1.5
100°-110°	157.4	4.6
110°-120°	266.7	7.8
120°-130°	350.9	10.2
130°-140°	393.2	11.4
140°-150°	385.4	11.2
150°-160°	323.7	9.4
160°-170°	215.2	6.3
170°-180°	75.3	2.2
0°-30°	365.9	10.6
0°-40°	610.7	17.8
0°-60°	1010.8	29.4
0°-90°	1218.7	35.4
90°-120°	477.4	13.9
90°-150°	1607.0	46.7
90°-180°	2221.0	64.6
0°-180°	3439.8	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	431	431	431	431	431	
5°	498	431	378	431	498	50
15°	621	413	296	413	621	178
25°	764	378	250	378	764	349
35°	614	328	214	328	614	375
45°	289	259	178	259	289	231
55°	178	183	145	183	178	161
65°	110	113	112	113	110	109
75°	54	55	69	55	54	58
85°	12	11	17	11	12	14
90°	15	1	15	1	15	9
95°	53	40	53	40	53	54
105°	154	141	154	141	154	163
115°	270	267	270	267	270	267
125°	392	390	392	390	392	350
135°	509	507	509	507	509	392
145°	616	614	616	614	616	385
155°	702	702	702	702	702	323
165°	762	764	762	764	762	215
175°	791	794	791	794	791	75
180°	796	796	796	796	796	



TEST NUMBER: P333134-927

CATALOG NUMBER: S125DIP-S375D810U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3
2.5°	456.1	455.6	455.0	453.8	454.7	452.2	451.1	449.0	446.5	445.6	444.6
5°	497.5	498.4	499.4	495.5	495.9	493.3	487.4	482.7	478.9	473.9	470.4
7.5°	547.3	545.2	544.9	542.5	538.2	534.7	528.6	520.8	513.2	504.5	497.4
10°	572.2	572.4	570.8	567.8	563.2	559.9	551.9	544.2	534.9	523.9	516.0
12.5°	591.0	591.8	589.6	585.7	583.4	576.1	569.7	560.6	549.5	540.7	528.8
15°	621.2	619.2	617.8	612.8	609.0	601.3	591.3	581.7	569.7	558.5	547.3
17.5°	650.5	652.1	649.4	644.8	632.9	623.9	610.5	597.4	582.3	567.4	554.1
20°	676.5	678.0	673.8	665.9	651.6	642.7	625.0	608.1	590.7	571.5	556.8
22.5°	709.1	707.9	702.2	690.2	677.9	661.3	642.1	621.5	599.8	578.1	558.6
25°	764.4	756.7	753.2	738.4	722.2	697.8	671.5	641.4	614.3	585.6	560.7
27.5°	795.1	792.7	788.8	778.5	761.4	735.3	704.3	667.7	629.5	593.2	560.5
30°	788.9	789.3	789.6	786.4	775.4	755.8	724.8	685.6	640.1	599.3	561.6
32.5°	734.4	741.1	747.5	755.0	758.1	754.3	735.0	699.4	652.7	606.3	561.0
35°	613.5	615.6	636.3	656.8	684.6	706.2	720.6	704.9	665.6	612.3	560.3
37.5°	478.4	488.3	502.6	525.8	565.9	601.9	648.2	669.4	656.7	614.3	559.0
40°	407.8	417.0	426.4	450.0	483.8	527.4	579.9	624.7	635.2	608.1	554.6
42.5°	353.4	360.6	371.0	388.7	417.0	455.6	505.8	564.4	600.5	590.3	545.4
45°	289.2	293.8	301.8	315.9	336.4	366.6	410.9	475.0	530.8	549.3	523.6
47.5°	247.6	247.6	253.8	263.5	278.3	304.0	336.8	386.9	446.6	490.7	488.6
50°	224.4	223.5	228.5	236.9	248.6	265.6	296.9	337.0	394.3	444.3	458.2
52.5°	204.5	204.6	207.6	213.9	223.7	238.2	261.6	297.8	346.7	398.0	424.2
55°	178.3	177.5	181.0	185.2	192.4	201.9	218.7	246.4	286.1	336.6	370.7
57.5°	154.2	156.3	157.6	160.6	166.5	172.9	187.1	207.4	238.9	282.3	318.2
60°	140.2	142.2	143.3	146.2	151.0	156.5	167.5	183.9	210.5	247.9	283.5
62.5°	127.6	129.2	129.6	132.2	136.1	141.4	150.0	163.9	184.9	217.5	252.5
65°	109.5	109.5	110.2	113.0	114.8	119.5	126.1	136.2	153.0	178.5	208.3
67.5°	92.0	92.8	92.7	93.9	95.5	99.3	103.9	112.3	124.8	143.3	167.2
70°	80.6	81.3	81.1	82.0	83.8	86.2	90.1	97.9	106.9	122.8	143.3
72.5°	70.3	70.6	70.1	71.3	72.4	74.5	78.8	83.0	91.3	104.8	121.7
75°	53.8	54.2	54.6	55.3	56.4	57.5	59.7	63.8	69.4	79.5	90.2
77.5°	40.3	39.6	40.6	40.4	41.0	41.9	43.8	46.0	50.5	57.0	65.3
80°	30.4	30.6	30.6	30.7	31.7	32.2	33.8	35.5	39.0	43.7	49.6
82.5°	22.2	22.7	22.3	22.7	23.4	23.8	24.8	26.1	28.1	31.9	36.1
85°	12.1	11.2	11.6	11.9	11.9	12.1	12.8	13.4	14.5	15.9	17.6
87.5°	6.5	6.7	6.7	6.7	6.7	6.7	7.1	7.0	7.2	7.5	7.9
90°	14.9	14.4	14.0	13.6	13.2	12.7	12.0	11.2	10.6	9.9	9.0
92.5°	29.2	28.9	28.6	28.4	28.0	27.4	26.5	25.6	24.7	23.8	22.6
95°	53.2	53.0	52.8	52.4	52.2	51.6	50.6	49.6	48.6	47.7	46.3
97.5°	80.8	80.6	80.4	80.2	80.1	79.6	78.7	77.8	76.8	76.0	74.1
100°	101.6	101.3	101.0	100.8	100.5	99.7	98.5	97.3	96.0	94.7	93.0
102.5°	122.4	122.0	121.6	121.3	120.9	120.0	118.7	117.3	116.0	114.6	113.7
105°	153.6	153.2	152.8	152.4	151.9	151.4	150.5	149.7	148.9	148.1	147.2
107.5°	185.6	185.6	185.6	185.7	185.7	185.5	185.1	184.7	184.3	183.9	183.2
110°	209.4	209.5	209.6	209.8	209.9	209.8	209.4	209.0	208.6	208.1	207.7



TEST NUMBER: P333134-927

CATALOG NUMBER: S125DIP-S375D810U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	232.7	232.9	233.1	233.4	233.7	233.7	233.5	233.3	233.1	232.9	232.4
115°	269.5	269.6	269.7	269.9	270.0	270.1	270.3	270.5	270.5	270.7	270.5
117.5°	305.4	305.9	306.5	307.0	307.6	307.8	307.7	307.6	307.4	307.4	307.1
120°	330.2	330.7	331.3	331.8	332.4	332.6	332.6	332.6	332.6	332.6	332.5
122.5°	355.0	355.4	355.8	356.2	356.7	357.0	357.1	357.2	357.3	357.4	357.0
125°	392.1	392.3	392.4	392.5	392.7	392.8	393.2	393.4	393.7	394.0	393.8
127.5°	427.8	428.1	428.3	428.6	428.9	429.1	429.2	429.4	429.5	429.7	429.5
130°	451.5	451.9	452.1	452.4	452.7	452.9	453.0	453.1	453.3	453.4	453.1
132.5°	473.9	474.3	474.7	475.1	475.4	475.7	475.8	475.9	476.1	476.3	476.3
135°	508.6	509.1	509.7	510.2	510.8	511.0	511.0	511.0	511.0	511.0	510.9
137.5°	542.5	543.2	543.9	544.5	545.3	545.5	545.3	545.2	545.0	544.9	544.5
140°	564.4	565.0	565.7	566.4	567.0	567.3	567.0	566.7	566.5	566.2	565.8
142.5°	585.1	585.8	586.5	587.2	587.9	588.1	588.0	587.8	587.6	587.5	586.9
145°	616.3	616.8	617.2	617.6	618.0	618.2	618.2	618.2	618.2	618.2	617.8
147.5°	643.0	644.0	644.8	645.8	646.7	647.1	646.7	646.3	646.0	645.7	645.4
150°	662.8	663.1	663.4	663.6	663.9	664.1	664.1	664.1	664.1	664.1	663.5
152.5°	679.1	679.7	680.2	680.6	681.1	681.2	680.9	680.6	680.2	679.9	679.7
155°	702.4	703.1	703.9	704.5	705.2	705.3	704.7	704.2	703.6	703.1	702.9
157.5°	721.9	722.8	723.7	724.6	725.6	725.7	725.2	724.6	724.1	723.5	723.3
160°	735.3	735.9	736.7	737.4	738.1	738.1	737.5	737.0	736.5	735.9	735.8
162.5°	746.7	747.5	748.3	749.1	749.9	750.0	749.3	748.6	748.0	747.3	747.3
165°	761.9	762.7	763.6	764.4	765.2	765.3	764.9	764.3	763.7	763.2	763.0
167.5°	774.0	774.9	775.8	776.7	777.4	777.5	776.7	775.9	775.0	774.2	774.2
170°	780.5	781.5	782.4	783.4	784.3	784.4	783.6	782.8	782.0	781.1	781.1
172.5°	785.9	786.8	787.7	788.5	789.4	789.4	788.5	787.7	786.9	786.1	786.1
175°	791.1	792.0	793.0	793.9	794.9	795.0	794.2	793.3	792.5	791.6	791.6
177.5°	794.0	794.8	795.6	796.3	797.1	797.2	796.5	795.8	795.2	794.5	794.6
180°	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0



TEST NUMBER: P333134-927

CATALOG NUMBER: S125DIP-S375D810U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3
2.5°	443.7	442.7	441.5	439.4	437.0	435.6	433.6	432.3	429.7	427.5	425.1
5°	466.2	461.4	457.1	451.4	445.2	441.2	436.4	431.1	425.6	419.9	413.7
7.5°	489.6	481.1	472.0	462.2	452.5	443.6	435.1	426.9	419.1	409.7	401.8
10°	505.2	494.6	483.2	469.9	456.9	445.5	434.0	424.0	413.7	402.7	393.0
12.5°	520.9	506.8	490.7	476.0	460.4	446.7	433.2	420.3	407.4	395.2	383.9
15°	532.0	519.5	504.7	483.8	466.2	447.3	429.4	412.8	397.2	383.7	369.4
17.5°	539.2	523.2	507.2	487.3	464.2	443.1	422.8	403.7	386.2	369.0	355.3
20°	540.5	524.0	507.4	487.8	464.2	440.1	419.7	396.9	378.0	360.2	343.4
22.5°	540.1	521.4	503.3	483.2	460.1	437.8	413.3	390.0	369.5	352.0	334.5
25°	536.0	516.0	493.3	473.0	450.3	426.7	401.8	377.6	356.8	336.8	319.4
27.5°	532.5	506.7	480.9	457.2	435.3	413.7	389.8	365.1	342.0	321.8	305.4
30°	528.3	499.9	471.0	446.2	423.7	402.7	380.2	356.0	331.8	312.1	294.5
32.5°	524.5	491.4	460.9	434.0	410.1	389.7	368.9	345.9	322.2	302.1	284.6
35°	517.1	478.9	443.9	413.5	388.1	367.0	349.6	328.2	306.4	287.0	270.2
37.5°	507.8	462.4	424.8	393.0	365.1	342.9	326.8	310.3	289.4	270.7	255.5
40°	500.4	450.7	410.9	378.3	349.4	326.4	311.3	295.8	278.5	261.0	244.9
42.5°	491.2	440.1	396.9	361.8	333.2	310.7	294.9	281.8	266.4	250.2	235.3
45°	474.3	421.0	374.1	336.4	307.5	285.3	269.1	259.2	247.6	232.3	219.7
47.5°	449.3	398.1	349.6	310.7	280.8	260.3	245.0	235.5	227.4	216.0	204.5
50°	427.2	381.0	331.8	293.3	263.4	242.7	228.6	220.0	213.1	204.3	194.6
52.5°	402.5	359.4	314.4	276.2	246.7	226.3	212.5	204.9	199.2	192.9	183.3
55°	363.1	326.5	284.8	248.6	221.3	201.4	189.3	182.7	177.9	173.2	167.3
57.5°	319.9	291.2	254.3	221.1	196.0	177.8	166.6	160.2	156.5	154.0	150.6
60°	289.4	264.9	233.1	202.8	178.3	162.2	151.2	146.2	143.1	141.2	138.6
62.5°	261.1	241.0	211.5	183.9	162.5	147.3	137.4	132.6	129.7	128.7	126.6
65°	219.5	203.9	179.6	156.7	138.4	125.4	117.2	112.6	110.7	109.6	109.8
67.5°	178.4	169.0	149.4	129.9	115.3	104.4	97.8	94.3	93.3	91.9	91.9
70°	153.4	146.2	129.8	112.7	99.7	91.3	85.5	81.8	80.9	80.2	80.0
72.5°	131.3	125.0	110.7	97.1	85.4	78.0	73.2	71.0	69.5	69.1	69.0
75°	98.6	95.2	83.8	73.0	65.0	59.9	56.6	54.6	53.5	53.2	53.5
77.5°	70.1	67.1	59.9	52.2	47.1	43.3	40.5	39.8	38.6	38.6	38.4
80°	52.7	50.7	46.1	40.1	35.9	32.6	31.1	29.9	29.5	28.9	29.5
82.5°	38.2	36.0	33.0	29.1	25.6	23.7	22.2	21.8	21.5	21.3	21.4
85°	18.9	19.0	17.2	14.3	12.8	11.7	10.8	10.8	10.6	10.5	10.6
87.5°	8.0	7.5	6.8	6.1	5.1	4.5	4.1	4.0	3.9	4.0	4.3
90°	8.0	7.1	6.0	5.0	4.0	2.9	1.7	0.6	1.7	2.9	4.0
92.5°	21.4	20.2	19.0	18.1	17.3	16.6	15.8	15.0	15.8	16.6	17.3
95°	44.9	43.6	42.2	41.4	41.1	40.8	40.6	40.2	40.6	40.8	41.1
97.5°	72.2	70.3	68.4	67.3	67.3	67.1	67.0	66.9	67.0	67.1	67.3
100°	91.2	89.4	87.6	86.7	86.7	86.7	86.7	86.7	86.7	86.7	86.7
102.5°	112.8	111.9	111.0	110.3	109.7	109.2	108.6	108.1	108.6	109.2	109.7
105°	146.4	145.6	144.7	144.0	143.3	142.6	142.0	141.2	142.0	142.6	143.3
107.5°	182.6	182.0	181.3	180.7	180.0	179.3	178.6	177.9	178.6	179.3	180.0
110°	207.3	206.9	206.5	206.0	205.3	204.5	203.9	203.2	203.9	204.5	205.3





TEST NUMBER: P333134-927

CATALOG NUMBER: S125DIP-S375D810U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	231.9	231.3	230.8	230.4	230.0	229.7	229.3	228.9	229.3	229.7	230.0
115°	270.1	269.9	269.6	269.2	268.6	268.1	267.5	267.0	267.5	268.1	268.6
117.5°	306.9	306.7	306.4	306.1	305.9	305.6	305.4	305.1	305.4	305.6	305.9
120°	332.4	332.2	332.1	331.7	331.0	330.3	329.6	328.9	329.6	330.3	331.0
122.5°	356.7	356.3	356.0	355.7	355.5	355.2	355.0	354.7	355.0	355.2	355.5
125°	393.7	393.6	393.4	392.9	392.1	391.3	390.5	389.6	390.5	391.3	392.1
127.5°	429.3	429.1	429.0	428.6	428.2	427.7	427.3	426.8	427.3	427.7	428.2
130°	452.9	452.6	452.3	451.9	451.1	450.5	449.8	449.1	449.8	450.5	451.1
132.5°	476.3	476.4	476.4	475.9	474.8	473.6	472.5	471.4	472.5	473.6	474.8
135°	510.8	510.6	510.5	510.0	509.2	508.3	507.6	506.7	507.6	508.3	509.2
137.5°	544.2	544.0	543.7	543.1	542.3	541.5	540.7	540.0	540.7	541.5	542.3
140°	565.4	564.9	564.5	564.0	563.3	562.6	561.9	561.3	561.9	562.6	563.3
142.5°	586.5	585.9	585.4	584.9	584.2	583.7	583.1	582.6	583.1	583.7	584.2
145°	617.3	617.0	616.6	616.1	615.5	615.0	614.4	613.9	614.4	615.0	615.5
147.5°	645.1	644.8	644.4	644.0	643.8	643.5	643.2	642.9	643.2	643.5	643.8
150°	663.0	662.4	661.9	661.6	661.8	661.9	662.0	662.2	662.0	661.9	661.8
152.5°	679.5	679.2	679.1	678.8	678.7	678.4	678.3	678.0	678.3	678.4	678.7
155°	702.8	702.7	702.5	702.4	702.4	702.4	702.4	702.4	702.4	702.4	702.4
157.5°	723.3	723.1	722.9	723.0	723.3	723.7	724.0	724.3	724.0	723.7	723.3
160°	735.6	735.5	735.4	735.5	735.9	736.3	736.7	737.1	736.7	736.3	735.9
162.5°	747.3	747.2	747.2	747.3	747.7	747.9	748.2	748.5	748.2	747.9	747.7
165°	762.9	762.7	762.6	762.7	763.0	763.3	763.5	763.8	763.5	763.3	763.0
167.5°	774.2	774.2	774.2	774.4	775.0	775.5	776.1	776.7	776.1	775.5	775.0
170°	781.1	781.1	781.1	781.4	782.0	782.5	783.1	783.6	783.1	782.5	782.0
172.5°	786.1	786.1	786.1	786.3	786.9	787.4	788.0	788.5	788.0	787.4	786.9
175°	791.6	791.6	791.6	791.9	792.5	793.1	793.6	794.2	793.6	793.1	792.5
177.5°	794.7	794.9	795.0	795.2	795.7	796.1	796.5	797.0	796.5	796.1	795.7
180°	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0



TEST NUMBER: P333134-927

CATALOG NUMBER: S125DIP-S375D810U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3
2.5°	423.8	422.2	420.9	418.0	416.3	414.2	412.4	414.3	412.3	413.1	411.8
5°	410.6	405.4	401.8	396.5	391.9	387.7	384.6	384.0	382.5	381.8	379.6
7.5°	394.7	388.2	382.0	375.0	369.2	363.2	359.4	356.2	354.2	351.4	349.5
10°	385.3	376.7	369.4	361.0	353.6	347.2	342.1	339.5	337.2	333.7	332.4
12.5°	373.8	364.9	355.9	346.9	339.8	332.7	328.4	324.5	322.8	318.9	318.5
15°	359.9	346.5	337.7	328.6	318.9	313.0	309.3	305.1	303.3	300.6	298.6
17.5°	343.3	331.4	320.4	310.9	302.6	297.7	293.1	290.3	287.1	285.3	282.0
20°	331.3	320.0	309.0	298.9	292.5	286.8	283.2	280.4	277.1	276.2	272.9
22.5°	321.2	308.7	298.2	289.7	282.7	276.3	272.4	270.5	268.2	265.4	264.7
25°	304.8	291.8	282.8	274.4	268.2	262.3	259.6	257.2	255.0	252.9	252.2
27.5°	290.6	278.9	268.3	260.7	255.2	249.9	247.6	244.6	243.0	241.4	239.4
30°	280.6	268.7	259.4	252.1	246.2	241.5	238.8	236.9	235.4	233.9	232.8
32.5°	270.4	259.4	250.3	243.1	237.3	233.7	231.4	230.0	228.4	226.6	225.2
35°	256.8	244.7	235.9	229.7	225.1	222.4	219.8	218.6	216.7	216.7	215.2
37.5°	241.5	231.1	223.3	217.7	213.6	211.1	208.3	207.5	206.3	205.5	205.0
40°	232.5	222.8	215.5	209.8	205.4	203.4	201.1	199.7	199.0	198.0	197.7
42.5°	223.1	213.8	206.8	201.6	197.7	196.1	194.0	193.0	191.5	190.3	190.0
45°	208.8	199.9	193.5	189.3	186.0	183.9	182.7	180.5	179.7	178.3	178.1
47.5°	195.4	186.7	180.5	177.0	174.1	172.5	170.5	168.3	167.4	166.7	166.6
50°	185.2	177.4	171.5	168.3	165.5	163.1	161.1	159.6	159.1	159.1	159.5
52.5°	175.0	168.3	163.3	159.3	156.7	154.2	152.3	151.4	150.6	151.5	152.1
55°	160.0	153.2	149.6	145.7	143.1	140.2	139.3	138.9	138.4	139.8	140.6
57.5°	144.1	139.3	135.1	131.3	129.0	127.2	126.0	125.8	126.8	127.5	129.9
60°	134.0	128.5	124.7	121.8	119.0	117.9	117.5	117.2	117.9	119.9	123.0
62.5°	122.9	118.4	114.2	112.1	110.0	108.2	108.1	108.4	109.8	112.2	115.3
65°	106.5	102.7	100.0	97.4	95.7	94.7	95.0	95.7	97.4	100.5	103.9
67.5°	89.9	87.3	84.8	82.8	81.2	81.2	81.6	82.7	84.6	88.2	91.3
70°	79.3	76.4	74.3	73.4	72.1	71.4	72.5	74.3	76.0	79.3	82.0
72.5°	68.6	66.1	64.5	63.8	63.3	62.7	63.1	65.1	67.3	70.6	73.8
75°	52.7	51.8	50.7	50.0	49.4	49.8	50.1	52.0	53.8	57.3	60.9
77.5°	38.5	37.5	36.8	36.7	36.4	36.6	37.6	39.0	40.7	43.3	46.0
80°	29.1	28.8	28.4	28.2	28.2	28.4	29.9	30.7	32.4	34.8	37.0
82.5°	21.2	21.0	20.9	20.8	21.0	21.1	21.9	23.1	24.5	26.3	28.2
85°	11.2	10.8	11.3	11.6	11.2	11.7	12.1	12.8	13.4	14.3	15.2
87.5°	4.7	5.1	5.2	5.5	5.8	6.3	6.3	7.0	7.4	7.8	7.8
90°	5.0	6.0	7.1	8.0	9.0	9.9	10.6	11.2	12.0	12.7	13.2
92.5°	18.1	19.0	20.2	21.4	22.6	23.8	24.7	25.6	26.5	27.4	28.0
95°	41.4	42.2	43.6	44.9	46.3	47.7	48.6	49.6	50.6	51.6	52.2
97.5°	67.3	68.4	70.3	72.2	74.1	76.0	76.8	77.8	78.7	79.6	80.1
100°	86.7	87.6	89.4	91.2	93.0	94.7	96.0	97.3	98.5	99.7	100.5
102.5°	110.3	111.0	111.9	112.8	113.7	114.6	116.0	117.3	118.7	120.0	120.9
105°	144.0	144.7	145.6	146.4	147.2	148.1	148.9	149.7	150.5	151.4	151.9
107.5°	180.7	181.3	182.0	182.6	183.2	183.9	184.3	184.7	185.1	185.5	185.7
110°	206.0	206.5	206.9	207.3	207.7	208.1	208.6	209.0	209.4	209.8	209.9



TEST NUMBER: P333134-927

CATALOG NUMBER: S125DIP-S375D810U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	230.4	230.8	231.3	231.9	232.4	232.9	233.1	233.3	233.5	233.7	233.7
115°	269.2	269.6	269.9	270.1	270.5	270.7	270.5	270.5	270.3	270.1	270.0
117.5°	306.1	306.4	306.7	306.9	307.1	307.4	307.4	307.6	307.7	307.8	307.6
120°	331.7	332.1	332.2	332.4	332.5	332.6	332.6	332.6	332.6	332.6	332.4
122.5°	355.7	356.0	356.3	356.7	357.0	357.4	357.3	357.2	357.1	357.0	356.7
125°	392.9	393.4	393.6	393.7	393.8	394.0	393.7	393.4	393.2	392.8	392.7
127.5°	428.6	429.0	429.1	429.3	429.5	429.7	429.5	429.4	429.2	429.1	428.9
130°	451.9	452.3	452.6	452.9	453.1	453.4	453.3	453.1	453.0	452.9	452.7
132.5°	475.9	476.4	476.4	476.3	476.3	476.3	476.1	475.9	475.8	475.7	475.4
135°	510.0	510.5	510.6	510.8	510.9	511.0	511.0	511.0	511.0	511.0	510.8
137.5°	543.1	543.7	544.0	544.2	544.5	544.9	545.0	545.2	545.3	545.5	545.3
140°	564.0	564.5	564.9	565.4	565.8	566.2	566.5	566.7	567.0	567.3	567.0
142.5°	584.9	585.4	585.9	586.5	586.9	587.5	587.6	587.8	588.0	588.1	587.9
145°	616.1	616.6	617.0	617.3	617.8	618.2	618.2	618.2	618.2	618.2	618.0
147.5°	644.0	644.4	644.8	645.1	645.4	645.7	646.0	646.3	646.7	647.1	646.7
150°	661.6	661.9	662.4	663.0	663.5	664.1	664.1	664.1	664.1	664.1	663.9
152.5°	678.8	679.1	679.2	679.5	679.7	679.9	680.2	680.6	680.9	681.2	681.1
155°	702.4	702.5	702.7	702.8	702.9	703.1	703.6	704.2	704.7	705.3	705.2
157.5°	723.0	722.9	723.1	723.3	723.3	723.5	724.1	724.6	725.2	725.7	725.6
160°	735.5	735.4	735.5	735.6	735.8	735.9	736.5	737.0	737.5	738.1	738.1
162.5°	747.3	747.2	747.2	747.3	747.3	747.3	748.0	748.6	749.3	750.0	749.9
165°	762.7	762.6	762.7	762.9	763.0	763.2	763.7	764.3	764.9	765.3	765.2
167.5°	774.4	774.2	774.2	774.2	774.2	774.2	775.0	775.9	776.7	777.5	777.4
170°	781.4	781.1	781.1	781.1	781.1	781.1	782.0	782.8	783.6	784.4	784.3
172.5°	786.3	786.1	786.1	786.1	786.1	786.1	786.9	787.7	788.5	789.4	789.4
175°	791.9	791.6	791.6	791.6	791.6	791.6	792.5	793.3	794.2	795.0	794.9
177.5°	795.2	795.0	794.9	794.7	794.6	794.5	795.2	795.8	796.5	797.2	797.1
180°	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0



TEST NUMBER: P333134-927

CATALOG NUMBER: S125DIP-S375D810U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3
2.5°	410.9	411.9	411.1	412.3	411.1	411.9	410.9	411.8	413.1	412.3	414.3
5°	378.7	377.1	378.2	377.5	378.2	377.1	378.7	379.6	381.8	382.5	384.0
7.5°	349.0	347.5	345.6	344.8	345.6	347.5	349.0	349.5	351.4	354.2	356.2
10°	330.4	328.4	328.2	326.9	328.2	328.4	330.4	332.4	333.7	337.2	339.5
12.5°	316.8	314.9	312.8	312.3	312.8	314.9	316.8	318.5	318.9	322.8	324.5
15°	297.5	296.0	294.7	295.8	294.7	296.0	297.5	298.6	300.6	303.3	305.1
17.5°	281.4	280.2	280.0	278.6	280.0	280.2	281.4	282.0	285.3	287.1	290.3
20°	271.2	270.4	270.8	268.3	270.8	270.4	271.2	272.9	276.2	277.1	280.4
22.5°	263.2	261.4	261.2	260.7	261.2	261.4	263.2	264.7	265.4	268.2	270.5
25°	250.6	249.7	248.7	249.7	248.7	249.7	250.6	252.2	252.9	255.0	257.2
27.5°	239.6	238.4	238.2	238.4	238.2	238.4	239.6	239.4	241.4	243.0	244.6
30°	232.8	231.0	231.2	231.0	231.2	231.0	232.8	232.8	233.9	235.4	236.9
32.5°	225.5	224.3	224.0	223.7	224.0	224.3	225.5	225.2	226.6	228.4	230.0
35°	214.7	214.7	213.8	213.8	213.8	214.7	214.7	215.2	216.7	216.7	218.6
37.5°	204.5	204.4	203.8	203.9	203.8	204.4	204.5	205.0	205.5	206.3	207.5
40°	196.9	196.8	196.2	195.1	196.2	196.8	196.9	197.7	198.0	199.0	199.7
42.5°	189.6	189.0	188.8	188.4	188.8	189.0	189.6	190.0	190.3	191.5	193.0
45°	178.1	178.1	177.8	177.5	177.8	178.1	178.1	178.1	178.3	179.7	180.5
47.5°	166.9	167.2	167.9	167.8	167.9	167.2	166.9	166.6	166.7	167.4	168.3
50°	160.2	160.3	160.9	161.1	160.9	160.3	160.2	159.5	159.1	159.1	159.6
52.5°	152.7	153.8	154.5	154.3	154.5	153.8	152.7	152.1	151.5	150.6	151.4
55°	142.2	143.5	144.8	145.0	144.8	143.5	142.2	140.6	139.8	138.4	138.9
57.5°	131.9	133.6	135.0	135.5	135.0	133.6	131.9	129.9	127.5	126.8	125.8
60°	124.8	127.2	128.9	129.6	128.9	127.2	124.8	123.0	119.9	117.9	117.2
62.5°	118.1	120.8	122.4	122.6	122.4	120.8	118.1	115.3	112.2	109.8	108.4
65°	107.1	109.8	111.3	112.4	111.3	109.8	107.1	103.9	100.5	97.4	95.7
67.5°	95.2	98.0	99.6	100.4	99.6	98.0	95.2	91.3	88.2	84.6	82.7
70°	86.6	89.4	91.5	92.3	91.5	89.4	86.6	82.0	79.3	76.0	74.3
72.5°	78.1	80.6	82.3	83.2	82.3	80.6	78.1	73.8	70.6	67.3	65.1
75°	63.3	66.6	68.3	69.2	68.3	66.6	63.3	60.9	57.3	53.8	52.0
77.5°	48.8	51.8	52.8	53.3	52.8	51.8	48.8	46.0	43.3	40.7	39.0
80°	39.1	41.0	42.3	42.5	42.3	41.0	39.1	37.0	34.8	32.4	30.7
82.5°	30.1	31.6	32.0	32.5	32.0	31.6	30.1	28.2	26.3	24.5	23.1
85°	16.5	17.2	17.4	17.2	17.4	17.2	16.5	15.2	14.3	13.4	12.8
87.5°	8.2	8.1	8.2	8.6	8.2	8.1	8.2	7.8	7.8	7.4	7.0
90°	13.6	14.0	14.4	14.9	14.4	14.0	13.6	13.2	12.7	12.0	11.2
92.5°	28.4	28.6	28.9	29.2	28.9	28.6	28.4	28.0	27.4	26.5	25.6
95°	52.4	52.8	53.0	53.2	53.0	52.8	52.4	52.2	51.6	50.6	49.6
97.5°	80.2	80.4	80.6	80.8	80.6	80.4	80.2	80.1	79.6	78.7	77.8
100°	100.8	101.0	101.3	101.6	101.3	101.0	100.8	100.5	99.7	98.5	97.3
102.5°	121.3	121.6	122.0	122.4	122.0	121.6	121.3	120.9	120.0	118.7	117.3
105°	152.4	152.8	153.2	153.6	153.2	152.8	152.4	151.9	151.4	150.5	149.7
107.5°	185.7	185.6	185.6	185.6	185.6	185.6	185.7	185.7	185.5	185.1	184.7
110°	209.8	209.6	209.5	209.4	209.5	209.6	209.8	209.9	209.8	209.4	209.0



TEST NUMBER: P333134-927

CATALOG NUMBER: S125DIP-S375D810U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	233.4	233.1	232.9	232.7	232.9	233.1	233.4	233.7	233.7	233.5	233.3
115°	269.9	269.7	269.6	269.5	269.6	269.7	269.9	270.0	270.1	270.3	270.5
117.5°	307.0	306.5	305.9	305.4	305.9	306.5	307.0	307.6	307.8	307.7	307.6
120°	331.8	331.3	330.7	330.2	330.7	331.3	331.8	332.4	332.6	332.6	332.6
122.5°	356.2	355.8	355.4	355.0	355.4	355.8	356.2	356.7	357.0	357.1	357.2
125°	392.5	392.4	392.3	392.1	392.3	392.4	392.5	392.7	392.8	393.2	393.4
127.5°	428.6	428.3	428.1	427.8	428.1	428.3	428.6	428.9	429.1	429.2	429.4
130°	452.4	452.1	451.9	451.5	451.9	452.1	452.4	452.7	452.9	453.0	453.1
132.5°	475.1	474.7	474.3	473.9	474.3	474.7	475.1	475.4	475.7	475.8	475.9
135°	510.2	509.7	509.1	508.6	509.1	509.7	510.2	510.8	511.0	511.0	511.0
137.5°	544.5	543.9	543.2	542.5	543.2	543.9	544.5	545.3	545.5	545.3	545.2
140°	566.4	565.7	565.0	564.4	565.0	565.7	566.4	567.0	567.3	567.0	566.7
142.5°	587.2	586.5	585.8	585.1	585.8	586.5	587.2	587.9	588.1	588.0	587.8
145°	617.6	617.2	616.8	616.3	616.8	617.2	617.6	618.0	618.2	618.2	618.2
147.5°	645.8	644.8	644.0	643.0	644.0	644.8	645.8	646.7	647.1	646.7	646.3
150°	663.6	663.4	663.1	662.8	663.1	663.4	663.6	663.9	664.1	664.1	664.1
152.5°	680.6	680.2	679.7	679.1	679.7	680.2	680.6	681.1	681.2	680.9	680.6
155°	704.5	703.9	703.1	702.4	703.1	703.9	704.5	705.2	705.3	704.7	704.2
157.5°	724.6	723.7	722.8	721.9	722.8	723.7	724.6	725.6	725.7	725.2	724.6
160°	737.4	736.7	735.9	735.3	735.9	736.7	737.4	738.1	738.1	737.5	737.0
162.5°	749.1	748.3	747.5	746.7	747.5	748.3	749.1	749.9	750.0	749.3	748.6
165°	764.4	763.6	762.7	761.9	762.7	763.6	764.4	765.2	765.3	764.9	764.3
167.5°	776.7	775.8	774.9	774.0	774.9	775.8	776.7	777.4	777.5	776.7	775.9
170°	783.4	782.4	781.5	780.5	781.5	782.4	783.4	784.3	784.4	783.6	782.8
172.5°	788.5	787.7	786.8	785.9	786.8	787.7	788.5	789.4	789.4	788.5	787.7
175°	793.9	793.0	792.0	791.1	792.0	793.0	793.9	794.9	795.0	794.2	793.3
177.5°	796.3	795.6	794.8	794.0	794.8	795.6	796.3	797.1	797.2	796.5	795.8
180°	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0



TEST NUMBER: P333134-927

CATALOG NUMBER: S125DIP-S375D810U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3
2.5°	412.4	414.2	416.3	418.0	420.9	422.2	423.8	425.1	427.5	429.7	432.3
5°	384.6	387.7	391.9	396.5	401.8	405.4	410.6	413.7	419.9	425.6	431.1
7.5°	359.4	363.2	369.2	375.0	382.0	388.2	394.7	401.8	409.7	419.1	426.9
10°	342.1	347.2	353.6	361.0	369.4	376.7	385.3	393.0	402.7	413.7	424.0
12.5°	328.4	332.7	339.8	346.9	355.9	364.9	373.8	383.9	395.2	407.4	420.3
15°	309.3	313.0	318.9	328.6	337.7	346.5	359.9	369.4	383.7	397.2	412.8
17.5°	293.1	297.7	302.6	310.9	320.4	331.4	343.3	355.3	369.0	386.2	403.7
20°	283.2	286.8	292.5	298.9	309.0	320.0	331.3	343.4	360.2	378.0	396.9
22.5°	272.4	276.3	282.7	289.7	298.2	308.7	321.2	334.5	352.0	369.5	390.0
25°	259.6	262.3	268.2	274.4	282.8	291.8	304.8	319.4	336.8	356.8	377.6
27.5°	247.6	249.9	255.2	260.7	268.3	278.9	290.6	305.4	321.8	342.0	365.1
30°	238.8	241.5	246.2	252.1	259.4	268.7	280.6	294.5	312.1	331.8	356.0
32.5°	231.4	233.7	237.3	243.1	250.3	259.4	270.4	284.6	302.1	322.2	345.9
35°	219.8	222.4	225.1	229.7	235.9	244.7	256.8	270.2	287.0	306.4	328.2
37.5°	208.3	211.1	213.6	217.7	223.3	231.1	241.5	255.5	270.7	289.4	310.3
40°	201.1	203.4	205.4	209.8	215.5	222.8	232.5	244.9	261.0	278.5	295.8
42.5°	194.0	196.1	197.7	201.6	206.8	213.8	223.1	235.3	250.2	266.4	281.8
45°	182.7	183.9	186.0	189.3	193.5	199.9	208.8	219.7	232.3	247.6	259.2
47.5°	170.5	172.5	174.1	177.0	180.5	186.7	195.4	204.5	216.0	227.4	235.5
50°	161.1	163.1	165.5	168.3	171.5	177.4	185.2	194.6	204.3	213.1	220.0
52.5°	152.3	154.2	156.7	159.3	163.3	168.3	175.0	183.3	192.9	199.2	204.9
55°	139.3	140.2	143.1	145.7	149.6	153.2	160.0	167.3	173.2	177.9	182.7
57.5°	126.0	127.2	129.0	131.3	135.1	139.3	144.1	150.6	154.0	156.5	160.2
60°	117.5	117.9	119.0	121.8	124.7	128.5	134.0	138.6	141.2	143.1	146.2
62.5°	108.1	108.2	110.0	112.1	114.2	118.4	122.9	126.6	128.7	129.7	132.6
65°	95.0	94.7	95.7	97.4	100.0	102.7	106.5	109.8	109.6	110.7	112.6
67.5°	81.6	81.2	81.2	82.8	84.8	87.3	89.9	91.9	91.9	93.3	94.3
70°	72.5	71.4	72.1	73.4	74.3	76.4	79.3	80.0	80.2	80.9	81.8
72.5°	63.1	62.7	63.3	63.8	64.5	66.1	68.6	69.0	69.1	69.5	71.0
75°	50.1	49.8	49.4	50.0	50.7	51.8	52.7	53.5	53.2	53.5	54.6
77.5°	37.6	36.6	36.4	36.7	36.8	37.5	38.5	38.4	38.6	38.6	39.8
80°	29.9	28.4	28.2	28.2	28.4	28.8	29.1	29.5	28.9	29.5	29.9
82.5°	21.9	21.1	21.0	20.8	20.9	21.0	21.2	21.4	21.3	21.5	21.8
85°	12.1	11.7	11.2	11.6	11.3	10.8	11.2	10.6	10.5	10.6	10.8
87.5°	6.3	6.3	5.8	5.5	5.2	5.1	4.7	4.3	4.0	3.9	4.0
90°	10.6	9.9	9.0	8.0	7.1	6.0	5.0	4.0	2.9	1.7	0.6
92.5°	24.7	23.8	22.6	21.4	20.2	19.0	18.1	17.3	16.6	15.8	15.0
95°	48.6	47.7	46.3	44.9	43.6	42.2	41.4	41.1	40.8	40.6	40.2
97.5°	76.8	76.0	74.1	72.2	70.3	68.4	67.3	67.3	67.1	67.0	66.9
100°	96.0	94.7	93.0	91.2	89.4	87.6	86.7	86.7	86.7	86.7	86.7
102.5°	116.0	114.6	113.7	112.8	111.9	111.0	110.3	109.7	109.2	108.6	108.1
105°	148.9	148.1	147.2	146.4	145.6	144.7	144.0	143.3	142.6	142.0	141.2
107.5°	184.3	183.9	183.2	182.6	182.0	181.3	180.7	180.0	179.3	178.6	177.9
110°	208.6	208.1	207.7	207.3	206.9	206.5	206.0	205.3	204.5	203.9	203.2



TEST NUMBER: P333134-927

CATALOG NUMBER: S125DIP-S375D810U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	233.1	232.9	232.4	231.9	231.3	230.8	230.4	230.0	229.7	229.3	228.9
115°	270.5	270.7	270.5	270.1	269.9	269.6	269.2	268.6	268.1	267.5	267.0
117.5°	307.4	307.4	307.1	306.9	306.7	306.4	306.1	305.9	305.6	305.4	305.1
120°	332.6	332.6	332.5	332.4	332.2	332.1	331.7	331.0	330.3	329.6	328.9
122.5°	357.3	357.4	357.0	356.7	356.3	356.0	355.7	355.5	355.2	355.0	354.7
125°	393.7	394.0	393.8	393.7	393.6	393.4	392.9	392.1	391.3	390.5	389.6
127.5°	429.5	429.7	429.5	429.3	429.1	429.0	428.6	428.2	427.7	427.3	426.8
130°	453.3	453.4	453.1	452.9	452.6	452.3	451.9	451.1	450.5	449.8	449.1
132.5°	476.1	476.3	476.3	476.3	476.4	476.4	475.9	474.8	473.6	472.5	471.4
135°	511.0	511.0	510.9	510.8	510.6	510.5	510.0	509.2	508.3	507.6	506.7
137.5°	545.0	544.9	544.5	544.2	544.0	543.7	543.1	542.3	541.5	540.7	540.0
140°	566.5	566.2	565.8	565.4	564.9	564.5	564.0	563.3	562.6	561.9	561.3
142.5°	587.6	587.5	586.9	586.5	585.9	585.4	584.9	584.2	583.7	583.1	582.6
145°	618.2	618.2	617.8	617.3	617.0	616.6	616.1	615.5	615.0	614.4	613.9
147.5°	646.0	645.7	645.4	645.1	644.8	644.4	644.0	643.8	643.5	643.2	642.9
150°	664.1	664.1	663.5	663.0	662.4	661.9	661.6	661.8	661.9	662.0	662.2
152.5°	680.2	679.9	679.7	679.5	679.2	679.1	678.8	678.7	678.4	678.3	678.0
155°	703.6	703.1	702.9	702.8	702.7	702.5	702.4	702.4	702.4	702.4	702.4
157.5°	724.1	723.5	723.3	723.3	723.1	722.9	723.0	723.3	723.7	724.0	724.3
160°	736.5	735.9	735.8	735.6	735.5	735.4	735.5	735.9	736.3	736.7	737.1
162.5°	748.0	747.3	747.3	747.3	747.2	747.2	747.3	747.7	747.9	748.2	748.5
165°	763.7	763.2	763.0	762.9	762.7	762.6	762.7	763.0	763.3	763.5	763.8
167.5°	775.0	774.2	774.2	774.2	774.2	774.2	774.4	775.0	775.5	776.1	776.7
170°	782.0	781.1	781.1	781.1	781.1	781.1	781.4	782.0	782.5	783.1	783.6
172.5°	786.9	786.1	786.1	786.1	786.1	786.1	786.3	786.9	787.4	788.0	788.5
175°	792.5	791.6	791.6	791.6	791.6	791.6	791.9	792.5	793.1	793.6	794.2
177.5°	795.2	794.5	794.6	794.7	794.9	795.0	795.2	795.7	796.1	796.5	797.0
180°	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0



TEST NUMBER: P333134-927

CATALOG NUMBER: S125DIP-S375D810U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3
2.5°	433.6	435.6	437.0	439.4	441.5	442.7	443.7	444.6	445.6	446.5	449.0
5°	436.4	441.2	445.2	451.4	457.1	461.4	466.2	470.4	473.9	478.9	482.7
7.5°	435.1	443.6	452.5	462.2	472.0	481.1	489.6	497.4	504.5	513.2	520.8
10°	434.0	445.5	456.9	469.9	483.2	494.6	505.2	516.0	523.9	534.9	544.2
12.5°	433.2	446.7	460.4	476.0	490.7	506.8	520.9	528.8	540.7	549.5	560.6
15°	429.4	447.3	466.2	483.8	504.7	519.5	532.0	547.3	558.5	569.7	581.7
17.5°	422.8	443.1	464.2	487.3	507.2	523.2	539.2	554.1	567.4	582.3	597.4
20°	419.7	440.1	464.2	487.8	507.4	524.0	540.5	556.8	571.5	590.7	608.1
22.5°	413.3	437.8	460.1	483.2	503.3	521.4	540.1	558.6	578.1	599.8	621.5
25°	401.8	426.7	450.3	473.0	493.3	516.0	536.0	560.7	585.6	614.3	641.4
27.5°	389.8	413.7	435.3	457.2	480.9	506.7	532.5	560.5	593.2	629.5	667.7
30°	380.2	402.7	423.7	446.2	471.0	499.9	528.3	561.6	599.3	640.1	685.6
32.5°	368.9	389.7	410.1	434.0	460.9	491.4	524.5	561.0	606.3	652.7	699.4
35°	349.6	367.0	388.1	413.5	443.9	478.9	517.1	560.3	612.3	665.6	704.9
37.5°	326.8	342.9	365.1	393.0	424.8	462.4	507.8	559.0	614.3	656.7	669.4
40°	311.3	326.4	349.4	378.3	410.9	450.7	500.4	554.6	608.1	635.2	624.7
42.5°	294.9	310.7	333.2	361.8	396.9	440.1	491.2	545.4	590.3	600.5	564.4
45°	269.1	285.3	307.5	336.4	374.1	421.0	474.3	523.6	549.3	530.8	475.0
47.5°	245.0	260.3	280.8	310.7	349.6	398.1	449.3	488.6	490.7	446.6	386.9
50°	228.6	242.7	263.4	293.3	331.8	381.0	427.2	458.2	444.3	394.3	337.0
52.5°	212.5	226.3	246.7	276.2	314.4	359.4	402.5	424.2	398.0	346.7	297.8
55°	189.3	201.4	221.3	248.6	284.8	326.5	363.1	370.7	336.6	286.1	246.4
57.5°	166.6	177.8	196.0	221.1	254.3	291.2	319.9	318.2	282.3	238.9	207.4
60°	151.2	162.2	178.3	202.8	233.1	264.9	289.4	283.5	247.9	210.5	183.9
62.5°	137.4	147.3	162.5	183.9	211.5	241.0	261.1	252.5	217.5	184.9	163.9
65°	117.2	125.4	138.4	156.7	179.6	203.9	219.5	208.3	178.5	153.0	136.2
67.5°	97.8	104.4	115.3	129.9	149.4	169.0	178.4	167.2	143.3	124.8	112.3
70°	85.5	91.3	99.7	112.7	129.8	146.2	153.4	143.3	122.8	106.9	97.9
72.5°	73.2	78.0	85.4	97.1	110.7	125.0	131.3	121.7	104.8	91.3	83.0
75°	56.6	59.9	65.0	73.0	83.8	95.2	98.6	90.2	79.5	69.4	63.8
77.5°	40.5	43.3	47.1	52.2	59.9	67.1	70.1	65.3	57.0	50.5	46.0
80°	31.1	32.6	35.9	40.1	46.1	50.7	52.7	49.6	43.7	39.0	35.5
82.5°	22.2	23.7	25.6	29.1	33.0	36.0	38.2	36.1	31.9	28.1	26.1
85°	10.8	11.7	12.8	14.3	17.2	19.0	18.9	17.6	15.9	14.5	13.4
87.5°	4.1	4.5	5.1	6.1	6.8	7.5	8.0	7.9	7.5	7.2	7.0
90°	1.7	2.9	4.0	5.0	6.0	7.1	8.0	9.0	9.9	10.6	11.2
92.5°	15.8	16.6	17.3	18.1	19.0	20.2	21.4	22.6	23.8	24.7	25.6
95°	40.6	40.8	41.1	41.4	42.2	43.6	44.9	46.3	47.7	48.6	49.6
97.5°	67.0	67.1	67.3	67.3	68.4	70.3	72.2	74.1	76.0	76.8	77.8
100°	86.7	86.7	86.7	86.7	87.6	89.4	91.2	93.0	94.7	96.0	97.3
102.5°	108.6	109.2	109.7	110.3	111.0	111.9	112.8	113.7	114.6	116.0	117.3
105°	142.0	142.6	143.3	144.0	144.7	145.6	146.4	147.2	148.1	148.9	149.7
107.5°	178.6	179.3	180.0	180.7	181.3	182.0	182.6	183.2	183.9	184.3	184.7
110°	203.9	204.5	205.3	206.0	206.5	206.9	207.3	207.7	208.1	208.6	209.0





TEST NUMBER: P333134-927

CATALOG NUMBER: S125DIP-S375D810U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	229.3	229.7	230.0	230.4	230.8	231.3	231.9	232.4	232.9	233.1	233.3
115°	267.5	268.1	268.6	269.2	269.6	269.9	270.1	270.5	270.7	270.5	270.5
117.5°	305.4	305.6	305.9	306.1	306.4	306.7	306.9	307.1	307.4	307.4	307.6
120°	329.6	330.3	331.0	331.7	332.1	332.2	332.4	332.5	332.6	332.6	332.6
122.5°	355.0	355.2	355.5	355.7	356.0	356.3	356.7	357.0	357.4	357.3	357.2
125°	390.5	391.3	392.1	392.9	393.4	393.6	393.7	393.8	394.0	393.7	393.4
127.5°	427.3	427.7	428.2	428.6	429.0	429.1	429.3	429.5	429.7	429.5	429.4
130°	449.8	450.5	451.1	451.9	452.3	452.6	452.9	453.1	453.4	453.3	453.1
132.5°	472.5	473.6	474.8	475.9	476.4	476.4	476.3	476.3	476.3	476.1	475.9
135°	507.6	508.3	509.2	510.0	510.5	510.6	510.8	510.9	511.0	511.0	511.0
137.5°	540.7	541.5	542.3	543.1	543.7	544.0	544.2	544.5	544.9	545.0	545.2
140°	561.9	562.6	563.3	564.0	564.5	564.9	565.4	565.8	566.2	566.5	566.7
142.5°	583.1	583.7	584.2	584.9	585.4	585.9	586.5	586.9	587.5	587.6	587.8
145°	614.4	615.0	615.5	616.1	616.6	617.0	617.3	617.8	618.2	618.2	618.2
147.5°	643.2	643.5	643.8	644.0	644.4	644.8	645.1	645.4	645.7	646.0	646.3
150°	662.0	661.9	661.8	661.6	661.9	662.4	663.0	663.5	664.1	664.1	664.1
152.5°	678.3	678.4	678.7	678.8	679.1	679.2	679.5	679.7	679.9	680.2	680.6
155°	702.4	702.4	702.4	702.4	702.5	702.7	702.8	702.9	703.1	703.6	704.2
157.5°	724.0	723.7	723.3	723.0	722.9	723.1	723.3	723.3	723.5	724.1	724.6
160°	736.7	736.3	735.9	735.5	735.4	735.5	735.6	735.8	735.9	736.5	737.0
162.5°	748.2	747.9	747.7	747.3	747.2	747.2	747.3	747.3	747.3	748.0	748.6
165°	763.5	763.3	763.0	762.7	762.6	762.7	762.9	763.0	763.2	763.7	764.3
167.5°	776.1	775.5	775.0	774.4	774.2	774.2	774.2	774.2	774.2	775.0	775.9
170°	783.1	782.5	782.0	781.4	781.1	781.1	781.1	781.1	781.1	782.0	782.8
172.5°	788.0	787.4	786.9	786.3	786.1	786.1	786.1	786.1	786.1	786.9	787.7
175°	793.6	793.1	792.5	791.9	791.6	791.6	791.6	791.6	791.6	792.5	793.3
177.5°	796.5	796.1	795.7	795.2	795.0	794.9	794.7	794.6	794.5	795.2	795.8
180°	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0



TEST NUMBER: P333134-927

CATALOG NUMBER: S125DIP-S375D810U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	431.3	431.3	431.3	431.3	431.3	431.3	431.3
2.5°	451.1	452.2	454.7	453.8	455.0	455.6	456.1
5°	487.4	493.3	495.9	495.5	499.4	498.4	497.5
7.5°	528.6	534.7	538.2	542.5	544.9	545.2	547.3
10°	551.9	559.9	563.2	567.8	570.8	572.4	572.2
12.5°	569.7	576.1	583.4	585.7	589.6	591.8	591.0
15°	591.3	601.3	609.0	612.8	617.8	619.2	621.2
17.5°	610.5	623.9	632.9	644.8	649.4	652.1	650.5
20°	625.0	642.7	651.6	665.9	673.8	678.0	676.5
22.5°	642.1	661.3	677.9	690.2	702.2	707.9	709.1
25°	671.5	697.8	722.2	738.4	753.2	756.7	764.4
27.5°	704.3	735.3	761.4	778.5	788.8	792.7	795.1
30°	724.8	755.8	775.4	786.4	789.6	789.3	788.9
32.5°	735.0	754.3	758.1	755.0	747.5	741.1	734.4
35°	720.6	706.2	684.6	656.8	636.3	615.6	613.5
37.5°	648.2	601.9	565.9	525.8	502.6	488.3	478.4
40°	579.9	527.4	483.8	450.0	426.4	417.0	407.8
42.5°	505.8	455.6	417.0	388.7	371.0	360.6	353.4
45°	410.9	366.6	336.4	315.9	301.8	293.8	289.2
47.5°	336.8	304.0	278.3	263.5	253.8	247.6	247.6
50°	296.9	265.6	248.6	236.9	228.5	223.5	224.4
52.5°	261.6	238.2	223.7	213.9	207.6	204.6	204.5
55°	218.7	201.9	192.4	185.2	181.0	177.5	178.3
57.5°	187.1	172.9	166.5	160.6	157.6	156.3	154.2
60°	167.5	156.5	151.0	146.2	143.3	142.2	140.2
62.5°	150.0	141.4	136.1	132.2	129.6	129.2	127.6
65°	126.1	119.5	114.8	113.0	110.2	109.5	109.5
67.5°	103.9	99.3	95.5	93.9	92.7	92.8	92.0
70°	90.1	86.2	83.8	82.0	81.1	81.3	80.6
72.5°	78.8	74.5	72.4	71.3	70.1	70.6	70.3
75°	59.7	57.5	56.4	55.3	54.6	54.2	53.8
77.5°	43.8	41.9	41.0	40.4	40.6	39.6	40.3
80°	33.8	32.2	31.7	30.7	30.6	30.6	30.4
82.5°	24.8	23.8	23.4	22.7	22.3	22.7	22.2
85°	12.8	12.1	11.9	11.9	11.6	11.2	12.1
87.5°	7.1	6.7	6.7	6.7	6.7	6.7	6.5
90°	12.0	12.7	13.2	13.6	14.0	14.4	14.9
92.5°	26.5	27.4	28.0	28.4	28.6	28.9	29.2
95°	50.6	51.6	52.2	52.4	52.8	53.0	53.2
97.5°	78.7	79.6	80.1	80.2	80.4	80.6	80.8
100°	98.5	99.7	100.5	100.8	101.0	101.3	101.6
102.5°	118.7	120.0	120.9	121.3	121.6	122.0	122.4
105°	150.5	151.4	151.9	152.4	152.8	153.2	153.6
107.5°	185.1	185.5	185.7	185.7	185.6	185.6	185.6
110°	209.4	209.8	209.9	209.8	209.6	209.5	209.4



TEST NUMBER: P333134-927

CATALOG NUMBER: S125DIP-S375D810U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	233.5	233.7	233.7	233.4	233.1	232.9	232.7
115°	270.3	270.1	270.0	269.9	269.7	269.6	269.5
117.5°	307.7	307.8	307.6	307.0	306.5	305.9	305.4
120°	332.6	332.6	332.4	331.8	331.3	330.7	330.2
122.5°	357.1	357.0	356.7	356.2	355.8	355.4	355.0
125°	393.2	392.8	392.7	392.5	392.4	392.3	392.1
127.5°	429.2	429.1	428.9	428.6	428.3	428.1	427.8
130°	453.0	452.9	452.7	452.4	452.1	451.9	451.5
132.5°	475.8	475.7	475.4	475.1	474.7	474.3	473.9
135°	511.0	511.0	510.8	510.2	509.7	509.1	508.6
137.5°	545.3	545.5	545.3	544.5	543.9	543.2	542.5
140°	567.0	567.3	567.0	566.4	565.7	565.0	564.4
142.5°	588.0	588.1	587.9	587.2	586.5	585.8	585.1
145°	618.2	618.2	618.0	617.6	617.2	616.8	616.3
147.5°	646.7	647.1	646.7	645.8	644.8	644.0	643.0
150°	664.1	664.1	663.9	663.6	663.4	663.1	662.8
152.5°	680.9	681.2	681.1	680.6	680.2	679.7	679.1
155°	704.7	705.3	705.2	704.5	703.9	703.1	702.4
157.5°	725.2	725.7	725.6	724.6	723.7	722.8	721.9
160°	737.5	738.1	738.1	737.4	736.7	735.9	735.3
162.5°	749.3	750.0	749.9	749.1	748.3	747.5	746.7
165°	764.9	765.3	765.2	764.4	763.6	762.7	761.9
167.5°	776.7	777.5	777.4	776.7	775.8	774.9	774.0
170°	783.6	784.4	784.3	783.4	782.4	781.5	780.5
172.5°	788.5	789.4	789.4	788.5	787.7	786.8	785.9
175°	794.2	795.0	794.9	793.9	793.0	792.0	791.1
177.5°	796.5	797.2	797.1	796.3	795.6	794.8	794.0
180°	796.0	796.0	796.0	796.0	796.0	796.0	796.0

(END OF REPORT)