

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333234-927

Luminaire Tested: **S125DIP-S850D1035U927-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333234-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIP-S850D1035U927-4F0-1E-UDD-A4  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 850 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 1035 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5678.4 lumens  
Efficiency: N/A  
Efficacy: 109.2 lumens/watt  
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 52  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333234-927

CATALOG NUMBER: S125DIP-S850D1035U927-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P333234-927

CATALOG NUMBER: S125DIP-S850D1035U927-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	54	54	54	48
1	98	93	90	86	90	86	83	80	72	70	68	60	58	57	48	47	46	41
2	89	82	76	71	82	76	70	66	64	60	57	53	50	48	43	41	39	35
3	81	72	65	59	75	67	60	55	56	52	48	47	44	41	38	36	34	30
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	34	31	29	25
5	68	57	49	43	63	53	46	40	45	39	35	38	34	30	31	28	25	22
6	63	51	43	37	58	47	40	35	40	35	31	34	30	27	28	25	22	20
7	58	46	38	33	53	43	36	31	37	31	27	31	27	24	26	22	20	17
8	54	42	34	29	50	39	32	27	33	28	24	28	24	21	23	20	18	16
9	50	38	31	26	46	36	29	24	31	25	22	26	22	19	22	18	16	14
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	15	13

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	6259	6259	6259	6259
5°	7248	6280	5499	6280
10°	8433	6248	4818	6248
15°	9335	6202	4444	6202
20°	10449	6129	4144	6129
25°	12241	6047	3998	6047
30°	13221	5967	3871	5967
35°	10871	5815	3788	5815
40°	7727	5604	3697	5604
45°	5936	5320	3644	5320
50°	5067	4967	3636	4967
55°	4512	4622	3668	4622
60°	4070	4246	3761	4246
65°	3759	3865	3859	3865
70°	3418	3473	3914	3473
75°	3019	3059	3880	3059
80°	2540	2492	3552	2492
85°	2016	1793	2868	1793



TEST NUMBER: P333234-927

CATALOG NUMBER: S125DIP-S850D1035U927-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	93.3	1.6
10°-20°	277.8	4.9
20°-30°	451.1	7.9
30°-40°	550.2	9.7
40°-50°	500.5	8.8
50°-60°	398.7	7.0
60°-70°	277.7	4.9
70°-80°	148.1	2.6
80°-90°	39.6	0.7
90°-100°	284.3	5.0
100°-110°	611.2	10.8
110°-120°	573.6	10.1
120°-130°	464.9	8.2
130°-140°	373.0	6.6
140°-150°	281.5	5.0
150°-160°	198.2	3.5
160°-170°	116.8	2.1
170°-180°	38.0	0.7
0°-30°	822.1	14.5
0°-40°	1372.3	24.2
0°-60°	2271.6	40.0
0°-90°	2736.9	48.2
90°-120°	1469.1	25.9
90°-150°	2588.5	45.6
90°-180°	2941.0	51.8
0°-180°	5678.4	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	969	969	969	969	969	
5°	1118	969	848	969	1118	113
15°	1396	928	665	928	1396	400
25°	1718	849	561	849	1718	785
35°	1379	738	480	738	1379	844
45°	650	582	399	582	650	520
55°	401	410	326	410	401	361
65°	246	253	252	253	246	244
75°	121	123	156	123	121	130
85°	27	24	39	24	27	32
90°	18	1	18	1	18	13
95°	186	26	186	26	186	263
105°	1048	89	1048	89	1048	1042
115°	1167	160	1167	160	1167	1140
125°	920	221	920	221	920	832
135°	764	259	764	259	764	592
145°	603	302	603	302	603	383
155°	505	345	505	345	505	236
165°	443	376	443	376	443	127
175°	398	391	398	391	398	39
180°	392	392	392	392	392	



TEST NUMBER: P333234-927

CATALOG NUMBER: S125DIP-S850D1035U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2
2.5°	1025.1	1023.7	1022.5	1019.8	1021.8	1016.2	1013.5	1008.9	1003.4	1001.4	999.1
5°	1118.0	1120.1	1122.1	1113.5	1114.4	1108.6	1095.4	1084.7	1076.1	1065.0	1057.2
7.5°	1229.9	1225.0	1224.6	1219.1	1209.4	1201.7	1187.9	1170.3	1153.3	1133.9	1117.8
10°	1285.9	1286.3	1282.5	1276.0	1265.7	1258.3	1240.2	1222.9	1202.0	1177.3	1159.6
12.5°	1328.0	1329.7	1325.0	1316.1	1311.1	1294.5	1280.3	1259.8	1234.9	1215.1	1188.2
15°	1396.1	1391.5	1388.3	1377.2	1368.6	1351.3	1328.6	1307.3	1280.1	1255.0	1229.9
17.5°	1461.7	1465.4	1459.2	1449.1	1422.3	1402.1	1371.7	1342.4	1308.7	1275.0	1245.1
20°	1520.4	1523.6	1514.2	1496.5	1464.4	1444.2	1404.3	1366.5	1327.4	1284.2	1251.3
22.5°	1593.4	1590.8	1578.0	1551.1	1523.3	1486.1	1442.8	1396.8	1347.8	1299.0	1255.3
25°	1717.8	1700.5	1692.7	1659.4	1622.8	1568.0	1508.8	1441.4	1380.5	1315.9	1260.0
27.5°	1786.7	1781.3	1772.6	1749.4	1710.9	1652.4	1582.5	1500.3	1414.4	1332.9	1259.7
30°	1772.9	1773.7	1774.6	1767.1	1742.5	1698.4	1629.0	1540.5	1438.4	1346.7	1262.0
32.5°	1650.5	1665.5	1679.7	1696.7	1703.6	1695.2	1651.6	1571.8	1466.8	1362.6	1260.7
35°	1378.8	1383.4	1429.8	1475.9	1538.4	1587.0	1619.5	1584.1	1495.6	1375.9	1259.1
37.5°	1075.1	1097.3	1129.5	1181.5	1271.8	1352.6	1456.5	1504.3	1475.8	1380.3	1256.2
40°	916.5	937.1	958.0	1011.1	1087.2	1185.1	1303.1	1403.9	1427.4	1366.5	1246.3
42.5°	794.1	810.3	833.6	873.5	937.2	1023.8	1136.6	1268.4	1349.4	1326.4	1225.7
45°	649.9	660.2	678.3	710.0	756.1	823.9	923.4	1067.5	1192.9	1234.5	1176.5
47.5°	556.3	556.2	570.3	592.2	625.4	683.1	756.7	869.5	1003.5	1102.6	1098.0
50°	504.3	502.2	513.3	532.3	558.6	596.8	667.2	757.2	886.1	998.3	1029.6
52.5°	459.5	459.8	466.6	480.6	502.6	535.4	587.9	669.1	779.1	894.4	953.2
55°	400.7	399.0	406.8	416.3	432.3	453.7	491.5	553.7	642.9	756.5	833.0
57.5°	346.7	351.2	354.3	360.9	374.2	388.6	420.5	466.0	536.9	634.3	715.2
60°	315.1	319.6	322.1	328.7	339.4	351.7	376.4	413.4	473.0	557.0	637.2
62.5°	286.8	290.3	291.1	297.1	305.8	317.8	337.2	368.3	415.4	488.9	567.4
65°	246.0	246.0	247.6	253.8	257.9	268.6	283.4	306.0	343.9	401.1	468.1
67.5°	206.7	208.7	208.2	211.0	214.8	223.0	233.6	252.3	280.4	322.1	375.7
70°	181.0	182.6	182.2	184.3	188.4	193.8	202.4	220.1	240.2	276.0	322.1
72.5°	158.0	158.6	157.6	160.3	162.7	167.4	177.1	186.5	205.3	235.5	273.4
75°	121.0	121.8	122.6	124.2	126.7	129.1	134.1	143.5	155.9	178.6	202.8
77.5°	90.6	89.1	91.1	90.9	92.2	94.1	98.5	103.5	113.6	127.9	146.7
80°	68.3	68.7	68.7	69.1	71.1	72.4	76.1	79.8	87.6	98.3	111.5
82.5°	49.8	50.9	50.3	51.0	52.8	53.6	55.7	58.7	63.3	71.7	81.2
85°	27.2	25.1	25.9	26.8	26.8	27.2	28.8	30.0	32.5	35.8	39.5
87.5°	11.6	12.2	12.4	12.4	12.7	12.4	13.5	13.4	14.2	15.1	16.0
90°	18.2	18.2	17.4	17.4	17.4	15.8	15.1	14.3	13.5	12.7	11.1
92.5°	50.5	51.7	52.8	54.7	64.9	76.5	101.7	140.1	206.4	254.9	259.0
95°	185.8	198.5	204.9	228.5	284.7	351.1	448.4	568.6	685.6	700.7	571.8
97.5°	449.2	459.3	482.2	526.6	575.4	667.7	762.5	846.8	867.5	748.3	510.6
100°	616.9	629.5	658.8	715.7	770.2	852.5	934.0	972.7	911.8	714.1	455.5
102.5°	804.1	813.6	845.4	885.9	944.2	999.9	1038.9	1015.1	885.3	654.0	413.8
105°	1047.8	1057.3	1073.2	1099.2	1124.5	1133.2	1098.4	990.1	800.3	573.3	373.3
107.5°	1177.2	1183.5	1188.7	1188.9	1176.1	1134.8	1045.4	900.9	713.6	517.8	356.2
110°	1220.2	1220.2	1214.7	1199.7	1164.1	1096.9	985.3	835.1	664.2	491.9	351.1



TEST NUMBER: P333234-927

CATALOG NUMBER: S125DIP-S850D1035U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1215.1	1209.5	1195.7	1169.9	1117.9	1038.6	925.9	783.2	627.6	476.7	351.1
115°	1167.3	1157.0	1134.8	1096.9	1035.1	949.0	840.7	718.0	587.6	460.3	353.5
117.5°	1083.2	1076.9	1054.9	1015.7	954.0	875.0	781.6	676.0	563.7	452.2	358.7
120°	1028.9	1022.5	1001.2	963.2	904.7	835.1	748.1	653.2	550.4	448.4	363.8
122.5°	980.8	975.1	953.7	918.9	866.7	801.5	724.1	636.1	539.0	445.2	368.2
125°	919.7	911.8	894.4	862.0	817.7	760.7	692.0	611.3	523.6	441.2	375.7
127.5°	867.5	864.0	847.6	819.0	778.8	725.5	661.3	586.0	509.3	439.3	384.0
130°	839.1	834.3	818.5	792.4	752.9	701.5	639.8	570.2	499.8	438.1	389.1
132.5°	810.6	805.2	790.7	764.5	725.0	675.5	619.5	554.4	492.2	438.1	394.7
135°	763.9	759.1	745.0	718.8	684.0	639.0	588.4	533.8	483.2	438.1	402.5
137.5°	714.1	708.9	695.8	672.0	640.9	602.6	560.5	516.4	475.2	439.0	409.6
140°	679.3	675.3	663.5	642.9	613.7	580.4	544.1	506.9	471.3	439.7	412.8
142.5°	647.1	643.7	632.5	615.1	590.3	561.5	530.1	498.7	468.2	440.3	414.7
145°	602.6	599.4	590.7	577.3	558.3	536.9	512.5	487.9	463.4	439.7	416.8
147.5°	565.0	563.6	558.5	547.7	532.7	516.6	497.7	477.8	458.5	437.6	417.6
150°	544.1	543.3	540.1	530.6	518.8	504.5	489.5	472.1	454.7	435.7	417.6
152.5°	527.6	526.8	523.7	516.1	506.1	495.0	481.3	465.8	450.3	433.2	416.9
155°	505.3	504.5	502.2	496.6	488.7	480.1	469.0	456.3	442.8	428.6	415.2
157.5°	485.4	485.5	483.3	478.8	472.6	465.8	457.2	446.8	435.9	423.9	413.1
160°	472.1	472.9	471.3	467.4	461.8	456.3	448.4	440.5	430.2	420.7	411.2
162.5°	460.1	460.3	459.9	456.6	452.3	447.4	440.8	433.6	425.2	416.9	409.3
165°	442.8	442.8	442.8	441.2	438.1	434.2	429.4	423.9	417.6	411.2	406.5
167.5°	427.1	427.2	427.9	426.4	424.8	422.0	418.4	414.7	410.1	405.7	402.0
170°	417.6	418.4	418.4	417.6	416.0	414.4	412.0	409.6	405.7	402.5	400.1
172.5°	408.7	409.5	410.7	409.3	409.0	408.1	406.3	403.9	401.2	398.7	397.6
175°	397.8	398.5	400.1	399.3	399.3	399.3	397.8	397.8	395.4	394.6	394.6
177.5°	392.2	392.2	394.1	393.5	394.1	394.1	394.1	393.5	392.8	392.2	392.2
180°	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2



TEST NUMBER: P333234-927

CATALOG NUMBER: S125DIP-S850D1035U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2
2.5°	997.1	994.8	992.1	987.5	982.0	979.0	974.4	971.5	965.5	960.6	955.3
5°	1047.7	1037.0	1027.1	1014.4	1000.4	991.3	980.6	968.7	956.4	943.6	929.6
7.5°	1100.1	1081.2	1060.6	1038.5	1016.8	997.0	977.9	959.3	941.8	920.8	902.9
10°	1135.3	1111.4	1085.9	1055.9	1026.7	1001.2	975.3	952.7	929.6	905.0	883.1
12.5°	1170.5	1138.8	1102.7	1069.8	1034.6	1003.9	973.4	944.4	915.5	888.2	862.8
15°	1195.4	1167.4	1134.1	1087.2	1047.7	1005.4	965.0	927.6	892.6	862.2	830.1
17.5°	1211.7	1175.7	1140.0	1095.0	1043.1	995.8	950.1	907.3	867.8	829.3	798.4
20°	1214.7	1177.7	1140.3	1096.2	1043.1	988.9	943.3	891.8	849.5	809.5	771.7
22.5°	1213.7	1171.8	1131.0	1085.7	1034.0	984.0	928.8	876.3	830.4	791.1	751.6
25°	1204.4	1159.6	1108.6	1063.0	1011.9	958.9	902.9	848.6	801.7	756.9	717.8
27.5°	1196.7	1138.5	1080.8	1027.5	978.3	929.6	876.1	820.5	768.5	723.0	686.2
30°	1187.2	1123.4	1058.4	1002.8	952.3	905.0	854.4	800.1	745.8	701.3	661.9
32.5°	1178.6	1104.3	1035.7	975.3	921.6	875.7	829.0	777.4	724.1	679.0	639.4
35°	1162.1	1076.1	997.5	929.2	872.0	824.7	785.7	737.5	688.6	645.0	607.1
37.5°	1141.1	1039.0	954.7	883.1	820.5	770.6	734.3	697.3	650.3	608.3	574.1
40°	1124.6	1012.7	923.4	850.2	785.3	733.4	699.7	664.7	625.7	586.6	550.4
42.5°	1103.9	989.0	891.9	813.1	748.7	698.2	662.8	633.1	598.7	562.2	528.6
45°	1065.8	946.1	840.8	756.1	691.0	641.3	604.7	582.5	556.6	522.0	493.6
47.5°	1009.8	894.5	785.6	698.2	631.1	584.9	550.6	529.3	511.0	485.4	459.6
50°	960.0	856.0	745.8	658.9	591.9	545.4	513.8	494.4	478.8	459.1	437.3
52.5°	904.4	807.6	706.6	620.8	554.4	508.6	477.6	460.6	447.6	433.4	411.9
55°	816.1	733.9	640.1	558.6	497.3	452.5	425.3	410.5	399.8	389.1	376.0
57.5°	718.7	654.4	571.3	496.9	440.5	399.7	374.3	359.9	351.6	346.1	338.3
60°	650.3	595.2	523.6	455.7	400.7	364.5	339.8	328.7	321.7	317.1	311.4
62.5°	586.8	541.6	475.2	413.3	365.1	330.9	308.9	298.1	291.4	289.1	284.4
65°	493.2	458.3	403.5	352.1	311.0	281.8	263.2	252.9	248.8	246.4	246.8
67.5°	401.0	379.7	335.7	291.9	259.0	234.6	219.8	211.8	209.8	206.5	206.4
70°	344.7	328.7	291.7	253.4	224.2	205.3	192.1	183.9	181.8	180.1	179.7
72.5°	295.0	281.0	248.8	218.2	191.9	175.3	164.5	159.5	156.1	155.2	155.1
75°	221.7	213.9	188.4	164.1	146.0	134.5	127.1	122.6	120.1	119.7	120.1
77.5°	157.6	150.8	134.6	117.4	106.0	97.3	91.0	89.4	86.7	86.7	86.3
80°	118.4	113.9	103.7	90.1	80.6	73.2	69.9	67.0	66.2	65.0	66.2
82.5°	85.9	81.0	74.1	65.4	57.6	53.2	49.8	49.0	48.5	47.8	48.2
85°	42.4	42.8	38.7	32.1	28.8	26.3	24.2	24.2	23.8	23.4	23.8
87.5°	16.6	15.5	14.1	12.8	10.9	9.5	8.9	9.0	8.2	8.2	8.9
90°	10.3	8.7	7.9	6.3	4.8	3.2	1.6	0.8	1.6	3.2	4.8
92.5°	180.5	108.1	64.9	41.7	28.1	18.4	11.7	9.7	11.7	18.4	28.1
95°	353.5	179.5	94.9	59.3	41.9	33.2	26.9	26.1	26.9	33.2	41.9
97.5°	282.2	154.7	98.7	73.0	57.4	48.7	44.3	43.3	44.3	48.7	57.4
100°	256.2	153.4	107.6	83.8	68.8	60.1	57.0	55.4	57.0	60.1	68.8
102.5°	245.5	159.1	118.3	95.2	81.4	72.1	69.6	68.7	69.6	72.1	81.4
105°	241.2	170.8	136.0	113.9	101.2	93.3	89.4	89.4	89.4	93.3	101.2
107.5°	248.5	188.2	154.6	134.6	121.4	114.9	111.2	109.6	111.2	114.9	121.4
110°	255.4	200.9	168.4	147.9	136.0	128.9	125.7	124.1	125.7	128.9	136.0





TEST NUMBER: P333234-927

CATALOG NUMBER: S125DIP-S850D1035U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	264.3	212.9	181.7	161.8	150.0	142.8	140.3	138.7	140.3	142.8	150.0
115°	277.6	231.7	202.5	182.7	170.8	163.7	161.3	159.8	161.3	163.7	170.8
117.5°	292.8	251.0	223.3	204.2	190.8	183.6	181.1	178.7	181.1	183.6	190.8
120°	302.9	264.9	237.3	217.5	204.1	196.9	193.8	191.4	193.8	196.9	204.1
122.5°	314.3	278.2	250.6	230.8	216.0	208.9	206.4	204.7	206.4	208.9	216.0
125°	329.8	295.8	269.7	249.1	234.1	227.0	223.0	221.4	223.0	227.0	234.1
127.5°	344.0	312.7	287.6	267.0	251.0	242.0	236.9	234.6	236.9	242.0	251.0
130°	353.5	323.4	298.9	278.4	261.7	251.5	245.2	242.8	245.2	251.5	261.7
132.5°	361.7	333.6	309.0	288.5	271.2	259.7	252.1	249.1	252.1	259.7	271.2
135°	373.3	347.1	322.7	301.3	284.7	272.0	262.5	259.4	262.5	272.0	284.7
137.5°	381.8	356.8	334.5	312.5	296.3	283.6	274.7	272.4	274.7	283.6	296.3
140°	387.5	363.8	340.9	319.5	304.4	291.8	282.3	280.0	282.3	291.8	304.4
142.5°	390.6	368.2	346.5	326.5	312.0	299.4	290.6	288.8	290.6	299.4	312.0
145°	395.4	375.7	355.1	336.9	322.7	311.6	303.6	302.1	303.6	311.6	322.7
147.5°	398.2	380.4	362.3	346.3	334.1	323.8	317.0	316.0	317.0	323.8	334.1
150°	400.1	383.6	366.1	352.7	341.7	331.4	325.8	324.2	325.8	331.4	341.7
152.5°	401.4	386.7	370.6	358.4	347.9	339.0	334.1	333.1	334.1	339.0	347.9
155°	402.5	389.8	376.4	365.4	357.4	349.5	344.8	344.8	344.8	349.5	357.4
157.5°	403.3	392.5	381.0	372.6	365.7	358.9	355.1	355.2	355.1	358.9	365.7
160°	403.3	393.8	383.6	376.4	370.1	364.6	361.4	362.2	361.4	364.6	370.1
162.5°	402.7	395.1	386.1	380.2	375.2	370.3	367.1	367.9	367.1	370.3	375.2
165°	401.7	395.4	389.1	384.4	381.2	377.2	374.9	376.4	374.9	377.2	381.2
167.5°	399.8	395.4	390.1	387.2	385.0	382.8	381.4	382.1	381.4	382.8	385.0
170°	398.5	395.4	391.4	389.1	387.5	386.0	385.2	386.0	385.2	386.0	387.5
172.5°	397.3	394.7	391.4	390.3	389.4	387.9	387.1	388.5	387.1	387.9	389.4
175°	395.4	393.8	391.4	391.4	391.4	390.6	389.8	391.4	389.8	390.6	391.4
177.5°	393.5	392.8	391.6	391.6	392.2	391.6	391.6	392.8	391.6	391.6	392.2
180°	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2



TEST NUMBER: P333234-927

CATALOG NUMBER: S125DIP-S850D1035U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2
2.5°	952.4	948.7	945.8	939.2	935.6	930.7	926.7	931.0	926.4	928.4	925.3
5°	922.7	911.2	902.9	891.0	880.7	871.2	864.3	863.0	859.7	858.1	853.1
7.5°	886.9	872.5	858.4	842.8	829.6	816.2	807.6	800.6	795.9	789.7	785.5
10°	865.9	846.5	830.1	811.2	794.7	780.3	768.8	763.0	757.7	749.9	747.0
12.5°	839.9	819.9	799.8	779.6	763.8	747.7	737.8	729.1	725.5	716.6	715.7
15°	808.7	778.7	758.9	738.4	716.5	703.4	695.1	685.7	681.6	675.4	670.9
17.5°	771.5	744.7	720.0	698.7	680.0	668.9	658.7	652.2	645.2	641.1	633.7
20°	744.6	719.1	694.3	671.7	657.4	644.6	636.4	630.2	622.8	620.8	613.3
22.5°	721.8	693.7	670.0	651.0	635.3	620.9	612.0	607.8	602.7	596.4	594.8
25°	684.9	655.7	635.6	616.6	602.6	589.5	583.3	578.0	573.0	568.5	566.8
27.5°	653.0	626.9	602.9	585.8	573.7	561.7	556.2	549.7	546.1	542.5	538.1
30°	630.6	603.9	582.9	566.4	553.3	542.6	536.8	532.3	529.0	525.7	523.2
32.5°	607.5	582.8	562.4	546.4	533.2	525.1	520.0	516.8	513.2	509.2	506.1
35°	577.1	549.9	530.2	516.3	506.0	499.8	494.0	491.2	487.0	487.0	483.7
37.5°	542.8	519.4	501.9	489.2	480.0	474.4	468.2	466.2	463.6	461.8	460.7
40°	522.4	500.6	484.2	471.4	461.5	457.0	452.1	448.8	447.1	445.0	444.3
42.5°	501.4	480.5	464.8	453.0	444.4	440.5	435.9	433.6	430.3	427.6	427.1
45°	469.4	449.2	434.8	425.3	418.0	413.4	410.5	405.6	403.9	400.7	400.2
47.5°	438.9	419.6	405.5	397.8	391.3	387.5	383.0	378.1	376.2	374.5	374.4
50°	416.3	398.6	385.4	378.0	371.9	366.5	361.9	358.7	357.4	357.4	358.3
52.5°	393.2	378.2	367.0	358.0	352.1	346.4	342.2	340.2	338.3	340.3	341.8
55°	359.5	344.3	336.0	327.4	321.7	315.1	313.1	312.2	311.0	314.3	315.9
57.5°	323.8	313.1	303.5	294.9	289.8	286.0	283.2	282.7	284.9	286.5	291.9
60°	301.1	288.8	280.1	273.5	267.4	264.9	264.1	263.2	264.9	269.4	276.4
62.5°	276.1	266.1	256.7	251.8	247.3	243.2	243.0	243.5	246.8	252.0	259.0
65°	239.4	230.8	224.6	218.8	215.2	212.7	213.5	215.2	218.8	225.9	233.6
67.5°	202.2	196.2	190.7	186.0	182.4	182.4	183.3	185.8	190.1	198.2	205.3
70°	178.1	171.5	167.0	164.9	162.1	160.4	162.9	167.0	170.7	178.1	184.3
72.5°	154.1	148.5	145.0	143.5	142.4	141.0	141.8	146.2	151.3	158.7	165.9
75°	118.4	116.4	113.9	112.3	111.1	111.9	112.7	116.8	121.0	128.7	137.0
77.5°	86.4	84.3	82.9	82.5	81.8	82.1	84.5	87.5	91.6	97.3	103.5
80°	65.4	64.6	63.8	63.4	63.4	63.8	67.0	69.1	72.8	78.2	83.1
82.5°	47.6	47.1	47.0	46.9	47.2	47.3	49.3	52.0	55.1	59.1	63.4
85°	25.1	24.2	25.5	25.9	25.1	26.3	27.2	28.8	30.0	32.1	34.1
87.5°	9.5	10.5	10.3	10.9	11.1	12.0	11.9	13.4	14.2	15.0	15.0
90°	6.3	7.9	8.7	10.3	11.1	12.7	13.5	14.3	15.1	15.8	17.4
92.5°	41.7	64.9	108.1	180.5	259.0	254.9	206.4	140.1	101.7	76.5	64.9
95°	59.3	94.9	179.5	353.5	571.8	700.7	685.6	568.6	448.4	351.1	284.7
97.5°	73.0	98.7	154.7	282.2	510.6	748.3	867.5	846.8	762.5	667.7	575.4
100°	83.8	107.6	153.4	256.2	455.5	714.1	911.8	972.7	934.0	852.5	770.2
102.5°	95.2	118.3	159.1	245.5	413.8	654.0	885.3	1015.1	1038.9	999.9	944.2
105°	113.9	136.0	170.8	241.2	373.3	573.3	800.3	990.1	1098.4	1133.2	1124.5
107.5°	134.6	154.6	188.2	248.5	356.2	517.8	713.6	900.9	1045.4	1134.8	1176.1
110°	147.9	168.4	200.9	255.4	351.1	491.9	664.2	835.1	985.3	1096.9	1164.1



TEST NUMBER: P333234-927

CATALOG NUMBER: S125DIP-S850D1035U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	161.8	181.7	212.9	264.3	351.1	476.7	627.6	783.2	925.9	1038.6	1117.9
115°	182.7	202.5	231.7	277.6	353.5	460.3	587.6	718.0	840.7	949.0	1035.1
117.5°	204.2	223.3	251.0	292.8	358.7	452.2	563.7	676.0	781.6	875.0	954.0
120°	217.5	237.3	264.9	302.9	363.8	448.4	550.4	653.2	748.1	835.1	904.7
122.5°	230.8	250.6	278.2	314.3	368.2	445.2	539.0	636.1	724.1	801.5	866.7
125°	249.1	269.7	295.8	329.8	375.7	441.2	523.6	611.3	692.0	760.7	817.7
127.5°	267.0	287.6	312.7	344.0	384.0	439.3	509.3	586.0	661.3	725.5	778.8
130°	278.4	298.9	323.4	353.5	389.1	438.1	499.8	570.2	639.8	701.5	752.9
132.5°	288.5	309.0	333.6	361.7	394.7	438.1	492.2	554.4	619.5	675.5	725.0
135°	301.3	322.7	347.1	373.3	402.5	438.1	483.2	533.8	588.4	639.0	684.0
137.5°	312.5	334.5	356.8	381.8	409.6	439.0	475.2	516.4	560.5	602.6	640.9
140°	319.5	340.9	363.8	387.5	412.8	439.7	471.3	506.9	544.1	580.4	613.7
142.5°	326.5	346.5	368.2	390.6	414.7	440.3	468.2	498.7	530.1	561.5	590.3
145°	336.9	355.1	375.7	395.4	416.8	439.7	463.4	487.9	512.5	536.9	558.3
147.5°	346.3	362.3	380.4	398.2	417.6	437.6	458.5	477.8	497.7	516.6	532.7
150°	352.7	366.1	383.6	400.1	417.6	435.7	454.7	472.1	489.5	504.5	518.8
152.5°	358.4	370.6	386.7	401.4	416.9	433.2	450.3	465.8	481.3	495.0	506.1
155°	365.4	376.4	389.8	402.5	415.2	428.6	442.8	456.3	469.0	480.1	488.7
157.5°	372.6	381.0	392.5	403.3	413.1	423.9	435.9	446.8	457.2	465.8	472.6
160°	376.4	383.6	393.8	403.3	411.2	420.7	430.2	440.5	448.4	456.3	461.8
162.5°	380.2	386.1	395.1	402.7	409.3	416.9	425.2	433.6	440.8	447.4	452.3
165°	384.4	389.1	395.4	401.7	406.5	411.2	417.6	423.9	429.4	434.2	438.1
167.5°	387.2	390.1	395.4	399.8	402.0	405.7	410.1	414.7	418.4	422.0	424.8
170°	389.1	391.4	395.4	398.5	400.1	402.5	405.7	409.6	412.0	414.4	416.0
172.5°	390.3	391.4	394.7	397.3	397.6	398.7	401.2	403.9	406.3	408.1	409.0
175°	391.4	391.4	393.8	395.4	394.6	394.6	395.4	397.8	397.8	399.3	399.3
177.5°	391.6	391.6	392.8	393.5	392.2	392.2	392.8	393.5	394.1	394.1	394.1
180°	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2



TEST NUMBER: P333234-927

CATALOG NUMBER: S125DIP-S850D1035U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2
2.5°	923.4	925.7	923.7	926.4	923.7	925.7	923.4	925.3	928.4	926.4	931.0
5°	851.0	847.4	849.9	848.2	849.9	847.4	851.0	853.1	858.1	859.7	863.0
7.5°	784.3	780.7	776.7	774.8	776.7	780.7	784.3	785.5	789.7	795.9	800.6
10°	742.5	737.9	737.5	734.7	737.5	737.9	742.5	747.0	749.9	757.7	763.0
12.5°	711.9	707.7	703.0	701.8	703.0	707.7	711.9	715.7	716.6	725.5	729.1
15°	668.4	665.1	662.3	664.7	662.3	665.1	668.4	670.9	675.4	681.6	685.7
17.5°	632.3	629.6	629.1	626.1	629.1	629.6	632.3	633.7	641.1	645.2	652.2
20°	609.6	607.5	608.4	603.0	608.4	607.5	609.6	613.3	620.8	622.8	630.2
22.5°	591.5	587.5	587.0	585.9	587.0	587.5	591.5	594.8	596.4	602.7	607.8
25°	563.2	561.1	559.0	561.1	559.0	561.1	563.2	566.8	568.5	573.0	578.0
27.5°	538.4	535.9	535.4	535.6	535.4	535.9	538.4	538.1	542.5	546.1	549.7
30°	523.2	519.1	519.5	519.1	519.5	519.1	523.2	523.2	525.7	529.0	532.3
32.5°	506.8	504.0	503.4	502.6	503.4	504.0	506.8	506.1	509.2	513.2	516.8
35°	482.5	482.5	480.5	480.5	480.5	482.5	482.5	483.7	487.0	487.0	491.2
37.5°	459.7	459.3	458.0	458.3	458.0	459.3	459.7	460.7	461.8	463.6	466.2
40°	442.6	442.2	440.9	438.5	440.9	442.2	442.6	444.3	445.0	447.1	448.8
42.5°	426.1	424.8	424.2	423.3	424.2	424.8	426.1	427.1	427.6	430.3	433.6
45°	400.2	400.2	399.4	399.0	399.4	400.2	400.2	400.2	400.7	403.9	405.6
47.5°	375.1	375.8	377.4	377.2	377.4	375.8	375.1	374.4	374.5	376.2	378.1
50°	359.9	360.4	361.6	361.9	361.6	360.4	359.9	358.3	357.4	357.4	358.7
52.5°	343.2	345.5	347.1	346.8	347.1	345.5	343.2	341.8	340.3	338.3	340.2
55°	319.6	322.5	325.3	325.8	325.3	322.5	319.6	315.9	314.3	311.0	312.2
57.5°	296.4	300.4	303.4	304.4	303.4	300.4	296.4	291.9	286.5	284.9	282.7
60°	280.5	285.9	289.6	291.2	289.6	285.9	280.5	276.4	269.4	264.9	263.2
62.5°	265.4	271.4	275.1	275.4	275.1	271.4	265.4	259.0	252.0	246.8	243.5
65°	240.7	246.8	250.1	252.5	250.1	246.8	240.7	233.6	225.9	218.8	215.2
67.5°	214.0	220.1	223.8	225.8	223.8	220.1	214.0	205.3	198.2	190.1	185.8
70°	194.6	200.7	205.7	207.3	205.7	200.7	194.6	184.3	178.1	170.7	167.0
72.5°	175.5	181.0	185.0	186.9	185.0	181.0	175.5	165.9	158.7	151.3	146.2
75°	142.4	149.7	153.4	155.5	153.4	149.7	142.4	137.0	128.7	121.0	116.8
77.5°	109.7	116.5	118.7	119.8	118.7	116.5	109.7	103.5	97.3	91.6	87.5
80°	88.0	92.1	95.0	95.5	95.0	92.1	88.0	83.1	78.2	72.8	69.1
82.5°	67.7	71.1	72.0	73.0	72.0	71.1	67.7	63.4	59.1	55.1	52.0
85°	37.0	38.7	39.1	38.7	39.1	38.7	37.0	34.1	32.1	30.0	28.8
87.5°	15.7	15.3	15.4	16.2	15.4	15.3	15.7	15.0	15.0	14.2	13.4
90°	17.4	17.4	18.2	18.2	18.2	17.4	17.4	17.4	15.8	15.1	14.3
92.5°	54.7	52.8	51.7	50.5	51.7	52.8	54.7	64.9	76.5	101.7	140.1
95°	228.5	204.9	198.5	185.8	198.5	204.9	228.5	284.7	351.1	448.4	568.6
97.5°	526.6	482.2	459.3	449.2	459.3	482.2	526.6	575.4	667.7	762.5	846.8
100°	715.7	658.8	629.5	616.9	629.5	658.8	715.7	770.2	852.5	934.0	972.7
102.5°	885.9	845.4	813.6	804.1	813.6	845.4	885.9	944.2	999.9	1038.9	1015.1
105°	1099.2	1073.2	1057.3	1047.8	1057.3	1073.2	1099.2	1124.5	1133.2	1098.4	990.1
107.5°	1188.9	1188.7	1183.5	1177.2	1183.5	1188.7	1188.9	1176.1	1134.8	1045.4	900.9
110°	1199.7	1214.7	1220.2	1220.2	1220.2	1214.7	1199.7	1164.1	1096.9	985.3	835.1



TEST NUMBER: P333234-927

CATALOG NUMBER: S125DIP-S850D1035U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1169.9	1195.7	1209.5	1215.1	1209.5	1195.7	1169.9	1117.9	1038.6	925.9	783.2
115°	1096.9	1134.8	1157.0	1167.3	1157.0	1134.8	1096.9	1035.1	949.0	840.7	718.0
117.5°	1015.7	1054.9	1076.9	1083.2	1076.9	1054.9	1015.7	954.0	875.0	781.6	676.0
120°	963.2	1001.2	1022.5	1028.9	1022.5	1001.2	963.2	904.7	835.1	748.1	653.2
122.5°	918.9	953.7	975.1	980.8	975.1	953.7	918.9	866.7	801.5	724.1	636.1
125°	862.0	894.4	911.8	919.7	911.8	894.4	862.0	817.7	760.7	692.0	611.3
127.5°	819.0	847.6	864.0	867.5	864.0	847.6	819.0	778.8	725.5	661.3	586.0
130°	792.4	818.5	834.3	839.1	834.3	818.5	792.4	752.9	701.5	639.8	570.2
132.5°	764.5	790.7	805.2	810.6	805.2	790.7	764.5	725.0	675.5	619.5	554.4
135°	718.8	745.0	759.1	763.9	759.1	745.0	718.8	684.0	639.0	588.4	533.8
137.5°	672.0	695.8	708.9	714.1	708.9	695.8	672.0	640.9	602.6	560.5	516.4
140°	642.9	663.5	675.3	679.3	675.3	663.5	642.9	613.7	580.4	544.1	506.9
142.5°	615.1	632.5	643.7	647.1	643.7	632.5	615.1	590.3	561.5	530.1	498.7
145°	577.3	590.7	599.4	602.6	599.4	590.7	577.3	558.3	536.9	512.5	487.9
147.5°	547.7	558.5	563.6	565.0	563.6	558.5	547.7	532.7	516.6	497.7	477.8
150°	530.6	540.1	543.3	544.1	543.3	540.1	530.6	518.8	504.5	489.5	472.1
152.5°	516.1	523.7	526.8	527.6	526.8	523.7	516.1	506.1	495.0	481.3	465.8
155°	496.6	502.2	504.5	505.3	504.5	502.2	496.6	488.7	480.1	469.0	456.3
157.5°	478.8	483.3	485.5	485.4	485.5	483.3	478.8	472.6	465.8	457.2	446.8
160°	467.4	471.3	472.9	472.1	472.9	471.3	467.4	461.8	456.3	448.4	440.5
162.5°	456.6	459.9	460.3	460.1	460.3	459.9	456.6	452.3	447.4	440.8	433.6
165°	441.2	442.8	442.8	442.8	442.8	442.8	441.2	438.1	434.2	429.4	423.9
167.5°	426.4	427.9	427.2	427.1	427.2	427.9	426.4	424.8	422.0	418.4	414.7
170°	417.6	418.4	418.4	417.6	418.4	418.4	417.6	416.0	414.4	412.0	409.6
172.5°	409.3	410.7	409.5	408.7	409.5	410.7	409.3	409.0	408.1	406.3	403.9
175°	399.3	400.1	398.5	397.8	398.5	400.1	399.3	399.3	399.3	397.8	397.8
177.5°	393.5	394.1	392.2	392.2	392.2	394.1	393.5	394.1	394.1	394.1	393.5
180°	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2



TEST NUMBER: P333234-927

CATALOG NUMBER: S125DIP-S850D1035U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2
2.5°	926.7	930.7	935.6	939.2	945.8	948.7	952.4	955.3	960.6	965.5	971.5
5°	864.3	871.2	880.7	891.0	902.9	911.2	922.7	929.6	943.6	956.4	968.7
7.5°	807.6	816.2	829.6	842.8	858.4	872.5	886.9	902.9	920.8	941.8	959.3
10°	768.8	780.3	794.7	811.2	830.1	846.5	865.9	883.1	905.0	929.6	952.7
12.5°	737.8	747.7	763.8	779.6	799.8	819.9	839.9	862.8	888.2	915.5	944.4
15°	695.1	703.4	716.5	738.4	758.9	778.7	808.7	830.1	862.2	892.6	927.6
17.5°	658.7	668.9	680.0	698.7	720.0	744.7	771.5	798.4	829.3	867.8	907.3
20°	636.4	644.6	657.4	671.7	694.3	719.1	744.6	771.7	809.5	849.5	891.8
22.5°	612.0	620.9	635.3	651.0	670.0	693.7	721.8	751.6	791.1	830.4	876.3
25°	583.3	589.5	602.6	616.6	635.6	655.7	684.9	717.8	756.9	801.7	848.6
27.5°	556.2	561.7	573.7	585.8	602.9	626.9	653.0	686.2	723.0	768.5	820.5
30°	536.8	542.6	553.3	566.4	582.9	603.9	630.6	661.9	701.3	745.8	800.1
32.5°	520.0	525.1	533.2	546.4	562.4	582.8	607.5	639.4	679.0	724.1	777.4
35°	494.0	499.8	506.0	516.3	530.2	549.9	577.1	607.1	645.0	688.6	737.5
37.5°	468.2	474.4	480.0	489.2	501.9	519.4	542.8	574.1	608.3	650.3	697.3
40°	452.1	457.0	461.5	471.4	484.2	500.6	522.4	550.4	586.6	625.7	664.7
42.5°	435.9	440.5	444.4	453.0	464.8	480.5	501.4	528.6	562.2	598.7	633.1
45°	410.5	413.4	418.0	425.3	434.8	449.2	469.4	493.6	522.0	556.6	582.5
47.5°	383.0	387.5	391.3	397.8	405.5	419.6	438.9	459.6	485.4	511.0	529.3
50°	361.9	366.5	371.9	378.0	385.4	398.6	416.3	437.3	459.1	478.8	494.4
52.5°	342.2	346.4	352.1	358.0	367.0	378.2	393.2	411.9	433.4	447.6	460.6
55°	313.1	315.1	321.7	327.4	336.0	344.3	359.5	376.0	389.1	399.8	410.5
57.5°	283.2	286.0	289.8	294.9	303.5	313.1	323.8	338.3	346.1	351.6	359.9
60°	264.1	264.9	267.4	273.5	280.1	288.8	301.1	311.4	317.1	321.7	328.7
62.5°	243.0	243.2	247.3	251.8	256.7	266.1	276.1	284.4	289.1	291.4	298.1
65°	213.5	212.7	215.2	218.8	224.6	230.8	239.4	246.8	246.4	248.8	252.9
67.5°	183.3	182.4	182.4	186.0	190.7	196.2	202.2	206.4	206.5	209.8	211.8
70°	162.9	160.4	162.1	164.9	167.0	171.5	178.1	179.7	180.1	181.8	183.9
72.5°	141.8	141.0	142.4	143.5	145.0	148.5	154.1	155.1	155.2	156.1	159.5
75°	112.7	111.9	111.1	112.3	113.9	116.4	118.4	120.1	119.7	120.1	122.6
77.5°	84.5	82.1	81.8	82.5	82.9	84.3	86.4	86.3	86.7	86.7	89.4
80°	67.0	63.8	63.4	63.4	63.8	64.6	65.4	66.2	65.0	66.2	67.0
82.5°	49.3	47.3	47.2	46.9	47.0	47.1	47.6	48.2	47.8	48.5	49.0
85°	27.2	26.3	25.1	25.9	25.5	24.2	25.1	23.8	23.4	23.8	24.2
87.5°	11.9	12.0	11.1	10.9	10.3	10.5	9.5	8.9	8.2	8.2	9.0
90°	13.5	12.7	11.1	10.3	8.7	7.9	6.3	4.8	3.2	1.6	0.8
92.5°	206.4	254.9	259.0	180.5	108.1	64.9	41.7	28.1	18.4	11.7	9.7
95°	685.6	700.7	571.8	353.5	179.5	94.9	59.3	41.9	33.2	26.9	26.1
97.5°	867.5	748.3	510.6	282.2	154.7	98.7	73.0	57.4	48.7	44.3	43.3
100°	911.8	714.1	455.5	256.2	153.4	107.6	83.8	68.8	60.1	57.0	55.4
102.5°	885.3	654.0	413.8	245.5	159.1	118.3	95.2	81.4	72.1	69.6	68.7
105°	800.3	573.3	373.3	241.2	170.8	136.0	113.9	101.2	93.3	89.4	89.4
107.5°	713.6	517.8	356.2	248.5	188.2	154.6	134.6	121.4	114.9	111.2	109.6
110°	664.2	491.9	351.1	255.4	200.9	168.4	147.9	136.0	128.9	125.7	124.1



TEST NUMBER: P333234-927

CATALOG NUMBER: S125DIP-S850D1035U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	627.6	476.7	351.1	264.3	212.9	181.7	161.8	150.0	142.8	140.3	138.7
115°	587.6	460.3	353.5	277.6	231.7	202.5	182.7	170.8	163.7	161.3	159.8
117.5°	563.7	452.2	358.7	292.8	251.0	223.3	204.2	190.8	183.6	181.1	178.7
120°	550.4	448.4	363.8	302.9	264.9	237.3	217.5	204.1	196.9	193.8	191.4
122.5°	539.0	445.2	368.2	314.3	278.2	250.6	230.8	216.0	208.9	206.4	204.7
125°	523.6	441.2	375.7	329.8	295.8	269.7	249.1	234.1	227.0	223.0	221.4
127.5°	509.3	439.3	384.0	344.0	312.7	287.6	267.0	251.0	242.0	236.9	234.6
130°	499.8	438.1	389.1	353.5	323.4	298.9	278.4	261.7	251.5	245.2	242.8
132.5°	492.2	438.1	394.7	361.7	333.6	309.0	288.5	271.2	259.7	252.1	249.1
135°	483.2	438.1	402.5	373.3	347.1	322.7	301.3	284.7	272.0	262.5	259.4
137.5°	475.2	439.0	409.6	381.8	356.8	334.5	312.5	296.3	283.6	274.7	272.4
140°	471.3	439.7	412.8	387.5	363.8	340.9	319.5	304.4	291.8	282.3	280.0
142.5°	468.2	440.3	414.7	390.6	368.2	346.5	326.5	312.0	299.4	290.6	288.8
145°	463.4	439.7	416.8	395.4	375.7	355.1	336.9	322.7	311.6	303.6	302.1
147.5°	458.5	437.6	417.6	398.2	380.4	362.3	346.3	334.1	323.8	317.0	316.0
150°	454.7	435.7	417.6	400.1	383.6	366.1	352.7	341.7	331.4	325.8	324.2
152.5°	450.3	433.2	416.9	401.4	386.7	370.6	358.4	347.9	339.0	334.1	333.1
155°	442.8	428.6	415.2	402.5	389.8	376.4	365.4	357.4	349.5	344.8	344.8
157.5°	435.9	423.9	413.1	403.3	392.5	381.0	372.6	365.7	358.9	355.1	355.2
160°	430.2	420.7	411.2	403.3	393.8	383.6	376.4	370.1	364.6	361.4	362.2
162.5°	425.2	416.9	409.3	402.7	395.1	386.1	380.2	375.2	370.3	367.1	367.9
165°	417.6	411.2	406.5	401.7	395.4	389.1	384.4	381.2	377.2	374.9	376.4
167.5°	410.1	405.7	402.0	399.8	395.4	390.1	387.2	385.0	382.8	381.4	382.1
170°	405.7	402.5	400.1	398.5	395.4	391.4	389.1	387.5	386.0	385.2	386.0
172.5°	401.2	398.7	397.6	397.3	394.7	391.4	390.3	389.4	387.9	387.1	388.5
175°	395.4	394.6	394.6	395.4	393.8	391.4	391.4	391.4	390.6	389.8	391.4
177.5°	392.8	392.2	392.2	393.5	392.8	391.6	391.6	392.2	391.6	391.6	392.8
180°	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2



TEST NUMBER: P333234-927

CATALOG NUMBER: S125DIP-S850D1035U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2
2.5°	974.4	979.0	982.0	987.5	992.1	994.8	997.1	999.1	1001.4	1003.4	1008.9
5°	980.6	991.3	1000.4	1014.4	1027.1	1037.0	1047.7	1057.2	1065.0	1076.1	1084.7
7.5°	977.9	997.0	1016.8	1038.5	1060.6	1081.2	1100.1	1117.8	1133.9	1153.3	1170.3
10°	975.3	1001.2	1026.7	1055.9	1085.9	1111.4	1135.3	1159.6	1177.3	1202.0	1222.9
12.5°	973.4	1003.9	1034.6	1069.8	1102.7	1138.8	1170.5	1188.2	1215.1	1234.9	1259.8
15°	965.0	1005.4	1047.7	1087.2	1134.1	1167.4	1195.4	1229.9	1255.0	1280.1	1307.3
17.5°	950.1	995.8	1043.1	1095.0	1140.0	1175.7	1211.7	1245.1	1275.0	1308.7	1342.4
20°	943.3	988.9	1043.1	1096.2	1140.3	1177.7	1214.7	1251.3	1284.2	1327.4	1366.5
22.5°	928.8	984.0	1034.0	1085.7	1131.0	1171.8	1213.7	1255.3	1299.0	1347.8	1396.8
25°	902.9	958.9	1011.9	1063.0	1108.6	1159.6	1204.4	1260.0	1315.9	1380.5	1441.4
27.5°	876.1	929.6	978.3	1027.5	1080.8	1138.5	1196.7	1259.7	1332.9	1414.4	1500.3
30°	854.4	905.0	952.3	1002.8	1058.4	1123.4	1187.2	1262.0	1346.7	1438.4	1540.5
32.5°	829.0	875.7	921.6	975.3	1035.7	1104.3	1178.6	1260.7	1362.6	1466.8	1571.8
35°	785.7	824.7	872.0	929.2	997.5	1076.1	1162.1	1259.1	1375.9	1495.6	1584.1
37.5°	734.3	770.6	820.5	883.1	954.7	1039.0	1141.1	1256.2	1380.3	1475.8	1504.3
40°	699.7	733.4	785.3	850.2	923.4	1012.7	1124.6	1246.3	1366.5	1427.4	1403.9
42.5°	662.8	698.2	748.7	813.1	891.9	989.0	1103.9	1225.7	1326.4	1349.4	1268.4
45°	604.7	641.3	691.0	756.1	840.8	946.1	1065.8	1176.5	1234.5	1192.9	1067.5
47.5°	550.6	584.9	631.1	698.2	785.6	894.5	1009.8	1098.0	1102.6	1003.5	869.5
50°	513.8	545.4	591.9	658.9	745.8	856.0	960.0	1029.6	998.3	886.1	757.2
52.5°	477.6	508.6	554.4	620.8	706.6	807.6	904.4	953.2	894.4	779.1	669.1
55°	425.3	452.5	497.3	558.6	640.1	733.9	816.1	833.0	756.5	642.9	553.7
57.5°	374.3	399.7	440.5	496.9	571.3	654.4	718.7	715.2	634.3	536.9	466.0
60°	339.8	364.5	400.7	455.7	523.6	595.2	650.3	637.2	557.0	473.0	413.4
62.5°	308.9	330.9	365.1	413.3	475.2	541.6	586.8	567.4	488.9	415.4	368.3
65°	263.2	281.8	311.0	352.1	403.5	458.3	493.2	468.1	401.1	343.9	306.0
67.5°	219.8	234.6	259.0	291.9	335.7	379.7	401.0	375.7	322.1	280.4	252.3
70°	192.1	205.3	224.2	253.4	291.7	328.7	344.7	322.1	276.0	240.2	220.1
72.5°	164.5	175.3	191.9	218.2	248.8	281.0	295.0	273.4	235.5	205.3	186.5
75°	127.1	134.5	146.0	164.1	188.4	213.9	221.7	202.8	178.6	155.9	143.5
77.5°	91.0	97.3	106.0	117.4	134.6	150.8	157.6	146.7	127.9	113.6	103.5
80°	69.9	73.2	80.6	90.1	103.7	113.9	118.4	111.5	98.3	87.6	79.8
82.5°	49.8	53.2	57.6	65.4	74.1	81.0	85.9	81.2	71.7	63.3	58.7
85°	24.2	26.3	28.8	32.1	38.7	42.8	42.4	39.5	35.8	32.5	30.0
87.5°	8.9	9.5	10.9	12.8	14.1	15.5	16.6	16.0	15.1	14.2	13.4
90°	1.6	3.2	4.8	6.3	7.9	8.7	10.3	11.1	12.7	13.5	14.3
92.5°	11.7	18.4	28.1	41.7	64.9	108.1	180.5	259.0	254.9	206.4	140.1
95°	26.9	33.2	41.9	59.3	94.9	179.5	353.5	571.8	700.7	685.6	568.6
97.5°	44.3	48.7	57.4	73.0	98.7	154.7	282.2	510.6	748.3	867.5	846.8
100°	57.0	60.1	68.8	83.8	107.6	153.4	256.2	455.5	714.1	911.8	972.7
102.5°	69.6	72.1	81.4	95.2	118.3	159.1	245.5	413.8	654.0	885.3	1015.1
105°	89.4	93.3	101.2	113.9	136.0	170.8	241.2	373.3	573.3	800.3	990.1
107.5°	111.2	114.9	121.4	134.6	154.6	188.2	248.5	356.2	517.8	713.6	900.9
110°	125.7	128.9	136.0	147.9	168.4	200.9	255.4	351.1	491.9	664.2	835.1





TEST NUMBER: P333234-927

CATALOG NUMBER: S125DIP-S850D1035U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	140.3	142.8	150.0	161.8	181.7	212.9	264.3	351.1	476.7	627.6	783.2
115°	161.3	163.7	170.8	182.7	202.5	231.7	277.6	353.5	460.3	587.6	718.0
117.5°	181.1	183.6	190.8	204.2	223.3	251.0	292.8	358.7	452.2	563.7	676.0
120°	193.8	196.9	204.1	217.5	237.3	264.9	302.9	363.8	448.4	550.4	653.2
122.5°	206.4	208.9	216.0	230.8	250.6	278.2	314.3	368.2	445.2	539.0	636.1
125°	223.0	227.0	234.1	249.1	269.7	295.8	329.8	375.7	441.2	523.6	611.3
127.5°	236.9	242.0	251.0	267.0	287.6	312.7	344.0	384.0	439.3	509.3	586.0
130°	245.2	251.5	261.7	278.4	298.9	323.4	353.5	389.1	438.1	499.8	570.2
132.5°	252.1	259.7	271.2	288.5	309.0	333.6	361.7	394.7	438.1	492.2	554.4
135°	262.5	272.0	284.7	301.3	322.7	347.1	373.3	402.5	438.1	483.2	533.8
137.5°	274.7	283.6	296.3	312.5	334.5	356.8	381.8	409.6	439.0	475.2	516.4
140°	282.3	291.8	304.4	319.5	340.9	363.8	387.5	412.8	439.7	471.3	506.9
142.5°	290.6	299.4	312.0	326.5	346.5	368.2	390.6	414.7	440.3	468.2	498.7
145°	303.6	311.6	322.7	336.9	355.1	375.7	395.4	416.8	439.7	463.4	487.9
147.5°	317.0	323.8	334.1	346.3	362.3	380.4	398.2	417.6	437.6	458.5	477.8
150°	325.8	331.4	341.7	352.7	366.1	383.6	400.1	417.6	435.7	454.7	472.1
152.5°	334.1	339.0	347.9	358.4	370.6	386.7	401.4	416.9	433.2	450.3	465.8
155°	344.8	349.5	357.4	365.4	376.4	389.8	402.5	415.2	428.6	442.8	456.3
157.5°	355.1	358.9	365.7	372.6	381.0	392.5	403.3	413.1	423.9	435.9	446.8
160°	361.4	364.6	370.1	376.4	383.6	393.8	403.3	411.2	420.7	430.2	440.5
162.5°	367.1	370.3	375.2	380.2	386.1	395.1	402.7	409.3	416.9	425.2	433.6
165°	374.9	377.2	381.2	384.4	389.1	395.4	401.7	406.5	411.2	417.6	423.9
167.5°	381.4	382.8	385.0	387.2	390.1	395.4	399.8	402.0	405.7	410.1	414.7
170°	385.2	386.0	387.5	389.1	391.4	395.4	398.5	400.1	402.5	405.7	409.6
172.5°	387.1	387.9	389.4	390.3	391.4	394.7	397.3	397.6	398.7	401.2	403.9
175°	389.8	390.6	391.4	391.4	391.4	393.8	395.4	394.6	394.6	395.4	397.8
177.5°	391.6	391.6	392.2	391.6	391.6	392.8	393.5	392.2	392.2	392.8	393.5
180°	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2



TEST NUMBER: P333234-927

CATALOG NUMBER: S125DIP-S850D1035U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	969.2	969.2	969.2	969.2	969.2	969.2	969.2
2.5°	1013.5	1016.2	1021.8	1019.8	1022.5	1023.7	1025.1
5°	1095.4	1108.6	1114.4	1113.5	1122.1	1120.1	1118.0
7.5°	1187.9	1201.7	1209.4	1219.1	1224.6	1225.0	1229.9
10°	1240.2	1258.3	1265.7	1276.0	1282.5	1286.3	1285.9
12.5°	1280.3	1294.5	1311.1	1316.1	1325.0	1329.7	1328.0
15°	1328.6	1351.3	1368.6	1377.2	1388.3	1391.5	1396.1
17.5°	1371.7	1402.1	1422.3	1449.1	1459.2	1465.4	1461.7
20°	1404.3	1444.2	1464.4	1496.5	1514.2	1523.6	1520.4
22.5°	1442.8	1486.1	1523.3	1551.1	1578.0	1590.8	1593.4
25°	1508.8	1568.0	1622.8	1659.4	1692.7	1700.5	1717.8
27.5°	1582.5	1652.4	1710.9	1749.4	1772.6	1781.3	1786.7
30°	1629.0	1698.4	1742.5	1767.1	1774.6	1773.7	1772.9
32.5°	1651.6	1695.2	1703.6	1696.7	1679.7	1665.5	1650.5
35°	1619.5	1587.0	1538.4	1475.9	1429.8	1383.4	1378.8
37.5°	1456.5	1352.6	1271.8	1181.5	1129.5	1097.3	1075.1
40°	1303.1	1185.1	1087.2	1011.1	958.0	937.1	916.5
42.5°	1136.6	1023.8	937.2	873.5	833.6	810.3	794.1
45°	923.4	823.9	756.1	710.0	678.3	660.2	649.9
47.5°	756.7	683.1	625.4	592.2	570.3	556.2	556.3
50°	667.2	596.8	558.6	532.3	513.3	502.2	504.3
52.5°	587.9	535.4	502.6	480.6	466.6	459.8	459.5
55°	491.5	453.7	432.3	416.3	406.8	399.0	400.7
57.5°	420.5	388.6	374.2	360.9	354.3	351.2	346.7
60°	376.4	351.7	339.4	328.7	322.1	319.6	315.1
62.5°	337.2	317.8	305.8	297.1	291.1	290.3	286.8
65°	283.4	268.6	257.9	253.8	247.6	246.0	246.0
67.5°	233.6	223.0	214.8	211.0	208.2	208.7	206.7
70°	202.4	193.8	188.4	184.3	182.2	182.6	181.0
72.5°	177.1	167.4	162.7	160.3	157.6	158.6	158.0
75°	134.1	129.1	126.7	124.2	122.6	121.8	121.0
77.5°	98.5	94.1	92.2	90.9	91.1	89.1	90.6
80°	76.1	72.4	71.1	69.1	68.7	68.7	68.3
82.5°	55.7	53.6	52.8	51.0	50.3	50.9	49.8
85°	28.8	27.2	26.8	26.8	25.9	25.1	27.2
87.5°	13.5	12.4	12.7	12.4	12.4	12.2	11.6
90°	15.1	15.8	17.4	17.4	17.4	18.2	18.2
92.5°	101.7	76.5	64.9	54.7	52.8	51.7	50.5
95°	448.4	351.1	284.7	228.5	204.9	198.5	185.8
97.5°	762.5	667.7	575.4	526.6	482.2	459.3	449.2
100°	934.0	852.5	770.2	715.7	658.8	629.5	616.9
102.5°	1038.9	999.9	944.2	885.9	845.4	813.6	804.1
105°	1098.4	1133.2	1124.5	1099.2	1073.2	1057.3	1047.8
107.5°	1045.4	1134.8	1176.1	1188.9	1188.7	1183.5	1177.2
110°	985.3	1096.9	1164.1	1199.7	1214.7	1220.2	1220.2



TEST NUMBER: P333234-927

CATALOG NUMBER: S125DIP-S850D1035U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	925.9	1038.6	1117.9	1169.9	1195.7	1209.5	1215.1
115°	840.7	949.0	1035.1	1096.9	1134.8	1157.0	1167.3
117.5°	781.6	875.0	954.0	1015.7	1054.9	1076.9	1083.2
120°	748.1	835.1	904.7	963.2	1001.2	1022.5	1028.9
122.5°	724.1	801.5	866.7	918.9	953.7	975.1	980.8
125°	692.0	760.7	817.7	862.0	894.4	911.8	919.7
127.5°	661.3	725.5	778.8	819.0	847.6	864.0	867.5
130°	639.8	701.5	752.9	792.4	818.5	834.3	839.1
132.5°	619.5	675.5	725.0	764.5	790.7	805.2	810.6
135°	588.4	639.0	684.0	718.8	745.0	759.1	763.9
137.5°	560.5	602.6	640.9	672.0	695.8	708.9	714.1
140°	544.1	580.4	613.7	642.9	663.5	675.3	679.3
142.5°	530.1	561.5	590.3	615.1	632.5	643.7	647.1
145°	512.5	536.9	558.3	577.3	590.7	599.4	602.6
147.5°	497.7	516.6	532.7	547.7	558.5	563.6	565.0
150°	489.5	504.5	518.8	530.6	540.1	543.3	544.1
152.5°	481.3	495.0	506.1	516.1	523.7	526.8	527.6
155°	469.0	480.1	488.7	496.6	502.2	504.5	505.3
157.5°	457.2	465.8	472.6	478.8	483.3	485.5	485.4
160°	448.4	456.3	461.8	467.4	471.3	472.9	472.1
162.5°	440.8	447.4	452.3	456.6	459.9	460.3	460.1
165°	429.4	434.2	438.1	441.2	442.8	442.8	442.8
167.5°	418.4	422.0	424.8	426.4	427.9	427.2	427.1
170°	412.0	414.4	416.0	417.6	418.4	418.4	417.6
172.5°	406.3	408.1	409.0	409.3	410.7	409.5	408.7
175°	397.8	399.3	399.3	399.3	400.1	398.5	397.8
177.5°	394.1	394.1	394.1	393.5	394.1	392.2	392.2
180°	392.2	392.2	392.2	392.2	392.2	392.2	392.2

(END OF REPORT)