

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333238-927

Luminaire Tested: **S125DIP-S850D1035U927-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333238-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIP-S850D1035U927-4F0-1E-UDD-F  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 850 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1035 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5985.0 lumens  
Efficiency: N/A  
Efficacy: 115.1 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 52  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333238-927

CATALOG NUMBER: S125DIP-S850D1035U927-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P333238-927

CATALOG NUMBER: S125DIP-S850D1035U927-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52	45				
1	97	92	88	85	88	85	81	78	71	68	66	58	56	54	46	45	44	38				
2	88	81	74	69	80	74	69	64	62	58	55	51	48	45	40	38	37	32				
3	80	71	63	58	73	65	59	54	55	50	46	45	41	38	36	33	31	27				
4	73	63	55	49	67	58	51	45	48	43	39	40	36	33	32	29	27	23				
5	67	56	48	42	61	51	44	39	43	38	34	36	32	28	29	26	23	20				
6	62	50	42	36	57	46	39	34	39	33	29	32	28	25	26	23	21	18				
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	24	21	18	16				
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	22	19	16	14				
9	49	37	30	25	45	35	28	23	29	24	20	25	21	18	20	17	15	13				
10	46	34	27	22	42	32	25	21	27	22	18	23	19	16	19	16	13	11				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	6716	6716	6716
5°	6731	6667	6710
10°	6690	6620	6658
15°	6618	6540	6568
20°	6514	6429	6441
25°	6402	6297	6291
30°	6264	6154	6123
35°	6117	6000	5916
40°	5966	5833	5751
45°	5802	5681	5569
50°	5621	5497	5332
55°	5447	5290	5141
60°	5239	5079	4899
65°	4991	4828	4664
70°	4755	4538	4381
75°	4332	4190	4045
80°	3857	3794	3704
85°	3349	3416	3231



TEST NUMBER: P333238-927

CATALOG NUMBER: S125DIP-S850D1035U927-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	98.1	1.6
10°-20°	277.0	4.6
20°-30°	409.0	6.8
30°-40°	477.2	8.0
40°-50°	479.3	8.0
50°-60°	420.7	7.0
60°-70°	313.5	5.2
70°-80°	179.3	3.0
80°-90°	54.4	0.9
90°-100°	38.8	0.6
100°-110°	239.0	4.0
110°-120°	433.4	7.2
120°-130°	556.2	9.3
130°-140°	598.3	10.0
140°-150°	561.6	9.4
150°-160°	454.3	7.6
160°-170°	293.8	4.9
170°-180°	101.3	1.7
0°-30°	784.0	13.1
0°-40°	1261.2	21.1
0°-60°	2161.2	36.1
0°-90°	2708.3	45.3
90°-120°	711.2	11.9
90°-150°	2427.2	40.6
90°-180°	3277.0	54.8
0°-180°	5985.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1040	1040	1040	1040	1040	
5°	1038	1036	1028	1035	1035	98
15°	990	987	978	982	982	279
25°	898	894	884	885	883	413
35°	776	772	761	757	750	485
45°	635	631	622	612	610	489
55°	484	481	470	462	457	432
65°	327	325	316	309	305	324
75°	174	172	168	165	162	185
85°	45	46	46	45	44	51
90°	1	7	13	17	19	4
95°	45	41	13	16	17	57
105°	232	236	236	236	235	246
115°	437	440	441	438	434	433
125°	621	626	626	623	621	554
135°	774	779	778	776	771	597
145°	898	899	899	900	895	561
155°	989	984	986	987	982	455
165°	1043	1039	1039	1043	1038	295
175°	1067	1063	1063	1069	1062	102
180°	1067	1067	1067	1067	1067	



TEST NUMBER: P333238-927

CATALOG NUMBER: S125DIP-S850D1035U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1039.9	1039.9	1039.9	1039.9	1039.9	1039.9	1039.9	1039.9	1039.9	1039.9	1039.9
2.5°	1042.6	1042.1	1041.7	1041.2	1040.8	1039.8	1038.4	1037.0	1035.5	1034.0	1035.5
5°	1038.3	1037.9	1037.5	1037.2	1036.8	1035.7	1033.9	1032.1	1030.2	1028.4	1030.1
7.5°	1028.7	1028.4	1028.0	1027.6	1027.3	1026.1	1024.1	1022.1	1020.1	1018.0	1019.6
10°	1020.2	1019.9	1019.5	1019.1	1018.7	1017.6	1015.5	1013.5	1011.5	1009.5	1011.0
12.5°	1009.6	1009.0	1008.4	1007.7	1007.0	1005.8	1003.9	1002.0	1000.1	998.3	999.5
15°	989.8	989.2	988.6	988.1	987.5	986.3	984.3	982.2	980.2	978.2	979.1
17.5°	966.9	966.1	965.3	964.5	963.7	962.2	960.1	958.1	955.9	953.9	955.0
20°	947.8	947.5	947.1	946.7	946.3	944.9	942.5	940.2	937.8	935.4	936.8
22.5°	928.7	928.0	927.4	926.7	926.1	924.6	922.4	920.1	917.9	915.7	916.6
25°	898.4	897.5	896.6	895.6	894.8	893.1	890.7	888.4	886.0	883.6	884.0
27.5°	863.0	862.5	862.0	861.4	860.9	859.4	856.9	854.4	852.0	849.5	849.6
30°	840.0	839.5	838.9	838.4	837.8	836.1	833.5	830.7	827.9	825.2	824.8
32.5°	815.0	814.1	813.3	812.5	811.7	810.0	807.6	805.1	802.6	800.2	799.5
35°	775.9	775.1	774.4	773.6	772.9	771.3	768.7	766.1	763.6	761.0	760.1
37.5°	735.2	734.3	733.3	732.5	731.5	729.8	727.5	725.0	722.6	720.3	718.8
40°	707.6	706.6	705.8	704.8	703.9	702.2	699.6	697.0	694.5	691.9	690.3
42.5°	677.9	677.2	676.4	675.7	674.9	673.2	670.7	668.0	665.5	663.0	661.5
45°	635.2	634.4	633.7	633.0	632.2	630.7	628.6	626.4	624.2	622.0	619.8
47.5°	589.1	589.1	589.1	589.1	589.2	588.0	585.3	582.7	580.0	577.4	575.1
50°	559.4	558.9	558.3	557.8	557.3	555.9	553.7	551.5	549.3	547.1	544.7
52.5°	529.2	528.8	528.4	528.0	527.6	526.2	523.9	521.5	519.2	516.8	514.8
55°	483.8	483.2	482.7	482.1	481.6	480.0	477.4	474.9	472.3	469.8	468.1
57.5°	435.9	435.6	435.3	435.0	434.7	433.5	431.3	429.2	427.0	424.8	422.7
60°	405.6	404.9	404.2	403.4	402.7	401.3	399.3	397.3	395.3	393.2	391.4
62.5°	374.0	373.4	372.9	372.2	371.7	370.5	368.8	367.1	365.4	363.6	361.7
65°	326.6	326.2	325.9	325.5	325.2	324.0	321.9	320.0	317.9	315.9	314.3
67.5°	280.7	280.0	279.2	278.4	277.7	276.5	275.0	273.5	272.0	270.5	269.1
70°	251.8	250.8	249.9	249.0	248.1	246.8	245.2	243.5	241.9	240.3	239.2
72.5°	220.1	219.5	218.9	218.3	217.7	216.8	215.8	214.7	213.7	212.6	211.4
75°	173.6	173.3	172.9	172.5	172.1	171.5	170.6	169.7	168.7	167.9	167.3
77.5°	130.6	130.5	130.4	130.2	130.1	129.8	129.2	128.7	128.2	127.7	127.4
80°	103.7	103.7	103.7	103.7	103.7	103.5	103.1	102.7	102.3	102.0	101.9
82.5°	79.9	79.7	79.4	79.1	78.8	78.6	78.5	78.5	78.4	78.3	78.0
85°	45.2	45.5	45.6	45.8	45.9	46.1	46.1	46.1	46.1	46.1	45.9
87.5°	17.9	18.2	18.5	18.8	19.1	19.3	19.3	19.4	19.6	19.6	19.8
90°	0.8	2.2	3.6	5.0	6.4	7.8	9.0	10.2	11.4	12.7	13.5
92.5°	12.2	11.2	10.2	9.2	8.2	8.3	9.3	10.5	11.6	12.7	13.5
95°	45.1	44.5	44.0	43.5	43.0	39.4	32.7	26.0	19.3	12.7	13.5
97.5°	94.1	95.1	96.0	97.0	97.9	91.8	78.6	65.4	52.1	38.9	34.0
100°	132.1	132.6	133.2	133.6	134.2	134.8	135.5	136.3	136.9	137.6	111.5
102.5°	170.7	171.3	172.1	172.7	173.3	173.9	174.4	174.8	175.2	175.6	170.6
105°	232.5	233.2	233.9	234.6	235.4	235.7	235.7	235.7	235.7	235.7	235.7
107.5°	296.8	296.8	296.8	296.8	296.8	296.9	297.3	297.6	298.0	298.3	298.4
110°	338.5	338.5	338.5	338.5	338.5	338.7	339.1	339.5	339.8	340.1	339.6



TEST NUMBER: P333238-927

CATALOG NUMBER: S125DIP-S850D1035U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	377.8	378.2	378.6	379.1	379.5	379.8	380.0	380.2	380.4	380.6	379.9
115°	436.7	437.5	438.4	439.3	440.1	440.7	440.8	441.0	441.2	441.3	440.7
117.5°	497.5	497.5	497.4	497.4	497.4	497.7	498.4	499.0	499.7	500.3	499.5
120°	535.5	535.3	535.1	535.0	534.8	535.0	535.5	536.0	536.5	537.1	536.7
122.5°	569.0	569.7	570.4	571.0	571.7	572.1	572.4	572.7	572.9	573.1	572.7
125°	620.9	622.1	623.4	624.6	625.8	626.5	626.5	626.5	626.5	626.5	625.7
127.5°	670.4	671.3	672.2	673.0	673.9	674.3	674.2	674.1	674.0	673.9	673.5
130°	700.8	701.7	702.6	703.5	704.3	704.8	705.0	705.2	705.4	705.5	705.0
132.5°	731.2	732.2	733.2	734.2	735.2	735.5	735.1	734.8	734.4	734.0	733.9
135°	774.4	775.4	776.5	777.5	778.6	779.0	778.6	778.2	777.8	777.5	777.1
137.5°	814.0	815.0	815.9	816.8	817.7	818.0	817.7	817.4	817.1	816.7	816.8
140°	840.0	840.3	840.7	841.1	841.4	841.5	841.3	841.1	841.0	840.8	841.1
142.5°	863.4	863.6	863.9	864.0	864.3	864.5	864.7	865.0	865.2	865.5	865.5
145°	897.8	898.1	898.4	898.8	899.1	899.4	899.4	899.4	899.4	899.4	899.5
147.5°	927.8	927.7	927.6	927.6	927.5	927.6	927.8	928.0	928.2	928.4	928.7
150°	946.8	946.4	946.1	945.7	945.4	945.4	945.7	946.1	946.4	946.8	947.1
152.5°	965.1	964.4	963.6	962.8	962.0	961.9	962.2	962.5	962.9	963.2	963.6
155°	988.7	987.7	986.6	985.6	984.5	984.1	984.5	984.8	985.2	985.6	986.1
157.5°	1006.9	1006.2	1005.7	1005.0	1004.4	1004.1	1004.1	1004.2	1004.2	1004.2	1004.8
160°	1019.5	1018.5	1017.5	1016.4	1015.3	1014.9	1015.1	1015.3	1015.4	1015.6	1016.3
162.5°	1029.7	1028.6	1027.5	1026.5	1025.5	1025.0	1025.2	1025.4	1025.6	1025.7	1026.7
165°	1043.3	1042.2	1041.2	1040.1	1039.1	1038.6	1038.8	1038.9	1039.2	1039.3	1040.4
167.5°	1053.4	1052.3	1051.2	1050.1	1049.1	1048.6	1048.8	1048.9	1049.1	1049.3	1050.6
170°	1059.1	1057.9	1056.6	1055.4	1054.2	1053.7	1053.8	1054.0	1054.2	1054.4	1055.7
172.5°	1062.9	1061.7	1060.4	1059.2	1058.0	1057.6	1057.8	1058.1	1058.4	1058.8	1060.0
175°	1067.0	1066.0	1064.9	1063.8	1062.8	1062.4	1062.6	1062.7	1062.9	1063.0	1064.5
177.5°	1068.9	1068.1	1067.2	1066.4	1065.6	1065.2	1065.3	1065.5	1065.6	1065.7	1066.8
180°	1067.0	1067.0	1067.0	1067.0	1067.0	1067.0	1067.0	1067.0	1067.0	1067.0	1067.0



TEST NUMBER: P333238-927

CATALOG NUMBER: S125DIP-S850D1035U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1039.9	1039.9	1039.9	1039.9	1039.9	1039.9	1039.9	1039.9
2.5°	1037.0	1038.4	1039.8	1040.5	1040.4	1040.2	1040.1	1039.9
5°	1031.7	1033.3	1035.0	1035.7	1035.5	1035.4	1035.1	1035.0
7.5°	1021.3	1022.9	1024.5	1025.2	1025.0	1024.8	1024.6	1024.5
10°	1012.4	1013.9	1015.3	1016.0	1015.8	1015.6	1015.4	1015.3
12.5°	1000.6	1001.8	1003.0	1003.5	1003.5	1003.5	1003.5	1003.4
15°	980.1	981.0	981.9	982.3	982.3	982.3	982.3	982.3
17.5°	956.2	957.3	958.4	958.5	957.6	956.7	955.8	954.9
20°	938.0	939.3	940.6	940.7	939.8	938.9	938.0	937.1
22.5°	917.3	918.2	919.1	919.2	918.5	917.9	917.3	916.7
25°	884.3	884.7	885.1	884.9	884.5	883.9	883.4	882.8
27.5°	849.7	849.8	849.9	849.6	849.1	848.5	848.0	847.4
30°	824.5	824.1	823.7	823.3	822.8	822.2	821.7	821.1
32.5°	798.8	798.2	797.6	796.7	795.7	794.7	793.8	792.8
35°	759.2	758.3	757.4	756.2	754.7	753.3	751.8	750.4
37.5°	717.5	716.1	714.8	713.7	712.9	712.0	711.2	710.3
40°	688.6	687.0	685.3	684.2	683.7	683.2	682.6	682.1
42.5°	660.0	658.5	657.0	655.8	655.0	654.1	653.2	652.4
45°	617.6	615.4	613.2	611.8	611.3	610.8	610.2	609.7
47.5°	572.9	570.7	568.5	566.7	565.5	564.2	562.8	561.6
50°	542.3	540.0	537.6	535.8	534.5	533.2	532.0	530.7
52.5°	512.7	510.6	508.5	506.8	505.3	503.9	502.5	501.1
55°	466.5	464.9	463.2	461.8	460.4	459.1	457.9	456.6
57.5°	420.6	418.5	416.4	414.9	414.2	413.6	412.9	412.2
60°	389.6	387.8	386.0	384.4	383.1	381.8	380.6	379.3
62.5°	359.7	357.7	355.8	354.3	353.3	352.3	351.3	350.3
65°	312.7	311.0	309.3	308.2	307.4	306.7	305.9	305.2
67.5°	267.8	266.3	265.0	264.0	263.6	263.2	262.7	262.3
70°	238.1	236.9	235.8	235.0	234.2	233.5	232.7	232.0
72.5°	210.1	208.9	207.6	206.6	205.9	205.2	204.5	203.7
75°	166.8	166.2	165.6	165.0	164.3	163.5	162.8	162.1
77.5°	127.1	126.7	126.4	126.0	125.4	124.9	124.5	123.9
80°	101.6	101.5	101.3	101.0	100.7	100.3	99.9	99.6
82.5°	77.6	77.3	77.0	76.8	76.8	76.7	76.6	76.5
85°	45.7	45.6	45.3	45.1	44.7	44.4	44.0	43.6
87.5°	20.0	20.2	20.4	20.4	20.1	20.0	19.8	19.6
90°	14.4	15.3	16.2	16.9	17.4	17.9	18.5	19.0
92.5°	14.4	15.3	16.2	16.7	17.0	17.2	17.5	17.7
95°	14.4	15.3	16.2	16.6	16.6	16.6	16.6	16.6
97.5°	29.0	24.1	19.1	16.6	16.6	16.6	16.6	16.6
100°	85.2	59.1	32.9	19.4	18.7	18.0	17.3	16.6
102.5°	165.6	160.7	155.7	147.3	135.4	123.4	111.5	99.5
105°	235.7	235.7	235.7	235.6	235.4	235.3	235.1	234.9
107.5°	298.4	298.5	298.5	298.3	297.7	297.2	296.7	296.1
110°	339.1	338.5	338.0	337.9	338.0	338.2	338.3	338.5





TEST NUMBER: P333238-927

CATALOG NUMBER: S125DIP-S850D1035U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	379.3	378.6	378.0	377.5	377.2	377.0	376.8	376.5
115°	440.0	439.3	438.6	437.7	436.7	435.5	434.5	433.5
117.5°	498.5	497.6	496.7	496.0	495.6	495.1	494.6	494.2
120°	536.4	536.0	535.7	535.0	534.2	533.3	532.4	531.6
122.5°	572.4	572.1	571.7	571.0	570.1	569.0	568.0	567.0
125°	625.0	624.3	623.6	623.1	622.5	621.9	621.5	620.9
127.5°	673.1	672.7	672.3	671.5	670.2	668.9	667.7	666.3
130°	704.5	703.9	703.5	702.7	701.9	701.0	700.1	699.2
132.5°	733.8	733.7	733.6	733.1	732.2	731.3	730.5	729.6
135°	776.8	776.5	776.1	775.4	774.4	773.3	772.2	771.2
137.5°	816.9	817.0	817.1	816.6	815.7	814.8	813.9	812.9
140°	841.5	841.9	842.2	841.9	840.8	839.7	838.7	837.7
142.5°	865.6	865.7	865.8	865.3	864.2	863.2	862.1	861.0
145°	899.7	899.8	900.0	899.6	898.6	897.5	896.4	895.4
147.5°	928.8	929.1	929.3	928.8	927.5	926.2	925.0	923.7
150°	947.5	947.8	948.2	947.7	946.3	944.8	943.4	942.1
152.5°	963.9	964.3	964.6	964.2	962.9	961.6	960.4	959.1
155°	986.6	987.1	987.7	987.2	985.8	984.4	983.0	981.6
157.5°	1005.4	1005.9	1006.5	1006.1	1004.6	1003.2	1001.8	1000.4
160°	1017.0	1017.7	1018.4	1018.0	1016.7	1015.3	1013.8	1012.4
162.5°	1027.7	1028.6	1029.7	1029.4	1027.9	1026.3	1024.8	1023.2
165°	1041.4	1042.5	1043.5	1043.4	1042.0	1040.5	1039.2	1037.8
167.5°	1051.9	1053.1	1054.4	1054.2	1052.7	1051.1	1049.5	1047.9
170°	1057.2	1058.6	1060.0	1059.9	1058.3	1056.8	1055.2	1053.6
172.5°	1061.3	1062.6	1063.8	1063.7	1062.1	1060.5	1058.9	1057.4
175°	1065.9	1067.3	1068.7	1068.6	1067.0	1065.4	1063.8	1062.2
177.5°	1067.7	1068.7	1069.7	1069.6	1068.5	1067.4	1066.3	1065.1
180°	1067.0	1067.0	1067.0	1067.0	1067.0	1067.0	1067.0	1067.0

(END OF REPORT)