

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332560

Luminaire Tested: **S124DIP-S575D810U835-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332560
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIP-S575D810U835-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 810 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5299.7 lumens
Efficiency: N/A
Efficacy: 138.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 38.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332560

CATALOG NUMBER: S124DIP-S575D810U835-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332560

CATALOG NUMBER: S124DIP-S575D810U835-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	98	98	98	98	82	82	82	67	67	67	53	53	53	47
1	97	93	89	85	89	85	82	79	72	69	67	59	57	56	47	46	45	40
2	88	81	75	70	81	75	69	65	63	59	55	52	49	46	41	40	38	33
3	81	71	64	58	74	66	59	54	55	51	47	46	42	39	37	34	32	28
4	74	63	55	49	67	58	51	46	49	44	40	41	37	34	33	30	28	24
5	68	56	48	42	62	52	45	39	44	38	34	36	32	29	30	27	24	21
6	62	50	42	36	57	47	39	34	40	34	30	33	29	26	27	24	21	18
7	58	45	37	32	53	42	35	30	36	30	26	30	26	23	25	21	19	16
8	53	41	33	28	49	38	31	27	33	27	23	27	23	20	23	19	17	15
9	50	38	30	25	46	35	28	24	30	25	21	25	21	18	21	18	15	13
10	46	34	27	22	43	32	26	21	28	22	19	23	19	16	19	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7840	7840	7840
5°	7864	7769	7826
10°	7814	7706	7744
15°	7720	7596	7616
20°	7594	7460	7467
25°	7451	7306	7285
30°	7276	7124	7058
35°	7094	6933	6841
40°	6905	6716	6593
45°	6707	6503	6379
50°	6489	6314	6118
55°	6253	6068	5871
60°	6018	5792	5616
65°	5752	5530	5307
70°	5455	5179	4978
75°	5000	4757	4635
80°	4449	4268	4161
85°	3890	3751	3677



TEST NUMBER: P332560

CATALOG NUMBER: S124DIP-S575D810U835-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	91.5	1.7
10°-20°	257.7	4.9
20°-30°	379.3	7.2
30°-40°	440.9	8.3
40°-50°	440.9	8.3
50°-60°	385.7	7.3
60°-70°	286.4	5.4
70°-80°	162.7	3.1
80°-90°	50.0	0.9
90°-100°	66.7	1.3
100°-110°	197.5	3.7
110°-120°	335.2	6.3
120°-130°	442.0	8.3
130°-140°	496.4	9.4
140°-150°	487.8	9.2
150°-160°	410.3	7.7
160°-170°	273.0	5.2
170°-180°	95.6	1.8
0°-30°	728.4	13.7
0°-40°	1169.3	22.1
0°-60°	1996.0	37.7
0°-90°	2495.1	47.1
90°-120°	599.4	11.3
90°-150°	2025.7	38.2
90°-180°	2805.0	52.9
0°-180°	5299.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	971	971	971	971	971	
5°	970	967	959	967	966	92
15°	924	920	909	913	911	260
25°	836	831	820	821	818	385
35°	720	714	704	698	694	450
45°	588	582	570	561	559	453
55°	444	442	431	422	417	398
65°	301	297	290	282	278	298
75°	160	156	152	150	149	170
85°	42	42	40	40	40	46
90°	2	11	17	22	24	5
95°	47	54	59	62	62	52
105°	182	183	186	188	191	193
115°	341	341	339	338	338	336
125°	496	496	496	494	492	442
135°	640	645	645	643	641	495
145°	778	781	782	781	779	487
155°	891	891	890	893	890	410
165°	970	968	966	971	968	273
175°	1009	1006	1005	1010	1005	96
180°	1011	1011	1011	1011	1011	



TEST NUMBER: P332560

CATALOG NUMBER: S124DIP-S575D810U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	971.1	971.1	971.1	971.1	971.1	971.1	971.1	971.1	971.1	971.1	971.1
2.5°	973.6	973.2	972.8	972.4	972.0	971.0	969.5	968.0	966.4	964.9	966.3
5°	970.4	969.7	969.0	968.3	967.6	966.3	964.4	962.5	960.6	958.7	960.6
7.5°	961.3	960.6	960.0	959.3	958.6	957.2	955.1	953.0	950.8	948.7	950.3
10°	953.2	952.6	951.9	951.2	950.5	949.0	946.8	944.5	942.3	940.0	941.4
12.5°	942.7	942.0	941.3	940.6	939.9	938.4	936.0	933.6	931.2	928.8	930.3
15°	923.7	923.0	922.3	921.6	920.9	919.3	916.7	914.1	911.5	908.9	909.9
17.5°	900.8	899.9	899.1	898.2	897.3	895.7	893.2	890.8	888.3	885.9	886.5
20°	884.0	883.1	882.3	881.4	880.5	878.8	876.2	873.6	871.0	868.4	868.9
22.5°	865.9	864.8	863.7	862.5	861.4	859.5	856.9	854.3	851.7	849.1	850.1
25°	836.5	835.3	834.1	832.9	831.7	829.9	827.4	825.0	822.6	820.2	820.4
27.5°	802.9	801.7	800.4	799.2	797.9	796.2	793.9	791.7	789.4	787.2	786.8
30°	780.5	779.1	777.7	776.3	775.0	773.1	770.9	768.6	766.4	764.2	763.5
32.5°	756.8	755.6	754.3	753.1	751.9	750.0	747.7	745.3	742.9	740.5	739.7
35°	719.8	718.6	717.4	716.2	715.0	713.1	710.7	708.3	705.9	703.5	702.2
37.5°	680.7	679.6	678.5	677.4	676.3	674.5	671.9	669.3	666.7	664.1	662.8
40°	655.2	653.8	652.4	651.1	649.7	647.7	645.1	642.5	639.9	637.3	635.6
42.5°	627.8	627.0	626.2	625.3	624.5	622.6	619.8	616.9	614.0	611.2	609.2
45°	587.5	586.3	585.1	583.9	582.7	580.7	577.9	575.1	572.4	569.6	567.7
47.5°	545.3	544.5	543.7	542.8	542.0	540.3	537.8	535.2	532.6	530.1	527.9
50°	516.7	516.0	515.3	514.6	513.9	512.4	510.0	507.5	505.1	502.7	500.3
52.5°	488.7	487.9	487.0	486.2	485.4	483.7	481.1	478.6	476.0	473.4	471.3
55°	444.3	443.8	443.3	442.8	442.3	440.8	438.4	435.9	433.5	431.1	429.0
57.5°	402.0	401.4	400.8	400.2	399.6	398.2	395.8	393.4	391.0	388.6	386.6
60°	372.7	371.9	371.0	370.1	369.3	367.7	365.5	363.2	361.0	358.7	357.2
62.5°	344.1	343.4	342.6	341.9	341.2	339.6	337.3	334.9	332.5	330.1	328.7
65°	301.1	300.3	299.4	298.6	297.7	296.4	294.7	292.9	291.2	289.5	287.7
67.5°	257.9	257.1	256.3	255.5	254.7	253.5	251.8	250.2	248.5	246.8	245.2
70°	231.1	229.9	228.7	227.5	226.3	225.0	223.6	222.2	220.8	219.4	218.1
72.5°	202.5	201.3	200.1	198.8	197.6	196.5	195.4	194.3	193.2	192.0	190.9
75°	160.3	159.4	158.6	157.7	156.8	156.0	155.1	154.2	153.4	152.5	151.8
77.5°	120.0	119.6	119.2	118.9	118.5	117.9	117.1	116.4	115.6	114.9	114.6
80°	95.7	95.2	94.7	94.2	93.6	93.2	92.9	92.5	92.2	91.8	91.5
82.5°	72.1	71.8	71.6	71.3	71.1	70.9	70.9	70.8	70.7	70.7	70.4
85°	42.0	42.0	42.0	42.0	42.0	41.8	41.5	41.2	40.8	40.5	40.5
87.5°	16.7	16.9	17.1	17.4	17.6	17.8	18.0	18.1	18.2	18.4	18.6
90°	2.3	4.3	6.2	8.1	10.0	11.6	13.0	14.4	15.8	17.2	18.2
92.5°	16.7	18.9	21.1	23.3	25.5	27.1	28.0	29.0	30.0	31.0	31.6
95°	46.9	48.5	50.0	51.6	53.2	54.6	55.8	57.0	58.2	59.4	59.9
97.5°	81.9	83.2	84.4	85.7	86.9	88.3	89.7	91.1	92.5	94.0	94.6
100°	109.5	110.1	110.8	111.5	112.2	113.4	114.9	116.5	118.0	119.6	120.0
102.5°	138.2	138.5	138.8	139.1	139.3	140.2	141.6	143.0	144.5	145.9	146.4
105°	182.2	182.3	182.5	182.7	182.9	183.3	184.0	184.7	185.4	186.1	186.6
107.5°	228.3	228.5	228.7	228.9	229.1	229.3	229.4	229.5	229.6	229.7	230.2
110°	259.6	259.9	260.2	260.6	260.9	261.0	260.9	260.7	260.5	260.3	260.0



TEST NUMBER: P332560

CATALOG NUMBER: S124DIP-S575D810U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	292.1	292.1	292.2	292.3	292.4	292.2	291.9	291.6	291.3	291.0	290.9
115°	340.9	340.9	340.9	340.9	340.9	340.7	340.3	340.0	339.6	339.3	339.1
117.5°	386.8	387.0	387.1	387.2	387.4	387.3	387.1	386.8	386.6	386.4	385.8
120°	417.5	418.2	418.9	419.6	420.3	420.3	419.8	419.3	418.8	418.3	417.4
122.5°	449.4	449.6	449.9	450.2	450.5	450.5	450.3	450.0	449.8	449.5	448.9
125°	496.4	496.4	496.4	496.4	496.4	496.3	496.2	496.0	495.8	495.7	495.3
127.5°	539.1	539.6	540.2	540.7	541.2	541.3	541.0	540.8	540.5	540.2	539.9
130°	569.1	569.7	570.2	570.7	571.2	571.5	571.5	571.5	571.5	571.5	571.1
132.5°	599.8	600.2	600.6	600.9	601.3	601.4	601.3	601.2	601.0	600.9	600.5
135°	640.3	641.3	642.4	643.4	644.5	645.0	645.0	645.0	645.0	645.0	644.6
137.5°	684.4	684.9	685.3	685.8	686.3	686.7	687.0	687.3	687.5	687.8	687.4
140°	713.8	714.1	714.5	714.8	715.2	715.3	715.3	715.3	715.3	715.3	715.2
142.5°	740.7	741.0	741.4	741.7	742.1	742.2	742.0	741.9	741.7	741.6	741.6
145°	777.9	778.6	779.3	780.0	780.7	781.1	781.3	781.4	781.6	781.8	781.6
147.5°	814.8	815.6	816.4	817.3	818.1	818.5	818.3	818.2	818.0	817.9	817.8
150°	837.3	838.0	838.7	839.4	840.1	840.4	840.4	840.4	840.4	840.4	840.4
152.5°	858.6	859.0	859.4	859.8	860.2	860.5	860.6	860.8	860.9	861.1	861.5
155°	891.2	891.2	891.2	891.2	891.2	891.1	891.0	890.8	890.6	890.5	891.1
157.5°	918.8	918.4	918.1	917.8	917.5	917.3	917.3	917.3	917.2	917.2	917.7
160°	935.0	934.8	934.7	934.5	934.3	934.1	934.0	933.8	933.6	933.5	934.0
162.5°	950.0	949.6	949.1	948.7	948.2	947.9	947.7	947.6	947.4	947.2	948.2
165°	970.2	969.7	969.2	968.6	968.1	967.7	967.3	967.0	966.6	966.3	967.3
167.5°	985.7	984.9	984.2	983.5	982.8	982.4	982.4	982.5	982.5	982.5	983.6
170°	994.4	993.6	992.7	991.8	991.0	990.6	990.8	991.0	991.1	991.3	992.3
172.5°	1000.7	1000.0	999.2	998.5	997.8	997.4	997.5	997.5	997.5	997.6	998.7
175°	1009.3	1008.4	1007.5	1006.7	1005.8	1005.3	1005.1	1004.9	1004.8	1004.6	1005.8
177.5°	1012.1	1011.4	1010.7	1010.0	1009.3	1009.0	1009.0	1009.0	1009.0	1009.0	1009.9
180°	1010.8	1010.8	1010.8	1010.8	1010.8	1010.8	1010.8	1010.8	1010.8	1010.8	1010.8



TEST NUMBER: P332560

CATALOG NUMBER: S124DIP-S575D810U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	971.1	971.1	971.1	971.1	971.1	971.1	971.1	971.1
2.5°	967.7	969.1	970.5	971.1	970.9	970.8	970.7	970.5
5°	962.5	964.4	966.3	967.1	966.7	966.4	966.0	965.7
7.5°	951.8	953.3	954.8	955.5	955.3	955.1	954.9	954.6
10°	942.8	944.2	945.6	946.1	945.7	945.4	945.0	944.7
12.5°	931.9	933.4	934.9	935.4	934.9	934.4	934.0	933.5
15°	911.0	912.0	913.0	913.3	912.8	912.3	911.7	911.2
17.5°	887.2	887.8	888.5	888.6	888.3	887.9	887.6	887.3
20°	869.5	870.0	870.5	870.6	870.2	869.9	869.6	869.2
22.5°	851.0	851.9	852.9	853.0	852.4	851.8	851.2	850.5
25°	820.5	820.7	820.9	820.6	819.9	819.2	818.5	817.8
27.5°	786.4	785.9	785.5	784.9	784.0	783.2	782.3	781.4
30°	762.8	762.1	761.4	760.6	759.7	758.9	758.0	757.1
32.5°	738.8	738.0	737.2	736.3	735.5	734.6	733.7	732.9
35°	701.0	699.8	698.6	697.6	696.7	695.8	695.0	694.1
37.5°	661.5	660.1	658.8	657.6	656.5	655.3	654.2	653.0
40°	633.9	632.1	630.4	629.1	628.2	627.4	626.5	625.6
42.5°	607.2	605.1	603.1	601.8	601.3	600.7	600.1	599.5
45°	565.8	563.9	562.0	560.8	560.3	559.8	559.2	558.7
47.5°	525.8	523.6	521.5	519.8	518.5	517.1	515.8	514.5
50°	497.8	495.4	493.0	491.3	490.2	489.2	488.2	487.1
52.5°	469.1	467.0	464.9	463.1	461.8	460.5	459.2	457.9
55°	427.0	424.9	422.8	421.2	420.2	419.2	418.1	417.1
57.5°	384.7	382.7	380.7	379.2	378.2	377.2	376.2	375.2
60°	355.6	354.1	352.5	351.3	350.4	349.6	348.7	347.8
62.5°	327.3	325.8	324.4	323.3	322.4	321.6	320.7	319.8
65°	286.0	284.3	282.6	281.3	280.4	279.5	278.7	277.8
67.5°	243.5	241.9	240.2	239.2	239.0	238.8	238.5	238.3
70°	216.7	215.3	213.9	213.0	212.4	211.9	211.4	210.9
72.5°	189.8	188.7	187.6	186.8	186.3	185.8	185.3	184.7
75°	151.1	150.4	149.8	149.3	149.1	149.0	148.8	148.6
77.5°	114.4	114.2	114.0	113.7	113.2	112.8	112.3	111.9
80°	91.1	90.8	90.4	90.2	90.0	89.8	89.7	89.5
82.5°	70.2	70.0	69.8	69.6	69.5	69.3	69.1	68.9
85°	40.5	40.5	40.5	40.4	40.2	40.0	39.9	39.7
87.5°	18.8	19.0	19.2	19.4	19.4	19.5	19.6	19.6
90°	19.3	20.3	21.4	22.1	22.4	22.8	23.1	23.5
92.5°	32.2	32.8	33.5	33.9	34.1	34.3	34.5	34.7
95°	60.5	61.0	61.5	61.8	61.8	61.8	61.8	61.8
97.5°	95.2	95.8	96.5	96.8	96.8	96.8	96.8	96.8
100°	120.3	120.7	121.0	121.2	121.2	121.2	121.2	121.2
102.5°	146.9	147.3	147.8	148.1	148.3	148.4	148.6	148.7
105°	187.1	187.6	188.1	188.7	189.2	189.7	190.2	190.8
107.5°	230.7	231.1	231.6	231.9	231.8	231.8	231.8	231.7
110°	259.6	259.3	258.9	259.0	259.6	260.1	260.6	261.1



TEST NUMBER: P332560

CATALOG NUMBER: S124DIP-S575D810U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	290.8	290.8	290.7	290.7	290.8	290.9	291.0	291.1
115°	338.9	338.8	338.6	338.4	338.3	338.1	337.9	337.7
117.5°	385.2	384.6	384.0	383.5	383.2	382.8	382.5	382.1
120°	416.5	415.6	414.8	414.5	414.9	415.2	415.6	415.9
122.5°	448.3	447.8	447.2	446.6	445.9	445.3	444.7	444.1
125°	495.0	494.6	494.3	493.9	493.6	493.2	492.9	492.5
127.5°	539.5	539.2	538.8	538.5	538.2	538.0	537.7	537.4
130°	570.8	570.4	570.1	569.6	568.9	568.2	567.5	566.8
132.5°	600.2	599.8	599.5	599.2	598.9	598.6	598.3	598.1
135°	644.3	643.9	643.6	643.1	642.6	642.1	641.6	641.1
137.5°	686.9	686.5	686.0	685.8	685.9	686.0	686.1	686.3
140°	715.0	714.8	714.6	714.5	714.3	714.1	713.9	713.8
142.5°	741.5	741.5	741.5	741.4	741.4	741.4	741.3	741.3
145°	781.4	781.3	781.1	780.7	780.2	779.7	779.2	778.7
147.5°	817.6	817.5	817.3	817.2	817.0	816.8	816.7	816.5
150°	840.4	840.4	840.4	840.3	840.2	840.0	839.8	839.6
152.5°	861.9	862.3	862.7	862.7	862.3	861.8	861.4	860.9
155°	891.8	892.5	893.2	893.2	892.5	891.8	891.1	890.5
157.5°	918.2	918.8	919.3	919.2	918.7	918.1	917.5	916.9
160°	934.5	935.0	935.5	935.4	934.5	933.6	932.8	931.9
162.5°	949.1	950.0	951.0	951.0	950.1	949.3	948.4	947.5
165°	968.4	969.4	970.5	970.6	969.9	969.2	968.5	967.9
167.5°	984.6	985.7	986.7	986.7	985.6	984.5	983.5	982.4
170°	993.4	994.4	995.5	995.4	994.2	993.0	991.7	990.5
172.5°	999.9	1001.1	1002.3	1002.3	1001.1	999.8	998.6	997.4
175°	1007.0	1008.2	1009.5	1009.5	1008.2	1007.0	1005.8	1004.6
177.5°	1010.9	1011.9	1012.9	1012.8	1011.7	1010.6	1009.5	1008.3
180°	1010.8	1010.8	1010.8	1010.8	1010.8	1010.8	1010.8	1010.8

(END OF REPORT)