

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332984

Luminaire Tested: **S124RDIP-S1020D1205U835-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332984
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIP-S1020D1205U835-4F0-1E-UDD-F4
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1205 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8476.7 lumens
Efficiency: N/A
Efficacy: 129.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 65.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332984

CATALOG NUMBER: S124RDIP-S1020D1205U835-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P332984

CATALOG NUMBER: S124RDIP-S1020D1205U835-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	55	55	55	49																												
1	98	94	90	86	90	87	83	80	73	71	69	61	59	58	49	48	47	42																												
2	89	82	76	71	82	76	71	66	64	61	57	54	51	49	44	42	40	36																												
3	82	72	65	59	75	67	61	56	57	52	48	48	44	41	39	37	35	30																												
4	75	64	56	50	69	60	53	47	51	46	41	43	39	36	35	32	30	26																												
5	69	57	49	43	63	53	46	41	46	40	36	38	34	31	32	29	26	23																												
6	63	51	43	38	58	48	41	36	41	36	31	35	30	27	29	26	23	20																												
7	59	47	39	33	54	43	36	31	37	32	28	32	27	24	26	23	21	18																												
8	54	42	35	29	50	39	33	28	34	29	25	29	25	22	24	21	19	16																												
9	51	39	31	26	47	36	29	25	31	26	22	27	23	19	22	19	17	15																												
10	47	35	28	24	44	33	27	22	29	24	20	25	21	18	21	18	15	13																												

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14577	14577	14577
5°	14610	14431	14521
10°	14519	14258	14258
15°	14352	13959	13855
20°	14123	13564	13315
25°	13831	13104	12772
30°	13546	12618	12089
35°	13231	12113	11404
40°	12852	11540	10666
45°	12501	10970	9913
50°	12103	10315	9117
55°	11676	9633	8251
60°	11207	8885	7367
65°	10776	7950	6497
70°	10150	6918	5516
75°	9357	5736	4485
80°	8164	4370	4114
85°	6919	3974	3714



TEST NUMBER: P332984

CATALOG NUMBER: S124RDIP-S1020D1205U835-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	169.6	2.0
10°-20°	473.0	5.6
20°-30°	683.0	8.1
30°-40°	774.2	9.1
40°-50°	747.6	8.8
50°-60°	621.7	7.3
60°-70°	429.3	5.1
70°-80°	217.6	2.6
80°-90°	59.1	0.7
90°-100°	427.2	5.0
100°-110°	889.1	10.5
110°-120°	796.4	9.4
120°-130°	669.9	7.9
130°-140°	558.5	6.6
140°-150°	426.7	5.0
150°-160°	299.9	3.5
160°-170°	176.4	2.1
170°-180°	57.4	0.7
0°-30°	1325.6	15.6
0°-40°	2099.9	24.8
0°-60°	3469.2	40.9
0°-90°	4175.1	49.3
90°-120°	2112.7	24.9
90°-150°	3767.8	44.4
90°-180°	4302.0	50.8
0°-180°	8476.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1806	1806	1806	1806	1806	
5°	1803	1797	1781	1794	1792	171
15°	1717	1704	1670	1667	1658	484
25°	1553	1526	1471	1448	1434	715
35°	1342	1297	1229	1183	1157	839
45°	1095	1042	961	896	868	844
55°	830	772	684	615	586	742
65°	564	503	416	359	340	557
75°	300	248	184	153	144	317
85°	75	48	43	40	40	84
90°	1	9	21	23	24	6
95°	38	121	947	469	284	43
105°	136	197	762	1641	1635	145
115°	239	300	680	1306	1570	237
125°	334	396	676	1111	1253	297
135°	396	472	670	987	1120	306
145°	457	523	667	832	914	287
155°	519	561	648	734	766	239
165°	566	583	622	658	668	160
175°	590	592	596	604	602	56
180°	592	592	592	592	592	



TEST NUMBER: P332984

CATALOG NUMBER: S124RDIP-S1020D1205U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1805.7	1805.7	1805.7	1805.7	1805.7	1805.7	1805.7	1805.7	1805.7	1805.7	1805.7
2.5°	1810.1	1809.1	1808.1	1807.2	1806.2	1804.3	1801.6	1798.9	1796.2	1793.5	1796.2
5°	1802.9	1801.7	1800.5	1799.2	1798.0	1795.5	1791.9	1788.2	1784.5	1780.8	1783.9
7.5°	1786.6	1785.3	1784.0	1782.7	1781.4	1778.4	1773.6	1768.8	1764.0	1759.2	1761.2
10°	1771.1	1769.6	1768.0	1766.5	1765.0	1761.4	1755.9	1750.4	1744.8	1739.3	1740.5
12.5°	1751.2	1749.4	1747.6	1745.9	1744.1	1739.9	1733.4	1726.9	1720.4	1713.9	1714.6
15°	1717.2	1714.4	1711.7	1708.9	1706.1	1700.9	1693.2	1685.5	1677.9	1670.2	1669.6
17.5°	1676.0	1672.0	1668.0	1664.0	1660.0	1653.4	1644.2	1635.0	1625.8	1616.5	1614.8
20°	1643.9	1639.9	1635.9	1631.9	1627.9	1620.7	1610.3	1599.8	1589.4	1578.9	1576.5
22.5°	1608.5	1604.0	1599.5	1595.1	1590.6	1582.7	1571.6	1560.4	1549.2	1538.0	1534.3
25°	1552.7	1547.1	1541.6	1536.1	1530.5	1521.5	1508.9	1496.3	1483.7	1471.1	1465.9
27.5°	1494.0	1487.1	1480.2	1473.2	1466.3	1456.1	1442.6	1429.2	1415.7	1402.2	1395.8
30°	1453.1	1445.4	1437.8	1430.1	1422.4	1411.3	1396.9	1382.4	1368.0	1353.6	1345.9
32.5°	1410.0	1401.3	1392.6	1384.0	1375.3	1363.5	1348.6	1333.7	1318.7	1303.8	1294.9
35°	1342.5	1332.7	1322.8	1313.0	1303.2	1290.6	1275.2	1259.9	1244.5	1229.1	1218.7
37.5°	1270.3	1260.2	1250.1	1239.9	1229.8	1216.2	1199.2	1182.2	1165.1	1148.1	1136.4
40°	1219.5	1209.3	1199.2	1189.0	1178.9	1165.1	1147.6	1130.0	1112.5	1095.0	1082.1
42.5°	1170.8	1160.2	1149.5	1138.9	1128.3	1113.8	1095.6	1077.3	1059.1	1040.8	1027.7
45°	1095.0	1083.7	1072.3	1060.9	1049.5	1034.6	1016.2	997.8	979.3	960.9	945.9
47.5°	1016.8	1005.0	993.3	981.6	969.8	954.4	935.2	916.0	896.8	877.7	862.1
50°	963.7	951.7	939.7	927.7	915.7	899.9	880.3	860.6	840.9	821.3	805.9
52.5°	909.5	897.7	886.0	874.3	862.5	846.6	826.4	806.3	786.1	766.0	750.4
55°	829.6	817.3	805.0	792.7	780.4	764.3	744.3	724.3	704.4	684.4	668.4
57.5°	750.5	737.7	724.9	712.1	699.4	683.1	663.5	643.8	624.1	604.5	588.3
60°	694.1	681.8	669.5	657.2	644.9	628.9	609.3	589.6	569.9	550.3	534.3
62.5°	643.2	630.4	617.6	604.8	592.1	575.6	555.4	535.3	515.1	495.0	480.2
65°	564.1	550.9	537.7	524.5	511.3	494.8	475.2	455.5	435.8	416.2	403.0
67.5°	482.0	469.3	456.7	444.0	431.3	415.9	397.6	379.4	361.1	342.9	331.5
70°	430.0	417.1	404.2	391.3	378.4	363.2	345.7	328.1	310.6	293.1	283.0
72.5°	374.7	363.0	351.3	339.7	328.0	313.9	297.4	280.8	264.3	247.8	239.1
75°	300.0	288.7	277.3	265.9	254.6	241.6	227.2	212.8	198.3	183.9	176.8
77.5°	224.3	214.6	205.0	195.3	185.7	175.0	163.3	151.7	140.0	128.3	124.2
80°	175.6	166.7	157.8	148.9	140.0	130.9	121.7	112.5	103.2	94.0	93.1
82.5°	133.6	125.4	117.2	109.0	100.9	94.1	88.9	83.6	78.3	73.0	72.3
85°	74.7	68.5	62.4	56.2	50.1	46.5	45.6	44.7	43.8	42.9	42.2
87.5°	25.7	24.2	22.9	21.2	19.4	18.3	19.5	19.2	19.4	19.7	19.2
90°	1.2	3.5	7.0	8.1	9.3	9.3	16.3	16.3	18.6	20.9	19.8
92.5°	13.2	19.3	30.2	44.4	61.4	85.5	144.6	234.7	322.6	368.6	307.0
95°	38.3	41.8	53.5	68.6	96.4	145.3	246.3	436.9	714.6	947.0	973.8
97.5°	68.8	68.8	78.8	92.7	116.7	157.6	235.4	392.8	668.8	997.5	1223.4
100°	88.3	88.3	96.4	110.4	132.5	169.7	238.2	369.5	606.6	934.2	1231.7
102.5°	106.9	108.8	116.0	129.0	150.1	185.5	247.5	363.0	564.7	855.2	1162.0
105°	136.0	139.4	145.3	159.2	180.1	213.8	269.6	366.0	528.7	762.3	1035.3
107.5°	168.0	170.3	176.2	191.0	211.0	244.3	295.4	383.2	522.2	710.2	933.1
110°	189.4	191.7	197.5	211.5	232.4	263.8	314.9	396.2	524.1	692.6	882.0



TEST NUMBER: P332984

CATALOG NUMBER: S124RDIP-S1020D1205U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	209.9	212.2	218.9	231.9	252.9	284.2	333.5	410.2	529.6	684.2	853.1
115°	239.4	242.9	251.0	262.6	284.7	316.1	362.5	432.3	540.3	679.8	826.2
117.5°	270.0	273.3	280.5	293.3	314.0	346.5	390.7	454.8	551.7	678.6	814.1
120°	290.5	292.8	301.0	313.7	333.5	366.0	410.2	470.6	560.1	678.6	807.6
122.5°	309.1	311.4	319.6	331.4	353.0	384.6	428.8	485.5	568.5	677.7	800.2
125°	333.5	338.1	345.1	357.9	380.0	412.5	454.3	507.8	581.0	676.3	787.8
127.5°	355.1	358.8	367.2	381.8	404.8	437.6	478.0	527.1	591.0	673.7	771.3
130°	367.2	371.8	381.1	398.6	420.6	454.3	493.9	539.2	598.4	672.8	761.1
132.5°	379.3	383.0	395.1	411.6	435.5	467.4	506.9	551.3	604.9	671.9	751.8
135°	396.2	400.9	412.5	432.3	456.7	486.9	525.2	567.1	614.7	670.5	737.9
137.5°	413.2	417.6	430.4	449.2	474.6	503.4	539.2	578.2	620.5	670.2	725.8
140°	425.3	428.8	441.6	461.3	485.7	513.6	548.5	585.6	625.2	669.3	719.3
142.5°	438.3	441.8	453.6	472.5	495.9	522.9	556.8	591.2	628.9	669.3	713.7
145°	456.7	460.2	471.8	488.0	510.1	535.7	565.9	597.3	631.0	667.0	704.2
147.5°	477.3	478.5	488.7	505.5	523.8	546.8	575.2	602.6	632.1	662.8	695.6
150°	490.4	491.5	500.8	514.8	532.2	554.3	579.8	605.4	632.1	660.0	689.1
152.5°	502.4	502.7	512.0	525.0	540.6	560.8	583.6	607.3	630.3	655.4	681.6
155°	519.4	520.6	527.5	539.2	552.0	569.4	589.1	608.9	627.5	648.4	670.5
157.5°	535.9	535.9	542.4	551.5	562.6	576.4	593.1	608.9	624.5	641.2	659.1
160°	546.1	546.1	550.8	558.9	568.2	581.0	594.9	608.9	621.7	635.6	650.7
162.5°	555.4	554.5	558.2	565.4	573.8	583.8	596.8	608.9	618.9	630.0	643.3
165°	565.9	565.9	568.2	574.0	579.8	586.8	597.3	606.6	613.5	621.7	631.0
167.5°	576.4	575.2	576.4	580.8	584.0	589.4	597.0	603.8	608.0	613.3	619.8
170°	581.0	579.8	581.0	584.5	586.8	590.3	596.1	601.9	604.2	607.7	612.4
172.5°	585.6	584.5	584.7	587.3	588.7	591.2	595.2	600.1	600.5	602.1	605.9
175°	590.3	589.1	589.1	590.3	591.5	591.5	593.8	597.3	596.1	596.1	598.4
177.5°	592.4	591.5	590.5	591.5	591.5	591.5	592.4	594.2	592.4	592.4	593.3
180°	591.5	591.5	591.5	591.5	591.5	591.5	591.5	591.5	591.5	591.5	591.5



TEST NUMBER: P332984

CATALOG NUMBER: S124RDIP-S1020D1205U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1805.7	1805.7	1805.7	1805.7	1805.7	1805.7	1805.7	1805.7
2.5°	1798.9	1801.6	1804.3	1805.6	1805.3	1805.1	1804.8	1804.6
5°	1786.9	1790.0	1793.1	1794.3	1793.7	1793.1	1792.5	1791.9
7.5°	1763.2	1765.1	1767.1	1767.6	1766.6	1765.6	1764.6	1763.6
10°	1741.8	1743.0	1744.2	1744.2	1743.0	1741.8	1740.5	1739.3
12.5°	1715.3	1716.1	1716.8	1716.3	1714.6	1712.9	1711.2	1709.5
15°	1669.0	1668.3	1667.7	1666.3	1664.2	1662.0	1659.9	1657.7
17.5°	1613.1	1611.4	1609.7	1607.2	1603.9	1600.7	1597.4	1594.1
20°	1574.0	1571.6	1569.1	1565.9	1561.9	1557.9	1553.9	1549.9
22.5°	1530.6	1526.9	1523.3	1519.8	1516.5	1513.3	1510.0	1506.8
25°	1460.6	1455.4	1450.2	1446.0	1443.0	1439.9	1436.8	1433.8
27.5°	1389.3	1382.9	1376.4	1371.0	1366.6	1362.1	1357.7	1353.3
30°	1338.2	1330.5	1322.8	1316.5	1311.6	1306.7	1301.8	1296.9
32.5°	1286.0	1277.1	1268.2	1261.4	1256.7	1252.0	1247.4	1242.7
35°	1208.2	1197.8	1187.3	1179.4	1173.8	1168.3	1162.8	1157.2
37.5°	1124.8	1113.1	1101.4	1092.8	1087.3	1081.7	1076.2	1070.7
40°	1069.2	1056.3	1043.4	1034.2	1028.7	1023.1	1017.6	1012.1
42.5°	1014.5	1001.4	988.2	978.8	973.0	967.2	961.4	955.7
45°	930.8	915.7	900.7	890.4	884.9	879.3	873.8	868.3
47.5°	846.5	830.9	815.2	804.4	798.3	792.2	786.1	780.1
50°	790.5	775.2	759.8	749.2	743.4	737.5	731.7	725.9
52.5°	734.7	719.1	703.5	692.7	686.6	680.5	674.4	668.4
55°	652.4	636.5	620.5	609.6	603.7	597.9	592.1	586.2
57.5°	572.0	555.8	539.6	529.3	524.8	520.4	516.0	511.6
60°	518.3	502.3	486.4	475.9	471.0	466.1	461.2	456.3
62.5°	465.5	450.7	436.0	426.6	422.7	418.8	414.8	410.9
65°	389.7	376.5	363.3	354.9	351.2	347.5	343.8	340.1
67.5°	320.1	308.8	297.4	289.7	285.6	281.6	277.5	273.5
70°	272.8	262.7	252.6	245.9	242.9	239.8	236.7	233.7
72.5°	230.4	221.8	213.1	207.4	204.5	201.7	198.9	196.1
75°	169.8	162.7	155.6	151.2	149.3	147.5	145.6	143.8
77.5°	120.1	116.0	111.8	109.5	108.9	108.4	107.8	107.3
80°	92.2	91.3	90.3	89.7	89.4	89.1	88.8	88.5
82.5°	71.6	71.0	70.3	69.8	69.5	69.2	68.9	68.6
85°	41.6	41.0	40.4	40.1	40.1	40.1	40.1	40.1
87.5°	19.2	19.2	19.1	19.1	19.6	20.1	20.1	20.4
90°	20.9	22.1	23.2	23.2	24.4	25.6	24.4	24.4
92.5°	228.2	171.7	136.7	113.4	99.7	93.4	89.5	89.5
95°	861.0	680.9	525.2	412.5	355.6	319.6	298.6	283.5
97.5°	1272.2	1205.2	1091.6	970.3	886.8	816.9	782.0	757.9
100°	1401.4	1424.6	1367.7	1281.7	1180.6	1109.7	1074.9	1065.6
102.5°	1394.9	1510.1	1526.6	1490.8	1428.8	1377.4	1340.7	1333.3
105°	1301.4	1502.5	1617.5	1665.1	1667.5	1658.2	1641.9	1634.9
107.5°	1168.7	1382.8	1544.8	1648.4	1705.8	1732.3	1743.9	1747.0
110°	1088.8	1289.8	1458.3	1586.1	1668.6	1717.4	1738.4	1748.8



TEST NUMBER: P332984

CATALOG NUMBER: S124RDIP-S1020D1205U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	1030.2	1208.0	1367.2	1495.0	1588.7	1647.7	1677.0	1694.0
115°	971.4	1114.4	1250.3	1361.9	1453.7	1523.4	1560.6	1569.9
117.5°	942.6	1060.9	1167.8	1262.4	1340.7	1399.3	1436.9	1444.1
120°	929.6	1037.7	1130.6	1213.1	1279.4	1330.5	1360.7	1373.5
122.5°	918.4	1022.8	1107.4	1179.7	1235.7	1279.4	1304.9	1317.7
125°	899.4	999.3	1079.5	1143.4	1189.9	1223.6	1245.7	1252.6
127.5°	876.1	971.7	1051.6	1112.3	1159.0	1189.0	1207.6	1214.5
130°	857.6	949.4	1028.4	1090.0	1137.6	1166.6	1185.2	1192.2
132.5°	838.0	924.3	1001.4	1063.0	1109.7	1142.5	1160.1	1167.1
135°	811.1	886.6	957.5	1015.6	1062.1	1094.6	1113.2	1120.2
137.5°	786.7	850.6	910.3	962.8	1006.3	1038.4	1053.7	1062.1
140°	772.7	827.3	879.6	928.4	969.1	994.7	1010.9	1020.2
142.5°	759.7	807.8	852.7	895.0	931.0	954.7	969.1	975.6
145°	741.4	780.9	815.7	848.3	877.3	897.1	908.7	914.5
147.5°	726.3	757.6	785.5	811.1	832.5	849.4	858.3	860.3
150°	717.0	743.7	766.9	787.8	806.4	821.5	828.5	829.7
152.5°	706.7	729.7	751.1	768.3	784.1	796.4	800.6	801.8
155°	691.4	710.0	727.4	741.4	753.0	762.3	765.8	765.8
157.5°	674.9	690.5	705.1	716.3	725.1	732.1	734.2	734.2
160°	664.7	677.4	690.2	699.5	706.5	713.5	714.6	714.6
162.5°	654.4	665.4	675.4	683.7	688.8	695.8	697.0	696.0
165°	640.3	647.2	655.4	661.2	665.8	670.5	669.3	668.2
167.5°	626.6	631.9	638.4	641.9	644.2	647.2	647.0	646.1
170°	618.2	621.7	626.3	629.8	632.1	633.3	632.1	632.1
172.5°	610.7	613.3	616.1	618.6	620.0	621.2	620.0	618.2
175°	600.8	601.9	604.2	604.2	604.2	606.6	604.2	601.9
177.5°	594.2	595.2	595.2	596.1	595.2	596.1	594.2	592.4
180°	591.5	591.5	591.5	591.5	591.5	591.5	591.5	591.5

(END OF REPORT)